

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832105

Luminaire Tested: S123RDIP-S340D365U930-4F0-1E-UDD-G1

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832105
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D365U930-4F0-1E-UDD-G1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2217.9 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 22.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832105

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-G1

Luminous Intensity Polar Plot





TEST NUMBER: P832105

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-G1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54	54	54
1	100	96	92	89	92	89	86	83	76	74	72	65	63	62	54	53	52	47	47	47
2	91	85	79	74	85	79	74	70	68	64	61	58	55	53	49	47	45	41	41	41
3	84	75	68	63	78	70	64	59	61	56	53	52	49	46	44	42	40	36	36	36
4	77	67	60	54	72	63	56	51	55	50	46	47	44	40	40	38	35	32	32	32
5	72	61	53	47	66	57	50	45	50	44	40	43	39	36	37	34	31	28	28	28
6	66	55	47	42	62	52	45	40	45	40	36	39	35	32	34	31	28	26	26	26
7	62	50	42	37	57	47	40	35	41	36	32	36	32	29	31	28	26	23	23	23
8	58	46	38	33	54	43	37	32	38	33	29	34	29	26	29	26	24	21	21	21
9	54	42	35	30	50	40	33	29	35	30	26	31	27	24	27	24	22	20	20	20
10	51	39	32	27	47	37	31	26	33	28	24	29	25	22	26	22	20	18	18	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	9749	9749	9749	9749	9749
5°	11577	11207	9811	7931	7363
10°	10488	11384	9762	6355	5451
15°	7221	9760	9658	5194	4313
20°	5024	7514	9465	4379	3790
25°	3828	5727	9183	3892	3493
30°	3332	4579	8830	3614	3235
35°	3059	3862	8330	3380	3001
40°	2792	3450	7676	3149	2786
45°	2521	3154	6970	2930	2573
50°	2289	2910	6137	2718	2308
55°	2070	2672	5339	2509	1980
60°	1856	2430	4637	2278	1871
65°	1712	2157	3991	2048	1768
70°	1391	1863	3484	1854	1438
75°	1219	1485	2949	1535	1268
80°	1103	1252	2417	1289	1196
85°	1013	1099	1840	1173	1099

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 7354 cd/sqm



TEST NUMBER: P832105

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-G1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.6	3.7
10°-20°	191.0	8.6
20°-30°	219.2	9.9
30°-40°	216.0	9.7
40°-50°	190.5	8.6
50°-60°	146.6	6.6
60°-70°	96.4	4.3
70°-80°	46.8	2.1
80°-90°	12.6	0.6
90°-100°	23.6	1.1
100°-110°	71.5	3.2
110°-120°	121.7	5.5
120°-130°	160.0	7.2
130°-140°	179.9	8.1
140°-150°	176.9	8.0
150°-160°	148.9	6.7
160°-170°	99.1	4.5
170°-180°	34.7	1.6
0°-30°	492.8	22.2
0°-40°	708.8	32.0
0°-60°	1045.9	47.2
0°-90°	1201.7	54.2
90°-120°	216.7	9.8
90°-150°	733.5	33.1
90°-180°	1016.0	45.8
0°-180°	2217.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	906	906	906	906	906	
5°	1071	1037	908	734	681	98
15°	648	876	867	466	387	183
25°	322	482	773	328	294	152
35°	233	294	634	257	228	145
45°	166	207	458	192	169	129
55°	110	142	284	134	106	99
65°	67	85	157	80	69	66
75°	29	36	71	37	30	32
85°	8	9	15	10	9	9
90°	9	7	0	7	9	5
95°	22	21	17	21	22	23
105°	69	68	65	68	69	73
115°	123	123	122	123	123	122
125°	177	180	179	180	177	158
135°	232	234	232	234	232	179
145°	282	284	282	284	282	176
155°	322	323	323	323	322	149
165°	351	351	352	351	351	99
175°	364	365	366	365	364	35
180°	367	367	367	367	367	



TEST NUMBER: P832105

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7
2.5°	1003.8	1000.6	997.5	996.5	995.6	992.6	989.7	983.0	976.3	969.4	962.6
5°	1071.4	1071.7	1072.1	1071.2	1070.2	1066.3	1062.4	1054.3	1046.1	1037.2	1028.3
7.5°	1050.6	1056.5	1062.4	1063.6	1064.7	1067.6	1070.6	1068.8	1066.9	1063.6	1060.2
10°	959.6	959.2	958.8	965.5	972.2	992.1	1011.9	1022.2	1032.4	1041.5	1050.6
12.5°	811.0	811.6	812.2	834.1	856.0	874.7	893.5	919.5	945.5	973.5	1001.5
15°	648.0	657.1	666.2	685.7	705.2	733.4	761.7	796.6	831.5	875.8	920.2
17.5°	532.2	536.1	540.0	558.7	577.5	604.2	630.9	670.5	710.0	767.2	824.4
20°	438.6	442.1	445.6	459.2	472.7	498.4	524.0	561.7	599.4	656.0	712.6
22.5°	366.2	373.0	379.9	389.0	398.1	416.7	435.2	473.7	512.1	563.7	615.3
25°	322.3	325.5	328.7	336.4	344.2	362.1	379.9	405.3	430.8	482.2	533.6
27.5°	292.6	293.6	294.5	300.2	306.0	317.5	329.0	352.6	376.2	418.5	460.9
30°	268.1	269.8	271.5	275.9	280.4	288.7	297.1	313.8	330.5	368.4	406.3
32.5°	249.2	250.1	251.0	254.8	258.5	264.6	270.7	283.9	297.1	326.1	355.0
35°	232.8	233.0	233.2	236.0	238.8	244.7	250.7	261.6	272.6	293.9	315.3
37.5°	214.3	215.6	216.9	218.9	221.0	226.2	231.4	240.3	249.2	266.8	284.5
40°	198.7	199.8	200.9	203.3	205.7	209.8	213.9	222.1	230.2	245.5	260.7
42.5°	183.1	183.8	184.6	187.0	189.4	194.4	199.4	205.9	212.4	225.0	237.7
45°	165.6	167.5	169.3	171.9	174.5	178.8	183.1	189.8	196.4	207.2	218.0
47.5°	151.1	152.1	153.0	155.2	157.5	162.7	167.9	173.8	179.7	189.8	199.8
50°	136.7	137.0	137.4	139.4	141.5	146.1	150.8	157.6	164.5	173.8	183.1
52.5°	122.9	123.8	124.8	126.8	128.9	132.0	135.2	142.2	149.3	158.4	167.5
55°	110.3	110.8	111.4	112.9	114.4	118.1	121.8	127.9	134.1	142.4	150.8
57.5°	98.4	99.2	99.9	101.0	102.1	105.5	108.8	114.2	119.6	127.9	136.3
60°	86.2	87.1	88.0	89.3	90.6	93.2	95.8	100.6	105.5	112.9	120.3
62.5°	77.2	77.4	77.6	78.7	79.8	81.7	83.6	87.5	91.4	98.8	106.2
65°	67.2	67.8	68.3	68.9	69.4	70.9	72.4	75.8	79.1	84.7	90.2
67.5°	56.8	57.4	57.9	58.9	59.8	61.1	62.4	64.6	66.8	72.0	77.2
70°	44.2	44.2	44.2	45.7	47.2	49.4	51.6	53.3	55.0	59.2	63.5
72.5°	36.0	36.2	36.4	36.6	36.8	38.1	39.4	42.1	44.9	47.5	50.1
75°	29.3	29.5	29.7	29.9	30.1	30.5	30.8	31.8	32.7	35.7	38.6
77.5°	23.4	23.6	23.8	24.0	24.1	24.5	24.9	25.3	25.6	26.7	27.9
80°	17.8	18.0	18.2	18.4	18.6	18.8	18.9	19.3	19.7	20.2	20.8
82.5°	13.0	13.0	13.0	13.0	13.0	13.4	13.7	13.7	13.7	14.1	14.5
85°	8.2	8.2	8.2	8.4	8.5	8.5	8.5	8.7	8.9	8.9	8.9
87.5°	3.7	3.5	3.3	3.5	3.7	3.7	3.7	3.9	4.1	4.1	4.1
90°	8.6	8.5	8.4	8.3	8.1	7.9	7.7	7.4	7.2	6.9	6.1
92.5°	12.4	12.5	12.6	12.8	12.9	12.9	12.7	12.5	12.3	12.1	11.7
95°	22.5	22.5	22.5	22.5	22.5	22.3	22.1	21.8	21.6	21.3	20.8
97.5°	32.3	32.3	32.4	32.5	32.5	32.4	32.1	31.8	31.4	31.1	30.7
100°	43.8	43.7	43.5	43.4	43.3	43.1	42.9	42.7	42.5	42.4	42.0
102.5°	55.6	55.7	55.7	55.8	55.9	55.8	55.6	55.4	55.2	55.0	54.6
105°	68.6	68.4	68.3	68.2	68.1	68.0	68.0	68.0	68.0	68.0	67.4
107.5°	81.8	81.9	82.0	82.0	82.1	82.0	81.8	81.6	81.4	81.2	81.0
110°	95.4	95.5	95.6	95.8	95.9	95.8	95.6	95.3	95.0	94.8	94.7



TEST NUMBER: P832105

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	109.8	109.8	109.8	109.8	109.8	109.6	109.3	109.0	108.7	108.3	108.3
115°	122.7	122.8	122.9	122.9	123.0	123.0	122.9	122.9	122.8	122.7	122.9
117.5°	136.0	136.2	136.4	136.6	136.8	136.9	136.9	136.9	136.9	136.9	137.0
120°	150.1	150.2	150.4	150.5	150.6	150.7	150.8	150.8	150.9	151.0	151.3
122.5°	163.7	163.8	164.0	164.2	164.4	164.6	164.8	165.0	165.2	165.4	165.5
125°	177.2	177.4	177.7	178.0	178.2	178.5	178.7	179.0	179.2	179.5	179.6
127.5°	190.7	191.0	191.2	191.5	191.8	192.1	192.5	192.8	193.2	193.6	193.7
130°	204.0	204.4	204.9	205.3	205.8	206.1	206.4	206.6	206.9	207.2	207.3
132.5°	217.8	218.1	218.5	218.8	219.1	219.4	219.7	220.1	220.4	220.7	220.8
135°	232.2	232.4	232.5	232.6	232.7	232.9	233.2	233.4	233.7	234.0	234.0
137.5°	244.9	245.1	245.3	245.5	245.7	245.9	246.2	246.6	246.9	247.2	247.0
140°	257.3	257.7	258.2	258.6	259.1	259.3	259.4	259.5	259.5	259.6	259.5
142.5°	270.0	270.3	270.6	270.9	271.2	271.4	271.5	271.6	271.6	271.7	271.6
145°	282.1	282.3	282.6	282.8	283.1	283.3	283.3	283.4	283.4	283.5	283.3
147.5°	293.0	293.4	293.8	294.2	294.6	294.7	294.7	294.7	294.7	294.7	294.6
150°	303.4	303.8	304.2	304.5	304.9	305.1	305.1	305.1	305.1	305.1	305.0
152.5°	313.5	313.8	314.1	314.4	314.8	314.9	314.7	314.6	314.5	314.3	314.3
155°	322.4	322.9	323.3	323.7	324.2	324.3	324.0	323.8	323.5	323.3	323.2
157.5°	330.8	331.1	331.5	331.9	332.3	332.4	332.1	331.8	331.6	331.3	331.3
160°	338.8	339.1	339.3	339.6	339.9	339.8	339.5	339.2	338.9	338.5	338.5
162.5°	344.9	345.3	345.8	346.2	346.7	346.7	346.4	346.1	345.8	345.5	345.4
165°	350.6	351.1	351.5	352.0	352.4	352.5	352.1	351.7	351.3	350.9	350.9
167.5°	355.8	356.2	356.6	357.0	357.4	357.4	357.0	356.6	356.2	355.8	355.8
170°	359.6	360.0	360.5	360.9	361.4	361.4	360.9	360.5	360.0	359.6	359.6
172.5°	362.5	362.9	363.4	363.8	364.2	364.3	363.9	363.5	363.1	362.7	362.7
175°	364.5	364.9	365.4	365.8	366.3	366.3	365.9	365.5	365.1	364.8	364.8
177.5°	365.6	366.1	366.5	367.0	367.4	367.4	367.1	366.7	366.3	365.9	365.9
180°	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8



TEST NUMBER: P832105

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7
2.5°	961.6	960.7	951.8	942.9	934.1	925.4	918.9	912.4	901.5	890.5	883.6
5°	1021.2	1014.2	1000.1	986.0	964.8	943.6	925.8	908.0	885.3	862.7	843.7
7.5°	1054.5	1048.7	1031.6	1014.5	986.5	958.5	930.6	902.8	869.3	835.9	807.3
10°	1055.4	1060.2	1046.1	1032.0	1000.4	968.9	931.0	893.1	848.2	803.2	766.3
12.5°	1022.3	1043.1	1040.2	1037.2	1005.1	973.0	926.9	880.9	825.7	770.6	724.3
15°	960.5	1000.8	1012.7	1024.6	998.0	971.5	919.1	866.7	801.9	737.1	684.0
17.5°	880.9	937.3	968.7	1000.1	980.8	961.4	904.1	846.7	773.7	700.7	643.0
20°	786.5	860.4	909.6	958.8	951.8	944.7	885.5	826.3	747.5	668.8	606.2
22.5°	693.3	771.3	839.3	907.2	914.5	921.7	861.9	802.1	716.0	629.8	566.1
25°	612.9	692.2	773.2	854.1	870.5	886.8	830.0	773.2	683.9	594.5	531.2
27.5°	536.2	611.6	700.7	789.9	819.6	849.3	797.3	745.3	652.3	559.3	496.1
30°	473.7	541.1	632.0	723.0	764.4	805.8	758.1	710.4	618.1	525.8	464.0
32.5°	415.4	475.7	567.1	658.4	706.5	754.6	713.4	672.2	583.4	494.6	433.6
35°	369.3	423.3	508.6	593.8	647.6	701.5	667.7	633.9	547.2	460.5	402.7
37.5°	329.8	375.1	455.1	535.1	592.3	649.5	621.3	593.1	511.5	430.0	375.4
40°	297.1	333.5	407.9	482.4	538.5	594.5	570.4	546.3	473.3	400.3	349.3
42.5°	269.0	300.4	367.3	434.1	485.5	537.0	521.0	505.0	438.9	372.8	325.5
45°	244.4	270.7	329.6	388.4	435.8	483.1	470.5	457.9	400.9	343.9	300.4
47.5°	222.4	245.1	297.6	350.2	392.7	435.2	423.5	411.8	364.7	317.5	278.0
50°	202.4	221.7	265.5	309.3	347.6	385.8	376.2	366.5	327.5	288.5	254.4
52.5°	183.4	199.4	238.8	278.1	309.0	339.8	332.4	324.9	294.9	264.8	233.8
55°	165.4	180.1	213.3	246.6	272.9	299.3	291.9	284.5	261.1	237.7	210.4
57.5°	149.1	161.9	188.8	215.8	236.7	257.7	254.2	250.7	231.2	211.7	189.2
60°	131.8	143.3	166.6	189.8	206.7	223.6	219.5	215.4	201.5	187.5	168.2
62.5°	116.4	126.6	145.2	163.8	177.5	191.2	188.3	185.3	174.7	164.1	148.2
65°	100.3	110.3	125.3	140.4	151.1	161.9	159.3	156.7	148.7	140.7	127.9
67.5°	85.6	94.0	107.0	119.9	127.2	134.4	132.9	131.5	125.3	119.2	109.2
70°	70.7	78.0	88.8	99.5	104.5	109.6	110.1	110.7	105.1	99.5	92.1
72.5°	55.9	61.6	71.7	81.7	85.6	89.5	89.3	89.1	85.8	82.4	75.8
75°	42.9	47.2	55.0	62.8	66.1	69.4	70.2	70.9	67.8	64.6	60.9
77.5°	30.8	33.8	39.7	45.7	49.4	53.1	53.5	53.8	52.4	50.9	47.3
80°	21.7	22.7	26.4	30.1	34.0	37.9	38.4	39.0	37.5	36.0	33.8
82.5°	15.0	15.6	16.9	18.2	21.4	24.5	25.3	26.0	25.3	24.5	22.1
85°	9.1	9.3	9.8	10.4	11.9	13.4	14.1	14.9	14.5	14.1	12.8
87.5°	4.1	4.1	4.3	4.5	4.8	5.2	6.1	7.1	6.5	5.9	5.4
90°	5.3	4.4	3.6	2.8	2.2	1.6	0.9	0.3	0.9	1.6	2.2
92.5°	11.3	10.9	10.6	10.2	9.8	9.4	9.0	8.6	9.0	9.4	9.8
95°	20.3	19.8	19.3	18.8	18.3	17.9	17.4	17.0	17.4	17.9	18.3
97.5°	30.3	30.0	29.6	29.2	28.9	28.6	28.3	27.9	28.3	28.6	28.9
100°	41.7	41.4	41.1	40.7	40.3	40.0	39.6	39.2	39.6	40.0	40.3
102.5°	54.1	53.7	53.2	52.9	52.7	52.5	52.3	52.1	52.3	52.5	52.7
105°	66.8	66.3	65.7	65.3	65.2	65.1	65.0	64.8	65.0	65.1	65.2
107.5°	80.7	80.5	80.2	80.1	80.0	79.9	79.9	79.8	79.9	79.9	80.0
110°	94.5	94.4	94.3	94.2	94.0	93.9	93.8	93.6	93.8	93.9	94.0



TEST NUMBER: P832105

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	108.3	108.3	108.3	108.3	108.2	108.2	108.1	108.0	108.1	108.2	108.2
115°	123.0	123.1	123.3	123.2	123.0	122.8	122.6	122.5	122.6	122.8	123.0
117.5°	137.1	137.2	137.4	137.4	137.3	137.3	137.2	137.1	137.2	137.3	137.3
120°	151.6	151.9	152.3	152.2	151.8	151.5	151.1	150.7	151.1	151.5	151.8
122.5°	165.6	165.8	165.9	165.8	165.6	165.3	165.1	164.8	165.1	165.3	165.6
125°	179.8	179.9	180.0	180.0	179.8	179.6	179.4	179.2	179.4	179.6	179.8
127.5°	193.9	194.0	194.1	194.0	193.6	193.2	192.8	192.5	192.8	193.2	193.6
130°	207.5	207.7	207.9	207.8	207.3	206.7	206.2	205.7	206.2	206.7	207.3
132.5°	221.0	221.1	221.2	221.0	220.5	220.0	219.5	219.0	219.5	220.0	220.5
135°	234.1	234.1	234.2	234.0	233.7	233.3	232.9	232.5	232.9	233.3	233.7
137.5°	246.8	246.6	246.4	246.2	245.9	245.5	245.2	244.9	245.2	245.5	245.9
140°	259.5	259.4	259.3	259.1	258.8	258.5	258.2	257.9	258.2	258.5	258.8
142.5°	271.4	271.3	271.2	271.0	270.6	270.3	270.0	269.7	270.0	270.3	270.6
145°	283.1	282.9	282.7	282.6	282.5	282.3	282.2	282.1	282.2	282.3	282.5
147.5°	294.4	294.2	294.0	293.8	293.5	293.2	293.0	292.7	293.0	293.2	293.5
150°	304.9	304.7	304.6	304.5	304.3	304.2	304.1	304.0	304.1	304.2	304.3
152.5°	314.2	314.1	314.1	314.0	313.8	313.6	313.4	313.2	313.4	313.6	313.8
155°	323.1	323.1	323.0	323.0	323.0	323.0	323.0	323.0	323.0	323.0	323.0
157.5°	331.2	331.1	331.1	331.1	331.1	331.2	331.3	331.3	331.3	331.2	331.1
160°	338.5	338.5	338.5	338.6	338.7	338.9	339.0	339.1	339.0	338.9	338.7
162.5°	345.3	345.3	345.2	345.3	345.5	345.6	345.8	346.0	345.8	345.6	345.5
165°	350.9	350.9	350.9	351.0	351.2	351.4	351.6	351.8	351.6	351.4	351.2
167.5°	355.7	355.6	355.6	355.7	355.9	356.2	356.4	356.7	356.4	356.2	355.9
170°	359.6	359.6	359.6	359.7	360.0	360.2	360.5	360.7	360.5	360.2	360.0
172.5°	362.7	362.7	362.7	362.9	363.1	363.4	363.6	363.9	363.6	363.4	363.1
175°	364.8	364.8	364.8	364.9	365.1	365.4	365.7	365.9	365.7	365.4	365.1
177.5°	365.9	365.9	365.9	366.0	366.3	366.6	366.8	367.1	366.8	366.6	366.3
180°	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8



TEST NUMBER: P832105

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7
2.5°	876.8	866.2	855.6	848.0	840.4	830.9	821.4	821.1	820.7	813.6	806.6
5°	824.8	806.4	788.0	770.0	752.0	734.0	716.0	711.9	707.8	701.7	695.6
7.5°	778.7	749.4	720.1	697.0	674.0	656.0	638.0	625.7	613.5	604.0	594.5
10°	729.3	693.0	656.6	628.7	600.9	581.4	561.9	547.8	533.6	527.0	520.3
12.5°	678.1	638.5	599.0	571.7	544.4	521.0	497.6	484.8	472.0	462.7	453.4
15°	630.9	588.4	545.9	516.9	488.0	466.1	444.1	431.3	418.5	409.2	400.0
17.5°	585.3	542.4	499.5	470.1	440.8	420.9	401.1	388.6	376.2	370.4	364.7
20°	543.7	500.4	457.1	429.5	401.8	382.3	362.8	356.1	349.4	344.1	338.7
22.5°	502.4	460.9	419.3	392.7	366.2	352.0	337.9	332.5	327.2	323.1	319.0
25°	467.9	426.5	385.1	361.9	338.7	327.7	316.8	313.2	309.7	305.6	301.5
27.5°	433.0	393.6	354.3	335.7	317.1	308.2	299.3	294.9	290.4	287.1	283.7
30°	402.2	365.8	329.4	314.0	298.6	290.8	283.0	278.1	273.3	270.2	267.0
32.5°	372.5	340.2	307.9	294.7	281.5	273.9	266.3	261.6	257.0	253.3	249.6
35°	345.0	317.0	288.9	276.8	264.8	257.2	249.6	244.9	240.3	236.6	232.8
37.5°	320.9	295.4	270.0	258.6	247.3	240.6	234.0	229.1	224.3	220.4	216.5
40°	298.2	275.7	253.3	242.3	231.4	224.1	216.9	212.6	208.3	204.8	201.3
42.5°	278.1	257.5	236.9	226.2	215.4	208.5	201.6	196.6	191.6	189.6	187.5
45°	257.0	238.8	220.6	210.2	199.8	192.5	185.3	181.0	176.8	174.9	173.1
47.5°	238.4	221.5	204.6	194.4	184.2	177.7	171.2	167.9	164.5	161.9	159.3
50°	220.2	203.9	187.5	177.7	167.9	162.3	156.7	152.6	148.5	146.7	144.8
52.5°	202.8	187.9	173.1	163.0	153.0	147.6	142.2	138.7	135.2	131.3	127.4
55°	183.1	170.1	157.1	148.2	139.3	133.7	128.1	124.0	119.9	115.9	111.8
57.5°	166.7	153.9	141.1	133.1	125.1	119.8	114.4	109.9	105.5	102.1	98.8
60°	148.9	137.8	126.6	118.8	111.0	105.8	100.6	96.4	92.1	90.4	88.8
62.5°	132.2	121.8	111.4	104.5	97.7	92.7	87.6	84.9	82.1	81.0	79.8
65°	115.1	106.2	97.3	91.0	84.7	80.4	76.1	74.8	73.5	72.6	71.7
67.5°	99.2	91.5	83.9	78.4	72.8	69.8	66.8	65.4	63.9	62.8	61.6
70°	84.7	78.0	71.3	66.5	61.6	58.9	56.1	54.8	53.5	51.4	49.4
72.5°	69.1	63.9	58.7	55.0	51.2	48.8	46.4	43.8	41.2	39.4	37.5
75°	57.2	52.0	46.8	43.3	39.7	36.9	34.2	33.2	32.3	31.8	31.2
77.5°	43.8	39.4	34.9	32.1	29.3	28.0	26.7	26.2	25.6	25.4	25.3
80°	31.6	27.9	24.1	22.7	21.2	20.8	20.4	20.1	19.7	19.5	19.3
82.5°	19.7	17.8	16.0	15.6	15.2	15.0	14.9	14.7	14.5	14.3	14.1
85°	11.5	10.8	10.0	9.8	9.7	9.5	9.3	9.3	9.3	9.3	9.3
87.5°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.6	4.5
90°	2.8	3.6	4.4	5.3	6.1	6.9	7.2	7.4	7.7	7.9	8.1
92.5°	10.2	10.6	10.9	11.3	11.7	12.1	12.3	12.5	12.7	12.9	12.9
95°	18.8	19.3	19.8	20.3	20.8	21.3	21.6	21.8	22.1	22.3	22.5
97.5°	29.2	29.6	30.0	30.3	30.7	31.1	31.4	31.8	32.1	32.4	32.5
100°	40.7	41.1	41.4	41.7	42.0	42.4	42.5	42.7	42.9	43.1	43.3
102.5°	52.9	53.2	53.7	54.1	54.6	55.0	55.2	55.4	55.6	55.8	55.9
105°	65.3	65.7	66.3	66.8	67.4	68.0	68.0	68.0	68.0	68.0	68.1
107.5°	80.1	80.2	80.5	80.7	81.0	81.2	81.4	81.6	81.8	82.0	82.1
110°	94.2	94.3	94.4	94.5	94.7	94.8	95.0	95.3	95.6	95.8	95.9



TEST NUMBER: P832105

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	108.3	108.3	108.3	108.3	108.3	108.3	108.7	109.0	109.3	109.6	109.8
115°	123.2	123.3	123.1	123.0	122.9	122.7	122.8	122.9	122.9	123.0	123.0
117.5°	137.4	137.4	137.2	137.1	137.0	136.9	136.9	136.9	136.9	136.9	136.8
120°	152.2	152.3	151.9	151.6	151.3	151.0	150.9	150.8	150.8	150.7	150.6
122.5°	165.8	165.9	165.8	165.6	165.5	165.4	165.2	165.0	164.8	164.6	164.4
125°	180.0	180.0	179.9	179.8	179.6	179.5	179.2	179.0	178.7	178.5	178.2
127.5°	194.0	194.1	194.0	193.9	193.7	193.6	193.2	192.8	192.5	192.1	191.8
130°	207.8	207.9	207.7	207.5	207.3	207.2	206.9	206.6	206.4	206.1	205.8
132.5°	221.0	221.2	221.1	221.0	220.8	220.7	220.4	220.1	219.7	219.4	219.1
135°	234.0	234.2	234.1	234.1	234.0	234.0	233.7	233.4	233.2	232.9	232.7
137.5°	246.2	246.4	246.6	246.8	247.0	247.2	246.9	246.6	246.2	245.9	245.7
140°	259.1	259.3	259.4	259.5	259.5	259.6	259.5	259.5	259.4	259.3	259.1
142.5°	271.0	271.2	271.3	271.4	271.6	271.7	271.6	271.6	271.5	271.4	271.2
145°	282.6	282.7	282.9	283.1	283.3	283.5	283.4	283.4	283.3	283.3	283.1
147.5°	293.8	294.0	294.2	294.4	294.6	294.7	294.7	294.7	294.7	294.7	294.6
150°	304.5	304.6	304.7	304.9	305.0	305.1	305.1	305.1	305.1	305.1	304.9
152.5°	314.0	314.1	314.1	314.2	314.3	314.3	314.5	314.6	314.7	314.9	314.8
155°	323.0	323.0	323.1	323.1	323.2	323.3	323.5	323.8	324.0	324.3	324.2
157.5°	331.1	331.1	331.1	331.2	331.3	331.3	331.6	331.8	332.1	332.4	332.3
160°	338.6	338.5	338.5	338.5	338.5	338.5	338.9	339.2	339.5	339.8	339.9
162.5°	345.3	345.2	345.3	345.3	345.4	345.5	345.8	346.1	346.4	346.7	346.7
165°	351.0	350.9	350.9	350.9	350.9	350.9	351.3	351.7	352.1	352.5	352.4
167.5°	355.7	355.6	355.6	355.7	355.8	355.8	356.2	356.6	357.0	357.4	357.4
170°	359.7	359.6	359.6	359.6	359.6	359.6	360.0	360.5	360.9	361.4	361.4
172.5°	362.9	362.7	362.7	362.7	362.7	362.7	363.1	363.5	363.9	364.3	364.2
175°	364.9	364.8	364.8	364.8	364.8	364.8	365.1	365.5	365.9	366.3	366.3
177.5°	366.0	365.9	365.9	365.9	365.9	365.9	366.3	366.7	367.1	367.4	367.4
180°	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8



TEST NUMBER: P832105

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	905.7	905.7	905.7	905.7
2.5°	804.7	802.9	802.1	801.4
5°	689.8	684.0	682.7	681.4
7.5°	592.1	589.7	581.7	573.7
10°	512.8	505.4	502.1	498.7
12.5°	446.6	439.7	438.6	437.5
15°	395.1	390.3	388.6	387.0
17.5°	361.3	358.0	355.9	353.9
20°	336.3	333.8	332.4	330.9
22.5°	317.1	315.3	314.2	313.1
25°	298.8	296.0	295.0	294.1
27.5°	281.3	278.9	278.0	277.0
30°	265.0	262.9	261.6	260.3
32.5°	247.1	244.7	244.0	243.2
35°	231.4	229.9	229.1	228.4
37.5°	214.6	212.8	211.7	210.6
40°	200.3	199.4	198.9	198.3
42.5°	185.9	184.2	184.0	183.8
45°	171.4	169.7	169.3	169.0
47.5°	157.8	156.3	156.2	156.0
50°	142.8	140.7	139.3	137.8
52.5°	125.5	123.7	122.4	121.1
55°	109.7	107.7	106.6	105.5
57.5°	97.9	96.9	96.4	95.8
60°	88.2	87.6	87.3	86.9
62.5°	79.3	78.7	78.7	78.7
65°	71.1	70.6	70.0	69.4
67.5°	60.5	59.4	59.2	59.0
70°	47.7	46.0	45.9	45.7
72.5°	37.3	37.1	36.8	36.4
75°	30.8	30.5	30.5	30.5
77.5°	24.9	24.5	24.5	24.5
80°	19.1	18.9	19.1	19.3
82.5°	14.1	14.1	13.9	13.7
85°	9.1	8.9	8.9	8.9
87.5°	4.5	4.5	4.5	4.5
90°	8.3	8.4	8.5	8.6
92.5°	12.8	12.6	12.5	12.4
95°	22.5	22.5	22.5	22.5
97.5°	32.5	32.4	32.3	32.3
100°	43.4	43.5	43.7	43.8
102.5°	55.8	55.7	55.7	55.6
105°	68.2	68.3	68.4	68.6
107.5°	82.0	82.0	81.9	81.8
110°	95.8	95.6	95.5	95.4



TEST NUMBER: P832105

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	109.8	109.8	109.8	109.8
115°	122.9	122.9	122.8	122.7
117.5°	136.6	136.4	136.2	136.0
120°	150.5	150.4	150.2	150.1
122.5°	164.2	164.0	163.8	163.7
125°	178.0	177.7	177.4	177.2
127.5°	191.5	191.2	191.0	190.7
130°	205.3	204.9	204.4	204.0
132.5°	218.8	218.5	218.1	217.8
135°	232.6	232.5	232.4	232.2
137.5°	245.5	245.3	245.1	244.9
140°	258.6	258.2	257.7	257.3
142.5°	270.9	270.6	270.3	270.0
145°	282.8	282.6	282.3	282.1
147.5°	294.2	293.8	293.4	293.0
150°	304.5	304.2	303.8	303.4
152.5°	314.4	314.1	313.8	313.5
155°	323.7	323.3	322.9	322.4
157.5°	331.9	331.5	331.1	330.8
160°	339.6	339.3	339.1	338.8
162.5°	346.2	345.8	345.3	344.9
165°	352.0	351.5	351.1	350.6
167.5°	357.0	356.6	356.2	355.8
170°	360.9	360.5	360.0	359.6
172.5°	363.8	363.4	362.9	362.5
175°	365.8	365.4	364.9	364.5
177.5°	367.0	366.5	366.1	365.6
180°	366.8	366.8	366.8	366.8



TEST NUMBER: P832105

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-G1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.04	9.88	9.97	10.82	12.04	13.71	14.55	14.64	15.49	16.70
	3H	10.26	11.02	11.21	11.97	13.21	15.21	15.96	16.15	16.91	18.15
	4H	10.65	11.36	11.61	12.31	13.56	15.70	16.41	16.65	17.36	18.61
	6H	10.93	11.58	11.90	12.54	13.80	16.01	16.66	16.98	17.62	18.88
	8H	11.02	11.64	11.99	12.61	13.87	16.09	16.71	17.06	17.69	18.94
	12H	11.07	11.66	12.05	12.63	13.91	16.12	16.71	17.10	17.68	18.96
4H	2H	9.77	10.48	10.73	11.43	12.68	13.70	14.41	14.67	15.37	16.62
	3H	11.14	11.73	12.11	12.71	13.97	15.36	15.95	16.33	16.94	18.20
	4H	11.59	12.13	12.57	13.11	14.40	15.97	16.51	16.95	17.48	18.77
	6H	11.96	12.42	12.95	13.42	14.71	16.41	16.87	17.40	17.87	19.16
	8H	12.09	12.52	13.08	13.51	14.81	16.54	16.97	17.53	17.96	19.26
	12H	12.16	12.55	13.18	13.56	14.87	16.60	16.99	17.61	18.00	19.30
8H	4H	11.91	12.34	12.90	13.33	14.63	15.94	16.37	16.93	17.36	18.66
	6H	12.37	12.73	13.39	13.76	15.06	16.43	16.79	17.45	17.83	19.12
	8H	12.56	12.88	13.59	13.90	15.22	16.62	16.93	17.65	17.96	19.27
	12H	12.71	12.98	13.74	14.00	15.36	16.74	17.01	17.77	18.03	19.39
12H	4H	11.92	12.31	12.93	13.32	14.62	15.89	16.27	16.90	17.29	18.59
	6H	12.43	12.74	13.46	13.77	15.08	16.41	16.72	17.44	17.75	19.06
	8H	12.65	12.92	13.68	13.94	15.30	16.60	16.88	17.63	17.89	19.25