

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332248-930

Luminaire Tested: **S123RDIP-S340D585U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332248-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D585U930-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2834.9 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332248-930

CATALOG NUMBER: S123RDIP-S340D585U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332248-930

CATALOG NUMBER: S123RDIP-S340D585U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39																												
1	96	92	88	85	87	84	80	78	68	66	64	54	53	52	41	41	40	34																												
2	88	81	75	70	79	74	69	64	60	57	54	48	46	44	37	35	34	29																												
3	80	71	64	59	73	65	59	54	54	49	46	43	40	38	33	31	30	25																												
4	73	63	56	50	67	58	51	46	48	43	39	39	35	32	30	28	26	22																												
5	68	56	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19																												
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20	17																												
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18	15																												
8	53	42	34	29	49	38	32	27	32	27	24	26	23	20	21	18	16	14																												
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	19	17	15	13																												
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4776	4776	4776	4776
5°	5693	4796	4224	4796
10°	7109	4769	3816	4769
15°	8344	4719	3480	4719
20°	9313	4647	3194	4647
25°	9164	4570	3018	4570
30°	6586	4501	2838	4501
35°	4398	4407	2720	4407
40°	3240	4297	2599	4297
45°	2719	4102	2481	4102
50°	2398	3848	2316	3848
55°	2104	3558	2089	3558
60°	1873	3279	1914	3279
65°	1645	2980	1780	2980
70°	1290	2716	1627	2716
75°	1135	2371	1485	2371
80°	992	2008	1463	2008
85°	790	1618	1556	1618



TEST NUMBER: P332248-930

CATALOG NUMBER: S123RDIP-S340D585U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.6	1.5
10°-20°	136.3	4.8
20°-30°	214.2	7.6
30°-40°	223.4	7.9
40°-50°	191.2	6.7
50°-60°	145.7	5.1
60°-70°	93.4	3.3
70°-80°	44.9	1.6
80°-90°	13.7	0.5
90°-100°	127.8	4.5
100°-110°	362.0	12.8
110°-120°	356.1	12.6
120°-130°	284.0	10.0
130°-140°	224.0	7.9
140°-150°	167.1	5.9
150°-160°	116.5	4.1
160°-170°	68.4	2.4
170°-180°	22.3	0.8
0°-30°	394.1	13.9
0°-40°	617.6	21.8
0°-60°	954.5	33.7
0°-90°	1106.6	39.0
90°-120°	846.0	29.8
90°-150°	1521.1	53.7
90°-180°	1728.0	61.0
0°-180°	2834.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	444	444	444	444	444	
5°	527	444	391	444	527	54
15°	749	424	312	424	749	212
25°	772	385	254	385	772	332
35°	335	335	207	335	335	219
45°	179	270	163	270	179	140
55°	112	190	111	190	112	101
65°	65	117	70	117	65	64
75°	27	57	36	57	27	29
85°	6	13	13	13	6	8
90°	14	1	14	1	14	7
95°	54	16	54	16	54	97
105°	592	54	592	54	592	584
115°	719	95	719	95	719	699
125°	567	133	567	133	567	514
135°	460	155	460	155	460	357
145°	360	177	360	177	360	229
155°	298	201	298	201	298	139
165°	260	220	260	220	260	74
175°	234	229	234	229	234	23
180°	230	230	230	230	230	



TEST NUMBER: P332248-930

CATALOG NUMBER: S123RDIP-S340D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	472.6	473.2	471.2	470.9	468.6	468.1	468.1	464.8	462.8	460.3	458.8
5°	526.9	529.9	528.4	525.1	519.3	518.0	514.4	508.7	502.2	494.2	490.5
7.5°	594.8	598.9	597.3	592.1	586.0	581.2	571.0	561.6	548.4	536.7	526.8
10°	650.4	646.0	642.6	637.5	631.9	623.1	612.4	597.8	580.9	567.5	552.8
12.5°	692.0	691.3	687.0	681.7	673.9	665.4	652.3	634.5	614.9	595.7	578.7
15°	748.8	749.9	747.1	741.6	730.5	715.5	695.8	688.4	660.2	639.4	618.5
17.5°	788.1	787.8	787.4	779.8	768.6	757.9	739.6	720.1	694.6	665.2	637.1
20°	813.0	811.1	811.5	802.9	794.6	782.2	764.3	736.1	715.2	681.2	652.1
22.5°	812.4	812.0	813.4	810.5	804.5	795.0	780.9	757.0	730.3	696.0	663.3
25°	771.6	770.1	778.9	781.5	791.2	792.9	788.6	775.6	750.3	714.9	674.5
27.5°	645.7	644.9	661.5	682.2	708.5	729.0	748.7	758.2	750.3	725.0	684.4
30°	529.9	547.8	556.2	586.2	619.6	659.5	694.5	727.7	735.9	724.8	691.6
32.5°	440.0	455.6	462.6	488.3	519.5	566.2	618.6	665.7	699.0	707.4	687.4
35°	334.7	334.8	350.8	362.2	391.1	439.1	490.1	553.1	615.8	663.3	668.2
37.5°	267.1	268.0	277.7	289.0	310.7	336.1	380.9	433.3	505.7	578.6	621.4
40°	230.6	232.3	239.5	250.7	266.3	285.5	320.4	369.8	430.2	511.4	577.6
42.5°	207.2	209.9	213.7	222.3	232.0	250.0	278.2	316.3	371.3	448.0	524.5
45°	178.6	180.1	183.0	186.9	195.7	208.1	227.1	252.8	298.4	360.1	436.7
47.5°	157.5	156.7	159.7	162.9	168.8	177.3	190.0	210.9	243.4	293.0	357.9
50°	143.2	143.0	145.1	147.6	153.1	159.4	169.8	185.6	211.4	252.4	311.9
52.5°	129.9	130.5	132.1	135.1	139.1	144.1	153.5	164.9	187.1	222.5	272.1
55°	112.1	112.7	114.7	116.4	119.3	124.4	130.3	139.8	155.0	179.7	220.5
57.5°	97.0	96.8	98.7	99.2	102.4	106.6	111.1	118.5	129.6	147.9	175.4
60°	87.0	86.4	88.1	89.4	91.2	94.6	98.4	105.6	114.4	127.8	151.4
62.5°	77.9	77.6	78.8	80.2	81.6	84.7	87.9	93.4	100.4	111.7	130.4
65°	64.6	65.1	65.7	66.3	67.0	69.0	72.0	75.8	80.6	88.5	102.0
67.5°	50.8	51.4	51.5	52.7	54.3	55.5	57.4	60.7	64.1	70.8	78.4
70°	41.0	40.8	41.0	41.6	43.7	45.7	48.3	50.7	52.8	57.6	64.0
72.5°	35.2	34.9	35.4	35.5	36.5	37.1	38.6	41.0	43.7	46.9	51.5
75°	27.3	27.3	27.3	27.3	28.1	28.5	29.0	29.6	30.6	32.1	35.5
77.5°	20.2	20.2	20.5	20.7	20.9	21.1	21.4	22.0	22.3	23.2	24.6
80°	16.0	16.1	16.0	16.1	16.1	16.6	16.7	17.3	17.4	18.4	19.0
82.5°	12.0	11.9	12.0	12.2	12.2	12.6	12.6	13.0	13.0	13.5	14.1
85°	6.4	6.1	6.4	6.3	6.7	6.3	6.4	6.8	6.8	7.0	7.8
87.5°	4.2	4.6	4.2	4.2	4.4	4.3	4.2	4.2	4.3	4.3	4.2
90°	13.5	13.9	13.5	13.0	13.5	12.6	12.1	11.7	11.2	11.7	10.2
92.5°	22.4	23.2	22.7	24.2	25.0	27.5	31.1	39.1	54.0	71.5	78.7
95°	54.0	55.8	59.0	63.3	72.1	88.8	113.5	167.4	223.6	275.7	245.6
97.5°	146.8	150.8	163.4	184.3	218.7	274.3	334.3	417.4	457.2	427.4	312.8
100°	291.6	291.1	309.2	343.2	390.1	456.2	510.6	548.3	532.0	440.3	297.6
102.5°	427.7	438.4	453.6	480.5	517.0	558.9	590.6	591.8	535.7	416.2	275.3
105°	591.5	593.9	608.7	626.4	647.8	659.9	651.0	604.5	507.4	373.9	247.9
107.5°	685.8	690.1	695.1	701.1	700.7	684.1	643.4	567.9	457.7	336.5	230.4
110°	724.5	725.5	726.4	722.7	709.6	677.1	618.5	532.9	426.4	315.3	223.6



TEST NUMBER: P332248-930

CATALOG NUMBER: S123RDIP-S340D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	732.3	732.1	728.6	717.1	693.2	651.4	585.7	498.3	399.3	301.2	220.0
115°	719.4	717.1	707.8	687.3	652.4	601.8	533.4	452.5	366.5	286.0	218.6
117.5°	678.2	675.1	661.7	638.3	601.9	550.5	489.1	419.2	346.7	277.0	219.4
120°	644.1	641.2	630.1	604.1	567.4	520.3	464.6	401.8	336.2	273.0	220.9
122.5°	612.0	608.5	596.2	572.8	540.1	496.5	444.8	388.0	327.7	270.4	223.5
125°	567.4	564.1	552.4	532.0	502.2	465.0	420.4	369.7	316.7	266.9	227.4
127.5°	530.5	527.5	517.0	499.5	473.0	439.2	398.9	353.7	307.0	265.2	231.9
130°	509.6	506.0	496.2	479.5	454.8	423.1	385.5	343.6	301.8	264.2	234.8
132.5°	489.2	486.6	477.9	461.2	438.1	407.9	372.8	334.4	296.9	263.7	237.1
135°	459.9	456.6	448.3	434.3	411.6	385.1	354.8	321.8	290.7	263.2	240.4
137.5°	428.9	426.8	419.7	405.6	386.5	363.5	337.5	310.4	285.2	262.2	242.6
140°	407.3	407.8	400.4	387.3	369.7	349.7	327.3	303.7	281.8	261.8	244.1
142.5°	387.3	387.8	381.1	369.5	354.4	337.0	317.7	297.3	278.8	261.1	245.2
145°	359.5	358.6	354.8	345.0	333.5	319.9	305.1	289.7	274.8	259.9	246.0
147.5°	336.6	336.2	332.6	326.0	317.2	307.7	295.6	283.5	270.9	258.2	246.0
150°	323.2	323.2	320.4	315.3	308.3	299.5	289.7	279.0	268.3	256.7	246.0
152.5°	312.0	312.0	310.4	305.6	300.1	292.8	284.1	274.9	265.4	254.9	244.9
155°	298.1	297.6	296.7	292.9	288.8	283.2	276.2	268.8	260.9	251.6	243.7
157.5°	285.4	285.4	284.7	281.9	278.3	273.9	268.5	262.3	255.8	248.7	242.1
160°	277.1	277.6	277.6	274.8	271.6	268.3	263.7	258.5	252.5	246.5	241.3
162.5°	269.7	270.2	270.2	267.7	265.6	262.8	258.4	254.1	249.2	244.3	239.9
165°	259.9	259.9	260.4	258.5	256.7	254.4	251.1	248.3	244.6	240.9	237.7
167.5°	250.6	250.6	251.1	249.8	249.0	247.3	245.4	243.3	240.3	237.5	235.4
170°	245.1	245.1	245.6	244.6	244.1	243.2	241.3	239.9	237.7	235.3	233.9
172.5°	239.9	240.3	241.1	240.1	240.0	239.5	238.0	237.0	235.1	233.4	232.8
175°	233.9	234.4	234.8	234.4	234.4	234.4	233.4	233.0	232.0	231.1	231.1
177.5°	230.5	230.5	231.2	230.8	231.2	231.2	230.8	230.5	230.1	229.8	230.1
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8



TEST NUMBER: P332248-930

CATALOG NUMBER: S123RDIP-S340D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	458.1	457.7	455.6	453.1	450.0	447.8	446.1	445.2	442.5	439.1	436.9
5°	486.5	480.8	474.7	467.2	460.4	453.4	449.1	443.9	437.7	430.6	425.7
7.5°	516.7	505.6	493.6	481.1	468.9	457.9	448.1	439.8	429.8	419.7	412.7
10°	540.1	523.7	506.8	489.5	473.8	458.9	447.5	436.3	424.4	412.8	404.0
12.5°	561.2	539.6	520.2	498.9	478.7	461.1	444.7	431.5	417.0	404.7	394.8
15°	587.9	565.8	542.3	510.0	483.2	460.8	440.8	423.5	406.1	390.9	381.2
17.5°	612.9	579.8	548.0	521.1	486.3	458.4	434.0	413.4	394.1	378.1	366.1
20°	623.2	591.1	556.8	522.4	488.2	456.8	428.5	405.7	385.8	367.5	356.5
22.5°	629.4	593.1	556.8	519.9	483.6	451.0	423.1	397.9	376.3	359.1	345.4
25°	636.7	593.4	553.5	517.1	480.0	444.7	411.4	384.8	361.5	343.1	328.6
27.5°	641.5	590.5	543.4	502.9	465.3	430.2	399.7	371.5	347.7	328.2	312.7
30°	642.4	588.2	535.7	491.8	453.6	421.3	389.0	362.1	337.0	316.3	301.8
32.5°	643.6	582.6	525.1	478.6	439.4	407.5	378.2	352.5	326.8	306.4	291.6
35°	638.6	579.5	509.2	455.7	416.5	385.6	359.2	335.4	310.2	290.4	275.4
37.5°	617.0	567.2	492.8	429.9	389.0	360.4	338.8	318.1	295.0	273.6	259.5
40°	595.3	555.1	480.0	414.3	371.5	342.1	322.7	305.8	283.4	263.4	248.3
42.5°	563.0	538.4	467.8	397.9	351.8	323.4	307.0	291.2	271.6	251.3	237.0
45°	503.5	506.8	443.0	371.7	324.4	296.0	280.5	269.5	252.1	235.4	220.7
47.5°	429.1	459.3	413.8	343.9	295.6	268.9	255.4	245.8	234.0	217.6	204.2
50°	380.5	423.5	390.4	325.2	277.5	250.9	237.7	229.8	219.6	206.7	194.0
52.5°	335.7	382.0	362.1	304.4	257.9	233.6	220.6	214.2	206.0	193.9	182.4
55°	273.7	320.7	316.1	273.0	228.5	206.7	196.8	189.6	184.1	175.0	165.8
57.5°	221.4	265.9	268.2	238.0	202.6	181.0	172.5	167.1	163.5	156.6	148.1
60°	188.4	229.3	237.3	214.4	184.1	165.1	156.7	152.3	149.5	144.0	137.5
62.5°	161.1	195.8	204.9	188.5	166.3	148.5	141.9	137.8	135.8	131.1	125.4
65°	123.3	152.1	160.9	151.8	140.1	126.0	120.6	117.0	115.3	112.7	108.4
67.5°	92.7	113.7	123.4	116.9	112.7	103.7	100.4	98.4	96.9	95.1	91.6
70°	74.4	90.0	99.9	98.2	94.8	90.0	87.6	86.3	84.7	83.2	80.1
72.5°	59.8	70.6	79.8	80.7	77.9	77.0	74.8	74.2	73.3	71.5	69.8
75°	39.7	47.1	53.6	56.0	57.2	58.1	57.2	57.0	56.8	55.3	54.3
77.5°	26.0	30.0	34.1	38.3	40.1	41.3	41.7	42.4	41.8	41.1	40.6
80°	20.0	20.9	23.7	27.3	30.2	31.3	32.1	32.4	32.3	32.1	31.3
82.5°	14.5	15.2	16.6	19.2	21.5	23.4	23.9	23.8	24.2	24.4	23.7
85°	7.8	8.0	8.4	8.7	10.0	12.1	12.7	13.1	13.5	13.5	12.3
87.5°	4.2	3.8	3.8	3.6	3.9	3.8	4.5	5.1	5.4	5.0	5.2
90°	8.8	7.4	6.0	5.1	4.2	2.8	1.9	0.9	1.9	2.8	4.2
92.5°	59.0	39.1	26.9	20.0	16.1	12.5	8.6	5.8	8.6	12.5	16.1
95°	169.3	100.0	60.4	42.3	30.2	22.3	17.2	15.8	17.2	22.3	30.2
97.5°	185.7	107.6	69.9	50.2	38.3	31.5	27.5	27.0	27.5	31.5	38.3
100°	175.3	106.5	73.9	55.8	44.7	38.2	34.9	34.4	34.9	38.2	44.7
102.5°	166.4	107.9	78.8	62.1	52.1	46.0	43.0	42.2	43.0	46.0	52.1
105°	160.0	112.1	87.0	72.6	63.7	58.1	55.4	54.0	55.4	58.1	63.7
107.5°	159.5	119.7	97.7	84.3	76.0	70.5	67.8	66.4	67.8	70.5	76.0
110°	161.3	126.0	105.1	92.0	84.1	79.1	76.7	75.3	76.7	79.1	84.1



TEST NUMBER: P332248-930

CATALOG NUMBER: S123RDIP-S340D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	165.1	132.3	112.9	100.3	92.4	87.2	85.0	83.5	85.0	87.2	92.4
115°	171.1	142.8	125.1	112.5	104.6	100.0	97.2	95.3	97.2	100.0	104.6
117.5°	179.1	153.8	136.3	124.7	115.9	111.6	109.3	107.1	109.3	111.6	115.9
120°	185.1	160.9	144.1	132.6	123.7	119.0	116.8	115.4	116.8	119.0	123.7
122.5°	190.7	168.4	152.0	139.6	131.1	126.1	123.8	122.4	123.8	126.1	131.1
125°	199.5	179.0	162.7	150.2	141.4	136.2	133.5	132.6	133.5	136.2	141.4
127.5°	206.8	188.3	172.6	160.0	150.3	145.1	141.6	140.2	141.6	145.1	150.3
130°	211.6	193.9	178.6	166.0	156.2	150.7	146.5	145.1	146.5	150.7	156.2
132.5°	216.1	198.8	183.8	171.6	161.8	155.2	150.6	148.8	150.6	155.2	161.8
135°	221.8	206.0	191.6	179.0	169.3	162.3	157.2	155.3	157.2	162.3	169.3
137.5°	226.1	211.0	197.1	185.6	175.9	168.4	163.4	161.4	163.4	168.4	175.9
140°	228.4	214.3	200.9	189.2	179.9	172.5	167.9	165.6	167.9	172.5	179.9
142.5°	230.6	217.0	203.9	193.0	183.7	177.0	171.9	170.0	171.9	177.0	183.7
145°	233.0	220.5	208.3	197.6	189.7	182.8	178.6	177.2	178.6	182.8	189.7
147.5°	234.5	223.2	212.1	203.0	195.4	189.4	185.2	184.4	185.2	189.4	195.4
150°	234.8	225.1	214.3	206.0	199.5	193.5	189.7	189.2	189.7	193.5	199.5
152.5°	235.6	226.2	217.0	209.0	203.3	198.0	194.2	194.1	194.2	198.0	203.3
155°	235.8	228.4	220.5	213.9	208.8	204.2	201.4	201.4	201.4	204.2	208.8
157.5°	236.3	229.5	223.2	218.2	213.9	209.7	207.5	207.1	207.5	209.7	213.9
160°	236.3	230.6	225.1	220.5	217.2	213.4	211.6	211.6	211.6	213.4	217.2
162.5°	235.9	231.1	226.2	222.3	219.4	216.5	214.9	214.9	214.9	216.5	219.4
165°	234.8	231.5	227.9	224.6	222.7	220.5	219.5	220.0	219.5	220.5	222.7
167.5°	234.1	231.5	228.8	226.7	225.4	223.6	223.2	223.8	223.2	223.6	225.4
170°	233.0	231.1	228.8	227.9	226.9	225.5	225.1	226.0	225.1	225.5	226.9
172.5°	232.6	231.1	229.2	228.6	228.0	227.1	226.9	227.5	226.9	227.1	228.0
175°	231.5	230.6	229.8	229.3	229.3	228.4	228.8	229.3	228.8	228.4	229.3
177.5°	230.8	230.1	229.8	229.8	229.8	229.3	229.8	230.1	229.8	229.3	229.8
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8



TEST NUMBER: P332248-930

CATALOG NUMBER: S123RDIP-S340D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	436.1	434.1	432.8	429.7	427.8	425.7	423.5	424.9	424.7	424.6	424.6
5°	421.5	417.1	413.1	408.0	404.8	400.8	397.8	397.4	398.1	395.5	394.0
7.5°	407.0	401.0	395.3	389.7	383.7	378.9	375.9	374.5	372.6	371.0	369.2
10°	396.8	389.8	384.3	377.2	370.8	365.1	361.5	359.0	357.7	356.4	353.8
12.5°	386.3	379.4	372.4	364.4	358.3	351.7	349.0	346.3	343.7	342.2	338.8
15°	371.0	362.1	354.7	346.3	339.4	333.0	329.2	323.7	322.9	321.0	317.6
17.5°	355.6	345.9	335.7	329.5	321.8	315.0	309.2	307.4	302.0	299.9	296.9
20°	343.4	334.5	326.7	318.5	307.4	301.1	296.5	294.1	289.7	287.0	285.1
22.5°	333.0	323.8	314.9	305.3	296.1	289.0	285.7	281.8	279.5	275.7	273.7
25°	318.0	308.1	297.3	287.0	280.4	275.1	269.7	266.3	262.9	261.1	257.4
27.5°	300.6	290.2	280.1	272.3	264.2	258.9	254.1	251.1	247.0	244.1	242.0
30°	291.0	278.8	270.1	263.1	252.7	247.7	244.1	240.3	237.3	234.2	232.1
32.5°	279.9	268.8	260.6	251.8	243.9	238.4	233.7	230.4	227.8	224.9	222.8
35°	262.5	253.2	244.7	235.9	230.0	224.5	219.0	216.1	213.7	211.0	209.1
37.5°	246.8	238.1	229.9	221.7	214.3	209.9	205.5	203.3	199.9	198.1	196.2
40°	237.1	228.5	219.8	211.8	204.2	200.8	196.8	193.6	190.5	189.1	187.1
42.5°	226.4	217.8	210.5	201.9	195.7	191.0	187.4	183.8	181.6	179.6	178.5
45°	210.7	203.1	195.8	187.3	181.4	177.4	173.3	170.0	168.0	166.6	164.5
47.5°	195.3	187.8	180.4	173.0	167.3	162.7	158.5	156.3	153.5	151.9	150.5
50°	184.3	177.4	169.7	162.8	157.1	152.5	149.1	146.3	143.8	141.7	140.7
52.5°	174.1	166.8	160.0	153.7	147.7	142.5	139.4	136.4	134.5	132.2	131.0
55°	157.3	150.3	144.6	138.3	132.4	128.0	124.3	121.6	119.7	117.0	115.5
57.5°	141.5	135.2	128.4	122.9	116.9	113.2	110.1	106.5	104.1	102.1	100.5
60°	130.9	123.7	117.7	112.7	107.3	102.6	99.7	96.9	94.4	92.3	91.0
62.5°	119.8	113.5	107.9	102.3	97.4	93.3	90.0	87.6	85.4	84.1	82.8
65°	102.7	97.8	92.1	87.6	83.0	80.0	77.3	75.3	73.7	72.7	71.6
67.5°	87.1	82.3	77.4	72.9	69.8	67.5	65.8	64.0	63.2	62.0	61.2
70°	77.0	72.0	67.6	64.2	61.1	59.4	58.3	57.0	56.3	54.7	54.0
72.5°	65.9	62.3	59.1	56.3	53.9	52.3	50.9	49.2	48.0	46.3	45.6
75°	51.9	48.6	46.1	44.3	42.7	40.7	38.6	36.9	36.3	35.7	35.5
77.5°	38.4	36.4	34.6	32.9	31.1	29.6	29.1	28.7	28.6	28.3	28.3
80°	30.2	28.3	27.0	25.1	24.0	24.0	24.0	23.6	23.7	23.7	23.7
82.5°	22.4	20.7	20.0	19.3	19.1	19.2	19.2	19.3	19.2	19.5	19.3
85°	11.6	11.7	12.1	12.0	12.1	12.1	12.6	12.3	12.6	12.1	12.6
87.5°	5.3	6.0	6.4	6.8	7.2	7.3	7.4	7.5	7.7	7.8	8.0
90°	5.1	6.0	7.4	8.8	10.2	11.7	11.2	11.7	12.1	12.6	13.5
92.5°	20.0	26.9	39.1	59.0	78.7	71.5	54.0	39.1	31.1	27.5	25.0
95°	42.3	60.4	100.0	169.3	245.6	275.7	223.6	167.4	113.5	88.8	72.1
97.5°	50.2	69.9	107.6	185.7	312.8	427.4	457.2	417.4	334.3	274.3	218.7
100°	55.8	73.9	106.5	175.3	297.6	440.3	532.0	548.3	510.6	456.2	390.1
102.5°	62.1	78.8	107.9	166.4	275.3	416.2	535.7	591.8	590.6	558.9	517.0
105°	72.6	87.0	112.1	160.0	247.9	373.9	507.4	604.5	651.0	659.9	647.8
107.5°	84.3	97.7	119.7	159.5	230.4	336.5	457.7	567.9	643.4	684.1	700.7
110°	92.0	105.1	126.0	161.3	223.6	315.3	426.4	532.9	618.5	677.1	709.6



TEST NUMBER: P332248-930

CATALOG NUMBER: S123RDIP-S340D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	100.3	112.9	132.3	165.1	220.0	301.2	399.3	498.3	585.7	651.4	693.2
115°	112.5	125.1	142.8	171.1	218.6	286.0	366.5	452.5	533.4	601.8	652.4
117.5°	124.7	136.3	153.8	179.1	219.4	277.0	346.7	419.2	489.1	550.5	601.9
120°	132.6	144.1	160.9	185.1	220.9	273.0	336.2	401.8	464.6	520.3	567.4
122.5°	139.6	152.0	168.4	190.7	223.5	270.4	327.7	388.0	444.8	496.5	540.1
125°	150.2	162.7	179.0	199.5	227.4	266.9	316.7	369.7	420.4	465.0	502.2
127.5°	160.0	172.6	188.3	206.8	231.9	265.2	307.0	353.7	398.9	439.2	473.0
130°	166.0	178.6	193.9	211.6	234.8	264.2	301.8	343.6	385.5	423.1	454.8
132.5°	171.6	183.8	198.8	216.1	237.1	263.7	296.9	334.4	372.8	407.9	438.1
135°	179.0	191.6	206.0	221.8	240.4	263.2	290.7	321.8	354.8	385.1	411.6
137.5°	185.6	197.1	211.0	226.1	242.6	262.2	285.2	310.4	337.5	363.5	386.5
140°	189.2	200.9	214.3	228.4	244.1	261.8	281.8	303.7	327.3	349.7	369.7
142.5°	193.0	203.9	217.0	230.6	245.2	261.1	278.8	297.3	317.7	337.0	354.4
145°	197.6	208.3	220.5	233.0	246.0	259.9	274.8	289.7	305.1	319.9	333.5
147.5°	203.0	212.1	223.2	234.5	246.0	258.2	270.9	283.5	295.6	307.7	317.2
150°	206.0	214.3	225.1	234.8	246.0	256.7	268.3	279.0	289.7	299.5	308.3
152.5°	209.0	217.0	226.2	235.6	244.9	254.9	265.4	274.9	284.1	292.8	300.1
155°	213.9	220.5	228.4	235.8	243.7	251.6	260.9	268.8	276.2	283.2	288.8
157.5°	218.2	223.2	229.5	236.3	242.1	248.7	255.8	262.3	268.5	273.9	278.3
160°	220.5	225.1	230.6	236.3	241.3	246.5	252.5	258.5	263.7	268.3	271.6
162.5°	222.3	226.2	231.1	235.9	239.9	244.3	249.2	254.1	258.4	262.8	265.6
165°	224.6	227.9	231.5	234.8	237.7	240.9	244.6	248.3	251.1	254.4	256.7
167.5°	226.7	228.8	231.5	234.1	235.4	237.5	240.3	243.3	245.4	247.3	249.0
170°	227.9	228.8	231.1	233.0	233.9	235.3	237.7	239.9	241.3	243.2	244.1
172.5°	228.6	229.2	231.1	232.6	232.8	233.4	235.1	237.0	238.0	239.5	240.0
175°	229.3	229.8	230.6	231.5	231.1	231.1	232.0	233.0	233.4	234.4	234.4
177.5°	229.8	229.8	230.1	230.8	230.1	229.8	230.1	230.5	230.8	231.2	231.2
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8



TEST NUMBER: P332248-930

CATALOG NUMBER: S123RDIP-S340D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	422.7	422.6	422.7	422.2	422.7	422.6	422.7	424.6	424.6	424.7	424.9
5°	393.4	393.2	392.6	390.9	392.6	393.2	393.4	394.0	395.5	398.1	397.4
7.5°	367.7	367.5	365.8	365.8	365.8	367.5	367.7	369.2	371.0	372.6	374.5
10°	352.5	352.7	350.4	349.1	350.4	352.7	352.5	353.8	356.4	357.7	359.0
12.5°	337.8	337.0	335.1	333.6	335.1	337.0	337.8	338.8	342.2	343.7	346.3
15°	318.4	316.4	311.9	312.3	311.9	316.4	318.4	317.6	321.0	322.9	323.7
17.5°	295.5	294.1	294.0	291.3	294.0	294.1	295.5	296.9	299.9	302.0	307.4
20°	282.1	281.1	281.5	278.8	281.5	281.1	282.1	285.1	287.0	289.7	294.1
22.5°	271.6	270.6	269.0	268.2	269.0	270.6	271.6	273.7	275.7	279.5	281.8
25°	256.2	254.7	253.2	254.1	253.2	254.7	256.2	257.4	261.1	262.9	266.3
27.5°	240.9	239.8	238.2	238.1	238.2	239.8	240.9	242.0	244.1	247.0	251.1
30°	231.1	230.0	229.3	228.3	229.3	230.0	231.1	232.1	234.2	237.3	240.3
32.5°	221.3	221.0	219.7	219.5	219.7	221.0	221.3	222.8	224.9	227.8	230.4
35°	208.4	207.2	206.8	207.0	206.8	207.2	208.4	209.1	211.0	213.7	216.1
37.5°	196.1	194.6	193.9	193.2	193.9	194.6	196.1	196.2	198.1	199.9	203.3
40°	187.3	185.8	185.4	185.0	185.4	185.8	187.3	187.1	189.1	190.5	193.6
42.5°	177.4	176.8	176.6	175.9	176.6	176.8	177.4	178.5	179.6	181.6	183.8
45°	164.0	163.7	162.6	163.0	162.6	163.7	164.0	164.5	166.6	168.0	170.0
47.5°	149.7	148.9	148.1	148.6	148.1	148.9	149.7	150.5	151.9	153.5	156.3
50°	140.0	139.6	137.9	138.3	137.9	139.6	140.0	140.7	141.7	143.8	146.3
52.5°	130.3	128.8	128.2	127.9	128.2	128.8	130.3	131.0	132.2	134.5	136.4
55°	114.1	112.4	111.7	111.3	111.7	112.4	114.1	115.5	117.0	119.7	121.6
57.5°	98.3	97.9	97.3	97.7	97.3	97.9	98.3	100.5	102.1	104.1	106.5
60°	89.1	89.1	89.1	88.9	89.1	89.1	89.1	91.0	92.3	94.4	96.9
62.5°	81.9	81.4	81.4	81.6	81.4	81.4	81.9	82.8	84.1	85.4	87.6
65°	71.0	70.8	70.1	69.9	70.1	70.8	71.0	71.6	72.7	73.7	75.3
67.5°	60.7	60.1	59.8	59.6	59.8	60.1	60.7	61.2	62.0	63.2	64.0
70°	53.0	52.6	51.4	51.7	51.4	52.6	53.0	54.0	54.7	56.3	57.0
72.5°	44.7	44.3	44.0	43.8	44.0	44.3	44.7	45.6	46.3	48.0	49.2
75°	35.3	35.1	35.0	35.7	35.0	35.1	35.3	35.5	35.7	36.3	36.9
77.5°	28.3	28.3	28.5	28.1	28.5	28.3	28.3	28.3	28.3	28.6	28.7
80°	23.7	23.7	23.6	23.6	23.6	23.7	23.7	23.7	23.7	23.7	23.6
82.5°	19.0	19.2	19.3	19.0	19.3	19.2	19.0	19.3	19.5	19.2	19.3
85°	12.6	12.3	12.7	12.6	12.7	12.3	12.6	12.6	12.1	12.6	12.3
87.5°	8.2	8.0	8.1	8.2	8.1	8.0	8.2	8.0	7.8	7.7	7.5
90°	13.0	13.5	13.9	13.5	13.9	13.5	13.0	13.5	12.6	12.1	11.7
92.5°	24.2	22.7	23.2	22.4	23.2	22.7	24.2	25.0	27.5	31.1	39.1
95°	63.3	59.0	55.8	54.0	55.8	59.0	63.3	72.1	88.8	113.5	167.4
97.5°	184.3	163.4	150.8	146.8	150.8	163.4	184.3	218.7	274.3	334.3	417.4
100°	343.2	309.2	291.1	291.6	291.1	309.2	343.2	390.1	456.2	510.6	548.3
102.5°	480.5	453.6	438.4	427.7	438.4	453.6	480.5	517.0	558.9	590.6	591.8
105°	626.4	608.7	593.9	591.5	593.9	608.7	626.4	647.8	659.9	651.0	604.5
107.5°	701.1	695.1	690.1	685.8	690.1	695.1	701.1	700.7	684.1	643.4	567.9
110°	722.7	726.4	725.5	724.5	725.5	726.4	722.7	709.6	677.1	618.5	532.9



TEST NUMBER: P332248-930

CATALOG NUMBER: S123RDIP-S340D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	717.1	728.6	732.1	732.3	732.1	728.6	717.1	693.2	651.4	585.7	498.3
115°	687.3	707.8	717.1	719.4	717.1	707.8	687.3	652.4	601.8	533.4	452.5
117.5°	638.3	661.7	675.1	678.2	675.1	661.7	638.3	601.9	550.5	489.1	419.2
120°	604.1	630.1	641.2	644.1	641.2	630.1	604.1	567.4	520.3	464.6	401.8
122.5°	572.8	596.2	608.5	612.0	608.5	596.2	572.8	540.1	496.5	444.8	388.0
125°	532.0	552.4	564.1	567.4	564.1	552.4	532.0	502.2	465.0	420.4	369.7
127.5°	499.5	517.0	527.5	530.5	527.5	517.0	499.5	473.0	439.2	398.9	353.7
130°	479.5	496.2	506.0	509.6	506.0	496.2	479.5	454.8	423.1	385.5	343.6
132.5°	461.2	477.9	486.6	489.2	486.6	477.9	461.2	438.1	407.9	372.8	334.4
135°	434.3	448.3	456.6	459.9	456.6	448.3	434.3	411.6	385.1	354.8	321.8
137.5°	405.6	419.7	426.8	428.9	426.8	419.7	405.6	386.5	363.5	337.5	310.4
140°	387.3	400.4	407.8	407.3	407.8	400.4	387.3	369.7	349.7	327.3	303.7
142.5°	369.5	381.1	387.8	387.3	387.8	381.1	369.5	354.4	337.0	317.7	297.3
145°	345.0	354.8	358.6	359.5	358.6	354.8	345.0	333.5	319.9	305.1	289.7
147.5°	326.0	332.6	336.2	336.6	336.2	332.6	326.0	317.2	307.7	295.6	283.5
150°	315.3	320.4	323.2	323.2	323.2	320.4	315.3	308.3	299.5	289.7	279.0
152.5°	305.6	310.4	312.0	312.0	312.0	310.4	305.6	300.1	292.8	284.1	274.9
155°	292.9	296.7	297.6	298.1	297.6	296.7	292.9	288.8	283.2	276.2	268.8
157.5°	281.9	284.7	285.4	285.4	285.4	284.7	281.9	278.3	273.9	268.5	262.3
160°	274.8	277.6	277.6	277.1	277.6	277.6	274.8	271.6	268.3	263.7	258.5
162.5°	267.7	270.2	270.2	269.7	270.2	270.2	267.7	265.6	262.8	258.4	254.1
165°	258.5	260.4	259.9	259.9	259.9	260.4	258.5	256.7	254.4	251.1	248.3
167.5°	249.8	251.1	250.6	250.6	250.6	251.1	249.8	249.0	247.3	245.4	243.3
170°	244.6	245.6	245.1	245.1	245.1	245.6	244.6	244.1	243.2	241.3	239.9
172.5°	240.1	241.1	240.3	239.9	240.3	241.1	240.1	240.0	239.5	238.0	237.0
175°	234.4	234.8	234.4	233.9	234.4	234.8	234.4	234.4	234.4	233.4	233.0
177.5°	230.8	231.2	230.5	230.5	230.5	231.2	230.8	231.2	231.2	230.8	230.5
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8



TEST NUMBER: P332248-930

CATALOG NUMBER: S123RDIP-S340D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	423.5	425.7	427.8	429.7	432.8	434.1	436.1	436.9	439.1	442.5	445.2
5°	397.8	400.8	404.8	408.0	413.1	417.1	421.5	425.7	430.6	437.7	443.9
7.5°	375.9	378.9	383.7	389.7	395.3	401.0	407.0	412.7	419.7	429.8	439.8
10°	361.5	365.1	370.8	377.2	384.3	389.8	396.8	404.0	412.8	424.4	436.3
12.5°	349.0	351.7	358.3	364.4	372.4	379.4	386.3	394.8	404.7	417.0	431.5
15°	329.2	333.0	339.4	346.3	354.7	362.1	371.0	381.2	390.9	406.1	423.5
17.5°	309.2	315.0	321.8	329.5	335.7	345.9	355.6	366.1	378.1	394.1	413.4
20°	296.5	301.1	307.4	318.5	326.7	334.5	343.4	356.5	367.5	385.8	405.7
22.5°	285.7	289.0	296.1	305.3	314.9	323.8	333.0	345.4	359.1	376.3	397.9
25°	269.7	275.1	280.4	287.0	297.3	308.1	318.0	328.6	343.1	361.5	384.8
27.5°	254.1	258.9	264.2	272.3	280.1	290.2	300.6	312.7	328.2	347.7	371.5
30°	244.1	247.7	252.7	263.1	270.1	278.8	291.0	301.8	316.3	337.0	362.1
32.5°	233.7	238.4	243.9	251.8	260.6	268.8	279.9	291.6	306.4	326.8	352.5
35°	219.0	224.5	230.0	235.9	244.7	253.2	262.5	275.4	290.4	310.2	335.4
37.5°	205.5	209.9	214.3	221.7	229.9	238.1	246.8	259.5	273.6	295.0	318.1
40°	196.8	200.8	204.2	211.8	219.8	228.5	237.1	248.3	263.4	283.4	305.8
42.5°	187.4	191.0	195.7	201.9	210.5	217.8	226.4	237.0	251.3	271.6	291.2
45°	173.3	177.4	181.4	187.3	195.8	203.1	210.7	220.7	235.4	252.1	269.5
47.5°	158.5	162.7	167.3	173.0	180.4	187.8	195.3	204.2	217.6	234.0	245.8
50°	149.1	152.5	157.1	162.8	169.7	177.4	184.3	194.0	206.7	219.6	229.8
52.5°	139.4	142.5	147.7	153.7	160.0	166.8	174.1	182.4	193.9	206.0	214.2
55°	124.3	128.0	132.4	138.3	144.6	150.3	157.3	165.8	175.0	184.1	189.6
57.5°	110.1	113.2	116.9	122.9	128.4	135.2	141.5	148.1	156.6	163.5	167.1
60°	99.7	102.6	107.3	112.7	117.7	123.7	130.9	137.5	144.0	149.5	152.3
62.5°	90.0	93.3	97.4	102.3	107.9	113.5	119.8	125.4	131.1	135.8	137.8
65°	77.3	80.0	83.0	87.6	92.1	97.8	102.7	108.4	112.7	115.3	117.0
67.5°	65.8	67.5	69.8	72.9	77.4	82.3	87.1	91.6	95.1	96.9	98.4
70°	58.3	59.4	61.1	64.2	67.6	72.0	77.0	80.1	83.2	84.7	86.3
72.5°	50.9	52.3	53.9	56.3	59.1	62.3	65.9	69.8	71.5	73.3	74.2
75°	38.6	40.7	42.7	44.3	46.1	48.6	51.9	54.3	55.3	56.8	57.0
77.5°	29.1	29.6	31.1	32.9	34.6	36.4	38.4	40.6	41.1	41.8	42.4
80°	24.0	24.0	24.0	25.1	27.0	28.3	30.2	31.3	32.1	32.3	32.4
82.5°	19.2	19.2	19.1	19.3	20.0	20.7	22.4	23.7	24.4	24.2	23.8
85°	12.6	12.1	12.1	12.0	12.1	11.7	11.6	12.3	13.5	13.5	13.1
87.5°	7.4	7.3	7.2	6.8	6.4	6.0	5.3	5.2	5.0	5.4	5.1
90°	11.2	11.7	10.2	8.8	7.4	6.0	5.1	4.2	2.8	1.9	0.9
92.5°	54.0	71.5	78.7	59.0	39.1	26.9	20.0	16.1	12.5	8.6	5.8
95°	223.6	275.7	245.6	169.3	100.0	60.4	42.3	30.2	22.3	17.2	15.8
97.5°	457.2	427.4	312.8	185.7	107.6	69.9	50.2	38.3	31.5	27.5	27.0
100°	532.0	440.3	297.6	175.3	106.5	73.9	55.8	44.7	38.2	34.9	34.4
102.5°	535.7	416.2	275.3	166.4	107.9	78.8	62.1	52.1	46.0	43.0	42.2
105°	507.4	373.9	247.9	160.0	112.1	87.0	72.6	63.7	58.1	55.4	54.0
107.5°	457.7	336.5	230.4	159.5	119.7	97.7	84.3	76.0	70.5	67.8	66.4
110°	426.4	315.3	223.6	161.3	126.0	105.1	92.0	84.1	79.1	76.7	75.3



TEST NUMBER: P332248-930

CATALOG NUMBER: S123RDIP-S340D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	399.3	301.2	220.0	165.1	132.3	112.9	100.3	92.4	87.2	85.0	83.5
115°	366.5	286.0	218.6	171.1	142.8	125.1	112.5	104.6	100.0	97.2	95.3
117.5°	346.7	277.0	219.4	179.1	153.8	136.3	124.7	115.9	111.6	109.3	107.1
120°	336.2	273.0	220.9	185.1	160.9	144.1	132.6	123.7	119.0	116.8	115.4
122.5°	327.7	270.4	223.5	190.7	168.4	152.0	139.6	131.1	126.1	123.8	122.4
125°	316.7	266.9	227.4	199.5	179.0	162.7	150.2	141.4	136.2	133.5	132.6
127.5°	307.0	265.2	231.9	206.8	188.3	172.6	160.0	150.3	145.1	141.6	140.2
130°	301.8	264.2	234.8	211.6	193.9	178.6	166.0	156.2	150.7	146.5	145.1
132.5°	296.9	263.7	237.1	216.1	198.8	183.8	171.6	161.8	155.2	150.6	148.8
135°	290.7	263.2	240.4	221.8	206.0	191.6	179.0	169.3	162.3	157.2	155.3
137.5°	285.2	262.2	242.6	226.1	211.0	197.1	185.6	175.9	168.4	163.4	161.4
140°	281.8	261.8	244.1	228.4	214.3	200.9	189.2	179.9	172.5	167.9	165.6
142.5°	278.8	261.1	245.2	230.6	217.0	203.9	193.0	183.7	177.0	171.9	170.0
145°	274.8	259.9	246.0	233.0	220.5	208.3	197.6	189.7	182.8	178.6	177.2
147.5°	270.9	258.2	246.0	234.5	223.2	212.1	203.0	195.4	189.4	185.2	184.4
150°	268.3	256.7	246.0	234.8	225.1	214.3	206.0	199.5	193.5	189.7	189.2
152.5°	265.4	254.9	244.9	235.6	226.2	217.0	209.0	203.3	198.0	194.2	194.1
155°	260.9	251.6	243.7	235.8	228.4	220.5	213.9	208.8	204.2	201.4	201.4
157.5°	255.8	248.7	242.1	236.3	229.5	223.2	218.2	213.9	209.7	207.5	207.1
160°	252.5	246.5	241.3	236.3	230.6	225.1	220.5	217.2	213.4	211.6	211.6
162.5°	249.2	244.3	239.9	235.9	231.1	226.2	222.3	219.4	216.5	214.9	214.9
165°	244.6	240.9	237.7	234.8	231.5	227.9	224.6	222.7	220.5	219.5	220.0
167.5°	240.3	237.5	235.4	234.1	231.5	228.8	226.7	225.4	223.6	223.2	223.8
170°	237.7	235.3	233.9	233.0	231.1	228.8	227.9	226.9	225.5	225.1	226.0
172.5°	235.1	233.4	232.8	232.6	231.1	229.2	228.6	228.0	227.1	226.9	227.5
175°	232.0	231.1	231.1	231.5	230.6	229.8	229.3	229.3	228.4	228.8	229.3
177.5°	230.1	229.8	230.1	230.8	230.1	229.8	229.8	229.8	229.3	229.8	230.1
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8



TEST NUMBER: P332248-930

CATALOG NUMBER: S123RDIP-S340D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	446.1	447.8	450.0	453.1	455.6	457.7	458.1	458.8	460.3	462.8	464.8
5°	449.1	453.4	460.4	467.2	474.7	480.8	486.5	490.5	494.2	502.2	508.7
7.5°	448.1	457.9	468.9	481.1	493.6	505.6	516.7	526.8	536.7	548.4	561.6
10°	447.5	458.9	473.8	489.5	506.8	523.7	540.1	552.8	567.5	580.9	597.8
12.5°	444.7	461.1	478.7	498.9	520.2	539.6	561.2	578.7	595.7	614.9	634.5
15°	440.8	460.8	483.2	510.0	542.3	565.8	587.9	618.5	639.4	660.2	688.4
17.5°	434.0	458.4	486.3	521.1	548.0	579.8	612.9	637.1	665.2	694.6	720.1
20°	428.5	456.8	488.2	522.4	556.8	591.1	623.2	652.1	681.2	715.2	736.1
22.5°	423.1	451.0	483.6	519.9	556.8	593.1	629.4	663.3	696.0	730.3	757.0
25°	411.4	444.7	480.0	517.1	553.5	593.4	636.7	674.5	714.9	750.3	775.6
27.5°	399.7	430.2	465.3	502.9	543.4	590.5	641.5	684.4	725.0	750.3	758.2
30°	389.0	421.3	453.6	491.8	535.7	588.2	642.4	691.6	724.8	735.9	727.7
32.5°	378.2	407.5	439.4	478.6	525.1	582.6	643.6	687.4	707.4	699.0	665.7
35°	359.2	385.6	416.5	455.7	509.2	579.5	638.6	668.2	663.3	615.8	553.1
37.5°	338.8	360.4	389.0	429.9	492.8	567.2	617.0	621.4	578.6	505.7	433.3
40°	322.7	342.1	371.5	414.3	480.0	555.1	595.3	577.6	511.4	430.2	369.8
42.5°	307.0	323.4	351.8	397.9	467.8	538.4	563.0	524.5	448.0	371.3	316.3
45°	280.5	296.0	324.4	371.7	443.0	506.8	503.5	436.7	360.1	298.4	252.8
47.5°	255.4	268.9	295.6	343.9	413.8	459.3	429.1	357.9	293.0	243.4	210.9
50°	237.7	250.9	277.5	325.2	390.4	423.5	380.5	311.9	252.4	211.4	185.6
52.5°	220.6	233.6	257.9	304.4	362.1	382.0	335.7	272.1	222.5	187.1	164.9
55°	196.8	206.7	228.5	273.0	316.1	320.7	273.7	220.5	179.7	155.0	139.8
57.5°	172.5	181.0	202.6	238.0	268.2	265.9	221.4	175.4	147.9	129.6	118.5
60°	156.7	165.1	184.1	214.4	237.3	229.3	188.4	151.4	127.8	114.4	105.6
62.5°	141.9	148.5	166.3	188.5	204.9	195.8	161.1	130.4	111.7	100.4	93.4
65°	120.6	126.0	140.1	151.8	160.9	152.1	123.3	102.0	88.5	80.6	75.8
67.5°	100.4	103.7	112.7	116.9	123.4	113.7	92.7	78.4	70.8	64.1	60.7
70°	87.6	90.0	94.8	98.2	99.9	90.0	74.4	64.0	57.6	52.8	50.7
72.5°	74.8	77.0	77.9	80.7	79.8	70.6	59.8	51.5	46.9	43.7	41.0
75°	57.2	58.1	57.2	56.0	53.6	47.1	39.7	35.5	32.1	30.6	29.6
77.5°	41.7	41.3	40.1	38.3	34.1	30.0	26.0	24.6	23.2	22.3	22.0
80°	32.1	31.3	30.2	27.3	23.7	20.9	20.0	19.0	18.4	17.4	17.3
82.5°	23.9	23.4	21.5	19.2	16.6	15.2	14.5	14.1	13.5	13.0	13.0
85°	12.7	12.1	10.0	8.7	8.4	8.0	7.8	7.8	7.0	6.8	6.8
87.5°	4.5	3.8	3.9	3.6	3.8	3.8	4.2	4.2	4.3	4.3	4.2
90°	1.9	2.8	4.2	5.1	6.0	7.4	8.8	10.2	11.7	11.2	11.7
92.5°	8.6	12.5	16.1	20.0	26.9	39.1	59.0	78.7	71.5	54.0	39.1
95°	17.2	22.3	30.2	42.3	60.4	100.0	169.3	245.6	275.7	223.6	167.4
97.5°	27.5	31.5	38.3	50.2	69.9	107.6	185.7	312.8	427.4	457.2	417.4
100°	34.9	38.2	44.7	55.8	73.9	106.5	175.3	297.6	440.3	532.0	548.3
102.5°	43.0	46.0	52.1	62.1	78.8	107.9	166.4	275.3	416.2	535.7	591.8
105°	55.4	58.1	63.7	72.6	87.0	112.1	160.0	247.9	373.9	507.4	604.5
107.5°	67.8	70.5	76.0	84.3	97.7	119.7	159.5	230.4	336.5	457.7	567.9
110°	76.7	79.1	84.1	92.0	105.1	126.0	161.3	223.6	315.3	426.4	532.9



TEST NUMBER: P332248-930

CATALOG NUMBER: S123RDIP-S340D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	85.0	87.2	92.4	100.3	112.9	132.3	165.1	220.0	301.2	399.3	498.3
115°	97.2	100.0	104.6	112.5	125.1	142.8	171.1	218.6	286.0	366.5	452.5
117.5°	109.3	111.6	115.9	124.7	136.3	153.8	179.1	219.4	277.0	346.7	419.2
120°	116.8	119.0	123.7	132.6	144.1	160.9	185.1	220.9	273.0	336.2	401.8
122.5°	123.8	126.1	131.1	139.6	152.0	168.4	190.7	223.5	270.4	327.7	388.0
125°	133.5	136.2	141.4	150.2	162.7	179.0	199.5	227.4	266.9	316.7	369.7
127.5°	141.6	145.1	150.3	160.0	172.6	188.3	206.8	231.9	265.2	307.0	353.7
130°	146.5	150.7	156.2	166.0	178.6	193.9	211.6	234.8	264.2	301.8	343.6
132.5°	150.6	155.2	161.8	171.6	183.8	198.8	216.1	237.1	263.7	296.9	334.4
135°	157.2	162.3	169.3	179.0	191.6	206.0	221.8	240.4	263.2	290.7	321.8
137.5°	163.4	168.4	175.9	185.6	197.1	211.0	226.1	242.6	262.2	285.2	310.4
140°	167.9	172.5	179.9	189.2	200.9	214.3	228.4	244.1	261.8	281.8	303.7
142.5°	171.9	177.0	183.7	193.0	203.9	217.0	230.6	245.2	261.1	278.8	297.3
145°	178.6	182.8	189.7	197.6	208.3	220.5	233.0	246.0	259.9	274.8	289.7
147.5°	185.2	189.4	195.4	203.0	212.1	223.2	234.5	246.0	258.2	270.9	283.5
150°	189.7	193.5	199.5	206.0	214.3	225.1	234.8	246.0	256.7	268.3	279.0
152.5°	194.2	198.0	203.3	209.0	217.0	226.2	235.6	244.9	254.9	265.4	274.9
155°	201.4	204.2	208.8	213.9	220.5	228.4	235.8	243.7	251.6	260.9	268.8
157.5°	207.5	209.7	213.9	218.2	223.2	229.5	236.3	242.1	248.7	255.8	262.3
160°	211.6	213.4	217.2	220.5	225.1	230.6	236.3	241.3	246.5	252.5	258.5
162.5°	214.9	216.5	219.4	222.3	226.2	231.1	235.9	239.9	244.3	249.2	254.1
165°	219.5	220.5	222.7	224.6	227.9	231.5	234.8	237.7	240.9	244.6	248.3
167.5°	223.2	223.6	225.4	226.7	228.8	231.5	234.1	235.4	237.5	240.3	243.3
170°	225.1	225.5	226.9	227.9	228.8	231.1	233.0	233.9	235.3	237.7	239.9
172.5°	226.9	227.1	228.0	228.6	229.2	231.1	232.6	232.8	233.4	235.1	237.0
175°	228.8	228.4	229.3	229.3	229.8	230.6	231.5	231.1	231.1	232.0	233.0
177.5°	229.8	229.3	229.8	229.8	229.8	230.1	230.8	230.1	229.8	230.1	230.5
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8



TEST NUMBER: P332248-930

CATALOG NUMBER: S123RDIP-S340D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	468.1	468.1	468.6	470.9	471.2	473.2	472.6
5°	514.4	518.0	519.3	525.1	528.4	529.9	526.9
7.5°	571.0	581.2	586.0	592.1	597.3	598.9	594.8
10°	612.4	623.1	631.9	637.5	642.6	646.0	650.4
12.5°	652.3	665.4	673.9	681.7	687.0	691.3	692.0
15°	695.8	715.5	730.5	741.6	747.1	749.9	748.8
17.5°	739.6	757.9	768.6	779.8	787.4	787.8	788.1
20°	764.3	782.2	794.6	802.9	811.5	811.1	813.0
22.5°	780.9	795.0	804.5	810.5	813.4	812.0	812.4
25°	788.6	792.9	791.2	781.5	778.9	770.1	771.6
27.5°	748.7	729.0	708.5	682.2	661.5	644.9	645.7
30°	694.5	659.5	619.6	586.2	556.2	547.8	529.9
32.5°	618.6	566.2	519.5	488.3	462.6	455.6	440.0
35°	490.1	439.1	391.1	362.2	350.8	334.8	334.7
37.5°	380.9	336.1	310.7	289.0	277.7	268.0	267.1
40°	320.4	285.5	266.3	250.7	239.5	232.3	230.6
42.5°	278.2	250.0	232.0	222.3	213.7	209.9	207.2
45°	227.1	208.1	195.7	186.9	183.0	180.1	178.6
47.5°	190.0	177.3	168.8	162.9	159.7	156.7	157.5
50°	169.8	159.4	153.1	147.6	145.1	143.0	143.2
52.5°	153.5	144.1	139.1	135.1	132.1	130.5	129.9
55°	130.3	124.4	119.3	116.4	114.7	112.7	112.1
57.5°	111.1	106.6	102.4	99.2	98.7	96.8	97.0
60°	98.4	94.6	91.2	89.4	88.1	86.4	87.0
62.5°	87.9	84.7	81.6	80.2	78.8	77.6	77.9
65°	72.0	69.0	67.0	66.3	65.7	65.1	64.6
67.5°	57.4	55.5	54.3	52.7	51.5	51.4	50.8
70°	48.3	45.7	43.7	41.6	41.0	40.8	41.0
72.5°	38.6	37.1	36.5	35.5	35.4	34.9	35.2
75°	29.0	28.5	28.1	27.3	27.3	27.3	27.3
77.5°	21.4	21.1	20.9	20.7	20.5	20.2	20.2
80°	16.7	16.6	16.1	16.1	16.0	16.1	16.0
82.5°	12.6	12.6	12.2	12.2	12.0	11.9	12.0
85°	6.4	6.3	6.7	6.3	6.4	6.1	6.4
87.5°	4.2	4.3	4.4	4.2	4.2	4.6	4.2
90°	12.1	12.6	13.5	13.0	13.5	13.9	13.5
92.5°	31.1	27.5	25.0	24.2	22.7	23.2	22.4
95°	113.5	88.8	72.1	63.3	59.0	55.8	54.0
97.5°	334.3	274.3	218.7	184.3	163.4	150.8	146.8
100°	510.6	456.2	390.1	343.2	309.2	291.1	291.6
102.5°	590.6	558.9	517.0	480.5	453.6	438.4	427.7
105°	651.0	659.9	647.8	626.4	608.7	593.9	591.5
107.5°	643.4	684.1	700.7	701.1	695.1	690.1	685.8
110°	618.5	677.1	709.6	722.7	726.4	725.5	724.5



TEST NUMBER: P332248-930

CATALOG NUMBER: S123RDIP-S340D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	585.7	651.4	693.2	717.1	728.6	732.1	732.3
115°	533.4	601.8	652.4	687.3	707.8	717.1	719.4
117.5°	489.1	550.5	601.9	638.3	661.7	675.1	678.2
120°	464.6	520.3	567.4	604.1	630.1	641.2	644.1
122.5°	444.8	496.5	540.1	572.8	596.2	608.5	612.0
125°	420.4	465.0	502.2	532.0	552.4	564.1	567.4
127.5°	398.9	439.2	473.0	499.5	517.0	527.5	530.5
130°	385.5	423.1	454.8	479.5	496.2	506.0	509.6
132.5°	372.8	407.9	438.1	461.2	477.9	486.6	489.2
135°	354.8	385.1	411.6	434.3	448.3	456.6	459.9
137.5°	337.5	363.5	386.5	405.6	419.7	426.8	428.9
140°	327.3	349.7	369.7	387.3	400.4	407.8	407.3
142.5°	317.7	337.0	354.4	369.5	381.1	387.8	387.3
145°	305.1	319.9	333.5	345.0	354.8	358.6	359.5
147.5°	295.6	307.7	317.2	326.0	332.6	336.2	336.6
150°	289.7	299.5	308.3	315.3	320.4	323.2	323.2
152.5°	284.1	292.8	300.1	305.6	310.4	312.0	312.0
155°	276.2	283.2	288.8	292.9	296.7	297.6	298.1
157.5°	268.5	273.9	278.3	281.9	284.7	285.4	285.4
160°	263.7	268.3	271.6	274.8	277.6	277.6	277.1
162.5°	258.4	262.8	265.6	267.7	270.2	270.2	269.7
165°	251.1	254.4	256.7	258.5	260.4	259.9	259.9
167.5°	245.4	247.3	249.0	249.8	251.1	250.6	250.6
170°	241.3	243.2	244.1	244.6	245.6	245.1	245.1
172.5°	238.0	239.5	240.0	240.1	241.1	240.3	239.9
175°	233.4	234.4	234.4	234.4	234.8	234.4	233.9
177.5°	230.8	231.2	231.2	230.8	231.2	230.5	230.5
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8

(END OF REPORT)