

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332253-930

Luminaire Tested: **S123RDIP-S340D805U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332253-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D805U930-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3355.4 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332253-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332253-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	41	41	41	33
1	94	90	87	83	85	82	78	76	65	63	61	50	49	48	36	36	35	29
2	86	79	73	69	78	72	67	63	58	54	51	45	42	40	32	31	30	25
3	79	70	63	58	71	63	58	53	51	47	44	40	37	35	29	27	26	21
4	72	62	55	49	65	56	50	45	46	41	37	36	32	30	26	24	23	19
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16
6	61	50	42	36	55	45	39	34	37	32	28	29	26	23	22	19	18	15
7	57	45	37	32	51	41	34	30	33	28	25	26	23	20	20	18	16	13
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14	12
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4776	4776	4776	4776
5°	5693	4796	4224	4796
10°	7109	4769	3816	4769
15°	8344	4719	3480	4719
20°	9313	4647	3194	4647
25°	9164	4570	3018	4570
30°	6586	4501	2838	4501
35°	4398	4407	2720	4407
40°	3240	4297	2599	4297
45°	2719	4102	2481	4102
50°	2398	3848	2316	3848
55°	2104	3558	2089	3558
60°	1873	3279	1914	3279
65°	1645	2980	1780	2980
70°	1290	2716	1627	2716
75°	1135	2371	1485	2371
80°	992	2008	1463	2008
85°	790	1618	1556	1618



TEST NUMBER: P332253-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.6	1.3
10°-20°	136.3	4.1
20°-30°	214.2	6.4
30°-40°	223.4	6.7
40°-50°	191.2	5.7
50°-60°	145.7	4.3
60°-70°	93.4	2.8
70°-80°	44.9	1.3
80°-90°	14.3	0.4
90°-100°	52.9	1.6
100°-110°	158.2	4.7
110°-120°	269.1	8.0
120°-130°	354.0	10.5
130°-140°	397.9	11.9
140°-150°	391.1	11.7
150°-160°	329.2	9.8
160°-170°	219.2	6.5
170°-180°	76.7	2.3
0°-30°	394.1	11.7
0°-40°	617.6	18.4
0°-60°	954.5	28.4
0°-90°	1107.2	33.0
90°-120°	480.2	14.3
90°-150°	1623.1	48.4
90°-180°	2248.0	67.0
0°-180°	3355.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	444	444	444	444	444	
5°	527	444	391	444	527	54
15°	749	424	312	424	749	212
25°	772	385	254	385	772	332
35°	335	335	207	335	335	219
45°	179	270	163	270	179	140
55°	112	190	111	190	112	101
65°	65	117	70	117	65	64
75°	27	57	36	57	27	29
85°	6	13	13	13	6	8
90°	19	1	19	1	19	10
95°	50	38	50	38	50	51
105°	152	143	152	143	152	161
115°	272	271	272	271	272	269
125°	392	396	392	396	392	350
135°	514	514	514	514	514	395
145°	624	624	624	624	624	390
155°	713	714	713	714	713	328
165°	776	778	776	778	776	219
175°	806	810	806	810	806	77
180°	812	812	812	812	812	



TEST NUMBER: P332253-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	472.6	473.2	471.2	470.9	468.6	468.1	468.1	464.8	462.8	460.3	458.8
5°	526.9	529.9	528.4	525.1	519.3	518.0	514.4	508.7	502.2	494.2	490.5
7.5°	594.8	598.9	597.3	592.1	586.0	581.2	571.0	561.6	548.4	536.7	526.8
10°	650.4	646.0	642.6	637.5	631.9	623.1	612.4	597.8	580.9	567.5	552.8
12.5°	692.0	691.3	687.0	681.7	673.9	665.4	652.3	634.5	614.9	595.7	578.7
15°	748.8	749.9	747.1	741.6	730.5	715.5	695.8	688.4	660.2	639.4	618.5
17.5°	788.1	787.8	787.4	779.8	768.6	757.9	739.6	720.1	694.6	665.2	637.1
20°	813.0	811.1	811.5	802.9	794.6	782.2	764.3	736.1	715.2	681.2	652.1
22.5°	812.4	812.0	813.4	810.5	804.5	795.0	780.9	757.0	730.3	696.0	663.3
25°	771.6	770.1	778.9	781.5	791.2	792.9	788.6	775.6	750.3	714.9	674.5
27.5°	645.7	644.9	661.5	682.2	708.5	729.0	748.7	758.2	750.3	725.0	684.4
30°	529.9	547.8	556.2	586.2	619.6	659.5	694.5	727.7	735.9	724.8	691.6
32.5°	440.0	455.6	462.6	488.3	519.5	566.2	618.6	665.7	699.0	707.4	687.4
35°	334.7	334.8	350.8	362.2	391.1	439.1	490.1	553.1	615.8	663.3	668.2
37.5°	267.1	268.0	277.7	289.0	310.7	336.1	380.9	433.3	505.7	578.6	621.4
40°	230.6	232.3	239.5	250.7	266.3	285.5	320.4	369.8	430.2	511.4	577.6
42.5°	207.2	209.9	213.7	222.3	232.0	250.0	278.2	316.3	371.3	448.0	524.5
45°	178.6	180.1	183.0	186.9	195.7	208.1	227.1	252.8	298.4	360.1	436.7
47.5°	157.5	156.7	159.7	162.9	168.8	177.3	190.0	210.9	243.4	293.0	357.9
50°	143.2	143.0	145.1	147.6	153.1	159.4	169.8	185.6	211.4	252.4	311.9
52.5°	129.9	130.5	132.1	135.1	139.1	144.1	153.5	164.9	187.1	222.5	272.1
55°	112.1	112.7	114.7	116.4	119.3	124.4	130.3	139.8	155.0	179.7	220.5
57.5°	97.0	96.8	98.7	99.2	102.4	106.6	111.1	118.5	129.6	147.9	175.4
60°	87.0	86.4	88.1	89.4	91.2	94.6	98.4	105.6	114.4	127.8	151.4
62.5°	77.9	77.6	78.8	80.2	81.6	84.7	87.9	93.4	100.4	111.7	130.4
65°	64.6	65.1	65.7	66.3	67.0	69.0	72.0	75.8	80.6	88.5	102.0
67.5°	50.8	51.4	51.5	52.7	54.3	55.5	57.4	60.7	64.1	70.8	78.4
70°	41.0	40.8	41.0	41.6	43.7	45.7	48.3	50.7	52.8	57.6	64.0
72.5°	35.2	34.9	35.4	35.5	36.5	37.1	38.6	41.0	43.7	46.9	51.5
75°	27.3	27.3	27.3	27.3	28.1	28.5	29.0	29.6	30.6	32.1	35.5
77.5°	20.2	20.2	20.5	20.7	20.9	21.1	21.4	22.0	22.3	23.2	24.6
80°	16.0	16.1	16.0	16.1	16.1	16.6	16.7	17.3	17.4	18.4	19.0
82.5°	12.0	11.9	12.0	12.2	12.2	12.6	12.6	13.0	13.0	13.5	14.1
85°	6.4	6.1	6.4	6.3	6.7	6.3	6.4	6.8	6.8	7.0	7.8
87.5°	5.4	5.6	5.2	5.3	5.3	5.3	5.2	5.1	5.3	5.1	4.8
90°	19.2	18.8	18.6	18.3	18.0	17.5	17.0	16.5	15.9	15.3	13.5
92.5°	25.8	25.9	26.1	26.3	26.4	26.3	25.8	25.4	24.9	24.5	23.4
95°	49.7	49.7	49.7	49.7	49.7	49.4	48.8	48.3	47.8	47.2	46.1
97.5°	76.5	76.6	76.6	76.6	76.7	76.4	75.7	75.1	74.4	73.8	73.0
100°	96.9	96.6	96.3	96.0	95.8	95.4	95.0	94.6	94.2	93.7	93.0
102.5°	117.8	117.9	117.9	118.0	118.1	117.8	117.4	117.0	116.6	116.2	115.2
105°	151.7	151.4	151.2	150.8	150.6	150.4	150.4	150.4	150.4	150.4	149.2
107.5°	187.0	187.2	187.4	187.5	187.7	187.6	187.1	186.6	186.2	185.7	185.2
110°	211.0	211.2	211.6	211.8	212.1	212.0	211.4	210.8	210.3	209.7	209.5



TEST NUMBER: P332253-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	236.5	236.5	236.6	236.7	236.7	236.4	235.7	235.1	234.4	233.7	233.7
115°	271.6	271.7	271.8	272.0	272.1	272.1	272.0	271.8	271.7	271.6	271.8
117.5°	307.1	307.5	307.9	308.3	308.7	308.9	308.9	309.0	309.0	309.0	309.4
120°	332.1	332.4	332.6	333.0	333.2	333.5	333.6	333.7	333.9	334.0	334.8
122.5°	356.0	356.4	356.9	357.3	357.7	358.1	358.4	358.8	359.1	359.5	359.9
125°	392.0	392.6	393.1	393.7	394.3	394.8	395.4	396.0	396.6	397.1	397.4
127.5°	427.9	428.5	429.2	429.8	430.5	431.2	431.9	432.8	433.6	434.3	434.6
130°	451.3	452.3	453.3	454.3	455.3	456.1	456.6	457.2	457.7	458.3	458.8
132.5°	475.8	476.5	477.3	478.1	478.8	479.6	480.2	480.9	481.6	482.2	482.6
135°	513.8	514.0	514.4	514.6	514.9	515.4	515.9	516.5	517.1	517.6	517.7
137.5°	547.3	547.9	548.4	548.9	549.4	550.0	550.7	551.2	551.8	552.4	552.0
140°	569.2	570.2	571.2	572.2	573.2	573.7	573.9	574.1	574.2	574.3	574.2
142.5°	591.7	592.4	593.2	593.9	594.8	595.2	595.3	595.5	595.6	595.7	595.5
145°	624.0	624.6	625.2	625.7	626.3	626.6	626.8	627.0	627.1	627.2	626.8
147.5°	652.9	653.7	654.5	655.4	656.2	656.7	656.7	656.7	656.7	656.7	656.3
150°	671.2	672.1	672.9	673.8	674.7	675.1	675.1	675.1	675.1	675.1	674.7
152.5°	689.1	689.8	690.6	691.3	692.0	692.3	692.0	691.8	691.6	691.4	691.2
155°	713.3	714.3	715.3	716.2	717.2	717.5	716.9	716.3	715.8	715.2	715.1
157.5°	735.3	736.1	736.9	737.8	738.5	738.6	738.0	737.4	736.9	736.2	736.1
160°	749.6	750.2	750.7	751.3	751.9	751.8	751.1	750.4	749.7	749.0	749.0
162.5°	760.3	761.2	762.1	763.0	763.9	764.1	763.4	762.6	761.9	761.2	761.1
165°	775.8	776.7	777.7	778.8	779.8	779.8	778.9	778.1	777.2	776.4	776.4
167.5°	788.9	789.8	790.7	791.5	792.4	792.4	791.5	790.7	789.8	788.9	788.8
170°	795.5	796.5	797.5	798.5	799.5	799.5	798.5	797.5	796.5	795.5	795.5
172.5°	800.6	801.6	802.6	803.6	804.6	804.6	803.8	802.9	802.0	801.1	801.1
175°	806.3	807.3	808.4	809.3	810.3	810.4	809.5	808.7	807.9	807.0	807.0
177.5°	809.4	810.2	811.0	811.8	812.6	812.6	812.0	811.3	810.6	809.9	809.9
180°	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5



TEST NUMBER: P332253-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	458.1	457.7	455.6	453.1	450.0	447.8	446.1	445.2	442.5	439.1	436.9
5°	486.5	480.8	474.7	467.2	460.4	453.4	449.1	443.9	437.7	430.6	425.7
7.5°	516.7	505.6	493.6	481.1	468.9	457.9	448.1	439.8	429.8	419.7	412.7
10°	540.1	523.7	506.8	489.5	473.8	458.9	447.5	436.3	424.4	412.8	404.0
12.5°	561.2	539.6	520.2	498.9	478.7	461.1	444.7	431.5	417.0	404.7	394.8
15°	587.9	565.8	542.3	510.0	483.2	460.8	440.8	423.5	406.1	390.9	381.2
17.5°	612.9	579.8	548.0	521.1	486.3	458.4	434.0	413.4	394.1	378.1	366.1
20°	623.2	591.1	556.8	522.4	488.2	456.8	428.5	405.7	385.8	367.5	356.5
22.5°	629.4	593.1	556.8	519.9	483.6	451.0	423.1	397.9	376.3	359.1	345.4
25°	636.7	593.4	553.5	517.1	480.0	444.7	411.4	384.8	361.5	343.1	328.6
27.5°	641.5	590.5	543.4	502.9	465.3	430.2	399.7	371.5	347.7	328.2	312.7
30°	642.4	588.2	535.7	491.8	453.6	421.3	389.0	362.1	337.0	316.3	301.8
32.5°	643.6	582.6	525.1	478.6	439.4	407.5	378.2	352.5	326.8	306.4	291.6
35°	638.6	579.5	509.2	455.7	416.5	385.6	359.2	335.4	310.2	290.4	275.4
37.5°	617.0	567.2	492.8	429.9	389.0	360.4	338.8	318.1	295.0	273.6	259.5
40°	595.3	555.1	480.0	414.3	371.5	342.1	322.7	305.8	283.4	263.4	248.3
42.5°	563.0	538.4	467.8	397.9	351.8	323.4	307.0	291.2	271.6	251.3	237.0
45°	503.5	506.8	443.0	371.7	324.4	296.0	280.5	269.5	252.1	235.4	220.7
47.5°	429.1	459.3	413.8	343.9	295.6	268.9	255.4	245.8	234.0	217.6	204.2
50°	380.5	423.5	390.4	325.2	277.5	250.9	237.7	229.8	219.6	206.7	194.0
52.5°	335.7	382.0	362.1	304.4	257.9	233.6	220.6	214.2	206.0	193.9	182.4
55°	273.7	320.7	316.1	273.0	228.5	206.7	196.8	189.6	184.1	175.0	165.8
57.5°	221.4	265.9	268.2	238.0	202.6	181.0	172.5	167.1	163.5	156.6	148.1
60°	188.4	229.3	237.3	214.4	184.1	165.1	156.7	152.3	149.5	144.0	137.5
62.5°	161.1	195.8	204.9	188.5	166.3	148.5	141.9	137.8	135.8	131.1	125.4
65°	123.3	152.1	160.9	151.8	140.1	126.0	120.6	117.0	115.3	112.7	108.4
67.5°	92.7	113.7	123.4	116.9	112.7	103.7	100.4	98.4	96.9	95.1	91.6
70°	74.4	90.0	99.9	98.2	94.8	90.0	87.6	86.3	84.7	83.2	80.1
72.5°	59.8	70.6	79.8	80.7	77.9	77.0	74.8	74.2	73.3	71.5	69.8
75°	39.7	47.1	53.6	56.0	57.2	58.1	57.2	57.0	56.8	55.3	54.3
77.5°	26.0	30.0	34.1	38.3	40.1	41.3	41.7	42.4	41.8	41.1	40.6
80°	20.0	20.9	23.7	27.3	30.2	31.3	32.1	32.4	32.3	32.1	31.3
82.5°	14.5	15.2	16.6	19.2	21.5	23.4	23.9	23.8	24.2	24.4	23.7
85°	7.8	8.0	8.4	8.7	10.0	12.1	12.7	13.1	13.5	13.5	12.3
87.5°	4.7	4.2	4.2	3.8	4.0	3.9	4.5	5.0	5.5	5.1	5.4
90°	11.6	9.8	7.9	6.3	4.9	3.5	2.0	0.7	2.0	3.5	4.9
92.5°	22.4	21.4	20.3	19.2	18.3	17.4	16.4	15.4	16.4	17.4	18.3
95°	44.9	43.8	42.6	41.6	40.6	39.6	38.6	37.6	38.6	39.6	40.6
97.5°	72.2	71.3	70.5	69.8	69.0	68.2	67.5	66.8	67.5	68.2	69.0
100°	92.3	91.6	90.9	90.1	89.3	88.4	87.6	86.7	87.6	88.4	89.3
102.5°	114.3	113.3	112.4	111.7	111.2	110.6	110.1	109.7	110.1	110.6	111.2
105°	147.9	146.6	145.4	144.6	144.3	144.0	143.7	143.4	143.7	144.0	144.3
107.5°	184.7	184.3	183.7	183.4	183.2	183.0	182.9	182.7	182.9	183.0	183.2
110°	209.1	208.9	208.6	208.3	208.0	207.7	207.4	207.2	207.4	207.7	208.0



TEST NUMBER: P332253-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	233.6	233.5	233.4	233.3	233.2	233.0	232.8	232.7	232.8	233.0	233.2
115°	272.1	272.4	272.7	272.6	272.1	271.7	271.3	270.9	271.3	271.7	272.1
117.5°	309.7	310.1	310.5	310.5	310.2	310.0	309.7	309.4	309.7	310.0	310.2
120°	335.4	336.1	336.9	336.8	335.9	335.1	334.2	333.4	334.2	335.1	335.9
122.5°	360.3	360.6	361.0	360.9	360.2	359.6	359.0	358.4	359.0	359.6	360.2
125°	397.7	397.9	398.3	398.2	397.8	397.3	396.9	396.5	396.9	397.3	397.8
127.5°	435.0	435.3	435.6	435.3	434.4	433.5	432.6	431.7	432.6	433.5	434.4
130°	459.2	459.6	460.0	459.7	458.5	457.4	456.2	455.1	456.2	457.4	458.5
132.5°	482.9	483.2	483.6	483.1	482.0	480.9	479.7	478.6	479.7	480.9	482.0
135°	517.9	518.0	518.2	517.8	517.0	516.1	515.3	514.4	515.3	516.1	517.0
137.5°	551.6	551.3	550.9	550.4	549.7	548.9	548.3	547.6	548.3	548.9	549.7
140°	574.1	573.9	573.7	573.3	572.7	571.9	571.2	570.5	571.2	571.9	572.7
142.5°	595.3	595.0	594.8	594.3	593.5	592.8	592.2	591.4	592.2	592.8	593.5
145°	626.4	626.0	625.5	625.2	624.9	624.6	624.4	624.0	624.4	624.6	624.9
147.5°	655.9	655.5	655.1	654.7	654.1	653.6	653.1	652.6	653.1	653.6	654.1
150°	674.5	674.2	673.9	673.6	673.4	673.0	672.8	672.5	672.8	673.0	673.4
152.5°	691.0	690.9	690.7	690.4	690.0	689.6	689.2	688.8	689.2	689.6	690.0
155°	714.9	714.8	714.6	714.5	714.5	714.5	714.5	714.5	714.5	714.5	714.5
157.5°	736.1	735.9	735.8	735.8	736.0	736.1	736.3	736.5	736.3	736.1	736.0
160°	749.0	749.0	749.0	749.1	749.4	749.7	750.0	750.2	750.0	749.7	749.4
162.5°	761.0	760.9	760.8	760.9	761.3	761.7	762.1	762.5	762.1	761.7	761.3
165°	776.4	776.4	776.4	776.6	777.1	777.5	777.9	778.3	777.9	777.5	777.1
167.5°	788.6	788.6	788.5	788.6	789.2	789.8	790.4	790.9	790.4	789.8	789.2
170°	795.5	795.5	795.5	795.8	796.4	797.0	797.5	798.1	797.5	797.0	796.4
172.5°	801.1	801.1	801.1	801.4	802.0	802.6	803.2	803.6	803.2	802.6	802.0
175°	807.0	807.0	807.0	807.3	807.9	808.5	808.9	809.5	808.9	808.5	807.9
177.5°	809.9	809.9	809.9	810.2	810.6	811.1	811.5	812.0	811.5	811.1	810.6
180°	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5



TEST NUMBER: P332253-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	436.1	434.1	432.8	429.7	427.8	425.7	423.5	424.9	424.7	424.6	424.6
5°	421.5	417.1	413.1	408.0	404.8	400.8	397.8	397.4	398.1	395.5	394.0
7.5°	407.0	401.0	395.3	389.7	383.7	378.9	375.9	374.5	372.6	371.0	369.2
10°	396.8	389.8	384.3	377.2	370.8	365.1	361.5	359.0	357.7	356.4	353.8
12.5°	386.3	379.4	372.4	364.4	358.3	351.7	349.0	346.3	343.7	342.2	338.8
15°	371.0	362.1	354.7	346.3	339.4	333.0	329.2	323.7	322.9	321.0	317.6
17.5°	355.6	345.9	335.7	329.5	321.8	315.0	309.2	307.4	302.0	299.9	296.9
20°	343.4	334.5	326.7	318.5	307.4	301.1	296.5	294.1	289.7	287.0	285.1
22.5°	333.0	323.8	314.9	305.3	296.1	289.0	285.7	281.8	279.5	275.7	273.7
25°	318.0	308.1	297.3	287.0	280.4	275.1	269.7	266.3	262.9	261.1	257.4
27.5°	300.6	290.2	280.1	272.3	264.2	258.9	254.1	251.1	247.0	244.1	242.0
30°	291.0	278.8	270.1	263.1	252.7	247.7	244.1	240.3	237.3	234.2	232.1
32.5°	279.9	268.8	260.6	251.8	243.9	238.4	233.7	230.4	227.8	224.9	222.8
35°	262.5	253.2	244.7	235.9	230.0	224.5	219.0	216.1	213.7	211.0	209.1
37.5°	246.8	238.1	229.9	221.7	214.3	209.9	205.5	203.3	199.9	198.1	196.2
40°	237.1	228.5	219.8	211.8	204.2	200.8	196.8	193.6	190.5	189.1	187.1
42.5°	226.4	217.8	210.5	201.9	195.7	191.0	187.4	183.8	181.6	179.6	178.5
45°	210.7	203.1	195.8	187.3	181.4	177.4	173.3	170.0	168.0	166.6	164.5
47.5°	195.3	187.8	180.4	173.0	167.3	162.7	158.5	156.3	153.5	151.9	150.5
50°	184.3	177.4	169.7	162.8	157.1	152.5	149.1	146.3	143.8	141.7	140.7
52.5°	174.1	166.8	160.0	153.7	147.7	142.5	139.4	136.4	134.5	132.2	131.0
55°	157.3	150.3	144.6	138.3	132.4	128.0	124.3	121.6	119.7	117.0	115.5
57.5°	141.5	135.2	128.4	122.9	116.9	113.2	110.1	106.5	104.1	102.1	100.5
60°	130.9	123.7	117.7	112.7	107.3	102.6	99.7	96.9	94.4	92.3	91.0
62.5°	119.8	113.5	107.9	102.3	97.4	93.3	90.0	87.6	85.4	84.1	82.8
65°	102.7	97.8	92.1	87.6	83.0	80.0	77.3	75.3	73.7	72.7	71.6
67.5°	87.1	82.3	77.4	72.9	69.8	67.5	65.8	64.0	63.2	62.0	61.2
70°	77.0	72.0	67.6	64.2	61.1	59.4	58.3	57.0	56.3	54.7	54.0
72.5°	65.9	62.3	59.1	56.3	53.9	52.3	50.9	49.2	48.0	46.3	45.6
75°	51.9	48.6	46.1	44.3	42.7	40.7	38.6	36.9	36.3	35.7	35.5
77.5°	38.4	36.4	34.6	32.9	31.1	29.6	29.1	28.7	28.6	28.3	28.3
80°	30.2	28.3	27.0	25.1	24.0	24.0	24.0	23.6	23.7	23.7	23.7
82.5°	22.4	20.7	20.0	19.3	19.1	19.2	19.2	19.3	19.2	19.5	19.3
85°	11.6	11.7	12.1	12.0	12.1	12.1	12.6	12.3	12.6	12.1	12.6
87.5°	5.5	6.3	6.8	7.3	7.8	8.1	8.3	8.5	8.7	8.8	8.9
90°	6.3	7.9	9.8	11.6	13.5	15.3	15.9	16.5	17.0	17.5	18.0
92.5°	19.2	20.3	21.4	22.4	23.4	24.5	24.9	25.4	25.8	26.3	26.4
95°	41.6	42.6	43.8	44.9	46.1	47.2	47.8	48.3	48.8	49.4	49.7
97.5°	69.8	70.5	71.3	72.2	73.0	73.8	74.4	75.1	75.7	76.4	76.7
100°	90.1	90.9	91.6	92.3	93.0	93.7	94.2	94.6	95.0	95.4	95.8
102.5°	111.7	112.4	113.3	114.3	115.2	116.2	116.6	117.0	117.4	117.8	118.1
105°	144.6	145.4	146.6	147.9	149.2	150.4	150.4	150.4	150.4	150.4	150.6
107.5°	183.4	183.7	184.3	184.7	185.2	185.7	186.2	186.6	187.1	187.6	187.7
110°	208.3	208.6	208.9	209.1	209.5	209.7	210.3	210.8	211.4	212.0	212.1



TEST NUMBER: P332253-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	233.3	233.4	233.5	233.6	233.7	233.7	234.4	235.1	235.7	236.4	236.7
115°	272.6	272.7	272.4	272.1	271.8	271.6	271.7	271.8	272.0	272.1	272.1
117.5°	310.5	310.5	310.1	309.7	309.4	309.0	309.0	309.0	308.9	308.9	308.7
120°	336.8	336.9	336.1	335.4	334.8	334.0	333.9	333.7	333.6	333.5	333.2
122.5°	360.9	361.0	360.6	360.3	359.9	359.5	359.1	358.8	358.4	358.1	357.7
125°	398.2	398.3	397.9	397.7	397.4	397.1	396.6	396.0	395.4	394.8	394.3
127.5°	435.3	435.6	435.3	435.0	434.6	434.3	433.6	432.8	431.9	431.2	430.5
130°	459.7	460.0	459.6	459.2	458.8	458.3	457.7	457.2	456.6	456.1	455.3
132.5°	483.1	483.6	483.2	482.9	482.6	482.2	481.6	480.9	480.2	479.6	478.8
135°	517.8	518.2	518.0	517.9	517.7	517.6	517.1	516.5	515.9	515.4	514.9
137.5°	550.4	550.9	551.3	551.6	552.0	552.4	551.8	551.2	550.7	550.0	549.4
140°	573.3	573.7	573.9	574.1	574.2	574.3	574.2	574.1	573.9	573.7	573.2
142.5°	594.3	594.8	595.0	595.3	595.5	595.7	595.6	595.5	595.3	595.2	594.8
145°	625.2	625.5	626.0	626.4	626.8	627.2	627.1	627.0	626.8	626.6	626.3
147.5°	654.7	655.1	655.5	655.9	656.3	656.7	656.7	656.7	656.7	656.7	656.2
150°	673.6	673.9	674.2	674.5	674.7	675.1	675.1	675.1	675.1	675.1	674.7
152.5°	690.4	690.7	690.9	691.0	691.2	691.4	691.6	691.8	692.0	692.3	692.0
155°	714.5	714.6	714.8	714.9	715.1	715.2	715.8	716.3	716.9	717.5	717.2
157.5°	735.8	735.8	735.9	736.1	736.1	736.2	736.9	737.4	738.0	738.6	738.5
160°	749.1	749.0	749.0	749.0	749.0	749.0	749.7	750.4	751.1	751.8	751.9
162.5°	760.9	760.8	760.9	761.0	761.1	761.2	761.9	762.6	763.4	764.1	763.9
165°	776.6	776.4	776.4	776.4	776.4	776.4	777.2	778.1	778.9	779.8	779.8
167.5°	788.6	788.5	788.6	788.6	788.8	788.9	789.8	790.7	791.5	792.4	792.4
170°	795.8	795.5	795.5	795.5	795.5	795.5	796.5	797.5	798.5	799.5	799.5
172.5°	801.4	801.1	801.1	801.1	801.1	801.1	802.0	802.9	803.8	804.6	804.6
175°	807.3	807.0	807.0	807.0	807.0	807.0	807.9	808.7	809.5	810.4	810.3
177.5°	810.2	809.9	809.9	809.9	809.9	809.9	810.6	811.3	812.0	812.6	812.6
180°	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5



TEST NUMBER: P332253-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	422.7	422.6	422.7	422.2	422.7	422.6	422.7	424.6	424.6	424.7	424.9
5°	393.4	393.2	392.6	390.9	392.6	393.2	393.4	394.0	395.5	398.1	397.4
7.5°	367.7	367.5	365.8	365.8	365.8	367.5	367.7	369.2	371.0	372.6	374.5
10°	352.5	352.7	350.4	349.1	350.4	352.7	352.5	353.8	356.4	357.7	359.0
12.5°	337.8	337.0	335.1	333.6	335.1	337.0	337.8	338.8	342.2	343.7	346.3
15°	318.4	316.4	311.9	312.3	311.9	316.4	318.4	317.6	321.0	322.9	323.7
17.5°	295.5	294.1	294.0	291.3	294.0	294.1	295.5	296.9	299.9	302.0	307.4
20°	282.1	281.1	281.5	278.8	281.5	281.1	282.1	285.1	287.0	289.7	294.1
22.5°	271.6	270.6	269.0	268.2	269.0	270.6	271.6	273.7	275.7	279.5	281.8
25°	256.2	254.7	253.2	254.1	253.2	254.7	256.2	257.4	261.1	262.9	266.3
27.5°	240.9	239.8	238.2	238.1	238.2	239.8	240.9	242.0	244.1	247.0	251.1
30°	231.1	230.0	229.3	228.3	229.3	230.0	231.1	232.1	234.2	237.3	240.3
32.5°	221.3	221.0	219.7	219.5	219.7	221.0	221.3	222.8	224.9	227.8	230.4
35°	208.4	207.2	206.8	207.0	206.8	207.2	208.4	209.1	211.0	213.7	216.1
37.5°	196.1	194.6	193.9	193.2	193.9	194.6	196.1	196.2	198.1	199.9	203.3
40°	187.3	185.8	185.4	185.0	185.4	185.8	187.3	187.1	189.1	190.5	193.6
42.5°	177.4	176.8	176.6	175.9	176.6	176.8	177.4	178.5	179.6	181.6	183.8
45°	164.0	163.7	162.6	163.0	162.6	163.7	164.0	164.5	166.6	168.0	170.0
47.5°	149.7	148.9	148.1	148.6	148.1	148.9	149.7	150.5	151.9	153.5	156.3
50°	140.0	139.6	137.9	138.3	137.9	139.6	140.0	140.7	141.7	143.8	146.3
52.5°	130.3	128.8	128.2	127.9	128.2	128.8	130.3	131.0	132.2	134.5	136.4
55°	114.1	112.4	111.7	111.3	111.7	112.4	114.1	115.5	117.0	119.7	121.6
57.5°	98.3	97.9	97.3	97.7	97.3	97.9	98.3	100.5	102.1	104.1	106.5
60°	89.1	89.1	89.1	88.9	89.1	89.1	89.1	91.0	92.3	94.4	96.9
62.5°	81.9	81.4	81.4	81.6	81.4	81.4	81.9	82.8	84.1	85.4	87.6
65°	71.0	70.8	70.1	69.9	70.1	70.8	71.0	71.6	72.7	73.7	75.3
67.5°	60.7	60.1	59.8	59.6	59.8	60.1	60.7	61.2	62.0	63.2	64.0
70°	53.0	52.6	51.4	51.7	51.4	52.6	53.0	54.0	54.7	56.3	57.0
72.5°	44.7	44.3	44.0	43.8	44.0	44.3	44.7	45.6	46.3	48.0	49.2
75°	35.3	35.1	35.0	35.7	35.0	35.1	35.3	35.5	35.7	36.3	36.9
77.5°	28.3	28.3	28.5	28.1	28.5	28.3	28.3	28.3	28.3	28.6	28.7
80°	23.7	23.7	23.6	23.6	23.6	23.7	23.7	23.7	23.7	23.7	23.6
82.5°	19.0	19.2	19.3	19.0	19.3	19.2	19.0	19.3	19.5	19.2	19.3
85°	12.6	12.3	12.7	12.6	12.7	12.3	12.6	12.6	12.1	12.6	12.3
87.5°	9.3	9.0	9.0	9.3	9.0	9.0	9.3	8.9	8.8	8.7	8.5
90°	18.3	18.6	18.8	19.2	18.8	18.6	18.3	18.0	17.5	17.0	16.5
92.5°	26.3	26.1	25.9	25.8	25.9	26.1	26.3	26.4	26.3	25.8	25.4
95°	49.7	49.7	49.7	49.7	49.7	49.7	49.7	49.7	49.4	48.8	48.3
97.5°	76.6	76.6	76.6	76.5	76.6	76.6	76.6	76.7	76.4	75.7	75.1
100°	96.0	96.3	96.6	96.9	96.6	96.3	96.0	95.8	95.4	95.0	94.6
102.5°	118.0	117.9	117.9	117.8	117.9	117.9	118.0	118.1	117.8	117.4	117.0
105°	150.8	151.2	151.4	151.7	151.4	151.2	150.8	150.6	150.4	150.4	150.4
107.5°	187.5	187.4	187.2	187.0	187.2	187.4	187.5	187.7	187.6	187.1	186.6
110°	211.8	211.6	211.2	211.0	211.2	211.6	211.8	212.1	212.0	211.4	210.8



TEST NUMBER: P332253-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	236.7	236.6	236.5	236.5	236.5	236.6	236.7	236.7	236.4	235.7	235.1
115°	272.0	271.8	271.7	271.6	271.7	271.8	272.0	272.1	272.1	272.0	271.8
117.5°	308.3	307.9	307.5	307.1	307.5	307.9	308.3	308.7	308.9	308.9	309.0
120°	333.0	332.6	332.4	332.1	332.4	332.6	333.0	333.2	333.5	333.6	333.7
122.5°	357.3	356.9	356.4	356.0	356.4	356.9	357.3	357.7	358.1	358.4	358.8
125°	393.7	393.1	392.6	392.0	392.6	393.1	393.7	394.3	394.8	395.4	396.0
127.5°	429.8	429.2	428.5	427.9	428.5	429.2	429.8	430.5	431.2	431.9	432.8
130°	454.3	453.3	452.3	451.3	452.3	453.3	454.3	455.3	456.1	456.6	457.2
132.5°	478.1	477.3	476.5	475.8	476.5	477.3	478.1	478.8	479.6	480.2	480.9
135°	514.6	514.4	514.0	513.8	514.0	514.4	514.6	514.9	515.4	515.9	516.5
137.5°	548.9	548.4	547.9	547.3	547.9	548.4	548.9	549.4	550.0	550.7	551.2
140°	572.2	571.2	570.2	569.2	570.2	571.2	572.2	573.2	573.7	573.9	574.1
142.5°	593.9	593.2	592.4	591.7	592.4	593.2	593.9	594.8	595.2	595.3	595.5
145°	625.7	625.2	624.6	624.0	624.6	625.2	625.7	626.3	626.6	626.8	627.0
147.5°	655.4	654.5	653.7	652.9	653.7	654.5	655.4	656.2	656.7	656.7	656.7
150°	673.8	672.9	672.1	671.2	672.1	672.9	673.8	674.7	675.1	675.1	675.1
152.5°	691.3	690.6	689.8	689.1	689.8	690.6	691.3	692.0	692.3	692.0	691.8
155°	716.2	715.3	714.3	713.3	714.3	715.3	716.2	717.2	717.5	716.9	716.3
157.5°	737.8	736.9	736.1	735.3	736.1	736.9	737.8	738.5	738.6	738.0	737.4
160°	751.3	750.7	750.2	749.6	750.2	750.7	751.3	751.9	751.8	751.1	750.4
162.5°	763.0	762.1	761.2	760.3	761.2	762.1	763.0	763.9	764.1	763.4	762.6
165°	778.8	777.7	776.7	775.8	776.7	777.7	778.8	779.8	779.8	778.9	778.1
167.5°	791.5	790.7	789.8	788.9	789.8	790.7	791.5	792.4	792.4	791.5	790.7
170°	798.5	797.5	796.5	795.5	796.5	797.5	798.5	799.5	799.5	798.5	797.5
172.5°	803.6	802.6	801.6	800.6	801.6	802.6	803.6	804.6	804.6	803.8	802.9
175°	809.3	808.4	807.3	806.3	807.3	808.4	809.3	810.3	810.4	809.5	808.7
177.5°	811.8	811.0	810.2	809.4	810.2	811.0	811.8	812.6	812.6	812.0	811.3
180°	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5



TEST NUMBER: P332253-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	423.5	425.7	427.8	429.7	432.8	434.1	436.1	436.9	439.1	442.5	445.2
5°	397.8	400.8	404.8	408.0	413.1	417.1	421.5	425.7	430.6	437.7	443.9
7.5°	375.9	378.9	383.7	389.7	395.3	401.0	407.0	412.7	419.7	429.8	439.8
10°	361.5	365.1	370.8	377.2	384.3	389.8	396.8	404.0	412.8	424.4	436.3
12.5°	349.0	351.7	358.3	364.4	372.4	379.4	386.3	394.8	404.7	417.0	431.5
15°	329.2	333.0	339.4	346.3	354.7	362.1	371.0	381.2	390.9	406.1	423.5
17.5°	309.2	315.0	321.8	329.5	335.7	345.9	355.6	366.1	378.1	394.1	413.4
20°	296.5	301.1	307.4	318.5	326.7	334.5	343.4	356.5	367.5	385.8	405.7
22.5°	285.7	289.0	296.1	305.3	314.9	323.8	333.0	345.4	359.1	376.3	397.9
25°	269.7	275.1	280.4	287.0	297.3	308.1	318.0	328.6	343.1	361.5	384.8
27.5°	254.1	258.9	264.2	272.3	280.1	290.2	300.6	312.7	328.2	347.7	371.5
30°	244.1	247.7	252.7	263.1	270.1	278.8	291.0	301.8	316.3	337.0	362.1
32.5°	233.7	238.4	243.9	251.8	260.6	268.8	279.9	291.6	306.4	326.8	352.5
35°	219.0	224.5	230.0	235.9	244.7	253.2	262.5	275.4	290.4	310.2	335.4
37.5°	205.5	209.9	214.3	221.7	229.9	238.1	246.8	259.5	273.6	295.0	318.1
40°	196.8	200.8	204.2	211.8	219.8	228.5	237.1	248.3	263.4	283.4	305.8
42.5°	187.4	191.0	195.7	201.9	210.5	217.8	226.4	237.0	251.3	271.6	291.2
45°	173.3	177.4	181.4	187.3	195.8	203.1	210.7	220.7	235.4	252.1	269.5
47.5°	158.5	162.7	167.3	173.0	180.4	187.8	195.3	204.2	217.6	234.0	245.8
50°	149.1	152.5	157.1	162.8	169.7	177.4	184.3	194.0	206.7	219.6	229.8
52.5°	139.4	142.5	147.7	153.7	160.0	166.8	174.1	182.4	193.9	206.0	214.2
55°	124.3	128.0	132.4	138.3	144.6	150.3	157.3	165.8	175.0	184.1	189.6
57.5°	110.1	113.2	116.9	122.9	128.4	135.2	141.5	148.1	156.6	163.5	167.1
60°	99.7	102.6	107.3	112.7	117.7	123.7	130.9	137.5	144.0	149.5	152.3
62.5°	90.0	93.3	97.4	102.3	107.9	113.5	119.8	125.4	131.1	135.8	137.8
65°	77.3	80.0	83.0	87.6	92.1	97.8	102.7	108.4	112.7	115.3	117.0
67.5°	65.8	67.5	69.8	72.9	77.4	82.3	87.1	91.6	95.1	96.9	98.4
70°	58.3	59.4	61.1	64.2	67.6	72.0	77.0	80.1	83.2	84.7	86.3
72.5°	50.9	52.3	53.9	56.3	59.1	62.3	65.9	69.8	71.5	73.3	74.2
75°	38.6	40.7	42.7	44.3	46.1	48.6	51.9	54.3	55.3	56.8	57.0
77.5°	29.1	29.6	31.1	32.9	34.6	36.4	38.4	40.6	41.1	41.8	42.4
80°	24.0	24.0	24.0	25.1	27.0	28.3	30.2	31.3	32.1	32.3	32.4
82.5°	19.2	19.2	19.1	19.3	20.0	20.7	22.4	23.7	24.4	24.2	23.8
85°	12.6	12.1	12.1	12.0	12.1	11.7	11.6	12.3	13.5	13.5	13.1
87.5°	8.3	8.1	7.8	7.3	6.8	6.3	5.5	5.4	5.1	5.5	5.0
90°	15.9	15.3	13.5	11.6	9.8	7.9	6.3	4.9	3.5	2.0	0.7
92.5°	24.9	24.5	23.4	22.4	21.4	20.3	19.2	18.3	17.4	16.4	15.4
95°	47.8	47.2	46.1	44.9	43.8	42.6	41.6	40.6	39.6	38.6	37.6
97.5°	74.4	73.8	73.0	72.2	71.3	70.5	69.8	69.0	68.2	67.5	66.8
100°	94.2	93.7	93.0	92.3	91.6	90.9	90.1	89.3	88.4	87.6	86.7
102.5°	116.6	116.2	115.2	114.3	113.3	112.4	111.7	111.2	110.6	110.1	109.7
105°	150.4	150.4	149.2	147.9	146.6	145.4	144.6	144.3	144.0	143.7	143.4
107.5°	186.2	185.7	185.2	184.7	184.3	183.7	183.4	183.2	183.0	182.9	182.7
110°	210.3	209.7	209.5	209.1	208.9	208.6	208.3	208.0	207.7	207.4	207.2



TEST NUMBER: P332253-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	234.4	233.7	233.7	233.6	233.5	233.4	233.3	233.2	233.0	232.8	232.7
115°	271.7	271.6	271.8	272.1	272.4	272.7	272.6	272.1	271.7	271.3	270.9
117.5°	309.0	309.0	309.4	309.7	310.1	310.5	310.5	310.2	310.0	309.7	309.4
120°	333.9	334.0	334.8	335.4	336.1	336.9	336.8	335.9	335.1	334.2	333.4
122.5°	359.1	359.5	359.9	360.3	360.6	361.0	360.9	360.2	359.6	359.0	358.4
125°	396.6	397.1	397.4	397.7	397.9	398.3	398.2	397.8	397.3	396.9	396.5
127.5°	433.6	434.3	434.6	435.0	435.3	435.6	435.3	434.4	433.5	432.6	431.7
130°	457.7	458.3	458.8	459.2	459.6	460.0	459.7	458.5	457.4	456.2	455.1
132.5°	481.6	482.2	482.6	482.9	483.2	483.6	483.1	482.0	480.9	479.7	478.6
135°	517.1	517.6	517.7	517.9	518.0	518.2	517.8	517.0	516.1	515.3	514.4
137.5°	551.8	552.4	552.0	551.6	551.3	550.9	550.4	549.7	548.9	548.3	547.6
140°	574.2	574.3	574.2	574.1	573.9	573.7	573.3	572.7	571.9	571.2	570.5
142.5°	595.6	595.7	595.5	595.3	595.0	594.8	594.3	593.5	592.8	592.2	591.4
145°	627.1	627.2	626.8	626.4	626.0	625.5	625.2	624.9	624.6	624.4	624.0
147.5°	656.7	656.7	656.3	655.9	655.5	655.1	654.7	654.1	653.6	653.1	652.6
150°	675.1	675.1	674.7	674.5	674.2	673.9	673.6	673.4	673.0	672.8	672.5
152.5°	691.6	691.4	691.2	691.0	690.9	690.7	690.4	690.0	689.6	689.2	688.8
155°	715.8	715.2	715.1	714.9	714.8	714.6	714.5	714.5	714.5	714.5	714.5
157.5°	736.9	736.2	736.1	736.1	735.9	735.8	735.8	736.0	736.1	736.3	736.5
160°	749.7	749.0	749.0	749.0	749.0	749.0	749.1	749.4	749.7	750.0	750.2
162.5°	761.9	761.2	761.1	761.0	760.9	760.8	760.9	761.3	761.7	762.1	762.5
165°	777.2	776.4	776.4	776.4	776.4	776.4	776.6	777.1	777.5	777.9	778.3
167.5°	789.8	788.9	788.8	788.6	788.6	788.5	788.6	789.2	789.8	790.4	790.9
170°	796.5	795.5	795.5	795.5	795.5	795.5	795.8	796.4	797.0	797.5	798.1
172.5°	802.0	801.1	801.1	801.1	801.1	801.1	801.4	802.0	802.6	803.2	803.6
175°	807.9	807.0	807.0	807.0	807.0	807.0	807.3	807.9	808.5	808.9	809.5
177.5°	810.6	809.9	809.9	809.9	809.9	809.9	810.2	810.6	811.1	811.5	812.0
180°	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5



TEST NUMBER: P332253-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	446.1	447.8	450.0	453.1	455.6	457.7	458.1	458.8	460.3	462.8	464.8
5°	449.1	453.4	460.4	467.2	474.7	480.8	486.5	490.5	494.2	502.2	508.7
7.5°	448.1	457.9	468.9	481.1	493.6	505.6	516.7	526.8	536.7	548.4	561.6
10°	447.5	458.9	473.8	489.5	506.8	523.7	540.1	552.8	567.5	580.9	597.8
12.5°	444.7	461.1	478.7	498.9	520.2	539.6	561.2	578.7	595.7	614.9	634.5
15°	440.8	460.8	483.2	510.0	542.3	565.8	587.9	618.5	639.4	660.2	688.4
17.5°	434.0	458.4	486.3	521.1	548.0	579.8	612.9	637.1	665.2	694.6	720.1
20°	428.5	456.8	488.2	522.4	556.8	591.1	623.2	652.1	681.2	715.2	736.1
22.5°	423.1	451.0	483.6	519.9	556.8	593.1	629.4	663.3	696.0	730.3	757.0
25°	411.4	444.7	480.0	517.1	553.5	593.4	636.7	674.5	714.9	750.3	775.6
27.5°	399.7	430.2	465.3	502.9	543.4	590.5	641.5	684.4	725.0	750.3	758.2
30°	389.0	421.3	453.6	491.8	535.7	588.2	642.4	691.6	724.8	735.9	727.7
32.5°	378.2	407.5	439.4	478.6	525.1	582.6	643.6	687.4	707.4	699.0	665.7
35°	359.2	385.6	416.5	455.7	509.2	579.5	638.6	668.2	663.3	615.8	553.1
37.5°	338.8	360.4	389.0	429.9	492.8	567.2	617.0	621.4	578.6	505.7	433.3
40°	322.7	342.1	371.5	414.3	480.0	555.1	595.3	577.6	511.4	430.2	369.8
42.5°	307.0	323.4	351.8	397.9	467.8	538.4	563.0	524.5	448.0	371.3	316.3
45°	280.5	296.0	324.4	371.7	443.0	506.8	503.5	436.7	360.1	298.4	252.8
47.5°	255.4	268.9	295.6	343.9	413.8	459.3	429.1	357.9	293.0	243.4	210.9
50°	237.7	250.9	277.5	325.2	390.4	423.5	380.5	311.9	252.4	211.4	185.6
52.5°	220.6	233.6	257.9	304.4	362.1	382.0	335.7	272.1	222.5	187.1	164.9
55°	196.8	206.7	228.5	273.0	316.1	320.7	273.7	220.5	179.7	155.0	139.8
57.5°	172.5	181.0	202.6	238.0	268.2	265.9	221.4	175.4	147.9	129.6	118.5
60°	156.7	165.1	184.1	214.4	237.3	229.3	188.4	151.4	127.8	114.4	105.6
62.5°	141.9	148.5	166.3	188.5	204.9	195.8	161.1	130.4	111.7	100.4	93.4
65°	120.6	126.0	140.1	151.8	160.9	152.1	123.3	102.0	88.5	80.6	75.8
67.5°	100.4	103.7	112.7	116.9	123.4	113.7	92.7	78.4	70.8	64.1	60.7
70°	87.6	90.0	94.8	98.2	99.9	90.0	74.4	64.0	57.6	52.8	50.7
72.5°	74.8	77.0	77.9	80.7	79.8	70.6	59.8	51.5	46.9	43.7	41.0
75°	57.2	58.1	57.2	56.0	53.6	47.1	39.7	35.5	32.1	30.6	29.6
77.5°	41.7	41.3	40.1	38.3	34.1	30.0	26.0	24.6	23.2	22.3	22.0
80°	32.1	31.3	30.2	27.3	23.7	20.9	20.0	19.0	18.4	17.4	17.3
82.5°	23.9	23.4	21.5	19.2	16.6	15.2	14.5	14.1	13.5	13.0	13.0
85°	12.7	12.1	10.0	8.7	8.4	8.0	7.8	7.8	7.0	6.8	6.8
87.5°	4.5	3.9	4.0	3.8	4.2	4.2	4.7	4.8	5.1	5.3	5.1
90°	2.0	3.5	4.9	6.3	7.9	9.8	11.6	13.5	15.3	15.9	16.5
92.5°	16.4	17.4	18.3	19.2	20.3	21.4	22.4	23.4	24.5	24.9	25.4
95°	38.6	39.6	40.6	41.6	42.6	43.8	44.9	46.1	47.2	47.8	48.3
97.5°	67.5	68.2	69.0	69.8	70.5	71.3	72.2	73.0	73.8	74.4	75.1
100°	87.6	88.4	89.3	90.1	90.9	91.6	92.3	93.0	93.7	94.2	94.6
102.5°	110.1	110.6	111.2	111.7	112.4	113.3	114.3	115.2	116.2	116.6	117.0
105°	143.7	144.0	144.3	144.6	145.4	146.6	147.9	149.2	150.4	150.4	150.4
107.5°	182.9	183.0	183.2	183.4	183.7	184.3	184.7	185.2	185.7	186.2	186.6
110°	207.4	207.7	208.0	208.3	208.6	208.9	209.1	209.5	209.7	210.3	210.8



TEST NUMBER: P332253-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	232.8	233.0	233.2	233.3	233.4	233.5	233.6	233.7	233.7	234.4	235.1
115°	271.3	271.7	272.1	272.6	272.7	272.4	272.1	271.8	271.6	271.7	271.8
117.5°	309.7	310.0	310.2	310.5	310.5	310.1	309.7	309.4	309.0	309.0	309.0
120°	334.2	335.1	335.9	336.8	336.9	336.1	335.4	334.8	334.0	333.9	333.7
122.5°	359.0	359.6	360.2	360.9	361.0	360.6	360.3	359.9	359.5	359.1	358.8
125°	396.9	397.3	397.8	398.2	398.3	397.9	397.7	397.4	397.1	396.6	396.0
127.5°	432.6	433.5	434.4	435.3	435.6	435.3	435.0	434.6	434.3	433.6	432.8
130°	456.2	457.4	458.5	459.7	460.0	459.6	459.2	458.8	458.3	457.7	457.2
132.5°	479.7	480.9	482.0	483.1	483.6	483.2	482.9	482.6	482.2	481.6	480.9
135°	515.3	516.1	517.0	517.8	518.2	518.0	517.9	517.7	517.6	517.1	516.5
137.5°	548.3	548.9	549.7	550.4	550.9	551.3	551.6	552.0	552.4	551.8	551.2
140°	571.2	571.9	572.7	573.3	573.7	573.9	574.1	574.2	574.3	574.2	574.1
142.5°	592.2	592.8	593.5	594.3	594.8	595.0	595.3	595.5	595.7	595.6	595.5
145°	624.4	624.6	624.9	625.2	625.5	626.0	626.4	626.8	627.2	627.1	627.0
147.5°	653.1	653.6	654.1	654.7	655.1	655.5	655.9	656.3	656.7	656.7	656.7
150°	672.8	673.0	673.4	673.6	673.9	674.2	674.5	674.7	675.1	675.1	675.1
152.5°	689.2	689.6	690.0	690.4	690.7	690.9	691.0	691.2	691.4	691.6	691.8
155°	714.5	714.5	714.5	714.5	714.6	714.8	714.9	715.1	715.2	715.8	716.3
157.5°	736.3	736.1	736.0	735.8	735.8	735.9	736.1	736.1	736.2	736.9	737.4
160°	750.0	749.7	749.4	749.1	749.0	749.0	749.0	749.0	749.0	749.7	750.4
162.5°	762.1	761.7	761.3	760.9	760.8	760.9	761.0	761.1	761.2	761.9	762.6
165°	777.9	777.5	777.1	776.6	776.4	776.4	776.4	776.4	776.4	777.2	778.1
167.5°	790.4	789.8	789.2	788.6	788.5	788.6	788.6	788.8	788.9	789.8	790.7
170°	797.5	797.0	796.4	795.8	795.5	795.5	795.5	795.5	795.5	796.5	797.5
172.5°	803.2	802.6	802.0	801.4	801.1	801.1	801.1	801.1	801.1	802.0	802.9
175°	808.9	808.5	807.9	807.3	807.0	807.0	807.0	807.0	807.0	807.9	808.7
177.5°	811.5	811.1	810.6	810.2	809.9	809.9	809.9	809.9	809.9	810.6	811.3
180°	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5



TEST NUMBER: P332253-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	468.1	468.1	468.6	470.9	471.2	473.2	472.6
5°	514.4	518.0	519.3	525.1	528.4	529.9	526.9
7.5°	571.0	581.2	586.0	592.1	597.3	598.9	594.8
10°	612.4	623.1	631.9	637.5	642.6	646.0	650.4
12.5°	652.3	665.4	673.9	681.7	687.0	691.3	692.0
15°	695.8	715.5	730.5	741.6	747.1	749.9	748.8
17.5°	739.6	757.9	768.6	779.8	787.4	787.8	788.1
20°	764.3	782.2	794.6	802.9	811.5	811.1	813.0
22.5°	780.9	795.0	804.5	810.5	813.4	812.0	812.4
25°	788.6	792.9	791.2	781.5	778.9	770.1	771.6
27.5°	748.7	729.0	708.5	682.2	661.5	644.9	645.7
30°	694.5	659.5	619.6	586.2	556.2	547.8	529.9
32.5°	618.6	566.2	519.5	488.3	462.6	455.6	440.0
35°	490.1	439.1	391.1	362.2	350.8	334.8	334.7
37.5°	380.9	336.1	310.7	289.0	277.7	268.0	267.1
40°	320.4	285.5	266.3	250.7	239.5	232.3	230.6
42.5°	278.2	250.0	232.0	222.3	213.7	209.9	207.2
45°	227.1	208.1	195.7	186.9	183.0	180.1	178.6
47.5°	190.0	177.3	168.8	162.9	159.7	156.7	157.5
50°	169.8	159.4	153.1	147.6	145.1	143.0	143.2
52.5°	153.5	144.1	139.1	135.1	132.1	130.5	129.9
55°	130.3	124.4	119.3	116.4	114.7	112.7	112.1
57.5°	111.1	106.6	102.4	99.2	98.7	96.8	97.0
60°	98.4	94.6	91.2	89.4	88.1	86.4	87.0
62.5°	87.9	84.7	81.6	80.2	78.8	77.6	77.9
65°	72.0	69.0	67.0	66.3	65.7	65.1	64.6
67.5°	57.4	55.5	54.3	52.7	51.5	51.4	50.8
70°	48.3	45.7	43.7	41.6	41.0	40.8	41.0
72.5°	38.6	37.1	36.5	35.5	35.4	34.9	35.2
75°	29.0	28.5	28.1	27.3	27.3	27.3	27.3
77.5°	21.4	21.1	20.9	20.7	20.5	20.2	20.2
80°	16.7	16.6	16.1	16.1	16.0	16.1	16.0
82.5°	12.6	12.6	12.2	12.2	12.0	11.9	12.0
85°	6.4	6.3	6.7	6.3	6.4	6.1	6.4
87.5°	5.2	5.3	5.3	5.3	5.2	5.6	5.4
90°	17.0	17.5	18.0	18.3	18.6	18.8	19.2
92.5°	25.8	26.3	26.4	26.3	26.1	25.9	25.8
95°	48.8	49.4	49.7	49.7	49.7	49.7	49.7
97.5°	75.7	76.4	76.7	76.6	76.6	76.6	76.5
100°	95.0	95.4	95.8	96.0	96.3	96.6	96.9
102.5°	117.4	117.8	118.1	118.0	117.9	117.9	117.8
105°	150.4	150.4	150.6	150.8	151.2	151.4	151.7
107.5°	187.1	187.6	187.7	187.5	187.4	187.2	187.0
110°	211.4	212.0	212.1	211.8	211.6	211.2	211.0



TEST NUMBER: P332253-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	235.7	236.4	236.7	236.7	236.6	236.5	236.5
115°	272.0	272.1	272.1	272.0	271.8	271.7	271.6
117.5°	308.9	308.9	308.7	308.3	307.9	307.5	307.1
120°	333.6	333.5	333.2	333.0	332.6	332.4	332.1
122.5°	358.4	358.1	357.7	357.3	356.9	356.4	356.0
125°	395.4	394.8	394.3	393.7	393.1	392.6	392.0
127.5°	431.9	431.2	430.5	429.8	429.2	428.5	427.9
130°	456.6	456.1	455.3	454.3	453.3	452.3	451.3
132.5°	480.2	479.6	478.8	478.1	477.3	476.5	475.8
135°	515.9	515.4	514.9	514.6	514.4	514.0	513.8
137.5°	550.7	550.0	549.4	548.9	548.4	547.9	547.3
140°	573.9	573.7	573.2	572.2	571.2	570.2	569.2
142.5°	595.3	595.2	594.8	593.9	593.2	592.4	591.7
145°	626.8	626.6	626.3	625.7	625.2	624.6	624.0
147.5°	656.7	656.7	656.2	655.4	654.5	653.7	652.9
150°	675.1	675.1	674.7	673.8	672.9	672.1	671.2
152.5°	692.0	692.3	692.0	691.3	690.6	689.8	689.1
155°	716.9	717.5	717.2	716.2	715.3	714.3	713.3
157.5°	738.0	738.6	738.5	737.8	736.9	736.1	735.3
160°	751.1	751.8	751.9	751.3	750.7	750.2	749.6
162.5°	763.4	764.1	763.9	763.0	762.1	761.2	760.3
165°	778.9	779.8	779.8	778.8	777.7	776.7	775.8
167.5°	791.5	792.4	792.4	791.5	790.7	789.8	788.9
170°	798.5	799.5	799.5	798.5	797.5	796.5	795.5
172.5°	803.8	804.6	804.6	803.6	802.6	801.6	800.6
175°	809.5	810.4	810.3	809.3	808.4	807.3	806.3
177.5°	812.0	812.6	812.6	811.8	811.0	810.2	809.4
180°	811.5	811.5	811.5	811.5	811.5	811.5	811.5

(END OF REPORT)