

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332254-930

Luminaire Tested: **S123RDIP-S340D805U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332254-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D805U930-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3476.2 lumens
Efficiency: N/A
Efficacy: 111.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332254-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332254-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	39	39	39	32
1	94	90	86	83	85	81	78	75	65	63	61	49	48	47	35	35	34	28
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	30	29	24
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	28	27	25	20
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	26	24	22	18
5	66	55	47	42	59	50	43	38	40	36	32	31	28	26	23	21	19	16
6	61	49	42	36	55	45	38	33	36	32	28	28	25	22	21	19	17	14
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15	13
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14	11
9	49	37	30	25	44	34	27	23	28	23	20	22	18	16	16	14	13	10
10	45	34	27	22	41	31	25	21	25	21	18	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4776	4776	4776	4776
5°	5693	4796	4224	4796
10°	7109	4769	3816	4769
15°	8344	4719	3480	4719
20°	9313	4647	3194	4647
25°	9164	4570	3018	4570
30°	6586	4501	2838	4501
35°	4398	4407	2720	4407
40°	3240	4297	2599	4297
45°	2719	4102	2481	4102
50°	2398	3848	2316	3848
55°	2104	3558	2089	3558
60°	1873	3279	1914	3279
65°	1645	2980	1780	2980
70°	1290	2716	1627	2716
75°	1135	2371	1485	2371
80°	992	2008	1463	2008
85°	790	1618	1556	1618



TEST NUMBER: P332254-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.6	1.3
10°-20°	136.3	3.9
20°-30°	214.2	6.2
30°-40°	223.4	6.4
40°-50°	191.2	5.5
50°-60°	145.7	4.2
60°-70°	93.4	2.7
70°-80°	44.9	1.3
80°-90°	14.3	0.4
90°-100°	175.2	5.0
100°-110°	496.2	14.3
110°-120°	488.1	14.0
120°-130°	389.3	11.2
130°-140°	307.0	8.8
140°-150°	229.1	6.6
150°-160°	159.7	4.6
160°-170°	93.8	2.7
170°-180°	30.5	0.9
0°-30°	394.1	11.3
0°-40°	617.6	17.8
0°-60°	954.5	27.5
0°-90°	1107.2	31.9
90°-120°	1159.6	33.4
90°-150°	2085.0	60.0
90°-180°	2369.0	68.1
0°-180°	3476.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	444	444	444	444	444	
5°	527	444	391	444	527	54
15°	749	424	312	424	749	212
25°	772	385	254	385	772	332
35°	335	335	207	335	335	219
45°	179	270	163	270	179	140
55°	112	190	111	190	112	101
65°	65	117	70	117	65	64
75°	27	57	36	57	27	29
85°	6	13	13	13	6	8
90°	18	1	18	1	18	10
95°	74	22	74	22	74	133
105°	811	74	811	74	811	800
115°	986	131	986	131	986	958
125°	778	182	778	182	778	705
135°	630	213	630	213	630	489
145°	493	243	493	243	493	313
155°	408	276	408	276	408	191
165°	356	302	356	302	356	102
175°	321	314	321	314	321	31
180°	315	315	315	315	315	



TEST NUMBER: P332254-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	472.6	473.2	471.2	470.9	468.6	468.1	468.1	464.8	462.8	460.3	458.8
5°	526.9	529.9	528.4	525.1	519.3	518.0	514.4	508.7	502.2	494.2	490.5
7.5°	594.8	598.9	597.3	592.1	586.0	581.2	571.0	561.6	548.4	536.7	526.8
10°	650.4	646.0	642.6	637.5	631.9	623.1	612.4	597.8	580.9	567.5	552.8
12.5°	692.0	691.3	687.0	681.7	673.9	665.4	652.3	634.5	614.9	595.7	578.7
15°	748.8	749.9	747.1	741.6	730.5	715.5	695.8	688.4	660.2	639.4	618.5
17.5°	788.1	787.8	787.4	779.8	768.6	757.9	739.6	720.1	694.6	665.2	637.1
20°	813.0	811.1	811.5	802.9	794.6	782.2	764.3	736.1	715.2	681.2	652.1
22.5°	812.4	812.0	813.4	810.5	804.5	795.0	780.9	757.0	730.3	696.0	663.3
25°	771.6	770.1	778.9	781.5	791.2	792.9	788.6	775.6	750.3	714.9	674.5
27.5°	645.7	644.9	661.5	682.2	708.5	729.0	748.7	758.2	750.3	725.0	684.4
30°	529.9	547.8	556.2	586.2	619.6	659.5	694.5	727.7	735.9	724.8	691.6
32.5°	440.0	455.6	462.6	488.3	519.5	566.2	618.6	665.7	699.0	707.4	687.4
35°	334.7	334.8	350.8	362.2	391.1	439.1	490.1	553.1	615.8	663.3	668.2
37.5°	267.1	268.0	277.7	289.0	310.7	336.1	380.9	433.3	505.7	578.6	621.4
40°	230.6	232.3	239.5	250.7	266.3	285.5	320.4	369.8	430.2	511.4	577.6
42.5°	207.2	209.9	213.7	222.3	232.0	250.0	278.2	316.3	371.3	448.0	524.5
45°	178.6	180.1	183.0	186.9	195.7	208.1	227.1	252.8	298.4	360.1	436.7
47.5°	157.5	156.7	159.7	162.9	168.8	177.3	190.0	210.9	243.4	293.0	357.9
50°	143.2	143.0	145.1	147.6	153.1	159.4	169.8	185.6	211.4	252.4	311.9
52.5°	129.9	130.5	132.1	135.1	139.1	144.1	153.5	164.9	187.1	222.5	272.1
55°	112.1	112.7	114.7	116.4	119.3	124.4	130.3	139.8	155.0	179.7	220.5
57.5°	97.0	96.8	98.7	99.2	102.4	106.6	111.1	118.5	129.6	147.9	175.4
60°	87.0	86.4	88.1	89.4	91.2	94.6	98.4	105.6	114.4	127.8	151.4
62.5°	77.9	77.6	78.8	80.2	81.6	84.7	87.9	93.4	100.4	111.7	130.4
65°	64.6	65.1	65.7	66.3	67.0	69.0	72.0	75.8	80.6	88.5	102.0
67.5°	50.8	51.4	51.5	52.7	54.3	55.5	57.4	60.7	64.1	70.8	78.4
70°	41.0	40.8	41.0	41.6	43.7	45.7	48.3	50.7	52.8	57.6	64.0
72.5°	35.2	34.9	35.4	35.5	36.5	37.1	38.6	41.0	43.7	46.9	51.5
75°	27.3	27.3	27.3	27.3	28.1	28.5	29.0	29.6	30.6	32.1	35.5
77.5°	20.2	20.2	20.5	20.7	20.9	21.1	21.4	22.0	22.3	23.2	24.6
80°	16.0	16.1	16.0	16.1	16.1	16.6	16.7	17.3	17.4	18.4	19.0
82.5°	12.0	11.9	12.0	12.2	12.2	12.6	12.6	13.0	13.0	13.5	14.1
85°	6.4	6.1	6.4	6.3	6.7	6.3	6.4	6.8	6.8	7.0	7.8
87.5°	5.2	5.6	5.2	5.2	5.4	5.3	5.1	5.0	5.2	5.1	4.9
90°	18.5	19.2	18.5	17.9	18.5	17.2	16.6	15.9	15.3	15.9	14.0
92.5°	30.7	31.9	31.2	33.2	34.3	37.6	42.6	53.6	73.9	98.0	107.9
95°	73.9	76.5	81.0	86.7	98.8	121.7	155.6	229.5	306.6	378.0	336.6
97.5°	201.3	206.8	224.0	252.7	299.7	375.9	458.2	572.0	626.7	585.8	428.8
100°	399.7	399.0	423.9	470.4	534.8	625.3	699.9	751.5	729.2	603.6	408.0
102.5°	586.3	601.0	621.7	658.6	708.7	766.1	809.5	811.1	734.3	570.5	377.3
105°	810.8	814.0	834.4	858.6	887.9	904.5	892.3	828.7	695.5	512.5	339.7
107.5°	940.0	945.9	952.8	961.0	960.4	937.8	881.9	778.4	627.4	461.2	315.8
110°	993.1	994.3	995.6	990.5	972.7	928.1	847.7	730.5	584.5	432.2	306.6



TEST NUMBER: P332254-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1003.8	1003.6	998.7	982.9	950.2	892.9	802.9	683.1	547.3	412.8	301.5
115°	986.1	982.9	970.1	942.1	894.3	824.8	731.1	620.2	502.3	392.0	299.6
117.5°	929.8	925.4	907.0	874.9	825.1	754.6	670.4	574.7	475.2	379.8	300.8
120°	882.8	879.0	863.7	828.0	777.6	713.3	636.7	550.7	460.9	374.1	302.8
122.5°	838.9	834.1	817.3	785.1	740.5	680.6	609.8	531.9	449.1	370.6	306.3
125°	777.6	773.1	757.2	729.2	688.4	637.4	576.3	506.7	434.1	365.9	311.7
127.5°	727.2	723.1	708.7	684.7	648.4	602.0	546.7	484.9	420.9	363.6	317.8
130°	698.6	693.5	680.1	657.2	623.4	580.1	528.4	471.1	413.7	362.1	321.9
132.5°	670.6	667.0	655.2	632.2	600.5	559.1	511.1	458.3	407.1	361.5	325.0
135°	630.4	625.9	614.5	595.3	564.1	527.7	486.3	441.1	398.4	360.8	329.5
137.5°	588.0	585.1	575.4	556.0	529.7	498.2	462.5	425.4	390.9	359.4	332.6
140°	558.4	559.1	548.8	531.0	506.7	479.3	448.7	416.2	386.3	358.9	334.7
142.5°	530.8	531.5	522.3	506.5	485.8	462.0	435.5	407.6	382.2	357.8	336.1
145°	492.7	491.5	486.3	473.0	457.1	438.5	418.2	397.1	376.7	356.3	337.2
147.5°	461.4	460.9	456.0	446.9	434.9	421.8	405.3	388.6	371.4	353.9	337.2
150°	443.0	443.0	439.2	432.2	422.6	410.5	397.1	382.5	367.8	351.9	337.2
152.5°	427.7	427.7	425.4	418.9	411.4	401.3	389.5	376.8	363.7	349.3	335.7
155°	408.5	408.0	406.7	401.5	395.8	388.2	378.6	368.4	357.6	344.9	334.0
157.5°	391.1	391.3	390.2	386.4	381.4	375.4	368.0	359.5	350.7	340.9	331.8
160°	379.9	380.5	380.5	376.7	372.3	367.8	361.4	354.4	346.1	337.9	330.8
162.5°	369.7	370.3	370.3	367.0	364.1	360.1	354.2	348.3	341.5	334.8	328.8
165°	356.3	356.3	356.9	354.4	351.9	348.7	344.2	340.4	335.3	330.2	325.7
167.5°	343.6	343.6	344.2	342.4	341.3	339.0	336.4	333.5	329.3	325.6	322.7
170°	335.9	335.9	336.6	335.3	334.7	333.4	330.8	328.9	325.7	322.5	320.7
172.5°	328.8	329.3	330.4	329.1	329.1	328.2	326.2	324.8	322.1	320.0	319.1
175°	320.7	321.2	321.9	321.2	321.2	321.2	320.0	319.4	318.0	316.8	316.8
177.5°	315.9	315.9	316.9	316.4	316.9	316.9	316.4	315.9	315.4	314.9	315.4
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P332254-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	458.1	457.7	455.6	453.1	450.0	447.8	446.1	445.2	442.5	439.1	436.9
5°	486.5	480.8	474.7	467.2	460.4	453.4	449.1	443.9	437.7	430.6	425.7
7.5°	516.7	505.6	493.6	481.1	468.9	457.9	448.1	439.8	429.8	419.7	412.7
10°	540.1	523.7	506.8	489.5	473.8	458.9	447.5	436.3	424.4	412.8	404.0
12.5°	561.2	539.6	520.2	498.9	478.7	461.1	444.7	431.5	417.0	404.7	394.8
15°	587.9	565.8	542.3	510.0	483.2	460.8	440.8	423.5	406.1	390.9	381.2
17.5°	612.9	579.8	548.0	521.1	486.3	458.4	434.0	413.4	394.1	378.1	366.1
20°	623.2	591.1	556.8	522.4	488.2	456.8	428.5	405.7	385.8	367.5	356.5
22.5°	629.4	593.1	556.8	519.9	483.6	451.0	423.1	397.9	376.3	359.1	345.4
25°	636.7	593.4	553.5	517.1	480.0	444.7	411.4	384.8	361.5	343.1	328.6
27.5°	641.5	590.5	543.4	502.9	465.3	430.2	399.7	371.5	347.7	328.2	312.7
30°	642.4	588.2	535.7	491.8	453.6	421.3	389.0	362.1	337.0	316.3	301.8
32.5°	643.6	582.6	525.1	478.6	439.4	407.5	378.2	352.5	326.8	306.4	291.6
35°	638.6	579.5	509.2	455.7	416.5	385.6	359.2	335.4	310.2	290.4	275.4
37.5°	617.0	567.2	492.8	429.9	389.0	360.4	338.8	318.1	295.0	273.6	259.5
40°	595.3	555.1	480.0	414.3	371.5	342.1	322.7	305.8	283.4	263.4	248.3
42.5°	563.0	538.4	467.8	397.9	351.8	323.4	307.0	291.2	271.6	251.3	237.0
45°	503.5	506.8	443.0	371.7	324.4	296.0	280.5	269.5	252.1	235.4	220.7
47.5°	429.1	459.3	413.8	343.9	295.6	268.9	255.4	245.8	234.0	217.6	204.2
50°	380.5	423.5	390.4	325.2	277.5	250.9	237.7	229.8	219.6	206.7	194.0
52.5°	335.7	382.0	362.1	304.4	257.9	233.6	220.6	214.2	206.0	193.9	182.4
55°	273.7	320.7	316.1	273.0	228.5	206.7	196.8	189.6	184.1	175.0	165.8
57.5°	221.4	265.9	268.2	238.0	202.6	181.0	172.5	167.1	163.5	156.6	148.1
60°	188.4	229.3	237.3	214.4	184.1	165.1	156.7	152.3	149.5	144.0	137.5
62.5°	161.1	195.8	204.9	188.5	166.3	148.5	141.9	137.8	135.8	131.1	125.4
65°	123.3	152.1	160.9	151.8	140.1	126.0	120.6	117.0	115.3	112.7	108.4
67.5°	92.7	113.7	123.4	116.9	112.7	103.7	100.4	98.4	96.9	95.1	91.6
70°	74.4	90.0	99.9	98.2	94.8	90.0	87.6	86.3	84.7	83.2	80.1
72.5°	59.8	70.6	79.8	80.7	77.9	77.0	74.8	74.2	73.3	71.5	69.8
75°	39.7	47.1	53.6	56.0	57.2	58.1	57.2	57.0	56.8	55.3	54.3
77.5°	26.0	30.0	34.1	38.3	40.1	41.3	41.7	42.4	41.8	41.1	40.6
80°	20.0	20.9	23.7	27.3	30.2	31.3	32.1	32.4	32.3	32.1	31.3
82.5°	14.5	15.2	16.6	19.2	21.5	23.4	23.9	23.8	24.2	24.4	23.7
85°	7.8	8.0	8.4	8.7	10.0	12.1	12.7	13.1	13.5	13.5	12.3
87.5°	4.9	4.3	4.2	4.0	4.2	4.0	4.6	5.1	5.5	5.1	5.5
90°	12.1	10.2	8.3	7.0	5.7	3.8	2.5	1.3	2.5	3.8	5.7
92.5°	81.0	53.6	36.9	27.4	22.1	17.1	11.7	7.9	11.7	17.1	22.1
95°	232.0	137.1	82.8	58.0	41.4	30.6	23.6	21.7	23.6	30.6	41.4
97.5°	254.6	147.5	95.7	68.8	52.5	43.1	37.6	36.9	37.6	43.1	52.5
100°	240.3	145.9	101.3	76.5	61.2	52.3	47.8	47.2	47.8	52.3	61.2
102.5°	228.0	148.0	107.9	85.2	71.4	62.9	59.0	57.9	59.0	62.9	71.4
105°	219.2	153.6	119.2	99.5	87.3	79.7	75.8	73.9	75.8	79.7	87.3
107.5°	218.7	164.0	133.9	115.5	104.1	96.6	92.9	91.0	92.9	96.6	104.1
110°	221.2	172.8	144.1	126.2	115.4	108.4	105.2	103.3	105.2	108.4	115.4



TEST NUMBER: P332254-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	226.2	181.4	154.7	137.5	126.6	119.6	116.4	114.5	116.4	119.6	126.6
115°	234.6	195.7	171.5	154.3	143.4	137.1	133.2	130.7	133.2	137.1	143.4
117.5°	245.6	210.8	186.9	171.0	158.8	153.0	149.8	146.8	149.8	153.0	158.8
120°	253.7	220.5	197.6	181.6	169.6	163.1	160.0	158.1	160.0	163.1	169.6
122.5°	261.3	230.7	208.3	191.4	179.8	172.8	169.7	167.8	169.7	172.8	179.8
125°	273.5	245.4	223.1	205.9	193.8	186.8	183.0	181.6	183.0	186.8	193.8
127.5°	283.4	258.1	236.6	219.4	206.0	198.9	194.1	192.2	194.1	198.9	206.0
130°	290.0	265.8	244.8	227.6	214.2	206.5	200.8	198.9	200.8	206.5	214.2
132.5°	296.1	272.4	251.9	235.2	221.8	212.6	206.4	204.0	206.4	212.6	221.8
135°	304.0	282.3	262.6	245.4	232.0	222.5	215.5	212.9	215.5	222.5	232.0
137.5°	309.9	289.3	270.3	254.3	241.1	230.9	224.0	221.3	224.0	230.9	241.1
140°	313.0	293.8	275.3	259.4	246.7	236.5	230.1	226.9	230.1	236.5	246.7
142.5°	316.0	297.4	279.4	264.6	251.8	242.6	235.7	233.0	235.7	242.6	251.8
145°	319.4	302.1	285.6	270.9	260.1	250.5	244.8	242.9	244.8	250.5	260.1
147.5°	321.4	306.0	290.8	278.3	267.8	259.6	254.0	252.8	254.0	259.6	267.8
150°	321.9	308.5	293.8	282.3	273.5	265.1	260.1	259.4	260.1	265.1	273.5
152.5°	322.9	310.1	297.4	286.4	278.6	271.3	266.2	266.0	266.2	271.3	278.6
155°	323.2	313.0	302.1	293.2	286.2	279.8	276.0	276.0	276.0	279.8	286.2
157.5°	323.8	314.6	306.0	299.1	293.1	287.5	284.4	283.9	284.4	287.5	293.1
160°	323.8	316.2	308.5	302.1	297.7	292.6	290.0	290.0	290.0	292.6	297.7
162.5°	323.3	316.7	310.1	304.7	300.8	296.7	294.6	294.6	294.6	296.7	300.8
165°	321.9	317.4	312.3	307.9	305.3	302.1	300.8	301.5	300.8	302.1	305.3
167.5°	320.9	317.3	313.6	310.8	309.0	306.6	306.0	306.7	306.0	306.6	309.0
170°	319.4	316.8	313.6	312.3	311.0	309.2	308.5	309.8	308.5	309.2	311.0
172.5°	318.9	316.8	314.1	313.3	312.6	311.2	311.0	311.9	311.0	311.2	312.6
175°	317.4	316.2	314.9	314.2	314.2	313.0	313.6	314.2	313.6	313.0	314.2
177.5°	316.4	315.4	314.9	314.9	314.9	314.4	314.9	315.4	314.9	314.4	314.9
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P332254-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	436.1	434.1	432.8	429.7	427.8	425.7	423.5	424.9	424.7	424.6	424.6
5°	421.5	417.1	413.1	408.0	404.8	400.8	397.8	397.4	398.1	395.5	394.0
7.5°	407.0	401.0	395.3	389.7	383.7	378.9	375.9	374.5	372.6	371.0	369.2
10°	396.8	389.8	384.3	377.2	370.8	365.1	361.5	359.0	357.7	356.4	353.8
12.5°	386.3	379.4	372.4	364.4	358.3	351.7	349.0	346.3	343.7	342.2	338.8
15°	371.0	362.1	354.7	346.3	339.4	333.0	329.2	323.7	322.9	321.0	317.6
17.5°	355.6	345.9	335.7	329.5	321.8	315.0	309.2	307.4	302.0	299.9	296.9
20°	343.4	334.5	326.7	318.5	307.4	301.1	296.5	294.1	289.7	287.0	285.1
22.5°	333.0	323.8	314.9	305.3	296.1	289.0	285.7	281.8	279.5	275.7	273.7
25°	318.0	308.1	297.3	287.0	280.4	275.1	269.7	266.3	262.9	261.1	257.4
27.5°	300.6	290.2	280.1	272.3	264.2	258.9	254.1	251.1	247.0	244.1	242.0
30°	291.0	278.8	270.1	263.1	252.7	247.7	244.1	240.3	237.3	234.2	232.1
32.5°	279.9	268.8	260.6	251.8	243.9	238.4	233.7	230.4	227.8	224.9	222.8
35°	262.5	253.2	244.7	235.9	230.0	224.5	219.0	216.1	213.7	211.0	209.1
37.5°	246.8	238.1	229.9	221.7	214.3	209.9	205.5	203.3	199.9	198.1	196.2
40°	237.1	228.5	219.8	211.8	204.2	200.8	196.8	193.6	190.5	189.1	187.1
42.5°	226.4	217.8	210.5	201.9	195.7	191.0	187.4	183.8	181.6	179.6	178.5
45°	210.7	203.1	195.8	187.3	181.4	177.4	173.3	170.0	168.0	166.6	164.5
47.5°	195.3	187.8	180.4	173.0	167.3	162.7	158.5	156.3	153.5	151.9	150.5
50°	184.3	177.4	169.7	162.8	157.1	152.5	149.1	146.3	143.8	141.7	140.7
52.5°	174.1	166.8	160.0	153.7	147.7	142.5	139.4	136.4	134.5	132.2	131.0
55°	157.3	150.3	144.6	138.3	132.4	128.0	124.3	121.6	119.7	117.0	115.5
57.5°	141.5	135.2	128.4	122.9	116.9	113.2	110.1	106.5	104.1	102.1	100.5
60°	130.9	123.7	117.7	112.7	107.3	102.6	99.7	96.9	94.4	92.3	91.0
62.5°	119.8	113.5	107.9	102.3	97.4	93.3	90.0	87.6	85.4	84.1	82.8
65°	102.7	97.8	92.1	87.6	83.0	80.0	77.3	75.3	73.7	72.7	71.6
67.5°	87.1	82.3	77.4	72.9	69.8	67.5	65.8	64.0	63.2	62.0	61.2
70°	77.0	72.0	67.6	64.2	61.1	59.4	58.3	57.0	56.3	54.7	54.0
72.5°	65.9	62.3	59.1	56.3	53.9	52.3	50.9	49.2	48.0	46.3	45.6
75°	51.9	48.6	46.1	44.3	42.7	40.7	38.6	36.9	36.3	35.7	35.5
77.5°	38.4	36.4	34.6	32.9	31.1	29.6	29.1	28.7	28.6	28.3	28.3
80°	30.2	28.3	27.0	25.1	24.0	24.0	24.0	23.6	23.7	23.7	23.7
82.5°	22.4	20.7	20.0	19.3	19.1	19.2	19.2	19.3	19.2	19.5	19.3
85°	11.6	11.7	12.1	12.0	12.1	12.1	12.6	12.3	12.6	12.1	12.6
87.5°	5.6	6.4	6.9	7.4	8.0	8.2	8.2	8.3	8.6	8.7	9.0
90°	7.0	8.3	10.2	12.1	14.0	15.9	15.3	15.9	16.6	17.2	18.5
92.5°	27.4	36.9	53.6	81.0	107.9	98.0	73.9	53.6	42.6	37.6	34.3
95°	58.0	82.8	137.1	232.0	336.6	378.0	306.6	229.5	155.6	121.7	98.8
97.5°	68.8	95.7	147.5	254.6	428.8	585.8	626.7	572.0	458.2	375.9	299.7
100°	76.5	101.3	145.9	240.3	408.0	603.6	729.2	751.5	699.9	625.3	534.8
102.5°	85.2	107.9	148.0	228.0	377.3	570.5	734.3	811.1	809.5	766.1	708.7
105°	99.5	119.2	153.6	219.2	339.7	512.5	695.5	828.7	892.3	904.5	887.9
107.5°	115.5	133.9	164.0	218.7	315.8	461.2	627.4	778.4	881.9	937.8	960.4
110°	126.2	144.1	172.8	221.2	306.6	432.2	584.5	730.5	847.7	928.1	972.7



TEST NUMBER: P332254-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	137.5	154.7	181.4	226.2	301.5	412.8	547.3	683.1	802.9	892.9	950.2
115°	154.3	171.5	195.7	234.6	299.6	392.0	502.3	620.2	731.1	824.8	894.3
117.5°	171.0	186.9	210.8	245.6	300.8	379.8	475.2	574.7	670.4	754.6	825.1
120°	181.6	197.6	220.5	253.7	302.8	374.1	460.9	550.7	636.7	713.3	777.6
122.5°	191.4	208.3	230.7	261.3	306.3	370.6	449.1	531.9	609.8	680.6	740.5
125°	205.9	223.1	245.4	273.5	311.7	365.9	434.1	506.7	576.3	637.4	688.4
127.5°	219.4	236.6	258.1	283.4	317.8	363.6	420.9	484.9	546.7	602.0	648.4
130°	227.6	244.8	265.8	290.0	321.9	362.1	413.7	471.1	528.4	580.1	623.4
132.5°	235.2	251.9	272.4	296.1	325.0	361.5	407.1	458.3	511.1	559.1	600.5
135°	245.4	262.6	282.3	304.0	329.5	360.8	398.4	441.1	486.3	527.7	564.1
137.5°	254.3	270.3	289.3	309.9	332.6	359.4	390.9	425.4	462.5	498.2	529.7
140°	259.4	275.3	293.8	313.0	334.7	358.9	386.3	416.2	448.7	479.3	506.7
142.5°	264.6	279.4	297.4	316.0	336.1	357.8	382.2	407.6	435.5	462.0	485.8
145°	270.9	285.6	302.1	319.4	337.2	356.3	376.7	397.1	418.2	438.5	457.1
147.5°	278.3	290.8	306.0	321.4	337.2	353.9	371.4	388.6	405.3	421.8	434.9
150°	282.3	293.8	308.5	321.9	337.2	351.9	367.8	382.5	397.1	410.5	422.6
152.5°	286.4	297.4	310.1	322.9	335.7	349.3	363.7	376.8	389.5	401.3	411.4
155°	293.2	302.1	313.0	323.2	334.0	344.9	357.6	368.4	378.6	388.2	395.8
157.5°	299.1	306.0	314.6	323.8	331.8	340.9	350.7	359.5	368.0	375.4	381.4
160°	302.1	308.5	316.2	323.8	330.8	337.9	346.1	354.4	361.4	367.8	372.3
162.5°	304.7	310.1	316.7	323.3	328.8	334.8	341.5	348.3	354.2	360.1	364.1
165°	307.9	312.3	317.4	321.9	325.7	330.2	335.3	340.4	344.2	348.7	351.9
167.5°	310.8	313.6	317.3	320.9	322.7	325.6	329.3	333.5	336.4	339.0	341.3
170°	312.3	313.6	316.8	319.4	320.7	322.5	325.7	328.9	330.8	333.4	334.7
172.5°	313.3	314.1	316.8	318.9	319.1	320.0	322.1	324.8	326.2	328.2	329.1
175°	314.2	314.9	316.2	317.4	316.8	316.8	318.0	319.4	320.0	321.2	321.2
177.5°	314.9	314.9	315.4	316.4	315.4	314.9	315.4	315.9	316.4	316.9	316.9
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P332254-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	422.7	422.6	422.7	422.2	422.7	422.6	422.7	424.6	424.6	424.7	424.9
5°	393.4	393.2	392.6	390.9	392.6	393.2	393.4	394.0	395.5	398.1	397.4
7.5°	367.7	367.5	365.8	365.8	365.8	367.5	367.7	369.2	371.0	372.6	374.5
10°	352.5	352.7	350.4	349.1	350.4	352.7	352.5	353.8	356.4	357.7	359.0
12.5°	337.8	337.0	335.1	333.6	335.1	337.0	337.8	338.8	342.2	343.7	346.3
15°	318.4	316.4	311.9	312.3	311.9	316.4	318.4	317.6	321.0	322.9	323.7
17.5°	295.5	294.1	294.0	291.3	294.0	294.1	295.5	296.9	299.9	302.0	307.4
20°	282.1	281.1	281.5	278.8	281.5	281.1	282.1	285.1	287.0	289.7	294.1
22.5°	271.6	270.6	269.0	268.2	269.0	270.6	271.6	273.7	275.7	279.5	281.8
25°	256.2	254.7	253.2	254.1	253.2	254.7	256.2	257.4	261.1	262.9	266.3
27.5°	240.9	239.8	238.2	238.1	238.2	239.8	240.9	242.0	244.1	247.0	251.1
30°	231.1	230.0	229.3	228.3	229.3	230.0	231.1	232.1	234.2	237.3	240.3
32.5°	221.3	221.0	219.7	219.5	219.7	221.0	221.3	222.8	224.9	227.8	230.4
35°	208.4	207.2	206.8	207.0	206.8	207.2	208.4	209.1	211.0	213.7	216.1
37.5°	196.1	194.6	193.9	193.2	193.9	194.6	196.1	196.2	198.1	199.9	203.3
40°	187.3	185.8	185.4	185.0	185.4	185.8	187.3	187.1	189.1	190.5	193.6
42.5°	177.4	176.8	176.6	175.9	176.6	176.8	177.4	178.5	179.6	181.6	183.8
45°	164.0	163.7	162.6	163.0	162.6	163.7	164.0	164.5	166.6	168.0	170.0
47.5°	149.7	148.9	148.1	148.6	148.1	148.9	149.7	150.5	151.9	153.5	156.3
50°	140.0	139.6	137.9	138.3	137.9	139.6	140.0	140.7	141.7	143.8	146.3
52.5°	130.3	128.8	128.2	127.9	128.2	128.8	130.3	131.0	132.2	134.5	136.4
55°	114.1	112.4	111.7	111.3	111.7	112.4	114.1	115.5	117.0	119.7	121.6
57.5°	98.3	97.9	97.3	97.7	97.3	97.9	98.3	100.5	102.1	104.1	106.5
60°	89.1	89.1	89.1	88.9	89.1	89.1	89.1	91.0	92.3	94.4	96.9
62.5°	81.9	81.4	81.4	81.6	81.4	81.4	81.9	82.8	84.1	85.4	87.6
65°	71.0	70.8	70.1	69.9	70.1	70.8	71.0	71.6	72.7	73.7	75.3
67.5°	60.7	60.1	59.8	59.6	59.8	60.1	60.7	61.2	62.0	63.2	64.0
70°	53.0	52.6	51.4	51.7	51.4	52.6	53.0	54.0	54.7	56.3	57.0
72.5°	44.7	44.3	44.0	43.8	44.0	44.3	44.7	45.6	46.3	48.0	49.2
75°	35.3	35.1	35.0	35.7	35.0	35.1	35.3	35.5	35.7	36.3	36.9
77.5°	28.3	28.3	28.5	28.1	28.5	28.3	28.3	28.3	28.3	28.6	28.7
80°	23.7	23.7	23.6	23.6	23.6	23.7	23.7	23.7	23.7	23.7	23.6
82.5°	19.0	19.2	19.3	19.0	19.3	19.2	19.0	19.3	19.5	19.2	19.3
85°	12.6	12.3	12.7	12.6	12.7	12.3	12.6	12.6	12.1	12.6	12.3
87.5°	9.2	9.0	9.1	9.1	9.1	9.0	9.2	9.0	8.7	8.6	8.3
90°	17.9	18.5	19.2	18.5	19.2	18.5	17.9	18.5	17.2	16.6	15.9
92.5°	33.2	31.2	31.9	30.7	31.9	31.2	33.2	34.3	37.6	42.6	53.6
95°	86.7	81.0	76.5	73.9	76.5	81.0	86.7	98.8	121.7	155.6	229.5
97.5°	252.7	224.0	206.8	201.3	206.8	224.0	252.7	299.7	375.9	458.2	572.0
100°	470.4	423.9	399.0	399.7	399.0	423.9	470.4	534.8	625.3	699.9	751.5
102.5°	658.6	621.7	601.0	586.3	601.0	621.7	658.6	708.7	766.1	809.5	811.1
105°	858.6	834.4	814.0	810.8	814.0	834.4	858.6	887.9	904.5	892.3	828.7
107.5°	961.0	952.8	945.9	940.0	945.9	952.8	961.0	960.4	937.8	881.9	778.4
110°	990.5	995.6	994.3	993.1	994.3	995.6	990.5	972.7	928.1	847.7	730.5



TEST NUMBER: P332254-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	982.9	998.7	1003.6	1003.8	1003.6	998.7	982.9	950.2	892.9	802.9	683.1
115°	942.1	970.1	982.9	986.1	982.9	970.1	942.1	894.3	824.8	731.1	620.2
117.5°	874.9	907.0	925.4	929.8	925.4	907.0	874.9	825.1	754.6	670.4	574.7
120°	828.0	863.7	879.0	882.8	879.0	863.7	828.0	777.6	713.3	636.7	550.7
122.5°	785.1	817.3	834.1	838.9	834.1	817.3	785.1	740.5	680.6	609.8	531.9
125°	729.2	757.2	773.1	777.6	773.1	757.2	729.2	688.4	637.4	576.3	506.7
127.5°	684.7	708.7	723.1	727.2	723.1	708.7	684.7	648.4	602.0	546.7	484.9
130°	657.2	680.1	693.5	698.6	693.5	680.1	657.2	623.4	580.1	528.4	471.1
132.5°	632.2	655.2	667.0	670.6	667.0	655.2	632.2	600.5	559.1	511.1	458.3
135°	595.3	614.5	625.9	630.4	625.9	614.5	595.3	564.1	527.7	486.3	441.1
137.5°	556.0	575.4	585.1	588.0	585.1	575.4	556.0	529.7	498.2	462.5	425.4
140°	531.0	548.8	559.1	558.4	559.1	548.8	531.0	506.7	479.3	448.7	416.2
142.5°	506.5	522.3	531.5	530.8	531.5	522.3	506.5	485.8	462.0	435.5	407.6
145°	473.0	486.3	491.5	492.7	491.5	486.3	473.0	457.1	438.5	418.2	397.1
147.5°	446.9	456.0	460.9	461.4	460.9	456.0	446.9	434.9	421.8	405.3	388.6
150°	432.2	439.2	443.0	443.0	443.0	439.2	432.2	422.6	410.5	397.1	382.5
152.5°	418.9	425.4	427.7	427.7	427.7	425.4	418.9	411.4	401.3	389.5	376.8
155°	401.5	406.7	408.0	408.5	408.0	406.7	401.5	395.8	388.2	378.6	368.4
157.5°	386.4	390.2	391.3	391.1	391.3	390.2	386.4	381.4	375.4	368.0	359.5
160°	376.7	380.5	380.5	379.9	380.5	380.5	376.7	372.3	367.8	361.4	354.4
162.5°	367.0	370.3	370.3	369.7	370.3	370.3	367.0	364.1	360.1	354.2	348.3
165°	354.4	356.9	356.3	356.3	356.3	356.9	354.4	351.9	348.7	344.2	340.4
167.5°	342.4	344.2	343.6	343.6	343.6	344.2	342.4	341.3	339.0	336.4	333.5
170°	335.3	336.6	335.9	335.9	335.9	336.6	335.3	334.7	333.4	330.8	328.9
172.5°	329.1	330.4	329.3	328.8	329.3	330.4	329.1	329.1	328.2	326.2	324.8
175°	321.2	321.9	321.2	320.7	321.2	321.9	321.2	321.2	321.2	320.0	319.4
177.5°	316.4	316.9	315.9	315.9	315.9	316.9	316.4	316.9	316.9	316.4	315.9
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P332254-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	423.5	425.7	427.8	429.7	432.8	434.1	436.1	436.9	439.1	442.5	445.2
5°	397.8	400.8	404.8	408.0	413.1	417.1	421.5	425.7	430.6	437.7	443.9
7.5°	375.9	378.9	383.7	389.7	395.3	401.0	407.0	412.7	419.7	429.8	439.8
10°	361.5	365.1	370.8	377.2	384.3	389.8	396.8	404.0	412.8	424.4	436.3
12.5°	349.0	351.7	358.3	364.4	372.4	379.4	386.3	394.8	404.7	417.0	431.5
15°	329.2	333.0	339.4	346.3	354.7	362.1	371.0	381.2	390.9	406.1	423.5
17.5°	309.2	315.0	321.8	329.5	335.7	345.9	355.6	366.1	378.1	394.1	413.4
20°	296.5	301.1	307.4	318.5	326.7	334.5	343.4	356.5	367.5	385.8	405.7
22.5°	285.7	289.0	296.1	305.3	314.9	323.8	333.0	345.4	359.1	376.3	397.9
25°	269.7	275.1	280.4	287.0	297.3	308.1	318.0	328.6	343.1	361.5	384.8
27.5°	254.1	258.9	264.2	272.3	280.1	290.2	300.6	312.7	328.2	347.7	371.5
30°	244.1	247.7	252.7	263.1	270.1	278.8	291.0	301.8	316.3	337.0	362.1
32.5°	233.7	238.4	243.9	251.8	260.6	268.8	279.9	291.6	306.4	326.8	352.5
35°	219.0	224.5	230.0	235.9	244.7	253.2	262.5	275.4	290.4	310.2	335.4
37.5°	205.5	209.9	214.3	221.7	229.9	238.1	246.8	259.5	273.6	295.0	318.1
40°	196.8	200.8	204.2	211.8	219.8	228.5	237.1	248.3	263.4	283.4	305.8
42.5°	187.4	191.0	195.7	201.9	210.5	217.8	226.4	237.0	251.3	271.6	291.2
45°	173.3	177.4	181.4	187.3	195.8	203.1	210.7	220.7	235.4	252.1	269.5
47.5°	158.5	162.7	167.3	173.0	180.4	187.8	195.3	204.2	217.6	234.0	245.8
50°	149.1	152.5	157.1	162.8	169.7	177.4	184.3	194.0	206.7	219.6	229.8
52.5°	139.4	142.5	147.7	153.7	160.0	166.8	174.1	182.4	193.9	206.0	214.2
55°	124.3	128.0	132.4	138.3	144.6	150.3	157.3	165.8	175.0	184.1	189.6
57.5°	110.1	113.2	116.9	122.9	128.4	135.2	141.5	148.1	156.6	163.5	167.1
60°	99.7	102.6	107.3	112.7	117.7	123.7	130.9	137.5	144.0	149.5	152.3
62.5°	90.0	93.3	97.4	102.3	107.9	113.5	119.8	125.4	131.1	135.8	137.8
65°	77.3	80.0	83.0	87.6	92.1	97.8	102.7	108.4	112.7	115.3	117.0
67.5°	65.8	67.5	69.8	72.9	77.4	82.3	87.1	91.6	95.1	96.9	98.4
70°	58.3	59.4	61.1	64.2	67.6	72.0	77.0	80.1	83.2	84.7	86.3
72.5°	50.9	52.3	53.9	56.3	59.1	62.3	65.9	69.8	71.5	73.3	74.2
75°	38.6	40.7	42.7	44.3	46.1	48.6	51.9	54.3	55.3	56.8	57.0
77.5°	29.1	29.6	31.1	32.9	34.6	36.4	38.4	40.6	41.1	41.8	42.4
80°	24.0	24.0	24.0	25.1	27.0	28.3	30.2	31.3	32.1	32.3	32.4
82.5°	19.2	19.2	19.1	19.3	20.0	20.7	22.4	23.7	24.4	24.2	23.8
85°	12.6	12.1	12.1	12.0	12.1	11.7	11.6	12.3	13.5	13.5	13.1
87.5°	8.2	8.2	8.0	7.4	6.9	6.4	5.6	5.5	5.1	5.5	5.1
90°	15.3	15.9	14.0	12.1	10.2	8.3	7.0	5.7	3.8	2.5	1.3
92.5°	73.9	98.0	107.9	81.0	53.6	36.9	27.4	22.1	17.1	11.7	7.9
95°	306.6	378.0	336.6	232.0	137.1	82.8	58.0	41.4	30.6	23.6	21.7
97.5°	626.7	585.8	428.8	254.6	147.5	95.7	68.8	52.5	43.1	37.6	36.9
100°	729.2	603.6	408.0	240.3	145.9	101.3	76.5	61.2	52.3	47.8	47.2
102.5°	734.3	570.5	377.3	228.0	148.0	107.9	85.2	71.4	62.9	59.0	57.9
105°	695.5	512.5	339.7	219.2	153.6	119.2	99.5	87.3	79.7	75.8	73.9
107.5°	627.4	461.2	315.8	218.7	164.0	133.9	115.5	104.1	96.6	92.9	91.0
110°	584.5	432.2	306.6	221.2	172.8	144.1	126.2	115.4	108.4	105.2	103.3



TEST NUMBER: P332254-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	547.3	412.8	301.5	226.2	181.4	154.7	137.5	126.6	119.6	116.4	114.5
115°	502.3	392.0	299.6	234.6	195.7	171.5	154.3	143.4	137.1	133.2	130.7
117.5°	475.2	379.8	300.8	245.6	210.8	186.9	171.0	158.8	153.0	149.8	146.8
120°	460.9	374.1	302.8	253.7	220.5	197.6	181.6	169.6	163.1	160.0	158.1
122.5°	449.1	370.6	306.3	261.3	230.7	208.3	191.4	179.8	172.8	169.7	167.8
125°	434.1	365.9	311.7	273.5	245.4	223.1	205.9	193.8	186.8	183.0	181.6
127.5°	420.9	363.6	317.8	283.4	258.1	236.6	219.4	206.0	198.9	194.1	192.2
130°	413.7	362.1	321.9	290.0	265.8	244.8	227.6	214.2	206.5	200.8	198.9
132.5°	407.1	361.5	325.0	296.1	272.4	251.9	235.2	221.8	212.6	206.4	204.0
135°	398.4	360.8	329.5	304.0	282.3	262.6	245.4	232.0	222.5	215.5	212.9
137.5°	390.9	359.4	332.6	309.9	289.3	270.3	254.3	241.1	230.9	224.0	221.3
140°	386.3	358.9	334.7	313.0	293.8	275.3	259.4	246.7	236.5	230.1	226.9
142.5°	382.2	357.8	336.1	316.0	297.4	279.4	264.6	251.8	242.6	235.7	233.0
145°	376.7	356.3	337.2	319.4	302.1	285.6	270.9	260.1	250.5	244.8	242.9
147.5°	371.4	353.9	337.2	321.4	306.0	290.8	278.3	267.8	259.6	254.0	252.8
150°	367.8	351.9	337.2	321.9	308.5	293.8	282.3	273.5	265.1	260.1	259.4
152.5°	363.7	349.3	335.7	322.9	310.1	297.4	286.4	278.6	271.3	266.2	266.0
155°	357.6	344.9	334.0	323.2	313.0	302.1	293.2	286.2	279.8	276.0	276.0
157.5°	350.7	340.9	331.8	323.8	314.6	306.0	299.1	293.1	287.5	284.4	283.9
160°	346.1	337.9	330.8	323.8	316.2	308.5	302.1	297.7	292.6	290.0	290.0
162.5°	341.5	334.8	328.8	323.3	316.7	310.1	304.7	300.8	296.7	294.6	294.6
165°	335.3	330.2	325.7	321.9	317.4	312.3	307.9	305.3	302.1	300.8	301.5
167.5°	329.3	325.6	322.7	320.9	317.3	313.6	310.8	309.0	306.6	306.0	306.7
170°	325.7	322.5	320.7	319.4	316.8	313.6	312.3	311.0	309.2	308.5	309.8
172.5°	322.1	320.0	319.1	318.9	316.8	314.1	313.3	312.6	311.2	311.0	311.9
175°	318.0	316.8	316.8	317.4	316.2	314.9	314.2	314.2	313.0	313.6	314.2
177.5°	315.4	314.9	315.4	316.4	315.4	314.9	314.9	314.9	314.4	314.9	315.4
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P332254-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	446.1	447.8	450.0	453.1	455.6	457.7	458.1	458.8	460.3	462.8	464.8
5°	449.1	453.4	460.4	467.2	474.7	480.8	486.5	490.5	494.2	502.2	508.7
7.5°	448.1	457.9	468.9	481.1	493.6	505.6	516.7	526.8	536.7	548.4	561.6
10°	447.5	458.9	473.8	489.5	506.8	523.7	540.1	552.8	567.5	580.9	597.8
12.5°	444.7	461.1	478.7	498.9	520.2	539.6	561.2	578.7	595.7	614.9	634.5
15°	440.8	460.8	483.2	510.0	542.3	565.8	587.9	618.5	639.4	660.2	688.4
17.5°	434.0	458.4	486.3	521.1	548.0	579.8	612.9	637.1	665.2	694.6	720.1
20°	428.5	456.8	488.2	522.4	556.8	591.1	623.2	652.1	681.2	715.2	736.1
22.5°	423.1	451.0	483.6	519.9	556.8	593.1	629.4	663.3	696.0	730.3	757.0
25°	411.4	444.7	480.0	517.1	553.5	593.4	636.7	674.5	714.9	750.3	775.6
27.5°	399.7	430.2	465.3	502.9	543.4	590.5	641.5	684.4	725.0	750.3	758.2
30°	389.0	421.3	453.6	491.8	535.7	588.2	642.4	691.6	724.8	735.9	727.7
32.5°	378.2	407.5	439.4	478.6	525.1	582.6	643.6	687.4	707.4	699.0	665.7
35°	359.2	385.6	416.5	455.7	509.2	579.5	638.6	668.2	663.3	615.8	553.1
37.5°	338.8	360.4	389.0	429.9	492.8	567.2	617.0	621.4	578.6	505.7	433.3
40°	322.7	342.1	371.5	414.3	480.0	555.1	595.3	577.6	511.4	430.2	369.8
42.5°	307.0	323.4	351.8	397.9	467.8	538.4	563.0	524.5	448.0	371.3	316.3
45°	280.5	296.0	324.4	371.7	443.0	506.8	503.5	436.7	360.1	298.4	252.8
47.5°	255.4	268.9	295.6	343.9	413.8	459.3	429.1	357.9	293.0	243.4	210.9
50°	237.7	250.9	277.5	325.2	390.4	423.5	380.5	311.9	252.4	211.4	185.6
52.5°	220.6	233.6	257.9	304.4	362.1	382.0	335.7	272.1	222.5	187.1	164.9
55°	196.8	206.7	228.5	273.0	316.1	320.7	273.7	220.5	179.7	155.0	139.8
57.5°	172.5	181.0	202.6	238.0	268.2	265.9	221.4	175.4	147.9	129.6	118.5
60°	156.7	165.1	184.1	214.4	237.3	229.3	188.4	151.4	127.8	114.4	105.6
62.5°	141.9	148.5	166.3	188.5	204.9	195.8	161.1	130.4	111.7	100.4	93.4
65°	120.6	126.0	140.1	151.8	160.9	152.1	123.3	102.0	88.5	80.6	75.8
67.5°	100.4	103.7	112.7	116.9	123.4	113.7	92.7	78.4	70.8	64.1	60.7
70°	87.6	90.0	94.8	98.2	99.9	90.0	74.4	64.0	57.6	52.8	50.7
72.5°	74.8	77.0	77.9	80.7	79.8	70.6	59.8	51.5	46.9	43.7	41.0
75°	57.2	58.1	57.2	56.0	53.6	47.1	39.7	35.5	32.1	30.6	29.6
77.5°	41.7	41.3	40.1	38.3	34.1	30.0	26.0	24.6	23.2	22.3	22.0
80°	32.1	31.3	30.2	27.3	23.7	20.9	20.0	19.0	18.4	17.4	17.3
82.5°	23.9	23.4	21.5	19.2	16.6	15.2	14.5	14.1	13.5	13.0	13.0
85°	12.7	12.1	10.0	8.7	8.4	8.0	7.8	7.8	7.0	6.8	6.8
87.5°	4.6	4.0	4.2	4.0	4.2	4.3	4.9	4.9	5.1	5.2	5.0
90°	2.5	3.8	5.7	7.0	8.3	10.2	12.1	14.0	15.9	15.3	15.9
92.5°	11.7	17.1	22.1	27.4	36.9	53.6	81.0	107.9	98.0	73.9	53.6
95°	23.6	30.6	41.4	58.0	82.8	137.1	232.0	336.6	378.0	306.6	229.5
97.5°	37.6	43.1	52.5	68.8	95.7	147.5	254.6	428.8	585.8	626.7	572.0
100°	47.8	52.3	61.2	76.5	101.3	145.9	240.3	408.0	603.6	729.2	751.5
102.5°	59.0	62.9	71.4	85.2	107.9	148.0	228.0	377.3	570.5	734.3	811.1
105°	75.8	79.7	87.3	99.5	119.2	153.6	219.2	339.7	512.5	695.5	828.7
107.5°	92.9	96.6	104.1	115.5	133.9	164.0	218.7	315.8	461.2	627.4	778.4
110°	105.2	108.4	115.4	126.2	144.1	172.8	221.2	306.6	432.2	584.5	730.5



TEST NUMBER: P332254-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	116.4	119.6	126.6	137.5	154.7	181.4	226.2	301.5	412.8	547.3	683.1
115°	133.2	137.1	143.4	154.3	171.5	195.7	234.6	299.6	392.0	502.3	620.2
117.5°	149.8	153.0	158.8	171.0	186.9	210.8	245.6	300.8	379.8	475.2	574.7
120°	160.0	163.1	169.6	181.6	197.6	220.5	253.7	302.8	374.1	460.9	550.7
122.5°	169.7	172.8	179.8	191.4	208.3	230.7	261.3	306.3	370.6	449.1	531.9
125°	183.0	186.8	193.8	205.9	223.1	245.4	273.5	311.7	365.9	434.1	506.7
127.5°	194.1	198.9	206.0	219.4	236.6	258.1	283.4	317.8	363.6	420.9	484.9
130°	200.8	206.5	214.2	227.6	244.8	265.8	290.0	321.9	362.1	413.7	471.1
132.5°	206.4	212.6	221.8	235.2	251.9	272.4	296.1	325.0	361.5	407.1	458.3
135°	215.5	222.5	232.0	245.4	262.6	282.3	304.0	329.5	360.8	398.4	441.1
137.5°	224.0	230.9	241.1	254.3	270.3	289.3	309.9	332.6	359.4	390.9	425.4
140°	230.1	236.5	246.7	259.4	275.3	293.8	313.0	334.7	358.9	386.3	416.2
142.5°	235.7	242.6	251.8	264.6	279.4	297.4	316.0	336.1	357.8	382.2	407.6
145°	244.8	250.5	260.1	270.9	285.6	302.1	319.4	337.2	356.3	376.7	397.1
147.5°	254.0	259.6	267.8	278.3	290.8	306.0	321.4	337.2	353.9	371.4	388.6
150°	260.1	265.1	273.5	282.3	293.8	308.5	321.9	337.2	351.9	367.8	382.5
152.5°	266.2	271.3	278.6	286.4	297.4	310.1	322.9	335.7	349.3	363.7	376.8
155°	276.0	279.8	286.2	293.2	302.1	313.0	323.2	334.0	344.9	357.6	368.4
157.5°	284.4	287.5	293.1	299.1	306.0	314.6	323.8	331.8	340.9	350.7	359.5
160°	290.0	292.6	297.7	302.1	308.5	316.2	323.8	330.8	337.9	346.1	354.4
162.5°	294.6	296.7	300.8	304.7	310.1	316.7	323.3	328.8	334.8	341.5	348.3
165°	300.8	302.1	305.3	307.9	312.3	317.4	321.9	325.7	330.2	335.3	340.4
167.5°	306.0	306.6	309.0	310.8	313.6	317.3	320.9	322.7	325.6	329.3	333.5
170°	308.5	309.2	311.0	312.3	313.6	316.8	319.4	320.7	322.5	325.7	328.9
172.5°	311.0	311.2	312.6	313.3	314.1	316.8	318.9	319.1	320.0	322.1	324.8
175°	313.6	313.0	314.2	314.2	314.9	316.2	317.4	316.8	316.8	318.0	319.4
177.5°	314.9	314.4	314.9	314.9	314.9	315.4	316.4	315.4	314.9	315.4	315.9
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P332254-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	468.1	468.1	468.6	470.9	471.2	473.2	472.6
5°	514.4	518.0	519.3	525.1	528.4	529.9	526.9
7.5°	571.0	581.2	586.0	592.1	597.3	598.9	594.8
10°	612.4	623.1	631.9	637.5	642.6	646.0	650.4
12.5°	652.3	665.4	673.9	681.7	687.0	691.3	692.0
15°	695.8	715.5	730.5	741.6	747.1	749.9	748.8
17.5°	739.6	757.9	768.6	779.8	787.4	787.8	788.1
20°	764.3	782.2	794.6	802.9	811.5	811.1	813.0
22.5°	780.9	795.0	804.5	810.5	813.4	812.0	812.4
25°	788.6	792.9	791.2	781.5	778.9	770.1	771.6
27.5°	748.7	729.0	708.5	682.2	661.5	644.9	645.7
30°	694.5	659.5	619.6	586.2	556.2	547.8	529.9
32.5°	618.6	566.2	519.5	488.3	462.6	455.6	440.0
35°	490.1	439.1	391.1	362.2	350.8	334.8	334.7
37.5°	380.9	336.1	310.7	289.0	277.7	268.0	267.1
40°	320.4	285.5	266.3	250.7	239.5	232.3	230.6
42.5°	278.2	250.0	232.0	222.3	213.7	209.9	207.2
45°	227.1	208.1	195.7	186.9	183.0	180.1	178.6
47.5°	190.0	177.3	168.8	162.9	159.7	156.7	157.5
50°	169.8	159.4	153.1	147.6	145.1	143.0	143.2
52.5°	153.5	144.1	139.1	135.1	132.1	130.5	129.9
55°	130.3	124.4	119.3	116.4	114.7	112.7	112.1
57.5°	111.1	106.6	102.4	99.2	98.7	96.8	97.0
60°	98.4	94.6	91.2	89.4	88.1	86.4	87.0
62.5°	87.9	84.7	81.6	80.2	78.8	77.6	77.9
65°	72.0	69.0	67.0	66.3	65.7	65.1	64.6
67.5°	57.4	55.5	54.3	52.7	51.5	51.4	50.8
70°	48.3	45.7	43.7	41.6	41.0	40.8	41.0
72.5°	38.6	37.1	36.5	35.5	35.4	34.9	35.2
75°	29.0	28.5	28.1	27.3	27.3	27.3	27.3
77.5°	21.4	21.1	20.9	20.7	20.5	20.2	20.2
80°	16.7	16.6	16.1	16.1	16.0	16.1	16.0
82.5°	12.6	12.6	12.2	12.2	12.0	11.9	12.0
85°	6.4	6.3	6.7	6.3	6.4	6.1	6.4
87.5°	5.1	5.3	5.4	5.2	5.2	5.6	5.2
90°	16.6	17.2	18.5	17.9	18.5	19.2	18.5
92.5°	42.6	37.6	34.3	33.2	31.2	31.9	30.7
95°	155.6	121.7	98.8	86.7	81.0	76.5	73.9
97.5°	458.2	375.9	299.7	252.7	224.0	206.8	201.3
100°	699.9	625.3	534.8	470.4	423.9	399.0	399.7
102.5°	809.5	766.1	708.7	658.6	621.7	601.0	586.3
105°	892.3	904.5	887.9	858.6	834.4	814.0	810.8
107.5°	881.9	937.8	960.4	961.0	952.8	945.9	940.0
110°	847.7	928.1	972.7	990.5	995.6	994.3	993.1



TEST NUMBER: P332254-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	802.9	892.9	950.2	982.9	998.7	1003.6	1003.8
115°	731.1	824.8	894.3	942.1	970.1	982.9	986.1
117.5°	670.4	754.6	825.1	874.9	907.0	925.4	929.8
120°	636.7	713.3	777.6	828.0	863.7	879.0	882.8
122.5°	609.8	680.6	740.5	785.1	817.3	834.1	838.9
125°	576.3	637.4	688.4	729.2	757.2	773.1	777.6
127.5°	546.7	602.0	648.4	684.7	708.7	723.1	727.2
130°	528.4	580.1	623.4	657.2	680.1	693.5	698.6
132.5°	511.1	559.1	600.5	632.2	655.2	667.0	670.6
135°	486.3	527.7	564.1	595.3	614.5	625.9	630.4
137.5°	462.5	498.2	529.7	556.0	575.4	585.1	588.0
140°	448.7	479.3	506.7	531.0	548.8	559.1	558.4
142.5°	435.5	462.0	485.8	506.5	522.3	531.5	530.8
145°	418.2	438.5	457.1	473.0	486.3	491.5	492.7
147.5°	405.3	421.8	434.9	446.9	456.0	460.9	461.4
150°	397.1	410.5	422.6	432.2	439.2	443.0	443.0
152.5°	389.5	401.3	411.4	418.9	425.4	427.7	427.7
155°	378.6	388.2	395.8	401.5	406.7	408.0	408.5
157.5°	368.0	375.4	381.4	386.4	390.2	391.3	391.1
160°	361.4	367.8	372.3	376.7	380.5	380.5	379.9
162.5°	354.2	360.1	364.1	367.0	370.3	370.3	369.7
165°	344.2	348.7	351.9	354.4	356.9	356.3	356.3
167.5°	336.4	339.0	341.3	342.4	344.2	343.6	343.6
170°	330.8	333.4	334.7	335.3	336.6	335.9	335.9
172.5°	326.2	328.2	329.1	329.1	330.4	329.3	328.8
175°	320.0	321.2	321.2	321.2	321.9	321.2	320.7
177.5°	316.4	316.9	316.9	316.4	316.9	315.9	315.9
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9

(END OF REPORT)