

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332272-930

Luminaire Tested: **S123RDIP-S560D365U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332272-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D365U930-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2888.2 lumens
Efficiency: N/A
Efficacy: 105.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332272-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332272-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63
1	101	97	94	90	95	91	88	85	81	78	76	71	69	67	61	60	59	54
2	93	86	80	75	87	81	76	71	71	68	64	63	60	57	55	53	51	47
3	85	76	69	63	80	72	66	60	64	59	55	56	52	49	49	46	44	41
4	78	68	60	54	73	64	57	52	57	52	47	51	46	43	44	41	39	35
5	72	61	53	47	68	58	51	45	51	46	41	46	41	38	40	37	34	31
6	67	55	47	41	63	52	45	40	47	41	37	42	37	33	37	33	30	28
7	62	50	42	37	58	47	40	35	43	37	32	38	33	30	34	30	27	25
8	58	46	38	33	54	43	36	31	39	33	29	35	30	27	31	27	25	22
9	54	42	34	29	51	40	33	28	36	30	26	32	28	24	29	25	22	20
10	50	38	31	27	47	37	30	26	33	28	24	30	25	22	27	23	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7851	7851	7851	7851
5°	9360	7886	6944	7886
10°	11687	7840	6274	7840
15°	13718	7759	5721	7759
20°	15309	7640	5251	7640
25°	15064	7514	4962	7514
30°	10828	7398	4666	7398
35°	7230	7247	4473	7247
40°	5327	7065	4274	7065
45°	4468	6745	4078	6745
50°	3944	6328	3806	6328
55°	3459	5849	3434	5849
60°	3078	5393	3147	5393
65°	2705	4898	2929	4898
70°	2121	4463	2675	4463
75°	1871	3897	2441	3897
80°	1630	3310	2399	3310
85°	1309	2655	2544	2655



TEST NUMBER: P332272-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.7	2.5
10°-20°	224.1	7.8
20°-30°	352.1	12.2
30°-40°	367.3	12.7
40°-50°	314.4	10.9
50°-60°	239.6	8.3
60°-70°	153.6	5.3
70°-80°	73.9	2.6
80°-90°	20.7	0.7
90°-100°	79.2	2.7
100°-110°	224.3	7.8
110°-120°	220.6	7.6
120°-130°	176.0	6.1
130°-140°	138.8	4.8
140°-150°	103.6	3.6
150°-160°	72.2	2.5
160°-170°	42.4	1.5
170°-180°	13.8	0.5
0°-30°	647.9	22.4
0°-40°	1015.3	35.2
0°-60°	1569.3	54.3
0°-90°	1817.4	62.9
90°-120°	524.1	18.1
90°-150°	942.4	32.6
90°-180°	1071.0	37.1
0°-180°	2888.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	729	729	729	729	729	
5°	866	730	643	730	866	89
15°	1231	696	513	696	1231	349
25°	1268	633	418	633	1268	545
35°	550	552	340	552	550	361
45°	294	443	268	443	294	231
55°	184	312	183	312	184	167
65°	106	192	115	192	106	104
75°	45	94	59	94	45	48
85°	11	22	21	22	11	12
90°	8	1	8	1	8	5
95°	33	10	33	10	33	60
105°	366	33	366	33	366	362
115°	446	59	446	59	446	433
125°	352	82	352	82	352	319
135°	285	96	285	96	285	221
145°	223	110	223	110	223	142
155°	185	125	185	125	185	86
165°	161	136	161	136	161	46
175°	145	142	145	142	145	14
180°	142	142	142	142	142	



TEST NUMBER: P332272-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	776.9	778.0	774.7	774.2	770.5	769.5	769.5	764.2	760.9	756.7	754.2
5°	866.3	871.2	868.8	863.2	853.8	851.6	845.6	836.3	825.7	812.5	806.3
7.5°	977.8	984.6	981.9	973.3	963.5	955.5	938.8	923.2	901.5	882.4	866.0
10°	1069.3	1062.0	1056.5	1048.0	1038.9	1024.3	1006.8	982.8	955.0	933.1	908.7
12.5°	1137.7	1136.5	1129.4	1120.7	1107.9	1094.0	1072.4	1043.2	1010.9	979.3	951.5
15°	1231.0	1232.9	1228.2	1219.1	1201.0	1176.3	1143.9	1131.7	1085.5	1051.1	1016.8
17.5°	1295.6	1295.2	1294.5	1282.0	1263.6	1245.9	1215.9	1183.8	1142.0	1093.6	1047.3
20°	1336.5	1333.4	1334.1	1320.0	1306.3	1286.0	1256.6	1210.1	1175.7	1119.8	1072.0
22.5°	1335.5	1334.9	1337.3	1332.4	1322.5	1306.9	1283.9	1244.6	1200.7	1144.3	1090.5
25°	1268.4	1266.0	1280.7	1284.7	1300.6	1303.4	1296.6	1275.0	1233.5	1175.4	1108.9
27.5°	1061.6	1060.2	1087.4	1121.5	1164.8	1198.4	1230.9	1246.5	1233.5	1191.9	1125.3
30°	871.2	900.6	914.4	963.7	1018.6	1084.2	1141.7	1196.3	1209.7	1191.6	1137.0
32.5°	723.3	748.9	760.4	802.8	854.0	930.8	1017.0	1094.4	1149.1	1162.9	1130.0
35°	550.2	550.6	576.7	595.5	642.9	721.9	805.7	909.3	1012.4	1090.5	1098.6
37.5°	439.0	440.6	456.5	475.2	510.8	552.5	626.2	712.4	831.4	951.3	1021.6
40°	379.1	381.9	393.8	412.2	437.8	469.4	526.8	608.0	707.3	840.7	949.7
42.5°	340.6	345.2	351.3	365.5	381.3	410.9	457.4	520.1	610.3	736.5	862.2
45°	293.5	296.0	300.7	307.3	321.6	342.3	373.5	415.6	490.6	592.1	718.0
47.5°	258.9	257.6	262.5	267.9	277.4	291.5	312.4	346.8	400.3	481.7	588.5
50°	235.5	235.1	238.6	242.6	251.7	262.0	279.2	305.1	347.6	415.0	512.7
52.5°	213.4	214.7	217.1	222.2	228.7	237.0	252.4	271.1	307.6	365.8	447.3
55°	184.3	185.2	188.6	191.4	196.1	204.6	214.3	229.8	254.8	295.4	362.6
57.5°	159.5	159.1	162.4	163.1	168.4	175.2	182.7	194.9	213.0	243.1	288.4
60°	143.0	142.1	144.9	147.1	149.9	155.5	161.8	173.7	188.0	210.2	248.9
62.5°	128.0	127.6	129.6	131.8	134.1	139.3	144.6	153.6	165.0	183.7	214.4
65°	106.2	107.1	108.0	109.0	110.2	113.3	118.4	124.6	132.4	145.5	167.7
67.5°	83.4	84.4	84.7	86.6	89.3	91.2	94.3	99.9	105.3	116.3	129.0
70°	67.4	67.1	67.4	68.4	71.8	75.3	79.3	83.4	86.8	94.7	105.3
72.5°	58.0	57.4	58.2	58.4	60.1	61.0	63.6	67.4	71.8	77.1	84.8
75°	45.0	45.0	45.0	45.0	46.2	46.9	47.8	48.8	50.3	52.7	58.4
77.5°	33.3	33.3	33.8	34.0	34.3	34.7	35.2	36.2	36.7	38.1	40.4
80°	26.3	26.6	26.3	26.6	26.6	27.1	27.5	28.5	28.7	30.3	31.2
82.5°	19.7	19.6	19.7	20.1	20.1	20.7	20.7	21.4	21.5	22.3	23.2
85°	10.6	10.0	10.6	10.3	10.9	10.3	10.6	11.3	11.3	11.6	12.8
87.5°	4.2	4.7	4.2	4.3	4.4	4.6	4.5	4.4	4.9	4.7	4.7
90°	8.3	8.6	8.3	8.1	8.3	7.7	7.5	7.2	6.9	7.2	6.4
92.5°	13.9	14.4	14.1	15.0	15.5	17.0	19.2	24.3	33.4	44.3	48.8
95°	33.4	34.6	36.6	39.2	44.7	55.0	70.3	103.7	138.6	170.9	152.1
97.5°	91.0	93.4	101.3	114.2	135.5	169.9	207.1	258.5	283.2	264.8	193.9
100°	180.7	180.3	191.6	212.6	241.7	282.7	316.3	339.7	329.6	272.9	184.4
102.5°	265.0	271.7	281.0	297.7	320.3	346.3	365.9	366.6	331.9	257.9	170.6
105°	366.5	367.9	377.2	388.1	401.4	408.8	403.3	374.5	314.3	231.6	153.6
107.5°	424.9	427.5	430.6	434.4	434.1	423.9	398.6	351.8	283.6	208.5	142.8
110°	448.9	449.5	450.0	447.8	439.7	419.5	383.2	330.2	264.2	195.3	138.6



TEST NUMBER: P332272-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	453.7	453.6	451.4	444.3	429.5	403.6	362.9	308.8	247.4	186.5	136.2
115°	445.7	444.3	438.5	425.8	404.2	372.8	330.4	280.3	227.1	177.2	135.4
117.5°	420.2	418.2	410.0	395.5	372.9	341.0	303.0	259.8	214.7	171.6	135.9
120°	399.0	397.3	390.4	374.2	351.5	322.4	287.8	248.9	208.3	169.1	136.9
122.5°	379.2	377.0	369.4	354.9	334.7	307.6	275.6	240.4	203.0	167.5	138.4
125°	351.5	349.5	342.3	329.6	311.2	288.1	260.5	229.0	196.2	165.3	140.9
127.5°	328.6	326.9	320.3	309.5	293.1	272.1	247.1	219.2	190.2	164.4	143.7
130°	315.8	313.5	307.4	297.0	281.8	262.2	238.9	212.9	186.9	163.6	145.5
132.5°	303.1	301.5	296.1	285.8	271.4	252.7	231.0	207.2	184.0	163.4	146.9
135°	284.9	282.9	277.8	269.1	254.9	238.6	219.8	199.3	180.1	163.1	149.0
137.5°	265.8	264.4	260.1	251.3	239.5	225.2	209.0	192.2	176.7	162.4	150.3
140°	252.4	252.7	248.1	240.0	229.0	216.6	202.8	188.2	174.6	162.2	151.2
142.5°	239.9	240.2	236.1	228.9	219.6	208.8	196.8	184.3	172.8	161.8	152.0
145°	222.7	222.2	219.8	213.8	206.6	198.2	189.0	179.5	170.2	161.0	152.4
147.5°	208.6	208.3	206.1	202.0	196.6	190.6	183.2	175.6	167.9	160.0	152.4
150°	200.2	200.2	198.5	195.3	191.0	185.6	179.5	172.8	166.2	159.1	152.4
152.5°	193.3	193.3	192.2	189.3	186.0	181.4	176.0	170.3	164.4	157.9	151.7
155°	184.7	184.4	183.8	181.5	178.9	175.5	171.1	166.6	161.6	155.9	151.0
157.5°	176.8	176.8	176.3	174.6	172.4	169.7	166.3	162.5	158.5	154.1	150.0
160°	171.7	172.0	172.0	170.2	168.3	166.2	163.4	160.2	156.5	152.7	149.5
162.5°	167.1	167.4	167.4	165.9	164.6	162.8	160.1	157.4	154.3	151.3	148.6
165°	161.0	161.0	161.3	160.2	159.1	157.6	155.6	153.8	151.6	149.3	147.2
167.5°	155.3	155.3	155.6	154.7	154.3	153.2	152.1	150.7	148.9	147.2	145.9
170°	151.8	151.8	152.1	151.6	151.2	150.7	149.5	148.6	147.2	145.8	145.0
172.5°	148.6	148.9	149.4	148.8	148.7	148.4	147.5	146.8	145.6	144.6	144.2
175°	145.0	145.2	145.5	145.2	145.2	145.2	144.6	144.3	143.7	143.2	143.2
177.5°	142.8	142.8	143.2	143.0	143.2	143.2	143.0	142.8	142.6	142.4	142.6
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4



TEST NUMBER: P332272-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	753.2	752.4	748.9	744.9	739.7	736.2	733.4	732.0	727.5	721.9	718.2
5°	799.7	790.4	780.4	768.2	756.9	745.4	738.3	729.8	719.5	707.9	699.8
7.5°	849.5	831.2	811.4	791.0	770.8	752.7	736.7	723.0	706.6	690.1	678.4
10°	887.8	861.0	833.2	804.7	778.8	754.5	735.7	717.3	697.7	678.6	664.2
12.5°	922.5	887.2	855.2	820.2	787.1	758.0	731.0	709.3	685.7	665.4	649.0
15°	966.5	930.3	891.5	838.5	794.4	757.6	724.8	696.3	667.6	642.7	626.7
17.5°	1007.5	953.1	901.1	856.7	799.6	753.5	713.5	679.5	648.0	621.5	601.9
20°	1024.6	971.8	915.3	858.8	802.6	751.1	704.5	667.0	634.2	604.2	586.1
22.5°	1034.8	975.0	915.5	854.8	795.1	741.5	695.5	654.3	618.7	590.3	567.9
25°	1046.8	975.5	910.0	850.0	789.1	731.0	676.4	632.7	594.3	563.9	540.2
27.5°	1054.6	970.9	893.3	826.7	764.9	707.1	657.0	610.7	571.7	539.6	514.2
30°	1056.1	967.1	880.6	808.5	745.7	692.6	639.5	595.2	554.0	519.9	496.2
32.5°	1058.1	957.9	863.4	786.8	722.5	669.9	621.8	579.4	537.2	503.7	479.5
35°	1049.9	952.8	837.2	749.2	684.9	633.9	590.5	551.5	510.0	477.4	452.8
37.5°	1014.4	932.5	810.1	706.8	639.5	592.4	557.0	523.0	484.9	449.9	426.6
40°	978.7	912.5	789.1	681.1	610.8	562.4	530.5	502.8	465.9	433.1	408.1
42.5°	925.4	885.3	769.2	654.1	578.3	531.7	504.8	478.7	446.5	413.1	389.6
45°	827.9	833.2	728.2	611.1	533.4	486.5	461.2	443.1	414.4	386.9	362.9
47.5°	705.4	755.0	680.2	565.3	486.0	442.0	419.9	404.1	384.7	357.8	335.8
50°	625.5	696.3	641.7	534.6	456.2	412.5	390.7	377.9	361.0	339.7	318.9
52.5°	551.8	627.9	595.3	500.3	424.0	384.0	362.6	352.1	338.8	318.8	299.9
55°	450.0	527.1	519.6	448.7	375.7	339.7	323.5	311.7	302.6	287.6	272.6
57.5°	363.9	437.1	441.0	391.3	333.0	297.6	283.6	274.7	268.7	257.5	243.6
60°	309.8	376.9	390.0	352.5	302.6	271.3	257.6	250.5	245.7	236.7	226.1
62.5°	264.8	322.0	336.8	309.8	273.4	244.1	233.4	226.5	223.3	215.5	206.1
65°	202.7	250.1	264.5	249.5	230.5	207.0	198.3	192.3	189.6	185.2	178.3
67.5°	152.4	187.0	202.8	192.2	185.3	170.5	164.9	161.8	159.2	156.3	150.5
70°	122.4	148.1	164.3	161.4	155.8	148.1	144.0	141.8	139.3	136.8	131.8
72.5°	98.4	116.0	131.3	132.7	128.1	126.5	122.9	122.1	120.5	117.6	114.8
75°	65.3	77.5	88.1	92.1	94.0	95.6	94.0	93.7	93.4	90.9	89.3
77.5°	42.8	49.3	56.0	62.9	65.9	68.0	68.5	69.6	68.8	67.5	66.8
80°	32.8	34.3	39.1	45.0	49.7	51.5	52.7	53.4	53.1	52.7	51.5
82.5°	23.8	25.1	27.3	31.5	35.4	38.6	39.3	39.1	39.9	40.0	39.1
85°	12.8	13.1	13.8	14.3	16.6	20.0	21.0	21.5	22.2	22.2	20.3
87.5°	5.1	4.6	5.0	4.9	5.5	5.6	7.0	8.1	8.5	7.6	7.7
90°	5.5	4.6	3.8	3.2	2.6	1.7	1.1	0.6	1.1	1.7	2.6
92.5°	36.6	24.2	16.6	12.4	9.9	7.7	5.3	3.6	5.3	7.7	9.9
95°	104.8	62.0	37.4	26.3	18.8	13.9	10.7	9.8	10.7	13.9	18.8
97.5°	115.0	66.7	43.3	31.1	23.7	19.5	17.0	16.7	17.0	19.5	23.7
100°	108.6	66.0	45.8	34.6	27.6	23.6	21.6	21.4	21.6	23.6	27.6
102.5°	103.1	66.9	48.8	38.5	32.3	28.5	26.7	26.2	26.7	28.5	32.3
105°	99.1	69.5	53.9	44.9	39.5	36.0	34.3	33.4	34.3	36.0	39.5
107.5°	98.8	74.2	60.5	52.2	47.0	43.7	42.0	41.2	42.0	43.7	47.0
110°	100.0	78.1	65.1	57.1	52.2	49.0	47.5	46.6	47.5	49.0	52.2



TEST NUMBER: P332272-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	102.3	82.0	70.0	62.1	57.2	54.1	52.6	51.8	52.6	54.1	57.2
115°	106.0	88.5	77.5	69.7	64.8	62.0	60.3	59.0	60.3	62.0	64.8
117.5°	111.0	95.3	84.5	77.3	71.8	69.1	67.7	66.4	67.7	69.1	71.8
120°	114.6	99.7	89.3	82.1	76.6	73.8	72.3	71.4	72.3	73.8	76.6
122.5°	118.1	104.3	94.2	86.5	81.3	78.1	76.7	75.8	76.7	78.1	81.3
125°	123.6	111.0	100.9	93.0	87.6	84.4	82.7	82.1	82.7	84.4	87.6
127.5°	128.1	116.7	107.0	99.1	93.1	89.9	87.7	86.9	87.7	89.9	93.1
130°	131.1	120.2	110.6	102.9	96.8	93.4	90.7	89.9	90.7	93.4	96.8
132.5°	133.9	123.1	113.9	106.3	100.3	96.1	93.3	92.2	93.3	96.1	100.3
135°	137.5	127.6	118.7	111.0	104.8	100.5	97.3	96.2	97.3	100.5	104.8
137.5°	140.1	130.8	122.1	115.0	108.9	104.4	101.3	100.0	101.3	104.4	108.9
140°	141.5	132.8	124.5	117.2	111.5	106.9	104.0	102.6	104.0	106.9	111.5
142.5°	142.8	134.4	126.3	119.6	113.8	109.7	106.6	105.3	106.6	109.7	113.8
145°	144.3	136.6	129.1	122.5	117.6	113.2	110.6	109.7	110.6	113.2	117.6
147.5°	145.3	138.3	131.4	125.8	121.1	117.3	114.8	114.3	114.8	117.3	121.1
150°	145.5	139.4	132.8	127.6	123.6	119.8	117.6	117.2	117.6	119.8	123.6
152.5°	145.9	140.1	134.4	129.5	125.9	122.6	120.3	120.3	120.3	122.6	125.9
155°	146.1	141.5	136.6	132.6	129.4	126.5	124.7	124.7	124.7	126.5	129.4
157.5°	146.3	142.2	138.3	135.2	132.5	130.0	128.6	128.3	128.6	130.0	132.5
160°	146.3	142.9	139.4	136.6	134.5	132.2	131.1	131.1	131.1	132.2	134.5
162.5°	146.1	143.2	140.1	137.7	135.9	134.1	133.1	133.1	133.1	134.1	135.9
165°	145.5	143.5	141.2	139.2	138.0	136.6	136.0	136.2	136.0	136.6	138.0
167.5°	145.0	143.4	141.8	140.5	139.7	138.6	138.3	138.6	138.3	138.6	139.7
170°	144.3	143.2	141.8	141.2	140.6	139.7	139.4	140.0	139.4	139.7	140.6
172.5°	144.1	143.2	141.9	141.6	141.3	140.6	140.6	141.0	140.6	140.6	141.3
175°	143.5	142.9	142.4	142.0	142.0	141.5	141.8	142.0	141.8	141.5	142.0
177.5°	143.0	142.6	142.4	142.4	142.4	142.1	142.4	142.6	142.4	142.1	142.4
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4



TEST NUMBER: P332272-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	717.0	713.7	711.5	706.5	703.3	699.8	696.3	698.5	698.2	698.0	698.0
5°	692.9	685.7	679.2	670.7	665.4	658.9	653.9	653.3	654.5	650.1	647.7
7.5°	669.1	659.3	650.0	640.7	630.8	622.9	618.0	615.7	612.5	609.8	607.0
10°	652.3	640.8	631.7	620.2	609.6	600.2	594.3	590.2	588.0	585.8	581.8
12.5°	635.1	623.8	612.2	599.2	589.1	578.2	573.8	569.2	565.0	562.6	557.0
15°	609.8	595.2	583.0	569.2	558.1	547.4	541.2	532.1	530.8	527.7	522.1
17.5°	584.6	568.7	551.9	541.7	529.0	518.0	508.4	505.4	496.4	493.1	488.2
20°	564.6	549.9	537.1	523.7	505.2	495.0	487.5	483.4	476.2	471.8	468.7
22.5°	547.4	532.4	517.6	502.0	486.7	475.2	469.7	463.4	459.5	453.4	450.0
25°	522.8	506.5	488.7	471.8	460.9	452.2	443.4	437.8	432.2	429.3	423.1
27.5°	494.2	477.2	460.6	447.8	434.3	425.7	417.8	412.8	406.0	401.3	397.9
30°	478.4	458.4	444.1	432.5	415.3	407.2	401.3	395.0	390.0	385.1	381.6
32.5°	460.2	441.9	428.3	414.0	400.8	392.0	384.3	378.8	374.5	369.8	366.4
35°	431.5	416.3	402.2	387.8	378.1	369.1	360.0	355.4	351.3	346.9	343.8
37.5°	405.7	391.4	378.1	364.4	352.5	345.0	337.8	334.2	328.7	325.8	322.6
40°	389.7	375.7	361.3	348.2	335.7	330.1	323.5	318.2	313.2	311.0	307.6
42.5°	372.3	358.2	346.1	331.9	321.7	314.1	308.0	302.2	298.5	295.3	293.3
45°	346.3	333.8	322.0	307.9	298.2	291.6	284.8	279.5	276.1	273.9	270.4
47.5°	321.1	308.7	296.6	284.4	275.0	267.5	260.7	256.9	252.4	249.7	247.4
50°	302.9	291.6	278.8	267.6	258.3	250.8	245.2	240.4	236.4	232.9	231.4
52.5°	286.2	274.2	263.1	252.7	242.8	234.2	229.2	224.2	221.2	217.2	215.4
55°	258.5	247.0	237.7	227.3	217.7	210.5	204.2	199.8	196.7	192.3	189.9
57.5°	232.6	222.3	211.1	202.2	192.2	186.1	180.9	175.0	171.2	167.8	165.3
60°	215.2	203.3	193.6	185.2	176.4	168.6	164.0	159.2	155.2	151.7	149.6
62.5°	196.9	186.5	177.4	168.2	160.2	153.4	148.0	144.0	140.5	138.3	136.1
65°	168.9	160.9	151.5	144.0	136.5	131.5	127.1	123.7	121.2	119.6	117.7
67.5°	143.2	135.3	127.2	119.8	114.8	111.0	108.1	105.2	104.0	101.9	100.7
70°	126.5	118.4	111.2	105.6	100.5	97.8	95.9	93.7	92.5	89.9	88.7
72.5°	108.3	102.4	97.2	92.5	88.5	86.0	83.6	81.0	78.9	76.2	74.9
75°	85.3	80.0	75.9	72.7	70.3	66.9	63.4	60.6	59.7	58.7	58.4
77.5°	63.1	59.8	56.8	54.2	51.1	48.6	47.9	47.2	47.0	46.6	46.6
80°	49.7	46.6	44.4	41.3	39.4	39.4	39.4	38.7	39.1	39.1	39.1
82.5°	36.9	34.0	32.9	31.7	31.4	31.6	31.6	31.7	31.6	32.0	31.8
85°	19.1	19.3	20.0	19.6	20.0	20.0	20.6	20.3	20.6	20.0	20.6
87.5°	7.7	8.5	8.9	9.4	9.8	9.7	9.9	9.9	10.3	10.3	10.4
90°	3.2	3.8	4.6	5.5	6.4	7.2	6.9	7.2	7.5	7.7	8.3
92.5°	12.4	16.6	24.2	36.6	48.8	44.3	33.4	24.3	19.2	17.0	15.5
95°	26.3	37.4	62.0	104.8	152.1	170.9	138.6	103.7	70.3	55.0	44.7
97.5°	31.1	43.3	66.7	115.0	193.9	264.8	283.2	258.5	207.1	169.9	135.5
100°	34.6	45.8	66.0	108.6	184.4	272.9	329.6	339.7	316.3	282.7	241.7
102.5°	38.5	48.8	66.9	103.1	170.6	257.9	331.9	366.6	365.9	346.3	320.3
105°	44.9	53.9	69.5	99.1	153.6	231.6	314.3	374.5	403.3	408.8	401.4
107.5°	52.2	60.5	74.2	98.8	142.8	208.5	283.6	351.8	398.6	423.9	434.1
110°	57.1	65.1	78.1	100.0	138.6	195.3	264.2	330.2	383.2	419.5	439.7



TEST NUMBER: P332272-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	62.1	70.0	82.0	102.3	136.2	186.5	247.4	308.8	362.9	403.6	429.5
115°	69.7	77.5	88.5	106.0	135.4	177.2	227.1	280.3	330.4	372.8	404.2
117.5°	77.3	84.5	95.3	111.0	135.9	171.6	214.7	259.8	303.0	341.0	372.9
120°	82.1	89.3	99.7	114.6	136.9	169.1	208.3	248.9	287.8	322.4	351.5
122.5°	86.5	94.2	104.3	118.1	138.4	167.5	203.0	240.4	275.6	307.6	334.7
125°	93.0	100.9	111.0	123.6	140.9	165.3	196.2	229.0	260.5	288.1	311.2
127.5°	99.1	107.0	116.7	128.1	143.7	164.4	190.2	219.2	247.1	272.1	293.1
130°	102.9	110.6	120.2	131.1	145.5	163.6	186.9	212.9	238.9	262.2	281.8
132.5°	106.3	113.9	123.1	133.9	146.9	163.4	184.0	207.2	231.0	252.7	271.4
135°	111.0	118.7	127.6	137.5	149.0	163.1	180.1	199.3	219.8	238.6	254.9
137.5°	115.0	122.1	130.8	140.1	150.3	162.4	176.7	192.2	209.0	225.2	239.5
140°	117.2	124.5	132.8	141.5	151.2	162.2	174.6	188.2	202.8	216.6	229.0
142.5°	119.6	126.3	134.4	142.8	152.0	161.8	172.8	184.3	196.8	208.8	219.6
145°	122.5	129.1	136.6	144.3	152.4	161.0	170.2	179.5	189.0	198.2	206.6
147.5°	125.8	131.4	138.3	145.3	152.4	160.0	167.9	175.6	183.2	190.6	196.6
150°	127.6	132.8	139.4	145.5	152.4	159.1	166.2	172.8	179.5	185.6	191.0
152.5°	129.5	134.4	140.1	145.9	151.7	157.9	164.4	170.3	176.0	181.4	186.0
155°	132.6	136.6	141.5	146.1	151.0	155.9	161.6	166.6	171.1	175.5	178.9
157.5°	135.2	138.3	142.2	146.3	150.0	154.1	158.5	162.5	166.3	169.7	172.4
160°	136.6	139.4	142.9	146.3	149.5	152.7	156.5	160.2	163.4	166.2	168.3
162.5°	137.7	140.1	143.2	146.1	148.6	151.3	154.3	157.4	160.1	162.8	164.6
165°	139.2	141.2	143.5	145.5	147.2	149.3	151.6	153.8	155.6	157.6	159.1
167.5°	140.5	141.8	143.4	145.0	145.9	147.2	148.9	150.7	152.1	153.2	154.3
170°	141.2	141.8	143.2	144.3	145.0	145.8	147.2	148.6	149.5	150.7	151.2
172.5°	141.6	141.9	143.2	144.1	144.2	144.6	145.6	146.8	147.5	148.4	148.7
175°	142.0	142.4	142.9	143.5	143.2	143.2	143.7	144.3	144.6	145.2	145.2
177.5°	142.4	142.4	142.6	143.0	142.6	142.4	142.6	142.8	143.0	143.2	143.2
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4



TEST NUMBER: P332272-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	695.0	694.7	695.0	694.0	695.0	694.7	695.0	698.0	698.0	698.2	698.5
5°	646.7	646.4	645.5	642.7	645.5	646.4	646.7	647.7	650.1	654.5	653.3
7.5°	604.5	604.1	601.4	601.4	601.4	604.1	604.5	607.0	609.8	612.5	615.7
10°	579.6	579.9	576.2	574.0	576.2	579.9	579.6	581.8	585.8	588.0	590.2
12.5°	555.4	553.9	550.9	548.5	550.9	553.9	555.4	557.0	562.6	565.0	569.2
15°	523.3	520.2	512.7	513.4	512.7	520.2	523.3	522.1	527.7	530.8	532.1
17.5°	485.7	483.4	483.3	478.9	483.3	483.4	485.7	488.2	493.1	496.4	505.4
20°	463.7	462.2	462.8	458.4	462.8	462.2	463.7	468.7	471.8	476.2	483.4
22.5°	446.5	444.9	442.3	440.9	442.3	444.9	446.5	450.0	453.4	459.5	463.4
25°	421.3	418.7	416.3	417.8	416.3	418.7	421.3	423.1	429.3	432.2	437.8
27.5°	396.0	394.1	391.7	391.3	391.7	394.1	396.0	397.9	401.3	406.0	412.8
30°	380.0	378.1	376.9	375.4	376.9	378.1	380.0	381.6	385.1	390.0	395.0
32.5°	363.8	363.5	361.2	360.9	361.2	363.5	363.8	366.4	369.8	374.5	378.8
35°	342.6	340.7	340.1	340.4	340.1	340.7	342.6	343.8	346.9	351.3	355.4
37.5°	322.4	319.9	318.8	317.6	318.8	319.9	322.4	322.6	325.8	328.7	334.2
40°	307.9	305.4	304.8	304.2	304.8	305.4	307.9	307.6	311.0	313.2	318.2
42.5°	291.6	290.7	290.3	289.2	290.3	290.7	291.6	293.3	295.3	298.5	302.2
45°	269.5	269.2	267.3	267.9	267.3	269.2	269.5	270.4	273.9	276.1	279.5
47.5°	246.1	244.8	243.4	244.3	243.4	244.8	246.1	247.4	249.7	252.4	256.9
50°	230.2	229.5	226.7	227.3	226.7	229.5	230.2	231.4	232.9	236.4	240.4
52.5°	214.2	211.8	210.8	210.3	210.8	211.8	214.2	215.4	217.2	221.2	224.2
55°	187.7	184.8	183.6	183.0	183.6	184.8	187.7	189.9	192.3	196.7	199.8
57.5°	161.7	160.9	160.0	160.6	160.0	160.9	161.7	165.3	167.8	171.2	175.0
60°	146.4	146.4	146.4	146.2	146.4	146.4	146.4	149.6	151.7	155.2	159.2
62.5°	134.7	134.0	133.7	134.1	133.7	134.0	134.7	136.1	138.3	140.5	144.0
65°	116.8	116.5	115.2	115.0	115.2	116.5	116.8	117.7	119.6	121.2	123.7
67.5°	99.9	98.7	98.4	97.9	98.4	98.7	99.9	100.7	101.9	104.0	105.2
70°	87.2	86.5	84.6	85.0	84.6	86.5	87.2	88.7	89.9	92.5	93.7
72.5°	73.4	72.7	72.4	71.9	72.4	72.7	73.4	74.9	76.2	78.9	81.0
75°	58.0	57.8	57.5	58.7	57.5	57.8	58.0	58.4	58.7	59.7	60.6
77.5°	46.6	46.6	46.7	46.2	46.7	46.6	46.6	46.6	46.6	47.0	47.2
80°	39.1	39.1	38.7	38.7	38.7	39.1	39.1	39.1	39.1	39.1	38.7
82.5°	31.3	31.6	31.7	31.2	31.7	31.6	31.3	31.8	32.0	31.6	31.7
85°	20.6	20.3	21.0	20.6	21.0	20.3	20.6	20.6	20.0	20.6	20.3
87.5°	10.8	10.4	10.4	10.7	10.4	10.4	10.8	10.4	10.3	10.3	9.9
90°	8.1	8.3	8.6	8.3	8.6	8.3	8.1	8.3	7.7	7.5	7.2
92.5°	15.0	14.1	14.4	13.9	14.4	14.1	15.0	15.5	17.0	19.2	24.3
95°	39.2	36.6	34.6	33.4	34.6	36.6	39.2	44.7	55.0	70.3	103.7
97.5°	114.2	101.3	93.4	91.0	93.4	101.3	114.2	135.5	169.9	207.1	258.5
100°	212.6	191.6	180.3	180.7	180.3	191.6	212.6	241.7	282.7	316.3	339.7
102.5°	297.7	281.0	271.7	265.0	271.7	281.0	297.7	320.3	346.3	365.9	366.6
105°	388.1	377.2	367.9	366.5	367.9	377.2	388.1	401.4	408.8	403.3	374.5
107.5°	434.4	430.6	427.5	424.9	427.5	430.6	434.4	434.1	423.9	398.6	351.8
110°	447.8	450.0	449.5	448.9	449.5	450.0	447.8	439.7	419.5	383.2	330.2



TEST NUMBER: P332272-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	444.3	451.4	453.6	453.7	453.6	451.4	444.3	429.5	403.6	362.9	308.8
115°	425.8	438.5	444.3	445.7	444.3	438.5	425.8	404.2	372.8	330.4	280.3
117.5°	395.5	410.0	418.2	420.2	418.2	410.0	395.5	372.9	341.0	303.0	259.8
120°	374.2	390.4	397.3	399.0	397.3	390.4	374.2	351.5	322.4	287.8	248.9
122.5°	354.9	369.4	377.0	379.2	377.0	369.4	354.9	334.7	307.6	275.6	240.4
125°	329.6	342.3	349.5	351.5	349.5	342.3	329.6	311.2	288.1	260.5	229.0
127.5°	309.5	320.3	326.9	328.6	326.9	320.3	309.5	293.1	272.1	247.1	219.2
130°	297.0	307.4	313.5	315.8	313.5	307.4	297.0	281.8	262.2	238.9	212.9
132.5°	285.8	296.1	301.5	303.1	301.5	296.1	285.8	271.4	252.7	231.0	207.2
135°	269.1	277.8	282.9	284.9	282.9	277.8	269.1	254.9	238.6	219.8	199.3
137.5°	251.3	260.1	264.4	265.8	264.4	260.1	251.3	239.5	225.2	209.0	192.2
140°	240.0	248.1	252.7	252.4	252.7	248.1	240.0	229.0	216.6	202.8	188.2
142.5°	228.9	236.1	240.2	239.9	240.2	236.1	228.9	219.6	208.8	196.8	184.3
145°	213.8	219.8	222.2	222.7	222.2	219.8	213.8	206.6	198.2	189.0	179.5
147.5°	202.0	206.1	208.3	208.6	208.3	206.1	202.0	196.6	190.6	183.2	175.6
150°	195.3	198.5	200.2	200.2	200.2	198.5	195.3	191.0	185.6	179.5	172.8
152.5°	189.3	192.2	193.3	193.3	193.3	192.2	189.3	186.0	181.4	176.0	170.3
155°	181.5	183.8	184.4	184.7	184.4	183.8	181.5	178.9	175.5	171.1	166.6
157.5°	174.6	176.3	176.8	176.8	176.8	176.3	174.6	172.4	169.7	166.3	162.5
160°	170.2	172.0	172.0	171.7	172.0	172.0	170.2	168.3	166.2	163.4	160.2
162.5°	165.9	167.4	167.4	167.1	167.4	167.4	165.9	164.6	162.8	160.1	157.4
165°	160.2	161.3	161.0	161.0	161.0	161.3	160.2	159.1	157.6	155.6	153.8
167.5°	154.7	155.6	155.3	155.3	155.3	155.6	154.7	154.3	153.2	152.1	150.7
170°	151.6	152.1	151.8	151.8	151.8	152.1	151.6	151.2	150.7	149.5	148.6
172.5°	148.8	149.4	148.9	148.6	148.9	149.4	148.8	148.7	148.4	147.5	146.8
175°	145.2	145.5	145.2	145.0	145.2	145.5	145.2	145.2	145.2	144.6	144.3
177.5°	143.0	143.2	142.8	142.8	142.8	143.2	143.0	143.2	143.2	143.0	142.8
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4



TEST NUMBER: P332272-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	696.3	699.8	703.3	706.5	711.5	713.7	717.0	718.2	721.9	727.5	732.0
5°	653.9	658.9	665.4	670.7	679.2	685.7	692.9	699.8	707.9	719.5	729.8
7.5°	618.0	622.9	630.8	640.7	650.0	659.3	669.1	678.4	690.1	706.6	723.0
10°	594.3	600.2	609.6	620.2	631.7	640.8	652.3	664.2	678.6	697.7	717.3
12.5°	573.8	578.2	589.1	599.2	612.2	623.8	635.1	649.0	665.4	685.7	709.3
15°	541.2	547.4	558.1	569.2	583.0	595.2	609.8	626.7	642.7	667.6	696.3
17.5°	508.4	518.0	529.0	541.7	551.9	568.7	584.6	601.9	621.5	648.0	679.5
20°	487.5	495.0	505.2	523.7	537.1	549.9	564.6	586.1	604.2	634.2	667.0
22.5°	469.7	475.2	486.7	502.0	517.6	532.4	547.4	567.9	590.3	618.7	654.3
25°	443.4	452.2	460.9	471.8	488.7	506.5	522.8	540.2	563.9	594.3	632.7
27.5°	417.8	425.7	434.3	447.8	460.6	477.2	494.2	514.2	539.6	571.7	610.7
30°	401.3	407.2	415.3	432.5	444.1	458.4	478.4	496.2	519.9	554.0	595.2
32.5°	384.3	392.0	400.8	414.0	428.3	441.9	460.2	479.5	503.7	537.2	579.4
35°	360.0	369.1	378.1	387.8	402.2	416.3	431.5	452.8	477.4	510.0	551.5
37.5°	337.8	345.0	352.5	364.4	378.1	391.4	405.7	426.6	449.9	484.9	523.0
40°	323.5	330.1	335.7	348.2	361.3	375.7	389.7	408.1	433.1	465.9	502.8
42.5°	308.0	314.1	321.7	331.9	346.1	358.2	372.3	389.6	413.1	446.5	478.7
45°	284.8	291.6	298.2	307.9	322.0	333.8	346.3	362.9	386.9	414.4	443.1
47.5°	260.7	267.5	275.0	284.4	296.6	308.7	321.1	335.8	357.8	384.7	404.1
50°	245.2	250.8	258.3	267.6	278.8	291.6	302.9	318.9	339.7	361.0	377.9
52.5°	229.2	234.2	242.8	252.7	263.1	274.2	286.2	299.9	318.8	338.8	352.1
55°	204.2	210.5	217.7	227.3	237.7	247.0	258.5	272.6	287.6	302.6	311.7
57.5°	180.9	186.1	192.2	202.2	211.1	222.3	232.6	243.6	257.5	268.7	274.7
60°	164.0	168.6	176.4	185.2	193.6	203.3	215.2	226.1	236.7	245.7	250.5
62.5°	148.0	153.4	160.2	168.2	177.4	186.5	196.9	206.1	215.5	223.3	226.5
65°	127.1	131.5	136.5	144.0	151.5	160.9	168.9	178.3	185.2	189.6	192.3
67.5°	108.1	111.0	114.8	119.8	127.2	135.3	143.2	150.5	156.3	159.2	161.8
70°	95.9	97.8	100.5	105.6	111.2	118.4	126.5	131.8	136.8	139.3	141.8
72.5°	83.6	86.0	88.5	92.5	97.2	102.4	108.3	114.8	117.6	120.5	122.1
75°	63.4	66.9	70.3	72.7	75.9	80.0	85.3	89.3	90.9	93.4	93.7
77.5°	47.9	48.6	51.1	54.2	56.8	59.8	63.1	66.8	67.5	68.8	69.6
80°	39.4	39.4	39.4	41.3	44.4	46.6	49.7	51.5	52.7	53.1	53.4
82.5°	31.6	31.6	31.4	31.7	32.9	34.0	36.9	39.1	40.0	39.9	39.1
85°	20.6	20.0	20.0	19.6	20.0	19.3	19.1	20.3	22.2	22.2	21.5
87.5°	9.9	9.7	9.8	9.4	8.9	8.5	7.7	7.7	7.6	8.5	8.1
90°	6.9	7.2	6.4	5.5	4.6	3.8	3.2	2.6	1.7	1.1	0.6
92.5°	33.4	44.3	48.8	36.6	24.2	16.6	12.4	9.9	7.7	5.3	3.6
95°	138.6	170.9	152.1	104.8	62.0	37.4	26.3	18.8	13.9	10.7	9.8
97.5°	283.2	264.8	193.9	115.0	66.7	43.3	31.1	23.7	19.5	17.0	16.7
100°	329.6	272.9	184.4	108.6	66.0	45.8	34.6	27.6	23.6	21.6	21.4
102.5°	331.9	257.9	170.6	103.1	66.9	48.8	38.5	32.3	28.5	26.7	26.2
105°	314.3	231.6	153.6	99.1	69.5	53.9	44.9	39.5	36.0	34.3	33.4
107.5°	283.6	208.5	142.8	98.8	74.2	60.5	52.2	47.0	43.7	42.0	41.2
110°	264.2	195.3	138.6	100.0	78.1	65.1	57.1	52.2	49.0	47.5	46.6



TEST NUMBER: P332272-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	247.4	186.5	136.2	102.3	82.0	70.0	62.1	57.2	54.1	52.6	51.8
115°	227.1	177.2	135.4	106.0	88.5	77.5	69.7	64.8	62.0	60.3	59.0
117.5°	214.7	171.6	135.9	111.0	95.3	84.5	77.3	71.8	69.1	67.7	66.4
120°	208.3	169.1	136.9	114.6	99.7	89.3	82.1	76.6	73.8	72.3	71.4
122.5°	203.0	167.5	138.4	118.1	104.3	94.2	86.5	81.3	78.1	76.7	75.8
125°	196.2	165.3	140.9	123.6	111.0	100.9	93.0	87.6	84.4	82.7	82.1
127.5°	190.2	164.4	143.7	128.1	116.7	107.0	99.1	93.1	89.9	87.7	86.9
130°	186.9	163.6	145.5	131.1	120.2	110.6	102.9	96.8	93.4	90.7	89.9
132.5°	184.0	163.4	146.9	133.9	123.1	113.9	106.3	100.3	96.1	93.3	92.2
135°	180.1	163.1	149.0	137.5	127.6	118.7	111.0	104.8	100.5	97.3	96.2
137.5°	176.7	162.4	150.3	140.1	130.8	122.1	115.0	108.9	104.4	101.3	100.0
140°	174.6	162.2	151.2	141.5	132.8	124.5	117.2	111.5	106.9	104.0	102.6
142.5°	172.8	161.8	152.0	142.8	134.4	126.3	119.6	113.8	109.7	106.6	105.3
145°	170.2	161.0	152.4	144.3	136.6	129.1	122.5	117.6	113.2	110.6	109.7
147.5°	167.9	160.0	152.4	145.3	138.3	131.4	125.8	121.1	117.3	114.8	114.3
150°	166.2	159.1	152.4	145.5	139.4	132.8	127.6	123.6	119.8	117.6	117.2
152.5°	164.4	157.9	151.7	145.9	140.1	134.4	129.5	125.9	122.6	120.3	120.3
155°	161.6	155.9	151.0	146.1	141.5	136.6	132.6	129.4	126.5	124.7	124.7
157.5°	158.5	154.1	150.0	146.3	142.2	138.3	135.2	132.5	130.0	128.6	128.3
160°	156.5	152.7	149.5	146.3	142.9	139.4	136.6	134.5	132.2	131.1	131.1
162.5°	154.3	151.3	148.6	146.1	143.2	140.1	137.7	135.9	134.1	133.1	133.1
165°	151.6	149.3	147.2	145.5	143.5	141.2	139.2	138.0	136.6	136.0	136.2
167.5°	148.9	147.2	145.9	145.0	143.4	141.8	140.5	139.7	138.6	138.3	138.6
170°	147.2	145.8	145.0	144.3	143.2	141.8	141.2	140.6	139.7	139.4	140.0
172.5°	145.6	144.6	144.2	144.1	143.2	141.9	141.6	141.3	140.6	140.6	141.0
175°	143.7	143.2	143.2	143.5	142.9	142.4	142.0	142.0	141.5	141.8	142.0
177.5°	142.6	142.4	142.6	143.0	142.6	142.4	142.4	142.4	142.1	142.4	142.6
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4



TEST NUMBER: P332272-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	733.4	736.2	739.7	744.9	748.9	752.4	753.2	754.2	756.7	760.9	764.2
5°	738.3	745.4	756.9	768.2	780.4	790.4	799.7	806.3	812.5	825.7	836.3
7.5°	736.7	752.7	770.8	791.0	811.4	831.2	849.5	866.0	882.4	901.5	923.2
10°	735.7	754.5	778.8	804.7	833.2	861.0	887.8	908.7	933.1	955.0	982.8
12.5°	731.0	758.0	787.1	820.2	855.2	887.2	922.5	951.5	979.3	1010.9	1043.2
15°	724.8	757.6	794.4	838.5	891.5	930.3	966.5	1016.8	1051.1	1085.5	1131.7
17.5°	713.5	753.5	799.6	856.7	901.1	953.1	1007.5	1047.3	1093.6	1142.0	1183.8
20°	704.5	751.1	802.6	858.8	915.3	971.8	1024.6	1072.0	1119.8	1175.7	1210.1
22.5°	695.5	741.5	795.1	854.8	915.5	975.0	1034.8	1090.5	1144.3	1200.7	1244.6
25°	676.4	731.0	789.1	850.0	910.0	975.5	1046.8	1108.9	1175.4	1233.5	1275.0
27.5°	657.0	707.1	764.9	826.7	893.3	970.9	1054.6	1125.3	1191.9	1233.5	1246.5
30°	639.5	692.6	745.7	808.5	880.6	967.1	1056.1	1137.0	1191.6	1209.7	1196.3
32.5°	621.8	669.9	722.5	786.8	863.4	957.9	1058.1	1130.0	1162.9	1149.1	1094.4
35°	590.5	633.9	684.9	749.2	837.2	952.8	1049.9	1098.6	1090.5	1012.4	909.3
37.5°	557.0	592.4	639.5	706.8	810.1	932.5	1014.4	1021.6	951.3	831.4	712.4
40°	530.5	562.4	610.8	681.1	789.1	912.5	978.7	949.7	840.7	707.3	608.0
42.5°	504.8	531.7	578.3	654.1	769.2	885.3	925.4	862.2	736.5	610.3	520.1
45°	461.2	486.5	533.4	611.1	728.2	833.2	827.9	718.0	592.1	490.6	415.6
47.5°	419.9	442.0	486.0	565.3	680.2	755.0	705.4	588.5	481.7	400.3	346.8
50°	390.7	412.5	456.2	534.6	641.7	696.3	625.5	512.7	415.0	347.6	305.1
52.5°	362.6	384.0	424.0	500.3	595.3	627.9	551.8	447.3	365.8	307.6	271.1
55°	323.5	339.7	375.7	448.7	519.6	527.1	450.0	362.6	295.4	254.8	229.8
57.5°	283.6	297.6	333.0	391.3	441.0	437.1	363.9	288.4	243.1	213.0	194.9
60°	257.6	271.3	302.6	352.5	390.0	376.9	309.8	248.9	210.2	188.0	173.7
62.5°	233.4	244.1	273.4	309.8	336.8	322.0	264.8	214.4	183.7	165.0	153.6
65°	198.3	207.0	230.5	249.5	264.5	250.1	202.7	167.7	145.5	132.4	124.6
67.5°	164.9	170.5	185.3	192.2	202.8	187.0	152.4	129.0	116.3	105.3	99.9
70°	144.0	148.1	155.8	161.4	164.3	148.1	122.4	105.3	94.7	86.8	83.4
72.5°	122.9	126.5	128.1	132.7	131.3	116.0	98.4	84.8	77.1	71.8	67.4
75°	94.0	95.6	94.0	92.1	88.1	77.5	65.3	58.4	52.7	50.3	48.8
77.5°	68.5	68.0	65.9	62.9	56.0	49.3	42.8	40.4	38.1	36.7	36.2
80°	52.7	51.5	49.7	45.0	39.1	34.3	32.8	31.2	30.3	28.7	28.5
82.5°	39.3	38.6	35.4	31.5	27.3	25.1	23.8	23.2	22.3	21.5	21.4
85°	21.0	20.0	16.6	14.3	13.8	13.1	12.8	12.8	11.6	11.3	11.3
87.5°	7.0	5.6	5.5	4.9	5.0	4.6	5.1	4.7	4.7	4.9	4.4
90°	1.1	1.7	2.6	3.2	3.8	4.6	5.5	6.4	7.2	6.9	7.2
92.5°	5.3	7.7	9.9	12.4	16.6	24.2	36.6	48.8	44.3	33.4	24.3
95°	10.7	13.9	18.8	26.3	37.4	62.0	104.8	152.1	170.9	138.6	103.7
97.5°	17.0	19.5	23.7	31.1	43.3	66.7	115.0	193.9	264.8	283.2	258.5
100°	21.6	23.6	27.6	34.6	45.8	66.0	108.6	184.4	272.9	329.6	339.7
102.5°	26.7	28.5	32.3	38.5	48.8	66.9	103.1	170.6	257.9	331.9	366.6
105°	34.3	36.0	39.5	44.9	53.9	69.5	99.1	153.6	231.6	314.3	374.5
107.5°	42.0	43.7	47.0	52.2	60.5	74.2	98.8	142.8	208.5	283.6	351.8
110°	47.5	49.0	52.2	57.1	65.1	78.1	100.0	138.6	195.3	264.2	330.2



TEST NUMBER: P332272-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	52.6	54.1	57.2	62.1	70.0	82.0	102.3	136.2	186.5	247.4	308.8
115°	60.3	62.0	64.8	69.7	77.5	88.5	106.0	135.4	177.2	227.1	280.3
117.5°	67.7	69.1	71.8	77.3	84.5	95.3	111.0	135.9	171.6	214.7	259.8
120°	72.3	73.8	76.6	82.1	89.3	99.7	114.6	136.9	169.1	208.3	248.9
122.5°	76.7	78.1	81.3	86.5	94.2	104.3	118.1	138.4	167.5	203.0	240.4
125°	82.7	84.4	87.6	93.0	100.9	111.0	123.6	140.9	165.3	196.2	229.0
127.5°	87.7	89.9	93.1	99.1	107.0	116.7	128.1	143.7	164.4	190.2	219.2
130°	90.7	93.4	96.8	102.9	110.6	120.2	131.1	145.5	163.6	186.9	212.9
132.5°	93.3	96.1	100.3	106.3	113.9	123.1	133.9	146.9	163.4	184.0	207.2
135°	97.3	100.5	104.8	111.0	118.7	127.6	137.5	149.0	163.1	180.1	199.3
137.5°	101.3	104.4	108.9	115.0	122.1	130.8	140.1	150.3	162.4	176.7	192.2
140°	104.0	106.9	111.5	117.2	124.5	132.8	141.5	151.2	162.2	174.6	188.2
142.5°	106.6	109.7	113.8	119.6	126.3	134.4	142.8	152.0	161.8	172.8	184.3
145°	110.6	113.2	117.6	122.5	129.1	136.6	144.3	152.4	161.0	170.2	179.5
147.5°	114.8	117.3	121.1	125.8	131.4	138.3	145.3	152.4	160.0	167.9	175.6
150°	117.6	119.8	123.6	127.6	132.8	139.4	145.5	152.4	159.1	166.2	172.8
152.5°	120.3	122.6	125.9	129.5	134.4	140.1	145.9	151.7	157.9	164.4	170.3
155°	124.7	126.5	129.4	132.6	136.6	141.5	146.1	151.0	155.9	161.6	166.6
157.5°	128.6	130.0	132.5	135.2	138.3	142.2	146.3	150.0	154.1	158.5	162.5
160°	131.1	132.2	134.5	136.6	139.4	142.9	146.3	149.5	152.7	156.5	160.2
162.5°	133.1	134.1	135.9	137.7	140.1	143.2	146.1	148.6	151.3	154.3	157.4
165°	136.0	136.6	138.0	139.2	141.2	143.5	145.5	147.2	149.3	151.6	153.8
167.5°	138.3	138.6	139.7	140.5	141.8	143.4	145.0	145.9	147.2	148.9	150.7
170°	139.4	139.7	140.6	141.2	141.8	143.2	144.3	145.0	145.8	147.2	148.6
172.5°	140.6	140.6	141.3	141.6	141.9	143.2	144.1	144.2	144.6	145.6	146.8
175°	141.8	141.5	142.0	142.0	142.4	142.9	143.5	143.2	143.2	143.7	144.3
177.5°	142.4	142.1	142.4	142.4	142.4	142.6	143.0	142.6	142.4	142.6	142.8
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4



TEST NUMBER: P332272-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	769.5	769.5	770.5	774.2	774.7	778.0	776.9
5°	845.6	851.6	853.8	863.2	868.8	871.2	866.3
7.5°	938.8	955.5	963.5	973.3	981.9	984.6	977.8
10°	1006.8	1024.3	1038.9	1048.0	1056.5	1062.0	1069.3
12.5°	1072.4	1094.0	1107.9	1120.7	1129.4	1136.5	1137.7
15°	1143.9	1176.3	1201.0	1219.1	1228.2	1232.9	1231.0
17.5°	1215.9	1245.9	1263.6	1282.0	1294.5	1295.2	1295.6
20°	1256.6	1286.0	1306.3	1320.0	1334.1	1333.4	1336.5
22.5°	1283.9	1306.9	1322.5	1332.4	1337.3	1334.9	1335.5
25°	1296.6	1303.4	1300.6	1284.7	1280.7	1266.0	1268.4
27.5°	1230.9	1198.4	1164.8	1121.5	1087.4	1060.2	1061.6
30°	1141.7	1084.2	1018.6	963.7	914.4	900.6	871.2
32.5°	1017.0	930.8	854.0	802.8	760.4	748.9	723.3
35°	805.7	721.9	642.9	595.5	576.7	550.6	550.2
37.5°	626.2	552.5	510.8	475.2	456.5	440.6	439.0
40°	526.8	469.4	437.8	412.2	393.8	381.9	379.1
42.5°	457.4	410.9	381.3	365.5	351.3	345.2	340.6
45°	373.5	342.3	321.6	307.3	300.7	296.0	293.5
47.5°	312.4	291.5	277.4	267.9	262.5	257.6	258.9
50°	279.2	262.0	251.7	242.6	238.6	235.1	235.5
52.5°	252.4	237.0	228.7	222.2	217.1	214.7	213.4
55°	214.3	204.6	196.1	191.4	188.6	185.2	184.3
57.5°	182.7	175.2	168.4	163.1	162.4	159.1	159.5
60°	161.8	155.5	149.9	147.1	144.9	142.1	143.0
62.5°	144.6	139.3	134.1	131.8	129.6	127.6	128.0
65°	118.4	113.3	110.2	109.0	108.0	107.1	106.2
67.5°	94.3	91.2	89.3	86.6	84.7	84.4	83.4
70°	79.3	75.3	71.8	68.4	67.4	67.1	67.4
72.5°	63.6	61.0	60.1	58.4	58.2	57.4	58.0
75°	47.8	46.9	46.2	45.0	45.0	45.0	45.0
77.5°	35.2	34.7	34.3	34.0	33.8	33.3	33.3
80°	27.5	27.1	26.6	26.6	26.3	26.6	26.3
82.5°	20.7	20.7	20.1	20.1	19.7	19.6	19.7
85°	10.6	10.3	10.9	10.3	10.6	10.0	10.6
87.5°	4.5	4.6	4.4	4.3	4.2	4.7	4.2
90°	7.5	7.7	8.3	8.1	8.3	8.6	8.3
92.5°	19.2	17.0	15.5	15.0	14.1	14.4	13.9
95°	70.3	55.0	44.7	39.2	36.6	34.6	33.4
97.5°	207.1	169.9	135.5	114.2	101.3	93.4	91.0
100°	316.3	282.7	241.7	212.6	191.6	180.3	180.7
102.5°	365.9	346.3	320.3	297.7	281.0	271.7	265.0
105°	403.3	408.8	401.4	388.1	377.2	367.9	366.5
107.5°	398.6	423.9	434.1	434.4	430.6	427.5	424.9
110°	383.2	419.5	439.7	447.8	450.0	449.5	448.9



TEST NUMBER: P332272-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	362.9	403.6	429.5	444.3	451.4	453.6	453.7
115°	330.4	372.8	404.2	425.8	438.5	444.3	445.7
117.5°	303.0	341.0	372.9	395.5	410.0	418.2	420.2
120°	287.8	322.4	351.5	374.2	390.4	397.3	399.0
122.5°	275.6	307.6	334.7	354.9	369.4	377.0	379.2
125°	260.5	288.1	311.2	329.6	342.3	349.5	351.5
127.5°	247.1	272.1	293.1	309.5	320.3	326.9	328.6
130°	238.9	262.2	281.8	297.0	307.4	313.5	315.8
132.5°	231.0	252.7	271.4	285.8	296.1	301.5	303.1
135°	219.8	238.6	254.9	269.1	277.8	282.9	284.9
137.5°	209.0	225.2	239.5	251.3	260.1	264.4	265.8
140°	202.8	216.6	229.0	240.0	248.1	252.7	252.4
142.5°	196.8	208.8	219.6	228.9	236.1	240.2	239.9
145°	189.0	198.2	206.6	213.8	219.8	222.2	222.7
147.5°	183.2	190.6	196.6	202.0	206.1	208.3	208.6
150°	179.5	185.6	191.0	195.3	198.5	200.2	200.2
152.5°	176.0	181.4	186.0	189.3	192.2	193.3	193.3
155°	171.1	175.5	178.9	181.5	183.8	184.4	184.7
157.5°	166.3	169.7	172.4	174.6	176.3	176.8	176.8
160°	163.4	166.2	168.3	170.2	172.0	172.0	171.7
162.5°	160.1	162.8	164.6	165.9	167.4	167.4	167.1
165°	155.6	157.6	159.1	160.2	161.3	161.0	161.0
167.5°	152.1	153.2	154.3	154.7	155.6	155.3	155.3
170°	149.5	150.7	151.2	151.6	152.1	151.8	151.8
172.5°	147.5	148.4	148.7	148.8	149.4	148.9	148.6
175°	144.6	145.2	145.2	145.2	145.5	145.2	145.0
177.5°	143.0	143.2	143.2	143.0	143.2	142.8	142.8
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4

(END OF REPORT)