

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332277-930

Luminaire Tested: **S123RDIP-S560D585U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332277-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S560D585U930-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3458.2 lumens  
Efficiency: N/A  
Efficacy: 105.4 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 32.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332277-930

CATALOG NUMBER: S123RDIP-S560D585U930-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332277-930

CATALOG NUMBER: S123RDIP-S560D585U930-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	53
1	99	95	91	88	92	88	85	82	75	73	71	63	62	60	53	52	51	46
2	91	84	78	73	84	78	73	68	67	63	60	56	54	51	47	45	44	39
3	83	74	67	61	77	69	63	58	59	55	51	50	47	44	42	40	38	34
4	76	66	58	52	70	61	55	50	53	48	44	45	42	38	38	35	33	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26
6	65	53	45	40	60	50	43	38	43	38	34	37	33	30	32	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	27	29	26	23	21
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	23	21	19
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	21	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7851	7851	7851	7851
5°	9360	7886	6944	7886
10°	11687	7840	6274	7840
15°	13718	7759	5721	7759
20°	15309	7640	5251	7640
25°	15064	7514	4962	7514
30°	10828	7398	4666	7398
35°	7230	7247	4473	7247
40°	5327	7065	4274	7065
45°	4468	6745	4078	6745
50°	3944	6328	3806	6328
55°	3459	5849	3434	5849
60°	3078	5393	3147	5393
65°	2705	4898	2929	4898
70°	2121	4463	2675	4463
75°	1871	3897	2441	3897
80°	1630	3310	2399	3310
85°	1309	2655	2544	2655



TEST NUMBER: P332277-930

CATALOG NUMBER: S123RDIP-S560D585U930-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	71.7	2.1
10°-20°	224.1	6.5
20°-30°	352.1	10.2
30°-40°	367.3	10.6
40°-50°	314.4	9.1
50°-60°	239.6	6.9
60°-70°	153.6	4.4
70°-80°	73.9	2.1
80°-90°	21.3	0.6
90°-100°	38.6	1.1
100°-110°	115.4	3.3
110°-120°	196.3	5.7
120°-130°	258.2	7.5
130°-140°	290.3	8.4
140°-150°	285.3	8.3
150°-160°	240.2	6.9
160°-170°	159.9	4.6
170°-180°	56.0	1.6
0°-30°	647.9	18.7
0°-40°	1015.3	29.4
0°-60°	1569.3	45.4
0°-90°	1818.0	52.6
90°-120°	350.3	10.1
90°-150°	1184.1	34.2
90°-180°	1640.0	47.4
0°-180°	3458.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	729	729	729	729	729	
5°	866	730	643	730	866	89
15°	1231	696	513	696	1231	349
25°	1268	633	418	633	1268	545
35°	550	552	340	552	550	361
45°	294	443	268	443	294	231
55°	184	312	183	312	184	167
65°	106	192	115	192	106	104
75°	45	94	59	94	45	48
85°	11	22	21	22	11	13
90°	14	0	14	0	14	7
95°	36	28	36	28	36	37
105°	111	105	111	105	111	117
115°	198	198	198	198	198	196
125°	286	289	286	289	286	256
135°	375	375	375	375	375	288
145°	455	455	455	455	455	284
155°	520	521	520	521	520	240
165°	566	568	566	568	566	160
175°	588	591	588	591	588	56
180°	592	592	592	592	592	



TEST NUMBER: P332277-930

CATALOG NUMBER: S123RDIP-S560D585U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	776.9	778.0	774.7	774.2	770.5	769.5	769.5	764.2	760.9	756.7	754.2
5°	866.3	871.2	868.8	863.2	853.8	851.6	845.6	836.3	825.7	812.5	806.3
7.5°	977.8	984.6	981.9	973.3	963.5	955.5	938.8	923.2	901.5	882.4	866.0
10°	1069.3	1062.0	1056.5	1048.0	1038.9	1024.3	1006.8	982.8	955.0	933.1	908.7
12.5°	1137.7	1136.5	1129.4	1120.7	1107.9	1094.0	1072.4	1043.2	1010.9	979.3	951.5
15°	1231.0	1232.9	1228.2	1219.1	1201.0	1176.3	1143.9	1131.7	1085.5	1051.1	1016.8
17.5°	1295.6	1295.2	1294.5	1282.0	1263.6	1245.9	1215.9	1183.8	1142.0	1093.6	1047.3
20°	1336.5	1333.4	1334.1	1320.0	1306.3	1286.0	1256.6	1210.1	1175.7	1119.8	1072.0
22.5°	1335.5	1334.9	1337.3	1332.4	1322.5	1306.9	1283.9	1244.6	1200.7	1144.3	1090.5
25°	1268.4	1266.0	1280.7	1284.7	1300.6	1303.4	1296.6	1275.0	1233.5	1175.4	1108.9
27.5°	1061.6	1060.2	1087.4	1121.5	1164.8	1198.4	1230.9	1246.5	1233.5	1191.9	1125.3
30°	871.2	900.6	914.4	963.7	1018.6	1084.2	1141.7	1196.3	1209.7	1191.6	1137.0
32.5°	723.3	748.9	760.4	802.8	854.0	930.8	1017.0	1094.4	1149.1	1162.9	1130.0
35°	550.2	550.6	576.7	595.5	642.9	721.9	805.7	909.3	1012.4	1090.5	1098.6
37.5°	439.0	440.6	456.5	475.2	510.8	552.5	626.2	712.4	831.4	951.3	1021.6
40°	379.1	381.9	393.8	412.2	437.8	469.4	526.8	608.0	707.3	840.7	949.7
42.5°	340.6	345.2	351.3	365.5	381.3	410.9	457.4	520.1	610.3	736.5	862.2
45°	293.5	296.0	300.7	307.3	321.6	342.3	373.5	415.6	490.6	592.1	718.0
47.5°	258.9	257.6	262.5	267.9	277.4	291.5	312.4	346.8	400.3	481.7	588.5
50°	235.5	235.1	238.6	242.6	251.7	262.0	279.2	305.1	347.6	415.0	512.7
52.5°	213.4	214.7	217.1	222.2	228.7	237.0	252.4	271.1	307.6	365.8	447.3
55°	184.3	185.2	188.6	191.4	196.1	204.6	214.3	229.8	254.8	295.4	362.6
57.5°	159.5	159.1	162.4	163.1	168.4	175.2	182.7	194.9	213.0	243.1	288.4
60°	143.0	142.1	144.9	147.1	149.9	155.5	161.8	173.7	188.0	210.2	248.9
62.5°	128.0	127.6	129.6	131.8	134.1	139.3	144.6	153.6	165.0	183.7	214.4
65°	106.2	107.1	108.0	109.0	110.2	113.3	118.4	124.6	132.4	145.5	167.7
67.5°	83.4	84.4	84.7	86.6	89.3	91.2	94.3	99.9	105.3	116.3	129.0
70°	67.4	67.1	67.4	68.4	71.8	75.3	79.3	83.4	86.8	94.7	105.3
72.5°	58.0	57.4	58.2	58.4	60.1	61.0	63.6	67.4	71.8	77.1	84.8
75°	45.0	45.0	45.0	45.0	46.2	46.9	47.8	48.8	50.3	52.7	58.4
77.5°	33.3	33.3	33.8	34.0	34.3	34.7	35.2	36.2	36.7	38.1	40.4
80°	26.3	26.6	26.3	26.6	26.6	27.1	27.5	28.5	28.7	30.3	31.2
82.5°	19.7	19.6	19.7	20.1	20.1	20.7	20.7	21.4	21.5	22.3	23.2
85°	10.6	10.0	10.6	10.3	10.9	10.3	10.6	11.3	11.3	11.6	12.8
87.5°	5.3	5.7	5.2	5.4	5.4	5.5	5.5	5.4	5.8	5.5	5.5
90°	13.9	13.8	13.5	13.4	13.1	12.8	12.4	12.0	11.6	11.2	9.8
92.5°	18.8	18.9	19.0	19.2	19.3	19.2	18.8	18.5	18.2	17.9	17.1
95°	36.3	36.3	36.3	36.3	36.3	36.0	35.6	35.2	34.8	34.4	33.6
97.5°	55.8	55.8	55.8	55.9	55.9	55.8	55.3	54.8	54.3	53.9	53.2
100°	70.7	70.4	70.3	70.0	69.9	69.6	69.3	69.0	68.6	68.3	67.8
102.5°	85.9	86.0	86.0	86.1	86.1	85.9	85.7	85.4	85.0	84.7	84.1
105°	110.7	110.5	110.2	110.1	109.8	109.7	109.7	109.7	109.7	109.7	108.8
107.5°	136.5	136.6	136.7	136.8	137.0	136.8	136.5	136.2	135.8	135.5	135.2
110°	153.9	154.2	154.3	154.6	154.7	154.7	154.3	153.8	153.4	153.0	152.8



TEST NUMBER: P332277-930

CATALOG NUMBER: S123RDIP-S560D585U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	172.5	172.6	172.6	172.7	172.7	172.4	171.9	171.5	171.0	170.5	170.5
115°	198.1	198.2	198.3	198.4	198.5	198.5	198.4	198.3	198.2	198.1	198.3
117.5°	224.0	224.4	224.6	224.9	225.2	225.3	225.3	225.4	225.4	225.4	225.8
120°	242.3	242.5	242.7	242.9	243.1	243.3	243.4	243.4	243.6	243.7	244.2
122.5°	259.8	260.1	260.3	260.7	260.9	261.2	261.5	261.7	262.0	262.3	262.5
125°	286.0	286.4	286.8	287.2	287.6	288.0	288.5	288.9	289.3	289.8	289.9
127.5°	312.1	312.6	313.1	313.6	314.1	314.5	315.1	315.7	316.3	316.9	317.1
130°	329.2	330.0	330.7	331.4	332.2	332.7	333.1	333.5	333.9	334.4	334.7
132.5°	347.1	347.6	348.2	348.8	349.4	349.8	350.3	350.8	351.3	351.9	352.0
135°	374.8	375.0	375.2	375.4	375.6	375.9	376.3	376.7	377.2	377.6	377.7
137.5°	399.3	399.7	400.1	400.5	400.9	401.3	401.7	402.1	402.6	403.0	402.8
140°	415.3	416.0	416.7	417.4	418.2	418.6	418.7	418.8	418.9	419.0	418.9
142.5°	431.6	432.2	432.8	433.3	433.9	434.2	434.3	434.4	434.6	434.6	434.5
145°	455.3	455.7	456.1	456.5	456.9	457.2	457.3	457.4	457.5	457.6	457.3
147.5°	476.3	477.0	477.5	478.2	478.7	479.1	479.1	479.1	479.1	479.1	478.8
150°	489.7	490.3	490.9	491.5	492.2	492.4	492.4	492.4	492.4	492.4	492.3
152.5°	502.7	503.3	503.8	504.3	504.8	505.1	504.9	504.8	504.5	504.3	504.3
155°	520.4	521.1	521.8	522.5	523.3	523.4	523.0	522.6	522.2	521.8	521.7
157.5°	536.5	537.0	537.6	538.2	538.7	538.8	538.4	538.0	537.5	537.1	537.0
160°	546.9	547.3	547.7	548.1	548.5	548.5	548.0	547.5	546.9	546.4	546.4
162.5°	554.7	555.4	556.0	556.7	557.3	557.4	556.9	556.4	555.9	555.4	555.3
165°	566.0	566.7	567.4	568.1	568.8	568.9	568.3	567.7	567.0	566.4	566.4
167.5°	575.5	576.2	576.8	577.5	578.1	578.1	577.5	576.8	576.2	575.5	575.4
170°	580.3	581.1	581.8	582.5	583.3	583.3	582.5	581.8	581.1	580.3	580.3
172.5°	584.1	584.8	585.5	586.3	587.0	587.0	586.4	585.7	585.1	584.5	584.5
175°	588.2	589.0	589.7	590.4	591.2	591.3	590.6	590.0	589.4	588.7	588.7
177.5°	590.5	591.1	591.7	592.2	592.8	592.9	592.4	591.9	591.3	590.8	590.8
180°	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0



TEST NUMBER: P332277-930

CATALOG NUMBER: S123RDIP-S560D585U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	753.2	752.4	748.9	744.9	739.7	736.2	733.4	732.0	727.5	721.9	718.2
5°	799.7	790.4	780.4	768.2	756.9	745.4	738.3	729.8	719.5	707.9	699.8
7.5°	849.5	831.2	811.4	791.0	770.8	752.7	736.7	723.0	706.6	690.1	678.4
10°	887.8	861.0	833.2	804.7	778.8	754.5	735.7	717.3	697.7	678.6	664.2
12.5°	922.5	887.2	855.2	820.2	787.1	758.0	731.0	709.3	685.7	665.4	649.0
15°	966.5	930.3	891.5	838.5	794.4	757.6	724.8	696.3	667.6	642.7	626.7
17.5°	1007.5	953.1	901.1	856.7	799.6	753.5	713.5	679.5	648.0	621.5	601.9
20°	1024.6	971.8	915.3	858.8	802.6	751.1	704.5	667.0	634.2	604.2	586.1
22.5°	1034.8	975.0	915.5	854.8	795.1	741.5	695.5	654.3	618.7	590.3	567.9
25°	1046.8	975.5	910.0	850.0	789.1	731.0	676.4	632.7	594.3	563.9	540.2
27.5°	1054.6	970.9	893.3	826.7	764.9	707.1	657.0	610.7	571.7	539.6	514.2
30°	1056.1	967.1	880.6	808.5	745.7	692.6	639.5	595.2	554.0	519.9	496.2
32.5°	1058.1	957.9	863.4	786.8	722.5	669.9	621.8	579.4	537.2	503.7	479.5
35°	1049.9	952.8	837.2	749.2	684.9	633.9	590.5	551.5	510.0	477.4	452.8
37.5°	1014.4	932.5	810.1	706.8	639.5	592.4	557.0	523.0	484.9	449.9	426.6
40°	978.7	912.5	789.1	681.1	610.8	562.4	530.5	502.8	465.9	433.1	408.1
42.5°	925.4	885.3	769.2	654.1	578.3	531.7	504.8	478.7	446.5	413.1	389.6
45°	827.9	833.2	728.2	611.1	533.4	486.5	461.2	443.1	414.4	386.9	362.9
47.5°	705.4	755.0	680.2	565.3	486.0	442.0	419.9	404.1	384.7	357.8	335.8
50°	625.5	696.3	641.7	534.6	456.2	412.5	390.7	377.9	361.0	339.7	318.9
52.5°	551.8	627.9	595.3	500.3	424.0	384.0	362.6	352.1	338.8	318.8	299.9
55°	450.0	527.1	519.6	448.7	375.7	339.7	323.5	311.7	302.6	287.6	272.6
57.5°	363.9	437.1	441.0	391.3	333.0	297.6	283.6	274.7	268.7	257.5	243.6
60°	309.8	376.9	390.0	352.5	302.6	271.3	257.6	250.5	245.7	236.7	226.1
62.5°	264.8	322.0	336.8	309.8	273.4	244.1	233.4	226.5	223.3	215.5	206.1
65°	202.7	250.1	264.5	249.5	230.5	207.0	198.3	192.3	189.6	185.2	178.3
67.5°	152.4	187.0	202.8	192.2	185.3	170.5	164.9	161.8	159.2	156.3	150.5
70°	122.4	148.1	164.3	161.4	155.8	148.1	144.0	141.8	139.3	136.8	131.8
72.5°	98.4	116.0	131.3	132.7	128.1	126.5	122.9	122.1	120.5	117.6	114.8
75°	65.3	77.5	88.1	92.1	94.0	95.6	94.0	93.7	93.4	90.9	89.3
77.5°	42.8	49.3	56.0	62.9	65.9	68.0	68.5	69.6	68.8	67.5	66.8
80°	32.8	34.3	39.1	45.0	49.7	51.5	52.7	53.4	53.1	52.7	51.5
82.5°	23.8	25.1	27.3	31.5	35.4	38.6	39.3	39.1	39.9	40.0	39.1
85°	12.8	13.1	13.8	14.3	16.6	20.0	21.0	21.5	22.2	22.2	20.3
87.5°	5.7	5.1	5.4	5.1	5.7	5.8	7.0	8.1	8.6	7.7	8.0
90°	8.5	7.1	5.8	4.6	3.6	2.5	1.5	0.5	1.5	2.5	3.6
92.5°	16.3	15.6	14.8	14.1	13.4	12.6	12.0	11.3	12.0	12.6	13.4
95°	32.8	32.0	31.1	30.3	29.6	28.9	28.1	27.5	28.1	28.9	29.6
97.5°	52.7	52.0	51.4	50.9	50.4	49.8	49.2	48.8	49.2	49.8	50.4
100°	67.3	66.8	66.3	65.7	65.1	64.5	63.8	63.3	63.8	64.5	65.1
102.5°	83.4	82.7	82.0	81.4	81.1	80.7	80.4	80.0	80.4	80.7	81.1
105°	107.9	107.0	106.0	105.5	105.3	105.0	104.8	104.6	104.8	105.0	105.3
107.5°	134.8	134.4	134.0	133.8	133.6	133.5	133.4	133.3	133.4	133.5	133.6
110°	152.6	152.4	152.1	152.0	151.7	151.6	151.3	151.2	151.3	151.6	151.7





TEST NUMBER: P332277-930

CATALOG NUMBER: S123RDIP-S560D585U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	170.4	170.4	170.3	170.2	170.1	170.0	169.8	169.7	169.8	170.0	170.1
115°	198.5	198.7	198.9	198.9	198.6	198.3	198.0	197.6	198.0	198.3	198.6
117.5°	226.0	226.2	226.5	226.6	226.3	226.2	225.9	225.8	225.9	226.2	226.3
120°	244.8	245.2	245.7	245.7	245.1	244.4	243.9	243.2	243.9	244.4	245.1
122.5°	262.9	263.1	263.3	263.3	262.8	262.4	261.9	261.5	261.9	262.4	262.8
125°	290.2	290.3	290.6	290.5	290.2	289.8	289.6	289.3	289.6	289.8	290.2
127.5°	317.3	317.6	317.8	317.6	316.9	316.3	315.6	315.0	315.6	316.3	316.9
130°	335.0	335.3	335.6	335.3	334.5	333.7	332.9	332.1	332.9	333.7	334.5
132.5°	352.3	352.5	352.8	352.5	351.6	350.8	350.0	349.1	350.0	350.8	351.6
135°	377.8	377.9	378.1	377.7	377.2	376.5	375.9	375.3	375.9	376.5	377.2
137.5°	402.4	402.2	401.9	401.5	401.0	400.5	400.0	399.5	400.0	400.5	401.0
140°	418.8	418.7	418.6	418.2	417.8	417.3	416.7	416.2	416.7	417.3	417.8
142.5°	434.2	434.1	433.9	433.5	433.0	432.5	431.9	431.5	431.9	432.5	433.0
145°	457.0	456.6	456.3	456.1	455.9	455.7	455.5	455.3	455.5	455.7	455.9
147.5°	478.5	478.3	477.9	477.6	477.2	476.9	476.5	476.1	476.5	476.9	477.2
150°	492.0	491.9	491.6	491.5	491.2	491.1	490.8	490.6	490.8	491.1	491.2
152.5°	504.1	504.0	503.9	503.7	503.4	503.1	502.8	502.6	502.8	503.1	503.4
155°	521.5	521.5	521.4	521.3	521.3	521.3	521.3	521.3	521.3	521.3	521.3
157.5°	537.0	536.9	536.8	536.8	537.0	537.0	537.2	537.3	537.2	537.0	537.0
160°	546.4	546.4	546.4	546.5	546.7	546.9	547.1	547.3	547.1	546.9	546.7
162.5°	555.2	555.1	555.1	555.1	555.4	555.7	556.0	556.3	556.0	555.7	555.4
165°	566.4	566.4	566.4	566.6	566.9	567.2	567.5	567.8	567.5	567.2	566.9
167.5°	575.4	575.3	575.2	575.4	575.8	576.2	576.6	577.0	576.6	576.2	575.8
170°	580.3	580.3	580.3	580.6	581.0	581.4	581.8	582.2	581.8	581.4	581.0
172.5°	584.5	584.5	584.5	584.7	585.1	585.5	585.9	586.3	585.9	585.5	585.1
175°	588.7	588.7	588.7	589.0	589.4	589.8	590.2	590.6	590.2	589.8	589.4
177.5°	590.8	590.8	590.8	591.0	591.3	591.7	592.1	592.4	592.1	591.7	591.3
180°	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0



TEST NUMBER: P332277-930

CATALOG NUMBER: S123RDIP-S560D585U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	717.0	713.7	711.5	706.5	703.3	699.8	696.3	698.5	698.2	698.0	698.0
5°	692.9	685.7	679.2	670.7	665.4	658.9	653.9	653.3	654.5	650.1	647.7
7.5°	669.1	659.3	650.0	640.7	630.8	622.9	618.0	615.7	612.5	609.8	607.0
10°	652.3	640.8	631.7	620.2	609.6	600.2	594.3	590.2	588.0	585.8	581.8
12.5°	635.1	623.8	612.2	599.2	589.1	578.2	573.8	569.2	565.0	562.6	557.0
15°	609.8	595.2	583.0	569.2	558.1	547.4	541.2	532.1	530.8	527.7	522.1
17.5°	584.6	568.7	551.9	541.7	529.0	518.0	508.4	505.4	496.4	493.1	488.2
20°	564.6	549.9	537.1	523.7	505.2	495.0	487.5	483.4	476.2	471.8	468.7
22.5°	547.4	532.4	517.6	502.0	486.7	475.2	469.7	463.4	459.5	453.4	450.0
25°	522.8	506.5	488.7	471.8	460.9	452.2	443.4	437.8	432.2	429.3	423.1
27.5°	494.2	477.2	460.6	447.8	434.3	425.7	417.8	412.8	406.0	401.3	397.9
30°	478.4	458.4	444.1	432.5	415.3	407.2	401.3	395.0	390.0	385.1	381.6
32.5°	460.2	441.9	428.3	414.0	400.8	392.0	384.3	378.8	374.5	369.8	366.4
35°	431.5	416.3	402.2	387.8	378.1	369.1	360.0	355.4	351.3	346.9	343.8
37.5°	405.7	391.4	378.1	364.4	352.5	345.0	337.8	334.2	328.7	325.8	322.6
40°	389.7	375.7	361.3	348.2	335.7	330.1	323.5	318.2	313.2	311.0	307.6
42.5°	372.3	358.2	346.1	331.9	321.7	314.1	308.0	302.2	298.5	295.3	293.3
45°	346.3	333.8	322.0	307.9	298.2	291.6	284.8	279.5	276.1	273.9	270.4
47.5°	321.1	308.7	296.6	284.4	275.0	267.5	260.7	256.9	252.4	249.7	247.4
50°	302.9	291.6	278.8	267.6	258.3	250.8	245.2	240.4	236.4	232.9	231.4
52.5°	286.2	274.2	263.1	252.7	242.8	234.2	229.2	224.2	221.2	217.2	215.4
55°	258.5	247.0	237.7	227.3	217.7	210.5	204.2	199.8	196.7	192.3	189.9
57.5°	232.6	222.3	211.1	202.2	192.2	186.1	180.9	175.0	171.2	167.8	165.3
60°	215.2	203.3	193.6	185.2	176.4	168.6	164.0	159.2	155.2	151.7	149.6
62.5°	196.9	186.5	177.4	168.2	160.2	153.4	148.0	144.0	140.5	138.3	136.1
65°	168.9	160.9	151.5	144.0	136.5	131.5	127.1	123.7	121.2	119.6	117.7
67.5°	143.2	135.3	127.2	119.8	114.8	111.0	108.1	105.2	104.0	101.9	100.7
70°	126.5	118.4	111.2	105.6	100.5	97.8	95.9	93.7	92.5	89.9	88.7
72.5°	108.3	102.4	97.2	92.5	88.5	86.0	83.6	81.0	78.9	76.2	74.9
75°	85.3	80.0	75.9	72.7	70.3	66.9	63.4	60.6	59.7	58.7	58.4
77.5°	63.1	59.8	56.8	54.2	51.1	48.6	47.9	47.2	47.0	46.6	46.6
80°	49.7	46.6	44.4	41.3	39.4	39.4	39.4	38.7	39.1	39.1	39.1
82.5°	36.9	34.0	32.9	31.7	31.4	31.6	31.6	31.7	31.6	32.0	31.8
85°	19.1	19.3	20.0	19.6	20.0	20.0	20.6	20.3	20.6	20.0	20.6
87.5°	7.9	8.9	9.5	9.9	10.4	10.4	10.8	10.9	11.3	11.3	11.3
90°	4.6	5.8	7.1	8.5	9.8	11.2	11.6	12.0	12.4	12.8	13.1
92.5°	14.1	14.8	15.6	16.3	17.1	17.9	18.2	18.5	18.8	19.2	19.3
95°	30.3	31.1	32.0	32.8	33.6	34.4	34.8	35.2	35.6	36.0	36.3
97.5°	50.9	51.4	52.0	52.7	53.2	53.9	54.3	54.8	55.3	55.8	55.9
100°	65.7	66.3	66.8	67.3	67.8	68.3	68.6	69.0	69.3	69.6	69.9
102.5°	81.4	82.0	82.7	83.4	84.1	84.7	85.0	85.4	85.7	85.9	86.1
105°	105.5	106.0	107.0	107.9	108.8	109.7	109.7	109.7	109.7	109.7	109.8
107.5°	133.8	134.0	134.4	134.8	135.2	135.5	135.8	136.2	136.5	136.8	137.0
110°	152.0	152.1	152.4	152.6	152.8	153.0	153.4	153.8	154.3	154.7	154.7



TEST NUMBER: P332277-930

CATALOG NUMBER: S123RDIP-S560D585U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	170.2	170.3	170.4	170.4	170.5	170.5	171.0	171.5	171.9	172.4	172.7
115°	198.9	198.9	198.7	198.5	198.3	198.1	198.2	198.3	198.4	198.5	198.5
117.5°	226.6	226.5	226.2	226.0	225.8	225.4	225.4	225.4	225.3	225.3	225.2
120°	245.7	245.7	245.2	244.8	244.2	243.7	243.6	243.4	243.4	243.3	243.1
122.5°	263.3	263.3	263.1	262.9	262.5	262.3	262.0	261.7	261.5	261.2	260.9
125°	290.5	290.6	290.3	290.2	289.9	289.8	289.3	288.9	288.5	288.0	287.6
127.5°	317.6	317.8	317.6	317.3	317.1	316.9	316.3	315.7	315.1	314.5	314.1
130°	335.3	335.6	335.3	335.0	334.7	334.4	333.9	333.5	333.1	332.7	332.2
132.5°	352.5	352.8	352.5	352.3	352.0	351.9	351.3	350.8	350.3	349.8	349.4
135°	377.7	378.1	377.9	377.8	377.7	377.6	377.2	376.7	376.3	375.9	375.6
137.5°	401.5	401.9	402.2	402.4	402.8	403.0	402.6	402.1	401.7	401.3	400.9
140°	418.2	418.6	418.7	418.8	418.9	419.0	418.9	418.8	418.7	418.6	418.2
142.5°	433.5	433.9	434.1	434.2	434.5	434.6	434.6	434.4	434.3	434.2	433.9
145°	456.1	456.3	456.6	457.0	457.3	457.6	457.5	457.4	457.3	457.2	456.9
147.5°	477.6	477.9	478.3	478.5	478.8	479.1	479.1	479.1	479.1	479.1	478.7
150°	491.5	491.6	491.9	492.0	492.3	492.4	492.4	492.4	492.4	492.4	492.2
152.5°	503.7	503.9	504.0	504.1	504.3	504.3	504.5	504.8	504.9	505.1	504.8
155°	521.3	521.4	521.5	521.5	521.7	521.8	522.2	522.6	523.0	523.4	523.3
157.5°	536.8	536.8	536.9	537.0	537.0	537.1	537.5	538.0	538.4	538.8	538.7
160°	546.5	546.4	546.4	546.4	546.4	546.4	546.9	547.5	548.0	548.5	548.5
162.5°	555.1	555.1	555.1	555.2	555.3	555.4	555.9	556.4	556.9	557.4	557.3
165°	566.6	566.4	566.4	566.4	566.4	566.4	567.0	567.7	568.3	568.9	568.8
167.5°	575.4	575.2	575.3	575.4	575.4	575.5	576.2	576.8	577.5	578.1	578.1
170°	580.6	580.3	580.3	580.3	580.3	580.3	581.1	581.8	582.5	583.3	583.3
172.5°	584.7	584.5	584.5	584.5	584.5	584.5	585.1	585.7	586.4	587.0	587.0
175°	589.0	588.7	588.7	588.7	588.7	588.7	589.4	590.0	590.6	591.3	591.2
177.5°	591.0	590.8	590.8	590.8	590.8	590.8	591.3	591.9	592.4	592.9	592.8
180°	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0



TEST NUMBER: P332277-930

CATALOG NUMBER: S123RDIP-S560D585U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	695.0	694.7	695.0	694.0	695.0	694.7	695.0	698.0	698.0	698.2	698.5
5°	646.7	646.4	645.5	642.7	645.5	646.4	646.7	647.7	650.1	654.5	653.3
7.5°	604.5	604.1	601.4	601.4	601.4	604.1	604.5	607.0	609.8	612.5	615.7
10°	579.6	579.9	576.2	574.0	576.2	579.9	579.6	581.8	585.8	588.0	590.2
12.5°	555.4	553.9	550.9	548.5	550.9	553.9	555.4	557.0	562.6	565.0	569.2
15°	523.3	520.2	512.7	513.4	512.7	520.2	523.3	522.1	527.7	530.8	532.1
17.5°	485.7	483.4	483.3	478.9	483.3	483.4	485.7	488.2	493.1	496.4	505.4
20°	463.7	462.2	462.8	458.4	462.8	462.2	463.7	468.7	471.8	476.2	483.4
22.5°	446.5	444.9	442.3	440.9	442.3	444.9	446.5	450.0	453.4	459.5	463.4
25°	421.3	418.7	416.3	417.8	416.3	418.7	421.3	423.1	429.3	432.2	437.8
27.5°	396.0	394.1	391.7	391.3	391.7	394.1	396.0	397.9	401.3	406.0	412.8
30°	380.0	378.1	376.9	375.4	376.9	378.1	380.0	381.6	385.1	390.0	395.0
32.5°	363.8	363.5	361.2	360.9	361.2	363.5	363.8	366.4	369.8	374.5	378.8
35°	342.6	340.7	340.1	340.4	340.1	340.7	342.6	343.8	346.9	351.3	355.4
37.5°	322.4	319.9	318.8	317.6	318.8	319.9	322.4	322.6	325.8	328.7	334.2
40°	307.9	305.4	304.8	304.2	304.8	305.4	307.9	307.6	311.0	313.2	318.2
42.5°	291.6	290.7	290.3	289.2	290.3	290.7	291.6	293.3	295.3	298.5	302.2
45°	269.5	269.2	267.3	267.9	267.3	269.2	269.5	270.4	273.9	276.1	279.5
47.5°	246.1	244.8	243.4	244.3	243.4	244.8	246.1	247.4	249.7	252.4	256.9
50°	230.2	229.5	226.7	227.3	226.7	229.5	230.2	231.4	232.9	236.4	240.4
52.5°	214.2	211.8	210.8	210.3	210.8	211.8	214.2	215.4	217.2	221.2	224.2
55°	187.7	184.8	183.6	183.0	183.6	184.8	187.7	189.9	192.3	196.7	199.8
57.5°	161.7	160.9	160.0	160.6	160.0	160.9	161.7	165.3	167.8	171.2	175.0
60°	146.4	146.4	146.4	146.2	146.4	146.4	146.4	149.6	151.7	155.2	159.2
62.5°	134.7	134.0	133.7	134.1	133.7	134.0	134.7	136.1	138.3	140.5	144.0
65°	116.8	116.5	115.2	115.0	115.2	116.5	116.8	117.7	119.6	121.2	123.7
67.5°	99.9	98.7	98.4	97.9	98.4	98.7	99.9	100.7	101.9	104.0	105.2
70°	87.2	86.5	84.6	85.0	84.6	86.5	87.2	88.7	89.9	92.5	93.7
72.5°	73.4	72.7	72.4	71.9	72.4	72.7	73.4	74.9	76.2	78.9	81.0
75°	58.0	57.8	57.5	58.7	57.5	57.8	58.0	58.4	58.7	59.7	60.6
77.5°	46.6	46.6	46.7	46.2	46.7	46.6	46.6	46.6	46.6	47.0	47.2
80°	39.1	39.1	38.7	38.7	38.7	39.1	39.1	39.1	39.1	39.1	38.7
82.5°	31.3	31.6	31.7	31.2	31.7	31.6	31.3	31.8	32.0	31.6	31.7
85°	20.6	20.3	21.0	20.6	21.0	20.3	20.6	20.6	20.0	20.6	20.3
87.5°	11.9	11.4	11.5	11.8	11.5	11.4	11.9	11.3	11.3	11.3	10.9
90°	13.4	13.5	13.8	13.9	13.8	13.5	13.4	13.1	12.8	12.4	12.0
92.5°	19.2	19.0	18.9	18.8	18.9	19.0	19.2	19.3	19.2	18.8	18.5
95°	36.3	36.3	36.3	36.3	36.3	36.3	36.3	36.3	36.0	35.6	35.2
97.5°	55.9	55.8	55.8	55.8	55.8	55.8	55.9	55.9	55.8	55.3	54.8
100°	70.0	70.3	70.4	70.7	70.4	70.3	70.0	69.9	69.6	69.3	69.0
102.5°	86.1	86.0	86.0	85.9	86.0	86.0	86.1	86.1	85.9	85.7	85.4
105°	110.1	110.2	110.5	110.7	110.5	110.2	110.1	109.8	109.7	109.7	109.7
107.5°	136.8	136.7	136.6	136.5	136.6	136.7	136.8	137.0	136.8	136.5	136.2
110°	154.6	154.3	154.2	153.9	154.2	154.3	154.6	154.7	154.7	154.3	153.8



TEST NUMBER: P332277-930

CATALOG NUMBER: S123RDIP-S560D585U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	172.7	172.6	172.6	172.5	172.6	172.6	172.7	172.7	172.4	171.9	171.5
115°	198.4	198.3	198.2	198.1	198.2	198.3	198.4	198.5	198.5	198.4	198.3
117.5°	224.9	224.6	224.4	224.0	224.4	224.6	224.9	225.2	225.3	225.3	225.4
120°	242.9	242.7	242.5	242.3	242.5	242.7	242.9	243.1	243.3	243.4	243.4
122.5°	260.7	260.3	260.1	259.8	260.1	260.3	260.7	260.9	261.2	261.5	261.7
125°	287.2	286.8	286.4	286.0	286.4	286.8	287.2	287.6	288.0	288.5	288.9
127.5°	313.6	313.1	312.6	312.1	312.6	313.1	313.6	314.1	314.5	315.1	315.7
130°	331.4	330.7	330.0	329.2	330.0	330.7	331.4	332.2	332.7	333.1	333.5
132.5°	348.8	348.2	347.6	347.1	347.6	348.2	348.8	349.4	349.8	350.3	350.8
135°	375.4	375.2	375.0	374.8	375.0	375.2	375.4	375.6	375.9	376.3	376.7
137.5°	400.5	400.1	399.7	399.3	399.7	400.1	400.5	400.9	401.3	401.7	402.1
140°	417.4	416.7	416.0	415.3	416.0	416.7	417.4	418.2	418.6	418.7	418.8
142.5°	433.3	432.8	432.2	431.6	432.2	432.8	433.3	433.9	434.2	434.3	434.4
145°	456.5	456.1	455.7	455.3	455.7	456.1	456.5	456.9	457.2	457.3	457.4
147.5°	478.2	477.5	477.0	476.3	477.0	477.5	478.2	478.7	479.1	479.1	479.1
150°	491.5	490.9	490.3	489.7	490.3	490.9	491.5	492.2	492.4	492.4	492.4
152.5°	504.3	503.8	503.3	502.7	503.3	503.8	504.3	504.8	505.1	504.9	504.8
155°	522.5	521.8	521.1	520.4	521.1	521.8	522.5	523.3	523.4	523.0	522.6
157.5°	538.2	537.6	537.0	536.5	537.0	537.6	538.2	538.7	538.8	538.4	538.0
160°	548.1	547.7	547.3	546.9	547.3	547.7	548.1	548.5	548.5	548.0	547.5
162.5°	556.7	556.0	555.4	554.7	555.4	556.0	556.7	557.3	557.4	556.9	556.4
165°	568.1	567.4	566.7	566.0	566.7	567.4	568.1	568.8	568.9	568.3	567.7
167.5°	577.5	576.8	576.2	575.5	576.2	576.8	577.5	578.1	578.1	577.5	576.8
170°	582.5	581.8	581.1	580.3	581.1	581.8	582.5	583.3	583.3	582.5	581.8
172.5°	586.3	585.5	584.8	584.1	584.8	585.5	586.3	587.0	587.0	586.4	585.7
175°	590.4	589.7	589.0	588.2	589.0	589.7	590.4	591.2	591.3	590.6	590.0
177.5°	592.2	591.7	591.1	590.5	591.1	591.7	592.2	592.8	592.9	592.4	591.9
180°	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0



TEST NUMBER: P332277-930

CATALOG NUMBER: S123RDIP-S560D585U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	696.3	699.8	703.3	706.5	711.5	713.7	717.0	718.2	721.9	727.5	732.0
5°	653.9	658.9	665.4	670.7	679.2	685.7	692.9	699.8	707.9	719.5	729.8
7.5°	618.0	622.9	630.8	640.7	650.0	659.3	669.1	678.4	690.1	706.6	723.0
10°	594.3	600.2	609.6	620.2	631.7	640.8	652.3	664.2	678.6	697.7	717.3
12.5°	573.8	578.2	589.1	599.2	612.2	623.8	635.1	649.0	665.4	685.7	709.3
15°	541.2	547.4	558.1	569.2	583.0	595.2	609.8	626.7	642.7	667.6	696.3
17.5°	508.4	518.0	529.0	541.7	551.9	568.7	584.6	601.9	621.5	648.0	679.5
20°	487.5	495.0	505.2	523.7	537.1	549.9	564.6	586.1	604.2	634.2	667.0
22.5°	469.7	475.2	486.7	502.0	517.6	532.4	547.4	567.9	590.3	618.7	654.3
25°	443.4	452.2	460.9	471.8	488.7	506.5	522.8	540.2	563.9	594.3	632.7
27.5°	417.8	425.7	434.3	447.8	460.6	477.2	494.2	514.2	539.6	571.7	610.7
30°	401.3	407.2	415.3	432.5	444.1	458.4	478.4	496.2	519.9	554.0	595.2
32.5°	384.3	392.0	400.8	414.0	428.3	441.9	460.2	479.5	503.7	537.2	579.4
35°	360.0	369.1	378.1	387.8	402.2	416.3	431.5	452.8	477.4	510.0	551.5
37.5°	337.8	345.0	352.5	364.4	378.1	391.4	405.7	426.6	449.9	484.9	523.0
40°	323.5	330.1	335.7	348.2	361.3	375.7	389.7	408.1	433.1	465.9	502.8
42.5°	308.0	314.1	321.7	331.9	346.1	358.2	372.3	389.6	413.1	446.5	478.7
45°	284.8	291.6	298.2	307.9	322.0	333.8	346.3	362.9	386.9	414.4	443.1
47.5°	260.7	267.5	275.0	284.4	296.6	308.7	321.1	335.8	357.8	384.7	404.1
50°	245.2	250.8	258.3	267.6	278.8	291.6	302.9	318.9	339.7	361.0	377.9
52.5°	229.2	234.2	242.8	252.7	263.1	274.2	286.2	299.9	318.8	338.8	352.1
55°	204.2	210.5	217.7	227.3	237.7	247.0	258.5	272.6	287.6	302.6	311.7
57.5°	180.9	186.1	192.2	202.2	211.1	222.3	232.6	243.6	257.5	268.7	274.7
60°	164.0	168.6	176.4	185.2	193.6	203.3	215.2	226.1	236.7	245.7	250.5
62.5°	148.0	153.4	160.2	168.2	177.4	186.5	196.9	206.1	215.5	223.3	226.5
65°	127.1	131.5	136.5	144.0	151.5	160.9	168.9	178.3	185.2	189.6	192.3
67.5°	108.1	111.0	114.8	119.8	127.2	135.3	143.2	150.5	156.3	159.2	161.8
70°	95.9	97.8	100.5	105.6	111.2	118.4	126.5	131.8	136.8	139.3	141.8
72.5°	83.6	86.0	88.5	92.5	97.2	102.4	108.3	114.8	117.6	120.5	122.1
75°	63.4	66.9	70.3	72.7	75.9	80.0	85.3	89.3	90.9	93.4	93.7
77.5°	47.9	48.6	51.1	54.2	56.8	59.8	63.1	66.8	67.5	68.8	69.6
80°	39.4	39.4	39.4	41.3	44.4	46.6	49.7	51.5	52.7	53.1	53.4
82.5°	31.6	31.6	31.4	31.7	32.9	34.0	36.9	39.1	40.0	39.9	39.1
85°	20.6	20.0	20.0	19.6	20.0	19.3	19.1	20.3	22.2	22.2	21.5
87.5°	10.8	10.4	10.4	9.9	9.5	8.9	7.9	8.0	7.7	8.6	8.1
90°	11.6	11.2	9.8	8.5	7.1	5.8	4.6	3.6	2.5	1.5	0.5
92.5°	18.2	17.9	17.1	16.3	15.6	14.8	14.1	13.4	12.6	12.0	11.3
95°	34.8	34.4	33.6	32.8	32.0	31.1	30.3	29.6	28.9	28.1	27.5
97.5°	54.3	53.9	53.2	52.7	52.0	51.4	50.9	50.4	49.8	49.2	48.8
100°	68.6	68.3	67.8	67.3	66.8	66.3	65.7	65.1	64.5	63.8	63.3
102.5°	85.0	84.7	84.1	83.4	82.7	82.0	81.4	81.1	80.7	80.4	80.0
105°	109.7	109.7	108.8	107.9	107.0	106.0	105.5	105.3	105.0	104.8	104.6
107.5°	135.8	135.5	135.2	134.8	134.4	134.0	133.8	133.6	133.5	133.4	133.3
110°	153.4	153.0	152.8	152.6	152.4	152.1	152.0	151.7	151.6	151.3	151.2



TEST NUMBER: P332277-930

CATALOG NUMBER: S123RDIP-S560D585U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	171.0	170.5	170.5	170.4	170.4	170.3	170.2	170.1	170.0	169.8	169.7
115°	198.2	198.1	198.3	198.5	198.7	198.9	198.9	198.6	198.3	198.0	197.6
117.5°	225.4	225.4	225.8	226.0	226.2	226.5	226.6	226.3	226.2	225.9	225.8
120°	243.6	243.7	244.2	244.8	245.2	245.7	245.7	245.1	244.4	243.9	243.2
122.5°	262.0	262.3	262.5	262.9	263.1	263.3	263.3	262.8	262.4	261.9	261.5
125°	289.3	289.8	289.9	290.2	290.3	290.6	290.5	290.2	289.8	289.6	289.3
127.5°	316.3	316.9	317.1	317.3	317.6	317.8	317.6	316.9	316.3	315.6	315.0
130°	333.9	334.4	334.7	335.0	335.3	335.6	335.3	334.5	333.7	332.9	332.1
132.5°	351.3	351.9	352.0	352.3	352.5	352.8	352.5	351.6	350.8	350.0	349.1
135°	377.2	377.6	377.7	377.8	377.9	378.1	377.7	377.2	376.5	375.9	375.3
137.5°	402.6	403.0	402.8	402.4	402.2	401.9	401.5	401.0	400.5	400.0	399.5
140°	418.9	419.0	418.9	418.8	418.7	418.6	418.2	417.8	417.3	416.7	416.2
142.5°	434.6	434.6	434.5	434.2	434.1	433.9	433.5	433.0	432.5	431.9	431.5
145°	457.5	457.6	457.3	457.0	456.6	456.3	456.1	455.9	455.7	455.5	455.3
147.5°	479.1	479.1	478.8	478.5	478.3	477.9	477.6	477.2	476.9	476.5	476.1
150°	492.4	492.4	492.3	492.0	491.9	491.6	491.5	491.2	491.1	490.8	490.6
152.5°	504.5	504.3	504.3	504.1	504.0	503.9	503.7	503.4	503.1	502.8	502.6
155°	522.2	521.8	521.7	521.5	521.5	521.4	521.3	521.3	521.3	521.3	521.3
157.5°	537.5	537.1	537.0	537.0	536.9	536.8	536.8	537.0	537.0	537.2	537.3
160°	546.9	546.4	546.4	546.4	546.4	546.4	546.5	546.7	546.9	547.1	547.3
162.5°	555.9	555.4	555.3	555.2	555.1	555.1	555.1	555.4	555.7	556.0	556.3
165°	567.0	566.4	566.4	566.4	566.4	566.4	566.6	566.9	567.2	567.5	567.8
167.5°	576.2	575.5	575.4	575.4	575.3	575.2	575.4	575.8	576.2	576.6	577.0
170°	581.1	580.3	580.3	580.3	580.3	580.3	580.6	581.0	581.4	581.8	582.2
172.5°	585.1	584.5	584.5	584.5	584.5	584.5	584.7	585.1	585.5	585.9	586.3
175°	589.4	588.7	588.7	588.7	588.7	588.7	589.0	589.4	589.8	590.2	590.6
177.5°	591.3	590.8	590.8	590.8	590.8	590.8	591.0	591.3	591.7	592.1	592.4
180°	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0



TEST NUMBER: P332277-930

CATALOG NUMBER: S123RDIP-S560D585U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	733.4	736.2	739.7	744.9	748.9	752.4	753.2	754.2	756.7	760.9	764.2
5°	738.3	745.4	756.9	768.2	780.4	790.4	799.7	806.3	812.5	825.7	836.3
7.5°	736.7	752.7	770.8	791.0	811.4	831.2	849.5	866.0	882.4	901.5	923.2
10°	735.7	754.5	778.8	804.7	833.2	861.0	887.8	908.7	933.1	955.0	982.8
12.5°	731.0	758.0	787.1	820.2	855.2	887.2	922.5	951.5	979.3	1010.9	1043.2
15°	724.8	757.6	794.4	838.5	891.5	930.3	966.5	1016.8	1051.1	1085.5	1131.7
17.5°	713.5	753.5	799.6	856.7	901.1	953.1	1007.5	1047.3	1093.6	1142.0	1183.8
20°	704.5	751.1	802.6	858.8	915.3	971.8	1024.6	1072.0	1119.8	1175.7	1210.1
22.5°	695.5	741.5	795.1	854.8	915.5	975.0	1034.8	1090.5	1144.3	1200.7	1244.6
25°	676.4	731.0	789.1	850.0	910.0	975.5	1046.8	1108.9	1175.4	1233.5	1275.0
27.5°	657.0	707.1	764.9	826.7	893.3	970.9	1054.6	1125.3	1191.9	1233.5	1246.5
30°	639.5	692.6	745.7	808.5	880.6	967.1	1056.1	1137.0	1191.6	1209.7	1196.3
32.5°	621.8	669.9	722.5	786.8	863.4	957.9	1058.1	1130.0	1162.9	1149.1	1094.4
35°	590.5	633.9	684.9	749.2	837.2	952.8	1049.9	1098.6	1090.5	1012.4	909.3
37.5°	557.0	592.4	639.5	706.8	810.1	932.5	1014.4	1021.6	951.3	831.4	712.4
40°	530.5	562.4	610.8	681.1	789.1	912.5	978.7	949.7	840.7	707.3	608.0
42.5°	504.8	531.7	578.3	654.1	769.2	885.3	925.4	862.2	736.5	610.3	520.1
45°	461.2	486.5	533.4	611.1	728.2	833.2	827.9	718.0	592.1	490.6	415.6
47.5°	419.9	442.0	486.0	565.3	680.2	755.0	705.4	588.5	481.7	400.3	346.8
50°	390.7	412.5	456.2	534.6	641.7	696.3	625.5	512.7	415.0	347.6	305.1
52.5°	362.6	384.0	424.0	500.3	595.3	627.9	551.8	447.3	365.8	307.6	271.1
55°	323.5	339.7	375.7	448.7	519.6	527.1	450.0	362.6	295.4	254.8	229.8
57.5°	283.6	297.6	333.0	391.3	441.0	437.1	363.9	288.4	243.1	213.0	194.9
60°	257.6	271.3	302.6	352.5	390.0	376.9	309.8	248.9	210.2	188.0	173.7
62.5°	233.4	244.1	273.4	309.8	336.8	322.0	264.8	214.4	183.7	165.0	153.6
65°	198.3	207.0	230.5	249.5	264.5	250.1	202.7	167.7	145.5	132.4	124.6
67.5°	164.9	170.5	185.3	192.2	202.8	187.0	152.4	129.0	116.3	105.3	99.9
70°	144.0	148.1	155.8	161.4	164.3	148.1	122.4	105.3	94.7	86.8	83.4
72.5°	122.9	126.5	128.1	132.7	131.3	116.0	98.4	84.8	77.1	71.8	67.4
75°	94.0	95.6	94.0	92.1	88.1	77.5	65.3	58.4	52.7	50.3	48.8
77.5°	68.5	68.0	65.9	62.9	56.0	49.3	42.8	40.4	38.1	36.7	36.2
80°	52.7	51.5	49.7	45.0	39.1	34.3	32.8	31.2	30.3	28.7	28.5
82.5°	39.3	38.6	35.4	31.5	27.3	25.1	23.8	23.2	22.3	21.5	21.4
85°	21.0	20.0	16.6	14.3	13.8	13.1	12.8	12.8	11.6	11.3	11.3
87.5°	7.0	5.8	5.7	5.1	5.4	5.1	5.7	5.5	5.5	5.8	5.4
90°	1.5	2.5	3.6	4.6	5.8	7.1	8.5	9.8	11.2	11.6	12.0
92.5°	12.0	12.6	13.4	14.1	14.8	15.6	16.3	17.1	17.9	18.2	18.5
95°	28.1	28.9	29.6	30.3	31.1	32.0	32.8	33.6	34.4	34.8	35.2
97.5°	49.2	49.8	50.4	50.9	51.4	52.0	52.7	53.2	53.9	54.3	54.8
100°	63.8	64.5	65.1	65.7	66.3	66.8	67.3	67.8	68.3	68.6	69.0
102.5°	80.4	80.7	81.1	81.4	82.0	82.7	83.4	84.1	84.7	85.0	85.4
105°	104.8	105.0	105.3	105.5	106.0	107.0	107.9	108.8	109.7	109.7	109.7
107.5°	133.4	133.5	133.6	133.8	134.0	134.4	134.8	135.2	135.5	135.8	136.2
110°	151.3	151.6	151.7	152.0	152.1	152.4	152.6	152.8	153.0	153.4	153.8





TEST NUMBER: P332277-930

CATALOG NUMBER: S123RDIP-S560D585U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	169.8	170.0	170.1	170.2	170.3	170.4	170.4	170.5	170.5	171.0	171.5
115°	198.0	198.3	198.6	198.9	198.9	198.7	198.5	198.3	198.1	198.2	198.3
117.5°	225.9	226.2	226.3	226.6	226.5	226.2	226.0	225.8	225.4	225.4	225.4
120°	243.9	244.4	245.1	245.7	245.7	245.2	244.8	244.2	243.7	243.6	243.4
122.5°	261.9	262.4	262.8	263.3	263.3	263.1	262.9	262.5	262.3	262.0	261.7
125°	289.6	289.8	290.2	290.5	290.6	290.3	290.2	289.9	289.8	289.3	288.9
127.5°	315.6	316.3	316.9	317.6	317.8	317.6	317.3	317.1	316.9	316.3	315.7
130°	332.9	333.7	334.5	335.3	335.6	335.3	335.0	334.7	334.4	333.9	333.5
132.5°	350.0	350.8	351.6	352.5	352.8	352.5	352.3	352.0	351.9	351.3	350.8
135°	375.9	376.5	377.2	377.7	378.1	377.9	377.8	377.7	377.6	377.2	376.7
137.5°	400.0	400.5	401.0	401.5	401.9	402.2	402.4	402.8	403.0	402.6	402.1
140°	416.7	417.3	417.8	418.2	418.6	418.7	418.8	418.9	419.0	418.9	418.8
142.5°	431.9	432.5	433.0	433.5	433.9	434.1	434.2	434.5	434.6	434.6	434.4
145°	455.5	455.7	455.9	456.1	456.3	456.6	457.0	457.3	457.6	457.5	457.4
147.5°	476.5	476.9	477.2	477.6	477.9	478.3	478.5	478.8	479.1	479.1	479.1
150°	490.8	491.1	491.2	491.5	491.6	491.9	492.0	492.3	492.4	492.4	492.4
152.5°	502.8	503.1	503.4	503.7	503.9	504.0	504.1	504.3	504.3	504.5	504.8
155°	521.3	521.3	521.3	521.3	521.4	521.5	521.5	521.7	521.8	522.2	522.6
157.5°	537.2	537.0	537.0	536.8	536.8	536.9	537.0	537.0	537.1	537.5	538.0
160°	547.1	546.9	546.7	546.5	546.4	546.4	546.4	546.4	546.4	546.9	547.5
162.5°	556.0	555.7	555.4	555.1	555.1	555.1	555.2	555.3	555.4	555.9	556.4
165°	567.5	567.2	566.9	566.6	566.4	566.4	566.4	566.4	566.4	567.0	567.7
167.5°	576.6	576.2	575.8	575.4	575.2	575.3	575.4	575.4	575.5	576.2	576.8
170°	581.8	581.4	581.0	580.6	580.3	580.3	580.3	580.3	580.3	581.1	581.8
172.5°	585.9	585.5	585.1	584.7	584.5	584.5	584.5	584.5	584.5	585.1	585.7
175°	590.2	589.8	589.4	589.0	588.7	588.7	588.7	588.7	588.7	589.4	590.0
177.5°	592.1	591.7	591.3	591.0	590.8	590.8	590.8	590.8	590.8	591.3	591.9
180°	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0



TEST NUMBER: P332277-930

CATALOG NUMBER: S123RDIP-S560D585U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	769.5	769.5	770.5	774.2	774.7	778.0	776.9
5°	845.6	851.6	853.8	863.2	868.8	871.2	866.3
7.5°	938.8	955.5	963.5	973.3	981.9	984.6	977.8
10°	1006.8	1024.3	1038.9	1048.0	1056.5	1062.0	1069.3
12.5°	1072.4	1094.0	1107.9	1120.7	1129.4	1136.5	1137.7
15°	1143.9	1176.3	1201.0	1219.1	1228.2	1232.9	1231.0
17.5°	1215.9	1245.9	1263.6	1282.0	1294.5	1295.2	1295.6
20°	1256.6	1286.0	1306.3	1320.0	1334.1	1333.4	1336.5
22.5°	1283.9	1306.9	1322.5	1332.4	1337.3	1334.9	1335.5
25°	1296.6	1303.4	1300.6	1284.7	1280.7	1266.0	1268.4
27.5°	1230.9	1198.4	1164.8	1121.5	1087.4	1060.2	1061.6
30°	1141.7	1084.2	1018.6	963.7	914.4	900.6	871.2
32.5°	1017.0	930.8	854.0	802.8	760.4	748.9	723.3
35°	805.7	721.9	642.9	595.5	576.7	550.6	550.2
37.5°	626.2	552.5	510.8	475.2	456.5	440.6	439.0
40°	526.8	469.4	437.8	412.2	393.8	381.9	379.1
42.5°	457.4	410.9	381.3	365.5	351.3	345.2	340.6
45°	373.5	342.3	321.6	307.3	300.7	296.0	293.5
47.5°	312.4	291.5	277.4	267.9	262.5	257.6	258.9
50°	279.2	262.0	251.7	242.6	238.6	235.1	235.5
52.5°	252.4	237.0	228.7	222.2	217.1	214.7	213.4
55°	214.3	204.6	196.1	191.4	188.6	185.2	184.3
57.5°	182.7	175.2	168.4	163.1	162.4	159.1	159.5
60°	161.8	155.5	149.9	147.1	144.9	142.1	143.0
62.5°	144.6	139.3	134.1	131.8	129.6	127.6	128.0
65°	118.4	113.3	110.2	109.0	108.0	107.1	106.2
67.5°	94.3	91.2	89.3	86.6	84.7	84.4	83.4
70°	79.3	75.3	71.8	68.4	67.4	67.1	67.4
72.5°	63.6	61.0	60.1	58.4	58.2	57.4	58.0
75°	47.8	46.9	46.2	45.0	45.0	45.0	45.0
77.5°	35.2	34.7	34.3	34.0	33.8	33.3	33.3
80°	27.5	27.1	26.6	26.6	26.3	26.6	26.3
82.5°	20.7	20.7	20.1	20.1	19.7	19.6	19.7
85°	10.6	10.3	10.9	10.3	10.6	10.0	10.6
87.5°	5.5	5.5	5.4	5.4	5.2	5.7	5.3
90°	12.4	12.8	13.1	13.4	13.5	13.8	13.9
92.5°	18.8	19.2	19.3	19.2	19.0	18.9	18.8
95°	35.6	36.0	36.3	36.3	36.3	36.3	36.3
97.5°	55.3	55.8	55.9	55.9	55.8	55.8	55.8
100°	69.3	69.6	69.9	70.0	70.3	70.4	70.7
102.5°	85.7	85.9	86.1	86.1	86.0	86.0	85.9
105°	109.7	109.7	109.8	110.1	110.2	110.5	110.7
107.5°	136.5	136.8	137.0	136.8	136.7	136.6	136.5
110°	154.3	154.7	154.7	154.6	154.3	154.2	153.9



TEST NUMBER: P332277-930

CATALOG NUMBER: S123RDIP-S560D585U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	171.9	172.4	172.7	172.7	172.6	172.6	172.5
115°	198.4	198.5	198.5	198.4	198.3	198.2	198.1
117.5°	225.3	225.3	225.2	224.9	224.6	224.4	224.0
120°	243.4	243.3	243.1	242.9	242.7	242.5	242.3
122.5°	261.5	261.2	260.9	260.7	260.3	260.1	259.8
125°	288.5	288.0	287.6	287.2	286.8	286.4	286.0
127.5°	315.1	314.5	314.1	313.6	313.1	312.6	312.1
130°	333.1	332.7	332.2	331.4	330.7	330.0	329.2
132.5°	350.3	349.8	349.4	348.8	348.2	347.6	347.1
135°	376.3	375.9	375.6	375.4	375.2	375.0	374.8
137.5°	401.7	401.3	400.9	400.5	400.1	399.7	399.3
140°	418.7	418.6	418.2	417.4	416.7	416.0	415.3
142.5°	434.3	434.2	433.9	433.3	432.8	432.2	431.6
145°	457.3	457.2	456.9	456.5	456.1	455.7	455.3
147.5°	479.1	479.1	478.7	478.2	477.5	477.0	476.3
150°	492.4	492.4	492.2	491.5	490.9	490.3	489.7
152.5°	504.9	505.1	504.8	504.3	503.8	503.3	502.7
155°	523.0	523.4	523.3	522.5	521.8	521.1	520.4
157.5°	538.4	538.8	538.7	538.2	537.6	537.0	536.5
160°	548.0	548.5	548.5	548.1	547.7	547.3	546.9
162.5°	556.9	557.4	557.3	556.7	556.0	555.4	554.7
165°	568.3	568.9	568.8	568.1	567.4	566.7	566.0
167.5°	577.5	578.1	578.1	577.5	576.8	576.2	575.5
170°	582.5	583.3	583.3	582.5	581.8	581.1	580.3
172.5°	586.4	587.0	587.0	586.3	585.5	584.8	584.1
175°	590.6	591.3	591.2	590.4	589.7	589.0	588.2
177.5°	592.4	592.9	592.8	592.2	591.7	591.1	590.5
180°	592.0	592.0	592.0	592.0	592.0	592.0	592.0

(END OF REPORT)