

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332318-930

Luminaire Tested: **S123RDIP-S775D1025U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332318-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S775D1025U930-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1025 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5826.1 lumens  
Efficiency: N/A  
Efficacy: 112.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332318-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332318-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	43																												
1	97	93	89	86	88	85	82	79	70	68	66	57	55	54	44	43	43	37																												
2	88	81	76	71	81	75	70	65	62	58	55	50	48	46	40	38	37	32																												
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	27																												
4	74	64	56	51	68	59	52	47	49	44	41	40	37	34	32	30	28	24																												
5	68	57	49	44	62	53	46	41	44	39	35	36	33	30	29	27	24	21																												
6	63	51	44	38	57	47	41	36	40	35	31	33	29	26	27	24	22	19																												
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17																												
8	54	42	35	30	49	39	32	28	33	28	24	28	24	21	22	20	18	15																												
9	50	39	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16	14																												
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10733	10733	10733	10733
5°	12794	10778	9492	10778
10°	15974	10717	8576	10717
15°	18750	10608	7819	10608
20°	20927	10443	7178	10443
25°	20593	10271	6783	10271
30°	14802	10112	6377	10112
35°	9883	9905	6114	9905
40°	7281	9656	5841	9656
45°	6107	9220	5574	9220
50°	5390	8649	5203	8649
55°	4725	7994	4693	7994
60°	4209	7369	4299	7369
65°	3696	6696	4001	6696
70°	2902	6099	3654	6099
75°	2558	5327	3335	5327
80°	2225	4525	3279	4525
85°	1791	3631	3483	3631



TEST NUMBER: P332318-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	98.1	1.7
10°-20°	306.3	5.3
20°-30°	481.3	8.3
30°-40°	502.1	8.6
40°-50°	429.7	7.4
50°-60°	327.5	5.6
60°-70°	209.9	3.6
70°-80°	101.0	1.7
80°-90°	29.8	0.5
90°-100°	39.8	0.7
100°-110°	189.8	3.3
110°-120°	455.9	7.8
120°-130°	580.5	10.0
130°-140°	620.3	10.6
140°-150°	580.0	10.0
150°-160°	467.9	8.0
160°-170°	302.0	5.2
170°-180°	104.1	1.8
0°-30°	885.7	15.2
0°-40°	1387.8	23.8
0°-60°	2145.0	36.8
0°-90°	2485.7	42.7
90°-120°	685.5	11.8
90°-150°	2466.4	42.3
90°-180°	3340.0	57.3
0°-180°	5826.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	997	997	997	997	997	
5°	1184	998	878	998	1184	122
15°	1683	952	702	952	1683	477
25°	1734	865	571	865	1734	745
35°	752	754	465	754	752	493
45°	401	606	366	606	401	315
55°	252	426	250	426	252	228
65°	145	263	157	263	145	143
75°	62	128	80	128	62	66
85°	14	29	28	29	14	17
90°	24	1	24	1	24	12
95°	31	50	31	50	31	26
105°	36	242	36	242	36	82
115°	478	455	478	455	478	442
125°	654	641	654	641	654	584
135°	806	798	806	798	806	622
145°	930	921	930	921	930	581
155°	1013	1015	1013	1015	1013	467
165°	1068	1070	1068	1070	1068	301
175°	1091	1095	1091	1095	1091	104
180°	1095	1095	1095	1095	1095	



TEST NUMBER: P332318-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1062.0	1063.4	1058.9	1058.3	1053.1	1051.7	1051.7	1044.6	1040.2	1034.4	1030.9
5°	1184.1	1190.9	1187.5	1179.8	1167.0	1164.0	1155.9	1143.1	1128.6	1110.7	1102.1
7.5°	1336.5	1345.9	1342.3	1330.4	1317.0	1306.2	1283.3	1262.0	1232.2	1206.1	1183.7
10°	1461.5	1451.7	1444.1	1432.5	1420.2	1400.0	1376.1	1343.3	1305.3	1275.5	1242.1
12.5°	1555.1	1553.5	1543.8	1531.9	1514.4	1495.3	1466.0	1426.0	1381.8	1338.6	1300.6
15°	1682.6	1685.2	1678.8	1666.4	1641.7	1607.9	1563.6	1546.9	1483.8	1436.8	1389.8
17.5°	1770.9	1770.4	1769.5	1752.4	1727.1	1703.2	1662.0	1618.2	1561.0	1494.9	1431.6
20°	1826.9	1822.7	1823.5	1804.3	1785.5	1757.8	1717.7	1654.1	1607.1	1530.7	1465.3
22.5°	1825.5	1824.7	1828.0	1821.4	1807.7	1786.5	1754.9	1701.2	1641.3	1564.2	1490.6
25°	1733.9	1730.5	1750.5	1756.1	1777.8	1781.7	1772.3	1742.9	1686.0	1606.6	1515.7
27.5°	1451.2	1449.3	1486.5	1533.1	1592.1	1638.1	1682.5	1703.9	1686.0	1629.2	1538.1
30°	1190.9	1231.0	1249.9	1317.3	1392.4	1482.1	1560.6	1635.2	1653.6	1628.9	1554.1
32.5°	988.8	1023.8	1039.4	1097.3	1167.3	1272.4	1390.2	1495.9	1570.7	1589.6	1544.6
35°	752.1	752.5	788.4	814.0	878.9	986.8	1101.3	1243.0	1383.8	1490.5	1501.6
37.5°	600.1	602.3	623.9	649.5	698.1	755.3	856.0	973.8	1136.5	1300.3	1396.4
40°	518.2	522.0	538.3	563.5	598.4	641.6	720.1	831.1	966.8	1149.1	1298.0
42.5°	465.6	471.8	480.2	499.6	521.3	561.7	625.2	710.9	834.3	1006.7	1178.5
45°	401.2	404.6	411.1	420.0	439.7	467.8	510.5	568.1	670.6	809.3	981.3
47.5°	353.9	352.1	358.9	366.2	379.2	398.4	427.1	474.1	547.1	658.4	804.4
50°	321.9	321.4	326.1	331.7	344.1	358.2	381.6	417.0	475.1	567.3	700.9
52.5°	291.8	293.4	296.8	303.7	312.6	324.0	345.0	370.6	420.4	500.0	611.4
55°	251.8	253.2	257.8	261.6	268.1	279.6	292.9	314.1	348.3	403.8	495.5
57.5°	218.0	217.4	221.9	222.9	230.2	239.5	249.8	266.4	291.1	332.3	394.1
60°	195.5	194.2	198.0	201.1	204.9	212.5	221.1	237.3	257.0	287.2	340.2
62.5°	175.0	174.4	177.2	180.2	183.4	190.4	197.5	210.0	225.5	251.1	293.1
65°	145.1	146.4	147.7	149.0	150.7	154.9	161.8	170.3	181.0	198.9	229.2
67.5°	114.1	115.4	115.8	118.4	122.1	124.7	128.9	136.5	143.9	159.1	176.3
70°	92.2	91.8	92.2	93.5	98.2	102.9	108.4	114.0	118.6	129.3	143.8
72.5°	79.2	78.4	79.6	79.8	82.1	83.4	86.9	92.1	98.2	105.4	115.9
75°	61.5	61.5	61.5	61.5	63.2	64.0	65.3	66.6	68.7	72.2	79.8
77.5°	45.4	45.5	46.1	46.6	46.9	47.4	48.2	49.4	50.2	52.0	55.4
80°	35.9	36.3	35.9	36.3	36.3	37.1	37.6	38.8	39.3	41.4	42.7
82.5°	27.0	26.7	27.0	27.4	27.4	28.3	28.4	29.3	29.4	30.5	31.8
85°	14.5	13.7	14.5	14.1	14.9	14.1	14.5	15.3	15.3	15.8	17.5
87.5°	8.3	8.9	8.2	8.4	8.3	8.6	8.4	8.3	8.8	8.3	8.2
90°	24.4	24.1	23.7	23.3	23.0	22.4	21.7	21.0	20.2	19.6	17.2
92.5°	27.0	26.8	26.6	26.3	26.2	25.4	24.3	23.2	22.0	20.9	19.1
95°	30.9	30.9	30.9	30.9	30.9	30.3	29.0	27.7	26.5	25.2	23.2
97.5°	33.5	33.3	33.2	33.0	32.8	32.0	30.6	29.1	27.6	26.2	39.2
100°	34.2	34.0	33.8	33.7	33.4	32.6	31.2	29.8	28.3	26.8	55.0
102.5°	34.8	34.5	34.2	33.8	33.5	35.6	40.1	44.6	49.1	53.6	84.4
105°	35.8	35.5	35.1	34.7	34.3	50.2	82.2	114.2	146.2	178.2	194.5
107.5°	112.4	136.6	160.7	184.8	209.0	232.8	256.2	279.7	303.2	326.7	324.1
110°	223.8	249.6	275.5	301.3	327.3	343.2	349.1	355.1	361.0	367.0	365.0



TEST NUMBER: P332318-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	383.9	389.4	394.8	400.3	405.8	408.5	408.4	408.2	408.1	408.1	406.0
115°	478.5	477.8	477.0	476.3	475.6	474.3	472.5	470.8	469.0	467.1	465.5
117.5°	531.6	531.4	531.2	531.2	531.0	530.2	528.7	527.3	525.9	524.4	523.6
120°	568.0	568.0	568.0	568.0	568.0	567.3	565.8	564.4	563.0	561.5	561.0
122.5°	603.8	603.6	603.6	603.4	603.2	602.7	601.7	600.6	599.7	598.6	597.9
125°	654.3	654.0	653.5	653.2	652.8	652.5	652.1	651.8	651.4	651.0	650.3
127.5°	702.8	703.1	703.5	703.8	704.3	704.1	703.5	703.0	702.4	701.8	700.9
130°	734.0	734.4	734.7	735.2	735.5	735.3	734.6	733.9	733.1	732.4	731.6
132.5°	762.7	763.2	763.7	764.2	764.7	764.6	763.9	763.1	762.5	761.7	761.2
135°	806.5	807.0	807.6	808.1	808.6	808.6	808.1	807.6	807.0	806.5	805.8
137.5°	847.7	848.0	848.4	848.7	849.1	848.8	848.0	847.1	846.2	845.4	845.0
140°	872.4	872.8	873.1	873.4	873.8	873.7	872.9	872.2	871.5	870.7	870.3
142.5°	895.2	895.7	896.2	896.7	897.2	897.2	896.6	896.0	895.4	894.9	894.3
145°	930.2	930.2	930.2	930.2	930.2	930.0	929.6	929.3	928.9	928.5	928.1
147.5°	956.2	957.0	957.9	958.7	959.5	959.8	959.4	959.0	958.7	958.3	958.0
150°	975.8	976.2	976.8	977.4	977.9	978.0	977.6	977.3	976.9	976.6	976.2
152.5°	991.3	992.2	993.0	993.8	994.7	994.7	994.1	993.4	992.8	992.1	992.0
155°	1013.2	1014.2	1015.4	1016.4	1017.5	1017.6	1016.7	1015.8	1014.9	1014.0	1013.8
157.5°	1031.6	1033.0	1034.4	1035.8	1037.2	1037.4	1036.2	1035.2	1034.1	1033.0	1033.2
160°	1043.3	1044.6	1045.8	1047.1	1048.3	1048.4	1047.3	1046.3	1045.2	1044.1	1044.2
162.5°	1054.3	1055.5	1056.5	1057.7	1058.8	1058.7	1057.5	1056.3	1055.1	1053.9	1054.0
165°	1067.7	1068.9	1070.2	1071.5	1072.8	1072.7	1071.2	1069.8	1068.3	1066.9	1067.1
167.5°	1077.3	1078.7	1080.2	1081.7	1083.0	1083.0	1081.7	1080.2	1078.7	1077.3	1077.3
170°	1083.1	1084.6	1086.1	1087.5	1088.9	1088.9	1087.5	1086.1	1084.6	1083.1	1083.1
172.5°	1086.4	1088.0	1089.6	1091.2	1092.7	1092.8	1091.4	1090.0	1088.5	1087.0	1086.9
175°	1091.3	1092.7	1094.2	1095.6	1097.1	1097.1	1095.9	1094.6	1093.4	1092.1	1091.9
177.5°	1092.7	1094.2	1095.7	1097.1	1098.5	1098.7	1097.6	1096.3	1095.2	1094.1	1093.9
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P332318-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1029.6	1028.5	1023.8	1018.3	1011.1	1006.3	1002.6	1000.5	994.4	986.8	981.8
5°	1093.2	1080.4	1066.7	1050.0	1034.7	1018.9	1009.1	997.5	983.5	967.7	956.6
7.5°	1161.3	1136.2	1109.1	1081.2	1053.6	1028.9	1007.1	988.3	965.9	943.2	927.4
10°	1213.6	1176.8	1138.8	1100.0	1064.5	1031.3	1005.7	980.5	953.6	927.6	907.9
12.5°	1261.0	1212.7	1168.9	1121.2	1075.9	1036.1	999.1	969.6	937.2	909.5	887.0
15°	1321.1	1271.6	1218.6	1146.1	1085.9	1035.5	990.8	951.9	912.6	878.5	856.7
17.5°	1377.3	1302.8	1231.7	1171.1	1092.9	1030.0	975.3	928.8	885.7	849.5	822.7
20°	1400.5	1328.4	1251.1	1173.9	1097.0	1026.5	963.0	911.7	866.9	826.0	801.2
22.5°	1414.5	1332.8	1251.4	1168.4	1086.8	1013.6	950.7	894.3	845.8	806.8	776.2
25°	1430.8	1333.5	1243.8	1161.9	1078.6	999.2	924.5	864.8	812.3	770.9	738.4
27.5°	1441.5	1327.1	1221.2	1130.0	1045.6	966.5	898.1	834.8	781.5	737.7	702.9
30°	1443.6	1321.9	1203.7	1105.1	1019.3	946.7	874.2	813.6	757.2	710.7	678.2
32.5°	1446.3	1309.3	1180.1	1075.4	987.6	915.7	849.9	792.1	734.3	688.5	655.4
35°	1435.1	1302.4	1144.4	1024.0	936.0	866.5	807.1	753.8	697.1	652.6	618.9
37.5°	1386.6	1274.6	1107.3	966.1	874.2	809.8	761.4	714.9	662.8	614.9	583.2
40°	1337.7	1247.2	1078.6	931.0	834.9	768.7	725.2	687.2	636.8	592.1	557.9
42.5°	1265.0	1210.1	1051.3	894.1	790.5	726.8	690.1	654.4	610.3	564.8	532.6
45°	1131.6	1138.8	995.4	835.4	729.0	665.0	630.5	605.7	566.5	528.9	496.0
47.5°	964.3	1032.1	929.8	772.7	664.2	604.1	574.0	552.4	525.9	489.0	459.0
50°	855.0	951.9	877.2	730.8	623.6	563.9	534.0	516.5	493.4	464.4	435.8
52.5°	754.2	858.3	813.7	684.0	579.6	525.0	495.8	481.4	463.0	435.7	409.9
55°	615.1	720.6	710.3	613.3	513.5	464.4	442.2	426.0	413.6	393.1	372.7
57.5°	497.6	597.5	602.8	534.8	455.3	406.8	387.7	375.4	367.4	351.9	333.0
60°	423.5	515.2	533.1	481.9	413.6	371.0	352.1	342.3	335.9	323.6	309.1
62.5°	362.0	440.1	460.4	423.5	373.7	333.7	319.0	309.6	305.2	294.5	281.7
65°	277.0	341.9	361.5	341.0	315.0	283.0	271.1	262.9	259.1	253.2	243.7
67.5°	208.3	255.6	277.1	262.7	253.3	233.1	225.4	221.1	217.7	213.6	205.8
70°	167.3	202.4	224.5	220.7	213.0	202.4	196.8	193.8	190.4	186.9	180.1
72.5°	134.5	158.7	179.4	181.4	175.1	172.9	168.1	166.8	164.8	160.7	156.9
75°	89.2	105.8	120.3	125.9	128.5	130.6	128.5	128.1	127.6	124.3	122.1
77.5°	58.5	67.4	76.6	86.0	90.1	92.9	93.7	95.2	94.1	92.3	91.2
80°	44.8	47.0	53.3	61.5	67.8	70.4	72.2	73.0	72.6	72.2	70.4
82.5°	32.5	34.3	37.3	43.0	48.4	52.7	53.7	53.6	54.5	54.7	53.3
85°	17.5	17.9	18.8	19.6	22.6	27.3	28.6	29.4	30.3	30.3	27.7
87.5°	8.4	7.6	7.8	7.4	8.1	8.1	9.8	11.1	11.8	10.8	11.2
90°	14.8	12.5	10.1	8.1	6.3	4.4	2.6	0.8	2.6	4.4	6.3
92.5°	17.3	15.5	13.8	13.1	13.6	14.1	14.6	15.2	14.6	14.1	13.6
95°	21.3	19.2	17.3	20.0	27.4	34.8	42.2	49.7	42.2	34.8	27.4
97.5°	52.3	65.3	78.3	86.4	89.8	93.1	96.4	99.8	96.4	93.1	89.8
100°	83.2	111.5	139.7	152.0	148.4	144.8	141.1	137.5	141.1	144.8	148.4
102.5°	115.2	146.0	176.8	190.9	188.3	185.7	183.1	180.5	183.1	185.7	188.3
105°	210.8	227.1	243.3	250.5	248.5	246.5	244.5	242.5	244.5	246.5	248.5
107.5°	321.6	318.9	316.4	314.3	312.7	311.1	309.6	307.9	309.6	311.1	312.7
110°	363.1	361.0	359.1	357.3	355.9	354.4	353.0	351.6	353.0	354.4	355.9





TEST NUMBER: P332318-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	404.1	402.1	400.1	398.4	397.1	395.8	394.5	393.2	394.5	395.8	397.1
115°	463.8	462.2	460.6	459.3	458.2	457.1	456.0	454.9	456.0	457.1	458.2
117.5°	522.8	521.9	521.1	520.0	518.7	517.3	516.0	514.6	516.0	517.3	518.7
120°	560.4	559.9	559.4	558.2	556.6	555.0	553.3	551.7	553.3	555.0	556.6
122.5°	597.3	596.6	595.9	594.8	593.5	592.2	590.8	589.5	590.8	592.2	593.5
125°	649.5	648.9	648.2	647.0	645.6	644.2	642.7	641.2	642.7	644.2	645.6
127.5°	700.1	699.2	698.3	697.2	695.7	694.3	692.8	691.4	692.8	694.3	695.7
130°	731.0	730.3	729.5	728.5	727.0	725.5	724.1	722.7	724.1	725.5	727.0
132.5°	760.5	759.9	759.4	758.4	756.9	755.5	754.1	752.6	754.1	755.5	756.9
135°	805.0	804.3	803.6	802.7	801.6	800.5	799.4	798.3	799.4	800.5	801.6
137.5°	844.6	844.2	843.8	842.9	841.6	840.2	838.8	837.4	838.8	840.2	841.6
140°	869.7	869.1	868.6	867.8	866.7	865.6	864.5	863.4	864.5	865.6	866.7
142.5°	893.7	893.2	892.7	891.9	890.8	889.7	888.6	887.5	888.6	889.7	890.8
145°	927.8	927.5	927.1	926.3	925.0	923.7	922.5	921.2	922.5	923.7	925.0
147.5°	957.6	957.2	956.8	956.3	955.4	954.6	953.8	952.9	953.8	954.6	955.4
150°	975.8	975.4	975.1	974.6	974.1	973.5	973.1	972.5	973.1	973.5	974.1
152.5°	991.7	991.5	991.3	991.1	990.8	990.6	990.3	990.0	990.3	990.6	990.8
155°	1013.6	1013.4	1013.3	1013.3	1013.7	1014.1	1014.4	1014.8	1014.4	1014.1	1013.7
157.5°	1033.4	1033.6	1033.7	1033.9	1033.9	1034.0	1034.0	1034.0	1034.0	1034.0	1033.9
160°	1044.5	1044.6	1044.8	1045.0	1045.2	1045.4	1045.5	1045.7	1045.5	1045.4	1045.2
162.5°	1054.2	1054.4	1054.6	1054.9	1055.4	1055.8	1056.3	1056.8	1056.3	1055.8	1055.4
165°	1067.2	1067.4	1067.6	1068.0	1068.5	1069.0	1069.6	1070.2	1069.6	1069.0	1068.5
167.5°	1077.3	1077.3	1077.3	1077.7	1078.4	1079.1	1079.9	1080.5	1079.9	1079.1	1078.4
170°	1083.1	1083.1	1083.1	1083.5	1084.3	1085.0	1085.7	1086.4	1085.7	1085.0	1084.3
172.5°	1086.8	1086.6	1086.5	1086.9	1087.7	1088.6	1089.5	1090.3	1089.5	1088.6	1087.7
175°	1091.8	1091.5	1091.4	1091.8	1092.7	1093.6	1094.5	1095.4	1094.5	1093.6	1092.7
177.5°	1093.8	1093.6	1093.5	1093.8	1094.5	1095.2	1095.9	1096.7	1095.9	1095.2	1094.5
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P332318-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	980.1	975.6	972.6	965.7	961.2	956.5	951.7	954.8	954.5	954.1	954.1
5°	947.2	937.3	928.4	916.9	909.6	900.7	893.8	893.0	894.7	888.7	885.3
7.5°	914.6	901.2	888.4	875.7	862.3	851.5	844.7	841.6	837.2	833.6	829.7
10°	891.7	875.9	863.5	847.7	833.2	820.4	812.3	806.7	803.7	800.8	795.2
12.5°	868.1	852.6	836.9	819.0	805.2	790.4	784.3	778.0	772.3	769.0	761.4
15°	833.6	813.6	797.0	778.1	762.8	748.3	739.7	727.3	725.6	721.4	713.7
17.5°	799.1	777.3	754.3	740.5	723.1	708.0	695.0	690.8	678.6	674.0	667.3
20°	771.8	751.7	734.2	715.8	690.6	676.5	666.3	660.8	650.9	645.0	640.7
22.5°	748.2	727.8	707.5	686.2	665.4	649.5	642.0	633.4	628.1	619.7	615.1
25°	714.5	692.4	668.1	645.0	630.1	618.1	606.1	598.4	590.8	586.9	578.4
27.5°	675.5	652.2	629.5	612.0	593.7	581.9	571.0	564.2	555.0	548.5	543.8
30°	654.0	626.6	607.0	591.2	567.7	556.6	548.5	540.0	533.1	526.3	521.6
32.5°	629.0	604.1	585.5	565.9	547.9	535.8	525.3	517.8	511.9	505.5	500.8
35°	589.9	569.0	549.8	530.1	516.9	504.5	492.2	485.8	480.2	474.3	469.9
37.5°	554.6	535.0	516.7	498.1	481.8	471.7	461.7	456.8	449.3	445.3	440.9
40°	532.7	513.5	493.8	476.0	458.9	451.2	442.2	435.0	428.1	425.2	420.4
42.5°	508.8	489.6	473.0	453.7	439.8	429.3	421.0	413.1	408.0	403.7	401.0
45°	473.4	456.3	440.1	420.9	407.6	398.7	389.3	382.0	377.3	374.4	369.7
47.5°	439.0	421.9	405.4	388.7	375.9	365.7	356.3	351.2	345.0	341.3	338.2
50°	414.0	398.7	381.2	365.8	353.0	342.8	335.1	328.6	323.1	318.5	316.3
52.5°	391.2	374.8	359.6	345.4	331.8	320.2	313.2	306.5	302.3	296.9	294.4
55°	353.4	337.6	324.8	310.7	297.5	287.7	279.2	273.2	268.9	262.9	259.5
57.5°	318.0	303.9	288.5	276.3	262.7	254.4	247.3	239.2	234.0	229.3	226.0
60°	294.1	277.9	264.6	253.2	241.2	230.5	224.1	217.7	212.1	207.4	204.5
62.5°	269.2	255.0	242.5	229.9	219.0	209.7	202.3	196.9	192.0	189.0	186.1
65°	230.9	219.8	207.0	196.8	186.5	179.7	173.7	169.0	165.6	163.5	160.9
67.5°	195.8	185.0	173.8	163.7	156.9	151.7	147.8	143.7	142.0	139.3	137.6
70°	172.8	161.8	152.0	144.3	137.5	133.6	131.0	128.1	126.4	122.9	121.2
72.5°	148.0	139.9	132.8	126.5	121.1	117.6	114.3	110.6	107.9	104.1	102.5
75°	116.5	109.3	103.7	99.5	96.0	91.3	86.7	82.8	81.5	80.2	79.8
77.5°	86.3	81.7	77.7	74.1	69.9	66.4	65.4	64.6	64.2	63.6	63.6
80°	67.8	63.6	60.6	56.3	53.8	53.8	53.8	52.9	53.3	53.3	53.3
82.5°	50.5	46.6	44.9	43.4	42.9	43.2	43.2	43.4	43.1	43.8	43.5
85°	26.0	26.5	27.3	26.9	27.3	27.3	28.2	27.7	28.2	27.3	28.2
87.5°	11.2	12.6	13.5	14.3	15.1	15.2	15.7	15.8	16.3	16.5	16.6
90°	8.1	10.1	12.5	14.8	17.2	19.6	20.2	21.0	21.7	22.4	23.0
92.5°	13.1	13.8	15.5	17.3	19.1	20.9	22.0	23.2	24.3	25.4	26.2
95°	20.0	17.3	19.2	21.3	23.2	25.2	26.5	27.7	29.0	30.3	30.9
97.5°	86.4	78.3	65.3	52.3	39.2	26.2	27.6	29.1	30.6	32.0	32.8
100°	152.0	139.7	111.5	83.2	55.0	26.8	28.3	29.8	31.2	32.6	33.4
102.5°	190.9	176.8	146.0	115.2	84.4	53.6	49.1	44.6	40.1	35.6	33.5
105°	250.5	243.3	227.1	210.8	194.5	178.2	146.2	114.2	82.2	50.2	34.3
107.5°	314.3	316.4	318.9	321.6	324.1	326.7	303.2	279.7	256.2	232.8	209.0
110°	357.3	359.1	361.0	363.1	365.0	367.0	361.0	355.1	349.1	343.2	327.3



TEST NUMBER: P332318-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	398.4	400.1	402.1	404.1	406.0	408.1	408.1	408.2	408.4	408.5	405.8
115°	459.3	460.6	462.2	463.8	465.5	467.1	469.0	470.8	472.5	474.3	475.6
117.5°	520.0	521.1	521.9	522.8	523.6	524.4	525.9	527.3	528.7	530.2	531.0
120°	558.2	559.4	559.9	560.4	561.0	561.5	563.0	564.4	565.8	567.3	568.0
122.5°	594.8	595.9	596.6	597.3	597.9	598.6	599.7	600.6	601.7	602.7	603.2
125°	647.0	648.2	648.9	649.5	650.3	651.0	651.4	651.8	652.1	652.5	652.8
127.5°	697.2	698.3	699.2	700.1	700.9	701.8	702.4	703.0	703.5	704.1	704.3
130°	728.5	729.5	730.3	731.0	731.6	732.4	733.1	733.9	734.6	735.3	735.5
132.5°	758.4	759.4	759.9	760.5	761.2	761.7	762.5	763.1	763.9	764.6	764.7
135°	802.7	803.6	804.3	805.0	805.8	806.5	807.0	807.6	808.1	808.6	808.6
137.5°	842.9	843.8	844.2	844.6	845.0	845.4	846.2	847.1	848.0	848.8	849.1
140°	867.8	868.6	869.1	869.7	870.3	870.7	871.5	872.2	872.9	873.7	873.8
142.5°	891.9	892.7	893.2	893.7	894.3	894.9	895.4	896.0	896.6	897.2	897.2
145°	926.3	927.1	927.5	927.8	928.1	928.5	928.9	929.3	929.6	930.0	930.2
147.5°	956.3	956.8	957.2	957.6	958.0	958.3	958.7	959.0	959.4	959.8	959.5
150°	974.6	975.1	975.4	975.8	976.2	976.6	976.9	977.3	977.6	978.0	977.9
152.5°	991.1	991.3	991.5	991.7	992.0	992.1	992.8	993.4	994.1	994.7	994.7
155°	1013.3	1013.3	1013.4	1013.6	1013.8	1014.0	1014.9	1015.8	1016.7	1017.6	1017.5
157.5°	1033.9	1033.7	1033.6	1033.4	1033.2	1033.0	1034.1	1035.2	1036.2	1037.4	1037.2
160°	1045.0	1044.8	1044.6	1044.5	1044.2	1044.1	1045.2	1046.3	1047.3	1048.4	1048.3
162.5°	1054.9	1054.6	1054.4	1054.2	1054.0	1053.9	1055.1	1056.3	1057.5	1058.7	1058.8
165°	1068.0	1067.6	1067.4	1067.2	1067.1	1066.9	1068.3	1069.8	1071.2	1072.7	1072.8
167.5°	1077.7	1077.3	1077.3	1077.3	1077.3	1077.3	1078.7	1080.2	1081.7	1083.0	1083.0
170°	1083.5	1083.1	1083.1	1083.1	1083.1	1083.1	1084.6	1086.1	1087.5	1088.9	1088.9
172.5°	1086.9	1086.5	1086.6	1086.8	1086.9	1087.0	1088.5	1090.0	1091.4	1092.8	1092.7
175°	1091.8	1091.4	1091.5	1091.8	1091.9	1092.1	1093.4	1094.6	1095.9	1097.1	1097.1
177.5°	1093.8	1093.5	1093.6	1093.8	1093.9	1094.1	1095.2	1096.3	1097.6	1098.7	1098.5
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P332318-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	950.0	949.7	950.0	948.6	950.0	949.7	950.0	954.1	954.1	954.5	954.8
5°	884.0	883.5	882.3	878.5	882.3	883.5	884.0	885.3	888.7	894.7	893.0
7.5°	826.4	825.8	822.1	822.1	822.1	825.8	826.4	829.7	833.6	837.2	841.6
10°	792.2	792.6	787.6	784.6	787.6	792.6	792.2	795.2	800.8	803.7	806.7
12.5°	759.1	757.2	753.0	749.7	753.0	757.2	759.1	761.4	769.0	772.3	778.0
15°	715.4	711.1	700.9	701.7	700.9	711.1	715.4	713.7	721.4	725.6	727.3
17.5°	663.9	660.8	660.6	654.6	660.6	660.8	663.9	667.3	674.0	678.6	690.8
20°	633.9	631.8	632.6	626.6	632.6	631.8	633.9	640.7	645.0	650.9	660.8
22.5°	610.3	608.2	604.6	602.8	604.6	608.2	610.3	615.1	619.7	628.1	633.4
25°	575.8	572.4	569.0	571.1	569.0	572.4	575.8	578.4	586.9	590.8	598.4
27.5°	541.4	538.7	535.3	534.9	535.3	538.7	541.4	543.8	548.5	555.0	564.2
30°	519.5	516.9	515.2	513.1	515.2	516.9	519.5	521.6	526.3	533.1	540.0
32.5°	497.3	496.8	493.7	493.3	493.7	496.8	497.3	500.8	505.5	511.9	517.8
35°	468.2	465.7	464.8	465.3	464.8	465.7	468.2	469.9	474.3	480.2	485.8
37.5°	440.7	437.2	435.7	434.2	435.7	437.2	440.7	440.9	445.3	449.3	456.8
40°	420.9	417.4	416.6	415.7	416.6	417.4	420.9	420.4	425.2	428.1	435.0
42.5°	398.7	397.3	396.8	395.3	396.8	397.3	398.7	401.0	403.7	408.0	413.1
45°	368.4	367.9	365.4	366.2	365.4	367.9	368.4	369.7	374.4	377.3	382.0
47.5°	336.5	334.6	332.8	333.9	332.8	334.6	336.5	338.2	341.3	345.0	351.2
50°	314.6	313.7	309.9	310.7	309.9	313.7	314.6	316.3	318.5	323.1	328.6
52.5°	292.8	289.5	288.0	287.6	288.0	289.5	292.8	294.4	296.9	302.3	306.5
55°	256.6	252.7	250.9	250.1	250.9	252.7	256.6	259.5	262.9	268.9	273.2
57.5°	221.0	220.0	218.7	219.6	218.7	220.0	221.0	226.0	229.3	234.0	239.2
60°	200.2	200.2	200.2	199.7	200.2	200.2	200.2	204.5	207.4	212.1	217.7
62.5°	184.2	183.1	182.8	183.4	182.8	183.1	184.2	186.1	189.0	192.0	196.9
65°	159.6	159.2	157.5	157.1	157.5	159.2	159.6	160.9	163.5	165.6	169.0
67.5°	136.5	134.9	134.4	133.9	134.4	134.9	136.5	137.6	139.3	142.0	143.7
70°	119.1	118.2	115.7	116.1	115.7	118.2	119.1	121.2	122.9	126.4	128.1
72.5°	100.3	99.5	99.0	98.3	99.0	99.5	100.3	102.5	104.1	107.9	110.6
75°	79.4	79.0	78.5	80.2	78.5	79.0	79.4	79.8	80.2	81.5	82.8
77.5°	63.6	63.6	63.8	63.2	63.8	63.6	63.6	63.6	63.6	64.2	64.6
80°	53.3	53.3	52.9	52.9	52.9	53.3	53.3	53.3	53.3	53.3	52.9
82.5°	42.8	43.1	43.4	42.7	43.4	43.1	42.8	43.5	43.8	43.1	43.4
85°	28.2	27.7	28.6	28.2	28.6	27.7	28.2	28.2	27.3	28.2	27.7
87.5°	17.3	16.7	16.8	17.2	16.8	16.7	17.3	16.6	16.5	16.3	15.8
90°	23.3	23.7	24.1	24.4	24.1	23.7	23.3	23.0	22.4	21.7	21.0
92.5°	26.3	26.6	26.8	27.0	26.8	26.6	26.3	26.2	25.4	24.3	23.2
95°	30.9	30.9	30.9	30.9	30.9	30.9	30.9	30.9	30.3	29.0	27.7
97.5°	33.0	33.2	33.3	33.5	33.3	33.2	33.0	32.8	32.0	30.6	29.1
100°	33.7	33.8	34.0	34.2	34.0	33.8	33.7	33.4	32.6	31.2	29.8
102.5°	33.8	34.2	34.5	34.8	34.5	34.2	33.8	33.5	35.6	40.1	44.6
105°	34.7	35.1	35.5	35.8	35.5	35.1	34.7	34.3	50.2	82.2	114.2
107.5°	184.8	160.7	136.6	112.4	136.6	160.7	184.8	209.0	232.8	256.2	279.7
110°	301.3	275.5	249.6	223.8	249.6	275.5	301.3	327.3	343.2	349.1	355.1



TEST NUMBER: P332318-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	400.3	394.8	389.4	383.9	389.4	394.8	400.3	405.8	408.5	408.4	408.2
115°	476.3	477.0	477.8	478.5	477.8	477.0	476.3	475.6	474.3	472.5	470.8
117.5°	531.2	531.2	531.4	531.6	531.4	531.2	531.2	531.0	530.2	528.7	527.3
120°	568.0	568.0	568.0	568.0	568.0	568.0	568.0	568.0	567.3	565.8	564.4
122.5°	603.4	603.6	603.6	603.8	603.6	603.6	603.4	603.2	602.7	601.7	600.6
125°	653.2	653.5	654.0	654.3	654.0	653.5	653.2	652.8	652.5	652.1	651.8
127.5°	703.8	703.5	703.1	702.8	703.1	703.5	703.8	704.3	704.1	703.5	703.0
130°	735.2	734.7	734.4	734.0	734.4	734.7	735.2	735.5	735.3	734.6	733.9
132.5°	764.2	763.7	763.2	762.7	763.2	763.7	764.2	764.7	764.6	763.9	763.1
135°	808.1	807.6	807.0	806.5	807.0	807.6	808.1	808.6	808.6	808.1	807.6
137.5°	848.7	848.4	848.0	847.7	848.0	848.4	848.7	849.1	848.8	848.0	847.1
140°	873.4	873.1	872.8	872.4	872.8	873.1	873.4	873.8	873.7	872.9	872.2
142.5°	896.7	896.2	895.7	895.2	895.7	896.2	896.7	897.2	897.2	896.6	896.0
145°	930.2	930.2	930.2	930.2	930.2	930.2	930.2	930.2	930.0	929.6	929.3
147.5°	958.7	957.9	957.0	956.2	957.0	957.9	958.7	959.5	959.8	959.4	959.0
150°	977.4	976.8	976.2	975.8	976.2	976.8	977.4	977.9	978.0	977.6	977.3
152.5°	993.8	993.0	992.2	991.3	992.2	993.0	993.8	994.7	994.7	994.1	993.4
155°	1016.4	1015.4	1014.2	1013.2	1014.2	1015.4	1016.4	1017.5	1017.6	1016.7	1015.8
157.5°	1035.8	1034.4	1033.0	1031.6	1033.0	1034.4	1035.8	1037.2	1037.4	1036.2	1035.2
160°	1047.1	1045.8	1044.6	1043.3	1044.6	1045.8	1047.1	1048.3	1048.4	1047.3	1046.3
162.5°	1057.7	1056.5	1055.5	1054.3	1055.5	1056.5	1057.7	1058.8	1058.7	1057.5	1056.3
165°	1071.5	1070.2	1068.9	1067.7	1068.9	1070.2	1071.5	1072.8	1072.7	1071.2	1069.8
167.5°	1081.7	1080.2	1078.7	1077.3	1078.7	1080.2	1081.7	1083.0	1083.0	1081.7	1080.2
170°	1087.5	1086.1	1084.6	1083.1	1084.6	1086.1	1087.5	1088.9	1088.9	1087.5	1086.1
172.5°	1091.2	1089.6	1088.0	1086.4	1088.0	1089.6	1091.2	1092.7	1092.8	1091.4	1090.0
175°	1095.6	1094.2	1092.7	1091.3	1092.7	1094.2	1095.6	1097.1	1097.1	1095.9	1094.6
177.5°	1097.1	1095.7	1094.2	1092.7	1094.2	1095.7	1097.1	1098.5	1098.7	1097.6	1096.3
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P332318-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	951.7	956.5	961.2	965.7	972.6	975.6	980.1	981.8	986.8	994.4	1000.5
5°	893.8	900.7	909.6	916.9	928.4	937.3	947.2	956.6	967.7	983.5	997.5
7.5°	844.7	851.5	862.3	875.7	888.4	901.2	914.6	927.4	943.2	965.9	988.3
10°	812.3	820.4	833.2	847.7	863.5	875.9	891.7	907.9	927.6	953.6	980.5
12.5°	784.3	790.4	805.2	819.0	836.9	852.6	868.1	887.0	909.5	937.2	969.6
15°	739.7	748.3	762.8	778.1	797.0	813.6	833.6	856.7	878.5	912.6	951.9
17.5°	695.0	708.0	723.1	740.5	754.3	777.3	799.1	822.7	849.5	885.7	928.8
20°	666.3	676.5	690.6	715.8	734.2	751.7	771.8	801.2	826.0	866.9	911.7
22.5°	642.0	649.5	665.4	686.2	707.5	727.8	748.2	776.2	806.8	845.8	894.3
25°	606.1	618.1	630.1	645.0	668.1	692.4	714.5	738.4	770.9	812.3	864.8
27.5°	571.0	581.9	593.7	612.0	629.5	652.2	675.5	702.9	737.7	781.5	834.8
30°	548.5	556.6	567.7	591.2	607.0	626.6	654.0	678.2	710.7	757.2	813.6
32.5°	525.3	535.8	547.9	565.9	585.5	604.1	629.0	655.4	688.5	734.3	792.1
35°	492.2	504.5	516.9	530.1	549.8	569.0	589.9	618.9	652.6	697.1	753.8
37.5°	461.7	471.7	481.8	498.1	516.7	535.0	554.6	583.2	614.9	662.8	714.9
40°	442.2	451.2	458.9	476.0	493.8	513.5	532.7	557.9	592.1	636.8	687.2
42.5°	421.0	429.3	439.8	453.7	473.0	489.6	508.8	532.6	564.8	610.3	654.4
45°	389.3	398.7	407.6	420.9	440.1	456.3	473.4	496.0	528.9	566.5	605.7
47.5°	356.3	365.7	375.9	388.7	405.4	421.9	439.0	459.0	489.0	525.9	552.4
50°	335.1	342.8	353.0	365.8	381.2	398.7	414.0	435.8	464.4	493.4	516.5
52.5°	313.2	320.2	331.8	345.4	359.6	374.8	391.2	409.9	435.7	463.0	481.4
55°	279.2	287.7	297.5	310.7	324.8	337.6	353.4	372.7	393.1	413.6	426.0
57.5°	247.3	254.4	262.7	276.3	288.5	303.9	318.0	333.0	351.9	367.4	375.4
60°	224.1	230.5	241.2	253.2	264.6	277.9	294.1	309.1	323.6	335.9	342.3
62.5°	202.3	209.7	219.0	229.9	242.5	255.0	269.2	281.7	294.5	305.2	309.6
65°	173.7	179.7	186.5	196.8	207.0	219.8	230.9	243.7	253.2	259.1	262.9
67.5°	147.8	151.7	156.9	163.7	173.8	185.0	195.8	205.8	213.6	217.7	221.1
70°	131.0	133.6	137.5	144.3	152.0	161.8	172.8	180.1	186.9	190.4	193.8
72.5°	114.3	117.6	121.1	126.5	132.8	139.9	148.0	156.9	160.7	164.8	166.8
75°	86.7	91.3	96.0	99.5	103.7	109.3	116.5	122.1	124.3	127.6	128.1
77.5°	65.4	66.4	69.9	74.1	77.7	81.7	86.3	91.2	92.3	94.1	95.2
80°	53.8	53.8	53.8	56.3	60.6	63.6	67.8	70.4	72.2	72.6	73.0
82.5°	43.2	43.2	42.9	43.4	44.9	46.6	50.5	53.3	54.7	54.5	53.6
85°	28.2	27.3	27.3	26.9	27.3	26.5	26.0	27.7	30.3	30.3	29.4
87.5°	15.7	15.2	15.1	14.3	13.5	12.6	11.2	11.2	10.8	11.8	11.1
90°	20.2	19.6	17.2	14.8	12.5	10.1	8.1	6.3	4.4	2.6	0.8
92.5°	22.0	20.9	19.1	17.3	15.5	13.8	13.1	13.6	14.1	14.6	15.2
95°	26.5	25.2	23.2	21.3	19.2	17.3	20.0	27.4	34.8	42.2	49.7
97.5°	27.6	26.2	39.2	52.3	65.3	78.3	86.4	89.8	93.1	96.4	99.8
100°	28.3	26.8	55.0	83.2	111.5	139.7	152.0	148.4	144.8	141.1	137.5
102.5°	49.1	53.6	84.4	115.2	146.0	176.8	190.9	188.3	185.7	183.1	180.5
105°	146.2	178.2	194.5	210.8	227.1	243.3	250.5	248.5	246.5	244.5	242.5
107.5°	303.2	326.7	324.1	321.6	318.9	316.4	314.3	312.7	311.1	309.6	307.9
110°	361.0	367.0	365.0	363.1	361.0	359.1	357.3	355.9	354.4	353.0	351.6



TEST NUMBER: P332318-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	408.1	408.1	406.0	404.1	402.1	400.1	398.4	397.1	395.8	394.5	393.2
115°	469.0	467.1	465.5	463.8	462.2	460.6	459.3	458.2	457.1	456.0	454.9
117.5°	525.9	524.4	523.6	522.8	521.9	521.1	520.0	518.7	517.3	516.0	514.6
120°	563.0	561.5	561.0	560.4	559.9	559.4	558.2	556.6	555.0	553.3	551.7
122.5°	599.7	598.6	597.9	597.3	596.6	595.9	594.8	593.5	592.2	590.8	589.5
125°	651.4	651.0	650.3	649.5	648.9	648.2	647.0	645.6	644.2	642.7	641.2
127.5°	702.4	701.8	700.9	700.1	699.2	698.3	697.2	695.7	694.3	692.8	691.4
130°	733.1	732.4	731.6	731.0	730.3	729.5	728.5	727.0	725.5	724.1	722.7
132.5°	762.5	761.7	761.2	760.5	759.9	759.4	758.4	756.9	755.5	754.1	752.6
135°	807.0	806.5	805.8	805.0	804.3	803.6	802.7	801.6	800.5	799.4	798.3
137.5°	846.2	845.4	845.0	844.6	844.2	843.8	842.9	841.6	840.2	838.8	837.4
140°	871.5	870.7	870.3	869.7	869.1	868.6	867.8	866.7	865.6	864.5	863.4
142.5°	895.4	894.9	894.3	893.7	893.2	892.7	891.9	890.8	889.7	888.6	887.5
145°	928.9	928.5	928.1	927.8	927.5	927.1	926.3	925.0	923.7	922.5	921.2
147.5°	958.7	958.3	958.0	957.6	957.2	956.8	956.3	955.4	954.6	953.8	952.9
150°	976.9	976.6	976.2	975.8	975.4	975.1	974.6	974.1	973.5	973.1	972.5
152.5°	992.8	992.1	992.0	991.7	991.5	991.3	991.1	990.8	990.6	990.3	990.0
155°	1014.9	1014.0	1013.8	1013.6	1013.4	1013.3	1013.3	1013.7	1014.1	1014.4	1014.8
157.5°	1034.1	1033.0	1033.2	1033.4	1033.6	1033.7	1033.9	1033.9	1034.0	1034.0	1034.0
160°	1045.2	1044.1	1044.2	1044.5	1044.6	1044.8	1045.0	1045.2	1045.4	1045.5	1045.7
162.5°	1055.1	1053.9	1054.0	1054.2	1054.4	1054.6	1054.9	1055.4	1055.8	1056.3	1056.8
165°	1068.3	1066.9	1067.1	1067.2	1067.4	1067.6	1068.0	1068.5	1069.0	1069.6	1070.2
167.5°	1078.7	1077.3	1077.3	1077.3	1077.3	1077.3	1077.7	1078.4	1079.1	1079.9	1080.5
170°	1084.6	1083.1	1083.1	1083.1	1083.1	1083.1	1083.5	1084.3	1085.0	1085.7	1086.4
172.5°	1088.5	1087.0	1086.9	1086.8	1086.6	1086.5	1086.9	1087.7	1088.6	1089.5	1090.3
175°	1093.4	1092.1	1091.9	1091.8	1091.5	1091.4	1091.8	1092.7	1093.6	1094.5	1095.4
177.5°	1095.2	1094.1	1093.9	1093.8	1093.6	1093.5	1093.8	1094.5	1095.2	1095.9	1096.7
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P332318-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1002.6	1006.3	1011.1	1018.3	1023.8	1028.5	1029.6	1030.9	1034.4	1040.2	1044.6
5°	1009.1	1018.9	1034.7	1050.0	1066.7	1080.4	1093.2	1102.1	1110.7	1128.6	1143.1
7.5°	1007.1	1028.9	1053.6	1081.2	1109.1	1136.2	1161.3	1183.7	1206.1	1232.2	1262.0
10°	1005.7	1031.3	1064.5	1100.0	1138.8	1176.8	1213.6	1242.1	1275.5	1305.3	1343.3
12.5°	999.1	1036.1	1075.9	1121.2	1168.9	1212.7	1261.0	1300.6	1338.6	1381.8	1426.0
15°	990.8	1035.5	1085.9	1146.1	1218.6	1271.6	1321.1	1389.8	1436.8	1483.8	1546.9
17.5°	975.3	1030.0	1092.9	1171.1	1231.7	1302.8	1377.3	1431.6	1494.9	1561.0	1618.2
20°	963.0	1026.5	1097.0	1173.9	1251.1	1328.4	1400.5	1465.3	1530.7	1607.1	1654.1
22.5°	950.7	1013.6	1086.8	1168.4	1251.4	1332.8	1414.5	1490.6	1564.2	1641.3	1701.2
25°	924.5	999.2	1078.6	1161.9	1243.8	1333.5	1430.8	1515.7	1606.6	1686.0	1742.9
27.5°	898.1	966.5	1045.6	1130.0	1221.2	1327.1	1441.5	1538.1	1629.2	1686.0	1703.9
30°	874.2	946.7	1019.3	1105.1	1203.7	1321.9	1443.6	1554.1	1628.9	1653.6	1635.2
32.5°	849.9	915.7	987.6	1075.4	1180.1	1309.3	1446.3	1544.6	1589.6	1570.7	1495.9
35°	807.1	866.5	936.0	1024.0	1144.4	1302.4	1435.1	1501.6	1490.5	1383.8	1243.0
37.5°	761.4	809.8	874.2	966.1	1107.3	1274.6	1386.6	1396.4	1300.3	1136.5	973.8
40°	725.2	768.7	834.9	931.0	1078.6	1247.2	1337.7	1298.0	1149.1	966.8	831.1
42.5°	690.1	726.8	790.5	894.1	1051.3	1210.1	1265.0	1178.5	1006.7	834.3	710.9
45°	630.5	665.0	729.0	835.4	995.4	1138.8	1131.6	981.3	809.3	670.6	568.1
47.5°	574.0	604.1	664.2	772.7	929.8	1032.1	964.3	804.4	658.4	547.1	474.1
50°	534.0	563.9	623.6	730.8	877.2	951.9	855.0	700.9	567.3	475.1	417.0
52.5°	495.8	525.0	579.6	684.0	813.7	858.3	754.2	611.4	500.0	420.4	370.6
55°	442.2	464.4	513.5	613.3	710.3	720.6	615.1	495.5	403.8	348.3	314.1
57.5°	387.7	406.8	455.3	534.8	602.8	597.5	497.6	394.1	332.3	291.1	266.4
60°	352.1	371.0	413.6	481.9	533.1	515.2	423.5	340.2	287.2	257.0	237.3
62.5°	319.0	333.7	373.7	423.5	460.4	440.1	362.0	293.1	251.1	225.5	210.0
65°	271.1	283.0	315.0	341.0	361.5	341.9	277.0	229.2	198.9	181.0	170.3
67.5°	225.4	233.1	253.3	262.7	277.1	255.6	208.3	176.3	159.1	143.9	136.5
70°	196.8	202.4	213.0	220.7	224.5	202.4	167.3	143.8	129.3	118.6	114.0
72.5°	168.1	172.9	175.1	181.4	179.4	158.7	134.5	115.9	105.4	98.2	92.1
75°	128.5	130.6	128.5	125.9	120.3	105.8	89.2	79.8	72.2	68.7	66.6
77.5°	93.7	92.9	90.1	86.0	76.6	67.4	58.5	55.4	52.0	50.2	49.4
80°	72.2	70.4	67.8	61.5	53.3	47.0	44.8	42.7	41.4	39.3	38.8
82.5°	53.7	52.7	48.4	43.0	37.3	34.3	32.5	31.8	30.5	29.4	29.3
85°	28.6	27.3	22.6	19.6	18.8	17.9	17.5	17.5	15.8	15.3	15.3
87.5°	9.8	8.1	8.1	7.4	7.8	7.6	8.4	8.2	8.3	8.8	8.3
90°	2.6	4.4	6.3	8.1	10.1	12.5	14.8	17.2	19.6	20.2	21.0
92.5°	14.6	14.1	13.6	13.1	13.8	15.5	17.3	19.1	20.9	22.0	23.2
95°	42.2	34.8	27.4	20.0	17.3	19.2	21.3	23.2	25.2	26.5	27.7
97.5°	96.4	93.1	89.8	86.4	78.3	65.3	52.3	39.2	26.2	27.6	29.1
100°	141.1	144.8	148.4	152.0	139.7	111.5	83.2	55.0	26.8	28.3	29.8
102.5°	183.1	185.7	188.3	190.9	176.8	146.0	115.2	84.4	53.6	49.1	44.6
105°	244.5	246.5	248.5	250.5	243.3	227.1	210.8	194.5	178.2	146.2	114.2
107.5°	309.6	311.1	312.7	314.3	316.4	318.9	321.6	324.1	326.7	303.2	279.7
110°	353.0	354.4	355.9	357.3	359.1	361.0	363.1	365.0	367.0	361.0	355.1





TEST NUMBER: P332318-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	394.5	395.8	397.1	398.4	400.1	402.1	404.1	406.0	408.1	408.1	408.2
115°	456.0	457.1	458.2	459.3	460.6	462.2	463.8	465.5	467.1	469.0	470.8
117.5°	516.0	517.3	518.7	520.0	521.1	521.9	522.8	523.6	524.4	525.9	527.3
120°	553.3	555.0	556.6	558.2	559.4	559.9	560.4	561.0	561.5	563.0	564.4
122.5°	590.8	592.2	593.5	594.8	595.9	596.6	597.3	597.9	598.6	599.7	600.6
125°	642.7	644.2	645.6	647.0	648.2	648.9	649.5	650.3	651.0	651.4	651.8
127.5°	692.8	694.3	695.7	697.2	698.3	699.2	700.1	700.9	701.8	702.4	703.0
130°	724.1	725.5	727.0	728.5	729.5	730.3	731.0	731.6	732.4	733.1	733.9
132.5°	754.1	755.5	756.9	758.4	759.4	759.9	760.5	761.2	761.7	762.5	763.1
135°	799.4	800.5	801.6	802.7	803.6	804.3	805.0	805.8	806.5	807.0	807.6
137.5°	838.8	840.2	841.6	842.9	843.8	844.2	844.6	845.0	845.4	846.2	847.1
140°	864.5	865.6	866.7	867.8	868.6	869.1	869.7	870.3	870.7	871.5	872.2
142.5°	888.6	889.7	890.8	891.9	892.7	893.2	893.7	894.3	894.9	895.4	896.0
145°	922.5	923.7	925.0	926.3	927.1	927.5	927.8	928.1	928.5	928.9	929.3
147.5°	953.8	954.6	955.4	956.3	956.8	957.2	957.6	958.0	958.3	958.7	959.0
150°	973.1	973.5	974.1	974.6	975.1	975.4	975.8	976.2	976.6	976.9	977.3
152.5°	990.3	990.6	990.8	991.1	991.3	991.5	991.7	992.0	992.1	992.8	993.4
155°	1014.4	1014.1	1013.7	1013.3	1013.3	1013.4	1013.6	1013.8	1014.0	1014.9	1015.8
157.5°	1034.0	1034.0	1033.9	1033.9	1033.7	1033.6	1033.4	1033.2	1033.0	1034.1	1035.2
160°	1045.5	1045.4	1045.2	1045.0	1044.8	1044.6	1044.5	1044.2	1044.1	1045.2	1046.3
162.5°	1056.3	1055.8	1055.4	1054.9	1054.6	1054.4	1054.2	1054.0	1053.9	1055.1	1056.3
165°	1069.6	1069.0	1068.5	1068.0	1067.6	1067.4	1067.2	1067.1	1066.9	1068.3	1069.8
167.5°	1079.9	1079.1	1078.4	1077.7	1077.3	1077.3	1077.3	1077.3	1077.3	1078.7	1080.2
170°	1085.7	1085.0	1084.3	1083.5	1083.1	1083.1	1083.1	1083.1	1083.1	1084.6	1086.1
172.5°	1089.5	1088.6	1087.7	1086.9	1086.5	1086.6	1086.8	1086.9	1087.0	1088.5	1090.0
175°	1094.5	1093.6	1092.7	1091.8	1091.4	1091.5	1091.8	1091.9	1092.1	1093.4	1094.6
177.5°	1095.9	1095.2	1094.5	1093.8	1093.5	1093.6	1093.8	1093.9	1094.1	1095.2	1096.3
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P332318-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1051.7	1051.7	1053.1	1058.3	1058.9	1063.4	1062.0
5°	1155.9	1164.0	1167.0	1179.8	1187.5	1190.9	1184.1
7.5°	1283.3	1306.2	1317.0	1330.4	1342.3	1345.9	1336.5
10°	1376.1	1400.0	1420.2	1432.5	1444.1	1451.7	1461.5
12.5°	1466.0	1495.3	1514.4	1531.9	1543.8	1553.5	1555.1
15°	1563.6	1607.9	1641.7	1666.4	1678.8	1685.2	1682.6
17.5°	1662.0	1703.2	1727.1	1752.4	1769.5	1770.4	1770.9
20°	1717.7	1757.8	1785.5	1804.3	1823.5	1822.7	1826.9
22.5°	1754.9	1786.5	1807.7	1821.4	1828.0	1824.7	1825.5
25°	1772.3	1781.7	1777.8	1756.1	1750.5	1730.5	1733.9
27.5°	1682.5	1638.1	1592.1	1533.1	1486.5	1449.3	1451.2
30°	1560.6	1482.1	1392.4	1317.3	1249.9	1231.0	1190.9
32.5°	1390.2	1272.4	1167.3	1097.3	1039.4	1023.8	988.8
35°	1101.3	986.8	878.9	814.0	788.4	752.5	752.1
37.5°	856.0	755.3	698.1	649.5	623.9	602.3	600.1
40°	720.1	641.6	598.4	563.5	538.3	522.0	518.2
42.5°	625.2	561.7	521.3	499.6	480.2	471.8	465.6
45°	510.5	467.8	439.7	420.0	411.1	404.6	401.2
47.5°	427.1	398.4	379.2	366.2	358.9	352.1	353.9
50°	381.6	358.2	344.1	331.7	326.1	321.4	321.9
52.5°	345.0	324.0	312.6	303.7	296.8	293.4	291.8
55°	292.9	279.6	268.1	261.6	257.8	253.2	251.8
57.5°	249.8	239.5	230.2	222.9	221.9	217.4	218.0
60°	221.1	212.5	204.9	201.1	198.0	194.2	195.5
62.5°	197.5	190.4	183.4	180.2	177.2	174.4	175.0
65°	161.8	154.9	150.7	149.0	147.7	146.4	145.1
67.5°	128.9	124.7	122.1	118.4	115.8	115.4	114.1
70°	108.4	102.9	98.2	93.5	92.2	91.8	92.2
72.5°	86.9	83.4	82.1	79.8	79.6	78.4	79.2
75°	65.3	64.0	63.2	61.5	61.5	61.5	61.5
77.5°	48.2	47.4	46.9	46.6	46.1	45.5	45.4
80°	37.6	37.1	36.3	36.3	35.9	36.3	35.9
82.5°	28.4	28.3	27.4	27.4	27.0	26.7	27.0
85°	14.5	14.1	14.9	14.1	14.5	13.7	14.5
87.5°	8.4	8.6	8.3	8.4	8.2	8.9	8.3
90°	21.7	22.4	23.0	23.3	23.7	24.1	24.4
92.5°	24.3	25.4	26.2	26.3	26.6	26.8	27.0
95°	29.0	30.3	30.9	30.9	30.9	30.9	30.9
97.5°	30.6	32.0	32.8	33.0	33.2	33.3	33.5
100°	31.2	32.6	33.4	33.7	33.8	34.0	34.2
102.5°	40.1	35.6	33.5	33.8	34.2	34.5	34.8
105°	82.2	50.2	34.3	34.7	35.1	35.5	35.8
107.5°	256.2	232.8	209.0	184.8	160.7	136.6	112.4
110°	349.1	343.2	327.3	301.3	275.5	249.6	223.8



TEST NUMBER: P332318-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	408.4	408.5	405.8	400.3	394.8	389.4	383.9
115°	472.5	474.3	475.6	476.3	477.0	477.8	478.5
117.5°	528.7	530.2	531.0	531.2	531.2	531.4	531.6
120°	565.8	567.3	568.0	568.0	568.0	568.0	568.0
122.5°	601.7	602.7	603.2	603.4	603.6	603.6	603.8
125°	652.1	652.5	652.8	653.2	653.5	654.0	654.3
127.5°	703.5	704.1	704.3	703.8	703.5	703.1	702.8
130°	734.6	735.3	735.5	735.2	734.7	734.4	734.0
132.5°	763.9	764.6	764.7	764.2	763.7	763.2	762.7
135°	808.1	808.6	808.6	808.1	807.6	807.0	806.5
137.5°	848.0	848.8	849.1	848.7	848.4	848.0	847.7
140°	872.9	873.7	873.8	873.4	873.1	872.8	872.4
142.5°	896.6	897.2	897.2	896.7	896.2	895.7	895.2
145°	929.6	930.0	930.2	930.2	930.2	930.2	930.2
147.5°	959.4	959.8	959.5	958.7	957.9	957.0	956.2
150°	977.6	978.0	977.9	977.4	976.8	976.2	975.8
152.5°	994.1	994.7	994.7	993.8	993.0	992.2	991.3
155°	1016.7	1017.6	1017.5	1016.4	1015.4	1014.2	1013.2
157.5°	1036.2	1037.4	1037.2	1035.8	1034.4	1033.0	1031.6
160°	1047.3	1048.4	1048.3	1047.1	1045.8	1044.6	1043.3
162.5°	1057.5	1058.7	1058.8	1057.7	1056.5	1055.5	1054.3
165°	1071.2	1072.7	1072.8	1071.5	1070.2	1068.9	1067.7
167.5°	1081.7	1083.0	1083.0	1081.7	1080.2	1078.7	1077.3
170°	1087.5	1088.9	1088.9	1087.5	1086.1	1084.6	1083.1
172.5°	1091.4	1092.8	1092.7	1091.2	1089.6	1088.0	1086.4
175°	1095.9	1097.1	1097.1	1095.6	1094.2	1092.7	1091.3
177.5°	1097.6	1098.7	1098.5	1097.1	1095.7	1094.2	1092.7
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4

(END OF REPORT)