

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332319-930

Luminaire Tested: **S123RDIP-S775D1025U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332319-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D1025U930-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5356.2 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332319-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332319-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53	46
1	98	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	71	82	76	71	67	64	60	57	53	50	48	42	41	39	35
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	38	36	34	30
4	75	65	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30	26
5	69	58	50	44	63	54	47	42	46	40	36	38	34	31	31	28	26	23
6	64	52	44	39	58	48	41	36	41	36	32	35	31	28	28	26	23	20
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21	18
8	55	43	35	30	50	40	33	29	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	37	30	26	31	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10733	10733	10733	10733
5°	12794	10778	9492	10778
10°	15974	10717	8576	10717
15°	18750	10608	7819	10608
20°	20927	10443	7178	10443
25°	20593	10271	6783	10271
30°	14802	10112	6377	10112
35°	9883	9905	6114	9905
40°	7281	9656	5841	9656
45°	6107	9220	5574	9220
50°	5390	8649	5203	8649
55°	4725	7994	4693	7994
60°	4209	7369	4299	7369
65°	3696	6696	4001	6696
70°	2902	6099	3654	6099
75°	2558	5327	3335	5327
80°	2225	4525	3279	4525
85°	1791	3631	3483	3631



TEST NUMBER: P332319-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.1	1.8
10°-20°	306.3	5.7
20°-30°	481.3	9.0
30°-40°	502.1	9.4
40°-50°	429.7	8.0
50°-60°	327.5	6.1
60°-70°	209.9	3.9
70°-80°	101.0	1.9
80°-90°	29.8	0.6
90°-100°	67.5	1.3
100°-110°	202.0	3.8
110°-120°	343.6	6.4
120°-130°	451.9	8.4
130°-140°	508.0	9.5
140°-150°	499.3	9.3
150°-160°	420.4	7.8
160°-170°	279.8	5.2
170°-180°	98.0	1.8
0°-30°	885.7	16.5
0°-40°	1387.8	25.9
0°-60°	2145.0	40.0
0°-90°	2485.7	46.4
90°-120°	613.1	11.4
90°-150°	2072.3	38.7
90°-180°	2870.0	53.6
0°-180°	5356.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	997	997	997	997	997	
5°	1184	998	878	998	1184	122
15°	1683	952	702	952	1683	477
25°	1734	865	571	865	1734	745
35°	752	754	465	754	752	493
45°	401	606	366	606	401	315
55°	252	426	250	426	252	228
65°	145	263	157	263	145	143
75°	62	128	80	128	62	66
85°	14	29	28	29	14	17
90°	24	1	24	1	24	12
95°	64	48	64	48	64	65
105°	194	183	194	183	194	206
115°	347	346	347	346	347	343
125°	500	506	500	506	500	448
135°	656	657	656	657	656	504
145°	797	797	797	797	797	497
155°	911	912	911	912	911	419
165°	990	994	990	994	990	279
175°	1030	1034	1030	1034	1030	98
180°	1036	1036	1036	1036	1036	



TEST NUMBER: P332319-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1062.0	1063.4	1058.9	1058.3	1053.1	1051.7	1051.7	1044.6	1040.2	1034.4	1030.9
5°	1184.1	1190.9	1187.5	1179.8	1167.0	1164.0	1155.9	1143.1	1128.6	1110.7	1102.1
7.5°	1336.5	1345.9	1342.3	1330.4	1317.0	1306.2	1283.3	1262.0	1232.2	1206.1	1183.7
10°	1461.5	1451.7	1444.1	1432.5	1420.2	1400.0	1376.1	1343.3	1305.3	1275.5	1242.1
12.5°	1555.1	1553.5	1543.8	1531.9	1514.4	1495.3	1466.0	1426.0	1381.8	1338.6	1300.6
15°	1682.6	1685.2	1678.8	1666.4	1641.7	1607.9	1563.6	1546.9	1483.8	1436.8	1389.8
17.5°	1770.9	1770.4	1769.5	1752.4	1727.1	1703.2	1662.0	1618.2	1561.0	1494.9	1431.6
20°	1826.9	1822.7	1823.5	1804.3	1785.5	1757.8	1717.7	1654.1	1607.1	1530.7	1465.3
22.5°	1825.5	1824.7	1828.0	1821.4	1807.7	1786.5	1754.9	1701.2	1641.3	1564.2	1490.6
25°	1733.9	1730.5	1750.5	1756.1	1777.8	1781.7	1772.3	1742.9	1686.0	1606.6	1515.7
27.5°	1451.2	1449.3	1486.5	1533.1	1592.1	1638.1	1682.5	1703.9	1686.0	1629.2	1538.1
30°	1190.9	1231.0	1249.9	1317.3	1392.4	1482.1	1560.6	1635.2	1653.6	1628.9	1554.1
32.5°	988.8	1023.8	1039.4	1097.3	1167.3	1272.4	1390.2	1495.9	1570.7	1589.6	1544.6
35°	752.1	752.5	788.4	814.0	878.9	986.8	1101.3	1243.0	1383.8	1490.5	1501.6
37.5°	600.1	602.3	623.9	649.5	698.1	755.3	856.0	973.8	1136.5	1300.3	1396.4
40°	518.2	522.0	538.3	563.5	598.4	641.6	720.1	831.1	966.8	1149.1	1298.0
42.5°	465.6	471.8	480.2	499.6	521.3	561.7	625.2	710.9	834.3	1006.7	1178.5
45°	401.2	404.6	411.1	420.0	439.7	467.8	510.5	568.1	670.6	809.3	981.3
47.5°	353.9	352.1	358.9	366.2	379.2	398.4	427.1	474.1	547.1	658.4	804.4
50°	321.9	321.4	326.1	331.7	344.1	358.2	381.6	417.0	475.1	567.3	700.9
52.5°	291.8	293.4	296.8	303.7	312.6	324.0	345.0	370.6	420.4	500.0	611.4
55°	251.8	253.2	257.8	261.6	268.1	279.6	292.9	314.1	348.3	403.8	495.5
57.5°	218.0	217.4	221.9	222.9	230.2	239.5	249.8	266.4	291.1	332.3	394.1
60°	195.5	194.2	198.0	201.1	204.9	212.5	221.1	237.3	257.0	287.2	340.2
62.5°	175.0	174.4	177.2	180.2	183.4	190.4	197.5	210.0	225.5	251.1	293.1
65°	145.1	146.4	147.7	149.0	150.7	154.9	161.8	170.3	181.0	198.9	229.2
67.5°	114.1	115.4	115.8	118.4	122.1	124.7	128.9	136.5	143.9	159.1	176.3
70°	92.2	91.8	92.2	93.5	98.2	102.9	108.4	114.0	118.6	129.3	143.8
72.5°	79.2	78.4	79.6	79.8	82.1	83.4	86.9	92.1	98.2	105.4	115.9
75°	61.5	61.5	61.5	61.5	63.2	64.0	65.3	66.6	68.7	72.2	79.8
77.5°	45.4	45.5	46.1	46.6	46.9	47.4	48.2	49.4	50.2	52.0	55.4
80°	35.9	36.3	35.9	36.3	36.3	37.1	37.6	38.8	39.3	41.4	42.7
82.5°	27.0	26.7	27.0	27.4	27.4	28.3	28.4	29.3	29.4	30.5	31.8
85°	14.5	13.7	14.5	14.1	14.9	14.1	14.5	15.3	15.3	15.8	17.5
87.5°	8.3	8.9	8.2	8.4	8.3	8.6	8.4	8.3	8.8	8.3	8.2
90°	24.4	24.1	23.7	23.3	23.0	22.4	21.7	21.0	20.2	19.6	17.2
92.5°	32.9	33.1	33.3	33.5	33.8	33.6	33.0	32.4	31.8	31.2	29.9
95°	63.5	63.5	63.5	63.5	63.5	63.1	62.4	61.6	61.0	60.3	58.8
97.5°	97.7	97.8	97.8	97.9	97.9	97.6	96.8	95.9	95.1	94.2	93.2
100°	123.7	123.4	122.9	122.6	122.3	121.8	121.2	120.7	120.2	119.6	118.7
102.5°	150.4	150.5	150.5	150.6	150.7	150.4	149.9	149.4	148.8	148.3	147.1
105°	193.7	193.3	193.0	192.6	192.2	192.1	192.1	192.1	192.1	192.1	190.5
107.5°	238.8	239.0	239.2	239.5	239.6	239.5	238.9	238.3	237.7	237.2	236.5
110°	269.4	269.8	270.1	270.4	270.8	270.7	269.9	269.2	268.5	267.7	267.4



TEST NUMBER: P332319-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	301.9	302.0	302.1	302.1	302.2	301.8	300.9	300.1	299.2	298.3	298.3
115°	346.7	346.9	347.1	347.2	347.4	347.4	347.2	347.1	346.9	346.7	347.1
117.5°	392.1	392.6	393.1	393.6	394.1	394.4	394.4	394.4	394.5	394.5	395.0
120°	424.0	424.4	424.8	425.1	425.4	425.7	425.9	426.1	426.2	426.5	427.4
122.5°	454.6	455.1	455.6	456.2	456.6	457.1	457.6	458.0	458.5	459.0	459.5
125°	500.5	501.2	502.0	502.7	503.4	504.1	504.8	505.6	506.3	507.0	507.4
127.5°	546.3	547.1	547.9	548.8	549.6	550.5	551.5	552.5	553.5	554.6	555.0
130°	576.2	577.5	578.7	580.0	581.2	582.3	582.9	583.7	584.4	585.1	585.7
132.5°	607.5	608.5	609.4	610.4	611.4	612.3	613.2	614.0	614.9	615.7	616.1
135°	656.0	656.3	656.6	657.0	657.4	657.9	658.7	659.4	660.1	660.8	661.0
137.5°	698.8	699.4	700.1	700.8	701.5	702.2	703.0	703.8	704.5	705.2	704.8
140°	726.8	728.1	729.3	730.6	731.8	732.5	732.7	732.9	733.1	733.3	733.1
142.5°	755.4	756.4	757.3	758.3	759.3	759.9	760.1	760.3	760.4	760.6	760.3
145°	796.7	797.4	798.2	798.9	799.6	800.1	800.3	800.5	800.6	800.8	800.3
147.5°	833.6	834.6	835.7	836.8	837.9	838.5	838.5	838.5	838.5	838.5	837.9
150°	857.0	858.0	859.2	860.2	861.3	861.9	861.9	861.9	861.9	861.9	861.5
152.5°	879.8	880.7	881.7	882.6	883.5	883.9	883.5	883.3	883.0	882.7	882.5
155°	910.7	911.9	913.2	914.5	915.7	916.0	915.3	914.6	913.9	913.1	913.0
157.5°	938.8	939.9	940.9	941.9	942.9	943.1	942.2	941.5	940.8	940.0	939.9
160°	957.1	957.8	958.5	959.3	959.9	959.9	959.0	958.1	957.2	956.3	956.3
162.5°	970.8	971.9	973.1	974.2	975.3	975.5	974.6	973.7	972.8	971.9	971.8
165°	990.4	991.7	993.0	994.3	995.5	995.6	994.5	993.4	992.3	991.2	991.2
167.5°	1007.2	1008.4	1009.4	1010.6	1011.7	1011.7	1010.6	1009.4	1008.4	1007.2	1007.1
170°	1015.7	1016.9	1018.2	1019.5	1020.8	1020.8	1019.5	1018.2	1016.9	1015.7	1015.7
172.5°	1022.1	1023.4	1024.7	1026.0	1027.3	1027.3	1026.2	1025.1	1023.9	1022.8	1022.8
175°	1029.5	1030.8	1032.0	1033.3	1034.5	1034.7	1033.6	1032.5	1031.4	1030.3	1030.3
177.5°	1033.4	1034.5	1035.4	1036.5	1037.5	1037.5	1036.7	1035.8	1034.9	1034.0	1034.0
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P332319-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1029.6	1028.5	1023.8	1018.3	1011.1	1006.3	1002.6	1000.5	994.4	986.8	981.8
5°	1093.2	1080.4	1066.7	1050.0	1034.7	1018.9	1009.1	997.5	983.5	967.7	956.6
7.5°	1161.3	1136.2	1109.1	1081.2	1053.6	1028.9	1007.1	988.3	965.9	943.2	927.4
10°	1213.6	1176.8	1138.8	1100.0	1064.5	1031.3	1005.7	980.5	953.6	927.6	907.9
12.5°	1261.0	1212.7	1168.9	1121.2	1075.9	1036.1	999.1	969.6	937.2	909.5	887.0
15°	1321.1	1271.6	1218.6	1146.1	1085.9	1035.5	990.8	951.9	912.6	878.5	856.7
17.5°	1377.3	1302.8	1231.7	1171.1	1092.9	1030.0	975.3	928.8	885.7	849.5	822.7
20°	1400.5	1328.4	1251.1	1173.9	1097.0	1026.5	963.0	911.7	866.9	826.0	801.2
22.5°	1414.5	1332.8	1251.4	1168.4	1086.8	1013.6	950.7	894.3	845.8	806.8	776.2
25°	1430.8	1333.5	1243.8	1161.9	1078.6	999.2	924.5	864.8	812.3	770.9	738.4
27.5°	1441.5	1327.1	1221.2	1130.0	1045.6	966.5	898.1	834.8	781.5	737.7	702.9
30°	1443.6	1321.9	1203.7	1105.1	1019.3	946.7	874.2	813.6	757.2	710.7	678.2
32.5°	1446.3	1309.3	1180.1	1075.4	987.6	915.7	849.9	792.1	734.3	688.5	655.4
35°	1435.1	1302.4	1144.4	1024.0	936.0	866.5	807.1	753.8	697.1	652.6	618.9
37.5°	1386.6	1274.6	1107.3	966.1	874.2	809.8	761.4	714.9	662.8	614.9	583.2
40°	1337.7	1247.2	1078.6	931.0	834.9	768.7	725.2	687.2	636.8	592.1	557.9
42.5°	1265.0	1210.1	1051.3	894.1	790.5	726.8	690.1	654.4	610.3	564.8	532.6
45°	1131.6	1138.8	995.4	835.4	729.0	665.0	630.5	605.7	566.5	528.9	496.0
47.5°	964.3	1032.1	929.8	772.7	664.2	604.1	574.0	552.4	525.9	489.0	459.0
50°	855.0	951.9	877.2	730.8	623.6	563.9	534.0	516.5	493.4	464.4	435.8
52.5°	754.2	858.3	813.7	684.0	579.6	525.0	495.8	481.4	463.0	435.7	409.9
55°	615.1	720.6	710.3	613.3	513.5	464.4	442.2	426.0	413.6	393.1	372.7
57.5°	497.6	597.5	602.8	534.8	455.3	406.8	387.7	375.4	367.4	351.9	333.0
60°	423.5	515.2	533.1	481.9	413.6	371.0	352.1	342.3	335.9	323.6	309.1
62.5°	362.0	440.1	460.4	423.5	373.7	333.7	319.0	309.6	305.2	294.5	281.7
65°	277.0	341.9	361.5	341.0	315.0	283.0	271.1	262.9	259.1	253.2	243.7
67.5°	208.3	255.6	277.1	262.7	253.3	233.1	225.4	221.1	217.7	213.6	205.8
70°	167.3	202.4	224.5	220.7	213.0	202.4	196.8	193.8	190.4	186.9	180.1
72.5°	134.5	158.7	179.4	181.4	175.1	172.9	168.1	166.8	164.8	160.7	156.9
75°	89.2	105.8	120.3	125.9	128.5	130.6	128.5	128.1	127.6	124.3	122.1
77.5°	58.5	67.4	76.6	86.0	90.1	92.9	93.7	95.2	94.1	92.3	91.2
80°	44.8	47.0	53.3	61.5	67.8	70.4	72.2	73.0	72.6	72.2	70.4
82.5°	32.5	34.3	37.3	43.0	48.4	52.7	53.7	53.6	54.5	54.7	53.3
85°	17.5	17.9	18.8	19.6	22.6	27.3	28.6	29.4	30.3	30.3	27.7
87.5°	8.4	7.6	7.8	7.4	8.1	8.1	9.8	11.1	11.8	10.8	11.2
90°	14.8	12.5	10.1	8.1	6.3	4.4	2.6	0.8	2.6	4.4	6.3
92.5°	28.5	27.2	25.9	24.6	23.4	22.2	21.0	19.7	21.0	22.2	23.4
95°	57.3	55.8	54.5	53.1	51.9	50.5	49.2	48.0	49.2	50.5	51.9
97.5°	92.1	91.1	90.0	89.0	88.1	87.2	86.3	85.3	86.3	87.2	88.1
100°	117.8	116.9	116.0	115.0	113.9	112.8	111.8	110.7	111.8	112.8	113.9
102.5°	145.9	144.7	143.5	142.6	141.9	141.3	140.6	140.0	140.6	141.3	141.9
105°	188.8	187.2	185.6	184.6	184.2	183.8	183.4	183.1	183.4	183.8	184.2
107.5°	235.9	235.2	234.6	234.2	233.9	233.7	233.5	233.3	233.5	233.7	233.9
110°	267.0	266.7	266.3	266.0	265.5	265.2	264.9	264.5	264.9	265.2	265.5



TEST NUMBER: P332319-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	298.2	298.2	298.1	297.9	297.7	297.5	297.3	297.0	297.3	297.5	297.7
115°	347.4	347.8	348.1	348.1	347.5	347.0	346.4	345.8	346.4	347.0	347.5
117.5°	395.5	396.0	396.4	396.5	396.2	395.7	395.4	395.0	395.4	395.7	396.2
120°	428.3	429.2	430.1	430.0	428.9	427.8	426.7	425.7	426.7	427.8	428.9
122.5°	459.9	460.4	460.9	460.7	459.9	459.1	458.4	457.5	458.4	459.1	459.9
125°	507.8	508.1	508.5	508.3	507.8	507.3	506.8	506.2	506.8	507.3	507.8
127.5°	555.4	555.7	556.1	555.8	554.6	553.4	552.3	551.1	552.3	553.4	554.6
130°	586.2	586.8	587.3	586.9	585.4	584.0	582.5	581.1	582.5	584.0	585.4
132.5°	616.5	616.9	617.3	616.9	615.4	613.9	612.5	611.1	612.5	613.9	615.4
135°	661.2	661.4	661.5	661.1	660.0	658.9	657.9	656.8	657.9	658.9	660.0
137.5°	704.3	703.8	703.4	702.7	701.8	700.9	700.0	699.1	700.0	700.9	701.8
140°	732.9	732.7	732.5	732.0	731.1	730.2	729.3	728.4	729.3	730.2	731.1
142.5°	759.9	759.6	759.3	758.7	757.8	756.9	755.9	755.0	755.9	756.9	757.8
145°	799.7	799.2	798.7	798.2	797.9	797.4	797.1	796.7	797.1	797.4	797.9
147.5°	837.4	836.9	836.4	835.8	835.2	834.5	833.9	833.2	833.9	834.5	835.2
150°	861.1	860.8	860.4	860.1	859.7	859.3	859.0	858.6	859.0	859.3	859.7
152.5°	882.2	882.1	881.8	881.4	880.9	880.4	880.0	879.5	880.0	880.4	880.9
155°	912.7	912.6	912.4	912.3	912.3	912.3	912.3	912.3	912.3	912.3	912.3
157.5°	939.7	939.6	939.4	939.5	939.6	939.9	940.1	940.3	940.1	939.9	939.6
160°	956.3	956.3	956.3	956.4	956.8	957.2	957.5	957.9	957.5	957.2	956.8
162.5°	971.6	971.4	971.3	971.5	972.0	972.5	973.0	973.5	973.0	972.5	972.0
165°	991.2	991.2	991.2	991.6	992.1	992.6	993.1	993.7	993.1	992.6	992.1
167.5°	1006.9	1006.8	1006.7	1006.9	1007.6	1008.4	1009.1	1009.8	1009.1	1008.4	1007.6
170°	1015.7	1015.7	1015.7	1016.0	1016.8	1017.5	1018.2	1019.0	1018.2	1017.5	1016.8
172.5°	1022.8	1022.8	1022.8	1023.2	1023.9	1024.7	1025.4	1026.1	1025.4	1024.7	1023.9
175°	1030.3	1030.3	1030.3	1030.7	1031.4	1032.1	1032.8	1033.6	1032.8	1032.1	1031.4
177.5°	1034.0	1034.0	1034.0	1034.4	1034.9	1035.5	1036.1	1036.7	1036.1	1035.5	1034.9
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P332319-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	980.1	975.6	972.6	965.7	961.2	956.5	951.7	954.8	954.5	954.1	954.1
5°	947.2	937.3	928.4	916.9	909.6	900.7	893.8	893.0	894.7	888.7	885.3
7.5°	914.6	901.2	888.4	875.7	862.3	851.5	844.7	841.6	837.2	833.6	829.7
10°	891.7	875.9	863.5	847.7	833.2	820.4	812.3	806.7	803.7	800.8	795.2
12.5°	868.1	852.6	836.9	819.0	805.2	790.4	784.3	778.0	772.3	769.0	761.4
15°	833.6	813.6	797.0	778.1	762.8	748.3	739.7	727.3	725.6	721.4	713.7
17.5°	799.1	777.3	754.3	740.5	723.1	708.0	695.0	690.8	678.6	674.0	667.3
20°	771.8	751.7	734.2	715.8	690.6	676.5	666.3	660.8	650.9	645.0	640.7
22.5°	748.2	727.8	707.5	686.2	665.4	649.5	642.0	633.4	628.1	619.7	615.1
25°	714.5	692.4	668.1	645.0	630.1	618.1	606.1	598.4	590.8	586.9	578.4
27.5°	675.5	652.2	629.5	612.0	593.7	581.9	571.0	564.2	555.0	548.5	543.8
30°	654.0	626.6	607.0	591.2	567.7	556.6	548.5	540.0	533.1	526.3	521.6
32.5°	629.0	604.1	585.5	565.9	547.9	535.8	525.3	517.8	511.9	505.5	500.8
35°	589.9	569.0	549.8	530.1	516.9	504.5	492.2	485.8	480.2	474.3	469.9
37.5°	554.6	535.0	516.7	498.1	481.8	471.7	461.7	456.8	449.3	445.3	440.9
40°	532.7	513.5	493.8	476.0	458.9	451.2	442.2	435.0	428.1	425.2	420.4
42.5°	508.8	489.6	473.0	453.7	439.8	429.3	421.0	413.1	408.0	403.7	401.0
45°	473.4	456.3	440.1	420.9	407.6	398.7	389.3	382.0	377.3	374.4	369.7
47.5°	439.0	421.9	405.4	388.7	375.9	365.7	356.3	351.2	345.0	341.3	338.2
50°	414.0	398.7	381.2	365.8	353.0	342.8	335.1	328.6	323.1	318.5	316.3
52.5°	391.2	374.8	359.6	345.4	331.8	320.2	313.2	306.5	302.3	296.9	294.4
55°	353.4	337.6	324.8	310.7	297.5	287.7	279.2	273.2	268.9	262.9	259.5
57.5°	318.0	303.9	288.5	276.3	262.7	254.4	247.3	239.2	234.0	229.3	226.0
60°	294.1	277.9	264.6	253.2	241.2	230.5	224.1	217.7	212.1	207.4	204.5
62.5°	269.2	255.0	242.5	229.9	219.0	209.7	202.3	196.9	192.0	189.0	186.1
65°	230.9	219.8	207.0	196.8	186.5	179.7	173.7	169.0	165.6	163.5	160.9
67.5°	195.8	185.0	173.8	163.7	156.9	151.7	147.8	143.7	142.0	139.3	137.6
70°	172.8	161.8	152.0	144.3	137.5	133.6	131.0	128.1	126.4	122.9	121.2
72.5°	148.0	139.9	132.8	126.5	121.1	117.6	114.3	110.6	107.9	104.1	102.5
75°	116.5	109.3	103.7	99.5	96.0	91.3	86.7	82.8	81.5	80.2	79.8
77.5°	86.3	81.7	77.7	74.1	69.9	66.4	65.4	64.6	64.2	63.6	63.6
80°	67.8	63.6	60.6	56.3	53.8	53.8	53.8	52.9	53.3	53.3	53.3
82.5°	50.5	46.6	44.9	43.4	42.9	43.2	43.2	43.4	43.1	43.8	43.5
85°	26.0	26.5	27.3	26.9	27.3	27.3	28.2	27.7	28.2	27.3	28.2
87.5°	11.2	12.6	13.5	14.3	15.1	15.2	15.7	15.8	16.3	16.5	16.6
90°	8.1	10.1	12.5	14.8	17.2	19.6	20.2	21.0	21.7	22.4	23.0
92.5°	24.6	25.9	27.2	28.5	29.9	31.2	31.8	32.4	33.0	33.6	33.8
95°	53.1	54.5	55.8	57.3	58.8	60.3	61.0	61.6	62.4	63.1	63.5
97.5°	89.0	90.0	91.1	92.1	93.2	94.2	95.1	95.9	96.8	97.6	97.9
100°	115.0	116.0	116.9	117.8	118.7	119.6	120.2	120.7	121.2	121.8	122.3
102.5°	142.6	143.5	144.7	145.9	147.1	148.3	148.8	149.4	149.9	150.4	150.7
105°	184.6	185.6	187.2	188.8	190.5	192.1	192.1	192.1	192.1	192.1	192.2
107.5°	234.2	234.6	235.2	235.9	236.5	237.2	237.7	238.3	238.9	239.5	239.6
110°	266.0	266.3	266.7	267.0	267.4	267.7	268.5	269.2	269.9	270.7	270.8



TEST NUMBER: P332319-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	297.9	298.1	298.2	298.2	298.3	298.3	299.2	300.1	300.9	301.8	302.2
115°	348.1	348.1	347.8	347.4	347.1	346.7	346.9	347.1	347.2	347.4	347.4
117.5°	396.5	396.4	396.0	395.5	395.0	394.5	394.5	394.4	394.4	394.4	394.1
120°	430.0	430.1	429.2	428.3	427.4	426.5	426.2	426.1	425.9	425.7	425.4
122.5°	460.7	460.9	460.4	459.9	459.5	459.0	458.5	458.0	457.6	457.1	456.6
125°	508.3	508.5	508.1	507.8	507.4	507.0	506.3	505.6	504.8	504.1	503.4
127.5°	555.8	556.1	555.7	555.4	555.0	554.6	553.5	552.5	551.5	550.5	549.6
130°	586.9	587.3	586.8	586.2	585.7	585.1	584.4	583.7	582.9	582.3	581.2
132.5°	616.9	617.3	616.9	616.5	616.1	615.7	614.9	614.0	613.2	612.3	611.4
135°	661.1	661.5	661.4	661.2	661.0	660.8	660.1	659.4	658.7	657.9	657.4
137.5°	702.7	703.4	703.8	704.3	704.8	705.2	704.5	703.8	703.0	702.2	701.5
140°	732.0	732.5	732.7	732.9	733.1	733.3	733.1	732.9	732.7	732.5	731.8
142.5°	758.7	759.3	759.6	759.9	760.3	760.6	760.4	760.3	760.1	759.9	759.3
145°	798.2	798.7	799.2	799.7	800.3	800.8	800.6	800.5	800.3	800.1	799.6
147.5°	835.8	836.4	836.9	837.4	837.9	838.5	838.5	838.5	838.5	838.5	837.9
150°	860.1	860.4	860.8	861.1	861.5	861.9	861.9	861.9	861.9	861.9	861.3
152.5°	881.4	881.8	882.1	882.2	882.5	882.7	883.0	883.3	883.5	883.9	883.5
155°	912.3	912.4	912.6	912.7	913.0	913.1	913.9	914.6	915.3	916.0	915.7
157.5°	939.5	939.4	939.6	939.7	939.9	940.0	940.8	941.5	942.2	943.1	942.9
160°	956.4	956.3	956.3	956.3	956.3	956.3	957.2	958.1	959.0	959.9	959.9
162.5°	971.5	971.3	971.4	971.6	971.8	971.9	972.8	973.7	974.6	975.5	975.3
165°	991.6	991.2	991.2	991.2	991.2	991.2	992.3	993.4	994.5	995.6	995.5
167.5°	1006.9	1006.7	1006.8	1006.9	1007.1	1007.2	1008.4	1009.4	1010.6	1011.7	1011.7
170°	1016.0	1015.7	1015.7	1015.7	1015.7	1015.7	1016.9	1018.2	1019.5	1020.8	1020.8
172.5°	1023.2	1022.8	1022.8	1022.8	1022.8	1022.8	1023.9	1025.1	1026.2	1027.3	1027.3
175°	1030.7	1030.3	1030.3	1030.3	1030.3	1030.3	1031.4	1032.5	1033.6	1034.7	1034.5
177.5°	1034.4	1034.0	1034.0	1034.0	1034.0	1034.0	1034.9	1035.8	1036.7	1037.5	1037.5
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P332319-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	950.0	949.7	950.0	948.6	950.0	949.7	950.0	954.1	954.1	954.5	954.8
5°	884.0	883.5	882.3	878.5	882.3	883.5	884.0	885.3	888.7	894.7	893.0
7.5°	826.4	825.8	822.1	822.1	822.1	825.8	826.4	829.7	833.6	837.2	841.6
10°	792.2	792.6	787.6	784.6	787.6	792.6	792.2	795.2	800.8	803.7	806.7
12.5°	759.1	757.2	753.0	749.7	753.0	757.2	759.1	761.4	769.0	772.3	778.0
15°	715.4	711.1	700.9	701.7	700.9	711.1	715.4	713.7	721.4	725.6	727.3
17.5°	663.9	660.8	660.6	654.6	660.6	660.8	663.9	667.3	674.0	678.6	690.8
20°	633.9	631.8	632.6	626.6	632.6	631.8	633.9	640.7	645.0	650.9	660.8
22.5°	610.3	608.2	604.6	602.8	604.6	608.2	610.3	615.1	619.7	628.1	633.4
25°	575.8	572.4	569.0	571.1	569.0	572.4	575.8	578.4	586.9	590.8	598.4
27.5°	541.4	538.7	535.3	534.9	535.3	538.7	541.4	543.8	548.5	555.0	564.2
30°	519.5	516.9	515.2	513.1	515.2	516.9	519.5	521.6	526.3	533.1	540.0
32.5°	497.3	496.8	493.7	493.3	493.7	496.8	497.3	500.8	505.5	511.9	517.8
35°	468.2	465.7	464.8	465.3	464.8	465.7	468.2	469.9	474.3	480.2	485.8
37.5°	440.7	437.2	435.7	434.2	435.7	437.2	440.7	440.9	445.3	449.3	456.8
40°	420.9	417.4	416.6	415.7	416.6	417.4	420.9	420.4	425.2	428.1	435.0
42.5°	398.7	397.3	396.8	395.3	396.8	397.3	398.7	401.0	403.7	408.0	413.1
45°	368.4	367.9	365.4	366.2	365.4	367.9	368.4	369.7	374.4	377.3	382.0
47.5°	336.5	334.6	332.8	333.9	332.8	334.6	336.5	338.2	341.3	345.0	351.2
50°	314.6	313.7	309.9	310.7	309.9	313.7	314.6	316.3	318.5	323.1	328.6
52.5°	292.8	289.5	288.0	287.6	288.0	289.5	292.8	294.4	296.9	302.3	306.5
55°	256.6	252.7	250.9	250.1	250.9	252.7	256.6	259.5	262.9	268.9	273.2
57.5°	221.0	220.0	218.7	219.6	218.7	220.0	221.0	226.0	229.3	234.0	239.2
60°	200.2	200.2	200.2	199.7	200.2	200.2	200.2	204.5	207.4	212.1	217.7
62.5°	184.2	183.1	182.8	183.4	182.8	183.1	184.2	186.1	189.0	192.0	196.9
65°	159.6	159.2	157.5	157.1	157.5	159.2	159.6	160.9	163.5	165.6	169.0
67.5°	136.5	134.9	134.4	133.9	134.4	134.9	136.5	137.6	139.3	142.0	143.7
70°	119.1	118.2	115.7	116.1	115.7	118.2	119.1	121.2	122.9	126.4	128.1
72.5°	100.3	99.5	99.0	98.3	99.0	99.5	100.3	102.5	104.1	107.9	110.6
75°	79.4	79.0	78.5	80.2	78.5	79.0	79.4	79.8	80.2	81.5	82.8
77.5°	63.6	63.6	63.8	63.2	63.8	63.6	63.6	63.6	63.6	64.2	64.6
80°	53.3	53.3	52.9	52.9	52.9	53.3	53.3	53.3	53.3	53.3	52.9
82.5°	42.8	43.1	43.4	42.7	43.4	43.1	42.8	43.5	43.8	43.1	43.4
85°	28.2	27.7	28.6	28.2	28.6	27.7	28.2	28.2	27.3	28.2	27.7
87.5°	17.3	16.7	16.8	17.2	16.8	16.7	17.3	16.6	16.5	16.3	15.8
90°	23.3	23.7	24.1	24.4	24.1	23.7	23.3	23.0	22.4	21.7	21.0
92.5°	33.5	33.3	33.1	32.9	33.1	33.3	33.5	33.8	33.6	33.0	32.4
95°	63.5	63.5	63.5	63.5	63.5	63.5	63.5	63.5	63.1	62.4	61.6
97.5°	97.9	97.8	97.8	97.7	97.8	97.8	97.9	97.9	97.6	96.8	95.9
100°	122.6	122.9	123.4	123.7	123.4	122.9	122.6	122.3	121.8	121.2	120.7
102.5°	150.6	150.5	150.5	150.4	150.5	150.5	150.6	150.7	150.4	149.9	149.4
105°	192.6	193.0	193.3	193.7	193.3	193.0	192.6	192.2	192.1	192.1	192.1
107.5°	239.5	239.2	239.0	238.8	239.0	239.2	239.5	239.6	239.5	238.9	238.3
110°	270.4	270.1	269.8	269.4	269.8	270.1	270.4	270.8	270.7	269.9	269.2



TEST NUMBER: P332319-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	302.1	302.1	302.0	301.9	302.0	302.1	302.1	302.2	301.8	300.9	300.1
115°	347.2	347.1	346.9	346.7	346.9	347.1	347.2	347.4	347.4	347.2	347.1
117.5°	393.6	393.1	392.6	392.1	392.6	393.1	393.6	394.1	394.4	394.4	394.4
120°	425.1	424.8	424.4	424.0	424.4	424.8	425.1	425.4	425.7	425.9	426.1
122.5°	456.2	455.6	455.1	454.6	455.1	455.6	456.2	456.6	457.1	457.6	458.0
125°	502.7	502.0	501.2	500.5	501.2	502.0	502.7	503.4	504.1	504.8	505.6
127.5°	548.8	547.9	547.1	546.3	547.1	547.9	548.8	549.6	550.5	551.5	552.5
130°	580.0	578.7	577.5	576.2	577.5	578.7	580.0	581.2	582.3	582.9	583.7
132.5°	610.4	609.4	608.5	607.5	608.5	609.4	610.4	611.4	612.3	613.2	614.0
135°	657.0	656.6	656.3	656.0	656.3	656.6	657.0	657.4	657.9	658.7	659.4
137.5°	700.8	700.1	699.4	698.8	699.4	700.1	700.8	701.5	702.2	703.0	703.8
140°	730.6	729.3	728.1	726.8	728.1	729.3	730.6	731.8	732.5	732.7	732.9
142.5°	758.3	757.3	756.4	755.4	756.4	757.3	758.3	759.3	759.9	760.1	760.3
145°	798.9	798.2	797.4	796.7	797.4	798.2	798.9	799.6	800.1	800.3	800.5
147.5°	836.8	835.7	834.6	833.6	834.6	835.7	836.8	837.9	838.5	838.5	838.5
150°	860.2	859.2	858.0	857.0	858.0	859.2	860.2	861.3	861.9	861.9	861.9
152.5°	882.6	881.7	880.7	879.8	880.7	881.7	882.6	883.5	883.9	883.5	883.3
155°	914.5	913.2	911.9	910.7	911.9	913.2	914.5	915.7	916.0	915.3	914.6
157.5°	941.9	940.9	939.9	938.8	939.9	940.9	941.9	942.9	943.1	942.2	941.5
160°	959.3	958.5	957.8	957.1	957.8	958.5	959.3	959.9	959.9	959.0	958.1
162.5°	974.2	973.1	971.9	970.8	971.9	973.1	974.2	975.3	975.5	974.6	973.7
165°	994.3	993.0	991.7	990.4	991.7	993.0	994.3	995.5	995.6	994.5	993.4
167.5°	1010.6	1009.4	1008.4	1007.2	1008.4	1009.4	1010.6	1011.7	1011.7	1010.6	1009.4
170°	1019.5	1018.2	1016.9	1015.7	1016.9	1018.2	1019.5	1020.8	1020.8	1019.5	1018.2
172.5°	1026.0	1024.7	1023.4	1022.1	1023.4	1024.7	1026.0	1027.3	1027.3	1026.2	1025.1
175°	1033.3	1032.0	1030.8	1029.5	1030.8	1032.0	1033.3	1034.5	1034.7	1033.6	1032.5
177.5°	1036.5	1035.4	1034.5	1033.4	1034.5	1035.4	1036.5	1037.5	1037.5	1036.7	1035.8
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P332319-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	951.7	956.5	961.2	965.7	972.6	975.6	980.1	981.8	986.8	994.4	1000.5
5°	893.8	900.7	909.6	916.9	928.4	937.3	947.2	956.6	967.7	983.5	997.5
7.5°	844.7	851.5	862.3	875.7	888.4	901.2	914.6	927.4	943.2	965.9	988.3
10°	812.3	820.4	833.2	847.7	863.5	875.9	891.7	907.9	927.6	953.6	980.5
12.5°	784.3	790.4	805.2	819.0	836.9	852.6	868.1	887.0	909.5	937.2	969.6
15°	739.7	748.3	762.8	778.1	797.0	813.6	833.6	856.7	878.5	912.6	951.9
17.5°	695.0	708.0	723.1	740.5	754.3	777.3	799.1	822.7	849.5	885.7	928.8
20°	666.3	676.5	690.6	715.8	734.2	751.7	771.8	801.2	826.0	866.9	911.7
22.5°	642.0	649.5	665.4	686.2	707.5	727.8	748.2	776.2	806.8	845.8	894.3
25°	606.1	618.1	630.1	645.0	668.1	692.4	714.5	738.4	770.9	812.3	864.8
27.5°	571.0	581.9	593.7	612.0	629.5	652.2	675.5	702.9	737.7	781.5	834.8
30°	548.5	556.6	567.7	591.2	607.0	626.6	654.0	678.2	710.7	757.2	813.6
32.5°	525.3	535.8	547.9	565.9	585.5	604.1	629.0	655.4	688.5	734.3	792.1
35°	492.2	504.5	516.9	530.1	549.8	569.0	589.9	618.9	652.6	697.1	753.8
37.5°	461.7	471.7	481.8	498.1	516.7	535.0	554.6	583.2	614.9	662.8	714.9
40°	442.2	451.2	458.9	476.0	493.8	513.5	532.7	557.9	592.1	636.8	687.2
42.5°	421.0	429.3	439.8	453.7	473.0	489.6	508.8	532.6	564.8	610.3	654.4
45°	389.3	398.7	407.6	420.9	440.1	456.3	473.4	496.0	528.9	566.5	605.7
47.5°	356.3	365.7	375.9	388.7	405.4	421.9	439.0	459.0	489.0	525.9	552.4
50°	335.1	342.8	353.0	365.8	381.2	398.7	414.0	435.8	464.4	493.4	516.5
52.5°	313.2	320.2	331.8	345.4	359.6	374.8	391.2	409.9	435.7	463.0	481.4
55°	279.2	287.7	297.5	310.7	324.8	337.6	353.4	372.7	393.1	413.6	426.0
57.5°	247.3	254.4	262.7	276.3	288.5	303.9	318.0	333.0	351.9	367.4	375.4
60°	224.1	230.5	241.2	253.2	264.6	277.9	294.1	309.1	323.6	335.9	342.3
62.5°	202.3	209.7	219.0	229.9	242.5	255.0	269.2	281.7	294.5	305.2	309.6
65°	173.7	179.7	186.5	196.8	207.0	219.8	230.9	243.7	253.2	259.1	262.9
67.5°	147.8	151.7	156.9	163.7	173.8	185.0	195.8	205.8	213.6	217.7	221.1
70°	131.0	133.6	137.5	144.3	152.0	161.8	172.8	180.1	186.9	190.4	193.8
72.5°	114.3	117.6	121.1	126.5	132.8	139.9	148.0	156.9	160.7	164.8	166.8
75°	86.7	91.3	96.0	99.5	103.7	109.3	116.5	122.1	124.3	127.6	128.1
77.5°	65.4	66.4	69.9	74.1	77.7	81.7	86.3	91.2	92.3	94.1	95.2
80°	53.8	53.8	53.8	56.3	60.6	63.6	67.8	70.4	72.2	72.6	73.0
82.5°	43.2	43.2	42.9	43.4	44.9	46.6	50.5	53.3	54.7	54.5	53.6
85°	28.2	27.3	27.3	26.9	27.3	26.5	26.0	27.7	30.3	30.3	29.4
87.5°	15.7	15.2	15.1	14.3	13.5	12.6	11.2	11.2	10.8	11.8	11.1
90°	20.2	19.6	17.2	14.8	12.5	10.1	8.1	6.3	4.4	2.6	0.8
92.5°	31.8	31.2	29.9	28.5	27.2	25.9	24.6	23.4	22.2	21.0	19.7
95°	61.0	60.3	58.8	57.3	55.8	54.5	53.1	51.9	50.5	49.2	48.0
97.5°	95.1	94.2	93.2	92.1	91.1	90.0	89.0	88.1	87.2	86.3	85.3
100°	120.2	119.6	118.7	117.8	116.9	116.0	115.0	113.9	112.8	111.8	110.7
102.5°	148.8	148.3	147.1	145.9	144.7	143.5	142.6	141.9	141.3	140.6	140.0
105°	192.1	192.1	190.5	188.8	187.2	185.6	184.6	184.2	183.8	183.4	183.1
107.5°	237.7	237.2	236.5	235.9	235.2	234.6	234.2	233.9	233.7	233.5	233.3
110°	268.5	267.7	267.4	267.0	266.7	266.3	266.0	265.5	265.2	264.9	264.5



TEST NUMBER: P332319-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	299.2	298.3	298.3	298.2	298.2	298.1	297.9	297.7	297.5	297.3	297.0
115°	346.9	346.7	347.1	347.4	347.8	348.1	348.1	347.5	347.0	346.4	345.8
117.5°	394.5	394.5	395.0	395.5	396.0	396.4	396.5	396.2	395.7	395.4	395.0
120°	426.2	426.5	427.4	428.3	429.2	430.1	430.0	428.9	427.8	426.7	425.7
122.5°	458.5	459.0	459.5	459.9	460.4	460.9	460.7	459.9	459.1	458.4	457.5
125°	506.3	507.0	507.4	507.8	508.1	508.5	508.3	507.8	507.3	506.8	506.2
127.5°	553.5	554.6	555.0	555.4	555.7	556.1	555.8	554.6	553.4	552.3	551.1
130°	584.4	585.1	585.7	586.2	586.8	587.3	586.9	585.4	584.0	582.5	581.1
132.5°	614.9	615.7	616.1	616.5	616.9	617.3	616.9	615.4	613.9	612.5	611.1
135°	660.1	660.8	661.0	661.2	661.4	661.5	661.1	660.0	658.9	657.9	656.8
137.5°	704.5	705.2	704.8	704.3	703.8	703.4	702.7	701.8	700.9	700.0	699.1
140°	733.1	733.3	733.1	732.9	732.7	732.5	732.0	731.1	730.2	729.3	728.4
142.5°	760.4	760.6	760.3	759.9	759.6	759.3	758.7	757.8	756.9	755.9	755.0
145°	800.6	800.8	800.3	799.7	799.2	798.7	798.2	797.9	797.4	797.1	796.7
147.5°	838.5	838.5	837.9	837.4	836.9	836.4	835.8	835.2	834.5	833.9	833.2
150°	861.9	861.9	861.5	861.1	860.8	860.4	860.1	859.7	859.3	859.0	858.6
152.5°	883.0	882.7	882.5	882.2	882.1	881.8	881.4	880.9	880.4	880.0	879.5
155°	913.9	913.1	913.0	912.7	912.6	912.4	912.3	912.3	912.3	912.3	912.3
157.5°	940.8	940.0	939.9	939.7	939.6	939.4	939.5	939.6	939.9	940.1	940.3
160°	957.2	956.3	956.3	956.3	956.3	956.3	956.4	956.8	957.2	957.5	957.9
162.5°	972.8	971.9	971.8	971.6	971.4	971.3	971.5	972.0	972.5	973.0	973.5
165°	992.3	991.2	991.2	991.2	991.2	991.2	991.6	992.1	992.6	993.1	993.7
167.5°	1008.4	1007.2	1007.1	1006.9	1006.8	1006.7	1006.9	1007.6	1008.4	1009.1	1009.8
170°	1016.9	1015.7	1015.7	1015.7	1015.7	1015.7	1016.0	1016.8	1017.5	1018.2	1019.0
172.5°	1023.9	1022.8	1022.8	1022.8	1022.8	1022.8	1023.2	1023.9	1024.7	1025.4	1026.1
175°	1031.4	1030.3	1030.3	1030.3	1030.3	1030.3	1030.7	1031.4	1032.1	1032.8	1033.6
177.5°	1034.9	1034.0	1034.0	1034.0	1034.0	1034.0	1034.4	1034.9	1035.5	1036.1	1036.7
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P332319-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1002.6	1006.3	1011.1	1018.3	1023.8	1028.5	1029.6	1030.9	1034.4	1040.2	1044.6
5°	1009.1	1018.9	1034.7	1050.0	1066.7	1080.4	1093.2	1102.1	1110.7	1128.6	1143.1
7.5°	1007.1	1028.9	1053.6	1081.2	1109.1	1136.2	1161.3	1183.7	1206.1	1232.2	1262.0
10°	1005.7	1031.3	1064.5	1100.0	1138.8	1176.8	1213.6	1242.1	1275.5	1305.3	1343.3
12.5°	999.1	1036.1	1075.9	1121.2	1168.9	1212.7	1261.0	1300.6	1338.6	1381.8	1426.0
15°	990.8	1035.5	1085.9	1146.1	1218.6	1271.6	1321.1	1389.8	1436.8	1483.8	1546.9
17.5°	975.3	1030.0	1092.9	1171.1	1231.7	1302.8	1377.3	1431.6	1494.9	1561.0	1618.2
20°	963.0	1026.5	1097.0	1173.9	1251.1	1328.4	1400.5	1465.3	1530.7	1607.1	1654.1
22.5°	950.7	1013.6	1086.8	1168.4	1251.4	1332.8	1414.5	1490.6	1564.2	1641.3	1701.2
25°	924.5	999.2	1078.6	1161.9	1243.8	1333.5	1430.8	1515.7	1606.6	1686.0	1742.9
27.5°	898.1	966.5	1045.6	1130.0	1221.2	1327.1	1441.5	1538.1	1629.2	1686.0	1703.9
30°	874.2	946.7	1019.3	1105.1	1203.7	1321.9	1443.6	1554.1	1628.9	1653.6	1635.2
32.5°	849.9	915.7	987.6	1075.4	1180.1	1309.3	1446.3	1544.6	1589.6	1570.7	1495.9
35°	807.1	866.5	936.0	1024.0	1144.4	1302.4	1435.1	1501.6	1490.5	1383.8	1243.0
37.5°	761.4	809.8	874.2	966.1	1107.3	1274.6	1386.6	1396.4	1300.3	1136.5	973.8
40°	725.2	768.7	834.9	931.0	1078.6	1247.2	1337.7	1298.0	1149.1	966.8	831.1
42.5°	690.1	726.8	790.5	894.1	1051.3	1210.1	1265.0	1178.5	1006.7	834.3	710.9
45°	630.5	665.0	729.0	835.4	995.4	1138.8	1131.6	981.3	809.3	670.6	568.1
47.5°	574.0	604.1	664.2	772.7	929.8	1032.1	964.3	804.4	658.4	547.1	474.1
50°	534.0	563.9	623.6	730.8	877.2	951.9	855.0	700.9	567.3	475.1	417.0
52.5°	495.8	525.0	579.6	684.0	813.7	858.3	754.2	611.4	500.0	420.4	370.6
55°	442.2	464.4	513.5	613.3	710.3	720.6	615.1	495.5	403.8	348.3	314.1
57.5°	387.7	406.8	455.3	534.8	602.8	597.5	497.6	394.1	332.3	291.1	266.4
60°	352.1	371.0	413.6	481.9	533.1	515.2	423.5	340.2	287.2	257.0	237.3
62.5°	319.0	333.7	373.7	423.5	460.4	440.1	362.0	293.1	251.1	225.5	210.0
65°	271.1	283.0	315.0	341.0	361.5	341.9	277.0	229.2	198.9	181.0	170.3
67.5°	225.4	233.1	253.3	262.7	277.1	255.6	208.3	176.3	159.1	143.9	136.5
70°	196.8	202.4	213.0	220.7	224.5	202.4	167.3	143.8	129.3	118.6	114.0
72.5°	168.1	172.9	175.1	181.4	179.4	158.7	134.5	115.9	105.4	98.2	92.1
75°	128.5	130.6	128.5	125.9	120.3	105.8	89.2	79.8	72.2	68.7	66.6
77.5°	93.7	92.9	90.1	86.0	76.6	67.4	58.5	55.4	52.0	50.2	49.4
80°	72.2	70.4	67.8	61.5	53.3	47.0	44.8	42.7	41.4	39.3	38.8
82.5°	53.7	52.7	48.4	43.0	37.3	34.3	32.5	31.8	30.5	29.4	29.3
85°	28.6	27.3	22.6	19.6	18.8	17.9	17.5	17.5	15.8	15.3	15.3
87.5°	9.8	8.1	8.1	7.4	7.8	7.6	8.4	8.2	8.3	8.8	8.3
90°	2.6	4.4	6.3	8.1	10.1	12.5	14.8	17.2	19.6	20.2	21.0
92.5°	21.0	22.2	23.4	24.6	25.9	27.2	28.5	29.9	31.2	31.8	32.4
95°	49.2	50.5	51.9	53.1	54.5	55.8	57.3	58.8	60.3	61.0	61.6
97.5°	86.3	87.2	88.1	89.0	90.0	91.1	92.1	93.2	94.2	95.1	95.9
100°	111.8	112.8	113.9	115.0	116.0	116.9	117.8	118.7	119.6	120.2	120.7
102.5°	140.6	141.3	141.9	142.6	143.5	144.7	145.9	147.1	148.3	148.8	149.4
105°	183.4	183.8	184.2	184.6	185.6	187.2	188.8	190.5	192.1	192.1	192.1
107.5°	233.5	233.7	233.9	234.2	234.6	235.2	235.9	236.5	237.2	237.7	238.3
110°	264.9	265.2	265.5	266.0	266.3	266.7	267.0	267.4	267.7	268.5	269.2



TEST NUMBER: P332319-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	297.3	297.5	297.7	297.9	298.1	298.2	298.2	298.3	298.3	299.2	300.1
115°	346.4	347.0	347.5	348.1	348.1	347.8	347.4	347.1	346.7	346.9	347.1
117.5°	395.4	395.7	396.2	396.5	396.4	396.0	395.5	395.0	394.5	394.5	394.4
120°	426.7	427.8	428.9	430.0	430.1	429.2	428.3	427.4	426.5	426.2	426.1
122.5°	458.4	459.1	459.9	460.7	460.9	460.4	459.9	459.5	459.0	458.5	458.0
125°	506.8	507.3	507.8	508.3	508.5	508.1	507.8	507.4	507.0	506.3	505.6
127.5°	552.3	553.4	554.6	555.8	556.1	555.7	555.4	555.0	554.6	553.5	552.5
130°	582.5	584.0	585.4	586.9	587.3	586.8	586.2	585.7	585.1	584.4	583.7
132.5°	612.5	613.9	615.4	616.9	617.3	616.9	616.5	616.1	615.7	614.9	614.0
135°	657.9	658.9	660.0	661.1	661.5	661.4	661.2	661.0	660.8	660.1	659.4
137.5°	700.0	700.9	701.8	702.7	703.4	703.8	704.3	704.8	705.2	704.5	703.8
140°	729.3	730.2	731.1	732.0	732.5	732.7	732.9	733.1	733.3	733.1	732.9
142.5°	755.9	756.9	757.8	758.7	759.3	759.6	759.9	760.3	760.6	760.4	760.3
145°	797.1	797.4	797.9	798.2	798.7	799.2	799.7	800.3	800.8	800.6	800.5
147.5°	833.9	834.5	835.2	835.8	836.4	836.9	837.4	837.9	838.5	838.5	838.5
150°	859.0	859.3	859.7	860.1	860.4	860.8	861.1	861.5	861.9	861.9	861.9
152.5°	880.0	880.4	880.9	881.4	881.8	882.1	882.2	882.5	882.7	883.0	883.3
155°	912.3	912.3	912.3	912.3	912.4	912.6	912.7	913.0	913.1	913.9	914.6
157.5°	940.1	939.9	939.6	939.5	939.4	939.6	939.7	939.9	940.0	940.8	941.5
160°	957.5	957.2	956.8	956.4	956.3	956.3	956.3	956.3	956.3	957.2	958.1
162.5°	973.0	972.5	972.0	971.5	971.3	971.4	971.6	971.8	971.9	972.8	973.7
165°	993.1	992.6	992.1	991.6	991.2	991.2	991.2	991.2	991.2	992.3	993.4
167.5°	1009.1	1008.4	1007.6	1006.9	1006.7	1006.8	1006.9	1007.1	1007.2	1008.4	1009.4
170°	1018.2	1017.5	1016.8	1016.0	1015.7	1015.7	1015.7	1015.7	1015.7	1016.9	1018.2
172.5°	1025.4	1024.7	1023.9	1023.2	1022.8	1022.8	1022.8	1022.8	1022.8	1023.9	1025.1
175°	1032.8	1032.1	1031.4	1030.7	1030.3	1030.3	1030.3	1030.3	1030.3	1031.4	1032.5
177.5°	1036.1	1035.5	1034.9	1034.4	1034.0	1034.0	1034.0	1034.0	1034.0	1034.9	1035.8
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P332319-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1051.7	1051.7	1053.1	1058.3	1058.9	1063.4	1062.0
5°	1155.9	1164.0	1167.0	1179.8	1187.5	1190.9	1184.1
7.5°	1283.3	1306.2	1317.0	1330.4	1342.3	1345.9	1336.5
10°	1376.1	1400.0	1420.2	1432.5	1444.1	1451.7	1461.5
12.5°	1466.0	1495.3	1514.4	1531.9	1543.8	1553.5	1555.1
15°	1563.6	1607.9	1641.7	1666.4	1678.8	1685.2	1682.6
17.5°	1662.0	1703.2	1727.1	1752.4	1769.5	1770.4	1770.9
20°	1717.7	1757.8	1785.5	1804.3	1823.5	1822.7	1826.9
22.5°	1754.9	1786.5	1807.7	1821.4	1828.0	1824.7	1825.5
25°	1772.3	1781.7	1777.8	1756.1	1750.5	1730.5	1733.9
27.5°	1682.5	1638.1	1592.1	1533.1	1486.5	1449.3	1451.2
30°	1560.6	1482.1	1392.4	1317.3	1249.9	1231.0	1190.9
32.5°	1390.2	1272.4	1167.3	1097.3	1039.4	1023.8	988.8
35°	1101.3	986.8	878.9	814.0	788.4	752.5	752.1
37.5°	856.0	755.3	698.1	649.5	623.9	602.3	600.1
40°	720.1	641.6	598.4	563.5	538.3	522.0	518.2
42.5°	625.2	561.7	521.3	499.6	480.2	471.8	465.6
45°	510.5	467.8	439.7	420.0	411.1	404.6	401.2
47.5°	427.1	398.4	379.2	366.2	358.9	352.1	353.9
50°	381.6	358.2	344.1	331.7	326.1	321.4	321.9
52.5°	345.0	324.0	312.6	303.7	296.8	293.4	291.8
55°	292.9	279.6	268.1	261.6	257.8	253.2	251.8
57.5°	249.8	239.5	230.2	222.9	221.9	217.4	218.0
60°	221.1	212.5	204.9	201.1	198.0	194.2	195.5
62.5°	197.5	190.4	183.4	180.2	177.2	174.4	175.0
65°	161.8	154.9	150.7	149.0	147.7	146.4	145.1
67.5°	128.9	124.7	122.1	118.4	115.8	115.4	114.1
70°	108.4	102.9	98.2	93.5	92.2	91.8	92.2
72.5°	86.9	83.4	82.1	79.8	79.6	78.4	79.2
75°	65.3	64.0	63.2	61.5	61.5	61.5	61.5
77.5°	48.2	47.4	46.9	46.6	46.1	45.5	45.4
80°	37.6	37.1	36.3	36.3	35.9	36.3	35.9
82.5°	28.4	28.3	27.4	27.4	27.0	26.7	27.0
85°	14.5	14.1	14.9	14.1	14.5	13.7	14.5
87.5°	8.4	8.6	8.3	8.4	8.2	8.9	8.3
90°	21.7	22.4	23.0	23.3	23.7	24.1	24.4
92.5°	33.0	33.6	33.8	33.5	33.3	33.1	32.9
95°	62.4	63.1	63.5	63.5	63.5	63.5	63.5
97.5°	96.8	97.6	97.9	97.9	97.8	97.8	97.7
100°	121.2	121.8	122.3	122.6	122.9	123.4	123.7
102.5°	149.9	150.4	150.7	150.6	150.5	150.5	150.4
105°	192.1	192.1	192.2	192.6	193.0	193.3	193.7
107.5°	238.9	239.5	239.6	239.5	239.2	239.0	238.8
110°	269.9	270.7	270.8	270.4	270.1	269.8	269.4



TEST NUMBER: P332319-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	300.9	301.8	302.2	302.1	302.1	302.0	301.9
115°	347.2	347.4	347.4	347.2	347.1	346.9	346.7
117.5°	394.4	394.4	394.1	393.6	393.1	392.6	392.1
120°	425.9	425.7	425.4	425.1	424.8	424.4	424.0
122.5°	457.6	457.1	456.6	456.2	455.6	455.1	454.6
125°	504.8	504.1	503.4	502.7	502.0	501.2	500.5
127.5°	551.5	550.5	549.6	548.8	547.9	547.1	546.3
130°	582.9	582.3	581.2	580.0	578.7	577.5	576.2
132.5°	613.2	612.3	611.4	610.4	609.4	608.5	607.5
135°	658.7	657.9	657.4	657.0	656.6	656.3	656.0
137.5°	703.0	702.2	701.5	700.8	700.1	699.4	698.8
140°	732.7	732.5	731.8	730.6	729.3	728.1	726.8
142.5°	760.1	759.9	759.3	758.3	757.3	756.4	755.4
145°	800.3	800.1	799.6	798.9	798.2	797.4	796.7
147.5°	838.5	838.5	837.9	836.8	835.7	834.6	833.6
150°	861.9	861.9	861.3	860.2	859.2	858.0	857.0
152.5°	883.5	883.9	883.5	882.6	881.7	880.7	879.8
155°	915.3	916.0	915.7	914.5	913.2	911.9	910.7
157.5°	942.2	943.1	942.9	941.9	940.9	939.9	938.8
160°	959.0	959.9	959.9	959.3	958.5	957.8	957.1
162.5°	974.6	975.5	975.3	974.2	973.1	971.9	970.8
165°	994.5	995.6	995.5	994.3	993.0	991.7	990.4
167.5°	1010.6	1011.7	1011.7	1010.6	1009.4	1008.4	1007.2
170°	1019.5	1020.8	1020.8	1019.5	1018.2	1016.9	1015.7
172.5°	1026.2	1027.3	1027.3	1026.0	1024.7	1023.4	1022.1
175°	1033.6	1034.7	1034.5	1033.3	1032.0	1030.8	1029.5
177.5°	1036.7	1037.5	1037.5	1036.5	1035.4	1034.5	1033.4
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0

(END OF REPORT)