

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332326-930

Luminaire Tested: **S123RDIP-S775D1195U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332326-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D1195U930-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6006.9 lumens
Efficiency: N/A
Efficacy: 105.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332326-930

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332326-930

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41
1	96	92	89	85	88	84	81	78	70	67	65	56	54	53	43	42	42	36
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36	31
3	81	72	65	59	73	66	60	55	55	50	47	44	41	39	35	33	31	27
4	74	64	56	50	67	59	52	47	49	44	40	40	36	34	31	29	27	23
5	68	57	49	43	62	52	46	41	44	39	35	36	32	29	28	26	24	20
6	63	51	43	38	57	47	40	35	40	34	31	33	29	26	26	23	21	18
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19	16
8	54	42	35	29	49	39	32	28	33	28	24	27	23	21	22	19	17	15
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	20	18	16	13
10	47	35	28	24	43	33	26	22	28	23	19	23	19	17	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10733	10733	10733	10733
5°	12794	10778	9492	10778
10°	15974	10717	8576	10717
15°	18750	10608	7819	10608
20°	20927	10443	7178	10443
25°	20593	10271	6783	10271
30°	14802	10112	6377	10112
35°	9883	9905	6114	9905
40°	7281	9656	5841	9656
45°	6107	9220	5574	9220
50°	5390	8649	5203	8649
55°	4725	7994	4693	7994
60°	4209	7369	4299	7369
65°	3696	6696	4001	6696
70°	2902	6099	3654	6099
75°	2558	5327	3335	5327
80°	2225	4525	3279	4525
85°	1791	3631	3483	3631



TEST NUMBER: P332326-930

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.1	1.6
10°-20°	306.3	5.1
20°-30°	481.3	8.0
30°-40°	502.1	8.4
40°-50°	429.7	7.2
50°-60°	327.5	5.5
60°-70°	209.9	3.5
70°-80°	101.0	1.7
80°-90°	30.3	0.5
90°-100°	260.4	4.3
100°-110°	737.4	12.3
110°-120°	725.4	12.1
120°-130°	578.6	9.6
130°-140°	456.2	7.6
140°-150°	340.5	5.7
150°-160°	237.3	4.0
160°-170°	139.4	2.3
170°-180°	45.4	0.8
0°-30°	885.7	14.7
0°-40°	1387.8	23.1
0°-60°	2145.0	35.7
0°-90°	2486.3	41.4
90°-120°	1723.2	28.7
90°-150°	3098.5	51.6
90°-180°	3521.0	58.6
0°-180°	6006.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	997	997	997	997	997	
5°	1184	998	878	998	1184	122
15°	1683	952	702	952	1683	477
25°	1734	865	571	865	1734	745
35°	752	754	465	754	752	493
45°	401	606	366	606	401	315
55°	252	426	250	426	252	228
65°	145	263	157	263	145	143
75°	62	128	80	128	62	66
85°	14	29	28	29	14	17
90°	28	2	28	2	28	15
95°	110	32	110	32	110	198
105°	1205	110	1205	110	1205	1189
115°	1465	194	1465	194	1465	1424
125°	1156	270	1156	270	1156	1047
135°	937	316	937	316	937	727
145°	732	361	732	361	732	466
155°	607	410	607	410	607	283
165°	530	448	530	448	530	151
175°	476	467	476	467	476	46
180°	468	468	468	468	468	



TEST NUMBER: P332326-930

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1062.0	1063.4	1058.9	1058.3	1053.1	1051.7	1051.7	1044.6	1040.2	1034.4	1030.9
5°	1184.1	1190.9	1187.5	1179.8	1167.0	1164.0	1155.9	1143.1	1128.6	1110.7	1102.1
7.5°	1336.5	1345.9	1342.3	1330.4	1317.0	1306.2	1283.3	1262.0	1232.2	1206.1	1183.7
10°	1461.5	1451.7	1444.1	1432.5	1420.2	1400.0	1376.1	1343.3	1305.3	1275.5	1242.1
12.5°	1555.1	1553.5	1543.8	1531.9	1514.4	1495.3	1466.0	1426.0	1381.8	1338.6	1300.6
15°	1682.6	1685.2	1678.8	1666.4	1641.7	1607.9	1563.6	1546.9	1483.8	1436.8	1389.8
17.5°	1770.9	1770.4	1769.5	1752.4	1727.1	1703.2	1662.0	1618.2	1561.0	1494.9	1431.6
20°	1826.9	1822.7	1823.5	1804.3	1785.5	1757.8	1717.7	1654.1	1607.1	1530.7	1465.3
22.5°	1825.5	1824.7	1828.0	1821.4	1807.7	1786.5	1754.9	1701.2	1641.3	1564.2	1490.6
25°	1733.9	1730.5	1750.5	1756.1	1777.8	1781.7	1772.3	1742.9	1686.0	1606.6	1515.7
27.5°	1451.2	1449.3	1486.5	1533.1	1592.1	1638.1	1682.5	1703.9	1686.0	1629.2	1538.1
30°	1190.9	1231.0	1249.9	1317.3	1392.4	1482.1	1560.6	1635.2	1653.6	1628.9	1554.1
32.5°	988.8	1023.8	1039.4	1097.3	1167.3	1272.4	1390.2	1495.9	1570.7	1589.6	1544.6
35°	752.1	752.5	788.4	814.0	878.9	986.8	1101.3	1243.0	1383.8	1490.5	1501.6
37.5°	600.1	602.3	623.9	649.5	698.1	755.3	856.0	973.8	1136.5	1300.3	1396.4
40°	518.2	522.0	538.3	563.5	598.4	641.6	720.1	831.1	966.8	1149.1	1298.0
42.5°	465.6	471.8	480.2	499.6	521.3	561.7	625.2	710.9	834.3	1006.7	1178.5
45°	401.2	404.6	411.1	420.0	439.7	467.8	510.5	568.1	670.6	809.3	981.3
47.5°	353.9	352.1	358.9	366.2	379.2	398.4	427.1	474.1	547.1	658.4	804.4
50°	321.9	321.4	326.1	331.7	344.1	358.2	381.6	417.0	475.1	567.3	700.9
52.5°	291.8	293.4	296.8	303.7	312.6	324.0	345.0	370.6	420.4	500.0	611.4
55°	251.8	253.2	257.8	261.6	268.1	279.6	292.9	314.1	348.3	403.8	495.5
57.5°	218.0	217.4	221.9	222.9	230.2	239.5	249.8	266.4	291.1	332.3	394.1
60°	195.5	194.2	198.0	201.1	204.9	212.5	221.1	237.3	257.0	287.2	340.2
62.5°	175.0	174.4	177.2	180.2	183.4	190.4	197.5	210.0	225.5	251.1	293.1
65°	145.1	146.4	147.7	149.0	150.7	154.9	161.8	170.3	181.0	198.9	229.2
67.5°	114.1	115.4	115.8	118.4	122.1	124.7	128.9	136.5	143.9	159.1	176.3
70°	92.2	91.8	92.2	93.5	98.2	102.9	108.4	114.0	118.6	129.3	143.8
72.5°	79.2	78.4	79.6	79.8	82.1	83.4	86.9	92.1	98.2	105.4	115.9
75°	61.5	61.5	61.5	61.5	63.2	64.0	65.3	66.6	68.7	72.2	79.8
77.5°	45.4	45.5	46.1	46.6	46.9	47.4	48.2	49.4	50.2	52.0	55.4
80°	35.9	36.3	35.9	36.3	36.3	37.1	37.6	38.8	39.3	41.4	42.7
82.5°	27.0	26.7	27.0	27.4	27.4	28.3	28.4	29.3	29.4	30.5	31.8
85°	14.5	13.7	14.5	14.1	14.9	14.1	14.5	15.3	15.3	15.8	17.5
87.5°	8.9	9.8	8.9	9.0	9.2	9.2	9.0	8.8	9.3	9.2	9.0
90°	27.5	28.5	27.5	26.5	27.5	25.6	24.6	23.6	22.7	23.6	20.9
92.5°	45.7	47.4	46.4	49.2	51.0	55.8	63.3	79.7	109.9	145.7	160.3
95°	109.9	113.7	120.3	128.8	146.8	180.9	231.1	341.0	455.6	561.7	500.2
97.5°	299.1	307.3	332.9	375.5	445.4	558.7	680.9	850.0	931.3	870.5	637.3
100°	593.9	593.0	629.9	699.0	794.8	929.3	1040.1	1116.8	1083.7	897.1	606.3
102.5°	871.3	893.1	924.0	978.7	1053.1	1138.4	1203.0	1205.5	1091.2	847.8	560.8
105°	1204.9	1209.7	1240.0	1275.9	1319.6	1344.2	1326.2	1231.4	1033.5	761.6	504.9
107.5°	1397.0	1405.7	1415.9	1428.1	1427.3	1393.6	1310.6	1156.7	932.3	685.4	469.3
110°	1475.9	1477.7	1479.6	1472.0	1445.5	1379.2	1259.9	1085.6	868.6	642.2	455.6



TEST NUMBER: P332326-930

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1491.8	1491.3	1484.2	1460.7	1412.2	1326.9	1193.2	1015.0	813.3	613.4	448.1
115°	1465.4	1460.7	1441.7	1400.0	1329.0	1225.7	1086.5	921.7	746.4	582.5	445.2
117.5°	1381.7	1375.2	1347.9	1300.2	1226.1	1121.4	996.3	854.0	706.0	564.4	446.9
120°	1312.0	1306.3	1283.5	1230.4	1155.7	1060.0	946.3	818.4	684.9	556.0	450.0
122.5°	1246.8	1239.6	1214.6	1166.9	1100.3	1011.5	906.1	790.4	667.4	550.7	455.3
125°	1155.7	1149.0	1125.4	1083.7	1023.0	947.2	856.3	753.1	645.1	543.7	463.2
127.5°	1080.6	1074.6	1053.1	1017.6	963.5	894.5	812.5	720.5	625.4	540.3	472.3
130°	1038.2	1030.6	1010.7	976.6	926.4	862.0	785.3	700.0	614.7	538.0	478.3
132.5°	996.5	991.2	973.5	939.5	892.3	831.0	759.5	681.1	605.0	537.3	482.9
135°	936.9	930.2	913.1	884.8	838.3	784.3	722.8	655.5	592.1	536.1	489.8
137.5°	873.8	869.4	855.0	826.2	787.2	740.4	687.3	632.2	580.8	534.0	494.3
140°	829.8	830.7	815.6	789.0	753.1	712.3	666.8	618.6	574.1	533.3	497.3
142.5°	788.9	789.8	776.2	752.7	722.0	686.6	647.2	605.7	567.9	531.8	499.6
145°	732.2	730.3	722.8	702.9	679.1	651.8	621.4	590.1	559.9	529.5	501.1
147.5°	685.6	684.9	677.7	664.2	646.2	626.7	602.3	577.5	551.9	525.9	501.1
150°	658.4	658.4	652.6	642.2	628.0	610.0	590.1	568.3	546.6	522.9	501.1
152.5°	635.6	635.6	632.2	622.6	611.4	596.4	578.8	560.0	540.5	519.1	498.8
155°	607.2	606.3	604.4	596.8	588.2	576.9	562.6	547.5	531.4	512.5	496.4
157.5°	581.2	581.4	579.9	574.2	566.8	557.9	547.0	534.3	521.1	506.6	493.2
160°	564.6	565.5	565.5	559.9	553.2	546.6	537.1	526.7	514.4	502.1	491.6
162.5°	549.4	550.3	550.3	545.4	541.0	535.2	526.5	517.6	507.5	497.5	488.6
165°	529.5	529.5	530.4	526.7	522.9	518.1	511.5	505.8	498.2	490.6	484.0
167.5°	510.5	510.5	511.5	508.8	507.2	503.8	499.9	495.6	489.3	483.9	479.5
170°	499.2	499.2	500.2	498.2	497.3	495.4	491.6	488.8	484.0	479.3	476.5
172.5°	488.6	489.3	491.1	489.2	488.9	487.9	484.8	482.7	478.7	475.5	474.2
175°	476.5	477.4	478.3	477.4	477.4	477.4	475.5	474.6	472.7	470.8	470.8
177.5°	469.4	469.4	471.0	470.2	471.0	471.0	470.2	469.4	468.7	468.0	468.7
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0



TEST NUMBER: P332326-930

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1029.6	1028.5	1023.8	1018.3	1011.1	1006.3	1002.6	1000.5	994.4	986.8	981.8
5°	1093.2	1080.4	1066.7	1050.0	1034.7	1018.9	1009.1	997.5	983.5	967.7	956.6
7.5°	1161.3	1136.2	1109.1	1081.2	1053.6	1028.9	1007.1	988.3	965.9	943.2	927.4
10°	1213.6	1176.8	1138.8	1100.0	1064.5	1031.3	1005.7	980.5	953.6	927.6	907.9
12.5°	1261.0	1212.7	1168.9	1121.2	1075.9	1036.1	999.1	969.6	937.2	909.5	887.0
15°	1321.1	1271.6	1218.6	1146.1	1085.9	1035.5	990.8	951.9	912.6	878.5	856.7
17.5°	1377.3	1302.8	1231.7	1171.1	1092.9	1030.0	975.3	928.8	885.7	849.5	822.7
20°	1400.5	1328.4	1251.1	1173.9	1097.0	1026.5	963.0	911.7	866.9	826.0	801.2
22.5°	1414.5	1332.8	1251.4	1168.4	1086.8	1013.6	950.7	894.3	845.8	806.8	776.2
25°	1430.8	1333.5	1243.8	1161.9	1078.6	999.2	924.5	864.8	812.3	770.9	738.4
27.5°	1441.5	1327.1	1221.2	1130.0	1045.6	966.5	898.1	834.8	781.5	737.7	702.9
30°	1443.6	1321.9	1203.7	1105.1	1019.3	946.7	874.2	813.6	757.2	710.7	678.2
32.5°	1446.3	1309.3	1180.1	1075.4	987.6	915.7	849.9	792.1	734.3	688.5	655.4
35°	1435.1	1302.4	1144.4	1024.0	936.0	866.5	807.1	753.8	697.1	652.6	618.9
37.5°	1386.6	1274.6	1107.3	966.1	874.2	809.8	761.4	714.9	662.8	614.9	583.2
40°	1337.7	1247.2	1078.6	931.0	834.9	768.7	725.2	687.2	636.8	592.1	557.9
42.5°	1265.0	1210.1	1051.3	894.1	790.5	726.8	690.1	654.4	610.3	564.8	532.6
45°	1131.6	1138.8	995.4	835.4	729.0	665.0	630.5	605.7	566.5	528.9	496.0
47.5°	964.3	1032.1	929.8	772.7	664.2	604.1	574.0	552.4	525.9	489.0	459.0
50°	855.0	951.9	877.2	730.8	623.6	563.9	534.0	516.5	493.4	464.4	435.8
52.5°	754.2	858.3	813.7	684.0	579.6	525.0	495.8	481.4	463.0	435.7	409.9
55°	615.1	720.6	710.3	613.3	513.5	464.4	442.2	426.0	413.6	393.1	372.7
57.5°	497.6	597.5	602.8	534.8	455.3	406.8	387.7	375.4	367.4	351.9	333.0
60°	423.5	515.2	533.1	481.9	413.6	371.0	352.1	342.3	335.9	323.6	309.1
62.5°	362.0	440.1	460.4	423.5	373.7	333.7	319.0	309.6	305.2	294.5	281.7
65°	277.0	341.9	361.5	341.0	315.0	283.0	271.1	262.9	259.1	253.2	243.7
67.5°	208.3	255.6	277.1	262.7	253.3	233.1	225.4	221.1	217.7	213.6	205.8
70°	167.3	202.4	224.5	220.7	213.0	202.4	196.8	193.8	190.4	186.9	180.1
72.5°	134.5	158.7	179.4	181.4	175.1	172.9	168.1	166.8	164.8	160.7	156.9
75°	89.2	105.8	120.3	125.9	128.5	130.6	128.5	128.1	127.6	124.3	122.1
77.5°	58.5	67.4	76.6	86.0	90.1	92.9	93.7	95.2	94.1	92.3	91.2
80°	44.8	47.0	53.3	61.5	67.8	70.4	72.2	73.0	72.6	72.2	70.4
82.5°	32.5	34.3	37.3	43.0	48.4	52.7	53.7	53.6	54.5	54.7	53.3
85°	17.5	17.9	18.8	19.6	22.6	27.3	28.6	29.4	30.3	30.3	27.7
87.5°	9.0	8.2	8.2	7.9	8.6	8.3	9.9	11.3	12.1	11.0	11.6
90°	18.0	15.2	12.3	10.4	8.6	5.7	3.8	1.9	3.8	5.7	8.6
92.5°	120.3	79.6	54.8	40.8	32.8	25.4	17.4	11.7	17.4	25.4	32.8
95°	344.8	203.7	123.1	86.2	61.6	45.5	35.1	32.2	35.1	45.5	61.6
97.5°	378.3	219.2	142.3	102.3	78.0	64.0	55.8	55.0	55.8	64.0	78.0
100°	357.1	217.0	150.6	113.7	90.9	77.7	71.0	70.1	71.0	77.7	90.9
102.5°	338.9	220.0	160.5	126.5	106.1	93.6	87.7	86.0	87.7	93.6	106.1
105°	325.9	228.3	177.2	147.7	129.8	118.4	112.8	109.9	112.8	118.4	129.8
107.5°	324.9	243.9	198.9	171.6	154.7	143.6	138.1	135.3	138.1	143.6	154.7
110°	328.7	256.7	214.1	187.5	171.5	161.0	156.3	153.4	156.3	161.0	171.5



TEST NUMBER: P332326-930

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	336.3	269.6	230.0	204.2	188.1	177.7	173.0	170.2	173.0	177.7	188.1
115°	348.6	290.8	254.8	229.3	213.1	203.7	198.0	194.2	198.0	203.7	213.1
117.5°	364.8	313.3	277.8	254.0	236.0	227.3	222.6	218.3	222.6	227.3	236.0
120°	377.0	327.8	293.7	269.9	252.0	242.5	237.7	234.9	237.7	242.5	252.0
122.5°	388.4	342.9	309.6	284.4	267.1	256.9	252.2	249.3	252.2	256.9	267.1
125°	406.3	364.7	331.5	306.0	288.0	277.5	271.9	269.9	271.9	277.5	288.0
127.5°	421.2	383.6	351.6	326.0	306.1	295.5	288.5	285.7	288.5	295.5	306.1
130°	431.0	395.0	363.7	338.2	318.3	306.9	298.4	295.5	298.4	306.9	318.3
132.5°	440.1	404.9	374.4	349.5	329.6	316.0	306.7	303.1	306.7	316.0	329.6
135°	451.8	419.6	390.3	364.7	344.8	330.6	320.2	316.4	320.2	330.6	344.8
137.5°	460.6	429.8	401.6	378.0	358.2	343.1	332.9	328.9	332.9	343.1	358.2
140°	465.1	436.7	409.2	385.6	366.6	351.4	341.9	337.2	341.9	351.4	366.6
142.5°	469.6	442.0	415.3	393.1	374.1	360.5	350.3	346.3	350.3	360.5	374.1
145°	474.6	449.0	424.4	402.6	386.5	372.3	363.7	360.9	363.7	372.3	386.5
147.5°	477.6	454.7	432.1	413.6	398.0	385.7	377.4	375.7	377.4	385.7	398.0
150°	478.3	458.4	436.7	419.6	406.3	394.0	386.5	385.6	386.5	394.0	406.3
152.5°	479.9	460.7	442.0	425.7	413.9	403.2	395.6	395.4	395.6	403.2	413.9
155°	480.3	465.1	449.0	435.7	425.3	415.9	410.2	410.2	410.2	415.9	425.3
157.5°	481.2	467.6	454.7	444.4	435.5	427.2	422.7	421.9	422.7	427.2	435.5
160°	481.2	469.9	458.4	449.0	442.4	434.8	431.0	431.0	431.0	434.8	442.4
162.5°	480.5	470.6	460.7	452.8	446.9	440.8	437.8	437.8	437.8	440.8	446.9
165°	478.3	471.7	464.1	457.5	453.7	449.0	447.1	448.1	447.1	449.0	453.7
167.5°	476.9	471.6	466.0	461.9	459.3	455.6	454.7	455.8	454.7	455.6	459.3
170°	474.6	470.8	466.0	464.1	462.3	459.4	458.4	460.4	458.4	459.4	462.3
172.5°	473.9	470.8	466.8	465.7	464.6	462.4	462.3	463.4	462.3	462.4	464.6
175°	471.7	469.9	468.0	467.0	467.0	465.1	466.0	467.0	466.0	465.1	467.0
177.5°	470.2	468.7	468.0	468.0	468.0	467.2	468.0	468.7	468.0	467.2	468.0
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0



TEST NUMBER: P332326-930

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	980.1	975.6	972.6	965.7	961.2	956.5	951.7	954.8	954.5	954.1	954.1
5°	947.2	937.3	928.4	916.9	909.6	900.7	893.8	893.0	894.7	888.7	885.3
7.5°	914.6	901.2	888.4	875.7	862.3	851.5	844.7	841.6	837.2	833.6	829.7
10°	891.7	875.9	863.5	847.7	833.2	820.4	812.3	806.7	803.7	800.8	795.2
12.5°	868.1	852.6	836.9	819.0	805.2	790.4	784.3	778.0	772.3	769.0	761.4
15°	833.6	813.6	797.0	778.1	762.8	748.3	739.7	727.3	725.6	721.4	713.7
17.5°	799.1	777.3	754.3	740.5	723.1	708.0	695.0	690.8	678.6	674.0	667.3
20°	771.8	751.7	734.2	715.8	690.6	676.5	666.3	660.8	650.9	645.0	640.7
22.5°	748.2	727.8	707.5	686.2	665.4	649.5	642.0	633.4	628.1	619.7	615.1
25°	714.5	692.4	668.1	645.0	630.1	618.1	606.1	598.4	590.8	586.9	578.4
27.5°	675.5	652.2	629.5	612.0	593.7	581.9	571.0	564.2	555.0	548.5	543.8
30°	654.0	626.6	607.0	591.2	567.7	556.6	548.5	540.0	533.1	526.3	521.6
32.5°	629.0	604.1	585.5	565.9	547.9	535.8	525.3	517.8	511.9	505.5	500.8
35°	589.9	569.0	549.8	530.1	516.9	504.5	492.2	485.8	480.2	474.3	469.9
37.5°	554.6	535.0	516.7	498.1	481.8	471.7	461.7	456.8	449.3	445.3	440.9
40°	532.7	513.5	493.8	476.0	458.9	451.2	442.2	435.0	428.1	425.2	420.4
42.5°	508.8	489.6	473.0	453.7	439.8	429.3	421.0	413.1	408.0	403.7	401.0
45°	473.4	456.3	440.1	420.9	407.6	398.7	389.3	382.0	377.3	374.4	369.7
47.5°	439.0	421.9	405.4	388.7	375.9	365.7	356.3	351.2	345.0	341.3	338.2
50°	414.0	398.7	381.2	365.8	353.0	342.8	335.1	328.6	323.1	318.5	316.3
52.5°	391.2	374.8	359.6	345.4	331.8	320.2	313.2	306.5	302.3	296.9	294.4
55°	353.4	337.6	324.8	310.7	297.5	287.7	279.2	273.2	268.9	262.9	259.5
57.5°	318.0	303.9	288.5	276.3	262.7	254.4	247.3	239.2	234.0	229.3	226.0
60°	294.1	277.9	264.6	253.2	241.2	230.5	224.1	217.7	212.1	207.4	204.5
62.5°	269.2	255.0	242.5	229.9	219.0	209.7	202.3	196.9	192.0	189.0	186.1
65°	230.9	219.8	207.0	196.8	186.5	179.7	173.7	169.0	165.6	163.5	160.9
67.5°	195.8	185.0	173.8	163.7	156.9	151.7	147.8	143.7	142.0	139.3	137.6
70°	172.8	161.8	152.0	144.3	137.5	133.6	131.0	128.1	126.4	122.9	121.2
72.5°	148.0	139.9	132.8	126.5	121.1	117.6	114.3	110.6	107.9	104.1	102.5
75°	116.5	109.3	103.7	99.5	96.0	91.3	86.7	82.8	81.5	80.2	79.8
77.5°	86.3	81.7	77.7	74.1	69.9	66.4	65.4	64.6	64.2	63.6	63.6
80°	67.8	63.6	60.6	56.3	53.8	53.8	53.8	52.9	53.3	53.3	53.3
82.5°	50.5	46.6	44.9	43.4	42.9	43.2	43.2	43.4	43.1	43.8	43.5
85°	26.0	26.5	27.3	26.9	27.3	27.3	28.2	27.7	28.2	27.3	28.2
87.5°	11.7	13.0	13.9	14.8	15.8	16.0	16.1	16.3	16.9	17.0	17.4
90°	10.4	12.3	15.2	18.0	20.9	23.6	22.7	23.6	24.6	25.6	27.5
92.5°	40.8	54.8	79.6	120.3	160.3	145.7	109.9	79.7	63.3	55.8	51.0
95°	86.2	123.1	203.7	344.8	500.2	561.7	455.6	341.0	231.1	180.9	146.8
97.5°	102.3	142.3	219.2	378.3	637.3	870.5	931.3	850.0	680.9	558.7	445.4
100°	113.7	150.6	217.0	357.1	606.3	897.1	1083.7	1116.8	1040.1	929.3	794.8
102.5°	126.5	160.5	220.0	338.9	560.8	847.8	1091.2	1205.5	1203.0	1138.4	1053.1
105°	147.7	177.2	228.3	325.9	504.9	761.6	1033.5	1231.4	1326.2	1344.2	1319.6
107.5°	171.6	198.9	243.9	324.9	469.3	685.4	932.3	1156.7	1310.6	1393.6	1427.3
110°	187.5	214.1	256.7	328.7	455.6	642.2	868.6	1085.6	1259.9	1379.2	1445.5



TEST NUMBER: P332326-930

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	204.2	230.0	269.6	336.3	448.1	613.4	813.3	1015.0	1193.2	1326.9	1412.2
115°	229.3	254.8	290.8	348.6	445.2	582.5	746.4	921.7	1086.5	1225.7	1329.0
117.5°	254.0	277.8	313.3	364.8	446.9	564.4	706.0	854.0	996.3	1121.4	1226.1
120°	269.9	293.7	327.8	377.0	450.0	556.0	684.9	818.4	946.3	1060.0	1155.7
122.5°	284.4	309.6	342.9	388.4	455.3	550.7	667.4	790.4	906.1	1011.5	1100.3
125°	306.0	331.5	364.7	406.3	463.2	543.7	645.1	753.1	856.3	947.2	1023.0
127.5°	326.0	351.6	383.6	421.2	472.3	540.3	625.4	720.5	812.5	894.5	963.5
130°	338.2	363.7	395.0	431.0	478.3	538.0	614.7	700.0	785.3	862.0	926.4
132.5°	349.5	374.4	404.9	440.1	482.9	537.3	605.0	681.1	759.5	831.0	892.3
135°	364.7	390.3	419.6	451.8	489.8	536.1	592.1	655.5	722.8	784.3	838.3
137.5°	378.0	401.6	429.8	460.6	494.3	534.0	580.8	632.2	687.3	740.4	787.2
140°	385.6	409.2	436.7	465.1	497.3	533.3	574.1	618.6	666.8	712.3	753.1
142.5°	393.1	415.3	442.0	469.6	499.6	531.8	567.9	605.7	647.2	686.6	722.0
145°	402.6	424.4	449.0	474.6	501.1	529.5	559.9	590.1	621.4	651.8	679.1
147.5°	413.6	432.1	454.7	477.6	501.1	525.9	551.9	577.5	602.3	626.7	646.2
150°	419.6	436.7	458.4	478.3	501.1	522.9	546.6	568.3	590.1	610.0	628.0
152.5°	425.7	442.0	460.7	479.9	498.8	519.1	540.5	560.0	578.8	596.4	611.4
155°	435.7	449.0	465.1	480.3	496.4	512.5	531.4	547.5	562.6	576.9	588.2
157.5°	444.4	454.7	467.6	481.2	493.2	506.6	521.1	534.3	547.0	557.9	566.8
160°	449.0	458.4	469.9	481.2	491.6	502.1	514.4	526.7	537.1	546.6	553.2
162.5°	452.8	460.7	470.6	480.5	488.6	497.5	507.5	517.6	526.5	535.2	541.0
165°	457.5	464.1	471.7	478.3	484.0	490.6	498.2	505.8	511.5	518.1	522.9
167.5°	461.9	466.0	471.6	476.9	479.5	483.9	489.3	495.6	499.9	503.8	507.2
170°	464.1	466.0	470.8	474.6	476.5	479.3	484.0	488.8	491.6	495.4	497.3
172.5°	465.7	466.8	470.8	473.9	474.2	475.5	478.7	482.7	484.8	487.9	488.9
175°	467.0	468.0	469.9	471.7	470.8	470.8	472.7	474.6	475.5	477.4	477.4
177.5°	468.0	468.0	468.7	470.2	468.7	468.0	468.7	469.4	470.2	471.0	471.0
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0



TEST NUMBER: P332326-930

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	950.0	949.7	950.0	948.6	950.0	949.7	950.0	954.1	954.1	954.5	954.8
5°	884.0	883.5	882.3	878.5	882.3	883.5	884.0	885.3	888.7	894.7	893.0
7.5°	826.4	825.8	822.1	822.1	822.1	825.8	826.4	829.7	833.6	837.2	841.6
10°	792.2	792.6	787.6	784.6	787.6	792.6	792.2	795.2	800.8	803.7	806.7
12.5°	759.1	757.2	753.0	749.7	753.0	757.2	759.1	761.4	769.0	772.3	778.0
15°	715.4	711.1	700.9	701.7	700.9	711.1	715.4	713.7	721.4	725.6	727.3
17.5°	663.9	660.8	660.6	654.6	660.6	660.8	663.9	667.3	674.0	678.6	690.8
20°	633.9	631.8	632.6	626.6	632.6	631.8	633.9	640.7	645.0	650.9	660.8
22.5°	610.3	608.2	604.6	602.8	604.6	608.2	610.3	615.1	619.7	628.1	633.4
25°	575.8	572.4	569.0	571.1	569.0	572.4	575.8	578.4	586.9	590.8	598.4
27.5°	541.4	538.7	535.3	534.9	535.3	538.7	541.4	543.8	548.5	555.0	564.2
30°	519.5	516.9	515.2	513.1	515.2	516.9	519.5	521.6	526.3	533.1	540.0
32.5°	497.3	496.8	493.7	493.3	493.7	496.8	497.3	500.8	505.5	511.9	517.8
35°	468.2	465.7	464.8	465.3	464.8	465.7	468.2	469.9	474.3	480.2	485.8
37.5°	440.7	437.2	435.7	434.2	435.7	437.2	440.7	440.9	445.3	449.3	456.8
40°	420.9	417.4	416.6	415.7	416.6	417.4	420.9	420.4	425.2	428.1	435.0
42.5°	398.7	397.3	396.8	395.3	396.8	397.3	398.7	401.0	403.7	408.0	413.1
45°	368.4	367.9	365.4	366.2	365.4	367.9	368.4	369.7	374.4	377.3	382.0
47.5°	336.5	334.6	332.8	333.9	332.8	334.6	336.5	338.2	341.3	345.0	351.2
50°	314.6	313.7	309.9	310.7	309.9	313.7	314.6	316.3	318.5	323.1	328.6
52.5°	292.8	289.5	288.0	287.6	288.0	289.5	292.8	294.4	296.9	302.3	306.5
55°	256.6	252.7	250.9	250.1	250.9	252.7	256.6	259.5	262.9	268.9	273.2
57.5°	221.0	220.0	218.7	219.6	218.7	220.0	221.0	226.0	229.3	234.0	239.2
60°	200.2	200.2	200.2	199.7	200.2	200.2	200.2	204.5	207.4	212.1	217.7
62.5°	184.2	183.1	182.8	183.4	182.8	183.1	184.2	186.1	189.0	192.0	196.9
65°	159.6	159.2	157.5	157.1	157.5	159.2	159.6	160.9	163.5	165.6	169.0
67.5°	136.5	134.9	134.4	133.9	134.4	134.9	136.5	137.6	139.3	142.0	143.7
70°	119.1	118.2	115.7	116.1	115.7	118.2	119.1	121.2	122.9	126.4	128.1
72.5°	100.3	99.5	99.0	98.3	99.0	99.5	100.3	102.5	104.1	107.9	110.6
75°	79.4	79.0	78.5	80.2	78.5	79.0	79.4	79.8	80.2	81.5	82.8
77.5°	63.6	63.6	63.8	63.2	63.8	63.6	63.6	63.6	63.6	64.2	64.6
80°	53.3	53.3	52.9	52.9	52.9	53.3	53.3	53.3	53.3	53.3	52.9
82.5°	42.8	43.1	43.4	42.7	43.4	43.1	42.8	43.5	43.8	43.1	43.4
85°	28.2	27.7	28.6	28.2	28.6	27.7	28.2	28.2	27.3	28.2	27.7
87.5°	17.9	17.4	17.6	17.8	17.6	17.4	17.9	17.4	17.0	16.9	16.3
90°	26.5	27.5	28.5	27.5	28.5	27.5	26.5	27.5	25.6	24.6	23.6
92.5°	49.2	46.4	47.4	45.7	47.4	46.4	49.2	51.0	55.8	63.3	79.7
95°	128.8	120.3	113.7	109.9	113.7	120.3	128.8	146.8	180.9	231.1	341.0
97.5°	375.5	332.9	307.3	299.1	307.3	332.9	375.5	445.4	558.7	680.9	850.0
100°	699.0	629.9	593.0	593.9	593.0	629.9	699.0	794.8	929.3	1040.1	1116.8
102.5°	978.7	924.0	893.1	871.3	893.1	924.0	978.7	1053.1	1138.4	1203.0	1205.5
105°	1275.9	1240.0	1209.7	1204.9	1209.7	1240.0	1275.9	1319.6	1344.2	1326.2	1231.4
107.5°	1428.1	1415.9	1405.7	1397.0	1405.7	1415.9	1428.1	1427.3	1393.6	1310.6	1156.7
110°	1472.0	1479.6	1477.7	1475.9	1477.7	1479.6	1472.0	1445.5	1379.2	1259.9	1085.6



TEST NUMBER: P332326-930

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1460.7	1484.2	1491.3	1491.8	1491.3	1484.2	1460.7	1412.2	1326.9	1193.2	1015.0
115°	1400.0	1441.7	1460.7	1465.4	1460.7	1441.7	1400.0	1329.0	1225.7	1086.5	921.7
117.5°	1300.2	1347.9	1375.2	1381.7	1375.2	1347.9	1300.2	1226.1	1121.4	996.3	854.0
120°	1230.4	1283.5	1306.3	1312.0	1306.3	1283.5	1230.4	1155.7	1060.0	946.3	818.4
122.5°	1166.9	1214.6	1239.6	1246.8	1239.6	1214.6	1166.9	1100.3	1011.5	906.1	790.4
125°	1083.7	1125.4	1149.0	1155.7	1149.0	1125.4	1083.7	1023.0	947.2	856.3	753.1
127.5°	1017.6	1053.1	1074.6	1080.6	1074.6	1053.1	1017.6	963.5	894.5	812.5	720.5
130°	976.6	1010.7	1030.6	1038.2	1030.6	1010.7	976.6	926.4	862.0	785.3	700.0
132.5°	939.5	973.5	991.2	996.5	991.2	973.5	939.5	892.3	831.0	759.5	681.1
135°	884.8	913.1	930.2	936.9	930.2	913.1	884.8	838.3	784.3	722.8	655.5
137.5°	826.2	855.0	869.4	873.8	869.4	855.0	826.2	787.2	740.4	687.3	632.2
140°	789.0	815.6	830.7	829.8	830.7	815.6	789.0	753.1	712.3	666.8	618.6
142.5°	752.7	776.2	789.8	788.9	789.8	776.2	752.7	722.0	686.6	647.2	605.7
145°	702.9	722.8	730.3	732.2	730.3	722.8	702.9	679.1	651.8	621.4	590.1
147.5°	664.2	677.7	684.9	685.6	684.9	677.7	664.2	646.2	626.7	602.3	577.5
150°	642.2	652.6	658.4	658.4	658.4	652.6	642.2	628.0	610.0	590.1	568.3
152.5°	622.6	632.2	635.6	635.6	635.6	632.2	622.6	611.4	596.4	578.8	560.0
155°	596.8	604.4	606.3	607.2	606.3	604.4	596.8	588.2	576.9	562.6	547.5
157.5°	574.2	579.9	581.4	581.2	581.4	579.9	574.2	566.8	557.9	547.0	534.3
160°	559.9	565.5	565.5	564.6	565.5	565.5	559.9	553.2	546.6	537.1	526.7
162.5°	545.4	550.3	550.3	549.4	550.3	550.3	545.4	541.0	535.2	526.5	517.6
165°	526.7	530.4	529.5	529.5	529.5	530.4	526.7	522.9	518.1	511.5	505.8
167.5°	508.8	511.5	510.5	510.5	510.5	511.5	508.8	507.2	503.8	499.9	495.6
170°	498.2	500.2	499.2	499.2	499.2	500.2	498.2	497.3	495.4	491.6	488.8
172.5°	489.2	491.1	489.3	488.6	489.3	491.1	489.2	488.9	487.9	484.8	482.7
175°	477.4	478.3	477.4	476.5	477.4	478.3	477.4	477.4	477.4	475.5	474.6
177.5°	470.2	471.0	469.4	469.4	469.4	471.0	470.2	471.0	471.0	470.2	469.4
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0



TEST NUMBER: P332326-930

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	951.7	956.5	961.2	965.7	972.6	975.6	980.1	981.8	986.8	994.4	1000.5
5°	893.8	900.7	909.6	916.9	928.4	937.3	947.2	956.6	967.7	983.5	997.5
7.5°	844.7	851.5	862.3	875.7	888.4	901.2	914.6	927.4	943.2	965.9	988.3
10°	812.3	820.4	833.2	847.7	863.5	875.9	891.7	907.9	927.6	953.6	980.5
12.5°	784.3	790.4	805.2	819.0	836.9	852.6	868.1	887.0	909.5	937.2	969.6
15°	739.7	748.3	762.8	778.1	797.0	813.6	833.6	856.7	878.5	912.6	951.9
17.5°	695.0	708.0	723.1	740.5	754.3	777.3	799.1	822.7	849.5	885.7	928.8
20°	666.3	676.5	690.6	715.8	734.2	751.7	771.8	801.2	826.0	866.9	911.7
22.5°	642.0	649.5	665.4	686.2	707.5	727.8	748.2	776.2	806.8	845.8	894.3
25°	606.1	618.1	630.1	645.0	668.1	692.4	714.5	738.4	770.9	812.3	864.8
27.5°	571.0	581.9	593.7	612.0	629.5	652.2	675.5	702.9	737.7	781.5	834.8
30°	548.5	556.6	567.7	591.2	607.0	626.6	654.0	678.2	710.7	757.2	813.6
32.5°	525.3	535.8	547.9	565.9	585.5	604.1	629.0	655.4	688.5	734.3	792.1
35°	492.2	504.5	516.9	530.1	549.8	569.0	589.9	618.9	652.6	697.1	753.8
37.5°	461.7	471.7	481.8	498.1	516.7	535.0	554.6	583.2	614.9	662.8	714.9
40°	442.2	451.2	458.9	476.0	493.8	513.5	532.7	557.9	592.1	636.8	687.2
42.5°	421.0	429.3	439.8	453.7	473.0	489.6	508.8	532.6	564.8	610.3	654.4
45°	389.3	398.7	407.6	420.9	440.1	456.3	473.4	496.0	528.9	566.5	605.7
47.5°	356.3	365.7	375.9	388.7	405.4	421.9	439.0	459.0	489.0	525.9	552.4
50°	335.1	342.8	353.0	365.8	381.2	398.7	414.0	435.8	464.4	493.4	516.5
52.5°	313.2	320.2	331.8	345.4	359.6	374.8	391.2	409.9	435.7	463.0	481.4
55°	279.2	287.7	297.5	310.7	324.8	337.6	353.4	372.7	393.1	413.6	426.0
57.5°	247.3	254.4	262.7	276.3	288.5	303.9	318.0	333.0	351.9	367.4	375.4
60°	224.1	230.5	241.2	253.2	264.6	277.9	294.1	309.1	323.6	335.9	342.3
62.5°	202.3	209.7	219.0	229.9	242.5	255.0	269.2	281.7	294.5	305.2	309.6
65°	173.7	179.7	186.5	196.8	207.0	219.8	230.9	243.7	253.2	259.1	262.9
67.5°	147.8	151.7	156.9	163.7	173.8	185.0	195.8	205.8	213.6	217.7	221.1
70°	131.0	133.6	137.5	144.3	152.0	161.8	172.8	180.1	186.9	190.4	193.8
72.5°	114.3	117.6	121.1	126.5	132.8	139.9	148.0	156.9	160.7	164.8	166.8
75°	86.7	91.3	96.0	99.5	103.7	109.3	116.5	122.1	124.3	127.6	128.1
77.5°	65.4	66.4	69.9	74.1	77.7	81.7	86.3	91.2	92.3	94.1	95.2
80°	53.8	53.8	53.8	56.3	60.6	63.6	67.8	70.4	72.2	72.6	73.0
82.5°	43.2	43.2	42.9	43.4	44.9	46.6	50.5	53.3	54.7	54.5	53.6
85°	28.2	27.3	27.3	26.9	27.3	26.5	26.0	27.7	30.3	30.3	29.4
87.5°	16.1	16.0	15.8	14.8	13.9	13.0	11.7	11.6	11.0	12.1	11.3
90°	22.7	23.6	20.9	18.0	15.2	12.3	10.4	8.6	5.7	3.8	1.9
92.5°	109.9	145.7	160.3	120.3	79.6	54.8	40.8	32.8	25.4	17.4	11.7
95°	455.6	561.7	500.2	344.8	203.7	123.1	86.2	61.6	45.5	35.1	32.2
97.5°	931.3	870.5	637.3	378.3	219.2	142.3	102.3	78.0	64.0	55.8	55.0
100°	1083.7	897.1	606.3	357.1	217.0	150.6	113.7	90.9	77.7	71.0	70.1
102.5°	1091.2	847.8	560.8	338.9	220.0	160.5	126.5	106.1	93.6	87.7	86.0
105°	1033.5	761.6	504.9	325.9	228.3	177.2	147.7	129.8	118.4	112.8	109.9
107.5°	932.3	685.4	469.3	324.9	243.9	198.9	171.6	154.7	143.6	138.1	135.3
110°	868.6	642.2	455.6	328.7	256.7	214.1	187.5	171.5	161.0	156.3	153.4



TEST NUMBER: P332326-930

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	813.3	613.4	448.1	336.3	269.6	230.0	204.2	188.1	177.7	173.0	170.2
115°	746.4	582.5	445.2	348.6	290.8	254.8	229.3	213.1	203.7	198.0	194.2
117.5°	706.0	564.4	446.9	364.8	313.3	277.8	254.0	236.0	227.3	222.6	218.3
120°	684.9	556.0	450.0	377.0	327.8	293.7	269.9	252.0	242.5	237.7	234.9
122.5°	667.4	550.7	455.3	388.4	342.9	309.6	284.4	267.1	256.9	252.2	249.3
125°	645.1	543.7	463.2	406.3	364.7	331.5	306.0	288.0	277.5	271.9	269.9
127.5°	625.4	540.3	472.3	421.2	383.6	351.6	326.0	306.1	295.5	288.5	285.7
130°	614.7	538.0	478.3	431.0	395.0	363.7	338.2	318.3	306.9	298.4	295.5
132.5°	605.0	537.3	482.9	440.1	404.9	374.4	349.5	329.6	316.0	306.7	303.1
135°	592.1	536.1	489.8	451.8	419.6	390.3	364.7	344.8	330.6	320.2	316.4
137.5°	580.8	534.0	494.3	460.6	429.8	401.6	378.0	358.2	343.1	332.9	328.9
140°	574.1	533.3	497.3	465.1	436.7	409.2	385.6	366.6	351.4	341.9	337.2
142.5°	567.9	531.8	499.6	469.6	442.0	415.3	393.1	374.1	360.5	350.3	346.3
145°	559.9	529.5	501.1	474.6	449.0	424.4	402.6	386.5	372.3	363.7	360.9
147.5°	551.9	525.9	501.1	477.6	454.7	432.1	413.6	398.0	385.7	377.4	375.7
150°	546.6	522.9	501.1	478.3	458.4	436.7	419.6	406.3	394.0	386.5	385.6
152.5°	540.5	519.1	498.8	479.9	460.7	442.0	425.7	413.9	403.2	395.6	395.4
155°	531.4	512.5	496.4	480.3	465.1	449.0	435.7	425.3	415.9	410.2	410.2
157.5°	521.1	506.6	493.2	481.2	467.6	454.7	444.4	435.5	427.2	422.7	421.9
160°	514.4	502.1	491.6	481.2	469.9	458.4	449.0	442.4	434.8	431.0	431.0
162.5°	507.5	497.5	488.6	480.5	470.6	460.7	452.8	446.9	440.8	437.8	437.8
165°	498.2	490.6	484.0	478.3	471.7	464.1	457.5	453.7	449.0	447.1	448.1
167.5°	489.3	483.9	479.5	476.9	471.6	466.0	461.9	459.3	455.6	454.7	455.8
170°	484.0	479.3	476.5	474.6	470.8	466.0	464.1	462.3	459.4	458.4	460.4
172.5°	478.7	475.5	474.2	473.9	470.8	466.8	465.7	464.6	462.4	462.3	463.4
175°	472.7	470.8	470.8	471.7	469.9	468.0	467.0	467.0	465.1	466.0	467.0
177.5°	468.7	468.0	468.7	470.2	468.7	468.0	468.0	468.0	467.2	468.0	468.7
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0



TEST NUMBER: P332326-930

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1002.6	1006.3	1011.1	1018.3	1023.8	1028.5	1029.6	1030.9	1034.4	1040.2	1044.6
5°	1009.1	1018.9	1034.7	1050.0	1066.7	1080.4	1093.2	1102.1	1110.7	1128.6	1143.1
7.5°	1007.1	1028.9	1053.6	1081.2	1109.1	1136.2	1161.3	1183.7	1206.1	1232.2	1262.0
10°	1005.7	1031.3	1064.5	1100.0	1138.8	1176.8	1213.6	1242.1	1275.5	1305.3	1343.3
12.5°	999.1	1036.1	1075.9	1121.2	1168.9	1212.7	1261.0	1300.6	1338.6	1381.8	1426.0
15°	990.8	1035.5	1085.9	1146.1	1218.6	1271.6	1321.1	1389.8	1436.8	1483.8	1546.9
17.5°	975.3	1030.0	1092.9	1171.1	1231.7	1302.8	1377.3	1431.6	1494.9	1561.0	1618.2
20°	963.0	1026.5	1097.0	1173.9	1251.1	1328.4	1400.5	1465.3	1530.7	1607.1	1654.1
22.5°	950.7	1013.6	1086.8	1168.4	1251.4	1332.8	1414.5	1490.6	1564.2	1641.3	1701.2
25°	924.5	999.2	1078.6	1161.9	1243.8	1333.5	1430.8	1515.7	1606.6	1686.0	1742.9
27.5°	898.1	966.5	1045.6	1130.0	1221.2	1327.1	1441.5	1538.1	1629.2	1686.0	1703.9
30°	874.2	946.7	1019.3	1105.1	1203.7	1321.9	1443.6	1554.1	1628.9	1653.6	1635.2
32.5°	849.9	915.7	987.6	1075.4	1180.1	1309.3	1446.3	1544.6	1589.6	1570.7	1495.9
35°	807.1	866.5	936.0	1024.0	1144.4	1302.4	1435.1	1501.6	1490.5	1383.8	1243.0
37.5°	761.4	809.8	874.2	966.1	1107.3	1274.6	1386.6	1396.4	1300.3	1136.5	973.8
40°	725.2	768.7	834.9	931.0	1078.6	1247.2	1337.7	1298.0	1149.1	966.8	831.1
42.5°	690.1	726.8	790.5	894.1	1051.3	1210.1	1265.0	1178.5	1006.7	834.3	710.9
45°	630.5	665.0	729.0	835.4	995.4	1138.8	1131.6	981.3	809.3	670.6	568.1
47.5°	574.0	604.1	664.2	772.7	929.8	1032.1	964.3	804.4	658.4	547.1	474.1
50°	534.0	563.9	623.6	730.8	877.2	951.9	855.0	700.9	567.3	475.1	417.0
52.5°	495.8	525.0	579.6	684.0	813.7	858.3	754.2	611.4	500.0	420.4	370.6
55°	442.2	464.4	513.5	613.3	710.3	720.6	615.1	495.5	403.8	348.3	314.1
57.5°	387.7	406.8	455.3	534.8	602.8	597.5	497.6	394.1	332.3	291.1	266.4
60°	352.1	371.0	413.6	481.9	533.1	515.2	423.5	340.2	287.2	257.0	237.3
62.5°	319.0	333.7	373.7	423.5	460.4	440.1	362.0	293.1	251.1	225.5	210.0
65°	271.1	283.0	315.0	341.0	361.5	341.9	277.0	229.2	198.9	181.0	170.3
67.5°	225.4	233.1	253.3	262.7	277.1	255.6	208.3	176.3	159.1	143.9	136.5
70°	196.8	202.4	213.0	220.7	224.5	202.4	167.3	143.8	129.3	118.6	114.0
72.5°	168.1	172.9	175.1	181.4	179.4	158.7	134.5	115.9	105.4	98.2	92.1
75°	128.5	130.6	128.5	125.9	120.3	105.8	89.2	79.8	72.2	68.7	66.6
77.5°	93.7	92.9	90.1	86.0	76.6	67.4	58.5	55.4	52.0	50.2	49.4
80°	72.2	70.4	67.8	61.5	53.3	47.0	44.8	42.7	41.4	39.3	38.8
82.5°	53.7	52.7	48.4	43.0	37.3	34.3	32.5	31.8	30.5	29.4	29.3
85°	28.6	27.3	22.6	19.6	18.8	17.9	17.5	17.5	15.8	15.3	15.3
87.5°	9.9	8.3	8.6	7.9	8.2	8.2	9.0	9.0	9.2	9.3	8.8
90°	3.8	5.7	8.6	10.4	12.3	15.2	18.0	20.9	23.6	22.7	23.6
92.5°	17.4	25.4	32.8	40.8	54.8	79.6	120.3	160.3	145.7	109.9	79.7
95°	35.1	45.5	61.6	86.2	123.1	203.7	344.8	500.2	561.7	455.6	341.0
97.5°	55.8	64.0	78.0	102.3	142.3	219.2	378.3	637.3	870.5	931.3	850.0
100°	71.0	77.7	90.9	113.7	150.6	217.0	357.1	606.3	897.1	1083.7	1116.8
102.5°	87.7	93.6	106.1	126.5	160.5	220.0	338.9	560.8	847.8	1091.2	1205.5
105°	112.8	118.4	129.8	147.7	177.2	228.3	325.9	504.9	761.6	1033.5	1231.4
107.5°	138.1	143.6	154.7	171.6	198.9	243.9	324.9	469.3	685.4	932.3	1156.7
110°	156.3	161.0	171.5	187.5	214.1	256.7	328.7	455.6	642.2	868.6	1085.6



TEST NUMBER: P332326-930

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	173.0	177.7	188.1	204.2	230.0	269.6	336.3	448.1	613.4	813.3	1015.0
115°	198.0	203.7	213.1	229.3	254.8	290.8	348.6	445.2	582.5	746.4	921.7
117.5°	222.6	227.3	236.0	254.0	277.8	313.3	364.8	446.9	564.4	706.0	854.0
120°	237.7	242.5	252.0	269.9	293.7	327.8	377.0	450.0	556.0	684.9	818.4
122.5°	252.2	256.9	267.1	284.4	309.6	342.9	388.4	455.3	550.7	667.4	790.4
125°	271.9	277.5	288.0	306.0	331.5	364.7	406.3	463.2	543.7	645.1	753.1
127.5°	288.5	295.5	306.1	326.0	351.6	383.6	421.2	472.3	540.3	625.4	720.5
130°	298.4	306.9	318.3	338.2	363.7	395.0	431.0	478.3	538.0	614.7	700.0
132.5°	306.7	316.0	329.6	349.5	374.4	404.9	440.1	482.9	537.3	605.0	681.1
135°	320.2	330.6	344.8	364.7	390.3	419.6	451.8	489.8	536.1	592.1	655.5
137.5°	332.9	343.1	358.2	378.0	401.6	429.8	460.6	494.3	534.0	580.8	632.2
140°	341.9	351.4	366.6	385.6	409.2	436.7	465.1	497.3	533.3	574.1	618.6
142.5°	350.3	360.5	374.1	393.1	415.3	442.0	469.6	499.6	531.8	567.9	605.7
145°	363.7	372.3	386.5	402.6	424.4	449.0	474.6	501.1	529.5	559.9	590.1
147.5°	377.4	385.7	398.0	413.6	432.1	454.7	477.6	501.1	525.9	551.9	577.5
150°	386.5	394.0	406.3	419.6	436.7	458.4	478.3	501.1	522.9	546.6	568.3
152.5°	395.6	403.2	413.9	425.7	442.0	460.7	479.9	498.8	519.1	540.5	560.0
155°	410.2	415.9	425.3	435.7	449.0	465.1	480.3	496.4	512.5	531.4	547.5
157.5°	422.7	427.2	435.5	444.4	454.7	467.6	481.2	493.2	506.6	521.1	534.3
160°	431.0	434.8	442.4	449.0	458.4	469.9	481.2	491.6	502.1	514.4	526.7
162.5°	437.8	440.8	446.9	452.8	460.7	470.6	480.5	488.6	497.5	507.5	517.6
165°	447.1	449.0	453.7	457.5	464.1	471.7	478.3	484.0	490.6	498.2	505.8
167.5°	454.7	455.6	459.3	461.9	466.0	471.6	476.9	479.5	483.9	489.3	495.6
170°	458.4	459.4	462.3	464.1	466.0	470.8	474.6	476.5	479.3	484.0	488.8
172.5°	462.3	462.4	464.6	465.7	466.8	470.8	473.9	474.2	475.5	478.7	482.7
175°	466.0	465.1	467.0	467.0	468.0	469.9	471.7	470.8	470.8	472.7	474.6
177.5°	468.0	467.2	468.0	468.0	468.0	468.7	470.2	468.7	468.0	468.7	469.4
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0



TEST NUMBER: P332326-930

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1051.7	1051.7	1053.1	1058.3	1058.9	1063.4	1062.0
5°	1155.9	1164.0	1167.0	1179.8	1187.5	1190.9	1184.1
7.5°	1283.3	1306.2	1317.0	1330.4	1342.3	1345.9	1336.5
10°	1376.1	1400.0	1420.2	1432.5	1444.1	1451.7	1461.5
12.5°	1466.0	1495.3	1514.4	1531.9	1543.8	1553.5	1555.1
15°	1563.6	1607.9	1641.7	1666.4	1678.8	1685.2	1682.6
17.5°	1662.0	1703.2	1727.1	1752.4	1769.5	1770.4	1770.9
20°	1717.7	1757.8	1785.5	1804.3	1823.5	1822.7	1826.9
22.5°	1754.9	1786.5	1807.7	1821.4	1828.0	1824.7	1825.5
25°	1772.3	1781.7	1777.8	1756.1	1750.5	1730.5	1733.9
27.5°	1682.5	1638.1	1592.1	1533.1	1486.5	1449.3	1451.2
30°	1560.6	1482.1	1392.4	1317.3	1249.9	1231.0	1190.9
32.5°	1390.2	1272.4	1167.3	1097.3	1039.4	1023.8	988.8
35°	1101.3	986.8	878.9	814.0	788.4	752.5	752.1
37.5°	856.0	755.3	698.1	649.5	623.9	602.3	600.1
40°	720.1	641.6	598.4	563.5	538.3	522.0	518.2
42.5°	625.2	561.7	521.3	499.6	480.2	471.8	465.6
45°	510.5	467.8	439.7	420.0	411.1	404.6	401.2
47.5°	427.1	398.4	379.2	366.2	358.9	352.1	353.9
50°	381.6	358.2	344.1	331.7	326.1	321.4	321.9
52.5°	345.0	324.0	312.6	303.7	296.8	293.4	291.8
55°	292.9	279.6	268.1	261.6	257.8	253.2	251.8
57.5°	249.8	239.5	230.2	222.9	221.9	217.4	218.0
60°	221.1	212.5	204.9	201.1	198.0	194.2	195.5
62.5°	197.5	190.4	183.4	180.2	177.2	174.4	175.0
65°	161.8	154.9	150.7	149.0	147.7	146.4	145.1
67.5°	128.9	124.7	122.1	118.4	115.8	115.4	114.1
70°	108.4	102.9	98.2	93.5	92.2	91.8	92.2
72.5°	86.9	83.4	82.1	79.8	79.6	78.4	79.2
75°	65.3	64.0	63.2	61.5	61.5	61.5	61.5
77.5°	48.2	47.4	46.9	46.6	46.1	45.5	45.4
80°	37.6	37.1	36.3	36.3	35.9	36.3	35.9
82.5°	28.4	28.3	27.4	27.4	27.0	26.7	27.0
85°	14.5	14.1	14.9	14.1	14.5	13.7	14.5
87.5°	9.0	9.2	9.2	9.0	8.9	9.8	8.9
90°	24.6	25.6	27.5	26.5	27.5	28.5	27.5
92.5°	63.3	55.8	51.0	49.2	46.4	47.4	45.7
95°	231.1	180.9	146.8	128.8	120.3	113.7	109.9
97.5°	680.9	558.7	445.4	375.5	332.9	307.3	299.1
100°	1040.1	929.3	794.8	699.0	629.9	593.0	593.9
102.5°	1203.0	1138.4	1053.1	978.7	924.0	893.1	871.3
105°	1326.2	1344.2	1319.6	1275.9	1240.0	1209.7	1204.9
107.5°	1310.6	1393.6	1427.3	1428.1	1415.9	1405.7	1397.0
110°	1259.9	1379.2	1445.5	1472.0	1479.6	1477.7	1475.9



TEST NUMBER: P332326-930

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1193.2	1326.9	1412.2	1460.7	1484.2	1491.3	1491.8
115°	1086.5	1225.7	1329.0	1400.0	1441.7	1460.7	1465.4
117.5°	996.3	1121.4	1226.1	1300.2	1347.9	1375.2	1381.7
120°	946.3	1060.0	1155.7	1230.4	1283.5	1306.3	1312.0
122.5°	906.1	1011.5	1100.3	1166.9	1214.6	1239.6	1246.8
125°	856.3	947.2	1023.0	1083.7	1125.4	1149.0	1155.7
127.5°	812.5	894.5	963.5	1017.6	1053.1	1074.6	1080.6
130°	785.3	862.0	926.4	976.6	1010.7	1030.6	1038.2
132.5°	759.5	831.0	892.3	939.5	973.5	991.2	996.5
135°	722.8	784.3	838.3	884.8	913.1	930.2	936.9
137.5°	687.3	740.4	787.2	826.2	855.0	869.4	873.8
140°	666.8	712.3	753.1	789.0	815.6	830.7	829.8
142.5°	647.2	686.6	722.0	752.7	776.2	789.8	788.9
145°	621.4	651.8	679.1	702.9	722.8	730.3	732.2
147.5°	602.3	626.7	646.2	664.2	677.7	684.9	685.6
150°	590.1	610.0	628.0	642.2	652.6	658.4	658.4
152.5°	578.8	596.4	611.4	622.6	632.2	635.6	635.6
155°	562.6	576.9	588.2	596.8	604.4	606.3	607.2
157.5°	547.0	557.9	566.8	574.2	579.9	581.4	581.2
160°	537.1	546.6	553.2	559.9	565.5	565.5	564.6
162.5°	526.5	535.2	541.0	545.4	550.3	550.3	549.4
165°	511.5	518.1	522.9	526.7	530.4	529.5	529.5
167.5°	499.9	503.8	507.2	508.8	511.5	510.5	510.5
170°	491.6	495.4	497.3	498.2	500.2	499.2	499.2
172.5°	484.8	487.9	488.9	489.2	491.1	489.3	488.6
175°	475.5	477.4	477.4	477.4	478.3	477.4	476.5
177.5°	470.2	471.0	471.0	470.2	471.0	469.4	469.4
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0

(END OF REPORT)