

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332328-930

Luminaire Tested: **S123RDIP-S775D1195U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332328-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S775D1195U930-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5722.5 lumens  
Efficiency: N/A  
Efficacy: 100.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332328-930

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332328-930

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36
2	88	81	75	70	80	74	69	64	61	57	54	49	47	45	38	37	35	30
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	34	32	30	26
4	73	63	55	50	67	58	51	46	48	43	39	39	36	33	31	28	26	22
5	67	56	48	42	61	52	45	40	43	38	34	35	31	28	28	25	23	20
6	62	50	43	37	57	46	40	34	39	34	30	32	28	25	25	23	20	17
7	57	46	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	29	49	38	31	27	32	27	23	27	23	20	21	18	16	14
9	50	38	30	26	45	35	28	24	30	24	21	24	21	18	20	17	15	13
10	46	35	28	23	42	32	26	21	27	22	19	23	19	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11330	11330	11330
5°	11373	11217	11282
10°	11309	11075	11038
15°	11188	10816	10702
20°	11021	10493	10247
25°	10849	10128	9804
30°	10621	9708	9178
35°	10387	9289	8604
40°	10172	8792	7893
45°	9889	8304	7252
50°	9577	7748	6532
55°	9259	7112	5863
60°	8968	6433	5126
65°	8588	5695	4391
70°	8113	4784	3547
75°	7419	3764	3335
80°	6614	3335	3068
85°	5582	2952	2742



TEST NUMBER: P332328-930

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	98.8	1.7
10°-20°	275.0	4.8
20°-30°	396.0	6.9
30°-40°	446.1	7.8
40°-50°	426.7	7.5
50°-60°	349.5	6.1
60°-70°	235.8	4.1
70°-80°	118.6	2.1
80°-90°	35.0	0.6
90°-100°	78.6	1.4
100°-110°	235.1	4.1
110°-120°	399.9	7.0
120°-130°	526.0	9.2
130°-140°	591.2	10.3
140°-150°	581.2	10.2
150°-160°	489.3	8.5
160°-170°	325.7	5.7
170°-180°	114.0	2.0
0°-30°	769.9	13.5
0°-40°	1215.9	21.2
0°-60°	1992.1	34.8
0°-90°	2381.5	41.6
90°-120°	713.6	12.5
90°-150°	2412.1	42.2
90°-180°	3341.0	58.4
0°-180°	5722.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1053	1053	1053	1053	1053	
5°	1053	1048	1038	1045	1044	100
15°	1004	994	971	966	960	283
25°	914	891	853	835	826	420
35°	790	759	707	671	655	495
45°	650	610	546	498	476	501
55°	493	450	379	331	312	442
65°	337	289	224	184	172	334
75°	178	137	90	82	80	190
85°	45	27	24	22	22	51
90°	1	11	23	26	28	6
95°	56	63	70	74	74	63
105°	213	215	224	224	225	228
115°	403	405	404	404	404	398
125°	589	592	590	586	583	525
135°	764	770	769	766	764	589
145°	927	929	932	931	927	579
155°	1062	1062	1063	1066	1060	489
165°	1157	1154	1154	1159	1153	326
175°	1203	1199	1199	1204	1198	114
180°	1206	1206	1206	1206	1206	



TEST NUMBER: P332328-930

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6
2.5°	1056.0	1055.4	1054.8	1054.2	1053.6	1052.4	1050.5	1048.7	1046.9	1045.1	1046.8
5°	1052.6	1051.7	1050.7	1049.8	1048.8	1047.2	1044.9	1042.6	1040.3	1038.1	1039.8
7.5°	1042.8	1041.9	1040.8	1039.8	1038.8	1036.7	1033.8	1030.9	1027.9	1024.9	1025.9
10°	1034.7	1033.3	1032.0	1030.7	1029.3	1027.0	1023.5	1020.2	1016.8	1013.3	1013.5
12.5°	1023.0	1021.6	1020.1	1018.6	1017.2	1014.3	1010.2	1006.0	1001.8	997.6	997.5
15°	1004.0	1001.8	999.7	997.7	995.6	991.9	986.6	981.3	975.9	970.6	969.7
17.5°	979.8	977.5	975.0	972.6	970.1	965.6	958.8	952.0	945.3	938.6	936.5
20°	962.1	959.0	956.0	953.0	950.0	944.9	937.6	930.4	923.2	916.0	913.5
22.5°	942.3	938.8	935.3	931.8	928.3	922.8	915.1	907.4	899.8	892.1	889.0
25°	913.5	908.7	903.9	899.2	894.5	887.7	879.0	870.3	861.5	852.8	848.8
27.5°	878.4	873.2	868.0	862.7	857.5	850.0	840.3	830.6	820.8	811.1	805.6
30°	854.5	848.8	843.2	837.5	831.8	823.6	813.0	802.3	791.7	781.1	774.7
32.5°	830.6	824.2	817.7	811.3	804.9	796.0	784.7	773.6	762.3	751.1	744.0
35°	790.5	783.7	776.8	770.1	763.2	753.9	742.2	730.3	718.6	706.9	698.7
37.5°	749.9	742.2	734.7	727.1	719.5	709.5	696.9	684.4	671.8	659.3	650.0
40°	723.9	715.6	707.2	698.9	690.6	679.6	666.2	652.7	639.2	625.7	615.9
42.5°	694.6	686.2	677.8	669.5	661.2	650.0	636.1	622.2	608.3	594.4	583.6
45°	649.6	641.2	632.6	624.0	615.5	604.0	589.3	574.7	560.1	545.5	534.7
47.5°	604.8	595.4	586.0	576.7	567.3	555.3	540.7	526.0	511.4	496.8	485.1
50°	571.9	563.0	554.2	545.2	536.3	524.2	508.8	493.4	478.1	462.7	450.9
52.5°	542.6	533.0	523.3	513.6	503.9	491.5	476.2	461.1	445.8	430.6	418.4
55°	493.4	484.1	474.8	465.5	456.2	443.5	427.4	411.3	395.2	379.0	368.0
57.5°	448.0	437.9	427.8	417.6	407.5	394.4	378.1	361.9	345.7	329.5	319.1
60°	416.6	406.2	395.7	385.3	374.9	361.7	346.0	330.3	314.5	298.8	288.5
62.5°	385.1	374.7	364.3	353.8	343.5	330.4	314.6	298.9	283.2	267.3	257.7
65°	337.2	326.8	316.3	305.9	295.5	282.8	268.1	253.2	238.5	223.6	214.3
67.5°	289.3	278.7	268.2	257.6	247.0	234.6	220.5	206.3	192.1	177.9	171.0
70°	257.8	247.6	237.3	227.1	216.9	205.0	191.8	178.6	165.3	152.0	145.3
72.5°	226.4	216.3	206.2	196.1	186.1	175.0	162.9	150.8	138.8	126.7	121.2
75°	178.4	169.3	160.2	151.1	142.0	132.2	121.8	111.4	100.9	90.5	88.6
77.5°	134.7	126.5	118.2	110.0	101.7	94.3	87.6	80.9	74.2	67.4	66.4
80°	106.7	98.9	91.2	83.4	75.6	69.7	65.7	61.7	57.8	53.8	53.2
82.5°	80.1	73.4	66.6	59.9	53.2	48.9	47.0	45.2	43.4	41.5	40.9
85°	45.2	41.1	36.9	32.7	28.5	26.2	25.6	25.0	24.5	23.9	23.6
87.5°	16.6	15.3	14.1	12.8	11.6	11.3	11.8	12.3	12.9	13.5	13.5
90°	1.0	3.0	5.1	7.3	9.4	11.8	14.5	17.3	20.0	22.7	23.6
92.5°	22.9	24.4	25.8	27.2	28.6	30.2	31.7	33.3	34.8	36.4	37.0
95°	55.9	57.4	58.9	60.3	61.8	63.3	65.1	66.7	68.4	70.1	70.9
97.5°	99.3	100.4	101.5	102.6	103.6	104.8	106.1	107.3	108.4	109.7	110.6
100°	128.8	130.1	131.3	132.6	133.9	135.0	136.1	137.1	138.2	139.3	139.9
102.5°	162.9	163.7	164.4	165.2	166.0	167.1	168.4	169.8	171.2	172.6	173.3
105°	213.1	213.5	214.0	214.4	214.8	216.0	217.8	219.8	221.7	223.6	223.6
107.5°	271.5	271.7	272.0	272.2	272.5	273.0	273.8	274.5	275.2	276.1	276.7
110°	307.9	308.3	308.7	309.2	309.6	310.0	310.4	310.8	311.2	311.7	312.5



TEST NUMBER: P332328-930

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	345.8	346.0	346.3	346.5	346.7	346.9	347.0	347.1	347.2	347.2	348.3
115°	402.6	403.2	403.8	404.5	405.1	405.2	404.8	404.4	404.0	403.6	403.7
117.5°	459.8	460.2	460.6	461.1	461.5	461.5	460.9	460.3	459.8	459.3	459.2
120°	495.5	496.7	498.0	499.2	500.5	500.6	499.5	498.5	497.4	496.4	496.2
122.5°	532.6	533.5	534.4	535.3	536.3	536.5	535.9	535.3	534.8	534.3	533.7
125°	589.2	589.9	590.4	591.1	591.7	591.8	591.4	591.0	590.6	590.2	589.3
127.5°	641.5	642.9	644.2	645.6	646.9	647.3	646.9	646.4	646.0	645.5	644.3
130°	676.4	678.0	679.7	681.4	683.1	683.6	683.0	682.3	681.8	681.1	680.3
132.5°	711.2	712.9	714.6	716.2	718.0	718.6	718.1	717.6	717.1	716.7	715.7
135°	764.4	765.7	767.0	768.3	769.5	770.1	769.8	769.6	769.4	769.2	768.3
137.5°	813.8	814.7	815.8	816.8	817.9	818.7	819.3	819.8	820.4	820.9	820.0
140°	847.8	848.9	849.9	851.0	852.0	852.6	852.9	853.0	853.3	853.5	853.3
142.5°	878.9	880.0	881.0	882.1	883.1	883.8	884.2	884.6	884.9	885.3	885.1
145°	927.4	927.8	928.2	928.6	929.0	929.6	930.3	930.8	931.5	932.1	931.9
147.5°	969.8	970.6	971.3	972.1	972.9	973.5	974.1	974.7	975.3	975.9	975.9
150°	999.4	999.8	1000.2	1000.6	1001.1	1001.5	1001.9	1002.3	1002.7	1003.1	1003.1
152.5°	1023.6	1024.3	1024.8	1025.4	1026.0	1026.4	1026.6	1027.0	1027.2	1027.4	1027.8
155°	1061.9	1061.9	1061.9	1061.9	1061.9	1062.0	1062.3	1062.4	1062.7	1062.8	1063.7
157.5°	1094.5	1094.2	1094.0	1093.7	1093.5	1093.4	1093.6	1093.8	1094.0	1094.1	1095.0
160°	1114.9	1114.5	1114.1	1113.7	1113.3	1113.0	1113.0	1113.0	1113.0	1113.0	1114.1
162.5°	1133.1	1132.5	1132.0	1131.4	1130.8	1130.6	1130.7	1130.9	1131.1	1131.2	1132.3
165°	1156.7	1156.0	1155.4	1154.7	1154.1	1153.8	1153.8	1153.8	1153.8	1153.8	1155.0
167.5°	1175.4	1174.5	1173.7	1172.9	1172.0	1171.7	1171.8	1172.0	1172.2	1172.3	1173.6
170°	1186.0	1185.1	1184.3	1183.5	1182.6	1182.2	1182.2	1182.2	1182.2	1182.2	1183.7
172.5°	1194.3	1193.5	1192.6	1191.8	1191.0	1190.6	1190.6	1190.6	1190.6	1190.6	1191.9
175°	1203.1	1202.2	1201.3	1200.5	1199.7	1199.2	1199.2	1199.2	1199.2	1199.2	1200.5
177.5°	1206.6	1206.0	1205.3	1204.6	1204.0	1203.6	1203.6	1203.6	1203.6	1203.6	1204.6
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P332328-930

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6
2.5°	1048.4	1050.1	1051.7	1052.5	1052.1	1051.8	1051.5	1051.2
5°	1041.5	1043.2	1044.9	1045.5	1045.2	1044.8	1044.4	1044.1
7.5°	1026.9	1027.8	1028.7	1028.9	1028.3	1027.6	1027.0	1026.3
10°	1013.7	1013.9	1014.1	1013.7	1012.8	1011.8	1010.9	1009.9
12.5°	997.4	997.3	997.2	996.5	995.5	994.3	993.3	992.1
15°	968.7	967.8	966.9	965.7	964.4	963.0	961.7	960.4
17.5°	934.5	932.5	930.5	928.5	926.5	924.5	922.6	920.6
20°	911.1	908.6	906.1	903.8	901.5	899.2	896.9	894.6
22.5°	886.0	882.9	879.8	877.2	875.1	872.9	870.8	868.7
25°	844.9	840.9	836.9	833.9	831.8	829.6	827.6	825.5
27.5°	800.1	794.6	789.0	784.6	781.5	778.3	775.1	771.9
30°	768.3	761.7	755.3	750.6	747.5	744.5	741.4	738.4
32.5°	736.9	729.9	722.8	717.7	714.5	711.3	708.2	705.0
35°	690.6	682.4	674.3	668.5	665.0	661.6	658.2	654.8
37.5°	640.7	631.4	622.2	615.5	611.2	607.0	602.8	598.6
40°	606.0	596.1	586.3	579.2	574.8	570.5	566.1	561.7
42.5°	572.7	562.0	551.2	543.9	540.0	536.1	532.1	528.2
45°	523.9	513.1	502.2	494.6	490.0	485.4	480.9	476.4
47.5°	473.3	461.5	449.8	441.9	437.8	433.7	429.7	425.7
50°	439.2	427.4	415.6	407.6	403.2	398.8	394.5	390.1
52.5°	406.2	394.0	381.7	373.7	369.7	365.8	361.9	358.0
55°	357.0	346.0	335.0	327.6	323.8	320.0	316.3	312.4
57.5°	308.8	298.3	288.0	281.1	277.9	274.7	271.4	268.2
60°	278.3	268.1	257.8	251.1	247.9	244.6	241.4	238.1
62.5°	248.1	238.5	228.9	222.3	218.9	215.6	212.2	208.8
65°	205.0	195.8	186.5	180.8	178.7	176.6	174.6	172.4
67.5°	164.0	157.1	150.1	145.5	143.3	141.0	138.8	136.6
70°	138.7	132.0	125.4	121.1	119.0	116.8	114.8	112.7
72.5°	115.9	110.4	105.0	101.8	100.9	100.1	99.2	98.3
75°	86.7	84.8	82.9	81.8	81.4	81.0	80.6	80.2
77.5°	65.4	64.3	63.3	62.6	62.3	61.9	61.5	61.1
80°	52.7	52.1	51.5	51.0	50.6	50.3	49.9	49.5
82.5°	40.4	39.8	39.2	38.9	38.8	38.7	38.6	38.6
85°	23.2	22.7	22.4	22.2	22.2	22.2	22.2	22.2
87.5°	13.5	13.5	13.5	13.5	13.4	13.4	13.3	13.2
90°	24.5	25.3	26.1	26.7	27.1	27.6	28.0	28.5
92.5°	37.7	38.4	39.1	39.3	39.1	38.8	38.5	38.2
95°	71.7	72.6	73.5	73.9	73.9	73.9	73.9	73.9
97.5°	111.6	112.6	113.6	114.0	113.9	113.8	113.7	113.7
100°	140.5	141.1	141.8	142.3	142.8	143.2	143.6	144.0
102.5°	173.8	174.5	175.1	175.4	175.3	175.2	175.1	175.0
105°	223.6	223.6	223.6	223.8	224.2	224.6	225.0	225.4
107.5°	277.4	278.1	278.8	278.9	278.7	278.4	278.2	277.9
110°	313.3	314.2	315.0	315.2	314.8	314.4	314.0	313.6





TEST NUMBER: P332328-930

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	349.3	350.3	351.3	351.8	351.7	351.6	351.6	351.5
115°	404.0	404.1	404.4	404.4	404.1	404.0	403.7	403.6
117.5°	459.2	459.1	459.1	458.8	458.2	457.5	457.0	456.4
120°	495.9	495.8	495.5	495.2	494.8	494.4	494.0	493.5
122.5°	533.2	532.6	532.1	531.5	530.9	530.4	529.7	529.1
125°	588.5	587.7	586.8	586.0	585.1	584.2	583.4	582.6
127.5°	643.1	642.0	640.7	639.7	638.7	637.7	636.7	635.9
130°	679.4	678.6	677.8	676.5	675.1	673.6	672.1	670.7
132.5°	714.7	713.7	712.7	711.6	710.5	709.3	708.2	707.0
135°	767.5	766.6	765.8	765.2	764.8	764.3	763.9	763.5
137.5°	819.1	818.2	817.3	816.5	815.7	815.0	814.2	813.3
140°	853.0	852.9	852.6	851.8	850.4	848.9	847.4	846.0
142.5°	884.9	884.7	884.5	883.8	882.6	881.5	880.4	879.3
145°	931.7	931.5	931.3	930.7	929.9	929.0	928.2	927.4
147.5°	975.9	975.9	975.9	975.3	974.0	972.7	971.4	970.2
150°	1003.1	1003.1	1003.1	1002.6	1001.3	1000.0	998.7	997.5
152.5°	1028.1	1028.4	1028.7	1028.4	1027.3	1026.2	1025.1	1024.0
155°	1064.5	1065.4	1066.2	1065.9	1064.5	1063.0	1061.5	1060.0
157.5°	1095.8	1096.7	1097.6	1097.5	1096.3	1095.1	1094.0	1092.7
160°	1115.2	1116.2	1117.3	1117.4	1116.6	1115.7	1114.8	1114.0
162.5°	1133.3	1134.4	1135.5	1135.3	1133.9	1132.6	1131.2	1129.9
165°	1156.3	1157.6	1158.9	1158.7	1157.2	1155.8	1154.3	1152.8
167.5°	1174.9	1176.2	1177.5	1177.5	1176.2	1174.9	1173.6	1172.3
170°	1185.1	1186.7	1188.1	1188.1	1186.7	1185.1	1183.7	1182.2
172.5°	1193.2	1194.5	1195.8	1195.7	1194.2	1192.7	1191.2	1189.8
175°	1201.8	1203.1	1204.3	1204.2	1202.7	1201.3	1199.8	1198.3
177.5°	1205.7	1206.6	1207.6	1207.5	1206.4	1205.2	1204.0	1202.9
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9

(END OF REPORT)