

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332308-930

Luminaire Tested: **S123RDIP-S775D585U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332308-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D585U930-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4212.8 lumens
Efficiency: N/A
Efficacy: 104.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332308-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332308-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59								
1	100	96	93	89	94	90	87	84	79	76	74	68	66	65	58	57	56	51								
2	92	85	79	74	86	80	75	70	70	66	62	60	58	55	52	50	48	44								
3	84	75	68	63	79	71	64	59	62	57	53	54	50	47	47	44	42	38								
4	78	67	59	54	72	63	56	51	56	50	46	49	44	41	42	39	36	33								
5	72	60	52	46	67	57	50	44	50	44	40	44	40	36	38	35	32	29								
6	66	54	46	41	62	51	44	39	45	40	35	40	35	32	35	31	29	26								
7	61	49	41	36	57	47	39	34	41	36	31	37	32	29	32	28	26	23								
8	57	45	37	32	53	42	36	31	38	32	28	34	29	26	30	26	23	21								
9	53	41	34	29	50	39	32	28	35	29	25	31	26	23	27	24	21	19								
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19	17								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10733	10733	10733	10733
5°	12794	10778	9492	10778
10°	15974	10717	8576	10717
15°	18750	10608	7819	10608
20°	20927	10443	7178	10443
25°	20593	10271	6783	10271
30°	14802	10112	6377	10112
35°	9883	9905	6114	9905
40°	7281	9656	5841	9656
45°	6107	9220	5574	9220
50°	5390	8649	5203	8649
55°	4725	7994	4693	7994
60°	4209	7369	4299	7369
65°	3696	6696	4001	6696
70°	2902	6099	3654	6099
75°	2558	5327	3335	5327
80°	2225	4525	3279	4525
85°	1791	3631	3483	3631



TEST NUMBER: P332308-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.1	2.3
10°-20°	306.3	7.3
20°-30°	481.3	11.4
30°-40°	502.1	11.9
40°-50°	429.7	10.2
50°-60°	327.5	7.8
60°-70°	209.9	5.0
70°-80°	101.0	2.4
80°-90°	28.5	0.7
90°-100°	127.8	3.0
100°-110°	362.0	8.6
110°-120°	356.1	8.5
120°-130°	284.0	6.7
130°-140°	224.0	5.3
140°-150°	167.1	4.0
150°-160°	116.5	2.8
160°-170°	68.4	1.6
170°-180°	22.3	0.5
0°-30°	885.7	21.0
0°-40°	1387.8	32.9
0°-60°	2145.0	50.9
0°-90°	2484.4	59.0
90°-120°	846.0	20.1
90°-150°	1521.1	36.1
90°-180°	1728.0	41.0
0°-180°	4212.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	997	997	997	997	997	
5°	1184	998	878	998	1184	122
15°	1683	952	702	952	1683	477
25°	1734	865	571	865	1734	745
35°	752	754	465	754	752	493
45°	401	606	366	606	401	315
55°	252	426	250	426	252	228
65°	145	263	157	263	145	143
75°	62	128	80	128	62	66
85°	14	29	28	29	14	17
90°	14	1	14	1	14	8
95°	54	16	54	16	54	97
105°	592	54	592	54	592	584
115°	719	95	719	95	719	699
125°	567	133	567	133	567	514
135°	460	155	460	155	460	357
145°	360	177	360	177	360	229
155°	298	201	298	201	298	139
165°	260	220	260	220	260	74
175°	234	229	234	229	234	23
180°	230	230	230	230	230	



TEST NUMBER: P332308-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1062.0	1063.4	1058.9	1058.3	1053.1	1051.7	1051.7	1044.6	1040.2	1034.4	1030.9
5°	1184.1	1190.9	1187.5	1179.8	1167.0	1164.0	1155.9	1143.1	1128.6	1110.7	1102.1
7.5°	1336.5	1345.9	1342.3	1330.4	1317.0	1306.2	1283.3	1262.0	1232.2	1206.1	1183.7
10°	1461.5	1451.7	1444.1	1432.5	1420.2	1400.0	1376.1	1343.3	1305.3	1275.5	1242.1
12.5°	1555.1	1553.5	1543.8	1531.9	1514.4	1495.3	1466.0	1426.0	1381.8	1338.6	1300.6
15°	1682.6	1685.2	1678.8	1666.4	1641.7	1607.9	1563.6	1546.9	1483.8	1436.8	1389.8
17.5°	1770.9	1770.4	1769.5	1752.4	1727.1	1703.2	1662.0	1618.2	1561.0	1494.9	1431.6
20°	1826.9	1822.7	1823.5	1804.3	1785.5	1757.8	1717.7	1654.1	1607.1	1530.7	1465.3
22.5°	1825.5	1824.7	1828.0	1821.4	1807.7	1786.5	1754.9	1701.2	1641.3	1564.2	1490.6
25°	1733.9	1730.5	1750.5	1756.1	1777.8	1781.7	1772.3	1742.9	1686.0	1606.6	1515.7
27.5°	1451.2	1449.3	1486.5	1533.1	1592.1	1638.1	1682.5	1703.9	1686.0	1629.2	1538.1
30°	1190.9	1231.0	1249.9	1317.3	1392.4	1482.1	1560.6	1635.2	1653.6	1628.9	1554.1
32.5°	988.8	1023.8	1039.4	1097.3	1167.3	1272.4	1390.2	1495.9	1570.7	1589.6	1544.6
35°	752.1	752.5	788.4	814.0	878.9	986.8	1101.3	1243.0	1383.8	1490.5	1501.6
37.5°	600.1	602.3	623.9	649.5	698.1	755.3	856.0	973.8	1136.5	1300.3	1396.4
40°	518.2	522.0	538.3	563.5	598.4	641.6	720.1	831.1	966.8	1149.1	1298.0
42.5°	465.6	471.8	480.2	499.6	521.3	561.7	625.2	710.9	834.3	1006.7	1178.5
45°	401.2	404.6	411.1	420.0	439.7	467.8	510.5	568.1	670.6	809.3	981.3
47.5°	353.9	352.1	358.9	366.2	379.2	398.4	427.1	474.1	547.1	658.4	804.4
50°	321.9	321.4	326.1	331.7	344.1	358.2	381.6	417.0	475.1	567.3	700.9
52.5°	291.8	293.4	296.8	303.7	312.6	324.0	345.0	370.6	420.4	500.0	611.4
55°	251.8	253.2	257.8	261.6	268.1	279.6	292.9	314.1	348.3	403.8	495.5
57.5°	218.0	217.4	221.9	222.9	230.2	239.5	249.8	266.4	291.1	332.3	394.1
60°	195.5	194.2	198.0	201.1	204.9	212.5	221.1	237.3	257.0	287.2	340.2
62.5°	175.0	174.4	177.2	180.2	183.4	190.4	197.5	210.0	225.5	251.1	293.1
65°	145.1	146.4	147.7	149.0	150.7	154.9	161.8	170.3	181.0	198.9	229.2
67.5°	114.1	115.4	115.8	118.4	122.1	124.7	128.9	136.5	143.9	159.1	176.3
70°	92.2	91.8	92.2	93.5	98.2	102.9	108.4	114.0	118.6	129.3	143.8
72.5°	79.2	78.4	79.6	79.8	82.1	83.4	86.9	92.1	98.2	105.4	115.9
75°	61.5	61.5	61.5	61.5	63.2	64.0	65.3	66.6	68.7	72.2	79.8
77.5°	45.4	45.5	46.1	46.6	46.9	47.4	48.2	49.4	50.2	52.0	55.4
80°	35.9	36.3	35.9	36.3	36.3	37.1	37.6	38.8	39.3	41.4	42.7
82.5°	27.0	26.7	27.0	27.4	27.4	28.3	28.4	29.3	29.4	30.5	31.8
85°	14.5	13.7	14.5	14.1	14.9	14.1	14.5	15.3	15.3	15.8	17.5
87.5°	6.1	6.8	6.1	6.4	6.4	6.6	6.5	6.4	7.0	6.8	6.8
90°	13.5	13.9	13.5	13.0	13.5	12.6	12.1	11.7	11.2	11.7	10.2
92.5°	22.4	23.2	22.7	24.2	25.0	27.5	31.1	39.1	54.0	71.5	78.7
95°	54.0	55.8	59.0	63.3	72.1	88.8	113.5	167.4	223.6	275.7	245.6
97.5°	146.8	150.8	163.4	184.3	218.7	274.3	334.3	417.4	457.2	427.4	312.8
100°	291.6	291.1	309.2	343.2	390.1	456.2	510.6	548.3	532.0	440.3	297.6
102.5°	427.7	438.4	453.6	480.5	517.0	558.9	590.6	591.8	535.7	416.2	275.3
105°	591.5	593.9	608.7	626.4	647.8	659.9	651.0	604.5	507.4	373.9	247.9
107.5°	685.8	690.1	695.1	701.1	700.7	684.1	643.4	567.9	457.7	336.5	230.4
110°	724.5	725.5	726.4	722.7	709.6	677.1	618.5	532.9	426.4	315.3	223.6



TEST NUMBER: P332308-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	732.3	732.1	728.6	717.1	693.2	651.4	585.7	498.3	399.3	301.2	220.0
115°	719.4	717.1	707.8	687.3	652.4	601.8	533.4	452.5	366.5	286.0	218.6
117.5°	678.2	675.1	661.7	638.3	601.9	550.5	489.1	419.2	346.7	277.0	219.4
120°	644.1	641.2	630.1	604.1	567.4	520.3	464.6	401.8	336.2	273.0	220.9
122.5°	612.0	608.5	596.2	572.8	540.1	496.5	444.8	388.0	327.7	270.4	223.5
125°	567.4	564.1	552.4	532.0	502.2	465.0	420.4	369.7	316.7	266.9	227.4
127.5°	530.5	527.5	517.0	499.5	473.0	439.2	398.9	353.7	307.0	265.2	231.9
130°	509.6	506.0	496.2	479.5	454.8	423.1	385.5	343.6	301.8	264.2	234.8
132.5°	489.2	486.6	477.9	461.2	438.1	407.9	372.8	334.4	296.9	263.7	237.1
135°	459.9	456.6	448.3	434.3	411.6	385.1	354.8	321.8	290.7	263.2	240.4
137.5°	428.9	426.8	419.7	405.6	386.5	363.5	337.5	310.4	285.2	262.2	242.6
140°	407.3	407.8	400.4	387.3	369.7	349.7	327.3	303.7	281.8	261.8	244.1
142.5°	387.3	387.8	381.1	369.5	354.4	337.0	317.7	297.3	278.8	261.1	245.2
145°	359.5	358.6	354.8	345.0	333.5	319.9	305.1	289.7	274.8	259.9	246.0
147.5°	336.6	336.2	332.6	326.0	317.2	307.7	295.6	283.5	270.9	258.2	246.0
150°	323.2	323.2	320.4	315.3	308.3	299.5	289.7	279.0	268.3	256.7	246.0
152.5°	312.0	312.0	310.4	305.6	300.1	292.8	284.1	274.9	265.4	254.9	244.9
155°	298.1	297.6	296.7	292.9	288.8	283.2	276.2	268.8	260.9	251.6	243.7
157.5°	285.4	285.4	284.7	281.9	278.3	273.9	268.5	262.3	255.8	248.7	242.1
160°	277.1	277.6	277.6	274.8	271.6	268.3	263.7	258.5	252.5	246.5	241.3
162.5°	269.7	270.2	270.2	267.7	265.6	262.8	258.4	254.1	249.2	244.3	239.9
165°	259.9	259.9	260.4	258.5	256.7	254.4	251.1	248.3	244.6	240.9	237.7
167.5°	250.6	250.6	251.1	249.8	249.0	247.3	245.4	243.3	240.3	237.5	235.4
170°	245.1	245.1	245.6	244.6	244.1	243.2	241.3	239.9	237.7	235.3	233.9
172.5°	239.9	240.3	241.1	240.1	240.0	239.5	238.0	237.0	235.1	233.4	232.8
175°	233.9	234.4	234.8	234.4	234.4	234.4	233.4	233.0	232.0	231.1	231.1
177.5°	230.5	230.5	231.2	230.8	231.2	231.2	230.8	230.5	230.1	229.8	230.1
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8



TEST NUMBER: P332308-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1029.6	1028.5	1023.8	1018.3	1011.1	1006.3	1002.6	1000.5	994.4	986.8	981.8
5°	1093.2	1080.4	1066.7	1050.0	1034.7	1018.9	1009.1	997.5	983.5	967.7	956.6
7.5°	1161.3	1136.2	1109.1	1081.2	1053.6	1028.9	1007.1	988.3	965.9	943.2	927.4
10°	1213.6	1176.8	1138.8	1100.0	1064.5	1031.3	1005.7	980.5	953.6	927.6	907.9
12.5°	1261.0	1212.7	1168.9	1121.2	1075.9	1036.1	999.1	969.6	937.2	909.5	887.0
15°	1321.1	1271.6	1218.6	1146.1	1085.9	1035.5	990.8	951.9	912.6	878.5	856.7
17.5°	1377.3	1302.8	1231.7	1171.1	1092.9	1030.0	975.3	928.8	885.7	849.5	822.7
20°	1400.5	1328.4	1251.1	1173.9	1097.0	1026.5	963.0	911.7	866.9	826.0	801.2
22.5°	1414.5	1332.8	1251.4	1168.4	1086.8	1013.6	950.7	894.3	845.8	806.8	776.2
25°	1430.8	1333.5	1243.8	1161.9	1078.6	999.2	924.5	864.8	812.3	770.9	738.4
27.5°	1441.5	1327.1	1221.2	1130.0	1045.6	966.5	898.1	834.8	781.5	737.7	702.9
30°	1443.6	1321.9	1203.7	1105.1	1019.3	946.7	874.2	813.6	757.2	710.7	678.2
32.5°	1446.3	1309.3	1180.1	1075.4	987.6	915.7	849.9	792.1	734.3	688.5	655.4
35°	1435.1	1302.4	1144.4	1024.0	936.0	866.5	807.1	753.8	697.1	652.6	618.9
37.5°	1386.6	1274.6	1107.3	966.1	874.2	809.8	761.4	714.9	662.8	614.9	583.2
40°	1337.7	1247.2	1078.6	931.0	834.9	768.7	725.2	687.2	636.8	592.1	557.9
42.5°	1265.0	1210.1	1051.3	894.1	790.5	726.8	690.1	654.4	610.3	564.8	532.6
45°	1131.6	1138.8	995.4	835.4	729.0	665.0	630.5	605.7	566.5	528.9	496.0
47.5°	964.3	1032.1	929.8	772.7	664.2	604.1	574.0	552.4	525.9	489.0	459.0
50°	855.0	951.9	877.2	730.8	623.6	563.9	534.0	516.5	493.4	464.4	435.8
52.5°	754.2	858.3	813.7	684.0	579.6	525.0	495.8	481.4	463.0	435.7	409.9
55°	615.1	720.6	710.3	613.3	513.5	464.4	442.2	426.0	413.6	393.1	372.7
57.5°	497.6	597.5	602.8	534.8	455.3	406.8	387.7	375.4	367.4	351.9	333.0
60°	423.5	515.2	533.1	481.9	413.6	371.0	352.1	342.3	335.9	323.6	309.1
62.5°	362.0	440.1	460.4	423.5	373.7	333.7	319.0	309.6	305.2	294.5	281.7
65°	277.0	341.9	361.5	341.0	315.0	283.0	271.1	262.9	259.1	253.2	243.7
67.5°	208.3	255.6	277.1	262.7	253.3	233.1	225.4	221.1	217.7	213.6	205.8
70°	167.3	202.4	224.5	220.7	213.0	202.4	196.8	193.8	190.4	186.9	180.1
72.5°	134.5	158.7	179.4	181.4	175.1	172.9	168.1	166.8	164.8	160.7	156.9
75°	89.2	105.8	120.3	125.9	128.5	130.6	128.5	128.1	127.6	124.3	122.1
77.5°	58.5	67.4	76.6	86.0	90.1	92.9	93.7	95.2	94.1	92.3	91.2
80°	44.8	47.0	53.3	61.5	67.8	70.4	72.2	73.0	72.6	72.2	70.4
82.5°	32.5	34.3	37.3	43.0	48.4	52.7	53.7	53.6	54.5	54.7	53.3
85°	17.5	17.9	18.8	19.6	22.6	27.3	28.6	29.4	30.3	30.3	27.7
87.5°	7.3	6.6	7.0	6.8	7.7	7.7	9.6	11.1	11.7	10.4	10.8
90°	8.8	7.4	6.0	5.1	4.2	2.8	1.9	0.9	1.9	2.8	4.2
92.5°	59.0	39.1	26.9	20.0	16.1	12.5	8.6	5.8	8.6	12.5	16.1
95°	169.3	100.0	60.4	42.3	30.2	22.3	17.2	15.8	17.2	22.3	30.2
97.5°	185.7	107.6	69.9	50.2	38.3	31.5	27.5	27.0	27.5	31.5	38.3
100°	175.3	106.5	73.9	55.8	44.7	38.2	34.9	34.4	34.9	38.2	44.7
102.5°	166.4	107.9	78.8	62.1	52.1	46.0	43.0	42.2	43.0	46.0	52.1
105°	160.0	112.1	87.0	72.6	63.7	58.1	55.4	54.0	55.4	58.1	63.7
107.5°	159.5	119.7	97.7	84.3	76.0	70.5	67.8	66.4	67.8	70.5	76.0
110°	161.3	126.0	105.1	92.0	84.1	79.1	76.7	75.3	76.7	79.1	84.1



TEST NUMBER: P332308-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	165.1	132.3	112.9	100.3	92.4	87.2	85.0	83.5	85.0	87.2	92.4
115°	171.1	142.8	125.1	112.5	104.6	100.0	97.2	95.3	97.2	100.0	104.6
117.5°	179.1	153.8	136.3	124.7	115.9	111.6	109.3	107.1	109.3	111.6	115.9
120°	185.1	160.9	144.1	132.6	123.7	119.0	116.8	115.4	116.8	119.0	123.7
122.5°	190.7	168.4	152.0	139.6	131.1	126.1	123.8	122.4	123.8	126.1	131.1
125°	199.5	179.0	162.7	150.2	141.4	136.2	133.5	132.6	133.5	136.2	141.4
127.5°	206.8	188.3	172.6	160.0	150.3	145.1	141.6	140.2	141.6	145.1	150.3
130°	211.6	193.9	178.6	166.0	156.2	150.7	146.5	145.1	146.5	150.7	156.2
132.5°	216.1	198.8	183.8	171.6	161.8	155.2	150.6	148.8	150.6	155.2	161.8
135°	221.8	206.0	191.6	179.0	169.3	162.3	157.2	155.3	157.2	162.3	169.3
137.5°	226.1	211.0	197.1	185.6	175.9	168.4	163.4	161.4	163.4	168.4	175.9
140°	228.4	214.3	200.9	189.2	179.9	172.5	167.9	165.6	167.9	172.5	179.9
142.5°	230.6	217.0	203.9	193.0	183.7	177.0	171.9	170.0	171.9	177.0	183.7
145°	233.0	220.5	208.3	197.6	189.7	182.8	178.6	177.2	178.6	182.8	189.7
147.5°	234.5	223.2	212.1	203.0	195.4	189.4	185.2	184.4	185.2	189.4	195.4
150°	234.8	225.1	214.3	206.0	199.5	193.5	189.7	189.2	189.7	193.5	199.5
152.5°	235.6	226.2	217.0	209.0	203.3	198.0	194.2	194.1	194.2	198.0	203.3
155°	235.8	228.4	220.5	213.9	208.8	204.2	201.4	201.4	201.4	204.2	208.8
157.5°	236.3	229.5	223.2	218.2	213.9	209.7	207.5	207.1	207.5	209.7	213.9
160°	236.3	230.6	225.1	220.5	217.2	213.4	211.6	211.6	211.6	213.4	217.2
162.5°	235.9	231.1	226.2	222.3	219.4	216.5	214.9	214.9	214.9	216.5	219.4
165°	234.8	231.5	227.9	224.6	222.7	220.5	219.5	220.0	219.5	220.5	222.7
167.5°	234.1	231.5	228.8	226.7	225.4	223.6	223.2	223.8	223.2	223.6	225.4
170°	233.0	231.1	228.8	227.9	226.9	225.5	225.1	226.0	225.1	225.5	226.9
172.5°	232.6	231.1	229.2	228.6	228.0	227.1	226.9	227.5	226.9	227.1	228.0
175°	231.5	230.6	229.8	229.3	229.3	228.4	228.8	229.3	228.8	228.4	229.3
177.5°	230.8	230.1	229.8	229.8	229.8	229.3	229.8	230.1	229.8	229.3	229.8
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8



TEST NUMBER: P332308-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	980.1	975.6	972.6	965.7	961.2	956.5	951.7	954.8	954.5	954.1	954.1
5°	947.2	937.3	928.4	916.9	909.6	900.7	893.8	893.0	894.7	888.7	885.3
7.5°	914.6	901.2	888.4	875.7	862.3	851.5	844.7	841.6	837.2	833.6	829.7
10°	891.7	875.9	863.5	847.7	833.2	820.4	812.3	806.7	803.7	800.8	795.2
12.5°	868.1	852.6	836.9	819.0	805.2	790.4	784.3	778.0	772.3	769.0	761.4
15°	833.6	813.6	797.0	778.1	762.8	748.3	739.7	727.3	725.6	721.4	713.7
17.5°	799.1	777.3	754.3	740.5	723.1	708.0	695.0	690.8	678.6	674.0	667.3
20°	771.8	751.7	734.2	715.8	690.6	676.5	666.3	660.8	650.9	645.0	640.7
22.5°	748.2	727.8	707.5	686.2	665.4	649.5	642.0	633.4	628.1	619.7	615.1
25°	714.5	692.4	668.1	645.0	630.1	618.1	606.1	598.4	590.8	586.9	578.4
27.5°	675.5	652.2	629.5	612.0	593.7	581.9	571.0	564.2	555.0	548.5	543.8
30°	654.0	626.6	607.0	591.2	567.7	556.6	548.5	540.0	533.1	526.3	521.6
32.5°	629.0	604.1	585.5	565.9	547.9	535.8	525.3	517.8	511.9	505.5	500.8
35°	589.9	569.0	549.8	530.1	516.9	504.5	492.2	485.8	480.2	474.3	469.9
37.5°	554.6	535.0	516.7	498.1	481.8	471.7	461.7	456.8	449.3	445.3	440.9
40°	532.7	513.5	493.8	476.0	458.9	451.2	442.2	435.0	428.1	425.2	420.4
42.5°	508.8	489.6	473.0	453.7	439.8	429.3	421.0	413.1	408.0	403.7	401.0
45°	473.4	456.3	440.1	420.9	407.6	398.7	389.3	382.0	377.3	374.4	369.7
47.5°	439.0	421.9	405.4	388.7	375.9	365.7	356.3	351.2	345.0	341.3	338.2
50°	414.0	398.7	381.2	365.8	353.0	342.8	335.1	328.6	323.1	318.5	316.3
52.5°	391.2	374.8	359.6	345.4	331.8	320.2	313.2	306.5	302.3	296.9	294.4
55°	353.4	337.6	324.8	310.7	297.5	287.7	279.2	273.2	268.9	262.9	259.5
57.5°	318.0	303.9	288.5	276.3	262.7	254.4	247.3	239.2	234.0	229.3	226.0
60°	294.1	277.9	264.6	253.2	241.2	230.5	224.1	217.7	212.1	207.4	204.5
62.5°	269.2	255.0	242.5	229.9	219.0	209.7	202.3	196.9	192.0	189.0	186.1
65°	230.9	219.8	207.0	196.8	186.5	179.7	173.7	169.0	165.6	163.5	160.9
67.5°	195.8	185.0	173.8	163.7	156.9	151.7	147.8	143.7	142.0	139.3	137.6
70°	172.8	161.8	152.0	144.3	137.5	133.6	131.0	128.1	126.4	122.9	121.2
72.5°	148.0	139.9	132.8	126.5	121.1	117.6	114.3	110.6	107.9	104.1	102.5
75°	116.5	109.3	103.7	99.5	96.0	91.3	86.7	82.8	81.5	80.2	79.8
77.5°	86.3	81.7	77.7	74.1	69.9	66.4	65.4	64.6	64.2	63.6	63.6
80°	67.8	63.6	60.6	56.3	53.8	53.8	53.8	52.9	53.3	53.3	53.3
82.5°	50.5	46.6	44.9	43.4	42.9	43.2	43.2	43.4	43.1	43.8	43.5
85°	26.0	26.5	27.3	26.9	27.3	27.3	28.2	27.7	28.2	27.3	28.2
87.5°	10.6	11.8	12.4	13.0	13.7	13.6	13.9	13.9	14.3	14.4	14.7
90°	5.1	6.0	7.4	8.8	10.2	11.7	11.2	11.7	12.1	12.6	13.5
92.5°	20.0	26.9	39.1	59.0	78.7	71.5	54.0	39.1	31.1	27.5	25.0
95°	42.3	60.4	100.0	169.3	245.6	275.7	223.6	167.4	113.5	88.8	72.1
97.5°	50.2	69.9	107.6	185.7	312.8	427.4	457.2	417.4	334.3	274.3	218.7
100°	55.8	73.9	106.5	175.3	297.6	440.3	532.0	548.3	510.6	456.2	390.1
102.5°	62.1	78.8	107.9	166.4	275.3	416.2	535.7	591.8	590.6	558.9	517.0
105°	72.6	87.0	112.1	160.0	247.9	373.9	507.4	604.5	651.0	659.9	647.8
107.5°	84.3	97.7	119.7	159.5	230.4	336.5	457.7	567.9	643.4	684.1	700.7
110°	92.0	105.1	126.0	161.3	223.6	315.3	426.4	532.9	618.5	677.1	709.6



TEST NUMBER: P332308-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	100.3	112.9	132.3	165.1	220.0	301.2	399.3	498.3	585.7	651.4	693.2
115°	112.5	125.1	142.8	171.1	218.6	286.0	366.5	452.5	533.4	601.8	652.4
117.5°	124.7	136.3	153.8	179.1	219.4	277.0	346.7	419.2	489.1	550.5	601.9
120°	132.6	144.1	160.9	185.1	220.9	273.0	336.2	401.8	464.6	520.3	567.4
122.5°	139.6	152.0	168.4	190.7	223.5	270.4	327.7	388.0	444.8	496.5	540.1
125°	150.2	162.7	179.0	199.5	227.4	266.9	316.7	369.7	420.4	465.0	502.2
127.5°	160.0	172.6	188.3	206.8	231.9	265.2	307.0	353.7	398.9	439.2	473.0
130°	166.0	178.6	193.9	211.6	234.8	264.2	301.8	343.6	385.5	423.1	454.8
132.5°	171.6	183.8	198.8	216.1	237.1	263.7	296.9	334.4	372.8	407.9	438.1
135°	179.0	191.6	206.0	221.8	240.4	263.2	290.7	321.8	354.8	385.1	411.6
137.5°	185.6	197.1	211.0	226.1	242.6	262.2	285.2	310.4	337.5	363.5	386.5
140°	189.2	200.9	214.3	228.4	244.1	261.8	281.8	303.7	327.3	349.7	369.7
142.5°	193.0	203.9	217.0	230.6	245.2	261.1	278.8	297.3	317.7	337.0	354.4
145°	197.6	208.3	220.5	233.0	246.0	259.9	274.8	289.7	305.1	319.9	333.5
147.5°	203.0	212.1	223.2	234.5	246.0	258.2	270.9	283.5	295.6	307.7	317.2
150°	206.0	214.3	225.1	234.8	246.0	256.7	268.3	279.0	289.7	299.5	308.3
152.5°	209.0	217.0	226.2	235.6	244.9	254.9	265.4	274.9	284.1	292.8	300.1
155°	213.9	220.5	228.4	235.8	243.7	251.6	260.9	268.8	276.2	283.2	288.8
157.5°	218.2	223.2	229.5	236.3	242.1	248.7	255.8	262.3	268.5	273.9	278.3
160°	220.5	225.1	230.6	236.3	241.3	246.5	252.5	258.5	263.7	268.3	271.6
162.5°	222.3	226.2	231.1	235.9	239.9	244.3	249.2	254.1	258.4	262.8	265.6
165°	224.6	227.9	231.5	234.8	237.7	240.9	244.6	248.3	251.1	254.4	256.7
167.5°	226.7	228.8	231.5	234.1	235.4	237.5	240.3	243.3	245.4	247.3	249.0
170°	227.9	228.8	231.1	233.0	233.9	235.3	237.7	239.9	241.3	243.2	244.1
172.5°	228.6	229.2	231.1	232.6	232.8	233.4	235.1	237.0	238.0	239.5	240.0
175°	229.3	229.8	230.6	231.5	231.1	231.1	232.0	233.0	233.4	234.4	234.4
177.5°	229.8	229.8	230.1	230.8	230.1	229.8	230.1	230.5	230.8	231.2	231.2
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8



TEST NUMBER: P332308-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	950.0	949.7	950.0	948.6	950.0	949.7	950.0	954.1	954.1	954.5	954.8
5°	884.0	883.5	882.3	878.5	882.3	883.5	884.0	885.3	888.7	894.7	893.0
7.5°	826.4	825.8	822.1	822.1	822.1	825.8	826.4	829.7	833.6	837.2	841.6
10°	792.2	792.6	787.6	784.6	787.6	792.6	792.2	795.2	800.8	803.7	806.7
12.5°	759.1	757.2	753.0	749.7	753.0	757.2	759.1	761.4	769.0	772.3	778.0
15°	715.4	711.1	700.9	701.7	700.9	711.1	715.4	713.7	721.4	725.6	727.3
17.5°	663.9	660.8	660.6	654.6	660.6	660.8	663.9	667.3	674.0	678.6	690.8
20°	633.9	631.8	632.6	626.6	632.6	631.8	633.9	640.7	645.0	650.9	660.8
22.5°	610.3	608.2	604.6	602.8	604.6	608.2	610.3	615.1	619.7	628.1	633.4
25°	575.8	572.4	569.0	571.1	569.0	572.4	575.8	578.4	586.9	590.8	598.4
27.5°	541.4	538.7	535.3	534.9	535.3	538.7	541.4	543.8	548.5	555.0	564.2
30°	519.5	516.9	515.2	513.1	515.2	516.9	519.5	521.6	526.3	533.1	540.0
32.5°	497.3	496.8	493.7	493.3	493.7	496.8	497.3	500.8	505.5	511.9	517.8
35°	468.2	465.7	464.8	465.3	464.8	465.7	468.2	469.9	474.3	480.2	485.8
37.5°	440.7	437.2	435.7	434.2	435.7	437.2	440.7	440.9	445.3	449.3	456.8
40°	420.9	417.4	416.6	415.7	416.6	417.4	420.9	420.4	425.2	428.1	435.0
42.5°	398.7	397.3	396.8	395.3	396.8	397.3	398.7	401.0	403.7	408.0	413.1
45°	368.4	367.9	365.4	366.2	365.4	367.9	368.4	369.7	374.4	377.3	382.0
47.5°	336.5	334.6	332.8	333.9	332.8	334.6	336.5	338.2	341.3	345.0	351.2
50°	314.6	313.7	309.9	310.7	309.9	313.7	314.6	316.3	318.5	323.1	328.6
52.5°	292.8	289.5	288.0	287.6	288.0	289.5	292.8	294.4	296.9	302.3	306.5
55°	256.6	252.7	250.9	250.1	250.9	252.7	256.6	259.5	262.9	268.9	273.2
57.5°	221.0	220.0	218.7	219.6	218.7	220.0	221.0	226.0	229.3	234.0	239.2
60°	200.2	200.2	200.2	199.7	200.2	200.2	200.2	204.5	207.4	212.1	217.7
62.5°	184.2	183.1	182.8	183.4	182.8	183.1	184.2	186.1	189.0	192.0	196.9
65°	159.6	159.2	157.5	157.1	157.5	159.2	159.6	160.9	163.5	165.6	169.0
67.5°	136.5	134.9	134.4	133.9	134.4	134.9	136.5	137.6	139.3	142.0	143.7
70°	119.1	118.2	115.7	116.1	115.7	118.2	119.1	121.2	122.9	126.4	128.1
72.5°	100.3	99.5	99.0	98.3	99.0	99.5	100.3	102.5	104.1	107.9	110.6
75°	79.4	79.0	78.5	80.2	78.5	79.0	79.4	79.8	80.2	81.5	82.8
77.5°	63.6	63.6	63.8	63.2	63.8	63.6	63.6	63.6	63.6	64.2	64.6
80°	53.3	53.3	52.9	52.9	52.9	53.3	53.3	53.3	53.3	53.3	52.9
82.5°	42.8	43.1	43.4	42.7	43.4	43.1	42.8	43.5	43.8	43.1	43.4
85°	28.2	27.7	28.6	28.2	28.6	27.7	28.2	28.2	27.3	28.2	27.7
87.5°	15.2	14.7	14.8	15.0	14.8	14.7	15.2	14.7	14.4	14.3	13.9
90°	13.0	13.5	13.9	13.5	13.9	13.5	13.0	13.5	12.6	12.1	11.7
92.5°	24.2	22.7	23.2	22.4	23.2	22.7	24.2	25.0	27.5	31.1	39.1
95°	63.3	59.0	55.8	54.0	55.8	59.0	63.3	72.1	88.8	113.5	167.4
97.5°	184.3	163.4	150.8	146.8	150.8	163.4	184.3	218.7	274.3	334.3	417.4
100°	343.2	309.2	291.1	291.6	291.1	309.2	343.2	390.1	456.2	510.6	548.3
102.5°	480.5	453.6	438.4	427.7	438.4	453.6	480.5	517.0	558.9	590.6	591.8
105°	626.4	608.7	593.9	591.5	593.9	608.7	626.4	647.8	659.9	651.0	604.5
107.5°	701.1	695.1	690.1	685.8	690.1	695.1	701.1	700.7	684.1	643.4	567.9
110°	722.7	726.4	725.5	724.5	725.5	726.4	722.7	709.6	677.1	618.5	532.9



TEST NUMBER: P332308-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	717.1	728.6	732.1	732.3	732.1	728.6	717.1	693.2	651.4	585.7	498.3
115°	687.3	707.8	717.1	719.4	717.1	707.8	687.3	652.4	601.8	533.4	452.5
117.5°	638.3	661.7	675.1	678.2	675.1	661.7	638.3	601.9	550.5	489.1	419.2
120°	604.1	630.1	641.2	644.1	641.2	630.1	604.1	567.4	520.3	464.6	401.8
122.5°	572.8	596.2	608.5	612.0	608.5	596.2	572.8	540.1	496.5	444.8	388.0
125°	532.0	552.4	564.1	567.4	564.1	552.4	532.0	502.2	465.0	420.4	369.7
127.5°	499.5	517.0	527.5	530.5	527.5	517.0	499.5	473.0	439.2	398.9	353.7
130°	479.5	496.2	506.0	509.6	506.0	496.2	479.5	454.8	423.1	385.5	343.6
132.5°	461.2	477.9	486.6	489.2	486.6	477.9	461.2	438.1	407.9	372.8	334.4
135°	434.3	448.3	456.6	459.9	456.6	448.3	434.3	411.6	385.1	354.8	321.8
137.5°	405.6	419.7	426.8	428.9	426.8	419.7	405.6	386.5	363.5	337.5	310.4
140°	387.3	400.4	407.8	407.3	407.8	400.4	387.3	369.7	349.7	327.3	303.7
142.5°	369.5	381.1	387.8	387.3	387.8	381.1	369.5	354.4	337.0	317.7	297.3
145°	345.0	354.8	358.6	359.5	358.6	354.8	345.0	333.5	319.9	305.1	289.7
147.5°	326.0	332.6	336.2	336.6	336.2	332.6	326.0	317.2	307.7	295.6	283.5
150°	315.3	320.4	323.2	323.2	323.2	320.4	315.3	308.3	299.5	289.7	279.0
152.5°	305.6	310.4	312.0	312.0	312.0	310.4	305.6	300.1	292.8	284.1	274.9
155°	292.9	296.7	297.6	298.1	297.6	296.7	292.9	288.8	283.2	276.2	268.8
157.5°	281.9	284.7	285.4	285.4	285.4	284.7	281.9	278.3	273.9	268.5	262.3
160°	274.8	277.6	277.6	277.1	277.6	277.6	274.8	271.6	268.3	263.7	258.5
162.5°	267.7	270.2	270.2	269.7	270.2	270.2	267.7	265.6	262.8	258.4	254.1
165°	258.5	260.4	259.9	259.9	259.9	260.4	258.5	256.7	254.4	251.1	248.3
167.5°	249.8	251.1	250.6	250.6	250.6	251.1	249.8	249.0	247.3	245.4	243.3
170°	244.6	245.6	245.1	245.1	245.1	245.6	244.6	244.1	243.2	241.3	239.9
172.5°	240.1	241.1	240.3	239.9	240.3	241.1	240.1	240.0	239.5	238.0	237.0
175°	234.4	234.8	234.4	233.9	234.4	234.8	234.4	234.4	234.4	233.4	233.0
177.5°	230.8	231.2	230.5	230.5	230.5	231.2	230.8	231.2	231.2	230.8	230.5
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8



TEST NUMBER: P332308-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	951.7	956.5	961.2	965.7	972.6	975.6	980.1	981.8	986.8	994.4	1000.5
5°	893.8	900.7	909.6	916.9	928.4	937.3	947.2	956.6	967.7	983.5	997.5
7.5°	844.7	851.5	862.3	875.7	888.4	901.2	914.6	927.4	943.2	965.9	988.3
10°	812.3	820.4	833.2	847.7	863.5	875.9	891.7	907.9	927.6	953.6	980.5
12.5°	784.3	790.4	805.2	819.0	836.9	852.6	868.1	887.0	909.5	937.2	969.6
15°	739.7	748.3	762.8	778.1	797.0	813.6	833.6	856.7	878.5	912.6	951.9
17.5°	695.0	708.0	723.1	740.5	754.3	777.3	799.1	822.7	849.5	885.7	928.8
20°	666.3	676.5	690.6	715.8	734.2	751.7	771.8	801.2	826.0	866.9	911.7
22.5°	642.0	649.5	665.4	686.2	707.5	727.8	748.2	776.2	806.8	845.8	894.3
25°	606.1	618.1	630.1	645.0	668.1	692.4	714.5	738.4	770.9	812.3	864.8
27.5°	571.0	581.9	593.7	612.0	629.5	652.2	675.5	702.9	737.7	781.5	834.8
30°	548.5	556.6	567.7	591.2	607.0	626.6	654.0	678.2	710.7	757.2	813.6
32.5°	525.3	535.8	547.9	565.9	585.5	604.1	629.0	655.4	688.5	734.3	792.1
35°	492.2	504.5	516.9	530.1	549.8	569.0	589.9	618.9	652.6	697.1	753.8
37.5°	461.7	471.7	481.8	498.1	516.7	535.0	554.6	583.2	614.9	662.8	714.9
40°	442.2	451.2	458.9	476.0	493.8	513.5	532.7	557.9	592.1	636.8	687.2
42.5°	421.0	429.3	439.8	453.7	473.0	489.6	508.8	532.6	564.8	610.3	654.4
45°	389.3	398.7	407.6	420.9	440.1	456.3	473.4	496.0	528.9	566.5	605.7
47.5°	356.3	365.7	375.9	388.7	405.4	421.9	439.0	459.0	489.0	525.9	552.4
50°	335.1	342.8	353.0	365.8	381.2	398.7	414.0	435.8	464.4	493.4	516.5
52.5°	313.2	320.2	331.8	345.4	359.6	374.8	391.2	409.9	435.7	463.0	481.4
55°	279.2	287.7	297.5	310.7	324.8	337.6	353.4	372.7	393.1	413.6	426.0
57.5°	247.3	254.4	262.7	276.3	288.5	303.9	318.0	333.0	351.9	367.4	375.4
60°	224.1	230.5	241.2	253.2	264.6	277.9	294.1	309.1	323.6	335.9	342.3
62.5°	202.3	209.7	219.0	229.9	242.5	255.0	269.2	281.7	294.5	305.2	309.6
65°	173.7	179.7	186.5	196.8	207.0	219.8	230.9	243.7	253.2	259.1	262.9
67.5°	147.8	151.7	156.9	163.7	173.8	185.0	195.8	205.8	213.6	217.7	221.1
70°	131.0	133.6	137.5	144.3	152.0	161.8	172.8	180.1	186.9	190.4	193.8
72.5°	114.3	117.6	121.1	126.5	132.8	139.9	148.0	156.9	160.7	164.8	166.8
75°	86.7	91.3	96.0	99.5	103.7	109.3	116.5	122.1	124.3	127.6	128.1
77.5°	65.4	66.4	69.9	74.1	77.7	81.7	86.3	91.2	92.3	94.1	95.2
80°	53.8	53.8	53.8	56.3	60.6	63.6	67.8	70.4	72.2	72.6	73.0
82.5°	43.2	43.2	42.9	43.4	44.9	46.6	50.5	53.3	54.7	54.5	53.6
85°	28.2	27.3	27.3	26.9	27.3	26.5	26.0	27.7	30.3	30.3	29.4
87.5°	13.9	13.6	13.7	13.0	12.4	11.8	10.6	10.8	10.4	11.7	11.1
90°	11.2	11.7	10.2	8.8	7.4	6.0	5.1	4.2	2.8	1.9	0.9
92.5°	54.0	71.5	78.7	59.0	39.1	26.9	20.0	16.1	12.5	8.6	5.8
95°	223.6	275.7	245.6	169.3	100.0	60.4	42.3	30.2	22.3	17.2	15.8
97.5°	457.2	427.4	312.8	185.7	107.6	69.9	50.2	38.3	31.5	27.5	27.0
100°	532.0	440.3	297.6	175.3	106.5	73.9	55.8	44.7	38.2	34.9	34.4
102.5°	535.7	416.2	275.3	166.4	107.9	78.8	62.1	52.1	46.0	43.0	42.2
105°	507.4	373.9	247.9	160.0	112.1	87.0	72.6	63.7	58.1	55.4	54.0
107.5°	457.7	336.5	230.4	159.5	119.7	97.7	84.3	76.0	70.5	67.8	66.4
110°	426.4	315.3	223.6	161.3	126.0	105.1	92.0	84.1	79.1	76.7	75.3



TEST NUMBER: P332308-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	399.3	301.2	220.0	165.1	132.3	112.9	100.3	92.4	87.2	85.0	83.5
115°	366.5	286.0	218.6	171.1	142.8	125.1	112.5	104.6	100.0	97.2	95.3
117.5°	346.7	277.0	219.4	179.1	153.8	136.3	124.7	115.9	111.6	109.3	107.1
120°	336.2	273.0	220.9	185.1	160.9	144.1	132.6	123.7	119.0	116.8	115.4
122.5°	327.7	270.4	223.5	190.7	168.4	152.0	139.6	131.1	126.1	123.8	122.4
125°	316.7	266.9	227.4	199.5	179.0	162.7	150.2	141.4	136.2	133.5	132.6
127.5°	307.0	265.2	231.9	206.8	188.3	172.6	160.0	150.3	145.1	141.6	140.2
130°	301.8	264.2	234.8	211.6	193.9	178.6	166.0	156.2	150.7	146.5	145.1
132.5°	296.9	263.7	237.1	216.1	198.8	183.8	171.6	161.8	155.2	150.6	148.8
135°	290.7	263.2	240.4	221.8	206.0	191.6	179.0	169.3	162.3	157.2	155.3
137.5°	285.2	262.2	242.6	226.1	211.0	197.1	185.6	175.9	168.4	163.4	161.4
140°	281.8	261.8	244.1	228.4	214.3	200.9	189.2	179.9	172.5	167.9	165.6
142.5°	278.8	261.1	245.2	230.6	217.0	203.9	193.0	183.7	177.0	171.9	170.0
145°	274.8	259.9	246.0	233.0	220.5	208.3	197.6	189.7	182.8	178.6	177.2
147.5°	270.9	258.2	246.0	234.5	223.2	212.1	203.0	195.4	189.4	185.2	184.4
150°	268.3	256.7	246.0	234.8	225.1	214.3	206.0	199.5	193.5	189.7	189.2
152.5°	265.4	254.9	244.9	235.6	226.2	217.0	209.0	203.3	198.0	194.2	194.1
155°	260.9	251.6	243.7	235.8	228.4	220.5	213.9	208.8	204.2	201.4	201.4
157.5°	255.8	248.7	242.1	236.3	229.5	223.2	218.2	213.9	209.7	207.5	207.1
160°	252.5	246.5	241.3	236.3	230.6	225.1	220.5	217.2	213.4	211.6	211.6
162.5°	249.2	244.3	239.9	235.9	231.1	226.2	222.3	219.4	216.5	214.9	214.9
165°	244.6	240.9	237.7	234.8	231.5	227.9	224.6	222.7	220.5	219.5	220.0
167.5°	240.3	237.5	235.4	234.1	231.5	228.8	226.7	225.4	223.6	223.2	223.8
170°	237.7	235.3	233.9	233.0	231.1	228.8	227.9	226.9	225.5	225.1	226.0
172.5°	235.1	233.4	232.8	232.6	231.1	229.2	228.6	228.0	227.1	226.9	227.5
175°	232.0	231.1	231.1	231.5	230.6	229.8	229.3	229.3	228.4	228.8	229.3
177.5°	230.1	229.8	230.1	230.8	230.1	229.8	229.8	229.8	229.3	229.8	230.1
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8



TEST NUMBER: P332308-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1002.6	1006.3	1011.1	1018.3	1023.8	1028.5	1029.6	1030.9	1034.4	1040.2	1044.6
5°	1009.1	1018.9	1034.7	1050.0	1066.7	1080.4	1093.2	1102.1	1110.7	1128.6	1143.1
7.5°	1007.1	1028.9	1053.6	1081.2	1109.1	1136.2	1161.3	1183.7	1206.1	1232.2	1262.0
10°	1005.7	1031.3	1064.5	1100.0	1138.8	1176.8	1213.6	1242.1	1275.5	1305.3	1343.3
12.5°	999.1	1036.1	1075.9	1121.2	1168.9	1212.7	1261.0	1300.6	1338.6	1381.8	1426.0
15°	990.8	1035.5	1085.9	1146.1	1218.6	1271.6	1321.1	1389.8	1436.8	1483.8	1546.9
17.5°	975.3	1030.0	1092.9	1171.1	1231.7	1302.8	1377.3	1431.6	1494.9	1561.0	1618.2
20°	963.0	1026.5	1097.0	1173.9	1251.1	1328.4	1400.5	1465.3	1530.7	1607.1	1654.1
22.5°	950.7	1013.6	1086.8	1168.4	1251.4	1332.8	1414.5	1490.6	1564.2	1641.3	1701.2
25°	924.5	999.2	1078.6	1161.9	1243.8	1333.5	1430.8	1515.7	1606.6	1686.0	1742.9
27.5°	898.1	966.5	1045.6	1130.0	1221.2	1327.1	1441.5	1538.1	1629.2	1686.0	1703.9
30°	874.2	946.7	1019.3	1105.1	1203.7	1321.9	1443.6	1554.1	1628.9	1653.6	1635.2
32.5°	849.9	915.7	987.6	1075.4	1180.1	1309.3	1446.3	1544.6	1589.6	1570.7	1495.9
35°	807.1	866.5	936.0	1024.0	1144.4	1302.4	1435.1	1501.6	1490.5	1383.8	1243.0
37.5°	761.4	809.8	874.2	966.1	1107.3	1274.6	1386.6	1396.4	1300.3	1136.5	973.8
40°	725.2	768.7	834.9	931.0	1078.6	1247.2	1337.7	1298.0	1149.1	966.8	831.1
42.5°	690.1	726.8	790.5	894.1	1051.3	1210.1	1265.0	1178.5	1006.7	834.3	710.9
45°	630.5	665.0	729.0	835.4	995.4	1138.8	1131.6	981.3	809.3	670.6	568.1
47.5°	574.0	604.1	664.2	772.7	929.8	1032.1	964.3	804.4	658.4	547.1	474.1
50°	534.0	563.9	623.6	730.8	877.2	951.9	855.0	700.9	567.3	475.1	417.0
52.5°	495.8	525.0	579.6	684.0	813.7	858.3	754.2	611.4	500.0	420.4	370.6
55°	442.2	464.4	513.5	613.3	710.3	720.6	615.1	495.5	403.8	348.3	314.1
57.5°	387.7	406.8	455.3	534.8	602.8	597.5	497.6	394.1	332.3	291.1	266.4
60°	352.1	371.0	413.6	481.9	533.1	515.2	423.5	340.2	287.2	257.0	237.3
62.5°	319.0	333.7	373.7	423.5	460.4	440.1	362.0	293.1	251.1	225.5	210.0
65°	271.1	283.0	315.0	341.0	361.5	341.9	277.0	229.2	198.9	181.0	170.3
67.5°	225.4	233.1	253.3	262.7	277.1	255.6	208.3	176.3	159.1	143.9	136.5
70°	196.8	202.4	213.0	220.7	224.5	202.4	167.3	143.8	129.3	118.6	114.0
72.5°	168.1	172.9	175.1	181.4	179.4	158.7	134.5	115.9	105.4	98.2	92.1
75°	128.5	130.6	128.5	125.9	120.3	105.8	89.2	79.8	72.2	68.7	66.6
77.5°	93.7	92.9	90.1	86.0	76.6	67.4	58.5	55.4	52.0	50.2	49.4
80°	72.2	70.4	67.8	61.5	53.3	47.0	44.8	42.7	41.4	39.3	38.8
82.5°	53.7	52.7	48.4	43.0	37.3	34.3	32.5	31.8	30.5	29.4	29.3
85°	28.6	27.3	22.6	19.6	18.8	17.9	17.5	17.5	15.8	15.3	15.3
87.5°	9.6	7.7	7.7	6.8	7.0	6.6	7.3	6.8	6.8	7.0	6.4
90°	1.9	2.8	4.2	5.1	6.0	7.4	8.8	10.2	11.7	11.2	11.7
92.5°	8.6	12.5	16.1	20.0	26.9	39.1	59.0	78.7	71.5	54.0	39.1
95°	17.2	22.3	30.2	42.3	60.4	100.0	169.3	245.6	275.7	223.6	167.4
97.5°	27.5	31.5	38.3	50.2	69.9	107.6	185.7	312.8	427.4	457.2	417.4
100°	34.9	38.2	44.7	55.8	73.9	106.5	175.3	297.6	440.3	532.0	548.3
102.5°	43.0	46.0	52.1	62.1	78.8	107.9	166.4	275.3	416.2	535.7	591.8
105°	55.4	58.1	63.7	72.6	87.0	112.1	160.0	247.9	373.9	507.4	604.5
107.5°	67.8	70.5	76.0	84.3	97.7	119.7	159.5	230.4	336.5	457.7	567.9
110°	76.7	79.1	84.1	92.0	105.1	126.0	161.3	223.6	315.3	426.4	532.9



TEST NUMBER: P332308-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	85.0	87.2	92.4	100.3	112.9	132.3	165.1	220.0	301.2	399.3	498.3
115°	97.2	100.0	104.6	112.5	125.1	142.8	171.1	218.6	286.0	366.5	452.5
117.5°	109.3	111.6	115.9	124.7	136.3	153.8	179.1	219.4	277.0	346.7	419.2
120°	116.8	119.0	123.7	132.6	144.1	160.9	185.1	220.9	273.0	336.2	401.8
122.5°	123.8	126.1	131.1	139.6	152.0	168.4	190.7	223.5	270.4	327.7	388.0
125°	133.5	136.2	141.4	150.2	162.7	179.0	199.5	227.4	266.9	316.7	369.7
127.5°	141.6	145.1	150.3	160.0	172.6	188.3	206.8	231.9	265.2	307.0	353.7
130°	146.5	150.7	156.2	166.0	178.6	193.9	211.6	234.8	264.2	301.8	343.6
132.5°	150.6	155.2	161.8	171.6	183.8	198.8	216.1	237.1	263.7	296.9	334.4
135°	157.2	162.3	169.3	179.0	191.6	206.0	221.8	240.4	263.2	290.7	321.8
137.5°	163.4	168.4	175.9	185.6	197.1	211.0	226.1	242.6	262.2	285.2	310.4
140°	167.9	172.5	179.9	189.2	200.9	214.3	228.4	244.1	261.8	281.8	303.7
142.5°	171.9	177.0	183.7	193.0	203.9	217.0	230.6	245.2	261.1	278.8	297.3
145°	178.6	182.8	189.7	197.6	208.3	220.5	233.0	246.0	259.9	274.8	289.7
147.5°	185.2	189.4	195.4	203.0	212.1	223.2	234.5	246.0	258.2	270.9	283.5
150°	189.7	193.5	199.5	206.0	214.3	225.1	234.8	246.0	256.7	268.3	279.0
152.5°	194.2	198.0	203.3	209.0	217.0	226.2	235.6	244.9	254.9	265.4	274.9
155°	201.4	204.2	208.8	213.9	220.5	228.4	235.8	243.7	251.6	260.9	268.8
157.5°	207.5	209.7	213.9	218.2	223.2	229.5	236.3	242.1	248.7	255.8	262.3
160°	211.6	213.4	217.2	220.5	225.1	230.6	236.3	241.3	246.5	252.5	258.5
162.5°	214.9	216.5	219.4	222.3	226.2	231.1	235.9	239.9	244.3	249.2	254.1
165°	219.5	220.5	222.7	224.6	227.9	231.5	234.8	237.7	240.9	244.6	248.3
167.5°	223.2	223.6	225.4	226.7	228.8	231.5	234.1	235.4	237.5	240.3	243.3
170°	225.1	225.5	226.9	227.9	228.8	231.1	233.0	233.9	235.3	237.7	239.9
172.5°	226.9	227.1	228.0	228.6	229.2	231.1	232.6	232.8	233.4	235.1	237.0
175°	228.8	228.4	229.3	229.3	229.8	230.6	231.5	231.1	231.1	232.0	233.0
177.5°	229.8	229.3	229.8	229.8	229.8	230.1	230.8	230.1	229.8	230.1	230.5
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8



TEST NUMBER: P332308-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1051.7	1051.7	1053.1	1058.3	1058.9	1063.4	1062.0
5°	1155.9	1164.0	1167.0	1179.8	1187.5	1190.9	1184.1
7.5°	1283.3	1306.2	1317.0	1330.4	1342.3	1345.9	1336.5
10°	1376.1	1400.0	1420.2	1432.5	1444.1	1451.7	1461.5
12.5°	1466.0	1495.3	1514.4	1531.9	1543.8	1553.5	1555.1
15°	1563.6	1607.9	1641.7	1666.4	1678.8	1685.2	1682.6
17.5°	1662.0	1703.2	1727.1	1752.4	1769.5	1770.4	1770.9
20°	1717.7	1757.8	1785.5	1804.3	1823.5	1822.7	1826.9
22.5°	1754.9	1786.5	1807.7	1821.4	1828.0	1824.7	1825.5
25°	1772.3	1781.7	1777.8	1756.1	1750.5	1730.5	1733.9
27.5°	1682.5	1638.1	1592.1	1533.1	1486.5	1449.3	1451.2
30°	1560.6	1482.1	1392.4	1317.3	1249.9	1231.0	1190.9
32.5°	1390.2	1272.4	1167.3	1097.3	1039.4	1023.8	988.8
35°	1101.3	986.8	878.9	814.0	788.4	752.5	752.1
37.5°	856.0	755.3	698.1	649.5	623.9	602.3	600.1
40°	720.1	641.6	598.4	563.5	538.3	522.0	518.2
42.5°	625.2	561.7	521.3	499.6	480.2	471.8	465.6
45°	510.5	467.8	439.7	420.0	411.1	404.6	401.2
47.5°	427.1	398.4	379.2	366.2	358.9	352.1	353.9
50°	381.6	358.2	344.1	331.7	326.1	321.4	321.9
52.5°	345.0	324.0	312.6	303.7	296.8	293.4	291.8
55°	292.9	279.6	268.1	261.6	257.8	253.2	251.8
57.5°	249.8	239.5	230.2	222.9	221.9	217.4	218.0
60°	221.1	212.5	204.9	201.1	198.0	194.2	195.5
62.5°	197.5	190.4	183.4	180.2	177.2	174.4	175.0
65°	161.8	154.9	150.7	149.0	147.7	146.4	145.1
67.5°	128.9	124.7	122.1	118.4	115.8	115.4	114.1
70°	108.4	102.9	98.2	93.5	92.2	91.8	92.2
72.5°	86.9	83.4	82.1	79.8	79.6	78.4	79.2
75°	65.3	64.0	63.2	61.5	61.5	61.5	61.5
77.5°	48.2	47.4	46.9	46.6	46.1	45.5	45.4
80°	37.6	37.1	36.3	36.3	35.9	36.3	35.9
82.5°	28.4	28.3	27.4	27.4	27.0	26.7	27.0
85°	14.5	14.1	14.9	14.1	14.5	13.7	14.5
87.5°	6.5	6.6	6.4	6.4	6.1	6.8	6.1
90°	12.1	12.6	13.5	13.0	13.5	13.9	13.5
92.5°	31.1	27.5	25.0	24.2	22.7	23.2	22.4
95°	113.5	88.8	72.1	63.3	59.0	55.8	54.0
97.5°	334.3	274.3	218.7	184.3	163.4	150.8	146.8
100°	510.6	456.2	390.1	343.2	309.2	291.1	291.6
102.5°	590.6	558.9	517.0	480.5	453.6	438.4	427.7
105°	651.0	659.9	647.8	626.4	608.7	593.9	591.5
107.5°	643.4	684.1	700.7	701.1	695.1	690.1	685.8
110°	618.5	677.1	709.6	722.7	726.4	725.5	724.5



TEST NUMBER: P332308-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	585.7	651.4	693.2	717.1	728.6	732.1	732.3
115°	533.4	601.8	652.4	687.3	707.8	717.1	719.4
117.5°	489.1	550.5	601.9	638.3	661.7	675.1	678.2
120°	464.6	520.3	567.4	604.1	630.1	641.2	644.1
122.5°	444.8	496.5	540.1	572.8	596.2	608.5	612.0
125°	420.4	465.0	502.2	532.0	552.4	564.1	567.4
127.5°	398.9	439.2	473.0	499.5	517.0	527.5	530.5
130°	385.5	423.1	454.8	479.5	496.2	506.0	509.6
132.5°	372.8	407.9	438.1	461.2	477.9	486.6	489.2
135°	354.8	385.1	411.6	434.3	448.3	456.6	459.9
137.5°	337.5	363.5	386.5	405.6	419.7	426.8	428.9
140°	327.3	349.7	369.7	387.3	400.4	407.8	407.3
142.5°	317.7	337.0	354.4	369.5	381.1	387.8	387.3
145°	305.1	319.9	333.5	345.0	354.8	358.6	359.5
147.5°	295.6	307.7	317.2	326.0	332.6	336.2	336.6
150°	289.7	299.5	308.3	315.3	320.4	323.2	323.2
152.5°	284.1	292.8	300.1	305.6	310.4	312.0	312.0
155°	276.2	283.2	288.8	292.9	296.7	297.6	298.1
157.5°	268.5	273.9	278.3	281.9	284.7	285.4	285.4
160°	263.7	268.3	271.6	274.8	277.6	277.6	277.1
162.5°	258.4	262.8	265.6	267.7	270.2	270.2	269.7
165°	251.1	254.4	256.7	258.5	260.4	259.9	259.9
167.5°	245.4	247.3	249.0	249.8	251.1	250.6	250.6
170°	241.3	243.2	244.1	244.6	245.6	245.1	245.1
172.5°	238.0	239.5	240.0	240.1	241.1	240.3	239.9
175°	233.4	234.4	234.4	234.4	234.8	234.4	233.9
177.5°	230.8	231.2	231.2	230.8	231.2	230.5	230.5
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8

(END OF REPORT)