

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332313-930

Luminaire Tested: **S123RDIP-S775D805U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332313-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D805U930-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4733.3 lumens
Efficiency: N/A
Efficacy: 103.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332313-930

CATALOG NUMBER: S123RDIP-S775D805U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332313-930

CATALOG NUMBER: S123RDIP-S775D805U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	53
1	99	95	91	88	92	88	85	82	75	73	71	63	62	60	53	52	51	45
2	91	84	78	73	84	78	73	68	67	63	60	56	54	51	47	45	43	39
3	83	74	67	61	77	69	63	58	59	55	51	50	47	44	42	40	38	34
4	76	66	58	52	70	61	55	50	53	48	44	45	41	38	38	35	33	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26
6	65	53	45	40	60	50	43	38	43	38	34	37	33	30	32	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	27	29	26	23	21
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	23	21	19
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	21	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	22	20	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10733	10733	10733	10733
5°	12794	10778	9492	10778
10°	15974	10717	8576	10717
15°	18750	10608	7819	10608
20°	20927	10443	7178	10443
25°	20593	10271	6783	10271
30°	14802	10112	6377	10112
35°	9883	9905	6114	9905
40°	7281	9656	5841	9656
45°	6107	9220	5574	9220
50°	5390	8649	5203	8649
55°	4725	7994	4693	7994
60°	4209	7369	4299	7369
65°	3696	6696	4001	6696
70°	2902	6099	3654	6099
75°	2558	5327	3335	5327
80°	2225	4525	3279	4525
85°	1791	3631	3483	3631



TEST NUMBER: P332313-930

CATALOG NUMBER: S123RDIP-S775D805U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.1	2.1
10°-20°	306.3	6.5
20°-30°	481.3	10.2
30°-40°	502.1	10.6
40°-50°	429.7	9.1
50°-60°	327.5	6.9
60°-70°	209.9	4.4
70°-80°	101.0	2.1
80°-90°	29.1	0.6
90°-100°	52.9	1.1
100°-110°	158.2	3.3
110°-120°	269.1	5.7
120°-130°	354.0	7.5
130°-140°	397.9	8.4
140°-150°	391.1	8.3
150°-160°	329.2	7.0
160°-170°	219.2	4.6
170°-180°	76.7	1.6
0°-30°	885.7	18.7
0°-40°	1387.8	29.3
0°-60°	2145.0	45.3
0°-90°	2485.1	52.5
90°-120°	480.2	10.1
90°-150°	1623.1	34.3
90°-180°	2248.0	47.5
0°-180°	4733.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	997	997	997	997	997	
5°	1184	998	878	998	1184	122
15°	1683	952	702	952	1683	477
25°	1734	865	571	865	1734	745
35°	752	754	465	754	752	493
45°	401	606	366	606	401	315
55°	252	426	250	426	252	228
65°	145	263	157	263	145	143
75°	62	128	80	128	62	66
85°	14	29	28	29	14	17
90°	19	1	19	1	19	10
95°	50	38	50	38	50	51
105°	152	143	152	143	152	161
115°	272	271	272	271	272	269
125°	392	396	392	396	392	350
135°	514	514	514	514	514	395
145°	624	624	624	624	624	390
155°	713	714	713	714	713	328
165°	776	778	776	778	776	219
175°	806	810	806	810	806	77
180°	812	812	812	812	812	



TEST NUMBER: P332313-930

CATALOG NUMBER: S123RDIP-S775D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1062.0	1063.4	1058.9	1058.3	1053.1	1051.7	1051.7	1044.6	1040.2	1034.4	1030.9
5°	1184.1	1190.9	1187.5	1179.8	1167.0	1164.0	1155.9	1143.1	1128.6	1110.7	1102.1
7.5°	1336.5	1345.9	1342.3	1330.4	1317.0	1306.2	1283.3	1262.0	1232.2	1206.1	1183.7
10°	1461.5	1451.7	1444.1	1432.5	1420.2	1400.0	1376.1	1343.3	1305.3	1275.5	1242.1
12.5°	1555.1	1553.5	1543.8	1531.9	1514.4	1495.3	1466.0	1426.0	1381.8	1338.6	1300.6
15°	1682.6	1685.2	1678.8	1666.4	1641.7	1607.9	1563.6	1546.9	1483.8	1436.8	1389.8
17.5°	1770.9	1770.4	1769.5	1752.4	1727.1	1703.2	1662.0	1618.2	1561.0	1494.9	1431.6
20°	1826.9	1822.7	1823.5	1804.3	1785.5	1757.8	1717.7	1654.1	1607.1	1530.7	1465.3
22.5°	1825.5	1824.7	1828.0	1821.4	1807.7	1786.5	1754.9	1701.2	1641.3	1564.2	1490.6
25°	1733.9	1730.5	1750.5	1756.1	1777.8	1781.7	1772.3	1742.9	1686.0	1606.6	1515.7
27.5°	1451.2	1449.3	1486.5	1533.1	1592.1	1638.1	1682.5	1703.9	1686.0	1629.2	1538.1
30°	1190.9	1231.0	1249.9	1317.3	1392.4	1482.1	1560.6	1635.2	1653.6	1628.9	1554.1
32.5°	988.8	1023.8	1039.4	1097.3	1167.3	1272.4	1390.2	1495.9	1570.7	1589.6	1544.6
35°	752.1	752.5	788.4	814.0	878.9	986.8	1101.3	1243.0	1383.8	1490.5	1501.6
37.5°	600.1	602.3	623.9	649.5	698.1	755.3	856.0	973.8	1136.5	1300.3	1396.4
40°	518.2	522.0	538.3	563.5	598.4	641.6	720.1	831.1	966.8	1149.1	1298.0
42.5°	465.6	471.8	480.2	499.6	521.3	561.7	625.2	710.9	834.3	1006.7	1178.5
45°	401.2	404.6	411.1	420.0	439.7	467.8	510.5	568.1	670.6	809.3	981.3
47.5°	353.9	352.1	358.9	366.2	379.2	398.4	427.1	474.1	547.1	658.4	804.4
50°	321.9	321.4	326.1	331.7	344.1	358.2	381.6	417.0	475.1	567.3	700.9
52.5°	291.8	293.4	296.8	303.7	312.6	324.0	345.0	370.6	420.4	500.0	611.4
55°	251.8	253.2	257.8	261.6	268.1	279.6	292.9	314.1	348.3	403.8	495.5
57.5°	218.0	217.4	221.9	222.9	230.2	239.5	249.8	266.4	291.1	332.3	394.1
60°	195.5	194.2	198.0	201.1	204.9	212.5	221.1	237.3	257.0	287.2	340.2
62.5°	175.0	174.4	177.2	180.2	183.4	190.4	197.5	210.0	225.5	251.1	293.1
65°	145.1	146.4	147.7	149.0	150.7	154.9	161.8	170.3	181.0	198.9	229.2
67.5°	114.1	115.4	115.8	118.4	122.1	124.7	128.9	136.5	143.9	159.1	176.3
70°	92.2	91.8	92.2	93.5	98.2	102.9	108.4	114.0	118.6	129.3	143.8
72.5°	79.2	78.4	79.6	79.8	82.1	83.4	86.9	92.1	98.2	105.4	115.9
75°	61.5	61.5	61.5	61.5	63.2	64.0	65.3	66.6	68.7	72.2	79.8
77.5°	45.4	45.5	46.1	46.6	46.9	47.4	48.2	49.4	50.2	52.0	55.4
80°	35.9	36.3	35.9	36.3	36.3	37.1	37.6	38.8	39.3	41.4	42.7
82.5°	27.0	26.7	27.0	27.4	27.4	28.3	28.4	29.3	29.4	30.5	31.8
85°	14.5	13.7	14.5	14.1	14.9	14.1	14.5	15.3	15.3	15.8	17.5
87.5°	7.3	7.8	7.1	7.4	7.3	7.6	7.5	7.4	8.0	7.5	7.5
90°	19.2	18.8	18.6	18.3	18.0	17.5	17.0	16.5	15.9	15.3	13.5
92.5°	25.8	25.9	26.1	26.3	26.4	26.3	25.8	25.4	24.9	24.5	23.4
95°	49.7	49.7	49.7	49.7	49.7	49.4	48.8	48.3	47.8	47.2	46.1
97.5°	76.5	76.6	76.6	76.6	76.7	76.4	75.7	75.1	74.4	73.8	73.0
100°	96.9	96.6	96.3	96.0	95.8	95.4	95.0	94.6	94.2	93.7	93.0
102.5°	117.8	117.9	117.9	118.0	118.1	117.8	117.4	117.0	116.6	116.2	115.2
105°	151.7	151.4	151.2	150.8	150.6	150.4	150.4	150.4	150.4	150.4	149.2
107.5°	187.0	187.2	187.4	187.5	187.7	187.6	187.1	186.6	186.2	185.7	185.2
110°	211.0	211.2	211.6	211.8	212.1	212.0	211.4	210.8	210.3	209.7	209.5



TEST NUMBER: P332313-930

CATALOG NUMBER: S123RDIP-S775D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	236.5	236.5	236.6	236.7	236.7	236.4	235.7	235.1	234.4	233.7	233.7
115°	271.6	271.7	271.8	272.0	272.1	272.1	272.0	271.8	271.7	271.6	271.8
117.5°	307.1	307.5	307.9	308.3	308.7	308.9	308.9	309.0	309.0	309.0	309.4
120°	332.1	332.4	332.6	333.0	333.2	333.5	333.6	333.7	333.9	334.0	334.8
122.5°	356.0	356.4	356.9	357.3	357.7	358.1	358.4	358.8	359.1	359.5	359.9
125°	392.0	392.6	393.1	393.7	394.3	394.8	395.4	396.0	396.6	397.1	397.4
127.5°	427.9	428.5	429.2	429.8	430.5	431.2	431.9	432.8	433.6	434.3	434.6
130°	451.3	452.3	453.3	454.3	455.3	456.1	456.6	457.2	457.7	458.3	458.8
132.5°	475.8	476.5	477.3	478.1	478.8	479.6	480.2	480.9	481.6	482.2	482.6
135°	513.8	514.0	514.4	514.6	514.9	515.4	515.9	516.5	517.1	517.6	517.7
137.5°	547.3	547.9	548.4	548.9	549.4	550.0	550.7	551.2	551.8	552.4	552.0
140°	569.2	570.2	571.2	572.2	573.2	573.7	573.9	574.1	574.2	574.3	574.2
142.5°	591.7	592.4	593.2	593.9	594.8	595.2	595.3	595.5	595.6	595.7	595.5
145°	624.0	624.6	625.2	625.7	626.3	626.6	626.8	627.0	627.1	627.2	626.8
147.5°	652.9	653.7	654.5	655.4	656.2	656.7	656.7	656.7	656.7	656.7	656.3
150°	671.2	672.1	672.9	673.8	674.7	675.1	675.1	675.1	675.1	675.1	674.7
152.5°	689.1	689.8	690.6	691.3	692.0	692.3	692.0	691.8	691.6	691.4	691.2
155°	713.3	714.3	715.3	716.2	717.2	717.5	716.9	716.3	715.8	715.2	715.1
157.5°	735.3	736.1	736.9	737.8	738.5	738.6	738.0	737.4	736.9	736.2	736.1
160°	749.6	750.2	750.7	751.3	751.9	751.8	751.1	750.4	749.7	749.0	749.0
162.5°	760.3	761.2	762.1	763.0	763.9	764.1	763.4	762.6	761.9	761.2	761.1
165°	775.8	776.7	777.7	778.8	779.8	779.8	778.9	778.1	777.2	776.4	776.4
167.5°	788.9	789.8	790.7	791.5	792.4	792.4	791.5	790.7	789.8	788.9	788.8
170°	795.5	796.5	797.5	798.5	799.5	799.5	798.5	797.5	796.5	795.5	795.5
172.5°	800.6	801.6	802.6	803.6	804.6	804.6	803.8	802.9	802.0	801.1	801.1
175°	806.3	807.3	808.4	809.3	810.3	810.4	809.5	808.7	807.9	807.0	807.0
177.5°	809.4	810.2	811.0	811.8	812.6	812.6	812.0	811.3	810.6	809.9	809.9
180°	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5



TEST NUMBER: P332313-930

CATALOG NUMBER: S123RDIP-S775D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1029.6	1028.5	1023.8	1018.3	1011.1	1006.3	1002.6	1000.5	994.4	986.8	981.8
5°	1093.2	1080.4	1066.7	1050.0	1034.7	1018.9	1009.1	997.5	983.5	967.7	956.6
7.5°	1161.3	1136.2	1109.1	1081.2	1053.6	1028.9	1007.1	988.3	965.9	943.2	927.4
10°	1213.6	1176.8	1138.8	1100.0	1064.5	1031.3	1005.7	980.5	953.6	927.6	907.9
12.5°	1261.0	1212.7	1168.9	1121.2	1075.9	1036.1	999.1	969.6	937.2	909.5	887.0
15°	1321.1	1271.6	1218.6	1146.1	1085.9	1035.5	990.8	951.9	912.6	878.5	856.7
17.5°	1377.3	1302.8	1231.7	1171.1	1092.9	1030.0	975.3	928.8	885.7	849.5	822.7
20°	1400.5	1328.4	1251.1	1173.9	1097.0	1026.5	963.0	911.7	866.9	826.0	801.2
22.5°	1414.5	1332.8	1251.4	1168.4	1086.8	1013.6	950.7	894.3	845.8	806.8	776.2
25°	1430.8	1333.5	1243.8	1161.9	1078.6	999.2	924.5	864.8	812.3	770.9	738.4
27.5°	1441.5	1327.1	1221.2	1130.0	1045.6	966.5	898.1	834.8	781.5	737.7	702.9
30°	1443.6	1321.9	1203.7	1105.1	1019.3	946.7	874.2	813.6	757.2	710.7	678.2
32.5°	1446.3	1309.3	1180.1	1075.4	987.6	915.7	849.9	792.1	734.3	688.5	655.4
35°	1435.1	1302.4	1144.4	1024.0	936.0	866.5	807.1	753.8	697.1	652.6	618.9
37.5°	1386.6	1274.6	1107.3	966.1	874.2	809.8	761.4	714.9	662.8	614.9	583.2
40°	1337.7	1247.2	1078.6	931.0	834.9	768.7	725.2	687.2	636.8	592.1	557.9
42.5°	1265.0	1210.1	1051.3	894.1	790.5	726.8	690.1	654.4	610.3	564.8	532.6
45°	1131.6	1138.8	995.4	835.4	729.0	665.0	630.5	605.7	566.5	528.9	496.0
47.5°	964.3	1032.1	929.8	772.7	664.2	604.1	574.0	552.4	525.9	489.0	459.0
50°	855.0	951.9	877.2	730.8	623.6	563.9	534.0	516.5	493.4	464.4	435.8
52.5°	754.2	858.3	813.7	684.0	579.6	525.0	495.8	481.4	463.0	435.7	409.9
55°	615.1	720.6	710.3	613.3	513.5	464.4	442.2	426.0	413.6	393.1	372.7
57.5°	497.6	597.5	602.8	534.8	455.3	406.8	387.7	375.4	367.4	351.9	333.0
60°	423.5	515.2	533.1	481.9	413.6	371.0	352.1	342.3	335.9	323.6	309.1
62.5°	362.0	440.1	460.4	423.5	373.7	333.7	319.0	309.6	305.2	294.5	281.7
65°	277.0	341.9	361.5	341.0	315.0	283.0	271.1	262.9	259.1	253.2	243.7
67.5°	208.3	255.6	277.1	262.7	253.3	233.1	225.4	221.1	217.7	213.6	205.8
70°	167.3	202.4	224.5	220.7	213.0	202.4	196.8	193.8	190.4	186.9	180.1
72.5°	134.5	158.7	179.4	181.4	175.1	172.9	168.1	166.8	164.8	160.7	156.9
75°	89.2	105.8	120.3	125.9	128.5	130.6	128.5	128.1	127.6	124.3	122.1
77.5°	58.5	67.4	76.6	86.0	90.1	92.9	93.7	95.2	94.1	92.3	91.2
80°	44.8	47.0	53.3	61.5	67.8	70.4	72.2	73.0	72.6	72.2	70.4
82.5°	32.5	34.3	37.3	43.0	48.4	52.7	53.7	53.6	54.5	54.7	53.3
85°	17.5	17.9	18.8	19.6	22.6	27.3	28.6	29.4	30.3	30.3	27.7
87.5°	7.8	7.1	7.4	7.1	7.8	7.8	9.6	11.1	11.7	10.6	10.8
90°	11.6	9.8	7.9	6.3	4.9	3.5	2.0	0.7	2.0	3.5	4.9
92.5°	22.4	21.4	20.3	19.2	18.3	17.4	16.4	15.4	16.4	17.4	18.3
95°	44.9	43.8	42.6	41.6	40.6	39.6	38.6	37.6	38.6	39.6	40.6
97.5°	72.2	71.3	70.5	69.8	69.0	68.2	67.5	66.8	67.5	68.2	69.0
100°	92.3	91.6	90.9	90.1	89.3	88.4	87.6	86.7	87.6	88.4	89.3
102.5°	114.3	113.3	112.4	111.7	111.2	110.6	110.1	109.7	110.1	110.6	111.2
105°	147.9	146.6	145.4	144.6	144.3	144.0	143.7	143.4	143.7	144.0	144.3
107.5°	184.7	184.3	183.7	183.4	183.2	183.0	182.9	182.7	182.9	183.0	183.2
110°	209.1	208.9	208.6	208.3	208.0	207.7	207.4	207.2	207.4	207.7	208.0



TEST NUMBER: P332313-930

CATALOG NUMBER: S123RDIP-S775D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	233.6	233.5	233.4	233.3	233.2	233.0	232.8	232.7	232.8	233.0	233.2
115°	272.1	272.4	272.7	272.6	272.1	271.7	271.3	270.9	271.3	271.7	272.1
117.5°	309.7	310.1	310.5	310.5	310.2	310.0	309.7	309.4	309.7	310.0	310.2
120°	335.4	336.1	336.9	336.8	335.9	335.1	334.2	333.4	334.2	335.1	335.9
122.5°	360.3	360.6	361.0	360.9	360.2	359.6	359.0	358.4	359.0	359.6	360.2
125°	397.7	397.9	398.3	398.2	397.8	397.3	396.9	396.5	396.9	397.3	397.8
127.5°	435.0	435.3	435.6	435.3	434.4	433.5	432.6	431.7	432.6	433.5	434.4
130°	459.2	459.6	460.0	459.7	458.5	457.4	456.2	455.1	456.2	457.4	458.5
132.5°	482.9	483.2	483.6	483.1	482.0	480.9	479.7	478.6	479.7	480.9	482.0
135°	517.9	518.0	518.2	517.8	517.0	516.1	515.3	514.4	515.3	516.1	517.0
137.5°	551.6	551.3	550.9	550.4	549.7	548.9	548.3	547.6	548.3	548.9	549.7
140°	574.1	573.9	573.7	573.3	572.7	571.9	571.2	570.5	571.2	571.9	572.7
142.5°	595.3	595.0	594.8	594.3	593.5	592.8	592.2	591.4	592.2	592.8	593.5
145°	626.4	626.0	625.5	625.2	624.9	624.6	624.4	624.0	624.4	624.6	624.9
147.5°	655.9	655.5	655.1	654.7	654.1	653.6	653.1	652.6	653.1	653.6	654.1
150°	674.5	674.2	673.9	673.6	673.4	673.0	672.8	672.5	672.8	673.0	673.4
152.5°	691.0	690.9	690.7	690.4	690.0	689.6	689.2	688.8	689.2	689.6	690.0
155°	714.9	714.8	714.6	714.5	714.5	714.5	714.5	714.5	714.5	714.5	714.5
157.5°	736.1	735.9	735.8	735.8	736.0	736.1	736.3	736.5	736.3	736.1	736.0
160°	749.0	749.0	749.0	749.1	749.4	749.7	750.0	750.2	750.0	749.7	749.4
162.5°	761.0	760.9	760.8	760.9	761.3	761.7	762.1	762.5	762.1	761.7	761.3
165°	776.4	776.4	776.4	776.6	777.1	777.5	777.9	778.3	777.9	777.5	777.1
167.5°	788.6	788.6	788.5	788.6	789.2	789.8	790.4	790.9	790.4	789.8	789.2
170°	795.5	795.5	795.5	795.8	796.4	797.0	797.5	798.1	797.5	797.0	796.4
172.5°	801.1	801.1	801.1	801.4	802.0	802.6	803.2	803.6	803.2	802.6	802.0
175°	807.0	807.0	807.0	807.3	807.9	808.5	808.9	809.5	808.9	808.5	807.9
177.5°	809.9	809.9	809.9	810.2	810.6	811.1	811.5	812.0	811.5	811.1	810.6
180°	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5



TEST NUMBER: P332313-930

CATALOG NUMBER: S123RDIP-S775D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	980.1	975.6	972.6	965.7	961.2	956.5	951.7	954.8	954.5	954.1	954.1
5°	947.2	937.3	928.4	916.9	909.6	900.7	893.8	893.0	894.7	888.7	885.3
7.5°	914.6	901.2	888.4	875.7	862.3	851.5	844.7	841.6	837.2	833.6	829.7
10°	891.7	875.9	863.5	847.7	833.2	820.4	812.3	806.7	803.7	800.8	795.2
12.5°	868.1	852.6	836.9	819.0	805.2	790.4	784.3	778.0	772.3	769.0	761.4
15°	833.6	813.6	797.0	778.1	762.8	748.3	739.7	727.3	725.6	721.4	713.7
17.5°	799.1	777.3	754.3	740.5	723.1	708.0	695.0	690.8	678.6	674.0	667.3
20°	771.8	751.7	734.2	715.8	690.6	676.5	666.3	660.8	650.9	645.0	640.7
22.5°	748.2	727.8	707.5	686.2	665.4	649.5	642.0	633.4	628.1	619.7	615.1
25°	714.5	692.4	668.1	645.0	630.1	618.1	606.1	598.4	590.8	586.9	578.4
27.5°	675.5	652.2	629.5	612.0	593.7	581.9	571.0	564.2	555.0	548.5	543.8
30°	654.0	626.6	607.0	591.2	567.7	556.6	548.5	540.0	533.1	526.3	521.6
32.5°	629.0	604.1	585.5	565.9	547.9	535.8	525.3	517.8	511.9	505.5	500.8
35°	589.9	569.0	549.8	530.1	516.9	504.5	492.2	485.8	480.2	474.3	469.9
37.5°	554.6	535.0	516.7	498.1	481.8	471.7	461.7	456.8	449.3	445.3	440.9
40°	532.7	513.5	493.8	476.0	458.9	451.2	442.2	435.0	428.1	425.2	420.4
42.5°	508.8	489.6	473.0	453.7	439.8	429.3	421.0	413.1	408.0	403.7	401.0
45°	473.4	456.3	440.1	420.9	407.6	398.7	389.3	382.0	377.3	374.4	369.7
47.5°	439.0	421.9	405.4	388.7	375.9	365.7	356.3	351.2	345.0	341.3	338.2
50°	414.0	398.7	381.2	365.8	353.0	342.8	335.1	328.6	323.1	318.5	316.3
52.5°	391.2	374.8	359.6	345.4	331.8	320.2	313.2	306.5	302.3	296.9	294.4
55°	353.4	337.6	324.8	310.7	297.5	287.7	279.2	273.2	268.9	262.9	259.5
57.5°	318.0	303.9	288.5	276.3	262.7	254.4	247.3	239.2	234.0	229.3	226.0
60°	294.1	277.9	264.6	253.2	241.2	230.5	224.1	217.7	212.1	207.4	204.5
62.5°	269.2	255.0	242.5	229.9	219.0	209.7	202.3	196.9	192.0	189.0	186.1
65°	230.9	219.8	207.0	196.8	186.5	179.7	173.7	169.0	165.6	163.5	160.9
67.5°	195.8	185.0	173.8	163.7	156.9	151.7	147.8	143.7	142.0	139.3	137.6
70°	172.8	161.8	152.0	144.3	137.5	133.6	131.0	128.1	126.4	122.9	121.2
72.5°	148.0	139.9	132.8	126.5	121.1	117.6	114.3	110.6	107.9	104.1	102.5
75°	116.5	109.3	103.7	99.5	96.0	91.3	86.7	82.8	81.5	80.2	79.8
77.5°	86.3	81.7	77.7	74.1	69.9	66.4	65.4	64.6	64.2	63.6	63.6
80°	67.8	63.6	60.6	56.3	53.8	53.8	53.8	52.9	53.3	53.3	53.3
82.5°	50.5	46.6	44.9	43.4	42.9	43.2	43.2	43.4	43.1	43.8	43.5
85°	26.0	26.5	27.3	26.9	27.3	27.3	28.2	27.7	28.2	27.3	28.2
87.5°	10.8	12.1	12.9	13.6	14.3	14.3	14.8	14.9	15.3	15.5	15.6
90°	6.3	7.9	9.8	11.6	13.5	15.3	15.9	16.5	17.0	17.5	18.0
92.5°	19.2	20.3	21.4	22.4	23.4	24.5	24.9	25.4	25.8	26.3	26.4
95°	41.6	42.6	43.8	44.9	46.1	47.2	47.8	48.3	48.8	49.4	49.7
97.5°	69.8	70.5	71.3	72.2	73.0	73.8	74.4	75.1	75.7	76.4	76.7
100°	90.1	90.9	91.6	92.3	93.0	93.7	94.2	94.6	95.0	95.4	95.8
102.5°	111.7	112.4	113.3	114.3	115.2	116.2	116.6	117.0	117.4	117.8	118.1
105°	144.6	145.4	146.6	147.9	149.2	150.4	150.4	150.4	150.4	150.4	150.6
107.5°	183.4	183.7	184.3	184.7	185.2	185.7	186.2	186.6	187.1	187.6	187.7
110°	208.3	208.6	208.9	209.1	209.5	209.7	210.3	210.8	211.4	212.0	212.1



TEST NUMBER: P332313-930

CATALOG NUMBER: S123RDIP-S775D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	233.3	233.4	233.5	233.6	233.7	233.7	234.4	235.1	235.7	236.4	236.7
115°	272.6	272.7	272.4	272.1	271.8	271.6	271.7	271.8	272.0	272.1	272.1
117.5°	310.5	310.5	310.1	309.7	309.4	309.0	309.0	309.0	308.9	308.9	308.7
120°	336.8	336.9	336.1	335.4	334.8	334.0	333.9	333.7	333.6	333.5	333.2
122.5°	360.9	361.0	360.6	360.3	359.9	359.5	359.1	358.8	358.4	358.1	357.7
125°	398.2	398.3	397.9	397.7	397.4	397.1	396.6	396.0	395.4	394.8	394.3
127.5°	435.3	435.6	435.3	435.0	434.6	434.3	433.6	432.8	431.9	431.2	430.5
130°	459.7	460.0	459.6	459.2	458.8	458.3	457.7	457.2	456.6	456.1	455.3
132.5°	483.1	483.6	483.2	482.9	482.6	482.2	481.6	480.9	480.2	479.6	478.8
135°	517.8	518.2	518.0	517.9	517.7	517.6	517.1	516.5	515.9	515.4	514.9
137.5°	550.4	550.9	551.3	551.6	552.0	552.4	551.8	551.2	550.7	550.0	549.4
140°	573.3	573.7	573.9	574.1	574.2	574.3	574.2	574.1	573.9	573.7	573.2
142.5°	594.3	594.8	595.0	595.3	595.5	595.7	595.6	595.5	595.3	595.2	594.8
145°	625.2	625.5	626.0	626.4	626.8	627.2	627.1	627.0	626.8	626.6	626.3
147.5°	654.7	655.1	655.5	655.9	656.3	656.7	656.7	656.7	656.7	656.7	656.2
150°	673.6	673.9	674.2	674.5	674.7	675.1	675.1	675.1	675.1	675.1	674.7
152.5°	690.4	690.7	690.9	691.0	691.2	691.4	691.6	691.8	692.0	692.3	692.0
155°	714.5	714.6	714.8	714.9	715.1	715.2	715.8	716.3	716.9	717.5	717.2
157.5°	735.8	735.8	735.9	736.1	736.1	736.2	736.9	737.4	738.0	738.6	738.5
160°	749.1	749.0	749.0	749.0	749.0	749.0	749.7	750.4	751.1	751.8	751.9
162.5°	760.9	760.8	760.9	761.0	761.1	761.2	761.9	762.6	763.4	764.1	763.9
165°	776.6	776.4	776.4	776.4	776.4	776.4	777.2	778.1	778.9	779.8	779.8
167.5°	788.6	788.5	788.6	788.6	788.8	788.9	789.8	790.7	791.5	792.4	792.4
170°	795.8	795.5	795.5	795.5	795.5	795.5	796.5	797.5	798.5	799.5	799.5
172.5°	801.4	801.1	801.1	801.1	801.1	801.1	802.0	802.9	803.8	804.6	804.6
175°	807.3	807.0	807.0	807.0	807.0	807.0	807.9	808.7	809.5	810.4	810.3
177.5°	810.2	809.9	809.9	809.9	809.9	809.9	810.6	811.3	812.0	812.6	812.6
180°	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5



TEST NUMBER: P332313-930

CATALOG NUMBER: S123RDIP-S775D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	950.0	949.7	950.0	948.6	950.0	949.7	950.0	954.1	954.1	954.5	954.8
5°	884.0	883.5	882.3	878.5	882.3	883.5	884.0	885.3	888.7	894.7	893.0
7.5°	826.4	825.8	822.1	822.1	822.1	825.8	826.4	829.7	833.6	837.2	841.6
10°	792.2	792.6	787.6	784.6	787.6	792.6	792.2	795.2	800.8	803.7	806.7
12.5°	759.1	757.2	753.0	749.7	753.0	757.2	759.1	761.4	769.0	772.3	778.0
15°	715.4	711.1	700.9	701.7	700.9	711.1	715.4	713.7	721.4	725.6	727.3
17.5°	663.9	660.8	660.6	654.6	660.6	660.8	663.9	667.3	674.0	678.6	690.8
20°	633.9	631.8	632.6	626.6	632.6	631.8	633.9	640.7	645.0	650.9	660.8
22.5°	610.3	608.2	604.6	602.8	604.6	608.2	610.3	615.1	619.7	628.1	633.4
25°	575.8	572.4	569.0	571.1	569.0	572.4	575.8	578.4	586.9	590.8	598.4
27.5°	541.4	538.7	535.3	534.9	535.3	538.7	541.4	543.8	548.5	555.0	564.2
30°	519.5	516.9	515.2	513.1	515.2	516.9	519.5	521.6	526.3	533.1	540.0
32.5°	497.3	496.8	493.7	493.3	493.7	496.8	497.3	500.8	505.5	511.9	517.8
35°	468.2	465.7	464.8	465.3	464.8	465.7	468.2	469.9	474.3	480.2	485.8
37.5°	440.7	437.2	435.7	434.2	435.7	437.2	440.7	440.9	445.3	449.3	456.8
40°	420.9	417.4	416.6	415.7	416.6	417.4	420.9	420.4	425.2	428.1	435.0
42.5°	398.7	397.3	396.8	395.3	396.8	397.3	398.7	401.0	403.7	408.0	413.1
45°	368.4	367.9	365.4	366.2	365.4	367.9	368.4	369.7	374.4	377.3	382.0
47.5°	336.5	334.6	332.8	333.9	332.8	334.6	336.5	338.2	341.3	345.0	351.2
50°	314.6	313.7	309.9	310.7	309.9	313.7	314.6	316.3	318.5	323.1	328.6
52.5°	292.8	289.5	288.0	287.6	288.0	289.5	292.8	294.4	296.9	302.3	306.5
55°	256.6	252.7	250.9	250.1	250.9	252.7	256.6	259.5	262.9	268.9	273.2
57.5°	221.0	220.0	218.7	219.6	218.7	220.0	221.0	226.0	229.3	234.0	239.2
60°	200.2	200.2	200.2	199.7	200.2	200.2	200.2	204.5	207.4	212.1	217.7
62.5°	184.2	183.1	182.8	183.4	182.8	183.1	184.2	186.1	189.0	192.0	196.9
65°	159.6	159.2	157.5	157.1	157.5	159.2	159.6	160.9	163.5	165.6	169.0
67.5°	136.5	134.9	134.4	133.9	134.4	134.9	136.5	137.6	139.3	142.0	143.7
70°	119.1	118.2	115.7	116.1	115.7	118.2	119.1	121.2	122.9	126.4	128.1
72.5°	100.3	99.5	99.0	98.3	99.0	99.5	100.3	102.5	104.1	107.9	110.6
75°	79.4	79.0	78.5	80.2	78.5	79.0	79.4	79.8	80.2	81.5	82.8
77.5°	63.6	63.6	63.8	63.2	63.8	63.6	63.6	63.6	63.6	64.2	64.6
80°	53.3	53.3	52.9	52.9	52.9	53.3	53.3	53.3	53.3	53.3	52.9
82.5°	42.8	43.1	43.4	42.7	43.4	43.1	42.8	43.5	43.8	43.1	43.4
85°	28.2	27.7	28.6	28.2	28.6	27.7	28.2	28.2	27.3	28.2	27.7
87.5°	16.3	15.7	15.7	16.1	15.7	15.7	16.3	15.6	15.5	15.3	14.9
90°	18.3	18.6	18.8	19.2	18.8	18.6	18.3	18.0	17.5	17.0	16.5
92.5°	26.3	26.1	25.9	25.8	25.9	26.1	26.3	26.4	26.3	25.8	25.4
95°	49.7	49.7	49.7	49.7	49.7	49.7	49.7	49.7	49.4	48.8	48.3
97.5°	76.6	76.6	76.6	76.5	76.6	76.6	76.6	76.7	76.4	75.7	75.1
100°	96.0	96.3	96.6	96.9	96.6	96.3	96.0	95.8	95.4	95.0	94.6
102.5°	118.0	117.9	117.9	117.8	117.9	117.9	118.0	118.1	117.8	117.4	117.0
105°	150.8	151.2	151.4	151.7	151.4	151.2	150.8	150.6	150.4	150.4	150.4
107.5°	187.5	187.4	187.2	187.0	187.2	187.4	187.5	187.7	187.6	187.1	186.6
110°	211.8	211.6	211.2	211.0	211.2	211.6	211.8	212.1	212.0	211.4	210.8



TEST NUMBER: P332313-930

CATALOG NUMBER: S123RDIP-S775D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	236.7	236.6	236.5	236.5	236.5	236.6	236.7	236.7	236.4	235.7	235.1
115°	272.0	271.8	271.7	271.6	271.7	271.8	272.0	272.1	272.1	272.0	271.8
117.5°	308.3	307.9	307.5	307.1	307.5	307.9	308.3	308.7	308.9	308.9	309.0
120°	333.0	332.6	332.4	332.1	332.4	332.6	333.0	333.2	333.5	333.6	333.7
122.5°	357.3	356.9	356.4	356.0	356.4	356.9	357.3	357.7	358.1	358.4	358.8
125°	393.7	393.1	392.6	392.0	392.6	393.1	393.7	394.3	394.8	395.4	396.0
127.5°	429.8	429.2	428.5	427.9	428.5	429.2	429.8	430.5	431.2	431.9	432.8
130°	454.3	453.3	452.3	451.3	452.3	453.3	454.3	455.3	456.1	456.6	457.2
132.5°	478.1	477.3	476.5	475.8	476.5	477.3	478.1	478.8	479.6	480.2	480.9
135°	514.6	514.4	514.0	513.8	514.0	514.4	514.6	514.9	515.4	515.9	516.5
137.5°	548.9	548.4	547.9	547.3	547.9	548.4	548.9	549.4	550.0	550.7	551.2
140°	572.2	571.2	570.2	569.2	570.2	571.2	572.2	573.2	573.7	573.9	574.1
142.5°	593.9	593.2	592.4	591.7	592.4	593.2	593.9	594.8	595.2	595.3	595.5
145°	625.7	625.2	624.6	624.0	624.6	625.2	625.7	626.3	626.6	626.8	627.0
147.5°	655.4	654.5	653.7	652.9	653.7	654.5	655.4	656.2	656.7	656.7	656.7
150°	673.8	672.9	672.1	671.2	672.1	672.9	673.8	674.7	675.1	675.1	675.1
152.5°	691.3	690.6	689.8	689.1	689.8	690.6	691.3	692.0	692.3	692.0	691.8
155°	716.2	715.3	714.3	713.3	714.3	715.3	716.2	717.2	717.5	716.9	716.3
157.5°	737.8	736.9	736.1	735.3	736.1	736.9	737.8	738.5	738.6	738.0	737.4
160°	751.3	750.7	750.2	749.6	750.2	750.7	751.3	751.9	751.8	751.1	750.4
162.5°	763.0	762.1	761.2	760.3	761.2	762.1	763.0	763.9	764.1	763.4	762.6
165°	778.8	777.7	776.7	775.8	776.7	777.7	778.8	779.8	779.8	778.9	778.1
167.5°	791.5	790.7	789.8	788.9	789.8	790.7	791.5	792.4	792.4	791.5	790.7
170°	798.5	797.5	796.5	795.5	796.5	797.5	798.5	799.5	799.5	798.5	797.5
172.5°	803.6	802.6	801.6	800.6	801.6	802.6	803.6	804.6	804.6	803.8	802.9
175°	809.3	808.4	807.3	806.3	807.3	808.4	809.3	810.3	810.4	809.5	808.7
177.5°	811.8	811.0	810.2	809.4	810.2	811.0	811.8	812.6	812.6	812.0	811.3
180°	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5



TEST NUMBER: P332313-930

CATALOG NUMBER: S123RDIP-S775D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	951.7	956.5	961.2	965.7	972.6	975.6	980.1	981.8	986.8	994.4	1000.5
5°	893.8	900.7	909.6	916.9	928.4	937.3	947.2	956.6	967.7	983.5	997.5
7.5°	844.7	851.5	862.3	875.7	888.4	901.2	914.6	927.4	943.2	965.9	988.3
10°	812.3	820.4	833.2	847.7	863.5	875.9	891.7	907.9	927.6	953.6	980.5
12.5°	784.3	790.4	805.2	819.0	836.9	852.6	868.1	887.0	909.5	937.2	969.6
15°	739.7	748.3	762.8	778.1	797.0	813.6	833.6	856.7	878.5	912.6	951.9
17.5°	695.0	708.0	723.1	740.5	754.3	777.3	799.1	822.7	849.5	885.7	928.8
20°	666.3	676.5	690.6	715.8	734.2	751.7	771.8	801.2	826.0	866.9	911.7
22.5°	642.0	649.5	665.4	686.2	707.5	727.8	748.2	776.2	806.8	845.8	894.3
25°	606.1	618.1	630.1	645.0	668.1	692.4	714.5	738.4	770.9	812.3	864.8
27.5°	571.0	581.9	593.7	612.0	629.5	652.2	675.5	702.9	737.7	781.5	834.8
30°	548.5	556.6	567.7	591.2	607.0	626.6	654.0	678.2	710.7	757.2	813.6
32.5°	525.3	535.8	547.9	565.9	585.5	604.1	629.0	655.4	688.5	734.3	792.1
35°	492.2	504.5	516.9	530.1	549.8	569.0	589.9	618.9	652.6	697.1	753.8
37.5°	461.7	471.7	481.8	498.1	516.7	535.0	554.6	583.2	614.9	662.8	714.9
40°	442.2	451.2	458.9	476.0	493.8	513.5	532.7	557.9	592.1	636.8	687.2
42.5°	421.0	429.3	439.8	453.7	473.0	489.6	508.8	532.6	564.8	610.3	654.4
45°	389.3	398.7	407.6	420.9	440.1	456.3	473.4	496.0	528.9	566.5	605.7
47.5°	356.3	365.7	375.9	388.7	405.4	421.9	439.0	459.0	489.0	525.9	552.4
50°	335.1	342.8	353.0	365.8	381.2	398.7	414.0	435.8	464.4	493.4	516.5
52.5°	313.2	320.2	331.8	345.4	359.6	374.8	391.2	409.9	435.7	463.0	481.4
55°	279.2	287.7	297.5	310.7	324.8	337.6	353.4	372.7	393.1	413.6	426.0
57.5°	247.3	254.4	262.7	276.3	288.5	303.9	318.0	333.0	351.9	367.4	375.4
60°	224.1	230.5	241.2	253.2	264.6	277.9	294.1	309.1	323.6	335.9	342.3
62.5°	202.3	209.7	219.0	229.9	242.5	255.0	269.2	281.7	294.5	305.2	309.6
65°	173.7	179.7	186.5	196.8	207.0	219.8	230.9	243.7	253.2	259.1	262.9
67.5°	147.8	151.7	156.9	163.7	173.8	185.0	195.8	205.8	213.6	217.7	221.1
70°	131.0	133.6	137.5	144.3	152.0	161.8	172.8	180.1	186.9	190.4	193.8
72.5°	114.3	117.6	121.1	126.5	132.8	139.9	148.0	156.9	160.7	164.8	166.8
75°	86.7	91.3	96.0	99.5	103.7	109.3	116.5	122.1	124.3	127.6	128.1
77.5°	65.4	66.4	69.9	74.1	77.7	81.7	86.3	91.2	92.3	94.1	95.2
80°	53.8	53.8	53.8	56.3	60.6	63.6	67.8	70.4	72.2	72.6	73.0
82.5°	43.2	43.2	42.9	43.4	44.9	46.6	50.5	53.3	54.7	54.5	53.6
85°	28.2	27.3	27.3	26.9	27.3	26.5	26.0	27.7	30.3	30.3	29.4
87.5°	14.8	14.3	14.3	13.6	12.9	12.1	10.8	10.8	10.6	11.7	11.1
90°	15.9	15.3	13.5	11.6	9.8	7.9	6.3	4.9	3.5	2.0	0.7
92.5°	24.9	24.5	23.4	22.4	21.4	20.3	19.2	18.3	17.4	16.4	15.4
95°	47.8	47.2	46.1	44.9	43.8	42.6	41.6	40.6	39.6	38.6	37.6
97.5°	74.4	73.8	73.0	72.2	71.3	70.5	69.8	69.0	68.2	67.5	66.8
100°	94.2	93.7	93.0	92.3	91.6	90.9	90.1	89.3	88.4	87.6	86.7
102.5°	116.6	116.2	115.2	114.3	113.3	112.4	111.7	111.2	110.6	110.1	109.7
105°	150.4	150.4	149.2	147.9	146.6	145.4	144.6	144.3	144.0	143.7	143.4
107.5°	186.2	185.7	185.2	184.7	184.3	183.7	183.4	183.2	183.0	182.9	182.7
110°	210.3	209.7	209.5	209.1	208.9	208.6	208.3	208.0	207.7	207.4	207.2



TEST NUMBER: P332313-930

CATALOG NUMBER: S123RDIP-S775D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	234.4	233.7	233.7	233.6	233.5	233.4	233.3	233.2	233.0	232.8	232.7
115°	271.7	271.6	271.8	272.1	272.4	272.7	272.6	272.1	271.7	271.3	270.9
117.5°	309.0	309.0	309.4	309.7	310.1	310.5	310.5	310.2	310.0	309.7	309.4
120°	333.9	334.0	334.8	335.4	336.1	336.9	336.8	335.9	335.1	334.2	333.4
122.5°	359.1	359.5	359.9	360.3	360.6	361.0	360.9	360.2	359.6	359.0	358.4
125°	396.6	397.1	397.4	397.7	397.9	398.3	398.2	397.8	397.3	396.9	396.5
127.5°	433.6	434.3	434.6	435.0	435.3	435.6	435.3	434.4	433.5	432.6	431.7
130°	457.7	458.3	458.8	459.2	459.6	460.0	459.7	458.5	457.4	456.2	455.1
132.5°	481.6	482.2	482.6	482.9	483.2	483.6	483.1	482.0	480.9	479.7	478.6
135°	517.1	517.6	517.7	517.9	518.0	518.2	517.8	517.0	516.1	515.3	514.4
137.5°	551.8	552.4	552.0	551.6	551.3	550.9	550.4	549.7	548.9	548.3	547.6
140°	574.2	574.3	574.2	574.1	573.9	573.7	573.3	572.7	571.9	571.2	570.5
142.5°	595.6	595.7	595.5	595.3	595.0	594.8	594.3	593.5	592.8	592.2	591.4
145°	627.1	627.2	626.8	626.4	626.0	625.5	625.2	624.9	624.6	624.4	624.0
147.5°	656.7	656.7	656.3	655.9	655.5	655.1	654.7	654.1	653.6	653.1	652.6
150°	675.1	675.1	674.7	674.5	674.2	673.9	673.6	673.4	673.0	672.8	672.5
152.5°	691.6	691.4	691.2	691.0	690.9	690.7	690.4	690.0	689.6	689.2	688.8
155°	715.8	715.2	715.1	714.9	714.8	714.6	714.5	714.5	714.5	714.5	714.5
157.5°	736.9	736.2	736.1	736.1	735.9	735.8	735.8	736.0	736.1	736.3	736.5
160°	749.7	749.0	749.0	749.0	749.0	749.0	749.1	749.4	749.7	750.0	750.2
162.5°	761.9	761.2	761.1	761.0	760.9	760.8	760.9	761.3	761.7	762.1	762.5
165°	777.2	776.4	776.4	776.4	776.4	776.4	776.6	777.1	777.5	777.9	778.3
167.5°	789.8	788.9	788.8	788.6	788.6	788.5	788.6	789.2	789.8	790.4	790.9
170°	796.5	795.5	795.5	795.5	795.5	795.5	795.8	796.4	797.0	797.5	798.1
172.5°	802.0	801.1	801.1	801.1	801.1	801.1	801.4	802.0	802.6	803.2	803.6
175°	807.9	807.0	807.0	807.0	807.0	807.0	807.3	807.9	808.5	808.9	809.5
177.5°	810.6	809.9	809.9	809.9	809.9	809.9	810.2	810.6	811.1	811.5	812.0
180°	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5



TEST NUMBER: P332313-930

CATALOG NUMBER: S123RDIP-S775D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1002.6	1006.3	1011.1	1018.3	1023.8	1028.5	1029.6	1030.9	1034.4	1040.2	1044.6
5°	1009.1	1018.9	1034.7	1050.0	1066.7	1080.4	1093.2	1102.1	1110.7	1128.6	1143.1
7.5°	1007.1	1028.9	1053.6	1081.2	1109.1	1136.2	1161.3	1183.7	1206.1	1232.2	1262.0
10°	1005.7	1031.3	1064.5	1100.0	1138.8	1176.8	1213.6	1242.1	1275.5	1305.3	1343.3
12.5°	999.1	1036.1	1075.9	1121.2	1168.9	1212.7	1261.0	1300.6	1338.6	1381.8	1426.0
15°	990.8	1035.5	1085.9	1146.1	1218.6	1271.6	1321.1	1389.8	1436.8	1483.8	1546.9
17.5°	975.3	1030.0	1092.9	1171.1	1231.7	1302.8	1377.3	1431.6	1494.9	1561.0	1618.2
20°	963.0	1026.5	1097.0	1173.9	1251.1	1328.4	1400.5	1465.3	1530.7	1607.1	1654.1
22.5°	950.7	1013.6	1086.8	1168.4	1251.4	1332.8	1414.5	1490.6	1564.2	1641.3	1701.2
25°	924.5	999.2	1078.6	1161.9	1243.8	1333.5	1430.8	1515.7	1606.6	1686.0	1742.9
27.5°	898.1	966.5	1045.6	1130.0	1221.2	1327.1	1441.5	1538.1	1629.2	1686.0	1703.9
30°	874.2	946.7	1019.3	1105.1	1203.7	1321.9	1443.6	1554.1	1628.9	1653.6	1635.2
32.5°	849.9	915.7	987.6	1075.4	1180.1	1309.3	1446.3	1544.6	1589.6	1570.7	1495.9
35°	807.1	866.5	936.0	1024.0	1144.4	1302.4	1435.1	1501.6	1490.5	1383.8	1243.0
37.5°	761.4	809.8	874.2	966.1	1107.3	1274.6	1386.6	1396.4	1300.3	1136.5	973.8
40°	725.2	768.7	834.9	931.0	1078.6	1247.2	1337.7	1298.0	1149.1	966.8	831.1
42.5°	690.1	726.8	790.5	894.1	1051.3	1210.1	1265.0	1178.5	1006.7	834.3	710.9
45°	630.5	665.0	729.0	835.4	995.4	1138.8	1131.6	981.3	809.3	670.6	568.1
47.5°	574.0	604.1	664.2	772.7	929.8	1032.1	964.3	804.4	658.4	547.1	474.1
50°	534.0	563.9	623.6	730.8	877.2	951.9	855.0	700.9	567.3	475.1	417.0
52.5°	495.8	525.0	579.6	684.0	813.7	858.3	754.2	611.4	500.0	420.4	370.6
55°	442.2	464.4	513.5	613.3	710.3	720.6	615.1	495.5	403.8	348.3	314.1
57.5°	387.7	406.8	455.3	534.8	602.8	597.5	497.6	394.1	332.3	291.1	266.4
60°	352.1	371.0	413.6	481.9	533.1	515.2	423.5	340.2	287.2	257.0	237.3
62.5°	319.0	333.7	373.7	423.5	460.4	440.1	362.0	293.1	251.1	225.5	210.0
65°	271.1	283.0	315.0	341.0	361.5	341.9	277.0	229.2	198.9	181.0	170.3
67.5°	225.4	233.1	253.3	262.7	277.1	255.6	208.3	176.3	159.1	143.9	136.5
70°	196.8	202.4	213.0	220.7	224.5	202.4	167.3	143.8	129.3	118.6	114.0
72.5°	168.1	172.9	175.1	181.4	179.4	158.7	134.5	115.9	105.4	98.2	92.1
75°	128.5	130.6	128.5	125.9	120.3	105.8	89.2	79.8	72.2	68.7	66.6
77.5°	93.7	92.9	90.1	86.0	76.6	67.4	58.5	55.4	52.0	50.2	49.4
80°	72.2	70.4	67.8	61.5	53.3	47.0	44.8	42.7	41.4	39.3	38.8
82.5°	53.7	52.7	48.4	43.0	37.3	34.3	32.5	31.8	30.5	29.4	29.3
85°	28.6	27.3	22.6	19.6	18.8	17.9	17.5	17.5	15.8	15.3	15.3
87.5°	9.6	7.8	7.8	7.1	7.4	7.1	7.8	7.5	7.5	8.0	7.4
90°	2.0	3.5	4.9	6.3	7.9	9.8	11.6	13.5	15.3	15.9	16.5
92.5°	16.4	17.4	18.3	19.2	20.3	21.4	22.4	23.4	24.5	24.9	25.4
95°	38.6	39.6	40.6	41.6	42.6	43.8	44.9	46.1	47.2	47.8	48.3
97.5°	67.5	68.2	69.0	69.8	70.5	71.3	72.2	73.0	73.8	74.4	75.1
100°	87.6	88.4	89.3	90.1	90.9	91.6	92.3	93.0	93.7	94.2	94.6
102.5°	110.1	110.6	111.2	111.7	112.4	113.3	114.3	115.2	116.2	116.6	117.0
105°	143.7	144.0	144.3	144.6	145.4	146.6	147.9	149.2	150.4	150.4	150.4
107.5°	182.9	183.0	183.2	183.4	183.7	184.3	184.7	185.2	185.7	186.2	186.6
110°	207.4	207.7	208.0	208.3	208.6	208.9	209.1	209.5	209.7	210.3	210.8



TEST NUMBER: P332313-930

CATALOG NUMBER: S123RDIP-S775D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	232.8	233.0	233.2	233.3	233.4	233.5	233.6	233.7	233.7	234.4	235.1
115°	271.3	271.7	272.1	272.6	272.7	272.4	272.1	271.8	271.6	271.7	271.8
117.5°	309.7	310.0	310.2	310.5	310.5	310.1	309.7	309.4	309.0	309.0	309.0
120°	334.2	335.1	335.9	336.8	336.9	336.1	335.4	334.8	334.0	333.9	333.7
122.5°	359.0	359.6	360.2	360.9	361.0	360.6	360.3	359.9	359.5	359.1	358.8
125°	396.9	397.3	397.8	398.2	398.3	397.9	397.7	397.4	397.1	396.6	396.0
127.5°	432.6	433.5	434.4	435.3	435.6	435.3	435.0	434.6	434.3	433.6	432.8
130°	456.2	457.4	458.5	459.7	460.0	459.6	459.2	458.8	458.3	457.7	457.2
132.5°	479.7	480.9	482.0	483.1	483.6	483.2	482.9	482.6	482.2	481.6	480.9
135°	515.3	516.1	517.0	517.8	518.2	518.0	517.9	517.7	517.6	517.1	516.5
137.5°	548.3	548.9	549.7	550.4	550.9	551.3	551.6	552.0	552.4	551.8	551.2
140°	571.2	571.9	572.7	573.3	573.7	573.9	574.1	574.2	574.3	574.2	574.1
142.5°	592.2	592.8	593.5	594.3	594.8	595.0	595.3	595.5	595.7	595.6	595.5
145°	624.4	624.6	624.9	625.2	625.5	626.0	626.4	626.8	627.2	627.1	627.0
147.5°	653.1	653.6	654.1	654.7	655.1	655.5	655.9	656.3	656.7	656.7	656.7
150°	672.8	673.0	673.4	673.6	673.9	674.2	674.5	674.7	675.1	675.1	675.1
152.5°	689.2	689.6	690.0	690.4	690.7	690.9	691.0	691.2	691.4	691.6	691.8
155°	714.5	714.5	714.5	714.5	714.6	714.8	714.9	715.1	715.2	715.8	716.3
157.5°	736.3	736.1	736.0	735.8	735.8	735.9	736.1	736.1	736.2	736.9	737.4
160°	750.0	749.7	749.4	749.1	749.0	749.0	749.0	749.0	749.0	749.7	750.4
162.5°	762.1	761.7	761.3	760.9	760.8	760.9	761.0	761.1	761.2	761.9	762.6
165°	777.9	777.5	777.1	776.6	776.4	776.4	776.4	776.4	776.4	777.2	778.1
167.5°	790.4	789.8	789.2	788.6	788.5	788.6	788.6	788.8	788.9	789.8	790.7
170°	797.5	797.0	796.4	795.8	795.5	795.5	795.5	795.5	795.5	796.5	797.5
172.5°	803.2	802.6	802.0	801.4	801.1	801.1	801.1	801.1	801.1	802.0	802.9
175°	808.9	808.5	807.9	807.3	807.0	807.0	807.0	807.0	807.0	807.9	808.7
177.5°	811.5	811.1	810.6	810.2	809.9	809.9	809.9	809.9	809.9	810.6	811.3
180°	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5



TEST NUMBER: P332313-930

CATALOG NUMBER: S123RDIP-S775D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1051.7	1051.7	1053.1	1058.3	1058.9	1063.4	1062.0
5°	1155.9	1164.0	1167.0	1179.8	1187.5	1190.9	1184.1
7.5°	1283.3	1306.2	1317.0	1330.4	1342.3	1345.9	1336.5
10°	1376.1	1400.0	1420.2	1432.5	1444.1	1451.7	1461.5
12.5°	1466.0	1495.3	1514.4	1531.9	1543.8	1553.5	1555.1
15°	1563.6	1607.9	1641.7	1666.4	1678.8	1685.2	1682.6
17.5°	1662.0	1703.2	1727.1	1752.4	1769.5	1770.4	1770.9
20°	1717.7	1757.8	1785.5	1804.3	1823.5	1822.7	1826.9
22.5°	1754.9	1786.5	1807.7	1821.4	1828.0	1824.7	1825.5
25°	1772.3	1781.7	1777.8	1756.1	1750.5	1730.5	1733.9
27.5°	1682.5	1638.1	1592.1	1533.1	1486.5	1449.3	1451.2
30°	1560.6	1482.1	1392.4	1317.3	1249.9	1231.0	1190.9
32.5°	1390.2	1272.4	1167.3	1097.3	1039.4	1023.8	988.8
35°	1101.3	986.8	878.9	814.0	788.4	752.5	752.1
37.5°	856.0	755.3	698.1	649.5	623.9	602.3	600.1
40°	720.1	641.6	598.4	563.5	538.3	522.0	518.2
42.5°	625.2	561.7	521.3	499.6	480.2	471.8	465.6
45°	510.5	467.8	439.7	420.0	411.1	404.6	401.2
47.5°	427.1	398.4	379.2	366.2	358.9	352.1	353.9
50°	381.6	358.2	344.1	331.7	326.1	321.4	321.9
52.5°	345.0	324.0	312.6	303.7	296.8	293.4	291.8
55°	292.9	279.6	268.1	261.6	257.8	253.2	251.8
57.5°	249.8	239.5	230.2	222.9	221.9	217.4	218.0
60°	221.1	212.5	204.9	201.1	198.0	194.2	195.5
62.5°	197.5	190.4	183.4	180.2	177.2	174.4	175.0
65°	161.8	154.9	150.7	149.0	147.7	146.4	145.1
67.5°	128.9	124.7	122.1	118.4	115.8	115.4	114.1
70°	108.4	102.9	98.2	93.5	92.2	91.8	92.2
72.5°	86.9	83.4	82.1	79.8	79.6	78.4	79.2
75°	65.3	64.0	63.2	61.5	61.5	61.5	61.5
77.5°	48.2	47.4	46.9	46.6	46.1	45.5	45.4
80°	37.6	37.1	36.3	36.3	35.9	36.3	35.9
82.5°	28.4	28.3	27.4	27.4	27.0	26.7	27.0
85°	14.5	14.1	14.9	14.1	14.5	13.7	14.5
87.5°	7.5	7.6	7.3	7.4	7.1	7.8	7.3
90°	17.0	17.5	18.0	18.3	18.6	18.8	19.2
92.5°	25.8	26.3	26.4	26.3	26.1	25.9	25.8
95°	48.8	49.4	49.7	49.7	49.7	49.7	49.7
97.5°	75.7	76.4	76.7	76.6	76.6	76.6	76.5
100°	95.0	95.4	95.8	96.0	96.3	96.6	96.9
102.5°	117.4	117.8	118.1	118.0	117.9	117.9	117.8
105°	150.4	150.4	150.6	150.8	151.2	151.4	151.7
107.5°	187.1	187.6	187.7	187.5	187.4	187.2	187.0
110°	211.4	212.0	212.1	211.8	211.6	211.2	211.0



TEST NUMBER: P332313-930

CATALOG NUMBER: S123RDIP-S775D805U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	235.7	236.4	236.7	236.7	236.6	236.5	236.5
115°	272.0	272.1	272.1	272.0	271.8	271.7	271.6
117.5°	308.9	308.9	308.7	308.3	307.9	307.5	307.1
120°	333.6	333.5	333.2	333.0	332.6	332.4	332.1
122.5°	358.4	358.1	357.7	357.3	356.9	356.4	356.0
125°	395.4	394.8	394.3	393.7	393.1	392.6	392.0
127.5°	431.9	431.2	430.5	429.8	429.2	428.5	427.9
130°	456.6	456.1	455.3	454.3	453.3	452.3	451.3
132.5°	480.2	479.6	478.8	478.1	477.3	476.5	475.8
135°	515.9	515.4	514.9	514.6	514.4	514.0	513.8
137.5°	550.7	550.0	549.4	548.9	548.4	547.9	547.3
140°	573.9	573.7	573.2	572.2	571.2	570.2	569.2
142.5°	595.3	595.2	594.8	593.9	593.2	592.4	591.7
145°	626.8	626.6	626.3	625.7	625.2	624.6	624.0
147.5°	656.7	656.7	656.2	655.4	654.5	653.7	652.9
150°	675.1	675.1	674.7	673.8	672.9	672.1	671.2
152.5°	692.0	692.3	692.0	691.3	690.6	689.8	689.1
155°	716.9	717.5	717.2	716.2	715.3	714.3	713.3
157.5°	738.0	738.6	738.5	737.8	736.9	736.1	735.3
160°	751.1	751.8	751.9	751.3	750.7	750.2	749.6
162.5°	763.4	764.1	763.9	763.0	762.1	761.2	760.3
165°	778.9	779.8	779.8	778.8	777.7	776.7	775.8
167.5°	791.5	792.4	792.4	791.5	790.7	789.8	788.9
170°	798.5	799.5	799.5	798.5	797.5	796.5	795.5
172.5°	803.8	804.6	804.6	803.6	802.6	801.6	800.6
175°	809.5	810.4	810.3	809.3	808.4	807.3	806.3
177.5°	812.0	812.6	812.6	811.8	811.0	810.2	809.4
180°	811.5	811.5	811.5	811.5	811.5	811.5	811.5

(END OF REPORT)