

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331894

Luminaire Tested: **S123DIP-S340D1025U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331894
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D1025U835-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5164.9 lumens
Efficiency: N/A
Efficacy: 138.5 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331894

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331894

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28				
1	93	89	85	82	83	80	77	74	62	60	59	47	45	44	32	31	31	24				
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	28	27	26	20				
3	77	68	61	56	69	61	56	51	48	44	41	36	34	31	25	24	22	17				
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	23	21	19	15				
5	65	54	46	40	58	48	42	37	38	34	30	29	26	23	20	18	17	13				
6	60	48	40	35	53	43	37	32	35	30	26	26	23	20	18	16	15	12				
7	55	43	36	30	49	39	33	28	31	26	23	24	20	18	17	15	13	10				
8	51	39	32	27	46	35	29	24	28	24	20	22	18	16	15	13	12	9				
9	47	36	28	24	42	32	26	22	26	21	18	20	17	14	14	12	11	8				
10	44	33	26	21	40	30	23	19	24	19	16	18	15	13	13	11	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5175	5175	5175	5175
5°	6172	5198	4606	5198
10°	7725	5172	4161	5172
15°	9475	5129	3874	5129
20°	11287	5065	3688	5065
25°	11986	4986	3646	4986
30°	10274	4928	3665	4928
35°	7144	4846	3704	4846
40°	5382	4749	3693	4749
45°	4468	4606	3646	4606
50°	4002	4315	3612	4315
55°	3742	4001	3567	4001
60°	3511	3670	3531	3670
65°	3298	3347	3418	3347
70°	3094	2977	3254	2977
75°	2770	2608	2986	2608
80°	2424	2139	2572	2139
85°	1902	1556	1729	1556



TEST NUMBER: P331894

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.4	0.9
10°-20°	151.9	2.9
20°-30°	254.9	4.9
30°-40°	288.6	5.6
40°-50°	258.8	5.0
50°-60°	208.9	4.0
60°-70°	145.6	2.8
70°-80°	76.5	1.5
80°-90°	22.5	0.4
90°-100°	274.4	5.3
100°-110°	777.0	15.0
110°-120°	764.4	14.8
120°-130°	609.7	11.8
130°-140°	480.7	9.3
140°-150°	358.8	6.9
150°-160°	250.1	4.8
160°-170°	146.9	2.8
170°-180°	47.8	0.9
0°-30°	454.2	8.8
0°-40°	742.8	14.4
0°-60°	1210.5	23.4
0°-90°	1455.1	28.2
90°-120°	1815.8	35.2
90°-150°	3265.1	63.2
90°-180°	3710.0	71.8
0°-180°	5164.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	481	481	481	481	481	
5°	571	481	426	481	571	59
15°	850	460	348	460	850	246
25°	1009	420	307	420	1009	443
35°	544	369	282	369	544	353
45°	294	303	240	303	294	232
55°	199	213	190	213	199	179
65°	130	131	134	131	130	129
75°	67	63	72	63	67	71
85°	15	13	14	13	15	19
90°	29	2	29	2	29	16
95°	116	34	116	34	116	209
105°	1270	116	1270	116	1270	1253
115°	1544	205	1544	205	1544	1500
125°	1218	284	1218	284	1218	1104
135°	987	333	987	333	987	766
145°	772	380	772	380	772	491
155°	640	432	640	432	640	298
165°	558	472	558	472	558	159
175°	502	492	502	492	502	49
180°	493	493	493	493	493	



TEST NUMBER: P331894

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	510.3	509.9	509.0	509.7	508.2	506.2	506.0	504.1	498.7	498.4	496.9
5°	571.2	569.4	569.1	568.9	565.6	561.2	552.8	552.1	540.9	535.4	528.6
7.5°	650.2	651.1	647.7	644.8	634.8	628.2	619.2	607.7	594.0	580.0	570.8
10°	706.8	714.5	705.0	698.4	692.4	681.0	667.7	651.1	634.6	615.3	600.6
12.5°	767.6	771.3	769.4	763.3	753.9	736.5	713.0	694.7	679.5	647.3	634.3
15°	850.3	864.5	855.4	834.5	834.9	818.4	787.7	753.9	735.9	707.7	669.3
17.5°	938.5	940.2	936.4	918.9	907.3	884.5	856.1	823.8	787.4	753.3	712.5
20°	985.4	984.0	975.9	966.8	946.8	929.1	898.1	862.0	815.4	781.8	737.3
22.5°	1011.5	1009.2	1005.3	997.7	981.1	962.1	934.2	894.8	850.4	804.2	752.8
25°	1009.2	1012.2	1012.7	1010.6	1004.8	993.4	971.5	940.0	895.8	836.3	782.8
27.5°	917.9	922.2	934.6	945.7	958.0	970.6	968.9	953.3	920.5	869.2	803.7
30°	826.6	817.2	840.3	869.4	889.2	924.2	943.7	944.9	926.5	882.5	818.6
32.5°	699.8	710.1	720.3	756.1	799.4	838.6	877.6	908.9	912.5	883.2	827.4
35°	543.7	556.6	575.2	593.8	640.4	680.5	749.0	808.6	856.1	862.4	828.2
37.5°	438.2	444.5	456.3	475.0	505.4	553.0	605.9	681.3	750.2	801.4	803.6
40°	383.0	384.9	398.1	412.3	437.0	476.2	523.9	590.6	673.0	744.6	774.4
42.5°	341.6	345.7	351.4	365.0	384.7	414.1	458.5	513.6	589.2	671.5	729.8
45°	293.5	298.2	301.7	310.8	324.8	344.6	375.5	425.9	483.4	568.4	646.9
47.5°	261.8	262.1	264.7	271.6	281.1	296.0	317.9	350.2	403.0	472.0	552.6
50°	239.0	242.7	243.7	249.0	256.5	267.4	285.6	313.1	356.4	417.0	491.1
52.5°	223.0	224.1	226.7	230.6	237.1	245.6	261.4	282.9	316.9	368.6	436.7
55°	199.4	199.4	202.0	205.0	208.7	216.4	226.9	242.7	268.6	308.7	365.1
57.5°	177.6	178.8	180.6	181.5	184.7	189.8	198.5	210.6	229.8	260.7	305.5
60°	163.1	165.2	164.9	166.8	169.6	173.6	181.0	190.8	208.0	232.7	270.5
62.5°	150.4	150.3	150.2	152.5	155.2	159.0	163.9	172.3	187.0	208.9	241.0
65°	129.5	129.1	130.7	132.1	133.0	135.8	139.5	147.0	156.8	173.1	198.0
67.5°	111.0	109.6	110.5	111.0	112.6	114.8	118.3	122.9	130.6	143.7	162.5
70°	98.3	97.1	96.9	97.4	98.8	100.4	103.0	107.4	114.6	125.1	138.8
72.5°	85.3	84.5	84.4	85.5	86.1	87.2	89.0	93.0	98.8	106.7	119.5
75°	66.6	66.6	66.6	66.9	67.6	68.5	69.9	72.0	76.4	82.0	90.6
77.5°	49.9	49.9	49.6	49.6	50.6	51.0	51.3	53.3	55.8	59.5	65.8
80°	39.1	38.0	38.4	39.1	39.6	39.8	40.5	41.0	43.1	45.2	49.6
82.5°	29.1	28.1	28.2	29.3	29.4	29.6	30.3	30.9	31.7	33.6	36.0
85°	15.4	15.4	15.6	15.6	15.8	15.6	16.3	16.5	16.5	17.7	19.1
87.5°	11.4	11.2	11.2	11.2	11.2	11.0	11.0	11.0	10.9	11.3	10.9
90°	28.9	29.9	28.9	27.9	28.9	27.0	26.0	25.0	24.0	25.0	22.0
92.5°	48.1	49.9	48.9	51.9	53.7	58.9	66.7	84.0	115.8	153.5	168.9
95°	115.8	119.8	126.8	135.8	154.7	190.7	243.6	359.3	480.1	591.9	527.0
97.5°	315.2	323.8	350.8	395.7	469.3	588.7	717.5	895.8	981.4	917.3	671.6
100°	625.9	624.9	663.8	736.7	837.5	979.2	1096.0	1176.9	1141.9	945.3	638.8
102.5°	918.1	941.1	973.6	1031.3	1109.8	1199.6	1267.7	1270.3	1149.9	893.4	590.9
105°	1269.7	1274.7	1306.6	1344.5	1390.5	1416.4	1397.5	1297.6	1089.0	802.5	532.0
107.5°	1472.1	1481.3	1492.1	1504.9	1504.1	1468.5	1381.1	1219.0	982.4	722.3	494.5
110°	1555.2	1557.2	1559.2	1551.2	1523.2	1453.3	1327.6	1143.9	915.3	676.8	480.1



TEST NUMBER: P331894

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1571.9	1571.5	1563.9	1539.2	1488.1	1398.2	1257.3	1069.6	857.0	646.4	472.1
115°	1544.2	1539.2	1519.2	1475.3	1400.4	1291.6	1144.9	971.2	786.6	613.9	469.1
117.5°	1455.9	1449.2	1420.4	1370.1	1292.0	1181.6	1049.9	900.0	744.0	594.7	470.9
120°	1382.5	1376.5	1352.5	1296.6	1217.8	1117.0	997.2	862.4	721.7	585.9	474.1
122.5°	1313.8	1306.2	1279.9	1229.6	1159.5	1065.9	954.9	832.9	703.3	580.3	479.7
125°	1217.8	1210.8	1185.8	1141.9	1078.0	998.2	902.4	793.6	679.8	573.0	488.1
127.5°	1138.7	1132.3	1109.8	1072.2	1015.3	942.7	856.2	759.2	659.0	569.4	497.7
130°	1094.0	1086.0	1065.1	1029.1	976.2	908.3	827.5	737.7	647.8	567.0	504.1
132.5°	1050.1	1044.5	1025.9	990.0	940.3	875.6	800.3	717.7	637.4	566.2	508.9
135°	987.2	980.2	962.2	932.3	883.4	826.5	761.6	690.7	623.9	565.0	516.1
137.5°	920.7	916.1	901.0	870.6	829.5	780.2	724.3	666.2	612.1	562.8	520.8
140°	874.4	875.4	859.4	831.5	793.6	750.6	702.7	651.8	604.9	562.0	524.0
142.5°	831.3	832.3	817.9	793.2	760.8	723.5	682.0	638.2	598.5	560.4	526.4
145°	771.6	769.6	761.6	740.6	715.7	686.7	654.8	621.9	589.9	558.0	528.0
147.5°	722.5	721.7	714.1	699.9	681.0	660.4	634.6	608.5	581.5	554.2	528.0
150°	693.7	693.7	687.7	676.8	661.8	642.8	621.9	598.9	575.9	551.0	528.0
152.5°	669.8	669.8	666.2	656.0	644.2	628.5	609.9	590.1	569.6	547.0	525.6
155°	639.8	638.8	636.8	628.9	619.9	607.9	592.9	576.9	560.0	540.0	523.0
157.5°	612.5	612.7	611.1	605.1	597.3	587.9	576.3	563.0	549.2	533.8	519.7
160°	594.9	595.9	595.9	589.9	582.9	575.9	566.0	555.0	542.0	529.0	518.1
162.5°	578.9	579.9	579.9	574.8	570.2	564.0	554.8	545.4	534.8	524.2	514.9
165°	558.0	558.0	559.0	555.0	551.0	546.0	539.0	533.0	525.0	517.1	510.1
167.5°	538.0	538.0	539.0	536.2	534.4	530.8	526.8	522.2	515.7	509.9	505.3
170°	526.0	526.0	527.0	525.0	524.0	522.0	518.1	515.1	510.1	505.1	502.1
172.5°	514.9	515.7	517.5	515.5	515.3	514.1	510.9	508.7	504.5	501.1	499.7
175°	502.1	503.1	504.1	503.1	503.1	503.1	501.1	500.1	498.1	496.1	496.1
177.5°	494.7	494.7	496.3	495.5	496.3	496.3	495.5	494.7	493.9	493.1	493.9
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P331894

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	495.7	494.3	492.8	490.2	487.9	484.8	483.8	482.7	479.3	476.4	474.1
5°	526.0	520.4	512.3	504.8	498.8	490.6	486.0	481.1	474.1	467.8	462.7
7.5°	557.7	546.7	534.0	520.4	507.6	495.3	485.4	476.5	466.7	457.5	450.2
10°	582.9	567.0	549.3	530.2	513.9	498.1	484.8	473.2	460.6	449.6	440.5
12.5°	611.6	588.1	563.7	540.5	521.2	499.2	483.1	468.3	454.0	440.9	430.7
15°	645.5	615.7	586.8	554.9	525.6	498.1	479.0	460.3	443.8	430.3	417.2
17.5°	676.5	642.7	604.6	565.8	530.4	497.8	471.1	450.0	429.3	412.8	399.8
20°	694.0	655.6	612.5	572.2	533.0	496.7	467.3	442.2	419.8	402.3	387.7
22.5°	709.1	664.1	619.5	576.4	532.8	493.7	460.4	434.5	410.3	393.2	377.6
25°	724.8	670.9	626.2	575.7	527.0	486.4	449.2	419.8	395.6	375.5	359.5
27.5°	738.2	670.5	617.4	563.0	517.7	477.1	437.3	405.8	380.1	358.3	342.0
30°	747.1	671.4	608.3	554.5	508.8	466.9	428.2	396.5	369.5	347.4	332.0
32.5°	752.7	670.8	599.9	542.5	494.6	457.5	418.3	385.5	357.7	336.0	321.2
35°	756.0	666.7	585.4	517.9	471.8	435.6	402.8	368.8	339.7	319.4	302.6
37.5°	749.4	658.1	568.7	494.1	443.6	408.1	380.4	351.5	323.6	301.3	286.8
40°	739.2	652.5	555.6	477.3	424.2	390.0	366.5	338.0	310.5	289.3	275.8
42.5°	719.6	641.2	541.3	458.7	404.1	369.9	348.2	324.4	298.4	278.5	265.0
45°	671.9	616.4	519.7	430.8	374.4	339.0	319.9	302.6	279.1	259.8	248.1
47.5°	605.6	579.2	488.6	401.3	343.3	309.3	289.4	275.6	258.4	242.7	231.6
50°	559.6	548.6	467.6	381.1	322.7	289.3	270.2	257.7	245.3	229.7	219.5
52.5°	506.5	513.2	443.0	360.3	301.6	268.8	250.9	240.9	229.7	216.8	207.9
55°	431.7	456.1	400.5	325.2	270.2	239.0	222.0	213.2	206.6	197.1	189.4
57.5°	361.7	392.8	354.5	289.1	239.4	212.5	196.2	186.6	182.4	177.4	171.3
60°	320.1	350.8	321.7	264.9	218.8	193.1	178.7	170.5	166.3	162.8	157.7
62.5°	283.0	314.1	289.7	240.3	198.4	174.7	162.1	154.1	150.9	149.1	144.7
65°	232.0	258.8	242.5	202.0	169.4	148.4	137.0	131.4	128.4	127.7	124.9
67.5°	188.8	209.2	197.4	167.5	141.9	123.8	114.1	109.3	107.0	106.7	104.6
70°	160.5	179.6	170.5	143.5	121.4	107.2	98.8	94.6	93.2	93.0	91.8
72.5°	138.5	151.8	144.6	122.1	105.0	92.1	85.9	81.5	80.0	80.3	79.5
75°	102.5	112.5	108.3	92.7	79.0	70.6	65.5	62.7	61.3	62.0	61.0
77.5°	73.8	80.1	76.3	65.5	57.0	51.0	47.2	45.5	44.2	44.2	43.8
80°	55.7	59.4	57.3	50.8	43.8	38.7	35.6	34.5	33.8	33.5	33.3
82.5°	39.7	42.8	40.3	35.9	31.1	28.0	26.3	24.8	24.3	24.4	24.2
85°	20.0	21.2	20.3	17.5	15.6	14.2	13.3	12.6	12.1	12.3	11.9
87.5°	10.7	10.3	9.1	8.0	7.2	6.0	5.6	4.9	4.9	5.3	5.7
90°	19.0	16.0	13.0	11.0	9.0	6.0	4.0	2.0	4.0	6.0	9.0
92.5°	126.8	83.8	57.7	42.9	34.5	26.8	18.4	12.4	18.4	26.8	34.5
95°	363.3	214.6	129.8	90.8	64.9	47.9	36.9	33.9	36.9	47.9	64.9
97.5°	398.7	231.0	149.9	107.8	82.2	67.5	58.9	57.9	58.9	67.5	82.2
100°	376.3	228.6	158.7	119.8	95.8	81.9	74.9	73.9	74.9	81.9	95.8
102.5°	357.1	231.8	169.1	133.4	111.8	98.6	92.4	90.6	92.4	98.6	111.8
105°	343.4	240.6	186.7	155.7	136.8	124.8	118.8	115.8	118.8	124.8	136.8
107.5°	342.4	256.9	209.6	180.9	163.1	151.3	145.5	142.5	145.5	151.3	163.1
110°	346.4	270.5	225.6	197.6	180.7	169.7	164.7	161.7	164.7	169.7	180.7



TEST NUMBER: P331894

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	354.4	284.1	242.4	215.2	198.2	187.3	182.3	179.3	182.3	187.3	198.2
115°	367.3	306.4	268.5	241.6	224.6	214.6	208.6	204.6	208.6	214.6	224.6
117.5°	384.5	330.2	292.7	267.7	248.7	239.6	234.6	230.0	234.6	239.6	248.7
120°	397.3	345.4	309.4	284.5	265.5	255.5	250.5	247.5	250.5	255.5	265.5
122.5°	409.3	361.3	326.2	299.7	281.5	270.7	265.7	262.7	265.7	270.7	281.5
125°	428.2	384.3	349.4	322.4	303.4	292.5	286.5	284.5	286.5	292.5	303.4
127.5°	443.8	404.3	370.5	343.6	322.6	311.4	304.0	301.1	304.0	311.4	322.6
130°	454.2	416.2	383.3	356.3	335.4	323.4	314.4	311.4	314.4	323.4	335.4
132.5°	463.8	426.6	394.5	368.3	347.4	333.0	323.2	319.4	323.2	333.0	347.4
135°	476.1	442.2	411.2	384.3	363.3	348.4	337.4	333.4	337.4	348.4	363.3
137.5°	485.3	453.0	423.2	398.3	377.5	361.5	350.8	346.6	350.8	361.5	377.5
140°	490.1	460.2	431.2	406.3	386.3	370.3	360.3	355.4	360.3	370.3	386.3
142.5°	494.9	465.8	437.6	414.2	394.3	379.9	369.1	364.9	369.1	379.9	394.3
145°	500.1	473.1	447.2	424.2	407.3	392.3	383.3	380.3	383.3	392.3	407.3
147.5°	503.3	479.1	455.4	435.8	419.4	406.5	397.7	395.9	397.7	406.5	419.4
150°	504.1	483.1	460.2	442.2	428.2	415.2	407.3	406.3	407.3	415.2	428.2
152.5°	505.7	485.5	465.8	448.6	436.2	424.8	416.8	416.6	416.8	424.8	436.2
155°	506.1	490.1	473.1	459.2	448.2	438.2	432.2	432.2	432.2	438.2	448.2
157.5°	507.1	492.7	479.1	468.3	459.0	450.2	445.4	444.6	445.4	450.2	459.0
160°	507.1	495.1	483.1	473.1	466.1	458.2	454.2	454.2	454.2	458.2	466.1
162.5°	506.3	495.9	485.5	477.1	470.9	464.6	461.4	461.4	461.4	464.6	470.9
165°	504.1	497.1	489.1	482.1	478.1	473.1	471.1	472.1	471.1	473.1	478.1
167.5°	502.5	496.9	491.1	486.7	483.9	480.1	479.1	480.3	479.1	480.1	483.9
170°	500.1	496.1	491.1	489.1	487.1	484.1	483.1	485.1	483.1	484.1	487.1
172.5°	499.3	496.1	491.9	490.7	489.5	487.3	487.1	488.3	487.1	487.3	489.5
175°	497.1	495.1	493.1	492.1	492.1	490.1	491.1	492.1	491.1	490.1	492.1
177.5°	495.5	493.9	493.1	493.1	493.1	492.3	493.1	493.9	493.1	492.3	493.1
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P331894

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	472.8	471.5	469.7	466.9	464.6	461.1	461.1	461.6	461.6	461.5	461.1
5°	458.5	455.0	450.8	445.9	440.8	435.6	434.7	432.8	431.5	430.5	429.4
7.5°	443.3	437.1	431.0	424.2	417.9	412.8	409.2	406.2	404.3	402.2	400.7
10°	433.1	425.4	418.2	411.0	403.0	396.7	392.8	390.0	387.9	386.0	385.1
12.5°	421.0	412.2	404.2	397.3	388.7	382.2	378.4	377.1	374.7	370.7	368.7
15°	403.3	395.1	385.6	375.1	370.9	363.0	358.5	356.4	355.0	352.0	351.1
17.5°	388.1	377.5	366.7	358.9	351.1	344.7	342.2	339.6	337.8	335.3	334.5
20°	376.0	366.5	356.7	348.3	340.1	333.1	331.0	329.2	327.3	326.2	325.2
22.5°	363.7	354.2	346.0	338.2	329.5	324.9	322.7	320.6	319.3	318.5	317.6
25°	346.4	338.0	328.9	322.0	315.0	311.9	310.5	309.4	308.4	307.3	307.0
27.5°	331.0	321.8	314.5	307.9	302.9	300.4	299.0	298.5	298.7	299.1	299.4
30°	319.4	311.0	305.0	299.4	294.7	292.4	292.1	292.1	293.1	293.3	293.8
32.5°	308.8	301.9	295.8	290.4	286.9	285.3	286.2	286.2	286.9	287.5	288.4
35°	293.3	287.2	282.6	277.9	274.9	275.6	276.1	276.5	277.7	279.1	280.0
37.5°	278.5	273.3	268.4	264.8	263.4	264.6	265.8	266.7	268.1	269.2	270.1
40°	267.9	263.9	259.3	256.0	256.5	257.2	258.1	259.3	260.5	261.2	262.1
42.5°	258.0	253.9	250.3	247.6	248.3	249.2	249.7	250.3	251.7	253.0	253.5
45°	243.0	239.7	236.5	234.8	235.3	235.8	236.2	236.9	238.1	239.0	239.3
47.5°	226.1	223.8	221.6	220.0	220.8	220.6	221.2	222.7	223.0	223.6	224.9
50°	215.3	213.2	210.6	210.1	210.1	210.1	210.4	212.2	212.2	213.2	214.1
52.5°	203.3	202.0	200.4	199.5	199.1	199.1	200.1	201.0	201.4	202.7	203.7
55°	185.7	184.3	182.9	182.2	181.7	182.2	184.0	184.5	185.7	186.4	187.1
57.5°	167.3	166.2	165.1	164.7	164.6	165.2	166.2	167.6	167.9	170.1	171.1
60°	155.2	153.5	152.6	152.6	152.1	154.2	153.8	156.1	156.6	158.0	159.6
62.5°	142.7	140.5	140.1	140.1	140.8	141.4	142.0	143.0	144.3	146.0	147.3
65°	122.5	121.4	123.0	122.8	122.3	123.7	123.7	124.9	126.3	127.9	130.5
67.5°	103.5	102.9	103.0	103.0	103.7	104.5	105.2	106.2	107.9	109.6	111.3
70°	90.6	91.3	90.2	91.1	91.8	92.0	92.5	93.9	95.7	96.9	98.8
72.5°	78.1	78.1	78.2	78.6	79.3	79.7	80.2	81.8	83.8	84.8	86.3
75°	60.1	59.9	60.6	60.6	61.7	62.2	62.7	63.4	65.2	66.6	67.8
77.5°	43.9	44.2	44.0	44.8	44.5	44.6	46.0	46.7	46.9	49.7	50.3
80°	33.1	33.5	33.8	34.0	34.2	33.8	35.4	36.1	36.1	37.7	38.9
82.5°	23.8	24.0	24.6	24.9	24.9	25.4	25.5	26.0	26.6	27.3	28.8
85°	11.9	12.6	12.8	12.6	12.8	12.3	13.0	13.3	13.5	13.5	13.5
87.5°	5.9	6.5	6.9	7.7	8.1	8.9	8.7	8.5	8.7	9.5	9.1
90°	11.0	13.0	16.0	19.0	22.0	25.0	24.0	25.0	26.0	27.0	28.9
92.5°	42.9	57.7	83.8	126.8	168.9	153.5	115.8	84.0	66.7	58.9	53.7
95°	90.8	129.8	214.6	363.3	527.0	591.9	480.1	359.3	243.6	190.7	154.7
97.5°	107.8	149.9	231.0	398.7	671.6	917.3	981.4	895.8	717.5	588.7	469.3
100°	119.8	158.7	228.6	376.3	638.8	945.3	1141.9	1176.9	1096.0	979.2	837.5
102.5°	133.4	169.1	231.8	357.1	590.9	893.4	1149.9	1270.3	1267.7	1199.6	1109.8
105°	155.7	186.7	240.6	343.4	532.0	802.5	1089.0	1297.6	1397.5	1416.4	1390.5
107.5°	180.9	209.6	256.9	342.4	494.5	722.3	982.4	1219.0	1381.1	1468.5	1504.1
110°	197.6	225.6	270.5	346.4	480.1	676.8	915.3	1143.9	1327.6	1453.3	1523.2



TEST NUMBER: P331894

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	215.2	242.4	284.1	354.4	472.1	646.4	857.0	1069.6	1257.3	1398.2	1488.1
115°	241.6	268.5	306.4	367.3	469.1	613.9	786.6	971.2	1144.9	1291.6	1400.4
117.5°	267.7	292.7	330.2	384.5	470.9	594.7	744.0	900.0	1049.9	1181.6	1292.0
120°	284.5	309.4	345.4	397.3	474.1	585.9	721.7	862.4	997.2	1117.0	1217.8
122.5°	299.7	326.2	361.3	409.3	479.7	580.3	703.3	832.9	954.9	1065.9	1159.5
125°	322.4	349.4	384.3	428.2	488.1	573.0	679.8	793.6	902.4	998.2	1078.0
127.5°	343.6	370.5	404.3	443.8	497.7	569.4	659.0	759.2	856.2	942.7	1015.3
130°	356.3	383.3	416.2	454.2	504.1	567.0	647.8	737.7	827.5	908.3	976.2
132.5°	368.3	394.5	426.6	463.8	508.9	566.2	637.4	717.7	800.3	875.6	940.3
135°	384.3	411.2	442.2	476.1	516.1	565.0	623.9	690.7	761.6	826.5	883.4
137.5°	398.3	423.2	453.0	485.3	520.8	562.8	612.1	666.2	724.3	780.2	829.5
140°	406.3	431.2	460.2	490.1	524.0	562.0	604.9	651.8	702.7	750.6	793.6
142.5°	414.2	437.6	465.8	494.9	526.4	560.4	598.5	638.2	682.0	723.5	760.8
145°	424.2	447.2	473.1	500.1	528.0	558.0	589.9	621.9	654.8	686.7	715.7
147.5°	435.8	455.4	479.1	503.3	528.0	554.2	581.5	608.5	634.6	660.4	681.0
150°	442.2	460.2	483.1	504.1	528.0	551.0	575.9	598.9	621.9	642.8	661.8
152.5°	448.6	465.8	485.5	505.7	525.6	547.0	569.6	590.1	609.9	628.5	644.2
155°	459.2	473.1	490.1	506.1	523.0	540.0	560.0	576.9	592.9	607.9	619.9
157.5°	468.3	479.1	492.7	507.1	519.7	533.8	549.2	563.0	576.3	587.9	597.3
160°	473.1	483.1	495.1	507.1	518.1	529.0	542.0	555.0	566.0	575.9	582.9
162.5°	477.1	485.5	495.9	506.3	514.9	524.2	534.8	545.4	554.8	564.0	570.2
165°	482.1	489.1	497.1	504.1	510.1	517.1	525.0	533.0	539.0	546.0	551.0
167.5°	486.7	491.1	496.9	502.5	505.3	509.9	515.7	522.2	526.8	530.8	534.4
170°	489.1	491.1	496.1	500.1	502.1	505.1	510.1	515.1	518.1	522.0	524.0
172.5°	490.7	491.9	496.1	499.3	499.7	501.1	504.5	508.7	510.9	514.1	515.3
175°	492.1	493.1	495.1	497.1	496.1	496.1	498.1	500.1	501.1	503.1	503.1
177.5°	493.1	493.1	493.9	495.5	493.9	493.1	493.9	494.7	495.5	496.3	496.3
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P331894

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	459.8	459.6	460.9	460.0	460.9	459.6	459.8	461.1	461.5	461.6	461.6
5°	428.0	428.7	426.3	426.3	426.3	428.7	428.0	429.4	430.5	431.5	432.8
7.5°	399.6	398.6	398.7	397.4	398.7	398.6	399.6	400.7	402.2	404.3	406.2
10°	382.3	380.9	380.4	380.7	380.4	380.9	382.3	385.1	386.0	387.9	390.0
12.5°	367.9	367.7	364.6	364.6	364.6	367.7	367.9	368.7	370.7	374.7	377.1
15°	351.1	346.7	346.2	347.6	346.2	346.7	351.1	351.1	352.0	355.0	356.4
17.5°	334.2	331.8	332.0	331.3	332.0	331.8	334.2	334.5	335.3	337.8	339.6
20°	325.2	323.8	323.6	322.0	323.6	323.8	325.2	325.2	326.2	327.3	329.2
22.5°	317.0	316.6	316.7	314.9	316.7	316.6	317.0	317.6	318.5	319.3	320.6
25°	306.8	308.0	307.0	307.0	307.0	308.0	306.8	307.0	307.3	308.4	309.4
27.5°	299.9	299.9	299.4	299.4	299.4	299.9	299.9	299.4	299.1	298.7	298.5
30°	294.7	294.5	294.9	294.9	294.9	294.5	294.7	293.8	293.3	293.1	292.1
32.5°	289.5	289.8	289.9	290.1	289.9	289.8	289.5	288.4	287.5	286.9	286.2
35°	281.4	281.7	282.4	281.9	282.4	281.7	281.4	280.0	279.1	277.7	276.5
37.5°	270.5	271.6	271.4	271.7	271.4	271.6	270.5	270.1	269.2	268.1	266.7
40°	262.3	263.0	262.8	262.8	262.8	263.0	262.3	262.1	261.2	260.5	259.3
42.5°	253.9	254.4	253.8	253.5	253.8	254.4	253.9	253.5	253.0	251.7	250.3
45°	240.2	239.7	240.4	239.5	240.4	239.7	240.2	239.3	239.0	238.1	236.9
47.5°	224.8	225.3	225.5	226.2	225.5	225.3	224.8	224.9	223.6	223.0	222.7
50°	214.6	216.0	216.0	215.7	216.0	216.0	214.6	214.1	213.2	212.2	212.2
52.5°	204.5	205.1	206.1	206.0	206.1	205.1	204.5	203.7	202.7	201.4	201.0
55°	188.9	189.4	189.9	190.1	189.9	189.4	188.9	187.1	186.4	185.7	184.5
57.5°	172.8	172.6	173.7	174.1	173.7	172.6	172.8	171.1	170.1	167.9	167.6
60°	161.4	161.4	163.3	164.0	163.3	161.4	161.4	159.6	158.0	156.6	156.1
62.5°	149.3	150.1	151.9	151.0	151.9	150.1	149.3	147.3	146.0	144.3	143.0
65°	131.6	133.5	133.3	134.2	133.3	133.5	131.6	130.5	127.9	126.3	124.9
67.5°	113.1	114.3	116.0	116.1	116.0	114.3	113.1	111.3	109.6	107.9	106.2
70°	100.6	101.8	102.7	103.4	102.7	101.8	100.6	98.8	96.9	95.7	93.9
72.5°	88.5	89.1	91.4	90.4	91.4	89.1	88.5	86.3	84.8	83.8	81.8
75°	69.4	71.1	72.5	71.8	72.5	71.1	69.4	67.8	66.6	65.2	63.4
77.5°	51.3	53.0	53.6	53.0	53.6	53.0	51.3	50.3	49.7	46.9	46.7
80°	40.5	40.3	41.7	41.5	41.7	40.3	40.5	38.9	37.7	36.1	36.1
82.5°	29.7	29.5	30.1	30.3	30.1	29.5	29.7	28.8	27.3	26.6	26.0
85°	14.4	15.1	14.2	14.0	14.2	15.1	14.4	13.5	13.5	13.5	13.3
87.5°	8.9	9.1	9.2	8.8	9.2	9.1	8.9	9.1	9.5	8.7	8.5
90°	27.9	28.9	29.9	28.9	29.9	28.9	27.9	28.9	27.0	26.0	25.0
92.5°	51.9	48.9	49.9	48.1	49.9	48.9	51.9	53.7	58.9	66.7	84.0
95°	135.8	126.8	119.8	115.8	119.8	126.8	135.8	154.7	190.7	243.6	359.3
97.5°	395.7	350.8	323.8	315.2	323.8	350.8	395.7	469.3	588.7	717.5	895.8
100°	736.7	663.8	624.9	625.9	624.9	663.8	736.7	837.5	979.2	1096.0	1176.9
102.5°	1031.3	973.6	941.1	918.1	941.1	973.6	1031.3	1109.8	1199.6	1267.7	1270.3
105°	1344.5	1306.6	1274.7	1269.7	1274.7	1306.6	1344.5	1390.5	1416.4	1397.5	1297.6
107.5°	1504.9	1492.1	1481.3	1472.1	1481.3	1492.1	1504.9	1504.1	1468.5	1381.1	1219.0
110°	1551.2	1559.2	1557.2	1555.2	1557.2	1559.2	1551.2	1523.2	1453.3	1327.6	1143.9



TEST NUMBER: P331894

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1539.2	1563.9	1571.5	1571.9	1571.5	1563.9	1539.2	1488.1	1398.2	1257.3	1069.6
115°	1475.3	1519.2	1539.2	1544.2	1539.2	1519.2	1475.3	1400.4	1291.6	1144.9	971.2
117.5°	1370.1	1420.4	1449.2	1455.9	1449.2	1420.4	1370.1	1292.0	1181.6	1049.9	900.0
120°	1296.6	1352.5	1376.5	1382.5	1376.5	1352.5	1296.6	1217.8	1117.0	997.2	862.4
122.5°	1229.6	1279.9	1306.2	1313.8	1306.2	1279.9	1229.6	1159.5	1065.9	954.9	832.9
125°	1141.9	1185.8	1210.8	1217.8	1210.8	1185.8	1141.9	1078.0	998.2	902.4	793.6
127.5°	1072.2	1109.8	1132.3	1138.7	1132.3	1109.8	1072.2	1015.3	942.7	856.2	759.2
130°	1029.1	1065.1	1086.0	1094.0	1086.0	1065.1	1029.1	976.2	908.3	827.5	737.7
132.5°	990.0	1025.9	1044.5	1050.1	1044.5	1025.9	990.0	940.3	875.6	800.3	717.7
135°	932.3	962.2	980.2	987.2	980.2	962.2	932.3	883.4	826.5	761.6	690.7
137.5°	870.6	901.0	916.1	920.7	916.1	901.0	870.6	829.5	780.2	724.3	666.2
140°	831.5	859.4	875.4	874.4	875.4	859.4	831.5	793.6	750.6	702.7	651.8
142.5°	793.2	817.9	832.3	831.3	832.3	817.9	793.2	760.8	723.5	682.0	638.2
145°	740.6	761.6	769.6	771.6	769.6	761.6	740.6	715.7	686.7	654.8	621.9
147.5°	699.9	714.1	721.7	722.5	721.7	714.1	699.9	681.0	660.4	634.6	608.5
150°	676.8	687.7	693.7	693.7	693.7	687.7	676.8	661.8	642.8	621.9	598.9
152.5°	656.0	666.2	669.8	669.8	669.8	666.2	656.0	644.2	628.5	609.9	590.1
155°	628.9	636.8	638.8	639.8	638.8	636.8	628.9	619.9	607.9	592.9	576.9
157.5°	605.1	611.1	612.7	612.5	612.7	611.1	605.1	597.3	587.9	576.3	563.0
160°	589.9	595.9	595.9	594.9	595.9	595.9	589.9	582.9	575.9	566.0	555.0
162.5°	574.8	579.9	579.9	578.9	579.9	579.9	574.8	570.2	564.0	554.8	545.4
165°	555.0	559.0	558.0	558.0	558.0	559.0	555.0	551.0	546.0	539.0	533.0
167.5°	536.2	539.0	538.0	538.0	538.0	539.0	536.2	534.4	530.8	526.8	522.2
170°	525.0	527.0	526.0	526.0	526.0	527.0	525.0	524.0	522.0	518.1	515.1
172.5°	515.5	517.5	515.7	514.9	515.7	517.5	515.5	515.3	514.1	510.9	508.7
175°	503.1	504.1	503.1	502.1	503.1	504.1	503.1	503.1	503.1	501.1	500.1
177.5°	495.5	496.3	494.7	494.7	494.7	496.3	495.5	496.3	496.3	495.5	494.7
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P331894

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	461.1	461.1	464.6	466.9	469.7	471.5	472.8	474.1	476.4	479.3	482.7
5°	434.7	435.6	440.8	445.9	450.8	455.0	458.5	462.7	467.8	474.1	481.1
7.5°	409.2	412.8	417.9	424.2	431.0	437.1	443.3	450.2	457.5	466.7	476.5
10°	392.8	396.7	403.0	411.0	418.2	425.4	433.1	440.5	449.6	460.6	473.2
12.5°	378.4	382.2	388.7	397.3	404.2	412.2	421.0	430.7	440.9	454.0	468.3
15°	358.5	363.0	370.9	375.1	385.6	395.1	403.3	417.2	430.3	443.8	460.3
17.5°	342.2	344.7	351.1	358.9	366.7	377.5	388.1	399.8	412.8	429.3	450.0
20°	331.0	333.1	340.1	348.3	356.7	366.5	376.0	387.7	402.3	419.8	442.2
22.5°	322.7	324.9	329.5	338.2	346.0	354.2	363.7	377.6	393.2	410.3	434.5
25°	310.5	311.9	315.0	322.0	328.9	338.0	346.4	359.5	375.5	395.6	419.8
27.5°	299.0	300.4	302.9	307.9	314.5	321.8	331.0	342.0	358.3	380.1	405.8
30°	292.1	292.4	294.7	299.4	305.0	311.0	319.4	332.0	347.4	369.5	396.5
32.5°	286.2	285.3	286.9	290.4	295.8	301.9	308.8	321.2	336.0	357.7	385.5
35°	276.1	275.6	274.9	277.9	282.6	287.2	293.3	302.6	319.4	339.7	368.8
37.5°	265.8	264.6	263.4	264.8	268.4	273.3	278.5	286.8	301.3	323.6	351.5
40°	258.1	257.2	256.5	256.0	259.3	263.9	267.9	275.8	289.3	310.5	338.0
42.5°	249.7	249.2	248.3	247.6	250.3	253.9	258.0	265.0	278.5	298.4	324.4
45°	236.2	235.8	235.3	234.8	236.5	239.7	243.0	248.1	259.8	279.1	302.6
47.5°	221.2	220.6	220.8	220.0	221.6	223.8	226.1	231.6	242.7	258.4	275.6
50°	210.4	210.1	210.1	210.1	210.6	213.2	215.3	219.5	229.7	245.3	257.7
52.5°	200.1	199.1	199.1	199.5	200.4	202.0	203.3	207.9	216.8	229.7	240.9
55°	184.0	182.2	181.7	182.2	182.9	184.3	185.7	189.4	197.1	206.6	213.2
57.5°	166.2	165.2	164.6	164.7	165.1	166.2	167.3	171.3	177.4	182.4	186.6
60°	153.8	154.2	152.1	152.6	152.6	153.5	155.2	157.7	162.8	166.3	170.5
62.5°	142.0	141.4	140.8	140.1	140.1	140.5	142.7	144.7	149.1	150.9	154.1
65°	123.7	123.7	122.3	122.8	123.0	121.4	122.5	124.9	127.7	128.4	131.4
67.5°	105.2	104.5	103.7	103.0	103.0	102.9	103.5	104.6	106.7	107.0	109.3
70°	92.5	92.0	91.8	91.1	90.2	91.3	90.6	91.8	93.0	93.2	94.6
72.5°	80.2	79.7	79.3	78.6	78.2	78.1	78.1	79.5	80.3	80.0	81.5
75°	62.7	62.2	61.7	60.6	60.6	59.9	60.1	61.0	62.0	61.3	62.7
77.5°	46.0	44.6	44.5	44.8	44.0	44.2	43.9	43.8	44.2	44.2	45.5
80°	35.4	33.8	34.2	34.0	33.8	33.5	33.1	33.3	33.5	33.8	34.5
82.5°	25.5	25.4	24.9	24.9	24.6	24.0	23.8	24.2	24.4	24.3	24.8
85°	13.0	12.3	12.8	12.6	12.8	12.6	11.9	11.9	12.3	12.1	12.6
87.5°	8.7	8.9	8.1	7.7	6.9	6.5	5.9	5.7	5.3	4.9	4.9
90°	24.0	25.0	22.0	19.0	16.0	13.0	11.0	9.0	6.0	4.0	2.0
92.5°	115.8	153.5	168.9	126.8	83.8	57.7	42.9	34.5	26.8	18.4	12.4
95°	480.1	591.9	527.0	363.3	214.6	129.8	90.8	64.9	47.9	36.9	33.9
97.5°	981.4	917.3	671.6	398.7	231.0	149.9	107.8	82.2	67.5	58.9	57.9
100°	1141.9	945.3	638.8	376.3	228.6	158.7	119.8	95.8	81.9	74.9	73.9
102.5°	1149.9	893.4	590.9	357.1	231.8	169.1	133.4	111.8	98.6	92.4	90.6
105°	1089.0	802.5	532.0	343.4	240.6	186.7	155.7	136.8	124.8	118.8	115.8
107.5°	982.4	722.3	494.5	342.4	256.9	209.6	180.9	163.1	151.3	145.5	142.5
110°	915.3	676.8	480.1	346.4	270.5	225.6	197.6	180.7	169.7	164.7	161.7



TEST NUMBER: P331894

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	857.0	646.4	472.1	354.4	284.1	242.4	215.2	198.2	187.3	182.3	179.3
115°	786.6	613.9	469.1	367.3	306.4	268.5	241.6	224.6	214.6	208.6	204.6
117.5°	744.0	594.7	470.9	384.5	330.2	292.7	267.7	248.7	239.6	234.6	230.0
120°	721.7	585.9	474.1	397.3	345.4	309.4	284.5	265.5	255.5	250.5	247.5
122.5°	703.3	580.3	479.7	409.3	361.3	326.2	299.7	281.5	270.7	265.7	262.7
125°	679.8	573.0	488.1	428.2	384.3	349.4	322.4	303.4	292.5	286.5	284.5
127.5°	659.0	569.4	497.7	443.8	404.3	370.5	343.6	322.6	311.4	304.0	301.1
130°	647.8	567.0	504.1	454.2	416.2	383.3	356.3	335.4	323.4	314.4	311.4
132.5°	637.4	566.2	508.9	463.8	426.6	394.5	368.3	347.4	333.0	323.2	319.4
135°	623.9	565.0	516.1	476.1	442.2	411.2	384.3	363.3	348.4	337.4	333.4
137.5°	612.1	562.8	520.8	485.3	453.0	423.2	398.3	377.5	361.5	350.8	346.6
140°	604.9	562.0	524.0	490.1	460.2	431.2	406.3	386.3	370.3	360.3	355.4
142.5°	598.5	560.4	526.4	494.9	465.8	437.6	414.2	394.3	379.9	369.1	364.9
145°	589.9	558.0	528.0	500.1	473.1	447.2	424.2	407.3	392.3	383.3	380.3
147.5°	581.5	554.2	528.0	503.3	479.1	455.4	435.8	419.4	406.5	397.7	395.9
150°	575.9	551.0	528.0	504.1	483.1	460.2	442.2	428.2	415.2	407.3	406.3
152.5°	569.6	547.0	525.6	505.7	485.5	465.8	448.6	436.2	424.8	416.8	416.6
155°	560.0	540.0	523.0	506.1	490.1	473.1	459.2	448.2	438.2	432.2	432.2
157.5°	549.2	533.8	519.7	507.1	492.7	479.1	468.3	459.0	450.2	445.4	444.6
160°	542.0	529.0	518.1	507.1	495.1	483.1	473.1	466.1	458.2	454.2	454.2
162.5°	534.8	524.2	514.9	506.3	495.9	485.5	477.1	470.9	464.6	461.4	461.4
165°	525.0	517.1	510.1	504.1	497.1	489.1	482.1	478.1	473.1	471.1	472.1
167.5°	515.7	509.9	505.3	502.5	496.9	491.1	486.7	483.9	480.1	479.1	480.3
170°	510.1	505.1	502.1	500.1	496.1	491.1	489.1	487.1	484.1	483.1	485.1
172.5°	504.5	501.1	499.7	499.3	496.1	491.9	490.7	489.5	487.3	487.1	488.3
175°	498.1	496.1	496.1	497.1	495.1	493.1	492.1	492.1	490.1	491.1	492.1
177.5°	493.9	493.1	493.9	495.5	493.9	493.1	493.1	493.1	492.3	493.1	493.9
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P331894

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	483.8	484.8	487.9	490.2	492.8	494.3	495.7	496.9	498.4	498.7	504.1
5°	486.0	490.6	498.8	504.8	512.3	520.4	526.0	528.6	535.4	540.9	552.1
7.5°	485.4	495.3	507.6	520.4	534.0	546.7	557.7	570.8	580.0	594.0	607.7
10°	484.8	498.1	513.9	530.2	549.3	567.0	582.9	600.6	615.3	634.6	651.1
12.5°	483.1	499.2	521.2	540.5	563.7	588.1	611.6	634.3	647.3	679.5	694.7
15°	479.0	498.1	525.6	554.9	586.8	615.7	645.5	669.3	707.7	735.9	753.9
17.5°	471.1	497.8	530.4	565.8	604.6	642.7	676.5	712.5	753.3	787.4	823.8
20°	467.3	496.7	533.0	572.2	612.5	655.6	694.0	737.3	781.8	815.4	862.0
22.5°	460.4	493.7	532.8	576.4	619.5	664.1	709.1	752.8	804.2	850.4	894.8
25°	449.2	486.4	527.0	575.7	626.2	670.9	724.8	782.8	836.3	895.8	940.0
27.5°	437.3	477.1	517.7	563.0	617.4	670.5	738.2	803.7	869.2	920.5	953.3
30°	428.2	466.9	508.8	554.5	608.3	671.4	747.1	818.6	882.5	926.5	944.9
32.5°	418.3	457.5	494.6	542.5	599.9	670.8	752.7	827.4	883.2	912.5	908.9
35°	402.8	435.6	471.8	517.9	585.4	666.7	756.0	828.2	862.4	856.1	808.6
37.5°	380.4	408.1	443.6	494.1	568.7	658.1	749.4	803.6	801.4	750.2	681.3
40°	366.5	390.0	424.2	477.3	555.6	652.5	739.2	774.4	744.6	673.0	590.6
42.5°	348.2	369.9	404.1	458.7	541.3	641.2	719.6	729.8	671.5	589.2	513.6
45°	319.9	339.0	374.4	430.8	519.7	616.4	671.9	646.9	568.4	483.4	425.9
47.5°	289.4	309.3	343.3	401.3	488.6	579.2	605.6	552.6	472.0	403.0	350.2
50°	270.2	289.3	322.7	381.1	467.6	548.6	559.6	491.1	417.0	356.4	313.1
52.5°	250.9	268.8	301.6	360.3	443.0	513.2	506.5	436.7	368.6	316.9	282.9
55°	222.0	239.0	270.2	325.2	400.5	456.1	431.7	365.1	308.7	268.6	242.7
57.5°	196.2	212.5	239.4	289.1	354.5	392.8	361.7	305.5	260.7	229.8	210.6
60°	178.7	193.1	218.8	264.9	321.7	350.8	320.1	270.5	232.7	208.0	190.8
62.5°	162.1	174.7	198.4	240.3	289.7	314.1	283.0	241.0	208.9	187.0	172.3
65°	137.0	148.4	169.4	202.0	242.5	258.8	232.0	198.0	173.1	156.8	147.0
67.5°	114.1	123.8	141.9	167.5	197.4	209.2	188.8	162.5	143.7	130.6	122.9
70°	98.8	107.2	121.4	143.5	170.5	179.6	160.5	138.8	125.1	114.6	107.4
72.5°	85.9	92.1	105.0	122.1	144.6	151.8	138.5	119.5	106.7	98.8	93.0
75°	65.5	70.6	79.0	92.7	108.3	112.5	102.5	90.6	82.0	76.4	72.0
77.5°	47.2	51.0	57.0	65.5	76.3	80.1	73.8	65.8	59.5	55.8	53.3
80°	35.6	38.7	43.8	50.8	57.3	59.4	55.7	49.6	45.2	43.1	41.0
82.5°	26.3	28.0	31.1	35.9	40.3	42.8	39.7	36.0	33.6	31.7	30.9
85°	13.3	14.2	15.6	17.5	20.3	21.2	20.0	19.1	17.7	16.5	16.5
87.5°	5.6	6.0	7.2	8.0	9.1	10.3	10.7	10.9	11.3	10.9	11.0
90°	4.0	6.0	9.0	11.0	13.0	16.0	19.0	22.0	25.0	24.0	25.0
92.5°	18.4	26.8	34.5	42.9	57.7	83.8	126.8	168.9	153.5	115.8	84.0
95°	36.9	47.9	64.9	90.8	129.8	214.6	363.3	527.0	591.9	480.1	359.3
97.5°	58.9	67.5	82.2	107.8	149.9	231.0	398.7	671.6	917.3	981.4	895.8
100°	74.9	81.9	95.8	119.8	158.7	228.6	376.3	638.8	945.3	1141.9	1176.9
102.5°	92.4	98.6	111.8	133.4	169.1	231.8	357.1	590.9	893.4	1149.9	1270.3
105°	118.8	124.8	136.8	155.7	186.7	240.6	343.4	532.0	802.5	1089.0	1297.6
107.5°	145.5	151.3	163.1	180.9	209.6	256.9	342.4	494.5	722.3	982.4	1219.0
110°	164.7	169.7	180.7	197.6	225.6	270.5	346.4	480.1	676.8	915.3	1143.9



TEST NUMBER: P331894

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	182.3	187.3	198.2	215.2	242.4	284.1	354.4	472.1	646.4	857.0	1069.6
115°	208.6	214.6	224.6	241.6	268.5	306.4	367.3	469.1	613.9	786.6	971.2
117.5°	234.6	239.6	248.7	267.7	292.7	330.2	384.5	470.9	594.7	744.0	900.0
120°	250.5	255.5	265.5	284.5	309.4	345.4	397.3	474.1	585.9	721.7	862.4
122.5°	265.7	270.7	281.5	299.7	326.2	361.3	409.3	479.7	580.3	703.3	832.9
125°	286.5	292.5	303.4	322.4	349.4	384.3	428.2	488.1	573.0	679.8	793.6
127.5°	304.0	311.4	322.6	343.6	370.5	404.3	443.8	497.7	569.4	659.0	759.2
130°	314.4	323.4	335.4	356.3	383.3	416.2	454.2	504.1	567.0	647.8	737.7
132.5°	323.2	333.0	347.4	368.3	394.5	426.6	463.8	508.9	566.2	637.4	717.7
135°	337.4	348.4	363.3	384.3	411.2	442.2	476.1	516.1	565.0	623.9	690.7
137.5°	350.8	361.5	377.5	398.3	423.2	453.0	485.3	520.8	562.8	612.1	666.2
140°	360.3	370.3	386.3	406.3	431.2	460.2	490.1	524.0	562.0	604.9	651.8
142.5°	369.1	379.9	394.3	414.2	437.6	465.8	494.9	526.4	560.4	598.5	638.2
145°	383.3	392.3	407.3	424.2	447.2	473.1	500.1	528.0	558.0	589.9	621.9
147.5°	397.7	406.5	419.4	435.8	455.4	479.1	503.3	528.0	554.2	581.5	608.5
150°	407.3	415.2	428.2	442.2	460.2	483.1	504.1	528.0	551.0	575.9	598.9
152.5°	416.8	424.8	436.2	448.6	465.8	485.5	505.7	525.6	547.0	569.6	590.1
155°	432.2	438.2	448.2	459.2	473.1	490.1	506.1	523.0	540.0	560.0	576.9
157.5°	445.4	450.2	459.0	468.3	479.1	492.7	507.1	519.7	533.8	549.2	563.0
160°	454.2	458.2	466.1	473.1	483.1	495.1	507.1	518.1	529.0	542.0	555.0
162.5°	461.4	464.6	470.9	477.1	485.5	495.9	506.3	514.9	524.2	534.8	545.4
165°	471.1	473.1	478.1	482.1	489.1	497.1	504.1	510.1	517.1	525.0	533.0
167.5°	479.1	480.1	483.9	486.7	491.1	496.9	502.5	505.3	509.9	515.7	522.2
170°	483.1	484.1	487.1	489.1	491.1	496.1	500.1	502.1	505.1	510.1	515.1
172.5°	487.1	487.3	489.5	490.7	491.9	496.1	499.3	499.7	501.1	504.5	508.7
175°	491.1	490.1	492.1	492.1	493.1	495.1	497.1	496.1	496.1	498.1	500.1
177.5°	493.1	492.3	493.1	493.1	493.1	493.9	495.5	493.9	493.1	493.9	494.7
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P331894

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	506.0	506.2	508.2	509.7	509.0	509.9	510.3
5°	552.8	561.2	565.6	568.9	569.1	569.4	571.2
7.5°	619.2	628.2	634.8	644.8	647.7	651.1	650.2
10°	667.7	681.0	692.4	698.4	705.0	714.5	706.8
12.5°	713.0	736.5	753.9	763.3	769.4	771.3	767.6
15°	787.7	818.4	834.9	834.5	855.4	864.5	850.3
17.5°	856.1	884.5	907.3	918.9	936.4	940.2	938.5
20°	898.1	929.1	946.8	966.8	975.9	984.0	985.4
22.5°	934.2	962.1	981.1	997.7	1005.3	1009.2	1011.5
25°	971.5	993.4	1004.8	1010.6	1012.7	1012.2	1009.2
27.5°	968.9	970.6	958.0	945.7	934.6	922.2	917.9
30°	943.7	924.2	889.2	869.4	840.3	817.2	826.6
32.5°	877.6	838.6	799.4	756.1	720.3	710.1	699.8
35°	749.0	680.5	640.4	593.8	575.2	556.6	543.7
37.5°	605.9	553.0	505.4	475.0	456.3	444.5	438.2
40°	523.9	476.2	437.0	412.3	398.1	384.9	383.0
42.5°	458.5	414.1	384.7	365.0	351.4	345.7	341.6
45°	375.5	344.6	324.8	310.8	301.7	298.2	293.5
47.5°	317.9	296.0	281.1	271.6	264.7	262.1	261.8
50°	285.6	267.4	256.5	249.0	243.7	242.7	239.0
52.5°	261.4	245.6	237.1	230.6	226.7	224.1	223.0
55°	226.9	216.4	208.7	205.0	202.0	199.4	199.4
57.5°	198.5	189.8	184.7	181.5	180.6	178.8	177.6
60°	181.0	173.6	169.6	166.8	164.9	165.2	163.1
62.5°	163.9	159.0	155.2	152.5	150.2	150.3	150.4
65°	139.5	135.8	133.0	132.1	130.7	129.1	129.5
67.5°	118.3	114.8	112.6	111.0	110.5	109.6	111.0
70°	103.0	100.4	98.8	97.4	96.9	97.1	98.3
72.5°	89.0	87.2	86.1	85.5	84.4	84.5	85.3
75°	69.9	68.5	67.6	66.9	66.6	66.6	66.6
77.5°	51.3	51.0	50.6	49.6	49.6	49.9	49.9
80°	40.5	39.8	39.6	39.1	38.4	38.0	39.1
82.5°	30.3	29.6	29.4	29.3	28.2	28.1	29.1
85°	16.3	15.6	15.8	15.6	15.6	15.4	15.4
87.5°	11.0	11.0	11.2	11.2	11.2	11.2	11.4
90°	26.0	27.0	28.9	27.9	28.9	29.9	28.9
92.5°	66.7	58.9	53.7	51.9	48.9	49.9	48.1
95°	243.6	190.7	154.7	135.8	126.8	119.8	115.8
97.5°	717.5	588.7	469.3	395.7	350.8	323.8	315.2
100°	1096.0	979.2	837.5	736.7	663.8	624.9	625.9
102.5°	1267.7	1199.6	1109.8	1031.3	973.6	941.1	918.1
105°	1397.5	1416.4	1390.5	1344.5	1306.6	1274.7	1269.7
107.5°	1381.1	1468.5	1504.1	1504.9	1492.1	1481.3	1472.1
110°	1327.6	1453.3	1523.2	1551.2	1559.2	1557.2	1555.2



TEST NUMBER: P331894

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1257.3	1398.2	1488.1	1539.2	1563.9	1571.5	1571.9
115°	1144.9	1291.6	1400.4	1475.3	1519.2	1539.2	1544.2
117.5°	1049.9	1181.6	1292.0	1370.1	1420.4	1449.2	1455.9
120°	997.2	1117.0	1217.8	1296.6	1352.5	1376.5	1382.5
122.5°	954.9	1065.9	1159.5	1229.6	1279.9	1306.2	1313.8
125°	902.4	998.2	1078.0	1141.9	1185.8	1210.8	1217.8
127.5°	856.2	942.7	1015.3	1072.2	1109.8	1132.3	1138.7
130°	827.5	908.3	976.2	1029.1	1065.1	1086.0	1094.0
132.5°	800.3	875.6	940.3	990.0	1025.9	1044.5	1050.1
135°	761.6	826.5	883.4	932.3	962.2	980.2	987.2
137.5°	724.3	780.2	829.5	870.6	901.0	916.1	920.7
140°	702.7	750.6	793.6	831.5	859.4	875.4	874.4
142.5°	682.0	723.5	760.8	793.2	817.9	832.3	831.3
145°	654.8	686.7	715.7	740.6	761.6	769.6	771.6
147.5°	634.6	660.4	681.0	699.9	714.1	721.7	722.5
150°	621.9	642.8	661.8	676.8	687.7	693.7	693.7
152.5°	609.9	628.5	644.2	656.0	666.2	669.8	669.8
155°	592.9	607.9	619.9	628.9	636.8	638.8	639.8
157.5°	576.3	587.9	597.3	605.1	611.1	612.7	612.5
160°	566.0	575.9	582.9	589.9	595.9	595.9	594.9
162.5°	554.8	564.0	570.2	574.8	579.9	579.9	578.9
165°	539.0	546.0	551.0	555.0	559.0	558.0	558.0
167.5°	526.8	530.8	534.4	536.2	539.0	538.0	538.0
170°	518.1	522.0	524.0	525.0	527.0	526.0	526.0
172.5°	510.9	514.1	515.3	515.5	517.5	515.7	514.9
175°	501.1	503.1	503.1	503.1	504.1	503.1	502.1
177.5°	495.5	496.3	496.3	495.5	496.3	494.7	494.7
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1

(END OF REPORT)