

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331921

Luminaire Tested: **S123DIP-S560D585U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331921  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S560D585U835-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4507.9 lumens  
Efficiency: N/A  
Efficacy: 137.4 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 32.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331921  
CATALOG NUMBER: S123DIP-S560D585U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331921

CATALOG NUMBER: S123DIP-S560D585U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	87	91	88	84	81	75	73	70	63	62	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	38
3	82	73	66	60	76	68	62	57	58	54	50	50	46	43	41	39	37	33
4	75	65	57	51	70	60	53	48	52	47	43	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	30	28	25
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	30	27	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	37	30	25	32	26	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	29	24	20	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8509	8509	8509	8509
5°	10147	8546	7573	8546
10°	12701	8502	6840	8502
15°	15578	8433	6367	8433
20°	18558	8326	6063	8326
25°	19705	8197	5995	8197
30°	16890	8103	6027	8103
35°	11746	7967	6089	7967
40°	8847	7808	6070	7808
45°	7346	7573	5993	7573
50°	6581	7093	5940	7093
55°	6152	6576	5864	6576
60°	5772	6036	5804	6036
65°	5422	5501	5619	5501
70°	5086	4894	5350	4894
75°	4554	4284	4907	4284
80°	3986	3515	4228	3515
85°	3125	2556	2841	2556



TEST NUMBER: P331921

CATALOG NUMBER: S123DIP-S560D585U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	77.9	1.7
10°-20°	249.7	5.5
20°-30°	419.1	9.3
30°-40°	474.5	10.5
40°-50°	425.5	9.4
50°-60°	343.4	7.6
60°-70°	239.3	5.3
70°-80°	125.8	2.8
80°-90°	32.9	0.7
90°-100°	156.8	3.5
100°-110°	444.0	9.8
110°-120°	436.8	9.7
120°-130°	348.4	7.7
130°-140°	274.7	6.1
140°-150°	205.0	4.5
150°-160°	142.9	3.2
160°-170°	83.9	1.9
170°-180°	27.3	0.6
0°-30°	746.6	16.6
0°-40°	1221.1	27.1
0°-60°	1990.1	44.1
0°-90°	2388.1	53.0
90°-120°	1037.6	23.0
90°-150°	1865.7	41.4
90°-180°	2120.0	47.0
0°-180°	4507.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	790	790	790	790	790	
5°	939	791	701	791	939	97
15°	1398	757	571	757	1398	404
25°	1659	690	505	690	1659	728
35°	894	606	463	606	894	581
45°	483	498	394	498	483	382
55°	328	350	312	350	328	294
65°	213	216	221	216	213	212
75°	110	103	118	103	110	117
85°	25	21	23	21	25	30
90°	16	1	16	1	16	10
95°	66	19	66	19	66	119
105°	726	66	726	66	726	716
115°	882	117	882	117	882	857
125°	696	163	696	163	696	631
135°	564	190	564	190	564	438
145°	441	217	441	217	441	280
155°	366	247	366	247	366	171
165°	319	270	319	270	319	91
175°	287	281	287	281	287	28
180°	282	282	282	282	282	



TEST NUMBER: P331921

CATALOG NUMBER: S123DIP-S560D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	838.9	838.3	836.8	838.0	835.5	832.2	831.9	828.8	819.9	819.3	816.9
5°	939.1	936.0	935.7	935.3	929.9	922.6	908.8	907.7	889.3	880.1	869.0
7.5°	1068.9	1070.5	1064.9	1060.0	1043.6	1032.8	1018.0	999.1	976.5	953.6	938.3
10°	1162.0	1174.6	1158.9	1148.2	1138.3	1119.5	1097.7	1070.5	1043.3	1011.5	987.4
12.5°	1261.9	1268.1	1265.0	1254.8	1239.4	1210.8	1172.1	1142.2	1117.1	1064.2	1042.8
15°	1397.9	1421.3	1406.4	1371.9	1372.7	1345.5	1294.9	1239.4	1209.9	1163.5	1100.3
17.5°	1542.9	1545.8	1539.4	1510.7	1491.5	1454.2	1407.5	1354.3	1294.5	1238.5	1171.4
20°	1620.1	1617.8	1604.4	1589.4	1556.5	1527.4	1476.4	1417.1	1340.5	1285.3	1212.2
22.5°	1663.0	1659.1	1652.8	1640.3	1612.9	1581.6	1535.9	1471.0	1398.1	1322.1	1237.6
25°	1659.1	1664.1	1664.9	1661.4	1651.9	1633.1	1597.1	1545.4	1472.6	1375.0	1286.9
27.5°	1509.0	1516.0	1536.5	1554.7	1575.0	1595.6	1592.9	1567.2	1513.4	1429.0	1321.3
30°	1358.9	1343.5	1381.5	1429.3	1461.9	1519.3	1551.5	1553.4	1523.2	1450.8	1345.8
32.5°	1150.5	1167.4	1184.1	1243.0	1314.2	1378.7	1442.7	1494.3	1500.2	1452.0	1360.2
35°	893.9	915.0	945.6	976.3	1052.9	1118.7	1231.3	1329.4	1407.5	1417.8	1361.5
37.5°	720.3	730.8	750.1	780.8	830.9	909.1	996.2	1120.1	1233.3	1317.5	1321.2
40°	629.6	632.7	654.5	677.9	718.5	782.8	861.4	970.9	1106.5	1224.1	1273.1
42.5°	561.6	568.4	577.6	600.1	632.4	680.8	753.8	844.4	968.6	1103.9	1199.8
45°	482.6	490.2	496.0	510.9	533.9	566.4	617.4	700.1	794.7	934.5	1063.6
47.5°	430.3	430.9	435.2	446.5	462.1	486.6	522.6	575.7	662.6	775.9	908.5
50°	393.0	399.1	400.6	409.4	421.7	439.7	469.6	514.7	586.0	685.6	807.4
52.5°	366.6	368.4	372.7	379.1	389.8	403.8	429.7	465.1	521.0	605.9	717.9
55°	327.8	327.8	332.1	337.0	343.2	355.8	373.0	399.1	441.6	507.5	600.2
57.5°	292.0	293.9	296.9	298.4	303.6	312.0	326.4	346.2	377.9	428.6	502.3
60°	268.1	271.5	271.2	274.2	278.8	285.3	297.6	313.7	342.0	382.6	444.7
62.5°	247.3	247.0	247.0	250.6	255.2	261.4	269.4	283.3	307.4	343.4	396.2
65°	212.9	212.2	214.9	217.2	218.7	223.3	229.4	241.7	257.8	284.6	325.5
67.5°	182.5	180.2	181.7	182.5	185.1	188.7	194.4	202.0	214.8	236.3	267.2
70°	161.6	159.7	159.3	160.1	162.4	165.1	169.3	176.6	188.4	205.7	228.3
72.5°	140.2	138.9	138.8	140.5	141.6	143.3	146.3	153.0	162.4	175.3	196.4
75°	109.5	109.5	109.5	109.9	111.1	112.6	114.9	118.3	125.6	134.8	149.0
77.5°	82.1	82.0	81.6	81.5	83.2	83.9	84.4	87.6	91.7	97.9	108.2
80°	64.3	62.4	63.2	64.3	65.1	65.5	66.6	67.4	70.9	74.3	81.6
82.5°	47.8	46.2	46.3	48.1	48.3	48.6	49.8	50.9	52.2	55.3	59.2
85°	25.3	25.3	25.7	25.7	26.0	25.7	26.8	27.2	27.2	29.1	31.4
87.5°	12.5	12.0	12.2	12.4	12.2	12.3	12.5	12.7	12.8	13.3	13.2
90°	16.5	17.1	16.5	16.0	16.5	15.4	14.8	14.3	13.7	14.3	12.5
92.5°	27.5	28.5	27.9	29.7	30.7	33.7	38.1	48.0	66.2	87.7	96.5
95°	66.2	68.4	72.4	77.6	88.4	108.9	139.2	205.3	274.3	338.2	301.2
97.5°	180.1	185.0	200.4	226.1	268.2	336.4	410.0	511.9	560.8	524.2	383.7
100°	357.6	357.1	379.3	420.9	478.5	559.5	626.3	672.5	652.5	540.1	365.0
102.5°	524.6	537.7	556.3	589.3	634.1	685.5	724.4	725.9	657.1	510.5	337.7
105°	725.5	728.4	746.6	768.3	794.5	809.4	798.5	741.5	622.3	458.6	304.0
107.5°	841.2	846.4	852.6	859.9	859.4	839.1	789.2	696.5	561.4	412.7	282.6
110°	888.6	889.8	890.9	886.4	870.4	830.5	758.6	653.6	523.0	386.7	274.3



TEST NUMBER: P331921

CATALOG NUMBER: S123DIP-S560D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	898.2	898.0	893.7	879.5	850.3	799.0	718.4	611.2	489.7	369.4	269.8
115°	882.4	879.5	868.1	843.0	800.2	738.1	654.2	555.0	449.5	350.8	268.1
117.5°	831.9	828.1	811.6	782.9	738.3	675.2	599.9	514.2	425.2	339.8	269.1
120°	790.0	786.5	772.9	740.9	695.9	638.2	569.8	492.8	412.4	334.8	270.9
122.5°	750.7	746.4	731.3	702.6	662.5	609.0	545.6	475.9	401.9	331.6	274.1
125°	695.9	691.9	677.6	652.5	616.0	570.4	515.6	453.4	388.4	327.4	278.9
127.5°	650.7	647.0	634.1	612.7	580.2	538.7	489.3	433.8	376.6	325.3	284.4
130°	625.1	620.6	608.6	588.1	557.8	519.0	472.8	421.5	370.2	324.0	288.0
132.5°	600.0	596.8	586.2	565.7	537.3	500.3	457.3	410.1	364.2	323.5	290.8
135°	564.1	560.1	549.8	532.7	504.8	472.3	435.2	394.7	356.5	322.8	294.9
137.5°	526.1	523.5	514.8	497.5	474.0	445.8	413.9	380.7	349.8	321.6	297.6
140°	499.6	500.2	491.1	475.1	453.4	428.9	401.5	372.5	345.6	321.1	299.4
142.5°	475.0	475.6	467.4	453.2	434.7	413.4	389.7	364.7	342.0	320.2	300.8
145°	440.9	439.8	435.2	423.2	409.0	392.4	374.2	355.3	337.1	318.8	301.7
147.5°	412.8	412.4	408.0	399.9	389.1	377.4	362.6	347.7	332.3	316.7	301.7
150°	396.4	396.4	393.0	386.7	378.2	367.3	355.3	342.2	329.1	314.8	301.7
152.5°	382.7	382.7	380.7	374.8	368.1	359.1	348.5	337.2	325.5	312.6	300.4
155°	365.6	365.0	363.9	359.3	354.2	347.4	338.8	329.7	320.0	308.6	298.9
157.5°	350.0	350.1	349.2	345.8	341.3	336.0	329.3	321.7	313.8	305.0	296.9
160°	339.9	340.5	340.5	337.1	333.1	329.1	323.4	317.1	309.7	302.3	296.0
162.5°	330.8	331.4	331.4	328.4	325.8	322.3	317.0	311.7	305.6	299.6	294.2
165°	318.8	318.8	319.4	317.1	314.8	312.0	308.0	304.6	300.0	295.5	291.5
167.5°	307.4	307.4	308.0	306.4	305.4	303.3	301.0	298.4	294.7	291.3	288.7
170°	300.6	300.6	301.2	300.0	299.4	298.3	296.0	294.3	291.5	288.6	286.9
172.5°	294.2	294.7	295.7	294.5	294.4	293.7	291.9	290.7	288.3	286.3	285.5
175°	286.9	287.5	288.0	287.5	287.5	287.5	286.3	285.8	284.6	283.5	283.5
177.5°	282.7	282.7	283.6	283.1	283.6	283.6	283.1	282.7	282.2	281.8	282.2
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P331921

CATALOG NUMBER: S123DIP-S560D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	815.0	812.6	810.1	805.8	802.1	796.9	795.4	793.6	788.1	783.1	779.5
5°	864.8	855.6	842.2	829.9	820.0	806.6	798.9	790.9	779.4	769.1	760.6
7.5°	916.9	898.8	878.0	855.5	834.5	814.2	797.9	783.4	767.3	752.0	740.2
10°	958.3	932.2	903.1	871.7	844.9	818.8	797.0	777.9	757.2	739.2	724.2
12.5°	1005.4	966.8	926.7	888.5	856.8	820.7	794.3	769.9	746.5	724.8	708.0
15°	1061.3	1012.3	964.8	912.3	864.0	818.8	787.4	756.8	729.6	707.4	685.9
17.5°	1112.1	1056.6	994.0	930.2	872.0	818.4	774.4	739.8	705.8	678.6	657.2
20°	1140.9	1077.7	1006.9	940.6	876.3	816.5	768.3	726.9	690.2	661.4	637.3
22.5°	1165.8	1091.8	1018.5	947.7	876.0	811.6	757.0	714.4	674.5	646.4	620.8
25°	1191.5	1103.0	1029.5	946.4	866.3	799.7	738.4	690.2	650.3	617.4	591.0
27.5°	1213.6	1102.3	1015.0	925.6	851.2	784.4	719.0	667.2	624.9	589.1	562.3
30°	1228.3	1103.8	1000.0	911.5	836.5	767.5	703.9	651.9	607.4	571.0	545.8
32.5°	1237.5	1102.9	986.2	891.9	813.2	752.2	687.7	633.8	588.1	552.4	528.0
35°	1242.8	1096.1	962.5	851.4	775.6	716.2	662.2	606.3	558.4	525.1	497.5
37.5°	1232.1	1082.0	934.9	812.3	729.3	670.9	625.4	577.8	532.0	495.3	471.5
40°	1215.2	1072.8	913.4	784.8	697.4	641.1	602.5	555.7	510.5	475.7	453.5
42.5°	1183.1	1054.1	889.9	754.1	664.3	608.0	572.4	533.4	490.6	457.9	435.7
45°	1104.6	1013.4	854.5	708.2	615.5	557.3	525.9	497.5	458.8	427.0	407.9
47.5°	995.6	952.2	803.3	659.7	564.5	508.5	475.8	453.0	424.7	399.1	380.7
50°	920.0	902.0	768.7	626.6	530.4	475.7	444.3	423.6	403.3	377.6	360.8
52.5°	832.6	843.7	728.2	592.3	495.8	442.0	412.4	396.0	377.6	356.5	341.8
55°	709.7	749.9	658.4	534.7	444.3	393.0	365.0	350.4	339.7	324.0	311.4
57.5°	594.6	645.7	582.8	475.3	393.6	349.4	322.6	306.7	299.8	291.6	281.7
60°	526.2	576.8	528.9	435.5	359.6	317.5	293.8	280.4	273.5	267.7	259.3
62.5°	465.3	516.4	476.2	395.0	326.2	287.2	266.5	253.4	248.0	245.0	237.8
65°	381.5	425.5	398.7	332.1	278.4	244.0	225.2	216.0	211.0	209.9	205.3
67.5°	310.5	344.0	324.5	275.4	233.2	203.4	187.5	179.7	175.9	175.5	172.0
70°	263.9	295.3	280.4	235.9	199.5	176.2	162.4	155.5	153.2	152.8	150.9
72.5°	227.7	249.6	237.8	200.7	172.6	151.4	141.2	134.0	131.4	132.0	130.7
75°	168.5	185.0	178.1	152.4	129.8	116.0	107.6	103.0	100.7	101.9	100.3
77.5°	121.3	131.7	125.5	107.7	93.8	83.8	77.6	74.8	72.7	72.6	71.9
80°	91.5	97.7	94.2	83.5	72.0	63.6	58.6	56.7	55.5	55.2	54.8
82.5°	65.2	70.4	66.3	59.0	51.2	46.1	43.3	40.8	39.9	40.1	39.8
85°	32.9	34.9	33.3	28.7	25.7	23.4	21.8	20.7	19.9	20.3	19.5
87.5°	13.5	13.5	12.2	10.8	9.9	8.7	8.4	7.6	7.2	7.4	7.5
90°	10.8	9.1	7.4	6.3	5.1	3.4	2.3	1.1	2.3	3.4	5.1
92.5°	72.4	47.9	33.0	24.5	19.7	15.3	10.5	7.1	10.5	15.3	19.7
95°	207.6	122.6	74.1	51.9	37.1	27.4	21.1	19.4	21.1	27.4	37.1
97.5°	227.8	132.0	85.7	61.6	47.0	38.6	33.7	33.1	33.7	38.6	47.0
100°	215.0	130.6	90.7	68.4	54.8	46.8	42.8	42.2	42.8	46.8	54.8
102.5°	204.1	132.4	96.6	76.2	63.9	56.4	52.8	51.8	52.8	56.4	63.9
105°	196.2	137.5	106.7	89.0	78.1	71.3	67.9	66.2	67.9	71.3	78.1
107.5°	195.6	146.8	119.8	103.4	93.2	86.5	83.2	81.4	83.2	86.5	93.2
110°	197.9	154.6	128.9	112.9	103.2	97.0	94.1	92.4	94.1	97.0	103.2





TEST NUMBER: P331921

CATALOG NUMBER: S123DIP-S560D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	202.5	162.3	138.5	123.0	113.3	107.0	104.2	102.4	104.2	107.0	113.3
115°	209.9	175.1	153.4	138.0	128.3	122.6	119.2	116.9	119.2	122.6	128.3
117.5°	219.7	188.7	167.2	153.0	142.1	136.9	134.0	131.4	134.0	136.9	142.1
120°	227.0	197.3	176.8	162.6	151.7	146.0	143.2	141.5	143.2	146.0	151.7
122.5°	233.9	206.5	186.4	171.2	160.8	154.7	151.8	150.1	151.8	154.7	160.8
125°	244.7	219.6	199.6	184.2	173.4	167.1	163.7	162.6	163.7	167.1	173.4
127.5°	253.6	231.0	211.7	196.3	184.3	178.0	173.7	172.0	173.7	178.0	184.3
130°	259.5	237.8	219.0	203.6	191.6	184.8	179.7	178.0	179.7	184.8	191.6
132.5°	265.0	243.8	225.4	210.5	198.5	190.3	184.7	182.5	184.7	190.3	198.5
135°	272.1	252.7	235.0	219.6	207.6	199.1	192.8	190.5	192.8	199.1	207.6
137.5°	277.3	258.8	241.8	227.6	215.7	206.6	200.4	198.0	200.4	206.6	215.7
140°	280.1	262.9	246.4	232.1	220.7	211.6	205.9	203.1	205.9	211.6	220.7
142.5°	282.8	266.1	250.1	236.7	225.3	217.1	210.9	208.5	210.9	217.1	225.3
145°	285.8	270.4	255.5	242.4	232.7	224.2	219.0	217.3	219.0	224.2	232.7
147.5°	287.6	273.8	260.2	249.0	239.7	232.3	227.2	226.2	227.2	232.3	239.7
150°	288.0	276.1	262.9	252.7	244.7	237.3	232.7	232.1	232.7	237.3	244.7
152.5°	289.0	277.4	266.1	256.3	249.3	242.8	238.2	238.1	238.2	242.8	249.3
155°	289.2	280.1	270.4	262.4	256.1	250.4	247.0	247.0	247.0	250.4	256.1
157.5°	289.8	281.5	273.8	267.6	262.3	257.2	254.5	254.0	254.5	257.2	262.3
160°	289.8	282.9	276.1	270.4	266.4	261.8	259.5	259.5	259.5	261.8	266.4
162.5°	289.3	283.4	277.4	272.6	269.1	265.5	263.6	263.6	263.6	265.5	269.1
165°	288.0	284.0	279.5	275.5	273.2	270.4	269.2	269.8	269.2	270.4	273.2
167.5°	287.1	283.9	280.6	278.1	276.5	274.3	273.8	274.5	273.8	274.3	276.5
170°	285.8	283.5	280.6	279.5	278.3	276.6	276.1	277.2	276.1	276.6	278.3
172.5°	285.3	283.5	281.1	280.4	279.7	278.5	278.3	279.0	278.3	278.5	279.7
175°	284.0	282.9	281.8	281.2	281.2	280.1	280.6	281.2	280.6	280.1	281.2
177.5°	283.1	282.2	281.8	281.8	281.8	281.3	281.8	282.2	281.8	281.3	281.8
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P331921

CATALOG NUMBER: S123DIP-S560D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	777.3	775.2	772.1	767.5	763.8	758.0	758.0	758.9	758.9	758.6	758.0
5°	753.7	748.0	741.1	733.1	724.6	716.2	714.7	711.6	709.3	707.8	705.9
7.5°	728.8	718.7	708.6	697.4	687.1	678.6	672.7	667.8	664.6	661.3	658.8
10°	712.0	699.3	687.5	675.6	662.6	652.2	645.7	641.1	637.7	634.6	633.1
12.5°	692.1	677.6	664.5	653.2	639.0	628.3	622.1	620.0	615.9	609.5	606.1
15°	663.0	649.6	633.9	616.6	609.7	596.7	589.4	586.0	583.7	578.7	577.2
17.5°	638.1	620.5	602.9	590.0	577.2	566.7	562.6	558.3	555.3	551.2	550.0
20°	618.2	602.5	586.4	572.6	559.2	547.7	544.2	541.2	538.1	536.2	534.7
22.5°	597.9	582.2	568.9	556.0	541.7	534.2	530.4	527.1	524.9	523.6	522.1
25°	569.5	555.7	540.8	529.3	517.8	512.8	510.5	508.6	507.1	505.2	504.8
27.5°	544.1	529.1	517.0	506.2	498.0	493.8	491.6	490.7	491.0	491.7	492.1
30°	525.1	511.3	501.3	492.1	484.5	480.7	480.3	480.3	481.8	482.2	483.0
32.5°	507.6	496.3	486.3	477.4	471.6	469.0	470.5	470.5	471.7	472.7	474.1
35°	482.2	472.2	464.6	456.9	451.9	453.1	453.8	454.6	456.5	458.8	460.4
37.5°	457.9	449.3	441.3	435.3	433.0	435.1	436.9	438.5	440.8	442.5	444.0
40°	440.4	433.9	426.3	420.9	421.7	422.8	424.4	426.3	428.2	429.3	430.9
42.5°	424.2	417.4	411.6	407.1	408.2	409.7	410.6	411.6	413.8	415.9	416.8
45°	399.5	394.1	388.7	386.1	386.8	387.6	388.4	389.5	391.4	393.0	393.3
47.5°	371.7	367.9	364.3	361.7	362.9	362.6	363.6	366.1	366.7	367.6	369.7
50°	353.9	350.4	346.2	345.5	345.5	345.5	345.8	348.9	348.9	350.4	352.0
52.5°	334.3	332.1	329.4	328.0	327.4	327.4	329.0	330.5	331.1	333.3	334.8
55°	305.2	302.9	300.7	299.5	298.7	299.5	302.6	303.3	305.2	306.4	307.5
57.5°	275.0	273.2	271.4	270.8	270.6	271.6	273.3	275.6	276.1	279.6	281.3
60°	255.1	252.4	250.9	250.9	250.1	253.5	252.8	256.6	257.4	259.7	262.4
62.5°	234.5	230.9	230.3	230.3	231.4	232.4	233.5	235.2	237.2	240.1	242.1
65°	201.5	199.5	202.2	201.8	201.1	203.4	203.4	205.3	207.6	210.3	214.5
67.5°	170.1	169.1	169.4	169.4	170.5	171.8	172.9	174.6	177.3	180.2	182.9
70°	149.0	150.1	148.2	149.8	150.9	151.3	152.0	154.3	157.4	159.3	162.4
72.5°	128.5	128.4	128.6	129.2	130.4	131.1	131.8	134.4	137.8	139.4	141.9
75°	98.8	98.4	99.6	99.6	101.5	102.3	103.0	104.2	107.2	109.5	111.5
77.5°	72.2	72.6	72.4	73.7	73.2	73.3	75.7	76.8	77.1	81.7	82.7
80°	54.4	55.2	55.5	55.9	56.3	55.5	58.2	59.4	59.4	62.0	64.0
82.5°	39.1	39.5	40.5	40.9	41.0	41.7	42.0	42.8	43.7	44.9	47.4
85°	19.5	20.7	21.1	20.7	21.1	20.3	21.4	21.8	22.2	22.2	22.2
87.5°	7.4	7.9	8.0	8.6	8.6	9.3	9.2	8.7	8.8	9.8	8.8
90°	6.3	7.4	9.1	10.8	12.5	14.3	13.7	14.3	14.8	15.4	16.5
92.5°	24.5	33.0	47.9	72.4	96.5	87.7	66.2	48.0	38.1	33.7	30.7
95°	51.9	74.1	122.6	207.6	301.2	338.2	274.3	205.3	139.2	108.9	88.4
97.5°	61.6	85.7	132.0	227.8	383.7	524.2	560.8	511.9	410.0	336.4	268.2
100°	68.4	90.7	130.6	215.0	365.0	540.1	652.5	672.5	626.3	559.5	478.5
102.5°	76.2	96.6	132.4	204.1	337.7	510.5	657.1	725.9	724.4	685.5	634.1
105°	89.0	106.7	137.5	196.2	304.0	458.6	622.3	741.5	798.5	809.4	794.5
107.5°	103.4	119.8	146.8	195.6	282.6	412.7	561.4	696.5	789.2	839.1	859.4
110°	112.9	128.9	154.6	197.9	274.3	386.7	523.0	653.6	758.6	830.5	870.4



TEST NUMBER: P331921

CATALOG NUMBER: S123DIP-S560D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	123.0	138.5	162.3	202.5	269.8	369.4	489.7	611.2	718.4	799.0	850.3
115°	138.0	153.4	175.1	209.9	268.1	350.8	449.5	555.0	654.2	738.1	800.2
117.5°	153.0	167.2	188.7	219.7	269.1	339.8	425.2	514.2	599.9	675.2	738.3
120°	162.6	176.8	197.3	227.0	270.9	334.8	412.4	492.8	569.8	638.2	695.9
122.5°	171.2	186.4	206.5	233.9	274.1	331.6	401.9	475.9	545.6	609.0	662.5
125°	184.2	199.6	219.6	244.7	278.9	327.4	388.4	453.4	515.6	570.4	616.0
127.5°	196.3	211.7	231.0	253.6	284.4	325.3	376.6	433.8	489.3	538.7	580.2
130°	203.6	219.0	237.8	259.5	288.0	324.0	370.2	421.5	472.8	519.0	557.8
132.5°	210.5	225.4	243.8	265.0	290.8	323.5	364.2	410.1	457.3	500.3	537.3
135°	219.6	235.0	252.7	272.1	294.9	322.8	356.5	394.7	435.2	472.3	504.8
137.5°	227.6	241.8	258.8	277.3	297.6	321.6	349.8	380.7	413.9	445.8	474.0
140°	232.1	246.4	262.9	280.1	299.4	321.1	345.6	372.5	401.5	428.9	453.4
142.5°	236.7	250.1	266.1	282.8	300.8	320.2	342.0	364.7	389.7	413.4	434.7
145°	242.4	255.5	270.4	285.8	301.7	318.8	337.1	355.3	374.2	392.4	409.0
147.5°	249.0	260.2	273.8	287.6	301.7	316.7	332.3	347.7	362.6	377.4	389.1
150°	252.7	262.9	276.1	288.0	301.7	314.8	329.1	342.2	355.3	367.3	378.2
152.5°	256.3	266.1	277.4	289.0	300.4	312.6	325.5	337.2	348.5	359.1	368.1
155°	262.4	270.4	280.1	289.2	298.9	308.6	320.0	329.7	338.8	347.4	354.2
157.5°	267.6	273.8	281.5	289.8	296.9	305.0	313.8	321.7	329.3	336.0	341.3
160°	270.4	276.1	282.9	289.8	296.0	302.3	309.7	317.1	323.4	329.1	333.1
162.5°	272.6	277.4	283.4	289.3	294.2	299.6	305.6	311.7	317.0	322.3	325.8
165°	275.5	279.5	284.0	288.0	291.5	295.5	300.0	304.6	308.0	312.0	314.8
167.5°	278.1	280.6	283.9	287.1	288.7	291.3	294.7	298.4	301.0	303.3	305.4
170°	279.5	280.6	283.5	285.8	286.9	288.6	291.5	294.3	296.0	298.3	299.4
172.5°	280.4	281.1	283.5	285.3	285.5	286.3	288.3	290.7	291.9	293.7	294.4
175°	281.2	281.8	282.9	284.0	283.5	283.5	284.6	285.8	286.3	287.5	287.5
177.5°	281.8	281.8	282.2	283.1	282.2	281.8	282.2	282.7	283.1	283.6	283.6
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P331921

CATALOG NUMBER: S123DIP-S560D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	755.9	755.6	757.7	756.2	757.7	755.6	755.9	758.0	758.6	758.9	758.9
5°	703.6	704.7	700.9	700.9	700.9	704.7	703.6	705.9	707.8	709.3	711.6
7.5°	657.0	655.3	655.5	653.4	655.5	655.3	657.0	658.8	661.3	664.6	667.8
10°	628.5	626.2	625.4	625.8	625.4	626.2	628.5	633.1	634.6	637.7	641.1
12.5°	604.9	604.4	599.4	599.5	599.4	604.4	604.9	606.1	609.5	615.9	620.0
15°	577.2	569.9	569.1	571.4	569.1	569.9	577.2	577.2	578.7	583.7	586.0
17.5°	549.4	545.5	545.8	544.6	545.8	545.5	549.4	550.0	551.2	555.3	558.3
20°	534.7	532.4	532.0	529.3	532.0	532.4	534.7	534.7	536.2	538.1	541.2
22.5°	521.2	520.4	520.6	517.7	520.6	520.4	521.2	522.1	523.6	524.9	527.1
25°	504.4	506.3	504.8	504.8	504.8	506.3	504.4	504.8	505.2	507.1	508.6
27.5°	493.1	493.0	492.2	492.2	492.2	493.0	493.1	492.1	491.7	491.0	490.7
30°	484.5	484.1	484.9	484.9	484.9	484.1	484.5	483.0	482.2	481.8	480.3
32.5°	475.9	476.4	476.6	476.9	476.6	476.4	475.9	474.1	472.7	471.7	470.5
35°	462.7	463.0	464.2	463.4	464.2	463.0	462.7	460.4	458.8	456.5	454.6
37.5°	444.7	446.5	446.1	446.7	446.1	446.5	444.7	444.0	442.5	440.8	438.5
40°	431.3	432.4	432.0	432.0	432.0	432.4	431.3	430.9	429.3	428.2	426.3
42.5°	417.5	418.3	417.3	416.7	417.3	418.3	417.5	416.8	415.9	413.8	411.6
45°	394.9	394.1	395.3	393.7	395.3	394.1	394.9	393.3	393.0	391.4	389.5
47.5°	369.6	370.4	370.7	371.8	370.7	370.4	369.6	369.7	367.6	366.7	366.1
50°	352.7	355.0	355.0	354.7	355.0	355.0	352.7	352.0	350.4	348.9	348.9
52.5°	336.2	337.3	338.8	338.7	338.8	337.3	336.2	334.8	333.3	331.1	330.5
55°	310.6	311.4	312.1	312.5	312.1	311.4	310.6	307.5	306.4	305.2	303.3
57.5°	284.1	283.8	285.6	286.2	285.6	283.8	284.1	281.3	279.6	276.1	275.6
60°	265.4	265.4	268.5	269.6	268.5	265.4	265.4	262.4	259.7	257.4	256.6
62.5°	245.5	246.7	249.8	248.2	249.8	246.7	245.5	242.1	240.1	237.2	235.2
65°	216.4	219.5	219.1	220.6	219.1	219.5	216.4	214.5	210.3	207.6	205.3
67.5°	186.0	187.9	190.7	190.9	190.7	187.9	186.0	182.9	180.2	177.3	174.6
70°	165.5	167.4	168.9	170.0	168.9	167.4	165.5	162.4	159.3	157.4	154.3
72.5°	145.5	146.5	150.2	148.6	150.2	146.5	145.5	141.9	139.4	137.8	134.4
75°	114.1	116.8	119.1	118.0	119.1	116.8	114.1	111.5	109.5	107.2	104.2
77.5°	84.4	87.1	88.2	87.2	88.2	87.1	84.4	82.7	81.7	77.1	76.8
80°	66.6	66.3	68.6	68.2	68.6	66.3	66.6	64.0	62.0	59.4	59.4
82.5°	48.9	48.5	49.6	49.8	49.6	48.5	48.9	47.4	44.9	43.7	42.8
85°	23.7	24.9	23.4	23.0	23.4	24.9	23.7	22.2	22.2	22.2	21.8
87.5°	8.7	8.8	8.6	8.2	8.6	8.8	8.7	8.8	9.8	8.8	8.7
90°	16.0	16.5	17.1	16.5	17.1	16.5	16.0	16.5	15.4	14.8	14.3
92.5°	29.7	27.9	28.5	27.5	28.5	27.9	29.7	30.7	33.7	38.1	48.0
95°	77.6	72.4	68.4	66.2	68.4	72.4	77.6	88.4	108.9	139.2	205.3
97.5°	226.1	200.4	185.0	180.1	185.0	200.4	226.1	268.2	336.4	410.0	511.9
100°	420.9	379.3	357.1	357.6	357.1	379.3	420.9	478.5	559.5	626.3	672.5
102.5°	589.3	556.3	537.7	524.6	537.7	556.3	589.3	634.1	685.5	724.4	725.9
105°	768.3	746.6	728.4	725.5	728.4	746.6	768.3	794.5	809.4	798.5	741.5
107.5°	859.9	852.6	846.4	841.2	846.4	852.6	859.9	859.4	839.1	789.2	696.5
110°	886.4	890.9	889.8	888.6	889.8	890.9	886.4	870.4	830.5	758.6	653.6



TEST NUMBER: P331921

CATALOG NUMBER: S123DIP-S560D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	879.5	893.7	898.0	898.2	898.0	893.7	879.5	850.3	799.0	718.4	611.2
115°	843.0	868.1	879.5	882.4	879.5	868.1	843.0	800.2	738.1	654.2	555.0
117.5°	782.9	811.6	828.1	831.9	828.1	811.6	782.9	738.3	675.2	599.9	514.2
120°	740.9	772.9	786.5	790.0	786.5	772.9	740.9	695.9	638.2	569.8	492.8
122.5°	702.6	731.3	746.4	750.7	746.4	731.3	702.6	662.5	609.0	545.6	475.9
125°	652.5	677.6	691.9	695.9	691.9	677.6	652.5	616.0	570.4	515.6	453.4
127.5°	612.7	634.1	647.0	650.7	647.0	634.1	612.7	580.2	538.7	489.3	433.8
130°	588.1	608.6	620.6	625.1	620.6	608.6	588.1	557.8	519.0	472.8	421.5
132.5°	565.7	586.2	596.8	600.0	596.8	586.2	565.7	537.3	500.3	457.3	410.1
135°	532.7	549.8	560.1	564.1	560.1	549.8	532.7	504.8	472.3	435.2	394.7
137.5°	497.5	514.8	523.5	526.1	523.5	514.8	497.5	474.0	445.8	413.9	380.7
140°	475.1	491.1	500.2	499.6	500.2	491.1	475.1	453.4	428.9	401.5	372.5
142.5°	453.2	467.4	475.6	475.0	475.6	467.4	453.2	434.7	413.4	389.7	364.7
145°	423.2	435.2	439.8	440.9	439.8	435.2	423.2	409.0	392.4	374.2	355.3
147.5°	399.9	408.0	412.4	412.8	412.4	408.0	399.9	389.1	377.4	362.6	347.7
150°	386.7	393.0	396.4	396.4	396.4	393.0	386.7	378.2	367.3	355.3	342.2
152.5°	374.8	380.7	382.7	382.7	382.7	380.7	374.8	368.1	359.1	348.5	337.2
155°	359.3	363.9	365.0	365.6	365.0	363.9	359.3	354.2	347.4	338.8	329.7
157.5°	345.8	349.2	350.1	350.0	350.1	349.2	345.8	341.3	336.0	329.3	321.7
160°	337.1	340.5	340.5	339.9	340.5	340.5	337.1	333.1	329.1	323.4	317.1
162.5°	328.4	331.4	331.4	330.8	331.4	331.4	328.4	325.8	322.3	317.0	311.7
165°	317.1	319.4	318.8	318.8	318.8	319.4	317.1	314.8	312.0	308.0	304.6
167.5°	306.4	308.0	307.4	307.4	307.4	308.0	306.4	305.4	303.3	301.0	298.4
170°	300.0	301.2	300.6	300.6	300.6	301.2	300.0	299.4	298.3	296.0	294.3
172.5°	294.5	295.7	294.7	294.2	294.7	295.7	294.5	294.4	293.7	291.9	290.7
175°	287.5	288.0	287.5	286.9	287.5	288.0	287.5	287.5	287.5	286.3	285.8
177.5°	283.1	283.6	282.7	282.7	282.7	283.6	283.1	283.6	283.6	283.1	282.7
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P331921

CATALOG NUMBER: S123DIP-S560D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	758.0	758.0	763.8	767.5	772.1	775.2	777.3	779.5	783.1	788.1	793.6
5°	714.7	716.2	724.6	733.1	741.1	748.0	753.7	760.6	769.1	779.4	790.9
7.5°	672.7	678.6	687.1	697.4	708.6	718.7	728.8	740.2	752.0	767.3	783.4
10°	645.7	652.2	662.6	675.6	687.5	699.3	712.0	724.2	739.2	757.2	777.9
12.5°	622.1	628.3	639.0	653.2	664.5	677.6	692.1	708.0	724.8	746.5	769.9
15°	589.4	596.7	609.7	616.6	633.9	649.6	663.0	685.9	707.4	729.6	756.8
17.5°	562.6	566.7	577.2	590.0	602.9	620.5	638.1	657.2	678.6	705.8	739.8
20°	544.2	547.7	559.2	572.6	586.4	602.5	618.2	637.3	661.4	690.2	726.9
22.5°	530.4	534.2	541.7	556.0	568.9	582.2	597.9	620.8	646.4	674.5	714.4
25°	510.5	512.8	517.8	529.3	540.8	555.7	569.5	591.0	617.4	650.3	690.2
27.5°	491.6	493.8	498.0	506.2	517.0	529.1	544.1	562.3	589.1	624.9	667.2
30°	480.3	480.7	484.5	492.1	501.3	511.3	525.1	545.8	571.0	607.4	651.9
32.5°	470.5	469.0	471.6	477.4	486.3	496.3	507.6	528.0	552.4	588.1	633.8
35°	453.8	453.1	451.9	456.9	464.6	472.2	482.2	497.5	525.1	558.4	606.3
37.5°	436.9	435.1	433.0	435.3	441.3	449.3	457.9	471.5	495.3	532.0	577.8
40°	424.4	422.8	421.7	420.9	426.3	433.9	440.4	453.5	475.7	510.5	555.7
42.5°	410.6	409.7	408.2	407.1	411.6	417.4	424.2	435.7	457.9	490.6	533.4
45°	388.4	387.6	386.8	386.1	388.7	394.1	399.5	407.9	427.0	458.8	497.5
47.5°	363.6	362.6	362.9	361.7	364.3	367.9	371.7	380.7	399.1	424.7	453.0
50°	345.8	345.5	345.5	345.5	346.2	350.4	353.9	360.8	377.6	403.3	423.6
52.5°	329.0	327.4	327.4	328.0	329.4	332.1	334.3	341.8	356.5	377.6	396.0
55°	302.6	299.5	298.7	299.5	300.7	302.9	305.2	311.4	324.0	339.7	350.4
57.5°	273.3	271.6	270.6	270.8	271.4	273.2	275.0	281.7	291.6	299.8	306.7
60°	252.8	253.5	250.1	250.9	250.9	252.4	255.1	259.3	267.7	273.5	280.4
62.5°	233.5	232.4	231.4	230.3	230.3	230.9	234.5	237.8	245.0	248.0	253.4
65°	203.4	203.4	201.1	201.8	202.2	199.5	201.5	205.3	209.9	211.0	216.0
67.5°	172.9	171.8	170.5	169.4	169.4	169.1	170.1	172.0	175.5	175.9	179.7
70°	152.0	151.3	150.9	149.8	148.2	150.1	149.0	150.9	152.8	153.2	155.5
72.5°	131.8	131.1	130.4	129.2	128.6	128.4	128.5	130.7	132.0	131.4	134.0
75°	103.0	102.3	101.5	99.6	99.6	98.4	98.8	100.3	101.9	100.7	103.0
77.5°	75.7	73.3	73.2	73.7	72.4	72.6	72.2	71.9	72.6	72.7	74.8
80°	58.2	55.5	56.3	55.9	55.5	55.2	54.4	54.8	55.2	55.5	56.7
82.5°	42.0	41.7	41.0	40.9	40.5	39.5	39.1	39.8	40.1	39.9	40.8
85°	21.4	20.3	21.1	20.7	21.1	20.7	19.5	19.5	20.3	19.9	20.7
87.5°	9.2	9.3	8.6	8.6	8.0	7.9	7.4	7.5	7.4	7.2	7.6
90°	13.7	14.3	12.5	10.8	9.1	7.4	6.3	5.1	3.4	2.3	1.1
92.5°	66.2	87.7	96.5	72.4	47.9	33.0	24.5	19.7	15.3	10.5	7.1
95°	274.3	338.2	301.2	207.6	122.6	74.1	51.9	37.1	27.4	21.1	19.4
97.5°	560.8	524.2	383.7	227.8	132.0	85.7	61.6	47.0	38.6	33.7	33.1
100°	652.5	540.1	365.0	215.0	130.6	90.7	68.4	54.8	46.8	42.8	42.2
102.5°	657.1	510.5	337.7	204.1	132.4	96.6	76.2	63.9	56.4	52.8	51.8
105°	622.3	458.6	304.0	196.2	137.5	106.7	89.0	78.1	71.3	67.9	66.2
107.5°	561.4	412.7	282.6	195.6	146.8	119.8	103.4	93.2	86.5	83.2	81.4
110°	523.0	386.7	274.3	197.9	154.6	128.9	112.9	103.2	97.0	94.1	92.4



TEST NUMBER: P331921

CATALOG NUMBER: S123DIP-S560D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	489.7	369.4	269.8	202.5	162.3	138.5	123.0	113.3	107.0	104.2	102.4
115°	449.5	350.8	268.1	209.9	175.1	153.4	138.0	128.3	122.6	119.2	116.9
117.5°	425.2	339.8	269.1	219.7	188.7	167.2	153.0	142.1	136.9	134.0	131.4
120°	412.4	334.8	270.9	227.0	197.3	176.8	162.6	151.7	146.0	143.2	141.5
122.5°	401.9	331.6	274.1	233.9	206.5	186.4	171.2	160.8	154.7	151.8	150.1
125°	388.4	327.4	278.9	244.7	219.6	199.6	184.2	173.4	167.1	163.7	162.6
127.5°	376.6	325.3	284.4	253.6	231.0	211.7	196.3	184.3	178.0	173.7	172.0
130°	370.2	324.0	288.0	259.5	237.8	219.0	203.6	191.6	184.8	179.7	178.0
132.5°	364.2	323.5	290.8	265.0	243.8	225.4	210.5	198.5	190.3	184.7	182.5
135°	356.5	322.8	294.9	272.1	252.7	235.0	219.6	207.6	199.1	192.8	190.5
137.5°	349.8	321.6	297.6	277.3	258.8	241.8	227.6	215.7	206.6	200.4	198.0
140°	345.6	321.1	299.4	280.1	262.9	246.4	232.1	220.7	211.6	205.9	203.1
142.5°	342.0	320.2	300.8	282.8	266.1	250.1	236.7	225.3	217.1	210.9	208.5
145°	337.1	318.8	301.7	285.8	270.4	255.5	242.4	232.7	224.2	219.0	217.3
147.5°	332.3	316.7	301.7	287.6	273.8	260.2	249.0	239.7	232.3	227.2	226.2
150°	329.1	314.8	301.7	288.0	276.1	262.9	252.7	244.7	237.3	232.7	232.1
152.5°	325.5	312.6	300.4	289.0	277.4	266.1	256.3	249.3	242.8	238.2	238.1
155°	320.0	308.6	298.9	289.2	280.1	270.4	262.4	256.1	250.4	247.0	247.0
157.5°	313.8	305.0	296.9	289.8	281.5	273.8	267.6	262.3	257.2	254.5	254.0
160°	309.7	302.3	296.0	289.8	282.9	276.1	270.4	266.4	261.8	259.5	259.5
162.5°	305.6	299.6	294.2	289.3	283.4	277.4	272.6	269.1	265.5	263.6	263.6
165°	300.0	295.5	291.5	288.0	284.0	279.5	275.5	273.2	270.4	269.2	269.8
167.5°	294.7	291.3	288.7	287.1	283.9	280.6	278.1	276.5	274.3	273.8	274.5
170°	291.5	288.6	286.9	285.8	283.5	280.6	279.5	278.3	276.6	276.1	277.2
172.5°	288.3	286.3	285.5	285.3	283.5	281.1	280.4	279.7	278.5	278.3	279.0
175°	284.6	283.5	283.5	284.0	282.9	281.8	281.2	281.2	280.1	280.6	281.2
177.5°	282.2	281.8	282.2	283.1	282.2	281.8	281.8	281.8	281.3	281.8	282.2
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P331921

CATALOG NUMBER: S123DIP-S560D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	795.4	796.9	802.1	805.8	810.1	812.6	815.0	816.9	819.3	819.9	828.8
5°	798.9	806.6	820.0	829.9	842.2	855.6	864.8	869.0	880.1	889.3	907.7
7.5°	797.9	814.2	834.5	855.5	878.0	898.8	916.9	938.3	953.6	976.5	999.1
10°	797.0	818.8	844.9	871.7	903.1	932.2	958.3	987.4	1011.5	1043.3	1070.5
12.5°	794.3	820.7	856.8	888.5	926.7	966.8	1005.4	1042.8	1064.2	1117.1	1142.2
15°	787.4	818.8	864.0	912.3	964.8	1012.3	1061.3	1100.3	1163.5	1209.9	1239.4
17.5°	774.4	818.4	872.0	930.2	994.0	1056.6	1112.1	1171.4	1238.5	1294.5	1354.3
20°	768.3	816.5	876.3	940.6	1006.9	1077.7	1140.9	1212.2	1285.3	1340.5	1417.1
22.5°	757.0	811.6	876.0	947.7	1018.5	1091.8	1165.8	1237.6	1322.1	1398.1	1471.0
25°	738.4	799.7	866.3	946.4	1029.5	1103.0	1191.5	1286.9	1375.0	1472.6	1545.4
27.5°	719.0	784.4	851.2	925.6	1015.0	1102.3	1213.6	1321.3	1429.0	1513.4	1567.2
30°	703.9	767.5	836.5	911.5	1000.0	1103.8	1228.3	1345.8	1450.8	1523.2	1553.4
32.5°	687.7	752.2	813.2	891.9	986.2	1102.9	1237.5	1360.2	1452.0	1500.2	1494.3
35°	662.2	716.2	775.6	851.4	962.5	1096.1	1242.8	1361.5	1417.8	1407.5	1329.4
37.5°	625.4	670.9	729.3	812.3	934.9	1082.0	1232.1	1321.2	1317.5	1233.3	1120.1
40°	602.5	641.1	697.4	784.8	913.4	1072.8	1215.2	1273.1	1224.1	1106.5	970.9
42.5°	572.4	608.0	664.3	754.1	889.9	1054.1	1183.1	1199.8	1103.9	968.6	844.4
45°	525.9	557.3	615.5	708.2	854.5	1013.4	1104.6	1063.6	934.5	794.7	700.1
47.5°	475.8	508.5	564.5	659.7	803.3	952.2	995.6	908.5	775.9	662.6	575.7
50°	444.3	475.7	530.4	626.6	768.7	902.0	920.0	807.4	685.6	586.0	514.7
52.5°	412.4	442.0	495.8	592.3	728.2	843.7	832.6	717.9	605.9	521.0	465.1
55°	365.0	393.0	444.3	534.7	658.4	749.9	709.7	600.2	507.5	441.6	399.1
57.5°	322.6	349.4	393.6	475.3	582.8	645.7	594.6	502.3	428.6	377.9	346.2
60°	293.8	317.5	359.6	435.5	528.9	576.8	526.2	444.7	382.6	342.0	313.7
62.5°	266.5	287.2	326.2	395.0	476.2	516.4	465.3	396.2	343.4	307.4	283.3
65°	225.2	244.0	278.4	332.1	398.7	425.5	381.5	325.5	284.6	257.8	241.7
67.5°	187.5	203.4	233.2	275.4	324.5	344.0	310.5	267.2	236.3	214.8	202.0
70°	162.4	176.2	199.5	235.9	280.4	295.3	263.9	228.3	205.7	188.4	176.6
72.5°	141.2	151.4	172.6	200.7	237.8	249.6	227.7	196.4	175.3	162.4	153.0
75°	107.6	116.0	129.8	152.4	178.1	185.0	168.5	149.0	134.8	125.6	118.3
77.5°	77.6	83.8	93.8	107.7	125.5	131.7	121.3	108.2	97.9	91.7	87.6
80°	58.6	63.6	72.0	83.5	94.2	97.7	91.5	81.6	74.3	70.9	67.4
82.5°	43.3	46.1	51.2	59.0	66.3	70.4	65.2	59.2	55.3	52.2	50.9
85°	21.8	23.4	25.7	28.7	33.3	34.9	32.9	31.4	29.1	27.2	27.2
87.5°	8.4	8.7	9.9	10.8	12.2	13.5	13.5	13.2	13.3	12.8	12.7
90°	2.3	3.4	5.1	6.3	7.4	9.1	10.8	12.5	14.3	13.7	14.3
92.5°	10.5	15.3	19.7	24.5	33.0	47.9	72.4	96.5	87.7	66.2	48.0
95°	21.1	27.4	37.1	51.9	74.1	122.6	207.6	301.2	338.2	274.3	205.3
97.5°	33.7	38.6	47.0	61.6	85.7	132.0	227.8	383.7	524.2	560.8	511.9
100°	42.8	46.8	54.8	68.4	90.7	130.6	215.0	365.0	540.1	652.5	672.5
102.5°	52.8	56.4	63.9	76.2	96.6	132.4	204.1	337.7	510.5	657.1	725.9
105°	67.9	71.3	78.1	89.0	106.7	137.5	196.2	304.0	458.6	622.3	741.5
107.5°	83.2	86.5	93.2	103.4	119.8	146.8	195.6	282.6	412.7	561.4	696.5
110°	94.1	97.0	103.2	112.9	128.9	154.6	197.9	274.3	386.7	523.0	653.6





TEST NUMBER: P331921

CATALOG NUMBER: S123DIP-S560D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	104.2	107.0	113.3	123.0	138.5	162.3	202.5	269.8	369.4	489.7	611.2
115°	119.2	122.6	128.3	138.0	153.4	175.1	209.9	268.1	350.8	449.5	555.0
117.5°	134.0	136.9	142.1	153.0	167.2	188.7	219.7	269.1	339.8	425.2	514.2
120°	143.2	146.0	151.7	162.6	176.8	197.3	227.0	270.9	334.8	412.4	492.8
122.5°	151.8	154.7	160.8	171.2	186.4	206.5	233.9	274.1	331.6	401.9	475.9
125°	163.7	167.1	173.4	184.2	199.6	219.6	244.7	278.9	327.4	388.4	453.4
127.5°	173.7	178.0	184.3	196.3	211.7	231.0	253.6	284.4	325.3	376.6	433.8
130°	179.7	184.8	191.6	203.6	219.0	237.8	259.5	288.0	324.0	370.2	421.5
132.5°	184.7	190.3	198.5	210.5	225.4	243.8	265.0	290.8	323.5	364.2	410.1
135°	192.8	199.1	207.6	219.6	235.0	252.7	272.1	294.9	322.8	356.5	394.7
137.5°	200.4	206.6	215.7	227.6	241.8	258.8	277.3	297.6	321.6	349.8	380.7
140°	205.9	211.6	220.7	232.1	246.4	262.9	280.1	299.4	321.1	345.6	372.5
142.5°	210.9	217.1	225.3	236.7	250.1	266.1	282.8	300.8	320.2	342.0	364.7
145°	219.0	224.2	232.7	242.4	255.5	270.4	285.8	301.7	318.8	337.1	355.3
147.5°	227.2	232.3	239.7	249.0	260.2	273.8	287.6	301.7	316.7	332.3	347.7
150°	232.7	237.3	244.7	252.7	262.9	276.1	288.0	301.7	314.8	329.1	342.2
152.5°	238.2	242.8	249.3	256.3	266.1	277.4	289.0	300.4	312.6	325.5	337.2
155°	247.0	250.4	256.1	262.4	270.4	280.1	289.2	298.9	308.6	320.0	329.7
157.5°	254.5	257.2	262.3	267.6	273.8	281.5	289.8	296.9	305.0	313.8	321.7
160°	259.5	261.8	266.4	270.4	276.1	282.9	289.8	296.0	302.3	309.7	317.1
162.5°	263.6	265.5	269.1	272.6	277.4	283.4	289.3	294.2	299.6	305.6	311.7
165°	269.2	270.4	273.2	275.5	279.5	284.0	288.0	291.5	295.5	300.0	304.6
167.5°	273.8	274.3	276.5	278.1	280.6	283.9	287.1	288.7	291.3	294.7	298.4
170°	276.1	276.6	278.3	279.5	280.6	283.5	285.8	286.9	288.6	291.5	294.3
172.5°	278.3	278.5	279.7	280.4	281.1	283.5	285.3	285.5	286.3	288.3	290.7
175°	280.6	280.1	281.2	281.2	281.8	282.9	284.0	283.5	283.5	284.6	285.8
177.5°	281.8	281.3	281.8	281.8	281.8	282.2	283.1	282.2	281.8	282.2	282.7
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P331921

CATALOG NUMBER: S123DIP-S560D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	831.9	832.2	835.5	838.0	836.8	838.3	838.9
5°	908.8	922.6	929.9	935.3	935.7	936.0	939.1
7.5°	1018.0	1032.8	1043.6	1060.0	1064.9	1070.5	1068.9
10°	1097.7	1119.5	1138.3	1148.2	1158.9	1174.6	1162.0
12.5°	1172.1	1210.8	1239.4	1254.8	1265.0	1268.1	1261.9
15°	1294.9	1345.5	1372.7	1371.9	1406.4	1421.3	1397.9
17.5°	1407.5	1454.2	1491.5	1510.7	1539.4	1545.8	1542.9
20°	1476.4	1527.4	1556.5	1589.4	1604.4	1617.8	1620.1
22.5°	1535.9	1581.6	1612.9	1640.3	1652.8	1659.1	1663.0
25°	1597.1	1633.1	1651.9	1661.4	1664.9	1664.1	1659.1
27.5°	1592.9	1595.6	1575.0	1554.7	1536.5	1516.0	1509.0
30°	1551.5	1519.3	1461.9	1429.3	1381.5	1343.5	1358.9
32.5°	1442.7	1378.7	1314.2	1243.0	1184.1	1167.4	1150.5
35°	1231.3	1118.7	1052.9	976.3	945.6	915.0	893.9
37.5°	996.2	909.1	830.9	780.8	750.1	730.8	720.3
40°	861.4	782.8	718.5	677.9	654.5	632.7	629.6
42.5°	753.8	680.8	632.4	600.1	577.6	568.4	561.6
45°	617.4	566.4	533.9	510.9	496.0	490.2	482.6
47.5°	522.6	486.6	462.1	446.5	435.2	430.9	430.3
50°	469.6	439.7	421.7	409.4	400.6	399.1	393.0
52.5°	429.7	403.8	389.8	379.1	372.7	368.4	366.6
55°	373.0	355.8	343.2	337.0	332.1	327.8	327.8
57.5°	326.4	312.0	303.6	298.4	296.9	293.9	292.0
60°	297.6	285.3	278.8	274.2	271.2	271.5	268.1
62.5°	269.4	261.4	255.2	250.6	247.0	247.0	247.3
65°	229.4	223.3	218.7	217.2	214.9	212.2	212.9
67.5°	194.4	188.7	185.1	182.5	181.7	180.2	182.5
70°	169.3	165.1	162.4	160.1	159.3	159.7	161.6
72.5°	146.3	143.3	141.6	140.5	138.8	138.9	140.2
75°	114.9	112.6	111.1	109.9	109.5	109.5	109.5
77.5°	84.4	83.9	83.2	81.5	81.6	82.0	82.1
80°	66.6	65.5	65.1	64.3	63.2	62.4	64.3
82.5°	49.8	48.6	48.3	48.1	46.3	46.2	47.8
85°	26.8	25.7	26.0	25.7	25.7	25.3	25.3
87.5°	12.5	12.3	12.2	12.4	12.2	12.0	12.5
90°	14.8	15.4	16.5	16.0	16.5	17.1	16.5
92.5°	38.1	33.7	30.7	29.7	27.9	28.5	27.5
95°	139.2	108.9	88.4	77.6	72.4	68.4	66.2
97.5°	410.0	336.4	268.2	226.1	200.4	185.0	180.1
100°	626.3	559.5	478.5	420.9	379.3	357.1	357.6
102.5°	724.4	685.5	634.1	589.3	556.3	537.7	524.6
105°	798.5	809.4	794.5	768.3	746.6	728.4	725.5
107.5°	789.2	839.1	859.4	859.9	852.6	846.4	841.2
110°	758.6	830.5	870.4	886.4	890.9	889.8	888.6



TEST NUMBER: P331921

CATALOG NUMBER: S123DIP-S560D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	718.4	799.0	850.3	879.5	893.7	898.0	898.2
115°	654.2	738.1	800.2	843.0	868.1	879.5	882.4
117.5°	599.9	675.2	738.3	782.9	811.6	828.1	831.9
120°	569.8	638.2	695.9	740.9	772.9	786.5	790.0
122.5°	545.6	609.0	662.5	702.6	731.3	746.4	750.7
125°	515.6	570.4	616.0	652.5	677.6	691.9	695.9
127.5°	489.3	538.7	580.2	612.7	634.1	647.0	650.7
130°	472.8	519.0	557.8	588.1	608.6	620.6	625.1
132.5°	457.3	500.3	537.3	565.7	586.2	596.8	600.0
135°	435.2	472.3	504.8	532.7	549.8	560.1	564.1
137.5°	413.9	445.8	474.0	497.5	514.8	523.5	526.1
140°	401.5	428.9	453.4	475.1	491.1	500.2	499.6
142.5°	389.7	413.4	434.7	453.2	467.4	475.6	475.0
145°	374.2	392.4	409.0	423.2	435.2	439.8	440.9
147.5°	362.6	377.4	389.1	399.9	408.0	412.4	412.8
150°	355.3	367.3	378.2	386.7	393.0	396.4	396.4
152.5°	348.5	359.1	368.1	374.8	380.7	382.7	382.7
155°	338.8	347.4	354.2	359.3	363.9	365.0	365.6
157.5°	329.3	336.0	341.3	345.8	349.2	350.1	350.0
160°	323.4	329.1	333.1	337.1	340.5	340.5	339.9
162.5°	317.0	322.3	325.8	328.4	331.4	331.4	330.8
165°	308.0	312.0	314.8	317.1	319.4	318.8	318.8
167.5°	301.0	303.3	305.4	306.4	308.0	307.4	307.4
170°	296.0	298.3	299.4	300.0	301.2	300.6	300.6
172.5°	291.9	293.7	294.4	294.5	295.7	294.7	294.2
175°	286.3	287.5	287.5	287.5	288.0	287.5	286.9
177.5°	283.1	283.6	283.6	283.1	283.6	282.7	282.7
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8

(END OF REPORT)