

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831770

Luminaire Tested: S123RDIP-S1000D1025U835-4F0-1E-UDD-G4

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831770
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-17)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D1025U835-4F0-1E-UDD-G4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8014.3 lumens
Efficiency: N/A
Efficacy: 131.4 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 61
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831770

CATALOG NUMBER: S123RDIP-S1000D1025U835-4F0-1E-UDD-G4

Luminous Intensity Polar Plot





TEST NUMBER: P831770

CATALOG NUMBER: S123RDIP-S1000D1025U835-4F0-1E-UDD-G4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20																														
RC	80					70					50					30					10					0																									
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR																																																			
0	108	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54	54	54	47	47	47	41	41	41	36	36	36	32	32	32	28	28	28	25	25	25	23	23	23	21	21	21	19	19	19	18	18	18
1	99	95	92	89	92	89	86	83	76	74	72	65	63	62	54	53	52	47	47	47	41	41	41	36	36	36	32	32	32	28	28	28	25	25	25	23	23	23	21	21	21	19	19	19	18	18	18				
2	91	84	79	74	85	79	74	69	68	64	61	58	55	53	49	47	45	41	41	41	36	36	36	32	32	32	28	28	28	25	25	25	23	23	23	21	21	21	19	19	19	18	18	18							
3	84	75	68	63	78	70	64	59	61	56	52	52	49	46	44	42	40	36	36	36	32	32	32	28	28	28	25	25	25	23	23	23	21	21	21	19	19	19	18	18	18										
4	77	67	60	54	72	63	56	51	55	50	46	47	43	40	40	37	35	32	32	32	28	28	28	25	25	25	23	23	23	21	21	21	19	19	19	18	18	18													
5	71	60	53	47	66	57	50	45	50	44	40	43	39	36	37	34	31	28	28	28	25	25	25	23	23	23	21	21	21	19	19	19	18	18	18																
6	66	55	47	42	61	51	45	40	45	40	36	39	35	32	34	31	28	25	25	25	23	23	23	21	21	21	19	19	19	18	18	18																			
7	62	50	42	37	57	47	40	35	41	36	32	36	32	29	31	28	26	23	23	23	21	21	21	19	19	19	18	18	18																						
8	57	46	38	33	53	43	36	32	38	33	29	33	29	26	29	26	23	21	21	21	19	19	19	18	18	18																									
9	54	42	35	30	50	40	33	29	35	30	26	31	27	24	27	24	21	19	19	19	18	18	18																												
10	50	39	32	27	47	37	31	26	33	28	24	29	25	22	25	22	20	18	18	18	18	18																													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	34929	34929	34929	34929	34929
5°	41474	40151	35149	28414	26379
10°	37576	40783	34974	22766	19530
15°	25872	34968	34604	18607	15450
20°	17999	26922	33909	15690	13580
25°	13715	20518	32898	13944	12514
30°	11939	16404	31635	12949	11593
35°	10962	13838	29843	12107	10751
40°	10002	12357	27500	11282	9983
45°	9033	11301	24972	10500	9216
50°	8199	10428	21990	9736	8266
55°	7416	9575	19125	8989	7092
60°	6646	8708	16613	8163	6702
65°	6133	7725	14301	7335	6337
70°	4982	6678	12478	6637	5149
75°	4371	5311	10568	5506	4537
80°	3961	4494	8660	4618	4289
85°	3619	3940	6570	4187	3940

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 26349 cd/sqm



TEST NUMBER: P831770

CATALOG NUMBER: S123RDIP-S1000D1025U835-4F0-1E-UDD-G4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	295.8	3.7
10°-20°	684.4	8.5
20°-30°	785.3	9.8
30°-40°	774.0	9.7
40°-50°	682.6	8.5
50°-60°	525.1	6.6
60°-70°	345.2	4.3
70°-80°	167.7	2.1
80°-90°	45.0	0.6
90°-100°	267.6	3.3
100°-110°	783.4	9.8
110°-120°	765.0	9.5
120°-130°	609.2	7.6
130°-140°	480.7	6.0
140°-150°	358.6	4.5
150°-160°	250.0	3.1
160°-170°	146.9	1.8
170°-180°	47.8	0.6
0°-30°	1765.5	22.0
0°-40°	2539.5	31.7
0°-60°	3747.2	46.8
0°-90°	4305.2	53.7
90°-120°	1816.0	22.7
90°-150°	3264.5	40.7
90°-180°	3709.0	46.3
0°-180°	8014.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	3245	3245	3245	3245	3245	
5°	3838	3716	3253	2630	2441	351
15°	2322	3138	3105	1670	1386	655
25°	1155	1728	2770	1174	1054	545
35°	834	1053	2271	921	818	520
45°	593	742	1640	690	605	461
55°	395	510	1019	479	378	354
65°	241	303	562	288	249	236
75°	105	128	254	132	109	113
85°	29	32	53	34	32	31
90°	29	25	2	25	29	17
95°	116	592	34	592	116	188
105°	1270	802	116	802	1270	1267
115°	1544	614	205	614	1544	1506
125°	1218	573	284	573	1218	1102
135°	987	565	333	565	987	766
145°	772	558	380	558	772	490
155°	640	540	432	540	640	298
165°	558	517	472	517	558	159
175°	502	496	492	496	502	49
180°	493	493	493	493	493	



TEST NUMBER: P831770

CATALOG NUMBER: S123RDIP-S1000D1025U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0
2.5°	3596.3	3585.0	3573.6	3570.3	3567.0	3556.4	3545.7	3521.8	3497.8	3473.2	3448.6
5°	3838.4	3839.7	3841.1	3837.7	3834.4	3820.4	3806.5	3777.2	3747.9	3716.0	3684.1
7.5°	3763.9	3785.2	3806.5	3810.5	3814.5	3825.1	3835.8	3829.1	3822.4	3810.5	3798.5
10°	3437.9	3436.6	3435.3	3459.2	3483.2	3554.4	3625.5	3662.1	3698.7	3731.3	3763.9
12.5°	2905.8	2907.7	2909.7	2988.2	3066.7	3133.9	3201.1	3294.2	3387.4	3487.8	3588.3
15°	2321.7	2354.3	2386.9	2456.7	2526.6	2627.7	2728.8	2853.9	2978.9	3137.9	3296.9
17.5°	1906.6	1920.5	1934.5	2001.7	2068.9	2164.7	2260.5	2402.2	2543.9	2748.8	2953.6
20°	1571.3	1583.9	1596.6	1645.1	1693.7	1785.5	1877.3	2012.3	2147.4	2350.3	2553.2
22.5°	1311.8	1336.5	1361.1	1393.7	1426.3	1492.8	1559.3	1697.0	1834.7	2019.7	2204.6
25°	1154.8	1166.2	1177.5	1205.4	1233.3	1297.2	1361.1	1452.2	1543.3	1727.6	1911.9
27.5°	1048.4	1051.7	1055.1	1075.7	1096.3	1137.6	1178.8	1263.3	1347.8	1499.4	1651.1
30°	960.6	966.6	972.6	988.5	1004.5	1034.4	1064.4	1124.2	1184.1	1319.8	1455.5
32.5°	892.7	896.1	899.4	912.7	926.0	948.0	969.9	1017.1	1064.4	1168.2	1271.9
35°	834.2	834.9	835.5	845.5	855.5	876.8	898.1	937.3	976.6	1053.1	1129.6
37.5°	767.7	772.3	777.0	784.3	791.6	810.3	828.9	860.8	892.7	955.9	1019.1
40°	711.8	715.8	719.8	728.4	737.1	751.7	766.4	795.6	824.9	879.4	934.0
42.5°	655.9	658.6	661.2	669.9	678.5	696.5	714.5	737.7	761.0	806.3	851.5
45°	593.4	600.0	606.7	616.0	625.3	640.6	655.9	679.9	703.8	742.4	781.0
47.5°	541.5	544.8	548.2	556.1	564.1	582.7	601.4	622.7	643.9	679.9	715.8
50°	489.6	490.9	492.3	499.6	506.9	523.5	540.2	564.8	589.4	622.7	655.9
52.5°	440.4	443.7	447.0	454.4	461.7	473.0	484.3	509.6	534.8	567.4	600.0
55°	395.2	397.1	399.1	404.5	409.8	423.1	436.4	458.3	480.3	510.2	540.2
57.5°	352.6	355.2	357.9	361.9	365.9	377.9	389.8	409.1	428.4	458.3	488.3
60°	308.7	312.0	315.3	320.0	324.6	333.9	343.3	360.6	377.9	404.5	431.1
62.5°	276.7	277.4	278.1	282.1	286.1	292.7	299.4	313.3	327.3	353.9	380.5
65°	240.8	242.8	244.8	246.8	248.8	254.1	259.4	271.4	283.4	303.3	323.3
67.5°	203.6	205.6	207.6	210.9	214.2	218.9	223.5	231.5	239.5	258.1	276.7
70°	158.3	158.3	158.3	163.6	169.0	177.0	184.9	190.9	196.9	212.2	227.5
72.5°	129.1	129.7	130.4	131.1	131.7	136.4	141.0	151.0	161.0	170.3	179.6
75°	105.1	105.8	106.4	107.1	107.8	109.1	110.4	113.8	117.1	127.7	138.4
77.5°	83.8	84.5	85.2	85.8	86.5	87.8	89.1	90.5	91.8	95.8	99.8
80°	63.9	64.5	65.2	65.9	66.5	67.2	67.9	69.2	70.5	72.5	74.5
82.5°	46.6	46.6	46.6	46.6	46.6	47.9	49.2	49.2	49.2	50.6	51.9
85°	29.3	29.3	29.3	29.9	30.6	30.6	30.6	31.3	31.9	31.9	31.9
87.5°	13.3	12.6	12.0	12.6	13.3	13.3	13.3	14.0	14.6	14.6	14.6
90°	28.9	29.9	28.9	27.9	28.9	27.0	26.0	25.0	24.0	25.0	22.0
92.5°	52.9	54.9	53.9	57.9	59.9	66.9	76.9	98.8	138.7	185.7	205.6
95°	115.8	119.8	126.8	135.8	154.7	190.7	243.6	359.3	480.1	591.9	527.0
97.5°	237.6	248.5	272.5	310.4	377.3	491.1	622.9	825.5	941.3	910.3	679.8
100°	625.9	624.9	663.8	736.7	837.5	979.2	1096.0	1176.9	1141.9	945.3	638.8
102.5°	991.2	1020.1	1051.1	1105.0	1177.9	1254.7	1310.6	1293.6	1151.9	880.4	578.9
105°	1269.7	1274.7	1306.6	1344.5	1390.5	1416.4	1397.5	1297.6	1089.0	802.5	532.0
107.5°	1451.4	1462.3	1475.3	1493.3	1499.3	1472.3	1394.5	1237.7	999.2	733.7	498.1
110°	1555.2	1557.2	1559.2	1551.2	1523.2	1453.3	1327.6	1143.9	915.3	676.8	480.1



TEST NUMBER: P831770

CATALOG NUMBER: S123RDIP-S1000D1025U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1576.1	1575.1	1565.1	1536.2	1479.3	1384.5	1239.7	1051.1	842.5	638.8	470.1
115°	1544.2	1539.2	1519.2	1475.3	1400.4	1291.6	1144.9	971.2	786.6	613.9	469.1
117.5°	1474.3	1467.3	1437.4	1388.5	1310.6	1197.8	1063.1	909.3	749.6	596.9	470.1
120°	1382.5	1376.5	1352.5	1296.6	1217.8	1117.0	997.2	862.4	721.7	585.9	474.1
122.5°	1296.6	1288.6	1261.7	1212.8	1144.9	1053.1	944.3	825.5	698.7	578.9	481.1
125°	1217.8	1210.8	1185.8	1141.9	1078.0	998.2	902.4	793.6	679.8	573.0	488.1
127.5°	1149.9	1143.9	1121.0	1083.0	1025.1	951.3	863.4	764.6	661.8	570.0	496.1
130°	1094.0	1086.0	1065.1	1029.1	976.2	908.3	827.5	737.7	647.8	567.0	504.1
132.5°	1039.1	1034.1	1016.1	980.2	931.3	867.4	793.6	712.7	634.8	566.0	510.1
135°	987.2	980.2	962.2	932.3	883.4	826.5	761.6	690.7	623.9	565.0	516.1
137.5°	932.3	926.3	911.3	880.4	838.5	787.6	729.7	669.8	613.9	563.0	520.1
140°	874.4	875.4	859.4	831.5	793.6	750.6	702.7	651.8	604.9	562.0	524.0
142.5°	820.5	821.5	807.5	783.6	752.6	716.7	676.8	634.8	596.9	560.0	527.0
145°	771.6	769.6	761.6	740.6	715.7	686.7	654.8	621.9	589.9	558.0	528.0
147.5°	729.7	728.7	720.7	705.7	685.7	664.8	637.8	610.9	582.9	555.0	528.0
150°	693.7	693.7	687.7	676.8	661.8	642.8	621.9	598.9	575.9	551.0	528.0
152.5°	663.8	663.8	660.8	650.8	639.8	624.9	606.9	587.9	568.0	546.0	525.0
155°	639.8	638.8	636.8	628.9	619.9	607.9	592.9	576.9	560.0	540.0	523.0
157.5°	616.9	616.9	614.9	608.9	600.9	590.9	578.9	565.0	551.0	535.0	520.1
160°	594.9	595.9	595.9	589.9	582.9	575.9	566.0	555.0	542.0	529.0	518.1
162.5°	575.0	575.9	575.9	571.0	567.0	561.0	552.0	543.0	533.0	523.0	514.1
165°	558.0	558.0	559.0	555.0	551.0	546.0	539.0	533.0	525.0	517.1	510.1
167.5°	541.0	541.0	542.0	539.0	537.0	533.0	529.0	524.0	517.1	511.1	506.1
170°	526.0	526.0	527.0	525.0	524.0	522.0	518.1	515.1	510.1	505.1	502.1
172.5°	512.1	513.1	515.1	513.1	513.1	512.1	509.1	507.1	503.1	500.1	499.1
175°	502.1	503.1	504.1	503.1	503.1	503.1	501.1	500.1	498.1	496.1	496.1
177.5°	495.1	495.1	497.1	496.1	497.1	497.1	496.1	495.1	494.1	493.1	494.1
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P831770

CATALOG NUMBER: S123RDIP-S1000D1025U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0
2.5°	3445.3	3441.9	3410.0	3378.1	3346.8	3315.5	3292.3	3269.0	3229.7	3190.5	3165.9
5°	3658.8	3633.5	3583.0	3532.4	3456.6	3380.7	3316.9	3253.0	3171.8	3090.7	3022.8
7.5°	3777.9	3757.3	3696.1	3634.8	3534.4	3433.9	3334.2	3234.4	3114.6	2994.9	2892.4
10°	3781.2	3798.5	3747.9	3697.4	3584.3	3471.2	3335.5	3199.8	3038.8	2877.8	2745.4
12.5°	3662.8	3737.3	3726.7	3716.0	3600.9	3485.8	3320.9	3155.9	2958.3	2760.7	2595.1
15°	3441.3	3585.6	3628.2	3670.8	3575.6	3480.5	3292.9	3105.3	2873.2	2641.0	2450.7
17.5°	3155.9	3358.1	3470.5	3583.0	3513.8	3444.6	3239.0	3033.5	2772.0	2510.6	2303.7
20°	2817.9	3082.7	3259.0	3435.3	3410.0	3384.7	3172.5	2960.3	2678.2	2396.2	2172.0
22.5°	2484.0	2763.4	3006.9	3250.3	3276.3	3302.2	3088.0	2873.8	2565.1	2256.5	2028.3
25°	2195.9	2480.0	2770.0	3060.1	3118.6	3177.2	2973.6	2770.0	2450.1	2130.1	1903.2
27.5°	1921.2	2191.3	2510.6	2829.9	2936.4	3042.8	2856.5	2670.3	2337.0	2003.7	1777.5
30°	1697.0	1938.5	2264.5	2590.4	2738.8	2887.1	2716.2	2545.2	2214.6	1883.9	1662.4
32.5°	1488.1	1704.3	2031.6	2358.9	2531.2	2703.5	2555.8	2408.2	2090.2	1772.2	1553.3
35°	1323.2	1516.7	1822.1	2127.4	2320.3	2513.3	2392.2	2271.1	1960.5	1649.8	1442.9
37.5°	1181.5	1343.8	1630.5	1917.2	2122.1	2327.0	2225.9	2124.8	1832.7	1540.7	1345.1
40°	1064.4	1194.8	1461.5	1728.3	1929.2	2130.1	2043.6	1957.1	1695.7	1434.2	1251.3
42.5°	963.9	1076.4	1315.8	1555.3	1739.6	1923.9	1866.7	1809.4	1572.6	1335.8	1166.2
45°	875.5	969.9	1180.8	1391.7	1561.3	1730.9	1685.7	1640.5	1436.2	1232.0	1076.4
47.5°	797.0	878.1	1066.4	1254.6	1407.0	1559.3	1517.4	1475.5	1306.5	1137.6	995.9
50°	725.1	794.3	951.3	1108.3	1245.3	1382.4	1347.8	1313.2	1173.5	1033.8	911.4
52.5°	657.3	714.5	855.5	996.5	1107.0	1217.4	1190.8	1164.2	1056.4	948.6	837.5
55°	592.7	645.3	764.4	883.4	977.9	1072.4	1045.8	1019.1	935.3	851.5	753.7
57.5°	534.2	580.1	676.5	773.0	848.2	923.3	910.7	898.1	828.2	758.4	677.9
60°	472.3	513.6	596.7	679.9	740.4	800.9	786.3	771.7	721.8	671.9	602.7
62.5°	417.1	453.7	520.2	586.7	636.0	685.2	674.5	663.9	626.0	588.1	530.9
65°	359.2	395.2	449.0	502.9	541.5	580.1	570.8	561.5	532.9	504.2	458.3
67.5°	306.7	336.6	383.2	429.7	455.7	481.6	476.3	471.0	449.0	427.1	391.2
70°	253.5	279.4	318.0	356.6	374.5	392.5	394.5	396.5	376.5	356.6	330.0
72.5°	200.2	220.9	256.8	292.7	306.7	320.6	320.0	319.3	307.3	295.4	271.4
75°	153.7	169.0	196.9	224.8	236.8	248.8	251.5	254.1	242.8	231.5	218.2
77.5°	110.4	121.1	142.4	163.6	177.0	190.3	191.6	192.9	187.6	182.3	169.6
80°	77.8	81.2	94.5	107.8	121.7	135.7	137.7	139.7	134.4	129.1	121.1
82.5°	53.9	55.9	60.5	65.2	76.5	87.8	90.5	93.1	90.5	87.8	79.2
85°	32.6	33.3	35.3	37.3	42.6	47.9	50.6	53.2	51.9	50.6	45.9
87.5°	14.6	14.6	15.3	16.0	17.3	18.6	22.0	25.3	23.3	21.3	19.3
90°	19.0	16.0	13.0	11.0	9.0	6.0	4.0	2.0	4.0	6.0	9.0
92.5°	153.7	100.8	68.9	50.9	40.9	31.9	22.0	15.0	22.0	31.9	40.9
95°	363.3	214.6	129.8	90.8	64.9	47.9	36.9	33.9	36.9	47.9	64.9
97.5°	404.3	231.6	147.7	104.8	78.9	63.9	54.9	53.9	54.9	63.9	78.9
100°	376.3	228.6	158.7	119.8	95.8	81.9	74.9	73.9	74.9	81.9	95.8
102.5°	352.4	232.6	171.7	136.8	115.8	102.8	96.8	94.8	96.8	102.8	115.8
105°	343.4	240.6	186.7	155.7	136.8	124.8	118.8	115.8	118.8	124.8	136.8
107.5°	341.4	253.5	205.6	176.7	158.7	146.7	140.7	137.7	140.7	146.7	158.7
110°	346.4	270.5	225.6	197.6	180.7	169.7	164.7	161.7	164.7	169.7	180.7



TEST NUMBER: P831770

CATALOG NUMBER: S123RDIP-S1000D1025U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	356.3	287.5	246.6	219.6	202.6	191.7	186.7	183.7	186.7	191.7	202.6
115°	367.3	306.4	268.5	241.6	224.6	214.6	208.6	204.6	208.6	214.6	224.6
117.5°	381.3	326.4	288.5	263.5	244.6	235.6	230.6	225.6	230.6	235.6	244.6
120°	397.3	345.4	309.4	284.5	265.5	255.5	250.5	247.5	250.5	255.5	265.5
122.5°	412.2	365.3	330.4	303.4	285.5	274.5	269.5	266.5	269.5	274.5	285.5
125°	428.2	384.3	349.4	322.4	303.4	292.5	286.5	284.5	286.5	292.5	303.4
127.5°	441.2	401.3	367.3	340.4	319.4	308.4	301.5	298.5	301.5	308.4	319.4
130°	454.2	416.2	383.3	356.3	335.4	323.4	314.4	311.4	314.4	323.4	335.4
132.5°	466.1	429.2	397.3	371.3	350.4	335.4	325.4	321.4	325.4	335.4	350.4
135°	476.1	442.2	411.2	384.3	363.3	348.4	337.4	333.4	337.4	348.4	363.3
137.5°	484.1	451.2	421.2	396.3	375.3	359.3	348.4	344.4	348.4	359.3	375.3
140°	490.1	460.2	431.2	406.3	386.3	370.3	360.3	355.4	360.3	370.3	386.3
142.5°	496.1	467.1	439.2	416.2	396.3	382.3	371.3	367.3	371.3	382.3	396.3
145°	500.1	473.1	447.2	424.2	407.3	392.3	383.3	380.3	383.3	392.3	407.3
147.5°	503.1	478.1	454.2	434.2	417.2	404.3	395.3	393.3	395.3	404.3	417.2
150°	504.1	483.1	460.2	442.2	428.2	415.2	407.3	406.3	407.3	415.2	428.2
152.5°	506.1	486.1	467.1	450.2	438.2	427.2	419.2	419.2	419.2	427.2	438.2
155°	506.1	490.1	473.1	459.2	448.2	438.2	432.2	432.2	432.2	438.2	448.2
157.5°	507.1	492.1	478.1	467.1	457.2	448.2	443.2	442.2	443.2	448.2	457.2
160°	507.1	495.1	483.1	473.1	466.1	458.2	454.2	454.2	454.2	458.2	466.1
162.5°	506.1	496.1	486.1	478.1	472.1	466.1	463.2	463.2	463.2	466.1	472.1
165°	504.1	497.1	489.1	482.1	478.1	473.1	471.1	472.1	471.1	473.1	478.1
167.5°	503.1	497.1	491.1	486.1	483.1	479.1	478.1	479.1	478.1	479.1	483.1
170°	500.1	496.1	491.1	489.1	487.1	484.1	483.1	485.1	483.1	484.1	487.1
172.5°	499.1	496.1	492.1	491.1	490.1	488.1	488.1	489.1	488.1	488.1	490.1
175°	497.1	495.1	493.1	492.1	492.1	490.1	491.1	492.1	491.1	490.1	492.1
177.5°	496.1	494.1	493.1	493.1	493.1	492.1	493.1	494.1	493.1	492.1	493.1
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P831770

CATALOG NUMBER: S123RDIP-S1000D1025U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0
2.5°	3141.2	3103.3	3065.4	3038.1	3010.9	2976.9	2943.0	2941.7	2940.3	2915.1	2889.8
5°	2955.0	2889.1	2823.3	2758.7	2694.2	2629.7	2565.1	2550.5	2535.9	2513.9	2492.0
7.5°	2790.0	2684.9	2579.8	2497.3	2414.8	2350.3	2285.8	2241.8	2197.9	2164.0	2130.1
10°	2613.0	2482.7	2352.3	2252.5	2152.7	2082.9	2013.0	1962.4	1911.9	1887.9	1864.0
12.5°	2429.4	2287.7	2146.1	2048.3	1950.5	1866.7	1782.8	1736.9	1691.0	1657.8	1624.5
15°	2260.5	2108.1	1955.8	1852.0	1748.2	1669.7	1591.2	1545.3	1499.4	1466.2	1432.9
17.5°	2096.8	1943.2	1789.5	1684.4	1579.3	1508.1	1436.9	1392.3	1347.8	1327.1	1306.5
20°	1947.8	1792.8	1637.8	1538.7	1439.6	1369.7	1299.9	1275.9	1252.0	1232.7	1213.4
22.5°	1800.1	1651.1	1502.1	1407.0	1311.8	1261.3	1210.7	1191.4	1172.1	1157.5	1142.9
25°	1676.4	1528.0	1379.7	1296.5	1213.4	1174.1	1134.9	1122.3	1109.6	1095.0	1080.3
27.5°	1551.3	1410.3	1269.3	1202.7	1136.2	1104.3	1072.4	1056.4	1040.4	1028.5	1016.5
30°	1440.9	1310.5	1180.1	1124.9	1069.7	1041.8	1013.8	996.5	979.2	967.9	956.6
32.5°	1334.5	1218.7	1103.0	1055.7	1008.5	981.2	953.9	937.3	920.7	907.4	894.1
35°	1236.0	1135.6	1035.1	991.9	948.6	921.4	894.1	877.4	860.8	847.5	834.2
37.5°	1149.5	1058.4	967.3	926.7	886.1	862.1	838.2	820.9	803.6	789.6	775.7
40°	1068.4	987.9	907.4	868.1	828.9	802.9	777.0	761.7	746.4	733.8	721.1
42.5°	996.5	922.7	848.8	810.3	771.7	747.1	722.4	704.5	686.5	679.2	671.9
45°	920.7	855.5	790.3	753.0	715.8	689.8	663.9	648.6	633.3	626.7	620.0
47.5°	854.2	793.6	733.1	696.5	659.9	636.6	613.3	601.4	589.4	580.1	570.8
50°	789.0	730.4	671.9	636.6	601.4	581.4	561.5	546.8	532.2	525.5	518.9
52.5°	726.4	673.2	620.0	584.1	548.2	528.9	509.6	496.9	484.3	470.3	456.4
55°	655.9	609.4	562.8	530.9	498.9	479.0	459.0	444.4	429.7	415.1	400.5
57.5°	597.4	551.5	505.6	477.0	448.4	429.1	409.8	393.8	377.9	365.9	353.9
60°	533.5	493.6	453.7	425.8	397.8	379.2	360.6	345.3	330.0	324.0	318.0
62.5°	473.6	436.4	399.1	374.5	349.9	332.0	314.0	304.0	294.0	290.0	286.1
65°	412.4	380.5	348.6	326.0	303.3	288.0	272.7	268.1	263.4	260.1	256.8
67.5°	355.2	328.0	300.7	280.7	260.8	250.1	239.5	234.2	228.8	224.8	220.9
70°	303.3	279.4	255.5	238.2	220.9	210.9	200.9	196.2	191.6	184.3	177.0
72.5°	247.5	228.8	210.2	196.9	183.6	175.0	166.3	157.0	147.7	141.0	134.4
75°	204.9	186.3	167.6	155.0	142.4	132.4	122.4	119.1	115.8	113.8	111.8
77.5°	157.0	141.0	125.1	115.1	105.1	100.5	95.8	93.8	91.8	91.1	90.5
80°	113.1	99.8	86.5	81.2	75.8	74.5	73.2	71.8	70.5	69.8	69.2
82.5°	70.5	63.9	57.2	55.9	54.5	53.9	53.2	52.6	51.9	51.2	50.6
85°	41.2	38.6	35.9	35.3	34.6	33.9	33.3	33.3	33.3	33.3	33.3
87.5°	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3	16.6	16.0
90°	11.0	13.0	16.0	19.0	22.0	25.0	24.0	25.0	26.0	27.0	28.9
92.5°	50.9	68.9	100.8	153.7	205.6	185.7	138.7	98.8	76.9	66.9	59.9
95°	90.8	129.8	214.6	363.3	527.0	591.9	480.1	359.3	243.6	190.7	154.7
97.5°	104.8	147.7	231.6	404.3	679.8	910.3	941.3	825.5	622.9	491.1	377.3
100°	119.8	158.7	228.6	376.3	638.8	945.3	1141.9	1176.9	1096.0	979.2	837.5
102.5°	136.8	171.7	232.6	352.4	578.9	880.4	1151.9	1293.6	1310.6	1254.7	1177.9
105°	155.7	186.7	240.6	343.4	532.0	802.5	1089.0	1297.6	1397.5	1416.4	1390.5
107.5°	176.7	205.6	253.5	341.4	498.1	733.7	999.2	1237.7	1394.5	1472.3	1499.3
110°	197.6	225.6	270.5	346.4	480.1	676.8	915.3	1143.9	1327.6	1453.3	1523.2



TEST NUMBER: P831770

CATALOG NUMBER: S123RDIP-S1000D1025U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	219.6	246.6	287.5	356.3	470.1	638.8	842.5	1051.1	1239.7	1384.5	1479.3
115°	241.6	268.5	306.4	367.3	469.1	613.9	786.6	971.2	1144.9	1291.6	1400.4
117.5°	263.5	288.5	326.4	381.3	470.1	596.9	749.6	909.3	1063.1	1197.8	1310.6
120°	284.5	309.4	345.4	397.3	474.1	585.9	721.7	862.4	997.2	1117.0	1217.8
122.5°	303.4	330.4	365.3	412.2	481.1	578.9	698.7	825.5	944.3	1053.1	1144.9
125°	322.4	349.4	384.3	428.2	488.1	573.0	679.8	793.6	902.4	998.2	1078.0
127.5°	340.4	367.3	401.3	441.2	496.1	570.0	661.8	764.6	863.4	951.3	1025.1
130°	356.3	383.3	416.2	454.2	504.1	567.0	647.8	737.7	827.5	908.3	976.2
132.5°	371.3	397.3	429.2	466.1	510.1	566.0	634.8	712.7	793.6	867.4	931.3
135°	384.3	411.2	442.2	476.1	516.1	565.0	623.9	690.7	761.6	826.5	883.4
137.5°	396.3	421.2	451.2	484.1	520.1	563.0	613.9	669.8	729.7	787.6	838.5
140°	406.3	431.2	460.2	490.1	524.0	562.0	604.9	651.8	702.7	750.6	793.6
142.5°	416.2	439.2	467.1	496.1	527.0	560.0	596.9	634.8	676.8	716.7	752.6
145°	424.2	447.2	473.1	500.1	528.0	558.0	589.9	621.9	654.8	686.7	715.7
147.5°	434.2	454.2	478.1	503.1	528.0	555.0	582.9	610.9	637.8	664.8	685.7
150°	442.2	460.2	483.1	504.1	528.0	551.0	575.9	598.9	621.9	642.8	661.8
152.5°	450.2	467.1	486.1	506.1	525.0	546.0	568.0	587.9	606.9	624.9	639.8
155°	459.2	473.1	490.1	506.1	523.0	540.0	560.0	576.9	592.9	607.9	619.9
157.5°	467.1	478.1	492.1	507.1	520.1	535.0	551.0	565.0	578.9	590.9	600.9
160°	473.1	483.1	495.1	507.1	518.1	529.0	542.0	555.0	566.0	575.9	582.9
162.5°	478.1	486.1	496.1	506.1	514.1	523.0	533.0	543.0	552.0	561.0	567.0
165°	482.1	489.1	497.1	504.1	510.1	517.1	525.0	533.0	539.0	546.0	551.0
167.5°	486.1	491.1	497.1	503.1	506.1	511.1	517.1	524.0	529.0	533.0	537.0
170°	489.1	491.1	496.1	500.1	502.1	505.1	510.1	515.1	518.1	522.0	524.0
172.5°	491.1	492.1	496.1	499.1	499.1	500.1	503.1	507.1	509.1	512.1	513.1
175°	492.1	493.1	495.1	497.1	496.1	496.1	498.1	500.1	501.1	503.1	503.1
177.5°	493.1	493.1	494.1	496.1	494.1	493.1	494.1	495.1	496.1	497.1	497.1
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P831770

CATALOG NUMBER: S123RDIP-S1000D1025U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	3245.0	3245.0	3245.0	3245.0
2.5°	2883.1	2876.5	2873.8	2871.2
5°	2471.4	2450.7	2446.1	2441.4
7.5°	2121.4	2112.8	2084.2	2055.6
10°	1837.4	1810.8	1798.8	1786.8
12.5°	1599.9	1575.3	1571.3	1567.3
15°	1415.6	1398.3	1392.3	1386.4
17.5°	1294.5	1282.6	1275.3	1267.9
20°	1204.7	1196.1	1190.8	1185.5
22.5°	1136.2	1129.6	1125.6	1121.6
25°	1070.4	1060.4	1057.1	1053.7
27.5°	1007.8	999.2	995.9	992.5
30°	949.3	942.0	937.3	932.7
32.5°	885.4	876.8	874.1	871.5
35°	828.9	823.6	820.9	818.2
37.5°	769.0	762.4	758.4	754.4
40°	717.8	714.5	712.5	710.5
42.5°	665.9	659.9	659.2	658.6
45°	614.0	608.0	606.7	605.4
47.5°	565.5	560.1	559.5	558.8
50°	511.6	504.2	498.9	493.6
52.5°	449.7	443.0	438.4	433.7
55°	393.2	385.8	381.8	377.9
57.5°	350.6	347.3	345.3	343.3
60°	316.0	314.0	312.7	311.3
62.5°	284.1	282.1	282.1	282.1
65°	254.8	252.8	250.8	248.8
67.5°	216.9	212.9	212.2	211.5
70°	171.0	165.0	164.3	163.6
72.5°	133.7	133.0	131.7	130.4
75°	110.4	109.1	109.1	109.1
77.5°	89.1	87.8	87.8	87.8
80°	68.5	67.9	68.5	69.2
82.5°	50.6	50.6	49.9	49.2
85°	32.6	31.9	31.9	31.9
87.5°	16.0	16.0	16.0	16.0
90°	27.9	28.9	29.9	28.9
92.5°	57.9	53.9	54.9	52.9
95°	135.8	126.8	119.8	115.8
97.5°	310.4	272.5	248.5	237.6
100°	736.7	663.8	624.9	625.9
102.5°	1105.0	1051.1	1020.1	991.2
105°	1344.5	1306.6	1274.7	1269.7
107.5°	1493.3	1475.3	1462.3	1451.4
110°	1551.2	1559.2	1557.2	1555.2



TEST NUMBER: P831770

CATALOG NUMBER: S123RDIP-S1000D1025U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	1536.2	1565.1	1575.1	1576.1
115°	1475.3	1519.2	1539.2	1544.2
117.5°	1388.5	1437.4	1467.3	1474.3
120°	1296.6	1352.5	1376.5	1382.5
122.5°	1212.8	1261.7	1288.6	1296.6
125°	1141.9	1185.8	1210.8	1217.8
127.5°	1083.0	1121.0	1143.9	1149.9
130°	1029.1	1065.1	1086.0	1094.0
132.5°	980.2	1016.1	1034.1	1039.1
135°	932.3	962.2	980.2	987.2
137.5°	880.4	911.3	926.3	932.3
140°	831.5	859.4	875.4	874.4
142.5°	783.6	807.5	821.5	820.5
145°	740.6	761.6	769.6	771.6
147.5°	705.7	720.7	728.7	729.7
150°	676.8	687.7	693.7	693.7
152.5°	650.8	660.8	663.8	663.8
155°	628.9	636.8	638.8	639.8
157.5°	608.9	614.9	616.9	616.9
160°	589.9	595.9	595.9	594.9
162.5°	571.0	575.9	575.9	575.0
165°	555.0	559.0	558.0	558.0
167.5°	539.0	542.0	541.0	541.0
170°	525.0	527.0	526.0	526.0
172.5°	513.1	515.1	513.1	512.1
175°	503.1	504.1	503.1	502.1
177.5°	496.1	497.1	495.1	495.1
180°	493.1	493.1	493.1	493.1



TEST NUMBER: P831770

CATALOG NUMBER: S123RDIP-S1000D1025U835-4F0-1E-UDD-G4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.43	14.27	14.37	15.22	16.44	18.10	18.94	19.04	19.88	21.10
	3H	14.66	15.40	15.60	16.36	17.60	19.60	20.35	20.55	21.30	22.55
	4H	15.04	15.74	16.00	16.70	17.96	20.09	20.79	21.05	21.75	23.01
	6H	15.32	15.97	16.29	16.93	18.20	20.40	21.05	21.37	22.01	23.28
	8H	15.41	16.03	16.39	17.01	18.27	20.48	21.10	21.46	22.08	23.34
	12H	15.46	16.05	16.44	17.02	18.31	20.51	21.10	21.50	22.07	23.36
4H	2H	14.16	14.86	15.13	15.82	17.08	18.09	18.80	19.06	19.76	21.01
	3H	15.53	16.11	16.50	17.10	18.37	19.75	20.34	20.73	21.33	22.60
	4H	15.98	16.52	16.97	17.50	18.79	20.36	20.89	21.35	21.88	23.17
	6H	16.35	16.81	17.35	17.82	19.11	20.80	21.26	21.80	22.26	23.55
	8H	16.48	16.91	17.48	17.91	19.21	20.93	21.36	21.93	22.36	23.66
	12H	16.55	16.94	17.57	17.96	19.26	20.99	21.38	22.01	22.39	23.70
8H	4H	16.30	16.73	17.30	17.73	19.03	20.33	20.76	21.33	21.76	23.06
	6H	16.76	17.12	17.79	18.16	19.46	20.82	21.18	21.85	22.22	23.52
	8H	16.96	17.27	17.99	18.29	19.62	21.01	21.32	22.04	22.35	23.67
	12H	17.10	17.37	18.13	18.39	19.76	21.13	21.40	22.16	22.42	23.79
12H	4H	16.31	16.70	17.33	17.71	19.02	20.28	20.66	21.29	21.68	22.99
	6H	16.82	17.13	17.85	18.16	19.48	20.80	21.11	21.83	22.14	23.46
	8H	17.04	17.31	18.07	18.33	19.70	20.99	21.27	22.03	22.29	23.65