

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332368

Luminaire Tested: **S123RDIP-S1165D585U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332368  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1165D585U835-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6693.4 lumens  
Efficiency: N/A  
Efficacy: 121.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332368

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332368

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	68																												
1	103	99	95	92	97	93	90	87	83	81	79	74	72	71	66	64	63	59																												
2	94	87	81	76	89	82	77	73	74	70	66	66	63	60	59	57	54	51																												
3	86	77	70	64	81	73	67	62	66	61	57	59	55	52	53	50	47	44																												
4	80	69	61	55	75	66	59	53	59	54	49	53	49	45	48	44	41	38																												
5	73	62	54	48	69	59	52	46	53	48	43	48	43	40	43	40	37	34																												
6	68	56	48	42	64	53	46	41	48	42	38	44	39	35	40	36	33	30																												
7	63	51	43	37	60	49	41	36	44	38	34	40	35	32	36	32	29	27																												
8	59	46	39	33	55	44	37	32	41	35	30	37	32	28	34	29	26	24																												
9	55	43	35	30	52	41	34	29	37	32	27	34	29	26	31	27	24	22																												
10	51	39	32	27	49	38	31	26	35	29	25	32	27	23	29	25	22	20																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	19763	19763	19763	19763
5°	23558	19847	17477	19847
10°	29415	19733	15789	19733
15°	34526	19531	14399	19531
20°	38533	19230	13216	19230
25°	37917	18912	12490	18912
30°	27256	18620	11742	18620
35°	18198	18239	11257	18239
40°	13408	17781	10756	17781
45°	11246	16978	10266	16978
50°	9923	15925	9582	15925
55°	8702	14720	8644	14720
60°	7750	13569	7918	13569
65°	6805	12332	7366	12332
70°	5344	11229	6729	11229
75°	4708	9807	6147	9807
80°	4091	8331	6044	8331
85°	3298	6694	6410	6694



TEST NUMBER: P332368

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	180.6	2.7
10°-20°	564.1	8.4
20°-30°	886.2	13.2
30°-40°	924.6	13.8
40°-50°	791.2	11.8
50°-60°	603.1	9.0
60°-70°	386.5	5.8
70°-80°	186.0	2.8
80°-90°	51.4	0.8
90°-100°	156.8	2.3
100°-110°	444.0	6.6
110°-120°	436.8	6.5
120°-130°	348.4	5.2
130°-140°	274.7	4.1
140°-150°	205.0	3.1
150°-160°	142.9	2.1
160°-170°	83.9	1.3
170°-180°	27.3	0.4
0°-30°	1630.8	24.4
0°-40°	2555.4	38.2
0°-60°	3949.7	59.0
0°-90°	4573.6	68.3
90°-120°	1037.6	15.5
90°-150°	1865.7	27.9
90°-180°	2120.0	31.7
0°-180°	6693.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1836	1836	1836	1836	1836	
5°	2180	1837	1618	1837	2180	225
15°	3098	1753	1292	1753	3098	879
25°	3193	1592	1052	1592	3193	1372
35°	1385	1388	857	1388	1385	908
45°	739	1115	674	1115	739	581
55°	464	784	461	784	464	419
65°	267	484	289	484	267	263
75°	113	236	148	236	113	121
85°	27	54	52	54	27	31
90°	16	1	16	1	16	10
95°	66	19	66	19	66	119
105°	726	66	726	66	726	716
115°	882	117	882	117	882	857
125°	696	163	696	163	696	631
135°	564	190	564	190	564	438
145°	441	217	441	217	441	280
155°	366	247	366	247	366	171
165°	319	270	319	270	319	91
175°	287	281	287	281	287	28
180°	282	282	282	282	282	



TEST NUMBER: P332368

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1955.5	1958.0	1949.8	1948.6	1939.1	1936.6	1936.6	1923.4	1915.2	1904.6	1898.3
5°	2180.3	2192.9	2186.6	2172.4	2148.8	2143.3	2128.4	2104.8	2078.1	2045.1	2029.4
7.5°	2461.0	2478.2	2471.6	2449.7	2425.0	2405.1	2362.9	2323.8	2268.9	2220.8	2179.6
10°	2691.2	2673.1	2658.9	2637.7	2614.9	2578.0	2534.0	2473.4	2403.5	2348.5	2287.2
12.5°	2863.4	2860.5	2842.5	2820.7	2788.5	2753.4	2699.3	2625.6	2544.3	2464.8	2394.7
15°	3098.3	3103.0	3091.2	3068.4	3022.8	2960.7	2879.0	2848.4	2732.0	2645.6	2559.1
17.5°	3260.8	3259.9	3258.3	3226.7	3180.2	3136.0	3060.2	2979.6	2874.3	2752.5	2636.0
20°	3363.9	3356.1	3357.7	3322.3	3287.7	3236.6	3162.7	3045.6	2959.2	2818.5	2698.2
22.5°	3361.4	3359.9	3365.8	3353.7	3328.6	3289.4	3231.3	3132.4	3022.1	2880.1	2744.8
25°	3192.6	3186.3	3223.3	3233.5	3273.6	3280.6	3263.3	3209.1	3104.6	2958.4	2791.0
27.5°	2672.0	2668.5	2737.1	2822.9	2931.7	3016.2	3098.0	3137.4	3104.6	2999.9	2832.2
30°	2192.9	2266.7	2301.3	2425.5	2563.8	2728.9	2873.5	3011.0	3044.8	2999.3	2861.7
32.5°	1820.6	1885.1	1914.0	2020.6	2149.5	2342.8	2559.7	2754.5	2892.1	2926.9	2844.1
35°	1384.9	1385.7	1451.7	1498.8	1618.3	1817.2	2027.8	2288.7	2548.1	2744.6	2765.0
37.5°	1105.1	1109.0	1148.9	1195.9	1285.5	1390.7	1576.2	1793.1	2092.7	2394.4	2571.2
40°	954.2	961.2	991.1	1037.5	1101.9	1181.3	1325.9	1530.3	1780.2	2115.8	2390.1
42.5°	857.3	868.8	884.2	919.9	959.8	1034.2	1151.1	1309.0	1536.3	1853.6	2170.1
45°	738.8	745.1	756.9	773.4	809.5	861.4	940.0	1046.1	1234.8	1490.2	1806.9
47.5°	651.7	648.4	660.8	674.2	698.3	733.6	786.3	872.9	1007.5	1212.4	1481.1
50°	592.6	591.8	600.5	610.7	633.5	659.4	702.7	767.9	874.8	1044.6	1290.6
52.5°	537.3	540.3	546.4	559.1	575.6	596.6	635.4	682.4	774.2	920.7	1125.8
55°	463.7	466.1	474.7	481.8	493.6	514.8	539.2	578.5	641.4	743.5	912.5
57.5°	401.5	400.4	408.7	410.4	423.8	441.1	459.9	490.4	536.0	612.0	725.8
60°	360.0	357.6	364.7	370.2	377.3	391.4	407.1	437.0	473.2	529.0	626.4
62.5°	322.2	321.1	326.3	331.8	337.7	350.5	363.7	386.7	415.3	462.3	539.6
65°	267.2	269.6	271.9	274.3	277.4	285.3	297.9	313.6	333.3	366.3	422.1
67.5°	210.0	212.4	213.2	218.0	224.8	229.7	237.4	251.4	265.0	292.9	324.6
70°	169.8	169.0	169.8	172.1	180.8	189.4	199.6	209.9	218.5	238.1	264.9
72.5°	145.9	144.5	146.5	147.0	151.2	153.6	160.0	169.6	180.8	194.1	213.3
75°	113.2	113.2	113.2	113.2	116.3	117.9	120.3	122.6	126.5	132.8	147.0
77.5°	83.6	83.8	84.9	85.7	86.3	87.2	88.7	91.0	92.4	95.7	101.9
80°	66.0	66.8	66.0	66.8	66.8	68.4	69.2	71.5	72.3	76.2	78.6
82.5°	49.7	49.2	49.7	50.5	50.5	52.0	52.2	53.9	54.1	56.1	58.5
85°	26.7	25.2	26.7	25.9	27.5	25.9	26.7	28.3	28.3	29.1	32.2
87.5°	9.6	11.0	9.6	10.1	10.2	10.6	10.5	10.4	11.5	11.0	11.3
90°	16.5	17.1	16.5	16.0	16.5	15.4	14.8	14.3	13.7	14.3	12.5
92.5°	27.5	28.5	27.9	29.7	30.7	33.7	38.1	48.0	66.2	87.7	96.5
95°	66.2	68.4	72.4	77.6	88.4	108.9	139.2	205.3	274.3	338.2	301.2
97.5°	180.1	185.0	200.4	226.1	268.2	336.4	410.0	511.9	560.8	524.2	383.7
100°	357.6	357.1	379.3	420.9	478.5	559.5	626.3	672.5	652.5	540.1	365.0
102.5°	524.6	537.7	556.3	589.3	634.1	685.5	724.4	725.9	657.1	510.5	337.7
105°	725.5	728.4	746.6	768.3	794.5	809.4	798.5	741.5	622.3	458.6	304.0
107.5°	841.2	846.4	852.6	859.9	859.4	839.1	789.2	696.5	561.4	412.7	282.6
110°	888.6	889.8	890.9	886.4	870.4	830.5	758.6	653.6	523.0	386.7	274.3



TEST NUMBER: P332368

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	898.2	898.0	893.7	879.5	850.3	799.0	718.4	611.2	489.7	369.4	269.8
115°	882.4	879.5	868.1	843.0	800.2	738.1	654.2	555.0	449.5	350.8	268.1
117.5°	831.9	828.1	811.6	782.9	738.3	675.2	599.9	514.2	425.2	339.8	269.1
120°	790.0	786.5	772.9	740.9	695.9	638.2	569.8	492.8	412.4	334.8	270.9
122.5°	750.7	746.4	731.3	702.6	662.5	609.0	545.6	475.9	401.9	331.6	274.1
125°	695.9	691.9	677.6	652.5	616.0	570.4	515.6	453.4	388.4	327.4	278.9
127.5°	650.7	647.0	634.1	612.7	580.2	538.7	489.3	433.8	376.6	325.3	284.4
130°	625.1	620.6	608.6	588.1	557.8	519.0	472.8	421.5	370.2	324.0	288.0
132.5°	600.0	596.8	586.2	565.7	537.3	500.3	457.3	410.1	364.2	323.5	290.8
135°	564.1	560.1	549.8	532.7	504.8	472.3	435.2	394.7	356.5	322.8	294.9
137.5°	526.1	523.5	514.8	497.5	474.0	445.8	413.9	380.7	349.8	321.6	297.6
140°	499.6	500.2	491.1	475.1	453.4	428.9	401.5	372.5	345.6	321.1	299.4
142.5°	475.0	475.6	467.4	453.2	434.7	413.4	389.7	364.7	342.0	320.2	300.8
145°	440.9	439.8	435.2	423.2	409.0	392.4	374.2	355.3	337.1	318.8	301.7
147.5°	412.8	412.4	408.0	399.9	389.1	377.4	362.6	347.7	332.3	316.7	301.7
150°	396.4	396.4	393.0	386.7	378.2	367.3	355.3	342.2	329.1	314.8	301.7
152.5°	382.7	382.7	380.7	374.8	368.1	359.1	348.5	337.2	325.5	312.6	300.4
155°	365.6	365.0	363.9	359.3	354.2	347.4	338.8	329.7	320.0	308.6	298.9
157.5°	350.0	350.1	349.2	345.8	341.3	336.0	329.3	321.7	313.8	305.0	296.9
160°	339.9	340.5	340.5	337.1	333.1	329.1	323.4	317.1	309.7	302.3	296.0
162.5°	330.8	331.4	331.4	328.4	325.8	322.3	317.0	311.7	305.6	299.6	294.2
165°	318.8	318.8	319.4	317.1	314.8	312.0	308.0	304.6	300.0	295.5	291.5
167.5°	307.4	307.4	308.0	306.4	305.4	303.3	301.0	298.4	294.7	291.3	288.7
170°	300.6	300.6	301.2	300.0	299.4	298.3	296.0	294.3	291.5	288.6	286.9
172.5°	294.2	294.7	295.7	294.5	294.4	293.7	291.9	290.7	288.3	286.3	285.5
175°	286.9	287.5	288.0	287.5	287.5	287.5	286.3	285.8	284.6	283.5	283.5
177.5°	282.7	282.7	283.6	283.1	283.6	283.6	283.1	282.7	282.2	281.8	282.2
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332368

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1895.8	1893.9	1885.1	1875.0	1861.8	1853.0	1846.1	1842.3	1831.0	1817.2	1807.7
5°	2012.9	1989.3	1964.1	1933.5	1905.2	1876.1	1858.0	1836.8	1810.9	1781.8	1761.4
7.5°	2138.3	2092.1	2042.3	1990.9	1940.1	1894.5	1854.3	1819.8	1778.5	1736.8	1707.6
10°	2234.5	2166.9	2097.0	2025.4	1960.2	1898.9	1851.7	1805.4	1755.9	1707.9	1671.8
12.5°	2321.9	2232.9	2152.3	2064.4	1981.0	1907.7	1839.8	1785.2	1725.7	1674.6	1633.4
15°	2432.6	2341.4	2243.9	2110.3	1999.5	1906.8	1824.2	1752.7	1680.4	1617.5	1577.4
17.5°	2536.0	2398.8	2267.8	2156.4	2012.4	1896.5	1795.8	1710.3	1630.9	1564.2	1514.9
20°	2578.8	2445.9	2303.7	2161.4	2019.9	1890.3	1773.1	1678.8	1596.3	1520.8	1475.3
22.5°	2604.5	2454.1	2304.3	2151.4	2001.1	1866.4	1750.5	1646.8	1557.3	1485.6	1429.4
25°	2634.6	2455.4	2290.3	2139.4	1986.1	1840.0	1702.4	1592.4	1495.7	1419.5	1359.7
27.5°	2654.4	2443.6	2248.5	2080.8	1925.3	1779.7	1653.7	1537.0	1439.0	1358.3	1294.2
30°	2658.1	2434.1	2216.4	2034.9	1876.9	1743.3	1609.7	1498.1	1394.3	1308.6	1248.9
32.5°	2663.2	2410.9	2173.0	1980.2	1818.4	1686.1	1565.0	1458.4	1352.2	1267.8	1206.8
35°	2642.4	2398.0	2107.2	1885.5	1723.6	1595.5	1486.3	1388.0	1283.5	1201.7	1139.7
37.5°	2553.1	2346.9	2039.0	1779.0	1609.7	1491.0	1402.0	1316.3	1220.5	1132.3	1073.8
40°	2463.2	2296.6	1986.1	1714.2	1537.4	1415.5	1335.4	1265.4	1172.7	1090.1	1027.3
42.5°	2329.3	2228.1	1935.8	1646.3	1455.6	1338.2	1270.6	1205.0	1123.6	1039.8	980.7
45°	2083.6	2097.0	1832.9	1538.1	1342.4	1224.5	1160.9	1115.3	1043.0	973.8	913.3
47.5°	1775.5	1900.5	1712.0	1422.9	1223.1	1112.5	1056.8	1017.0	968.3	900.4	845.2
50°	1574.3	1752.7	1615.2	1345.6	1148.3	1038.3	983.2	951.0	908.6	855.1	802.5
52.5°	1388.8	1580.4	1498.2	1259.4	1067.2	966.6	912.8	886.3	852.6	802.3	754.7
55°	1132.6	1326.7	1307.9	1129.4	945.5	855.1	814.3	784.4	761.6	723.9	686.2
57.5°	916.1	1100.2	1109.9	984.8	838.3	749.0	713.8	691.3	676.4	648.0	613.1
60°	779.7	948.7	981.7	887.4	761.6	683.0	648.4	630.3	618.6	595.8	569.0
62.5°	666.5	810.3	847.7	779.8	688.0	614.5	587.4	570.0	562.0	542.3	518.7
65°	510.1	629.6	665.7	628.0	580.0	521.1	499.1	484.2	477.1	466.1	448.8
67.5°	383.6	470.6	510.3	483.7	466.4	429.1	415.1	407.1	400.8	393.3	378.8
70°	308.1	372.5	413.4	406.3	392.2	372.5	362.3	356.8	350.5	344.3	331.7
72.5°	247.7	292.1	330.4	334.0	322.4	318.5	309.5	307.2	303.4	295.8	288.9
75°	164.3	194.9	221.6	231.9	236.6	240.5	236.6	235.8	235.0	228.7	224.8
77.5°	107.7	124.2	141.0	158.5	165.8	171.2	172.4	175.3	173.2	169.9	168.0
80°	82.5	86.5	98.2	113.2	125.0	129.7	132.8	134.4	133.6	132.8	129.7
82.5°	59.9	63.2	68.7	79.2	89.1	97.0	98.9	98.6	100.3	100.8	98.2
85°	32.2	33.0	34.6	36.2	41.7	50.3	52.7	54.2	55.8	55.8	51.1
87.5°	12.2	11.3	12.2	11.9	13.6	13.9	17.4	20.3	21.2	18.9	19.3
90°	10.8	9.1	7.4	6.3	5.1	3.4	2.3	1.1	2.3	3.4	5.1
92.5°	72.4	47.9	33.0	24.5	19.7	15.3	10.5	7.1	10.5	15.3	19.7
95°	207.6	122.6	74.1	51.9	37.1	27.4	21.1	19.4	21.1	27.4	37.1
97.5°	227.8	132.0	85.7	61.6	47.0	38.6	33.7	33.1	33.7	38.6	47.0
100°	215.0	130.6	90.7	68.4	54.8	46.8	42.8	42.2	42.8	46.8	54.8
102.5°	204.1	132.4	96.6	76.2	63.9	56.4	52.8	51.8	52.8	56.4	63.9
105°	196.2	137.5	106.7	89.0	78.1	71.3	67.9	66.2	67.9	71.3	78.1
107.5°	195.6	146.8	119.8	103.4	93.2	86.5	83.2	81.4	83.2	86.5	93.2
110°	197.9	154.6	128.9	112.9	103.2	97.0	94.1	92.4	94.1	97.0	103.2





TEST NUMBER: P332368

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	202.5	162.3	138.5	123.0	113.3	107.0	104.2	102.4	104.2	107.0	113.3
115°	209.9	175.1	153.4	138.0	128.3	122.6	119.2	116.9	119.2	122.6	128.3
117.5°	219.7	188.7	167.2	153.0	142.1	136.9	134.0	131.4	134.0	136.9	142.1
120°	227.0	197.3	176.8	162.6	151.7	146.0	143.2	141.5	143.2	146.0	151.7
122.5°	233.9	206.5	186.4	171.2	160.8	154.7	151.8	150.1	151.8	154.7	160.8
125°	244.7	219.6	199.6	184.2	173.4	167.1	163.7	162.6	163.7	167.1	173.4
127.5°	253.6	231.0	211.7	196.3	184.3	178.0	173.7	172.0	173.7	178.0	184.3
130°	259.5	237.8	219.0	203.6	191.6	184.8	179.7	178.0	179.7	184.8	191.6
132.5°	265.0	243.8	225.4	210.5	198.5	190.3	184.7	182.5	184.7	190.3	198.5
135°	272.1	252.7	235.0	219.6	207.6	199.1	192.8	190.5	192.8	199.1	207.6
137.5°	277.3	258.8	241.8	227.6	215.7	206.6	200.4	198.0	200.4	206.6	215.7
140°	280.1	262.9	246.4	232.1	220.7	211.6	205.9	203.1	205.9	211.6	220.7
142.5°	282.8	266.1	250.1	236.7	225.3	217.1	210.9	208.5	210.9	217.1	225.3
145°	285.8	270.4	255.5	242.4	232.7	224.2	219.0	217.3	219.0	224.2	232.7
147.5°	287.6	273.8	260.2	249.0	239.7	232.3	227.2	226.2	227.2	232.3	239.7
150°	288.0	276.1	262.9	252.7	244.7	237.3	232.7	232.1	232.7	237.3	244.7
152.5°	289.0	277.4	266.1	256.3	249.3	242.8	238.2	238.1	238.2	242.8	249.3
155°	289.2	280.1	270.4	262.4	256.1	250.4	247.0	247.0	247.0	250.4	256.1
157.5°	289.8	281.5	273.8	267.6	262.3	257.2	254.5	254.0	254.5	257.2	262.3
160°	289.8	282.9	276.1	270.4	266.4	261.8	259.5	259.5	259.5	261.8	266.4
162.5°	289.3	283.4	277.4	272.6	269.1	265.5	263.6	263.6	263.6	265.5	269.1
165°	288.0	284.0	279.5	275.5	273.2	270.4	269.2	269.8	269.2	270.4	273.2
167.5°	287.1	283.9	280.6	278.1	276.5	274.3	273.8	274.5	273.8	274.3	276.5
170°	285.8	283.5	280.6	279.5	278.3	276.6	276.1	277.2	276.1	276.6	278.3
172.5°	285.3	283.5	281.1	280.4	279.7	278.5	278.3	279.0	278.3	278.5	279.7
175°	284.0	282.9	281.8	281.2	281.2	280.1	280.6	281.2	280.6	280.1	281.2
177.5°	283.1	282.2	281.8	281.8	281.8	281.3	281.8	282.2	281.8	281.3	281.8
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332368

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1804.6	1796.4	1790.8	1778.2	1770.0	1761.2	1752.4	1758.1	1757.4	1756.8	1756.8
5°	1744.1	1726.0	1709.5	1688.3	1674.9	1658.4	1645.8	1644.2	1647.4	1636.4	1630.1
7.5°	1684.0	1659.3	1635.9	1612.5	1587.7	1567.9	1555.4	1549.6	1541.6	1534.8	1527.8
10°	1641.9	1612.8	1590.0	1560.9	1534.2	1510.6	1495.7	1485.5	1480.0	1474.5	1464.3
12.5°	1598.5	1570.1	1541.0	1508.1	1482.7	1455.3	1444.1	1432.7	1422.1	1416.0	1402.0
15°	1535.0	1498.1	1467.4	1432.8	1404.5	1377.8	1362.1	1339.3	1336.1	1328.3	1314.1
17.5°	1471.3	1431.2	1389.0	1363.3	1331.4	1303.6	1279.7	1272.0	1249.5	1241.0	1228.8
20°	1421.0	1384.1	1351.9	1318.1	1271.7	1245.8	1226.9	1216.7	1198.6	1187.6	1179.7
22.5°	1377.6	1340.1	1302.8	1263.4	1225.2	1196.1	1182.3	1166.4	1156.5	1141.1	1132.6
25°	1315.7	1274.8	1230.0	1187.6	1160.1	1138.1	1116.1	1101.9	1087.8	1080.7	1065.0
27.5°	1243.7	1201.0	1159.1	1126.9	1093.1	1071.4	1051.5	1038.9	1021.9	1010.0	1001.3
30°	1204.1	1153.8	1117.6	1088.6	1045.3	1024.9	1010.0	994.3	981.7	969.1	960.5
32.5°	1158.2	1112.3	1078.0	1042.0	1008.9	986.5	967.2	953.4	942.7	930.7	922.1
35°	1086.2	1047.7	1012.3	976.2	951.8	929.0	906.2	894.4	884.2	873.2	865.4
37.5°	1021.1	985.1	951.5	917.2	887.0	868.5	850.1	841.1	827.3	819.9	811.9
40°	980.9	945.5	909.4	876.4	844.9	830.8	814.3	800.9	788.3	782.8	774.2
42.5°	936.9	901.5	871.0	835.5	809.7	790.5	775.3	760.7	751.2	743.2	738.3
45°	871.6	840.2	810.3	775.0	750.6	734.1	716.8	703.4	694.8	689.3	680.6
47.5°	808.3	776.9	746.5	715.7	692.1	673.3	656.0	646.7	635.2	628.5	622.6
50°	762.4	734.1	701.9	673.6	650.0	631.1	617.0	605.2	595.0	586.3	582.4
52.5°	720.3	690.1	662.3	635.8	611.0	589.6	576.7	564.3	556.6	546.7	542.2
55°	650.8	621.7	598.1	572.2	547.8	529.7	514.0	503.0	495.2	484.2	477.9
57.5°	585.5	559.5	531.3	508.8	483.7	468.4	455.4	440.5	430.9	422.2	416.1
60°	541.5	511.7	487.3	466.1	444.1	424.4	412.6	400.8	390.6	382.0	376.5
62.5°	495.6	469.5	446.4	423.3	403.2	386.1	372.4	362.5	353.5	348.0	342.5
65°	425.2	404.8	381.2	362.3	343.5	330.9	319.9	311.2	305.0	301.0	296.3
67.5°	360.4	340.6	320.0	301.5	288.9	279.3	272.1	264.7	261.6	256.5	253.4
70°	318.3	297.9	279.8	265.7	253.1	246.0	241.3	235.8	232.6	226.4	223.2
72.5°	272.4	257.6	244.6	233.0	222.9	216.5	210.5	203.7	198.7	191.8	188.6
75°	214.6	201.2	191.0	183.1	176.8	168.2	159.6	152.5	150.1	147.8	147.0
77.5°	158.9	150.4	143.0	136.4	128.6	122.3	120.4	118.8	118.4	117.1	117.1
80°	125.0	117.1	111.6	103.7	99.0	99.0	99.0	97.5	98.2	98.2	98.2
82.5°	92.9	85.7	82.7	79.9	78.9	79.5	79.5	79.9	79.4	80.6	80.0
85°	47.9	48.7	50.3	49.5	50.3	50.3	51.9	51.1	51.9	50.3	51.9
87.5°	18.9	21.0	21.9	22.9	23.9	23.6	24.1	24.2	25.0	25.1	25.3
90°	6.3	7.4	9.1	10.8	12.5	14.3	13.7	14.3	14.8	15.4	16.5
92.5°	24.5	33.0	47.9	72.4	96.5	87.7	66.2	48.0	38.1	33.7	30.7
95°	51.9	74.1	122.6	207.6	301.2	338.2	274.3	205.3	139.2	108.9	88.4
97.5°	61.6	85.7	132.0	227.8	383.7	524.2	560.8	511.9	410.0	336.4	268.2
100°	68.4	90.7	130.6	215.0	365.0	540.1	652.5	672.5	626.3	559.5	478.5
102.5°	76.2	96.6	132.4	204.1	337.7	510.5	657.1	725.9	724.4	685.5	634.1
105°	89.0	106.7	137.5	196.2	304.0	458.6	622.3	741.5	798.5	809.4	794.5
107.5°	103.4	119.8	146.8	195.6	282.6	412.7	561.4	696.5	789.2	839.1	859.4
110°	112.9	128.9	154.6	197.9	274.3	386.7	523.0	653.6	758.6	830.5	870.4



TEST NUMBER: P332368

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	123.0	138.5	162.3	202.5	269.8	369.4	489.7	611.2	718.4	799.0	850.3
115°	138.0	153.4	175.1	209.9	268.1	350.8	449.5	555.0	654.2	738.1	800.2
117.5°	153.0	167.2	188.7	219.7	269.1	339.8	425.2	514.2	599.9	675.2	738.3
120°	162.6	176.8	197.3	227.0	270.9	334.8	412.4	492.8	569.8	638.2	695.9
122.5°	171.2	186.4	206.5	233.9	274.1	331.6	401.9	475.9	545.6	609.0	662.5
125°	184.2	199.6	219.6	244.7	278.9	327.4	388.4	453.4	515.6	570.4	616.0
127.5°	196.3	211.7	231.0	253.6	284.4	325.3	376.6	433.8	489.3	538.7	580.2
130°	203.6	219.0	237.8	259.5	288.0	324.0	370.2	421.5	472.8	519.0	557.8
132.5°	210.5	225.4	243.8	265.0	290.8	323.5	364.2	410.1	457.3	500.3	537.3
135°	219.6	235.0	252.7	272.1	294.9	322.8	356.5	394.7	435.2	472.3	504.8
137.5°	227.6	241.8	258.8	277.3	297.6	321.6	349.8	380.7	413.9	445.8	474.0
140°	232.1	246.4	262.9	280.1	299.4	321.1	345.6	372.5	401.5	428.9	453.4
142.5°	236.7	250.1	266.1	282.8	300.8	320.2	342.0	364.7	389.7	413.4	434.7
145°	242.4	255.5	270.4	285.8	301.7	318.8	337.1	355.3	374.2	392.4	409.0
147.5°	249.0	260.2	273.8	287.6	301.7	316.7	332.3	347.7	362.6	377.4	389.1
150°	252.7	262.9	276.1	288.0	301.7	314.8	329.1	342.2	355.3	367.3	378.2
152.5°	256.3	266.1	277.4	289.0	300.4	312.6	325.5	337.2	348.5	359.1	368.1
155°	262.4	270.4	280.1	289.2	298.9	308.6	320.0	329.7	338.8	347.4	354.2
157.5°	267.6	273.8	281.5	289.8	296.9	305.0	313.8	321.7	329.3	336.0	341.3
160°	270.4	276.1	282.9	289.8	296.0	302.3	309.7	317.1	323.4	329.1	333.1
162.5°	272.6	277.4	283.4	289.3	294.2	299.6	305.6	311.7	317.0	322.3	325.8
165°	275.5	279.5	284.0	288.0	291.5	295.5	300.0	304.6	308.0	312.0	314.8
167.5°	278.1	280.6	283.9	287.1	288.7	291.3	294.7	298.4	301.0	303.3	305.4
170°	279.5	280.6	283.5	285.8	286.9	288.6	291.5	294.3	296.0	298.3	299.4
172.5°	280.4	281.1	283.5	285.3	285.5	286.3	288.3	290.7	291.9	293.7	294.4
175°	281.2	281.8	282.9	284.0	283.5	283.5	284.6	285.8	286.3	287.5	287.5
177.5°	281.8	281.8	282.2	283.1	282.2	281.8	282.2	282.7	283.1	283.6	283.6
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332368

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1749.3	1748.6	1749.3	1746.7	1749.3	1748.6	1749.3	1756.8	1756.8	1757.4	1758.1
5°	1627.7	1627.0	1624.6	1617.5	1624.6	1627.0	1627.7	1630.1	1636.4	1647.4	1644.2
7.5°	1521.6	1520.5	1513.6	1513.8	1513.6	1520.5	1521.6	1527.8	1534.8	1541.6	1549.6
10°	1458.8	1459.5	1450.1	1444.6	1450.1	1459.5	1458.8	1464.3	1474.5	1480.0	1485.5
12.5°	1397.8	1394.2	1386.6	1380.5	1386.6	1394.2	1397.8	1402.0	1416.0	1422.1	1432.7
15°	1317.3	1309.4	1290.6	1292.1	1290.6	1309.4	1317.3	1314.1	1328.3	1336.1	1339.3
17.5°	1222.5	1216.7	1216.4	1205.4	1216.4	1216.7	1222.5	1228.8	1241.0	1249.5	1272.0
20°	1167.2	1163.2	1164.8	1153.8	1164.8	1163.2	1167.2	1179.7	1187.6	1198.6	1216.7
22.5°	1123.8	1119.8	1113.2	1109.8	1113.2	1119.8	1123.8	1132.6	1141.1	1156.5	1166.4
25°	1060.3	1054.0	1047.7	1051.6	1047.7	1054.0	1060.3	1065.0	1080.7	1087.8	1101.9
27.5°	996.8	992.1	985.8	985.0	985.8	992.1	996.8	1001.3	1010.0	1021.9	1038.9
30°	956.5	951.8	948.7	944.7	948.7	951.8	956.5	960.5	969.1	981.7	994.3
32.5°	915.7	914.7	909.1	908.3	909.1	914.7	915.7	922.1	930.7	942.7	953.4
35°	862.2	857.5	855.9	856.7	855.9	857.5	862.2	865.4	873.2	884.2	894.4
37.5°	811.4	805.1	802.3	799.5	802.3	805.1	811.4	811.9	819.9	827.3	841.1
40°	775.0	768.7	767.1	765.5	767.1	768.7	775.0	774.2	782.8	788.3	800.9
42.5°	734.1	731.6	730.6	727.8	730.6	731.6	734.1	738.3	743.2	751.2	760.7
45°	678.3	677.5	672.8	674.4	672.8	677.5	678.3	680.6	689.3	694.8	703.4
47.5°	619.5	616.0	612.7	614.9	612.7	616.0	619.5	622.6	628.5	635.2	646.7
50°	579.3	577.7	570.6	572.2	570.6	577.7	579.3	582.4	586.3	595.0	605.2
52.5°	539.0	533.0	530.4	529.4	530.4	533.0	539.0	542.2	546.7	556.6	564.3
55°	472.4	465.3	462.1	460.6	462.1	465.3	472.4	477.9	484.2	495.2	503.0
57.5°	407.0	405.1	402.6	404.3	402.6	405.1	407.0	416.1	422.2	430.9	440.5
60°	368.6	368.6	368.6	367.8	368.6	368.6	368.6	376.5	382.0	390.6	400.8
62.5°	339.1	337.2	336.6	337.7	336.6	337.2	339.1	342.5	348.0	353.5	362.5
65°	294.0	293.2	290.0	289.2	290.0	293.2	294.0	296.3	301.0	305.0	311.2
67.5°	251.4	248.5	247.6	246.5	247.6	248.5	251.4	253.4	256.5	261.6	264.7
70°	219.3	217.7	213.0	213.8	213.0	217.7	219.3	223.2	226.4	232.6	235.8
72.5°	184.7	183.1	182.2	181.1	182.2	183.1	184.7	188.6	191.8	198.7	203.7
75°	146.2	145.4	144.6	147.8	144.6	145.4	146.2	147.0	147.8	150.1	152.5
77.5°	117.1	117.1	117.6	116.3	117.6	117.1	117.1	117.1	117.1	118.4	118.8
80°	98.2	98.2	97.5	97.5	97.5	98.2	98.2	98.2	98.2	98.2	97.5
82.5°	78.8	79.4	79.9	78.6	79.9	79.4	78.8	80.0	80.6	79.4	79.9
85°	51.9	51.1	52.7	51.9	52.7	51.1	51.9	51.9	50.3	51.9	51.1
87.5°	26.5	25.3	25.4	25.9	25.4	25.3	26.5	25.3	25.1	25.0	24.2
90°	16.0	16.5	17.1	16.5	17.1	16.5	16.0	16.5	15.4	14.8	14.3
92.5°	29.7	27.9	28.5	27.5	28.5	27.9	29.7	30.7	33.7	38.1	48.0
95°	77.6	72.4	68.4	66.2	68.4	72.4	77.6	88.4	108.9	139.2	205.3
97.5°	226.1	200.4	185.0	180.1	185.0	200.4	226.1	268.2	336.4	410.0	511.9
100°	420.9	379.3	357.1	357.6	357.1	379.3	420.9	478.5	559.5	626.3	672.5
102.5°	589.3	556.3	537.7	524.6	537.7	556.3	589.3	634.1	685.5	724.4	725.9
105°	768.3	746.6	728.4	725.5	728.4	746.6	768.3	794.5	809.4	798.5	741.5
107.5°	859.9	852.6	846.4	841.2	846.4	852.6	859.9	859.4	839.1	789.2	696.5
110°	886.4	890.9	889.8	888.6	889.8	890.9	886.4	870.4	830.5	758.6	653.6



TEST NUMBER: P332368

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	879.5	893.7	898.0	898.2	898.0	893.7	879.5	850.3	799.0	718.4	611.2
115°	843.0	868.1	879.5	882.4	879.5	868.1	843.0	800.2	738.1	654.2	555.0
117.5°	782.9	811.6	828.1	831.9	828.1	811.6	782.9	738.3	675.2	599.9	514.2
120°	740.9	772.9	786.5	790.0	786.5	772.9	740.9	695.9	638.2	569.8	492.8
122.5°	702.6	731.3	746.4	750.7	746.4	731.3	702.6	662.5	609.0	545.6	475.9
125°	652.5	677.6	691.9	695.9	691.9	677.6	652.5	616.0	570.4	515.6	453.4
127.5°	612.7	634.1	647.0	650.7	647.0	634.1	612.7	580.2	538.7	489.3	433.8
130°	588.1	608.6	620.6	625.1	620.6	608.6	588.1	557.8	519.0	472.8	421.5
132.5°	565.7	586.2	596.8	600.0	596.8	586.2	565.7	537.3	500.3	457.3	410.1
135°	532.7	549.8	560.1	564.1	560.1	549.8	532.7	504.8	472.3	435.2	394.7
137.5°	497.5	514.8	523.5	526.1	523.5	514.8	497.5	474.0	445.8	413.9	380.7
140°	475.1	491.1	500.2	499.6	500.2	491.1	475.1	453.4	428.9	401.5	372.5
142.5°	453.2	467.4	475.6	475.0	475.6	467.4	453.2	434.7	413.4	389.7	364.7
145°	423.2	435.2	439.8	440.9	439.8	435.2	423.2	409.0	392.4	374.2	355.3
147.5°	399.9	408.0	412.4	412.8	412.4	408.0	399.9	389.1	377.4	362.6	347.7
150°	386.7	393.0	396.4	396.4	396.4	393.0	386.7	378.2	367.3	355.3	342.2
152.5°	374.8	380.7	382.7	382.7	382.7	380.7	374.8	368.1	359.1	348.5	337.2
155°	359.3	363.9	365.0	365.6	365.0	363.9	359.3	354.2	347.4	338.8	329.7
157.5°	345.8	349.2	350.1	350.0	350.1	349.2	345.8	341.3	336.0	329.3	321.7
160°	337.1	340.5	340.5	339.9	340.5	340.5	337.1	333.1	329.1	323.4	317.1
162.5°	328.4	331.4	331.4	330.8	331.4	331.4	328.4	325.8	322.3	317.0	311.7
165°	317.1	319.4	318.8	318.8	318.8	319.4	317.1	314.8	312.0	308.0	304.6
167.5°	306.4	308.0	307.4	307.4	307.4	308.0	306.4	305.4	303.3	301.0	298.4
170°	300.0	301.2	300.6	300.6	300.6	301.2	300.0	299.4	298.3	296.0	294.3
172.5°	294.5	295.7	294.7	294.2	294.7	295.7	294.5	294.4	293.7	291.9	290.7
175°	287.5	288.0	287.5	286.9	287.5	288.0	287.5	287.5	287.5	286.3	285.8
177.5°	283.1	283.6	282.7	282.7	282.7	283.6	283.1	283.6	283.6	283.1	282.7
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332368

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1752.4	1761.2	1770.0	1778.2	1790.8	1796.4	1804.6	1807.7	1817.2	1831.0	1842.3
5°	1645.8	1658.4	1674.9	1688.3	1709.5	1726.0	1744.1	1761.4	1781.8	1810.9	1836.8
7.5°	1555.4	1567.9	1587.7	1612.5	1635.9	1659.3	1684.0	1707.6	1736.8	1778.5	1819.8
10°	1495.7	1510.6	1534.2	1560.9	1590.0	1612.8	1641.9	1671.8	1707.9	1755.9	1805.4
12.5°	1444.1	1455.3	1482.7	1508.1	1541.0	1570.1	1598.5	1633.4	1674.6	1725.7	1785.2
15°	1362.1	1377.8	1404.5	1432.8	1467.4	1498.1	1535.0	1577.4	1617.5	1680.4	1752.7
17.5°	1279.7	1303.6	1331.4	1363.3	1389.0	1431.2	1471.3	1514.9	1564.2	1630.9	1710.3
20°	1226.9	1245.8	1271.7	1318.1	1351.9	1384.1	1421.0	1475.3	1520.8	1596.3	1678.8
22.5°	1182.3	1196.1	1225.2	1263.4	1302.8	1340.1	1377.6	1429.4	1485.6	1557.3	1646.8
25°	1116.1	1138.1	1160.1	1187.6	1230.0	1274.8	1315.7	1359.7	1419.5	1495.7	1592.4
27.5°	1051.5	1071.4	1093.1	1126.9	1159.1	1201.0	1243.7	1294.2	1358.3	1439.0	1537.0
30°	1010.0	1024.9	1045.3	1088.6	1117.6	1153.8	1204.1	1248.9	1308.6	1394.3	1498.1
32.5°	967.2	986.5	1008.9	1042.0	1078.0	1112.3	1158.2	1206.8	1267.8	1352.2	1458.4
35°	906.2	929.0	951.8	976.2	1012.3	1047.7	1086.2	1139.7	1201.7	1283.5	1388.0
37.5°	850.1	868.5	887.0	917.2	951.5	985.1	1021.1	1073.8	1132.3	1220.5	1316.3
40°	814.3	830.8	844.9	876.4	909.4	945.5	980.9	1027.3	1090.1	1172.7	1265.4
42.5°	775.3	790.5	809.7	835.5	871.0	901.5	936.9	980.7	1039.8	1123.6	1205.0
45°	716.8	734.1	750.6	775.0	810.3	840.2	871.6	913.3	973.8	1043.0	1115.3
47.5°	656.0	673.3	692.1	715.7	746.5	776.9	808.3	845.2	900.4	968.3	1017.0
50°	617.0	631.1	650.0	673.6	701.9	734.1	762.4	802.5	855.1	908.6	951.0
52.5°	576.7	589.6	611.0	635.8	662.3	690.1	720.3	754.7	802.3	852.6	886.3
55°	514.0	529.7	547.8	572.2	598.1	621.7	650.8	686.2	723.9	761.6	784.4
57.5°	455.4	468.4	483.7	508.8	531.3	559.5	585.5	613.1	648.0	676.4	691.3
60°	412.6	424.4	444.1	466.1	487.3	511.7	541.5	569.0	595.8	618.6	630.3
62.5°	372.4	386.1	403.2	423.3	446.4	469.5	495.6	518.7	542.3	562.0	570.0
65°	319.9	330.9	343.5	362.3	381.2	404.8	425.2	448.8	466.1	477.1	484.2
67.5°	272.1	279.3	288.9	301.5	320.0	340.6	360.4	378.8	393.3	400.8	407.1
70°	241.3	246.0	253.1	265.7	279.8	297.9	318.3	331.7	344.3	350.5	356.8
72.5°	210.5	216.5	222.9	233.0	244.6	257.6	272.4	288.9	295.8	303.4	307.2
75°	159.6	168.2	176.8	183.1	191.0	201.2	214.6	224.8	228.7	235.0	235.8
77.5°	120.4	122.3	128.6	136.4	143.0	150.4	158.9	168.0	169.9	173.2	175.3
80°	99.0	99.0	99.0	103.7	111.6	117.1	125.0	129.7	132.8	133.6	134.4
82.5°	79.5	79.5	78.9	79.9	82.7	85.7	92.9	98.2	100.8	100.3	98.6
85°	51.9	50.3	50.3	49.5	50.3	48.7	47.9	51.1	55.8	55.8	54.2
87.5°	24.1	23.6	23.9	22.9	21.9	21.0	18.9	19.3	18.9	21.2	20.3
90°	13.7	14.3	12.5	10.8	9.1	7.4	6.3	5.1	3.4	2.3	1.1
92.5°	66.2	87.7	96.5	72.4	47.9	33.0	24.5	19.7	15.3	10.5	7.1
95°	274.3	338.2	301.2	207.6	122.6	74.1	51.9	37.1	27.4	21.1	19.4
97.5°	560.8	524.2	383.7	227.8	132.0	85.7	61.6	47.0	38.6	33.7	33.1
100°	652.5	540.1	365.0	215.0	130.6	90.7	68.4	54.8	46.8	42.8	42.2
102.5°	657.1	510.5	337.7	204.1	132.4	96.6	76.2	63.9	56.4	52.8	51.8
105°	622.3	458.6	304.0	196.2	137.5	106.7	89.0	78.1	71.3	67.9	66.2
107.5°	561.4	412.7	282.6	195.6	146.8	119.8	103.4	93.2	86.5	83.2	81.4
110°	523.0	386.7	274.3	197.9	154.6	128.9	112.9	103.2	97.0	94.1	92.4



TEST NUMBER: P332368

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	489.7	369.4	269.8	202.5	162.3	138.5	123.0	113.3	107.0	104.2	102.4
115°	449.5	350.8	268.1	209.9	175.1	153.4	138.0	128.3	122.6	119.2	116.9
117.5°	425.2	339.8	269.1	219.7	188.7	167.2	153.0	142.1	136.9	134.0	131.4
120°	412.4	334.8	270.9	227.0	197.3	176.8	162.6	151.7	146.0	143.2	141.5
122.5°	401.9	331.6	274.1	233.9	206.5	186.4	171.2	160.8	154.7	151.8	150.1
125°	388.4	327.4	278.9	244.7	219.6	199.6	184.2	173.4	167.1	163.7	162.6
127.5°	376.6	325.3	284.4	253.6	231.0	211.7	196.3	184.3	178.0	173.7	172.0
130°	370.2	324.0	288.0	259.5	237.8	219.0	203.6	191.6	184.8	179.7	178.0
132.5°	364.2	323.5	290.8	265.0	243.8	225.4	210.5	198.5	190.3	184.7	182.5
135°	356.5	322.8	294.9	272.1	252.7	235.0	219.6	207.6	199.1	192.8	190.5
137.5°	349.8	321.6	297.6	277.3	258.8	241.8	227.6	215.7	206.6	200.4	198.0
140°	345.6	321.1	299.4	280.1	262.9	246.4	232.1	220.7	211.6	205.9	203.1
142.5°	342.0	320.2	300.8	282.8	266.1	250.1	236.7	225.3	217.1	210.9	208.5
145°	337.1	318.8	301.7	285.8	270.4	255.5	242.4	232.7	224.2	219.0	217.3
147.5°	332.3	316.7	301.7	287.6	273.8	260.2	249.0	239.7	232.3	227.2	226.2
150°	329.1	314.8	301.7	288.0	276.1	262.9	252.7	244.7	237.3	232.7	232.1
152.5°	325.5	312.6	300.4	289.0	277.4	266.1	256.3	249.3	242.8	238.2	238.1
155°	320.0	308.6	298.9	289.2	280.1	270.4	262.4	256.1	250.4	247.0	247.0
157.5°	313.8	305.0	296.9	289.8	281.5	273.8	267.6	262.3	257.2	254.5	254.0
160°	309.7	302.3	296.0	289.8	282.9	276.1	270.4	266.4	261.8	259.5	259.5
162.5°	305.6	299.6	294.2	289.3	283.4	277.4	272.6	269.1	265.5	263.6	263.6
165°	300.0	295.5	291.5	288.0	284.0	279.5	275.5	273.2	270.4	269.2	269.8
167.5°	294.7	291.3	288.7	287.1	283.9	280.6	278.1	276.5	274.3	273.8	274.5
170°	291.5	288.6	286.9	285.8	283.5	280.6	279.5	278.3	276.6	276.1	277.2
172.5°	288.3	286.3	285.5	285.3	283.5	281.1	280.4	279.7	278.5	278.3	279.0
175°	284.6	283.5	283.5	284.0	282.9	281.8	281.2	281.2	280.1	280.6	281.2
177.5°	282.2	281.8	282.2	283.1	282.2	281.8	281.8	281.8	281.3	281.8	282.2
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332368

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1846.1	1853.0	1861.8	1875.0	1885.1	1893.9	1895.8	1898.3	1904.6	1915.2	1923.4
5°	1858.0	1876.1	1905.2	1933.5	1964.1	1989.3	2012.9	2029.4	2045.1	2078.1	2104.8
7.5°	1854.3	1894.5	1940.1	1990.9	2042.3	2092.1	2138.3	2179.6	2220.8	2268.9	2323.8
10°	1851.7	1898.9	1960.2	2025.4	2097.0	2166.9	2234.5	2287.2	2348.5	2403.5	2473.4
12.5°	1839.8	1907.7	1981.0	2064.4	2152.3	2232.9	2321.9	2394.7	2464.8	2544.3	2625.6
15°	1824.2	1906.8	1999.5	2110.3	2243.9	2341.4	2432.6	2559.1	2645.6	2732.0	2848.4
17.5°	1795.8	1896.5	2012.4	2156.4	2267.8	2398.8	2536.0	2636.0	2752.5	2874.3	2979.6
20°	1773.1	1890.3	2019.9	2161.4	2303.7	2445.9	2578.8	2698.2	2818.5	2959.2	3045.6
22.5°	1750.5	1866.4	2001.1	2151.4	2304.3	2454.1	2604.5	2744.8	2880.1	3022.1	3132.4
25°	1702.4	1840.0	1986.1	2139.4	2290.3	2455.4	2634.6	2791.0	2958.4	3104.6	3209.1
27.5°	1653.7	1779.7	1925.3	2080.8	2248.5	2443.6	2654.4	2832.2	2999.9	3104.6	3137.4
30°	1609.7	1743.3	1876.9	2034.9	2216.4	2434.1	2658.1	2861.7	2999.3	3044.8	3011.0
32.5°	1565.0	1686.1	1818.4	1980.2	2173.0	2410.9	2663.2	2844.1	2926.9	2892.1	2754.5
35°	1486.3	1595.5	1723.6	1885.5	2107.2	2398.0	2642.4	2765.0	2744.6	2548.1	2288.7
37.5°	1402.0	1491.0	1609.7	1779.0	2039.0	2346.9	2553.1	2571.2	2394.4	2092.7	1793.1
40°	1335.4	1415.5	1537.4	1714.2	1986.1	2296.6	2463.2	2390.1	2115.8	1780.2	1530.3
42.5°	1270.6	1338.2	1455.6	1646.3	1935.8	2228.1	2329.3	2170.1	1853.6	1536.3	1309.0
45°	1160.9	1224.5	1342.4	1538.1	1832.9	2097.0	2083.6	1806.9	1490.2	1234.8	1046.1
47.5°	1056.8	1112.5	1223.1	1422.9	1712.0	1900.5	1775.5	1481.1	1212.4	1007.5	872.9
50°	983.2	1038.3	1148.3	1345.6	1615.2	1752.7	1574.3	1290.6	1044.6	874.8	767.9
52.5°	912.8	966.6	1067.2	1259.4	1498.2	1580.4	1388.8	1125.8	920.7	774.2	682.4
55°	814.3	855.1	945.5	1129.4	1307.9	1326.7	1132.6	912.5	743.5	641.4	578.5
57.5°	713.8	749.0	838.3	984.8	1109.9	1100.2	916.1	725.8	612.0	536.0	490.4
60°	648.4	683.0	761.6	887.4	981.7	948.7	779.7	626.4	529.0	473.2	437.0
62.5°	587.4	614.5	688.0	779.8	847.7	810.3	666.5	539.6	462.3	415.3	386.7
65°	499.1	521.1	580.0	628.0	665.7	629.6	510.1	422.1	366.3	333.3	313.6
67.5°	415.1	429.1	466.4	483.7	510.3	470.6	383.6	324.6	292.9	265.0	251.4
70°	362.3	372.5	392.2	406.3	413.4	372.5	308.1	264.9	238.1	218.5	209.9
72.5°	309.5	318.5	322.4	334.0	330.4	292.1	247.7	213.3	194.1	180.8	169.6
75°	236.6	240.5	236.6	231.9	221.6	194.9	164.3	147.0	132.8	126.5	122.6
77.5°	172.4	171.2	165.8	158.5	141.0	124.2	107.7	101.9	95.7	92.4	91.0
80°	132.8	129.7	125.0	113.2	98.2	86.5	82.5	78.6	76.2	72.3	71.5
82.5°	98.9	97.0	89.1	79.2	68.7	63.2	59.9	58.5	56.1	54.1	53.9
85°	52.7	50.3	41.7	36.2	34.6	33.0	32.2	32.2	29.1	28.3	28.3
87.5°	17.4	13.9	13.6	11.9	12.2	11.3	12.2	11.3	11.0	11.5	10.4
90°	2.3	3.4	5.1	6.3	7.4	9.1	10.8	12.5	14.3	13.7	14.3
92.5°	10.5	15.3	19.7	24.5	33.0	47.9	72.4	96.5	87.7	66.2	48.0
95°	21.1	27.4	37.1	51.9	74.1	122.6	207.6	301.2	338.2	274.3	205.3
97.5°	33.7	38.6	47.0	61.6	85.7	132.0	227.8	383.7	524.2	560.8	511.9
100°	42.8	46.8	54.8	68.4	90.7	130.6	215.0	365.0	540.1	652.5	672.5
102.5°	52.8	56.4	63.9	76.2	96.6	132.4	204.1	337.7	510.5	657.1	725.9
105°	67.9	71.3	78.1	89.0	106.7	137.5	196.2	304.0	458.6	622.3	741.5
107.5°	83.2	86.5	93.2	103.4	119.8	146.8	195.6	282.6	412.7	561.4	696.5
110°	94.1	97.0	103.2	112.9	128.9	154.6	197.9	274.3	386.7	523.0	653.6





TEST NUMBER: P332368

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	104.2	107.0	113.3	123.0	138.5	162.3	202.5	269.8	369.4	489.7	611.2
115°	119.2	122.6	128.3	138.0	153.4	175.1	209.9	268.1	350.8	449.5	555.0
117.5°	134.0	136.9	142.1	153.0	167.2	188.7	219.7	269.1	339.8	425.2	514.2
120°	143.2	146.0	151.7	162.6	176.8	197.3	227.0	270.9	334.8	412.4	492.8
122.5°	151.8	154.7	160.8	171.2	186.4	206.5	233.9	274.1	331.6	401.9	475.9
125°	163.7	167.1	173.4	184.2	199.6	219.6	244.7	278.9	327.4	388.4	453.4
127.5°	173.7	178.0	184.3	196.3	211.7	231.0	253.6	284.4	325.3	376.6	433.8
130°	179.7	184.8	191.6	203.6	219.0	237.8	259.5	288.0	324.0	370.2	421.5
132.5°	184.7	190.3	198.5	210.5	225.4	243.8	265.0	290.8	323.5	364.2	410.1
135°	192.8	199.1	207.6	219.6	235.0	252.7	272.1	294.9	322.8	356.5	394.7
137.5°	200.4	206.6	215.7	227.6	241.8	258.8	277.3	297.6	321.6	349.8	380.7
140°	205.9	211.6	220.7	232.1	246.4	262.9	280.1	299.4	321.1	345.6	372.5
142.5°	210.9	217.1	225.3	236.7	250.1	266.1	282.8	300.8	320.2	342.0	364.7
145°	219.0	224.2	232.7	242.4	255.5	270.4	285.8	301.7	318.8	337.1	355.3
147.5°	227.2	232.3	239.7	249.0	260.2	273.8	287.6	301.7	316.7	332.3	347.7
150°	232.7	237.3	244.7	252.7	262.9	276.1	288.0	301.7	314.8	329.1	342.2
152.5°	238.2	242.8	249.3	256.3	266.1	277.4	289.0	300.4	312.6	325.5	337.2
155°	247.0	250.4	256.1	262.4	270.4	280.1	289.2	298.9	308.6	320.0	329.7
157.5°	254.5	257.2	262.3	267.6	273.8	281.5	289.8	296.9	305.0	313.8	321.7
160°	259.5	261.8	266.4	270.4	276.1	282.9	289.8	296.0	302.3	309.7	317.1
162.5°	263.6	265.5	269.1	272.6	277.4	283.4	289.3	294.2	299.6	305.6	311.7
165°	269.2	270.4	273.2	275.5	279.5	284.0	288.0	291.5	295.5	300.0	304.6
167.5°	273.8	274.3	276.5	278.1	280.6	283.9	287.1	288.7	291.3	294.7	298.4
170°	276.1	276.6	278.3	279.5	280.6	283.5	285.8	286.9	288.6	291.5	294.3
172.5°	278.3	278.5	279.7	280.4	281.1	283.5	285.3	285.5	286.3	288.3	290.7
175°	280.6	280.1	281.2	281.2	281.8	282.9	284.0	283.5	283.5	284.6	285.8
177.5°	281.8	281.3	281.8	281.8	281.8	282.2	283.1	282.2	281.8	282.2	282.7
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332368

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1936.6	1936.6	1939.1	1948.6	1949.8	1958.0	1955.5
5°	2128.4	2143.3	2148.8	2172.4	2186.6	2192.9	2180.3
7.5°	2362.9	2405.1	2425.0	2449.7	2471.6	2478.2	2461.0
10°	2534.0	2578.0	2614.9	2637.7	2658.9	2673.1	2691.2
12.5°	2699.3	2753.4	2788.5	2820.7	2842.5	2860.5	2863.4
15°	2879.0	2960.7	3022.8	3068.4	3091.2	3103.0	3098.3
17.5°	3060.2	3136.0	3180.2	3226.7	3258.3	3259.9	3260.8
20°	3162.7	3236.6	3287.7	3322.3	3357.7	3356.1	3363.9
22.5°	3231.3	3289.4	3328.6	3353.7	3365.8	3359.9	3361.4
25°	3263.3	3280.6	3273.6	3233.5	3223.3	3186.3	3192.6
27.5°	3098.0	3016.2	2931.7	2822.9	2737.1	2668.5	2672.0
30°	2873.5	2728.9	2563.8	2425.5	2301.3	2266.7	2192.9
32.5°	2559.7	2342.8	2149.5	2020.6	1914.0	1885.1	1820.6
35°	2027.8	1817.2	1618.3	1498.8	1451.7	1385.7	1384.9
37.5°	1576.2	1390.7	1285.5	1195.9	1148.9	1109.0	1105.1
40°	1325.9	1181.3	1101.9	1037.5	991.1	961.2	954.2
42.5°	1151.1	1034.2	959.8	919.9	884.2	868.8	857.3
45°	940.0	861.4	809.5	773.4	756.9	745.1	738.8
47.5°	786.3	733.6	698.3	674.2	660.8	648.4	651.7
50°	702.7	659.4	633.5	610.7	600.5	591.8	592.6
52.5°	635.4	596.6	575.6	559.1	546.4	540.3	537.3
55°	539.2	514.8	493.6	481.8	474.7	466.1	463.7
57.5°	459.9	441.1	423.8	410.4	408.7	400.4	401.5
60°	407.1	391.4	377.3	370.2	364.7	357.6	360.0
62.5°	363.7	350.5	337.7	331.8	326.3	321.1	322.2
65°	297.9	285.3	277.4	274.3	271.9	269.6	267.2
67.5°	237.4	229.7	224.8	218.0	213.2	212.4	210.0
70°	199.6	189.4	180.8	172.1	169.8	169.0	169.8
72.5°	160.0	153.6	151.2	147.0	146.5	144.5	145.9
75°	120.3	117.9	116.3	113.2	113.2	113.2	113.2
77.5°	88.7	87.2	86.3	85.7	84.9	83.8	83.6
80°	69.2	68.4	66.8	66.8	66.0	66.8	66.0
82.5°	52.2	52.0	50.5	50.5	49.7	49.2	49.7
85°	26.7	25.9	27.5	25.9	26.7	25.2	26.7
87.5°	10.5	10.6	10.2	10.1	9.6	11.0	9.6
90°	14.8	15.4	16.5	16.0	16.5	17.1	16.5
92.5°	38.1	33.7	30.7	29.7	27.9	28.5	27.5
95°	139.2	108.9	88.4	77.6	72.4	68.4	66.2
97.5°	410.0	336.4	268.2	226.1	200.4	185.0	180.1
100°	626.3	559.5	478.5	420.9	379.3	357.1	357.6
102.5°	724.4	685.5	634.1	589.3	556.3	537.7	524.6
105°	798.5	809.4	794.5	768.3	746.6	728.4	725.5
107.5°	789.2	839.1	859.4	859.9	852.6	846.4	841.2
110°	758.6	830.5	870.4	886.4	890.9	889.8	888.6



TEST NUMBER: P332368

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	718.4	799.0	850.3	879.5	893.7	898.0	898.2
115°	654.2	738.1	800.2	843.0	868.1	879.5	882.4
117.5°	599.9	675.2	738.3	782.9	811.6	828.1	831.9
120°	569.8	638.2	695.9	740.9	772.9	786.5	790.0
122.5°	545.6	609.0	662.5	702.6	731.3	746.4	750.7
125°	515.6	570.4	616.0	652.5	677.6	691.9	695.9
127.5°	489.3	538.7	580.2	612.7	634.1	647.0	650.7
130°	472.8	519.0	557.8	588.1	608.6	620.6	625.1
132.5°	457.3	500.3	537.3	565.7	586.2	596.8	600.0
135°	435.2	472.3	504.8	532.7	549.8	560.1	564.1
137.5°	413.9	445.8	474.0	497.5	514.8	523.5	526.1
140°	401.5	428.9	453.4	475.1	491.1	500.2	499.6
142.5°	389.7	413.4	434.7	453.2	467.4	475.6	475.0
145°	374.2	392.4	409.0	423.2	435.2	439.8	440.9
147.5°	362.6	377.4	389.1	399.9	408.0	412.4	412.8
150°	355.3	367.3	378.2	386.7	393.0	396.4	396.4
152.5°	348.5	359.1	368.1	374.8	380.7	382.7	382.7
155°	338.8	347.4	354.2	359.3	363.9	365.0	365.6
157.5°	329.3	336.0	341.3	345.8	349.2	350.1	350.0
160°	323.4	329.1	333.1	337.1	340.5	340.5	339.9
162.5°	317.0	322.3	325.8	328.4	331.4	331.4	330.8
165°	308.0	312.0	314.8	317.1	319.4	318.8	318.8
167.5°	301.0	303.3	305.4	306.4	308.0	307.4	307.4
170°	296.0	298.3	299.4	300.0	301.2	300.6	300.6
172.5°	291.9	293.7	294.4	294.5	295.7	294.7	294.2
175°	286.3	287.5	287.5	287.5	288.0	287.5	286.9
177.5°	283.1	283.6	283.6	283.1	283.6	282.7	282.7
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8

(END OF REPORT)