

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332260

Luminaire Tested: **S123RDIP-S340D1025U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332260
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D1025U835-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5068.7 lumens
Efficiency: N/A
Efficacy: 135.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332260

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332260

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27				
1	93	89	85	82	83	79	76	74	62	60	58	46	45	44	31	31	30	23				
2	85	78	72	67	76	70	65	61	55	51	49	41	39	37	28	27	26	20				
3	77	69	62	56	69	62	56	51	48	44	41	36	34	32	25	23	22	17				
4	71	61	53	48	63	55	48	44	43	39	35	32	30	27	22	21	19	15				
5	65	54	47	41	58	49	42	37	39	34	30	29	26	24	20	18	17	13				
6	60	49	41	35	53	44	37	32	35	30	27	26	23	21	18	17	15	12				
7	55	44	36	31	49	40	33	28	32	27	23	24	21	18	17	15	13	11				
8	51	40	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12	10				
9	48	36	29	24	43	33	27	22	26	22	18	20	17	15	14	12	11	9				
10	44	33	26	22	40	30	24	20	24	20	17	19	15	13	13	11	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5858	5858	5858	5858
5°	6983	5883	5181	5883
10°	8719	5850	4680	5850
15°	10234	5789	4268	5789
20°	11423	5700	3918	5700
25°	11240	5606	3702	5606
30°	8079	5520	3480	5520
35°	5394	5406	3336	5406
40°	3974	5271	3188	5271
45°	3334	5033	3043	5033
50°	2942	4721	2840	4721
55°	2580	4363	2562	4363
60°	2297	4021	2347	4021
65°	2017	3655	2183	3655
70°	1583	3330	1995	3330
75°	1393	2907	1822	2907
80°	1215	2467	1791	2467
85°	976	1988	1902	1988



TEST NUMBER: P332260

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.5	1.1
10°-20°	167.2	3.3
20°-30°	262.7	5.2
30°-40°	274.1	5.4
40°-50°	234.5	4.6
50°-60°	178.8	3.5
60°-70°	114.6	2.3
70°-80°	55.1	1.1
80°-90°	18.4	0.4
90°-100°	274.4	5.4
100°-110°	777.0	15.3
110°-120°	764.4	15.1
120°-130°	609.7	12.0
130°-140°	480.7	9.5
140°-150°	358.8	7.1
150°-160°	250.1	4.9
160°-170°	146.9	2.9
170°-180°	47.8	0.9
0°-30°	483.4	9.5
0°-40°	757.5	14.9
0°-60°	1170.8	23.1
0°-90°	1358.9	26.8
90°-120°	1815.8	35.8
90°-150°	3265.1	64.4
90°-180°	3710.0	73.2
0°-180°	5068.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	544	544	544	544	544	
5°	646	544	480	544	646	67
15°	918	520	383	520	918	260
25°	946	472	312	472	946	407
35°	410	411	254	411	410	269
45°	219	331	200	331	219	172
55°	138	232	136	232	138	124
65°	79	144	86	144	79	78
75°	34	70	44	70	34	36
85°	8	16	15	16	8	10
90°	29	2	29	2	29	16
95°	116	34	116	34	116	209
105°	1270	116	1270	116	1270	1253
115°	1544	205	1544	205	1544	1500
125°	1218	284	1218	284	1218	1104
135°	987	333	987	333	987	766
145°	772	380	772	380	772	491
155°	640	432	640	432	640	298
165°	558	472	558	472	558	159
175°	502	492	502	492	502	49
180°	493	493	493	493	493	



TEST NUMBER: P332260

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	579.7	580.4	578.0	577.6	574.8	574.1	574.1	570.1	567.7	564.6	562.7
5°	646.3	650.0	648.1	644.0	637.0	635.3	630.9	623.9	616.0	606.2	601.6
7.5°	729.5	734.6	732.6	726.2	718.8	712.9	700.4	688.8	672.6	658.3	646.1
10°	797.7	792.4	788.2	781.9	775.1	764.2	751.1	733.2	712.5	696.1	678.0
12.5°	848.8	847.9	842.6	836.1	826.6	816.2	800.1	778.3	754.2	730.6	709.8
15°	918.4	919.8	916.3	909.6	896.0	877.6	853.4	844.3	809.8	784.2	758.6
17.5°	966.6	966.3	965.8	956.5	942.7	929.6	907.1	883.2	852.0	815.9	781.4
20°	997.2	994.8	995.3	984.8	974.6	959.4	937.5	902.8	877.2	835.5	799.8
22.5°	996.4	995.9	997.7	994.1	986.7	975.1	957.8	928.5	895.8	853.7	813.6
25°	946.4	944.5	955.4	958.5	970.4	972.5	967.3	951.3	920.3	876.9	827.3
27.5°	792.0	791.0	811.3	836.8	869.0	894.1	918.3	930.0	920.3	889.2	839.5
30°	650.0	671.9	682.2	719.0	760.0	808.9	851.8	892.5	902.6	889.0	848.3
32.5°	539.7	558.8	567.4	598.9	637.2	694.5	758.8	816.5	857.3	867.6	843.1
35°	410.5	410.7	430.3	444.3	479.7	538.6	601.1	678.4	755.3	813.6	819.6
37.5°	327.6	328.7	340.6	354.5	381.1	412.2	467.2	531.5	620.3	709.7	762.2
40°	282.8	284.9	293.8	307.5	326.6	350.2	393.0	453.6	527.7	627.2	708.5
42.5°	254.1	257.5	262.1	272.7	284.5	306.6	341.2	388.0	455.4	549.5	643.3
45°	219.0	220.9	224.4	229.3	240.0	255.3	278.6	310.1	366.0	441.7	535.6
47.5°	193.2	192.2	195.9	199.8	207.0	217.5	233.1	258.7	298.6	359.4	439.0
50°	175.7	175.4	178.0	181.0	187.8	195.5	208.3	227.6	259.3	309.6	382.6
52.5°	159.3	160.1	162.0	165.7	170.6	176.8	188.3	202.3	229.5	272.9	333.7
55°	137.5	138.2	140.7	142.8	146.3	152.6	159.8	171.5	190.1	220.4	270.5
57.5°	119.0	118.7	121.1	121.7	125.6	130.7	136.3	145.4	158.9	181.4	215.1
60°	106.7	106.0	108.1	109.7	111.8	116.0	120.7	129.5	140.3	156.8	185.7
62.5°	95.5	95.2	96.7	98.4	100.1	103.9	107.8	114.6	123.1	137.0	160.0
65°	79.2	79.9	80.6	81.3	82.2	84.6	88.3	93.0	98.8	108.6	125.1
67.5°	62.3	63.0	63.2	64.6	66.6	68.1	70.4	74.5	78.6	86.8	96.2
70°	50.3	50.1	50.3	51.0	53.6	56.1	59.2	62.2	64.8	70.6	78.5
72.5°	43.2	42.8	43.4	43.6	44.8	45.5	47.4	50.3	53.6	57.5	63.2
75°	33.5	33.5	33.5	33.5	34.5	34.9	35.6	36.3	37.5	39.4	43.6
77.5°	24.8	24.8	25.2	25.4	25.6	25.9	26.3	27.0	27.4	28.4	30.2
80°	19.6	19.8	19.6	19.8	19.8	20.3	20.5	21.2	21.4	22.6	23.3
82.5°	14.7	14.6	14.7	15.0	15.0	15.4	15.5	16.0	16.0	16.6	17.3
85°	7.9	7.5	7.9	7.7	8.2	7.7	7.9	8.4	8.4	8.6	9.6
87.5°	7.7	8.2	7.7	7.6	7.8	7.6	7.4	7.2	7.4	7.4	7.0
90°	28.9	29.9	28.9	27.9	28.9	27.0	26.0	25.0	24.0	25.0	22.0
92.5°	48.1	49.9	48.9	51.9	53.7	58.9	66.7	84.0	115.8	153.5	168.9
95°	115.8	119.8	126.8	135.8	154.7	190.7	243.6	359.3	480.1	591.9	527.0
97.5°	315.2	323.8	350.8	395.7	469.3	588.7	717.5	895.8	981.4	917.3	671.6
100°	625.9	624.9	663.8	736.7	837.5	979.2	1096.0	1176.9	1141.9	945.3	638.8
102.5°	918.1	941.1	973.6	1031.3	1109.8	1199.6	1267.7	1270.3	1149.9	893.4	590.9
105°	1269.7	1274.7	1306.6	1344.5	1390.5	1416.4	1397.5	1297.6	1089.0	802.5	532.0
107.5°	1472.1	1481.3	1492.1	1504.9	1504.1	1468.5	1381.1	1219.0	982.4	722.3	494.5
110°	1555.2	1557.2	1559.2	1551.2	1523.2	1453.3	1327.6	1143.9	915.3	676.8	480.1



TEST NUMBER: P332260

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1571.9	1571.5	1563.9	1539.2	1488.1	1398.2	1257.3	1069.6	857.0	646.4	472.1
115°	1544.2	1539.2	1519.2	1475.3	1400.4	1291.6	1144.9	971.2	786.6	613.9	469.1
117.5°	1455.9	1449.2	1420.4	1370.1	1292.0	1181.6	1049.9	900.0	744.0	594.7	470.9
120°	1382.5	1376.5	1352.5	1296.6	1217.8	1117.0	997.2	862.4	721.7	585.9	474.1
122.5°	1313.8	1306.2	1279.9	1229.6	1159.5	1065.9	954.9	832.9	703.3	580.3	479.7
125°	1217.8	1210.8	1185.8	1141.9	1078.0	998.2	902.4	793.6	679.8	573.0	488.1
127.5°	1138.7	1132.3	1109.8	1072.2	1015.3	942.7	856.2	759.2	659.0	569.4	497.7
130°	1094.0	1086.0	1065.1	1029.1	976.2	908.3	827.5	737.7	647.8	567.0	504.1
132.5°	1050.1	1044.5	1025.9	990.0	940.3	875.6	800.3	717.7	637.4	566.2	508.9
135°	987.2	980.2	962.2	932.3	883.4	826.5	761.6	690.7	623.9	565.0	516.1
137.5°	920.7	916.1	901.0	870.6	829.5	780.2	724.3	666.2	612.1	562.8	520.8
140°	874.4	875.4	859.4	831.5	793.6	750.6	702.7	651.8	604.9	562.0	524.0
142.5°	831.3	832.3	817.9	793.2	760.8	723.5	682.0	638.2	598.5	560.4	526.4
145°	771.6	769.6	761.6	740.6	715.7	686.7	654.8	621.9	589.9	558.0	528.0
147.5°	722.5	721.7	714.1	699.9	681.0	660.4	634.6	608.5	581.5	554.2	528.0
150°	693.7	693.7	687.7	676.8	661.8	642.8	621.9	598.9	575.9	551.0	528.0
152.5°	669.8	669.8	666.2	656.0	644.2	628.5	609.9	590.1	569.6	547.0	525.6
155°	639.8	638.8	636.8	628.9	619.9	607.9	592.9	576.9	560.0	540.0	523.0
157.5°	612.5	612.7	611.1	605.1	597.3	587.9	576.3	563.0	549.2	533.8	519.7
160°	594.9	595.9	595.9	589.9	582.9	575.9	566.0	555.0	542.0	529.0	518.1
162.5°	578.9	579.9	579.9	574.8	570.2	564.0	554.8	545.4	534.8	524.2	514.9
165°	558.0	558.0	559.0	555.0	551.0	546.0	539.0	533.0	525.0	517.1	510.1
167.5°	538.0	538.0	539.0	536.2	534.4	530.8	526.8	522.2	515.7	509.9	505.3
170°	526.0	526.0	527.0	525.0	524.0	522.0	518.1	515.1	510.1	505.1	502.1
172.5°	514.9	515.7	517.5	515.5	515.3	514.1	510.9	508.7	504.5	501.1	499.7
175°	502.1	503.1	504.1	503.1	503.1	503.1	501.1	500.1	498.1	496.1	496.1
177.5°	494.7	494.7	496.3	495.5	496.3	496.3	495.5	494.7	493.9	493.1	493.9
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P332260

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	561.9	561.4	558.8	555.8	551.9	549.3	547.2	546.1	542.7	538.6	535.9
5°	596.7	589.7	582.2	573.1	564.7	556.1	550.8	544.5	536.8	528.2	522.1
7.5°	633.8	620.1	605.4	590.1	575.1	561.6	549.6	539.4	527.2	514.8	506.2
10°	662.4	642.3	621.6	600.4	581.1	562.9	548.9	535.2	520.5	506.3	495.5
12.5°	688.3	661.9	638.0	611.9	587.2	565.5	545.4	529.2	511.5	496.4	484.2
15°	721.1	694.0	665.2	625.5	592.7	565.2	540.7	519.5	498.1	479.5	467.6
17.5°	751.7	711.1	672.2	639.2	596.5	562.2	532.3	507.0	483.4	463.7	449.0
20°	764.4	725.0	682.9	640.7	598.8	560.3	525.6	497.6	473.2	450.8	437.3
22.5°	772.0	727.5	683.0	637.7	593.2	553.2	518.9	488.1	461.6	440.4	423.7
25°	780.9	727.8	678.9	634.2	588.7	545.4	504.6	472.0	443.4	420.8	403.1
27.5°	786.8	724.3	666.5	616.8	570.7	527.6	490.2	455.6	426.5	402.6	383.6
30°	787.9	721.5	657.0	603.2	556.4	516.7	477.1	444.1	413.3	387.9	370.2
32.5°	789.4	714.6	644.1	587.0	539.0	499.8	463.9	432.3	400.8	375.8	357.7
35°	783.3	710.8	624.6	558.9	510.9	472.9	440.6	411.4	380.5	356.2	337.8
37.5°	756.8	695.7	604.4	527.3	477.1	442.0	415.6	390.2	361.8	335.6	318.3
40°	730.2	680.8	588.7	508.1	455.7	419.6	395.8	375.1	347.6	323.1	304.5
42.5°	690.5	660.4	573.8	488.0	431.5	396.7	376.6	357.2	333.1	308.2	290.7
45°	617.6	621.6	543.3	455.9	397.9	363.0	344.1	330.6	309.2	288.7	270.7
47.5°	526.3	563.3	507.5	421.8	362.6	329.8	313.3	301.5	287.0	266.9	250.5
50°	466.7	519.5	478.8	398.9	340.4	307.8	291.5	281.9	269.3	253.5	237.9
52.5°	411.7	468.5	444.1	373.3	316.3	286.5	270.6	262.7	252.7	237.8	223.7
55°	335.7	393.3	387.7	334.8	280.3	253.5	241.4	232.5	225.8	214.6	203.4
57.5°	271.6	326.1	329.0	291.9	248.5	222.0	211.6	204.9	200.5	192.1	181.7
60°	231.1	281.2	291.0	263.0	225.8	202.5	192.2	186.8	183.4	176.6	168.7
62.5°	197.6	240.2	251.3	231.2	204.0	182.1	174.1	169.0	166.6	160.8	153.8
65°	151.2	186.6	197.3	186.2	171.9	154.5	147.9	143.5	141.4	138.2	133.0
67.5°	113.7	139.5	151.3	143.4	138.2	127.2	123.1	120.7	118.8	116.6	112.3
70°	91.3	110.4	122.5	120.5	116.3	110.4	107.4	105.8	103.9	102.0	98.3
72.5°	73.4	86.6	97.9	99.0	95.6	94.4	91.7	91.0	89.9	87.7	85.6
75°	48.7	57.8	65.7	68.7	70.1	71.3	70.1	69.9	69.7	67.8	66.6
77.5°	31.9	36.8	41.8	47.0	49.2	50.7	51.1	52.0	51.3	50.4	49.8
80°	24.5	25.6	29.1	33.5	37.0	38.4	39.4	39.8	39.6	39.4	38.4
82.5°	17.8	18.7	20.4	23.5	26.4	28.7	29.3	29.2	29.7	29.9	29.1
85°	9.6	9.8	10.3	10.7	12.3	14.9	15.6	16.1	16.5	16.5	15.1
87.5°	6.8	6.0	5.8	5.4	5.5	5.1	5.8	6.4	6.9	6.6	7.2
90°	19.0	16.0	13.0	11.0	9.0	6.0	4.0	2.0	4.0	6.0	9.0
92.5°	126.8	83.8	57.7	42.9	34.5	26.8	18.4	12.4	18.4	26.8	34.5
95°	363.3	214.6	129.8	90.8	64.9	47.9	36.9	33.9	36.9	47.9	64.9
97.5°	398.7	231.0	149.9	107.8	82.2	67.5	58.9	57.9	58.9	67.5	82.2
100°	376.3	228.6	158.7	119.8	95.8	81.9	74.9	73.9	74.9	81.9	95.8
102.5°	357.1	231.8	169.1	133.4	111.8	98.6	92.4	90.6	92.4	98.6	111.8
105°	343.4	240.6	186.7	155.7	136.8	124.8	118.8	115.8	118.8	124.8	136.8
107.5°	342.4	256.9	209.6	180.9	163.1	151.3	145.5	142.5	145.5	151.3	163.1
110°	346.4	270.5	225.6	197.6	180.7	169.7	164.7	161.7	164.7	169.7	180.7



TEST NUMBER: P332260

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	354.4	284.1	242.4	215.2	198.2	187.3	182.3	179.3	182.3	187.3	198.2
115°	367.3	306.4	268.5	241.6	224.6	214.6	208.6	204.6	208.6	214.6	224.6
117.5°	384.5	330.2	292.7	267.7	248.7	239.6	234.6	230.0	234.6	239.6	248.7
120°	397.3	345.4	309.4	284.5	265.5	255.5	250.5	247.5	250.5	255.5	265.5
122.5°	409.3	361.3	326.2	299.7	281.5	270.7	265.7	262.7	265.7	270.7	281.5
125°	428.2	384.3	349.4	322.4	303.4	292.5	286.5	284.5	286.5	292.5	303.4
127.5°	443.8	404.3	370.5	343.6	322.6	311.4	304.0	301.1	304.0	311.4	322.6
130°	454.2	416.2	383.3	356.3	335.4	323.4	314.4	311.4	314.4	323.4	335.4
132.5°	463.8	426.6	394.5	368.3	347.4	333.0	323.2	319.4	323.2	333.0	347.4
135°	476.1	442.2	411.2	384.3	363.3	348.4	337.4	333.4	337.4	348.4	363.3
137.5°	485.3	453.0	423.2	398.3	377.5	361.5	350.8	346.6	350.8	361.5	377.5
140°	490.1	460.2	431.2	406.3	386.3	370.3	360.3	355.4	360.3	370.3	386.3
142.5°	494.9	465.8	437.6	414.2	394.3	379.9	369.1	364.9	369.1	379.9	394.3
145°	500.1	473.1	447.2	424.2	407.3	392.3	383.3	380.3	383.3	392.3	407.3
147.5°	503.3	479.1	455.4	435.8	419.4	406.5	397.7	395.9	397.7	406.5	419.4
150°	504.1	483.1	460.2	442.2	428.2	415.2	407.3	406.3	407.3	415.2	428.2
152.5°	505.7	485.5	465.8	448.6	436.2	424.8	416.8	416.6	416.8	424.8	436.2
155°	506.1	490.1	473.1	459.2	448.2	438.2	432.2	432.2	432.2	438.2	448.2
157.5°	507.1	492.7	479.1	468.3	459.0	450.2	445.4	444.6	445.4	450.2	459.0
160°	507.1	495.1	483.1	473.1	466.1	458.2	454.2	454.2	454.2	458.2	466.1
162.5°	506.3	495.9	485.5	477.1	470.9	464.6	461.4	461.4	461.4	464.6	470.9
165°	504.1	497.1	489.1	482.1	478.1	473.1	471.1	472.1	471.1	473.1	478.1
167.5°	502.5	496.9	491.1	486.7	483.9	480.1	479.1	480.3	479.1	480.1	483.9
170°	500.1	496.1	491.1	489.1	487.1	484.1	483.1	485.1	483.1	484.1	487.1
172.5°	499.3	496.1	491.9	490.7	489.5	487.3	487.1	488.3	487.1	487.3	489.5
175°	497.1	495.1	493.1	492.1	492.1	490.1	491.1	492.1	491.1	490.1	492.1
177.5°	495.5	493.9	493.1	493.1	493.1	492.3	493.1	493.9	493.1	492.3	493.1
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P332260

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	534.9	532.5	530.8	527.1	524.7	522.1	519.5	521.1	520.9	520.8	520.8
5°	517.0	511.6	506.7	500.4	496.5	491.6	487.9	487.4	488.3	485.1	483.2
7.5°	499.2	491.9	484.9	478.0	470.6	464.7	461.1	459.3	457.0	455.0	452.9
10°	486.7	478.1	471.3	462.7	454.8	447.8	443.4	440.3	438.7	437.1	434.0
12.5°	473.8	465.4	456.8	447.0	439.5	431.4	428.1	424.7	421.6	419.7	415.6
15°	455.0	444.1	435.0	424.7	416.3	408.4	403.8	397.0	396.1	393.7	389.5
17.5°	436.1	424.3	411.7	404.1	394.7	386.4	379.3	377.1	370.4	367.9	364.2
20°	421.2	410.3	400.7	390.7	377.0	369.3	363.7	360.7	355.3	352.0	349.7
22.5°	408.4	397.2	386.2	374.5	363.2	354.5	350.4	345.7	342.8	338.2	335.7
25°	390.0	377.9	364.6	352.0	343.9	337.4	330.8	326.6	322.4	320.3	315.7
27.5°	368.7	356.0	343.6	334.0	324.0	317.6	311.7	308.0	302.9	299.4	296.8
30°	356.9	342.0	331.3	322.7	309.9	303.8	299.4	294.7	291.0	287.3	284.7
32.5°	343.3	329.7	319.6	308.9	299.1	292.4	286.7	282.6	279.4	275.9	273.3
35°	322.0	310.6	300.1	289.4	282.1	275.4	268.6	265.1	262.1	258.8	256.5
37.5°	302.7	292.0	282.0	271.9	262.9	257.4	252.0	249.3	245.2	243.0	240.7
40°	290.8	280.3	269.6	259.8	250.5	246.3	241.4	237.4	233.7	232.0	229.5
42.5°	277.7	267.2	258.2	247.7	240.0	234.3	229.8	225.5	222.7	220.3	218.9
45°	258.4	249.1	240.2	229.7	222.5	217.6	212.5	208.5	206.0	204.3	201.8
47.5°	239.6	230.3	221.3	212.2	205.2	199.6	194.4	191.7	188.3	186.3	184.6
50°	226.0	217.6	208.1	199.7	192.7	187.1	182.9	179.4	176.4	173.8	172.6
52.5°	213.5	204.6	196.3	188.5	181.1	174.8	171.0	167.3	165.0	162.1	160.7
55°	192.9	184.3	177.3	169.6	162.4	157.0	152.4	149.1	146.8	143.5	141.7
57.5°	173.6	165.8	157.5	150.8	143.4	138.9	135.0	130.6	127.7	125.2	123.3
60°	160.5	151.7	144.4	138.2	131.6	125.8	122.3	118.8	115.8	113.2	111.6
62.5°	146.9	139.2	132.3	125.5	119.5	114.4	110.4	107.5	104.8	103.2	101.5
65°	126.0	120.0	113.0	107.4	101.8	98.1	94.8	92.3	90.4	89.2	87.8
67.5°	106.8	101.0	94.9	89.4	85.6	82.8	80.7	78.5	77.5	76.0	75.1
70°	94.4	88.3	82.9	78.7	75.0	72.9	71.5	69.9	69.0	67.1	66.2
72.5°	80.8	76.4	72.5	69.1	66.1	64.2	62.4	60.4	58.9	56.8	55.9
75°	63.6	59.6	56.6	54.3	52.4	49.9	47.3	45.2	44.5	43.8	43.6
77.5°	47.1	44.6	42.4	40.4	38.1	36.3	35.7	35.2	35.1	34.7	34.7
80°	37.0	34.7	33.1	30.8	29.4	29.4	29.4	28.9	29.1	29.1	29.1
82.5°	27.5	25.4	24.5	23.7	23.4	23.6	23.6	23.7	23.5	23.9	23.7
85°	14.2	14.4	14.9	14.7	14.9	14.9	15.4	15.1	15.4	14.9	15.4
87.5°	7.4	8.4	9.2	9.9	10.7	11.1	11.1	11.3	11.7	11.9	12.3
90°	11.0	13.0	16.0	19.0	22.0	25.0	24.0	25.0	26.0	27.0	28.9
92.5°	42.9	57.7	83.8	126.8	168.9	153.5	115.8	84.0	66.7	58.9	53.7
95°	90.8	129.8	214.6	363.3	527.0	591.9	480.1	359.3	243.6	190.7	154.7
97.5°	107.8	149.9	231.0	398.7	671.6	917.3	981.4	895.8	717.5	588.7	469.3
100°	119.8	158.7	228.6	376.3	638.8	945.3	1141.9	1176.9	1096.0	979.2	837.5
102.5°	133.4	169.1	231.8	357.1	590.9	893.4	1149.9	1270.3	1267.7	1199.6	1109.8
105°	155.7	186.7	240.6	343.4	532.0	802.5	1089.0	1297.6	1397.5	1416.4	1390.5
107.5°	180.9	209.6	256.9	342.4	494.5	722.3	982.4	1219.0	1381.1	1468.5	1504.1
110°	197.6	225.6	270.5	346.4	480.1	676.8	915.3	1143.9	1327.6	1453.3	1523.2



TEST NUMBER: P332260

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	215.2	242.4	284.1	354.4	472.1	646.4	857.0	1069.6	1257.3	1398.2	1488.1
115°	241.6	268.5	306.4	367.3	469.1	613.9	786.6	971.2	1144.9	1291.6	1400.4
117.5°	267.7	292.7	330.2	384.5	470.9	594.7	744.0	900.0	1049.9	1181.6	1292.0
120°	284.5	309.4	345.4	397.3	474.1	585.9	721.7	862.4	997.2	1117.0	1217.8
122.5°	299.7	326.2	361.3	409.3	479.7	580.3	703.3	832.9	954.9	1065.9	1159.5
125°	322.4	349.4	384.3	428.2	488.1	573.0	679.8	793.6	902.4	998.2	1078.0
127.5°	343.6	370.5	404.3	443.8	497.7	569.4	659.0	759.2	856.2	942.7	1015.3
130°	356.3	383.3	416.2	454.2	504.1	567.0	647.8	737.7	827.5	908.3	976.2
132.5°	368.3	394.5	426.6	463.8	508.9	566.2	637.4	717.7	800.3	875.6	940.3
135°	384.3	411.2	442.2	476.1	516.1	565.0	623.9	690.7	761.6	826.5	883.4
137.5°	398.3	423.2	453.0	485.3	520.8	562.8	612.1	666.2	724.3	780.2	829.5
140°	406.3	431.2	460.2	490.1	524.0	562.0	604.9	651.8	702.7	750.6	793.6
142.5°	414.2	437.6	465.8	494.9	526.4	560.4	598.5	638.2	682.0	723.5	760.8
145°	424.2	447.2	473.1	500.1	528.0	558.0	589.9	621.9	654.8	686.7	715.7
147.5°	435.8	455.4	479.1	503.3	528.0	554.2	581.5	608.5	634.6	660.4	681.0
150°	442.2	460.2	483.1	504.1	528.0	551.0	575.9	598.9	621.9	642.8	661.8
152.5°	448.6	465.8	485.5	505.7	525.6	547.0	569.6	590.1	609.9	628.5	644.2
155°	459.2	473.1	490.1	506.1	523.0	540.0	560.0	576.9	592.9	607.9	619.9
157.5°	468.3	479.1	492.7	507.1	519.7	533.8	549.2	563.0	576.3	587.9	597.3
160°	473.1	483.1	495.1	507.1	518.1	529.0	542.0	555.0	566.0	575.9	582.9
162.5°	477.1	485.5	495.9	506.3	514.9	524.2	534.8	545.4	554.8	564.0	570.2
165°	482.1	489.1	497.1	504.1	510.1	517.1	525.0	533.0	539.0	546.0	551.0
167.5°	486.7	491.1	496.9	502.5	505.3	509.9	515.7	522.2	526.8	530.8	534.4
170°	489.1	491.1	496.1	500.1	502.1	505.1	510.1	515.1	518.1	522.0	524.0
172.5°	490.7	491.9	496.1	499.3	499.7	501.1	504.5	508.7	510.9	514.1	515.3
175°	492.1	493.1	495.1	497.1	496.1	496.1	498.1	500.1	501.1	503.1	503.1
177.5°	493.1	493.1	493.9	495.5	493.9	493.1	493.9	494.7	495.5	496.3	496.3
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P332260

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	518.5	518.3	518.5	517.8	518.5	518.3	518.5	520.8	520.8	520.9	521.1
5°	482.5	482.3	481.6	479.5	481.6	482.3	482.5	483.2	485.1	488.3	487.4
7.5°	451.0	450.7	448.7	448.7	448.7	450.7	451.0	452.9	455.0	457.0	459.3
10°	432.4	432.6	429.8	428.2	429.8	432.6	432.4	434.0	437.1	438.7	440.3
12.5°	414.3	413.3	411.0	409.2	411.0	413.3	414.3	415.6	419.7	421.6	424.7
15°	390.5	388.1	382.6	383.0	382.6	388.1	390.5	389.5	393.7	396.1	397.0
17.5°	362.4	360.7	360.6	357.3	360.6	360.7	362.4	364.2	367.9	370.4	377.1
20°	346.0	344.8	345.3	342.0	345.3	344.8	346.0	349.7	352.0	355.3	360.7
22.5°	333.1	331.9	330.0	329.0	330.0	331.9	333.1	335.7	338.2	342.8	345.7
25°	314.3	312.4	310.6	311.7	310.6	312.4	314.3	315.7	320.3	322.4	326.6
27.5°	295.5	294.1	292.2	292.0	292.2	294.1	295.5	296.8	299.4	302.9	308.0
30°	283.5	282.1	281.2	280.0	281.2	282.1	283.5	284.7	287.3	291.0	294.7
32.5°	271.4	271.1	269.5	269.2	269.5	271.1	271.4	273.3	275.9	279.4	282.6
35°	255.6	254.2	253.7	253.9	253.7	254.2	255.6	256.5	258.8	262.1	265.1
37.5°	240.5	238.7	237.8	237.0	237.8	238.7	240.5	240.7	243.0	245.2	249.3
40°	229.7	227.9	227.4	226.9	227.4	227.9	229.7	229.5	232.0	233.7	237.4
42.5°	217.6	216.9	216.6	215.7	216.6	216.9	217.6	218.9	220.3	222.7	225.5
45°	201.1	200.8	199.4	199.9	199.4	200.8	201.1	201.8	204.3	206.0	208.5
47.5°	183.6	182.6	181.6	182.3	181.6	182.6	183.6	184.6	186.3	188.3	191.7
50°	171.7	171.2	169.1	169.6	169.1	171.2	171.7	172.6	173.8	176.4	179.4
52.5°	159.8	158.0	157.2	156.9	157.2	158.0	159.8	160.7	162.1	165.0	167.3
55°	140.0	137.9	137.0	136.5	137.0	137.9	140.0	141.7	143.5	146.8	149.1
57.5°	120.6	120.1	119.3	119.8	119.3	120.1	120.6	123.3	125.2	127.7	130.6
60°	109.3	109.3	109.3	109.0	109.3	109.3	109.3	111.6	113.2	115.8	118.8
62.5°	100.5	99.9	99.8	100.1	99.8	99.9	100.5	101.5	103.2	104.8	107.5
65°	87.1	86.9	86.0	85.7	86.0	86.9	87.1	87.8	89.2	90.4	92.3
67.5°	74.5	73.7	73.4	73.1	73.4	73.7	74.5	75.1	76.0	77.5	78.5
70°	65.0	64.5	63.1	63.4	63.1	64.5	65.0	66.2	67.1	69.0	69.9
72.5°	54.8	54.3	54.0	53.7	54.0	54.3	54.8	55.9	56.8	58.9	60.4
75°	43.3	43.1	42.9	43.8	42.9	43.1	43.3	43.6	43.8	44.5	45.2
77.5°	34.7	34.7	34.9	34.5	34.9	34.7	34.7	34.7	34.7	35.1	35.2
80°	29.1	29.1	28.9	28.9	28.9	29.1	29.1	29.1	29.1	29.1	28.9
82.5°	23.3	23.5	23.7	23.3	23.7	23.5	23.3	23.7	23.9	23.5	23.7
85°	15.4	15.1	15.6	15.4	15.6	15.1	15.4	15.4	14.9	15.4	15.1
87.5°	12.5	12.3	12.5	12.5	12.5	12.3	12.5	12.3	11.9	11.7	11.3
90°	27.9	28.9	29.9	28.9	29.9	28.9	27.9	28.9	27.0	26.0	25.0
92.5°	51.9	48.9	49.9	48.1	49.9	48.9	51.9	53.7	58.9	66.7	84.0
95°	135.8	126.8	119.8	115.8	119.8	126.8	135.8	154.7	190.7	243.6	359.3
97.5°	395.7	350.8	323.8	315.2	323.8	350.8	395.7	469.3	588.7	717.5	895.8
100°	736.7	663.8	624.9	625.9	624.9	663.8	736.7	837.5	979.2	1096.0	1176.9
102.5°	1031.3	973.6	941.1	918.1	941.1	973.6	1031.3	1109.8	1199.6	1267.7	1270.3
105°	1344.5	1306.6	1274.7	1269.7	1274.7	1306.6	1344.5	1390.5	1416.4	1397.5	1297.6
107.5°	1504.9	1492.1	1481.3	1472.1	1481.3	1492.1	1504.9	1504.1	1468.5	1381.1	1219.0
110°	1551.2	1559.2	1557.2	1555.2	1557.2	1559.2	1551.2	1523.2	1453.3	1327.6	1143.9



TEST NUMBER: P332260

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1539.2	1563.9	1571.5	1571.9	1571.5	1563.9	1539.2	1488.1	1398.2	1257.3	1069.6
115°	1475.3	1519.2	1539.2	1544.2	1539.2	1519.2	1475.3	1400.4	1291.6	1144.9	971.2
117.5°	1370.1	1420.4	1449.2	1455.9	1449.2	1420.4	1370.1	1292.0	1181.6	1049.9	900.0
120°	1296.6	1352.5	1376.5	1382.5	1376.5	1352.5	1296.6	1217.8	1117.0	997.2	862.4
122.5°	1229.6	1279.9	1306.2	1313.8	1306.2	1279.9	1229.6	1159.5	1065.9	954.9	832.9
125°	1141.9	1185.8	1210.8	1217.8	1210.8	1185.8	1141.9	1078.0	998.2	902.4	793.6
127.5°	1072.2	1109.8	1132.3	1138.7	1132.3	1109.8	1072.2	1015.3	942.7	856.2	759.2
130°	1029.1	1065.1	1086.0	1094.0	1086.0	1065.1	1029.1	976.2	908.3	827.5	737.7
132.5°	990.0	1025.9	1044.5	1050.1	1044.5	1025.9	990.0	940.3	875.6	800.3	717.7
135°	932.3	962.2	980.2	987.2	980.2	962.2	932.3	883.4	826.5	761.6	690.7
137.5°	870.6	901.0	916.1	920.7	916.1	901.0	870.6	829.5	780.2	724.3	666.2
140°	831.5	859.4	875.4	874.4	875.4	859.4	831.5	793.6	750.6	702.7	651.8
142.5°	793.2	817.9	832.3	831.3	832.3	817.9	793.2	760.8	723.5	682.0	638.2
145°	740.6	761.6	769.6	771.6	769.6	761.6	740.6	715.7	686.7	654.8	621.9
147.5°	699.9	714.1	721.7	722.5	721.7	714.1	699.9	681.0	660.4	634.6	608.5
150°	676.8	687.7	693.7	693.7	693.7	687.7	676.8	661.8	642.8	621.9	598.9
152.5°	656.0	666.2	669.8	669.8	669.8	666.2	656.0	644.2	628.5	609.9	590.1
155°	628.9	636.8	638.8	639.8	638.8	636.8	628.9	619.9	607.9	592.9	576.9
157.5°	605.1	611.1	612.7	612.5	612.7	611.1	605.1	597.3	587.9	576.3	563.0
160°	589.9	595.9	595.9	594.9	595.9	595.9	589.9	582.9	575.9	566.0	555.0
162.5°	574.8	579.9	579.9	578.9	579.9	579.9	574.8	570.2	564.0	554.8	545.4
165°	555.0	559.0	558.0	558.0	558.0	559.0	555.0	551.0	546.0	539.0	533.0
167.5°	536.2	539.0	538.0	538.0	538.0	539.0	536.2	534.4	530.8	526.8	522.2
170°	525.0	527.0	526.0	526.0	526.0	527.0	525.0	524.0	522.0	518.1	515.1
172.5°	515.5	517.5	515.7	514.9	515.7	517.5	515.5	515.3	514.1	510.9	508.7
175°	503.1	504.1	503.1	502.1	503.1	504.1	503.1	503.1	503.1	501.1	500.1
177.5°	495.5	496.3	494.7	494.7	494.7	496.3	495.5	496.3	496.3	495.5	494.7
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P332260

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	519.5	522.1	524.7	527.1	530.8	532.5	534.9	535.9	538.6	542.7	546.1
5°	487.9	491.6	496.5	500.4	506.7	511.6	517.0	522.1	528.2	536.8	544.5
7.5°	461.1	464.7	470.6	478.0	484.9	491.9	499.2	506.2	514.8	527.2	539.4
10°	443.4	447.8	454.8	462.7	471.3	478.1	486.7	495.5	506.3	520.5	535.2
12.5°	428.1	431.4	439.5	447.0	456.8	465.4	473.8	484.2	496.4	511.5	529.2
15°	403.8	408.4	416.3	424.7	435.0	444.1	455.0	467.6	479.5	498.1	519.5
17.5°	379.3	386.4	394.7	404.1	411.7	424.3	436.1	449.0	463.7	483.4	507.0
20°	363.7	369.3	377.0	390.7	400.7	410.3	421.2	437.3	450.8	473.2	497.6
22.5°	350.4	354.5	363.2	374.5	386.2	397.2	408.4	423.7	440.4	461.6	488.1
25°	330.8	337.4	343.9	352.0	364.6	377.9	390.0	403.1	420.8	443.4	472.0
27.5°	311.7	317.6	324.0	334.0	343.6	356.0	368.7	383.6	402.6	426.5	455.6
30°	299.4	303.8	309.9	322.7	331.3	342.0	356.9	370.2	387.9	413.3	444.1
32.5°	286.7	292.4	299.1	308.9	319.6	329.7	343.3	357.7	375.8	400.8	432.3
35°	268.6	275.4	282.1	289.4	300.1	310.6	322.0	337.8	356.2	380.5	411.4
37.5°	252.0	257.4	262.9	271.9	282.0	292.0	302.7	318.3	335.6	361.8	390.2
40°	241.4	246.3	250.5	259.8	269.6	280.3	290.8	304.5	323.1	347.6	375.1
42.5°	229.8	234.3	240.0	247.7	258.2	267.2	277.7	290.7	308.2	333.1	357.2
45°	212.5	217.6	222.5	229.7	240.2	249.1	258.4	270.7	288.7	309.2	330.6
47.5°	194.4	199.6	205.2	212.2	221.3	230.3	239.6	250.5	266.9	287.0	301.5
50°	182.9	187.1	192.7	199.7	208.1	217.6	226.0	237.9	253.5	269.3	281.9
52.5°	171.0	174.8	181.1	188.5	196.3	204.6	213.5	223.7	237.8	252.7	262.7
55°	152.4	157.0	162.4	169.6	177.3	184.3	192.9	203.4	214.6	225.8	232.5
57.5°	135.0	138.9	143.4	150.8	157.5	165.8	173.6	181.7	192.1	200.5	204.9
60°	122.3	125.8	131.6	138.2	144.4	151.7	160.5	168.7	176.6	183.4	186.8
62.5°	110.4	114.4	119.5	125.5	132.3	139.2	146.9	153.8	160.8	166.6	169.0
65°	94.8	98.1	101.8	107.4	113.0	120.0	126.0	133.0	138.2	141.4	143.5
67.5°	80.7	82.8	85.6	89.4	94.9	101.0	106.8	112.3	116.6	118.8	120.7
70°	71.5	72.9	75.0	78.7	82.9	88.3	94.4	98.3	102.0	103.9	105.8
72.5°	62.4	64.2	66.1	69.1	72.5	76.4	80.8	85.6	87.7	89.9	91.0
75°	47.3	49.9	52.4	54.3	56.6	59.6	63.6	66.6	67.8	69.7	69.9
77.5°	35.7	36.3	38.1	40.4	42.4	44.6	47.1	49.8	50.4	51.3	52.0
80°	29.4	29.4	29.4	30.8	33.1	34.7	37.0	38.4	39.4	39.6	39.8
82.5°	23.6	23.6	23.4	23.7	24.5	25.4	27.5	29.1	29.9	29.7	29.2
85°	15.4	14.9	14.9	14.7	14.9	14.4	14.2	15.1	16.5	16.5	16.1
87.5°	11.1	11.1	10.7	9.9	9.2	8.4	7.4	7.2	6.6	6.9	6.4
90°	24.0	25.0	22.0	19.0	16.0	13.0	11.0	9.0	6.0	4.0	2.0
92.5°	115.8	153.5	168.9	126.8	83.8	57.7	42.9	34.5	26.8	18.4	12.4
95°	480.1	591.9	527.0	363.3	214.6	129.8	90.8	64.9	47.9	36.9	33.9
97.5°	981.4	917.3	671.6	398.7	231.0	149.9	107.8	82.2	67.5	58.9	57.9
100°	1141.9	945.3	638.8	376.3	228.6	158.7	119.8	95.8	81.9	74.9	73.9
102.5°	1149.9	893.4	590.9	357.1	231.8	169.1	133.4	111.8	98.6	92.4	90.6
105°	1089.0	802.5	532.0	343.4	240.6	186.7	155.7	136.8	124.8	118.8	115.8
107.5°	982.4	722.3	494.5	342.4	256.9	209.6	180.9	163.1	151.3	145.5	142.5
110°	915.3	676.8	480.1	346.4	270.5	225.6	197.6	180.7	169.7	164.7	161.7



TEST NUMBER: P332260

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	857.0	646.4	472.1	354.4	284.1	242.4	215.2	198.2	187.3	182.3	179.3
115°	786.6	613.9	469.1	367.3	306.4	268.5	241.6	224.6	214.6	208.6	204.6
117.5°	744.0	594.7	470.9	384.5	330.2	292.7	267.7	248.7	239.6	234.6	230.0
120°	721.7	585.9	474.1	397.3	345.4	309.4	284.5	265.5	255.5	250.5	247.5
122.5°	703.3	580.3	479.7	409.3	361.3	326.2	299.7	281.5	270.7	265.7	262.7
125°	679.8	573.0	488.1	428.2	384.3	349.4	322.4	303.4	292.5	286.5	284.5
127.5°	659.0	569.4	497.7	443.8	404.3	370.5	343.6	322.6	311.4	304.0	301.1
130°	647.8	567.0	504.1	454.2	416.2	383.3	356.3	335.4	323.4	314.4	311.4
132.5°	637.4	566.2	508.9	463.8	426.6	394.5	368.3	347.4	333.0	323.2	319.4
135°	623.9	565.0	516.1	476.1	442.2	411.2	384.3	363.3	348.4	337.4	333.4
137.5°	612.1	562.8	520.8	485.3	453.0	423.2	398.3	377.5	361.5	350.8	346.6
140°	604.9	562.0	524.0	490.1	460.2	431.2	406.3	386.3	370.3	360.3	355.4
142.5°	598.5	560.4	526.4	494.9	465.8	437.6	414.2	394.3	379.9	369.1	364.9
145°	589.9	558.0	528.0	500.1	473.1	447.2	424.2	407.3	392.3	383.3	380.3
147.5°	581.5	554.2	528.0	503.3	479.1	455.4	435.8	419.4	406.5	397.7	395.9
150°	575.9	551.0	528.0	504.1	483.1	460.2	442.2	428.2	415.2	407.3	406.3
152.5°	569.6	547.0	525.6	505.7	485.5	465.8	448.6	436.2	424.8	416.8	416.6
155°	560.0	540.0	523.0	506.1	490.1	473.1	459.2	448.2	438.2	432.2	432.2
157.5°	549.2	533.8	519.7	507.1	492.7	479.1	468.3	459.0	450.2	445.4	444.6
160°	542.0	529.0	518.1	507.1	495.1	483.1	473.1	466.1	458.2	454.2	454.2
162.5°	534.8	524.2	514.9	506.3	495.9	485.5	477.1	470.9	464.6	461.4	461.4
165°	525.0	517.1	510.1	504.1	497.1	489.1	482.1	478.1	473.1	471.1	472.1
167.5°	515.7	509.9	505.3	502.5	496.9	491.1	486.7	483.9	480.1	479.1	480.3
170°	510.1	505.1	502.1	500.1	496.1	491.1	489.1	487.1	484.1	483.1	485.1
172.5°	504.5	501.1	499.7	499.3	496.1	491.9	490.7	489.5	487.3	487.1	488.3
175°	498.1	496.1	496.1	497.1	495.1	493.1	492.1	492.1	490.1	491.1	492.1
177.5°	493.9	493.1	493.9	495.5	493.9	493.1	493.1	493.1	492.3	493.1	493.9
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P332260

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	547.2	549.3	551.9	555.8	558.8	561.4	561.9	562.7	564.6	567.7	570.1
5°	550.8	556.1	564.7	573.1	582.2	589.7	596.7	601.6	606.2	616.0	623.9
7.5°	549.6	561.6	575.1	590.1	605.4	620.1	633.8	646.1	658.3	672.6	688.8
10°	548.9	562.9	581.1	600.4	621.6	642.3	662.4	678.0	696.1	712.5	733.2
12.5°	545.4	565.5	587.2	611.9	638.0	661.9	688.3	709.8	730.6	754.2	778.3
15°	540.7	565.2	592.7	625.5	665.2	694.0	721.1	758.6	784.2	809.8	844.3
17.5°	532.3	562.2	596.5	639.2	672.2	711.1	751.7	781.4	815.9	852.0	883.2
20°	525.6	560.3	598.8	640.7	682.9	725.0	764.4	799.8	835.5	877.2	902.8
22.5°	518.9	553.2	593.2	637.7	683.0	727.5	772.0	813.6	853.7	895.8	928.5
25°	504.6	545.4	588.7	634.2	678.9	727.8	780.9	827.3	876.9	920.3	951.3
27.5°	490.2	527.6	570.7	616.8	666.5	724.3	786.8	839.5	889.2	920.3	930.0
30°	477.1	516.7	556.4	603.2	657.0	721.5	787.9	848.3	889.0	902.6	892.5
32.5°	463.9	499.8	539.0	587.0	644.1	714.6	789.4	843.1	867.6	857.3	816.5
35°	440.6	472.9	510.9	558.9	624.6	710.8	783.3	819.6	813.6	755.3	678.4
37.5°	415.6	442.0	477.1	527.3	604.4	695.7	756.8	762.2	709.7	620.3	531.5
40°	395.8	419.6	455.7	508.1	588.7	680.8	730.2	708.5	627.2	527.7	453.6
42.5°	376.6	396.7	431.5	488.0	573.8	660.4	690.5	643.3	549.5	455.4	388.0
45°	344.1	363.0	397.9	455.9	543.3	621.6	617.6	535.6	441.7	366.0	310.1
47.5°	313.3	329.8	362.6	421.8	507.5	563.3	526.3	439.0	359.4	298.6	258.7
50°	291.5	307.8	340.4	398.9	478.8	519.5	466.7	382.6	309.6	259.3	227.6
52.5°	270.6	286.5	316.3	373.3	444.1	468.5	411.7	333.7	272.9	229.5	202.3
55°	241.4	253.5	280.3	334.8	387.7	393.3	335.7	270.5	220.4	190.1	171.5
57.5°	211.6	222.0	248.5	291.9	329.0	326.1	271.6	215.1	181.4	158.9	145.4
60°	192.2	202.5	225.8	263.0	291.0	281.2	231.1	185.7	156.8	140.3	129.5
62.5°	174.1	182.1	204.0	231.2	251.3	240.2	197.6	160.0	137.0	123.1	114.6
65°	147.9	154.5	171.9	186.2	197.3	186.6	151.2	125.1	108.6	98.8	93.0
67.5°	123.1	127.2	138.2	143.4	151.3	139.5	113.7	96.2	86.8	78.6	74.5
70°	107.4	110.4	116.3	120.5	122.5	110.4	91.3	78.5	70.6	64.8	62.2
72.5°	91.7	94.4	95.6	99.0	97.9	86.6	73.4	63.2	57.5	53.6	50.3
75°	70.1	71.3	70.1	68.7	65.7	57.8	48.7	43.6	39.4	37.5	36.3
77.5°	51.1	50.7	49.2	47.0	41.8	36.8	31.9	30.2	28.4	27.4	27.0
80°	39.4	38.4	37.0	33.5	29.1	25.6	24.5	23.3	22.6	21.4	21.2
82.5°	29.3	28.7	26.4	23.5	20.4	18.7	17.8	17.3	16.6	16.0	16.0
85°	15.6	14.9	12.3	10.7	10.3	9.8	9.6	9.6	8.6	8.4	8.4
87.5°	5.8	5.1	5.5	5.4	5.8	6.0	6.8	7.0	7.4	7.4	7.2
90°	4.0	6.0	9.0	11.0	13.0	16.0	19.0	22.0	25.0	24.0	25.0
92.5°	18.4	26.8	34.5	42.9	57.7	83.8	126.8	168.9	153.5	115.8	84.0
95°	36.9	47.9	64.9	90.8	129.8	214.6	363.3	527.0	591.9	480.1	359.3
97.5°	58.9	67.5	82.2	107.8	149.9	231.0	398.7	671.6	917.3	981.4	895.8
100°	74.9	81.9	95.8	119.8	158.7	228.6	376.3	638.8	945.3	1141.9	1176.9
102.5°	92.4	98.6	111.8	133.4	169.1	231.8	357.1	590.9	893.4	1149.9	1270.3
105°	118.8	124.8	136.8	155.7	186.7	240.6	343.4	532.0	802.5	1089.0	1297.6
107.5°	145.5	151.3	163.1	180.9	209.6	256.9	342.4	494.5	722.3	982.4	1219.0
110°	164.7	169.7	180.7	197.6	225.6	270.5	346.4	480.1	676.8	915.3	1143.9



TEST NUMBER: P332260

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	182.3	187.3	198.2	215.2	242.4	284.1	354.4	472.1	646.4	857.0	1069.6
115°	208.6	214.6	224.6	241.6	268.5	306.4	367.3	469.1	613.9	786.6	971.2
117.5°	234.6	239.6	248.7	267.7	292.7	330.2	384.5	470.9	594.7	744.0	900.0
120°	250.5	255.5	265.5	284.5	309.4	345.4	397.3	474.1	585.9	721.7	862.4
122.5°	265.7	270.7	281.5	299.7	326.2	361.3	409.3	479.7	580.3	703.3	832.9
125°	286.5	292.5	303.4	322.4	349.4	384.3	428.2	488.1	573.0	679.8	793.6
127.5°	304.0	311.4	322.6	343.6	370.5	404.3	443.8	497.7	569.4	659.0	759.2
130°	314.4	323.4	335.4	356.3	383.3	416.2	454.2	504.1	567.0	647.8	737.7
132.5°	323.2	333.0	347.4	368.3	394.5	426.6	463.8	508.9	566.2	637.4	717.7
135°	337.4	348.4	363.3	384.3	411.2	442.2	476.1	516.1	565.0	623.9	690.7
137.5°	350.8	361.5	377.5	398.3	423.2	453.0	485.3	520.8	562.8	612.1	666.2
140°	360.3	370.3	386.3	406.3	431.2	460.2	490.1	524.0	562.0	604.9	651.8
142.5°	369.1	379.9	394.3	414.2	437.6	465.8	494.9	526.4	560.4	598.5	638.2
145°	383.3	392.3	407.3	424.2	447.2	473.1	500.1	528.0	558.0	589.9	621.9
147.5°	397.7	406.5	419.4	435.8	455.4	479.1	503.3	528.0	554.2	581.5	608.5
150°	407.3	415.2	428.2	442.2	460.2	483.1	504.1	528.0	551.0	575.9	598.9
152.5°	416.8	424.8	436.2	448.6	465.8	485.5	505.7	525.6	547.0	569.6	590.1
155°	432.2	438.2	448.2	459.2	473.1	490.1	506.1	523.0	540.0	560.0	576.9
157.5°	445.4	450.2	459.0	468.3	479.1	492.7	507.1	519.7	533.8	549.2	563.0
160°	454.2	458.2	466.1	473.1	483.1	495.1	507.1	518.1	529.0	542.0	555.0
162.5°	461.4	464.6	470.9	477.1	485.5	495.9	506.3	514.9	524.2	534.8	545.4
165°	471.1	473.1	478.1	482.1	489.1	497.1	504.1	510.1	517.1	525.0	533.0
167.5°	479.1	480.1	483.9	486.7	491.1	496.9	502.5	505.3	509.9	515.7	522.2
170°	483.1	484.1	487.1	489.1	491.1	496.1	500.1	502.1	505.1	510.1	515.1
172.5°	487.1	487.3	489.5	490.7	491.9	496.1	499.3	499.7	501.1	504.5	508.7
175°	491.1	490.1	492.1	492.1	493.1	495.1	497.1	496.1	496.1	498.1	500.1
177.5°	493.1	492.3	493.1	493.1	493.1	493.9	495.5	493.9	493.1	493.9	494.7
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P332260

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	574.1	574.1	574.8	577.6	578.0	580.4	579.7
5°	630.9	635.3	637.0	644.0	648.1	650.0	646.3
7.5°	700.4	712.9	718.8	726.2	732.6	734.6	729.5
10°	751.1	764.2	775.1	781.9	788.2	792.4	797.7
12.5°	800.1	816.2	826.6	836.1	842.6	847.9	848.8
15°	853.4	877.6	896.0	909.6	916.3	919.8	918.4
17.5°	907.1	929.6	942.7	956.5	965.8	966.3	966.6
20°	937.5	959.4	974.6	984.8	995.3	994.8	997.2
22.5°	957.8	975.1	986.7	994.1	997.7	995.9	996.4
25°	967.3	972.5	970.4	958.5	955.4	944.5	946.4
27.5°	918.3	894.1	869.0	836.8	811.3	791.0	792.0
30°	851.8	808.9	760.0	719.0	682.2	671.9	650.0
32.5°	758.8	694.5	637.2	598.9	567.4	558.8	539.7
35°	601.1	538.6	479.7	444.3	430.3	410.7	410.5
37.5°	467.2	412.2	381.1	354.5	340.6	328.7	327.6
40°	393.0	350.2	326.6	307.5	293.8	284.9	282.8
42.5°	341.2	306.6	284.5	272.7	262.1	257.5	254.1
45°	278.6	255.3	240.0	229.3	224.4	220.9	219.0
47.5°	233.1	217.5	207.0	199.8	195.9	192.2	193.2
50°	208.3	195.5	187.8	181.0	178.0	175.4	175.7
52.5°	188.3	176.8	170.6	165.7	162.0	160.1	159.3
55°	159.8	152.6	146.3	142.8	140.7	138.2	137.5
57.5°	136.3	130.7	125.6	121.7	121.1	118.7	119.0
60°	120.7	116.0	111.8	109.7	108.1	106.0	106.7
62.5°	107.8	103.9	100.1	98.4	96.7	95.2	95.5
65°	88.3	84.6	82.2	81.3	80.6	79.9	79.2
67.5°	70.4	68.1	66.6	64.6	63.2	63.0	62.3
70°	59.2	56.1	53.6	51.0	50.3	50.1	50.3
72.5°	47.4	45.5	44.8	43.6	43.4	42.8	43.2
75°	35.6	34.9	34.5	33.5	33.5	33.5	33.5
77.5°	26.3	25.9	25.6	25.4	25.2	24.8	24.8
80°	20.5	20.3	19.8	19.8	19.6	19.8	19.6
82.5°	15.5	15.4	15.0	15.0	14.7	14.6	14.7
85°	7.9	7.7	8.2	7.7	7.9	7.5	7.9
87.5°	7.4	7.6	7.8	7.6	7.7	8.2	7.7
90°	26.0	27.0	28.9	27.9	28.9	29.9	28.9
92.5°	66.7	58.9	53.7	51.9	48.9	49.9	48.1
95°	243.6	190.7	154.7	135.8	126.8	119.8	115.8
97.5°	717.5	588.7	469.3	395.7	350.8	323.8	315.2
100°	1096.0	979.2	837.5	736.7	663.8	624.9	625.9
102.5°	1267.7	1199.6	1109.8	1031.3	973.6	941.1	918.1
105°	1397.5	1416.4	1390.5	1344.5	1306.6	1274.7	1269.7
107.5°	1381.1	1468.5	1504.1	1504.9	1492.1	1481.3	1472.1
110°	1327.6	1453.3	1523.2	1551.2	1559.2	1557.2	1555.2



TEST NUMBER: P332260

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1257.3	1398.2	1488.1	1539.2	1563.9	1571.5	1571.9
115°	1144.9	1291.6	1400.4	1475.3	1519.2	1539.2	1544.2
117.5°	1049.9	1181.6	1292.0	1370.1	1420.4	1449.2	1455.9
120°	997.2	1117.0	1217.8	1296.6	1352.5	1376.5	1382.5
122.5°	954.9	1065.9	1159.5	1229.6	1279.9	1306.2	1313.8
125°	902.4	998.2	1078.0	1141.9	1185.8	1210.8	1217.8
127.5°	856.2	942.7	1015.3	1072.2	1109.8	1132.3	1138.7
130°	827.5	908.3	976.2	1029.1	1065.1	1086.0	1094.0
132.5°	800.3	875.6	940.3	990.0	1025.9	1044.5	1050.1
135°	761.6	826.5	883.4	932.3	962.2	980.2	987.2
137.5°	724.3	780.2	829.5	870.6	901.0	916.1	920.7
140°	702.7	750.6	793.6	831.5	859.4	875.4	874.4
142.5°	682.0	723.5	760.8	793.2	817.9	832.3	831.3
145°	654.8	686.7	715.7	740.6	761.6	769.6	771.6
147.5°	634.6	660.4	681.0	699.9	714.1	721.7	722.5
150°	621.9	642.8	661.8	676.8	687.7	693.7	693.7
152.5°	609.9	628.5	644.2	656.0	666.2	669.8	669.8
155°	592.9	607.9	619.9	628.9	636.8	638.8	639.8
157.5°	576.3	587.9	597.3	605.1	611.1	612.7	612.5
160°	566.0	575.9	582.9	589.9	595.9	595.9	594.9
162.5°	554.8	564.0	570.2	574.8	579.9	579.9	578.9
165°	539.0	546.0	551.0	555.0	559.0	558.0	558.0
167.5°	526.8	530.8	534.4	536.2	539.0	538.0	538.0
170°	518.1	522.0	524.0	525.0	527.0	526.0	526.0
172.5°	510.9	514.1	515.3	515.5	517.5	515.7	514.9
175°	501.1	503.1	503.1	503.1	504.1	503.1	502.1
177.5°	495.5	496.3	496.3	495.5	496.3	494.7	494.7
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1

(END OF REPORT)