

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332246

Luminaire Tested: **S123RDIP-S340D585U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332246
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D585U835-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3698.3 lumens
Efficiency: N/A
Efficacy: 144.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332246

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332246

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37					37			
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	39	39	38	32					32			
2	87	80	74	69	79	73	68	64	59	56	53	47	44	42	35	34	33	27					27			
3	80	71	64	58	72	64	59	54	53	48	45	42	39	36	32	30	28	24					24			
4	73	63	55	50	66	57	51	46	47	42	39	37	34	31	28	26	25	21					21			
5	67	56	48	43	61	51	45	40	42	37	33	34	30	27	26	24	22	18					18			
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16					16			
7	57	45	38	33	52	42	35	30	35	30	26	28	24	21	22	19	17	14					14			
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	17	15	13					13			
9	49	38	30	26	45	35	28	24	29	24	21	23	20	17	18	16	14	12					12			
10	46	34	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13	11					11			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5858	5858	5858	5858
5°	6983	5883	5181	5883
10°	8719	5850	4680	5850
15°	10234	5789	4268	5789
20°	11423	5700	3918	5700
25°	11240	5606	3702	5606
30°	8079	5520	3480	5520
35°	5394	5406	3336	5406
40°	3974	5271	3188	5271
45°	3334	5033	3043	5033
50°	2942	4721	2840	4721
55°	2580	4363	2562	4363
60°	2297	4021	2347	4021
65°	2017	3655	2183	3655
70°	1583	3330	1995	3330
75°	1393	2907	1822	2907
80°	1215	2467	1791	2467
85°	976	1988	1902	1988



TEST NUMBER: P332246

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.5	1.4
10°-20°	167.2	4.5
20°-30°	262.7	7.1
30°-40°	274.1	7.4
40°-50°	234.5	6.3
50°-60°	178.8	4.8
60°-70°	114.6	3.1
70°-80°	55.1	1.5
80°-90°	16.7	0.5
90°-100°	27.9	0.8
100°-110°	133.0	3.6
110°-120°	319.5	8.6
120°-130°	406.9	11.0
130°-140°	434.7	11.8
140°-150°	406.5	11.0
150°-160°	327.9	8.9
160°-170°	211.6	5.7
170°-180°	72.9	2.0
0°-30°	483.4	13.1
0°-40°	757.5	20.5
0°-60°	1170.8	31.7
0°-90°	1357.2	36.7
90°-120°	480.5	13.0
90°-150°	1728.6	46.7
90°-180°	2341.0	63.3
0°-180°	3698.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	544	544	544	544	544	
5°	646	544	480	544	646	67
15°	918	520	383	520	918	260
25°	946	472	312	472	946	407
35°	410	411	254	411	410	269
45°	219	331	200	331	219	172
55°	138	232	136	232	138	124
65°	79	144	86	144	79	78
75°	34	70	44	70	34	36
85°	8	16	15	16	8	10
90°	17	1	17	1	17	8
95°	22	35	22	35	22	18
105°	25	170	25	170	25	57
115°	335	319	335	319	335	310
125°	459	449	459	449	459	410
135°	565	560	565	560	565	436
145°	652	646	652	646	652	407
155°	710	711	710	711	710	327
165°	748	750	748	750	748	211
175°	765	768	765	768	765	73
180°	768	768	768	768	768	



TEST NUMBER: P332246

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	579.7	580.4	578.0	577.6	574.8	574.1	574.1	570.1	567.7	564.6	562.7
5°	646.3	650.0	648.1	644.0	637.0	635.3	630.9	623.9	616.0	606.2	601.6
7.5°	729.5	734.6	732.6	726.2	718.8	712.9	700.4	688.8	672.6	658.3	646.1
10°	797.7	792.4	788.2	781.9	775.1	764.2	751.1	733.2	712.5	696.1	678.0
12.5°	848.8	847.9	842.6	836.1	826.6	816.2	800.1	778.3	754.2	730.6	709.8
15°	918.4	919.8	916.3	909.6	896.0	877.6	853.4	844.3	809.8	784.2	758.6
17.5°	966.6	966.3	965.8	956.5	942.7	929.6	907.1	883.2	852.0	815.9	781.4
20°	997.2	994.8	995.3	984.8	974.6	959.4	937.5	902.8	877.2	835.5	799.8
22.5°	996.4	995.9	997.7	994.1	986.7	975.1	957.8	928.5	895.8	853.7	813.6
25°	946.4	944.5	955.4	958.5	970.4	972.5	967.3	951.3	920.3	876.9	827.3
27.5°	792.0	791.0	811.3	836.8	869.0	894.1	918.3	930.0	920.3	889.2	839.5
30°	650.0	671.9	682.2	719.0	760.0	808.9	851.8	892.5	902.6	889.0	848.3
32.5°	539.7	558.8	567.4	598.9	637.2	694.5	758.8	816.5	857.3	867.6	843.1
35°	410.5	410.7	430.3	444.3	479.7	538.6	601.1	678.4	755.3	813.6	819.6
37.5°	327.6	328.7	340.6	354.5	381.1	412.2	467.2	531.5	620.3	709.7	762.2
40°	282.8	284.9	293.8	307.5	326.6	350.2	393.0	453.6	527.7	627.2	708.5
42.5°	254.1	257.5	262.1	272.7	284.5	306.6	341.2	388.0	455.4	549.5	643.3
45°	219.0	220.9	224.4	229.3	240.0	255.3	278.6	310.1	366.0	441.7	535.6
47.5°	193.2	192.2	195.9	199.8	207.0	217.5	233.1	258.7	298.6	359.4	439.0
50°	175.7	175.4	178.0	181.0	187.8	195.5	208.3	227.6	259.3	309.6	382.6
52.5°	159.3	160.1	162.0	165.7	170.6	176.8	188.3	202.3	229.5	272.9	333.7
55°	137.5	138.2	140.7	142.8	146.3	152.6	159.8	171.5	190.1	220.4	270.5
57.5°	119.0	118.7	121.1	121.7	125.6	130.7	136.3	145.4	158.9	181.4	215.1
60°	106.7	106.0	108.1	109.7	111.8	116.0	120.7	129.5	140.3	156.8	185.7
62.5°	95.5	95.2	96.7	98.4	100.1	103.9	107.8	114.6	123.1	137.0	160.0
65°	79.2	79.9	80.6	81.3	82.2	84.6	88.3	93.0	98.8	108.6	125.1
67.5°	62.3	63.0	63.2	64.6	66.6	68.1	70.4	74.5	78.6	86.8	96.2
70°	50.3	50.1	50.3	51.0	53.6	56.1	59.2	62.2	64.8	70.6	78.5
72.5°	43.2	42.8	43.4	43.6	44.8	45.5	47.4	50.3	53.6	57.5	63.2
75°	33.5	33.5	33.5	33.5	34.5	34.9	35.6	36.3	37.5	39.4	43.6
77.5°	24.8	24.8	25.2	25.4	25.6	25.9	26.3	27.0	27.4	28.4	30.2
80°	19.6	19.8	19.6	19.8	19.8	20.3	20.5	21.2	21.4	22.6	23.3
82.5°	14.7	14.6	14.7	15.0	15.0	15.4	15.5	16.0	16.0	16.6	17.3
85°	7.9	7.5	7.9	7.7	8.2	7.7	7.9	8.4	8.4	8.6	9.6
87.5°	5.3	5.6	5.2	5.3	5.3	5.4	5.3	5.2	5.4	5.2	5.0
90°	17.1	16.9	16.6	16.4	16.1	15.7	15.2	14.7	14.2	13.7	12.0
92.5°	18.9	18.8	18.6	18.5	18.3	17.8	17.0	16.2	15.4	14.6	13.4
95°	21.7	21.7	21.7	21.7	21.7	21.2	20.3	19.5	18.6	17.7	16.3
97.5°	23.5	23.4	23.2	23.1	23.0	22.4	21.4	20.4	19.4	18.4	27.5
100°	24.0	23.8	23.7	23.6	23.4	22.9	21.9	20.8	19.8	18.8	38.6
102.5°	24.4	24.2	24.0	23.7	23.5	25.0	28.1	31.2	34.4	37.5	59.1
105°	25.1	24.8	24.6	24.3	24.1	35.2	57.6	80.0	102.5	124.9	136.3
107.5°	78.8	95.7	112.6	129.5	146.5	163.1	179.6	196.0	212.5	228.9	227.1
110°	156.8	175.0	193.1	211.2	229.3	240.5	244.7	248.9	253.0	257.2	255.8



TEST NUMBER: P332246

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	269.1	272.9	276.7	280.6	284.4	286.3	286.2	286.1	286.1	286.0	284.6
115°	335.4	334.9	334.4	333.8	333.3	332.5	331.2	329.9	328.7	327.4	326.2
117.5°	372.6	372.5	372.4	372.3	372.2	371.6	370.6	369.6	368.6	367.5	367.0
120°	398.1	398.1	398.1	398.1	398.1	397.6	396.6	395.6	394.6	393.5	393.2
122.5°	423.2	423.1	423.0	422.9	422.8	422.4	421.7	421.0	420.3	419.6	419.1
125°	458.6	458.3	458.1	457.8	457.6	457.3	457.0	456.8	456.5	456.3	455.8
127.5°	492.6	492.8	493.1	493.3	493.6	493.5	493.1	492.7	492.3	491.9	491.3
130°	514.5	514.7	515.0	515.2	515.5	515.3	514.8	514.3	513.8	513.3	512.8
132.5°	534.5	534.9	535.2	535.6	536.0	535.9	535.4	534.9	534.4	533.9	533.4
135°	565.2	565.6	566.0	566.4	566.7	566.7	566.4	566.0	565.6	565.2	564.7
137.5°	594.1	594.3	594.6	594.8	595.1	594.9	594.3	593.7	593.1	592.5	592.2
140°	611.4	611.7	611.9	612.2	612.4	612.3	611.8	611.3	610.8	610.3	609.9
142.5°	627.4	627.7	628.1	628.5	628.8	628.8	628.4	628.0	627.6	627.2	626.8
145°	651.9	651.9	651.9	651.9	651.9	651.8	651.5	651.3	651.0	650.8	650.5
147.5°	670.2	670.8	671.3	671.9	672.5	672.7	672.4	672.2	671.9	671.7	671.4
150°	683.9	684.2	684.6	685.0	685.4	685.4	685.2	684.9	684.7	684.4	684.2
152.5°	694.8	695.4	696.0	696.6	697.1	697.2	696.7	696.3	695.8	695.4	695.2
155°	710.1	710.9	711.6	712.4	713.1	713.2	712.6	711.9	711.3	710.7	710.5
157.5°	723.0	724.0	725.0	725.9	726.9	727.1	726.3	725.5	724.8	724.0	724.1
160°	731.2	732.1	733.0	733.9	734.7	734.8	734.0	733.3	732.5	731.8	731.9
162.5°	739.0	739.7	740.5	741.3	742.1	742.1	741.2	740.3	739.5	738.6	738.7
165°	748.3	749.2	750.1	751.0	751.9	751.8	750.8	749.8	748.8	747.7	747.9
167.5°	755.0	756.1	757.1	758.1	759.1	759.1	758.1	757.1	756.1	755.0	755.0
170°	759.1	760.2	761.2	762.2	763.2	763.2	762.2	761.2	760.2	759.1	759.1
172.5°	761.4	762.5	763.7	764.8	765.9	765.9	764.9	763.9	762.9	761.9	761.8
175°	764.8	765.9	766.9	767.9	768.9	769.0	768.1	767.2	766.3	765.4	765.3
177.5°	765.9	766.9	767.9	768.9	769.9	770.0	769.2	768.4	767.6	766.8	766.7
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P332246

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	561.9	561.4	558.8	555.8	551.9	549.3	547.2	546.1	542.7	538.6	535.9
5°	596.7	589.7	582.2	573.1	564.7	556.1	550.8	544.5	536.8	528.2	522.1
7.5°	633.8	620.1	605.4	590.1	575.1	561.6	549.6	539.4	527.2	514.8	506.2
10°	662.4	642.3	621.6	600.4	581.1	562.9	548.9	535.2	520.5	506.3	495.5
12.5°	688.3	661.9	638.0	611.9	587.2	565.5	545.4	529.2	511.5	496.4	484.2
15°	721.1	694.0	665.2	625.5	592.7	565.2	540.7	519.5	498.1	479.5	467.6
17.5°	751.7	711.1	672.2	639.2	596.5	562.2	532.3	507.0	483.4	463.7	449.0
20°	764.4	725.0	682.9	640.7	598.8	560.3	525.6	497.6	473.2	450.8	437.3
22.5°	772.0	727.5	683.0	637.7	593.2	553.2	518.9	488.1	461.6	440.4	423.7
25°	780.9	727.8	678.9	634.2	588.7	545.4	504.6	472.0	443.4	420.8	403.1
27.5°	786.8	724.3	666.5	616.8	570.7	527.6	490.2	455.6	426.5	402.6	383.6
30°	787.9	721.5	657.0	603.2	556.4	516.7	477.1	444.1	413.3	387.9	370.2
32.5°	789.4	714.6	644.1	587.0	539.0	499.8	463.9	432.3	400.8	375.8	357.7
35°	783.3	710.8	624.6	558.9	510.9	472.9	440.6	411.4	380.5	356.2	337.8
37.5°	756.8	695.7	604.4	527.3	477.1	442.0	415.6	390.2	361.8	335.6	318.3
40°	730.2	680.8	588.7	508.1	455.7	419.6	395.8	375.1	347.6	323.1	304.5
42.5°	690.5	660.4	573.8	488.0	431.5	396.7	376.6	357.2	333.1	308.2	290.7
45°	617.6	621.6	543.3	455.9	397.9	363.0	344.1	330.6	309.2	288.7	270.7
47.5°	526.3	563.3	507.5	421.8	362.6	329.8	313.3	301.5	287.0	266.9	250.5
50°	466.7	519.5	478.8	398.9	340.4	307.8	291.5	281.9	269.3	253.5	237.9
52.5°	411.7	468.5	444.1	373.3	316.3	286.5	270.6	262.7	252.7	237.8	223.7
55°	335.7	393.3	387.7	334.8	280.3	253.5	241.4	232.5	225.8	214.6	203.4
57.5°	271.6	326.1	329.0	291.9	248.5	222.0	211.6	204.9	200.5	192.1	181.7
60°	231.1	281.2	291.0	263.0	225.8	202.5	192.2	186.8	183.4	176.6	168.7
62.5°	197.6	240.2	251.3	231.2	204.0	182.1	174.1	169.0	166.6	160.8	153.8
65°	151.2	186.6	197.3	186.2	171.9	154.5	147.9	143.5	141.4	138.2	133.0
67.5°	113.7	139.5	151.3	143.4	138.2	127.2	123.1	120.7	118.8	116.6	112.3
70°	91.3	110.4	122.5	120.5	116.3	110.4	107.4	105.8	103.9	102.0	98.3
72.5°	73.4	86.6	97.9	99.0	95.6	94.4	91.7	91.0	89.9	87.7	85.6
75°	48.7	57.8	65.7	68.7	70.1	71.3	70.1	69.9	69.7	67.8	66.6
77.5°	31.9	36.8	41.8	47.0	49.2	50.7	51.1	52.0	51.3	50.4	49.8
80°	24.5	25.6	29.1	33.5	37.0	38.4	39.4	39.8	39.6	39.4	38.4
82.5°	17.8	18.7	20.4	23.5	26.4	28.7	29.3	29.2	29.7	29.9	29.1
85°	9.6	9.8	10.3	10.7	12.3	14.9	15.6	16.1	16.5	16.5	15.1
87.5°	5.1	4.5	4.6	4.3	4.6	4.5	5.4	6.1	6.5	6.0	6.3
90°	10.4	8.7	7.1	5.6	4.4	3.1	1.8	0.6	1.8	3.1	4.4
92.5°	12.1	10.9	9.6	9.2	9.5	9.9	10.3	10.6	10.3	9.9	9.5
95°	14.9	13.5	12.1	14.0	19.2	24.4	29.6	34.8	29.6	24.4	19.2
97.5°	36.6	45.7	54.9	60.6	62.9	65.3	67.6	69.9	67.6	65.3	62.9
100°	58.4	78.1	97.9	106.5	104.0	101.5	98.9	96.4	98.9	101.5	104.0
102.5°	80.7	102.3	123.9	133.8	132.0	130.2	128.3	126.5	128.3	130.2	132.0
105°	147.7	159.1	170.5	175.5	174.1	172.8	171.4	170.0	171.4	172.8	174.1
107.5°	225.3	223.5	221.7	220.3	219.2	218.1	216.9	215.8	216.9	218.1	219.2
110°	254.4	253.0	251.7	250.4	249.4	248.4	247.4	246.4	247.4	248.4	249.4



TEST NUMBER: P332246

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	283.2	281.8	280.4	279.2	278.3	277.4	276.5	275.6	276.5	277.4	278.3
115°	325.1	324.0	322.8	321.9	321.1	320.3	319.6	318.8	319.6	320.3	321.1
117.5°	366.4	365.8	365.2	364.4	363.5	362.6	361.6	360.7	361.6	362.6	363.5
120°	392.8	392.4	392.0	391.3	390.1	389.0	387.8	386.7	387.8	389.0	390.1
122.5°	418.6	418.1	417.6	416.9	416.0	415.0	414.1	413.2	414.1	415.0	416.0
125°	455.3	454.8	454.3	453.5	452.5	451.5	450.5	449.4	450.5	451.5	452.5
127.5°	490.7	490.0	489.4	488.6	487.6	486.6	485.6	484.6	485.6	486.6	487.6
130°	512.3	511.8	511.3	510.5	509.5	508.5	507.5	506.5	507.5	508.5	509.5
132.5°	533.0	532.6	532.2	531.5	530.5	529.5	528.5	527.5	528.5	529.5	530.5
135°	564.2	563.7	563.2	562.6	561.8	561.0	560.3	559.5	560.3	561.0	561.8
137.5°	591.9	591.6	591.4	590.7	589.8	588.8	587.9	586.9	587.9	588.8	589.8
140°	609.5	609.1	608.8	608.2	607.4	606.7	605.9	605.1	605.9	606.7	607.4
142.5°	626.4	626.0	625.6	625.1	624.3	623.6	622.8	622.0	622.8	623.6	624.3
145°	650.3	650.0	649.8	649.2	648.3	647.4	646.5	645.6	646.5	647.4	648.3
147.5°	671.1	670.9	670.6	670.2	669.6	669.1	668.5	667.9	668.5	669.1	669.6
150°	683.9	683.7	683.4	683.1	682.7	682.3	682.0	681.6	682.0	682.3	682.7
152.5°	695.1	694.9	694.8	694.6	694.4	694.2	694.1	693.9	694.1	694.2	694.4
155°	710.4	710.3	710.2	710.2	710.5	710.7	711.0	711.2	711.0	710.7	710.5
157.5°	724.3	724.4	724.5	724.6	724.6	724.6	724.7	724.7	724.7	724.6	724.6
160°	732.0	732.1	732.3	732.4	732.5	732.7	732.8	732.9	732.8	732.7	732.5
162.5°	738.9	739.0	739.1	739.3	739.7	740.0	740.3	740.7	740.3	740.0	739.7
165°	748.0	748.1	748.2	748.5	748.9	749.3	749.6	750.0	749.6	749.3	748.9
167.5°	755.0	755.0	755.0	755.3	755.8	756.3	756.8	757.3	756.8	756.3	755.8
170°	759.1	759.1	759.1	759.4	759.9	760.4	760.9	761.4	760.9	760.4	759.9
172.5°	761.7	761.6	761.5	761.7	762.3	762.9	763.6	764.2	763.6	762.9	762.3
175°	765.2	765.0	764.9	765.2	765.8	766.4	767.1	767.7	767.1	766.4	765.8
177.5°	766.6	766.5	766.4	766.6	767.1	767.6	768.1	768.6	768.1	767.6	767.1
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P332246

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	534.9	532.5	530.8	527.1	524.7	522.1	519.5	521.1	520.9	520.8	520.8
5°	517.0	511.6	506.7	500.4	496.5	491.6	487.9	487.4	488.3	485.1	483.2
7.5°	499.2	491.9	484.9	478.0	470.6	464.7	461.1	459.3	457.0	455.0	452.9
10°	486.7	478.1	471.3	462.7	454.8	447.8	443.4	440.3	438.7	437.1	434.0
12.5°	473.8	465.4	456.8	447.0	439.5	431.4	428.1	424.7	421.6	419.7	415.6
15°	455.0	444.1	435.0	424.7	416.3	408.4	403.8	397.0	396.1	393.7	389.5
17.5°	436.1	424.3	411.7	404.1	394.7	386.4	379.3	377.1	370.4	367.9	364.2
20°	421.2	410.3	400.7	390.7	377.0	369.3	363.7	360.7	355.3	352.0	349.7
22.5°	408.4	397.2	386.2	374.5	363.2	354.5	350.4	345.7	342.8	338.2	335.7
25°	390.0	377.9	364.6	352.0	343.9	337.4	330.8	326.6	322.4	320.3	315.7
27.5°	368.7	356.0	343.6	334.0	324.0	317.6	311.7	308.0	302.9	299.4	296.8
30°	356.9	342.0	331.3	322.7	309.9	303.8	299.4	294.7	291.0	287.3	284.7
32.5°	343.3	329.7	319.6	308.9	299.1	292.4	286.7	282.6	279.4	275.9	273.3
35°	322.0	310.6	300.1	289.4	282.1	275.4	268.6	265.1	262.1	258.8	256.5
37.5°	302.7	292.0	282.0	271.9	262.9	257.4	252.0	249.3	245.2	243.0	240.7
40°	290.8	280.3	269.6	259.8	250.5	246.3	241.4	237.4	233.7	232.0	229.5
42.5°	277.7	267.2	258.2	247.7	240.0	234.3	229.8	225.5	222.7	220.3	218.9
45°	258.4	249.1	240.2	229.7	222.5	217.6	212.5	208.5	206.0	204.3	201.8
47.5°	239.6	230.3	221.3	212.2	205.2	199.6	194.4	191.7	188.3	186.3	184.6
50°	226.0	217.6	208.1	199.7	192.7	187.1	182.9	179.4	176.4	173.8	172.6
52.5°	213.5	204.6	196.3	188.5	181.1	174.8	171.0	167.3	165.0	162.1	160.7
55°	192.9	184.3	177.3	169.6	162.4	157.0	152.4	149.1	146.8	143.5	141.7
57.5°	173.6	165.8	157.5	150.8	143.4	138.9	135.0	130.6	127.7	125.2	123.3
60°	160.5	151.7	144.4	138.2	131.6	125.8	122.3	118.8	115.8	113.2	111.6
62.5°	146.9	139.2	132.3	125.5	119.5	114.4	110.4	107.5	104.8	103.2	101.5
65°	126.0	120.0	113.0	107.4	101.8	98.1	94.8	92.3	90.4	89.2	87.8
67.5°	106.8	101.0	94.9	89.4	85.6	82.8	80.7	78.5	77.5	76.0	75.1
70°	94.4	88.3	82.9	78.7	75.0	72.9	71.5	69.9	69.0	67.1	66.2
72.5°	80.8	76.4	72.5	69.1	66.1	64.2	62.4	60.4	58.9	56.8	55.9
75°	63.6	59.6	56.6	54.3	52.4	49.9	47.3	45.2	44.5	43.8	43.6
77.5°	47.1	44.6	42.4	40.4	38.1	36.3	35.7	35.2	35.1	34.7	34.7
80°	37.0	34.7	33.1	30.8	29.4	29.4	29.4	28.9	29.1	29.1	29.1
82.5°	27.5	25.4	24.5	23.7	23.4	23.6	23.6	23.7	23.5	23.9	23.7
85°	14.2	14.4	14.9	14.7	14.9	14.9	15.4	15.1	15.4	14.9	15.4
87.5°	6.3	7.2	7.7	8.2	8.7	8.9	9.2	9.3	9.6	9.7	9.7
90°	5.6	7.1	8.7	10.4	12.0	13.7	14.2	14.7	15.2	15.7	16.1
92.5°	9.2	9.6	10.9	12.1	13.4	14.6	15.4	16.2	17.0	17.8	18.3
95°	14.0	12.1	13.5	14.9	16.3	17.7	18.6	19.5	20.3	21.2	21.7
97.5°	60.6	54.9	45.7	36.6	27.5	18.4	19.4	20.4	21.4	22.4	23.0
100°	106.5	97.9	78.1	58.4	38.6	18.8	19.8	20.8	21.9	22.9	23.4
102.5°	133.8	123.9	102.3	80.7	59.1	37.5	34.4	31.2	28.1	25.0	23.5
105°	175.5	170.5	159.1	147.7	136.3	124.9	102.5	80.0	57.6	35.2	24.1
107.5°	220.3	221.7	223.5	225.3	227.1	228.9	212.5	196.0	179.6	163.1	146.5
110°	250.4	251.7	253.0	254.4	255.8	257.2	253.0	248.9	244.7	240.5	229.3



TEST NUMBER: P332246

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	279.2	280.4	281.8	283.2	284.6	286.0	286.1	286.1	286.2	286.3	284.4
115°	321.9	322.8	324.0	325.1	326.2	327.4	328.7	329.9	331.2	332.5	333.3
117.5°	364.4	365.2	365.8	366.4	367.0	367.5	368.6	369.6	370.6	371.6	372.2
120°	391.3	392.0	392.4	392.8	393.2	393.5	394.6	395.6	396.6	397.6	398.1
122.5°	416.9	417.6	418.1	418.6	419.1	419.6	420.3	421.0	421.7	422.4	422.8
125°	453.5	454.3	454.8	455.3	455.8	456.3	456.5	456.8	457.0	457.3	457.6
127.5°	488.6	489.4	490.0	490.7	491.3	491.9	492.3	492.7	493.1	493.5	493.6
130°	510.5	511.3	511.8	512.3	512.8	513.3	513.8	514.3	514.8	515.3	515.5
132.5°	531.5	532.2	532.6	533.0	533.4	533.9	534.4	534.9	535.4	535.9	536.0
135°	562.6	563.2	563.7	564.2	564.7	565.2	565.6	566.0	566.4	566.7	566.7
137.5°	590.7	591.4	591.6	591.9	592.2	592.5	593.1	593.7	594.3	594.9	595.1
140°	608.2	608.8	609.1	609.5	609.9	610.3	610.8	611.3	611.8	612.3	612.4
142.5°	625.1	625.6	626.0	626.4	626.8	627.2	627.6	628.0	628.4	628.8	628.8
145°	649.2	649.8	650.0	650.3	650.5	650.8	651.0	651.3	651.5	651.8	651.9
147.5°	670.2	670.6	670.9	671.1	671.4	671.7	671.9	672.2	672.4	672.7	672.5
150°	683.1	683.4	683.7	683.9	684.2	684.4	684.7	684.9	685.2	685.4	685.4
152.5°	694.6	694.8	694.9	695.1	695.2	695.4	695.8	696.3	696.7	697.2	697.1
155°	710.2	710.2	710.3	710.4	710.5	710.7	711.3	711.9	712.6	713.2	713.1
157.5°	724.6	724.5	724.4	724.3	724.1	724.0	724.8	725.5	726.3	727.1	726.9
160°	732.4	732.3	732.1	732.0	731.9	731.8	732.5	733.3	734.0	734.8	734.7
162.5°	739.3	739.1	739.0	738.9	738.7	738.6	739.5	740.3	741.2	742.1	742.1
165°	748.5	748.2	748.1	748.0	747.9	747.7	748.8	749.8	750.8	751.8	751.9
167.5°	755.3	755.0	755.0	755.0	755.0	755.0	756.1	757.1	758.1	759.1	759.1
170°	759.4	759.1	759.1	759.1	759.1	759.1	760.2	761.2	762.2	763.2	763.2
172.5°	761.7	761.5	761.6	761.7	761.8	761.9	762.9	763.9	764.9	765.9	765.9
175°	765.2	764.9	765.0	765.2	765.3	765.4	766.3	767.2	768.1	769.0	768.9
177.5°	766.6	766.4	766.5	766.6	766.7	766.8	767.6	768.4	769.2	770.0	769.9
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P332246

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	518.5	518.3	518.5	517.8	518.5	518.3	518.5	520.8	520.8	520.9	521.1
5°	482.5	482.3	481.6	479.5	481.6	482.3	482.5	483.2	485.1	488.3	487.4
7.5°	451.0	450.7	448.7	448.7	448.7	450.7	451.0	452.9	455.0	457.0	459.3
10°	432.4	432.6	429.8	428.2	429.8	432.6	432.4	434.0	437.1	438.7	440.3
12.5°	414.3	413.3	411.0	409.2	411.0	413.3	414.3	415.6	419.7	421.6	424.7
15°	390.5	388.1	382.6	383.0	382.6	388.1	390.5	389.5	393.7	396.1	397.0
17.5°	362.4	360.7	360.6	357.3	360.6	360.7	362.4	364.2	367.9	370.4	377.1
20°	346.0	344.8	345.3	342.0	345.3	344.8	346.0	349.7	352.0	355.3	360.7
22.5°	333.1	331.9	330.0	329.0	330.0	331.9	333.1	335.7	338.2	342.8	345.7
25°	314.3	312.4	310.6	311.7	310.6	312.4	314.3	315.7	320.3	322.4	326.6
27.5°	295.5	294.1	292.2	292.0	292.2	294.1	295.5	296.8	299.4	302.9	308.0
30°	283.5	282.1	281.2	280.0	281.2	282.1	283.5	284.7	287.3	291.0	294.7
32.5°	271.4	271.1	269.5	269.2	269.5	271.1	271.4	273.3	275.9	279.4	282.6
35°	255.6	254.2	253.7	253.9	253.7	254.2	255.6	256.5	258.8	262.1	265.1
37.5°	240.5	238.7	237.8	237.0	237.8	238.7	240.5	240.7	243.0	245.2	249.3
40°	229.7	227.9	227.4	226.9	227.4	227.9	229.7	229.5	232.0	233.7	237.4
42.5°	217.6	216.9	216.6	215.7	216.6	216.9	217.6	218.9	220.3	222.7	225.5
45°	201.1	200.8	199.4	199.9	199.4	200.8	201.1	201.8	204.3	206.0	208.5
47.5°	183.6	182.6	181.6	182.3	181.6	182.6	183.6	184.6	186.3	188.3	191.7
50°	171.7	171.2	169.1	169.6	169.1	171.2	171.7	172.6	173.8	176.4	179.4
52.5°	159.8	158.0	157.2	156.9	157.2	158.0	159.8	160.7	162.1	165.0	167.3
55°	140.0	137.9	137.0	136.5	137.0	137.9	140.0	141.7	143.5	146.8	149.1
57.5°	120.6	120.1	119.3	119.8	119.3	120.1	120.6	123.3	125.2	127.7	130.6
60°	109.3	109.3	109.3	109.0	109.3	109.3	109.3	111.6	113.2	115.8	118.8
62.5°	100.5	99.9	99.8	100.1	99.8	99.9	100.5	101.5	103.2	104.8	107.5
65°	87.1	86.9	86.0	85.7	86.0	86.9	87.1	87.8	89.2	90.4	92.3
67.5°	74.5	73.7	73.4	73.1	73.4	73.7	74.5	75.1	76.0	77.5	78.5
70°	65.0	64.5	63.1	63.4	63.1	64.5	65.0	66.2	67.1	69.0	69.9
72.5°	54.8	54.3	54.0	53.7	54.0	54.3	54.8	55.9	56.8	58.9	60.4
75°	43.3	43.1	42.9	43.8	42.9	43.1	43.3	43.6	43.8	44.5	45.2
77.5°	34.7	34.7	34.9	34.5	34.9	34.7	34.7	34.7	34.7	35.1	35.2
80°	29.1	29.1	28.9	28.9	28.9	29.1	29.1	29.1	29.1	29.1	28.9
82.5°	23.3	23.5	23.7	23.3	23.7	23.5	23.3	23.7	23.9	23.5	23.7
85°	15.4	15.1	15.6	15.4	15.6	15.1	15.4	15.4	14.9	15.4	15.1
87.5°	10.2	9.8	9.9	10.1	9.9	9.8	10.2	9.7	9.7	9.6	9.3
90°	16.4	16.6	16.9	17.1	16.9	16.6	16.4	16.1	15.7	15.2	14.7
92.5°	18.5	18.6	18.8	18.9	18.8	18.6	18.5	18.3	17.8	17.0	16.2
95°	21.7	21.7	21.7	21.7	21.7	21.7	21.7	21.7	21.2	20.3	19.5
97.5°	23.1	23.2	23.4	23.5	23.4	23.2	23.1	23.0	22.4	21.4	20.4
100°	23.6	23.7	23.8	24.0	23.8	23.7	23.6	23.4	22.9	21.9	20.8
102.5°	23.7	24.0	24.2	24.4	24.2	24.0	23.7	23.5	25.0	28.1	31.2
105°	24.3	24.6	24.8	25.1	24.8	24.6	24.3	24.1	35.2	57.6	80.0
107.5°	129.5	112.6	95.7	78.8	95.7	112.6	129.5	146.5	163.1	179.6	196.0
110°	211.2	193.1	175.0	156.8	175.0	193.1	211.2	229.3	240.5	244.7	248.9



TEST NUMBER: P332246

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	280.6	276.7	272.9	269.1	272.9	276.7	280.6	284.4	286.3	286.2	286.1
115°	333.8	334.4	334.9	335.4	334.9	334.4	333.8	333.3	332.5	331.2	329.9
117.5°	372.3	372.4	372.5	372.6	372.5	372.4	372.3	372.2	371.6	370.6	369.6
120°	398.1	398.1	398.1	398.1	398.1	398.1	398.1	398.1	397.6	396.6	395.6
122.5°	422.9	423.0	423.1	423.2	423.1	423.0	422.9	422.8	422.4	421.7	421.0
125°	457.8	458.1	458.3	458.6	458.3	458.1	457.8	457.6	457.3	457.0	456.8
127.5°	493.3	493.1	492.8	492.6	492.8	493.1	493.3	493.6	493.5	493.1	492.7
130°	515.2	515.0	514.7	514.5	514.7	515.0	515.2	515.5	515.3	514.8	514.3
132.5°	535.6	535.2	534.9	534.5	534.9	535.2	535.6	536.0	535.9	535.4	534.9
135°	566.4	566.0	565.6	565.2	565.6	566.0	566.4	566.7	566.7	566.4	566.0
137.5°	594.8	594.6	594.3	594.1	594.3	594.6	594.8	595.1	594.9	594.3	593.7
140°	612.2	611.9	611.7	611.4	611.7	611.9	612.2	612.4	612.3	611.8	611.3
142.5°	628.5	628.1	627.7	627.4	627.7	628.1	628.5	628.8	628.8	628.4	628.0
145°	651.9	651.9	651.9	651.9	651.9	651.9	651.9	651.9	651.8	651.5	651.3
147.5°	671.9	671.3	670.8	670.2	670.8	671.3	671.9	672.5	672.7	672.4	672.2
150°	685.0	684.6	684.2	683.9	684.2	684.6	685.0	685.4	685.4	685.2	684.9
152.5°	696.6	696.0	695.4	694.8	695.4	696.0	696.6	697.1	697.2	696.7	696.3
155°	712.4	711.6	710.9	710.1	710.9	711.6	712.4	713.1	713.2	712.6	711.9
157.5°	725.9	725.0	724.0	723.0	724.0	725.0	725.9	726.9	727.1	726.3	725.5
160°	733.9	733.0	732.1	731.2	732.1	733.0	733.9	734.7	734.8	734.0	733.3
162.5°	741.3	740.5	739.7	739.0	739.7	740.5	741.3	742.1	742.1	741.2	740.3
165°	751.0	750.1	749.2	748.3	749.2	750.1	751.0	751.9	751.8	750.8	749.8
167.5°	758.1	757.1	756.1	755.0	756.1	757.1	758.1	759.1	759.1	758.1	757.1
170°	762.2	761.2	760.2	759.1	760.2	761.2	762.2	763.2	763.2	762.2	761.2
172.5°	764.8	763.7	762.5	761.4	762.5	763.7	764.8	765.9	765.9	764.9	763.9
175°	767.9	766.9	765.9	764.8	765.9	766.9	767.9	768.9	769.0	768.1	767.2
177.5°	768.9	767.9	766.9	765.9	766.9	767.9	768.9	769.9	770.0	769.2	768.4
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P332246

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	519.5	522.1	524.7	527.1	530.8	532.5	534.9	535.9	538.6	542.7	546.1
5°	487.9	491.6	496.5	500.4	506.7	511.6	517.0	522.1	528.2	536.8	544.5
7.5°	461.1	464.7	470.6	478.0	484.9	491.9	499.2	506.2	514.8	527.2	539.4
10°	443.4	447.8	454.8	462.7	471.3	478.1	486.7	495.5	506.3	520.5	535.2
12.5°	428.1	431.4	439.5	447.0	456.8	465.4	473.8	484.2	496.4	511.5	529.2
15°	403.8	408.4	416.3	424.7	435.0	444.1	455.0	467.6	479.5	498.1	519.5
17.5°	379.3	386.4	394.7	404.1	411.7	424.3	436.1	449.0	463.7	483.4	507.0
20°	363.7	369.3	377.0	390.7	400.7	410.3	421.2	437.3	450.8	473.2	497.6
22.5°	350.4	354.5	363.2	374.5	386.2	397.2	408.4	423.7	440.4	461.6	488.1
25°	330.8	337.4	343.9	352.0	364.6	377.9	390.0	403.1	420.8	443.4	472.0
27.5°	311.7	317.6	324.0	334.0	343.6	356.0	368.7	383.6	402.6	426.5	455.6
30°	299.4	303.8	309.9	322.7	331.3	342.0	356.9	370.2	387.9	413.3	444.1
32.5°	286.7	292.4	299.1	308.9	319.6	329.7	343.3	357.7	375.8	400.8	432.3
35°	268.6	275.4	282.1	289.4	300.1	310.6	322.0	337.8	356.2	380.5	411.4
37.5°	252.0	257.4	262.9	271.9	282.0	292.0	302.7	318.3	335.6	361.8	390.2
40°	241.4	246.3	250.5	259.8	269.6	280.3	290.8	304.5	323.1	347.6	375.1
42.5°	229.8	234.3	240.0	247.7	258.2	267.2	277.7	290.7	308.2	333.1	357.2
45°	212.5	217.6	222.5	229.7	240.2	249.1	258.4	270.7	288.7	309.2	330.6
47.5°	194.4	199.6	205.2	212.2	221.3	230.3	239.6	250.5	266.9	287.0	301.5
50°	182.9	187.1	192.7	199.7	208.1	217.6	226.0	237.9	253.5	269.3	281.9
52.5°	171.0	174.8	181.1	188.5	196.3	204.6	213.5	223.7	237.8	252.7	262.7
55°	152.4	157.0	162.4	169.6	177.3	184.3	192.9	203.4	214.6	225.8	232.5
57.5°	135.0	138.9	143.4	150.8	157.5	165.8	173.6	181.7	192.1	200.5	204.9
60°	122.3	125.8	131.6	138.2	144.4	151.7	160.5	168.7	176.6	183.4	186.8
62.5°	110.4	114.4	119.5	125.5	132.3	139.2	146.9	153.8	160.8	166.6	169.0
65°	94.8	98.1	101.8	107.4	113.0	120.0	126.0	133.0	138.2	141.4	143.5
67.5°	80.7	82.8	85.6	89.4	94.9	101.0	106.8	112.3	116.6	118.8	120.7
70°	71.5	72.9	75.0	78.7	82.9	88.3	94.4	98.3	102.0	103.9	105.8
72.5°	62.4	64.2	66.1	69.1	72.5	76.4	80.8	85.6	87.7	89.9	91.0
75°	47.3	49.9	52.4	54.3	56.6	59.6	63.6	66.6	67.8	69.7	69.9
77.5°	35.7	36.3	38.1	40.4	42.4	44.6	47.1	49.8	50.4	51.3	52.0
80°	29.4	29.4	29.4	30.8	33.1	34.7	37.0	38.4	39.4	39.6	39.8
82.5°	23.6	23.6	23.4	23.7	24.5	25.4	27.5	29.1	29.9	29.7	29.2
85°	15.4	14.9	14.9	14.7	14.9	14.4	14.2	15.1	16.5	16.5	16.1
87.5°	9.2	8.9	8.7	8.2	7.7	7.2	6.3	6.3	6.0	6.5	6.1
90°	14.2	13.7	12.0	10.4	8.7	7.1	5.6	4.4	3.1	1.8	0.6
92.5°	15.4	14.6	13.4	12.1	10.9	9.6	9.2	9.5	9.9	10.3	10.6
95°	18.6	17.7	16.3	14.9	13.5	12.1	14.0	19.2	24.4	29.6	34.8
97.5°	19.4	18.4	27.5	36.6	45.7	54.9	60.6	62.9	65.3	67.6	69.9
100°	19.8	18.8	38.6	58.4	78.1	97.9	106.5	104.0	101.5	98.9	96.4
102.5°	34.4	37.5	59.1	80.7	102.3	123.9	133.8	132.0	130.2	128.3	126.5
105°	102.5	124.9	136.3	147.7	159.1	170.5	175.5	174.1	172.8	171.4	170.0
107.5°	212.5	228.9	227.1	225.3	223.5	221.7	220.3	219.2	218.1	216.9	215.8
110°	253.0	257.2	255.8	254.4	253.0	251.7	250.4	249.4	248.4	247.4	246.4



TEST NUMBER: P332246

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	286.1	286.0	284.6	283.2	281.8	280.4	279.2	278.3	277.4	276.5	275.6
115°	328.7	327.4	326.2	325.1	324.0	322.8	321.9	321.1	320.3	319.6	318.8
117.5°	368.6	367.5	367.0	366.4	365.8	365.2	364.4	363.5	362.6	361.6	360.7
120°	394.6	393.5	393.2	392.8	392.4	392.0	391.3	390.1	389.0	387.8	386.7
122.5°	420.3	419.6	419.1	418.6	418.1	417.6	416.9	416.0	415.0	414.1	413.2
125°	456.5	456.3	455.8	455.3	454.8	454.3	453.5	452.5	451.5	450.5	449.4
127.5°	492.3	491.9	491.3	490.7	490.0	489.4	488.6	487.6	486.6	485.6	484.6
130°	513.8	513.3	512.8	512.3	511.8	511.3	510.5	509.5	508.5	507.5	506.5
132.5°	534.4	533.9	533.4	533.0	532.6	532.2	531.5	530.5	529.5	528.5	527.5
135°	565.6	565.2	564.7	564.2	563.7	563.2	562.6	561.8	561.0	560.3	559.5
137.5°	593.1	592.5	592.2	591.9	591.6	591.4	590.7	589.8	588.8	587.9	586.9
140°	610.8	610.3	609.9	609.5	609.1	608.8	608.2	607.4	606.7	605.9	605.1
142.5°	627.6	627.2	626.8	626.4	626.0	625.6	625.1	624.3	623.6	622.8	622.0
145°	651.0	650.8	650.5	650.3	650.0	649.8	649.2	648.3	647.4	646.5	645.6
147.5°	671.9	671.7	671.4	671.1	670.9	670.6	670.2	669.6	669.1	668.5	667.9
150°	684.7	684.4	684.2	683.9	683.7	683.4	683.1	682.7	682.3	682.0	681.6
152.5°	695.8	695.4	695.2	695.1	694.9	694.8	694.6	694.4	694.2	694.1	693.9
155°	711.3	710.7	710.5	710.4	710.3	710.2	710.2	710.5	710.7	711.0	711.2
157.5°	724.8	724.0	724.1	724.3	724.4	724.5	724.6	724.6	724.6	724.7	724.7
160°	732.5	731.8	731.9	732.0	732.1	732.3	732.4	732.5	732.7	732.8	732.9
162.5°	739.5	738.6	738.7	738.9	739.0	739.1	739.3	739.7	740.0	740.3	740.7
165°	748.8	747.7	747.9	748.0	748.1	748.2	748.5	748.9	749.3	749.6	750.0
167.5°	756.1	755.0	755.0	755.0	755.0	755.0	755.3	755.8	756.3	756.8	757.3
170°	760.2	759.1	759.1	759.1	759.1	759.1	759.4	759.9	760.4	760.9	761.4
172.5°	762.9	761.9	761.8	761.7	761.6	761.5	761.7	762.3	762.9	763.6	764.2
175°	766.3	765.4	765.3	765.2	765.0	764.9	765.2	765.8	766.4	767.1	767.7
177.5°	767.6	766.8	766.7	766.6	766.5	766.4	766.6	767.1	767.6	768.1	768.6
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P332246

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	547.2	549.3	551.9	555.8	558.8	561.4	561.9	562.7	564.6	567.7	570.1
5°	550.8	556.1	564.7	573.1	582.2	589.7	596.7	601.6	606.2	616.0	623.9
7.5°	549.6	561.6	575.1	590.1	605.4	620.1	633.8	646.1	658.3	672.6	688.8
10°	548.9	562.9	581.1	600.4	621.6	642.3	662.4	678.0	696.1	712.5	733.2
12.5°	545.4	565.5	587.2	611.9	638.0	661.9	688.3	709.8	730.6	754.2	778.3
15°	540.7	565.2	592.7	625.5	665.2	694.0	721.1	758.6	784.2	809.8	844.3
17.5°	532.3	562.2	596.5	639.2	672.2	711.1	751.7	781.4	815.9	852.0	883.2
20°	525.6	560.3	598.8	640.7	682.9	725.0	764.4	799.8	835.5	877.2	902.8
22.5°	518.9	553.2	593.2	637.7	683.0	727.5	772.0	813.6	853.7	895.8	928.5
25°	504.6	545.4	588.7	634.2	678.9	727.8	780.9	827.3	876.9	920.3	951.3
27.5°	490.2	527.6	570.7	616.8	666.5	724.3	786.8	839.5	889.2	920.3	930.0
30°	477.1	516.7	556.4	603.2	657.0	721.5	787.9	848.3	889.0	902.6	892.5
32.5°	463.9	499.8	539.0	587.0	644.1	714.6	789.4	843.1	867.6	857.3	816.5
35°	440.6	472.9	510.9	558.9	624.6	710.8	783.3	819.6	813.6	755.3	678.4
37.5°	415.6	442.0	477.1	527.3	604.4	695.7	756.8	762.2	709.7	620.3	531.5
40°	395.8	419.6	455.7	508.1	588.7	680.8	730.2	708.5	627.2	527.7	453.6
42.5°	376.6	396.7	431.5	488.0	573.8	660.4	690.5	643.3	549.5	455.4	388.0
45°	344.1	363.0	397.9	455.9	543.3	621.6	617.6	535.6	441.7	366.0	310.1
47.5°	313.3	329.8	362.6	421.8	507.5	563.3	526.3	439.0	359.4	298.6	258.7
50°	291.5	307.8	340.4	398.9	478.8	519.5	466.7	382.6	309.6	259.3	227.6
52.5°	270.6	286.5	316.3	373.3	444.1	468.5	411.7	333.7	272.9	229.5	202.3
55°	241.4	253.5	280.3	334.8	387.7	393.3	335.7	270.5	220.4	190.1	171.5
57.5°	211.6	222.0	248.5	291.9	329.0	326.1	271.6	215.1	181.4	158.9	145.4
60°	192.2	202.5	225.8	263.0	291.0	281.2	231.1	185.7	156.8	140.3	129.5
62.5°	174.1	182.1	204.0	231.2	251.3	240.2	197.6	160.0	137.0	123.1	114.6
65°	147.9	154.5	171.9	186.2	197.3	186.6	151.2	125.1	108.6	98.8	93.0
67.5°	123.1	127.2	138.2	143.4	151.3	139.5	113.7	96.2	86.8	78.6	74.5
70°	107.4	110.4	116.3	120.5	122.5	110.4	91.3	78.5	70.6	64.8	62.2
72.5°	91.7	94.4	95.6	99.0	97.9	86.6	73.4	63.2	57.5	53.6	50.3
75°	70.1	71.3	70.1	68.7	65.7	57.8	48.7	43.6	39.4	37.5	36.3
77.5°	51.1	50.7	49.2	47.0	41.8	36.8	31.9	30.2	28.4	27.4	27.0
80°	39.4	38.4	37.0	33.5	29.1	25.6	24.5	23.3	22.6	21.4	21.2
82.5°	29.3	28.7	26.4	23.5	20.4	18.7	17.8	17.3	16.6	16.0	16.0
85°	15.6	14.9	12.3	10.7	10.3	9.8	9.6	9.6	8.6	8.4	8.4
87.5°	5.4	4.5	4.6	4.3	4.6	4.5	5.1	5.0	5.2	5.4	5.2
90°	1.8	3.1	4.4	5.6	7.1	8.7	10.4	12.0	13.7	14.2	14.7
92.5°	10.3	9.9	9.5	9.2	9.6	10.9	12.1	13.4	14.6	15.4	16.2
95°	29.6	24.4	19.2	14.0	12.1	13.5	14.9	16.3	17.7	18.6	19.5
97.5°	67.6	65.3	62.9	60.6	54.9	45.7	36.6	27.5	18.4	19.4	20.4
100°	98.9	101.5	104.0	106.5	97.9	78.1	58.4	38.6	18.8	19.8	20.8
102.5°	128.3	130.2	132.0	133.8	123.9	102.3	80.7	59.1	37.5	34.4	31.2
105°	171.4	172.8	174.1	175.5	170.5	159.1	147.7	136.3	124.9	102.5	80.0
107.5°	216.9	218.1	219.2	220.3	221.7	223.5	225.3	227.1	228.9	212.5	196.0
110°	247.4	248.4	249.4	250.4	251.7	253.0	254.4	255.8	257.2	253.0	248.9



TEST NUMBER: P332246

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	276.5	277.4	278.3	279.2	280.4	281.8	283.2	284.6	286.0	286.1	286.1
115°	319.6	320.3	321.1	321.9	322.8	324.0	325.1	326.2	327.4	328.7	329.9
117.5°	361.6	362.6	363.5	364.4	365.2	365.8	366.4	367.0	367.5	368.6	369.6
120°	387.8	389.0	390.1	391.3	392.0	392.4	392.8	393.2	393.5	394.6	395.6
122.5°	414.1	415.0	416.0	416.9	417.6	418.1	418.6	419.1	419.6	420.3	421.0
125°	450.5	451.5	452.5	453.5	454.3	454.8	455.3	455.8	456.3	456.5	456.8
127.5°	485.6	486.6	487.6	488.6	489.4	490.0	490.7	491.3	491.9	492.3	492.7
130°	507.5	508.5	509.5	510.5	511.3	511.8	512.3	512.8	513.3	513.8	514.3
132.5°	528.5	529.5	530.5	531.5	532.2	532.6	533.0	533.4	533.9	534.4	534.9
135°	560.3	561.0	561.8	562.6	563.2	563.7	564.2	564.7	565.2	565.6	566.0
137.5°	587.9	588.8	589.8	590.7	591.4	591.6	591.9	592.2	592.5	593.1	593.7
140°	605.9	606.7	607.4	608.2	608.8	609.1	609.5	609.9	610.3	610.8	611.3
142.5°	622.8	623.6	624.3	625.1	625.6	626.0	626.4	626.8	627.2	627.6	628.0
145°	646.5	647.4	648.3	649.2	649.8	650.0	650.3	650.5	650.8	651.0	651.3
147.5°	668.5	669.1	669.6	670.2	670.6	670.9	671.1	671.4	671.7	671.9	672.2
150°	682.0	682.3	682.7	683.1	683.4	683.7	683.9	684.2	684.4	684.7	684.9
152.5°	694.1	694.2	694.4	694.6	694.8	694.9	695.1	695.2	695.4	695.8	696.3
155°	711.0	710.7	710.5	710.2	710.2	710.3	710.4	710.5	710.7	711.3	711.9
157.5°	724.7	724.6	724.6	724.6	724.5	724.4	724.3	724.1	724.0	724.8	725.5
160°	732.8	732.7	732.5	732.4	732.3	732.1	732.0	731.9	731.8	732.5	733.3
162.5°	740.3	740.0	739.7	739.3	739.1	739.0	738.9	738.7	738.6	739.5	740.3
165°	749.6	749.3	748.9	748.5	748.2	748.1	748.0	747.9	747.7	748.8	749.8
167.5°	756.8	756.3	755.8	755.3	755.0	755.0	755.0	755.0	755.0	756.1	757.1
170°	760.9	760.4	759.9	759.4	759.1	759.1	759.1	759.1	759.1	760.2	761.2
172.5°	763.6	762.9	762.3	761.7	761.5	761.6	761.7	761.8	761.9	762.9	763.9
175°	767.1	766.4	765.8	765.2	764.9	765.0	765.2	765.3	765.4	766.3	767.2
177.5°	768.1	767.6	767.1	766.6	766.4	766.5	766.6	766.7	766.8	767.6	768.4
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P332246

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	574.1	574.1	574.8	577.6	578.0	580.4	579.7
5°	630.9	635.3	637.0	644.0	648.1	650.0	646.3
7.5°	700.4	712.9	718.8	726.2	732.6	734.6	729.5
10°	751.1	764.2	775.1	781.9	788.2	792.4	797.7
12.5°	800.1	816.2	826.6	836.1	842.6	847.9	848.8
15°	853.4	877.6	896.0	909.6	916.3	919.8	918.4
17.5°	907.1	929.6	942.7	956.5	965.8	966.3	966.6
20°	937.5	959.4	974.6	984.8	995.3	994.8	997.2
22.5°	957.8	975.1	986.7	994.1	997.7	995.9	996.4
25°	967.3	972.5	970.4	958.5	955.4	944.5	946.4
27.5°	918.3	894.1	869.0	836.8	811.3	791.0	792.0
30°	851.8	808.9	760.0	719.0	682.2	671.9	650.0
32.5°	758.8	694.5	637.2	598.9	567.4	558.8	539.7
35°	601.1	538.6	479.7	444.3	430.3	410.7	410.5
37.5°	467.2	412.2	381.1	354.5	340.6	328.7	327.6
40°	393.0	350.2	326.6	307.5	293.8	284.9	282.8
42.5°	341.2	306.6	284.5	272.7	262.1	257.5	254.1
45°	278.6	255.3	240.0	229.3	224.4	220.9	219.0
47.5°	233.1	217.5	207.0	199.8	195.9	192.2	193.2
50°	208.3	195.5	187.8	181.0	178.0	175.4	175.7
52.5°	188.3	176.8	170.6	165.7	162.0	160.1	159.3
55°	159.8	152.6	146.3	142.8	140.7	138.2	137.5
57.5°	136.3	130.7	125.6	121.7	121.1	118.7	119.0
60°	120.7	116.0	111.8	109.7	108.1	106.0	106.7
62.5°	107.8	103.9	100.1	98.4	96.7	95.2	95.5
65°	88.3	84.6	82.2	81.3	80.6	79.9	79.2
67.5°	70.4	68.1	66.6	64.6	63.2	63.0	62.3
70°	59.2	56.1	53.6	51.0	50.3	50.1	50.3
72.5°	47.4	45.5	44.8	43.6	43.4	42.8	43.2
75°	35.6	34.9	34.5	33.5	33.5	33.5	33.5
77.5°	26.3	25.9	25.6	25.4	25.2	24.8	24.8
80°	20.5	20.3	19.8	19.8	19.6	19.8	19.6
82.5°	15.5	15.4	15.0	15.0	14.7	14.6	14.7
85°	7.9	7.7	8.2	7.7	7.9	7.5	7.9
87.5°	5.3	5.4	5.3	5.3	5.2	5.6	5.3
90°	15.2	15.7	16.1	16.4	16.6	16.9	17.1
92.5°	17.0	17.8	18.3	18.5	18.6	18.8	18.9
95°	20.3	21.2	21.7	21.7	21.7	21.7	21.7
97.5°	21.4	22.4	23.0	23.1	23.2	23.4	23.5
100°	21.9	22.9	23.4	23.6	23.7	23.8	24.0
102.5°	28.1	25.0	23.5	23.7	24.0	24.2	24.4
105°	57.6	35.2	24.1	24.3	24.6	24.8	25.1
107.5°	179.6	163.1	146.5	129.5	112.6	95.7	78.8
110°	244.7	240.5	229.3	211.2	193.1	175.0	156.8



TEST NUMBER: P332246

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	286.2	286.3	284.4	280.6	276.7	272.9	269.1
115°	331.2	332.5	333.3	333.8	334.4	334.9	335.4
117.5°	370.6	371.6	372.2	372.3	372.4	372.5	372.6
120°	396.6	397.6	398.1	398.1	398.1	398.1	398.1
122.5°	421.7	422.4	422.8	422.9	423.0	423.1	423.2
125°	457.0	457.3	457.6	457.8	458.1	458.3	458.6
127.5°	493.1	493.5	493.6	493.3	493.1	492.8	492.6
130°	514.8	515.3	515.5	515.2	515.0	514.7	514.5
132.5°	535.4	535.9	536.0	535.6	535.2	534.9	534.5
135°	566.4	566.7	566.7	566.4	566.0	565.6	565.2
137.5°	594.3	594.9	595.1	594.8	594.6	594.3	594.1
140°	611.8	612.3	612.4	612.2	611.9	611.7	611.4
142.5°	628.4	628.8	628.8	628.5	628.1	627.7	627.4
145°	651.5	651.8	651.9	651.9	651.9	651.9	651.9
147.5°	672.4	672.7	672.5	671.9	671.3	670.8	670.2
150°	685.2	685.4	685.4	685.0	684.6	684.2	683.9
152.5°	696.7	697.2	697.1	696.6	696.0	695.4	694.8
155°	712.6	713.2	713.1	712.4	711.6	710.9	710.1
157.5°	726.3	727.1	726.9	725.9	725.0	724.0	723.0
160°	734.0	734.8	734.7	733.9	733.0	732.1	731.2
162.5°	741.2	742.1	742.1	741.3	740.5	739.7	739.0
165°	750.8	751.8	751.9	751.0	750.1	749.2	748.3
167.5°	758.1	759.1	759.1	758.1	757.1	756.1	755.0
170°	762.2	763.2	763.2	762.2	761.2	760.2	759.1
172.5°	764.9	765.9	765.9	764.8	763.7	762.5	761.4
175°	768.1	769.0	768.9	767.9	766.9	765.9	764.8
177.5°	769.2	770.0	769.9	768.9	767.9	766.9	765.9
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7

(END OF REPORT)