

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332248

Luminaire Tested: **S123RDIP-S340D585U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332248
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D585U835-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3477.1 lumens
Efficiency: N/A
Efficacy: 135.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332248

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332248

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39																				
1	96	92	88	85	87	84	80	78	68	66	64	54	53	52	41	41	40	34																				
2	88	81	75	70	79	74	69	64	60	57	54	48	46	44	37	35	34	29																				
3	80	71	64	59	73	65	59	54	54	49	46	43	40	38	33	31	30	25																				
4	73	63	56	50	67	58	51	46	48	43	39	39	35	32	30	28	26	22																				
5	68	56	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19																				
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20	17																				
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18	15																				
8	53	42	34	29	49	38	32	27	32	27	24	26	23	20	21	18	16	14																				
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	19	17	15	13																				
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5858	5858	5858	5858
5°	6983	5883	5181	5883
10°	8719	5850	4680	5850
15°	10234	5789	4268	5789
20°	11423	5700	3918	5700
25°	11240	5606	3702	5606
30°	8079	5520	3480	5520
35°	5394	5406	3336	5406
40°	3974	5271	3188	5271
45°	3334	5033	3043	5033
50°	2942	4721	2840	4721
55°	2580	4363	2562	4363
60°	2297	4021	2347	4021
65°	2017	3655	2183	3655
70°	1583	3330	1995	3330
75°	1393	2907	1822	2907
80°	1215	2467	1791	2467
85°	976	1988	1902	1988



TEST NUMBER: P332248

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.5	1.5
10°-20°	167.2	4.8
20°-30°	262.7	7.6
30°-40°	274.1	7.9
40°-50°	234.5	6.7
50°-60°	178.8	5.1
60°-70°	114.6	3.3
70°-80°	55.1	1.6
80°-90°	16.8	0.5
90°-100°	156.8	4.5
100°-110°	444.0	12.8
110°-120°	436.8	12.6
120°-130°	348.4	10.0
130°-140°	274.7	7.9
140°-150°	205.0	5.9
150°-160°	142.9	4.1
160°-170°	83.9	2.4
170°-180°	27.3	0.8
0°-30°	483.4	13.9
0°-40°	757.5	21.8
0°-60°	1170.8	33.7
0°-90°	1357.2	39.0
90°-120°	1037.6	29.8
90°-150°	1865.7	53.7
90°-180°	2120.0	61.0
0°-180°	3477.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	544	544	544	544	544	
5°	646	544	480	544	646	67
15°	918	520	383	520	918	260
25°	946	472	312	472	946	407
35°	410	411	254	411	410	269
45°	219	331	200	331	219	172
55°	138	232	136	232	138	124
65°	79	144	86	144	79	78
75°	34	70	44	70	34	36
85°	8	16	15	16	8	10
90°	16	1	16	1	16	9
95°	66	19	66	19	66	119
105°	726	66	726	66	726	716
115°	882	117	882	117	882	857
125°	696	163	696	163	696	631
135°	564	190	564	190	564	438
145°	441	217	441	217	441	280
155°	366	247	366	247	366	171
165°	319	270	319	270	319	91
175°	287	281	287	281	287	28
180°	282	282	282	282	282	



TEST NUMBER: P332248

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	579.7	580.4	578.0	577.6	574.8	574.1	574.1	570.1	567.7	564.6	562.7
5°	646.3	650.0	648.1	644.0	637.0	635.3	630.9	623.9	616.0	606.2	601.6
7.5°	729.5	734.6	732.6	726.2	718.8	712.9	700.4	688.8	672.6	658.3	646.1
10°	797.7	792.4	788.2	781.9	775.1	764.2	751.1	733.2	712.5	696.1	678.0
12.5°	848.8	847.9	842.6	836.1	826.6	816.2	800.1	778.3	754.2	730.6	709.8
15°	918.4	919.8	916.3	909.6	896.0	877.6	853.4	844.3	809.8	784.2	758.6
17.5°	966.6	966.3	965.8	956.5	942.7	929.6	907.1	883.2	852.0	815.9	781.4
20°	997.2	994.8	995.3	984.8	974.6	959.4	937.5	902.8	877.2	835.5	799.8
22.5°	996.4	995.9	997.7	994.1	986.7	975.1	957.8	928.5	895.8	853.7	813.6
25°	946.4	944.5	955.4	958.5	970.4	972.5	967.3	951.3	920.3	876.9	827.3
27.5°	792.0	791.0	811.3	836.8	869.0	894.1	918.3	930.0	920.3	889.2	839.5
30°	650.0	671.9	682.2	719.0	760.0	808.9	851.8	892.5	902.6	889.0	848.3
32.5°	539.7	558.8	567.4	598.9	637.2	694.5	758.8	816.5	857.3	867.6	843.1
35°	410.5	410.7	430.3	444.3	479.7	538.6	601.1	678.4	755.3	813.6	819.6
37.5°	327.6	328.7	340.6	354.5	381.1	412.2	467.2	531.5	620.3	709.7	762.2
40°	282.8	284.9	293.8	307.5	326.6	350.2	393.0	453.6	527.7	627.2	708.5
42.5°	254.1	257.5	262.1	272.7	284.5	306.6	341.2	388.0	455.4	549.5	643.3
45°	219.0	220.9	224.4	229.3	240.0	255.3	278.6	310.1	366.0	441.7	535.6
47.5°	193.2	192.2	195.9	199.8	207.0	217.5	233.1	258.7	298.6	359.4	439.0
50°	175.7	175.4	178.0	181.0	187.8	195.5	208.3	227.6	259.3	309.6	382.6
52.5°	159.3	160.1	162.0	165.7	170.6	176.8	188.3	202.3	229.5	272.9	333.7
55°	137.5	138.2	140.7	142.8	146.3	152.6	159.8	171.5	190.1	220.4	270.5
57.5°	119.0	118.7	121.1	121.7	125.6	130.7	136.3	145.4	158.9	181.4	215.1
60°	106.7	106.0	108.1	109.7	111.8	116.0	120.7	129.5	140.3	156.8	185.7
62.5°	95.5	95.2	96.7	98.4	100.1	103.9	107.8	114.6	123.1	137.0	160.0
65°	79.2	79.9	80.6	81.3	82.2	84.6	88.3	93.0	98.8	108.6	125.1
67.5°	62.3	63.0	63.2	64.6	66.6	68.1	70.4	74.5	78.6	86.8	96.2
70°	50.3	50.1	50.3	51.0	53.6	56.1	59.2	62.2	64.8	70.6	78.5
72.5°	43.2	42.8	43.4	43.6	44.8	45.5	47.4	50.3	53.6	57.5	63.2
75°	33.5	33.5	33.5	33.5	34.5	34.9	35.6	36.3	37.5	39.4	43.6
77.5°	24.8	24.8	25.2	25.4	25.6	25.9	26.3	27.0	27.4	28.4	30.2
80°	19.6	19.8	19.6	19.8	19.8	20.3	20.5	21.2	21.4	22.6	23.3
82.5°	14.7	14.6	14.7	15.0	15.0	15.4	15.5	16.0	16.0	16.6	17.3
85°	7.9	7.5	7.9	7.7	8.2	7.7	7.9	8.4	8.4	8.6	9.6
87.5°	5.2	5.7	5.2	5.2	5.4	5.3	5.2	5.1	5.3	5.3	5.1
90°	16.5	17.1	16.5	16.0	16.5	15.4	14.8	14.3	13.7	14.3	12.5
92.5°	27.5	28.5	27.9	29.7	30.7	33.7	38.1	48.0	66.2	87.7	96.5
95°	66.2	68.4	72.4	77.6	88.4	108.9	139.2	205.3	274.3	338.2	301.2
97.5°	180.1	185.0	200.4	226.1	268.2	336.4	410.0	511.9	560.8	524.2	383.7
100°	357.6	357.1	379.3	420.9	478.5	559.5	626.3	672.5	652.5	540.1	365.0
102.5°	524.6	537.7	556.3	589.3	634.1	685.5	724.4	725.9	657.1	510.5	337.7
105°	725.5	728.4	746.6	768.3	794.5	809.4	798.5	741.5	622.3	458.6	304.0
107.5°	841.2	846.4	852.6	859.9	859.4	839.1	789.2	696.5	561.4	412.7	282.6
110°	888.6	889.8	890.9	886.4	870.4	830.5	758.6	653.6	523.0	386.7	274.3



TEST NUMBER: P332248

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	898.2	898.0	893.7	879.5	850.3	799.0	718.4	611.2	489.7	369.4	269.8
115°	882.4	879.5	868.1	843.0	800.2	738.1	654.2	555.0	449.5	350.8	268.1
117.5°	831.9	828.1	811.6	782.9	738.3	675.2	599.9	514.2	425.2	339.8	269.1
120°	790.0	786.5	772.9	740.9	695.9	638.2	569.8	492.8	412.4	334.8	270.9
122.5°	750.7	746.4	731.3	702.6	662.5	609.0	545.6	475.9	401.9	331.6	274.1
125°	695.9	691.9	677.6	652.5	616.0	570.4	515.6	453.4	388.4	327.4	278.9
127.5°	650.7	647.0	634.1	612.7	580.2	538.7	489.3	433.8	376.6	325.3	284.4
130°	625.1	620.6	608.6	588.1	557.8	519.0	472.8	421.5	370.2	324.0	288.0
132.5°	600.0	596.8	586.2	565.7	537.3	500.3	457.3	410.1	364.2	323.5	290.8
135°	564.1	560.1	549.8	532.7	504.8	472.3	435.2	394.7	356.5	322.8	294.9
137.5°	526.1	523.5	514.8	497.5	474.0	445.8	413.9	380.7	349.8	321.6	297.6
140°	499.6	500.2	491.1	475.1	453.4	428.9	401.5	372.5	345.6	321.1	299.4
142.5°	475.0	475.6	467.4	453.2	434.7	413.4	389.7	364.7	342.0	320.2	300.8
145°	440.9	439.8	435.2	423.2	409.0	392.4	374.2	355.3	337.1	318.8	301.7
147.5°	412.8	412.4	408.0	399.9	389.1	377.4	362.6	347.7	332.3	316.7	301.7
150°	396.4	396.4	393.0	386.7	378.2	367.3	355.3	342.2	329.1	314.8	301.7
152.5°	382.7	382.7	380.7	374.8	368.1	359.1	348.5	337.2	325.5	312.6	300.4
155°	365.6	365.0	363.9	359.3	354.2	347.4	338.8	329.7	320.0	308.6	298.9
157.5°	350.0	350.1	349.2	345.8	341.3	336.0	329.3	321.7	313.8	305.0	296.9
160°	339.9	340.5	340.5	337.1	333.1	329.1	323.4	317.1	309.7	302.3	296.0
162.5°	330.8	331.4	331.4	328.4	325.8	322.3	317.0	311.7	305.6	299.6	294.2
165°	318.8	318.8	319.4	317.1	314.8	312.0	308.0	304.6	300.0	295.5	291.5
167.5°	307.4	307.4	308.0	306.4	305.4	303.3	301.0	298.4	294.7	291.3	288.7
170°	300.6	300.6	301.2	300.0	299.4	298.3	296.0	294.3	291.5	288.6	286.9
172.5°	294.2	294.7	295.7	294.5	294.4	293.7	291.9	290.7	288.3	286.3	285.5
175°	286.9	287.5	288.0	287.5	287.5	287.5	286.3	285.8	284.6	283.5	283.5
177.5°	282.7	282.7	283.6	283.1	283.6	283.6	283.1	282.7	282.2	281.8	282.2
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332248

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	561.9	561.4	558.8	555.8	551.9	549.3	547.2	546.1	542.7	538.6	535.9
5°	596.7	589.7	582.2	573.1	564.7	556.1	550.8	544.5	536.8	528.2	522.1
7.5°	633.8	620.1	605.4	590.1	575.1	561.6	549.6	539.4	527.2	514.8	506.2
10°	662.4	642.3	621.6	600.4	581.1	562.9	548.9	535.2	520.5	506.3	495.5
12.5°	688.3	661.9	638.0	611.9	587.2	565.5	545.4	529.2	511.5	496.4	484.2
15°	721.1	694.0	665.2	625.5	592.7	565.2	540.7	519.5	498.1	479.5	467.6
17.5°	751.7	711.1	672.2	639.2	596.5	562.2	532.3	507.0	483.4	463.7	449.0
20°	764.4	725.0	682.9	640.7	598.8	560.3	525.6	497.6	473.2	450.8	437.3
22.5°	772.0	727.5	683.0	637.7	593.2	553.2	518.9	488.1	461.6	440.4	423.7
25°	780.9	727.8	678.9	634.2	588.7	545.4	504.6	472.0	443.4	420.8	403.1
27.5°	786.8	724.3	666.5	616.8	570.7	527.6	490.2	455.6	426.5	402.6	383.6
30°	787.9	721.5	657.0	603.2	556.4	516.7	477.1	444.1	413.3	387.9	370.2
32.5°	789.4	714.6	644.1	587.0	539.0	499.8	463.9	432.3	400.8	375.8	357.7
35°	783.3	710.8	624.6	558.9	510.9	472.9	440.6	411.4	380.5	356.2	337.8
37.5°	756.8	695.7	604.4	527.3	477.1	442.0	415.6	390.2	361.8	335.6	318.3
40°	730.2	680.8	588.7	508.1	455.7	419.6	395.8	375.1	347.6	323.1	304.5
42.5°	690.5	660.4	573.8	488.0	431.5	396.7	376.6	357.2	333.1	308.2	290.7
45°	617.6	621.6	543.3	455.9	397.9	363.0	344.1	330.6	309.2	288.7	270.7
47.5°	526.3	563.3	507.5	421.8	362.6	329.8	313.3	301.5	287.0	266.9	250.5
50°	466.7	519.5	478.8	398.9	340.4	307.8	291.5	281.9	269.3	253.5	237.9
52.5°	411.7	468.5	444.1	373.3	316.3	286.5	270.6	262.7	252.7	237.8	223.7
55°	335.7	393.3	387.7	334.8	280.3	253.5	241.4	232.5	225.8	214.6	203.4
57.5°	271.6	326.1	329.0	291.9	248.5	222.0	211.6	204.9	200.5	192.1	181.7
60°	231.1	281.2	291.0	263.0	225.8	202.5	192.2	186.8	183.4	176.6	168.7
62.5°	197.6	240.2	251.3	231.2	204.0	182.1	174.1	169.0	166.6	160.8	153.8
65°	151.2	186.6	197.3	186.2	171.9	154.5	147.9	143.5	141.4	138.2	133.0
67.5°	113.7	139.5	151.3	143.4	138.2	127.2	123.1	120.7	118.8	116.6	112.3
70°	91.3	110.4	122.5	120.5	116.3	110.4	107.4	105.8	103.9	102.0	98.3
72.5°	73.4	86.6	97.9	99.0	95.6	94.4	91.7	91.0	89.9	87.7	85.6
75°	48.7	57.8	65.7	68.7	70.1	71.3	70.1	69.9	69.7	67.8	66.6
77.5°	31.9	36.8	41.8	47.0	49.2	50.7	51.1	52.0	51.3	50.4	49.8
80°	24.5	25.6	29.1	33.5	37.0	38.4	39.4	39.8	39.6	39.4	38.4
82.5°	17.8	18.7	20.4	23.5	26.4	28.7	29.3	29.2	29.7	29.9	29.1
85°	9.6	9.8	10.3	10.7	12.3	14.9	15.6	16.1	16.5	16.5	15.1
87.5°	5.1	4.6	4.7	4.4	4.8	4.6	5.5	6.2	6.6	6.1	6.4
90°	10.8	9.1	7.4	6.3	5.1	3.4	2.3	1.1	2.3	3.4	5.1
92.5°	72.4	47.9	33.0	24.5	19.7	15.3	10.5	7.1	10.5	15.3	19.7
95°	207.6	122.6	74.1	51.9	37.1	27.4	21.1	19.4	21.1	27.4	37.1
97.5°	227.8	132.0	85.7	61.6	47.0	38.6	33.7	33.1	33.7	38.6	47.0
100°	215.0	130.6	90.7	68.4	54.8	46.8	42.8	42.2	42.8	46.8	54.8
102.5°	204.1	132.4	96.6	76.2	63.9	56.4	52.8	51.8	52.8	56.4	63.9
105°	196.2	137.5	106.7	89.0	78.1	71.3	67.9	66.2	67.9	71.3	78.1
107.5°	195.6	146.8	119.8	103.4	93.2	86.5	83.2	81.4	83.2	86.5	93.2
110°	197.9	154.6	128.9	112.9	103.2	97.0	94.1	92.4	94.1	97.0	103.2



TEST NUMBER: P332248

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	202.5	162.3	138.5	123.0	113.3	107.0	104.2	102.4	104.2	107.0	113.3
115°	209.9	175.1	153.4	138.0	128.3	122.6	119.2	116.9	119.2	122.6	128.3
117.5°	219.7	188.7	167.2	153.0	142.1	136.9	134.0	131.4	134.0	136.9	142.1
120°	227.0	197.3	176.8	162.6	151.7	146.0	143.2	141.5	143.2	146.0	151.7
122.5°	233.9	206.5	186.4	171.2	160.8	154.7	151.8	150.1	151.8	154.7	160.8
125°	244.7	219.6	199.6	184.2	173.4	167.1	163.7	162.6	163.7	167.1	173.4
127.5°	253.6	231.0	211.7	196.3	184.3	178.0	173.7	172.0	173.7	178.0	184.3
130°	259.5	237.8	219.0	203.6	191.6	184.8	179.7	178.0	179.7	184.8	191.6
132.5°	265.0	243.8	225.4	210.5	198.5	190.3	184.7	182.5	184.7	190.3	198.5
135°	272.1	252.7	235.0	219.6	207.6	199.1	192.8	190.5	192.8	199.1	207.6
137.5°	277.3	258.8	241.8	227.6	215.7	206.6	200.4	198.0	200.4	206.6	215.7
140°	280.1	262.9	246.4	232.1	220.7	211.6	205.9	203.1	205.9	211.6	220.7
142.5°	282.8	266.1	250.1	236.7	225.3	217.1	210.9	208.5	210.9	217.1	225.3
145°	285.8	270.4	255.5	242.4	232.7	224.2	219.0	217.3	219.0	224.2	232.7
147.5°	287.6	273.8	260.2	249.0	239.7	232.3	227.2	226.2	227.2	232.3	239.7
150°	288.0	276.1	262.9	252.7	244.7	237.3	232.7	232.1	232.7	237.3	244.7
152.5°	289.0	277.4	266.1	256.3	249.3	242.8	238.2	238.1	238.2	242.8	249.3
155°	289.2	280.1	270.4	262.4	256.1	250.4	247.0	247.0	247.0	250.4	256.1
157.5°	289.8	281.5	273.8	267.6	262.3	257.2	254.5	254.0	254.5	257.2	262.3
160°	289.8	282.9	276.1	270.4	266.4	261.8	259.5	259.5	259.5	261.8	266.4
162.5°	289.3	283.4	277.4	272.6	269.1	265.5	263.6	263.6	263.6	265.5	269.1
165°	288.0	284.0	279.5	275.5	273.2	270.4	269.2	269.8	269.2	270.4	273.2
167.5°	287.1	283.9	280.6	278.1	276.5	274.3	273.8	274.5	273.8	274.3	276.5
170°	285.8	283.5	280.6	279.5	278.3	276.6	276.1	277.2	276.1	276.6	278.3
172.5°	285.3	283.5	281.1	280.4	279.7	278.5	278.3	279.0	278.3	278.5	279.7
175°	284.0	282.9	281.8	281.2	281.2	280.1	280.6	281.2	280.6	280.1	281.2
177.5°	283.1	282.2	281.8	281.8	281.8	281.3	281.8	282.2	281.8	281.3	281.8
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332248

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	534.9	532.5	530.8	527.1	524.7	522.1	519.5	521.1	520.9	520.8	520.8
5°	517.0	511.6	506.7	500.4	496.5	491.6	487.9	487.4	488.3	485.1	483.2
7.5°	499.2	491.9	484.9	478.0	470.6	464.7	461.1	459.3	457.0	455.0	452.9
10°	486.7	478.1	471.3	462.7	454.8	447.8	443.4	440.3	438.7	437.1	434.0
12.5°	473.8	465.4	456.8	447.0	439.5	431.4	428.1	424.7	421.6	419.7	415.6
15°	455.0	444.1	435.0	424.7	416.3	408.4	403.8	397.0	396.1	393.7	389.5
17.5°	436.1	424.3	411.7	404.1	394.7	386.4	379.3	377.1	370.4	367.9	364.2
20°	421.2	410.3	400.7	390.7	377.0	369.3	363.7	360.7	355.3	352.0	349.7
22.5°	408.4	397.2	386.2	374.5	363.2	354.5	350.4	345.7	342.8	338.2	335.7
25°	390.0	377.9	364.6	352.0	343.9	337.4	330.8	326.6	322.4	320.3	315.7
27.5°	368.7	356.0	343.6	334.0	324.0	317.6	311.7	308.0	302.9	299.4	296.8
30°	356.9	342.0	331.3	322.7	309.9	303.8	299.4	294.7	291.0	287.3	284.7
32.5°	343.3	329.7	319.6	308.9	299.1	292.4	286.7	282.6	279.4	275.9	273.3
35°	322.0	310.6	300.1	289.4	282.1	275.4	268.6	265.1	262.1	258.8	256.5
37.5°	302.7	292.0	282.0	271.9	262.9	257.4	252.0	249.3	245.2	243.0	240.7
40°	290.8	280.3	269.6	259.8	250.5	246.3	241.4	237.4	233.7	232.0	229.5
42.5°	277.7	267.2	258.2	247.7	240.0	234.3	229.8	225.5	222.7	220.3	218.9
45°	258.4	249.1	240.2	229.7	222.5	217.6	212.5	208.5	206.0	204.3	201.8
47.5°	239.6	230.3	221.3	212.2	205.2	199.6	194.4	191.7	188.3	186.3	184.6
50°	226.0	217.6	208.1	199.7	192.7	187.1	182.9	179.4	176.4	173.8	172.6
52.5°	213.5	204.6	196.3	188.5	181.1	174.8	171.0	167.3	165.0	162.1	160.7
55°	192.9	184.3	177.3	169.6	162.4	157.0	152.4	149.1	146.8	143.5	141.7
57.5°	173.6	165.8	157.5	150.8	143.4	138.9	135.0	130.6	127.7	125.2	123.3
60°	160.5	151.7	144.4	138.2	131.6	125.8	122.3	118.8	115.8	113.2	111.6
62.5°	146.9	139.2	132.3	125.5	119.5	114.4	110.4	107.5	104.8	103.2	101.5
65°	126.0	120.0	113.0	107.4	101.8	98.1	94.8	92.3	90.4	89.2	87.8
67.5°	106.8	101.0	94.9	89.4	85.6	82.8	80.7	78.5	77.5	76.0	75.1
70°	94.4	88.3	82.9	78.7	75.0	72.9	71.5	69.9	69.0	67.1	66.2
72.5°	80.8	76.4	72.5	69.1	66.1	64.2	62.4	60.4	58.9	56.8	55.9
75°	63.6	59.6	56.6	54.3	52.4	49.9	47.3	45.2	44.5	43.8	43.6
77.5°	47.1	44.6	42.4	40.4	38.1	36.3	35.7	35.2	35.1	34.7	34.7
80°	37.0	34.7	33.1	30.8	29.4	29.4	29.4	28.9	29.1	29.1	29.1
82.5°	27.5	25.4	24.5	23.7	23.4	23.6	23.6	23.7	23.5	23.9	23.7
85°	14.2	14.4	14.9	14.7	14.9	14.9	15.4	15.1	15.4	14.9	15.4
87.5°	6.5	7.3	7.8	8.3	8.8	9.0	9.1	9.2	9.5	9.6	9.8
90°	6.3	7.4	9.1	10.8	12.5	14.3	13.7	14.3	14.8	15.4	16.5
92.5°	24.5	33.0	47.9	72.4	96.5	87.7	66.2	48.0	38.1	33.7	30.7
95°	51.9	74.1	122.6	207.6	301.2	338.2	274.3	205.3	139.2	108.9	88.4
97.5°	61.6	85.7	132.0	227.8	383.7	524.2	560.8	511.9	410.0	336.4	268.2
100°	68.4	90.7	130.6	215.0	365.0	540.1	652.5	672.5	626.3	559.5	478.5
102.5°	76.2	96.6	132.4	204.1	337.7	510.5	657.1	725.9	724.4	685.5	634.1
105°	89.0	106.7	137.5	196.2	304.0	458.6	622.3	741.5	798.5	809.4	794.5
107.5°	103.4	119.8	146.8	195.6	282.6	412.7	561.4	696.5	789.2	839.1	859.4
110°	112.9	128.9	154.6	197.9	274.3	386.7	523.0	653.6	758.6	830.5	870.4



TEST NUMBER: P332248

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	123.0	138.5	162.3	202.5	269.8	369.4	489.7	611.2	718.4	799.0	850.3
115°	138.0	153.4	175.1	209.9	268.1	350.8	449.5	555.0	654.2	738.1	800.2
117.5°	153.0	167.2	188.7	219.7	269.1	339.8	425.2	514.2	599.9	675.2	738.3
120°	162.6	176.8	197.3	227.0	270.9	334.8	412.4	492.8	569.8	638.2	695.9
122.5°	171.2	186.4	206.5	233.9	274.1	331.6	401.9	475.9	545.6	609.0	662.5
125°	184.2	199.6	219.6	244.7	278.9	327.4	388.4	453.4	515.6	570.4	616.0
127.5°	196.3	211.7	231.0	253.6	284.4	325.3	376.6	433.8	489.3	538.7	580.2
130°	203.6	219.0	237.8	259.5	288.0	324.0	370.2	421.5	472.8	519.0	557.8
132.5°	210.5	225.4	243.8	265.0	290.8	323.5	364.2	410.1	457.3	500.3	537.3
135°	219.6	235.0	252.7	272.1	294.9	322.8	356.5	394.7	435.2	472.3	504.8
137.5°	227.6	241.8	258.8	277.3	297.6	321.6	349.8	380.7	413.9	445.8	474.0
140°	232.1	246.4	262.9	280.1	299.4	321.1	345.6	372.5	401.5	428.9	453.4
142.5°	236.7	250.1	266.1	282.8	300.8	320.2	342.0	364.7	389.7	413.4	434.7
145°	242.4	255.5	270.4	285.8	301.7	318.8	337.1	355.3	374.2	392.4	409.0
147.5°	249.0	260.2	273.8	287.6	301.7	316.7	332.3	347.7	362.6	377.4	389.1
150°	252.7	262.9	276.1	288.0	301.7	314.8	329.1	342.2	355.3	367.3	378.2
152.5°	256.3	266.1	277.4	289.0	300.4	312.6	325.5	337.2	348.5	359.1	368.1
155°	262.4	270.4	280.1	289.2	298.9	308.6	320.0	329.7	338.8	347.4	354.2
157.5°	267.6	273.8	281.5	289.8	296.9	305.0	313.8	321.7	329.3	336.0	341.3
160°	270.4	276.1	282.9	289.8	296.0	302.3	309.7	317.1	323.4	329.1	333.1
162.5°	272.6	277.4	283.4	289.3	294.2	299.6	305.6	311.7	317.0	322.3	325.8
165°	275.5	279.5	284.0	288.0	291.5	295.5	300.0	304.6	308.0	312.0	314.8
167.5°	278.1	280.6	283.9	287.1	288.7	291.3	294.7	298.4	301.0	303.3	305.4
170°	279.5	280.6	283.5	285.8	286.9	288.6	291.5	294.3	296.0	298.3	299.4
172.5°	280.4	281.1	283.5	285.3	285.5	286.3	288.3	290.7	291.9	293.7	294.4
175°	281.2	281.8	282.9	284.0	283.5	283.5	284.6	285.8	286.3	287.5	287.5
177.5°	281.8	281.8	282.2	283.1	282.2	281.8	282.2	282.7	283.1	283.6	283.6
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332248

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	518.5	518.3	518.5	517.8	518.5	518.3	518.5	520.8	520.8	520.9	521.1
5°	482.5	482.3	481.6	479.5	481.6	482.3	482.5	483.2	485.1	488.3	487.4
7.5°	451.0	450.7	448.7	448.7	448.7	450.7	451.0	452.9	455.0	457.0	459.3
10°	432.4	432.6	429.8	428.2	429.8	432.6	432.4	434.0	437.1	438.7	440.3
12.5°	414.3	413.3	411.0	409.2	411.0	413.3	414.3	415.6	419.7	421.6	424.7
15°	390.5	388.1	382.6	383.0	382.6	388.1	390.5	389.5	393.7	396.1	397.0
17.5°	362.4	360.7	360.6	357.3	360.6	360.7	362.4	364.2	367.9	370.4	377.1
20°	346.0	344.8	345.3	342.0	345.3	344.8	346.0	349.7	352.0	355.3	360.7
22.5°	333.1	331.9	330.0	329.0	330.0	331.9	333.1	335.7	338.2	342.8	345.7
25°	314.3	312.4	310.6	311.7	310.6	312.4	314.3	315.7	320.3	322.4	326.6
27.5°	295.5	294.1	292.2	292.0	292.2	294.1	295.5	296.8	299.4	302.9	308.0
30°	283.5	282.1	281.2	280.0	281.2	282.1	283.5	284.7	287.3	291.0	294.7
32.5°	271.4	271.1	269.5	269.2	269.5	271.1	271.4	273.3	275.9	279.4	282.6
35°	255.6	254.2	253.7	253.9	253.7	254.2	255.6	256.5	258.8	262.1	265.1
37.5°	240.5	238.7	237.8	237.0	237.8	238.7	240.5	240.7	243.0	245.2	249.3
40°	229.7	227.9	227.4	226.9	227.4	227.9	229.7	229.5	232.0	233.7	237.4
42.5°	217.6	216.9	216.6	215.7	216.6	216.9	217.6	218.9	220.3	222.7	225.5
45°	201.1	200.8	199.4	199.9	199.4	200.8	201.1	201.8	204.3	206.0	208.5
47.5°	183.6	182.6	181.6	182.3	181.6	182.6	183.6	184.6	186.3	188.3	191.7
50°	171.7	171.2	169.1	169.6	169.1	171.2	171.7	172.6	173.8	176.4	179.4
52.5°	159.8	158.0	157.2	156.9	157.2	158.0	159.8	160.7	162.1	165.0	167.3
55°	140.0	137.9	137.0	136.5	137.0	137.9	140.0	141.7	143.5	146.8	149.1
57.5°	120.6	120.1	119.3	119.8	119.3	120.1	120.6	123.3	125.2	127.7	130.6
60°	109.3	109.3	109.3	109.0	109.3	109.3	109.3	111.6	113.2	115.8	118.8
62.5°	100.5	99.9	99.8	100.1	99.8	99.9	100.5	101.5	103.2	104.8	107.5
65°	87.1	86.9	86.0	85.7	86.0	86.9	87.1	87.8	89.2	90.4	92.3
67.5°	74.5	73.7	73.4	73.1	73.4	73.7	74.5	75.1	76.0	77.5	78.5
70°	65.0	64.5	63.1	63.4	63.1	64.5	65.0	66.2	67.1	69.0	69.9
72.5°	54.8	54.3	54.0	53.7	54.0	54.3	54.8	55.9	56.8	58.9	60.4
75°	43.3	43.1	42.9	43.8	42.9	43.1	43.3	43.6	43.8	44.5	45.2
77.5°	34.7	34.7	34.9	34.5	34.9	34.7	34.7	34.7	34.7	35.1	35.2
80°	29.1	29.1	28.9	28.9	28.9	29.1	29.1	29.1	29.1	29.1	28.9
82.5°	23.3	23.5	23.7	23.3	23.7	23.5	23.3	23.7	23.9	23.5	23.7
85°	15.4	15.1	15.6	15.4	15.6	15.1	15.4	15.4	14.9	15.4	15.1
87.5°	10.1	9.8	9.9	10.0	9.9	9.8	10.1	9.8	9.6	9.5	9.2
90°	16.0	16.5	17.1	16.5	17.1	16.5	16.0	16.5	15.4	14.8	14.3
92.5°	29.7	27.9	28.5	27.5	28.5	27.9	29.7	30.7	33.7	38.1	48.0
95°	77.6	72.4	68.4	66.2	68.4	72.4	77.6	88.4	108.9	139.2	205.3
97.5°	226.1	200.4	185.0	180.1	185.0	200.4	226.1	268.2	336.4	410.0	511.9
100°	420.9	379.3	357.1	357.6	357.1	379.3	420.9	478.5	559.5	626.3	672.5
102.5°	589.3	556.3	537.7	524.6	537.7	556.3	589.3	634.1	685.5	724.4	725.9
105°	768.3	746.6	728.4	725.5	728.4	746.6	768.3	794.5	809.4	798.5	741.5
107.5°	859.9	852.6	846.4	841.2	846.4	852.6	859.9	859.4	839.1	789.2	696.5
110°	886.4	890.9	889.8	888.6	889.8	890.9	886.4	870.4	830.5	758.6	653.6



TEST NUMBER: P332248

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	879.5	893.7	898.0	898.2	898.0	893.7	879.5	850.3	799.0	718.4	611.2
115°	843.0	868.1	879.5	882.4	879.5	868.1	843.0	800.2	738.1	654.2	555.0
117.5°	782.9	811.6	828.1	831.9	828.1	811.6	782.9	738.3	675.2	599.9	514.2
120°	740.9	772.9	786.5	790.0	786.5	772.9	740.9	695.9	638.2	569.8	492.8
122.5°	702.6	731.3	746.4	750.7	746.4	731.3	702.6	662.5	609.0	545.6	475.9
125°	652.5	677.6	691.9	695.9	691.9	677.6	652.5	616.0	570.4	515.6	453.4
127.5°	612.7	634.1	647.0	650.7	647.0	634.1	612.7	580.2	538.7	489.3	433.8
130°	588.1	608.6	620.6	625.1	620.6	608.6	588.1	557.8	519.0	472.8	421.5
132.5°	565.7	586.2	596.8	600.0	596.8	586.2	565.7	537.3	500.3	457.3	410.1
135°	532.7	549.8	560.1	564.1	560.1	549.8	532.7	504.8	472.3	435.2	394.7
137.5°	497.5	514.8	523.5	526.1	523.5	514.8	497.5	474.0	445.8	413.9	380.7
140°	475.1	491.1	500.2	499.6	500.2	491.1	475.1	453.4	428.9	401.5	372.5
142.5°	453.2	467.4	475.6	475.0	475.6	467.4	453.2	434.7	413.4	389.7	364.7
145°	423.2	435.2	439.8	440.9	439.8	435.2	423.2	409.0	392.4	374.2	355.3
147.5°	399.9	408.0	412.4	412.8	412.4	408.0	399.9	389.1	377.4	362.6	347.7
150°	386.7	393.0	396.4	396.4	396.4	393.0	386.7	378.2	367.3	355.3	342.2
152.5°	374.8	380.7	382.7	382.7	382.7	380.7	374.8	368.1	359.1	348.5	337.2
155°	359.3	363.9	365.0	365.6	365.0	363.9	359.3	354.2	347.4	338.8	329.7
157.5°	345.8	349.2	350.1	350.0	350.1	349.2	345.8	341.3	336.0	329.3	321.7
160°	337.1	340.5	340.5	339.9	340.5	340.5	337.1	333.1	329.1	323.4	317.1
162.5°	328.4	331.4	331.4	330.8	331.4	331.4	328.4	325.8	322.3	317.0	311.7
165°	317.1	319.4	318.8	318.8	318.8	319.4	317.1	314.8	312.0	308.0	304.6
167.5°	306.4	308.0	307.4	307.4	307.4	308.0	306.4	305.4	303.3	301.0	298.4
170°	300.0	301.2	300.6	300.6	300.6	301.2	300.0	299.4	298.3	296.0	294.3
172.5°	294.5	295.7	294.7	294.2	294.7	295.7	294.5	294.4	293.7	291.9	290.7
175°	287.5	288.0	287.5	286.9	287.5	288.0	287.5	287.5	287.5	286.3	285.8
177.5°	283.1	283.6	282.7	282.7	282.7	283.6	283.1	283.6	283.6	283.1	282.7
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332248

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	519.5	522.1	524.7	527.1	530.8	532.5	534.9	535.9	538.6	542.7	546.1
5°	487.9	491.6	496.5	500.4	506.7	511.6	517.0	522.1	528.2	536.8	544.5
7.5°	461.1	464.7	470.6	478.0	484.9	491.9	499.2	506.2	514.8	527.2	539.4
10°	443.4	447.8	454.8	462.7	471.3	478.1	486.7	495.5	506.3	520.5	535.2
12.5°	428.1	431.4	439.5	447.0	456.8	465.4	473.8	484.2	496.4	511.5	529.2
15°	403.8	408.4	416.3	424.7	435.0	444.1	455.0	467.6	479.5	498.1	519.5
17.5°	379.3	386.4	394.7	404.1	411.7	424.3	436.1	449.0	463.7	483.4	507.0
20°	363.7	369.3	377.0	390.7	400.7	410.3	421.2	437.3	450.8	473.2	497.6
22.5°	350.4	354.5	363.2	374.5	386.2	397.2	408.4	423.7	440.4	461.6	488.1
25°	330.8	337.4	343.9	352.0	364.6	377.9	390.0	403.1	420.8	443.4	472.0
27.5°	311.7	317.6	324.0	334.0	343.6	356.0	368.7	383.6	402.6	426.5	455.6
30°	299.4	303.8	309.9	322.7	331.3	342.0	356.9	370.2	387.9	413.3	444.1
32.5°	286.7	292.4	299.1	308.9	319.6	329.7	343.3	357.7	375.8	400.8	432.3
35°	268.6	275.4	282.1	289.4	300.1	310.6	322.0	337.8	356.2	380.5	411.4
37.5°	252.0	257.4	262.9	271.9	282.0	292.0	302.7	318.3	335.6	361.8	390.2
40°	241.4	246.3	250.5	259.8	269.6	280.3	290.8	304.5	323.1	347.6	375.1
42.5°	229.8	234.3	240.0	247.7	258.2	267.2	277.7	290.7	308.2	333.1	357.2
45°	212.5	217.6	222.5	229.7	240.2	249.1	258.4	270.7	288.7	309.2	330.6
47.5°	194.4	199.6	205.2	212.2	221.3	230.3	239.6	250.5	266.9	287.0	301.5
50°	182.9	187.1	192.7	199.7	208.1	217.6	226.0	237.9	253.5	269.3	281.9
52.5°	171.0	174.8	181.1	188.5	196.3	204.6	213.5	223.7	237.8	252.7	262.7
55°	152.4	157.0	162.4	169.6	177.3	184.3	192.9	203.4	214.6	225.8	232.5
57.5°	135.0	138.9	143.4	150.8	157.5	165.8	173.6	181.7	192.1	200.5	204.9
60°	122.3	125.8	131.6	138.2	144.4	151.7	160.5	168.7	176.6	183.4	186.8
62.5°	110.4	114.4	119.5	125.5	132.3	139.2	146.9	153.8	160.8	166.6	169.0
65°	94.8	98.1	101.8	107.4	113.0	120.0	126.0	133.0	138.2	141.4	143.5
67.5°	80.7	82.8	85.6	89.4	94.9	101.0	106.8	112.3	116.6	118.8	120.7
70°	71.5	72.9	75.0	78.7	82.9	88.3	94.4	98.3	102.0	103.9	105.8
72.5°	62.4	64.2	66.1	69.1	72.5	76.4	80.8	85.6	87.7	89.9	91.0
75°	47.3	49.9	52.4	54.3	56.6	59.6	63.6	66.6	67.8	69.7	69.9
77.5°	35.7	36.3	38.1	40.4	42.4	44.6	47.1	49.8	50.4	51.3	52.0
80°	29.4	29.4	29.4	30.8	33.1	34.7	37.0	38.4	39.4	39.6	39.8
82.5°	23.6	23.6	23.4	23.7	24.5	25.4	27.5	29.1	29.9	29.7	29.2
85°	15.4	14.9	14.9	14.7	14.9	14.4	14.2	15.1	16.5	16.5	16.1
87.5°	9.1	9.0	8.8	8.3	7.8	7.3	6.5	6.4	6.1	6.6	6.2
90°	13.7	14.3	12.5	10.8	9.1	7.4	6.3	5.1	3.4	2.3	1.1
92.5°	66.2	87.7	96.5	72.4	47.9	33.0	24.5	19.7	15.3	10.5	7.1
95°	274.3	338.2	301.2	207.6	122.6	74.1	51.9	37.1	27.4	21.1	19.4
97.5°	560.8	524.2	383.7	227.8	132.0	85.7	61.6	47.0	38.6	33.7	33.1
100°	652.5	540.1	365.0	215.0	130.6	90.7	68.4	54.8	46.8	42.8	42.2
102.5°	657.1	510.5	337.7	204.1	132.4	96.6	76.2	63.9	56.4	52.8	51.8
105°	622.3	458.6	304.0	196.2	137.5	106.7	89.0	78.1	71.3	67.9	66.2
107.5°	561.4	412.7	282.6	195.6	146.8	119.8	103.4	93.2	86.5	83.2	81.4
110°	523.0	386.7	274.3	197.9	154.6	128.9	112.9	103.2	97.0	94.1	92.4



TEST NUMBER: P332248

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	489.7	369.4	269.8	202.5	162.3	138.5	123.0	113.3	107.0	104.2	102.4
115°	449.5	350.8	268.1	209.9	175.1	153.4	138.0	128.3	122.6	119.2	116.9
117.5°	425.2	339.8	269.1	219.7	188.7	167.2	153.0	142.1	136.9	134.0	131.4
120°	412.4	334.8	270.9	227.0	197.3	176.8	162.6	151.7	146.0	143.2	141.5
122.5°	401.9	331.6	274.1	233.9	206.5	186.4	171.2	160.8	154.7	151.8	150.1
125°	388.4	327.4	278.9	244.7	219.6	199.6	184.2	173.4	167.1	163.7	162.6
127.5°	376.6	325.3	284.4	253.6	231.0	211.7	196.3	184.3	178.0	173.7	172.0
130°	370.2	324.0	288.0	259.5	237.8	219.0	203.6	191.6	184.8	179.7	178.0
132.5°	364.2	323.5	290.8	265.0	243.8	225.4	210.5	198.5	190.3	184.7	182.5
135°	356.5	322.8	294.9	272.1	252.7	235.0	219.6	207.6	199.1	192.8	190.5
137.5°	349.8	321.6	297.6	277.3	258.8	241.8	227.6	215.7	206.6	200.4	198.0
140°	345.6	321.1	299.4	280.1	262.9	246.4	232.1	220.7	211.6	205.9	203.1
142.5°	342.0	320.2	300.8	282.8	266.1	250.1	236.7	225.3	217.1	210.9	208.5
145°	337.1	318.8	301.7	285.8	270.4	255.5	242.4	232.7	224.2	219.0	217.3
147.5°	332.3	316.7	301.7	287.6	273.8	260.2	249.0	239.7	232.3	227.2	226.2
150°	329.1	314.8	301.7	288.0	276.1	262.9	252.7	244.7	237.3	232.7	232.1
152.5°	325.5	312.6	300.4	289.0	277.4	266.1	256.3	249.3	242.8	238.2	238.1
155°	320.0	308.6	298.9	289.2	280.1	270.4	262.4	256.1	250.4	247.0	247.0
157.5°	313.8	305.0	296.9	289.8	281.5	273.8	267.6	262.3	257.2	254.5	254.0
160°	309.7	302.3	296.0	289.8	282.9	276.1	270.4	266.4	261.8	259.5	259.5
162.5°	305.6	299.6	294.2	289.3	283.4	277.4	272.6	269.1	265.5	263.6	263.6
165°	300.0	295.5	291.5	288.0	284.0	279.5	275.5	273.2	270.4	269.2	269.8
167.5°	294.7	291.3	288.7	287.1	283.9	280.6	278.1	276.5	274.3	273.8	274.5
170°	291.5	288.6	286.9	285.8	283.5	280.6	279.5	278.3	276.6	276.1	277.2
172.5°	288.3	286.3	285.5	285.3	283.5	281.1	280.4	279.7	278.5	278.3	279.0
175°	284.6	283.5	283.5	284.0	282.9	281.8	281.2	281.2	280.1	280.6	281.2
177.5°	282.2	281.8	282.2	283.1	282.2	281.8	281.8	281.8	281.3	281.8	282.2
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332248

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	547.2	549.3	551.9	555.8	558.8	561.4	561.9	562.7	564.6	567.7	570.1
5°	550.8	556.1	564.7	573.1	582.2	589.7	596.7	601.6	606.2	616.0	623.9
7.5°	549.6	561.6	575.1	590.1	605.4	620.1	633.8	646.1	658.3	672.6	688.8
10°	548.9	562.9	581.1	600.4	621.6	642.3	662.4	678.0	696.1	712.5	733.2
12.5°	545.4	565.5	587.2	611.9	638.0	661.9	688.3	709.8	730.6	754.2	778.3
15°	540.7	565.2	592.7	625.5	665.2	694.0	721.1	758.6	784.2	809.8	844.3
17.5°	532.3	562.2	596.5	639.2	672.2	711.1	751.7	781.4	815.9	852.0	883.2
20°	525.6	560.3	598.8	640.7	682.9	725.0	764.4	799.8	835.5	877.2	902.8
22.5°	518.9	553.2	593.2	637.7	683.0	727.5	772.0	813.6	853.7	895.8	928.5
25°	504.6	545.4	588.7	634.2	678.9	727.8	780.9	827.3	876.9	920.3	951.3
27.5°	490.2	527.6	570.7	616.8	666.5	724.3	786.8	839.5	889.2	920.3	930.0
30°	477.1	516.7	556.4	603.2	657.0	721.5	787.9	848.3	889.0	902.6	892.5
32.5°	463.9	499.8	539.0	587.0	644.1	714.6	789.4	843.1	867.6	857.3	816.5
35°	440.6	472.9	510.9	558.9	624.6	710.8	783.3	819.6	813.6	755.3	678.4
37.5°	415.6	442.0	477.1	527.3	604.4	695.7	756.8	762.2	709.7	620.3	531.5
40°	395.8	419.6	455.7	508.1	588.7	680.8	730.2	708.5	627.2	527.7	453.6
42.5°	376.6	396.7	431.5	488.0	573.8	660.4	690.5	643.3	549.5	455.4	388.0
45°	344.1	363.0	397.9	455.9	543.3	621.6	617.6	535.6	441.7	366.0	310.1
47.5°	313.3	329.8	362.6	421.8	507.5	563.3	526.3	439.0	359.4	298.6	258.7
50°	291.5	307.8	340.4	398.9	478.8	519.5	466.7	382.6	309.6	259.3	227.6
52.5°	270.6	286.5	316.3	373.3	444.1	468.5	411.7	333.7	272.9	229.5	202.3
55°	241.4	253.5	280.3	334.8	387.7	393.3	335.7	270.5	220.4	190.1	171.5
57.5°	211.6	222.0	248.5	291.9	329.0	326.1	271.6	215.1	181.4	158.9	145.4
60°	192.2	202.5	225.8	263.0	291.0	281.2	231.1	185.7	156.8	140.3	129.5
62.5°	174.1	182.1	204.0	231.2	251.3	240.2	197.6	160.0	137.0	123.1	114.6
65°	147.9	154.5	171.9	186.2	197.3	186.6	151.2	125.1	108.6	98.8	93.0
67.5°	123.1	127.2	138.2	143.4	151.3	139.5	113.7	96.2	86.8	78.6	74.5
70°	107.4	110.4	116.3	120.5	122.5	110.4	91.3	78.5	70.6	64.8	62.2
72.5°	91.7	94.4	95.6	99.0	97.9	86.6	73.4	63.2	57.5	53.6	50.3
75°	70.1	71.3	70.1	68.7	65.7	57.8	48.7	43.6	39.4	37.5	36.3
77.5°	51.1	50.7	49.2	47.0	41.8	36.8	31.9	30.2	28.4	27.4	27.0
80°	39.4	38.4	37.0	33.5	29.1	25.6	24.5	23.3	22.6	21.4	21.2
82.5°	29.3	28.7	26.4	23.5	20.4	18.7	17.8	17.3	16.6	16.0	16.0
85°	15.6	14.9	12.3	10.7	10.3	9.8	9.6	9.6	8.6	8.4	8.4
87.5°	5.5	4.6	4.8	4.4	4.7	4.6	5.1	5.1	5.3	5.3	5.1
90°	2.3	3.4	5.1	6.3	7.4	9.1	10.8	12.5	14.3	13.7	14.3
92.5°	10.5	15.3	19.7	24.5	33.0	47.9	72.4	96.5	87.7	66.2	48.0
95°	21.1	27.4	37.1	51.9	74.1	122.6	207.6	301.2	338.2	274.3	205.3
97.5°	33.7	38.6	47.0	61.6	85.7	132.0	227.8	383.7	524.2	560.8	511.9
100°	42.8	46.8	54.8	68.4	90.7	130.6	215.0	365.0	540.1	652.5	672.5
102.5°	52.8	56.4	63.9	76.2	96.6	132.4	204.1	337.7	510.5	657.1	725.9
105°	67.9	71.3	78.1	89.0	106.7	137.5	196.2	304.0	458.6	622.3	741.5
107.5°	83.2	86.5	93.2	103.4	119.8	146.8	195.6	282.6	412.7	561.4	696.5
110°	94.1	97.0	103.2	112.9	128.9	154.6	197.9	274.3	386.7	523.0	653.6



TEST NUMBER: P332248

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	104.2	107.0	113.3	123.0	138.5	162.3	202.5	269.8	369.4	489.7	611.2
115°	119.2	122.6	128.3	138.0	153.4	175.1	209.9	268.1	350.8	449.5	555.0
117.5°	134.0	136.9	142.1	153.0	167.2	188.7	219.7	269.1	339.8	425.2	514.2
120°	143.2	146.0	151.7	162.6	176.8	197.3	227.0	270.9	334.8	412.4	492.8
122.5°	151.8	154.7	160.8	171.2	186.4	206.5	233.9	274.1	331.6	401.9	475.9
125°	163.7	167.1	173.4	184.2	199.6	219.6	244.7	278.9	327.4	388.4	453.4
127.5°	173.7	178.0	184.3	196.3	211.7	231.0	253.6	284.4	325.3	376.6	433.8
130°	179.7	184.8	191.6	203.6	219.0	237.8	259.5	288.0	324.0	370.2	421.5
132.5°	184.7	190.3	198.5	210.5	225.4	243.8	265.0	290.8	323.5	364.2	410.1
135°	192.8	199.1	207.6	219.6	235.0	252.7	272.1	294.9	322.8	356.5	394.7
137.5°	200.4	206.6	215.7	227.6	241.8	258.8	277.3	297.6	321.6	349.8	380.7
140°	205.9	211.6	220.7	232.1	246.4	262.9	280.1	299.4	321.1	345.6	372.5
142.5°	210.9	217.1	225.3	236.7	250.1	266.1	282.8	300.8	320.2	342.0	364.7
145°	219.0	224.2	232.7	242.4	255.5	270.4	285.8	301.7	318.8	337.1	355.3
147.5°	227.2	232.3	239.7	249.0	260.2	273.8	287.6	301.7	316.7	332.3	347.7
150°	232.7	237.3	244.7	252.7	262.9	276.1	288.0	301.7	314.8	329.1	342.2
152.5°	238.2	242.8	249.3	256.3	266.1	277.4	289.0	300.4	312.6	325.5	337.2
155°	247.0	250.4	256.1	262.4	270.4	280.1	289.2	298.9	308.6	320.0	329.7
157.5°	254.5	257.2	262.3	267.6	273.8	281.5	289.8	296.9	305.0	313.8	321.7
160°	259.5	261.8	266.4	270.4	276.1	282.9	289.8	296.0	302.3	309.7	317.1
162.5°	263.6	265.5	269.1	272.6	277.4	283.4	289.3	294.2	299.6	305.6	311.7
165°	269.2	270.4	273.2	275.5	279.5	284.0	288.0	291.5	295.5	300.0	304.6
167.5°	273.8	274.3	276.5	278.1	280.6	283.9	287.1	288.7	291.3	294.7	298.4
170°	276.1	276.6	278.3	279.5	280.6	283.5	285.8	286.9	288.6	291.5	294.3
172.5°	278.3	278.5	279.7	280.4	281.1	283.5	285.3	285.5	286.3	288.3	290.7
175°	280.6	280.1	281.2	281.2	281.8	282.9	284.0	283.5	283.5	284.6	285.8
177.5°	281.8	281.3	281.8	281.8	281.8	282.2	283.1	282.2	281.8	282.2	282.7
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332248

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	574.1	574.1	574.8	577.6	578.0	580.4	579.7
5°	630.9	635.3	637.0	644.0	648.1	650.0	646.3
7.5°	700.4	712.9	718.8	726.2	732.6	734.6	729.5
10°	751.1	764.2	775.1	781.9	788.2	792.4	797.7
12.5°	800.1	816.2	826.6	836.1	842.6	847.9	848.8
15°	853.4	877.6	896.0	909.6	916.3	919.8	918.4
17.5°	907.1	929.6	942.7	956.5	965.8	966.3	966.6
20°	937.5	959.4	974.6	984.8	995.3	994.8	997.2
22.5°	957.8	975.1	986.7	994.1	997.7	995.9	996.4
25°	967.3	972.5	970.4	958.5	955.4	944.5	946.4
27.5°	918.3	894.1	869.0	836.8	811.3	791.0	792.0
30°	851.8	808.9	760.0	719.0	682.2	671.9	650.0
32.5°	758.8	694.5	637.2	598.9	567.4	558.8	539.7
35°	601.1	538.6	479.7	444.3	430.3	410.7	410.5
37.5°	467.2	412.2	381.1	354.5	340.6	328.7	327.6
40°	393.0	350.2	326.6	307.5	293.8	284.9	282.8
42.5°	341.2	306.6	284.5	272.7	262.1	257.5	254.1
45°	278.6	255.3	240.0	229.3	224.4	220.9	219.0
47.5°	233.1	217.5	207.0	199.8	195.9	192.2	193.2
50°	208.3	195.5	187.8	181.0	178.0	175.4	175.7
52.5°	188.3	176.8	170.6	165.7	162.0	160.1	159.3
55°	159.8	152.6	146.3	142.8	140.7	138.2	137.5
57.5°	136.3	130.7	125.6	121.7	121.1	118.7	119.0
60°	120.7	116.0	111.8	109.7	108.1	106.0	106.7
62.5°	107.8	103.9	100.1	98.4	96.7	95.2	95.5
65°	88.3	84.6	82.2	81.3	80.6	79.9	79.2
67.5°	70.4	68.1	66.6	64.6	63.2	63.0	62.3
70°	59.2	56.1	53.6	51.0	50.3	50.1	50.3
72.5°	47.4	45.5	44.8	43.6	43.4	42.8	43.2
75°	35.6	34.9	34.5	33.5	33.5	33.5	33.5
77.5°	26.3	25.9	25.6	25.4	25.2	24.8	24.8
80°	20.5	20.3	19.8	19.8	19.6	19.8	19.6
82.5°	15.5	15.4	15.0	15.0	14.7	14.6	14.7
85°	7.9	7.7	8.2	7.7	7.9	7.5	7.9
87.5°	5.2	5.3	5.4	5.2	5.2	5.7	5.2
90°	14.8	15.4	16.5	16.0	16.5	17.1	16.5
92.5°	38.1	33.7	30.7	29.7	27.9	28.5	27.5
95°	139.2	108.9	88.4	77.6	72.4	68.4	66.2
97.5°	410.0	336.4	268.2	226.1	200.4	185.0	180.1
100°	626.3	559.5	478.5	420.9	379.3	357.1	357.6
102.5°	724.4	685.5	634.1	589.3	556.3	537.7	524.6
105°	798.5	809.4	794.5	768.3	746.6	728.4	725.5
107.5°	789.2	839.1	859.4	859.9	852.6	846.4	841.2
110°	758.6	830.5	870.4	886.4	890.9	889.8	888.6



TEST NUMBER: P332248

CATALOG NUMBER: S123RDIP-S340D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	718.4	799.0	850.3	879.5	893.7	898.0	898.2
115°	654.2	738.1	800.2	843.0	868.1	879.5	882.4
117.5°	599.9	675.2	738.3	782.9	811.6	828.1	831.9
120°	569.8	638.2	695.9	740.9	772.9	786.5	790.0
122.5°	545.6	609.0	662.5	702.6	731.3	746.4	750.7
125°	515.6	570.4	616.0	652.5	677.6	691.9	695.9
127.5°	489.3	538.7	580.2	612.7	634.1	647.0	650.7
130°	472.8	519.0	557.8	588.1	608.6	620.6	625.1
132.5°	457.3	500.3	537.3	565.7	586.2	596.8	600.0
135°	435.2	472.3	504.8	532.7	549.8	560.1	564.1
137.5°	413.9	445.8	474.0	497.5	514.8	523.5	526.1
140°	401.5	428.9	453.4	475.1	491.1	500.2	499.6
142.5°	389.7	413.4	434.7	453.2	467.4	475.6	475.0
145°	374.2	392.4	409.0	423.2	435.2	439.8	440.9
147.5°	362.6	377.4	389.1	399.9	408.0	412.4	412.8
150°	355.3	367.3	378.2	386.7	393.0	396.4	396.4
152.5°	348.5	359.1	368.1	374.8	380.7	382.7	382.7
155°	338.8	347.4	354.2	359.3	363.9	365.0	365.6
157.5°	329.3	336.0	341.3	345.8	349.2	350.1	350.0
160°	323.4	329.1	333.1	337.1	340.5	340.5	339.9
162.5°	317.0	322.3	325.8	328.4	331.4	331.4	330.8
165°	308.0	312.0	314.8	317.1	319.4	318.8	318.8
167.5°	301.0	303.3	305.4	306.4	308.0	307.4	307.4
170°	296.0	298.3	299.4	300.0	301.2	300.6	300.6
172.5°	291.9	293.7	294.4	294.5	295.7	294.7	294.2
175°	286.3	287.5	287.5	287.5	288.0	287.5	286.9
177.5°	283.1	283.6	283.6	283.1	283.6	282.7	282.7
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8

(END OF REPORT)