

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332254

Luminaire Tested: **S123RDIP-S340D805U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332254
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D805U835-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4263.8 lumens
Efficiency: N/A
Efficacy: 136.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332254

CATALOG NUMBER: S123RDIP-S340D805U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332254

CATALOG NUMBER: S123RDIP-S340D805U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	39	39	39	32
1	94	90	86	83	85	81	78	75	65	63	61	49	48	47	35	35	34	28
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	30	29	24
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	28	27	25	20
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	26	24	22	18
5	66	55	47	42	59	50	43	38	40	36	32	31	28	26	23	21	19	16
6	61	49	42	36	55	45	38	33	36	32	28	28	25	22	21	19	17	14
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15	13
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14	11
9	49	37	30	25	44	34	27	23	28	23	20	22	18	16	16	14	13	10
10	45	34	27	22	41	31	25	21	25	21	18	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5858	5858	5858	5858
5°	6983	5883	5181	5883
10°	8719	5850	4680	5850
15°	10234	5789	4268	5789
20°	11423	5700	3918	5700
25°	11240	5606	3702	5606
30°	8079	5520	3480	5520
35°	5394	5406	3336	5406
40°	3974	5271	3188	5271
45°	3334	5033	3043	5033
50°	2942	4721	2840	4721
55°	2580	4363	2562	4363
60°	2297	4021	2347	4021
65°	2017	3655	2183	3655
70°	1583	3330	1995	3330
75°	1393	2907	1822	2907
80°	1215	2467	1791	2467
85°	976	1988	1902	1988



TEST NUMBER: P332254

CATALOG NUMBER: S123RDIP-S340D805U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.5	1.3
10°-20°	167.2	3.9
20°-30°	262.7	6.2
30°-40°	274.1	6.4
40°-50°	234.5	5.5
50°-60°	178.8	4.2
60°-70°	114.6	2.7
70°-80°	55.1	1.3
80°-90°	17.6	0.4
90°-100°	214.9	5.0
100°-110°	608.6	14.3
110°-120°	598.7	14.0
120°-130°	477.5	11.2
130°-140°	376.5	8.8
140°-150°	281.0	6.6
150°-160°	195.9	4.6
160°-170°	115.1	2.7
170°-180°	37.4	0.9
0°-30°	483.4	11.3
0°-40°	757.5	17.8
0°-60°	1170.8	27.5
0°-90°	1358.1	31.9
90°-120°	1422.2	33.4
90°-150°	2557.3	60.0
90°-180°	2906.0	68.2
0°-180°	4263.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	544	544	544	544	544	
5°	646	544	480	544	646	67
15°	918	520	383	520	918	260
25°	946	472	312	472	946	407
35°	410	411	254	411	410	269
45°	219	331	200	331	219	172
55°	138	232	136	232	138	124
65°	79	144	86	144	79	78
75°	34	70	44	70	34	36
85°	8	16	15	16	8	10
90°	23	2	23	2	23	12
95°	91	27	91	27	91	163
105°	994	91	994	91	994	981
115°	1210	160	1210	160	1210	1175
125°	954	223	954	223	954	864
135°	773	261	773	261	773	600
145°	604	298	604	298	604	384
155°	501	338	501	338	501	234
165°	437	370	437	370	437	125
175°	393	385	393	385	393	38
180°	386	386	386	386	386	



TEST NUMBER: P332254

CATALOG NUMBER: S123RDIP-S340D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	579.7	580.4	578.0	577.6	574.8	574.1	574.1	570.1	567.7	564.6	562.7
5°	646.3	650.0	648.1	644.0	637.0	635.3	630.9	623.9	616.0	606.2	601.6
7.5°	729.5	734.6	732.6	726.2	718.8	712.9	700.4	688.8	672.6	658.3	646.1
10°	797.7	792.4	788.2	781.9	775.1	764.2	751.1	733.2	712.5	696.1	678.0
12.5°	848.8	847.9	842.6	836.1	826.6	816.2	800.1	778.3	754.2	730.6	709.8
15°	918.4	919.8	916.3	909.6	896.0	877.6	853.4	844.3	809.8	784.2	758.6
17.5°	966.6	966.3	965.8	956.5	942.7	929.6	907.1	883.2	852.0	815.9	781.4
20°	997.2	994.8	995.3	984.8	974.6	959.4	937.5	902.8	877.2	835.5	799.8
22.5°	996.4	995.9	997.7	994.1	986.7	975.1	957.8	928.5	895.8	853.7	813.6
25°	946.4	944.5	955.4	958.5	970.4	972.5	967.3	951.3	920.3	876.9	827.3
27.5°	792.0	791.0	811.3	836.8	869.0	894.1	918.3	930.0	920.3	889.2	839.5
30°	650.0	671.9	682.2	719.0	760.0	808.9	851.8	892.5	902.6	889.0	848.3
32.5°	539.7	558.8	567.4	598.9	637.2	694.5	758.8	816.5	857.3	867.6	843.1
35°	410.5	410.7	430.3	444.3	479.7	538.6	601.1	678.4	755.3	813.6	819.6
37.5°	327.6	328.7	340.6	354.5	381.1	412.2	467.2	531.5	620.3	709.7	762.2
40°	282.8	284.9	293.8	307.5	326.6	350.2	393.0	453.6	527.7	627.2	708.5
42.5°	254.1	257.5	262.1	272.7	284.5	306.6	341.2	388.0	455.4	549.5	643.3
45°	219.0	220.9	224.4	229.3	240.0	255.3	278.6	310.1	366.0	441.7	535.6
47.5°	193.2	192.2	195.9	199.8	207.0	217.5	233.1	258.7	298.6	359.4	439.0
50°	175.7	175.4	178.0	181.0	187.8	195.5	208.3	227.6	259.3	309.6	382.6
52.5°	159.3	160.1	162.0	165.7	170.6	176.8	188.3	202.3	229.5	272.9	333.7
55°	137.5	138.2	140.7	142.8	146.3	152.6	159.8	171.5	190.1	220.4	270.5
57.5°	119.0	118.7	121.1	121.7	125.6	130.7	136.3	145.4	158.9	181.4	215.1
60°	106.7	106.0	108.1	109.7	111.8	116.0	120.7	129.5	140.3	156.8	185.7
62.5°	95.5	95.2	96.7	98.4	100.1	103.9	107.8	114.6	123.1	137.0	160.0
65°	79.2	79.9	80.6	81.3	82.2	84.6	88.3	93.0	98.8	108.6	125.1
67.5°	62.3	63.0	63.2	64.6	66.6	68.1	70.4	74.5	78.6	86.8	96.2
70°	50.3	50.1	50.3	51.0	53.6	56.1	59.2	62.2	64.8	70.6	78.5
72.5°	43.2	42.8	43.4	43.6	44.8	45.5	47.4	50.3	53.6	57.5	63.2
75°	33.5	33.5	33.5	33.5	34.5	34.9	35.6	36.3	37.5	39.4	43.6
77.5°	24.8	24.8	25.2	25.4	25.6	25.9	26.3	27.0	27.4	28.4	30.2
80°	19.6	19.8	19.6	19.8	19.8	20.3	20.5	21.2	21.4	22.6	23.3
82.5°	14.7	14.6	14.7	15.0	15.0	15.4	15.5	16.0	16.0	16.6	17.3
85°	7.9	7.5	7.9	7.7	8.2	7.7	7.9	8.4	8.4	8.6	9.6
87.5°	6.4	6.9	6.4	6.4	6.6	6.5	6.3	6.1	6.4	6.3	6.0
90°	22.7	23.5	22.7	21.9	22.7	21.1	20.3	19.5	18.8	19.5	17.2
92.5°	37.7	39.1	38.3	40.7	42.1	46.1	52.2	65.8	90.7	120.2	132.3
95°	90.7	93.8	99.3	106.3	121.2	149.3	190.8	281.5	376.1	463.6	412.8
97.5°	246.9	253.6	274.7	309.9	367.6	461.1	562.0	701.6	768.7	718.5	526.0
100°	490.2	489.4	519.9	577.0	655.9	767.0	858.4	921.8	894.4	740.4	500.4
102.5°	719.1	737.1	762.6	807.8	869.2	939.6	992.9	994.9	900.7	699.7	462.8
105°	994.5	998.4	1023.4	1053.1	1089.1	1109.4	1094.5	1016.4	853.0	628.6	416.7
107.5°	1153.0	1160.2	1168.7	1178.7	1178.0	1150.2	1081.7	954.8	769.5	565.7	387.3
110°	1218.1	1219.6	1221.2	1214.9	1193.1	1138.3	1039.8	896.0	716.9	530.1	376.1



TEST NUMBER: P332254

CATALOG NUMBER: S123RDIP-S340D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1231.2	1230.9	1225.0	1205.6	1165.5	1095.2	984.8	837.8	671.3	506.3	369.8
115°	1209.5	1205.6	1189.9	1155.5	1096.9	1011.7	896.7	760.7	616.1	480.8	367.5
117.5°	1140.4	1135.0	1112.5	1073.1	1012.0	925.5	822.3	704.9	582.8	465.8	368.9
120°	1082.8	1078.1	1059.4	1015.6	953.8	874.9	781.0	675.5	565.3	458.9	371.4
122.5°	1029.0	1023.1	1002.4	963.0	908.2	834.8	747.9	652.4	550.9	454.6	375.7
125°	953.8	948.3	928.8	894.4	844.4	781.8	706.8	621.5	532.4	448.8	382.3
127.5°	891.9	886.9	869.2	839.8	795.3	738.4	670.6	594.7	516.2	446.0	389.8
130°	856.9	850.6	834.2	806.1	764.6	711.5	648.1	577.8	507.4	444.1	394.8
132.5°	822.5	818.1	803.6	775.4	736.5	685.8	626.9	562.1	499.3	443.4	398.6
135°	773.2	767.7	753.7	730.2	691.9	647.3	596.5	541.0	488.6	442.5	404.2
137.5°	721.2	717.6	705.7	681.9	649.7	611.1	567.3	521.8	479.4	440.8	408.0
140°	684.9	685.7	673.1	651.3	621.5	587.9	550.4	510.5	473.8	440.2	410.5
142.5°	651.1	651.9	640.6	621.2	595.9	566.7	534.1	499.9	468.8	438.9	412.3
145°	604.3	602.8	596.5	580.1	560.6	537.9	512.9	487.1	462.1	437.0	413.6
147.5°	565.9	565.3	559.3	548.2	533.4	517.3	497.1	476.6	455.5	434.1	413.6
150°	543.4	543.4	538.7	530.1	518.3	503.5	487.1	469.1	451.1	431.6	413.6
152.5°	524.6	524.6	521.8	513.8	504.6	492.2	477.7	462.2	446.1	428.4	411.7
155°	501.1	500.4	498.8	492.5	485.5	476.1	464.4	451.9	438.6	423.0	409.7
157.5°	479.7	479.9	478.6	473.9	467.8	460.5	451.4	440.9	430.2	418.1	407.0
160°	466.0	466.7	466.7	462.1	456.6	451.1	443.3	434.7	424.5	414.4	405.8
162.5°	453.5	454.2	454.2	450.2	446.6	441.7	434.5	427.2	418.9	410.6	403.3
165°	437.0	437.0	437.8	434.7	431.6	427.7	422.2	417.5	411.2	405.0	399.5
167.5°	421.4	421.4	422.2	420.0	418.6	415.8	412.6	409.0	403.9	399.4	395.8
170°	412.0	412.0	412.8	411.2	410.5	408.9	405.8	403.4	399.5	395.6	393.3
172.5°	403.3	403.9	405.3	403.7	403.6	402.6	400.1	398.4	395.1	392.5	391.4
175°	393.3	394.0	394.8	394.0	394.0	394.0	392.5	391.7	390.1	388.6	388.6
177.5°	387.5	387.5	388.7	388.1	388.7	388.7	388.1	387.5	386.8	386.2	386.8
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332254

CATALOG NUMBER: S123RDIP-S340D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	561.9	561.4	558.8	555.8	551.9	549.3	547.2	546.1	542.7	538.6	535.9
5°	596.7	589.7	582.2	573.1	564.7	556.1	550.8	544.5	536.8	528.2	522.1
7.5°	633.8	620.1	605.4	590.1	575.1	561.6	549.6	539.4	527.2	514.8	506.2
10°	662.4	642.3	621.6	600.4	581.1	562.9	548.9	535.2	520.5	506.3	495.5
12.5°	688.3	661.9	638.0	611.9	587.2	565.5	545.4	529.2	511.5	496.4	484.2
15°	721.1	694.0	665.2	625.5	592.7	565.2	540.7	519.5	498.1	479.5	467.6
17.5°	751.7	711.1	672.2	639.2	596.5	562.2	532.3	507.0	483.4	463.7	449.0
20°	764.4	725.0	682.9	640.7	598.8	560.3	525.6	497.6	473.2	450.8	437.3
22.5°	772.0	727.5	683.0	637.7	593.2	553.2	518.9	488.1	461.6	440.4	423.7
25°	780.9	727.8	678.9	634.2	588.7	545.4	504.6	472.0	443.4	420.8	403.1
27.5°	786.8	724.3	666.5	616.8	570.7	527.6	490.2	455.6	426.5	402.6	383.6
30°	787.9	721.5	657.0	603.2	556.4	516.7	477.1	444.1	413.3	387.9	370.2
32.5°	789.4	714.6	644.1	587.0	539.0	499.8	463.9	432.3	400.8	375.8	357.7
35°	783.3	710.8	624.6	558.9	510.9	472.9	440.6	411.4	380.5	356.2	337.8
37.5°	756.8	695.7	604.4	527.3	477.1	442.0	415.6	390.2	361.8	335.6	318.3
40°	730.2	680.8	588.7	508.1	455.7	419.6	395.8	375.1	347.6	323.1	304.5
42.5°	690.5	660.4	573.8	488.0	431.5	396.7	376.6	357.2	333.1	308.2	290.7
45°	617.6	621.6	543.3	455.9	397.9	363.0	344.1	330.6	309.2	288.7	270.7
47.5°	526.3	563.3	507.5	421.8	362.6	329.8	313.3	301.5	287.0	266.9	250.5
50°	466.7	519.5	478.8	398.9	340.4	307.8	291.5	281.9	269.3	253.5	237.9
52.5°	411.7	468.5	444.1	373.3	316.3	286.5	270.6	262.7	252.7	237.8	223.7
55°	335.7	393.3	387.7	334.8	280.3	253.5	241.4	232.5	225.8	214.6	203.4
57.5°	271.6	326.1	329.0	291.9	248.5	222.0	211.6	204.9	200.5	192.1	181.7
60°	231.1	281.2	291.0	263.0	225.8	202.5	192.2	186.8	183.4	176.6	168.7
62.5°	197.6	240.2	251.3	231.2	204.0	182.1	174.1	169.0	166.6	160.8	153.8
65°	151.2	186.6	197.3	186.2	171.9	154.5	147.9	143.5	141.4	138.2	133.0
67.5°	113.7	139.5	151.3	143.4	138.2	127.2	123.1	120.7	118.8	116.6	112.3
70°	91.3	110.4	122.5	120.5	116.3	110.4	107.4	105.8	103.9	102.0	98.3
72.5°	73.4	86.6	97.9	99.0	95.6	94.4	91.7	91.0	89.9	87.7	85.6
75°	48.7	57.8	65.7	68.7	70.1	71.3	70.1	69.9	69.7	67.8	66.6
77.5°	31.9	36.8	41.8	47.0	49.2	50.7	51.1	52.0	51.3	50.4	49.8
80°	24.5	25.6	29.1	33.5	37.0	38.4	39.4	39.8	39.6	39.4	38.4
82.5°	17.8	18.7	20.4	23.5	26.4	28.7	29.3	29.2	29.7	29.9	29.1
85°	9.6	9.8	10.3	10.7	12.3	14.9	15.6	16.1	16.5	16.5	15.1
87.5°	6.0	5.3	5.2	4.9	5.1	4.9	5.7	6.3	6.8	6.3	6.8
90°	14.9	12.5	10.2	8.6	7.0	4.7	3.1	1.6	3.1	4.7	7.0
92.5°	99.3	65.7	45.2	33.6	27.1	21.0	14.4	9.7	14.4	21.0	27.1
95°	284.6	168.1	101.6	71.1	50.8	37.5	28.9	26.6	28.9	37.5	50.8
97.5°	312.3	180.9	117.4	84.4	64.4	52.9	46.1	45.3	46.1	52.9	64.4
100°	294.7	179.0	124.3	93.8	75.1	64.1	58.6	57.9	58.6	64.1	75.1
102.5°	279.7	181.5	132.4	104.5	87.6	77.2	72.4	71.0	72.4	77.2	87.6
105°	268.9	188.4	146.2	122.0	107.1	97.7	93.0	90.7	93.0	97.7	107.1
107.5°	268.2	201.2	164.2	141.7	127.7	118.5	114.0	111.6	114.0	118.5	127.7
110°	271.3	211.9	176.7	154.8	141.5	132.9	129.0	126.7	129.0	132.9	141.5



TEST NUMBER: P332254

CATALOG NUMBER: S123RDIP-S340D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	277.5	222.5	189.8	168.6	155.3	146.7	142.8	140.4	142.8	146.7	155.3
115°	287.7	240.0	210.3	189.2	175.9	168.1	163.4	160.3	163.4	168.1	175.9
117.5°	301.2	258.6	229.2	209.7	194.8	187.6	183.7	180.1	183.7	187.6	194.8
120°	311.2	270.5	242.4	222.8	208.0	200.1	196.2	193.9	196.2	200.1	208.0
122.5°	320.5	283.0	255.5	234.7	220.5	212.0	208.1	205.8	208.1	212.0	220.5
125°	335.4	301.0	273.6	252.5	237.7	229.1	224.4	222.8	224.4	229.1	237.7
127.5°	347.6	316.6	290.2	269.1	252.7	243.9	238.1	235.8	238.1	243.9	252.7
130°	355.7	326.0	300.2	279.1	262.7	253.3	246.3	243.9	246.3	253.3	262.7
132.5°	363.2	334.1	309.0	288.5	272.1	260.8	253.2	250.2	253.2	260.8	272.1
135°	372.9	346.3	322.1	301.0	284.6	272.9	264.3	261.1	264.3	272.9	284.6
137.5°	380.1	354.8	331.5	311.9	295.7	283.2	274.7	271.4	274.7	283.2	295.7
140°	383.9	360.4	337.7	318.2	302.6	290.1	282.2	278.3	282.2	290.1	302.6
142.5°	387.6	364.8	342.7	324.5	308.8	297.6	289.1	285.8	289.1	297.6	308.8
145°	391.7	370.6	350.3	332.3	319.0	307.3	300.2	297.9	300.2	307.3	319.0
147.5°	394.2	375.3	356.7	341.3	328.5	318.4	311.5	310.1	311.5	318.4	328.5
150°	394.8	378.4	360.4	346.3	335.4	325.2	319.0	318.2	319.0	325.2	335.4
152.5°	396.1	380.3	364.8	351.3	341.7	332.7	326.5	326.3	326.5	332.7	341.7
155°	396.4	383.9	370.6	359.6	351.0	343.2	338.5	338.5	338.5	343.2	351.0
157.5°	397.2	385.9	375.3	366.8	359.5	352.6	348.8	348.2	348.8	352.6	359.5
160°	397.2	387.8	378.4	370.6	365.1	358.9	355.7	355.7	355.7	358.9	365.1
162.5°	396.5	388.4	380.3	373.7	368.9	363.9	361.4	361.4	361.4	363.9	368.9
165°	394.8	389.3	383.1	377.6	374.5	370.6	369.0	369.8	369.0	370.6	374.5
167.5°	393.6	389.2	384.7	381.2	379.0	376.1	375.3	376.2	375.3	376.1	379.0
170°	391.7	388.6	384.7	383.1	381.5	379.2	378.4	380.0	378.4	379.2	381.5
172.5°	391.1	388.6	385.3	384.3	383.4	381.7	381.5	382.5	381.5	381.7	383.4
175°	389.3	387.8	386.2	385.4	385.4	383.9	384.7	385.4	384.7	383.9	385.4
177.5°	388.1	386.8	386.2	386.2	386.2	385.6	386.2	386.8	386.2	385.6	386.2
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332254

CATALOG NUMBER: S123RDIP-S340D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	534.9	532.5	530.8	527.1	524.7	522.1	519.5	521.1	520.9	520.8	520.8
5°	517.0	511.6	506.7	500.4	496.5	491.6	487.9	487.4	488.3	485.1	483.2
7.5°	499.2	491.9	484.9	478.0	470.6	464.7	461.1	459.3	457.0	455.0	452.9
10°	486.7	478.1	471.3	462.7	454.8	447.8	443.4	440.3	438.7	437.1	434.0
12.5°	473.8	465.4	456.8	447.0	439.5	431.4	428.1	424.7	421.6	419.7	415.6
15°	455.0	444.1	435.0	424.7	416.3	408.4	403.8	397.0	396.1	393.7	389.5
17.5°	436.1	424.3	411.7	404.1	394.7	386.4	379.3	377.1	370.4	367.9	364.2
20°	421.2	410.3	400.7	390.7	377.0	369.3	363.7	360.7	355.3	352.0	349.7
22.5°	408.4	397.2	386.2	374.5	363.2	354.5	350.4	345.7	342.8	338.2	335.7
25°	390.0	377.9	364.6	352.0	343.9	337.4	330.8	326.6	322.4	320.3	315.7
27.5°	368.7	356.0	343.6	334.0	324.0	317.6	311.7	308.0	302.9	299.4	296.8
30°	356.9	342.0	331.3	322.7	309.9	303.8	299.4	294.7	291.0	287.3	284.7
32.5°	343.3	329.7	319.6	308.9	299.1	292.4	286.7	282.6	279.4	275.9	273.3
35°	322.0	310.6	300.1	289.4	282.1	275.4	268.6	265.1	262.1	258.8	256.5
37.5°	302.7	292.0	282.0	271.9	262.9	257.4	252.0	249.3	245.2	243.0	240.7
40°	290.8	280.3	269.6	259.8	250.5	246.3	241.4	237.4	233.7	232.0	229.5
42.5°	277.7	267.2	258.2	247.7	240.0	234.3	229.8	225.5	222.7	220.3	218.9
45°	258.4	249.1	240.2	229.7	222.5	217.6	212.5	208.5	206.0	204.3	201.8
47.5°	239.6	230.3	221.3	212.2	205.2	199.6	194.4	191.7	188.3	186.3	184.6
50°	226.0	217.6	208.1	199.7	192.7	187.1	182.9	179.4	176.4	173.8	172.6
52.5°	213.5	204.6	196.3	188.5	181.1	174.8	171.0	167.3	165.0	162.1	160.7
55°	192.9	184.3	177.3	169.6	162.4	157.0	152.4	149.1	146.8	143.5	141.7
57.5°	173.6	165.8	157.5	150.8	143.4	138.9	135.0	130.6	127.7	125.2	123.3
60°	160.5	151.7	144.4	138.2	131.6	125.8	122.3	118.8	115.8	113.2	111.6
62.5°	146.9	139.2	132.3	125.5	119.5	114.4	110.4	107.5	104.8	103.2	101.5
65°	126.0	120.0	113.0	107.4	101.8	98.1	94.8	92.3	90.4	89.2	87.8
67.5°	106.8	101.0	94.9	89.4	85.6	82.8	80.7	78.5	77.5	76.0	75.1
70°	94.4	88.3	82.9	78.7	75.0	72.9	71.5	69.9	69.0	67.1	66.2
72.5°	80.8	76.4	72.5	69.1	66.1	64.2	62.4	60.4	58.9	56.8	55.9
75°	63.6	59.6	56.6	54.3	52.4	49.9	47.3	45.2	44.5	43.8	43.6
77.5°	47.1	44.6	42.4	40.4	38.1	36.3	35.7	35.2	35.1	34.7	34.7
80°	37.0	34.7	33.1	30.8	29.4	29.4	29.4	28.9	29.1	29.1	29.1
82.5°	27.5	25.4	24.5	23.7	23.4	23.6	23.6	23.7	23.5	23.9	23.7
85°	14.2	14.4	14.9	14.7	14.9	14.9	15.4	15.1	15.4	14.9	15.4
87.5°	6.9	7.8	8.5	9.1	9.8	10.1	10.1	10.2	10.6	10.7	11.1
90°	8.6	10.2	12.5	14.9	17.2	19.5	18.8	19.5	20.3	21.1	22.7
92.5°	33.6	45.2	65.7	99.3	132.3	120.2	90.7	65.8	52.2	46.1	42.1
95°	71.1	101.6	168.1	284.6	412.8	463.6	376.1	281.5	190.8	149.3	121.2
97.5°	84.4	117.4	180.9	312.3	526.0	718.5	768.7	701.6	562.0	461.1	367.6
100°	93.8	124.3	179.0	294.7	500.4	740.4	894.4	921.8	858.4	767.0	655.9
102.5°	104.5	132.4	181.5	279.7	462.8	699.7	900.7	994.9	992.9	939.6	869.2
105°	122.0	146.2	188.4	268.9	416.7	628.6	853.0	1016.4	1094.5	1109.4	1089.1
107.5°	141.7	164.2	201.2	268.2	387.3	565.7	769.5	954.8	1081.7	1150.2	1178.0
110°	154.8	176.7	211.9	271.3	376.1	530.1	716.9	896.0	1039.8	1138.3	1193.1



TEST NUMBER: P332254

CATALOG NUMBER: S123RDIP-S340D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	168.6	189.8	222.5	277.5	369.8	506.3	671.3	837.8	984.8	1095.2	1165.5
115°	189.2	210.3	240.0	287.7	367.5	480.8	616.1	760.7	896.7	1011.7	1096.9
117.5°	209.7	229.2	258.6	301.2	368.9	465.8	582.8	704.9	822.3	925.5	1012.0
120°	222.8	242.4	270.5	311.2	371.4	458.9	565.3	675.5	781.0	874.9	953.8
122.5°	234.7	255.5	283.0	320.5	375.7	454.6	550.9	652.4	747.9	834.8	908.2
125°	252.5	273.6	301.0	335.4	382.3	448.8	532.4	621.5	706.8	781.8	844.4
127.5°	269.1	290.2	316.6	347.6	389.8	446.0	516.2	594.7	670.6	738.4	795.3
130°	279.1	300.2	326.0	355.7	394.8	444.1	507.4	577.8	648.1	711.5	764.6
132.5°	288.5	309.0	334.1	363.2	398.6	443.4	499.3	562.1	626.9	685.8	736.5
135°	301.0	322.1	346.3	372.9	404.2	442.5	488.6	541.0	596.5	647.3	691.9
137.5°	311.9	331.5	354.8	380.1	408.0	440.8	479.4	521.8	567.3	611.1	649.7
140°	318.2	337.7	360.4	383.9	410.5	440.2	473.8	510.5	550.4	587.9	621.5
142.5°	324.5	342.7	364.8	387.6	412.3	438.9	468.8	499.9	534.1	566.7	595.9
145°	332.3	350.3	370.6	391.7	413.6	437.0	462.1	487.1	512.9	537.9	560.6
147.5°	341.3	356.7	375.3	394.2	413.6	434.1	455.5	476.6	497.1	517.3	533.4
150°	346.3	360.4	378.4	394.8	413.6	431.6	451.1	469.1	487.1	503.5	518.3
152.5°	351.3	364.8	380.3	396.1	411.7	428.4	446.1	462.2	477.7	492.2	504.6
155°	359.6	370.6	383.9	396.4	409.7	423.0	438.6	451.9	464.4	476.1	485.5
157.5°	366.8	375.3	385.9	397.2	407.0	418.1	430.2	440.9	451.4	460.5	467.8
160°	370.6	378.4	387.8	397.2	405.8	414.4	424.5	434.7	443.3	451.1	456.6
162.5°	373.7	380.3	388.4	396.5	403.3	410.6	418.9	427.2	434.5	441.7	446.6
165°	377.6	383.1	389.3	394.8	399.5	405.0	411.2	417.5	422.2	427.7	431.6
167.5°	381.2	384.7	389.2	393.6	395.8	399.4	403.9	409.0	412.6	415.8	418.6
170°	383.1	384.7	388.6	391.7	393.3	395.6	399.5	403.4	405.8	408.9	410.5
172.5°	384.3	385.3	388.6	391.1	391.4	392.5	395.1	398.4	400.1	402.6	403.6
175°	385.4	386.2	387.8	389.3	388.6	388.6	390.1	391.7	392.5	394.0	394.0
177.5°	386.2	386.2	386.8	388.1	386.8	386.2	386.8	387.5	388.1	388.7	388.7
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332254

CATALOG NUMBER: S123RDIP-S340D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	518.5	518.3	518.5	517.8	518.5	518.3	518.5	520.8	520.8	520.9	521.1
5°	482.5	482.3	481.6	479.5	481.6	482.3	482.5	483.2	485.1	488.3	487.4
7.5°	451.0	450.7	448.7	448.7	448.7	450.7	451.0	452.9	455.0	457.0	459.3
10°	432.4	432.6	429.8	428.2	429.8	432.6	432.4	434.0	437.1	438.7	440.3
12.5°	414.3	413.3	411.0	409.2	411.0	413.3	414.3	415.6	419.7	421.6	424.7
15°	390.5	388.1	382.6	383.0	382.6	388.1	390.5	389.5	393.7	396.1	397.0
17.5°	362.4	360.7	360.6	357.3	360.6	360.7	362.4	364.2	367.9	370.4	377.1
20°	346.0	344.8	345.3	342.0	345.3	344.8	346.0	349.7	352.0	355.3	360.7
22.5°	333.1	331.9	330.0	329.0	330.0	331.9	333.1	335.7	338.2	342.8	345.7
25°	314.3	312.4	310.6	311.7	310.6	312.4	314.3	315.7	320.3	322.4	326.6
27.5°	295.5	294.1	292.2	292.0	292.2	294.1	295.5	296.8	299.4	302.9	308.0
30°	283.5	282.1	281.2	280.0	281.2	282.1	283.5	284.7	287.3	291.0	294.7
32.5°	271.4	271.1	269.5	269.2	269.5	271.1	271.4	273.3	275.9	279.4	282.6
35°	255.6	254.2	253.7	253.9	253.7	254.2	255.6	256.5	258.8	262.1	265.1
37.5°	240.5	238.7	237.8	237.0	237.8	238.7	240.5	240.7	243.0	245.2	249.3
40°	229.7	227.9	227.4	226.9	227.4	227.9	229.7	229.5	232.0	233.7	237.4
42.5°	217.6	216.9	216.6	215.7	216.6	216.9	217.6	218.9	220.3	222.7	225.5
45°	201.1	200.8	199.4	199.9	199.4	200.8	201.1	201.8	204.3	206.0	208.5
47.5°	183.6	182.6	181.6	182.3	181.6	182.6	183.6	184.6	186.3	188.3	191.7
50°	171.7	171.2	169.1	169.6	169.1	171.2	171.7	172.6	173.8	176.4	179.4
52.5°	159.8	158.0	157.2	156.9	157.2	158.0	159.8	160.7	162.1	165.0	167.3
55°	140.0	137.9	137.0	136.5	137.0	137.9	140.0	141.7	143.5	146.8	149.1
57.5°	120.6	120.1	119.3	119.8	119.3	120.1	120.6	123.3	125.2	127.7	130.6
60°	109.3	109.3	109.3	109.0	109.3	109.3	109.3	111.6	113.2	115.8	118.8
62.5°	100.5	99.9	99.8	100.1	99.8	99.9	100.5	101.5	103.2	104.8	107.5
65°	87.1	86.9	86.0	85.7	86.0	86.9	87.1	87.8	89.2	90.4	92.3
67.5°	74.5	73.7	73.4	73.1	73.4	73.7	74.5	75.1	76.0	77.5	78.5
70°	65.0	64.5	63.1	63.4	63.1	64.5	65.0	66.2	67.1	69.0	69.9
72.5°	54.8	54.3	54.0	53.7	54.0	54.3	54.8	55.9	56.8	58.9	60.4
75°	43.3	43.1	42.9	43.8	42.9	43.1	43.3	43.6	43.8	44.5	45.2
77.5°	34.7	34.7	34.9	34.5	34.9	34.7	34.7	34.7	34.7	35.1	35.2
80°	29.1	29.1	28.9	28.9	28.9	29.1	29.1	29.1	29.1	29.1	28.9
82.5°	23.3	23.5	23.7	23.3	23.7	23.5	23.3	23.7	23.9	23.5	23.7
85°	15.4	15.1	15.6	15.4	15.6	15.1	15.4	15.4	14.9	15.4	15.1
87.5°	11.3	11.1	11.2	11.2	11.2	11.1	11.3	11.1	10.7	10.6	10.2
90°	21.9	22.7	23.5	22.7	23.5	22.7	21.9	22.7	21.1	20.3	19.5
92.5°	40.7	38.3	39.1	37.7	39.1	38.3	40.7	42.1	46.1	52.2	65.8
95°	106.3	99.3	93.8	90.7	93.8	99.3	106.3	121.2	149.3	190.8	281.5
97.5°	309.9	274.7	253.6	246.9	253.6	274.7	309.9	367.6	461.1	562.0	701.6
100°	577.0	519.9	489.4	490.2	489.4	519.9	577.0	655.9	767.0	858.4	921.8
102.5°	807.8	762.6	737.1	719.1	737.1	762.6	807.8	869.2	939.6	992.9	994.9
105°	1053.1	1023.4	998.4	994.5	998.4	1023.4	1053.1	1089.1	1109.4	1094.5	1016.4
107.5°	1178.7	1168.7	1160.2	1153.0	1160.2	1168.7	1178.7	1178.0	1150.2	1081.7	954.8
110°	1214.9	1221.2	1219.6	1218.1	1219.6	1221.2	1214.9	1193.1	1138.3	1039.8	896.0



TEST NUMBER: P332254

CATALOG NUMBER: S123RDIP-S340D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1205.6	1225.0	1230.9	1231.2	1230.9	1225.0	1205.6	1165.5	1095.2	984.8	837.8
115°	1155.5	1189.9	1205.6	1209.5	1205.6	1189.9	1155.5	1096.9	1011.7	896.7	760.7
117.5°	1073.1	1112.5	1135.0	1140.4	1135.0	1112.5	1073.1	1012.0	925.5	822.3	704.9
120°	1015.6	1059.4	1078.1	1082.8	1078.1	1059.4	1015.6	953.8	874.9	781.0	675.5
122.5°	963.0	1002.4	1023.1	1029.0	1023.1	1002.4	963.0	908.2	834.8	747.9	652.4
125°	894.4	928.8	948.3	953.8	948.3	928.8	894.4	844.4	781.8	706.8	621.5
127.5°	839.8	869.2	886.9	891.9	886.9	869.2	839.8	795.3	738.4	670.6	594.7
130°	806.1	834.2	850.6	856.9	850.6	834.2	806.1	764.6	711.5	648.1	577.8
132.5°	775.4	803.6	818.1	822.5	818.1	803.6	775.4	736.5	685.8	626.9	562.1
135°	730.2	753.7	767.7	773.2	767.7	753.7	730.2	691.9	647.3	596.5	541.0
137.5°	681.9	705.7	717.6	721.2	717.6	705.7	681.9	649.7	611.1	567.3	521.8
140°	651.3	673.1	685.7	684.9	685.7	673.1	651.3	621.5	587.9	550.4	510.5
142.5°	621.2	640.6	651.9	651.1	651.9	640.6	621.2	595.9	566.7	534.1	499.9
145°	580.1	596.5	602.8	604.3	602.8	596.5	580.1	560.6	537.9	512.9	487.1
147.5°	548.2	559.3	565.3	565.9	565.3	559.3	548.2	533.4	517.3	497.1	476.6
150°	530.1	538.7	543.4	543.4	543.4	538.7	530.1	518.3	503.5	487.1	469.1
152.5°	513.8	521.8	524.6	524.6	524.6	521.8	513.8	504.6	492.2	477.7	462.2
155°	492.5	498.8	500.4	501.1	500.4	498.8	492.5	485.5	476.1	464.4	451.9
157.5°	473.9	478.6	479.9	479.7	479.9	478.6	473.9	467.8	460.5	451.4	440.9
160°	462.1	466.7	466.7	466.0	466.7	466.7	462.1	456.6	451.1	443.3	434.7
162.5°	450.2	454.2	454.2	453.5	454.2	454.2	450.2	446.6	441.7	434.5	427.2
165°	434.7	437.8	437.0	437.0	437.0	437.8	434.7	431.6	427.7	422.2	417.5
167.5°	420.0	422.2	421.4	421.4	421.4	422.2	420.0	418.6	415.8	412.6	409.0
170°	411.2	412.8	412.0	412.0	412.0	412.8	411.2	410.5	408.9	405.8	403.4
172.5°	403.7	405.3	403.9	403.3	403.9	405.3	403.7	403.6	402.6	400.1	398.4
175°	394.0	394.8	394.0	393.3	394.0	394.8	394.0	394.0	394.0	392.5	391.7
177.5°	388.1	388.7	387.5	387.5	387.5	388.7	388.1	388.7	388.7	388.1	387.5
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332254

CATALOG NUMBER: S123RDIP-S340D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	519.5	522.1	524.7	527.1	530.8	532.5	534.9	535.9	538.6	542.7	546.1
5°	487.9	491.6	496.5	500.4	506.7	511.6	517.0	522.1	528.2	536.8	544.5
7.5°	461.1	464.7	470.6	478.0	484.9	491.9	499.2	506.2	514.8	527.2	539.4
10°	443.4	447.8	454.8	462.7	471.3	478.1	486.7	495.5	506.3	520.5	535.2
12.5°	428.1	431.4	439.5	447.0	456.8	465.4	473.8	484.2	496.4	511.5	529.2
15°	403.8	408.4	416.3	424.7	435.0	444.1	455.0	467.6	479.5	498.1	519.5
17.5°	379.3	386.4	394.7	404.1	411.7	424.3	436.1	449.0	463.7	483.4	507.0
20°	363.7	369.3	377.0	390.7	400.7	410.3	421.2	437.3	450.8	473.2	497.6
22.5°	350.4	354.5	363.2	374.5	386.2	397.2	408.4	423.7	440.4	461.6	488.1
25°	330.8	337.4	343.9	352.0	364.6	377.9	390.0	403.1	420.8	443.4	472.0
27.5°	311.7	317.6	324.0	334.0	343.6	356.0	368.7	383.6	402.6	426.5	455.6
30°	299.4	303.8	309.9	322.7	331.3	342.0	356.9	370.2	387.9	413.3	444.1
32.5°	286.7	292.4	299.1	308.9	319.6	329.7	343.3	357.7	375.8	400.8	432.3
35°	268.6	275.4	282.1	289.4	300.1	310.6	322.0	337.8	356.2	380.5	411.4
37.5°	252.0	257.4	262.9	271.9	282.0	292.0	302.7	318.3	335.6	361.8	390.2
40°	241.4	246.3	250.5	259.8	269.6	280.3	290.8	304.5	323.1	347.6	375.1
42.5°	229.8	234.3	240.0	247.7	258.2	267.2	277.7	290.7	308.2	333.1	357.2
45°	212.5	217.6	222.5	229.7	240.2	249.1	258.4	270.7	288.7	309.2	330.6
47.5°	194.4	199.6	205.2	212.2	221.3	230.3	239.6	250.5	266.9	287.0	301.5
50°	182.9	187.1	192.7	199.7	208.1	217.6	226.0	237.9	253.5	269.3	281.9
52.5°	171.0	174.8	181.1	188.5	196.3	204.6	213.5	223.7	237.8	252.7	262.7
55°	152.4	157.0	162.4	169.6	177.3	184.3	192.9	203.4	214.6	225.8	232.5
57.5°	135.0	138.9	143.4	150.8	157.5	165.8	173.6	181.7	192.1	200.5	204.9
60°	122.3	125.8	131.6	138.2	144.4	151.7	160.5	168.7	176.6	183.4	186.8
62.5°	110.4	114.4	119.5	125.5	132.3	139.2	146.9	153.8	160.8	166.6	169.0
65°	94.8	98.1	101.8	107.4	113.0	120.0	126.0	133.0	138.2	141.4	143.5
67.5°	80.7	82.8	85.6	89.4	94.9	101.0	106.8	112.3	116.6	118.8	120.7
70°	71.5	72.9	75.0	78.7	82.9	88.3	94.4	98.3	102.0	103.9	105.8
72.5°	62.4	64.2	66.1	69.1	72.5	76.4	80.8	85.6	87.7	89.9	91.0
75°	47.3	49.9	52.4	54.3	56.6	59.6	63.6	66.6	67.8	69.7	69.9
77.5°	35.7	36.3	38.1	40.4	42.4	44.6	47.1	49.8	50.4	51.3	52.0
80°	29.4	29.4	29.4	30.8	33.1	34.7	37.0	38.4	39.4	39.6	39.8
82.5°	23.6	23.6	23.4	23.7	24.5	25.4	27.5	29.1	29.9	29.7	29.2
85°	15.4	14.9	14.9	14.7	14.9	14.4	14.2	15.1	16.5	16.5	16.1
87.5°	10.1	10.1	9.8	9.1	8.5	7.8	6.9	6.8	6.3	6.8	6.3
90°	18.8	19.5	17.2	14.9	12.5	10.2	8.6	7.0	4.7	3.1	1.6
92.5°	90.7	120.2	132.3	99.3	65.7	45.2	33.6	27.1	21.0	14.4	9.7
95°	376.1	463.6	412.8	284.6	168.1	101.6	71.1	50.8	37.5	28.9	26.6
97.5°	768.7	718.5	526.0	312.3	180.9	117.4	84.4	64.4	52.9	46.1	45.3
100°	894.4	740.4	500.4	294.7	179.0	124.3	93.8	75.1	64.1	58.6	57.9
102.5°	900.7	699.7	462.8	279.7	181.5	132.4	104.5	87.6	77.2	72.4	71.0
105°	853.0	628.6	416.7	268.9	188.4	146.2	122.0	107.1	97.7	93.0	90.7
107.5°	769.5	565.7	387.3	268.2	201.2	164.2	141.7	127.7	118.5	114.0	111.6
110°	716.9	530.1	376.1	271.3	211.9	176.7	154.8	141.5	132.9	129.0	126.7



TEST NUMBER: P332254

CATALOG NUMBER: S123RDIP-S340D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	671.3	506.3	369.8	277.5	222.5	189.8	168.6	155.3	146.7	142.8	140.4
115°	616.1	480.8	367.5	287.7	240.0	210.3	189.2	175.9	168.1	163.4	160.3
117.5°	582.8	465.8	368.9	301.2	258.6	229.2	209.7	194.8	187.6	183.7	180.1
120°	565.3	458.9	371.4	311.2	270.5	242.4	222.8	208.0	200.1	196.2	193.9
122.5°	550.9	454.6	375.7	320.5	283.0	255.5	234.7	220.5	212.0	208.1	205.8
125°	532.4	448.8	382.3	335.4	301.0	273.6	252.5	237.7	229.1	224.4	222.8
127.5°	516.2	446.0	389.8	347.6	316.6	290.2	269.1	252.7	243.9	238.1	235.8
130°	507.4	444.1	394.8	355.7	326.0	300.2	279.1	262.7	253.3	246.3	243.9
132.5°	499.3	443.4	398.6	363.2	334.1	309.0	288.5	272.1	260.8	253.2	250.2
135°	488.6	442.5	404.2	372.9	346.3	322.1	301.0	284.6	272.9	264.3	261.1
137.5°	479.4	440.8	408.0	380.1	354.8	331.5	311.9	295.7	283.2	274.7	271.4
140°	473.8	440.2	410.5	383.9	360.4	337.7	318.2	302.6	290.1	282.2	278.3
142.5°	468.8	438.9	412.3	387.6	364.8	342.7	324.5	308.8	297.6	289.1	285.8
145°	462.1	437.0	413.6	391.7	370.6	350.3	332.3	319.0	307.3	300.2	297.9
147.5°	455.5	434.1	413.6	394.2	375.3	356.7	341.3	328.5	318.4	311.5	310.1
150°	451.1	431.6	413.6	394.8	378.4	360.4	346.3	335.4	325.2	319.0	318.2
152.5°	446.1	428.4	411.7	396.1	380.3	364.8	351.3	341.7	332.7	326.5	326.3
155°	438.6	423.0	409.7	396.4	383.9	370.6	359.6	351.0	343.2	338.5	338.5
157.5°	430.2	418.1	407.0	397.2	385.9	375.3	366.8	359.5	352.6	348.8	348.2
160°	424.5	414.4	405.8	397.2	387.8	378.4	370.6	365.1	358.9	355.7	355.7
162.5°	418.9	410.6	403.3	396.5	388.4	380.3	373.7	368.9	363.9	361.4	361.4
165°	411.2	405.0	399.5	394.8	389.3	383.1	377.6	374.5	370.6	369.0	369.8
167.5°	403.9	399.4	395.8	393.6	389.2	384.7	381.2	379.0	376.1	375.3	376.2
170°	399.5	395.6	393.3	391.7	388.6	384.7	383.1	381.5	379.2	378.4	380.0
172.5°	395.1	392.5	391.4	391.1	388.6	385.3	384.3	383.4	381.7	381.5	382.5
175°	390.1	388.6	388.6	389.3	387.8	386.2	385.4	385.4	383.9	384.7	385.4
177.5°	386.8	386.2	386.8	388.1	386.8	386.2	386.2	386.2	385.6	386.2	386.8
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332254

CATALOG NUMBER: S123RDIP-S340D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	547.2	549.3	551.9	555.8	558.8	561.4	561.9	562.7	564.6	567.7	570.1
5°	550.8	556.1	564.7	573.1	582.2	589.7	596.7	601.6	606.2	616.0	623.9
7.5°	549.6	561.6	575.1	590.1	605.4	620.1	633.8	646.1	658.3	672.6	688.8
10°	548.9	562.9	581.1	600.4	621.6	642.3	662.4	678.0	696.1	712.5	733.2
12.5°	545.4	565.5	587.2	611.9	638.0	661.9	688.3	709.8	730.6	754.2	778.3
15°	540.7	565.2	592.7	625.5	665.2	694.0	721.1	758.6	784.2	809.8	844.3
17.5°	532.3	562.2	596.5	639.2	672.2	711.1	751.7	781.4	815.9	852.0	883.2
20°	525.6	560.3	598.8	640.7	682.9	725.0	764.4	799.8	835.5	877.2	902.8
22.5°	518.9	553.2	593.2	637.7	683.0	727.5	772.0	813.6	853.7	895.8	928.5
25°	504.6	545.4	588.7	634.2	678.9	727.8	780.9	827.3	876.9	920.3	951.3
27.5°	490.2	527.6	570.7	616.8	666.5	724.3	786.8	839.5	889.2	920.3	930.0
30°	477.1	516.7	556.4	603.2	657.0	721.5	787.9	848.3	889.0	902.6	892.5
32.5°	463.9	499.8	539.0	587.0	644.1	714.6	789.4	843.1	867.6	857.3	816.5
35°	440.6	472.9	510.9	558.9	624.6	710.8	783.3	819.6	813.6	755.3	678.4
37.5°	415.6	442.0	477.1	527.3	604.4	695.7	756.8	762.2	709.7	620.3	531.5
40°	395.8	419.6	455.7	508.1	588.7	680.8	730.2	708.5	627.2	527.7	453.6
42.5°	376.6	396.7	431.5	488.0	573.8	660.4	690.5	643.3	549.5	455.4	388.0
45°	344.1	363.0	397.9	455.9	543.3	621.6	617.6	535.6	441.7	366.0	310.1
47.5°	313.3	329.8	362.6	421.8	507.5	563.3	526.3	439.0	359.4	298.6	258.7
50°	291.5	307.8	340.4	398.9	478.8	519.5	466.7	382.6	309.6	259.3	227.6
52.5°	270.6	286.5	316.3	373.3	444.1	468.5	411.7	333.7	272.9	229.5	202.3
55°	241.4	253.5	280.3	334.8	387.7	393.3	335.7	270.5	220.4	190.1	171.5
57.5°	211.6	222.0	248.5	291.9	329.0	326.1	271.6	215.1	181.4	158.9	145.4
60°	192.2	202.5	225.8	263.0	291.0	281.2	231.1	185.7	156.8	140.3	129.5
62.5°	174.1	182.1	204.0	231.2	251.3	240.2	197.6	160.0	137.0	123.1	114.6
65°	147.9	154.5	171.9	186.2	197.3	186.6	151.2	125.1	108.6	98.8	93.0
67.5°	123.1	127.2	138.2	143.4	151.3	139.5	113.7	96.2	86.8	78.6	74.5
70°	107.4	110.4	116.3	120.5	122.5	110.4	91.3	78.5	70.6	64.8	62.2
72.5°	91.7	94.4	95.6	99.0	97.9	86.6	73.4	63.2	57.5	53.6	50.3
75°	70.1	71.3	70.1	68.7	65.7	57.8	48.7	43.6	39.4	37.5	36.3
77.5°	51.1	50.7	49.2	47.0	41.8	36.8	31.9	30.2	28.4	27.4	27.0
80°	39.4	38.4	37.0	33.5	29.1	25.6	24.5	23.3	22.6	21.4	21.2
82.5°	29.3	28.7	26.4	23.5	20.4	18.7	17.8	17.3	16.6	16.0	16.0
85°	15.6	14.9	12.3	10.7	10.3	9.8	9.6	9.6	8.6	8.4	8.4
87.5°	5.7	4.9	5.1	4.9	5.2	5.3	6.0	6.0	6.3	6.4	6.1
90°	3.1	4.7	7.0	8.6	10.2	12.5	14.9	17.2	19.5	18.8	19.5
92.5°	14.4	21.0	27.1	33.6	45.2	65.7	99.3	132.3	120.2	90.7	65.8
95°	28.9	37.5	50.8	71.1	101.6	168.1	284.6	412.8	463.6	376.1	281.5
97.5°	46.1	52.9	64.4	84.4	117.4	180.9	312.3	526.0	718.5	768.7	701.6
100°	58.6	64.1	75.1	93.8	124.3	179.0	294.7	500.4	740.4	894.4	921.8
102.5°	72.4	77.2	87.6	104.5	132.4	181.5	279.7	462.8	699.7	900.7	994.9
105°	93.0	97.7	107.1	122.0	146.2	188.4	268.9	416.7	628.6	853.0	1016.4
107.5°	114.0	118.5	127.7	141.7	164.2	201.2	268.2	387.3	565.7	769.5	954.8
110°	129.0	132.9	141.5	154.8	176.7	211.9	271.3	376.1	530.1	716.9	896.0



TEST NUMBER: P332254

CATALOG NUMBER: S123RDIP-S340D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	142.8	146.7	155.3	168.6	189.8	222.5	277.5	369.8	506.3	671.3	837.8
115°	163.4	168.1	175.9	189.2	210.3	240.0	287.7	367.5	480.8	616.1	760.7
117.5°	183.7	187.6	194.8	209.7	229.2	258.6	301.2	368.9	465.8	582.8	704.9
120°	196.2	200.1	208.0	222.8	242.4	270.5	311.2	371.4	458.9	565.3	675.5
122.5°	208.1	212.0	220.5	234.7	255.5	283.0	320.5	375.7	454.6	550.9	652.4
125°	224.4	229.1	237.7	252.5	273.6	301.0	335.4	382.3	448.8	532.4	621.5
127.5°	238.1	243.9	252.7	269.1	290.2	316.6	347.6	389.8	446.0	516.2	594.7
130°	246.3	253.3	262.7	279.1	300.2	326.0	355.7	394.8	444.1	507.4	577.8
132.5°	253.2	260.8	272.1	288.5	309.0	334.1	363.2	398.6	443.4	499.3	562.1
135°	264.3	272.9	284.6	301.0	322.1	346.3	372.9	404.2	442.5	488.6	541.0
137.5°	274.7	283.2	295.7	311.9	331.5	354.8	380.1	408.0	440.8	479.4	521.8
140°	282.2	290.1	302.6	318.2	337.7	360.4	383.9	410.5	440.2	473.8	510.5
142.5°	289.1	297.6	308.8	324.5	342.7	364.8	387.6	412.3	438.9	468.8	499.9
145°	300.2	307.3	319.0	332.3	350.3	370.6	391.7	413.6	437.0	462.1	487.1
147.5°	311.5	318.4	328.5	341.3	356.7	375.3	394.2	413.6	434.1	455.5	476.6
150°	319.0	325.2	335.4	346.3	360.4	378.4	394.8	413.6	431.6	451.1	469.1
152.5°	326.5	332.7	341.7	351.3	364.8	380.3	396.1	411.7	428.4	446.1	462.2
155°	338.5	343.2	351.0	359.6	370.6	383.9	396.4	409.7	423.0	438.6	451.9
157.5°	348.8	352.6	359.5	366.8	375.3	385.9	397.2	407.0	418.1	430.2	440.9
160°	355.7	358.9	365.1	370.6	378.4	387.8	397.2	405.8	414.4	424.5	434.7
162.5°	361.4	363.9	368.9	373.7	380.3	388.4	396.5	403.3	410.6	418.9	427.2
165°	369.0	370.6	374.5	377.6	383.1	389.3	394.8	399.5	405.0	411.2	417.5
167.5°	375.3	376.1	379.0	381.2	384.7	389.2	393.6	395.8	399.4	403.9	409.0
170°	378.4	379.2	381.5	383.1	384.7	388.6	391.7	393.3	395.6	399.5	403.4
172.5°	381.5	381.7	383.4	384.3	385.3	388.6	391.1	391.4	392.5	395.1	398.4
175°	384.7	383.9	385.4	385.4	386.2	387.8	389.3	388.6	388.6	390.1	391.7
177.5°	386.2	385.6	386.2	386.2	386.2	386.8	388.1	386.8	386.2	386.8	387.5
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332254

CATALOG NUMBER: S123RDIP-S340D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	574.1	574.1	574.8	577.6	578.0	580.4	579.7
5°	630.9	635.3	637.0	644.0	648.1	650.0	646.3
7.5°	700.4	712.9	718.8	726.2	732.6	734.6	729.5
10°	751.1	764.2	775.1	781.9	788.2	792.4	797.7
12.5°	800.1	816.2	826.6	836.1	842.6	847.9	848.8
15°	853.4	877.6	896.0	909.6	916.3	919.8	918.4
17.5°	907.1	929.6	942.7	956.5	965.8	966.3	966.6
20°	937.5	959.4	974.6	984.8	995.3	994.8	997.2
22.5°	957.8	975.1	986.7	994.1	997.7	995.9	996.4
25°	967.3	972.5	970.4	958.5	955.4	944.5	946.4
27.5°	918.3	894.1	869.0	836.8	811.3	791.0	792.0
30°	851.8	808.9	760.0	719.0	682.2	671.9	650.0
32.5°	758.8	694.5	637.2	598.9	567.4	558.8	539.7
35°	601.1	538.6	479.7	444.3	430.3	410.7	410.5
37.5°	467.2	412.2	381.1	354.5	340.6	328.7	327.6
40°	393.0	350.2	326.6	307.5	293.8	284.9	282.8
42.5°	341.2	306.6	284.5	272.7	262.1	257.5	254.1
45°	278.6	255.3	240.0	229.3	224.4	220.9	219.0
47.5°	233.1	217.5	207.0	199.8	195.9	192.2	193.2
50°	208.3	195.5	187.8	181.0	178.0	175.4	175.7
52.5°	188.3	176.8	170.6	165.7	162.0	160.1	159.3
55°	159.8	152.6	146.3	142.8	140.7	138.2	137.5
57.5°	136.3	130.7	125.6	121.7	121.1	118.7	119.0
60°	120.7	116.0	111.8	109.7	108.1	106.0	106.7
62.5°	107.8	103.9	100.1	98.4	96.7	95.2	95.5
65°	88.3	84.6	82.2	81.3	80.6	79.9	79.2
67.5°	70.4	68.1	66.6	64.6	63.2	63.0	62.3
70°	59.2	56.1	53.6	51.0	50.3	50.1	50.3
72.5°	47.4	45.5	44.8	43.6	43.4	42.8	43.2
75°	35.6	34.9	34.5	33.5	33.5	33.5	33.5
77.5°	26.3	25.9	25.6	25.4	25.2	24.8	24.8
80°	20.5	20.3	19.8	19.8	19.6	19.8	19.6
82.5°	15.5	15.4	15.0	15.0	14.7	14.6	14.7
85°	7.9	7.7	8.2	7.7	7.9	7.5	7.9
87.5°	6.3	6.5	6.6	6.4	6.4	6.9	6.4
90°	20.3	21.1	22.7	21.9	22.7	23.5	22.7
92.5°	52.2	46.1	42.1	40.7	38.3	39.1	37.7
95°	190.8	149.3	121.2	106.3	99.3	93.8	90.7
97.5°	562.0	461.1	367.6	309.9	274.7	253.6	246.9
100°	858.4	767.0	655.9	577.0	519.9	489.4	490.2
102.5°	992.9	939.6	869.2	807.8	762.6	737.1	719.1
105°	1094.5	1109.4	1089.1	1053.1	1023.4	998.4	994.5
107.5°	1081.7	1150.2	1178.0	1178.7	1168.7	1160.2	1153.0
110°	1039.8	1138.3	1193.1	1214.9	1221.2	1219.6	1218.1



TEST NUMBER: P332254

CATALOG NUMBER: S123RDIP-S340D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	984.8	1095.2	1165.5	1205.6	1225.0	1230.9	1231.2
115°	896.7	1011.7	1096.9	1155.5	1189.9	1205.6	1209.5
117.5°	822.3	925.5	1012.0	1073.1	1112.5	1135.0	1140.4
120°	781.0	874.9	953.8	1015.6	1059.4	1078.1	1082.8
122.5°	747.9	834.8	908.2	963.0	1002.4	1023.1	1029.0
125°	706.8	781.8	844.4	894.4	928.8	948.3	953.8
127.5°	670.6	738.4	795.3	839.8	869.2	886.9	891.9
130°	648.1	711.5	764.6	806.1	834.2	850.6	856.9
132.5°	626.9	685.8	736.5	775.4	803.6	818.1	822.5
135°	596.5	647.3	691.9	730.2	753.7	767.7	773.2
137.5°	567.3	611.1	649.7	681.9	705.7	717.6	721.2
140°	550.4	587.9	621.5	651.3	673.1	685.7	684.9
142.5°	534.1	566.7	595.9	621.2	640.6	651.9	651.1
145°	512.9	537.9	560.6	580.1	596.5	602.8	604.3
147.5°	497.1	517.3	533.4	548.2	559.3	565.3	565.9
150°	487.1	503.5	518.3	530.1	538.7	543.4	543.4
152.5°	477.7	492.2	504.6	513.8	521.8	524.6	524.6
155°	464.4	476.1	485.5	492.5	498.8	500.4	501.1
157.5°	451.4	460.5	467.8	473.9	478.6	479.9	479.7
160°	443.3	451.1	456.6	462.1	466.7	466.7	466.0
162.5°	434.5	441.7	446.6	450.2	454.2	454.2	453.5
165°	422.2	427.7	431.6	434.7	437.8	437.0	437.0
167.5°	412.6	415.8	418.6	420.0	422.2	421.4	421.4
170°	405.8	408.9	410.5	411.2	412.8	412.0	412.0
172.5°	400.1	402.6	403.6	403.7	405.3	403.9	403.3
175°	392.5	394.0	394.0	394.0	394.8	394.0	393.3
177.5°	388.1	388.7	388.7	388.1	388.7	387.5	387.5
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2

(END OF REPORT)