

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332270

Luminaire Tested: **S123RDIP-S560D365U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332270  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S560D365U835-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3679.5 lumens  
Efficiency: N/A  
Efficacy: 133.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332270

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332270

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	101	97	93	90	94	91	87	85	79	77	75	69	67	66	59	58	57	52
2	92	85	79	74	86	80	75	71	70	66	63	61	58	56	53	51	49	45
3	85	76	69	63	79	71	65	60	63	58	54	55	51	48	48	45	43	39
4	78	67	60	54	73	64	57	51	56	51	47	49	45	42	43	40	37	34
5	72	60	53	47	67	57	50	45	51	45	41	45	40	37	39	36	33	30
6	66	55	47	41	62	52	44	39	46	40	36	41	36	33	36	32	29	27
7	62	50	42	36	58	47	40	35	42	36	32	37	33	29	33	29	26	24
8	57	45	38	32	54	43	36	31	38	33	29	34	30	26	30	27	24	22
9	53	41	34	29	50	39	33	28	35	30	26	32	27	24	28	24	22	20
10	50	38	31	26	47	36	30	25	33	27	23	29	25	22	26	22	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9630	9630	9630	9630
5°	11480	9672	8518	9672
10°	14335	9616	7695	9616
15°	16826	9518	7017	9518
20°	18778	9371	6441	9371
25°	18478	9216	6087	9216
30°	13282	9073	5722	9073
35°	8868	8888	5486	8888
40°	6534	8665	5243	8665
45°	5480	8273	5002	8273
50°	4836	7762	4669	7762
55°	4241	7174	4211	7174
60°	3776	6613	3860	6613
65°	3316	6008	3591	6008
70°	2603	5473	3279	5473
75°	2296	4779	2994	4779
80°	1996	4060	2944	4060
85°	1606	3260	3125	3260



TEST NUMBER: P332270

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	88.0	2.4
10°-20°	274.9	7.5
20°-30°	431.9	11.7
30°-40°	450.6	12.2
40°-50°	385.6	10.5
50°-60°	293.9	8.0
60°-70°	188.4	5.1
70°-80°	90.6	2.5
80°-90°	25.3	0.7
90°-100°	17.3	0.5
100°-110°	82.4	2.2
110°-120°	198.0	5.4
120°-130°	252.1	6.9
130°-140°	269.3	7.3
140°-150°	251.9	6.8
150°-160°	203.2	5.5
160°-170°	131.1	3.6
170°-180°	45.2	1.2
0°-30°	794.7	21.6
0°-40°	1245.3	33.8
0°-60°	1924.8	52.3
0°-90°	2229.1	60.6
90°-120°	297.7	8.1
90°-150°	1071.0	29.1
90°-180°	1450.0	39.4
0°-180°	3679.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	895	895	895	895	895	
5°	1062	895	788	895	1062	110
15°	1510	854	630	854	1510	428
25°	1556	776	512	776	1556	669
35°	675	676	418	676	675	442
45°	360	544	329	544	360	283
55°	226	382	224	382	226	204
65°	130	236	141	236	130	128
75°	55	115	72	115	55	59
85°	13	26	25	26	13	15
90°	11	0	11	0	11	5
95°	13	22	13	22	13	11
105°	16	105	16	105	16	36
115°	208	198	208	198	208	192
125°	284	278	284	278	284	254
135°	350	347	350	347	350	270
145°	404	400	404	400	404	252
155°	440	441	440	441	440	203
165°	464	465	464	465	464	131
175°	474	476	474	476	474	45
180°	476	476	476	476	476	



TEST NUMBER: P332270

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	952.9	954.2	950.2	949.6	945.0	943.8	943.8	937.3	933.3	928.1	925.1
5°	1062.5	1068.6	1065.6	1058.7	1047.2	1044.5	1037.2	1025.7	1012.7	996.6	989.0
7.5°	1199.3	1207.7	1204.4	1193.8	1181.8	1172.0	1151.5	1132.4	1105.7	1082.3	1062.2
10°	1311.5	1302.6	1295.8	1285.4	1274.3	1256.3	1234.9	1205.4	1171.3	1144.5	1114.6
12.5°	1395.4	1394.0	1385.2	1374.6	1358.9	1341.8	1315.4	1279.5	1239.9	1201.1	1167.0
15°	1509.9	1512.2	1506.4	1495.3	1473.1	1442.8	1403.0	1388.1	1331.4	1289.2	1247.1
17.5°	1589.1	1588.6	1587.8	1572.4	1549.8	1528.2	1491.3	1452.0	1400.7	1341.3	1284.6
20°	1639.3	1635.5	1636.3	1619.0	1602.2	1577.3	1541.3	1484.2	1442.1	1373.5	1314.9
22.5°	1638.1	1637.3	1640.2	1634.3	1622.1	1603.0	1574.7	1526.5	1472.7	1403.5	1337.6
25°	1555.8	1552.8	1570.8	1575.7	1595.3	1598.7	1590.3	1563.9	1512.9	1441.7	1360.1
27.5°	1302.1	1300.4	1333.8	1375.6	1428.7	1469.9	1509.7	1528.9	1512.9	1461.9	1380.2
30°	1068.6	1104.6	1121.5	1182.0	1249.4	1329.8	1400.3	1467.3	1483.8	1461.6	1394.6
32.5°	887.2	918.6	932.7	984.7	1047.5	1141.7	1247.4	1342.3	1409.4	1426.4	1386.0
35°	674.9	675.3	707.4	730.4	788.6	885.5	988.2	1115.3	1241.7	1337.5	1347.5
37.5°	538.5	540.4	559.9	582.8	626.5	677.7	768.1	873.8	1019.8	1166.8	1253.0
40°	465.0	468.4	483.0	505.6	537.0	575.7	646.2	745.7	867.5	1031.1	1164.8
42.5°	417.8	423.4	430.9	448.3	467.7	504.0	561.0	637.9	748.6	903.3	1057.5
45°	360.0	363.1	368.8	376.9	394.5	419.8	458.1	509.8	601.7	726.2	880.6
47.5°	317.6	316.0	322.0	328.6	340.3	357.5	383.2	425.4	491.0	590.8	721.8
50°	288.8	288.4	292.6	297.6	308.7	321.4	342.4	374.2	426.3	509.0	628.9
52.5°	261.8	263.3	266.3	272.5	280.5	290.7	309.6	332.5	377.3	448.7	548.6
55°	226.0	227.1	231.3	234.8	240.5	250.9	262.8	281.9	312.5	362.3	444.7
57.5°	195.6	195.1	199.2	200.0	206.5	214.9	224.1	239.0	261.2	298.2	353.7
60°	175.4	174.3	177.7	180.4	183.8	190.7	198.4	213.0	230.6	257.8	305.3
62.5°	157.0	156.5	159.0	161.7	164.5	170.8	177.3	188.4	202.4	225.3	263.0
65°	130.2	131.4	132.5	133.7	135.2	139.0	145.2	152.8	162.4	178.5	205.7
67.5°	102.3	103.5	103.9	106.2	109.5	111.9	115.7	122.5	129.2	142.7	158.2
70°	82.7	82.3	82.7	83.9	88.1	92.3	97.3	102.3	106.5	116.1	129.1
72.5°	71.1	70.4	71.4	71.6	73.7	74.8	78.0	82.7	88.1	94.6	104.0
75°	55.2	55.2	55.2	55.2	56.7	57.5	58.6	59.8	61.7	64.7	71.6
77.5°	40.8	40.8	41.4	41.7	42.1	42.5	43.2	44.4	45.0	46.7	49.6
80°	32.2	32.6	32.2	32.6	32.6	33.3	33.7	34.9	35.2	37.2	38.3
82.5°	24.2	24.0	24.2	24.6	24.6	25.4	25.4	26.3	26.4	27.3	28.5
85°	13.0	12.3	13.0	12.6	13.4	12.6	13.0	13.8	13.8	14.2	15.7
87.5°	5.2	5.8	5.1	5.4	5.4	5.6	5.6	5.5	6.0	5.7	5.8
90°	10.6	10.4	10.3	10.1	10.0	9.7	9.4	9.1	8.8	8.5	7.5
92.5°	11.7	11.6	11.5	11.4	11.4	11.1	10.6	10.1	9.5	9.0	8.3
95°	13.4	13.4	13.4	13.4	13.4	13.2	12.6	12.1	11.5	11.0	10.1
97.5°	14.6	14.5	14.4	14.3	14.2	13.9	13.3	12.6	12.0	11.4	17.0
100°	14.8	14.8	14.7	14.6	14.5	14.2	13.5	12.9	12.3	11.7	23.9
102.5°	15.1	15.0	14.8	14.7	14.6	15.5	17.4	19.4	21.3	23.3	36.6
105°	15.5	15.4	15.2	15.1	14.9	21.8	35.7	49.6	63.5	77.4	84.5
107.5°	48.8	59.3	69.8	80.3	90.7	101.1	111.3	121.5	131.6	141.8	140.7
110°	97.2	108.4	119.6	130.9	142.1	149.0	151.6	154.2	156.8	159.4	158.5



TEST NUMBER: P332270

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	166.7	169.1	171.5	173.8	176.2	177.4	177.3	177.3	177.2	177.2	176.3
115°	207.8	207.5	207.2	206.8	206.5	206.0	205.2	204.4	203.6	202.8	202.1
117.5°	230.8	230.8	230.7	230.6	230.6	230.2	229.6	229.0	228.3	227.7	227.4
120°	246.7	246.7	246.7	246.7	246.7	246.3	245.7	245.1	244.5	243.8	243.6
122.5°	262.2	262.1	262.1	262.0	261.9	261.7	261.3	260.8	260.4	259.9	259.6
125°	284.1	284.0	283.8	283.6	283.5	283.3	283.2	283.0	282.9	282.7	282.4
127.5°	305.2	305.3	305.5	305.6	305.8	305.8	305.5	305.2	305.0	304.7	304.4
130°	318.7	318.9	319.1	319.2	319.4	319.3	319.0	318.7	318.3	318.0	317.7
132.5°	331.2	331.4	331.6	331.8	332.1	332.0	331.7	331.4	331.1	330.8	330.5
135°	350.2	350.4	350.7	350.9	351.1	351.1	350.9	350.7	350.4	350.2	349.9
137.5°	368.1	368.2	368.4	368.5	368.7	368.6	368.2	367.8	367.5	367.1	366.9
140°	378.8	379.0	379.1	379.3	379.4	379.4	379.0	378.7	378.4	378.1	377.9
142.5°	388.7	388.9	389.1	389.4	389.6	389.6	389.3	389.1	388.8	388.6	388.3
145°	403.9	403.9	403.9	403.9	403.9	403.8	403.7	403.5	403.4	403.2	403.0
147.5°	415.2	415.6	415.9	416.3	416.7	416.8	416.6	416.4	416.3	416.1	416.0
150°	423.7	423.9	424.2	424.4	424.6	424.7	424.5	424.4	424.2	424.0	423.9
152.5°	430.5	430.8	431.2	431.6	431.9	432.0	431.7	431.4	431.1	430.8	430.7
155°	439.9	440.4	440.9	441.4	441.8	441.9	441.5	441.1	440.7	440.3	440.2
157.5°	447.9	448.5	449.2	449.8	450.4	450.5	450.0	449.5	449.0	448.6	448.6
160°	453.0	453.6	454.1	454.7	455.2	455.3	454.8	454.3	453.8	453.4	453.5
162.5°	457.8	458.3	458.8	459.3	459.8	459.7	459.2	458.7	458.1	457.6	457.7
165°	463.6	464.2	464.7	465.3	465.8	465.8	465.2	464.5	463.9	463.3	463.3
167.5°	467.8	468.4	469.0	469.7	470.3	470.3	469.7	469.0	468.4	467.8	467.8
170°	470.3	471.0	471.6	472.2	472.8	472.8	472.2	471.6	471.0	470.3	470.3
172.5°	471.7	472.4	473.1	473.8	474.5	474.5	473.9	473.3	472.7	472.0	472.0
175°	473.9	474.5	475.1	475.8	476.4	476.4	475.9	475.3	474.8	474.2	474.1
177.5°	474.5	475.1	475.8	476.4	477.0	477.1	476.6	476.1	475.6	475.1	475.0
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6



TEST NUMBER: P332270

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	923.8	922.9	918.6	913.7	907.3	903.0	899.6	897.8	892.3	885.5	880.9
5°	980.9	969.4	957.2	942.2	928.4	914.3	905.5	895.1	882.5	868.3	858.3
7.5°	1042.0	1019.5	995.2	970.2	945.4	923.2	903.6	886.8	866.7	846.4	832.1
10°	1088.9	1056.0	1021.9	987.0	955.2	925.4	902.4	879.8	855.7	832.3	814.7
12.5°	1131.5	1088.2	1048.9	1006.0	965.4	929.7	896.6	870.0	841.0	816.1	796.0
15°	1185.4	1141.0	1093.5	1028.4	974.4	929.2	889.0	854.1	818.9	788.3	768.7
17.5°	1235.8	1169.0	1105.2	1050.8	980.7	924.2	875.1	833.4	794.8	762.3	738.2
20°	1256.7	1192.0	1122.6	1053.3	984.4	921.2	864.1	818.1	777.9	741.1	718.9
22.5°	1269.2	1195.9	1122.9	1048.4	975.2	909.5	853.1	802.5	758.9	724.0	696.6
25°	1283.9	1196.5	1116.1	1042.6	967.9	896.6	829.6	776.0	728.9	691.7	662.6
27.5°	1293.5	1190.8	1095.7	1014.0	938.2	867.3	805.9	749.0	701.2	661.9	630.7
30°	1295.4	1186.2	1080.1	991.6	914.6	849.5	784.4	730.0	679.5	637.7	608.6
32.5°	1297.8	1174.9	1059.0	965.0	886.2	821.7	762.7	710.7	658.9	617.8	588.1
35°	1287.7	1168.6	1026.9	918.9	840.0	777.5	724.3	676.4	625.5	585.6	555.4
37.5°	1244.2	1143.7	993.6	866.9	784.4	726.6	683.2	641.5	594.8	551.8	523.3
40°	1200.4	1119.2	967.9	835.4	749.2	689.8	650.7	616.7	571.5	531.2	500.6
42.5°	1135.1	1085.8	943.4	802.3	709.3	652.1	619.2	587.2	547.6	506.7	477.9
45°	1015.4	1021.9	893.2	749.6	654.2	596.7	565.7	543.5	508.3	474.6	445.1
47.5°	865.2	926.1	834.3	693.4	596.1	542.1	515.0	495.6	471.9	438.8	411.9
50°	767.2	854.1	787.1	655.7	559.6	506.0	479.2	463.5	442.8	416.7	391.1
52.5°	676.8	770.2	730.1	613.7	520.1	471.0	444.8	431.9	415.5	391.0	367.8
55°	551.9	646.5	637.3	550.4	460.8	416.7	396.8	382.3	371.1	352.8	334.4
57.5°	446.4	536.1	540.9	479.9	408.5	365.0	347.9	336.9	329.6	315.8	298.8
60°	380.0	462.3	478.4	432.4	371.1	332.8	316.0	307.2	301.4	290.3	277.3
62.5°	324.8	394.9	413.1	380.0	335.3	299.4	286.3	277.8	273.9	264.3	252.8
65°	248.6	306.8	324.4	306.0	282.7	253.9	243.2	235.9	232.5	227.1	218.7
67.5°	186.9	229.4	248.7	235.7	227.3	209.1	202.3	198.4	195.3	191.7	184.6
70°	150.1	181.6	201.5	198.0	191.1	181.6	176.6	173.9	170.8	167.8	161.6
72.5°	120.7	142.3	161.0	162.8	157.1	155.2	150.8	149.7	147.8	144.2	140.8
75°	80.1	95.0	108.0	113.0	115.3	117.2	115.3	114.9	114.5	111.5	109.5
77.5°	52.5	60.5	68.7	77.2	80.8	83.4	84.0	85.4	84.4	82.8	81.9
80°	40.2	42.1	47.9	55.2	60.9	63.2	64.7	65.5	65.1	64.7	63.2
82.5°	29.2	30.8	33.5	38.6	43.4	47.3	48.2	48.0	48.9	49.1	47.9
85°	15.7	16.1	16.9	17.6	20.3	24.5	25.7	26.4	27.2	27.2	24.9
87.5°	6.2	5.7	6.1	5.9	6.7	6.8	8.5	9.9	10.3	9.3	9.4
90°	6.4	5.4	4.4	3.5	2.7	1.9	1.1	0.4	1.1	1.9	2.7
92.5°	7.5	6.7	6.0	5.7	5.9	6.1	6.4	6.6	6.4	6.1	5.9
95°	9.2	8.4	7.5	8.7	11.9	15.1	18.3	21.6	18.3	15.1	11.9
97.5°	22.7	28.3	34.0	37.5	39.0	40.4	41.9	43.3	41.9	40.4	39.0
100°	36.2	48.4	60.7	66.0	64.4	62.9	61.3	59.7	61.3	62.9	64.4
102.5°	50.0	63.4	76.8	82.9	81.8	80.6	79.5	78.4	79.5	80.6	81.8
105°	91.5	98.6	105.7	108.8	107.9	107.0	106.2	105.3	106.2	107.0	107.9
107.5°	139.6	138.5	137.4	136.5	135.8	135.1	134.4	133.7	134.4	135.1	135.8
110°	157.6	156.8	155.9	155.2	154.5	153.9	153.3	152.7	153.3	153.9	154.5





TEST NUMBER: P332270

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	175.5	174.6	173.7	173.0	172.4	171.9	171.3	170.7	171.3	171.9	172.4
115°	201.4	200.7	200.0	199.4	198.9	198.5	198.0	197.5	198.0	198.5	198.9
117.5°	227.0	226.6	226.3	225.8	225.2	224.6	224.1	223.5	224.1	224.6	225.2
120°	243.4	243.1	242.9	242.4	241.7	241.0	240.3	239.6	240.3	241.0	241.7
122.5°	259.3	259.0	258.7	258.3	257.7	257.1	256.6	256.0	256.6	257.1	257.7
125°	282.1	281.8	281.4	281.0	280.3	279.7	279.1	278.5	279.1	279.7	280.3
127.5°	304.0	303.6	303.2	302.7	302.1	301.5	300.9	300.2	300.9	301.5	302.1
130°	317.4	317.1	316.8	316.3	315.7	315.0	314.4	313.8	314.4	315.0	315.7
132.5°	330.3	330.0	329.7	329.3	328.7	328.1	327.4	326.8	327.4	328.1	328.7
135°	349.6	349.2	348.9	348.5	348.1	347.6	347.1	346.7	347.1	347.6	348.1
137.5°	366.7	366.6	366.4	366.0	365.4	364.8	364.2	363.6	364.2	364.8	365.4
140°	377.6	377.4	377.2	376.8	376.3	375.9	375.4	374.9	375.4	375.9	376.3
142.5°	388.1	387.9	387.6	387.3	386.8	386.3	385.9	385.4	385.9	386.3	386.8
145°	402.9	402.7	402.6	402.2	401.7	401.1	400.6	400.0	400.6	401.1	401.7
147.5°	415.8	415.7	415.5	415.2	414.9	414.5	414.2	413.8	414.2	414.5	414.9
150°	423.7	423.6	423.4	423.2	423.0	422.7	422.5	422.3	422.5	422.7	423.0
152.5°	430.6	430.5	430.5	430.3	430.2	430.1	430.0	429.9	430.0	430.1	430.2
155°	440.1	440.1	440.0	440.0	440.2	440.3	440.5	440.7	440.5	440.3	440.2
157.5°	448.7	448.8	448.9	448.9	448.9	449.0	449.0	449.0	449.0	449.0	448.9
160°	453.5	453.6	453.7	453.8	453.8	453.9	454.0	454.1	454.0	453.9	453.8
162.5°	457.8	457.8	457.9	458.1	458.3	458.5	458.7	458.9	458.7	458.5	458.3
165°	463.4	463.5	463.6	463.7	464.0	464.2	464.4	464.7	464.4	464.2	464.0
167.5°	467.8	467.8	467.8	467.9	468.3	468.6	468.9	469.2	468.9	468.6	468.3
170°	470.3	470.3	470.3	470.5	470.8	471.1	471.4	471.7	471.4	471.1	470.8
172.5°	471.9	471.8	471.8	471.9	472.3	472.7	473.1	473.4	473.1	472.7	472.3
175°	474.1	474.0	473.9	474.1	474.5	474.8	475.2	475.6	475.2	474.8	474.5
177.5°	474.9	474.9	474.8	474.9	475.3	475.6	475.9	476.2	475.9	475.6	475.3
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6



TEST NUMBER: P332270

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	879.4	875.4	872.7	866.5	862.6	858.3	854.0	856.7	856.4	856.1	856.1
5°	849.9	841.1	833.1	822.7	816.2	808.2	802.0	801.3	802.8	797.4	794.4
7.5°	820.7	808.6	797.2	785.8	773.7	764.0	758.0	755.2	751.3	748.0	744.5
10°	800.1	786.0	774.8	760.7	747.7	736.2	728.9	723.9	721.2	718.5	713.6
12.5°	779.0	765.1	750.9	734.9	722.5	709.2	703.8	698.2	693.0	690.0	683.2
15°	748.0	730.0	715.1	698.2	684.5	671.4	663.8	652.7	651.1	647.3	640.4
17.5°	717.0	697.5	676.9	664.4	648.8	635.3	623.6	619.9	608.9	604.8	598.8
20°	692.5	674.5	658.8	642.3	619.7	607.1	597.9	592.9	584.1	578.7	574.9
22.5°	671.4	653.0	634.9	615.7	597.0	582.9	576.1	568.4	563.6	556.1	551.9
25°	641.2	621.3	599.4	578.7	565.3	554.6	543.9	537.0	530.1	526.6	519.0
27.5°	606.1	585.3	564.9	549.2	532.7	522.1	512.4	506.3	498.0	492.2	488.0
30°	586.8	562.3	544.7	530.5	509.4	499.5	492.2	484.5	478.4	472.3	468.0
32.5°	564.4	542.0	525.3	507.8	491.6	480.8	471.3	464.6	459.4	453.6	449.4
35°	529.3	510.6	493.3	475.7	463.8	452.7	441.6	435.9	430.9	425.5	421.7
37.5°	497.6	480.1	463.7	447.0	432.3	423.2	414.3	409.9	403.2	399.6	395.7
40°	478.0	460.8	443.2	427.1	411.7	404.9	396.8	390.3	384.2	381.5	377.3
42.5°	456.6	439.3	424.5	407.1	394.6	385.2	377.8	370.7	366.1	362.2	359.8
45°	424.8	409.4	394.9	377.7	365.8	357.7	349.3	342.8	338.6	335.9	331.7
47.5°	393.9	378.6	363.8	348.8	337.3	328.1	319.7	315.1	309.6	306.3	303.4
50°	371.5	357.7	342.0	328.2	316.8	307.6	300.7	294.9	289.9	285.7	283.8
52.5°	351.0	336.3	322.7	309.9	297.8	287.3	281.1	275.0	271.3	266.4	264.2
55°	317.1	303.0	291.5	278.8	267.0	258.2	250.5	245.1	241.3	235.9	232.9
57.5°	285.3	272.6	258.9	248.0	235.7	228.3	221.9	214.6	210.0	205.8	202.8
60°	263.9	249.3	237.5	227.1	216.4	206.8	201.1	195.3	190.4	186.1	183.5
62.5°	241.5	228.8	217.6	206.3	196.5	188.1	181.5	176.6	172.3	169.6	166.9
65°	207.2	197.3	185.8	176.6	167.4	161.3	155.9	151.7	148.6	146.7	144.4
67.5°	175.7	166.0	156.0	146.9	140.8	136.1	132.6	129.0	127.5	125.0	123.5
70°	155.1	145.2	136.4	129.5	123.3	119.9	117.6	114.9	113.4	110.3	108.8
72.5°	132.8	125.6	119.2	113.5	108.6	105.5	102.6	99.3	96.8	93.5	91.9
75°	104.6	98.1	93.1	89.2	86.2	82.0	77.8	74.3	73.2	72.0	71.6
77.5°	77.4	73.3	69.7	66.5	62.7	59.6	58.7	57.9	57.7	57.1	57.1
80°	60.9	57.1	54.4	50.6	48.3	48.3	48.3	47.5	47.9	47.9	47.9
82.5°	45.3	41.7	40.3	38.9	38.5	38.8	38.8	38.9	38.7	39.3	39.0
85°	23.4	23.7	24.5	24.1	24.5	24.5	25.3	24.9	25.3	24.5	25.3
87.5°	9.3	10.4	10.9	11.4	11.9	11.8	12.2	12.2	12.6	12.7	12.7
90°	3.5	4.4	5.4	6.4	7.5	8.5	8.8	9.1	9.4	9.7	10.0
92.5°	5.7	6.0	6.7	7.5	8.3	9.0	9.5	10.1	10.6	11.1	11.4
95°	8.7	7.5	8.4	9.2	10.1	11.0	11.5	12.1	12.6	13.2	13.4
97.5°	37.5	34.0	28.3	22.7	17.0	11.4	12.0	12.6	13.3	13.9	14.2
100°	66.0	60.7	48.4	36.2	23.9	11.7	12.3	12.9	13.5	14.2	14.5
102.5°	82.9	76.8	63.4	50.0	36.6	23.3	21.3	19.4	17.4	15.5	14.6
105°	108.8	105.7	98.6	91.5	84.5	77.4	63.5	49.6	35.7	21.8	14.9
107.5°	136.5	137.4	138.5	139.6	140.7	141.8	131.6	121.5	111.3	101.1	90.7
110°	155.2	155.9	156.8	157.6	158.5	159.4	156.8	154.2	151.6	149.0	142.1



TEST NUMBER: P332270

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	173.0	173.7	174.6	175.5	176.3	177.2	177.2	177.3	177.3	177.4	176.2
115°	199.4	200.0	200.7	201.4	202.1	202.8	203.6	204.4	205.2	206.0	206.5
117.5°	225.8	226.3	226.6	227.0	227.4	227.7	228.3	229.0	229.6	230.2	230.6
120°	242.4	242.9	243.1	243.4	243.6	243.8	244.5	245.1	245.7	246.3	246.7
122.5°	258.3	258.7	259.0	259.3	259.6	259.9	260.4	260.8	261.3	261.7	261.9
125°	281.0	281.4	281.8	282.1	282.4	282.7	282.9	283.0	283.2	283.3	283.5
127.5°	302.7	303.2	303.6	304.0	304.4	304.7	305.0	305.2	305.5	305.8	305.8
130°	316.3	316.8	317.1	317.4	317.7	318.0	318.3	318.7	319.0	319.3	319.4
132.5°	329.3	329.7	330.0	330.3	330.5	330.8	331.1	331.4	331.7	332.0	332.1
135°	348.5	348.9	349.2	349.6	349.9	350.2	350.4	350.7	350.9	351.1	351.1
137.5°	366.0	366.4	366.6	366.7	366.9	367.1	367.5	367.8	368.2	368.6	368.7
140°	376.8	377.2	377.4	377.6	377.9	378.1	378.4	378.7	379.0	379.4	379.4
142.5°	387.3	387.6	387.9	388.1	388.3	388.6	388.8	389.1	389.3	389.6	389.6
145°	402.2	402.6	402.7	402.9	403.0	403.2	403.4	403.5	403.7	403.8	403.9
147.5°	415.2	415.5	415.7	415.8	416.0	416.1	416.3	416.4	416.6	416.8	416.7
150°	423.2	423.4	423.6	423.7	423.9	424.0	424.2	424.4	424.5	424.7	424.6
152.5°	430.3	430.5	430.5	430.6	430.7	430.8	431.1	431.4	431.7	432.0	431.9
155°	440.0	440.0	440.1	440.1	440.2	440.3	440.7	441.1	441.5	441.9	441.8
157.5°	448.9	448.9	448.8	448.7	448.6	448.6	449.0	449.5	450.0	450.5	450.4
160°	453.8	453.7	453.6	453.5	453.5	453.4	453.8	454.3	454.8	455.3	455.2
162.5°	458.1	457.9	457.8	457.8	457.7	457.6	458.1	458.7	459.2	459.7	459.8
165°	463.7	463.6	463.5	463.4	463.3	463.3	463.9	464.5	465.2	465.8	465.8
167.5°	467.9	467.8	467.8	467.8	467.8	467.8	468.4	469.0	469.7	470.3	470.3
170°	470.5	470.3	470.3	470.3	470.3	470.3	471.0	471.6	472.2	472.8	472.8
172.5°	471.9	471.8	471.8	471.9	472.0	472.0	472.7	473.3	473.9	474.5	474.5
175°	474.1	473.9	474.0	474.1	474.1	474.2	474.8	475.3	475.9	476.4	476.4
177.5°	474.9	474.8	474.9	474.9	475.0	475.1	475.6	476.1	476.6	477.1	477.0
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6



TEST NUMBER: P332270

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	852.4	852.1	852.4	851.2	852.4	852.1	852.4	856.1	856.1	856.4	856.7
5°	793.2	792.8	791.7	788.3	791.7	792.8	793.2	794.4	797.4	802.8	801.3
7.5°	741.5	741.0	737.6	737.7	737.6	741.0	741.5	744.5	748.0	751.3	755.2
10°	710.9	711.3	706.7	704.0	706.7	711.3	710.9	713.6	718.5	721.2	723.9
12.5°	681.2	679.4	675.7	672.7	675.7	679.4	681.2	683.2	690.0	693.0	698.2
15°	641.9	638.1	628.9	629.7	628.9	638.1	641.9	640.4	647.3	651.1	652.7
17.5°	595.7	592.9	592.8	587.4	592.8	592.9	595.7	598.8	604.8	608.9	619.9
20°	568.8	566.9	567.6	562.3	567.6	566.9	568.8	574.9	578.7	584.1	592.9
22.5°	547.6	545.7	542.5	540.8	542.5	545.7	547.6	551.9	556.1	563.6	568.4
25°	516.7	513.6	510.6	512.5	510.6	513.6	516.7	519.0	526.6	530.1	537.0
27.5°	485.7	483.4	480.4	480.0	480.4	483.4	485.7	488.0	492.2	498.0	506.3
30°	466.1	463.8	462.3	460.4	462.3	463.8	466.1	468.0	472.3	478.4	484.5
32.5°	446.2	445.8	443.0	442.6	443.0	445.8	446.2	449.4	453.6	459.4	464.6
35°	420.2	417.9	417.1	417.5	417.1	417.9	420.2	421.7	425.5	430.9	435.9
37.5°	395.4	392.4	391.0	389.6	391.0	392.4	395.4	395.7	399.6	403.2	409.9
40°	377.7	374.6	373.8	373.1	373.8	374.6	377.7	377.3	381.5	384.2	390.3
42.5°	357.7	356.5	356.1	354.7	356.1	356.5	357.7	359.8	362.2	366.1	370.7
45°	330.5	330.2	327.9	328.6	327.9	330.2	330.5	331.7	335.9	338.6	342.8
47.5°	301.9	300.2	298.6	299.7	298.6	300.2	301.9	303.4	306.3	309.6	315.1
50°	282.3	281.5	278.1	278.8	278.1	281.5	282.3	283.8	285.7	289.9	294.9
52.5°	262.7	259.8	258.5	258.0	258.5	259.8	262.7	264.2	266.4	271.3	275.0
55°	230.2	226.7	225.2	224.4	225.2	226.7	230.2	232.9	235.9	241.3	245.1
57.5°	198.3	197.4	196.2	197.0	196.2	197.4	198.3	202.8	205.8	210.0	214.6
60°	179.6	179.6	179.6	179.3	179.6	179.6	179.6	183.5	186.1	190.4	195.3
62.5°	165.2	164.3	164.0	164.5	164.0	164.3	165.2	166.9	169.6	172.3	176.6
65°	143.2	142.9	141.3	141.0	141.3	142.9	143.2	144.4	146.7	148.6	151.7
67.5°	122.5	121.1	120.7	120.1	120.7	121.1	122.5	123.5	125.0	127.5	129.0
70°	106.9	106.1	103.8	104.2	103.8	106.1	106.9	108.8	110.3	113.4	114.9
72.5°	90.0	89.2	88.8	88.2	88.8	89.2	90.0	91.9	93.5	96.8	99.3
75°	71.2	70.9	70.5	72.0	70.5	70.9	71.2	71.6	72.0	73.2	74.3
77.5°	57.1	57.1	57.3	56.7	57.3	57.1	57.1	57.1	57.1	57.7	57.9
80°	47.9	47.9	47.5	47.5	47.5	47.9	47.9	47.9	47.9	47.9	47.5
82.5°	38.4	38.7	38.9	38.3	38.9	38.7	38.4	39.0	39.3	38.7	38.9
85°	25.3	24.9	25.7	25.3	25.7	24.9	25.3	25.3	24.5	25.3	24.9
87.5°	13.4	12.8	12.8	13.2	12.8	12.8	13.4	12.7	12.7	12.6	12.2
90°	10.1	10.3	10.4	10.6	10.4	10.3	10.1	10.0	9.7	9.4	9.1
92.5°	11.4	11.5	11.6	11.7	11.6	11.5	11.4	11.4	11.1	10.6	10.1
95°	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.2	12.6	12.1
97.5°	14.3	14.4	14.5	14.6	14.5	14.4	14.3	14.2	13.9	13.3	12.6
100°	14.6	14.7	14.8	14.8	14.8	14.7	14.6	14.5	14.2	13.5	12.9
102.5°	14.7	14.8	15.0	15.1	15.0	14.8	14.7	14.6	15.5	17.4	19.4
105°	15.1	15.2	15.4	15.5	15.4	15.2	15.1	14.9	21.8	35.7	49.6
107.5°	80.3	69.8	59.3	48.8	59.3	69.8	80.3	90.7	101.1	111.3	121.5
110°	130.9	119.6	108.4	97.2	108.4	119.6	130.9	142.1	149.0	151.6	154.2



TEST NUMBER: P332270

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	173.8	171.5	169.1	166.7	169.1	171.5	173.8	176.2	177.4	177.3	177.3
115°	206.8	207.2	207.5	207.8	207.5	207.2	206.8	206.5	206.0	205.2	204.4
117.5°	230.6	230.7	230.8	230.8	230.8	230.7	230.6	230.6	230.2	229.6	229.0
120°	246.7	246.7	246.7	246.7	246.7	246.7	246.7	246.7	246.3	245.7	245.1
122.5°	262.0	262.1	262.1	262.2	262.1	262.1	262.0	261.9	261.7	261.3	260.8
125°	283.6	283.8	284.0	284.1	284.0	283.8	283.6	283.5	283.3	283.2	283.0
127.5°	305.6	305.5	305.3	305.2	305.3	305.5	305.6	305.8	305.8	305.5	305.2
130°	319.2	319.1	318.9	318.7	318.9	319.1	319.2	319.4	319.3	319.0	318.7
132.5°	331.8	331.6	331.4	331.2	331.4	331.6	331.8	332.1	332.0	331.7	331.4
135°	350.9	350.7	350.4	350.2	350.4	350.7	350.9	351.1	351.1	350.9	350.7
137.5°	368.5	368.4	368.2	368.1	368.2	368.4	368.5	368.7	368.6	368.2	367.8
140°	379.3	379.1	379.0	378.8	379.0	379.1	379.3	379.4	379.4	379.0	378.7
142.5°	389.4	389.1	388.9	388.7	388.9	389.1	389.4	389.6	389.6	389.3	389.1
145°	403.9	403.9	403.9	403.9	403.9	403.9	403.9	403.9	403.8	403.7	403.5
147.5°	416.3	415.9	415.6	415.2	415.6	415.9	416.3	416.7	416.8	416.6	416.4
150°	424.4	424.2	423.9	423.7	423.9	424.2	424.4	424.6	424.7	424.5	424.4
152.5°	431.6	431.2	430.8	430.5	430.8	431.2	431.6	431.9	432.0	431.7	431.4
155°	441.4	440.9	440.4	439.9	440.4	440.9	441.4	441.8	441.9	441.5	441.1
157.5°	449.8	449.2	448.5	447.9	448.5	449.2	449.8	450.4	450.5	450.0	449.5
160°	454.7	454.1	453.6	453.0	453.6	454.1	454.7	455.2	455.3	454.8	454.3
162.5°	459.3	458.8	458.3	457.8	458.3	458.8	459.3	459.8	459.7	459.2	458.7
165°	465.3	464.7	464.2	463.6	464.2	464.7	465.3	465.8	465.8	465.2	464.5
167.5°	469.7	469.0	468.4	467.8	468.4	469.0	469.7	470.3	470.3	469.7	469.0
170°	472.2	471.6	471.0	470.3	471.0	471.6	472.2	472.8	472.8	472.2	471.6
172.5°	473.8	473.1	472.4	471.7	472.4	473.1	473.8	474.5	474.5	473.9	473.3
175°	475.8	475.1	474.5	473.9	474.5	475.1	475.8	476.4	476.4	475.9	475.3
177.5°	476.4	475.8	475.1	474.5	475.1	475.8	476.4	477.0	477.1	476.6	476.1
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6



TEST NUMBER: P332270

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	854.0	858.3	862.6	866.5	872.7	875.4	879.4	880.9	885.5	892.3	897.8
5°	802.0	808.2	816.2	822.7	833.1	841.1	849.9	858.3	868.3	882.5	895.1
7.5°	758.0	764.0	773.7	785.8	797.2	808.6	820.7	832.1	846.4	866.7	886.8
10°	728.9	736.2	747.7	760.7	774.8	786.0	800.1	814.7	832.3	855.7	879.8
12.5°	703.8	709.2	722.5	734.9	750.9	765.1	779.0	796.0	816.1	841.0	870.0
15°	663.8	671.4	684.5	698.2	715.1	730.0	748.0	768.7	788.3	818.9	854.1
17.5°	623.6	635.3	648.8	664.4	676.9	697.5	717.0	738.2	762.3	794.8	833.4
20°	597.9	607.1	619.7	642.3	658.8	674.5	692.5	718.9	741.1	777.9	818.1
22.5°	576.1	582.9	597.0	615.7	634.9	653.0	671.4	696.6	724.0	758.9	802.5
25°	543.9	554.6	565.3	578.7	599.4	621.3	641.2	662.6	691.7	728.9	776.0
27.5°	512.4	522.1	532.7	549.2	564.9	585.3	606.1	630.7	661.9	701.2	749.0
30°	492.2	499.5	509.4	530.5	544.7	562.3	586.8	608.6	637.7	679.5	730.0
32.5°	471.3	480.8	491.6	507.8	525.3	542.0	564.4	588.1	617.8	658.9	710.7
35°	441.6	452.7	463.8	475.7	493.3	510.6	529.3	555.4	585.6	625.5	676.4
37.5°	414.3	423.2	432.3	447.0	463.7	480.1	497.6	523.3	551.8	594.8	641.5
40°	396.8	404.9	411.7	427.1	443.2	460.8	478.0	500.6	531.2	571.5	616.7
42.5°	377.8	385.2	394.6	407.1	424.5	439.3	456.6	477.9	506.7	547.6	587.2
45°	349.3	357.7	365.8	377.7	394.9	409.4	424.8	445.1	474.6	508.3	543.5
47.5°	319.7	328.1	337.3	348.8	363.8	378.6	393.9	411.9	438.8	471.9	495.6
50°	300.7	307.6	316.8	328.2	342.0	357.7	371.5	391.1	416.7	442.8	463.5
52.5°	281.1	287.3	297.8	309.9	322.7	336.3	351.0	367.8	391.0	415.5	431.9
55°	250.5	258.2	267.0	278.8	291.5	303.0	317.1	334.4	352.8	371.1	382.3
57.5°	221.9	228.3	235.7	248.0	258.9	272.6	285.3	298.8	315.8	329.6	336.9
60°	201.1	206.8	216.4	227.1	237.5	249.3	263.9	277.3	290.3	301.4	307.2
62.5°	181.5	188.1	196.5	206.3	217.6	228.8	241.5	252.8	264.3	273.9	277.8
65°	155.9	161.3	167.4	176.6	185.8	197.3	207.2	218.7	227.1	232.5	235.9
67.5°	132.6	136.1	140.8	146.9	156.0	166.0	175.7	184.6	191.7	195.3	198.4
70°	117.6	119.9	123.3	129.5	136.4	145.2	155.1	161.6	167.8	170.8	173.9
72.5°	102.6	105.5	108.6	113.5	119.2	125.6	132.8	140.8	144.2	147.8	149.7
75°	77.8	82.0	86.2	89.2	93.1	98.1	104.6	109.5	111.5	114.5	114.9
77.5°	58.7	59.6	62.7	66.5	69.7	73.3	77.4	81.9	82.8	84.4	85.4
80°	48.3	48.3	48.3	50.6	54.4	57.1	60.9	63.2	64.7	65.1	65.5
82.5°	38.8	38.8	38.5	38.9	40.3	41.7	45.3	47.9	49.1	48.9	48.0
85°	25.3	24.5	24.5	24.1	24.5	23.7	23.4	24.9	27.2	27.2	26.4
87.5°	12.2	11.8	11.9	11.4	10.9	10.4	9.3	9.4	9.3	10.3	9.9
90°	8.8	8.5	7.5	6.4	5.4	4.4	3.5	2.7	1.9	1.1	0.4
92.5°	9.5	9.0	8.3	7.5	6.7	6.0	5.7	5.9	6.1	6.4	6.6
95°	11.5	11.0	10.1	9.2	8.4	7.5	8.7	11.9	15.1	18.3	21.6
97.5°	12.0	11.4	17.0	22.7	28.3	34.0	37.5	39.0	40.4	41.9	43.3
100°	12.3	11.7	23.9	36.2	48.4	60.7	66.0	64.4	62.9	61.3	59.7
102.5°	21.3	23.3	36.6	50.0	63.4	76.8	82.9	81.8	80.6	79.5	78.4
105°	63.5	77.4	84.5	91.5	98.6	105.7	108.8	107.9	107.0	106.2	105.3
107.5°	131.6	141.8	140.7	139.6	138.5	137.4	136.5	135.8	135.1	134.4	133.7
110°	156.8	159.4	158.5	157.6	156.8	155.9	155.2	154.5	153.9	153.3	152.7



TEST NUMBER: P332270

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	177.2	177.2	176.3	175.5	174.6	173.7	173.0	172.4	171.9	171.3	170.7
115°	203.6	202.8	202.1	201.4	200.7	200.0	199.4	198.9	198.5	198.0	197.5
117.5°	228.3	227.7	227.4	227.0	226.6	226.3	225.8	225.2	224.6	224.1	223.5
120°	244.5	243.8	243.6	243.4	243.1	242.9	242.4	241.7	241.0	240.3	239.6
122.5°	260.4	259.9	259.6	259.3	259.0	258.7	258.3	257.7	257.1	256.6	256.0
125°	282.9	282.7	282.4	282.1	281.8	281.4	281.0	280.3	279.7	279.1	278.5
127.5°	305.0	304.7	304.4	304.0	303.6	303.2	302.7	302.1	301.5	300.9	300.2
130°	318.3	318.0	317.7	317.4	317.1	316.8	316.3	315.7	315.0	314.4	313.8
132.5°	331.1	330.8	330.5	330.3	330.0	329.7	329.3	328.7	328.1	327.4	326.8
135°	350.4	350.2	349.9	349.6	349.2	348.9	348.5	348.1	347.6	347.1	346.7
137.5°	367.5	367.1	366.9	366.7	366.6	366.4	366.0	365.4	364.8	364.2	363.6
140°	378.4	378.1	377.9	377.6	377.4	377.2	376.8	376.3	375.9	375.4	374.9
142.5°	388.8	388.6	388.3	388.1	387.9	387.6	387.3	386.8	386.3	385.9	385.4
145°	403.4	403.2	403.0	402.9	402.7	402.6	402.2	401.7	401.1	400.6	400.0
147.5°	416.3	416.1	416.0	415.8	415.7	415.5	415.2	414.9	414.5	414.2	413.8
150°	424.2	424.0	423.9	423.7	423.6	423.4	423.2	423.0	422.7	422.5	422.3
152.5°	431.1	430.8	430.7	430.6	430.5	430.5	430.3	430.2	430.1	430.0	429.9
155°	440.7	440.3	440.2	440.1	440.1	440.0	440.0	440.2	440.3	440.5	440.7
157.5°	449.0	448.6	448.6	448.7	448.8	448.9	448.9	448.9	449.0	449.0	449.0
160°	453.8	453.4	453.5	453.5	453.6	453.7	453.8	453.8	453.9	454.0	454.1
162.5°	458.1	457.6	457.7	457.8	457.8	457.9	458.1	458.3	458.5	458.7	458.9
165°	463.9	463.3	463.3	463.4	463.5	463.6	463.7	464.0	464.2	464.4	464.7
167.5°	468.4	467.8	467.8	467.8	467.8	467.8	467.9	468.3	468.6	468.9	469.2
170°	471.0	470.3	470.3	470.3	470.3	470.3	470.5	470.8	471.1	471.4	471.7
172.5°	472.7	472.0	472.0	471.9	471.8	471.8	471.9	472.3	472.7	473.1	473.4
175°	474.8	474.2	474.1	474.1	474.0	473.9	474.1	474.5	474.8	475.2	475.6
177.5°	475.6	475.1	475.0	474.9	474.9	474.8	474.9	475.3	475.6	475.9	476.2
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6



TEST NUMBER: P332270

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	899.6	903.0	907.3	913.7	918.6	922.9	923.8	925.1	928.1	933.3	937.3
5°	905.5	914.3	928.4	942.2	957.2	969.4	980.9	989.0	996.6	1012.7	1025.7
7.5°	903.6	923.2	945.4	970.2	995.2	1019.5	1042.0	1062.2	1082.3	1105.7	1132.4
10°	902.4	925.4	955.2	987.0	1021.9	1056.0	1088.9	1114.6	1144.5	1171.3	1205.4
12.5°	896.6	929.7	965.4	1006.0	1048.9	1088.2	1131.5	1167.0	1201.1	1239.9	1279.5
15°	889.0	929.2	974.4	1028.4	1093.5	1141.0	1185.4	1247.1	1289.2	1331.4	1388.1
17.5°	875.1	924.2	980.7	1050.8	1105.2	1169.0	1235.8	1284.6	1341.3	1400.7	1452.0
20°	864.1	921.2	984.4	1053.3	1122.6	1192.0	1256.7	1314.9	1373.5	1442.1	1484.2
22.5°	853.1	909.5	975.2	1048.4	1122.9	1195.9	1269.2	1337.6	1403.5	1472.7	1526.5
25°	829.6	896.6	967.9	1042.6	1116.1	1196.5	1283.9	1360.1	1441.7	1512.9	1563.9
27.5°	805.9	867.3	938.2	1014.0	1095.7	1190.8	1293.5	1380.2	1461.9	1512.9	1528.9
30°	784.4	849.5	914.6	991.6	1080.1	1186.2	1295.4	1394.6	1461.6	1483.8	1467.3
32.5°	762.7	821.7	886.2	965.0	1059.0	1174.9	1297.8	1386.0	1426.4	1409.4	1342.3
35°	724.3	777.5	840.0	918.9	1026.9	1168.6	1287.7	1347.5	1337.5	1241.7	1115.3
37.5°	683.2	726.6	784.4	866.9	993.6	1143.7	1244.2	1253.0	1166.8	1019.8	873.8
40°	650.7	689.8	749.2	835.4	967.9	1119.2	1200.4	1164.8	1031.1	867.5	745.7
42.5°	619.2	652.1	709.3	802.3	943.4	1085.8	1135.1	1057.5	903.3	748.6	637.9
45°	565.7	596.7	654.2	749.6	893.2	1021.9	1015.4	880.6	726.2	601.7	509.8
47.5°	515.0	542.1	596.1	693.4	834.3	926.1	865.2	721.8	590.8	491.0	425.4
50°	479.2	506.0	559.6	655.7	787.1	854.1	767.2	628.9	509.0	426.3	374.2
52.5°	444.8	471.0	520.1	613.7	730.1	770.2	676.8	548.6	448.7	377.3	332.5
55°	396.8	416.7	460.8	550.4	637.3	646.5	551.9	444.7	362.3	312.5	281.9
57.5°	347.9	365.0	408.5	479.9	540.9	536.1	446.4	353.7	298.2	261.2	239.0
60°	316.0	332.8	371.1	432.4	478.4	462.3	380.0	305.3	257.8	230.6	213.0
62.5°	286.3	299.4	335.3	380.0	413.1	394.9	324.8	263.0	225.3	202.4	188.4
65°	243.2	253.9	282.7	306.0	324.4	306.8	248.6	205.7	178.5	162.4	152.8
67.5°	202.3	209.1	227.3	235.7	248.7	229.4	186.9	158.2	142.7	129.2	122.5
70°	176.6	181.6	191.1	198.0	201.5	181.6	150.1	129.1	116.1	106.5	102.3
72.5°	150.8	155.2	157.1	162.8	161.0	142.3	120.7	104.0	94.6	88.1	82.7
75°	115.3	117.2	115.3	113.0	108.0	95.0	80.1	71.6	64.7	61.7	59.8
77.5°	84.0	83.4	80.8	77.2	68.7	60.5	52.5	49.6	46.7	45.0	44.4
80°	64.7	63.2	60.9	55.2	47.9	42.1	40.2	38.3	37.2	35.2	34.9
82.5°	48.2	47.3	43.4	38.6	33.5	30.8	29.2	28.5	27.3	26.4	26.3
85°	25.7	24.5	20.3	17.6	16.9	16.1	15.7	15.7	14.2	13.8	13.8
87.5°	8.5	6.8	6.7	5.9	6.1	5.7	6.2	5.8	5.7	6.0	5.5
90°	1.1	1.9	2.7	3.5	4.4	5.4	6.4	7.5	8.5	8.8	9.1
92.5°	6.4	6.1	5.9	5.7	6.0	6.7	7.5	8.3	9.0	9.5	10.1
95°	18.3	15.1	11.9	8.7	7.5	8.4	9.2	10.1	11.0	11.5	12.1
97.5°	41.9	40.4	39.0	37.5	34.0	28.3	22.7	17.0	11.4	12.0	12.6
100°	61.3	62.9	64.4	66.0	60.7	48.4	36.2	23.9	11.7	12.3	12.9
102.5°	79.5	80.6	81.8	82.9	76.8	63.4	50.0	36.6	23.3	21.3	19.4
105°	106.2	107.0	107.9	108.8	105.7	98.6	91.5	84.5	77.4	63.5	49.6
107.5°	134.4	135.1	135.8	136.5	137.4	138.5	139.6	140.7	141.8	131.6	121.5
110°	153.3	153.9	154.5	155.2	155.9	156.8	157.6	158.5	159.4	156.8	154.2





TEST NUMBER: P332270

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	171.3	171.9	172.4	173.0	173.7	174.6	175.5	176.3	177.2	177.2	177.3
115°	198.0	198.5	198.9	199.4	200.0	200.7	201.4	202.1	202.8	203.6	204.4
117.5°	224.1	224.6	225.2	225.8	226.3	226.6	227.0	227.4	227.7	228.3	229.0
120°	240.3	241.0	241.7	242.4	242.9	243.1	243.4	243.6	243.8	244.5	245.1
122.5°	256.6	257.1	257.7	258.3	258.7	259.0	259.3	259.6	259.9	260.4	260.8
125°	279.1	279.7	280.3	281.0	281.4	281.8	282.1	282.4	282.7	282.9	283.0
127.5°	300.9	301.5	302.1	302.7	303.2	303.6	304.0	304.4	304.7	305.0	305.2
130°	314.4	315.0	315.7	316.3	316.8	317.1	317.4	317.7	318.0	318.3	318.7
132.5°	327.4	328.1	328.7	329.3	329.7	330.0	330.3	330.5	330.8	331.1	331.4
135°	347.1	347.6	348.1	348.5	348.9	349.2	349.6	349.9	350.2	350.4	350.7
137.5°	364.2	364.8	365.4	366.0	366.4	366.6	366.7	366.9	367.1	367.5	367.8
140°	375.4	375.9	376.3	376.8	377.2	377.4	377.6	377.9	378.1	378.4	378.7
142.5°	385.9	386.3	386.8	387.3	387.6	387.9	388.1	388.3	388.6	388.8	389.1
145°	400.6	401.1	401.7	402.2	402.6	402.7	402.9	403.0	403.2	403.4	403.5
147.5°	414.2	414.5	414.9	415.2	415.5	415.7	415.8	416.0	416.1	416.3	416.4
150°	422.5	422.7	423.0	423.2	423.4	423.6	423.7	423.9	424.0	424.2	424.4
152.5°	430.0	430.1	430.2	430.3	430.5	430.5	430.6	430.7	430.8	431.1	431.4
155°	440.5	440.3	440.2	440.0	440.0	440.1	440.1	440.2	440.3	440.7	441.1
157.5°	449.0	449.0	448.9	448.9	448.9	448.8	448.7	448.6	448.6	449.0	449.5
160°	454.0	453.9	453.8	453.8	453.7	453.6	453.5	453.5	453.4	453.8	454.3
162.5°	458.7	458.5	458.3	458.1	457.9	457.8	457.8	457.7	457.6	458.1	458.7
165°	464.4	464.2	464.0	463.7	463.6	463.5	463.4	463.3	463.3	463.9	464.5
167.5°	468.9	468.6	468.3	467.9	467.8	467.8	467.8	467.8	467.8	468.4	469.0
170°	471.4	471.1	470.8	470.5	470.3	470.3	470.3	470.3	470.3	471.0	471.6
172.5°	473.1	472.7	472.3	471.9	471.8	471.8	471.9	472.0	472.0	472.7	473.3
175°	475.2	474.8	474.5	474.1	473.9	474.0	474.1	474.1	474.2	474.8	475.3
177.5°	475.9	475.6	475.3	474.9	474.8	474.9	474.9	475.0	475.1	475.6	476.1
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6



TEST NUMBER: P332270

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	943.8	943.8	945.0	949.6	950.2	954.2	952.9
5°	1037.2	1044.5	1047.2	1058.7	1065.6	1068.6	1062.5
7.5°	1151.5	1172.0	1181.8	1193.8	1204.4	1207.7	1199.3
10°	1234.9	1256.3	1274.3	1285.4	1295.8	1302.6	1311.5
12.5°	1315.4	1341.8	1358.9	1374.6	1385.2	1394.0	1395.4
15°	1403.0	1442.8	1473.1	1495.3	1506.4	1512.2	1509.9
17.5°	1491.3	1528.2	1549.8	1572.4	1587.8	1588.6	1589.1
20°	1541.3	1577.3	1602.2	1619.0	1636.3	1635.5	1639.3
22.5°	1574.7	1603.0	1622.1	1634.3	1640.2	1637.3	1638.1
25°	1590.3	1598.7	1595.3	1575.7	1570.8	1552.8	1555.8
27.5°	1509.7	1469.9	1428.7	1375.6	1333.8	1300.4	1302.1
30°	1400.3	1329.8	1249.4	1182.0	1121.5	1104.6	1068.6
32.5°	1247.4	1141.7	1047.5	984.7	932.7	918.6	887.2
35°	988.2	885.5	788.6	730.4	707.4	675.3	674.9
37.5°	768.1	677.7	626.5	582.8	559.9	540.4	538.5
40°	646.2	575.7	537.0	505.6	483.0	468.4	465.0
42.5°	561.0	504.0	467.7	448.3	430.9	423.4	417.8
45°	458.1	419.8	394.5	376.9	368.8	363.1	360.0
47.5°	383.2	357.5	340.3	328.6	322.0	316.0	317.6
50°	342.4	321.4	308.7	297.6	292.6	288.4	288.8
52.5°	309.6	290.7	280.5	272.5	266.3	263.3	261.8
55°	262.8	250.9	240.5	234.8	231.3	227.1	226.0
57.5°	224.1	214.9	206.5	200.0	199.2	195.1	195.6
60°	198.4	190.7	183.8	180.4	177.7	174.3	175.4
62.5°	177.3	170.8	164.5	161.7	159.0	156.5	157.0
65°	145.2	139.0	135.2	133.7	132.5	131.4	130.2
67.5°	115.7	111.9	109.5	106.2	103.9	103.5	102.3
70°	97.3	92.3	88.1	83.9	82.7	82.3	82.7
72.5°	78.0	74.8	73.7	71.6	71.4	70.4	71.1
75°	58.6	57.5	56.7	55.2	55.2	55.2	55.2
77.5°	43.2	42.5	42.1	41.7	41.4	40.8	40.8
80°	33.7	33.3	32.6	32.6	32.2	32.6	32.2
82.5°	25.4	25.4	24.6	24.6	24.2	24.0	24.2
85°	13.0	12.6	13.4	12.6	13.0	12.3	13.0
87.5°	5.6	5.6	5.4	5.4	5.1	5.8	5.2
90°	9.4	9.7	10.0	10.1	10.3	10.4	10.6
92.5°	10.6	11.1	11.4	11.4	11.5	11.6	11.7
95°	12.6	13.2	13.4	13.4	13.4	13.4	13.4
97.5°	13.3	13.9	14.2	14.3	14.4	14.5	14.6
100°	13.5	14.2	14.5	14.6	14.7	14.8	14.8
102.5°	17.4	15.5	14.6	14.7	14.8	15.0	15.1
105°	35.7	21.8	14.9	15.1	15.2	15.4	15.5
107.5°	111.3	101.1	90.7	80.3	69.8	59.3	48.8
110°	151.6	149.0	142.1	130.9	119.6	108.4	97.2



TEST NUMBER: P332270

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	177.3	177.4	176.2	173.8	171.5	169.1	166.7
115°	205.2	206.0	206.5	206.8	207.2	207.5	207.8
117.5°	229.6	230.2	230.6	230.6	230.7	230.8	230.8
120°	245.7	246.3	246.7	246.7	246.7	246.7	246.7
122.5°	261.3	261.7	261.9	262.0	262.1	262.1	262.2
125°	283.2	283.3	283.5	283.6	283.8	284.0	284.1
127.5°	305.5	305.8	305.8	305.6	305.5	305.3	305.2
130°	319.0	319.3	319.4	319.2	319.1	318.9	318.7
132.5°	331.7	332.0	332.1	331.8	331.6	331.4	331.2
135°	350.9	351.1	351.1	350.9	350.7	350.4	350.2
137.5°	368.2	368.6	368.7	368.5	368.4	368.2	368.1
140°	379.0	379.4	379.4	379.3	379.1	379.0	378.8
142.5°	389.3	389.6	389.6	389.4	389.1	388.9	388.7
145°	403.7	403.8	403.9	403.9	403.9	403.9	403.9
147.5°	416.6	416.8	416.7	416.3	415.9	415.6	415.2
150°	424.5	424.7	424.6	424.4	424.2	423.9	423.7
152.5°	431.7	432.0	431.9	431.6	431.2	430.8	430.5
155°	441.5	441.9	441.8	441.4	440.9	440.4	439.9
157.5°	450.0	450.5	450.4	449.8	449.2	448.5	447.9
160°	454.8	455.3	455.2	454.7	454.1	453.6	453.0
162.5°	459.2	459.7	459.8	459.3	458.8	458.3	457.8
165°	465.2	465.8	465.8	465.3	464.7	464.2	463.6
167.5°	469.7	470.3	470.3	469.7	469.0	468.4	467.8
170°	472.2	472.8	472.8	472.2	471.6	471.0	470.3
172.5°	473.9	474.5	474.5	473.8	473.1	472.4	471.7
175°	475.9	476.4	476.4	475.8	475.1	474.5	473.9
177.5°	476.6	477.1	477.0	476.4	475.8	475.1	474.5
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6

(END OF REPORT)