

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332272

Luminaire Tested: **S123RDIP-S560D365U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332272
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D365U835-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3542.5 lumens
Efficiency: N/A
Efficacy: 128.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332272

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332272

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63
1	101	97	94	90	95	91	88	85	81	78	76	71	69	67	61	60	59	54
2	93	86	80	75	87	81	76	71	71	68	64	63	60	57	55	53	51	47
3	85	76	69	63	80	72	66	60	64	59	55	56	52	49	49	46	44	41
4	78	68	60	54	73	64	57	52	57	52	47	51	46	43	44	41	39	35
5	72	61	53	47	68	58	51	45	51	46	41	46	41	38	40	37	34	31
6	67	55	47	41	63	52	45	40	47	41	37	42	37	33	37	33	30	28
7	62	50	42	37	58	47	40	35	43	37	32	38	33	30	34	30	27	25
8	58	46	38	33	54	43	36	31	39	33	29	35	30	27	31	27	25	22
9	54	42	34	29	51	40	33	28	36	30	26	32	28	24	29	25	22	20
10	50	38	31	27	47	37	30	26	33	28	24	30	25	22	27	23	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9630	9630	9630	9630
5°	11480	9672	8518	9672
10°	14335	9616	7695	9616
15°	16826	9518	7017	9518
20°	18778	9371	6441	9371
25°	18478	9216	6087	9216
30°	13282	9073	5722	9073
35°	8868	8888	5486	8888
40°	6534	8665	5243	8665
45°	5480	8273	5002	8273
50°	4836	7762	4669	7762
55°	4241	7174	4211	7174
60°	3776	6613	3860	6613
65°	3316	6008	3591	6008
70°	2603	5473	3279	5473
75°	2296	4779	2994	4779
80°	1996	4060	2944	4060
85°	1606	3260	3125	3260



TEST NUMBER: P332272

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.0	2.5
10°-20°	274.9	7.8
20°-30°	431.9	12.2
30°-40°	450.6	12.7
40°-50°	385.6	10.9
50°-60°	293.9	8.3
60°-70°	188.4	5.3
70°-80°	90.6	2.6
80°-90°	25.3	0.7
90°-100°	97.2	2.7
100°-110°	275.1	7.8
110°-120°	270.6	7.6
120°-130°	215.9	6.1
130°-140°	170.2	4.8
140°-150°	127.0	3.6
150°-160°	88.5	2.5
160°-170°	52.0	1.5
170°-180°	16.9	0.5
0°-30°	794.7	22.4
0°-40°	1245.3	35.2
0°-60°	1924.8	54.3
0°-90°	2229.1	62.9
90°-120°	642.9	18.1
90°-150°	1155.9	32.6
90°-180°	1313.0	37.1
0°-180°	3542.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	895	895	895	895	895	
5°	1062	895	788	895	1062	110
15°	1510	854	630	854	1510	428
25°	1556	776	512	776	1556	669
35°	675	676	418	676	675	442
45°	360	544	329	544	360	283
55°	226	382	224	382	226	204
65°	130	236	141	236	130	128
75°	55	115	72	115	55	59
85°	13	26	25	26	13	15
90°	10	1	10	1	10	6
95°	41	12	41	12	41	74
105°	450	41	450	41	450	443
115°	547	72	547	72	547	531
125°	431	101	431	101	431	391
135°	350	118	350	118	350	271
145°	273	135	273	135	273	174
155°	226	153	226	153	226	106
165°	198	167	198	167	198	56
175°	178	174	178	174	178	17
180°	175	175	175	175	175	



TEST NUMBER: P332272

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	952.9	954.2	950.2	949.6	945.0	943.8	943.8	937.3	933.3	928.1	925.1
5°	1062.5	1068.6	1065.6	1058.7	1047.2	1044.5	1037.2	1025.7	1012.7	996.6	989.0
7.5°	1199.3	1207.7	1204.4	1193.8	1181.8	1172.0	1151.5	1132.4	1105.7	1082.3	1062.2
10°	1311.5	1302.6	1295.8	1285.4	1274.3	1256.3	1234.9	1205.4	1171.3	1144.5	1114.6
12.5°	1395.4	1394.0	1385.2	1374.6	1358.9	1341.8	1315.4	1279.5	1239.9	1201.1	1167.0
15°	1509.9	1512.2	1506.4	1495.3	1473.1	1442.8	1403.0	1388.1	1331.4	1289.2	1247.1
17.5°	1589.1	1588.6	1587.8	1572.4	1549.8	1528.2	1491.3	1452.0	1400.7	1341.3	1284.6
20°	1639.3	1635.5	1636.3	1619.0	1602.2	1577.3	1541.3	1484.2	1442.1	1373.5	1314.9
22.5°	1638.1	1637.3	1640.2	1634.3	1622.1	1603.0	1574.7	1526.5	1472.7	1403.5	1337.6
25°	1555.8	1552.8	1570.8	1575.7	1595.3	1598.7	1590.3	1563.9	1512.9	1441.7	1360.1
27.5°	1302.1	1300.4	1333.8	1375.6	1428.7	1469.9	1509.7	1528.9	1512.9	1461.9	1380.2
30°	1068.6	1104.6	1121.5	1182.0	1249.4	1329.8	1400.3	1467.3	1483.8	1461.6	1394.6
32.5°	887.2	918.6	932.7	984.7	1047.5	1141.7	1247.4	1342.3	1409.4	1426.4	1386.0
35°	674.9	675.3	707.4	730.4	788.6	885.5	988.2	1115.3	1241.7	1337.5	1347.5
37.5°	538.5	540.4	559.9	582.8	626.5	677.7	768.1	873.8	1019.8	1166.8	1253.0
40°	465.0	468.4	483.0	505.6	537.0	575.7	646.2	745.7	867.5	1031.1	1164.8
42.5°	417.8	423.4	430.9	448.3	467.7	504.0	561.0	637.9	748.6	903.3	1057.5
45°	360.0	363.1	368.8	376.9	394.5	419.8	458.1	509.8	601.7	726.2	880.6
47.5°	317.6	316.0	322.0	328.6	340.3	357.5	383.2	425.4	491.0	590.8	721.8
50°	288.8	288.4	292.6	297.6	308.7	321.4	342.4	374.2	426.3	509.0	628.9
52.5°	261.8	263.3	266.3	272.5	280.5	290.7	309.6	332.5	377.3	448.7	548.6
55°	226.0	227.1	231.3	234.8	240.5	250.9	262.8	281.9	312.5	362.3	444.7
57.5°	195.6	195.1	199.2	200.0	206.5	214.9	224.1	239.0	261.2	298.2	353.7
60°	175.4	174.3	177.7	180.4	183.8	190.7	198.4	213.0	230.6	257.8	305.3
62.5°	157.0	156.5	159.0	161.7	164.5	170.8	177.3	188.4	202.4	225.3	263.0
65°	130.2	131.4	132.5	133.7	135.2	139.0	145.2	152.8	162.4	178.5	205.7
67.5°	102.3	103.5	103.9	106.2	109.5	111.9	115.7	122.5	129.2	142.7	158.2
70°	82.7	82.3	82.7	83.9	88.1	92.3	97.3	102.3	106.5	116.1	129.1
72.5°	71.1	70.4	71.4	71.6	73.7	74.8	78.0	82.7	88.1	94.6	104.0
75°	55.2	55.2	55.2	55.2	56.7	57.5	58.6	59.8	61.7	64.7	71.6
77.5°	40.8	40.8	41.4	41.7	42.1	42.5	43.2	44.4	45.0	46.7	49.6
80°	32.2	32.6	32.2	32.6	32.6	33.3	33.7	34.9	35.2	37.2	38.3
82.5°	24.2	24.0	24.2	24.6	24.6	25.4	25.4	26.3	26.4	27.3	28.5
85°	13.0	12.3	13.0	12.6	13.4	12.6	13.0	13.8	13.8	14.2	15.7
87.5°	5.1	5.8	5.1	5.3	5.4	5.6	5.5	5.4	6.0	5.8	5.8
90°	10.2	10.6	10.2	9.9	10.2	9.5	9.2	8.8	8.5	8.8	7.8
92.5°	17.0	17.7	17.3	18.4	19.0	20.8	23.6	29.8	41.0	54.3	59.8
95°	41.0	42.4	44.9	48.1	54.8	67.5	86.2	127.2	170.0	209.6	186.6
97.5°	111.6	114.6	124.2	140.1	166.2	208.4	254.0	317.1	347.4	324.8	237.8
100°	221.6	221.2	235.0	260.8	296.5	346.7	388.0	416.6	404.3	334.7	226.2
102.5°	325.0	333.2	344.7	365.1	392.9	424.7	448.8	449.7	407.1	316.3	209.2
105°	449.5	451.3	462.6	476.0	492.3	501.4	494.7	459.4	385.5	284.1	188.4
107.5°	521.2	524.4	528.2	532.8	532.5	519.9	488.9	431.5	347.8	255.7	175.1
110°	550.6	551.3	552.0	549.2	539.3	514.5	470.0	405.0	324.1	239.6	170.0



TEST NUMBER: P332272

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	556.5	556.4	553.7	544.9	526.8	495.0	445.1	378.7	303.4	228.8	167.1
115°	546.7	544.9	537.8	522.3	495.8	457.3	405.3	343.8	278.5	217.3	166.1
117.5°	515.4	513.0	502.9	485.1	457.4	418.3	371.7	318.6	263.4	210.5	166.7
120°	489.4	487.3	478.8	459.0	431.1	395.4	353.0	305.3	255.5	207.4	167.9
122.5°	465.1	462.4	453.1	435.3	410.5	377.3	338.0	294.9	249.0	205.5	169.8
125°	431.1	428.7	419.8	404.3	381.7	353.4	319.5	280.9	240.7	202.8	172.8
127.5°	403.1	400.9	392.9	379.6	359.5	333.7	303.1	268.8	233.3	201.6	176.2
130°	387.3	384.5	377.1	364.3	345.6	321.6	293.0	261.1	229.3	200.7	178.5
132.5°	371.8	369.8	363.2	350.5	332.9	310.0	283.3	254.1	225.7	200.4	180.2
135°	349.5	347.0	340.7	330.1	312.7	292.6	269.6	244.5	220.9	200.0	182.7
137.5°	326.0	324.3	319.0	308.2	293.7	276.2	256.4	235.8	216.7	199.2	184.4
140°	309.6	309.9	304.3	294.4	280.9	265.7	248.8	230.8	214.1	199.0	185.5
142.5°	294.3	294.6	289.6	280.8	269.3	256.1	241.4	226.0	211.9	198.4	186.4
145°	273.2	272.5	269.6	262.2	253.4	243.1	231.8	220.2	208.8	197.5	186.9
147.5°	255.8	255.5	252.8	247.8	241.1	233.8	224.7	215.4	205.9	196.2	186.9
150°	245.6	245.6	243.5	239.6	234.3	227.6	220.2	212.0	203.9	195.1	186.9
152.5°	237.1	237.1	235.8	232.2	228.1	222.5	215.9	208.9	201.6	193.7	186.1
155°	226.5	226.2	225.5	222.6	219.4	215.2	209.9	204.3	198.2	191.2	185.2
157.5°	216.8	216.9	216.3	214.2	211.5	208.1	204.0	199.3	194.4	189.0	184.0
160°	210.6	211.0	211.0	208.8	206.4	203.9	200.4	196.5	191.9	187.3	183.4
162.5°	205.0	205.3	205.3	203.5	201.9	199.7	196.4	193.1	189.3	185.6	182.3
165°	197.5	197.5	197.9	196.5	195.1	193.3	190.8	188.7	185.9	183.1	180.6
167.5°	190.5	190.5	190.8	189.8	189.2	187.9	186.5	184.9	182.6	180.5	178.9
170°	186.2	186.2	186.6	185.9	185.5	184.8	183.4	182.3	180.6	178.8	177.8
172.5°	182.3	182.6	183.2	182.5	182.4	182.0	180.9	180.1	178.6	177.4	176.9
175°	177.8	178.1	178.5	178.1	178.1	178.1	177.4	177.0	176.3	175.6	175.6
177.5°	175.1	175.1	175.7	175.4	175.7	175.7	175.4	175.1	174.9	174.6	174.9
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6



TEST NUMBER: P332272

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	923.8	922.9	918.6	913.7	907.3	903.0	899.6	897.8	892.3	885.5	880.9
5°	980.9	969.4	957.2	942.2	928.4	914.3	905.5	895.1	882.5	868.3	858.3
7.5°	1042.0	1019.5	995.2	970.2	945.4	923.2	903.6	886.8	866.7	846.4	832.1
10°	1088.9	1056.0	1021.9	987.0	955.2	925.4	902.4	879.8	855.7	832.3	814.7
12.5°	1131.5	1088.2	1048.9	1006.0	965.4	929.7	896.6	870.0	841.0	816.1	796.0
15°	1185.4	1141.0	1093.5	1028.4	974.4	929.2	889.0	854.1	818.9	788.3	768.7
17.5°	1235.8	1169.0	1105.2	1050.8	980.7	924.2	875.1	833.4	794.8	762.3	738.2
20°	1256.7	1192.0	1122.6	1053.3	984.4	921.2	864.1	818.1	777.9	741.1	718.9
22.5°	1269.2	1195.9	1122.9	1048.4	975.2	909.5	853.1	802.5	758.9	724.0	696.6
25°	1283.9	1196.5	1116.1	1042.6	967.9	896.6	829.6	776.0	728.9	691.7	662.6
27.5°	1293.5	1190.8	1095.7	1014.0	938.2	867.3	805.9	749.0	701.2	661.9	630.7
30°	1295.4	1186.2	1080.1	991.6	914.6	849.5	784.4	730.0	679.5	637.7	608.6
32.5°	1297.8	1174.9	1059.0	965.0	886.2	821.7	762.7	710.7	658.9	617.8	588.1
35°	1287.7	1168.6	1026.9	918.9	840.0	777.5	724.3	676.4	625.5	585.6	555.4
37.5°	1244.2	1143.7	993.6	866.9	784.4	726.6	683.2	641.5	594.8	551.8	523.3
40°	1200.4	1119.2	967.9	835.4	749.2	689.8	650.7	616.7	571.5	531.2	500.6
42.5°	1135.1	1085.8	943.4	802.3	709.3	652.1	619.2	587.2	547.6	506.7	477.9
45°	1015.4	1021.9	893.2	749.6	654.2	596.7	565.7	543.5	508.3	474.6	445.1
47.5°	865.2	926.1	834.3	693.4	596.1	542.1	515.0	495.6	471.9	438.8	411.9
50°	767.2	854.1	787.1	655.7	559.6	506.0	479.2	463.5	442.8	416.7	391.1
52.5°	676.8	770.2	730.1	613.7	520.1	471.0	444.8	431.9	415.5	391.0	367.8
55°	551.9	646.5	637.3	550.4	460.8	416.7	396.8	382.3	371.1	352.8	334.4
57.5°	446.4	536.1	540.9	479.9	408.5	365.0	347.9	336.9	329.6	315.8	298.8
60°	380.0	462.3	478.4	432.4	371.1	332.8	316.0	307.2	301.4	290.3	277.3
62.5°	324.8	394.9	413.1	380.0	335.3	299.4	286.3	277.8	273.9	264.3	252.8
65°	248.6	306.8	324.4	306.0	282.7	253.9	243.2	235.9	232.5	227.1	218.7
67.5°	186.9	229.4	248.7	235.7	227.3	209.1	202.3	198.4	195.3	191.7	184.6
70°	150.1	181.6	201.5	198.0	191.1	181.6	176.6	173.9	170.8	167.8	161.6
72.5°	120.7	142.3	161.0	162.8	157.1	155.2	150.8	149.7	147.8	144.2	140.8
75°	80.1	95.0	108.0	113.0	115.3	117.2	115.3	114.9	114.5	111.5	109.5
77.5°	52.5	60.5	68.7	77.2	80.8	83.4	84.0	85.4	84.4	82.8	81.9
80°	40.2	42.1	47.9	55.2	60.9	63.2	64.7	65.5	65.1	64.7	63.2
82.5°	29.2	30.8	33.5	38.6	43.4	47.3	48.2	48.0	48.9	49.1	47.9
85°	15.7	16.1	16.9	17.6	20.3	24.5	25.7	26.4	27.2	27.2	24.9
87.5°	6.2	5.7	6.1	6.0	6.8	6.9	8.6	9.9	10.4	9.3	9.5
90°	6.7	5.7	4.6	3.9	3.2	2.1	1.4	0.7	1.4	2.1	3.2
92.5°	44.9	29.7	20.4	15.2	12.2	9.5	6.5	4.4	6.5	9.5	12.2
95°	128.6	76.0	45.9	32.2	23.0	17.0	13.1	12.0	13.1	17.0	23.0
97.5°	141.1	81.8	53.1	38.2	29.1	23.9	20.8	20.5	20.8	23.9	29.1
100°	133.2	80.9	56.2	42.4	33.9	29.0	26.5	26.2	26.5	29.0	33.9
102.5°	126.4	82.1	59.9	47.2	39.6	34.9	32.7	32.1	32.7	34.9	39.6
105°	121.6	85.2	66.1	55.1	48.4	44.2	42.1	41.0	42.1	44.2	48.4
107.5°	121.2	91.0	74.2	64.0	57.7	53.6	51.5	50.5	51.5	53.6	57.7
110°	122.6	95.8	79.9	70.0	64.0	60.1	58.3	57.2	58.3	60.1	64.0



TEST NUMBER: P332272

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	125.5	100.6	85.8	76.2	70.2	66.3	64.5	63.5	64.5	66.3	70.2
115°	130.0	108.5	95.1	85.5	79.5	76.0	73.9	72.4	73.9	76.0	79.5
117.5°	136.1	116.9	103.6	94.8	88.1	84.8	83.0	81.4	83.0	84.8	88.1
120°	140.6	122.3	109.5	100.7	94.0	90.5	88.7	87.6	88.7	90.5	94.0
122.5°	144.9	127.9	115.5	106.1	99.7	95.8	94.1	93.0	94.1	95.8	99.7
125°	151.6	136.1	123.7	114.1	107.4	103.5	101.4	100.7	101.4	103.5	107.4
127.5°	157.1	143.1	131.2	121.6	114.2	110.3	107.6	106.6	107.6	110.3	114.2
130°	160.8	147.4	135.7	126.2	118.7	114.5	111.3	110.3	111.3	114.5	118.7
132.5°	164.2	151.0	139.7	130.4	123.0	117.9	114.4	113.1	114.4	117.9	123.0
135°	168.6	156.5	145.6	136.1	128.6	123.3	119.4	118.0	119.4	123.3	128.6
137.5°	171.8	160.4	149.8	141.0	133.6	128.0	124.2	122.7	124.2	128.0	133.6
140°	173.5	162.9	152.7	143.8	136.8	131.1	127.6	125.8	127.6	131.1	136.8
142.5°	175.2	164.9	154.9	146.7	139.6	134.5	130.7	129.2	130.7	134.5	139.6
145°	177.0	167.5	158.3	150.2	144.2	138.9	135.7	134.6	135.7	138.9	144.2
147.5°	178.2	169.6	161.2	154.3	148.5	143.9	140.8	140.2	140.8	143.9	148.5
150°	178.5	171.0	162.9	156.5	151.6	147.0	144.2	143.8	144.2	147.0	151.6
152.5°	179.0	171.9	164.9	158.8	154.4	150.4	147.6	147.5	147.6	150.4	154.4
155°	179.2	173.5	167.5	162.6	158.7	155.1	153.0	153.0	153.0	155.1	158.7
157.5°	179.5	174.4	169.6	165.8	162.5	159.4	157.7	157.4	157.7	159.4	162.5
160°	179.5	175.3	171.0	167.5	165.0	162.2	160.8	160.8	160.8	162.2	165.0
162.5°	179.2	175.6	171.9	168.9	166.7	164.5	163.3	163.3	163.3	164.5	166.7
165°	178.5	176.0	173.2	170.7	169.3	167.5	166.8	167.1	166.8	167.5	169.3
167.5°	177.9	175.9	173.9	172.3	171.3	170.0	169.6	170.0	169.6	170.0	171.3
170°	177.0	175.6	173.9	173.2	172.4	171.4	171.0	171.7	171.0	171.4	172.4
172.5°	176.8	175.6	174.1	173.7	173.3	172.5	172.4	172.9	172.4	172.5	173.3
175°	176.0	175.3	174.6	174.2	174.2	173.5	173.9	174.2	173.9	173.5	174.2
177.5°	175.4	174.9	174.6	174.6	174.6	174.3	174.6	174.9	174.6	174.3	174.6
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6



TEST NUMBER: P332272

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	879.4	875.4	872.7	866.5	862.6	858.3	854.0	856.7	856.4	856.1	856.1
5°	849.9	841.1	833.1	822.7	816.2	808.2	802.0	801.3	802.8	797.4	794.4
7.5°	820.7	808.6	797.2	785.8	773.7	764.0	758.0	755.2	751.3	748.0	744.5
10°	800.1	786.0	774.8	760.7	747.7	736.2	728.9	723.9	721.2	718.5	713.6
12.5°	779.0	765.1	750.9	734.9	722.5	709.2	703.8	698.2	693.0	690.0	683.2
15°	748.0	730.0	715.1	698.2	684.5	671.4	663.8	652.7	651.1	647.3	640.4
17.5°	717.0	697.5	676.9	664.4	648.8	635.3	623.6	619.9	608.9	604.8	598.8
20°	692.5	674.5	658.8	642.3	619.7	607.1	597.9	592.9	584.1	578.7	574.9
22.5°	671.4	653.0	634.9	615.7	597.0	582.9	576.1	568.4	563.6	556.1	551.9
25°	641.2	621.3	599.4	578.7	565.3	554.6	543.9	537.0	530.1	526.6	519.0
27.5°	606.1	585.3	564.9	549.2	532.7	522.1	512.4	506.3	498.0	492.2	488.0
30°	586.8	562.3	544.7	530.5	509.4	499.5	492.2	484.5	478.4	472.3	468.0
32.5°	564.4	542.0	525.3	507.8	491.6	480.8	471.3	464.6	459.4	453.6	449.4
35°	529.3	510.6	493.3	475.7	463.8	452.7	441.6	435.9	430.9	425.5	421.7
37.5°	497.6	480.1	463.7	447.0	432.3	423.2	414.3	409.9	403.2	399.6	395.7
40°	478.0	460.8	443.2	427.1	411.7	404.9	396.8	390.3	384.2	381.5	377.3
42.5°	456.6	439.3	424.5	407.1	394.6	385.2	377.8	370.7	366.1	362.2	359.8
45°	424.8	409.4	394.9	377.7	365.8	357.7	349.3	342.8	338.6	335.9	331.7
47.5°	393.9	378.6	363.8	348.8	337.3	328.1	319.7	315.1	309.6	306.3	303.4
50°	371.5	357.7	342.0	328.2	316.8	307.6	300.7	294.9	289.9	285.7	283.8
52.5°	351.0	336.3	322.7	309.9	297.8	287.3	281.1	275.0	271.3	266.4	264.2
55°	317.1	303.0	291.5	278.8	267.0	258.2	250.5	245.1	241.3	235.9	232.9
57.5°	285.3	272.6	258.9	248.0	235.7	228.3	221.9	214.6	210.0	205.8	202.8
60°	263.9	249.3	237.5	227.1	216.4	206.8	201.1	195.3	190.4	186.1	183.5
62.5°	241.5	228.8	217.6	206.3	196.5	188.1	181.5	176.6	172.3	169.6	166.9
65°	207.2	197.3	185.8	176.6	167.4	161.3	155.9	151.7	148.6	146.7	144.4
67.5°	175.7	166.0	156.0	146.9	140.8	136.1	132.6	129.0	127.5	125.0	123.5
70°	155.1	145.2	136.4	129.5	123.3	119.9	117.6	114.9	113.4	110.3	108.8
72.5°	132.8	125.6	119.2	113.5	108.6	105.5	102.6	99.3	96.8	93.5	91.9
75°	104.6	98.1	93.1	89.2	86.2	82.0	77.8	74.3	73.2	72.0	71.6
77.5°	77.4	73.3	69.7	66.5	62.7	59.6	58.7	57.9	57.7	57.1	57.1
80°	60.9	57.1	54.4	50.6	48.3	48.3	48.3	47.5	47.9	47.9	47.9
82.5°	45.3	41.7	40.3	38.9	38.5	38.8	38.8	38.9	38.7	39.3	39.0
85°	23.4	23.7	24.5	24.1	24.5	24.5	25.3	24.9	25.3	24.5	25.3
87.5°	9.4	10.4	10.9	11.5	12.0	11.9	12.1	12.2	12.6	12.6	12.8
90°	3.9	4.6	5.7	6.7	7.8	8.8	8.5	8.8	9.2	9.5	10.2
92.5°	15.2	20.4	29.7	44.9	59.8	54.3	41.0	29.8	23.6	20.8	19.0
95°	32.2	45.9	76.0	128.6	186.6	209.6	170.0	127.2	86.2	67.5	54.8
97.5°	38.2	53.1	81.8	141.1	237.8	324.8	347.4	317.1	254.0	208.4	166.2
100°	42.4	56.2	80.9	133.2	226.2	334.7	404.3	416.6	388.0	346.7	296.5
102.5°	47.2	59.9	82.1	126.4	209.2	316.3	407.1	449.7	448.8	424.7	392.9
105°	55.1	66.1	85.2	121.6	188.4	284.1	385.5	459.4	494.7	501.4	492.3
107.5°	64.0	74.2	91.0	121.2	175.1	255.7	347.8	431.5	488.9	519.9	532.5
110°	70.0	79.9	95.8	122.6	170.0	239.6	324.1	405.0	470.0	514.5	539.3



TEST NUMBER: P332272

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	76.2	85.8	100.6	125.5	167.1	228.8	303.4	378.7	445.1	495.0	526.8
115°	85.5	95.1	108.5	130.0	166.1	217.3	278.5	343.8	405.3	457.3	495.8
117.5°	94.8	103.6	116.9	136.1	166.7	210.5	263.4	318.6	371.7	418.3	457.4
120°	100.7	109.5	122.3	140.6	167.9	207.4	255.5	305.3	353.0	395.4	431.1
122.5°	106.1	115.5	127.9	144.9	169.8	205.5	249.0	294.9	338.0	377.3	410.5
125°	114.1	123.7	136.1	151.6	172.8	202.8	240.7	280.9	319.5	353.4	381.7
127.5°	121.6	131.2	143.1	157.1	176.2	201.6	233.3	268.8	303.1	333.7	359.5
130°	126.2	135.7	147.4	160.8	178.5	200.7	229.3	261.1	293.0	321.6	345.6
132.5°	130.4	139.7	151.0	164.2	180.2	200.4	225.7	254.1	283.3	310.0	332.9
135°	136.1	145.6	156.5	168.6	182.7	200.0	220.9	244.5	269.6	292.6	312.7
137.5°	141.0	149.8	160.4	171.8	184.4	199.2	216.7	235.8	256.4	276.2	293.7
140°	143.8	152.7	162.9	173.5	185.5	199.0	214.1	230.8	248.8	265.7	280.9
142.5°	146.7	154.9	164.9	175.2	186.4	198.4	211.9	226.0	241.4	256.1	269.3
145°	150.2	158.3	167.5	177.0	186.9	197.5	208.8	220.2	231.8	243.1	253.4
147.5°	154.3	161.2	169.6	178.2	186.9	196.2	205.9	215.4	224.7	233.8	241.1
150°	156.5	162.9	171.0	178.5	186.9	195.1	203.9	212.0	220.2	227.6	234.3
152.5°	158.8	164.9	171.9	179.0	186.1	193.7	201.6	208.9	215.9	222.5	228.1
155°	162.6	167.5	173.5	179.2	185.2	191.2	198.2	204.3	209.9	215.2	219.4
157.5°	165.8	169.6	174.4	179.5	184.0	189.0	194.4	199.3	204.0	208.1	211.5
160°	167.5	171.0	175.3	179.5	183.4	187.3	191.9	196.5	200.4	203.9	206.4
162.5°	168.9	171.9	175.6	179.2	182.3	185.6	189.3	193.1	196.4	199.7	201.9
165°	170.7	173.2	176.0	178.5	180.6	183.1	185.9	188.7	190.8	193.3	195.1
167.5°	172.3	173.9	175.9	177.9	178.9	180.5	182.6	184.9	186.5	187.9	189.2
170°	173.2	173.9	175.6	177.0	177.8	178.8	180.6	182.3	183.4	184.8	185.5
172.5°	173.7	174.1	175.6	176.8	176.9	177.4	178.6	180.1	180.9	182.0	182.4
175°	174.2	174.6	175.3	176.0	175.6	175.6	176.3	177.0	177.4	178.1	178.1
177.5°	174.6	174.6	174.9	175.4	174.9	174.6	174.9	175.1	175.4	175.7	175.7
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6



TEST NUMBER: P332272

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	852.4	852.1	852.4	851.2	852.4	852.1	852.4	856.1	856.1	856.4	856.7
5°	793.2	792.8	791.7	788.3	791.7	792.8	793.2	794.4	797.4	802.8	801.3
7.5°	741.5	741.0	737.6	737.7	737.6	741.0	741.5	744.5	748.0	751.3	755.2
10°	710.9	711.3	706.7	704.0	706.7	711.3	710.9	713.6	718.5	721.2	723.9
12.5°	681.2	679.4	675.7	672.7	675.7	679.4	681.2	683.2	690.0	693.0	698.2
15°	641.9	638.1	628.9	629.7	628.9	638.1	641.9	640.4	647.3	651.1	652.7
17.5°	595.7	592.9	592.8	587.4	592.8	592.9	595.7	598.8	604.8	608.9	619.9
20°	568.8	566.9	567.6	562.3	567.6	566.9	568.8	574.9	578.7	584.1	592.9
22.5°	547.6	545.7	542.5	540.8	542.5	545.7	547.6	551.9	556.1	563.6	568.4
25°	516.7	513.6	510.6	512.5	510.6	513.6	516.7	519.0	526.6	530.1	537.0
27.5°	485.7	483.4	480.4	480.0	480.4	483.4	485.7	488.0	492.2	498.0	506.3
30°	466.1	463.8	462.3	460.4	462.3	463.8	466.1	468.0	472.3	478.4	484.5
32.5°	446.2	445.8	443.0	442.6	443.0	445.8	446.2	449.4	453.6	459.4	464.6
35°	420.2	417.9	417.1	417.5	417.1	417.9	420.2	421.7	425.5	430.9	435.9
37.5°	395.4	392.4	391.0	389.6	391.0	392.4	395.4	395.7	399.6	403.2	409.9
40°	377.7	374.6	373.8	373.1	373.8	374.6	377.7	377.3	381.5	384.2	390.3
42.5°	357.7	356.5	356.1	354.7	356.1	356.5	357.7	359.8	362.2	366.1	370.7
45°	330.5	330.2	327.9	328.6	327.9	330.2	330.5	331.7	335.9	338.6	342.8
47.5°	301.9	300.2	298.6	299.7	298.6	300.2	301.9	303.4	306.3	309.6	315.1
50°	282.3	281.5	278.1	278.8	278.1	281.5	282.3	283.8	285.7	289.9	294.9
52.5°	262.7	259.8	258.5	258.0	258.5	259.8	262.7	264.2	266.4	271.3	275.0
55°	230.2	226.7	225.2	224.4	225.2	226.7	230.2	232.9	235.9	241.3	245.1
57.5°	198.3	197.4	196.2	197.0	196.2	197.4	198.3	202.8	205.8	210.0	214.6
60°	179.6	179.6	179.6	179.3	179.6	179.6	179.6	183.5	186.1	190.4	195.3
62.5°	165.2	164.3	164.0	164.5	164.0	164.3	165.2	166.9	169.6	172.3	176.6
65°	143.2	142.9	141.3	141.0	141.3	142.9	143.2	144.4	146.7	148.6	151.7
67.5°	122.5	121.1	120.7	120.1	120.7	121.1	122.5	123.5	125.0	127.5	129.0
70°	106.9	106.1	103.8	104.2	103.8	106.1	106.9	108.8	110.3	113.4	114.9
72.5°	90.0	89.2	88.8	88.2	88.8	89.2	90.0	91.9	93.5	96.8	99.3
75°	71.2	70.9	70.5	72.0	70.5	70.9	71.2	71.6	72.0	73.2	74.3
77.5°	57.1	57.1	57.3	56.7	57.3	57.1	57.1	57.1	57.1	57.7	57.9
80°	47.9	47.9	47.5	47.5	47.5	47.9	47.9	47.9	47.9	47.9	47.5
82.5°	38.4	38.7	38.9	38.3	38.9	38.7	38.4	39.0	39.3	38.7	38.9
85°	25.3	24.9	25.7	25.3	25.7	24.9	25.3	25.3	24.5	25.3	24.9
87.5°	13.3	12.8	12.8	13.1	12.8	12.8	13.3	12.8	12.6	12.6	12.2
90°	9.9	10.2	10.6	10.2	10.6	10.2	9.9	10.2	9.5	9.2	8.8
92.5°	18.4	17.3	17.7	17.0	17.7	17.3	18.4	19.0	20.8	23.6	29.8
95°	48.1	44.9	42.4	41.0	42.4	44.9	48.1	54.8	67.5	86.2	127.2
97.5°	140.1	124.2	114.6	111.6	114.6	124.2	140.1	166.2	208.4	254.0	317.1
100°	260.8	235.0	221.2	221.6	221.2	235.0	260.8	296.5	346.7	388.0	416.6
102.5°	365.1	344.7	333.2	325.0	333.2	344.7	365.1	392.9	424.7	448.8	449.7
105°	476.0	462.6	451.3	449.5	451.3	462.6	476.0	492.3	501.4	494.7	459.4
107.5°	532.8	528.2	524.4	521.2	524.4	528.2	532.8	532.5	519.9	488.9	431.5
110°	549.2	552.0	551.3	550.6	551.3	552.0	549.2	539.3	514.5	470.0	405.0



TEST NUMBER: P332272

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	544.9	553.7	556.4	556.5	556.4	553.7	544.9	526.8	495.0	445.1	378.7
115°	522.3	537.8	544.9	546.7	544.9	537.8	522.3	495.8	457.3	405.3	343.8
117.5°	485.1	502.9	513.0	515.4	513.0	502.9	485.1	457.4	418.3	371.7	318.6
120°	459.0	478.8	487.3	489.4	487.3	478.8	459.0	431.1	395.4	353.0	305.3
122.5°	435.3	453.1	462.4	465.1	462.4	453.1	435.3	410.5	377.3	338.0	294.9
125°	404.3	419.8	428.7	431.1	428.7	419.8	404.3	381.7	353.4	319.5	280.9
127.5°	379.6	392.9	400.9	403.1	400.9	392.9	379.6	359.5	333.7	303.1	268.8
130°	364.3	377.1	384.5	387.3	384.5	377.1	364.3	345.6	321.6	293.0	261.1
132.5°	350.5	363.2	369.8	371.8	369.8	363.2	350.5	332.9	310.0	283.3	254.1
135°	330.1	340.7	347.0	349.5	347.0	340.7	330.1	312.7	292.6	269.6	244.5
137.5°	308.2	319.0	324.3	326.0	324.3	319.0	308.2	293.7	276.2	256.4	235.8
140°	294.4	304.3	309.9	309.6	309.9	304.3	294.4	280.9	265.7	248.8	230.8
142.5°	280.8	289.6	294.6	294.3	294.6	289.6	280.8	269.3	256.1	241.4	226.0
145°	262.2	269.6	272.5	273.2	272.5	269.6	262.2	253.4	243.1	231.8	220.2
147.5°	247.8	252.8	255.5	255.8	255.5	252.8	247.8	241.1	233.8	224.7	215.4
150°	239.6	243.5	245.6	245.6	245.6	243.5	239.6	234.3	227.6	220.2	212.0
152.5°	232.2	235.8	237.1	237.1	237.1	235.8	232.2	228.1	222.5	215.9	208.9
155°	222.6	225.5	226.2	226.5	226.2	225.5	222.6	219.4	215.2	209.9	204.3
157.5°	214.2	216.3	216.9	216.8	216.9	216.3	214.2	211.5	208.1	204.0	199.3
160°	208.8	211.0	211.0	210.6	211.0	211.0	208.8	206.4	203.9	200.4	196.5
162.5°	203.5	205.3	205.3	205.0	205.3	205.3	203.5	201.9	199.7	196.4	193.1
165°	196.5	197.9	197.5	197.5	197.5	197.9	196.5	195.1	193.3	190.8	188.7
167.5°	189.8	190.8	190.5	190.5	190.5	190.8	189.8	189.2	187.9	186.5	184.9
170°	185.9	186.6	186.2	186.2	186.2	186.6	185.9	185.5	184.8	183.4	182.3
172.5°	182.5	183.2	182.6	182.3	182.6	183.2	182.5	182.4	182.0	180.9	180.1
175°	178.1	178.5	178.1	177.8	178.1	178.5	178.1	178.1	178.1	177.4	177.0
177.5°	175.4	175.7	175.1	175.1	175.1	175.7	175.4	175.7	175.7	175.4	175.1
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6



TEST NUMBER: P332272

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	854.0	858.3	862.6	866.5	872.7	875.4	879.4	880.9	885.5	892.3	897.8
5°	802.0	808.2	816.2	822.7	833.1	841.1	849.9	858.3	868.3	882.5	895.1
7.5°	758.0	764.0	773.7	785.8	797.2	808.6	820.7	832.1	846.4	866.7	886.8
10°	728.9	736.2	747.7	760.7	774.8	786.0	800.1	814.7	832.3	855.7	879.8
12.5°	703.8	709.2	722.5	734.9	750.9	765.1	779.0	796.0	816.1	841.0	870.0
15°	663.8	671.4	684.5	698.2	715.1	730.0	748.0	768.7	788.3	818.9	854.1
17.5°	623.6	635.3	648.8	664.4	676.9	697.5	717.0	738.2	762.3	794.8	833.4
20°	597.9	607.1	619.7	642.3	658.8	674.5	692.5	718.9	741.1	777.9	818.1
22.5°	576.1	582.9	597.0	615.7	634.9	653.0	671.4	696.6	724.0	758.9	802.5
25°	543.9	554.6	565.3	578.7	599.4	621.3	641.2	662.6	691.7	728.9	776.0
27.5°	512.4	522.1	532.7	549.2	564.9	585.3	606.1	630.7	661.9	701.2	749.0
30°	492.2	499.5	509.4	530.5	544.7	562.3	586.8	608.6	637.7	679.5	730.0
32.5°	471.3	480.8	491.6	507.8	525.3	542.0	564.4	588.1	617.8	658.9	710.7
35°	441.6	452.7	463.8	475.7	493.3	510.6	529.3	555.4	585.6	625.5	676.4
37.5°	414.3	423.2	432.3	447.0	463.7	480.1	497.6	523.3	551.8	594.8	641.5
40°	396.8	404.9	411.7	427.1	443.2	460.8	478.0	500.6	531.2	571.5	616.7
42.5°	377.8	385.2	394.6	407.1	424.5	439.3	456.6	477.9	506.7	547.6	587.2
45°	349.3	357.7	365.8	377.7	394.9	409.4	424.8	445.1	474.6	508.3	543.5
47.5°	319.7	328.1	337.3	348.8	363.8	378.6	393.9	411.9	438.8	471.9	495.6
50°	300.7	307.6	316.8	328.2	342.0	357.7	371.5	391.1	416.7	442.8	463.5
52.5°	281.1	287.3	297.8	309.9	322.7	336.3	351.0	367.8	391.0	415.5	431.9
55°	250.5	258.2	267.0	278.8	291.5	303.0	317.1	334.4	352.8	371.1	382.3
57.5°	221.9	228.3	235.7	248.0	258.9	272.6	285.3	298.8	315.8	329.6	336.9
60°	201.1	206.8	216.4	227.1	237.5	249.3	263.9	277.3	290.3	301.4	307.2
62.5°	181.5	188.1	196.5	206.3	217.6	228.8	241.5	252.8	264.3	273.9	277.8
65°	155.9	161.3	167.4	176.6	185.8	197.3	207.2	218.7	227.1	232.5	235.9
67.5°	132.6	136.1	140.8	146.9	156.0	166.0	175.7	184.6	191.7	195.3	198.4
70°	117.6	119.9	123.3	129.5	136.4	145.2	155.1	161.6	167.8	170.8	173.9
72.5°	102.6	105.5	108.6	113.5	119.2	125.6	132.8	140.8	144.2	147.8	149.7
75°	77.8	82.0	86.2	89.2	93.1	98.1	104.6	109.5	111.5	114.5	114.9
77.5°	58.7	59.6	62.7	66.5	69.7	73.3	77.4	81.9	82.8	84.4	85.4
80°	48.3	48.3	48.3	50.6	54.4	57.1	60.9	63.2	64.7	65.1	65.5
82.5°	38.8	38.8	38.5	38.9	40.3	41.7	45.3	47.9	49.1	48.9	48.0
85°	25.3	24.5	24.5	24.1	24.5	23.7	23.4	24.9	27.2	27.2	26.4
87.5°	12.1	11.9	12.0	11.5	10.9	10.4	9.4	9.5	9.3	10.4	9.9
90°	8.5	8.8	7.8	6.7	5.7	4.6	3.9	3.2	2.1	1.4	0.7
92.5°	41.0	54.3	59.8	44.9	29.7	20.4	15.2	12.2	9.5	6.5	4.4
95°	170.0	209.6	186.6	128.6	76.0	45.9	32.2	23.0	17.0	13.1	12.0
97.5°	347.4	324.8	237.8	141.1	81.8	53.1	38.2	29.1	23.9	20.8	20.5
100°	404.3	334.7	226.2	133.2	80.9	56.2	42.4	33.9	29.0	26.5	26.2
102.5°	407.1	316.3	209.2	126.4	82.1	59.9	47.2	39.6	34.9	32.7	32.1
105°	385.5	284.1	188.4	121.6	85.2	66.1	55.1	48.4	44.2	42.1	41.0
107.5°	347.8	255.7	175.1	121.2	91.0	74.2	64.0	57.7	53.6	51.5	50.5
110°	324.1	239.6	170.0	122.6	95.8	79.9	70.0	64.0	60.1	58.3	57.2



TEST NUMBER: P332272

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	303.4	228.8	167.1	125.5	100.6	85.8	76.2	70.2	66.3	64.5	63.5
115°	278.5	217.3	166.1	130.0	108.5	95.1	85.5	79.5	76.0	73.9	72.4
117.5°	263.4	210.5	166.7	136.1	116.9	103.6	94.8	88.1	84.8	83.0	81.4
120°	255.5	207.4	167.9	140.6	122.3	109.5	100.7	94.0	90.5	88.7	87.6
122.5°	249.0	205.5	169.8	144.9	127.9	115.5	106.1	99.7	95.8	94.1	93.0
125°	240.7	202.8	172.8	151.6	136.1	123.7	114.1	107.4	103.5	101.4	100.7
127.5°	233.3	201.6	176.2	157.1	143.1	131.2	121.6	114.2	110.3	107.6	106.6
130°	229.3	200.7	178.5	160.8	147.4	135.7	126.2	118.7	114.5	111.3	110.3
132.5°	225.7	200.4	180.2	164.2	151.0	139.7	130.4	123.0	117.9	114.4	113.1
135°	220.9	200.0	182.7	168.6	156.5	145.6	136.1	128.6	123.3	119.4	118.0
137.5°	216.7	199.2	184.4	171.8	160.4	149.8	141.0	133.6	128.0	124.2	122.7
140°	214.1	199.0	185.5	173.5	162.9	152.7	143.8	136.8	131.1	127.6	125.8
142.5°	211.9	198.4	186.4	175.2	164.9	154.9	146.7	139.6	134.5	130.7	129.2
145°	208.8	197.5	186.9	177.0	167.5	158.3	150.2	144.2	138.9	135.7	134.6
147.5°	205.9	196.2	186.9	178.2	169.6	161.2	154.3	148.5	143.9	140.8	140.2
150°	203.9	195.1	186.9	178.5	171.0	162.9	156.5	151.6	147.0	144.2	143.8
152.5°	201.6	193.7	186.1	179.0	171.9	164.9	158.8	154.4	150.4	147.6	147.5
155°	198.2	191.2	185.2	179.2	173.5	167.5	162.6	158.7	155.1	153.0	153.0
157.5°	194.4	189.0	184.0	179.5	174.4	169.6	165.8	162.5	159.4	157.7	157.4
160°	191.9	187.3	183.4	179.5	175.3	171.0	167.5	165.0	162.2	160.8	160.8
162.5°	189.3	185.6	182.3	179.2	175.6	171.9	168.9	166.7	164.5	163.3	163.3
165°	185.9	183.1	180.6	178.5	176.0	173.2	170.7	169.3	167.5	166.8	167.1
167.5°	182.6	180.5	178.9	177.9	175.9	173.9	172.3	171.3	170.0	169.6	170.0
170°	180.6	178.8	177.8	177.0	175.6	173.9	173.2	172.4	171.4	171.0	171.7
172.5°	178.6	177.4	176.9	176.8	175.6	174.1	173.7	173.3	172.5	172.4	172.9
175°	176.3	175.6	175.6	176.0	175.3	174.6	174.2	174.2	173.5	173.9	174.2
177.5°	174.9	174.6	174.9	175.4	174.9	174.6	174.6	174.6	174.3	174.6	174.9
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6



TEST NUMBER: P332272

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	899.6	903.0	907.3	913.7	918.6	922.9	923.8	925.1	928.1	933.3	937.3
5°	905.5	914.3	928.4	942.2	957.2	969.4	980.9	989.0	996.6	1012.7	1025.7
7.5°	903.6	923.2	945.4	970.2	995.2	1019.5	1042.0	1062.2	1082.3	1105.7	1132.4
10°	902.4	925.4	955.2	987.0	1021.9	1056.0	1088.9	1114.6	1144.5	1171.3	1205.4
12.5°	896.6	929.7	965.4	1006.0	1048.9	1088.2	1131.5	1167.0	1201.1	1239.9	1279.5
15°	889.0	929.2	974.4	1028.4	1093.5	1141.0	1185.4	1247.1	1289.2	1331.4	1388.1
17.5°	875.1	924.2	980.7	1050.8	1105.2	1169.0	1235.8	1284.6	1341.3	1400.7	1452.0
20°	864.1	921.2	984.4	1053.3	1122.6	1192.0	1256.7	1314.9	1373.5	1442.1	1484.2
22.5°	853.1	909.5	975.2	1048.4	1122.9	1195.9	1269.2	1337.6	1403.5	1472.7	1526.5
25°	829.6	896.6	967.9	1042.6	1116.1	1196.5	1283.9	1360.1	1441.7	1512.9	1563.9
27.5°	805.9	867.3	938.2	1014.0	1095.7	1190.8	1293.5	1380.2	1461.9	1512.9	1528.9
30°	784.4	849.5	914.6	991.6	1080.1	1186.2	1295.4	1394.6	1461.6	1483.8	1467.3
32.5°	762.7	821.7	886.2	965.0	1059.0	1174.9	1297.8	1386.0	1426.4	1409.4	1342.3
35°	724.3	777.5	840.0	918.9	1026.9	1168.6	1287.7	1347.5	1337.5	1241.7	1115.3
37.5°	683.2	726.6	784.4	866.9	993.6	1143.7	1244.2	1253.0	1166.8	1019.8	873.8
40°	650.7	689.8	749.2	835.4	967.9	1119.2	1200.4	1164.8	1031.1	867.5	745.7
42.5°	619.2	652.1	709.3	802.3	943.4	1085.8	1135.1	1057.5	903.3	748.6	637.9
45°	565.7	596.7	654.2	749.6	893.2	1021.9	1015.4	880.6	726.2	601.7	509.8
47.5°	515.0	542.1	596.1	693.4	834.3	926.1	865.2	721.8	590.8	491.0	425.4
50°	479.2	506.0	559.6	655.7	787.1	854.1	767.2	628.9	509.0	426.3	374.2
52.5°	444.8	471.0	520.1	613.7	730.1	770.2	676.8	548.6	448.7	377.3	332.5
55°	396.8	416.7	460.8	550.4	637.3	646.5	551.9	444.7	362.3	312.5	281.9
57.5°	347.9	365.0	408.5	479.9	540.9	536.1	446.4	353.7	298.2	261.2	239.0
60°	316.0	332.8	371.1	432.4	478.4	462.3	380.0	305.3	257.8	230.6	213.0
62.5°	286.3	299.4	335.3	380.0	413.1	394.9	324.8	263.0	225.3	202.4	188.4
65°	243.2	253.9	282.7	306.0	324.4	306.8	248.6	205.7	178.5	162.4	152.8
67.5°	202.3	209.1	227.3	235.7	248.7	229.4	186.9	158.2	142.7	129.2	122.5
70°	176.6	181.6	191.1	198.0	201.5	181.6	150.1	129.1	116.1	106.5	102.3
72.5°	150.8	155.2	157.1	162.8	161.0	142.3	120.7	104.0	94.6	88.1	82.7
75°	115.3	117.2	115.3	113.0	108.0	95.0	80.1	71.6	64.7	61.7	59.8
77.5°	84.0	83.4	80.8	77.2	68.7	60.5	52.5	49.6	46.7	45.0	44.4
80°	64.7	63.2	60.9	55.2	47.9	42.1	40.2	38.3	37.2	35.2	34.9
82.5°	48.2	47.3	43.4	38.6	33.5	30.8	29.2	28.5	27.3	26.4	26.3
85°	25.7	24.5	20.3	17.6	16.9	16.1	15.7	15.7	14.2	13.8	13.8
87.5°	8.6	6.9	6.8	6.0	6.1	5.7	6.2	5.8	5.8	6.0	5.4
90°	1.4	2.1	3.2	3.9	4.6	5.7	6.7	7.8	8.8	8.5	8.8
92.5°	6.5	9.5	12.2	15.2	20.4	29.7	44.9	59.8	54.3	41.0	29.8
95°	13.1	17.0	23.0	32.2	45.9	76.0	128.6	186.6	209.6	170.0	127.2
97.5°	20.8	23.9	29.1	38.2	53.1	81.8	141.1	237.8	324.8	347.4	317.1
100°	26.5	29.0	33.9	42.4	56.2	80.9	133.2	226.2	334.7	404.3	416.6
102.5°	32.7	34.9	39.6	47.2	59.9	82.1	126.4	209.2	316.3	407.1	449.7
105°	42.1	44.2	48.4	55.1	66.1	85.2	121.6	188.4	284.1	385.5	459.4
107.5°	51.5	53.6	57.7	64.0	74.2	91.0	121.2	175.1	255.7	347.8	431.5
110°	58.3	60.1	64.0	70.0	79.9	95.8	122.6	170.0	239.6	324.1	405.0



TEST NUMBER: P332272

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	64.5	66.3	70.2	76.2	85.8	100.6	125.5	167.1	228.8	303.4	378.7
115°	73.9	76.0	79.5	85.5	95.1	108.5	130.0	166.1	217.3	278.5	343.8
117.5°	83.0	84.8	88.1	94.8	103.6	116.9	136.1	166.7	210.5	263.4	318.6
120°	88.7	90.5	94.0	100.7	109.5	122.3	140.6	167.9	207.4	255.5	305.3
122.5°	94.1	95.8	99.7	106.1	115.5	127.9	144.9	169.8	205.5	249.0	294.9
125°	101.4	103.5	107.4	114.1	123.7	136.1	151.6	172.8	202.8	240.7	280.9
127.5°	107.6	110.3	114.2	121.6	131.2	143.1	157.1	176.2	201.6	233.3	268.8
130°	111.3	114.5	118.7	126.2	135.7	147.4	160.8	178.5	200.7	229.3	261.1
132.5°	114.4	117.9	123.0	130.4	139.7	151.0	164.2	180.2	200.4	225.7	254.1
135°	119.4	123.3	128.6	136.1	145.6	156.5	168.6	182.7	200.0	220.9	244.5
137.5°	124.2	128.0	133.6	141.0	149.8	160.4	171.8	184.4	199.2	216.7	235.8
140°	127.6	131.1	136.8	143.8	152.7	162.9	173.5	185.5	199.0	214.1	230.8
142.5°	130.7	134.5	139.6	146.7	154.9	164.9	175.2	186.4	198.4	211.9	226.0
145°	135.7	138.9	144.2	150.2	158.3	167.5	177.0	186.9	197.5	208.8	220.2
147.5°	140.8	143.9	148.5	154.3	161.2	169.6	178.2	186.9	196.2	205.9	215.4
150°	144.2	147.0	151.6	156.5	162.9	171.0	178.5	186.9	195.1	203.9	212.0
152.5°	147.6	150.4	154.4	158.8	164.9	171.9	179.0	186.1	193.7	201.6	208.9
155°	153.0	155.1	158.7	162.6	167.5	173.5	179.2	185.2	191.2	198.2	204.3
157.5°	157.7	159.4	162.5	165.8	169.6	174.4	179.5	184.0	189.0	194.4	199.3
160°	160.8	162.2	165.0	167.5	171.0	175.3	179.5	183.4	187.3	191.9	196.5
162.5°	163.3	164.5	166.7	168.9	171.9	175.6	179.2	182.3	185.6	189.3	193.1
165°	166.8	167.5	169.3	170.7	173.2	176.0	178.5	180.6	183.1	185.9	188.7
167.5°	169.6	170.0	171.3	172.3	173.9	175.9	177.9	178.9	180.5	182.6	184.9
170°	171.0	171.4	172.4	173.2	173.9	175.6	177.0	177.8	178.8	180.6	182.3
172.5°	172.4	172.5	173.3	173.7	174.1	175.6	176.8	176.9	177.4	178.6	180.1
175°	173.9	173.5	174.2	174.2	174.6	175.3	176.0	175.6	175.6	176.3	177.0
177.5°	174.6	174.3	174.6	174.6	174.6	174.9	175.4	174.9	174.6	174.9	175.1
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6



TEST NUMBER: P332272

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	943.8	943.8	945.0	949.6	950.2	954.2	952.9
5°	1037.2	1044.5	1047.2	1058.7	1065.6	1068.6	1062.5
7.5°	1151.5	1172.0	1181.8	1193.8	1204.4	1207.7	1199.3
10°	1234.9	1256.3	1274.3	1285.4	1295.8	1302.6	1311.5
12.5°	1315.4	1341.8	1358.9	1374.6	1385.2	1394.0	1395.4
15°	1403.0	1442.8	1473.1	1495.3	1506.4	1512.2	1509.9
17.5°	1491.3	1528.2	1549.8	1572.4	1587.8	1588.6	1589.1
20°	1541.3	1577.3	1602.2	1619.0	1636.3	1635.5	1639.3
22.5°	1574.7	1603.0	1622.1	1634.3	1640.2	1637.3	1638.1
25°	1590.3	1598.7	1595.3	1575.7	1570.8	1552.8	1555.8
27.5°	1509.7	1469.9	1428.7	1375.6	1333.8	1300.4	1302.1
30°	1400.3	1329.8	1249.4	1182.0	1121.5	1104.6	1068.6
32.5°	1247.4	1141.7	1047.5	984.7	932.7	918.6	887.2
35°	988.2	885.5	788.6	730.4	707.4	675.3	674.9
37.5°	768.1	677.7	626.5	582.8	559.9	540.4	538.5
40°	646.2	575.7	537.0	505.6	483.0	468.4	465.0
42.5°	561.0	504.0	467.7	448.3	430.9	423.4	417.8
45°	458.1	419.8	394.5	376.9	368.8	363.1	360.0
47.5°	383.2	357.5	340.3	328.6	322.0	316.0	317.6
50°	342.4	321.4	308.7	297.6	292.6	288.4	288.8
52.5°	309.6	290.7	280.5	272.5	266.3	263.3	261.8
55°	262.8	250.9	240.5	234.8	231.3	227.1	226.0
57.5°	224.1	214.9	206.5	200.0	199.2	195.1	195.6
60°	198.4	190.7	183.8	180.4	177.7	174.3	175.4
62.5°	177.3	170.8	164.5	161.7	159.0	156.5	157.0
65°	145.2	139.0	135.2	133.7	132.5	131.4	130.2
67.5°	115.7	111.9	109.5	106.2	103.9	103.5	102.3
70°	97.3	92.3	88.1	83.9	82.7	82.3	82.7
72.5°	78.0	74.8	73.7	71.6	71.4	70.4	71.1
75°	58.6	57.5	56.7	55.2	55.2	55.2	55.2
77.5°	43.2	42.5	42.1	41.7	41.4	40.8	40.8
80°	33.7	33.3	32.6	32.6	32.2	32.6	32.2
82.5°	25.4	25.4	24.6	24.6	24.2	24.0	24.2
85°	13.0	12.6	13.4	12.6	13.0	12.3	13.0
87.5°	5.5	5.6	5.4	5.3	5.1	5.8	5.1
90°	9.2	9.5	10.2	9.9	10.2	10.6	10.2
92.5°	23.6	20.8	19.0	18.4	17.3	17.7	17.0
95°	86.2	67.5	54.8	48.1	44.9	42.4	41.0
97.5°	254.0	208.4	166.2	140.1	124.2	114.6	111.6
100°	388.0	346.7	296.5	260.8	235.0	221.2	221.6
102.5°	448.8	424.7	392.9	365.1	344.7	333.2	325.0
105°	494.7	501.4	492.3	476.0	462.6	451.3	449.5
107.5°	488.9	519.9	532.5	532.8	528.2	524.4	521.2
110°	470.0	514.5	539.3	549.2	552.0	551.3	550.6



TEST NUMBER: P332272

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	445.1	495.0	526.8	544.9	553.7	556.4	556.5
115°	405.3	457.3	495.8	522.3	537.8	544.9	546.7
117.5°	371.7	418.3	457.4	485.1	502.9	513.0	515.4
120°	353.0	395.4	431.1	459.0	478.8	487.3	489.4
122.5°	338.0	377.3	410.5	435.3	453.1	462.4	465.1
125°	319.5	353.4	381.7	404.3	419.8	428.7	431.1
127.5°	303.1	333.7	359.5	379.6	392.9	400.9	403.1
130°	293.0	321.6	345.6	364.3	377.1	384.5	387.3
132.5°	283.3	310.0	332.9	350.5	363.2	369.8	371.8
135°	269.6	292.6	312.7	330.1	340.7	347.0	349.5
137.5°	256.4	276.2	293.7	308.2	319.0	324.3	326.0
140°	248.8	265.7	280.9	294.4	304.3	309.9	309.6
142.5°	241.4	256.1	269.3	280.8	289.6	294.6	294.3
145°	231.8	243.1	253.4	262.2	269.6	272.5	273.2
147.5°	224.7	233.8	241.1	247.8	252.8	255.5	255.8
150°	220.2	227.6	234.3	239.6	243.5	245.6	245.6
152.5°	215.9	222.5	228.1	232.2	235.8	237.1	237.1
155°	209.9	215.2	219.4	222.6	225.5	226.2	226.5
157.5°	204.0	208.1	211.5	214.2	216.3	216.9	216.8
160°	200.4	203.9	206.4	208.8	211.0	211.0	210.6
162.5°	196.4	199.7	201.9	203.5	205.3	205.3	205.0
165°	190.8	193.3	195.1	196.5	197.9	197.5	197.5
167.5°	186.5	187.9	189.2	189.8	190.8	190.5	190.5
170°	183.4	184.8	185.5	185.9	186.6	186.2	186.2
172.5°	180.9	182.0	182.4	182.5	183.2	182.6	182.3
175°	177.4	178.1	178.1	178.1	178.5	178.1	177.8
177.5°	175.4	175.7	175.7	175.4	175.7	175.1	175.1
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6

(END OF REPORT)