

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332277

Luminaire Tested: **S123RDIP-S560D585U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332277
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D585U835-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4241.7 lumens
Efficiency: N/A
Efficacy: 129.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332277

CATALOG NUMBER: S123RDIP-S560D585U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332277

CATALOG NUMBER: S123RDIP-S560D585U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	53
1	99	95	91	88	92	88	85	82	75	73	71	63	62	60	53	52	51	46
2	91	84	78	73	84	78	73	68	67	63	60	56	54	51	47	45	44	39
3	83	74	67	61	77	69	63	58	59	55	51	50	47	44	42	40	38	34
4	76	66	58	52	70	61	55	50	53	48	44	45	42	38	38	35	33	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26
6	65	53	45	40	60	50	43	38	43	38	34	37	33	30	32	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	27	29	26	23	21
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	23	21	19
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	21	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9630	9630	9630	9630
5°	11480	9672	8518	9672
10°	14335	9616	7695	9616
15°	16826	9518	7017	9518
20°	18778	9371	6441	9371
25°	18478	9216	6087	9216
30°	13282	9073	5722	9073
35°	8868	8888	5486	8888
40°	6534	8665	5243	8665
45°	5480	8273	5002	8273
50°	4836	7762	4669	7762
55°	4241	7174	4211	7174
60°	3776	6613	3860	6613
65°	3316	6008	3591	6008
70°	2603	5473	3279	5473
75°	2296	4779	2994	4779
80°	1996	4060	2944	4060
85°	1606	3260	3125	3260



TEST NUMBER: P332277

CATALOG NUMBER: S123RDIP-S560D585U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.0	2.1
10°-20°	274.9	6.5
20°-30°	431.9	10.2
30°-40°	450.6	10.6
40°-50°	385.6	9.1
50°-60°	293.9	6.9
60°-70°	188.4	4.4
70°-80°	90.6	2.1
80°-90°	26.1	0.6
90°-100°	47.3	1.1
100°-110°	141.6	3.3
110°-120°	240.8	5.7
120°-130°	316.7	7.5
130°-140°	356.0	8.4
140°-150°	349.9	8.3
150°-160°	294.6	6.9
160°-170°	196.1	4.6
170°-180°	68.7	1.6
0°-30°	794.7	18.7
0°-40°	1245.3	29.4
0°-60°	1924.8	45.4
0°-90°	2229.9	52.6
90°-120°	429.7	10.1
90°-150°	1452.4	34.2
90°-180°	2012.0	47.4
0°-180°	4241.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	895	895	895	895	895	
5°	1062	895	788	895	1062	110
15°	1510	854	630	854	1510	428
25°	1556	776	512	776	1556	669
35°	675	676	418	676	675	442
45°	360	544	329	544	360	283
55°	226	382	224	382	226	204
65°	130	236	141	236	130	128
75°	55	115	72	115	55	59
85°	13	26	25	26	13	15
90°	17	1	17	1	17	9
95°	44	34	44	34	44	46
105°	136	128	136	128	136	144
115°	243	242	243	242	243	241
125°	351	355	351	355	351	314
135°	460	460	460	460	460	353
145°	558	558	558	558	558	349
155°	638	639	638	639	638	294
165°	694	696	694	696	694	196
175°	722	724	722	724	722	69
180°	726	726	726	726	726	



TEST NUMBER: P332277

CATALOG NUMBER: S123RDIP-S560D585U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	952.9	954.2	950.2	949.6	945.0	943.8	943.8	937.3	933.3	928.1	925.1
5°	1062.5	1068.6	1065.6	1058.7	1047.2	1044.5	1037.2	1025.7	1012.7	996.6	989.0
7.5°	1199.3	1207.7	1204.4	1193.8	1181.8	1172.0	1151.5	1132.4	1105.7	1082.3	1062.2
10°	1311.5	1302.6	1295.8	1285.4	1274.3	1256.3	1234.9	1205.4	1171.3	1144.5	1114.6
12.5°	1395.4	1394.0	1385.2	1374.6	1358.9	1341.8	1315.4	1279.5	1239.9	1201.1	1167.0
15°	1509.9	1512.2	1506.4	1495.3	1473.1	1442.8	1403.0	1388.1	1331.4	1289.2	1247.1
17.5°	1589.1	1588.6	1587.8	1572.4	1549.8	1528.2	1491.3	1452.0	1400.7	1341.3	1284.6
20°	1639.3	1635.5	1636.3	1619.0	1602.2	1577.3	1541.3	1484.2	1442.1	1373.5	1314.9
22.5°	1638.1	1637.3	1640.2	1634.3	1622.1	1603.0	1574.7	1526.5	1472.7	1403.5	1337.6
25°	1555.8	1552.8	1570.8	1575.7	1595.3	1598.7	1590.3	1563.9	1512.9	1441.7	1360.1
27.5°	1302.1	1300.4	1333.8	1375.6	1428.7	1469.9	1509.7	1528.9	1512.9	1461.9	1380.2
30°	1068.6	1104.6	1121.5	1182.0	1249.4	1329.8	1400.3	1467.3	1483.8	1461.6	1394.6
32.5°	887.2	918.6	932.7	984.7	1047.5	1141.7	1247.4	1342.3	1409.4	1426.4	1386.0
35°	674.9	675.3	707.4	730.4	788.6	885.5	988.2	1115.3	1241.7	1337.5	1347.5
37.5°	538.5	540.4	559.9	582.8	626.5	677.7	768.1	873.8	1019.8	1166.8	1253.0
40°	465.0	468.4	483.0	505.6	537.0	575.7	646.2	745.7	867.5	1031.1	1164.8
42.5°	417.8	423.4	430.9	448.3	467.7	504.0	561.0	637.9	748.6	903.3	1057.5
45°	360.0	363.1	368.8	376.9	394.5	419.8	458.1	509.8	601.7	726.2	880.6
47.5°	317.6	316.0	322.0	328.6	340.3	357.5	383.2	425.4	491.0	590.8	721.8
50°	288.8	288.4	292.6	297.6	308.7	321.4	342.4	374.2	426.3	509.0	628.9
52.5°	261.8	263.3	266.3	272.5	280.5	290.7	309.6	332.5	377.3	448.7	548.6
55°	226.0	227.1	231.3	234.8	240.5	250.9	262.8	281.9	312.5	362.3	444.7
57.5°	195.6	195.1	199.2	200.0	206.5	214.9	224.1	239.0	261.2	298.2	353.7
60°	175.4	174.3	177.7	180.4	183.8	190.7	198.4	213.0	230.6	257.8	305.3
62.5°	157.0	156.5	159.0	161.7	164.5	170.8	177.3	188.4	202.4	225.3	263.0
65°	130.2	131.4	132.5	133.7	135.2	139.0	145.2	152.8	162.4	178.5	205.7
67.5°	102.3	103.5	103.9	106.2	109.5	111.9	115.7	122.5	129.2	142.7	158.2
70°	82.7	82.3	82.7	83.9	88.1	92.3	97.3	102.3	106.5	116.1	129.1
72.5°	71.1	70.4	71.4	71.6	73.7	74.8	78.0	82.7	88.1	94.6	104.0
75°	55.2	55.2	55.2	55.2	56.7	57.5	58.6	59.8	61.7	64.7	71.6
77.5°	40.8	40.8	41.4	41.7	42.1	42.5	43.2	44.4	45.0	46.7	49.6
80°	32.2	32.6	32.2	32.6	32.6	33.3	33.7	34.9	35.2	37.2	38.3
82.5°	24.2	24.0	24.2	24.6	24.6	25.4	25.4	26.3	26.4	27.3	28.5
85°	13.0	12.3	13.0	12.6	13.4	12.6	13.0	13.8	13.8	14.2	15.7
87.5°	6.5	7.0	6.4	6.6	6.6	6.8	6.7	6.6	7.1	6.7	6.7
90°	17.1	16.9	16.6	16.4	16.1	15.7	15.2	14.7	14.2	13.7	12.0
92.5°	23.0	23.2	23.3	23.5	23.7	23.5	23.1	22.7	22.3	21.9	21.0
95°	44.5	44.5	44.5	44.5	44.5	44.2	43.7	43.2	42.7	42.2	41.2
97.5°	68.4	68.5	68.5	68.6	68.6	68.4	67.8	67.2	66.6	66.1	65.3
100°	86.7	86.4	86.2	85.9	85.7	85.4	85.0	84.6	84.2	83.8	83.2
102.5°	105.4	105.5	105.5	105.6	105.6	105.4	105.1	104.7	104.3	103.9	103.1
105°	135.8	135.5	135.2	135.0	134.7	134.6	134.6	134.6	134.6	134.6	133.5
107.5°	167.4	167.5	167.7	167.8	168.0	167.8	167.4	167.0	166.6	166.2	165.8
110°	188.8	189.1	189.3	189.6	189.8	189.7	189.2	188.7	188.2	187.7	187.4



TEST NUMBER: P332277

CATALOG NUMBER: S123RDIP-S560D585U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	211.6	211.7	211.7	211.8	211.8	211.5	210.9	210.3	209.7	209.1	209.1
115°	243.0	243.1	243.2	243.4	243.5	243.5	243.4	243.2	243.1	243.0	243.2
117.5°	274.8	275.2	275.5	275.9	276.2	276.4	276.4	276.5	276.5	276.5	276.9
120°	297.2	297.4	297.7	297.9	298.2	298.4	298.5	298.6	298.8	298.9	299.5
122.5°	318.6	319.0	319.3	319.7	320.0	320.4	320.7	321.0	321.4	321.7	322.0
125°	350.8	351.3	351.8	352.3	352.8	353.3	353.8	354.3	354.8	355.4	355.6
127.5°	382.8	383.4	384.0	384.6	385.2	385.8	386.5	387.2	388.0	388.7	388.9
130°	403.8	404.7	405.6	406.5	407.4	408.1	408.6	409.1	409.6	410.1	410.5
132.5°	425.7	426.4	427.1	427.8	428.5	429.1	429.7	430.3	430.9	431.6	431.8
135°	459.7	460.0	460.2	460.5	460.7	461.1	461.6	462.1	462.7	463.2	463.3
137.5°	489.7	490.2	490.7	491.2	491.7	492.2	492.7	493.2	493.8	494.3	494.0
140°	509.4	510.2	511.1	512.0	512.9	513.4	513.5	513.7	513.8	513.9	513.8
142.5°	529.4	530.1	530.8	531.5	532.2	532.6	532.7	532.8	533.0	533.1	532.9
145°	558.4	558.9	559.4	559.9	560.4	560.8	560.9	561.0	561.1	561.3	560.9
147.5°	584.2	585.0	585.7	586.5	587.2	587.6	587.6	587.6	587.6	587.6	587.3
150°	600.6	601.4	602.1	602.9	603.7	604.0	604.0	604.0	604.0	604.0	603.8
152.5°	616.6	617.3	617.9	618.6	619.2	619.5	619.3	619.1	618.8	618.6	618.5
155°	638.3	639.2	640.0	640.9	641.8	642.0	641.5	641.0	640.5	640.0	639.9
157.5°	658.0	658.7	659.4	660.1	660.8	660.9	660.4	659.9	659.3	658.8	658.7
160°	670.8	671.3	671.8	672.3	672.8	672.7	672.1	671.5	670.8	670.2	670.2
162.5°	680.4	681.2	682.0	682.8	683.6	683.7	683.1	682.4	681.8	681.2	681.1
165°	694.2	695.1	695.9	696.8	697.7	697.8	697.0	696.3	695.5	694.7	694.7
167.5°	705.9	706.7	707.5	708.3	709.1	709.1	708.3	707.5	706.7	705.9	705.8
170°	711.8	712.7	713.6	714.5	715.4	715.4	714.5	713.6	712.7	711.8	711.8
172.5°	716.4	717.3	718.2	719.1	720.0	720.0	719.2	718.4	717.7	716.9	716.9
175°	721.5	722.4	723.3	724.2	725.1	725.2	724.4	723.6	722.9	722.1	722.1
177.5°	724.3	725.0	725.7	726.4	727.1	727.2	726.6	726.0	725.3	724.7	724.7
180°	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1



TEST NUMBER: P332277

CATALOG NUMBER: S123RDIP-S560D585U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	923.8	922.9	918.6	913.7	907.3	903.0	899.6	897.8	892.3	885.5	880.9
5°	980.9	969.4	957.2	942.2	928.4	914.3	905.5	895.1	882.5	868.3	858.3
7.5°	1042.0	1019.5	995.2	970.2	945.4	923.2	903.6	886.8	866.7	846.4	832.1
10°	1088.9	1056.0	1021.9	987.0	955.2	925.4	902.4	879.8	855.7	832.3	814.7
12.5°	1131.5	1088.2	1048.9	1006.0	965.4	929.7	896.6	870.0	841.0	816.1	796.0
15°	1185.4	1141.0	1093.5	1028.4	974.4	929.2	889.0	854.1	818.9	788.3	768.7
17.5°	1235.8	1169.0	1105.2	1050.8	980.7	924.2	875.1	833.4	794.8	762.3	738.2
20°	1256.7	1192.0	1122.6	1053.3	984.4	921.2	864.1	818.1	777.9	741.1	718.9
22.5°	1269.2	1195.9	1122.9	1048.4	975.2	909.5	853.1	802.5	758.9	724.0	696.6
25°	1283.9	1196.5	1116.1	1042.6	967.9	896.6	829.6	776.0	728.9	691.7	662.6
27.5°	1293.5	1190.8	1095.7	1014.0	938.2	867.3	805.9	749.0	701.2	661.9	630.7
30°	1295.4	1186.2	1080.1	991.6	914.6	849.5	784.4	730.0	679.5	637.7	608.6
32.5°	1297.8	1174.9	1059.0	965.0	886.2	821.7	762.7	710.7	658.9	617.8	588.1
35°	1287.7	1168.6	1026.9	918.9	840.0	777.5	724.3	676.4	625.5	585.6	555.4
37.5°	1244.2	1143.7	993.6	866.9	784.4	726.6	683.2	641.5	594.8	551.8	523.3
40°	1200.4	1119.2	967.9	835.4	749.2	689.8	650.7	616.7	571.5	531.2	500.6
42.5°	1135.1	1085.8	943.4	802.3	709.3	652.1	619.2	587.2	547.6	506.7	477.9
45°	1015.4	1021.9	893.2	749.6	654.2	596.7	565.7	543.5	508.3	474.6	445.1
47.5°	865.2	926.1	834.3	693.4	596.1	542.1	515.0	495.6	471.9	438.8	411.9
50°	767.2	854.1	787.1	655.7	559.6	506.0	479.2	463.5	442.8	416.7	391.1
52.5°	676.8	770.2	730.1	613.7	520.1	471.0	444.8	431.9	415.5	391.0	367.8
55°	551.9	646.5	637.3	550.4	460.8	416.7	396.8	382.3	371.1	352.8	334.4
57.5°	446.4	536.1	540.9	479.9	408.5	365.0	347.9	336.9	329.6	315.8	298.8
60°	380.0	462.3	478.4	432.4	371.1	332.8	316.0	307.2	301.4	290.3	277.3
62.5°	324.8	394.9	413.1	380.0	335.3	299.4	286.3	277.8	273.9	264.3	252.8
65°	248.6	306.8	324.4	306.0	282.7	253.9	243.2	235.9	232.5	227.1	218.7
67.5°	186.9	229.4	248.7	235.7	227.3	209.1	202.3	198.4	195.3	191.7	184.6
70°	150.1	181.6	201.5	198.0	191.1	181.6	176.6	173.9	170.8	167.8	161.6
72.5°	120.7	142.3	161.0	162.8	157.1	155.2	150.8	149.7	147.8	144.2	140.8
75°	80.1	95.0	108.0	113.0	115.3	117.2	115.3	114.9	114.5	111.5	109.5
77.5°	52.5	60.5	68.7	77.2	80.8	83.4	84.0	85.4	84.4	82.8	81.9
80°	40.2	42.1	47.9	55.2	60.9	63.2	64.7	65.5	65.1	64.7	63.2
82.5°	29.2	30.8	33.5	38.6	43.4	47.3	48.2	48.0	48.9	49.1	47.9
85°	15.7	16.1	16.9	17.6	20.3	24.5	25.7	26.4	27.2	27.2	24.9
87.5°	7.0	6.3	6.6	6.3	7.0	7.1	8.6	9.9	10.5	9.5	9.8
90°	10.4	8.7	7.1	5.6	4.4	3.1	1.8	0.6	1.8	3.1	4.4
92.5°	20.0	19.1	18.2	17.3	16.4	15.5	14.7	13.8	14.7	15.5	16.4
95°	40.2	39.2	38.2	37.2	36.3	35.4	34.5	33.7	34.5	35.4	36.3
97.5°	64.6	63.8	63.1	62.4	61.8	61.1	60.4	59.8	60.4	61.1	61.8
100°	82.6	81.9	81.3	80.6	79.9	79.1	78.3	77.6	78.3	79.1	79.9
102.5°	102.3	101.4	100.6	99.9	99.5	99.0	98.6	98.1	98.6	99.0	99.5
105°	132.3	131.2	130.0	129.4	129.1	128.8	128.6	128.3	128.6	128.8	129.1
107.5°	165.3	164.8	164.4	164.1	163.9	163.8	163.6	163.5	163.6	163.8	163.9
110°	187.2	186.9	186.6	186.4	186.1	185.9	185.6	185.4	185.6	185.9	186.1



TEST NUMBER: P332277

CATALOG NUMBER: S123RDIP-S560D585U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	209.0	209.0	208.9	208.8	208.6	208.5	208.3	208.2	208.3	208.5	208.6
115°	243.5	243.7	244.0	243.9	243.6	243.2	242.8	242.4	242.8	243.2	243.6
117.5°	277.2	277.5	277.8	277.9	277.6	277.4	277.1	276.9	277.1	277.4	277.6
120°	300.2	300.8	301.4	301.4	300.6	299.8	299.1	298.3	299.1	299.8	300.6
122.5°	322.4	322.7	323.0	322.9	322.3	321.8	321.2	320.7	321.2	321.8	322.3
125°	355.9	356.1	356.4	356.3	355.9	355.5	355.2	354.8	355.2	355.5	355.9
127.5°	389.2	389.5	389.8	389.5	388.7	387.9	387.1	386.3	387.1	387.9	388.7
130°	410.9	411.3	411.6	411.3	410.3	409.3	408.3	407.3	408.3	409.3	410.3
132.5°	432.1	432.4	432.7	432.3	431.3	430.3	429.3	428.2	429.3	430.3	431.3
135°	463.4	463.5	463.7	463.3	462.6	461.8	461.1	460.3	461.1	461.8	462.6
137.5°	493.6	493.3	493.0	492.5	491.9	491.2	490.6	490.0	490.6	491.2	491.9
140°	513.7	513.5	513.4	513.0	512.4	511.8	511.1	510.5	511.1	511.8	512.4
142.5°	532.6	532.4	532.2	531.7	531.1	530.5	529.8	529.2	529.8	530.5	531.1
145°	560.5	560.1	559.7	559.4	559.2	558.9	558.7	558.4	558.7	558.9	559.2
147.5°	586.9	586.6	586.2	585.8	585.3	584.9	584.4	584.0	584.4	584.9	585.3
150°	603.5	603.3	603.0	602.8	602.5	602.3	602.0	601.8	602.0	602.3	602.5
152.5°	618.3	618.2	618.0	617.8	617.4	617.1	616.7	616.4	616.7	617.1	617.4
155°	639.7	639.6	639.5	639.4	639.4	639.4	639.4	639.4	639.4	639.4	639.4
157.5°	658.6	658.5	658.4	658.4	658.6	658.7	658.9	659.0	658.9	658.7	658.6
160°	670.2	670.2	670.2	670.3	670.6	670.8	671.1	671.3	671.1	670.8	670.6
162.5°	681.0	680.9	680.8	680.9	681.2	681.6	681.9	682.3	681.9	681.6	681.2
165°	694.7	694.7	694.7	694.9	695.3	695.7	696.1	696.4	696.1	695.7	695.3
167.5°	705.7	705.6	705.5	705.7	706.2	706.7	707.2	707.7	707.2	706.7	706.2
170°	711.8	711.8	711.8	712.1	712.6	713.1	713.6	714.1	713.6	713.1	712.6
172.5°	716.9	716.9	716.9	717.1	717.6	718.1	718.6	719.1	718.6	718.1	717.6
175°	722.1	722.1	722.1	722.4	722.9	723.4	723.9	724.4	723.9	723.4	722.9
177.5°	724.7	724.7	724.7	724.9	725.3	725.8	726.2	726.6	726.2	725.8	725.3
180°	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1



TEST NUMBER: P332277

CATALOG NUMBER: S123RDIP-S560D585U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	879.4	875.4	872.7	866.5	862.6	858.3	854.0	856.7	856.4	856.1	856.1
5°	849.9	841.1	833.1	822.7	816.2	808.2	802.0	801.3	802.8	797.4	794.4
7.5°	820.7	808.6	797.2	785.8	773.7	764.0	758.0	755.2	751.3	748.0	744.5
10°	800.1	786.0	774.8	760.7	747.7	736.2	728.9	723.9	721.2	718.5	713.6
12.5°	779.0	765.1	750.9	734.9	722.5	709.2	703.8	698.2	693.0	690.0	683.2
15°	748.0	730.0	715.1	698.2	684.5	671.4	663.8	652.7	651.1	647.3	640.4
17.5°	717.0	697.5	676.9	664.4	648.8	635.3	623.6	619.9	608.9	604.8	598.8
20°	692.5	674.5	658.8	642.3	619.7	607.1	597.9	592.9	584.1	578.7	574.9
22.5°	671.4	653.0	634.9	615.7	597.0	582.9	576.1	568.4	563.6	556.1	551.9
25°	641.2	621.3	599.4	578.7	565.3	554.6	543.9	537.0	530.1	526.6	519.0
27.5°	606.1	585.3	564.9	549.2	532.7	522.1	512.4	506.3	498.0	492.2	488.0
30°	586.8	562.3	544.7	530.5	509.4	499.5	492.2	484.5	478.4	472.3	468.0
32.5°	564.4	542.0	525.3	507.8	491.6	480.8	471.3	464.6	459.4	453.6	449.4
35°	529.3	510.6	493.3	475.7	463.8	452.7	441.6	435.9	430.9	425.5	421.7
37.5°	497.6	480.1	463.7	447.0	432.3	423.2	414.3	409.9	403.2	399.6	395.7
40°	478.0	460.8	443.2	427.1	411.7	404.9	396.8	390.3	384.2	381.5	377.3
42.5°	456.6	439.3	424.5	407.1	394.6	385.2	377.8	370.7	366.1	362.2	359.8
45°	424.8	409.4	394.9	377.7	365.8	357.7	349.3	342.8	338.6	335.9	331.7
47.5°	393.9	378.6	363.8	348.8	337.3	328.1	319.7	315.1	309.6	306.3	303.4
50°	371.5	357.7	342.0	328.2	316.8	307.6	300.7	294.9	289.9	285.7	283.8
52.5°	351.0	336.3	322.7	309.9	297.8	287.3	281.1	275.0	271.3	266.4	264.2
55°	317.1	303.0	291.5	278.8	267.0	258.2	250.5	245.1	241.3	235.9	232.9
57.5°	285.3	272.6	258.9	248.0	235.7	228.3	221.9	214.6	210.0	205.8	202.8
60°	263.9	249.3	237.5	227.1	216.4	206.8	201.1	195.3	190.4	186.1	183.5
62.5°	241.5	228.8	217.6	206.3	196.5	188.1	181.5	176.6	172.3	169.6	166.9
65°	207.2	197.3	185.8	176.6	167.4	161.3	155.9	151.7	148.6	146.7	144.4
67.5°	175.7	166.0	156.0	146.9	140.8	136.1	132.6	129.0	127.5	125.0	123.5
70°	155.1	145.2	136.4	129.5	123.3	119.9	117.6	114.9	113.4	110.3	108.8
72.5°	132.8	125.6	119.2	113.5	108.6	105.5	102.6	99.3	96.8	93.5	91.9
75°	104.6	98.1	93.1	89.2	86.2	82.0	77.8	74.3	73.2	72.0	71.6
77.5°	77.4	73.3	69.7	66.5	62.7	59.6	58.7	57.9	57.7	57.1	57.1
80°	60.9	57.1	54.4	50.6	48.3	48.3	48.3	47.5	47.9	47.9	47.9
82.5°	45.3	41.7	40.3	38.9	38.5	38.8	38.8	38.9	38.7	39.3	39.0
85°	23.4	23.7	24.5	24.1	24.5	24.5	25.3	24.9	25.3	24.5	25.3
87.5°	9.7	10.9	11.6	12.2	12.8	12.8	13.3	13.4	13.8	13.9	13.9
90°	5.6	7.1	8.7	10.4	12.0	13.7	14.2	14.7	15.2	15.7	16.1
92.5°	17.3	18.2	19.1	20.0	21.0	21.9	22.3	22.7	23.1	23.5	23.7
95°	37.2	38.2	39.2	40.2	41.2	42.2	42.7	43.2	43.7	44.2	44.5
97.5°	62.4	63.1	63.8	64.6	65.3	66.1	66.6	67.2	67.8	68.4	68.6
100°	80.6	81.3	81.9	82.6	83.2	83.8	84.2	84.6	85.0	85.4	85.7
102.5°	99.9	100.6	101.4	102.3	103.1	103.9	104.3	104.7	105.1	105.4	105.6
105°	129.4	130.0	131.2	132.3	133.5	134.6	134.6	134.6	134.6	134.6	134.7
107.5°	164.1	164.4	164.8	165.3	165.8	166.2	166.6	167.0	167.4	167.8	168.0
110°	186.4	186.6	186.9	187.2	187.4	187.7	188.2	188.7	189.2	189.7	189.8



TEST NUMBER: P332277

CATALOG NUMBER: S123RDIP-S560D585U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	208.8	208.9	209.0	209.0	209.1	209.1	209.7	210.3	210.9	211.5	211.8
115°	243.9	244.0	243.7	243.5	243.2	243.0	243.1	243.2	243.4	243.5	243.5
117.5°	277.9	277.8	277.5	277.2	276.9	276.5	276.5	276.5	276.4	276.4	276.2
120°	301.4	301.4	300.8	300.2	299.5	298.9	298.8	298.6	298.5	298.4	298.2
122.5°	322.9	323.0	322.7	322.4	322.0	321.7	321.4	321.0	320.7	320.4	320.0
125°	356.3	356.4	356.1	355.9	355.6	355.4	354.8	354.3	353.8	353.3	352.8
127.5°	389.5	389.8	389.5	389.2	388.9	388.7	388.0	387.2	386.5	385.8	385.2
130°	411.3	411.6	411.3	410.9	410.5	410.1	409.6	409.1	408.6	408.1	407.4
132.5°	432.3	432.7	432.4	432.1	431.8	431.6	430.9	430.3	429.7	429.1	428.5
135°	463.3	463.7	463.5	463.4	463.3	463.2	462.7	462.1	461.6	461.1	460.7
137.5°	492.5	493.0	493.3	493.6	494.0	494.3	493.8	493.2	492.7	492.2	491.7
140°	513.0	513.4	513.5	513.7	513.8	513.9	513.8	513.7	513.5	513.4	512.9
142.5°	531.7	532.2	532.4	532.6	532.9	533.1	533.0	532.8	532.7	532.6	532.2
145°	559.4	559.7	560.1	560.5	560.9	561.3	561.1	561.0	560.9	560.8	560.4
147.5°	585.8	586.2	586.6	586.9	587.3	587.6	587.6	587.6	587.6	587.6	587.2
150°	602.8	603.0	603.3	603.5	603.8	604.0	604.0	604.0	604.0	604.0	603.7
152.5°	617.8	618.0	618.2	618.3	618.5	618.6	618.8	619.1	619.3	619.5	619.2
155°	639.4	639.5	639.6	639.7	639.9	640.0	640.5	641.0	641.5	642.0	641.8
157.5°	658.4	658.4	658.5	658.6	658.7	658.8	659.3	659.9	660.4	660.9	660.8
160°	670.3	670.2	670.2	670.2	670.2	670.2	670.8	671.5	672.1	672.7	672.8
162.5°	680.9	680.8	680.9	681.0	681.1	681.2	681.8	682.4	683.1	683.7	683.6
165°	694.9	694.7	694.7	694.7	694.7	694.7	695.5	696.3	697.0	697.8	697.7
167.5°	705.7	705.5	705.6	705.7	705.8	705.9	706.7	707.5	708.3	709.1	709.1
170°	712.1	711.8	711.8	711.8	711.8	711.8	712.7	713.6	714.5	715.4	715.4
172.5°	717.1	716.9	716.9	716.9	716.9	716.9	717.7	718.4	719.2	720.0	720.0
175°	722.4	722.1	722.1	722.1	722.1	722.1	722.9	723.6	724.4	725.2	725.1
177.5°	724.9	724.7	724.7	724.7	724.7	724.7	725.3	726.0	726.6	727.2	727.1
180°	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1



TEST NUMBER: P332277

CATALOG NUMBER: S123RDIP-S560D585U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	852.4	852.1	852.4	851.2	852.4	852.1	852.4	856.1	856.1	856.4	856.7
5°	793.2	792.8	791.7	788.3	791.7	792.8	793.2	794.4	797.4	802.8	801.3
7.5°	741.5	741.0	737.6	737.7	737.6	741.0	741.5	744.5	748.0	751.3	755.2
10°	710.9	711.3	706.7	704.0	706.7	711.3	710.9	713.6	718.5	721.2	723.9
12.5°	681.2	679.4	675.7	672.7	675.7	679.4	681.2	683.2	690.0	693.0	698.2
15°	641.9	638.1	628.9	629.7	628.9	638.1	641.9	640.4	647.3	651.1	652.7
17.5°	595.7	592.9	592.8	587.4	592.8	592.9	595.7	598.8	604.8	608.9	619.9
20°	568.8	566.9	567.6	562.3	567.6	566.9	568.8	574.9	578.7	584.1	592.9
22.5°	547.6	545.7	542.5	540.8	542.5	545.7	547.6	551.9	556.1	563.6	568.4
25°	516.7	513.6	510.6	512.5	510.6	513.6	516.7	519.0	526.6	530.1	537.0
27.5°	485.7	483.4	480.4	480.0	480.4	483.4	485.7	488.0	492.2	498.0	506.3
30°	466.1	463.8	462.3	460.4	462.3	463.8	466.1	468.0	472.3	478.4	484.5
32.5°	446.2	445.8	443.0	442.6	443.0	445.8	446.2	449.4	453.6	459.4	464.6
35°	420.2	417.9	417.1	417.5	417.1	417.9	420.2	421.7	425.5	430.9	435.9
37.5°	395.4	392.4	391.0	389.6	391.0	392.4	395.4	395.7	399.6	403.2	409.9
40°	377.7	374.6	373.8	373.1	373.8	374.6	377.7	377.3	381.5	384.2	390.3
42.5°	357.7	356.5	356.1	354.7	356.1	356.5	357.7	359.8	362.2	366.1	370.7
45°	330.5	330.2	327.9	328.6	327.9	330.2	330.5	331.7	335.9	338.6	342.8
47.5°	301.9	300.2	298.6	299.7	298.6	300.2	301.9	303.4	306.3	309.6	315.1
50°	282.3	281.5	278.1	278.8	278.1	281.5	282.3	283.8	285.7	289.9	294.9
52.5°	262.7	259.8	258.5	258.0	258.5	259.8	262.7	264.2	266.4	271.3	275.0
55°	230.2	226.7	225.2	224.4	225.2	226.7	230.2	232.9	235.9	241.3	245.1
57.5°	198.3	197.4	196.2	197.0	196.2	197.4	198.3	202.8	205.8	210.0	214.6
60°	179.6	179.6	179.6	179.3	179.6	179.6	179.6	183.5	186.1	190.4	195.3
62.5°	165.2	164.3	164.0	164.5	164.0	164.3	165.2	166.9	169.6	172.3	176.6
65°	143.2	142.9	141.3	141.0	141.3	142.9	143.2	144.4	146.7	148.6	151.7
67.5°	122.5	121.1	120.7	120.1	120.7	121.1	122.5	123.5	125.0	127.5	129.0
70°	106.9	106.1	103.8	104.2	103.8	106.1	106.9	108.8	110.3	113.4	114.9
72.5°	90.0	89.2	88.8	88.2	88.8	89.2	90.0	91.9	93.5	96.8	99.3
75°	71.2	70.9	70.5	72.0	70.5	70.9	71.2	71.6	72.0	73.2	74.3
77.5°	57.1	57.1	57.3	56.7	57.3	57.1	57.1	57.1	57.1	57.7	57.9
80°	47.9	47.9	47.5	47.5	47.5	47.9	47.9	47.9	47.9	47.9	47.5
82.5°	38.4	38.7	38.9	38.3	38.9	38.7	38.4	39.0	39.3	38.7	38.9
85°	25.3	24.9	25.7	25.3	25.7	24.9	25.3	25.3	24.5	25.3	24.9
87.5°	14.6	14.0	14.1	14.5	14.1	14.0	14.6	13.9	13.9	13.8	13.4
90°	16.4	16.6	16.9	17.1	16.9	16.6	16.4	16.1	15.7	15.2	14.7
92.5°	23.5	23.3	23.2	23.0	23.2	23.3	23.5	23.7	23.5	23.1	22.7
95°	44.5	44.5	44.5	44.5	44.5	44.5	44.5	44.5	44.2	43.7	43.2
97.5°	68.6	68.5	68.5	68.4	68.5	68.5	68.6	68.6	68.4	67.8	67.2
100°	85.9	86.2	86.4	86.7	86.4	86.2	85.9	85.7	85.4	85.0	84.6
102.5°	105.6	105.5	105.5	105.4	105.5	105.5	105.6	105.6	105.4	105.1	104.7
105°	135.0	135.2	135.5	135.8	135.5	135.2	135.0	134.7	134.6	134.6	134.6
107.5°	167.8	167.7	167.5	167.4	167.5	167.7	167.8	168.0	167.8	167.4	167.0
110°	189.6	189.3	189.1	188.8	189.1	189.3	189.6	189.8	189.7	189.2	188.7



TEST NUMBER: P332277

CATALOG NUMBER: S123RDIP-S560D585U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	211.8	211.7	211.7	211.6	211.7	211.7	211.8	211.8	211.5	210.9	210.3
115°	243.4	243.2	243.1	243.0	243.1	243.2	243.4	243.5	243.5	243.4	243.2
117.5°	275.9	275.5	275.2	274.8	275.2	275.5	275.9	276.2	276.4	276.4	276.5
120°	297.9	297.7	297.4	297.2	297.4	297.7	297.9	298.2	298.4	298.5	298.6
122.5°	319.7	319.3	319.0	318.6	319.0	319.3	319.7	320.0	320.4	320.7	321.0
125°	352.3	351.8	351.3	350.8	351.3	351.8	352.3	352.8	353.3	353.8	354.3
127.5°	384.6	384.0	383.4	382.8	383.4	384.0	384.6	385.2	385.8	386.5	387.2
130°	406.5	405.6	404.7	403.8	404.7	405.6	406.5	407.4	408.1	408.6	409.1
132.5°	427.8	427.1	426.4	425.7	426.4	427.1	427.8	428.5	429.1	429.7	430.3
135°	460.5	460.2	460.0	459.7	460.0	460.2	460.5	460.7	461.1	461.6	462.1
137.5°	491.2	490.7	490.2	489.7	490.2	490.7	491.2	491.7	492.2	492.7	493.2
140°	512.0	511.1	510.2	509.4	510.2	511.1	512.0	512.9	513.4	513.5	513.7
142.5°	531.5	530.8	530.1	529.4	530.1	530.8	531.5	532.2	532.6	532.7	532.8
145°	559.9	559.4	558.9	558.4	558.9	559.4	559.9	560.4	560.8	560.9	561.0
147.5°	586.5	585.7	585.0	584.2	585.0	585.7	586.5	587.2	587.6	587.6	587.6
150°	602.9	602.1	601.4	600.6	601.4	602.1	602.9	603.7	604.0	604.0	604.0
152.5°	618.6	617.9	617.3	616.6	617.3	617.9	618.6	619.2	619.5	619.3	619.1
155°	640.9	640.0	639.2	638.3	639.2	640.0	640.9	641.8	642.0	641.5	641.0
157.5°	660.1	659.4	658.7	658.0	658.7	659.4	660.1	660.8	660.9	660.4	659.9
160°	672.3	671.8	671.3	670.8	671.3	671.8	672.3	672.8	672.7	672.1	671.5
162.5°	682.8	682.0	681.2	680.4	681.2	682.0	682.8	683.6	683.7	683.1	682.4
165°	696.8	695.9	695.1	694.2	695.1	695.9	696.8	697.7	697.8	697.0	696.3
167.5°	708.3	707.5	706.7	705.9	706.7	707.5	708.3	709.1	709.1	708.3	707.5
170°	714.5	713.6	712.7	711.8	712.7	713.6	714.5	715.4	715.4	714.5	713.6
172.5°	719.1	718.2	717.3	716.4	717.3	718.2	719.1	720.0	720.0	719.2	718.4
175°	724.2	723.3	722.4	721.5	722.4	723.3	724.2	725.1	725.2	724.4	723.6
177.5°	726.4	725.7	725.0	724.3	725.0	725.7	726.4	727.1	727.2	726.6	726.0
180°	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1



TEST NUMBER: P332277

CATALOG NUMBER: S123RDIP-S560D585U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	854.0	858.3	862.6	866.5	872.7	875.4	879.4	880.9	885.5	892.3	897.8
5°	802.0	808.2	816.2	822.7	833.1	841.1	849.9	858.3	868.3	882.5	895.1
7.5°	758.0	764.0	773.7	785.8	797.2	808.6	820.7	832.1	846.4	866.7	886.8
10°	728.9	736.2	747.7	760.7	774.8	786.0	800.1	814.7	832.3	855.7	879.8
12.5°	703.8	709.2	722.5	734.9	750.9	765.1	779.0	796.0	816.1	841.0	870.0
15°	663.8	671.4	684.5	698.2	715.1	730.0	748.0	768.7	788.3	818.9	854.1
17.5°	623.6	635.3	648.8	664.4	676.9	697.5	717.0	738.2	762.3	794.8	833.4
20°	597.9	607.1	619.7	642.3	658.8	674.5	692.5	718.9	741.1	777.9	818.1
22.5°	576.1	582.9	597.0	615.7	634.9	653.0	671.4	696.6	724.0	758.9	802.5
25°	543.9	554.6	565.3	578.7	599.4	621.3	641.2	662.6	691.7	728.9	776.0
27.5°	512.4	522.1	532.7	549.2	564.9	585.3	606.1	630.7	661.9	701.2	749.0
30°	492.2	499.5	509.4	530.5	544.7	562.3	586.8	608.6	637.7	679.5	730.0
32.5°	471.3	480.8	491.6	507.8	525.3	542.0	564.4	588.1	617.8	658.9	710.7
35°	441.6	452.7	463.8	475.7	493.3	510.6	529.3	555.4	585.6	625.5	676.4
37.5°	414.3	423.2	432.3	447.0	463.7	480.1	497.6	523.3	551.8	594.8	641.5
40°	396.8	404.9	411.7	427.1	443.2	460.8	478.0	500.6	531.2	571.5	616.7
42.5°	377.8	385.2	394.6	407.1	424.5	439.3	456.6	477.9	506.7	547.6	587.2
45°	349.3	357.7	365.8	377.7	394.9	409.4	424.8	445.1	474.6	508.3	543.5
47.5°	319.7	328.1	337.3	348.8	363.8	378.6	393.9	411.9	438.8	471.9	495.6
50°	300.7	307.6	316.8	328.2	342.0	357.7	371.5	391.1	416.7	442.8	463.5
52.5°	281.1	287.3	297.8	309.9	322.7	336.3	351.0	367.8	391.0	415.5	431.9
55°	250.5	258.2	267.0	278.8	291.5	303.0	317.1	334.4	352.8	371.1	382.3
57.5°	221.9	228.3	235.7	248.0	258.9	272.6	285.3	298.8	315.8	329.6	336.9
60°	201.1	206.8	216.4	227.1	237.5	249.3	263.9	277.3	290.3	301.4	307.2
62.5°	181.5	188.1	196.5	206.3	217.6	228.8	241.5	252.8	264.3	273.9	277.8
65°	155.9	161.3	167.4	176.6	185.8	197.3	207.2	218.7	227.1	232.5	235.9
67.5°	132.6	136.1	140.8	146.9	156.0	166.0	175.7	184.6	191.7	195.3	198.4
70°	117.6	119.9	123.3	129.5	136.4	145.2	155.1	161.6	167.8	170.8	173.9
72.5°	102.6	105.5	108.6	113.5	119.2	125.6	132.8	140.8	144.2	147.8	149.7
75°	77.8	82.0	86.2	89.2	93.1	98.1	104.6	109.5	111.5	114.5	114.9
77.5°	58.7	59.6	62.7	66.5	69.7	73.3	77.4	81.9	82.8	84.4	85.4
80°	48.3	48.3	48.3	50.6	54.4	57.1	60.9	63.2	64.7	65.1	65.5
82.5°	38.8	38.8	38.5	38.9	40.3	41.7	45.3	47.9	49.1	48.9	48.0
85°	25.3	24.5	24.5	24.1	24.5	23.7	23.4	24.9	27.2	27.2	26.4
87.5°	13.3	12.8	12.8	12.2	11.6	10.9	9.7	9.8	9.5	10.5	9.9
90°	14.2	13.7	12.0	10.4	8.7	7.1	5.6	4.4	3.1	1.8	0.6
92.5°	22.3	21.9	21.0	20.0	19.1	18.2	17.3	16.4	15.5	14.7	13.8
95°	42.7	42.2	41.2	40.2	39.2	38.2	37.2	36.3	35.4	34.5	33.7
97.5°	66.6	66.1	65.3	64.6	63.8	63.1	62.4	61.8	61.1	60.4	59.8
100°	84.2	83.8	83.2	82.6	81.9	81.3	80.6	79.9	79.1	78.3	77.6
102.5°	104.3	103.9	103.1	102.3	101.4	100.6	99.9	99.5	99.0	98.6	98.1
105°	134.6	134.6	133.5	132.3	131.2	130.0	129.4	129.1	128.8	128.6	128.3
107.5°	166.6	166.2	165.8	165.3	164.8	164.4	164.1	163.9	163.8	163.6	163.5
110°	188.2	187.7	187.4	187.2	186.9	186.6	186.4	186.1	185.9	185.6	185.4



TEST NUMBER: P332277

CATALOG NUMBER: S123RDIP-S560D585U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	209.7	209.1	209.1	209.0	209.0	208.9	208.8	208.6	208.5	208.3	208.2
115°	243.1	243.0	243.2	243.5	243.7	244.0	243.9	243.6	243.2	242.8	242.4
117.5°	276.5	276.5	276.9	277.2	277.5	277.8	277.9	277.6	277.4	277.1	276.9
120°	298.8	298.9	299.5	300.2	300.8	301.4	301.4	300.6	299.8	299.1	298.3
122.5°	321.4	321.7	322.0	322.4	322.7	323.0	322.9	322.3	321.8	321.2	320.7
125°	354.8	355.4	355.6	355.9	356.1	356.4	356.3	355.9	355.5	355.2	354.8
127.5°	388.0	388.7	388.9	389.2	389.5	389.8	389.5	388.7	387.9	387.1	386.3
130°	409.6	410.1	410.5	410.9	411.3	411.6	411.3	410.3	409.3	408.3	407.3
132.5°	430.9	431.6	431.8	432.1	432.4	432.7	432.3	431.3	430.3	429.3	428.2
135°	462.7	463.2	463.3	463.4	463.5	463.7	463.3	462.6	461.8	461.1	460.3
137.5°	493.8	494.3	494.0	493.6	493.3	493.0	492.5	491.9	491.2	490.6	490.0
140°	513.8	513.9	513.8	513.7	513.5	513.4	513.0	512.4	511.8	511.1	510.5
142.5°	533.0	533.1	532.9	532.6	532.4	532.2	531.7	531.1	530.5	529.8	529.2
145°	561.1	561.3	560.9	560.5	560.1	559.7	559.4	559.2	558.9	558.7	558.4
147.5°	587.6	587.6	587.3	586.9	586.6	586.2	585.8	585.3	584.9	584.4	584.0
150°	604.0	604.0	603.8	603.5	603.3	603.0	602.8	602.5	602.3	602.0	601.8
152.5°	618.8	618.6	618.5	618.3	618.2	618.0	617.8	617.4	617.1	616.7	616.4
155°	640.5	640.0	639.9	639.7	639.6	639.5	639.4	639.4	639.4	639.4	639.4
157.5°	659.3	658.8	658.7	658.6	658.5	658.4	658.4	658.6	658.7	658.9	659.0
160°	670.8	670.2	670.2	670.2	670.2	670.2	670.3	670.6	670.8	671.1	671.3
162.5°	681.8	681.2	681.1	681.0	680.9	680.8	680.9	681.2	681.6	681.9	682.3
165°	695.5	694.7	694.7	694.7	694.7	694.7	694.9	695.3	695.7	696.1	696.4
167.5°	706.7	705.9	705.8	705.7	705.6	705.5	705.7	706.2	706.7	707.2	707.7
170°	712.7	711.8	711.8	711.8	711.8	711.8	712.1	712.6	713.1	713.6	714.1
172.5°	717.7	716.9	716.9	716.9	716.9	716.9	717.1	717.6	718.1	718.6	719.1
175°	722.9	722.1	722.1	722.1	722.1	722.1	722.4	722.9	723.4	723.9	724.4
177.5°	725.3	724.7	724.7	724.7	724.7	724.7	724.9	725.3	725.8	726.2	726.6
180°	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1



TEST NUMBER: P332277

CATALOG NUMBER: S123RDIP-S560D585U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	899.6	903.0	907.3	913.7	918.6	922.9	923.8	925.1	928.1	933.3	937.3
5°	905.5	914.3	928.4	942.2	957.2	969.4	980.9	989.0	996.6	1012.7	1025.7
7.5°	903.6	923.2	945.4	970.2	995.2	1019.5	1042.0	1062.2	1082.3	1105.7	1132.4
10°	902.4	925.4	955.2	987.0	1021.9	1056.0	1088.9	1114.6	1144.5	1171.3	1205.4
12.5°	896.6	929.7	965.4	1006.0	1048.9	1088.2	1131.5	1167.0	1201.1	1239.9	1279.5
15°	889.0	929.2	974.4	1028.4	1093.5	1141.0	1185.4	1247.1	1289.2	1331.4	1388.1
17.5°	875.1	924.2	980.7	1050.8	1105.2	1169.0	1235.8	1284.6	1341.3	1400.7	1452.0
20°	864.1	921.2	984.4	1053.3	1122.6	1192.0	1256.7	1314.9	1373.5	1442.1	1484.2
22.5°	853.1	909.5	975.2	1048.4	1122.9	1195.9	1269.2	1337.6	1403.5	1472.7	1526.5
25°	829.6	896.6	967.9	1042.6	1116.1	1196.5	1283.9	1360.1	1441.7	1512.9	1563.9
27.5°	805.9	867.3	938.2	1014.0	1095.7	1190.8	1293.5	1380.2	1461.9	1512.9	1528.9
30°	784.4	849.5	914.6	991.6	1080.1	1186.2	1295.4	1394.6	1461.6	1483.8	1467.3
32.5°	762.7	821.7	886.2	965.0	1059.0	1174.9	1297.8	1386.0	1426.4	1409.4	1342.3
35°	724.3	777.5	840.0	918.9	1026.9	1168.6	1287.7	1347.5	1337.5	1241.7	1115.3
37.5°	683.2	726.6	784.4	866.9	993.6	1143.7	1244.2	1253.0	1166.8	1019.8	873.8
40°	650.7	689.8	749.2	835.4	967.9	1119.2	1200.4	1164.8	1031.1	867.5	745.7
42.5°	619.2	652.1	709.3	802.3	943.4	1085.8	1135.1	1057.5	903.3	748.6	637.9
45°	565.7	596.7	654.2	749.6	893.2	1021.9	1015.4	880.6	726.2	601.7	509.8
47.5°	515.0	542.1	596.1	693.4	834.3	926.1	865.2	721.8	590.8	491.0	425.4
50°	479.2	506.0	559.6	655.7	787.1	854.1	767.2	628.9	509.0	426.3	374.2
52.5°	444.8	471.0	520.1	613.7	730.1	770.2	676.8	548.6	448.7	377.3	332.5
55°	396.8	416.7	460.8	550.4	637.3	646.5	551.9	444.7	362.3	312.5	281.9
57.5°	347.9	365.0	408.5	479.9	540.9	536.1	446.4	353.7	298.2	261.2	239.0
60°	316.0	332.8	371.1	432.4	478.4	462.3	380.0	305.3	257.8	230.6	213.0
62.5°	286.3	299.4	335.3	380.0	413.1	394.9	324.8	263.0	225.3	202.4	188.4
65°	243.2	253.9	282.7	306.0	324.4	306.8	248.6	205.7	178.5	162.4	152.8
67.5°	202.3	209.1	227.3	235.7	248.7	229.4	186.9	158.2	142.7	129.2	122.5
70°	176.6	181.6	191.1	198.0	201.5	181.6	150.1	129.1	116.1	106.5	102.3
72.5°	150.8	155.2	157.1	162.8	161.0	142.3	120.7	104.0	94.6	88.1	82.7
75°	115.3	117.2	115.3	113.0	108.0	95.0	80.1	71.6	64.7	61.7	59.8
77.5°	84.0	83.4	80.8	77.2	68.7	60.5	52.5	49.6	46.7	45.0	44.4
80°	64.7	63.2	60.9	55.2	47.9	42.1	40.2	38.3	37.2	35.2	34.9
82.5°	48.2	47.3	43.4	38.6	33.5	30.8	29.2	28.5	27.3	26.4	26.3
85°	25.7	24.5	20.3	17.6	16.9	16.1	15.7	15.7	14.2	13.8	13.8
87.5°	8.6	7.1	7.0	6.3	6.6	6.3	7.0	6.7	6.7	7.1	6.6
90°	1.8	3.1	4.4	5.6	7.1	8.7	10.4	12.0	13.7	14.2	14.7
92.5°	14.7	15.5	16.4	17.3	18.2	19.1	20.0	21.0	21.9	22.3	22.7
95°	34.5	35.4	36.3	37.2	38.2	39.2	40.2	41.2	42.2	42.7	43.2
97.5°	60.4	61.1	61.8	62.4	63.1	63.8	64.6	65.3	66.1	66.6	67.2
100°	78.3	79.1	79.9	80.6	81.3	81.9	82.6	83.2	83.8	84.2	84.6
102.5°	98.6	99.0	99.5	99.9	100.6	101.4	102.3	103.1	103.9	104.3	104.7
105°	128.6	128.8	129.1	129.4	130.0	131.2	132.3	133.5	134.6	134.6	134.6
107.5°	163.6	163.8	163.9	164.1	164.4	164.8	165.3	165.8	166.2	166.6	167.0
110°	185.6	185.9	186.1	186.4	186.6	186.9	187.2	187.4	187.7	188.2	188.7



TEST NUMBER: P332277

CATALOG NUMBER: S123RDIP-S560D585U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	208.3	208.5	208.6	208.8	208.9	209.0	209.0	209.1	209.1	209.7	210.3
115°	242.8	243.2	243.6	243.9	244.0	243.7	243.5	243.2	243.0	243.1	243.2
117.5°	277.1	277.4	277.6	277.9	277.8	277.5	277.2	276.9	276.5	276.5	276.5
120°	299.1	299.8	300.6	301.4	301.4	300.8	300.2	299.5	298.9	298.8	298.6
122.5°	321.2	321.8	322.3	322.9	323.0	322.7	322.4	322.0	321.7	321.4	321.0
125°	355.2	355.5	355.9	356.3	356.4	356.1	355.9	355.6	355.4	354.8	354.3
127.5°	387.1	387.9	388.7	389.5	389.8	389.5	389.2	388.9	388.7	388.0	387.2
130°	408.3	409.3	410.3	411.3	411.6	411.3	410.9	410.5	410.1	409.6	409.1
132.5°	429.3	430.3	431.3	432.3	432.7	432.4	432.1	431.8	431.6	430.9	430.3
135°	461.1	461.8	462.6	463.3	463.7	463.5	463.4	463.3	463.2	462.7	462.1
137.5°	490.6	491.2	491.9	492.5	493.0	493.3	493.6	494.0	494.3	493.8	493.2
140°	511.1	511.8	512.4	513.0	513.4	513.5	513.7	513.8	513.9	513.8	513.7
142.5°	529.8	530.5	531.1	531.7	532.2	532.4	532.6	532.9	533.1	533.0	532.8
145°	558.7	558.9	559.2	559.4	559.7	560.1	560.5	560.9	561.3	561.1	561.0
147.5°	584.4	584.9	585.3	585.8	586.2	586.6	586.9	587.3	587.6	587.6	587.6
150°	602.0	602.3	602.5	602.8	603.0	603.3	603.5	603.8	604.0	604.0	604.0
152.5°	616.7	617.1	617.4	617.8	618.0	618.2	618.3	618.5	618.6	618.8	619.1
155°	639.4	639.4	639.4	639.4	639.5	639.6	639.7	639.9	640.0	640.5	641.0
157.5°	658.9	658.7	658.6	658.4	658.4	658.5	658.6	658.7	658.8	659.3	659.9
160°	671.1	670.8	670.6	670.3	670.2	670.2	670.2	670.2	670.2	670.8	671.5
162.5°	681.9	681.6	681.2	680.9	680.8	680.9	681.0	681.1	681.2	681.8	682.4
165°	696.1	695.7	695.3	694.9	694.7	694.7	694.7	694.7	694.7	695.5	696.3
167.5°	707.2	706.7	706.2	705.7	705.5	705.6	705.7	705.8	705.9	706.7	707.5
170°	713.6	713.1	712.6	712.1	711.8	711.8	711.8	711.8	711.8	712.7	713.6
172.5°	718.6	718.1	717.6	717.1	716.9	716.9	716.9	716.9	716.9	717.7	718.4
175°	723.9	723.4	722.9	722.4	722.1	722.1	722.1	722.1	722.1	722.9	723.6
177.5°	726.2	725.8	725.3	724.9	724.7	724.7	724.7	724.7	724.7	725.3	726.0
180°	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1



TEST NUMBER: P332277

CATALOG NUMBER: S123RDIP-S560D585U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	943.8	943.8	945.0	949.6	950.2	954.2	952.9
5°	1037.2	1044.5	1047.2	1058.7	1065.6	1068.6	1062.5
7.5°	1151.5	1172.0	1181.8	1193.8	1204.4	1207.7	1199.3
10°	1234.9	1256.3	1274.3	1285.4	1295.8	1302.6	1311.5
12.5°	1315.4	1341.8	1358.9	1374.6	1385.2	1394.0	1395.4
15°	1403.0	1442.8	1473.1	1495.3	1506.4	1512.2	1509.9
17.5°	1491.3	1528.2	1549.8	1572.4	1587.8	1588.6	1589.1
20°	1541.3	1577.3	1602.2	1619.0	1636.3	1635.5	1639.3
22.5°	1574.7	1603.0	1622.1	1634.3	1640.2	1637.3	1638.1
25°	1590.3	1598.7	1595.3	1575.7	1570.8	1552.8	1555.8
27.5°	1509.7	1469.9	1428.7	1375.6	1333.8	1300.4	1302.1
30°	1400.3	1329.8	1249.4	1182.0	1121.5	1104.6	1068.6
32.5°	1247.4	1141.7	1047.5	984.7	932.7	918.6	887.2
35°	988.2	885.5	788.6	730.4	707.4	675.3	674.9
37.5°	768.1	677.7	626.5	582.8	559.9	540.4	538.5
40°	646.2	575.7	537.0	505.6	483.0	468.4	465.0
42.5°	561.0	504.0	467.7	448.3	430.9	423.4	417.8
45°	458.1	419.8	394.5	376.9	368.8	363.1	360.0
47.5°	383.2	357.5	340.3	328.6	322.0	316.0	317.6
50°	342.4	321.4	308.7	297.6	292.6	288.4	288.8
52.5°	309.6	290.7	280.5	272.5	266.3	263.3	261.8
55°	262.8	250.9	240.5	234.8	231.3	227.1	226.0
57.5°	224.1	214.9	206.5	200.0	199.2	195.1	195.6
60°	198.4	190.7	183.8	180.4	177.7	174.3	175.4
62.5°	177.3	170.8	164.5	161.7	159.0	156.5	157.0
65°	145.2	139.0	135.2	133.7	132.5	131.4	130.2
67.5°	115.7	111.9	109.5	106.2	103.9	103.5	102.3
70°	97.3	92.3	88.1	83.9	82.7	82.3	82.7
72.5°	78.0	74.8	73.7	71.6	71.4	70.4	71.1
75°	58.6	57.5	56.7	55.2	55.2	55.2	55.2
77.5°	43.2	42.5	42.1	41.7	41.4	40.8	40.8
80°	33.7	33.3	32.6	32.6	32.2	32.6	32.2
82.5°	25.4	25.4	24.6	24.6	24.2	24.0	24.2
85°	13.0	12.6	13.4	12.6	13.0	12.3	13.0
87.5°	6.7	6.8	6.6	6.6	6.4	7.0	6.5
90°	15.2	15.7	16.1	16.4	16.6	16.9	17.1
92.5°	23.1	23.5	23.7	23.5	23.3	23.2	23.0
95°	43.7	44.2	44.5	44.5	44.5	44.5	44.5
97.5°	67.8	68.4	68.6	68.6	68.5	68.5	68.4
100°	85.0	85.4	85.7	85.9	86.2	86.4	86.7
102.5°	105.1	105.4	105.6	105.6	105.5	105.5	105.4
105°	134.6	134.6	134.7	135.0	135.2	135.5	135.8
107.5°	167.4	167.8	168.0	167.8	167.7	167.5	167.4
110°	189.2	189.7	189.8	189.6	189.3	189.1	188.8



TEST NUMBER: P332277

CATALOG NUMBER: S123RDIP-S560D585U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	210.9	211.5	211.8	211.8	211.7	211.7	211.6
115°	243.4	243.5	243.5	243.4	243.2	243.1	243.0
117.5°	276.4	276.4	276.2	275.9	275.5	275.2	274.8
120°	298.5	298.4	298.2	297.9	297.7	297.4	297.2
122.5°	320.7	320.4	320.0	319.7	319.3	319.0	318.6
125°	353.8	353.3	352.8	352.3	351.8	351.3	350.8
127.5°	386.5	385.8	385.2	384.6	384.0	383.4	382.8
130°	408.6	408.1	407.4	406.5	405.6	404.7	403.8
132.5°	429.7	429.1	428.5	427.8	427.1	426.4	425.7
135°	461.6	461.1	460.7	460.5	460.2	460.0	459.7
137.5°	492.7	492.2	491.7	491.2	490.7	490.2	489.7
140°	513.5	513.4	512.9	512.0	511.1	510.2	509.4
142.5°	532.7	532.6	532.2	531.5	530.8	530.1	529.4
145°	560.9	560.8	560.4	559.9	559.4	558.9	558.4
147.5°	587.6	587.6	587.2	586.5	585.7	585.0	584.2
150°	604.0	604.0	603.7	602.9	602.1	601.4	600.6
152.5°	619.3	619.5	619.2	618.6	617.9	617.3	616.6
155°	641.5	642.0	641.8	640.9	640.0	639.2	638.3
157.5°	660.4	660.9	660.8	660.1	659.4	658.7	658.0
160°	672.1	672.7	672.8	672.3	671.8	671.3	670.8
162.5°	683.1	683.7	683.6	682.8	682.0	681.2	680.4
165°	697.0	697.8	697.7	696.8	695.9	695.1	694.2
167.5°	708.3	709.1	709.1	708.3	707.5	706.7	705.9
170°	714.5	715.4	715.4	714.5	713.6	712.7	711.8
172.5°	719.2	720.0	720.0	719.1	718.2	717.3	716.4
175°	724.4	725.2	725.1	724.2	723.3	722.4	721.5
177.5°	726.6	727.2	727.1	726.4	725.7	725.0	724.3
180°	726.1	726.1	726.1	726.1	726.1	726.1	726.1

(END OF REPORT)