

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332326

Luminaire Tested: **S123RDIP-S775D1195U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332326
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D1195U835-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7367.7 lumens
Efficiency: N/A
Efficacy: 129.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332326

CATALOG NUMBER: S123RDIP-S775D1195U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332326

CATALOG NUMBER: S123RDIP-S775D1195U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41				
1	96	92	89	85	88	84	81	78	70	67	65	56	54	53	43	42	42	36				
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36	31				
3	81	72	65	59	73	66	60	55	55	50	47	44	41	39	35	33	31	27				
4	74	64	56	50	67	59	52	47	49	44	40	40	36	34	31	29	27	23				
5	68	57	49	43	62	52	46	41	44	39	35	36	32	29	28	26	24	20				
6	63	51	43	38	57	47	40	35	40	34	31	33	29	26	26	23	21	18				
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19	16				
8	54	42	35	29	49	39	32	28	33	28	24	27	23	21	22	19	17	15				
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	20	18	16	13				
10	47	35	28	24	43	33	26	22	28	23	19	23	19	17	19	16	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13164	13164	13164	13164
5°	15692	13220	11642	13220
10°	19593	13144	10518	13144
15°	22998	13010	9591	13010
20°	25668	12810	8804	12810
25°	25258	12598	8320	12598
30°	18155	12403	7822	12403
35°	12122	12150	7499	12150
40°	8931	11844	7165	11844
45°	7491	11309	6838	11309
50°	6611	10608	6382	10608
55°	5797	9805	5758	9805
60°	5162	9040	5274	9040
65°	4534	8214	4908	8214
70°	3559	7481	4482	7481
75°	3136	6534	4092	6534
80°	2727	5548	4023	5548
85°	2198	4458	4273	4458



TEST NUMBER: P332326

CATALOG NUMBER: S123RDIP-S775D1195U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.3	1.6
10°-20°	375.7	5.1
20°-30°	590.3	8.0
30°-40°	615.9	8.4
40°-50°	527.1	7.2
50°-60°	401.7	5.5
60°-70°	257.5	3.5
70°-80°	123.9	1.7
80°-90°	37.2	0.5
90°-100°	319.4	4.3
100°-110°	904.4	12.3
110°-120°	889.7	12.1
120°-130°	709.7	9.6
130°-140°	559.5	7.6
140°-150°	417.6	5.7
150°-160°	291.1	4.0
160°-170°	171.0	2.3
170°-180°	55.6	0.8
0°-30°	1086.3	14.7
0°-40°	1702.2	23.1
0°-60°	2631.0	35.7
0°-90°	3049.5	41.4
90°-120°	2113.6	28.7
90°-150°	3800.4	51.6
90°-180°	4318.0	58.6
0°-180°	7367.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1223	1223	1223	1223	1223	
5°	1452	1224	1078	1224	1452	150
15°	2064	1168	861	1168	2064	585
25°	2127	1061	700	1061	2127	914
35°	922	925	571	925	922	605
45°	492	743	449	743	492	387
55°	309	522	307	522	309	279
65°	178	322	193	322	178	175
75°	75	157	98	157	75	81
85°	18	36	35	36	18	21
90°	34	2	34	2	34	18
95°	135	40	135	40	135	243
105°	1478	135	1478	135	1478	1458
115°	1797	238	1797	238	1797	1746
125°	1418	331	1418	331	1418	1285
135°	1149	388	1149	388	1149	891
145°	898	443	898	443	898	571
155°	745	503	745	503	745	347
165°	650	550	650	550	650	186
175°	584	573	584	573	584	57
180°	574	574	574	574	574	



TEST NUMBER: P332326

CATALOG NUMBER: S123RDIP-S775D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1302.6	1304.3	1298.8	1298.0	1291.7	1290.0	1290.0	1281.2	1275.8	1268.7	1264.5
5°	1452.3	1460.7	1456.5	1447.1	1431.4	1427.7	1417.8	1402.1	1384.3	1362.3	1351.8
7.5°	1639.3	1650.8	1646.4	1631.8	1615.4	1602.1	1574.0	1547.9	1511.4	1479.3	1451.9
10°	1792.6	1780.6	1771.2	1757.0	1741.9	1717.2	1687.9	1647.6	1601.0	1564.4	1523.5
12.5°	1907.4	1905.4	1893.5	1878.9	1857.5	1834.1	1798.1	1749.0	1694.8	1641.9	1595.2
15°	2063.8	2067.0	2059.1	2043.9	2013.6	1972.2	1917.8	1897.3	1819.9	1762.3	1704.7
17.5°	2172.1	2171.5	2170.4	2149.4	2118.4	2089.0	2038.5	1984.8	1914.6	1833.5	1755.9
20°	2240.8	2235.6	2236.6	2213.0	2190.0	2156.0	2106.8	2028.8	1971.2	1877.5	1797.3
22.5°	2239.1	2238.1	2242.1	2234.0	2217.2	2191.2	2152.4	2086.6	2013.1	1918.5	1828.3
25°	2126.7	2122.5	2147.1	2153.9	2180.6	2185.3	2173.8	2137.7	2068.0	1970.6	1859.1
27.5°	1779.9	1777.6	1823.2	1880.4	1952.8	2009.2	2063.6	2089.9	2068.0	1998.3	1886.6
30°	1460.7	1509.9	1533.0	1615.7	1707.8	1817.8	1914.1	2005.7	2028.2	1997.9	1906.2
32.5°	1212.8	1255.7	1274.9	1345.9	1431.8	1560.6	1705.1	1834.8	1926.5	1949.7	1894.5
35°	922.5	923.0	967.0	998.4	1078.0	1210.4	1350.8	1524.6	1697.3	1828.2	1841.8
37.5°	736.1	738.7	765.3	796.6	856.3	926.4	1049.9	1194.4	1394.0	1594.9	1712.7
40°	635.6	640.3	660.2	691.1	734.0	786.9	883.2	1019.4	1185.8	1409.4	1592.1
42.5°	571.1	578.7	589.0	612.8	639.4	688.9	766.8	871.9	1023.3	1234.7	1445.5
45°	492.1	496.3	504.2	515.2	539.3	573.8	626.2	696.8	822.5	992.7	1203.6
47.5°	434.1	431.9	440.2	449.1	465.1	488.7	523.8	581.5	671.1	807.6	986.6
50°	394.8	394.2	400.0	406.8	422.0	439.3	468.1	511.5	582.7	695.8	859.7
52.5°	357.9	359.9	364.0	372.5	383.4	397.4	423.2	454.5	515.7	613.3	749.9
55°	308.9	310.5	316.2	320.9	328.8	342.9	359.2	385.3	427.2	495.3	607.8
57.5°	267.4	266.7	272.2	273.4	282.3	293.8	306.4	326.7	357.1	407.6	483.4
60°	239.8	238.2	242.9	246.6	251.3	260.7	271.2	291.1	315.2	352.3	417.3
62.5°	214.7	213.9	217.4	221.0	224.9	233.5	242.3	257.6	276.6	308.0	359.5
65°	178.0	179.6	181.1	182.7	184.8	190.0	198.4	208.9	222.0	244.0	281.1
67.5°	139.9	141.5	142.0	145.2	149.7	153.0	158.1	167.4	176.5	195.1	216.2
70°	113.1	112.6	113.1	114.7	120.4	126.2	133.0	139.8	145.5	158.6	176.4
72.5°	97.2	96.2	97.6	97.9	100.7	102.3	106.6	113.0	120.4	129.3	142.1
75°	75.4	75.4	75.4	75.4	77.5	78.5	80.1	81.7	84.3	88.5	97.9
77.5°	55.7	55.8	56.5	57.1	57.5	58.1	59.1	60.6	61.6	63.8	67.9
80°	44.0	44.5	44.0	44.5	44.5	45.5	46.1	47.6	48.2	50.8	52.4
82.5°	33.1	32.8	33.1	33.6	33.6	34.7	34.8	35.9	36.0	37.4	39.0
85°	17.8	16.8	17.8	17.3	18.3	17.3	17.8	18.8	18.8	19.4	21.5
87.5°	10.9	12.0	10.9	11.1	11.3	11.3	11.1	10.8	11.4	11.3	11.0
90°	33.7	34.9	33.7	32.5	33.7	31.4	30.2	29.0	27.9	29.0	25.6
92.5°	56.0	58.1	56.9	60.4	62.5	68.5	77.6	97.8	134.8	178.7	196.6
95°	134.8	139.4	147.6	158.0	180.1	221.9	283.5	418.3	558.8	689.0	613.5
97.5°	366.9	376.9	408.3	460.6	546.3	685.3	835.1	1042.6	1142.3	1067.7	781.7
100°	728.5	727.3	772.6	857.4	974.8	1139.8	1275.7	1369.8	1329.2	1100.3	743.6
102.5°	1068.7	1095.4	1133.3	1200.4	1291.7	1396.3	1475.5	1478.6	1338.4	1039.9	687.8
105°	1477.9	1483.7	1520.9	1565.0	1618.5	1648.7	1626.6	1510.4	1267.6	934.1	619.3
107.5°	1713.5	1724.2	1736.7	1751.6	1750.7	1709.3	1607.5	1418.8	1143.5	840.7	575.6
110°	1810.2	1812.5	1814.8	1805.5	1773.0	1691.7	1545.3	1331.5	1065.4	787.7	558.8



TEST NUMBER: P332326

CATALOG NUMBER: S123RDIP-S775D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1829.7	1829.2	1820.4	1791.6	1732.1	1627.5	1463.5	1245.0	997.6	752.4	549.6
115°	1797.4	1791.6	1768.3	1717.2	1630.1	1503.4	1332.6	1130.5	915.5	714.5	546.1
117.5°	1694.7	1686.8	1653.3	1594.8	1503.9	1375.4	1222.0	1047.5	866.0	692.2	548.2
120°	1609.2	1602.2	1574.3	1509.2	1417.5	1300.1	1160.7	1003.8	840.0	682.0	551.9
122.5°	1529.2	1520.4	1489.7	1431.2	1349.6	1240.6	1111.4	969.4	818.6	675.5	558.4
125°	1417.5	1409.3	1380.3	1329.2	1254.8	1161.8	1050.3	923.7	791.2	666.9	568.1
127.5°	1325.4	1318.0	1291.7	1248.1	1181.8	1097.2	996.6	883.7	767.1	662.7	579.3
130°	1273.4	1264.1	1239.7	1197.9	1136.3	1057.3	963.2	858.6	754.0	659.9	586.7
132.5°	1222.3	1215.8	1194.1	1152.3	1094.5	1019.2	931.6	835.4	742.0	659.0	592.3
135°	1149.1	1140.9	1120.0	1085.2	1028.2	962.0	886.5	804.0	726.2	657.6	600.7
137.5°	1071.7	1066.3	1048.7	1013.4	965.5	908.1	843.0	775.4	712.4	655.0	606.3
140°	1017.8	1018.9	1000.4	967.8	923.7	873.7	817.9	758.7	704.1	654.1	610.0
142.5°	967.6	968.7	952.0	923.2	885.6	842.1	793.8	742.9	696.6	652.3	612.8
145°	898.1	895.8	886.5	862.1	833.0	799.4	762.2	723.8	686.7	649.5	614.6
147.5°	840.9	840.0	831.2	814.7	792.6	768.7	738.7	708.3	676.9	645.1	614.6
150°	807.5	807.5	800.5	787.7	770.3	748.2	723.8	697.1	670.4	641.3	614.6
152.5°	779.6	779.6	775.4	763.6	749.9	731.5	709.9	686.9	663.0	636.7	611.8
155°	744.7	743.6	741.3	732.0	721.5	707.6	690.1	671.5	651.8	628.6	608.8
157.5°	712.9	713.1	711.3	704.3	695.2	684.3	670.9	655.3	639.2	621.4	604.9
160°	692.5	693.6	693.6	686.7	678.5	670.4	658.8	646.0	630.9	615.8	603.0
162.5°	673.9	675.0	675.0	669.0	663.6	656.4	645.8	634.8	622.5	610.2	599.3
165°	649.5	649.5	650.6	646.0	641.3	635.5	627.4	620.4	611.1	601.8	593.7
167.5°	626.2	626.2	627.4	624.1	622.1	617.9	613.2	607.9	600.2	593.5	588.1
170°	612.3	612.3	613.5	611.1	610.0	607.6	603.0	599.5	593.7	587.9	584.4
172.5°	599.3	600.2	602.3	600.0	599.7	598.4	594.6	592.1	587.2	583.2	581.6
175°	584.4	585.6	586.7	585.6	585.6	585.6	583.2	582.1	579.8	577.4	577.4
177.5°	575.8	575.8	577.7	576.7	577.7	577.7	576.7	575.8	574.9	574.0	574.9
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0



TEST NUMBER: P332326

CATALOG NUMBER: S123RDIP-S775D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1262.8	1261.5	1255.7	1249.0	1240.2	1234.3	1229.7	1227.2	1219.7	1210.4	1204.2
5°	1340.8	1325.1	1308.4	1287.9	1269.1	1249.7	1237.7	1223.5	1206.3	1186.9	1173.3
7.5°	1424.4	1393.6	1360.4	1326.2	1292.3	1262.0	1235.2	1212.2	1184.7	1156.9	1137.5
10°	1488.5	1443.4	1396.8	1349.2	1305.7	1264.9	1233.5	1202.6	1169.6	1137.7	1113.6
12.5°	1546.7	1487.4	1433.7	1375.2	1319.6	1270.8	1225.5	1189.2	1149.5	1115.5	1088.0
15°	1620.4	1559.7	1494.7	1405.7	1331.9	1270.1	1215.2	1167.5	1119.4	1077.5	1050.8
17.5°	1689.3	1597.9	1510.7	1436.4	1340.5	1263.3	1196.2	1139.2	1086.4	1042.0	1009.1
20°	1717.8	1629.3	1534.5	1439.8	1345.5	1259.1	1181.1	1118.3	1063.3	1013.1	982.7
22.5°	1734.9	1634.7	1534.9	1433.1	1333.0	1243.2	1166.1	1096.9	1037.4	989.6	952.1
25°	1754.9	1635.6	1525.6	1425.1	1323.0	1225.6	1134.0	1060.7	996.3	945.5	905.7
27.5°	1768.1	1627.7	1497.8	1386.0	1282.5	1185.5	1101.5	1023.9	958.5	904.8	862.1
30°	1770.6	1621.4	1476.4	1355.5	1250.2	1161.2	1072.2	997.9	928.8	871.7	831.9
32.5°	1774.0	1605.9	1447.5	1319.0	1211.3	1123.1	1042.5	971.5	900.7	844.5	803.9
35°	1760.2	1597.4	1403.6	1256.0	1148.1	1062.8	990.0	924.6	855.0	800.5	759.1
37.5°	1700.7	1563.3	1358.2	1185.0	1072.2	993.2	933.9	876.8	813.0	754.2	715.3
40°	1640.8	1529.8	1323.0	1141.9	1024.1	942.9	889.5	842.9	781.1	726.2	684.3
42.5°	1551.6	1484.2	1289.5	1096.6	969.6	891.4	846.4	802.7	748.5	692.7	653.3
45°	1387.9	1396.8	1220.9	1024.6	894.2	815.7	773.3	742.9	694.8	648.7	608.4
47.5°	1182.7	1265.9	1140.4	947.8	814.7	741.0	704.0	677.5	645.0	599.8	563.0
50°	1048.7	1167.5	1075.9	896.3	764.9	691.6	655.0	633.5	605.2	569.6	534.5
52.5°	925.1	1052.8	998.0	838.9	710.9	643.9	608.1	590.4	567.9	534.4	502.7
55°	754.4	883.8	871.2	752.3	629.8	569.6	542.4	522.5	507.3	482.2	457.1
57.5°	610.3	732.9	739.4	656.0	558.4	498.9	475.5	460.5	450.6	431.6	408.4
60°	519.4	631.9	653.9	591.1	507.3	455.0	431.9	419.9	412.0	396.9	379.1
62.5°	444.0	539.8	564.7	519.5	458.3	409.3	391.3	379.7	374.3	361.2	345.5
65°	339.8	419.4	443.4	418.3	386.4	347.1	332.5	322.5	317.8	310.5	298.9
67.5°	255.5	313.5	339.9	322.2	310.7	285.9	276.5	271.2	267.0	262.0	252.4
70°	205.2	248.2	275.4	270.7	261.3	248.2	241.4	237.7	233.5	229.3	220.9
72.5°	165.0	194.6	220.1	222.5	214.8	212.1	206.2	204.6	202.1	197.1	192.5
75°	109.4	129.8	147.6	154.4	157.6	160.2	157.6	157.1	156.5	152.4	149.7
77.5°	71.7	82.7	93.9	105.5	110.5	114.0	114.9	116.8	115.4	113.2	111.9
80°	55.0	57.6	65.4	75.4	83.2	86.4	88.5	89.5	89.0	88.5	86.4
82.5°	39.9	42.1	45.8	52.8	59.4	64.6	65.9	65.7	66.8	67.1	65.4
85°	21.5	22.0	23.0	24.1	27.7	33.5	35.1	36.1	37.2	37.2	34.0
87.5°	11.1	10.0	10.1	9.7	10.5	10.2	12.2	13.9	14.8	13.5	14.2
90°	22.1	18.6	15.1	12.8	10.5	7.0	4.6	2.3	4.6	7.0	10.5
92.5°	147.6	97.6	67.2	50.0	40.2	31.1	21.4	14.4	21.4	31.1	40.2
95°	422.9	249.8	151.0	105.7	75.5	55.8	43.0	39.5	43.0	55.8	75.5
97.5°	464.0	268.9	174.5	125.5	95.7	78.5	68.5	67.4	68.5	78.5	95.7
100°	438.0	266.1	184.7	139.4	111.5	95.3	87.1	86.0	87.1	95.3	111.5
102.5°	415.7	269.8	196.8	155.2	130.1	114.8	107.6	105.5	107.6	114.8	130.1
105°	399.7	280.0	217.3	181.2	159.2	145.2	138.3	134.8	138.3	145.2	159.2
107.5°	398.5	299.1	244.0	210.5	189.8	176.1	169.4	165.9	169.4	176.1	189.8
110°	403.2	314.9	262.6	230.0	210.3	197.5	191.7	188.2	191.7	197.5	210.3



TEST NUMBER: P332326

CATALOG NUMBER: S123RDIP-S775D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	412.5	330.7	282.1	250.5	230.7	218.0	212.2	208.7	212.2	218.0	230.7
115°	427.6	356.7	312.5	281.2	261.4	249.8	242.8	238.2	242.8	249.8	261.4
117.5°	447.5	384.3	340.7	311.6	289.5	278.8	273.0	267.7	273.0	278.8	289.5
120°	462.4	402.0	360.2	331.1	309.1	297.4	291.6	288.1	291.6	297.4	309.1
122.5°	476.4	420.6	379.7	348.8	327.6	315.1	309.3	305.8	309.3	315.1	327.6
125°	498.4	447.3	406.6	375.3	353.2	340.4	333.5	331.1	333.5	340.4	353.2
127.5°	516.6	470.5	431.3	399.9	375.5	362.5	353.9	350.4	353.9	362.5	375.5
130°	528.6	484.5	446.1	414.8	390.4	376.4	366.0	362.5	366.0	376.4	390.4
132.5°	539.8	496.6	459.2	428.7	404.3	387.6	376.2	371.8	376.2	387.6	404.3
135°	554.2	514.7	478.7	447.3	422.9	405.5	392.7	388.1	392.7	405.5	422.9
137.5°	564.9	527.2	492.6	463.6	439.4	420.8	408.3	403.4	408.3	420.8	439.4
140°	570.5	535.6	501.9	472.9	449.6	431.0	419.4	413.6	419.4	431.0	449.6
142.5°	576.0	542.1	509.4	482.2	458.9	442.2	429.7	424.8	429.7	442.2	458.9
145°	582.1	550.7	520.5	493.8	474.0	456.6	446.1	442.7	446.1	456.6	474.0
147.5°	585.8	557.7	530.0	507.3	488.2	473.1	462.9	460.8	462.9	473.1	488.2
150°	586.7	562.3	535.6	514.7	498.4	483.3	474.0	472.9	474.0	483.3	498.4
152.5°	588.6	565.1	542.1	522.1	507.7	494.5	485.2	485.0	485.2	494.5	507.7
155°	589.1	570.5	550.7	534.4	521.7	510.1	503.1	503.1	503.1	510.1	521.7
157.5°	590.2	573.5	557.7	545.1	534.2	524.0	518.4	517.5	518.4	524.0	534.2
160°	590.2	576.3	562.3	550.7	542.6	533.3	528.6	528.6	528.6	533.3	542.6
162.5°	589.3	577.2	565.1	555.4	548.2	540.7	537.0	537.0	537.0	540.7	548.2
165°	586.7	578.6	569.3	561.2	556.5	550.7	548.4	549.6	548.4	550.7	556.5
167.5°	584.9	578.4	571.6	566.5	563.3	558.8	557.7	559.1	557.7	558.8	563.3
170°	582.1	577.4	571.6	569.3	567.0	563.5	562.3	564.7	562.3	563.5	567.0
172.5°	581.2	577.4	572.6	571.2	569.8	567.2	567.0	568.4	567.0	567.2	569.8
175°	578.6	576.3	574.0	572.8	572.8	570.5	571.6	572.8	571.6	570.5	572.8
177.5°	576.7	574.9	574.0	574.0	574.0	573.0	574.0	574.9	574.0	573.0	574.0
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0



TEST NUMBER: P332326

CATALOG NUMBER: S123RDIP-S775D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1202.1	1196.6	1192.9	1184.5	1179.0	1173.2	1167.3	1171.1	1170.7	1170.2	1170.2
5°	1161.8	1149.7	1138.7	1124.6	1115.7	1104.7	1096.3	1095.3	1097.4	1090.0	1085.8
7.5°	1121.8	1105.3	1089.7	1074.1	1057.6	1044.4	1036.1	1032.2	1026.9	1022.4	1017.7
10°	1093.7	1074.3	1059.1	1039.8	1022.0	1006.3	996.3	989.5	985.8	982.2	975.4
12.5°	1064.8	1045.8	1026.5	1004.6	987.6	969.4	962.0	954.3	947.3	943.2	933.9
15°	1022.5	997.9	977.5	954.4	935.6	917.8	907.3	892.1	890.0	884.8	875.4
17.5°	980.1	953.4	925.2	908.2	886.9	868.4	852.4	847.3	832.3	826.7	818.5
20°	946.6	922.0	900.5	878.0	847.1	829.8	817.3	810.5	798.4	791.1	785.8
22.5°	917.7	892.7	867.8	841.6	816.1	796.7	787.5	776.9	770.4	760.1	754.4
25°	876.4	849.2	819.4	791.1	772.8	758.1	743.4	734.0	724.6	719.9	709.4
27.5°	828.5	800.0	772.1	750.7	728.2	713.7	700.4	692.0	680.7	672.8	667.0
30°	802.1	768.6	744.5	725.1	696.3	682.7	672.8	662.3	653.9	645.5	639.8
32.5°	771.5	740.9	718.1	694.1	672.0	657.2	644.3	635.1	627.9	620.0	614.2
35°	723.5	697.9	674.3	650.2	634.0	618.8	603.7	595.8	589.0	581.7	576.4
37.5°	680.2	656.2	633.8	611.0	590.9	578.5	566.3	560.3	551.1	546.2	540.8
40°	653.4	629.8	605.7	583.8	562.8	553.4	542.4	533.5	525.1	521.5	515.7
42.5°	624.1	600.5	580.2	556.5	539.4	526.6	516.4	506.7	500.4	495.1	491.8
45°	580.6	559.7	539.8	516.2	500.0	489.0	477.5	468.6	462.8	459.2	453.4
47.5°	538.4	517.5	497.3	476.7	461.0	448.5	437.0	430.8	423.1	418.6	414.8
50°	507.8	489.0	467.5	448.7	433.0	420.4	411.0	403.1	396.3	390.6	388.0
52.5°	479.8	459.7	441.1	423.6	407.0	392.8	384.2	375.9	370.8	364.2	361.1
55°	433.5	414.1	398.4	381.1	364.9	352.9	342.4	335.1	329.8	322.5	318.3
57.5°	390.0	372.7	353.9	338.9	322.2	312.0	303.3	293.4	287.0	281.3	277.2
60°	360.7	340.8	324.6	310.5	295.8	282.7	274.9	267.0	260.2	254.4	250.8
62.5°	330.2	312.8	297.4	282.0	268.6	257.2	248.1	241.5	235.5	231.8	228.2
65°	283.2	269.6	253.9	241.4	228.8	220.4	213.1	207.3	203.1	200.5	197.4
67.5°	240.1	226.9	213.2	200.8	192.5	186.1	181.3	176.3	174.2	170.9	168.8
70°	212.0	198.4	186.4	177.0	168.6	163.9	160.7	157.1	155.0	150.8	148.7
72.5°	181.5	171.6	162.9	155.2	148.5	144.2	140.2	135.7	132.4	127.7	125.7
75°	142.9	134.0	127.2	122.0	117.8	112.0	106.3	101.6	100.0	98.4	97.9
77.5°	105.9	100.2	95.3	90.9	85.7	81.5	80.2	79.2	78.8	78.0	78.0
80°	83.2	78.0	74.3	69.1	66.0	66.0	66.0	64.9	65.4	65.4	65.4
82.5°	61.9	57.1	55.1	53.2	52.6	53.0	53.0	53.2	52.9	53.7	53.3
85°	31.9	32.5	33.5	33.0	33.5	33.5	34.6	34.0	34.6	33.5	34.6
87.5°	14.3	16.0	17.1	18.2	19.4	19.6	19.8	20.0	20.7	20.9	21.4
90°	12.8	15.1	18.6	22.1	25.6	29.0	27.9	29.0	30.2	31.4	33.7
92.5°	50.0	67.2	97.6	147.6	196.6	178.7	134.8	97.8	77.6	68.5	62.5
95°	105.7	151.0	249.8	422.9	613.5	689.0	558.8	418.3	283.5	221.9	180.1
97.5°	125.5	174.5	268.9	464.0	781.7	1067.7	1142.3	1042.6	835.1	685.3	546.3
100°	139.4	184.7	266.1	438.0	743.6	1100.3	1329.2	1369.8	1275.7	1139.8	974.8
102.5°	155.2	196.8	269.8	415.7	687.8	1039.9	1338.4	1478.6	1475.5	1396.3	1291.7
105°	181.2	217.3	280.0	399.7	619.3	934.1	1267.6	1510.4	1626.6	1648.7	1618.5
107.5°	210.5	244.0	299.1	398.5	575.6	840.7	1143.5	1418.8	1607.5	1709.3	1750.7
110°	230.0	262.6	314.9	403.2	558.8	787.7	1065.4	1331.5	1545.3	1691.7	1773.0



TEST NUMBER: P332326

CATALOG NUMBER: S123RDIP-S775D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	250.5	282.1	330.7	412.5	549.6	752.4	997.6	1245.0	1463.5	1627.5	1732.1
115°	281.2	312.5	356.7	427.6	546.1	714.5	915.5	1130.5	1332.6	1503.4	1630.1
117.5°	311.6	340.7	384.3	447.5	548.2	692.2	866.0	1047.5	1222.0	1375.4	1503.9
120°	331.1	360.2	402.0	462.4	551.9	682.0	840.0	1003.8	1160.7	1300.1	1417.5
122.5°	348.8	379.7	420.6	476.4	558.4	675.5	818.6	969.4	1111.4	1240.6	1349.6
125°	375.3	406.6	447.3	498.4	568.1	666.9	791.2	923.7	1050.3	1161.8	1254.8
127.5°	399.9	431.3	470.5	516.6	579.3	662.7	767.1	883.7	996.6	1097.2	1181.8
130°	414.8	446.1	484.5	528.6	586.7	659.9	754.0	858.6	963.2	1057.3	1136.3
132.5°	428.7	459.2	496.6	539.8	592.3	659.0	742.0	835.4	931.6	1019.2	1094.5
135°	447.3	478.7	514.7	554.2	600.7	657.6	726.2	804.0	886.5	962.0	1028.2
137.5°	463.6	492.6	527.2	564.9	606.3	655.0	712.4	775.4	843.0	908.1	965.5
140°	472.9	501.9	535.6	570.5	610.0	654.1	704.1	758.7	817.9	873.7	923.7
142.5°	482.2	509.4	542.1	576.0	612.8	652.3	696.6	742.9	793.8	842.1	885.6
145°	493.8	520.5	550.7	582.1	614.6	649.5	686.7	723.8	762.2	799.4	833.0
147.5°	507.3	530.0	557.7	585.8	614.6	645.1	676.9	708.3	738.7	768.7	792.6
150°	514.7	535.6	562.3	586.7	614.6	641.3	670.4	697.1	723.8	748.2	770.3
152.5°	522.1	542.1	565.1	588.6	611.8	636.7	663.0	686.9	709.9	731.5	749.9
155°	534.4	550.7	570.5	589.1	608.8	628.6	651.8	671.5	690.1	707.6	721.5
157.5°	545.1	557.7	573.5	590.2	604.9	621.4	639.2	655.3	670.9	684.3	695.2
160°	550.7	562.3	576.3	590.2	603.0	615.8	630.9	646.0	658.8	670.4	678.5
162.5°	555.4	565.1	577.2	589.3	599.3	610.2	622.5	634.8	645.8	656.4	663.6
165°	561.2	569.3	578.6	586.7	593.7	601.8	611.1	620.4	627.4	635.5	641.3
167.5°	566.5	571.6	578.4	584.9	588.1	593.5	600.2	607.9	613.2	617.9	622.1
170°	569.3	571.6	577.4	582.1	584.4	587.9	593.7	599.5	603.0	607.6	610.0
172.5°	571.2	572.6	577.4	581.2	581.6	583.2	587.2	592.1	594.6	598.4	599.7
175°	572.8	574.0	576.3	578.6	577.4	577.4	579.8	582.1	583.2	585.6	585.6
177.5°	574.0	574.0	574.9	576.7	574.9	574.0	574.9	575.8	576.7	577.7	577.7
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0



TEST NUMBER: P332326

CATALOG NUMBER: S123RDIP-S775D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1165.2	1164.8	1165.2	1163.5	1165.2	1164.8	1165.2	1170.2	1170.2	1170.7	1171.1
5°	1084.3	1083.7	1082.2	1077.5	1082.2	1083.7	1084.3	1085.8	1090.0	1097.4	1095.3
7.5°	1013.6	1012.9	1008.3	1008.4	1008.3	1012.9	1013.6	1017.7	1022.4	1026.9	1032.2
10°	971.7	972.2	966.0	962.3	966.0	972.2	971.7	975.4	982.2	985.8	989.5
12.5°	931.1	928.7	923.6	919.6	923.6	928.7	931.1	933.9	943.2	947.3	954.3
15°	877.5	872.2	859.7	860.7	859.7	872.2	877.5	875.4	884.8	890.0	892.1
17.5°	814.3	810.5	810.2	802.9	810.2	810.5	814.3	818.5	826.7	832.3	847.3
20°	777.5	774.9	775.9	768.6	775.9	774.9	777.5	785.8	791.1	798.4	810.5
22.5°	748.6	746.0	741.6	739.3	741.6	746.0	748.6	754.4	760.1	770.4	776.9
25°	706.3	702.1	697.9	700.5	697.9	702.1	706.3	709.4	719.9	724.6	734.0
27.5°	664.0	660.8	656.6	656.1	656.6	660.8	664.0	667.0	672.8	680.7	692.0
30°	637.2	634.0	631.9	629.3	631.9	634.0	637.2	639.8	645.5	653.9	662.3
32.5°	609.9	609.3	605.5	605.0	605.5	609.3	609.9	614.2	620.0	627.9	635.1
35°	574.3	571.2	570.1	570.7	570.1	571.2	574.3	576.4	581.7	589.0	595.8
37.5°	540.5	536.3	534.4	532.6	534.4	536.3	540.5	540.8	546.2	551.1	560.3
40°	516.2	512.0	511.0	509.9	511.0	512.0	516.2	515.7	521.5	525.1	533.5
42.5°	489.0	487.3	486.7	484.8	486.7	487.3	489.0	491.8	495.1	500.4	506.7
45°	451.8	451.3	448.2	449.2	448.2	451.3	451.8	453.4	459.2	462.8	468.6
47.5°	412.7	410.4	408.2	409.6	408.2	410.4	412.7	414.8	418.6	423.1	430.8
50°	385.9	384.8	380.1	381.1	380.1	384.8	385.9	388.0	390.6	396.3	403.1
52.5°	359.1	355.1	353.3	352.7	353.3	355.1	359.1	361.1	364.2	370.8	375.9
55°	314.7	309.9	307.8	306.8	307.8	309.9	314.7	318.3	322.5	329.8	335.1
57.5°	271.1	269.8	268.2	269.3	268.2	269.8	271.1	277.2	281.3	287.0	293.4
60°	245.5	245.5	245.5	245.0	245.5	245.5	245.5	250.8	254.4	260.2	267.0
62.5°	225.9	224.6	224.2	224.9	224.2	224.6	225.9	228.2	231.8	235.5	241.5
65°	195.8	195.3	193.2	192.7	193.2	195.3	195.8	197.4	200.5	203.1	207.3
67.5°	167.4	165.5	164.9	164.2	164.9	165.5	167.4	168.8	170.9	174.2	176.3
70°	146.1	145.0	141.9	142.4	141.9	145.0	146.1	148.7	150.8	155.0	157.1
72.5°	123.0	122.0	121.4	120.6	121.4	122.0	123.0	125.7	127.7	132.4	135.7
75°	97.4	96.9	96.3	98.4	96.3	96.9	97.4	97.9	98.4	100.0	101.6
77.5°	78.0	78.0	78.3	77.5	78.3	78.0	78.0	78.0	78.0	78.8	79.2
80°	65.4	65.4	64.9	64.9	64.9	65.4	65.4	65.4	65.4	65.4	64.9
82.5°	52.5	52.9	53.2	52.4	53.2	52.9	52.5	53.3	53.7	52.9	53.2
85°	34.6	34.0	35.1	34.6	35.1	34.0	34.6	34.6	33.5	34.6	34.0
87.5°	22.0	21.4	21.6	21.8	21.6	21.4	22.0	21.4	20.9	20.7	20.0
90°	32.5	33.7	34.9	33.7	34.9	33.7	32.5	33.7	31.4	30.2	29.0
92.5°	60.4	56.9	58.1	56.0	58.1	56.9	60.4	62.5	68.5	77.6	97.8
95°	158.0	147.6	139.4	134.8	139.4	147.6	158.0	180.1	221.9	283.5	418.3
97.5°	460.6	408.3	376.9	366.9	376.9	408.3	460.6	546.3	685.3	835.1	1042.6
100°	857.4	772.6	727.3	728.5	727.3	772.6	857.4	974.8	1139.8	1275.7	1369.8
102.5°	1200.4	1133.3	1095.4	1068.7	1095.4	1133.3	1200.4	1291.7	1396.3	1475.5	1478.6
105°	1565.0	1520.9	1483.7	1477.9	1483.7	1520.9	1565.0	1618.5	1648.7	1626.6	1510.4
107.5°	1751.6	1736.7	1724.2	1713.5	1724.2	1736.7	1751.6	1750.7	1709.3	1607.5	1418.8
110°	1805.5	1814.8	1812.5	1810.2	1812.5	1814.8	1805.5	1773.0	1691.7	1545.3	1331.5



TEST NUMBER: P332326

CATALOG NUMBER: S123RDIP-S775D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1791.6	1820.4	1829.2	1829.7	1829.2	1820.4	1791.6	1732.1	1627.5	1463.5	1245.0
115°	1717.2	1768.3	1791.6	1797.4	1791.6	1768.3	1717.2	1630.1	1503.4	1332.6	1130.5
117.5°	1594.8	1653.3	1686.8	1694.7	1686.8	1653.3	1594.8	1503.9	1375.4	1222.0	1047.5
120°	1509.2	1574.3	1602.2	1609.2	1602.2	1574.3	1509.2	1417.5	1300.1	1160.7	1003.8
122.5°	1431.2	1489.7	1520.4	1529.2	1520.4	1489.7	1431.2	1349.6	1240.6	1111.4	969.4
125°	1329.2	1380.3	1409.3	1417.5	1409.3	1380.3	1329.2	1254.8	1161.8	1050.3	923.7
127.5°	1248.1	1291.7	1318.0	1325.4	1318.0	1291.7	1248.1	1181.8	1097.2	996.6	883.7
130°	1197.9	1239.7	1264.1	1273.4	1264.1	1239.7	1197.9	1136.3	1057.3	963.2	858.6
132.5°	1152.3	1194.1	1215.8	1222.3	1215.8	1194.1	1152.3	1094.5	1019.2	931.6	835.4
135°	1085.2	1120.0	1140.9	1149.1	1140.9	1120.0	1085.2	1028.2	962.0	886.5	804.0
137.5°	1013.4	1048.7	1066.3	1071.7	1066.3	1048.7	1013.4	965.5	908.1	843.0	775.4
140°	967.8	1000.4	1018.9	1017.8	1018.9	1000.4	967.8	923.7	873.7	817.9	758.7
142.5°	923.2	952.0	968.7	967.6	968.7	952.0	923.2	885.6	842.1	793.8	742.9
145°	862.1	886.5	895.8	898.1	895.8	886.5	862.1	833.0	799.4	762.2	723.8
147.5°	814.7	831.2	840.0	840.9	840.0	831.2	814.7	792.6	768.7	738.7	708.3
150°	787.7	800.5	807.5	807.5	807.5	800.5	787.7	770.3	748.2	723.8	697.1
152.5°	763.6	775.4	779.6	779.6	779.6	775.4	763.6	749.9	731.5	709.9	686.9
155°	732.0	741.3	743.6	744.7	743.6	741.3	732.0	721.5	707.6	690.1	671.5
157.5°	704.3	711.3	713.1	712.9	713.1	711.3	704.3	695.2	684.3	670.9	655.3
160°	686.7	693.6	693.6	692.5	693.6	693.6	686.7	678.5	670.4	658.8	646.0
162.5°	669.0	675.0	675.0	673.9	675.0	675.0	669.0	663.6	656.4	645.8	634.8
165°	646.0	650.6	649.5	649.5	649.5	650.6	646.0	641.3	635.5	627.4	620.4
167.5°	624.1	627.4	626.2	626.2	626.2	627.4	624.1	622.1	617.9	613.2	607.9
170°	611.1	613.5	612.3	612.3	612.3	613.5	611.1	610.0	607.6	603.0	599.5
172.5°	600.0	602.3	600.2	599.3	600.2	602.3	600.0	599.7	598.4	594.6	592.1
175°	585.6	586.7	585.6	584.4	585.6	586.7	585.6	585.6	585.6	583.2	582.1
177.5°	576.7	577.7	575.8	575.8	575.8	577.7	576.7	577.7	577.7	576.7	575.8
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0



TEST NUMBER: P332326

CATALOG NUMBER: S123RDIP-S775D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1167.3	1173.2	1179.0	1184.5	1192.9	1196.6	1202.1	1204.2	1210.4	1219.7	1227.2
5°	1096.3	1104.7	1115.7	1124.6	1138.7	1149.7	1161.8	1173.3	1186.9	1206.3	1223.5
7.5°	1036.1	1044.4	1057.6	1074.1	1089.7	1105.3	1121.8	1137.5	1156.9	1184.7	1212.2
10°	996.3	1006.3	1022.0	1039.8	1059.1	1074.3	1093.7	1113.6	1137.7	1169.6	1202.6
12.5°	962.0	969.4	987.6	1004.6	1026.5	1045.8	1064.8	1088.0	1115.5	1149.5	1189.2
15°	907.3	917.8	935.6	954.4	977.5	997.9	1022.5	1050.8	1077.5	1119.4	1167.5
17.5°	852.4	868.4	886.9	908.2	925.2	953.4	980.1	1009.1	1042.0	1086.4	1139.2
20°	817.3	829.8	847.1	878.0	900.5	922.0	946.6	982.7	1013.1	1063.3	1118.3
22.5°	787.5	796.7	816.1	841.6	867.8	892.7	917.7	952.1	989.6	1037.4	1096.9
25°	743.4	758.1	772.8	791.1	819.4	849.2	876.4	905.7	945.5	996.3	1060.7
27.5°	700.4	713.7	728.2	750.7	772.1	800.0	828.5	862.1	904.8	958.5	1023.9
30°	672.8	682.7	696.3	725.1	744.5	768.6	802.1	831.9	871.7	928.8	997.9
32.5°	644.3	657.2	672.0	694.1	718.1	740.9	771.5	803.9	844.5	900.7	971.5
35°	603.7	618.8	634.0	650.2	674.3	697.9	723.5	759.1	800.5	855.0	924.6
37.5°	566.3	578.5	590.9	611.0	633.8	656.2	680.2	715.3	754.2	813.0	876.8
40°	542.4	553.4	562.8	583.8	605.7	629.8	653.4	684.3	726.2	781.1	842.9
42.5°	516.4	526.6	539.4	556.5	580.2	600.5	624.1	653.3	692.7	748.5	802.7
45°	477.5	489.0	500.0	516.2	539.8	559.7	580.6	608.4	648.7	694.8	742.9
47.5°	437.0	448.5	461.0	476.7	497.3	517.5	538.4	563.0	599.8	645.0	677.5
50°	411.0	420.4	433.0	448.7	467.5	489.0	507.8	534.5	569.6	605.2	633.5
52.5°	384.2	392.8	407.0	423.6	441.1	459.7	479.8	502.7	534.4	567.9	590.4
55°	342.4	352.9	364.9	381.1	398.4	414.1	433.5	457.1	482.2	507.3	522.5
57.5°	303.3	312.0	322.2	338.9	353.9	372.7	390.0	408.4	431.6	450.6	460.5
60°	274.9	282.7	295.8	310.5	324.6	340.8	360.7	379.1	396.9	412.0	419.9
62.5°	248.1	257.2	268.6	282.0	297.4	312.8	330.2	345.5	361.2	374.3	379.7
65°	213.1	220.4	228.8	241.4	253.9	269.6	283.2	298.9	310.5	317.8	322.5
67.5°	181.3	186.1	192.5	200.8	213.2	226.9	240.1	252.4	262.0	267.0	271.2
70°	160.7	163.9	168.6	177.0	186.4	198.4	212.0	220.9	229.3	233.5	237.7
72.5°	140.2	144.2	148.5	155.2	162.9	171.6	181.5	192.5	197.1	202.1	204.6
75°	106.3	112.0	117.8	122.0	127.2	134.0	142.9	149.7	152.4	156.5	157.1
77.5°	80.2	81.5	85.7	90.9	95.3	100.2	105.9	111.9	113.2	115.4	116.8
80°	66.0	66.0	66.0	69.1	74.3	78.0	83.2	86.4	88.5	89.0	89.5
82.5°	53.0	53.0	52.6	53.2	55.1	57.1	61.9	65.4	67.1	66.8	65.7
85°	34.6	33.5	33.5	33.0	33.5	32.5	31.9	34.0	37.2	37.2	36.1
87.5°	19.8	19.6	19.4	18.2	17.1	16.0	14.3	14.2	13.5	14.8	13.9
90°	27.9	29.0	25.6	22.1	18.6	15.1	12.8	10.5	7.0	4.6	2.3
92.5°	134.8	178.7	196.6	147.6	97.6	67.2	50.0	40.2	31.1	21.4	14.4
95°	558.8	689.0	613.5	422.9	249.8	151.0	105.7	75.5	55.8	43.0	39.5
97.5°	1142.3	1067.7	781.7	464.0	268.9	174.5	125.5	95.7	78.5	68.5	67.4
100°	1329.2	1100.3	743.6	438.0	266.1	184.7	139.4	111.5	95.3	87.1	86.0
102.5°	1338.4	1039.9	687.8	415.7	269.8	196.8	155.2	130.1	114.8	107.6	105.5
105°	1267.6	934.1	619.3	399.7	280.0	217.3	181.2	159.2	145.2	138.3	134.8
107.5°	1143.5	840.7	575.6	398.5	299.1	244.0	210.5	189.8	176.1	169.4	165.9
110°	1065.4	787.7	558.8	403.2	314.9	262.6	230.0	210.3	197.5	191.7	188.2



TEST NUMBER: P332326

CATALOG NUMBER: S123RDIP-S775D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	997.6	752.4	549.6	412.5	330.7	282.1	250.5	230.7	218.0	212.2	208.7
115°	915.5	714.5	546.1	427.6	356.7	312.5	281.2	261.4	249.8	242.8	238.2
117.5°	866.0	692.2	548.2	447.5	384.3	340.7	311.6	289.5	278.8	273.0	267.7
120°	840.0	682.0	551.9	462.4	402.0	360.2	331.1	309.1	297.4	291.6	288.1
122.5°	818.6	675.5	558.4	476.4	420.6	379.7	348.8	327.6	315.1	309.3	305.8
125°	791.2	666.9	568.1	498.4	447.3	406.6	375.3	353.2	340.4	333.5	331.1
127.5°	767.1	662.7	579.3	516.6	470.5	431.3	399.9	375.5	362.5	353.9	350.4
130°	754.0	659.9	586.7	528.6	484.5	446.1	414.8	390.4	376.4	366.0	362.5
132.5°	742.0	659.0	592.3	539.8	496.6	459.2	428.7	404.3	387.6	376.2	371.8
135°	726.2	657.6	600.7	554.2	514.7	478.7	447.3	422.9	405.5	392.7	388.1
137.5°	712.4	655.0	606.3	564.9	527.2	492.6	463.6	439.4	420.8	408.3	403.4
140°	704.1	654.1	610.0	570.5	535.6	501.9	472.9	449.6	431.0	419.4	413.6
142.5°	696.6	652.3	612.8	576.0	542.1	509.4	482.2	458.9	442.2	429.7	424.8
145°	686.7	649.5	614.6	582.1	550.7	520.5	493.8	474.0	456.6	446.1	442.7
147.5°	676.9	645.1	614.6	585.8	557.7	530.0	507.3	488.2	473.1	462.9	460.8
150°	670.4	641.3	614.6	586.7	562.3	535.6	514.7	498.4	483.3	474.0	472.9
152.5°	663.0	636.7	611.8	588.6	565.1	542.1	522.1	507.7	494.5	485.2	485.0
155°	651.8	628.6	608.8	589.1	570.5	550.7	534.4	521.7	510.1	503.1	503.1
157.5°	639.2	621.4	604.9	590.2	573.5	557.7	545.1	534.2	524.0	518.4	517.5
160°	630.9	615.8	603.0	590.2	576.3	562.3	550.7	542.6	533.3	528.6	528.6
162.5°	622.5	610.2	599.3	589.3	577.2	565.1	555.4	548.2	540.7	537.0	537.0
165°	611.1	601.8	593.7	586.7	578.6	569.3	561.2	556.5	550.7	548.4	549.6
167.5°	600.2	593.5	588.1	584.9	578.4	571.6	566.5	563.3	558.8	557.7	559.1
170°	593.7	587.9	584.4	582.1	577.4	571.6	569.3	567.0	563.5	562.3	564.7
172.5°	587.2	583.2	581.6	581.2	577.4	572.6	571.2	569.8	567.2	567.0	568.4
175°	579.8	577.4	577.4	578.6	576.3	574.0	572.8	572.8	570.5	571.6	572.8
177.5°	574.9	574.0	574.9	576.7	574.9	574.0	574.0	574.0	573.0	574.0	574.9
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0



TEST NUMBER: P332326

CATALOG NUMBER: S123RDIP-S775D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1229.7	1234.3	1240.2	1249.0	1255.7	1261.5	1262.8	1264.5	1268.7	1275.8	1281.2
5°	1237.7	1249.7	1269.1	1287.9	1308.4	1325.1	1340.8	1351.8	1362.3	1384.3	1402.1
7.5°	1235.2	1262.0	1292.3	1326.2	1360.4	1393.6	1424.4	1451.9	1479.3	1511.4	1547.9
10°	1233.5	1264.9	1305.7	1349.2	1396.8	1443.4	1488.5	1523.5	1564.4	1601.0	1647.6
12.5°	1225.5	1270.8	1319.6	1375.2	1433.7	1487.4	1546.7	1595.2	1641.9	1694.8	1749.0
15°	1215.2	1270.1	1331.9	1405.7	1494.7	1559.7	1620.4	1704.7	1762.3	1819.9	1897.3
17.5°	1196.2	1263.3	1340.5	1436.4	1510.7	1597.9	1689.3	1755.9	1833.5	1914.6	1984.8
20°	1181.1	1259.1	1345.5	1439.8	1534.5	1629.3	1717.8	1797.3	1877.5	1971.2	2028.8
22.5°	1166.1	1243.2	1333.0	1433.1	1534.9	1634.7	1734.9	1828.3	1918.5	2013.1	2086.6
25°	1134.0	1225.6	1323.0	1425.1	1525.6	1635.6	1754.9	1859.1	1970.6	2068.0	2137.7
27.5°	1101.5	1185.5	1282.5	1386.0	1497.8	1627.7	1768.1	1886.6	1998.3	2068.0	2089.9
30°	1072.2	1161.2	1250.2	1355.5	1476.4	1621.4	1770.6	1906.2	1997.9	2028.2	2005.7
32.5°	1042.5	1123.1	1211.3	1319.0	1447.5	1605.9	1774.0	1894.5	1949.7	1926.5	1834.8
35°	990.0	1062.8	1148.1	1256.0	1403.6	1597.4	1760.2	1841.8	1828.2	1697.3	1524.6
37.5°	933.9	993.2	1072.2	1185.0	1358.2	1563.3	1700.7	1712.7	1594.9	1394.0	1194.4
40°	889.5	942.9	1024.1	1141.9	1323.0	1529.8	1640.8	1592.1	1409.4	1185.8	1019.4
42.5°	846.4	891.4	969.6	1096.6	1289.5	1484.2	1551.6	1445.5	1234.7	1023.3	871.9
45°	773.3	815.7	894.2	1024.6	1220.9	1396.8	1387.9	1203.6	992.7	822.5	696.8
47.5°	704.0	741.0	814.7	947.8	1140.4	1265.9	1182.7	986.6	807.6	671.1	581.5
50°	655.0	691.6	764.9	896.3	1075.9	1167.5	1048.7	859.7	695.8	582.7	511.5
52.5°	608.1	643.9	710.9	838.9	998.0	1052.8	925.1	749.9	613.3	515.7	454.5
55°	542.4	569.6	629.8	752.3	871.2	883.8	754.4	607.8	495.3	427.2	385.3
57.5°	475.5	498.9	558.4	656.0	739.4	732.9	610.3	483.4	407.6	357.1	326.7
60°	431.9	455.0	507.3	591.1	653.9	631.9	519.4	417.3	352.3	315.2	291.1
62.5°	391.3	409.3	458.3	519.5	564.7	539.8	444.0	359.5	308.0	276.6	257.6
65°	332.5	347.1	386.4	418.3	443.4	419.4	339.8	281.1	244.0	222.0	208.9
67.5°	276.5	285.9	310.7	322.2	339.9	313.5	255.5	216.2	195.1	176.5	167.4
70°	241.4	248.2	261.3	270.7	275.4	248.2	205.2	176.4	158.6	145.5	139.8
72.5°	206.2	212.1	214.8	222.5	220.1	194.6	165.0	142.1	129.3	120.4	113.0
75°	157.6	160.2	157.6	154.4	147.6	129.8	109.4	97.9	88.5	84.3	81.7
77.5°	114.9	114.0	110.5	105.5	93.9	82.7	71.7	67.9	63.8	61.6	60.6
80°	88.5	86.4	83.2	75.4	65.4	57.6	55.0	52.4	50.8	48.2	47.6
82.5°	65.9	64.6	59.4	52.8	45.8	42.1	39.9	39.0	37.4	36.0	35.9
85°	35.1	33.5	27.7	24.1	23.0	22.0	21.5	21.5	19.4	18.8	18.8
87.5°	12.2	10.2	10.5	9.7	10.1	10.0	11.1	11.0	11.3	11.4	10.8
90°	4.6	7.0	10.5	12.8	15.1	18.6	22.1	25.6	29.0	27.9	29.0
92.5°	21.4	31.1	40.2	50.0	67.2	97.6	147.6	196.6	178.7	134.8	97.8
95°	43.0	55.8	75.5	105.7	151.0	249.8	422.9	613.5	689.0	558.8	418.3
97.5°	68.5	78.5	95.7	125.5	174.5	268.9	464.0	781.7	1067.7	1142.3	1042.6
100°	87.1	95.3	111.5	139.4	184.7	266.1	438.0	743.6	1100.3	1329.2	1369.8
102.5°	107.6	114.8	130.1	155.2	196.8	269.8	415.7	687.8	1039.9	1338.4	1478.6
105°	138.3	145.2	159.2	181.2	217.3	280.0	399.7	619.3	934.1	1267.6	1510.4
107.5°	169.4	176.1	189.8	210.5	244.0	299.1	398.5	575.6	840.7	1143.5	1418.8
110°	191.7	197.5	210.3	230.0	262.6	314.9	403.2	558.8	787.7	1065.4	1331.5



TEST NUMBER: P332326

CATALOG NUMBER: S123RDIP-S775D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	212.2	218.0	230.7	250.5	282.1	330.7	412.5	549.6	752.4	997.6	1245.0
115°	242.8	249.8	261.4	281.2	312.5	356.7	427.6	546.1	714.5	915.5	1130.5
117.5°	273.0	278.8	289.5	311.6	340.7	384.3	447.5	548.2	692.2	866.0	1047.5
120°	291.6	297.4	309.1	331.1	360.2	402.0	462.4	551.9	682.0	840.0	1003.8
122.5°	309.3	315.1	327.6	348.8	379.7	420.6	476.4	558.4	675.5	818.6	969.4
125°	333.5	340.4	353.2	375.3	406.6	447.3	498.4	568.1	666.9	791.2	923.7
127.5°	353.9	362.5	375.5	399.9	431.3	470.5	516.6	579.3	662.7	767.1	883.7
130°	366.0	376.4	390.4	414.8	446.1	484.5	528.6	586.7	659.9	754.0	858.6
132.5°	376.2	387.6	404.3	428.7	459.2	496.6	539.8	592.3	659.0	742.0	835.4
135°	392.7	405.5	422.9	447.3	478.7	514.7	554.2	600.7	657.6	726.2	804.0
137.5°	408.3	420.8	439.4	463.6	492.6	527.2	564.9	606.3	655.0	712.4	775.4
140°	419.4	431.0	449.6	472.9	501.9	535.6	570.5	610.0	654.1	704.1	758.7
142.5°	429.7	442.2	458.9	482.2	509.4	542.1	576.0	612.8	652.3	696.6	742.9
145°	446.1	456.6	474.0	493.8	520.5	550.7	582.1	614.6	649.5	686.7	723.8
147.5°	462.9	473.1	488.2	507.3	530.0	557.7	585.8	614.6	645.1	676.9	708.3
150°	474.0	483.3	498.4	514.7	535.6	562.3	586.7	614.6	641.3	670.4	697.1
152.5°	485.2	494.5	507.7	522.1	542.1	565.1	588.6	611.8	636.7	663.0	686.9
155°	503.1	510.1	521.7	534.4	550.7	570.5	589.1	608.8	628.6	651.8	671.5
157.5°	518.4	524.0	534.2	545.1	557.7	573.5	590.2	604.9	621.4	639.2	655.3
160°	528.6	533.3	542.6	550.7	562.3	576.3	590.2	603.0	615.8	630.9	646.0
162.5°	537.0	540.7	548.2	555.4	565.1	577.2	589.3	599.3	610.2	622.5	634.8
165°	548.4	550.7	556.5	561.2	569.3	578.6	586.7	593.7	601.8	611.1	620.4
167.5°	557.7	558.8	563.3	566.5	571.6	578.4	584.9	588.1	593.5	600.2	607.9
170°	562.3	563.5	567.0	569.3	571.6	577.4	582.1	584.4	587.9	593.7	599.5
172.5°	567.0	567.2	569.8	571.2	572.6	577.4	581.2	581.6	583.2	587.2	592.1
175°	571.6	570.5	572.8	572.8	574.0	576.3	578.6	577.4	577.4	579.8	582.1
177.5°	574.0	573.0	574.0	574.0	574.0	574.9	576.7	574.9	574.0	574.9	575.8
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0



TEST NUMBER: P332326

CATALOG NUMBER: S123RDIP-S775D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1290.0	1290.0	1291.7	1298.0	1298.8	1304.3	1302.6
5°	1417.8	1427.7	1431.4	1447.1	1456.5	1460.7	1452.3
7.5°	1574.0	1602.1	1615.4	1631.8	1646.4	1650.8	1639.3
10°	1687.9	1717.2	1741.9	1757.0	1771.2	1780.6	1792.6
12.5°	1798.1	1834.1	1857.5	1878.9	1893.5	1905.4	1907.4
15°	1917.8	1972.2	2013.6	2043.9	2059.1	2067.0	2063.8
17.5°	2038.5	2089.0	2118.4	2149.4	2170.4	2171.5	2172.1
20°	2106.8	2156.0	2190.0	2213.0	2236.6	2235.6	2240.8
22.5°	2152.4	2191.2	2217.2	2234.0	2242.1	2238.1	2239.1
25°	2173.8	2185.3	2180.6	2153.9	2147.1	2122.5	2126.7
27.5°	2063.6	2009.2	1952.8	1880.4	1823.2	1777.6	1779.9
30°	1914.1	1817.8	1707.8	1615.7	1533.0	1509.9	1460.7
32.5°	1705.1	1560.6	1431.8	1345.9	1274.9	1255.7	1212.8
35°	1350.8	1210.4	1078.0	998.4	967.0	923.0	922.5
37.5°	1049.9	926.4	856.3	796.6	765.3	738.7	736.1
40°	883.2	786.9	734.0	691.1	660.2	640.3	635.6
42.5°	766.8	688.9	639.4	612.8	589.0	578.7	571.1
45°	626.2	573.8	539.3	515.2	504.2	496.3	492.1
47.5°	523.8	488.7	465.1	449.1	440.2	431.9	434.1
50°	468.1	439.3	422.0	406.8	400.0	394.2	394.8
52.5°	423.2	397.4	383.4	372.5	364.0	359.9	357.9
55°	359.2	342.9	328.8	320.9	316.2	310.5	308.9
57.5°	306.4	293.8	282.3	273.4	272.2	266.7	267.4
60°	271.2	260.7	251.3	246.6	242.9	238.2	239.8
62.5°	242.3	233.5	224.9	221.0	217.4	213.9	214.7
65°	198.4	190.0	184.8	182.7	181.1	179.6	178.0
67.5°	158.1	153.0	149.7	145.2	142.0	141.5	139.9
70°	133.0	126.2	120.4	114.7	113.1	112.6	113.1
72.5°	106.6	102.3	100.7	97.9	97.6	96.2	97.2
75°	80.1	78.5	77.5	75.4	75.4	75.4	75.4
77.5°	59.1	58.1	57.5	57.1	56.5	55.8	55.7
80°	46.1	45.5	44.5	44.5	44.0	44.5	44.0
82.5°	34.8	34.7	33.6	33.6	33.1	32.8	33.1
85°	17.8	17.3	18.3	17.3	17.8	16.8	17.8
87.5°	11.1	11.3	11.3	11.1	10.9	12.0	10.9
90°	30.2	31.4	33.7	32.5	33.7	34.9	33.7
92.5°	77.6	68.5	62.5	60.4	56.9	58.1	56.0
95°	283.5	221.9	180.1	158.0	147.6	139.4	134.8
97.5°	835.1	685.3	546.3	460.6	408.3	376.9	366.9
100°	1275.7	1139.8	974.8	857.4	772.6	727.3	728.5
102.5°	1475.5	1396.3	1291.7	1200.4	1133.3	1095.4	1068.7
105°	1626.6	1648.7	1618.5	1565.0	1520.9	1483.7	1477.9
107.5°	1607.5	1709.3	1750.7	1751.6	1736.7	1724.2	1713.5
110°	1545.3	1691.7	1773.0	1805.5	1814.8	1812.5	1810.2



TEST NUMBER: P332326

CATALOG NUMBER: S123RDIP-S775D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1463.5	1627.5	1732.1	1791.6	1820.4	1829.2	1829.7
115°	1332.6	1503.4	1630.1	1717.2	1768.3	1791.6	1797.4
117.5°	1222.0	1375.4	1503.9	1594.8	1653.3	1686.8	1694.7
120°	1160.7	1300.1	1417.5	1509.2	1574.3	1602.2	1609.2
122.5°	1111.4	1240.6	1349.6	1431.2	1489.7	1520.4	1529.2
125°	1050.3	1161.8	1254.8	1329.2	1380.3	1409.3	1417.5
127.5°	996.6	1097.2	1181.8	1248.1	1291.7	1318.0	1325.4
130°	963.2	1057.3	1136.3	1197.9	1239.7	1264.1	1273.4
132.5°	931.6	1019.2	1094.5	1152.3	1194.1	1215.8	1222.3
135°	886.5	962.0	1028.2	1085.2	1120.0	1140.9	1149.1
137.5°	843.0	908.1	965.5	1013.4	1048.7	1066.3	1071.7
140°	817.9	873.7	923.7	967.8	1000.4	1018.9	1017.8
142.5°	793.8	842.1	885.6	923.2	952.0	968.7	967.6
145°	762.2	799.4	833.0	862.1	886.5	895.8	898.1
147.5°	738.7	768.7	792.6	814.7	831.2	840.0	840.9
150°	723.8	748.2	770.3	787.7	800.5	807.5	807.5
152.5°	709.9	731.5	749.9	763.6	775.4	779.6	779.6
155°	690.1	707.6	721.5	732.0	741.3	743.6	744.7
157.5°	670.9	684.3	695.2	704.3	711.3	713.1	712.9
160°	658.8	670.4	678.5	686.7	693.6	693.6	692.5
162.5°	645.8	656.4	663.6	669.0	675.0	675.0	673.9
165°	627.4	635.5	641.3	646.0	650.6	649.5	649.5
167.5°	613.2	617.9	622.1	624.1	627.4	626.2	626.2
170°	603.0	607.6	610.0	611.1	613.5	612.3	612.3
172.5°	594.6	598.4	599.7	600.0	602.3	600.2	599.3
175°	583.2	585.6	585.6	585.6	586.7	585.6	584.4
177.5°	576.7	577.7	577.7	576.7	577.7	575.8	575.8
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0

(END OF REPORT)