

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332317

Luminaire Tested: **S123RDIP-S775D805U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332317
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D805U835-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5825.3 lumens
Efficiency: N/A
Efficacy: 126.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332317

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332317

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50					50			
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	43					43			
2	90	82	76	71	82	76	71	67	65	61	58	54	52	49	45	43	41	36					36			
3	82	73	66	60	75	67	61	56	57	53	49	48	45	42	40	37	35	31					31			
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31	27					27			
5	69	58	50	44	64	54	47	41	46	41	36	39	35	32	32	29	27	24					24			
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	29	26	24	21					21			
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	24	21	19					19			
8	55	43	35	30	51	40	33	28	34	29	25	29	25	22	25	22	19	17					17			
9	51	39	32	27	47	36	30	25	32	26	23	27	23	20	23	20	17	15					15			
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14					14			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13897	13897	13897
5°	13950	13758	13837
10°	13871	13585	13539
15°	13722	13266	13127
20°	13518	12869	12569
25°	13307	12423	12025
30°	13027	11908	11257
35°	12741	11393	10553
40°	12476	10784	9681
45°	12129	10185	8894
50°	11747	9503	8013
55°	11357	8724	7191
60°	11001	7890	6288
65°	10534	6986	5387
70°	9951	5866	4349
75°	9100	4616	4092
80°	8114	4091	3763
85°	6854	3619	3359



TEST NUMBER: P332317

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.2	2.1
10°-20°	337.3	5.8
20°-30°	485.7	8.3
30°-40°	547.1	9.4
40°-50°	523.4	9.0
50°-60°	428.6	7.4
60°-70°	289.2	5.0
70°-80°	145.5	2.5
80°-90°	41.5	0.7
90°-100°	214.9	3.7
100°-110°	608.6	10.4
110°-120°	598.7	10.3
120°-130°	477.5	8.2
130°-140°	376.5	6.5
140°-150°	281.0	4.8
150°-160°	195.9	3.4
160°-170°	115.1	2.0
170°-180°	37.4	0.6
0°-30°	944.3	16.2
0°-40°	1491.4	25.6
0°-60°	2443.4	41.9
0°-90°	2919.6	50.1
90°-120°	1422.2	24.4
90°-150°	2557.3	43.9
90°-180°	2906.0	49.9
0°-180°	5825.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1291	1291	1291	1291	1291	
5°	1291	1285	1273	1282	1281	122
15°	1231	1219	1190	1185	1178	347
25°	1120	1093	1046	1025	1012	515
35°	970	930	867	823	803	607
45°	797	748	669	611	584	615
55°	605	552	465	406	383	542
65°	414	355	274	225	212	409
75°	219	168	111	101	98	233
85°	56	34	29	27	27	62
90°	2	9	20	22	23	5
95°	27	86	464	135	91	29
105°	91	134	629	1099	994	96
115°	160	200	481	1054	1210	159
125°	223	263	449	813	954	198
135°	261	312	442	670	773	202
145°	298	341	437	549	604	187
155°	338	365	423	481	501	156
165°	370	380	405	430	437	104
175°	385	386	389	394	393	37
180°	386	386	386	386	386	



TEST NUMBER: P332317

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1295.2	1294.5	1293.7	1293.0	1292.3	1290.8	1288.5	1286.3	1284.1	1281.8	1283.9
5°	1291.1	1289.9	1288.7	1287.6	1286.4	1284.4	1281.6	1278.8	1276.0	1273.3	1275.3
7.5°	1279.1	1277.9	1276.6	1275.3	1274.1	1271.6	1268.0	1264.4	1260.8	1257.1	1258.3
10°	1269.1	1267.4	1265.8	1264.2	1262.5	1259.6	1255.4	1251.3	1247.1	1242.9	1243.1
12.5°	1254.8	1253.0	1251.2	1249.4	1247.6	1244.1	1239.0	1233.9	1228.7	1223.6	1223.5
15°	1231.4	1228.8	1226.2	1223.7	1221.1	1216.6	1210.1	1203.6	1197.0	1190.5	1189.4
17.5°	1201.8	1198.9	1195.9	1192.9	1189.9	1184.3	1176.0	1167.7	1159.4	1151.2	1148.7
20°	1180.1	1176.3	1172.6	1168.9	1165.2	1158.9	1150.0	1141.2	1132.4	1123.5	1120.5
22.5°	1155.8	1151.5	1147.2	1142.9	1138.6	1131.8	1122.4	1113.0	1103.6	1094.2	1090.4
25°	1120.4	1114.6	1108.7	1102.9	1097.1	1088.8	1078.1	1067.4	1056.7	1046.0	1041.1
27.5°	1077.4	1071.0	1064.6	1058.2	1051.8	1042.6	1030.7	1018.8	1006.8	994.9	988.1
30°	1048.1	1041.1	1034.2	1027.2	1020.2	1010.2	997.2	984.1	971.1	958.1	950.2
32.5°	1018.8	1010.9	1003.0	995.1	987.2	976.3	962.5	948.8	935.0	921.2	912.6
35°	969.6	961.2	952.8	944.5	936.1	924.7	910.3	895.8	881.4	867.0	857.0
37.5°	919.8	910.4	901.1	891.8	882.5	870.2	854.8	839.4	824.0	808.6	797.2
40°	887.9	877.7	867.4	857.2	847.0	833.6	817.1	800.6	784.0	767.5	755.4
42.5°	851.9	841.7	831.4	821.2	811.0	797.3	780.2	763.1	746.1	729.0	715.8
45°	796.8	786.4	775.9	765.4	754.9	740.8	722.8	704.9	687.0	669.1	655.8
47.5°	741.8	730.3	718.8	707.3	695.8	681.1	663.2	645.2	627.3	609.4	595.0
50°	701.5	690.6	679.7	668.7	657.8	642.9	624.1	605.2	586.4	567.5	553.1
52.5°	665.5	653.7	641.8	629.9	618.1	602.8	584.1	565.5	546.8	528.1	513.2
55°	605.2	593.8	582.4	571.0	559.6	544.0	524.2	504.5	484.7	464.9	451.4
57.5°	549.5	537.1	524.7	512.2	499.8	483.7	463.8	443.9	424.0	404.2	391.4
60°	511.0	498.2	485.4	472.6	459.8	443.7	424.4	405.1	385.8	366.5	353.9
62.5°	472.4	459.6	446.8	434.0	421.3	405.2	385.9	366.6	347.3	327.9	316.1
65°	413.6	400.8	388.0	375.2	362.4	346.9	328.8	310.6	292.5	274.3	262.9
67.5°	354.8	341.8	328.9	315.9	303.0	287.8	270.4	253.0	235.6	218.2	209.7
70°	316.2	303.7	291.1	278.5	266.0	251.5	235.2	219.0	202.7	186.4	178.2
72.5°	277.7	265.3	252.9	240.5	228.2	214.6	199.8	185.0	170.2	155.4	148.7
75°	218.8	207.7	196.5	185.3	174.2	162.2	149.4	136.6	123.8	111.0	108.7
77.5°	165.2	155.1	145.0	134.9	124.8	115.7	107.4	99.2	91.0	82.7	81.5
80°	130.9	121.3	111.8	102.3	92.7	85.5	80.6	75.7	70.9	66.0	65.3
82.5°	98.2	90.0	81.7	73.5	65.3	60.0	57.7	55.4	53.2	50.9	50.2
85°	55.5	50.4	45.3	40.1	35.0	32.1	31.4	30.7	30.0	29.3	28.9
87.5°	20.4	18.7	16.9	15.4	13.6	12.9	13.4	13.9	14.3	14.8	14.5
90°	1.6	3.1	4.7	7.0	8.6	10.2	12.5	14.9	17.2	19.5	18.8
92.5°	9.7	14.4	21.0	27.1	33.6	45.2	65.7	99.3	132.3	120.2	90.7
95°	26.6	28.9	37.5	50.8	71.1	101.6	168.1	284.6	412.8	463.6	376.1
97.5°	45.3	46.1	52.9	64.4	84.4	117.4	180.9	312.3	526.0	718.5	768.7
100°	57.9	58.6	64.1	75.1	93.8	124.3	179.0	294.7	500.4	740.4	894.4
102.5°	71.0	72.4	77.2	87.6	104.5	132.4	181.5	279.7	462.8	699.7	900.7
105°	90.7	93.0	97.7	107.1	122.0	146.2	188.4	268.9	416.7	628.6	853.0
107.5°	111.6	114.0	118.5	127.7	141.7	164.2	201.2	268.2	387.3	565.7	769.5
110°	126.7	129.0	132.9	141.5	154.8	176.7	211.9	271.3	376.1	530.1	716.9



TEST NUMBER: P332317

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	140.4	142.8	146.7	155.3	168.6	189.8	222.5	277.5	369.8	506.3	671.3
115°	160.3	163.4	168.1	175.9	189.2	210.3	240.0	287.7	367.5	480.8	616.1
117.5°	180.1	183.7	187.6	194.8	209.7	229.2	258.6	301.2	368.9	465.8	582.8
120°	193.9	196.2	200.1	208.0	222.8	242.4	270.5	311.2	371.4	458.9	565.3
122.5°	205.8	208.1	212.0	220.5	234.7	255.5	283.0	320.5	375.7	454.6	550.9
125°	222.8	224.4	229.1	237.7	252.5	273.6	301.0	335.4	382.3	448.8	532.4
127.5°	235.8	238.1	243.9	252.7	269.1	290.2	316.6	347.6	389.8	446.0	516.2
130°	243.9	246.3	253.3	262.7	279.1	300.2	326.0	355.7	394.8	444.1	507.4
132.5°	250.2	253.2	260.8	272.1	288.5	309.0	334.1	363.2	398.6	443.4	499.3
135°	261.1	264.3	272.9	284.6	301.0	322.1	346.3	372.9	404.2	442.5	488.6
137.5°	271.4	274.7	283.2	295.7	311.9	331.5	354.8	380.1	408.0	440.8	479.4
140°	278.3	282.2	290.1	302.6	318.2	337.7	360.4	383.9	410.5	440.2	473.8
142.5°	285.8	289.1	297.6	308.8	324.5	342.7	364.8	387.6	412.3	438.9	468.8
145°	297.9	300.2	307.3	319.0	332.3	350.3	370.6	391.7	413.6	437.0	462.1
147.5°	310.1	311.5	318.4	328.5	341.3	356.7	375.3	394.2	413.6	434.1	455.5
150°	318.2	319.0	325.2	335.4	346.3	360.4	378.4	394.8	413.6	431.6	451.1
152.5°	326.3	326.5	332.7	341.7	351.3	364.8	380.3	396.1	411.7	428.4	446.1
155°	338.5	338.5	343.2	351.0	359.6	370.6	383.9	396.4	409.7	423.0	438.6
157.5°	348.2	348.8	352.6	359.5	366.8	375.3	385.9	397.2	407.0	418.1	430.2
160°	355.7	355.7	358.9	365.1	370.6	378.4	387.8	397.2	405.8	414.4	424.5
162.5°	361.4	361.4	363.9	368.9	373.7	380.3	388.4	396.5	403.3	410.6	418.9
165°	369.8	369.0	370.6	374.5	377.6	383.1	389.3	394.8	399.5	405.0	411.2
167.5°	376.2	375.3	376.1	379.0	381.2	384.7	389.2	393.6	395.8	399.4	403.9
170°	380.0	378.4	379.2	381.5	383.1	384.7	388.6	391.7	393.3	395.6	399.5
172.5°	382.5	381.5	381.7	383.4	384.3	385.3	388.6	391.1	391.4	392.5	395.1
175°	385.4	384.7	383.9	385.4	385.4	386.2	387.8	389.3	388.6	388.6	390.1
177.5°	386.8	386.2	385.6	386.2	386.2	386.2	386.8	388.1	386.8	386.2	386.8
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332317

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1285.9	1288.0	1290.0	1290.9	1290.5	1290.1	1289.7	1289.4
5°	1277.4	1279.5	1281.6	1282.4	1282.0	1281.5	1281.0	1280.6
7.5°	1259.5	1260.6	1261.8	1262.0	1261.2	1260.4	1259.6	1258.8
10°	1243.4	1243.6	1243.8	1243.4	1242.2	1241.0	1239.9	1238.7
12.5°	1223.3	1223.2	1223.1	1222.3	1221.0	1219.6	1218.3	1216.9
15°	1188.2	1187.0	1185.9	1184.5	1182.9	1181.2	1179.6	1178.0
17.5°	1146.2	1143.8	1141.3	1138.9	1136.4	1134.0	1131.6	1129.2
20°	1117.5	1114.4	1111.4	1108.5	1105.7	1102.9	1100.1	1097.3
22.5°	1086.7	1082.9	1079.1	1075.9	1073.3	1070.7	1068.1	1065.5
25°	1036.3	1031.4	1026.5	1022.8	1020.2	1017.6	1015.1	1012.5
27.5°	981.3	974.6	967.8	962.4	958.5	954.6	950.7	946.8
30°	942.3	934.3	926.4	920.6	916.9	913.2	909.4	905.7
32.5°	903.9	895.3	886.6	880.3	876.4	872.5	868.6	864.7
35°	847.0	837.0	827.0	819.9	815.7	811.5	807.3	803.1
37.5°	785.8	774.5	763.1	754.9	749.7	744.5	739.4	734.2
40°	743.3	731.2	719.1	710.4	705.0	699.7	694.3	689.0
42.5°	702.5	689.3	676.1	667.1	662.3	657.5	652.7	647.9
45°	642.6	629.3	616.0	606.6	601.0	595.4	589.9	584.3
47.5°	580.5	566.1	551.7	542.0	537.0	532.0	527.1	522.1
50°	538.7	524.2	509.8	499.9	494.6	489.2	483.9	478.5
52.5°	498.2	483.2	468.2	458.3	453.5	448.7	443.9	439.1
55°	437.9	424.4	410.9	401.8	397.2	392.5	387.9	383.2
57.5°	378.7	365.9	353.2	344.8	340.9	336.9	332.9	329.0
60°	341.3	328.8	316.2	308.0	304.0	300.0	296.1	292.1
62.5°	304.3	292.5	280.7	272.7	268.5	264.4	260.3	256.1
65°	251.5	240.1	228.7	221.7	219.2	216.6	214.1	211.5
67.5°	201.2	192.7	184.1	178.5	175.8	173.0	170.3	167.5
70°	170.1	161.9	153.8	148.5	145.9	143.3	140.8	138.2
72.5°	142.1	135.4	128.8	124.9	123.8	122.8	121.7	120.6
75°	106.3	104.0	101.7	100.3	99.8	99.4	98.9	98.4
77.5°	80.2	78.9	77.7	76.8	76.4	75.9	75.4	75.0
80°	64.6	63.9	63.2	62.6	62.1	61.7	61.2	60.7
82.5°	49.5	48.8	48.1	47.7	47.6	47.5	47.4	47.3
85°	28.4	27.9	27.5	27.2	27.2	27.2	27.2	27.2
87.5°	14.4	14.4	14.4	14.5	14.2	14.1	14.1	13.7
90°	19.5	20.3	21.1	22.7	21.9	22.7	23.5	22.7
92.5°	65.8	52.2	46.1	42.1	40.7	38.3	39.1	37.7
95°	281.5	190.8	149.3	121.2	106.3	99.3	93.8	90.7
97.5°	701.6	562.0	461.1	367.6	309.9	274.7	253.6	246.9
100°	921.8	858.4	767.0	655.9	577.0	519.9	489.4	490.2
102.5°	994.9	992.9	939.6	869.2	807.8	762.6	737.1	719.1
105°	1016.4	1094.5	1109.4	1089.1	1053.1	1023.4	998.4	994.5
107.5°	954.8	1081.7	1150.2	1178.0	1178.7	1168.7	1160.2	1153.0
110°	896.0	1039.8	1138.3	1193.1	1214.9	1221.2	1219.6	1218.1



TEST NUMBER: P332317

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	837.8	984.8	1095.2	1165.5	1205.6	1225.0	1230.9	1231.2
115°	760.7	896.7	1011.7	1096.9	1155.5	1189.9	1205.6	1209.5
117.5°	704.9	822.3	925.5	1012.0	1073.1	1112.5	1135.0	1140.4
120°	675.5	781.0	874.9	953.8	1015.6	1059.4	1078.1	1082.8
122.5°	652.4	747.9	834.8	908.2	963.0	1002.4	1023.1	1029.0
125°	621.5	706.8	781.8	844.4	894.4	928.8	948.3	953.8
127.5°	594.7	670.6	738.4	795.3	839.8	869.2	886.9	891.9
130°	577.8	648.1	711.5	764.6	806.1	834.2	850.6	856.9
132.5°	562.1	626.9	685.8	736.5	775.4	803.6	818.1	822.5
135°	541.0	596.5	647.3	691.9	730.2	753.7	767.7	773.2
137.5°	521.8	567.3	611.1	649.7	681.9	705.7	717.6	721.2
140°	510.5	550.4	587.9	621.5	651.3	673.1	685.7	684.9
142.5°	499.9	534.1	566.7	595.9	621.2	640.6	651.9	651.1
145°	487.1	512.9	537.9	560.6	580.1	596.5	602.8	604.3
147.5°	476.6	497.1	517.3	533.4	548.2	559.3	565.3	565.9
150°	469.1	487.1	503.5	518.3	530.1	538.7	543.4	543.4
152.5°	462.2	477.7	492.2	504.6	513.8	521.8	524.6	524.6
155°	451.9	464.4	476.1	485.5	492.5	498.8	500.4	501.1
157.5°	440.9	451.4	460.5	467.8	473.9	478.6	479.9	479.7
160°	434.7	443.3	451.1	456.6	462.1	466.7	466.7	466.0
162.5°	427.2	434.5	441.7	446.6	450.2	454.2	454.2	453.5
165°	417.5	422.2	427.7	431.6	434.7	437.8	437.0	437.0
167.5°	409.0	412.6	415.8	418.6	420.0	422.2	421.4	421.4
170°	403.4	405.8	408.9	410.5	411.2	412.8	412.0	412.0
172.5°	398.4	400.1	402.6	403.6	403.7	405.3	403.9	403.3
175°	391.7	392.5	394.0	394.0	394.0	394.8	394.0	393.3
177.5°	387.5	388.1	388.7	388.7	388.1	388.7	387.5	387.5
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2

(END OF REPORT)