

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331921-935

Luminaire Tested: **S123DIP-S560D585U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331921-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D585U935-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3881.3 lumens
Efficiency: N/A
Efficacy: 118.3 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331921-935

CATALOG NUMBER: S123DIP-S560D585U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331921-935

CATALOG NUMBER: S123DIP-S560D585U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	87	91	88	84	81	75	73	70	63	62	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	38
3	82	73	66	60	76	68	62	57	58	54	50	50	46	43	41	39	37	33
4	75	65	57	51	70	60	53	48	52	47	43	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	30	28	25
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	30	27	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	37	30	25	32	26	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	29	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7326	7326	7326	7326
5°	8737	7358	6521	7358
10°	10935	7321	5889	7321
15°	13412	7261	5483	7261
20°	15978	7170	5220	7170
25°	16966	7058	5162	7058
30°	14542	6976	5189	6976
35°	10113	6859	5243	6859
40°	7617	6724	5227	6724
45°	6325	6520	5160	6520
50°	5667	6107	5114	6107
55°	5296	5662	5050	5662
60°	4969	5197	4997	5197
65°	4669	4737	4837	4737
70°	4378	4214	4607	4214
75°	3922	3689	4225	3689
80°	3434	3025	3639	3025
85°	2692	2198	2445	2198



TEST NUMBER: P331921-935

CATALOG NUMBER: S123DIP-S560D585U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.0	1.7
10°-20°	215.0	5.5
20°-30°	360.8	9.3
30°-40°	408.6	10.5
40°-50°	366.4	9.4
50°-60°	295.7	7.6
60°-70°	206.0	5.3
70°-80°	108.3	2.8
80°-90°	28.4	0.7
90°-100°	135.0	3.5
100°-110°	382.3	9.8
110°-120°	376.1	9.7
120°-130°	300.0	7.7
130°-140°	236.5	6.1
140°-150°	176.5	4.5
150°-160°	123.0	3.2
160°-170°	72.3	1.9
170°-180°	23.5	0.6
0°-30°	642.9	16.6
0°-40°	1051.4	27.1
0°-60°	1713.5	44.1
0°-90°	2056.1	53.0
90°-120°	893.4	23.0
90°-150°	1606.4	41.4
90°-180°	1825.0	47.0
0°-180°	3881.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	681	681	681	681	681	
5°	809	681	604	681	809	84
15°	1204	652	492	652	1204	348
25°	1428	594	435	594	1428	626
35°	770	522	399	522	770	500
45°	416	428	339	428	416	329
55°	282	302	269	302	282	253
65°	183	186	190	186	183	183
75°	94	89	102	89	94	101
85°	22	18	20	18	22	26
90°	14	1	14	1	14	9
95°	57	17	57	17	57	103
105°	625	57	625	57	625	616
115°	760	101	760	101	760	738
125°	599	140	599	140	599	543
135°	486	164	486	164	486	377
145°	380	187	380	187	380	241
155°	315	213	315	213	315	147
165°	274	232	274	232	274	78
175°	247	242	247	242	247	24
180°	243	243	243	243	243	



TEST NUMBER: P331921-935

CATALOG NUMBER: S123DIP-S560D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	722.3	721.8	720.5	721.5	719.4	716.5	716.3	713.6	705.9	705.4	703.4
5°	808.6	805.9	805.6	805.3	800.6	794.4	782.5	781.5	765.7	757.8	748.2
7.5°	920.3	921.7	916.9	912.7	898.5	889.2	876.5	860.2	840.8	821.0	807.9
10°	1000.5	1011.3	997.8	988.6	980.1	963.9	945.1	921.7	898.3	870.9	850.2
12.5°	1086.5	1091.8	1089.2	1080.4	1067.1	1042.5	1009.2	983.4	961.8	916.3	897.9
15°	1203.6	1223.7	1210.9	1181.2	1181.9	1158.5	1114.9	1067.1	1041.7	1001.8	947.4
17.5°	1328.4	1330.9	1325.4	1300.7	1284.2	1252.1	1211.9	1166.1	1114.6	1066.3	1008.6
20°	1394.9	1392.9	1381.4	1368.5	1340.1	1315.1	1271.2	1220.1	1154.2	1106.6	1043.7
22.5°	1431.8	1428.5	1423.1	1412.3	1388.7	1361.8	1322.4	1266.5	1203.8	1138.3	1065.6
25°	1428.5	1432.8	1433.5	1430.5	1422.3	1406.1	1375.1	1330.6	1267.9	1183.9	1108.0
27.5°	1299.2	1305.3	1322.9	1338.6	1356.1	1373.8	1371.5	1349.4	1303.0	1230.4	1137.6
30°	1170.0	1156.8	1189.5	1230.6	1258.7	1308.1	1335.8	1337.5	1311.5	1249.1	1158.7
32.5°	990.6	1005.1	1019.5	1070.2	1131.5	1187.1	1242.2	1286.6	1291.7	1250.2	1171.1
35°	769.6	787.8	814.2	840.6	906.5	963.2	1060.1	1144.6	1211.9	1220.7	1172.3
37.5°	620.2	629.2	645.8	672.3	715.4	782.7	857.7	964.4	1061.9	1134.4	1137.6
40°	542.1	544.8	563.5	583.7	618.6	674.0	741.7	835.9	952.7	1054.0	1096.1
42.5°	483.5	489.4	497.3	516.7	544.5	586.2	649.0	727.0	834.0	950.5	1033.0
45°	415.5	422.1	427.1	439.9	459.7	487.7	531.6	602.8	684.2	804.6	915.8
47.5°	370.5	371.0	374.7	384.4	397.9	419.0	450.0	495.7	570.5	668.0	782.2
50°	338.4	343.6	344.9	352.5	363.1	378.6	404.3	443.2	504.5	590.3	695.2
52.5°	315.6	317.2	320.9	326.4	335.6	347.7	370.0	400.5	448.6	521.7	618.1
55°	282.2	282.2	285.9	290.2	295.5	306.3	321.2	343.6	380.2	437.0	516.8
57.5°	251.4	253.0	255.6	256.9	261.4	268.6	281.0	298.1	325.4	369.0	432.5
60°	230.8	233.8	233.5	236.1	240.0	245.6	256.2	270.1	294.5	329.4	382.9
62.5°	212.9	212.7	212.7	215.8	219.7	225.1	232.0	243.9	264.7	295.7	341.1
65°	183.3	182.7	185.0	187.0	188.3	192.3	197.5	208.1	222.0	245.0	280.3
67.5°	157.1	155.2	156.4	157.1	159.4	162.5	167.4	173.9	184.9	203.5	230.1
70°	139.1	137.5	137.2	137.8	139.8	142.2	145.8	152.1	162.2	177.1	196.6
72.5°	120.7	119.6	119.5	121.0	121.9	123.4	126.0	131.7	139.8	150.9	169.1
75°	94.3	94.3	94.3	94.6	95.7	96.9	98.9	101.9	108.1	116.1	128.3
77.5°	70.7	70.6	70.3	70.2	71.6	72.2	72.7	75.4	79.0	84.3	93.2
80°	55.4	53.7	54.4	55.4	56.1	56.4	57.3	58.0	61.0	64.0	70.3
82.5°	41.2	39.8	39.9	41.4	41.6	41.8	42.9	43.8	44.9	47.6	51.0
85°	21.8	21.8	22.1	22.1	22.4	22.1	23.1	23.4	23.4	25.1	27.0
87.5°	10.8	10.3	10.5	10.7	10.5	10.6	10.8	10.9	11.0	11.5	11.4
90°	14.2	14.7	14.2	13.8	14.2	13.3	12.7	12.3	11.8	12.3	10.8
92.5°	23.7	24.5	24.0	25.6	26.4	29.0	32.8	41.3	57.0	75.5	83.1
95°	57.0	58.9	62.3	66.8	76.1	93.8	119.9	176.8	236.2	291.2	259.3
97.5°	155.1	159.3	172.5	194.7	230.9	289.6	353.0	440.7	482.8	451.3	330.4
100°	307.9	307.5	326.6	362.4	412.0	481.7	539.2	579.0	561.8	465.0	314.3
102.5°	451.7	463.0	479.0	507.4	546.0	590.2	623.7	625.0	565.8	439.5	290.8
105°	624.7	627.2	642.8	661.5	684.1	696.9	687.5	638.4	535.8	394.9	261.7
107.5°	724.3	728.8	734.1	740.4	739.9	722.5	679.5	599.7	483.4	355.3	243.3
110°	765.1	766.1	767.1	763.2	749.4	715.1	653.2	562.7	450.3	332.9	236.2



TEST NUMBER: P331921-935

CATALOG NUMBER: S123DIP-S560D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	773.4	773.2	769.5	757.2	732.1	687.9	618.5	526.2	421.6	318.1	232.3
115°	759.7	757.2	747.4	725.8	689.0	635.5	563.3	477.9	387.0	302.0	230.8
117.5°	716.3	713.0	698.8	674.1	635.7	581.3	516.5	442.7	366.1	292.6	231.7
120°	680.2	677.2	665.5	637.9	599.2	549.5	490.6	424.3	355.1	288.3	233.2
122.5°	646.4	642.7	629.6	604.9	570.4	524.3	469.8	409.7	346.0	285.5	236.0
125°	599.2	595.7	583.4	561.8	530.4	491.1	443.9	390.4	334.4	281.9	240.1
127.5°	560.3	557.1	546.0	527.5	499.6	463.8	421.3	373.5	324.3	280.1	244.9
130°	538.2	534.3	524.0	506.4	480.3	446.9	407.1	362.9	318.7	279.0	248.0
132.5°	516.6	513.8	504.7	487.1	462.6	430.8	393.7	353.1	313.6	278.5	250.4
135°	485.7	482.2	473.4	458.7	434.6	406.7	374.7	339.8	306.9	277.9	253.9
137.5°	453.0	450.7	443.2	428.3	408.1	383.8	356.4	327.8	301.2	276.9	256.2
140°	430.2	430.7	422.8	409.1	390.4	369.3	345.7	320.7	297.6	276.5	257.8
142.5°	409.0	409.5	402.4	390.2	374.3	355.9	335.5	314.0	294.5	275.7	259.0
145°	379.6	378.7	374.7	364.4	352.1	337.9	322.2	305.9	290.2	274.5	259.8
147.5°	355.4	355.1	351.3	344.3	335.0	324.9	312.2	299.4	286.1	272.7	259.8
150°	341.3	341.3	338.4	332.9	325.6	316.2	305.9	294.6	283.4	271.0	259.8
152.5°	329.5	329.5	327.8	322.7	316.9	309.2	300.1	290.3	280.3	269.1	258.6
155°	314.8	314.3	313.3	309.4	305.0	299.1	291.7	283.9	275.5	265.7	257.4
157.5°	301.4	301.4	300.7	297.7	293.9	289.3	283.5	277.0	270.2	262.6	255.6
160°	292.7	293.2	293.2	290.2	286.8	283.4	278.4	273.0	266.7	260.3	254.9
162.5°	284.8	285.3	285.3	282.8	280.5	277.5	272.9	268.4	263.1	258.0	253.3
165°	274.5	274.5	275.0	273.0	271.0	268.6	265.2	262.3	258.3	254.4	251.0
167.5°	264.7	264.7	265.2	263.8	262.9	261.1	259.2	256.9	253.7	250.8	248.6
170°	258.8	258.8	259.3	258.3	257.8	256.8	254.9	253.4	251.0	248.5	247.0
172.5°	253.3	253.7	254.6	253.6	253.5	252.9	251.3	250.3	248.2	246.5	245.8
175°	247.0	247.5	248.0	247.5	247.5	247.5	246.5	246.1	245.0	244.1	244.1
177.5°	243.4	243.4	244.2	243.7	244.2	244.2	243.7	243.4	243.0	242.6	243.0
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P331921-935

CATALOG NUMBER: S123DIP-S560D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	701.7	699.6	697.5	693.8	690.6	686.1	684.8	683.3	678.6	674.2	671.1
5°	744.6	736.7	725.1	714.5	706.0	694.5	687.9	681.0	671.1	662.2	654.9
7.5°	789.5	773.9	756.0	736.6	718.5	701.0	687.0	674.5	660.6	647.5	637.3
10°	825.1	802.6	777.6	750.5	727.5	705.0	686.2	669.8	651.9	636.5	623.5
12.5°	865.6	832.4	797.9	765.0	737.7	706.6	683.9	662.9	642.7	624.1	609.6
15°	913.8	871.6	830.7	785.5	743.9	705.0	678.0	651.6	628.2	609.1	590.6
17.5°	957.5	909.7	855.8	800.9	750.8	704.6	666.8	637.0	607.7	584.3	565.8
20°	982.3	927.9	866.9	809.9	754.5	703.0	661.5	625.9	594.3	569.5	548.7
22.5°	1003.8	940.0	876.9	816.0	754.2	698.8	651.8	615.1	580.7	556.6	534.5
25°	1025.9	949.7	886.4	814.9	745.9	688.5	635.8	594.3	559.9	531.6	508.9
27.5°	1044.9	949.1	873.9	796.9	732.9	675.4	619.1	574.5	538.0	507.2	484.1
30°	1057.6	950.4	861.0	784.8	720.2	660.8	606.1	561.3	523.0	491.6	469.9
32.5°	1065.5	949.6	849.1	767.9	700.2	647.6	592.1	545.7	506.4	475.6	454.6
35°	1070.1	943.7	828.7	733.1	667.8	616.6	570.2	522.0	480.8	452.1	428.3
37.5°	1060.8	931.6	804.9	699.4	627.9	577.6	538.5	497.5	458.1	426.5	406.0
40°	1046.3	923.7	786.4	675.7	600.5	552.0	518.8	478.5	439.5	409.6	390.5
42.5°	1018.6	907.6	766.2	649.3	572.0	523.5	492.8	459.3	422.4	394.3	375.1
45°	951.1	872.5	735.7	609.8	529.9	479.8	452.8	428.3	395.0	367.6	351.2
47.5°	857.2	819.8	691.6	568.0	486.0	437.8	409.7	390.0	365.7	343.6	327.8
50°	792.1	776.6	661.9	539.5	456.7	409.6	382.5	364.7	347.2	325.1	310.6
52.5°	716.9	726.4	627.0	510.0	426.9	380.6	355.1	341.0	325.1	306.9	294.3
55°	611.1	645.7	566.9	460.4	382.5	338.4	314.3	301.7	292.5	279.0	268.1
57.5°	512.0	555.9	501.8	409.2	338.9	300.8	277.8	264.1	258.1	251.1	242.5
60°	453.1	496.6	455.4	375.0	309.6	273.4	253.0	241.4	235.5	230.5	223.3
62.5°	400.6	444.6	410.0	340.1	280.9	247.3	229.5	218.2	213.5	210.9	204.7
65°	328.5	366.4	343.3	285.9	239.7	210.1	193.9	186.0	181.7	180.7	176.8
67.5°	267.3	296.2	279.4	237.1	200.8	175.1	161.4	154.7	151.4	151.1	148.1
70°	227.2	254.3	241.4	203.1	171.8	151.7	139.8	133.9	131.9	131.6	129.9
72.5°	196.0	214.9	204.7	172.8	148.6	130.4	121.6	115.4	113.1	113.7	112.5
75°	145.1	159.3	153.3	131.2	111.8	99.9	92.6	88.7	86.7	87.7	86.4
77.5°	104.4	113.4	108.1	92.7	80.8	72.2	66.8	64.4	62.6	62.5	61.9
80°	78.8	84.1	81.1	71.9	62.0	54.8	50.5	48.8	47.8	47.5	47.2
82.5°	56.1	60.6	57.1	50.8	44.1	39.7	37.3	35.1	34.4	34.5	34.3
85°	28.3	30.0	28.7	24.7	22.1	20.1	18.8	17.8	17.1	17.5	16.8
87.5°	11.6	11.6	10.5	9.3	8.5	7.5	7.2	6.5	6.2	6.4	6.5
90°	9.3	7.8	6.4	5.4	4.4	2.9	2.0	0.9	2.0	2.9	4.4
92.5°	62.3	41.2	28.4	21.1	17.0	13.2	9.0	6.1	9.0	13.2	17.0
95°	178.7	105.6	63.8	44.7	31.9	23.6	18.2	16.7	18.2	23.6	31.9
97.5°	196.1	113.7	73.8	53.0	40.5	33.2	29.0	28.5	29.0	33.2	40.5
100°	185.1	112.4	78.1	58.9	47.2	40.3	36.9	36.3	36.9	40.3	47.2
102.5°	175.7	114.0	83.2	65.6	55.0	48.6	45.5	44.6	45.5	48.6	55.0
105°	168.9	118.4	91.9	76.6	67.2	61.4	58.5	57.0	58.5	61.4	67.2
107.5°	168.4	126.4	103.1	89.0	80.2	74.5	71.6	70.1	71.6	74.5	80.2
110°	170.4	133.1	111.0	97.2	88.9	83.5	81.0	79.6	81.0	83.5	88.9



TEST NUMBER: P331921-935

CATALOG NUMBER: S123DIP-S560D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	174.4	139.7	119.2	105.9	97.6	92.1	89.7	88.2	89.7	92.1	97.6
115°	180.7	150.8	132.1	118.8	110.5	105.6	102.6	100.7	102.6	105.6	110.5
117.5°	189.2	162.5	144.0	131.7	122.3	117.9	115.4	113.1	115.4	117.9	122.3
120°	195.4	169.9	152.2	140.0	130.6	125.7	123.3	121.8	123.3	125.7	130.6
122.5°	201.4	177.8	160.5	147.4	138.4	133.2	130.7	129.2	130.7	133.2	138.4
125°	210.7	189.1	171.9	158.6	149.3	143.9	140.9	140.0	140.9	143.9	149.3
127.5°	218.3	198.9	182.3	169.0	158.7	153.3	149.6	148.1	149.6	153.3	158.7
130°	223.4	204.7	188.6	175.3	165.0	159.1	154.7	153.3	154.7	159.1	165.0
132.5°	228.2	209.9	194.1	181.2	170.9	163.8	159.0	157.1	159.0	163.8	170.9
135°	234.3	217.6	202.3	189.1	178.7	171.4	166.0	164.0	166.0	171.4	178.7
137.5°	238.8	222.8	208.2	196.0	185.7	177.9	172.5	170.5	172.5	177.9	185.7
140°	241.2	226.4	212.2	199.8	190.0	182.2	177.3	174.9	177.3	182.2	190.0
142.5°	243.5	229.1	215.3	203.8	194.0	186.9	181.6	179.5	181.6	186.9	194.0
145°	246.1	232.8	220.0	208.7	200.4	193.0	188.6	187.1	188.6	193.0	200.4
147.5°	247.6	235.7	224.0	214.4	206.4	200.0	195.6	194.8	195.6	200.0	206.4
150°	248.0	237.7	226.4	217.6	210.7	204.3	200.4	199.8	200.4	204.3	210.7
152.5°	248.8	238.8	229.1	220.7	214.6	209.1	205.1	205.0	205.1	209.1	214.6
155°	249.0	241.2	232.8	225.9	220.5	215.6	212.7	212.7	212.7	215.6	220.5
157.5°	249.5	242.4	235.7	230.4	225.8	221.4	219.1	218.7	219.1	221.4	225.8
160°	249.5	243.6	237.7	232.8	229.4	225.4	223.4	223.4	223.4	225.4	229.4
162.5°	249.1	244.0	238.8	234.7	231.7	228.6	227.0	227.0	227.0	228.6	231.7
165°	248.0	244.5	240.6	237.2	235.2	232.8	231.8	232.3	231.8	232.8	235.2
167.5°	247.2	244.4	241.6	239.4	238.1	236.2	235.7	236.3	235.7	236.2	238.1
170°	246.1	244.1	241.6	240.6	239.6	238.2	237.7	238.7	237.7	238.2	239.6
172.5°	245.6	244.1	242.0	241.4	240.8	239.8	239.6	240.2	239.6	239.8	240.8
175°	244.5	243.6	242.6	242.1	242.1	241.2	241.6	242.1	241.6	241.2	242.1
177.5°	243.7	243.0	242.6	242.6	242.6	242.2	242.6	243.0	242.6	242.2	242.6
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P331921-935

CATALOG NUMBER: S123DIP-S560D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	669.3	667.4	664.8	660.8	657.6	652.6	652.6	653.4	653.4	653.2	652.6
5°	648.9	644.0	638.1	631.2	623.9	616.6	615.4	612.7	610.7	609.4	607.8
7.5°	627.5	618.8	610.1	600.5	591.6	584.3	579.2	575.0	572.2	569.4	567.2
10°	613.0	602.1	591.9	581.7	570.5	561.5	555.9	552.0	549.1	546.4	545.1
12.5°	595.9	583.4	572.1	562.4	550.2	541.0	535.6	533.8	530.3	524.8	521.9
15°	570.8	559.3	545.8	530.9	525.0	513.8	507.5	504.5	502.6	498.3	497.0
17.5°	549.4	534.3	519.1	508.0	497.0	487.9	484.4	480.7	478.1	474.6	473.6
20°	532.3	518.8	504.9	493.0	481.5	471.6	468.6	466.0	463.3	461.7	460.4
22.5°	514.8	501.3	489.8	478.7	466.4	459.9	456.7	453.8	451.9	450.8	449.5
25°	490.3	478.5	465.6	455.7	445.8	441.5	439.5	437.9	436.6	435.0	434.6
27.5°	468.5	455.6	445.1	435.8	428.8	425.2	423.3	422.5	422.8	423.4	423.7
30°	452.1	440.2	431.6	423.7	417.2	413.9	413.5	413.5	414.8	415.2	415.9
32.5°	437.0	427.3	418.7	411.0	406.0	403.8	405.1	405.1	406.1	407.0	408.2
35°	415.2	406.6	400.0	393.4	389.1	390.1	390.7	391.4	393.0	395.0	396.4
37.5°	394.3	386.8	380.0	374.8	372.8	374.6	376.2	377.5	379.5	381.0	382.3
40°	379.2	373.6	367.0	362.4	363.1	364.0	365.4	367.0	368.7	369.6	371.0
42.5°	365.2	359.4	354.4	350.5	351.5	352.8	353.5	354.4	356.3	358.1	358.9
45°	344.0	339.3	334.7	332.4	333.0	333.7	334.4	335.4	337.0	338.4	338.6
47.5°	320.0	316.8	313.7	311.4	312.5	312.2	313.1	315.2	315.7	316.5	318.3
50°	304.7	301.7	298.1	297.5	297.5	297.5	297.7	300.4	300.4	301.7	303.1
52.5°	287.8	285.9	283.6	282.4	281.9	281.9	283.3	284.6	285.1	287.0	288.3
55°	262.8	260.8	258.9	257.9	257.2	257.9	260.5	261.1	262.8	263.8	264.8
57.5°	236.8	235.2	233.7	233.2	233.0	233.8	235.3	237.3	237.7	240.7	242.2
60°	219.6	217.3	216.0	216.0	215.3	218.3	217.7	220.9	221.6	223.6	225.9
62.5°	201.9	198.8	198.3	198.3	199.2	200.1	201.0	202.5	204.2	206.7	208.4
65°	173.5	171.8	174.1	173.7	173.1	175.1	175.1	176.8	178.7	181.1	184.7
67.5°	146.5	145.6	145.9	145.9	146.8	147.9	148.9	150.3	152.7	155.2	157.5
70°	128.3	129.2	127.6	129.0	129.9	130.3	130.9	132.9	135.5	137.2	139.8
72.5°	110.6	110.6	110.7	111.2	112.3	112.9	113.5	115.7	118.6	120.0	122.2
75°	85.1	84.7	85.8	85.8	87.4	88.1	88.7	89.7	92.3	94.3	96.0
77.5°	62.2	62.5	62.3	63.5	63.0	63.1	65.2	66.1	66.4	70.3	71.2
80°	46.8	47.5	47.8	48.1	48.5	47.8	50.1	51.1	51.1	53.4	55.1
82.5°	33.7	34.0	34.9	35.2	35.3	35.9	36.2	36.9	37.6	38.7	40.8
85°	16.8	17.8	18.2	17.8	18.2	17.5	18.4	18.8	19.1	19.1	19.1
87.5°	6.4	6.8	6.9	7.4	7.4	8.0	7.9	7.5	7.6	8.4	7.6
90°	5.4	6.4	7.8	9.3	10.8	12.3	11.8	12.3	12.7	13.3	14.2
92.5°	21.1	28.4	41.2	62.3	83.1	75.5	57.0	41.3	32.8	29.0	26.4
95°	44.7	63.8	105.6	178.7	259.3	291.2	236.2	176.8	119.9	93.8	76.1
97.5°	53.0	73.8	113.7	196.1	330.4	451.3	482.8	440.7	353.0	289.6	230.9
100°	58.9	78.1	112.4	185.1	314.3	465.0	561.8	579.0	539.2	481.7	412.0
102.5°	65.6	83.2	114.0	175.7	290.8	439.5	565.8	625.0	623.7	590.2	546.0
105°	76.6	91.9	118.4	168.9	261.7	394.9	535.8	638.4	687.5	696.9	684.1
107.5°	89.0	103.1	126.4	168.4	243.3	355.3	483.4	599.7	679.5	722.5	739.9
110°	97.2	111.0	133.1	170.4	236.2	332.9	450.3	562.7	653.2	715.1	749.4



TEST NUMBER: P331921-935

CATALOG NUMBER: S123DIP-S560D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	105.9	119.2	139.7	174.4	232.3	318.1	421.6	526.2	618.5	687.9	732.1
115°	118.8	132.1	150.8	180.7	230.8	302.0	387.0	477.9	563.3	635.5	689.0
117.5°	131.7	144.0	162.5	189.2	231.7	292.6	366.1	442.7	516.5	581.3	635.7
120°	140.0	152.2	169.9	195.4	233.2	288.3	355.1	424.3	490.6	549.5	599.2
122.5°	147.4	160.5	177.8	201.4	236.0	285.5	346.0	409.7	469.8	524.3	570.4
125°	158.6	171.9	189.1	210.7	240.1	281.9	334.4	390.4	443.9	491.1	530.4
127.5°	169.0	182.3	198.9	218.3	244.9	280.1	324.3	373.5	421.3	463.8	499.6
130°	175.3	188.6	204.7	223.4	248.0	279.0	318.7	362.9	407.1	446.9	480.3
132.5°	181.2	194.1	209.9	228.2	250.4	278.5	313.6	353.1	393.7	430.8	462.6
135°	189.1	202.3	217.6	234.3	253.9	277.9	306.9	339.8	374.7	406.7	434.6
137.5°	196.0	208.2	222.8	238.8	256.2	276.9	301.2	327.8	356.4	383.8	408.1
140°	199.8	212.2	226.4	241.2	257.8	276.5	297.6	320.7	345.7	369.3	390.4
142.5°	203.8	215.3	229.1	243.5	259.0	275.7	294.5	314.0	335.5	355.9	374.3
145°	208.7	220.0	232.8	246.1	259.8	274.5	290.2	305.9	322.2	337.9	352.1
147.5°	214.4	224.0	235.7	247.6	259.8	272.7	286.1	299.4	312.2	324.9	335.0
150°	217.6	226.4	237.7	248.0	259.8	271.0	283.4	294.6	305.9	316.2	325.6
152.5°	220.7	229.1	238.8	248.8	258.6	269.1	280.3	290.3	300.1	309.2	316.9
155°	225.9	232.8	241.2	249.0	257.4	265.7	275.5	283.9	291.7	299.1	305.0
157.5°	230.4	235.7	242.4	249.5	255.6	262.6	270.2	277.0	283.5	289.3	293.9
160°	232.8	237.7	243.6	249.5	254.9	260.3	266.7	273.0	278.4	283.4	286.8
162.5°	234.7	238.8	244.0	249.1	253.3	258.0	263.1	268.4	272.9	277.5	280.5
165°	237.2	240.6	244.5	248.0	251.0	254.4	258.3	262.3	265.2	268.6	271.0
167.5°	239.4	241.6	244.4	247.2	248.6	250.8	253.7	256.9	259.2	261.1	262.9
170°	240.6	241.6	244.1	246.1	247.0	248.5	251.0	253.4	254.9	256.8	257.8
172.5°	241.4	242.0	244.1	245.6	245.8	246.5	248.2	250.3	251.3	252.9	253.5
175°	242.1	242.6	243.6	244.5	244.1	244.1	245.0	246.1	246.5	247.5	247.5
177.5°	242.6	242.6	243.0	243.7	243.0	242.6	243.0	243.4	243.7	244.2	244.2
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P331921-935

CATALOG NUMBER: S123DIP-S560D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	650.8	650.6	652.4	651.1	652.4	650.6	650.8	652.6	653.2	653.4	653.4
5°	605.8	606.7	603.5	603.5	603.5	606.7	605.8	607.8	609.4	610.7	612.7
7.5°	565.7	564.2	564.4	562.6	564.4	564.2	565.7	567.2	569.4	572.2	575.0
10°	541.1	539.2	538.5	538.8	538.5	539.2	541.1	545.1	546.4	549.1	552.0
12.5°	520.8	520.4	516.1	516.2	516.1	520.4	520.8	521.9	524.8	530.3	533.8
15°	497.0	490.7	490.0	492.0	490.0	490.7	497.0	497.0	498.3	502.6	504.5
17.5°	473.0	469.7	469.9	468.9	469.9	469.7	473.0	473.6	474.6	478.1	480.7
20°	460.4	458.4	458.1	455.7	458.1	458.4	460.4	460.4	461.7	463.3	466.0
22.5°	448.8	448.1	448.2	445.7	448.2	448.1	448.8	449.5	450.8	451.9	453.8
25°	434.3	435.9	434.6	434.6	434.6	435.9	434.3	434.6	435.0	436.6	437.9
27.5°	424.6	424.5	423.8	423.8	423.8	424.5	424.6	423.7	423.4	422.8	422.5
30°	417.2	416.8	417.5	417.5	417.5	416.8	417.2	415.9	415.2	414.8	413.5
32.5°	409.7	410.2	410.4	410.6	410.4	410.2	409.7	408.2	407.0	406.1	405.1
35°	398.4	398.6	399.7	399.0	399.7	398.6	398.4	396.4	395.0	393.0	391.4
37.5°	382.9	384.4	384.1	384.6	384.1	384.4	382.9	382.3	381.0	379.5	377.5
40°	371.3	372.3	372.0	372.0	372.0	372.3	371.3	371.0	369.6	368.7	367.0
42.5°	359.5	360.2	359.3	358.8	359.3	360.2	359.5	358.9	358.1	356.3	354.4
45°	340.0	339.3	340.4	339.0	340.4	339.3	340.0	338.6	338.4	337.0	335.4
47.5°	318.2	318.9	319.2	320.1	319.2	318.9	318.2	318.3	316.5	315.7	315.2
50°	303.7	305.7	305.7	305.4	305.7	305.7	303.7	303.1	301.7	300.4	300.4
52.5°	289.5	290.4	291.7	291.6	291.7	290.4	289.5	288.3	287.0	285.1	284.6
55°	267.4	268.1	268.7	269.1	268.7	268.1	267.4	264.8	263.8	262.8	261.1
57.5°	244.6	244.4	245.9	246.4	245.9	244.4	244.6	242.2	240.7	237.7	237.3
60°	228.5	228.5	231.2	232.1	231.2	228.5	228.5	225.9	223.6	221.6	220.9
62.5°	211.4	212.4	215.1	213.7	215.1	212.4	211.4	208.4	206.7	204.2	202.5
65°	186.3	189.0	188.6	189.9	188.6	189.0	186.3	184.7	181.1	178.7	176.8
67.5°	160.1	161.8	164.2	164.4	164.2	161.8	160.1	157.5	155.2	152.7	150.3
70°	142.5	144.1	145.4	146.4	145.4	144.1	142.5	139.8	137.2	135.5	132.9
72.5°	125.3	126.1	129.3	127.9	129.3	126.1	125.3	122.2	120.0	118.6	115.7
75°	98.2	100.6	102.5	101.6	102.5	100.6	98.2	96.0	94.3	92.3	89.7
77.5°	72.7	75.0	75.9	75.1	75.9	75.0	72.7	71.2	70.3	66.4	66.1
80°	57.3	57.1	59.1	58.7	59.1	57.1	57.3	55.1	53.4	51.1	51.1
82.5°	42.1	41.8	42.7	42.9	42.7	41.8	42.1	40.8	38.7	37.6	36.9
85°	20.4	21.4	20.1	19.8	20.1	21.4	20.4	19.1	19.1	19.1	18.8
87.5°	7.5	7.6	7.4	7.1	7.4	7.6	7.5	7.6	8.4	7.6	7.5
90°	13.8	14.2	14.7	14.2	14.7	14.2	13.8	14.2	13.3	12.7	12.3
92.5°	25.6	24.0	24.5	23.7	24.5	24.0	25.6	26.4	29.0	32.8	41.3
95°	66.8	62.3	58.9	57.0	58.9	62.3	66.8	76.1	93.8	119.9	176.8
97.5°	194.7	172.5	159.3	155.1	159.3	172.5	194.7	230.9	289.6	353.0	440.7
100°	362.4	326.6	307.5	307.9	307.5	326.6	362.4	412.0	481.7	539.2	579.0
102.5°	507.4	479.0	463.0	451.7	463.0	479.0	507.4	546.0	590.2	623.7	625.0
105°	661.5	642.8	627.2	624.7	627.2	642.8	661.5	684.1	696.9	687.5	638.4
107.5°	740.4	734.1	728.8	724.3	728.8	734.1	740.4	739.9	722.5	679.5	599.7
110°	763.2	767.1	766.1	765.1	766.1	767.1	763.2	749.4	715.1	653.2	562.7



TEST NUMBER: P331921-935

CATALOG NUMBER: S123DIP-S560D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	757.2	769.5	773.2	773.4	773.2	769.5	757.2	732.1	687.9	618.5	526.2
115°	725.8	747.4	757.2	759.7	757.2	747.4	725.8	689.0	635.5	563.3	477.9
117.5°	674.1	698.8	713.0	716.3	713.0	698.8	674.1	635.7	581.3	516.5	442.7
120°	637.9	665.5	677.2	680.2	677.2	665.5	637.9	599.2	549.5	490.6	424.3
122.5°	604.9	629.6	642.7	646.4	642.7	629.6	604.9	570.4	524.3	469.8	409.7
125°	561.8	583.4	595.7	599.2	595.7	583.4	561.8	530.4	491.1	443.9	390.4
127.5°	527.5	546.0	557.1	560.3	557.1	546.0	527.5	499.6	463.8	421.3	373.5
130°	506.4	524.0	534.3	538.2	534.3	524.0	506.4	480.3	446.9	407.1	362.9
132.5°	487.1	504.7	513.8	516.6	513.8	504.7	487.1	462.6	430.8	393.7	353.1
135°	458.7	473.4	482.2	485.7	482.2	473.4	458.7	434.6	406.7	374.7	339.8
137.5°	428.3	443.2	450.7	453.0	450.7	443.2	428.3	408.1	383.8	356.4	327.8
140°	409.1	422.8	430.7	430.2	430.7	422.8	409.1	390.4	369.3	345.7	320.7
142.5°	390.2	402.4	409.5	409.0	409.5	402.4	390.2	374.3	355.9	335.5	314.0
145°	364.4	374.7	378.7	379.6	378.7	374.7	364.4	352.1	337.9	322.2	305.9
147.5°	344.3	351.3	355.1	355.4	355.1	351.3	344.3	335.0	324.9	312.2	299.4
150°	332.9	338.4	341.3	341.3	341.3	338.4	332.9	325.6	316.2	305.9	294.6
152.5°	322.7	327.8	329.5	329.5	329.5	327.8	322.7	316.9	309.2	300.1	290.3
155°	309.4	313.3	314.3	314.8	314.3	313.3	309.4	305.0	299.1	291.7	283.9
157.5°	297.7	300.7	301.4	301.4	301.4	300.7	297.7	293.9	289.3	283.5	277.0
160°	290.2	293.2	293.2	292.7	293.2	293.2	290.2	286.8	283.4	278.4	273.0
162.5°	282.8	285.3	285.3	284.8	285.3	285.3	282.8	280.5	277.5	272.9	268.4
165°	273.0	275.0	274.5	274.5	274.5	275.0	273.0	271.0	268.6	265.2	262.3
167.5°	263.8	265.2	264.7	264.7	264.7	265.2	263.8	262.9	261.1	259.2	256.9
170°	258.3	259.3	258.8	258.8	258.8	259.3	258.3	257.8	256.8	254.9	253.4
172.5°	253.6	254.6	253.7	253.3	253.7	254.6	253.6	253.5	252.9	251.3	250.3
175°	247.5	248.0	247.5	247.0	247.5	248.0	247.5	247.5	247.5	246.5	246.1
177.5°	243.7	244.2	243.4	243.4	243.4	244.2	243.7	244.2	244.2	243.7	243.4
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P331921-935

CATALOG NUMBER: S123DIP-S560D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	652.6	652.6	657.6	660.8	664.8	667.4	669.3	671.1	674.2	678.6	683.3
5°	615.4	616.6	623.9	631.2	638.1	644.0	648.9	654.9	662.2	671.1	681.0
7.5°	579.2	584.3	591.6	600.5	610.1	618.8	627.5	637.3	647.5	660.6	674.5
10°	555.9	561.5	570.5	581.7	591.9	602.1	613.0	623.5	636.5	651.9	669.8
12.5°	535.6	541.0	550.2	562.4	572.1	583.4	595.9	609.6	624.1	642.7	662.9
15°	507.5	513.8	525.0	530.9	545.8	559.3	570.8	590.6	609.1	628.2	651.6
17.5°	484.4	487.9	497.0	508.0	519.1	534.3	549.4	565.8	584.3	607.7	637.0
20°	468.6	471.6	481.5	493.0	504.9	518.8	532.3	548.7	569.5	594.3	625.9
22.5°	456.7	459.9	466.4	478.7	489.8	501.3	514.8	534.5	556.6	580.7	615.1
25°	439.5	441.5	445.8	455.7	465.6	478.5	490.3	508.9	531.6	559.9	594.3
27.5°	423.3	425.2	428.8	435.8	445.1	455.6	468.5	484.1	507.2	538.0	574.5
30°	413.5	413.9	417.2	423.7	431.6	440.2	452.1	469.9	491.6	523.0	561.3
32.5°	405.1	403.8	406.0	411.0	418.7	427.3	437.0	454.6	475.6	506.4	545.7
35°	390.7	390.1	389.1	393.4	400.0	406.6	415.2	428.3	452.1	480.8	522.0
37.5°	376.2	374.6	372.8	374.8	380.0	386.8	394.3	406.0	426.5	458.1	497.5
40°	365.4	364.0	363.1	362.4	367.0	373.6	379.2	390.5	409.6	439.5	478.5
42.5°	353.5	352.8	351.5	350.5	354.4	359.4	365.2	375.1	394.3	422.4	459.3
45°	334.4	333.7	333.0	332.4	334.7	339.3	344.0	351.2	367.6	395.0	428.3
47.5°	313.1	312.2	312.5	311.4	313.7	316.8	320.0	327.8	343.6	365.7	390.0
50°	297.7	297.5	297.5	297.5	298.1	301.7	304.7	310.6	325.1	347.2	364.7
52.5°	283.3	281.9	281.9	282.4	283.6	285.9	287.8	294.3	306.9	325.1	341.0
55°	260.5	257.9	257.2	257.9	258.9	260.8	262.8	268.1	279.0	292.5	301.7
57.5°	235.3	233.8	233.0	233.2	233.7	235.2	236.8	242.5	251.1	258.1	264.1
60°	217.7	218.3	215.3	216.0	216.0	217.3	219.6	223.3	230.5	235.5	241.4
62.5°	201.0	200.1	199.2	198.3	198.3	198.8	201.9	204.7	210.9	213.5	218.2
65°	175.1	175.1	173.1	173.7	174.1	171.8	173.5	176.8	180.7	181.7	186.0
67.5°	148.9	147.9	146.8	145.9	145.9	145.6	146.5	148.1	151.1	151.4	154.7
70°	130.9	130.3	129.9	129.0	127.6	129.2	128.3	129.9	131.6	131.9	133.9
72.5°	113.5	112.9	112.3	111.2	110.7	110.6	110.6	112.5	113.7	113.1	115.4
75°	88.7	88.1	87.4	85.8	85.8	84.7	85.1	86.4	87.7	86.7	88.7
77.5°	65.2	63.1	63.0	63.5	62.3	62.5	62.2	61.9	62.5	62.6	64.4
80°	50.1	47.8	48.5	48.1	47.8	47.5	46.8	47.2	47.5	47.8	48.8
82.5°	36.2	35.9	35.3	35.2	34.9	34.0	33.7	34.3	34.5	34.4	35.1
85°	18.4	17.5	18.2	17.8	18.2	17.8	16.8	16.8	17.5	17.1	17.8
87.5°	7.9	8.0	7.4	7.4	6.9	6.8	6.4	6.5	6.4	6.2	6.5
90°	11.8	12.3	10.8	9.3	7.8	6.4	5.4	4.4	2.9	2.0	0.9
92.5°	57.0	75.5	83.1	62.3	41.2	28.4	21.1	17.0	13.2	9.0	6.1
95°	236.2	291.2	259.3	178.7	105.6	63.8	44.7	31.9	23.6	18.2	16.7
97.5°	482.8	451.3	330.4	196.1	113.7	73.8	53.0	40.5	33.2	29.0	28.5
100°	561.8	465.0	314.3	185.1	112.4	78.1	58.9	47.2	40.3	36.9	36.3
102.5°	565.8	439.5	290.8	175.7	114.0	83.2	65.6	55.0	48.6	45.5	44.6
105°	535.8	394.9	261.7	168.9	118.4	91.9	76.6	67.2	61.4	58.5	57.0
107.5°	483.4	355.3	243.3	168.4	126.4	103.1	89.0	80.2	74.5	71.6	70.1
110°	450.3	332.9	236.2	170.4	133.1	111.0	97.2	88.9	83.5	81.0	79.6



TEST NUMBER: P331921-935

CATALOG NUMBER: S123DIP-S560D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	421.6	318.1	232.3	174.4	139.7	119.2	105.9	97.6	92.1	89.7	88.2
115°	387.0	302.0	230.8	180.7	150.8	132.1	118.8	110.5	105.6	102.6	100.7
117.5°	366.1	292.6	231.7	189.2	162.5	144.0	131.7	122.3	117.9	115.4	113.1
120°	355.1	288.3	233.2	195.4	169.9	152.2	140.0	130.6	125.7	123.3	121.8
122.5°	346.0	285.5	236.0	201.4	177.8	160.5	147.4	138.4	133.2	130.7	129.2
125°	334.4	281.9	240.1	210.7	189.1	171.9	158.6	149.3	143.9	140.9	140.0
127.5°	324.3	280.1	244.9	218.3	198.9	182.3	169.0	158.7	153.3	149.6	148.1
130°	318.7	279.0	248.0	223.4	204.7	188.6	175.3	165.0	159.1	154.7	153.3
132.5°	313.6	278.5	250.4	228.2	209.9	194.1	181.2	170.9	163.8	159.0	157.1
135°	306.9	277.9	253.9	234.3	217.6	202.3	189.1	178.7	171.4	166.0	164.0
137.5°	301.2	276.9	256.2	238.8	222.8	208.2	196.0	185.7	177.9	172.5	170.5
140°	297.6	276.5	257.8	241.2	226.4	212.2	199.8	190.0	182.2	177.3	174.9
142.5°	294.5	275.7	259.0	243.5	229.1	215.3	203.8	194.0	186.9	181.6	179.5
145°	290.2	274.5	259.8	246.1	232.8	220.0	208.7	200.4	193.0	188.6	187.1
147.5°	286.1	272.7	259.8	247.6	235.7	224.0	214.4	206.4	200.0	195.6	194.8
150°	283.4	271.0	259.8	248.0	237.7	226.4	217.6	210.7	204.3	200.4	199.8
152.5°	280.3	269.1	258.6	248.8	238.8	229.1	220.7	214.6	209.1	205.1	205.0
155°	275.5	265.7	257.4	249.0	241.2	232.8	225.9	220.5	215.6	212.7	212.7
157.5°	270.2	262.6	255.6	249.5	242.4	235.7	230.4	225.8	221.4	219.1	218.7
160°	266.7	260.3	254.9	249.5	243.6	237.7	232.8	229.4	225.4	223.4	223.4
162.5°	263.1	258.0	253.3	249.1	244.0	238.8	234.7	231.7	228.6	227.0	227.0
165°	258.3	254.4	251.0	248.0	244.5	240.6	237.2	235.2	232.8	231.8	232.3
167.5°	253.7	250.8	248.6	247.2	244.4	241.6	239.4	238.1	236.2	235.7	236.3
170°	251.0	248.5	247.0	246.1	244.1	241.6	240.6	239.6	238.2	237.7	238.7
172.5°	248.2	246.5	245.8	245.6	244.1	242.0	241.4	240.8	239.8	239.6	240.2
175°	245.0	244.1	244.1	244.5	243.6	242.6	242.1	242.1	241.2	241.6	242.1
177.5°	243.0	242.6	243.0	243.7	243.0	242.6	242.6	242.6	242.2	242.6	243.0
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P331921-935

CATALOG NUMBER: S123DIP-S560D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	684.8	686.1	690.6	693.8	697.5	699.6	701.7	703.4	705.4	705.9	713.6
5°	687.9	694.5	706.0	714.5	725.1	736.7	744.6	748.2	757.8	765.7	781.5
7.5°	687.0	701.0	718.5	736.6	756.0	773.9	789.5	807.9	821.0	840.8	860.2
10°	686.2	705.0	727.5	750.5	777.6	802.6	825.1	850.2	870.9	898.3	921.7
12.5°	683.9	706.6	737.7	765.0	797.9	832.4	865.6	897.9	916.3	961.8	983.4
15°	678.0	705.0	743.9	785.5	830.7	871.6	913.8	947.4	1001.8	1041.7	1067.1
17.5°	666.8	704.6	750.8	800.9	855.8	909.7	957.5	1008.6	1066.3	1114.6	1166.1
20°	661.5	703.0	754.5	809.9	866.9	927.9	982.3	1043.7	1106.6	1154.2	1220.1
22.5°	651.8	698.8	754.2	816.0	876.9	940.0	1003.8	1065.6	1138.3	1203.8	1266.5
25°	635.8	688.5	745.9	814.9	886.4	949.7	1025.9	1108.0	1183.9	1267.9	1330.6
27.5°	619.1	675.4	732.9	796.9	873.9	949.1	1044.9	1137.6	1230.4	1303.0	1349.4
30°	606.1	660.8	720.2	784.8	861.0	950.4	1057.6	1158.7	1249.1	1311.5	1337.5
32.5°	592.1	647.6	700.2	767.9	849.1	949.6	1065.5	1171.1	1250.2	1291.7	1286.6
35°	570.2	616.6	667.8	733.1	828.7	943.7	1070.1	1172.3	1220.7	1211.9	1144.6
37.5°	538.5	577.6	627.9	699.4	804.9	931.6	1060.8	1137.6	1134.4	1061.9	964.4
40°	518.8	552.0	600.5	675.7	786.4	923.7	1046.3	1096.1	1054.0	952.7	835.9
42.5°	492.8	523.5	572.0	649.3	766.2	907.6	1018.6	1033.0	950.5	834.0	727.0
45°	452.8	479.8	529.9	609.8	735.7	872.5	951.1	915.8	804.6	684.2	602.8
47.5°	409.7	437.8	486.0	568.0	691.6	819.8	857.2	782.2	668.0	570.5	495.7
50°	382.5	409.6	456.7	539.5	661.9	776.6	792.1	695.2	590.3	504.5	443.2
52.5°	355.1	380.6	426.9	510.0	627.0	726.4	716.9	618.1	521.7	448.6	400.5
55°	314.3	338.4	382.5	460.4	566.9	645.7	611.1	516.8	437.0	380.2	343.6
57.5°	277.8	300.8	338.9	409.2	501.8	555.9	512.0	432.5	369.0	325.4	298.1
60°	253.0	273.4	309.6	375.0	455.4	496.6	453.1	382.9	329.4	294.5	270.1
62.5°	229.5	247.3	280.9	340.1	410.0	444.6	400.6	341.1	295.7	264.7	243.9
65°	193.9	210.1	239.7	285.9	343.3	366.4	328.5	280.3	245.0	222.0	208.1
67.5°	161.4	175.1	200.8	237.1	279.4	296.2	267.3	230.1	203.5	184.9	173.9
70°	139.8	151.7	171.8	203.1	241.4	254.3	227.2	196.6	177.1	162.2	152.1
72.5°	121.6	130.4	148.6	172.8	204.7	214.9	196.0	169.1	150.9	139.8	131.7
75°	92.6	99.9	111.8	131.2	153.3	159.3	145.1	128.3	116.1	108.1	101.9
77.5°	66.8	72.2	80.8	92.7	108.1	113.4	104.4	93.2	84.3	79.0	75.4
80°	50.5	54.8	62.0	71.9	81.1	84.1	78.8	70.3	64.0	61.0	58.0
82.5°	37.3	39.7	44.1	50.8	57.1	60.6	56.1	51.0	47.6	44.9	43.8
85°	18.8	20.1	22.1	24.7	28.7	30.0	28.3	27.0	25.1	23.4	23.4
87.5°	7.2	7.5	8.5	9.3	10.5	11.6	11.6	11.4	11.5	11.0	10.9
90°	2.0	2.9	4.4	5.4	6.4	7.8	9.3	10.8	12.3	11.8	12.3
92.5°	9.0	13.2	17.0	21.1	28.4	41.2	62.3	83.1	75.5	57.0	41.3
95°	18.2	23.6	31.9	44.7	63.8	105.6	178.7	259.3	291.2	236.2	176.8
97.5°	29.0	33.2	40.5	53.0	73.8	113.7	196.1	330.4	451.3	482.8	440.7
100°	36.9	40.3	47.2	58.9	78.1	112.4	185.1	314.3	465.0	561.8	579.0
102.5°	45.5	48.6	55.0	65.6	83.2	114.0	175.7	290.8	439.5	565.8	625.0
105°	58.5	61.4	67.2	76.6	91.9	118.4	168.9	261.7	394.9	535.8	638.4
107.5°	71.6	74.5	80.2	89.0	103.1	126.4	168.4	243.3	355.3	483.4	599.7
110°	81.0	83.5	88.9	97.2	111.0	133.1	170.4	236.2	332.9	450.3	562.7



TEST NUMBER: P331921-935

CATALOG NUMBER: S123DIP-S560D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	89.7	92.1	97.6	105.9	119.2	139.7	174.4	232.3	318.1	421.6	526.2
115°	102.6	105.6	110.5	118.8	132.1	150.8	180.7	230.8	302.0	387.0	477.9
117.5°	115.4	117.9	122.3	131.7	144.0	162.5	189.2	231.7	292.6	366.1	442.7
120°	123.3	125.7	130.6	140.0	152.2	169.9	195.4	233.2	288.3	355.1	424.3
122.5°	130.7	133.2	138.4	147.4	160.5	177.8	201.4	236.0	285.5	346.0	409.7
125°	140.9	143.9	149.3	158.6	171.9	189.1	210.7	240.1	281.9	334.4	390.4
127.5°	149.6	153.3	158.7	169.0	182.3	198.9	218.3	244.9	280.1	324.3	373.5
130°	154.7	159.1	165.0	175.3	188.6	204.7	223.4	248.0	279.0	318.7	362.9
132.5°	159.0	163.8	170.9	181.2	194.1	209.9	228.2	250.4	278.5	313.6	353.1
135°	166.0	171.4	178.7	189.1	202.3	217.6	234.3	253.9	277.9	306.9	339.8
137.5°	172.5	177.9	185.7	196.0	208.2	222.8	238.8	256.2	276.9	301.2	327.8
140°	177.3	182.2	190.0	199.8	212.2	226.4	241.2	257.8	276.5	297.6	320.7
142.5°	181.6	186.9	194.0	203.8	215.3	229.1	243.5	259.0	275.7	294.5	314.0
145°	188.6	193.0	200.4	208.7	220.0	232.8	246.1	259.8	274.5	290.2	305.9
147.5°	195.6	200.0	206.4	214.4	224.0	235.7	247.6	259.8	272.7	286.1	299.4
150°	200.4	204.3	210.7	217.6	226.4	237.7	248.0	259.8	271.0	283.4	294.6
152.5°	205.1	209.1	214.6	220.7	229.1	238.8	248.8	258.6	269.1	280.3	290.3
155°	212.7	215.6	220.5	225.9	232.8	241.2	249.0	257.4	265.7	275.5	283.9
157.5°	219.1	221.4	225.8	230.4	235.7	242.4	249.5	255.6	262.6	270.2	277.0
160°	223.4	225.4	229.4	232.8	237.7	243.6	249.5	254.9	260.3	266.7	273.0
162.5°	227.0	228.6	231.7	234.7	238.8	244.0	249.1	253.3	258.0	263.1	268.4
165°	231.8	232.8	235.2	237.2	240.6	244.5	248.0	251.0	254.4	258.3	262.3
167.5°	235.7	236.2	238.1	239.4	241.6	244.4	247.2	248.6	250.8	253.7	256.9
170°	237.7	238.2	239.6	240.6	241.6	244.1	246.1	247.0	248.5	251.0	253.4
172.5°	239.6	239.8	240.8	241.4	242.0	244.1	245.6	245.8	246.5	248.2	250.3
175°	241.6	241.2	242.1	242.1	242.6	243.6	244.5	244.1	244.1	245.0	246.1
177.5°	242.6	242.2	242.6	242.6	242.6	243.0	243.7	243.0	242.6	243.0	243.4
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P331921-935

CATALOG NUMBER: S123DIP-S560D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	716.3	716.5	719.4	721.5	720.5	721.8	722.3
5°	782.5	794.4	800.6	805.3	805.6	805.9	808.6
7.5°	876.5	889.2	898.5	912.7	916.9	921.7	920.3
10°	945.1	963.9	980.1	988.6	997.8	1011.3	1000.5
12.5°	1009.2	1042.5	1067.1	1080.4	1089.2	1091.8	1086.5
15°	1114.9	1158.5	1181.9	1181.2	1210.9	1223.7	1203.6
17.5°	1211.9	1252.1	1284.2	1300.7	1325.4	1330.9	1328.4
20°	1271.2	1315.1	1340.1	1368.5	1381.4	1392.9	1394.9
22.5°	1322.4	1361.8	1388.7	1412.3	1423.1	1428.5	1431.8
25°	1375.1	1406.1	1422.3	1430.5	1433.5	1432.8	1428.5
27.5°	1371.5	1373.8	1356.1	1338.6	1322.9	1305.3	1299.2
30°	1335.8	1308.1	1258.7	1230.6	1189.5	1156.8	1170.0
32.5°	1242.2	1187.1	1131.5	1070.2	1019.5	1005.1	990.6
35°	1060.1	963.2	906.5	840.6	814.2	787.8	769.6
37.5°	857.7	782.7	715.4	672.3	645.8	629.2	620.2
40°	741.7	674.0	618.6	583.7	563.5	544.8	542.1
42.5°	649.0	586.2	544.5	516.7	497.3	489.4	483.5
45°	531.6	487.7	459.7	439.9	427.1	422.1	415.5
47.5°	450.0	419.0	397.9	384.4	374.7	371.0	370.5
50°	404.3	378.6	363.1	352.5	344.9	343.6	338.4
52.5°	370.0	347.7	335.6	326.4	320.9	317.2	315.6
55°	321.2	306.3	295.5	290.2	285.9	282.2	282.2
57.5°	281.0	268.6	261.4	256.9	255.6	253.0	251.4
60°	256.2	245.6	240.0	236.1	233.5	233.8	230.8
62.5°	232.0	225.1	219.7	215.8	212.7	212.7	212.9
65°	197.5	192.3	188.3	187.0	185.0	182.7	183.3
67.5°	167.4	162.5	159.4	157.1	156.4	155.2	157.1
70°	145.8	142.2	139.8	137.8	137.2	137.5	139.1
72.5°	126.0	123.4	121.9	121.0	119.5	119.6	120.7
75°	98.9	96.9	95.7	94.6	94.3	94.3	94.3
77.5°	72.7	72.2	71.6	70.2	70.3	70.6	70.7
80°	57.3	56.4	56.1	55.4	54.4	53.7	55.4
82.5°	42.9	41.8	41.6	41.4	39.9	39.8	41.2
85°	23.1	22.1	22.4	22.1	22.1	21.8	21.8
87.5°	10.8	10.6	10.5	10.7	10.5	10.3	10.8
90°	12.7	13.3	14.2	13.8	14.2	14.7	14.2
92.5°	32.8	29.0	26.4	25.6	24.0	24.5	23.7
95°	119.9	93.8	76.1	66.8	62.3	58.9	57.0
97.5°	353.0	289.6	230.9	194.7	172.5	159.3	155.1
100°	539.2	481.7	412.0	362.4	326.6	307.5	307.9
102.5°	623.7	590.2	546.0	507.4	479.0	463.0	451.7
105°	687.5	696.9	684.1	661.5	642.8	627.2	624.7
107.5°	679.5	722.5	739.9	740.4	734.1	728.8	724.3
110°	653.2	715.1	749.4	763.2	767.1	766.1	765.1



TEST NUMBER: P331921-935

CATALOG NUMBER: S123DIP-S560D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	618.5	687.9	732.1	757.2	769.5	773.2	773.4
115°	563.3	635.5	689.0	725.8	747.4	757.2	759.7
117.5°	516.5	581.3	635.7	674.1	698.8	713.0	716.3
120°	490.6	549.5	599.2	637.9	665.5	677.2	680.2
122.5°	469.8	524.3	570.4	604.9	629.6	642.7	646.4
125°	443.9	491.1	530.4	561.8	583.4	595.7	599.2
127.5°	421.3	463.8	499.6	527.5	546.0	557.1	560.3
130°	407.1	446.9	480.3	506.4	524.0	534.3	538.2
132.5°	393.7	430.8	462.6	487.1	504.7	513.8	516.6
135°	374.7	406.7	434.6	458.7	473.4	482.2	485.7
137.5°	356.4	383.8	408.1	428.3	443.2	450.7	453.0
140°	345.7	369.3	390.4	409.1	422.8	430.7	430.2
142.5°	335.5	355.9	374.3	390.2	402.4	409.5	409.0
145°	322.2	337.9	352.1	364.4	374.7	378.7	379.6
147.5°	312.2	324.9	335.0	344.3	351.3	355.1	355.4
150°	305.9	316.2	325.6	332.9	338.4	341.3	341.3
152.5°	300.1	309.2	316.9	322.7	327.8	329.5	329.5
155°	291.7	299.1	305.0	309.4	313.3	314.3	314.8
157.5°	283.5	289.3	293.9	297.7	300.7	301.4	301.4
160°	278.4	283.4	286.8	290.2	293.2	293.2	292.7
162.5°	272.9	277.5	280.5	282.8	285.3	285.3	284.8
165°	265.2	268.6	271.0	273.0	275.0	274.5	274.5
167.5°	259.2	261.1	262.9	263.8	265.2	264.7	264.7
170°	254.9	256.8	257.8	258.3	259.3	258.8	258.8
172.5°	251.3	252.9	253.5	253.6	254.6	253.7	253.3
175°	246.5	247.5	247.5	247.5	248.0	247.5	247.0
177.5°	243.7	244.2	244.2	243.7	244.2	243.4	243.4
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6

(END OF REPORT)