

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331966-935

Luminaire Tested: **S123DIP-S775D585U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331966-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S775D585U935-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4635.0 lumens  
Efficiency: N/A  
Efficacy: 115.0 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331966-935

CATALOG NUMBER: S123DIP-S775D585U935-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331966-935

CATALOG NUMBER: S123DIP-S775D585U935-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	101	96	92	89	94	90	87	84	79	76	74	68	67	65	59	58	56	52
2	92	84	78	73	86	79	74	69	69	65	62	60	57	55	52	50	48	44
3	84	74	67	61	78	70	64	58	62	56	52	54	50	47	46	44	41	37
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	38	36	32
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31	28
6	65	53	45	39	61	50	43	37	44	39	34	39	34	31	34	30	28	25
7	60	48	40	34	56	45	38	33	40	34	30	36	31	27	31	27	25	22
8	56	44	36	31	52	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	37	29	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10014	10014	10014	10014
5°	11943	10057	8912	10057
10°	14948	10006	8050	10006
15°	18333	9926	7494	9926
20°	21841	9800	7135	9800
25°	23192	9647	7056	9647
30°	19877	9536	7093	9536
35°	13825	9376	7167	9376
40°	10413	9190	7144	9190
45°	8645	8914	7054	8914
50°	7743	8348	6990	8348
55°	7240	7739	6902	7739
60°	6794	7102	6833	7102
65°	6383	6477	6612	6477
70°	5986	5759	6297	5759
75°	5361	5041	5772	5041
80°	4699	4135	4971	4135
85°	3680	3013	3335	3013



TEST NUMBER: P331966-935

CATALOG NUMBER: S123DIP-S775D585U935-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	91.6	2.0
10°-20°	293.9	6.3
20°-30°	493.2	10.6
30°-40°	558.5	12.0
40°-50°	500.8	10.8
50°-60°	404.1	8.7
60°-70°	281.6	6.1
70°-80°	148.0	3.2
80°-90°	38.1	0.8
90°-100°	135.0	2.9
100°-110°	382.3	8.2
110°-120°	376.1	8.1
120°-130°	300.0	6.5
130°-140°	236.5	5.1
140°-150°	176.5	3.8
150°-160°	123.0	2.7
160°-170°	72.3	1.6
170°-180°	23.5	0.5
0°-30°	878.7	19.0
0°-40°	1437.2	31.0
0°-60°	2342.1	50.5
0°-90°	2809.8	60.6
90°-120°	893.4	19.3
90°-150°	1606.4	34.7
90°-180°	1825.0	39.4
0°-180°	4635.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	930	930	930	930	930	
5°	1105	931	825	931	1105	115
15°	1645	891	672	891	1645	475
25°	1953	812	594	812	1953	856
35°	1052	714	545	714	1052	684
45°	568	586	463	586	568	449
55°	386	412	368	412	386	346
65°	251	254	260	254	251	250
75°	129	121	139	121	129	138
85°	30	24	27	24	30	36
90°	14	1	14	1	14	9
95°	57	17	57	17	57	103
105°	625	57	625	57	625	616
115°	760	101	760	101	760	738
125°	599	140	599	140	599	543
135°	486	164	486	164	486	377
145°	380	187	380	187	380	241
155°	315	213	315	213	315	147
165°	274	232	274	232	274	78
175°	247	242	247	242	247	24
180°	243	243	243	243	243	



TEST NUMBER: P331966-935

CATALOG NUMBER: S123DIP-S775D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	987.3	986.6	984.8	986.3	983.3	979.4	979.0	975.4	964.9	964.2	961.4
5°	1105.3	1101.6	1101.2	1100.7	1094.4	1085.9	1069.6	1068.2	1046.6	1035.8	1022.8
7.5°	1257.9	1259.8	1253.3	1247.5	1228.2	1215.5	1198.1	1175.8	1149.3	1122.3	1104.3
10°	1367.6	1382.4	1364.0	1351.3	1339.6	1317.5	1291.8	1259.8	1227.9	1190.4	1162.0
12.5°	1485.1	1492.5	1488.8	1476.9	1458.6	1425.0	1379.5	1344.2	1314.7	1252.4	1227.3
15°	1645.2	1672.8	1655.2	1614.5	1615.5	1583.5	1524.0	1458.6	1423.9	1369.3	1295.0
17.5°	1815.8	1819.2	1811.7	1778.0	1755.4	1711.4	1656.5	1593.9	1523.5	1457.5	1378.6
20°	1906.7	1903.9	1888.2	1870.6	1831.9	1797.6	1737.7	1667.8	1577.6	1512.7	1426.6
22.5°	1957.1	1952.7	1945.2	1930.4	1898.2	1861.4	1807.6	1731.2	1645.5	1556.0	1456.6
25°	1952.7	1958.5	1959.4	1955.3	1944.1	1922.0	1879.6	1818.8	1733.1	1618.2	1514.5
27.5°	1776.0	1784.3	1808.4	1829.7	1853.6	1877.9	1874.7	1844.4	1781.1	1681.9	1555.1
30°	1599.2	1581.2	1625.8	1682.2	1720.5	1788.1	1826.0	1828.2	1792.6	1707.4	1583.9
32.5°	1354.0	1373.9	1393.6	1462.9	1546.7	1622.6	1698.0	1758.7	1765.6	1708.9	1600.9
35°	1052.1	1076.9	1112.9	1148.9	1239.2	1316.6	1449.1	1564.5	1656.5	1668.7	1602.4
37.5°	847.7	860.1	882.9	918.9	977.9	1069.9	1172.4	1318.3	1451.5	1550.6	1554.9
40°	741.1	744.7	770.3	797.8	845.6	921.4	1013.7	1142.6	1302.2	1440.6	1498.3
42.5°	661.0	668.9	679.8	706.2	744.2	801.2	887.2	993.7	1140.0	1299.2	1412.1
45°	567.9	577.0	583.8	601.3	628.4	666.7	726.6	824.0	935.3	1099.8	1251.7
47.5°	506.4	507.2	512.2	525.5	543.9	572.7	615.0	677.6	779.8	913.2	1069.2
50°	462.4	469.7	471.5	481.8	496.3	517.5	552.6	605.8	689.7	806.8	950.2
52.5°	431.4	433.6	438.7	446.2	458.7	475.3	505.8	547.4	613.2	713.1	844.9
55°	385.8	385.8	390.8	396.7	403.9	418.7	439.0	469.7	519.7	597.3	706.4
57.5°	343.6	345.9	349.4	351.2	357.3	367.2	384.1	407.4	444.7	504.4	591.1
60°	315.6	319.6	319.2	322.7	328.1	335.8	350.3	369.2	402.5	450.3	523.3
62.5°	291.0	290.8	290.7	295.0	300.4	307.7	317.0	333.5	361.8	404.2	466.3
65°	250.6	249.7	252.9	255.5	257.4	262.8	270.0	284.4	303.3	334.9	383.1
67.5°	214.7	212.2	213.9	214.7	217.8	222.1	228.8	237.7	252.8	278.1	314.4
70°	190.2	188.0	187.5	188.4	191.1	194.2	199.2	207.8	221.8	242.0	268.6
72.5°	165.0	163.4	163.3	165.3	166.6	168.7	172.2	180.0	191.1	206.4	231.2
75°	128.9	128.9	128.9	129.3	130.7	132.5	135.3	139.3	147.8	158.7	175.3
77.5°	96.6	96.5	96.0	95.9	97.9	98.8	99.4	103.1	107.9	115.2	127.3
80°	75.8	73.4	74.4	75.8	76.6	77.1	78.4	79.3	83.4	87.5	96.0
82.5°	56.2	54.3	54.5	56.7	56.8	57.3	58.6	59.8	61.4	65.1	69.7
85°	29.8	29.8	30.2	30.2	30.7	30.2	31.5	32.0	32.0	34.3	36.9
87.5°	13.7	13.0	13.3	13.6	13.3	13.4	13.7	14.0	14.3	14.7	14.8
90°	14.2	14.7	14.2	13.8	14.2	13.3	12.7	12.3	11.8	12.3	10.8
92.5°	23.7	24.5	24.0	25.6	26.4	29.0	32.8	41.3	57.0	75.5	83.1
95°	57.0	58.9	62.3	66.8	76.1	93.8	119.9	176.8	236.2	291.2	259.3
97.5°	155.1	159.3	172.5	194.7	230.9	289.6	353.0	440.7	482.8	451.3	330.4
100°	307.9	307.5	326.6	362.4	412.0	481.7	539.2	579.0	561.8	465.0	314.3
102.5°	451.7	463.0	479.0	507.4	546.0	590.2	623.7	625.0	565.8	439.5	290.8
105°	624.7	627.2	642.8	661.5	684.1	696.9	687.5	638.4	535.8	394.9	261.7
107.5°	724.3	728.8	734.1	740.4	739.9	722.5	679.5	599.7	483.4	355.3	243.3
110°	765.1	766.1	767.1	763.2	749.4	715.1	653.2	562.7	450.3	332.9	236.2



TEST NUMBER: P331966-935

CATALOG NUMBER: S123DIP-S775D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	773.4	773.2	769.5	757.2	732.1	687.9	618.5	526.2	421.6	318.1	232.3
115°	759.7	757.2	747.4	725.8	689.0	635.5	563.3	477.9	387.0	302.0	230.8
117.5°	716.3	713.0	698.8	674.1	635.7	581.3	516.5	442.7	366.1	292.6	231.7
120°	680.2	677.2	665.5	637.9	599.2	549.5	490.6	424.3	355.1	288.3	233.2
122.5°	646.4	642.7	629.6	604.9	570.4	524.3	469.8	409.7	346.0	285.5	236.0
125°	599.2	595.7	583.4	561.8	530.4	491.1	443.9	390.4	334.4	281.9	240.1
127.5°	560.3	557.1	546.0	527.5	499.6	463.8	421.3	373.5	324.3	280.1	244.9
130°	538.2	534.3	524.0	506.4	480.3	446.9	407.1	362.9	318.7	279.0	248.0
132.5°	516.6	513.8	504.7	487.1	462.6	430.8	393.7	353.1	313.6	278.5	250.4
135°	485.7	482.2	473.4	458.7	434.6	406.7	374.7	339.8	306.9	277.9	253.9
137.5°	453.0	450.7	443.2	428.3	408.1	383.8	356.4	327.8	301.2	276.9	256.2
140°	430.2	430.7	422.8	409.1	390.4	369.3	345.7	320.7	297.6	276.5	257.8
142.5°	409.0	409.5	402.4	390.2	374.3	355.9	335.5	314.0	294.5	275.7	259.0
145°	379.6	378.7	374.7	364.4	352.1	337.9	322.2	305.9	290.2	274.5	259.8
147.5°	355.4	355.1	351.3	344.3	335.0	324.9	312.2	299.4	286.1	272.7	259.8
150°	341.3	341.3	338.4	332.9	325.6	316.2	305.9	294.6	283.4	271.0	259.8
152.5°	329.5	329.5	327.8	322.7	316.9	309.2	300.1	290.3	280.3	269.1	258.6
155°	314.8	314.3	313.3	309.4	305.0	299.1	291.7	283.9	275.5	265.7	257.4
157.5°	301.4	301.4	300.7	297.7	293.9	289.3	283.5	277.0	270.2	262.6	255.6
160°	292.7	293.2	293.2	290.2	286.8	283.4	278.4	273.0	266.7	260.3	254.9
162.5°	284.8	285.3	285.3	282.8	280.5	277.5	272.9	268.4	263.1	258.0	253.3
165°	274.5	274.5	275.0	273.0	271.0	268.6	265.2	262.3	258.3	254.4	251.0
167.5°	264.7	264.7	265.2	263.8	262.9	261.1	259.2	256.9	253.7	250.8	248.6
170°	258.8	258.8	259.3	258.3	257.8	256.8	254.9	253.4	251.0	248.5	247.0
172.5°	253.3	253.7	254.6	253.6	253.5	252.9	251.3	250.3	248.2	246.5	245.8
175°	247.0	247.5	248.0	247.5	247.5	247.5	246.5	246.1	245.0	244.1	244.1
177.5°	243.4	243.4	244.2	243.7	244.2	244.2	243.7	243.4	243.0	242.6	243.0
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P331966-935

CATALOG NUMBER: S123DIP-S775D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	959.2	956.3	953.4	948.4	944.1	937.9	936.1	933.9	927.5	921.7	917.4
5°	1017.8	1006.9	991.2	976.8	965.1	949.3	940.3	930.8	917.3	905.1	895.2
7.5°	1079.1	1057.8	1033.3	1006.8	982.1	958.3	939.1	922.0	903.0	885.1	871.2
10°	1127.7	1097.1	1062.9	1025.9	994.4	963.7	938.0	915.5	891.1	870.0	852.4
12.5°	1183.3	1137.9	1090.6	1045.8	1008.4	965.9	934.8	906.1	878.5	853.0	833.3
15°	1249.1	1191.4	1135.4	1073.7	1016.9	963.7	926.8	890.7	858.7	832.5	807.3
17.5°	1308.9	1243.5	1169.8	1094.8	1026.2	963.2	911.5	870.6	830.6	798.7	773.5
20°	1342.8	1268.4	1185.0	1107.1	1031.3	961.0	904.2	855.5	812.3	778.4	750.0
22.5°	1372.0	1285.0	1198.7	1115.3	1031.0	955.2	890.9	840.8	793.8	760.8	730.6
25°	1402.3	1298.1	1211.6	1113.8	1019.6	941.2	869.0	812.3	765.3	726.6	695.5
27.5°	1428.2	1297.3	1194.6	1089.3	1001.8	923.2	846.1	785.2	735.5	693.4	661.8
30°	1445.5	1299.1	1176.9	1072.8	984.5	903.3	828.5	767.2	714.9	672.1	642.3
32.5°	1456.4	1298.0	1160.7	1049.7	957.0	885.3	809.3	745.9	692.2	650.1	621.4
35°	1462.7	1290.0	1132.7	1002.0	912.7	842.9	779.4	713.5	657.2	617.9	585.6
37.5°	1450.1	1273.3	1100.3	956.1	858.3	789.5	736.1	680.0	626.1	582.9	555.0
40°	1430.2	1262.6	1075.0	923.6	820.8	754.6	709.0	654.0	600.8	559.8	533.6
42.5°	1392.3	1240.5	1047.2	887.5	781.9	715.6	673.7	627.8	577.4	538.9	512.8
45°	1299.9	1192.7	1005.6	833.4	724.4	655.8	618.9	585.6	540.0	502.6	480.0
47.5°	1171.7	1120.7	945.4	776.4	664.3	598.4	560.0	533.1	499.9	469.7	448.1
50°	1082.7	1061.5	904.7	737.4	624.3	559.8	522.9	498.5	474.7	444.4	424.6
52.5°	979.9	993.0	857.0	697.1	583.5	520.1	485.3	466.1	444.4	419.6	402.3
55°	835.3	882.5	774.8	629.2	522.9	462.4	429.6	412.4	399.8	381.3	366.4
57.5°	699.7	760.0	686.0	559.4	463.3	411.2	379.6	360.9	352.8	343.2	331.5
60°	619.3	678.8	622.5	512.5	423.3	373.7	345.7	329.9	321.8	315.0	305.1
62.5°	547.6	607.8	560.4	464.9	383.9	337.9	313.7	298.3	291.9	288.3	279.9
65°	448.9	500.8	469.2	390.8	327.7	287.1	265.0	254.3	248.4	247.0	241.6
67.5°	365.4	404.8	381.9	324.2	274.5	239.4	220.7	211.5	207.0	206.6	202.5
70°	310.6	347.5	329.9	277.7	234.9	207.3	191.1	183.0	180.3	179.9	177.6
72.5°	268.0	293.8	279.8	236.2	203.1	178.1	166.3	157.7	154.7	155.3	153.8
75°	198.3	217.7	209.6	179.4	152.8	136.6	126.7	121.2	118.6	119.9	118.1
77.5°	142.7	155.0	147.7	126.7	110.4	98.6	91.4	88.0	85.6	85.5	84.6
80°	107.7	114.9	110.9	98.2	84.7	74.8	69.0	66.7	65.3	64.9	64.5
82.5°	76.7	82.8	78.1	69.4	60.2	54.2	51.0	48.0	47.0	47.3	46.8
85°	38.7	41.0	39.2	33.8	30.2	27.5	25.7	24.4	23.4	23.8	23.0
87.5°	15.2	15.2	13.9	12.2	11.4	10.0	9.7	8.9	8.4	8.5	8.4
90°	9.3	7.8	6.4	5.4	4.4	2.9	2.0	0.9	2.0	2.9	4.4
92.5°	62.3	41.2	28.4	21.1	17.0	13.2	9.0	6.1	9.0	13.2	17.0
95°	178.7	105.6	63.8	44.7	31.9	23.6	18.2	16.7	18.2	23.6	31.9
97.5°	196.1	113.7	73.8	53.0	40.5	33.2	29.0	28.5	29.0	33.2	40.5
100°	185.1	112.4	78.1	58.9	47.2	40.3	36.9	36.3	36.9	40.3	47.2
102.5°	175.7	114.0	83.2	65.6	55.0	48.6	45.5	44.6	45.5	48.6	55.0
105°	168.9	118.4	91.9	76.6	67.2	61.4	58.5	57.0	58.5	61.4	67.2
107.5°	168.4	126.4	103.1	89.0	80.2	74.5	71.6	70.1	71.6	74.5	80.2
110°	170.4	133.1	111.0	97.2	88.9	83.5	81.0	79.6	81.0	83.5	88.9





TEST NUMBER: P331966-935

CATALOG NUMBER: S123DIP-S775D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	174.4	139.7	119.2	105.9	97.6	92.1	89.7	88.2	89.7	92.1	97.6
115°	180.7	150.8	132.1	118.8	110.5	105.6	102.6	100.7	102.6	105.6	110.5
117.5°	189.2	162.5	144.0	131.7	122.3	117.9	115.4	113.1	115.4	117.9	122.3
120°	195.4	169.9	152.2	140.0	130.6	125.7	123.3	121.8	123.3	125.7	130.6
122.5°	201.4	177.8	160.5	147.4	138.4	133.2	130.7	129.2	130.7	133.2	138.4
125°	210.7	189.1	171.9	158.6	149.3	143.9	140.9	140.0	140.9	143.9	149.3
127.5°	218.3	198.9	182.3	169.0	158.7	153.3	149.6	148.1	149.6	153.3	158.7
130°	223.4	204.7	188.6	175.3	165.0	159.1	154.7	153.3	154.7	159.1	165.0
132.5°	228.2	209.9	194.1	181.2	170.9	163.8	159.0	157.1	159.0	163.8	170.9
135°	234.3	217.6	202.3	189.1	178.7	171.4	166.0	164.0	166.0	171.4	178.7
137.5°	238.8	222.8	208.2	196.0	185.7	177.9	172.5	170.5	172.5	177.9	185.7
140°	241.2	226.4	212.2	199.8	190.0	182.2	177.3	174.9	177.3	182.2	190.0
142.5°	243.5	229.1	215.3	203.8	194.0	186.9	181.6	179.5	181.6	186.9	194.0
145°	246.1	232.8	220.0	208.7	200.4	193.0	188.6	187.1	188.6	193.0	200.4
147.5°	247.6	235.7	224.0	214.4	206.4	200.0	195.6	194.8	195.6	200.0	206.4
150°	248.0	237.7	226.4	217.6	210.7	204.3	200.4	199.8	200.4	204.3	210.7
152.5°	248.8	238.8	229.1	220.7	214.6	209.1	205.1	205.0	205.1	209.1	214.6
155°	249.0	241.2	232.8	225.9	220.5	215.6	212.7	212.7	212.7	215.6	220.5
157.5°	249.5	242.4	235.7	230.4	225.8	221.4	219.1	218.7	219.1	221.4	225.8
160°	249.5	243.6	237.7	232.8	229.4	225.4	223.4	223.4	223.4	225.4	229.4
162.5°	249.1	244.0	238.8	234.7	231.7	228.6	227.0	227.0	227.0	228.6	231.7
165°	248.0	244.5	240.6	237.2	235.2	232.8	231.8	232.3	231.8	232.8	235.2
167.5°	247.2	244.4	241.6	239.4	238.1	236.2	235.7	236.3	235.7	236.2	238.1
170°	246.1	244.1	241.6	240.6	239.6	238.2	237.7	238.7	237.7	238.2	239.6
172.5°	245.6	244.1	242.0	241.4	240.8	239.8	239.6	240.2	239.6	239.8	240.8
175°	244.5	243.6	242.6	242.1	242.1	241.2	241.6	242.1	241.6	241.2	242.1
177.5°	243.7	243.0	242.6	242.6	242.6	242.2	242.6	243.0	242.6	242.2	242.6
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P331966-935

CATALOG NUMBER: S123DIP-S775D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	914.8	912.3	908.7	903.3	899.0	892.1	892.1	893.2	893.2	892.9	892.1
5°	887.1	880.3	872.2	862.7	852.8	842.9	841.1	837.5	834.8	833.0	830.7
7.5°	857.8	845.8	834.0	820.7	808.7	798.7	791.7	785.9	782.2	778.3	775.4
10°	837.9	823.0	809.1	795.1	779.8	767.7	760.0	754.6	750.5	746.9	745.1
12.5°	814.5	797.5	782.0	768.8	752.0	739.5	732.2	729.7	724.9	717.3	713.3
15°	780.2	764.5	746.0	725.7	717.6	702.2	693.7	689.7	686.9	681.1	679.2
17.5°	751.0	730.3	709.6	694.4	679.3	666.9	662.1	657.1	653.5	648.7	647.3
20°	727.5	709.0	690.1	673.9	658.1	644.5	640.5	636.9	633.3	631.0	629.2
22.5°	703.7	685.3	669.5	654.4	637.6	628.7	624.3	620.4	617.8	616.3	614.5
25°	670.3	654.0	636.5	622.9	609.4	603.6	600.8	598.6	596.8	594.5	594.1
27.5°	640.3	622.7	608.4	595.8	586.1	581.2	578.6	577.5	577.9	578.7	579.2
30°	617.9	601.8	590.0	579.2	570.2	565.7	565.2	565.2	567.1	567.5	568.4
32.5°	597.4	584.1	572.4	561.9	555.1	552.0	553.7	553.7	555.2	556.3	557.9
35°	567.5	555.8	546.7	537.8	531.9	533.2	534.2	535.0	537.3	540.0	541.8
37.5°	538.9	528.7	519.4	512.3	509.6	512.0	514.2	516.1	518.8	520.8	522.6
40°	518.3	510.7	501.7	495.3	496.3	497.7	499.5	501.7	503.9	505.3	507.1
42.5°	499.2	491.2	484.4	479.1	480.4	482.2	483.2	484.4	487.0	489.4	490.5
45°	470.1	463.8	457.5	454.3	455.3	456.2	457.0	458.4	460.6	462.4	463.0
47.5°	437.4	433.0	428.8	425.7	427.1	426.8	427.9	430.8	431.5	432.7	435.1
50°	416.5	412.4	407.5	406.6	406.6	406.6	407.0	410.6	410.6	412.4	414.2
52.5°	393.4	390.8	387.6	386.0	385.3	385.3	387.2	389.0	389.7	392.3	394.1
55°	359.2	356.5	353.9	352.5	351.5	352.5	356.1	357.0	359.2	360.6	362.0
57.5°	323.6	321.6	319.4	318.7	318.5	319.7	321.7	324.3	324.9	329.1	331.1
60°	300.2	297.0	295.2	295.2	294.4	298.4	297.5	302.0	302.9	305.6	308.8
62.5°	276.0	271.8	271.0	271.0	272.3	273.5	274.7	276.7	279.1	282.5	285.0
65°	237.1	234.9	238.0	237.5	236.6	239.4	239.4	241.6	244.3	247.5	252.4
67.5°	200.2	199.1	199.3	199.3	200.7	202.2	203.5	205.4	208.7	212.1	215.2
70°	175.3	176.7	174.4	176.2	177.6	178.1	178.9	181.7	185.3	187.5	191.1
72.5°	151.2	151.1	151.4	152.1	153.4	154.2	155.2	158.3	162.2	164.1	166.9
75°	116.3	115.8	117.2	117.2	119.4	120.4	121.2	122.6	126.2	128.9	131.1
77.5°	84.9	85.5	85.2	86.7	86.1	86.3	89.0	90.4	90.7	96.1	97.3
80°	64.0	64.9	65.3	65.8	66.3	65.3	68.5	69.8	69.8	73.0	75.3
82.5°	46.0	46.5	47.7	48.1	48.2	49.2	49.4	50.4	51.5	52.9	55.8
85°	23.0	24.4	24.8	24.4	24.8	23.8	25.2	25.7	26.2	26.2	26.2
87.5°	8.3	8.9	8.8	9.5	9.4	10.0	9.9	9.3	9.4	10.6	9.3
90°	5.4	6.4	7.8	9.3	10.8	12.3	11.8	12.3	12.7	13.3	14.2
92.5°	21.1	28.4	41.2	62.3	83.1	75.5	57.0	41.3	32.8	29.0	26.4
95°	44.7	63.8	105.6	178.7	259.3	291.2	236.2	176.8	119.9	93.8	76.1
97.5°	53.0	73.8	113.7	196.1	330.4	451.3	482.8	440.7	353.0	289.6	230.9
100°	58.9	78.1	112.4	185.1	314.3	465.0	561.8	579.0	539.2	481.7	412.0
102.5°	65.6	83.2	114.0	175.7	290.8	439.5	565.8	625.0	623.7	590.2	546.0
105°	76.6	91.9	118.4	168.9	261.7	394.9	535.8	638.4	687.5	696.9	684.1
107.5°	89.0	103.1	126.4	168.4	243.3	355.3	483.4	599.7	679.5	722.5	739.9
110°	97.2	111.0	133.1	170.4	236.2	332.9	450.3	562.7	653.2	715.1	749.4



TEST NUMBER: P331966-935

CATALOG NUMBER: S123DIP-S775D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	105.9	119.2	139.7	174.4	232.3	318.1	421.6	526.2	618.5	687.9	732.1
115°	118.8	132.1	150.8	180.7	230.8	302.0	387.0	477.9	563.3	635.5	689.0
117.5°	131.7	144.0	162.5	189.2	231.7	292.6	366.1	442.7	516.5	581.3	635.7
120°	140.0	152.2	169.9	195.4	233.2	288.3	355.1	424.3	490.6	549.5	599.2
122.5°	147.4	160.5	177.8	201.4	236.0	285.5	346.0	409.7	469.8	524.3	570.4
125°	158.6	171.9	189.1	210.7	240.1	281.9	334.4	390.4	443.9	491.1	530.4
127.5°	169.0	182.3	198.9	218.3	244.9	280.1	324.3	373.5	421.3	463.8	499.6
130°	175.3	188.6	204.7	223.4	248.0	279.0	318.7	362.9	407.1	446.9	480.3
132.5°	181.2	194.1	209.9	228.2	250.4	278.5	313.6	353.1	393.7	430.8	462.6
135°	189.1	202.3	217.6	234.3	253.9	277.9	306.9	339.8	374.7	406.7	434.6
137.5°	196.0	208.2	222.8	238.8	256.2	276.9	301.2	327.8	356.4	383.8	408.1
140°	199.8	212.2	226.4	241.2	257.8	276.5	297.6	320.7	345.7	369.3	390.4
142.5°	203.8	215.3	229.1	243.5	259.0	275.7	294.5	314.0	335.5	355.9	374.3
145°	208.7	220.0	232.8	246.1	259.8	274.5	290.2	305.9	322.2	337.9	352.1
147.5°	214.4	224.0	235.7	247.6	259.8	272.7	286.1	299.4	312.2	324.9	335.0
150°	217.6	226.4	237.7	248.0	259.8	271.0	283.4	294.6	305.9	316.2	325.6
152.5°	220.7	229.1	238.8	248.8	258.6	269.1	280.3	290.3	300.1	309.2	316.9
155°	225.9	232.8	241.2	249.0	257.4	265.7	275.5	283.9	291.7	299.1	305.0
157.5°	230.4	235.7	242.4	249.5	255.6	262.6	270.2	277.0	283.5	289.3	293.9
160°	232.8	237.7	243.6	249.5	254.9	260.3	266.7	273.0	278.4	283.4	286.8
162.5°	234.7	238.8	244.0	249.1	253.3	258.0	263.1	268.4	272.9	277.5	280.5
165°	237.2	240.6	244.5	248.0	251.0	254.4	258.3	262.3	265.2	268.6	271.0
167.5°	239.4	241.6	244.4	247.2	248.6	250.8	253.7	256.9	259.2	261.1	262.9
170°	240.6	241.6	244.1	246.1	247.0	248.5	251.0	253.4	254.9	256.8	257.8
172.5°	241.4	242.0	244.1	245.6	245.8	246.5	248.2	250.3	251.3	252.9	253.5
175°	242.1	242.6	243.6	244.5	244.1	244.1	245.0	246.1	246.5	247.5	247.5
177.5°	242.6	242.6	243.0	243.7	243.0	242.6	243.0	243.4	243.7	244.2	244.2
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P331966-935

CATALOG NUMBER: S123DIP-S775D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	889.6	889.2	891.7	889.9	891.7	889.2	889.6	892.1	892.9	893.2	893.2
5°	828.0	829.4	824.8	824.8	824.8	829.4	828.0	830.7	833.0	834.8	837.5
7.5°	773.2	771.2	771.4	769.0	771.4	771.2	773.2	775.4	778.3	782.2	785.9
10°	739.7	737.0	736.1	736.5	736.1	737.0	739.7	745.1	746.9	750.5	754.6
12.5°	711.9	711.4	705.4	705.5	705.4	711.4	711.9	713.3	717.3	724.9	729.7
15°	679.2	670.7	669.8	672.5	669.8	670.7	679.2	679.2	681.1	686.9	689.7
17.5°	646.5	642.0	642.3	640.9	642.3	642.0	646.5	647.3	648.7	653.5	657.1
20°	629.2	626.5	626.1	622.9	626.1	626.5	629.2	629.2	631.0	633.3	636.9
22.5°	613.4	612.5	612.8	609.2	612.8	612.5	613.4	614.5	616.3	617.8	620.4
25°	593.7	595.9	594.1	594.1	594.1	595.9	593.7	594.1	594.5	596.8	598.6
27.5°	580.3	580.2	579.3	579.3	579.3	580.2	580.3	579.2	578.7	577.9	577.5
30°	570.2	569.7	570.7	570.7	570.7	569.7	570.2	568.4	567.5	567.1	565.2
32.5°	560.1	560.8	560.9	561.3	560.9	560.8	560.1	557.9	556.3	555.2	553.7
35°	544.5	544.9	546.3	545.4	546.3	544.9	544.5	541.8	540.0	537.3	535.0
37.5°	523.4	525.5	525.0	525.7	525.0	525.5	523.4	522.6	520.8	518.8	516.1
40°	507.6	508.9	508.4	508.4	508.4	508.9	507.6	507.1	505.3	503.9	501.7
42.5°	491.3	492.3	491.1	490.4	491.1	492.3	491.3	490.5	489.4	487.0	484.4
45°	464.7	463.8	465.2	463.4	465.2	463.8	464.7	463.0	462.4	460.6	458.4
47.5°	435.0	435.8	436.3	437.6	436.3	435.8	435.0	435.1	432.7	431.5	430.8
50°	415.2	417.8	417.8	417.4	417.8	417.8	415.2	414.2	412.4	410.6	410.6
52.5°	395.6	396.9	398.7	398.6	398.7	396.9	395.6	394.1	392.3	389.7	389.0
55°	365.6	366.4	367.4	367.8	367.4	366.4	365.6	362.0	360.6	359.2	357.0
57.5°	334.3	334.0	336.1	336.8	336.1	334.0	334.3	331.1	329.1	324.9	324.3
60°	312.4	312.4	316.0	317.4	316.0	312.4	312.4	308.8	305.6	302.9	302.0
62.5°	289.0	290.4	293.9	292.1	293.9	290.4	289.0	285.0	282.5	279.1	276.7
65°	254.7	258.3	257.9	259.6	257.9	258.3	254.7	252.4	247.5	244.3	241.6
67.5°	218.9	221.1	224.4	224.6	224.4	221.1	218.9	215.2	212.1	208.7	205.4
70°	194.8	197.0	198.8	200.1	198.8	197.0	194.8	191.1	187.5	185.3	181.7
72.5°	171.3	172.5	176.8	174.9	176.8	172.5	171.3	166.9	164.1	162.2	158.3
75°	134.3	137.5	140.2	138.8	140.2	137.5	134.3	131.1	128.9	126.2	122.6
77.5°	99.4	102.5	103.8	102.6	103.8	102.5	99.4	97.3	96.1	90.7	90.4
80°	78.4	78.0	80.7	80.2	80.7	78.0	78.4	75.3	73.0	69.8	69.8
82.5°	57.5	57.1	58.3	58.6	58.3	57.1	57.5	55.8	52.9	51.5	50.4
85°	28.0	29.3	27.5	27.0	27.5	29.3	28.0	26.2	26.2	26.2	25.7
87.5°	9.2	9.3	9.0	8.6	9.0	9.3	9.2	9.3	10.6	9.4	9.3
90°	13.8	14.2	14.7	14.2	14.7	14.2	13.8	14.2	13.3	12.7	12.3
92.5°	25.6	24.0	24.5	23.7	24.5	24.0	25.6	26.4	29.0	32.8	41.3
95°	66.8	62.3	58.9	57.0	58.9	62.3	66.8	76.1	93.8	119.9	176.8
97.5°	194.7	172.5	159.3	155.1	159.3	172.5	194.7	230.9	289.6	353.0	440.7
100°	362.4	326.6	307.5	307.9	307.5	326.6	362.4	412.0	481.7	539.2	579.0
102.5°	507.4	479.0	463.0	451.7	463.0	479.0	507.4	546.0	590.2	623.7	625.0
105°	661.5	642.8	627.2	624.7	627.2	642.8	661.5	684.1	696.9	687.5	638.4
107.5°	740.4	734.1	728.8	724.3	728.8	734.1	740.4	739.9	722.5	679.5	599.7
110°	763.2	767.1	766.1	765.1	766.1	767.1	763.2	749.4	715.1	653.2	562.7



TEST NUMBER: P331966-935

CATALOG NUMBER: S123DIP-S775D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	757.2	769.5	773.2	773.4	773.2	769.5	757.2	732.1	687.9	618.5	526.2
115°	725.8	747.4	757.2	759.7	757.2	747.4	725.8	689.0	635.5	563.3	477.9
117.5°	674.1	698.8	713.0	716.3	713.0	698.8	674.1	635.7	581.3	516.5	442.7
120°	637.9	665.5	677.2	680.2	677.2	665.5	637.9	599.2	549.5	490.6	424.3
122.5°	604.9	629.6	642.7	646.4	642.7	629.6	604.9	570.4	524.3	469.8	409.7
125°	561.8	583.4	595.7	599.2	595.7	583.4	561.8	530.4	491.1	443.9	390.4
127.5°	527.5	546.0	557.1	560.3	557.1	546.0	527.5	499.6	463.8	421.3	373.5
130°	506.4	524.0	534.3	538.2	534.3	524.0	506.4	480.3	446.9	407.1	362.9
132.5°	487.1	504.7	513.8	516.6	513.8	504.7	487.1	462.6	430.8	393.7	353.1
135°	458.7	473.4	482.2	485.7	482.2	473.4	458.7	434.6	406.7	374.7	339.8
137.5°	428.3	443.2	450.7	453.0	450.7	443.2	428.3	408.1	383.8	356.4	327.8
140°	409.1	422.8	430.7	430.2	430.7	422.8	409.1	390.4	369.3	345.7	320.7
142.5°	390.2	402.4	409.5	409.0	409.5	402.4	390.2	374.3	355.9	335.5	314.0
145°	364.4	374.7	378.7	379.6	378.7	374.7	364.4	352.1	337.9	322.2	305.9
147.5°	344.3	351.3	355.1	355.4	355.1	351.3	344.3	335.0	324.9	312.2	299.4
150°	332.9	338.4	341.3	341.3	341.3	338.4	332.9	325.6	316.2	305.9	294.6
152.5°	322.7	327.8	329.5	329.5	329.5	327.8	322.7	316.9	309.2	300.1	290.3
155°	309.4	313.3	314.3	314.8	314.3	313.3	309.4	305.0	299.1	291.7	283.9
157.5°	297.7	300.7	301.4	301.4	301.4	300.7	297.7	293.9	289.3	283.5	277.0
160°	290.2	293.2	293.2	292.7	293.2	293.2	290.2	286.8	283.4	278.4	273.0
162.5°	282.8	285.3	285.3	284.8	285.3	285.3	282.8	280.5	277.5	272.9	268.4
165°	273.0	275.0	274.5	274.5	274.5	275.0	273.0	271.0	268.6	265.2	262.3
167.5°	263.8	265.2	264.7	264.7	264.7	265.2	263.8	262.9	261.1	259.2	256.9
170°	258.3	259.3	258.8	258.8	258.8	259.3	258.3	257.8	256.8	254.9	253.4
172.5°	253.6	254.6	253.7	253.3	253.7	254.6	253.6	253.5	252.9	251.3	250.3
175°	247.5	248.0	247.5	247.0	247.5	248.0	247.5	247.5	247.5	246.5	246.1
177.5°	243.7	244.2	243.4	243.4	243.4	244.2	243.7	244.2	244.2	243.7	243.4
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P331966-935

CATALOG NUMBER: S123DIP-S775D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	892.1	892.1	899.0	903.3	908.7	912.3	914.8	917.4	921.7	927.5	933.9
5°	841.1	842.9	852.8	862.7	872.2	880.3	887.1	895.2	905.1	917.3	930.8
7.5°	791.7	798.7	808.7	820.7	834.0	845.8	857.8	871.2	885.1	903.0	922.0
10°	760.0	767.7	779.8	795.1	809.1	823.0	837.9	852.4	870.0	891.1	915.5
12.5°	732.2	739.5	752.0	768.8	782.0	797.5	814.5	833.3	853.0	878.5	906.1
15°	693.7	702.2	717.6	725.7	746.0	764.5	780.2	807.3	832.5	858.7	890.7
17.5°	662.1	666.9	679.3	694.4	709.6	730.3	751.0	773.5	798.7	830.6	870.6
20°	640.5	644.5	658.1	673.9	690.1	709.0	727.5	750.0	778.4	812.3	855.5
22.5°	624.3	628.7	637.6	654.4	669.5	685.3	703.7	730.6	760.8	793.8	840.8
25°	600.8	603.6	609.4	622.9	636.5	654.0	670.3	695.5	726.6	765.3	812.3
27.5°	578.6	581.2	586.1	595.8	608.4	622.7	640.3	661.8	693.4	735.5	785.2
30°	565.2	565.7	570.2	579.2	590.0	601.8	617.9	642.3	672.1	714.9	767.2
32.5°	553.7	552.0	555.1	561.9	572.4	584.1	597.4	621.4	650.1	692.2	745.9
35°	534.2	533.2	531.9	537.8	546.7	555.8	567.5	585.6	617.9	657.2	713.5
37.5°	514.2	512.0	509.6	512.3	519.4	528.7	538.9	555.0	582.9	626.1	680.0
40°	499.5	497.7	496.3	495.3	501.7	510.7	518.3	533.6	559.8	600.8	654.0
42.5°	483.2	482.2	480.4	479.1	484.4	491.2	499.2	512.8	538.9	577.4	627.8
45°	457.0	456.2	455.3	454.3	457.5	463.8	470.1	480.0	502.6	540.0	585.6
47.5°	427.9	426.8	427.1	425.7	428.8	433.0	437.4	448.1	469.7	499.9	533.1
50°	407.0	406.6	406.6	406.6	407.5	412.4	416.5	424.6	444.4	474.7	498.5
52.5°	387.2	385.3	385.3	386.0	387.6	390.8	393.4	402.3	419.6	444.4	466.1
55°	356.1	352.5	351.5	352.5	353.9	356.5	359.2	366.4	381.3	399.8	412.4
57.5°	321.7	319.7	318.5	318.7	319.4	321.6	323.6	331.5	343.2	352.8	360.9
60°	297.5	298.4	294.4	295.2	295.2	297.0	300.2	305.1	315.0	321.8	329.9
62.5°	274.7	273.5	272.3	271.0	271.0	271.8	276.0	279.9	288.3	291.9	298.3
65°	239.4	239.4	236.6	237.5	238.0	234.9	237.1	241.6	247.0	248.4	254.3
67.5°	203.5	202.2	200.7	199.3	199.3	199.1	200.2	202.5	206.6	207.0	211.5
70°	178.9	178.1	177.6	176.2	174.4	176.7	175.3	177.6	179.9	180.3	183.0
72.5°	155.2	154.2	153.4	152.1	151.4	151.1	151.2	153.8	155.3	154.7	157.7
75°	121.2	120.4	119.4	117.2	117.2	115.8	116.3	118.1	119.9	118.6	121.2
77.5°	89.0	86.3	86.1	86.7	85.2	85.5	84.9	84.6	85.5	85.6	88.0
80°	68.5	65.3	66.3	65.8	65.3	64.9	64.0	64.5	64.9	65.3	66.7
82.5°	49.4	49.2	48.2	48.1	47.7	46.5	46.0	46.8	47.3	47.0	48.0
85°	25.2	23.8	24.8	24.4	24.8	24.4	23.0	23.0	23.8	23.4	24.4
87.5°	9.9	10.0	9.4	9.5	8.8	8.9	8.3	8.4	8.5	8.4	8.9
90°	11.8	12.3	10.8	9.3	7.8	6.4	5.4	4.4	2.9	2.0	0.9
92.5°	57.0	75.5	83.1	62.3	41.2	28.4	21.1	17.0	13.2	9.0	6.1
95°	236.2	291.2	259.3	178.7	105.6	63.8	44.7	31.9	23.6	18.2	16.7
97.5°	482.8	451.3	330.4	196.1	113.7	73.8	53.0	40.5	33.2	29.0	28.5
100°	561.8	465.0	314.3	185.1	112.4	78.1	58.9	47.2	40.3	36.9	36.3
102.5°	565.8	439.5	290.8	175.7	114.0	83.2	65.6	55.0	48.6	45.5	44.6
105°	535.8	394.9	261.7	168.9	118.4	91.9	76.6	67.2	61.4	58.5	57.0
107.5°	483.4	355.3	243.3	168.4	126.4	103.1	89.0	80.2	74.5	71.6	70.1
110°	450.3	332.9	236.2	170.4	133.1	111.0	97.2	88.9	83.5	81.0	79.6



TEST NUMBER: P331966-935

CATALOG NUMBER: S123DIP-S775D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	421.6	318.1	232.3	174.4	139.7	119.2	105.9	97.6	92.1	89.7	88.2
115°	387.0	302.0	230.8	180.7	150.8	132.1	118.8	110.5	105.6	102.6	100.7
117.5°	366.1	292.6	231.7	189.2	162.5	144.0	131.7	122.3	117.9	115.4	113.1
120°	355.1	288.3	233.2	195.4	169.9	152.2	140.0	130.6	125.7	123.3	121.8
122.5°	346.0	285.5	236.0	201.4	177.8	160.5	147.4	138.4	133.2	130.7	129.2
125°	334.4	281.9	240.1	210.7	189.1	171.9	158.6	149.3	143.9	140.9	140.0
127.5°	324.3	280.1	244.9	218.3	198.9	182.3	169.0	158.7	153.3	149.6	148.1
130°	318.7	279.0	248.0	223.4	204.7	188.6	175.3	165.0	159.1	154.7	153.3
132.5°	313.6	278.5	250.4	228.2	209.9	194.1	181.2	170.9	163.8	159.0	157.1
135°	306.9	277.9	253.9	234.3	217.6	202.3	189.1	178.7	171.4	166.0	164.0
137.5°	301.2	276.9	256.2	238.8	222.8	208.2	196.0	185.7	177.9	172.5	170.5
140°	297.6	276.5	257.8	241.2	226.4	212.2	199.8	190.0	182.2	177.3	174.9
142.5°	294.5	275.7	259.0	243.5	229.1	215.3	203.8	194.0	186.9	181.6	179.5
145°	290.2	274.5	259.8	246.1	232.8	220.0	208.7	200.4	193.0	188.6	187.1
147.5°	286.1	272.7	259.8	247.6	235.7	224.0	214.4	206.4	200.0	195.6	194.8
150°	283.4	271.0	259.8	248.0	237.7	226.4	217.6	210.7	204.3	200.4	199.8
152.5°	280.3	269.1	258.6	248.8	238.8	229.1	220.7	214.6	209.1	205.1	205.0
155°	275.5	265.7	257.4	249.0	241.2	232.8	225.9	220.5	215.6	212.7	212.7
157.5°	270.2	262.6	255.6	249.5	242.4	235.7	230.4	225.8	221.4	219.1	218.7
160°	266.7	260.3	254.9	249.5	243.6	237.7	232.8	229.4	225.4	223.4	223.4
162.5°	263.1	258.0	253.3	249.1	244.0	238.8	234.7	231.7	228.6	227.0	227.0
165°	258.3	254.4	251.0	248.0	244.5	240.6	237.2	235.2	232.8	231.8	232.3
167.5°	253.7	250.8	248.6	247.2	244.4	241.6	239.4	238.1	236.2	235.7	236.3
170°	251.0	248.5	247.0	246.1	244.1	241.6	240.6	239.6	238.2	237.7	238.7
172.5°	248.2	246.5	245.8	245.6	244.1	242.0	241.4	240.8	239.8	239.6	240.2
175°	245.0	244.1	244.1	244.5	243.6	242.6	242.1	242.1	241.2	241.6	242.1
177.5°	243.0	242.6	243.0	243.7	243.0	242.6	242.6	242.6	242.2	242.6	243.0
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P331966-935

CATALOG NUMBER: S123DIP-S775D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	936.1	937.9	944.1	948.4	953.4	956.3	959.2	961.4	964.2	964.9	975.4
5°	940.3	949.3	965.1	976.8	991.2	1006.9	1017.8	1022.8	1035.8	1046.6	1068.2
7.5°	939.1	958.3	982.1	1006.8	1033.3	1057.8	1079.1	1104.3	1122.3	1149.3	1175.8
10°	938.0	963.7	994.4	1025.9	1062.9	1097.1	1127.7	1162.0	1190.4	1227.9	1259.8
12.5°	934.8	965.9	1008.4	1045.8	1090.6	1137.9	1183.3	1227.3	1252.4	1314.7	1344.2
15°	926.8	963.7	1016.9	1073.7	1135.4	1191.4	1249.1	1295.0	1369.3	1423.9	1458.6
17.5°	911.5	963.2	1026.2	1094.8	1169.8	1243.5	1308.9	1378.6	1457.5	1523.5	1593.9
20°	904.2	961.0	1031.3	1107.1	1185.0	1268.4	1342.8	1426.6	1512.7	1577.6	1667.8
22.5°	890.9	955.2	1031.0	1115.3	1198.7	1285.0	1372.0	1456.6	1556.0	1645.5	1731.2
25°	869.0	941.2	1019.6	1113.8	1211.6	1298.1	1402.3	1514.5	1618.2	1733.1	1818.8
27.5°	846.1	923.2	1001.8	1089.3	1194.6	1297.3	1428.2	1555.1	1681.9	1781.1	1844.4
30°	828.5	903.3	984.5	1072.8	1176.9	1299.1	1445.5	1583.9	1707.4	1792.6	1828.2
32.5°	809.3	885.3	957.0	1049.7	1160.7	1298.0	1456.4	1600.9	1708.9	1765.6	1758.7
35°	779.4	842.9	912.7	1002.0	1132.7	1290.0	1462.7	1602.4	1668.7	1656.5	1564.5
37.5°	736.1	789.5	858.3	956.1	1100.3	1273.3	1450.1	1554.9	1550.6	1451.5	1318.3
40°	709.0	754.6	820.8	923.6	1075.0	1262.6	1430.2	1498.3	1440.6	1302.2	1142.6
42.5°	673.7	715.6	781.9	887.5	1047.2	1240.5	1392.3	1412.1	1299.2	1140.0	993.7
45°	618.9	655.8	724.4	833.4	1005.6	1192.7	1299.9	1251.7	1099.8	935.3	824.0
47.5°	560.0	598.4	664.3	776.4	945.4	1120.7	1171.7	1069.2	913.2	779.8	677.6
50°	522.9	559.8	624.3	737.4	904.7	1061.5	1082.7	950.2	806.8	689.7	605.8
52.5°	485.3	520.1	583.5	697.1	857.0	993.0	979.9	844.9	713.1	613.2	547.4
55°	429.6	462.4	522.9	629.2	774.8	882.5	835.3	706.4	597.3	519.7	469.7
57.5°	379.6	411.2	463.3	559.4	686.0	760.0	699.7	591.1	504.4	444.7	407.4
60°	345.7	373.7	423.3	512.5	622.5	678.8	619.3	523.3	450.3	402.5	369.2
62.5°	313.7	337.9	383.9	464.9	560.4	607.8	547.6	466.3	404.2	361.8	333.5
65°	265.0	287.1	327.7	390.8	469.2	500.8	448.9	383.1	334.9	303.3	284.4
67.5°	220.7	239.4	274.5	324.2	381.9	404.8	365.4	314.4	278.1	252.8	237.7
70°	191.1	207.3	234.9	277.7	329.9	347.5	310.6	268.6	242.0	221.8	207.8
72.5°	166.3	178.1	203.1	236.2	279.8	293.8	268.0	231.2	206.4	191.1	180.0
75°	126.7	136.6	152.8	179.4	209.6	217.7	198.3	175.3	158.7	147.8	139.3
77.5°	91.4	98.6	110.4	126.7	147.7	155.0	142.7	127.3	115.2	107.9	103.1
80°	69.0	74.8	84.7	98.2	110.9	114.9	107.7	96.0	87.5	83.4	79.3
82.5°	51.0	54.2	60.2	69.4	78.1	82.8	76.7	69.7	65.1	61.4	59.8
85°	25.7	27.5	30.2	33.8	39.2	41.0	38.7	36.9	34.3	32.0	32.0
87.5°	9.7	10.0	11.4	12.2	13.9	15.2	15.2	14.8	14.7	14.3	14.0
90°	2.0	2.9	4.4	5.4	6.4	7.8	9.3	10.8	12.3	11.8	12.3
92.5°	9.0	13.2	17.0	21.1	28.4	41.2	62.3	83.1	75.5	57.0	41.3
95°	18.2	23.6	31.9	44.7	63.8	105.6	178.7	259.3	291.2	236.2	176.8
97.5°	29.0	33.2	40.5	53.0	73.8	113.7	196.1	330.4	451.3	482.8	440.7
100°	36.9	40.3	47.2	58.9	78.1	112.4	185.1	314.3	465.0	561.8	579.0
102.5°	45.5	48.6	55.0	65.6	83.2	114.0	175.7	290.8	439.5	565.8	625.0
105°	58.5	61.4	67.2	76.6	91.9	118.4	168.9	261.7	394.9	535.8	638.4
107.5°	71.6	74.5	80.2	89.0	103.1	126.4	168.4	243.3	355.3	483.4	599.7
110°	81.0	83.5	88.9	97.2	111.0	133.1	170.4	236.2	332.9	450.3	562.7





TEST NUMBER: P331966-935

CATALOG NUMBER: S123DIP-S775D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	89.7	92.1	97.6	105.9	119.2	139.7	174.4	232.3	318.1	421.6	526.2
115°	102.6	105.6	110.5	118.8	132.1	150.8	180.7	230.8	302.0	387.0	477.9
117.5°	115.4	117.9	122.3	131.7	144.0	162.5	189.2	231.7	292.6	366.1	442.7
120°	123.3	125.7	130.6	140.0	152.2	169.9	195.4	233.2	288.3	355.1	424.3
122.5°	130.7	133.2	138.4	147.4	160.5	177.8	201.4	236.0	285.5	346.0	409.7
125°	140.9	143.9	149.3	158.6	171.9	189.1	210.7	240.1	281.9	334.4	390.4
127.5°	149.6	153.3	158.7	169.0	182.3	198.9	218.3	244.9	280.1	324.3	373.5
130°	154.7	159.1	165.0	175.3	188.6	204.7	223.4	248.0	279.0	318.7	362.9
132.5°	159.0	163.8	170.9	181.2	194.1	209.9	228.2	250.4	278.5	313.6	353.1
135°	166.0	171.4	178.7	189.1	202.3	217.6	234.3	253.9	277.9	306.9	339.8
137.5°	172.5	177.9	185.7	196.0	208.2	222.8	238.8	256.2	276.9	301.2	327.8
140°	177.3	182.2	190.0	199.8	212.2	226.4	241.2	257.8	276.5	297.6	320.7
142.5°	181.6	186.9	194.0	203.8	215.3	229.1	243.5	259.0	275.7	294.5	314.0
145°	188.6	193.0	200.4	208.7	220.0	232.8	246.1	259.8	274.5	290.2	305.9
147.5°	195.6	200.0	206.4	214.4	224.0	235.7	247.6	259.8	272.7	286.1	299.4
150°	200.4	204.3	210.7	217.6	226.4	237.7	248.0	259.8	271.0	283.4	294.6
152.5°	205.1	209.1	214.6	220.7	229.1	238.8	248.8	258.6	269.1	280.3	290.3
155°	212.7	215.6	220.5	225.9	232.8	241.2	249.0	257.4	265.7	275.5	283.9
157.5°	219.1	221.4	225.8	230.4	235.7	242.4	249.5	255.6	262.6	270.2	277.0
160°	223.4	225.4	229.4	232.8	237.7	243.6	249.5	254.9	260.3	266.7	273.0
162.5°	227.0	228.6	231.7	234.7	238.8	244.0	249.1	253.3	258.0	263.1	268.4
165°	231.8	232.8	235.2	237.2	240.6	244.5	248.0	251.0	254.4	258.3	262.3
167.5°	235.7	236.2	238.1	239.4	241.6	244.4	247.2	248.6	250.8	253.7	256.9
170°	237.7	238.2	239.6	240.6	241.6	244.1	246.1	247.0	248.5	251.0	253.4
172.5°	239.6	239.8	240.8	241.4	242.0	244.1	245.6	245.8	246.5	248.2	250.3
175°	241.6	241.2	242.1	242.1	242.6	243.6	244.5	244.1	244.1	245.0	246.1
177.5°	242.6	242.2	242.6	242.6	242.6	243.0	243.7	243.0	242.6	243.0	243.4
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P331966-935

CATALOG NUMBER: S123DIP-S775D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	979.0	979.4	983.3	986.3	984.8	986.6	987.3
5°	1069.6	1085.9	1094.4	1100.7	1101.2	1101.6	1105.3
7.5°	1198.1	1215.5	1228.2	1247.5	1253.3	1259.8	1257.9
10°	1291.8	1317.5	1339.6	1351.3	1364.0	1382.4	1367.6
12.5°	1379.5	1425.0	1458.6	1476.9	1488.8	1492.5	1485.1
15°	1524.0	1583.5	1615.5	1614.5	1655.2	1672.8	1645.2
17.5°	1656.5	1711.4	1755.4	1778.0	1811.7	1819.2	1815.8
20°	1737.7	1797.6	1831.9	1870.6	1888.2	1903.9	1906.7
22.5°	1807.6	1861.4	1898.2	1930.4	1945.2	1952.7	1957.1
25°	1879.6	1922.0	1944.1	1955.3	1959.4	1958.5	1952.7
27.5°	1874.7	1877.9	1853.6	1829.7	1808.4	1784.3	1776.0
30°	1826.0	1788.1	1720.5	1682.2	1625.8	1581.2	1599.2
32.5°	1698.0	1622.6	1546.7	1462.9	1393.6	1373.9	1354.0
35°	1449.1	1316.6	1239.2	1148.9	1112.9	1076.9	1052.1
37.5°	1172.4	1069.9	977.9	918.9	882.9	860.1	847.7
40°	1013.7	921.4	845.6	797.8	770.3	744.7	741.1
42.5°	887.2	801.2	744.2	706.2	679.8	668.9	661.0
45°	726.6	666.7	628.4	601.3	583.8	577.0	567.9
47.5°	615.0	572.7	543.9	525.5	512.2	507.2	506.4
50°	552.6	517.5	496.3	481.8	471.5	469.7	462.4
52.5°	505.8	475.3	458.7	446.2	438.7	433.6	431.4
55°	439.0	418.7	403.9	396.7	390.8	385.8	385.8
57.5°	384.1	367.2	357.3	351.2	349.4	345.9	343.6
60°	350.3	335.8	328.1	322.7	319.2	319.6	315.6
62.5°	317.0	307.7	300.4	295.0	290.7	290.8	291.0
65°	270.0	262.8	257.4	255.5	252.9	249.7	250.6
67.5°	228.8	222.1	217.8	214.7	213.9	212.2	214.7
70°	199.2	194.2	191.1	188.4	187.5	188.0	190.2
72.5°	172.2	168.7	166.6	165.3	163.3	163.4	165.0
75°	135.3	132.5	130.7	129.3	128.9	128.9	128.9
77.5°	99.4	98.8	97.9	95.9	96.0	96.5	96.6
80°	78.4	77.1	76.6	75.8	74.4	73.4	75.8
82.5°	58.6	57.3	56.8	56.7	54.5	54.3	56.2
85°	31.5	30.2	30.7	30.2	30.2	29.8	29.8
87.5°	13.7	13.4	13.3	13.6	13.3	13.0	13.7
90°	12.7	13.3	14.2	13.8	14.2	14.7	14.2
92.5°	32.8	29.0	26.4	25.6	24.0	24.5	23.7
95°	119.9	93.8	76.1	66.8	62.3	58.9	57.0
97.5°	353.0	289.6	230.9	194.7	172.5	159.3	155.1
100°	539.2	481.7	412.0	362.4	326.6	307.5	307.9
102.5°	623.7	590.2	546.0	507.4	479.0	463.0	451.7
105°	687.5	696.9	684.1	661.5	642.8	627.2	624.7
107.5°	679.5	722.5	739.9	740.4	734.1	728.8	724.3
110°	653.2	715.1	749.4	763.2	767.1	766.1	765.1



TEST NUMBER: P331966-935

CATALOG NUMBER: S123DIP-S775D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	618.5	687.9	732.1	757.2	769.5	773.2	773.4
115°	563.3	635.5	689.0	725.8	747.4	757.2	759.7
117.5°	516.5	581.3	635.7	674.1	698.8	713.0	716.3
120°	490.6	549.5	599.2	637.9	665.5	677.2	680.2
122.5°	469.8	524.3	570.4	604.9	629.6	642.7	646.4
125°	443.9	491.1	530.4	561.8	583.4	595.7	599.2
127.5°	421.3	463.8	499.6	527.5	546.0	557.1	560.3
130°	407.1	446.9	480.3	506.4	524.0	534.3	538.2
132.5°	393.7	430.8	462.6	487.1	504.7	513.8	516.6
135°	374.7	406.7	434.6	458.7	473.4	482.2	485.7
137.5°	356.4	383.8	408.1	428.3	443.2	450.7	453.0
140°	345.7	369.3	390.4	409.1	422.8	430.7	430.2
142.5°	335.5	355.9	374.3	390.2	402.4	409.5	409.0
145°	322.2	337.9	352.1	364.4	374.7	378.7	379.6
147.5°	312.2	324.9	335.0	344.3	351.3	355.1	355.4
150°	305.9	316.2	325.6	332.9	338.4	341.3	341.3
152.5°	300.1	309.2	316.9	322.7	327.8	329.5	329.5
155°	291.7	299.1	305.0	309.4	313.3	314.3	314.8
157.5°	283.5	289.3	293.9	297.7	300.7	301.4	301.4
160°	278.4	283.4	286.8	290.2	293.2	293.2	292.7
162.5°	272.9	277.5	280.5	282.8	285.3	285.3	284.8
165°	265.2	268.6	271.0	273.0	275.0	274.5	274.5
167.5°	259.2	261.1	262.9	263.8	265.2	264.7	264.7
170°	254.9	256.8	257.8	258.3	259.3	258.8	258.8
172.5°	251.3	252.9	253.5	253.6	254.6	253.7	253.3
175°	246.5	247.5	247.5	247.5	248.0	247.5	247.0
177.5°	243.7	244.2	244.2	243.7	244.2	243.4	243.4
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6

(END OF REPORT)