

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332351-935

Luminaire Tested: **S123RDIP-S1000D1025U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332351-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D1025U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6795.0 lumens
Efficiency: N/A
Efficacy: 112.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332351-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332351-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48
1	98	93	90	86	90	86	83	80	73	70	68	60	58	57	49	47	47	41
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	40	35
3	82	72	65	59	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	64	56	51	69	59	53	47	51	45	41	42	38	35	35	32	30	26
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23
6	63	51	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20
7	59	47	39	33	54	43	36	31	37	32	28	31	27	24	26	23	21	18
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	18	16
9	51	39	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17	15
10	47	35	28	24	44	33	27	22	29	24	20	25	20	18	21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15553	15553	15553
5°	15612	15397	15486
10°	15524	15204	15152
15°	15357	14848	14692
20°	15128	14403	14068
25°	14892	13904	13459
30°	14579	13328	12599
35°	14259	12750	11811
40°	13964	12069	10835
45°	13575	11399	9954
50°	13147	10637	8967
55°	12710	9764	8049
60°	12312	8831	7037
65°	11790	7819	6029
70°	11138	6565	4869
75°	10189	5165	4579
80°	9081	4575	4209
85°	7669	4051	3767



TEST NUMBER: P332351-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.7	2.0
10°-20°	377.5	5.6
20°-30°	543.6	8.0
30°-40°	612.3	9.0
40°-50°	585.8	8.6
50°-60°	479.7	7.1
60°-70°	323.7	4.8
70°-80°	162.8	2.4
80°-90°	46.3	0.7
90°-100°	42.1	0.6
100°-110°	200.4	2.9
110°-120°	481.5	7.1
120°-130°	613.1	9.0
130°-140°	655.1	9.6
140°-150°	612.6	9.0
150°-160°	494.1	7.3
160°-170°	318.9	4.7
170°-180°	109.9	1.6
0°-30°	1056.8	15.6
0°-40°	1669.1	24.6
0°-60°	2734.6	40.2
0°-90°	3267.4	48.1
90°-120°	724.0	10.7
90°-150°	2604.6	38.3
90°-180°	3528.0	51.9
0°-180°	6795.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1445	1445	1445	1445	1445	
5°	1445	1439	1425	1435	1433	137
15°	1378	1364	1332	1326	1318	388
25°	1254	1223	1171	1147	1133	576
35°	1085	1041	970	922	899	679
45°	892	837	749	684	654	688
55°	677	618	520	455	429	607
65°	463	397	307	252	237	458
75°	245	188	124	113	110	261
85°	62	38	33	31	30	70
90°	1	10	21	24	26	6
95°	52	20	27	32	33	65
105°	256	261	188	45	38	272
115°	480	486	493	502	505	474
125°	677	684	688	689	691	605
135°	843	848	852	854	852	649
145°	973	979	981	982	982	609
155°	1072	1070	1071	1075	1070	494
165°	1130	1128	1127	1133	1128	319
175°	1157	1153	1153	1159	1152	110
180°	1157	1157	1157	1157	1157	



TEST NUMBER: P332351-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9
2.5°	1449.6	1448.7	1447.9	1447.1	1446.2	1444.6	1442.1	1439.6	1437.1	1434.6	1436.8
5°	1444.9	1443.6	1442.3	1441.0	1439.7	1437.4	1434.3	1431.2	1428.1	1425.0	1427.3
7.5°	1431.5	1430.1	1428.7	1427.3	1425.9	1423.1	1419.1	1415.1	1411.0	1407.0	1408.3
10°	1420.3	1418.5	1416.6	1414.8	1413.0	1409.7	1405.1	1400.3	1395.7	1391.0	1391.3
12.5°	1404.4	1402.3	1400.3	1398.3	1396.2	1392.3	1386.6	1380.9	1375.2	1369.4	1369.2
15°	1378.1	1375.3	1372.3	1369.5	1366.7	1361.6	1354.3	1346.9	1339.7	1332.4	1331.1
17.5°	1345.1	1341.7	1338.4	1335.1	1331.7	1325.4	1316.1	1306.9	1297.6	1288.3	1285.6
20°	1320.7	1316.6	1312.3	1308.2	1304.0	1297.0	1287.1	1277.2	1267.3	1257.4	1254.0
22.5°	1293.5	1288.7	1283.9	1279.1	1274.4	1266.7	1256.1	1245.6	1235.1	1224.6	1220.4
25°	1253.9	1247.4	1240.9	1234.3	1227.9	1218.6	1206.6	1194.6	1182.7	1170.7	1165.2
27.5°	1205.8	1198.7	1191.5	1184.3	1177.1	1166.8	1153.5	1140.1	1126.8	1113.5	1105.9
30°	1173.0	1165.2	1157.4	1149.6	1141.8	1130.6	1116.0	1101.4	1086.8	1072.3	1063.4
32.5°	1140.2	1131.4	1122.5	1113.6	1104.8	1092.7	1077.3	1061.9	1046.4	1031.0	1021.3
35°	1085.1	1075.7	1066.3	1057.0	1047.7	1034.8	1018.7	1002.5	986.4	970.3	959.1
37.5°	1029.3	1018.9	1008.5	998.1	987.7	973.9	956.7	939.4	922.1	904.9	892.2
40°	993.8	982.3	970.8	959.3	947.9	932.9	914.5	896.0	877.4	858.9	845.4
42.5°	953.4	941.9	930.5	919.0	907.6	892.3	873.2	854.1	835.0	815.9	801.1
45°	891.8	880.0	868.3	856.6	844.9	829.1	809.0	788.9	768.9	748.8	734.0
47.5°	830.2	817.3	804.4	791.5	778.7	762.2	742.2	722.1	702.1	682.0	665.9
50°	785.1	772.9	760.7	748.5	736.2	719.5	698.4	677.3	656.3	635.2	619.0
52.5°	744.9	731.6	718.2	705.0	691.7	674.6	653.8	632.8	612.0	591.1	574.3
55°	677.3	664.6	651.8	639.0	626.3	608.8	586.7	564.6	542.4	520.3	505.2
57.5°	615.0	601.1	587.2	573.3	559.4	541.3	519.0	496.8	474.6	452.4	438.1
60°	571.9	557.6	543.2	528.9	514.5	496.6	475.0	453.4	431.8	410.2	396.1
62.5°	528.7	514.4	500.1	485.8	471.5	453.5	431.9	410.3	388.7	367.0	353.8
65°	462.9	448.6	434.2	419.9	405.6	388.3	368.0	347.7	327.4	307.0	294.3
67.5°	397.0	382.5	368.1	353.6	339.1	322.1	302.6	283.2	263.7	244.2	234.7
70°	353.9	339.8	325.8	311.7	297.6	281.5	263.3	245.0	226.8	208.6	199.5
72.5°	310.7	297.0	283.1	269.2	255.4	240.1	223.6	207.1	190.5	173.9	166.4
75°	245.0	232.4	219.9	207.4	194.9	181.5	167.2	152.8	138.5	124.2	121.6
77.5°	184.9	173.6	162.3	151.0	139.7	129.4	120.2	111.0	101.8	92.6	91.2
80°	146.5	135.8	125.1	114.4	103.8	95.7	90.2	84.7	79.3	73.8	73.0
82.5°	109.9	100.7	91.5	82.2	73.0	67.2	64.6	62.1	59.5	56.9	56.1
85°	62.1	56.4	50.6	44.9	39.2	35.9	35.1	34.4	33.6	32.8	32.3
87.5°	22.6	20.8	18.9	17.0	15.1	14.3	14.8	15.3	15.8	16.3	16.3
90°	0.9	2.8	4.6	6.6	8.5	10.7	13.2	15.7	18.2	20.7	21.4
92.5°	16.0	15.4	14.9	14.4	13.9	14.6	16.4	18.3	20.1	22.0	23.2
95°	52.4	44.6	36.8	28.9	21.1	18.3	20.3	22.5	24.5	26.6	28.0
97.5°	105.4	101.9	98.3	94.8	91.3	82.7	69.0	55.2	41.4	27.6	29.2
100°	145.3	149.0	152.9	156.7	160.5	147.5	117.7	87.9	58.1	28.3	29.9
102.5°	190.6	193.4	196.1	198.9	201.6	186.8	154.2	121.7	89.1	56.6	51.8
105°	256.1	258.2	260.3	262.4	264.5	256.9	239.8	222.6	205.4	188.2	154.4
107.5°	325.2	326.9	328.6	330.3	331.9	334.2	336.8	339.6	342.2	345.0	320.2
110°	371.3	372.8	374.3	375.8	377.4	379.2	381.3	383.4	385.5	387.6	381.3



TEST NUMBER: P332351-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	415.3	416.6	418.0	419.4	420.8	422.5	424.6	426.7	428.8	430.9	431.0
115°	480.4	481.6	482.7	483.9	485.0	486.5	488.1	489.8	491.5	493.3	495.2
117.5°	543.5	544.9	546.3	547.8	549.1	550.3	551.1	552.1	552.9	553.8	555.3
120°	582.6	584.4	586.1	587.8	589.5	590.7	591.2	591.9	592.5	593.0	594.5
122.5°	622.6	624.0	625.3	626.8	628.2	629.3	630.0	630.8	631.5	632.1	633.3
125°	677.2	678.7	680.3	681.8	683.3	684.5	685.3	686.0	686.7	687.5	687.9
127.5°	730.1	731.7	733.2	734.7	736.2	737.4	738.4	739.3	740.2	741.1	741.8
130°	763.2	764.7	766.2	767.8	769.3	770.4	771.2	772.0	772.7	773.4	774.2
132.5°	794.8	796.3	797.8	799.4	800.9	801.9	802.5	803.1	803.8	804.4	805.2
135°	843.1	844.2	845.3	846.5	847.7	848.6	849.4	850.2	850.9	851.7	852.2
137.5°	884.3	885.8	887.3	888.7	890.1	891.0	891.5	891.9	892.3	892.8	893.6
140°	911.8	913.0	914.1	915.2	916.4	917.3	917.8	918.4	919.0	919.5	920.3
142.5°	937.3	938.4	939.5	940.7	941.8	942.7	943.3	943.8	944.4	945.0	945.6
145°	972.8	974.2	975.5	976.9	978.2	979.0	979.5	979.8	980.2	980.6	980.9
147.5°	1006.3	1007.3	1008.1	1009.0	1009.9	1010.5	1010.9	1011.2	1011.7	1012.0	1012.4
150°	1027.0	1027.6	1028.1	1028.7	1029.2	1029.8	1030.1	1030.5	1030.9	1031.3	1031.7
152.5°	1045.5	1045.9	1046.1	1046.4	1046.6	1046.9	1047.1	1047.3	1047.6	1047.8	1048.4
155°	1071.7	1071.3	1070.9	1070.6	1070.1	1070.1	1070.2	1070.4	1070.7	1070.8	1071.8
157.5°	1091.9	1091.9	1091.9	1091.8	1091.8	1091.7	1091.5	1091.3	1091.1	1090.9	1092.1
160°	1104.3	1104.1	1104.0	1103.8	1103.5	1103.4	1103.2	1103.0	1102.8	1102.6	1103.8
162.5°	1116.0	1115.5	1115.0	1114.6	1114.0	1113.7	1113.5	1113.3	1113.1	1112.9	1114.2
165°	1130.1	1129.5	1128.9	1128.4	1127.8	1127.5	1127.2	1127.0	1126.9	1126.7	1128.2
167.5°	1141.1	1140.4	1139.6	1138.8	1138.1	1137.6	1137.6	1137.6	1137.6	1137.6	1139.2
170°	1147.3	1146.5	1145.8	1145.0	1144.3	1143.8	1143.8	1143.8	1143.8	1143.8	1145.4
172.5°	1151.4	1150.6	1149.6	1148.7	1147.8	1147.4	1147.5	1147.7	1147.8	1148.0	1149.5
175°	1156.8	1155.8	1154.9	1153.9	1153.0	1152.5	1152.7	1153.0	1153.1	1153.3	1154.7
177.5°	1158.1	1157.4	1156.6	1155.8	1155.1	1154.8	1154.9	1155.1	1155.2	1155.4	1156.6
180°	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8



TEST NUMBER: P332351-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9
2.5°	1439.2	1441.5	1443.7	1444.7	1444.2	1443.9	1443.5	1443.0
5°	1429.7	1432.0	1434.3	1435.3	1434.8	1434.3	1433.7	1433.2
7.5°	1409.5	1410.8	1412.1	1412.4	1411.4	1410.6	1409.7	1408.8
10°	1391.5	1391.8	1392.1	1391.5	1390.2	1388.9	1387.6	1386.3
12.5°	1369.1	1369.0	1368.8	1368.0	1366.5	1364.9	1363.5	1361.9
15°	1329.8	1328.5	1327.2	1325.6	1323.8	1322.0	1320.2	1318.4
17.5°	1282.8	1280.0	1277.3	1274.5	1271.9	1269.1	1266.4	1263.7
20°	1250.6	1247.2	1243.9	1240.6	1237.5	1234.3	1231.2	1228.1
22.5°	1216.2	1211.9	1207.7	1204.1	1201.3	1198.3	1195.4	1192.5
25°	1159.8	1154.3	1148.8	1144.6	1141.8	1138.9	1136.1	1133.2
27.5°	1098.3	1090.7	1083.1	1077.1	1072.7	1068.3	1063.9	1059.6
30°	1054.6	1045.7	1036.8	1030.4	1026.1	1022.0	1017.8	1013.7
32.5°	1011.6	1001.9	992.2	985.2	980.9	976.5	972.1	967.7
35°	947.9	936.7	925.5	917.6	912.9	908.2	903.5	898.8
37.5°	879.5	866.8	854.1	844.8	839.0	833.3	827.5	821.7
40°	831.9	818.4	804.8	795.0	789.0	783.1	777.1	771.1
42.5°	786.3	771.5	756.6	746.6	741.2	735.9	730.5	725.1
45°	719.1	704.3	689.4	678.9	672.6	666.4	660.1	653.9
47.5°	649.7	633.6	617.4	606.6	601.0	595.5	589.9	584.3
50°	602.9	586.7	570.6	559.5	553.5	547.5	541.6	535.5
52.5°	557.6	540.8	524.0	512.9	507.6	502.2	496.9	491.5
55°	490.1	475.0	459.9	449.7	444.5	439.3	434.1	428.9
57.5°	423.8	409.5	395.3	385.9	381.5	377.0	372.6	368.2
60°	382.0	368.0	353.9	344.7	340.3	335.8	331.4	326.9
62.5°	340.5	327.4	314.1	305.1	300.6	295.9	291.3	286.6
65°	281.5	268.7	256.0	248.1	245.3	242.5	239.6	236.7
67.5°	225.2	215.6	206.1	199.8	196.7	193.6	190.5	187.5
70°	190.4	181.2	172.1	166.2	163.2	160.4	157.6	154.7
72.5°	159.0	151.5	144.1	139.8	138.6	137.4	136.2	135.0
75°	119.0	116.4	113.8	112.3	111.8	111.2	110.6	110.1
77.5°	89.8	88.3	87.0	86.0	85.5	85.0	84.5	83.9
80°	72.2	71.5	70.7	70.1	69.6	69.1	68.4	67.9
82.5°	55.4	54.6	53.8	53.4	53.3	53.2	53.0	53.0
85°	31.8	31.3	30.7	30.5	30.5	30.5	30.5	30.5
87.5°	16.2	16.2	16.1	16.0	15.8	15.8	15.6	15.5
90°	22.1	22.9	23.7	24.3	24.6	25.1	25.4	25.7
92.5°	24.5	25.7	26.9	27.6	27.8	28.1	28.3	28.5
95°	29.3	30.7	32.0	32.6	32.6	32.6	32.6	32.6
97.5°	30.7	32.3	33.8	34.6	34.9	35.0	35.2	35.4
100°	31.4	33.0	34.4	35.3	35.6	35.7	35.9	36.1
102.5°	47.1	42.4	37.6	35.4	35.7	36.1	36.4	36.8
105°	120.6	86.8	53.0	36.2	36.7	37.0	37.5	37.8
107.5°	295.4	270.6	245.8	220.7	195.2	169.7	144.2	118.7
110°	375.0	368.7	362.4	345.6	318.2	290.9	263.6	236.3



TEST NUMBER: P332351-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	431.1	431.3	431.4	428.5	422.8	417.0	411.2	405.4
115°	497.1	499.0	500.9	502.3	503.0	503.8	504.5	505.3
117.5°	556.9	558.4	559.9	560.8	560.9	561.0	561.2	561.4
120°	596.1	597.5	599.1	599.9	599.9	599.9	599.9	599.9
122.5°	634.3	635.4	636.5	637.1	637.2	637.4	637.5	637.7
125°	688.3	688.6	689.1	689.4	689.8	690.2	690.6	691.0
127.5°	742.4	743.0	743.6	743.7	743.3	743.0	742.5	742.2
130°	775.0	775.8	776.5	776.7	776.4	775.9	775.6	775.2
132.5°	805.9	806.7	807.4	807.5	807.0	806.5	806.0	805.5
135°	852.8	853.4	853.9	853.9	853.4	852.8	852.2	851.7
137.5°	894.6	895.5	896.4	896.6	896.3	896.0	895.5	895.2
140°	921.1	921.9	922.6	922.8	922.4	922.0	921.7	921.3
142.5°	946.2	946.8	947.4	947.4	946.9	946.4	945.9	945.4
145°	981.4	981.7	982.1	982.3	982.3	982.3	982.3	982.3
147.5°	1012.8	1013.1	1013.6	1013.3	1012.4	1011.6	1010.6	1009.8
150°	1032.1	1032.4	1032.9	1032.7	1032.2	1031.6	1031.0	1030.4
152.5°	1049.1	1049.8	1050.5	1050.4	1049.6	1048.7	1047.8	1046.9
155°	1072.7	1073.7	1074.6	1074.5	1073.4	1072.3	1071.1	1070.0
157.5°	1093.2	1094.3	1095.5	1095.4	1093.8	1092.4	1090.9	1089.4
160°	1104.9	1106.0	1107.2	1107.1	1105.8	1104.4	1103.1	1101.7
162.5°	1115.5	1116.8	1118.1	1118.2	1117.0	1115.8	1114.7	1113.4
165°	1129.7	1131.3	1132.8	1132.9	1131.5	1130.2	1128.9	1127.6
167.5°	1140.7	1142.3	1143.8	1143.8	1142.3	1140.7	1139.2	1137.6
170°	1146.9	1148.5	1150.0	1150.0	1148.5	1146.9	1145.4	1143.8
172.5°	1151.1	1152.5	1154.1	1154.0	1152.4	1150.6	1149.0	1147.3
175°	1156.0	1157.4	1158.6	1158.6	1157.0	1155.5	1154.0	1152.4
177.5°	1157.8	1159.1	1160.3	1160.1	1158.6	1157.1	1155.5	1154.0
180°	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8

(END OF REPORT)