

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332357-935

Luminaire Tested: **S123RDIP-S1000D1195U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332357-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D1195U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7373.9 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332357-935

CATALOG NUMBER: S123RDIP-S1000D1195U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332357-935

CATALOG NUMBER: S123RDIP-S1000D1195U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	93	89	85	89	85	82	79	71	68	66	58	56	55	45	44	44	38
2	88	81	75	70	81	75	70	65	62	59	55	51	48	46	40	39	37	32
3	81	72	64	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28
4	74	63	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	29	26	24	21
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21	18
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19	16
8	54	42	34	29	49	39	32	27	33	28	24	27	23	21	22	19	17	15
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	16	13
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15553	15553	15553
5°	15612	15397	15486
10°	15524	15204	15152
15°	15357	14848	14692
20°	15128	14403	14068
25°	14892	13904	13459
30°	14579	13328	12599
35°	14259	12750	11811
40°	13964	12069	10835
45°	13575	11399	9954
50°	13147	10637	8967
55°	12710	9764	8049
60°	12312	8831	7037
65°	11790	7819	6029
70°	11138	6565	4869
75°	10189	5165	4579
80°	9081	4575	4209
85°	7669	4051	3767



TEST NUMBER: P332357-935

CATALOG NUMBER: S123RDIP-S1000D1195U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.7	1.8
10°-20°	377.5	5.1
20°-30°	543.6	7.4
30°-40°	612.3	8.3
40°-50°	585.8	7.9
50°-60°	479.7	6.5
60°-70°	323.7	4.4
70°-80°	162.8	2.2
80°-90°	46.8	0.6
90°-100°	48.9	0.7
100°-110°	233.3	3.2
110°-120°	560.4	7.6
120°-130°	713.6	9.7
130°-140°	762.5	10.3
140°-150°	713.0	9.7
150°-160°	575.1	7.8
160°-170°	371.2	5.0
170°-180°	127.9	1.7
0°-30°	1056.8	14.3
0°-40°	1669.1	22.6
0°-60°	2734.6	37.1
0°-90°	3267.9	44.3
90°-120°	842.6	11.4
90°-150°	3031.7	41.1
90°-180°	4106.0	55.7
0°-180°	7373.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1445	1445	1445	1445	1445	
5°	1445	1439	1425	1435	1433	137
15°	1378	1364	1332	1326	1318	388
25°	1254	1223	1171	1147	1133	576
35°	1085	1041	970	922	899	679
45°	892	837	749	684	654	688
55°	677	618	520	455	429	607
65°	463	397	307	252	237	458
75°	245	188	124	113	110	261
85°	62	38	33	31	30	70
90°	1	11	24	28	30	6
95°	61	23	31	38	38	75
105°	298	304	219	52	44	316
115°	559	565	574	584	588	552
125°	788	796	800	802	804	704
135°	981	987	991	994	991	755
145°	1132	1139	1141	1143	1143	709
155°	1247	1246	1246	1251	1245	574
165°	1315	1313	1311	1319	1312	371
175°	1346	1342	1342	1349	1341	128
180°	1346	1346	1346	1346	1346	



TEST NUMBER: P332357-935

CATALOG NUMBER: S123RDIP-S1000D1195U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9
2.5°	1449.6	1448.7	1447.9	1447.1	1446.2	1444.6	1442.1	1439.6	1437.1	1434.6	1436.8
5°	1444.9	1443.6	1442.3	1441.0	1439.7	1437.4	1434.3	1431.2	1428.1	1425.0	1427.3
7.5°	1431.5	1430.1	1428.7	1427.3	1425.9	1423.1	1419.1	1415.1	1411.0	1407.0	1408.3
10°	1420.3	1418.5	1416.6	1414.8	1413.0	1409.7	1405.1	1400.3	1395.7	1391.0	1391.3
12.5°	1404.4	1402.3	1400.3	1398.3	1396.2	1392.3	1386.6	1380.9	1375.2	1369.4	1369.2
15°	1378.1	1375.3	1372.3	1369.5	1366.7	1361.6	1354.3	1346.9	1339.7	1332.4	1331.1
17.5°	1345.1	1341.7	1338.4	1335.1	1331.7	1325.4	1316.1	1306.9	1297.6	1288.3	1285.6
20°	1320.7	1316.6	1312.3	1308.2	1304.0	1297.0	1287.1	1277.2	1267.3	1257.4	1254.0
22.5°	1293.5	1288.7	1283.9	1279.1	1274.4	1266.7	1256.1	1245.6	1235.1	1224.6	1220.4
25°	1253.9	1247.4	1240.9	1234.3	1227.9	1218.6	1206.6	1194.6	1182.7	1170.7	1165.2
27.5°	1205.8	1198.7	1191.5	1184.3	1177.1	1166.8	1153.5	1140.1	1126.8	1113.5	1105.9
30°	1173.0	1165.2	1157.4	1149.6	1141.8	1130.6	1116.0	1101.4	1086.8	1072.3	1063.4
32.5°	1140.2	1131.4	1122.5	1113.6	1104.8	1092.7	1077.3	1061.9	1046.4	1031.0	1021.3
35°	1085.1	1075.7	1066.3	1057.0	1047.7	1034.8	1018.7	1002.5	986.4	970.3	959.1
37.5°	1029.3	1018.9	1008.5	998.1	987.7	973.9	956.7	939.4	922.1	904.9	892.2
40°	993.8	982.3	970.8	959.3	947.9	932.9	914.5	896.0	877.4	858.9	845.4
42.5°	953.4	941.9	930.5	919.0	907.6	892.3	873.2	854.1	835.0	815.9	801.1
45°	891.8	880.0	868.3	856.6	844.9	829.1	809.0	788.9	768.9	748.8	734.0
47.5°	830.2	817.3	804.4	791.5	778.7	762.2	742.2	722.1	702.1	682.0	665.9
50°	785.1	772.9	760.7	748.5	736.2	719.5	698.4	677.3	656.3	635.2	619.0
52.5°	744.9	731.6	718.2	705.0	691.7	674.6	653.8	632.8	612.0	591.1	574.3
55°	677.3	664.6	651.8	639.0	626.3	608.8	586.7	564.6	542.4	520.3	505.2
57.5°	615.0	601.1	587.2	573.3	559.4	541.3	519.0	496.8	474.6	452.4	438.1
60°	571.9	557.6	543.2	528.9	514.5	496.6	475.0	453.4	431.8	410.2	396.1
62.5°	528.7	514.4	500.1	485.8	471.5	453.5	431.9	410.3	388.7	367.0	353.8
65°	462.9	448.6	434.2	419.9	405.6	388.3	368.0	347.7	327.4	307.0	294.3
67.5°	397.0	382.5	368.1	353.6	339.1	322.1	302.6	283.2	263.7	244.2	234.7
70°	353.9	339.8	325.8	311.7	297.6	281.5	263.3	245.0	226.8	208.6	199.5
72.5°	310.7	297.0	283.1	269.2	255.4	240.1	223.6	207.1	190.5	173.9	166.4
75°	245.0	232.4	219.9	207.4	194.9	181.5	167.2	152.8	138.5	124.2	121.6
77.5°	184.9	173.6	162.3	151.0	139.7	129.4	120.2	111.0	101.8	92.6	91.2
80°	146.5	135.8	125.1	114.4	103.8	95.7	90.2	84.7	79.3	73.8	73.0
82.5°	109.9	100.7	91.5	82.2	73.0	67.2	64.6	62.1	59.5	56.9	56.1
85°	62.1	56.4	50.6	44.9	39.2	35.9	35.1	34.4	33.6	32.8	32.3
87.5°	22.7	20.8	19.0	17.1	15.3	14.6	15.2	15.8	16.4	17.0	17.0
90°	1.0	3.2	5.4	7.7	9.9	12.5	15.3	18.3	21.1	24.0	24.9
92.5°	18.6	18.0	17.4	16.7	16.1	16.9	19.1	21.3	23.4	25.6	27.0
95°	61.0	51.9	42.8	33.7	24.5	21.3	23.7	26.1	28.6	31.0	32.5
97.5°	122.6	118.6	114.4	110.4	106.2	96.3	80.2	64.2	48.2	32.2	34.0
100°	169.0	173.5	178.0	182.4	186.8	171.7	137.1	102.4	67.7	33.0	34.8
102.5°	221.9	225.1	228.3	231.4	234.7	217.3	179.4	141.5	103.7	65.8	60.3
105°	298.1	300.6	303.0	305.4	307.9	299.1	279.1	259.1	239.1	219.0	179.7
107.5°	378.5	380.5	382.5	384.4	386.3	388.9	392.1	395.2	398.4	401.6	372.6
110°	432.1	433.9	435.7	437.5	439.3	441.3	443.8	446.3	448.7	451.2	443.8



TEST NUMBER: P332357-935

CATALOG NUMBER: S123RDIP-S1000D1195U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	483.4	484.9	486.6	488.2	489.7	491.8	494.2	496.7	499.1	501.5	501.7
115°	559.2	560.5	561.8	563.2	564.5	566.2	568.2	570.2	572.2	574.2	576.4
117.5°	632.6	634.2	635.8	637.6	639.2	640.5	641.5	642.6	643.6	644.6	646.4
120°	678.2	680.2	682.3	684.2	686.2	687.6	688.2	688.9	689.6	690.2	692.0
122.5°	724.6	726.3	727.9	729.5	731.2	732.5	733.3	734.2	734.9	735.8	737.1
125°	788.2	790.1	791.8	793.6	795.4	796.7	797.5	798.5	799.4	800.2	800.7
127.5°	849.9	851.6	853.4	855.2	857.0	858.4	859.5	860.6	861.6	862.6	863.4
130°	888.3	890.1	891.8	893.6	895.4	896.7	897.6	898.5	899.4	900.3	901.2
132.5°	925.1	926.9	928.7	930.4	932.2	933.4	934.2	934.9	935.6	936.3	937.2
135°	981.3	982.7	984.0	985.3	986.6	987.7	988.7	989.5	990.4	991.4	992.0
137.5°	1029.3	1031.0	1032.7	1034.4	1036.1	1037.2	1037.7	1038.2	1038.6	1039.1	1040.2
140°	1061.4	1062.6	1064.0	1065.3	1066.7	1067.6	1068.3	1069.0	1069.7	1070.3	1071.3
142.5°	1091.0	1092.3	1093.6	1094.9	1096.3	1097.3	1097.9	1098.6	1099.3	1099.9	1100.7
145°	1132.4	1133.9	1135.5	1137.0	1138.6	1139.6	1140.1	1140.5	1140.9	1141.3	1141.8
147.5°	1171.4	1172.4	1173.5	1174.4	1175.4	1176.2	1176.6	1177.1	1177.5	1177.9	1178.5
150°	1195.4	1196.0	1196.7	1197.4	1198.1	1198.6	1199.0	1199.5	1200.0	1200.4	1200.8
152.5°	1217.0	1217.3	1217.6	1217.9	1218.2	1218.5	1218.7	1219.1	1219.3	1219.6	1220.4
155°	1247.4	1247.0	1246.5	1246.0	1245.6	1245.5	1245.7	1246.0	1246.2	1246.4	1247.5
157.5°	1271.0	1270.9	1270.9	1270.8	1270.8	1270.7	1270.5	1270.2	1270.1	1269.8	1271.2
160°	1285.4	1285.2	1285.0	1284.8	1284.5	1284.3	1284.1	1283.8	1283.7	1283.4	1284.8
162.5°	1299.0	1298.5	1297.9	1297.3	1296.7	1296.3	1296.1	1295.9	1295.6	1295.4	1296.9
165°	1315.4	1314.7	1314.1	1313.5	1312.8	1312.3	1312.1	1311.8	1311.6	1311.4	1313.2
167.5°	1328.3	1327.3	1326.5	1325.6	1324.6	1324.2	1324.2	1324.2	1324.2	1324.2	1326.0
170°	1335.4	1334.6	1333.7	1332.7	1331.9	1331.5	1331.5	1331.5	1331.5	1331.5	1333.2
172.5°	1340.2	1339.2	1338.1	1337.0	1335.9	1335.5	1335.7	1335.8	1336.0	1336.2	1338.0
175°	1346.4	1345.3	1344.2	1343.1	1342.0	1341.5	1341.8	1342.0	1342.2	1342.4	1344.0
177.5°	1348.1	1347.1	1346.3	1345.4	1344.5	1344.1	1344.3	1344.5	1344.6	1344.8	1346.3
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P332357-935

CATALOG NUMBER: S123RDIP-S1000D1195U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9
2.5°	1439.2	1441.5	1443.7	1444.7	1444.2	1443.9	1443.5	1443.0
5°	1429.7	1432.0	1434.3	1435.3	1434.8	1434.3	1433.7	1433.2
7.5°	1409.5	1410.8	1412.1	1412.4	1411.4	1410.6	1409.7	1408.8
10°	1391.5	1391.8	1392.1	1391.5	1390.2	1388.9	1387.6	1386.3
12.5°	1369.1	1369.0	1368.8	1368.0	1366.5	1364.9	1363.5	1361.9
15°	1329.8	1328.5	1327.2	1325.6	1323.8	1322.0	1320.2	1318.4
17.5°	1282.8	1280.0	1277.3	1274.5	1271.9	1269.1	1266.4	1263.7
20°	1250.6	1247.2	1243.9	1240.6	1237.5	1234.3	1231.2	1228.1
22.5°	1216.2	1211.9	1207.7	1204.1	1201.3	1198.3	1195.4	1192.5
25°	1159.8	1154.3	1148.8	1144.6	1141.8	1138.9	1136.1	1133.2
27.5°	1098.3	1090.7	1083.1	1077.1	1072.7	1068.3	1063.9	1059.6
30°	1054.6	1045.7	1036.8	1030.4	1026.1	1022.0	1017.8	1013.7
32.5°	1011.6	1001.9	992.2	985.2	980.9	976.5	972.1	967.7
35°	947.9	936.7	925.5	917.6	912.9	908.2	903.5	898.8
37.5°	879.5	866.8	854.1	844.8	839.0	833.3	827.5	821.7
40°	831.9	818.4	804.8	795.0	789.0	783.1	777.1	771.1
42.5°	786.3	771.5	756.6	746.6	741.2	735.9	730.5	725.1
45°	719.1	704.3	689.4	678.9	672.6	666.4	660.1	653.9
47.5°	649.7	633.6	617.4	606.6	601.0	595.5	589.9	584.3
50°	602.9	586.7	570.6	559.5	553.5	547.5	541.6	535.5
52.5°	557.6	540.8	524.0	512.9	507.6	502.2	496.9	491.5
55°	490.1	475.0	459.9	449.7	444.5	439.3	434.1	428.9
57.5°	423.8	409.5	395.3	385.9	381.5	377.0	372.6	368.2
60°	382.0	368.0	353.9	344.7	340.3	335.8	331.4	326.9
62.5°	340.5	327.4	314.1	305.1	300.6	295.9	291.3	286.6
65°	281.5	268.7	256.0	248.1	245.3	242.5	239.6	236.7
67.5°	225.2	215.6	206.1	199.8	196.7	193.6	190.5	187.5
70°	190.4	181.2	172.1	166.2	163.2	160.4	157.6	154.7
72.5°	159.0	151.5	144.1	139.8	138.6	137.4	136.2	135.0
75°	119.0	116.4	113.8	112.3	111.8	111.2	110.6	110.1
77.5°	89.8	88.3	87.0	86.0	85.5	85.0	84.5	83.9
80°	72.2	71.5	70.7	70.1	69.6	69.1	68.4	67.9
82.5°	55.4	54.6	53.8	53.4	53.3	53.2	53.0	53.0
85°	31.8	31.3	30.7	30.5	30.5	30.5	30.5	30.5
87.5°	17.0	16.9	16.9	16.8	16.7	16.5	16.4	16.3
90°	25.7	26.7	27.6	28.2	28.7	29.1	29.5	30.0
92.5°	28.4	29.9	31.3	32.1	32.4	32.7	33.0	33.2
95°	34.1	35.6	37.2	38.0	38.0	38.0	38.0	38.0
97.5°	35.7	37.5	39.3	40.3	40.6	40.8	41.0	41.2
100°	36.6	38.3	40.1	41.2	41.3	41.6	41.8	42.0
102.5°	54.8	49.2	43.7	41.2	41.6	42.0	42.4	42.8
105°	140.3	101.0	61.6	42.3	42.7	43.1	43.6	44.0
107.5°	343.8	315.0	286.1	256.8	227.2	197.5	167.9	138.3
110°	436.4	429.1	421.8	402.3	370.5	338.6	306.9	275.1



TEST NUMBER: P332357-935

CATALOG NUMBER: S123RDIP-S1000D1195U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	501.8	502.0	502.1	498.8	492.1	485.3	478.6	471.9
115°	578.6	580.8	583.1	584.6	585.5	586.4	587.3	588.1
117.5°	648.2	650.0	651.7	652.7	652.9	653.1	653.2	653.4
120°	693.8	695.5	697.3	698.2	698.2	698.2	698.2	698.2
122.5°	738.3	739.6	740.8	741.5	741.7	741.8	742.1	742.3
125°	801.2	801.6	802.0	802.5	802.9	803.4	803.8	804.3
127.5°	864.1	864.8	865.5	865.6	865.2	864.8	864.4	863.8
130°	902.1	902.9	903.9	904.0	903.6	903.2	902.8	902.3
132.5°	938.1	939.0	939.9	940.0	939.4	938.7	938.1	937.5
135°	992.6	993.3	994.0	994.0	993.3	992.6	992.0	991.4
137.5°	1041.3	1042.3	1043.4	1043.7	1043.3	1042.8	1042.4	1041.9
140°	1072.1	1073.0	1073.9	1074.1	1073.7	1073.2	1072.8	1072.4
142.5°	1101.4	1102.1	1102.8	1102.9	1102.3	1101.6	1101.0	1100.4
145°	1142.3	1142.7	1143.1	1143.3	1143.3	1143.3	1143.3	1143.3
147.5°	1178.9	1179.3	1179.7	1179.5	1178.5	1177.4	1176.4	1175.4
150°	1201.3	1201.7	1202.1	1202.0	1201.4	1200.8	1200.1	1199.4
152.5°	1221.2	1222.0	1222.8	1222.7	1221.7	1220.6	1219.6	1218.6
155°	1248.6	1249.7	1250.9	1250.7	1249.4	1248.1	1246.7	1245.4
157.5°	1272.5	1273.8	1275.1	1275.0	1273.2	1271.4	1269.7	1268.0
160°	1286.1	1287.4	1288.7	1288.7	1287.1	1285.6	1283.9	1282.4
162.5°	1298.5	1299.9	1301.5	1301.5	1300.1	1298.7	1297.4	1296.0
165°	1315.0	1316.7	1318.5	1318.6	1317.1	1315.5	1314.0	1312.4
167.5°	1327.7	1329.6	1331.4	1331.4	1329.6	1327.7	1326.0	1324.2
170°	1335.0	1336.8	1338.5	1338.5	1336.8	1335.0	1333.2	1331.5
172.5°	1339.8	1341.5	1343.3	1343.2	1341.3	1339.4	1337.4	1335.4
175°	1345.6	1347.1	1348.7	1348.5	1346.8	1345.0	1343.2	1341.4
177.5°	1347.6	1349.1	1350.5	1350.3	1348.6	1346.8	1345.0	1343.2
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4

(END OF REPORT)