

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332345-935

Luminaire Tested: **S123RDIP-S1000D805U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332345-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D805U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6029.7 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332345-935

CATALOG NUMBER: S123RDIP-S1000D805U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332345-935

CATALOG NUMBER: S123RDIP-S1000D805U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	54	52	51	46
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	39
3	83	73	66	61	77	68	62	57	59	54	50	50	47	44	42	40	38	34
4	76	65	57	51	70	61	54	49	53	47	43	45	41	38	38	35	33	29
5	70	58	50	44	65	55	47	42	47	42	37	41	36	33	34	31	29	26
6	64	52	44	39	60	49	42	37	43	37	33	37	32	29	31	28	25	23
7	60	47	40	34	55	45	37	32	39	33	29	34	29	26	29	25	23	20
8	55	43	36	30	51	41	34	29	36	30	26	31	26	23	26	23	20	18
9	52	40	32	27	48	37	30	26	33	27	23	28	24	21	24	21	19	16
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15553	15553	15553
5°	15612	15397	15486
10°	15524	15204	15152
15°	15357	14848	14692
20°	15128	14403	14068
25°	14892	13904	13459
30°	14579	13328	12599
35°	14259	12750	11811
40°	13964	12069	10835
45°	13575	11399	9954
50°	13147	10637	8967
55°	12710	9764	8049
60°	12312	8831	7037
65°	11790	7819	6029
70°	11138	6565	4869
75°	10189	5165	4579
80°	9081	4575	4209
85°	7669	4051	3767



TEST NUMBER: P332345-935

CATALOG NUMBER: S123RDIP-S1000D805U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.7	2.3
10°-20°	377.5	6.3
20°-30°	543.6	9.0
30°-40°	612.3	10.2
40°-50°	585.8	9.7
50°-60°	479.7	8.0
60°-70°	323.7	5.4
70°-80°	162.8	2.7
80°-90°	45.6	0.8
90°-100°	32.9	0.5
100°-110°	157.0	2.6
110°-120°	377.1	6.3
120°-130°	480.2	8.0
130°-140°	513.1	8.5
140°-150°	479.8	8.0
150°-160°	387.0	6.4
160°-170°	249.8	4.1
170°-180°	86.1	1.4
0°-30°	1056.8	17.5
0°-40°	1669.1	27.7
0°-60°	2734.6	45.4
0°-90°	3266.7	54.2
90°-120°	567.0	9.4
90°-150°	2040.1	33.8
90°-180°	2763.0	45.8
0°-180°	6029.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1445	1445	1445	1445	1445	
5°	1445	1439	1425	1435	1433	137
15°	1378	1364	1332	1326	1318	388
25°	1254	1223	1171	1147	1133	576
35°	1085	1041	970	922	899	679
45°	892	837	749	684	654	688
55°	677	618	520	455	429	607
65°	463	397	307	252	237	458
75°	245	188	124	113	110	261
85°	62	38	33	31	30	70
90°	1	8	16	19	20	5
95°	41	15	21	25	26	51
105°	201	204	147	35	30	213
115°	376	380	386	393	396	371
125°	530	536	538	540	541	474
135°	660	664	667	669	667	508
145°	762	766	768	769	769	477
155°	839	838	839	842	838	387
165°	885	883	882	887	883	250
175°	906	903	903	907	903	86
180°	906	906	906	906	906	



TEST NUMBER: P332345-935

CATALOG NUMBER: S123RDIP-S1000D805U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9
2.5°	1449.6	1448.7	1447.9	1447.1	1446.2	1444.6	1442.1	1439.6	1437.1	1434.6	1436.8
5°	1444.9	1443.6	1442.3	1441.0	1439.7	1437.4	1434.3	1431.2	1428.1	1425.0	1427.3
7.5°	1431.5	1430.1	1428.7	1427.3	1425.9	1423.1	1419.1	1415.1	1411.0	1407.0	1408.3
10°	1420.3	1418.5	1416.6	1414.8	1413.0	1409.7	1405.1	1400.3	1395.7	1391.0	1391.3
12.5°	1404.4	1402.3	1400.3	1398.3	1396.2	1392.3	1386.6	1380.9	1375.2	1369.4	1369.2
15°	1378.1	1375.3	1372.3	1369.5	1366.7	1361.6	1354.3	1346.9	1339.7	1332.4	1331.1
17.5°	1345.1	1341.7	1338.4	1335.1	1331.7	1325.4	1316.1	1306.9	1297.6	1288.3	1285.6
20°	1320.7	1316.6	1312.3	1308.2	1304.0	1297.0	1287.1	1277.2	1267.3	1257.4	1254.0
22.5°	1293.5	1288.7	1283.9	1279.1	1274.4	1266.7	1256.1	1245.6	1235.1	1224.6	1220.4
25°	1253.9	1247.4	1240.9	1234.3	1227.9	1218.6	1206.6	1194.6	1182.7	1170.7	1165.2
27.5°	1205.8	1198.7	1191.5	1184.3	1177.1	1166.8	1153.5	1140.1	1126.8	1113.5	1105.9
30°	1173.0	1165.2	1157.4	1149.6	1141.8	1130.6	1116.0	1101.4	1086.8	1072.3	1063.4
32.5°	1140.2	1131.4	1122.5	1113.6	1104.8	1092.7	1077.3	1061.9	1046.4	1031.0	1021.3
35°	1085.1	1075.7	1066.3	1057.0	1047.7	1034.8	1018.7	1002.5	986.4	970.3	959.1
37.5°	1029.3	1018.9	1008.5	998.1	987.7	973.9	956.7	939.4	922.1	904.9	892.2
40°	993.8	982.3	970.8	959.3	947.9	932.9	914.5	896.0	877.4	858.9	845.4
42.5°	953.4	941.9	930.5	919.0	907.6	892.3	873.2	854.1	835.0	815.9	801.1
45°	891.8	880.0	868.3	856.6	844.9	829.1	809.0	788.9	768.9	748.8	734.0
47.5°	830.2	817.3	804.4	791.5	778.7	762.2	742.2	722.1	702.1	682.0	665.9
50°	785.1	772.9	760.7	748.5	736.2	719.5	698.4	677.3	656.3	635.2	619.0
52.5°	744.9	731.6	718.2	705.0	691.7	674.6	653.8	632.8	612.0	591.1	574.3
55°	677.3	664.6	651.8	639.0	626.3	608.8	586.7	564.6	542.4	520.3	505.2
57.5°	615.0	601.1	587.2	573.3	559.4	541.3	519.0	496.8	474.6	452.4	438.1
60°	571.9	557.6	543.2	528.9	514.5	496.6	475.0	453.4	431.8	410.2	396.1
62.5°	528.7	514.4	500.1	485.8	471.5	453.5	431.9	410.3	388.7	367.0	353.8
65°	462.9	448.6	434.2	419.9	405.6	388.3	368.0	347.7	327.4	307.0	294.3
67.5°	397.0	382.5	368.1	353.6	339.1	322.1	302.6	283.2	263.7	244.2	234.7
70°	353.9	339.8	325.8	311.7	297.6	281.5	263.3	245.0	226.8	208.6	199.5
72.5°	310.7	297.0	283.1	269.2	255.4	240.1	223.6	207.1	190.5	173.9	166.4
75°	245.0	232.4	219.9	207.4	194.9	181.5	167.2	152.8	138.5	124.2	121.6
77.5°	184.9	173.6	162.3	151.0	139.7	129.4	120.2	111.0	101.8	92.6	91.2
80°	146.5	135.8	125.1	114.4	103.8	95.7	90.2	84.7	79.3	73.8	73.0
82.5°	109.9	100.7	91.5	82.2	73.0	67.2	64.6	62.1	59.5	56.9	56.1
85°	62.1	56.4	50.6	44.9	39.2	35.9	35.1	34.4	33.6	32.8	32.3
87.5°	22.6	20.7	18.7	16.6	14.6	13.9	14.3	14.6	15.1	15.4	15.3
90°	0.7	2.2	3.7	5.2	6.6	8.4	10.3	12.2	14.2	16.2	16.8
92.5°	12.5	12.1	11.7	11.3	10.8	11.4	12.8	14.3	15.8	17.2	18.2
95°	41.1	35.0	28.8	22.6	16.5	14.3	15.9	17.6	19.2	20.8	22.0
97.5°	82.5	79.8	77.1	74.3	71.5	64.7	54.0	43.2	32.5	21.7	22.9
100°	113.7	116.8	119.8	122.7	125.7	115.5	92.2	68.9	45.5	22.2	23.4
102.5°	149.3	151.4	153.6	155.8	157.9	146.3	120.8	95.2	69.7	44.3	40.6
105°	200.6	202.2	203.9	205.5	207.2	201.3	187.8	174.4	160.8	147.4	121.0
107.5°	254.7	256.1	257.4	258.6	259.9	261.7	263.8	266.0	268.0	270.2	250.8
110°	290.8	292.0	293.2	294.4	295.6	297.0	298.7	300.3	302.0	303.6	298.7



TEST NUMBER: P332345-935

CATALOG NUMBER: S123RDIP-S1000D805U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	325.3	326.3	327.4	328.5	329.6	330.9	332.6	334.2	335.9	337.5	337.6
115°	376.3	377.2	378.1	379.0	379.9	381.0	382.4	383.7	385.0	386.4	387.9
117.5°	425.7	426.8	427.9	429.0	430.1	431.0	431.7	432.4	433.1	433.8	435.0
120°	456.4	457.7	459.1	460.4	461.8	462.7	463.1	463.6	464.0	464.4	465.6
122.5°	487.6	488.7	489.8	490.9	492.1	492.8	493.4	494.0	494.6	495.2	496.0
125°	530.5	531.6	532.8	534.0	535.2	536.1	536.7	537.3	537.9	538.5	538.8
127.5°	571.9	573.1	574.3	575.5	576.7	577.6	578.3	579.1	579.8	580.5	581.0
130°	597.7	598.9	600.1	601.3	602.5	603.4	604.0	604.6	605.2	605.8	606.4
132.5°	622.5	623.7	624.9	626.1	627.3	628.1	628.6	629.0	629.6	630.1	630.7
135°	660.3	661.2	662.1	663.1	663.9	664.7	665.3	665.9	666.5	667.1	667.5
137.5°	692.7	693.8	694.9	696.0	697.2	697.9	698.3	698.6	698.9	699.2	700.0
140°	714.2	715.1	716.0	716.9	717.8	718.4	718.9	719.4	719.8	720.2	720.8
142.5°	734.1	735.0	735.9	736.8	737.7	738.4	738.8	739.3	739.7	740.2	740.6
145°	762.0	763.0	764.1	765.1	766.2	766.8	767.2	767.4	767.8	768.0	768.4
147.5°	788.2	788.9	789.6	790.3	791.0	791.5	791.8	792.0	792.4	792.6	793.0
150°	804.3	804.9	805.3	805.7	806.2	806.6	806.8	807.2	807.4	807.8	808.0
152.5°	818.9	819.2	819.3	819.6	819.8	819.9	820.1	820.3	820.5	820.7	821.2
155°	839.4	839.1	838.8	838.5	838.2	838.1	838.3	838.4	838.5	838.7	839.5
157.5°	855.2	855.2	855.2	855.1	855.1	855.1	854.9	854.8	854.6	854.5	855.4
160°	865.0	864.8	864.7	864.5	864.4	864.2	864.1	863.9	863.8	863.6	864.5
162.5°	874.1	873.7	873.3	873.0	872.5	872.3	872.1	872.0	871.8	871.7	872.7
165°	885.2	884.7	884.2	883.8	883.4	883.0	883.0	882.8	882.6	882.4	883.6
167.5°	893.8	893.2	892.6	892.0	891.4	891.0	891.0	891.0	891.0	891.0	892.3
170°	898.6	898.0	897.4	896.8	896.2	896.0	896.0	896.0	896.0	896.0	897.2
172.5°	901.8	901.1	900.4	899.7	899.0	898.7	898.8	898.9	899.1	899.1	900.3
175°	906.0	905.3	904.6	903.8	903.0	902.8	902.8	903.0	903.2	903.4	904.4
177.5°	907.1	906.5	905.9	905.3	904.7	904.5	904.6	904.7	904.8	904.9	905.9
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P332345-935

CATALOG NUMBER: S123RDIP-S1000D805U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9
2.5°	1439.2	1441.5	1443.7	1444.7	1444.2	1443.9	1443.5	1443.0
5°	1429.7	1432.0	1434.3	1435.3	1434.8	1434.3	1433.7	1433.2
7.5°	1409.5	1410.8	1412.1	1412.4	1411.4	1410.6	1409.7	1408.8
10°	1391.5	1391.8	1392.1	1391.5	1390.2	1388.9	1387.6	1386.3
12.5°	1369.1	1369.0	1368.8	1368.0	1366.5	1364.9	1363.5	1361.9
15°	1329.8	1328.5	1327.2	1325.6	1323.8	1322.0	1320.2	1318.4
17.5°	1282.8	1280.0	1277.3	1274.5	1271.9	1269.1	1266.4	1263.7
20°	1250.6	1247.2	1243.9	1240.6	1237.5	1234.3	1231.2	1228.1
22.5°	1216.2	1211.9	1207.7	1204.1	1201.3	1198.3	1195.4	1192.5
25°	1159.8	1154.3	1148.8	1144.6	1141.8	1138.9	1136.1	1133.2
27.5°	1098.3	1090.7	1083.1	1077.1	1072.7	1068.3	1063.9	1059.6
30°	1054.6	1045.7	1036.8	1030.4	1026.1	1022.0	1017.8	1013.7
32.5°	1011.6	1001.9	992.2	985.2	980.9	976.5	972.1	967.7
35°	947.9	936.7	925.5	917.6	912.9	908.2	903.5	898.8
37.5°	879.5	866.8	854.1	844.8	839.0	833.3	827.5	821.7
40°	831.9	818.4	804.8	795.0	789.0	783.1	777.1	771.1
42.5°	786.3	771.5	756.6	746.6	741.2	735.9	730.5	725.1
45°	719.1	704.3	689.4	678.9	672.6	666.4	660.1	653.9
47.5°	649.7	633.6	617.4	606.6	601.0	595.5	589.9	584.3
50°	602.9	586.7	570.6	559.5	553.5	547.5	541.6	535.5
52.5°	557.6	540.8	524.0	512.9	507.6	502.2	496.9	491.5
55°	490.1	475.0	459.9	449.7	444.5	439.3	434.1	428.9
57.5°	423.8	409.5	395.3	385.9	381.5	377.0	372.6	368.2
60°	382.0	368.0	353.9	344.7	340.3	335.8	331.4	326.9
62.5°	340.5	327.4	314.1	305.1	300.6	295.9	291.3	286.6
65°	281.5	268.7	256.0	248.1	245.3	242.5	239.6	236.7
67.5°	225.2	215.6	206.1	199.8	196.7	193.6	190.5	187.5
70°	190.4	181.2	172.1	166.2	163.2	160.4	157.6	154.7
72.5°	159.0	151.5	144.1	139.8	138.6	137.4	136.2	135.0
75°	119.0	116.4	113.8	112.3	111.8	111.2	110.6	110.1
77.5°	89.8	88.3	87.0	86.0	85.5	85.0	84.5	83.9
80°	72.2	71.5	70.7	70.1	69.6	69.1	68.4	67.9
82.5°	55.4	54.6	53.8	53.4	53.3	53.2	53.0	53.0
85°	31.8	31.3	30.7	30.5	30.5	30.5	30.5	30.5
87.5°	15.2	15.2	15.1	15.0	14.8	14.6	14.5	14.4
90°	17.4	17.9	18.5	19.0	19.3	19.6	19.9	20.2
92.5°	19.1	20.1	21.1	21.6	21.8	22.0	22.1	22.4
95°	23.0	24.0	25.1	25.6	25.6	25.6	25.6	25.6
97.5°	24.1	25.2	26.4	27.1	27.3	27.5	27.6	27.7
100°	24.6	25.8	27.0	27.6	27.8	28.0	28.2	28.2
102.5°	36.9	33.1	29.4	27.7	28.0	28.2	28.5	28.8
105°	94.5	68.0	41.5	28.4	28.8	29.0	29.4	29.6
107.5°	231.4	212.0	192.5	172.8	152.9	132.9	113.0	93.0
110°	293.7	288.8	283.9	270.7	249.3	227.9	206.5	185.1



TEST NUMBER: P332345-935

CATALOG NUMBER: S123RDIP-S1000D805U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	337.7	337.8	337.9	335.6	331.1	326.6	322.1	317.6
115°	389.3	390.9	392.4	393.4	394.0	394.6	395.2	395.8
117.5°	436.2	437.4	438.5	439.2	439.4	439.5	439.5	439.7
120°	466.8	468.0	469.2	469.8	469.8	469.8	469.8	469.8
122.5°	496.8	497.7	498.5	498.9	499.1	499.2	499.4	499.5
125°	539.1	539.4	539.7	540.0	540.3	540.6	540.9	541.2
127.5°	581.4	581.9	582.4	582.5	582.2	581.9	581.6	581.3
130°	607.0	607.6	608.2	608.4	608.0	607.8	607.4	607.2
132.5°	631.2	631.8	632.4	632.5	632.1	631.7	631.3	630.9
135°	668.0	668.4	668.8	668.8	668.4	668.0	667.5	667.1
137.5°	700.7	701.4	702.1	702.3	702.1	701.7	701.5	701.1
140°	721.4	722.0	722.6	722.8	722.5	722.2	721.9	721.6
142.5°	741.1	741.6	742.1	742.1	741.7	741.2	740.9	740.5
145°	768.6	769.0	769.2	769.4	769.4	769.4	769.4	769.4
147.5°	793.2	793.6	793.8	793.7	793.0	792.3	791.6	790.9
150°	808.3	808.7	808.9	808.9	808.4	808.0	807.5	807.1
152.5°	821.7	822.3	822.9	822.8	822.1	821.4	820.7	820.0
155°	840.2	840.9	841.7	841.6	840.8	839.8	839.0	838.0
157.5°	856.3	857.1	858.1	857.9	856.8	855.6	854.5	853.3
160°	865.4	866.3	867.2	867.1	866.1	865.0	864.0	863.0
162.5°	873.7	874.8	875.7	875.8	874.9	873.9	873.1	872.1
165°	884.8	886.1	887.3	887.3	886.3	885.2	884.2	883.1
167.5°	893.5	894.7	895.9	895.9	894.7	893.5	892.3	891.0
170°	898.3	899.5	900.7	900.7	899.5	898.3	897.2	896.0
172.5°	901.6	902.8	904.0	903.9	902.6	901.3	899.9	898.6
175°	905.4	906.5	907.5	907.4	906.3	905.1	903.9	902.7
177.5°	906.9	907.8	908.8	908.7	907.5	906.3	905.1	903.9
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0

(END OF REPORT)