

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332364-935

Luminaire Tested: **S123RDIP-S1165D365U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332364-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D365U935-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4844.2 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332364-935

CATALOG NUMBER: S123RDIP-S1165D365U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332364-935

CATALOG NUMBER: S123RDIP-S1165D365U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	78
1	105	100	96	93	100	96	92	89	88	85	82	80	78	76	73	72	70	67
2	96	88	82	77	91	84	79	74	77	73	69	71	67	64	65	62	60	57
3	88	78	71	65	83	75	68	63	69	63	59	63	59	55	58	54	51	48
4	80	69	61	55	77	67	59	54	61	55	51	57	52	48	52	48	45	42
5	74	62	54	48	71	60	52	47	55	49	44	51	46	42	47	43	39	37
6	69	56	48	42	65	54	46	41	50	44	39	46	41	37	43	38	35	32
7	64	51	43	37	61	49	42	36	46	39	35	42	37	33	39	35	31	29
8	59	47	39	33	57	45	38	32	42	36	31	39	34	30	36	32	28	26
9	55	43	35	30	53	41	34	29	39	32	28	36	31	27	34	29	26	24
10	52	40	32	27	50	38	31	27	36	30	25	33	28	24	31	27	23	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17963	17963	17963
5°	18031	17782	17884
10°	17930	17559	17500
15°	17736	17149	16967
20°	17472	16635	16247
25°	17199	16057	15543
30°	16839	15392	14551
35°	16469	14725	13641
40°	16127	13939	12513
45°	15678	13164	11496
50°	15185	12285	10357
55°	14681	11277	9295
60°	14219	10198	8129
65°	13616	9032	6963
70°	12862	7582	5624
75°	11761	5964	5294
80°	10488	5281	4866
85°	8855	4681	4347



TEST NUMBER: P332364-935

CATALOG NUMBER: S123RDIP-S1165D365U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.7	3.2
10°-20°	436.0	9.0
20°-30°	627.8	13.0
30°-40°	707.2	14.6
40°-50°	676.5	14.0
50°-60°	554.0	11.4
60°-70°	373.8	7.7
70°-80°	188.1	3.9
80°-90°	50.9	1.1
90°-100°	25.2	0.5
100°-110°	75.5	1.6
110°-120°	128.5	2.7
120°-130°	169.0	3.5
130°-140°	189.9	3.9
140°-150°	186.7	3.9
150°-160°	157.2	3.2
160°-170°	104.6	2.2
170°-180°	36.6	0.8
0°-30°	1220.5	25.2
0°-40°	1927.7	39.8
0°-60°	3158.3	65.2
0°-90°	3771.0	77.8
90°-120°	229.2	4.7
90°-150°	774.8	16.0
90°-180°	1073.0	22.2
0°-180°	4844.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1669	1669	1669	1669	1669	
5°	1669	1662	1646	1657	1655	158
15°	1592	1575	1539	1532	1523	448
25°	1448	1413	1352	1324	1309	666
35°	1253	1203	1121	1064	1038	784
45°	1030	967	865	790	755	794
55°	782	713	601	525	495	701
65°	535	458	355	291	273	529
75°	283	217	143	131	127	302
85°	72	43	38	35	35	81
90°	0	3	7	8	9	5
95°	18	20	23	24	24	20
105°	68	69	72	72	72	73
115°	129	130	130	130	130	128
125°	189	190	190	188	187	169
135°	246	247	247	246	245	189
145°	298	298	299	299	298	186
155°	341	341	341	342	340	157
165°	372	371	371	372	370	105
175°	386	385	385	387	385	37
180°	387	387	387	387	387	



TEST NUMBER: P332364-935

CATALOG NUMBER: S123RDIP-S1165D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1674.2	1673.2	1672.2	1671.3	1670.3	1668.4	1665.5	1662.6	1659.7	1656.8	1659.5
5°	1668.8	1667.2	1665.8	1664.2	1662.8	1660.2	1656.6	1652.9	1649.3	1645.7	1648.5
7.5°	1653.3	1651.7	1650.1	1648.5	1646.8	1643.6	1639.0	1634.3	1629.6	1624.9	1626.4
10°	1640.4	1638.2	1636.2	1634.0	1631.9	1628.2	1622.7	1617.3	1611.9	1606.5	1606.8
12.5°	1622.0	1619.6	1617.2	1614.9	1612.6	1608.1	1601.5	1594.8	1588.2	1581.6	1581.4
15°	1591.6	1588.3	1585.0	1581.7	1578.4	1572.5	1564.1	1555.7	1547.2	1538.9	1537.3
17.5°	1553.4	1549.6	1545.8	1541.9	1538.1	1530.8	1520.1	1509.3	1498.7	1488.0	1484.8
20°	1525.3	1520.5	1515.7	1510.9	1506.1	1498.0	1486.5	1475.1	1463.6	1452.2	1448.3
22.5°	1493.9	1488.3	1482.8	1477.3	1471.8	1462.9	1450.8	1438.6	1426.5	1414.3	1409.5
25°	1448.1	1440.6	1433.1	1425.6	1418.1	1407.4	1393.5	1379.8	1365.9	1352.0	1345.7
27.5°	1392.7	1384.4	1376.1	1367.8	1359.4	1347.6	1332.2	1316.8	1301.4	1286.0	1277.2
30°	1354.8	1345.7	1336.7	1327.7	1318.7	1305.7	1288.9	1272.0	1255.3	1238.4	1228.1
32.5°	1316.9	1306.7	1296.4	1286.2	1276.0	1262.0	1244.1	1226.3	1208.5	1190.8	1179.6
35°	1253.3	1242.4	1231.6	1220.8	1210.0	1195.2	1176.6	1158.0	1139.3	1120.6	1107.7
37.5°	1188.9	1176.8	1164.8	1152.7	1140.7	1124.7	1104.8	1084.9	1065.1	1045.1	1030.4
40°	1147.7	1134.5	1121.2	1108.0	1094.8	1077.5	1056.1	1034.7	1013.4	992.0	976.4
42.5°	1101.1	1087.9	1074.7	1061.4	1048.2	1030.5	1008.5	986.4	964.3	942.3	925.1
45°	1029.9	1016.4	1002.9	989.4	975.8	957.4	934.3	911.1	887.9	864.8	847.7
47.5°	958.7	943.9	929.0	914.2	899.3	880.3	857.1	834.0	810.8	787.7	769.0
50°	906.8	892.7	878.5	864.4	850.2	831.0	806.7	782.3	757.9	733.6	714.9
52.5°	860.2	844.9	829.6	814.2	798.8	779.1	755.0	730.9	706.8	682.7	663.3
55°	782.3	767.5	752.8	738.0	723.3	703.2	677.6	652.0	626.5	600.9	583.5
57.5°	710.2	694.2	678.1	662.1	646.0	625.2	599.5	573.8	548.1	522.5	505.9
60°	660.5	643.9	627.4	610.9	594.3	573.5	548.5	523.7	498.7	473.7	457.4
62.5°	610.6	594.1	577.6	561.0	544.5	523.7	498.8	473.8	448.8	423.9	408.6
65°	534.6	518.1	501.5	485.0	468.5	448.4	425.0	401.5	378.1	354.6	339.8
67.5°	458.6	441.8	425.1	408.4	391.7	372.0	349.6	327.0	304.5	282.1	271.0
70°	408.7	392.5	376.3	360.0	343.8	325.1	304.1	283.0	262.0	240.9	230.4
72.5°	359.0	342.9	326.9	310.9	294.9	277.3	258.2	239.1	220.0	200.9	192.3
75°	282.8	268.5	254.0	239.5	225.2	209.7	193.1	176.5	160.0	143.4	140.4
77.5°	213.5	200.5	187.4	174.4	161.4	149.5	138.9	128.2	117.5	106.9	105.3
80°	169.2	156.9	144.5	132.2	119.9	110.6	104.2	97.9	91.6	85.2	84.4
82.5°	126.9	116.3	105.6	95.0	84.4	77.6	74.6	71.6	68.7	65.8	64.8
85°	71.7	65.1	58.5	51.9	45.3	41.5	40.6	39.7	38.8	37.9	37.3
87.5°	26.1	23.5	21.0	18.5	16.0	14.8	15.0	15.2	15.3	15.5	15.3
90°	0.3	0.9	1.6	2.3	3.0	3.8	4.6	5.5	6.5	7.3	7.6
92.5°	7.4	7.8	8.3	8.8	9.2	9.6	10.2	10.7	11.2	11.7	11.9
95°	18.0	18.4	18.9	19.4	19.8	20.3	20.9	21.4	22.0	22.6	22.8
97.5°	31.9	32.2	32.6	33.0	33.3	33.7	34.1	34.4	34.9	35.2	35.6
100°	41.4	41.8	42.2	42.6	43.0	43.4	43.7	44.1	44.4	44.7	44.9
102.5°	52.3	52.6	52.8	53.0	53.3	53.6	54.1	54.6	55.0	55.4	55.6
105°	68.4	68.6	68.7	68.9	69.0	69.4	70.0	70.6	71.2	71.8	71.8
107.5°	87.2	87.3	87.4	87.5	87.6	87.6	87.9	88.2	88.4	88.7	88.9
110°	98.9	99.0	99.2	99.3	99.4	99.5	99.7	99.9	100.0	100.1	100.4



TEST NUMBER: P332364-935

CATALOG NUMBER: S123RDIP-S1165D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	111.1	111.2	111.2	111.3	111.4	111.4	111.5	111.5	111.5	111.6	111.8
115°	129.3	129.5	129.8	129.9	130.1	130.2	130.0	129.9	129.8	129.6	129.7
117.5°	147.7	147.8	148.0	148.1	148.3	148.2	148.0	147.8	147.7	147.5	147.5
120°	159.1	159.5	160.0	160.3	160.7	160.7	160.5	160.1	159.8	159.5	159.4
122.5°	171.1	171.3	171.7	171.9	172.3	172.3	172.1	171.9	171.8	171.6	171.4
125°	189.2	189.4	189.7	189.9	190.1	190.1	189.9	189.9	189.7	189.6	189.2
127.5°	206.0	206.5	206.9	207.3	207.8	207.9	207.8	207.6	207.5	207.3	207.0
130°	217.2	217.7	218.3	218.9	219.4	219.6	219.4	219.2	219.0	218.8	218.5
132.5°	228.4	229.0	229.5	230.1	230.6	230.8	230.7	230.5	230.3	230.2	229.9
135°	245.6	246.0	246.3	246.8	247.2	247.4	247.3	247.2	247.1	247.1	246.8
137.5°	261.4	261.7	262.0	262.3	262.7	262.9	263.1	263.3	263.5	263.6	263.4
140°	272.3	272.7	273.0	273.4	273.7	273.9	274.0	274.0	274.1	274.1	274.1
142.5°	282.3	282.7	283.0	283.4	283.6	283.9	284.0	284.1	284.2	284.4	284.3
145°	297.9	298.0	298.2	298.3	298.4	298.6	298.8	299.0	299.2	299.4	299.4
147.5°	311.5	311.8	312.0	312.3	312.5	312.7	312.9	313.1	313.2	313.5	313.5
150°	321.0	321.2	321.2	321.4	321.6	321.7	321.8	321.9	322.1	322.2	322.2
152.5°	328.8	329.0	329.2	329.3	329.6	329.7	329.8	329.8	329.9	330.0	330.1
155°	341.1	341.1	341.1	341.1	341.1	341.1	341.2	341.2	341.3	341.4	341.6
157.5°	351.5	351.5	351.4	351.3	351.2	351.2	351.3	351.3	351.4	351.5	351.7
160°	358.1	358.0	357.8	357.7	357.6	357.5	357.5	357.5	357.5	357.5	357.8
162.5°	363.9	363.8	363.6	363.4	363.2	363.2	363.2	363.3	363.3	363.3	363.7
165°	371.5	371.3	371.1	370.9	370.7	370.6	370.6	370.6	370.6	370.6	371.0
167.5°	377.5	377.3	377.0	376.7	376.4	376.3	376.4	376.4	376.5	376.6	376.9
170°	380.9	380.6	380.4	380.1	379.9	379.7	379.7	379.7	379.7	379.7	380.2
172.5°	383.7	383.3	383.1	382.8	382.5	382.4	382.4	382.4	382.4	382.4	382.8
175°	386.4	386.2	385.9	385.6	385.4	385.2	385.2	385.2	385.2	385.2	385.6
177.5°	387.5	387.4	387.1	386.9	386.7	386.6	386.6	386.6	386.6	386.6	386.9
180°	387.4	387.4	387.4	387.4	387.4	387.4	387.4	387.4	387.4	387.4	387.4



TEST NUMBER: P332364-935

CATALOG NUMBER: S123RDIP-S1165D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1662.2	1664.8	1667.4	1668.5	1668.0	1667.6	1667.1	1666.6
5°	1651.1	1653.9	1656.6	1657.6	1657.0	1656.4	1655.8	1655.2
7.5°	1627.9	1629.4	1630.9	1631.2	1630.1	1629.1	1628.1	1627.0
10°	1607.1	1607.4	1607.7	1607.1	1605.6	1604.1	1602.6	1601.1
12.5°	1581.2	1581.1	1580.9	1579.9	1578.2	1576.4	1574.7	1573.0
15°	1535.9	1534.3	1532.8	1531.0	1528.9	1526.8	1524.7	1522.6
17.5°	1481.6	1478.3	1475.2	1472.1	1468.9	1465.8	1462.7	1459.5
20°	1444.4	1440.5	1436.6	1432.8	1429.2	1425.6	1422.0	1418.4
22.5°	1404.5	1399.7	1394.8	1390.7	1387.3	1384.0	1380.6	1377.3
25°	1339.5	1333.1	1326.8	1322.0	1318.7	1315.3	1312.1	1308.7
27.5°	1268.4	1259.6	1250.9	1244.0	1238.9	1233.9	1228.8	1223.7
30°	1217.9	1207.7	1197.5	1190.0	1185.2	1180.3	1175.5	1170.7
32.5°	1168.4	1157.2	1146.0	1137.9	1132.8	1127.7	1122.7	1117.7
35°	1094.8	1081.8	1068.9	1059.7	1054.3	1048.9	1043.4	1038.1
37.5°	1015.7	1001.1	986.4	975.7	969.1	962.3	955.7	949.0
40°	960.8	945.1	929.5	918.3	911.3	904.4	897.5	890.5
42.5°	908.1	891.0	873.9	862.3	856.1	849.9	843.7	837.5
45°	830.5	813.4	796.3	784.1	776.9	769.6	762.4	755.2
47.5°	750.4	731.8	713.1	700.6	694.1	687.7	681.2	674.9
50°	696.3	677.6	658.9	646.2	639.3	632.3	625.4	618.5
52.5°	643.9	624.6	605.2	592.4	586.2	580.1	573.9	567.7
55°	566.0	548.5	531.2	519.4	513.4	507.4	501.4	495.3
57.5°	489.5	472.9	456.5	445.7	440.6	435.5	430.3	425.2
60°	441.2	425.0	408.7	398.0	393.0	387.8	382.7	377.6
62.5°	393.3	378.1	362.7	352.5	347.1	341.7	336.4	331.1
65°	325.1	310.4	295.7	286.6	283.4	280.0	276.7	273.4
67.5°	260.0	249.0	238.0	230.7	227.2	223.6	220.1	216.5
70°	219.8	209.3	198.8	191.9	188.6	185.3	181.9	178.7
72.5°	183.7	175.0	166.4	161.4	160.1	158.7	157.3	155.9
75°	137.4	134.4	131.4	129.7	129.1	128.5	127.9	127.3
77.5°	103.7	102.0	100.4	99.3	98.7	98.1	97.5	96.9
80°	83.4	82.6	81.6	80.9	80.3	79.7	79.1	78.5
82.5°	64.0	63.1	62.2	61.6	61.6	61.4	61.3	61.2
85°	36.7	36.1	35.5	35.2	35.2	35.2	35.2	35.2
87.5°	15.2	15.0	14.8	14.6	14.4	14.1	13.9	13.8
90°	7.8	8.1	8.4	8.6	8.7	8.9	9.0	9.1
92.5°	12.1	12.3	12.6	12.7	12.6	12.5	12.4	12.3
95°	23.1	23.3	23.6	23.8	23.8	23.8	23.8	23.8
97.5°	35.8	36.2	36.5	36.6	36.6	36.6	36.5	36.5
100°	45.1	45.4	45.5	45.7	45.8	46.0	46.1	46.2
102.5°	55.9	56.1	56.2	56.3	56.3	56.3	56.2	56.2
105°	71.8	71.8	71.8	71.9	72.0	72.2	72.3	72.4
107.5°	89.1	89.3	89.5	89.6	89.5	89.5	89.4	89.3
110°	100.7	100.9	101.2	101.3	101.1	101.0	100.8	100.7



TEST NUMBER: P332364-935

CATALOG NUMBER: S123RDIP-S1165D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	112.2	112.5	112.9	113.0	113.0	113.0	112.9	112.9
115°	129.8	129.8	129.9	129.9	129.8	129.8	129.7	129.6
117.5°	147.5	147.5	147.5	147.3	147.1	147.0	146.8	146.6
120°	159.3	159.2	159.2	159.0	158.9	158.8	158.7	158.5
122.5°	171.3	171.1	170.9	170.7	170.6	170.3	170.1	170.0
125°	189.0	188.7	188.5	188.2	188.0	187.7	187.4	187.1
127.5°	206.6	206.2	205.8	205.4	205.2	204.8	204.6	204.2
130°	218.3	217.9	217.7	217.3	216.9	216.4	215.9	215.4
132.5°	229.5	229.2	228.9	228.6	228.2	227.8	227.5	227.1
135°	246.5	246.2	246.0	245.8	245.6	245.5	245.4	245.2
137.5°	263.1	262.9	262.5	262.3	262.0	261.7	261.5	261.2
140°	274.0	274.0	273.9	273.6	273.1	272.7	272.2	271.7
142.5°	284.2	284.1	284.1	283.9	283.5	283.2	282.8	282.4
145°	299.3	299.2	299.1	298.9	298.7	298.4	298.2	297.9
147.5°	313.5	313.5	313.5	313.2	312.9	312.5	312.0	311.6
150°	322.2	322.2	322.2	322.0	321.6	321.2	320.8	320.4
152.5°	330.2	330.4	330.5	330.3	329.9	329.6	329.2	328.9
155°	341.9	342.2	342.5	342.3	341.9	341.4	341.0	340.4
157.5°	352.0	352.3	352.6	352.5	352.1	351.8	351.4	351.0
160°	358.2	358.5	358.9	358.9	358.6	358.3	358.1	357.8
162.5°	364.0	364.4	364.7	364.6	364.2	363.8	363.3	362.9
165°	371.4	371.8	372.2	372.2	371.7	371.3	370.7	370.3
167.5°	377.4	377.8	378.2	378.2	377.8	377.4	376.9	376.6
170°	380.6	381.2	381.6	381.6	381.2	380.6	380.2	379.7
172.5°	383.2	383.7	384.1	384.1	383.6	383.1	382.6	382.2
175°	386.0	386.4	386.8	386.8	386.3	385.8	385.4	384.9
177.5°	387.3	387.5	387.9	387.9	387.5	387.1	386.8	386.3
180°	387.4	387.4	387.4	387.4	387.4	387.4	387.4	387.4

(END OF REPORT)