

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332260-935

Luminaire Tested: **S123RDIP-S340D1025U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332260-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D1025U935-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4364.2 lumens  
Efficiency: N/A  
Efficacy: 117.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332260-935

CATALOG NUMBER: S123RDIP-S340D1025U935-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332260-935

CATALOG NUMBER: S123RDIP-S340D1025U935-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	74	62	60	58	46	45	44	31	31	30	23
2	85	78	72	67	76	70	65	61	55	51	49	41	39	37	28	27	26	20
3	77	69	62	56	69	62	56	51	48	44	41	36	34	32	25	23	22	17
4	71	61	53	48	63	55	48	44	43	39	35	32	30	27	22	21	19	15
5	65	54	47	41	58	49	42	37	39	34	30	29	26	24	20	18	17	13
6	60	49	41	35	53	44	37	32	35	30	27	26	23	21	18	17	15	12
7	55	44	36	31	49	40	33	28	32	27	23	24	21	18	17	15	13	11
8	51	40	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12	10
9	48	36	29	24	43	33	27	22	26	22	18	20	17	15	14	12	11	9
10	44	33	26	22	40	30	24	20	24	20	17	19	15	13	13	11	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	5044	5044	5044	5044
5°	6013	5065	4460	5065
10°	7507	5037	4030	5037
15°	8811	4985	3675	4985
20°	9835	4907	3373	4907
25°	9678	4827	3188	4827
30°	6955	4753	2997	4753
35°	4644	4654	2872	4654
40°	3421	4539	2746	4539
45°	2871	4332	2620	4332
50°	2534	4064	2445	4064
55°	2222	3757	2205	3757
60°	1978	3462	2019	3462
65°	1737	3148	1880	3148
70°	1363	2867	1718	2867
75°	1198	2504	1568	2504
80°	1048	2126	1543	2126
85°	840	1717	1643	1717



TEST NUMBER: P332260-935

CATALOG NUMBER: S123RDIP-S340D1025U935-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	46.1	1.1
10°-20°	144.0	3.3
20°-30°	226.2	5.2
30°-40°	236.0	5.4
40°-50°	201.9	4.6
50°-60°	153.9	3.5
60°-70°	98.7	2.3
70°-80°	47.5	1.1
80°-90°	15.8	0.4
90°-100°	236.3	5.4
100°-110°	669.0	15.3
110°-120°	658.1	15.1
120°-130°	525.0	12.0
130°-140°	413.9	9.5
140°-150°	308.9	7.1
150°-160°	215.3	4.9
160°-170°	126.5	2.9
170°-180°	41.2	0.9
0°-30°	416.2	9.5
0°-40°	652.2	14.9
0°-60°	1008.0	23.1
0°-90°	1170.0	26.8
90°-120°	1563.5	35.8
90°-150°	2811.2	64.4
90°-180°	3194.0	73.2
0°-180°	4364.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	469	469	469	469	469	
5°	556	469	413	469	556	57
15°	791	447	330	447	791	224
25°	815	406	268	406	815	350
35°	353	354	219	354	353	232
45°	189	285	172	285	189	148
55°	118	200	118	200	118	107
65°	68	124	74	124	68	67
75°	29	60	38	60	29	31
85°	7	14	13	14	7	8
90°	25	2	25	2	25	13
95°	100	29	100	29	100	180
105°	1093	100	1093	100	1093	1078
115°	1330	176	1330	176	1330	1292
125°	1048	245	1048	245	1048	950
135°	850	287	850	287	850	659
145°	664	327	664	327	664	423
155°	551	372	551	372	551	257
165°	480	406	480	406	480	137
175°	432	424	432	424	432	42
180°	425	425	425	425	425	



TEST NUMBER: P332260-935

CATALOG NUMBER: S123RDIP-S340D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	499.1	499.7	497.7	497.3	494.9	494.3	494.3	490.9	488.8	486.1	484.5
5°	556.5	559.6	558.0	554.5	548.5	547.0	543.2	537.2	530.4	521.9	518.0
7.5°	628.1	632.5	630.8	625.3	618.9	613.8	603.0	593.1	579.1	566.8	556.3
10°	686.8	682.3	678.6	673.2	667.4	658.0	646.7	631.3	613.5	599.3	583.8
12.5°	730.8	730.0	725.5	719.9	711.7	702.7	688.9	670.1	649.4	629.0	611.1
15°	790.7	791.9	788.9	783.2	771.5	755.6	734.8	726.9	697.2	675.2	653.2
17.5°	832.2	832.0	831.6	823.5	811.7	800.4	781.0	760.4	733.6	702.5	672.8
20°	858.6	856.5	857.0	847.9	839.1	826.0	807.2	777.3	755.3	719.4	688.6
22.5°	857.9	857.5	859.0	855.9	849.5	839.6	824.7	799.4	771.3	735.0	700.5
25°	814.9	813.2	822.6	825.3	835.5	837.3	832.8	819.1	792.4	755.0	712.3
27.5°	681.9	681.1	698.5	720.5	748.2	769.8	790.7	800.7	792.4	765.6	722.8
30°	559.6	578.5	587.4	619.1	654.4	696.5	733.4	768.4	777.1	765.4	730.4
32.5°	464.7	481.1	488.5	515.7	548.6	598.0	653.3	703.0	738.1	747.0	725.9
35°	353.4	353.6	370.5	382.5	413.0	463.7	517.5	584.1	650.3	700.5	705.7
37.5°	282.1	283.0	293.3	305.2	328.1	354.9	402.3	457.6	534.1	611.1	656.3
40°	243.5	245.3	253.0	264.8	281.2	301.5	338.4	390.5	454.3	540.0	610.0
42.5°	218.8	221.7	225.7	234.8	245.0	264.0	293.8	334.1	392.1	473.1	553.9
45°	188.6	190.2	193.2	197.4	206.6	219.8	239.9	267.0	315.1	380.3	461.2
47.5°	166.3	165.5	168.7	172.0	178.2	187.3	200.7	222.7	257.1	309.4	378.0
50°	151.3	151.0	153.3	155.8	161.7	168.3	179.3	196.0	223.3	266.6	329.4
52.5°	137.2	137.8	139.5	142.7	146.9	152.2	162.1	174.2	197.6	235.0	287.3
55°	118.4	119.0	121.1	123.0	126.0	131.4	137.6	147.7	163.7	189.8	232.9
57.5°	102.5	102.2	104.3	104.8	108.1	112.5	117.4	125.2	136.8	156.2	185.2
60°	91.9	91.3	93.1	94.5	96.3	99.9	103.9	111.5	120.8	135.0	159.9
62.5°	82.2	82.0	83.3	84.7	86.2	89.5	92.8	98.7	106.0	118.0	137.8
65°	68.2	68.8	69.4	70.0	70.8	72.8	76.0	80.1	85.1	93.5	107.7
67.5°	53.6	54.2	54.4	55.6	57.3	58.6	60.6	64.1	67.7	74.7	82.8
70°	43.3	43.1	43.3	43.9	46.1	48.3	51.0	53.6	55.8	60.8	67.6
72.5°	37.2	36.9	37.4	37.5	38.6	39.2	40.8	43.3	46.1	49.5	54.4
75°	28.8	28.8	28.8	28.8	29.7	30.0	30.7	31.3	32.3	33.9	37.5
77.5°	21.4	21.4	21.7	21.9	22.0	22.3	22.6	23.2	23.6	24.5	26.0
80°	16.9	17.0	16.9	17.0	17.0	17.5	17.7	18.3	18.4	19.5	20.1
82.5°	12.7	12.6	12.7	12.9	12.9	13.3	13.3	13.8	13.8	14.3	14.9
85°	6.8	6.5	6.8	6.6	7.1	6.6	6.8	7.2	7.2	7.4	8.3
87.5°	6.6	7.1	6.6	6.5	6.7	6.5	6.4	6.2	6.4	6.4	6.0
90°	24.9	25.7	24.9	24.0	24.9	23.2	22.4	21.5	20.7	21.5	18.9
92.5°	41.4	43.0	42.1	44.7	46.2	50.7	57.4	72.3	99.7	132.2	145.4
95°	99.7	103.1	109.2	116.9	133.2	164.2	209.7	309.4	413.4	509.6	453.7
97.5°	271.4	278.8	302.0	340.7	404.1	506.9	617.8	771.3	845.0	789.8	578.2
100°	538.9	538.0	571.5	634.3	721.1	843.1	943.7	1013.3	983.2	813.9	550.0
102.5°	790.5	810.3	838.3	887.9	955.5	1032.9	1091.5	1093.7	990.1	769.2	508.8
105°	1093.2	1097.5	1125.0	1157.6	1197.2	1219.5	1203.2	1117.2	937.6	691.0	458.1
107.5°	1267.5	1275.4	1284.7	1295.7	1295.0	1264.4	1189.1	1049.6	845.8	621.9	425.8
110°	1339.0	1340.7	1342.5	1335.6	1311.5	1251.3	1143.1	984.9	788.1	582.7	413.4



TEST NUMBER: P332260-935

CATALOG NUMBER: S123RDIP-S340D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1353.4	1353.1	1346.5	1325.3	1281.3	1203.9	1082.5	920.9	737.9	556.6	406.5
115°	1329.6	1325.3	1308.0	1270.2	1205.7	1112.1	985.8	836.2	677.3	528.6	403.9
117.5°	1253.5	1247.8	1223.0	1179.7	1112.4	1017.4	904.0	774.9	640.6	512.0	405.4
120°	1190.3	1185.2	1164.5	1116.4	1048.5	961.7	858.6	742.5	621.4	504.5	408.2
122.5°	1131.2	1124.6	1102.0	1058.7	998.3	917.7	822.2	717.1	605.5	499.6	413.0
125°	1048.5	1042.5	1021.0	983.2	928.2	859.5	777.0	683.3	585.3	493.4	420.3
127.5°	980.4	974.9	955.5	923.2	874.2	811.7	737.2	653.7	567.4	490.3	428.5
130°	941.9	935.0	917.1	886.1	840.5	782.0	712.5	635.2	557.8	488.2	434.0
132.5°	904.1	899.3	883.3	852.4	809.6	753.9	689.1	617.9	548.8	487.5	438.2
135°	850.0	844.0	828.5	802.7	760.6	711.6	655.7	594.7	537.2	486.5	444.4
137.5°	792.7	788.8	775.8	749.6	714.2	671.8	623.6	573.6	527.0	484.6	448.4
140°	752.9	753.7	739.9	715.9	683.3	646.3	605.0	561.2	520.8	483.9	451.2
142.5°	715.7	716.6	704.2	682.9	655.0	622.9	587.2	549.5	515.3	482.5	453.2
145°	664.3	662.6	655.7	637.7	616.2	591.2	563.8	535.5	507.9	480.4	454.6
147.5°	622.1	621.4	614.8	602.6	586.3	568.6	546.4	523.9	500.7	477.2	454.6
150°	597.3	597.3	592.1	582.7	569.8	553.5	535.5	515.7	495.8	474.4	454.6
152.5°	576.7	576.7	573.6	564.8	554.7	541.1	525.1	508.1	490.4	471.0	452.5
155°	550.9	550.0	548.3	541.5	533.7	523.4	510.5	496.7	482.2	464.9	450.3
157.5°	527.4	527.5	526.2	521.0	514.3	506.2	496.2	484.7	472.9	459.6	447.5
160°	512.2	513.1	513.1	507.9	501.9	495.8	487.3	477.9	466.7	455.5	446.1
162.5°	498.4	499.3	499.3	494.9	490.9	485.6	477.7	469.6	460.5	451.3	443.3
165°	480.4	480.4	481.3	477.9	474.4	470.1	464.1	458.9	452.0	445.2	439.2
167.5°	463.2	463.2	464.1	461.7	460.1	457.0	453.6	449.6	444.0	439.0	435.1
170°	452.9	452.9	453.7	452.0	451.2	449.4	446.1	443.5	439.2	434.9	432.3
172.5°	443.3	444.0	445.6	443.8	443.7	442.6	439.9	438.0	434.4	431.4	430.2
175°	432.3	433.2	434.0	433.2	433.2	433.2	431.4	430.6	428.9	427.1	427.1
177.5°	425.9	425.9	427.3	426.6	427.3	427.3	426.6	425.9	425.2	424.6	425.2
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P332260-935

CATALOG NUMBER: S123RDIP-S340D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	483.8	483.4	481.1	478.5	475.2	472.9	471.1	470.2	467.3	463.7	461.4
5°	513.8	507.7	501.3	493.4	486.2	478.8	474.2	468.8	462.2	454.8	449.5
7.5°	545.7	533.9	521.2	508.1	495.2	483.5	473.2	464.4	453.9	443.2	435.8
10°	570.3	553.0	535.2	516.9	500.3	484.7	472.6	460.8	448.2	435.9	426.6
12.5°	592.6	569.9	549.3	526.8	505.6	486.9	469.6	455.6	440.4	427.4	416.9
15°	620.9	597.5	572.7	538.6	510.3	486.6	465.5	447.3	428.9	412.8	402.6
17.5°	647.2	612.3	578.8	550.4	513.6	484.1	458.3	436.5	416.2	399.2	386.6
20°	658.1	624.2	588.0	551.6	515.6	482.4	452.5	428.4	407.4	388.1	376.5
22.5°	664.7	626.4	588.1	549.1	510.7	476.3	446.8	420.3	397.4	379.2	364.8
25°	672.4	626.6	584.5	546.0	506.9	469.6	434.5	406.4	381.8	362.3	347.1
27.5°	677.4	623.6	573.9	531.1	491.4	454.3	422.1	392.3	367.2	346.6	330.3
30°	678.4	621.2	565.7	519.4	479.1	444.9	410.8	382.4	355.9	334.0	318.7
32.5°	679.7	615.3	554.6	505.4	464.1	430.3	399.4	372.2	345.1	323.6	308.0
35°	674.4	612.0	537.8	481.2	439.9	407.2	379.4	354.2	327.6	306.7	290.8
37.5°	651.6	599.0	520.4	454.0	410.8	380.6	357.8	336.0	311.5	289.0	274.1
40°	628.7	586.2	506.9	437.5	392.4	361.3	340.8	323.0	299.3	278.2	262.2
42.5°	594.5	568.6	494.0	420.2	371.5	341.6	324.3	307.5	286.8	265.4	250.3
45°	531.8	535.2	467.8	392.5	342.6	312.5	296.3	284.6	266.2	248.6	233.1
47.5°	453.1	485.0	437.0	363.2	312.2	284.0	269.8	259.6	247.1	229.8	215.7
50°	401.8	447.3	412.2	343.5	293.1	265.0	251.0	242.7	231.9	218.3	204.8
52.5°	354.5	403.4	382.4	321.4	272.3	246.7	233.0	226.2	217.6	204.7	192.6
55°	289.0	338.6	333.8	288.3	241.3	218.3	207.8	200.2	194.4	184.8	175.1
57.5°	233.8	280.8	283.3	251.3	214.0	191.1	182.2	176.4	172.6	165.4	156.4
60°	199.0	242.1	250.6	226.4	194.4	174.4	165.5	160.8	157.9	152.1	145.3
62.5°	170.1	206.8	216.4	199.1	175.6	156.8	149.9	145.5	143.4	138.4	132.4
65°	130.2	160.7	169.9	160.3	148.0	133.0	127.3	123.6	121.7	119.0	114.5
67.5°	97.9	120.1	130.3	123.5	119.0	109.5	106.0	103.9	102.3	100.4	96.7
70°	78.6	95.1	105.5	103.8	100.1	95.1	92.5	91.1	89.5	87.8	84.6
72.5°	63.2	74.6	84.3	85.2	82.3	81.3	79.0	78.4	77.4	75.5	73.7
75°	41.9	49.8	56.6	59.2	60.4	61.4	60.4	60.2	60.0	58.4	57.3
77.5°	27.5	31.7	36.0	40.5	42.4	43.7	44.0	44.8	44.2	43.4	42.9
80°	21.1	22.0	25.1	28.8	31.9	33.1	33.9	34.3	34.1	33.9	33.1
82.5°	15.3	16.1	17.6	20.2	22.7	24.7	25.2	25.1	25.6	25.7	25.1
85°	8.3	8.4	8.9	9.2	10.6	12.8	13.4	13.9	14.2	14.2	13.0
87.5°	5.9	5.2	5.0	4.6	4.7	4.4	5.0	5.5	5.9	5.7	6.2
90°	16.4	13.8	11.2	9.5	7.7	5.2	3.4	1.7	3.4	5.2	7.7
92.5°	109.2	72.2	49.7	36.9	29.7	23.1	15.8	10.7	15.8	23.1	29.7
95°	312.8	184.8	111.8	78.2	55.9	41.2	31.8	29.2	31.8	41.2	55.9
97.5°	343.3	198.9	129.1	92.8	70.8	58.1	50.7	49.9	50.7	58.1	70.8
100°	324.0	196.8	136.6	103.1	82.5	70.5	64.5	63.6	64.5	70.5	82.5
102.5°	307.5	199.6	145.6	114.9	96.3	84.9	79.6	78.0	79.6	84.9	96.3
105°	295.7	207.2	160.7	134.1	117.8	107.5	102.3	99.7	102.3	107.5	117.8
107.5°	294.8	221.2	180.5	155.8	140.4	130.3	125.3	122.7	125.3	130.3	140.4
110°	298.3	232.9	194.2	170.1	155.6	146.1	141.8	139.2	141.8	146.1	155.6





TEST NUMBER: P332260-935

CATALOG NUMBER: S123RDIP-S340D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	305.1	244.6	208.7	185.3	170.7	161.3	157.0	154.4	157.0	161.3	170.7
115°	316.2	263.8	231.2	208.0	193.4	184.8	179.6	176.2	179.6	184.8	193.4
117.5°	331.1	284.3	252.0	230.5	214.1	206.3	202.0	198.0	202.0	206.3	214.1
120°	342.1	297.4	266.4	245.0	228.6	220.0	215.7	213.1	215.7	220.0	228.6
122.5°	352.4	311.1	280.9	258.0	242.4	233.1	228.8	226.2	228.8	233.1	242.4
125°	368.7	330.9	300.8	277.6	261.2	251.8	246.7	245.0	246.7	251.8	261.2
127.5°	382.1	348.1	319.0	295.8	277.8	268.1	261.7	259.2	261.7	268.1	277.8
130°	391.1	358.3	330.0	306.8	288.8	278.4	270.7	268.1	270.7	278.4	288.8
132.5°	399.3	367.3	339.7	317.1	299.1	286.7	278.3	275.0	278.3	286.7	299.1
135°	409.9	380.7	354.0	330.9	312.8	300.0	290.5	287.1	290.5	300.0	312.8
137.5°	417.8	390.0	364.4	342.9	325.0	311.3	302.0	298.4	302.0	311.3	325.0
140°	422.0	396.2	371.3	349.8	332.6	318.8	310.2	306.0	310.2	318.8	332.6
142.5°	426.1	401.1	376.8	356.6	339.5	327.1	317.8	314.2	317.8	327.1	339.5
145°	430.6	407.3	385.0	365.2	350.7	337.8	330.0	327.4	330.0	337.8	350.7
147.5°	433.3	412.5	392.1	375.2	361.1	350.0	342.4	340.9	342.4	350.0	361.1
150°	434.0	415.9	396.2	380.7	368.7	357.5	350.7	349.8	350.7	357.5	368.7
152.5°	435.4	418.0	401.1	386.2	375.6	365.8	358.9	358.7	358.9	365.8	375.6
155°	435.8	422.0	407.3	395.4	385.9	377.3	372.1	372.1	372.1	377.3	385.9
157.5°	436.6	424.2	412.5	403.2	395.2	387.6	383.5	382.8	383.5	387.6	395.2
160°	436.6	426.3	415.9	407.3	401.3	394.5	391.1	391.1	391.1	394.5	401.3
162.5°	435.9	427.0	418.0	410.8	405.4	400.0	397.3	397.3	397.3	400.0	405.4
165°	434.0	428.0	421.1	415.1	411.6	407.3	405.6	406.5	405.6	407.3	411.6
167.5°	432.7	427.8	422.8	419.0	416.6	413.4	412.5	413.5	412.5	413.4	416.6
170°	430.6	427.1	422.8	421.1	419.4	416.8	415.9	417.7	415.9	416.8	419.4
172.5°	429.9	427.1	423.5	422.5	421.5	419.6	419.4	420.4	419.4	419.6	421.5
175°	428.0	426.3	424.6	423.7	423.7	422.0	422.8	423.7	422.8	422.0	423.7
177.5°	426.6	425.2	424.6	424.6	424.6	423.9	424.6	425.2	424.6	423.9	424.6
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P332260-935

CATALOG NUMBER: S123RDIP-S340D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	460.5	458.5	457.0	453.8	451.8	449.5	447.3	448.7	448.5	448.4	448.4
5°	445.1	440.5	436.3	430.8	427.5	423.3	420.1	419.7	420.4	417.7	416.0
7.5°	429.8	423.5	417.5	411.6	405.2	400.1	397.0	395.5	393.5	391.8	389.9
10°	419.0	411.6	405.8	398.4	391.6	385.6	381.8	379.1	377.7	376.3	373.7
12.5°	407.9	400.7	393.3	384.9	378.4	371.4	368.6	365.7	363.0	361.4	357.8
15°	391.8	382.4	374.5	365.7	358.4	351.6	347.7	341.8	341.0	339.0	335.4
17.5°	375.5	365.3	354.5	347.9	339.8	332.7	326.6	324.7	318.9	316.8	313.6
20°	362.7	353.3	345.0	336.4	324.6	318.0	313.1	310.6	305.9	303.1	301.1
22.5°	351.6	342.0	332.5	322.4	312.7	305.2	301.7	297.6	295.2	291.2	289.0
25°	335.8	325.4	313.9	303.1	296.1	290.5	284.8	281.2	277.6	275.8	271.8
27.5°	317.5	306.5	295.8	287.6	279.0	273.5	268.4	265.2	260.8	257.8	255.5
30°	307.3	294.5	285.2	277.8	266.8	261.6	257.8	253.7	250.6	247.4	245.1
32.5°	295.6	283.9	275.2	266.0	257.5	251.8	246.8	243.3	240.6	237.5	235.3
35°	277.2	267.4	258.4	249.2	242.9	237.1	231.3	228.3	225.7	222.8	220.8
37.5°	260.6	251.4	242.8	234.1	226.4	221.6	217.0	214.6	211.1	209.2	207.2
40°	250.4	241.3	232.1	223.7	215.7	212.1	207.8	204.4	201.2	199.8	197.6
42.5°	239.1	230.1	222.3	213.3	206.6	201.7	197.9	194.2	191.7	189.7	188.5
45°	222.5	214.5	206.8	197.8	191.6	187.4	183.0	179.5	177.4	175.9	173.7
47.5°	206.3	198.3	190.5	182.7	176.7	171.9	167.4	165.1	162.1	160.4	158.9
50°	194.6	187.4	179.2	171.9	165.9	161.1	157.5	154.5	151.9	149.6	148.6
52.5°	183.8	176.2	169.0	162.3	155.9	150.5	147.2	144.0	142.1	139.6	138.4
55°	166.1	158.7	152.7	146.0	139.8	135.2	131.2	128.4	126.4	123.6	122.0
57.5°	149.5	142.8	135.6	129.8	123.5	119.6	116.2	112.4	109.9	107.8	106.2
60°	138.2	130.6	124.3	119.0	113.3	108.3	105.3	102.3	99.7	97.5	96.1
62.5°	126.5	119.9	113.9	108.1	102.9	98.5	95.1	92.6	90.2	88.9	87.4
65°	108.5	103.3	97.3	92.5	87.6	84.5	81.6	79.5	77.8	76.8	75.6
67.5°	92.0	87.0	81.7	77.0	73.7	71.3	69.5	67.6	66.7	65.4	64.7
70°	81.3	76.0	71.4	67.8	64.6	62.8	61.6	60.2	59.4	57.8	57.0
72.5°	69.6	65.8	62.4	59.5	56.9	55.3	53.7	52.0	50.7	48.9	48.1
75°	54.8	51.3	48.7	46.8	45.1	43.0	40.7	38.9	38.3	37.7	37.5
77.5°	40.6	38.4	36.5	34.8	32.8	31.3	30.7	30.3	30.2	29.9	29.9
80°	31.9	29.9	28.5	26.5	25.3	25.3	25.3	24.9	25.1	25.1	25.1
82.5°	23.7	21.9	21.1	20.4	20.1	20.3	20.3	20.4	20.2	20.6	20.4
85°	12.2	12.4	12.8	12.7	12.8	12.8	13.3	13.0	13.3	12.8	13.3
87.5°	6.4	7.2	7.9	8.5	9.2	9.6	9.6	9.7	10.1	10.2	10.6
90°	9.5	11.2	13.8	16.4	18.9	21.5	20.7	21.5	22.4	23.2	24.9
92.5°	36.9	49.7	72.2	109.2	145.4	132.2	99.7	72.3	57.4	50.7	46.2
95°	78.2	111.8	184.8	312.8	453.7	509.6	413.4	309.4	209.7	164.2	133.2
97.5°	92.8	129.1	198.9	343.3	578.2	789.8	845.0	771.3	617.8	506.9	404.1
100°	103.1	136.6	196.8	324.0	550.0	813.9	983.2	1013.3	943.7	843.1	721.1
102.5°	114.9	145.6	199.6	307.5	508.8	769.2	990.1	1093.7	1091.5	1032.9	955.5
105°	134.1	160.7	207.2	295.7	458.1	691.0	937.6	1117.2	1203.2	1219.5	1197.2
107.5°	155.8	180.5	221.2	294.8	425.8	621.9	845.8	1049.6	1189.1	1264.4	1295.0
110°	170.1	194.2	232.9	298.3	413.4	582.7	788.1	984.9	1143.1	1251.3	1311.5



TEST NUMBER: P332260-935

CATALOG NUMBER: S123RDIP-S340D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	185.3	208.7	244.6	305.1	406.5	556.6	737.9	920.9	1082.5	1203.9	1281.3
115°	208.0	231.2	263.8	316.2	403.9	528.6	677.3	836.2	985.8	1112.1	1205.7
117.5°	230.5	252.0	284.3	331.1	405.4	512.0	640.6	774.9	904.0	1017.4	1112.4
120°	245.0	266.4	297.4	342.1	408.2	504.5	621.4	742.5	858.6	961.7	1048.5
122.5°	258.0	280.9	311.1	352.4	413.0	499.6	605.5	717.1	822.2	917.7	998.3
125°	277.6	300.8	330.9	368.7	420.3	493.4	585.3	683.3	777.0	859.5	928.2
127.5°	295.8	319.0	348.1	382.1	428.5	490.3	567.4	653.7	737.2	811.7	874.2
130°	306.8	330.0	358.3	391.1	434.0	488.2	557.8	635.2	712.5	782.0	840.5
132.5°	317.1	339.7	367.3	399.3	438.2	487.5	548.8	617.9	689.1	753.9	809.6
135°	330.9	354.0	380.7	409.9	444.4	486.5	537.2	594.7	655.7	711.6	760.6
137.5°	342.9	364.4	390.0	417.8	448.4	484.6	527.0	573.6	623.6	671.8	714.2
140°	349.8	371.3	396.2	422.0	451.2	483.9	520.8	561.2	605.0	646.3	683.3
142.5°	356.6	376.8	401.1	426.1	453.2	482.5	515.3	549.5	587.2	622.9	655.0
145°	365.2	385.0	407.3	430.6	454.6	480.4	507.9	535.5	563.8	591.2	616.2
147.5°	375.2	392.1	412.5	433.3	454.6	477.2	500.7	523.9	546.4	568.6	586.3
150°	380.7	396.2	415.9	434.0	454.6	474.4	495.8	515.7	535.5	553.5	569.8
152.5°	386.2	401.1	418.0	435.4	452.5	471.0	490.4	508.1	525.1	541.1	554.7
155°	395.4	407.3	422.0	435.8	450.3	464.9	482.2	496.7	510.5	523.4	533.7
157.5°	403.2	412.5	424.2	436.6	447.5	459.6	472.9	484.7	496.2	506.2	514.3
160°	407.3	415.9	426.3	436.6	446.1	455.5	466.7	477.9	487.3	495.8	501.9
162.5°	410.8	418.0	427.0	435.9	443.3	451.3	460.5	469.6	477.7	485.6	490.9
165°	415.1	421.1	428.0	434.0	439.2	445.2	452.0	458.9	464.1	470.1	474.4
167.5°	419.0	422.8	427.8	432.7	435.1	439.0	444.0	449.6	453.6	457.0	460.1
170°	421.1	422.8	427.1	430.6	432.3	434.9	439.2	443.5	446.1	449.4	451.2
172.5°	422.5	423.5	427.1	429.9	430.2	431.4	434.4	438.0	439.9	442.6	443.7
175°	423.7	424.6	426.3	428.0	427.1	427.1	428.9	430.6	431.4	433.2	433.2
177.5°	424.6	424.6	425.2	426.6	425.2	424.6	425.2	425.9	426.6	427.3	427.3
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P332260-935

CATALOG NUMBER: S123RDIP-S340D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	446.4	446.3	446.4	445.8	446.4	446.3	446.4	448.4	448.4	448.5	448.7
5°	415.4	415.3	414.7	412.8	414.7	415.3	415.4	416.0	417.7	420.4	419.7
7.5°	388.3	388.1	386.3	386.3	386.3	388.1	388.3	389.9	391.8	393.5	395.5
10°	372.3	372.5	370.1	368.7	370.1	372.5	372.3	373.7	376.3	377.7	379.1
12.5°	356.7	355.9	353.9	352.3	353.9	355.9	356.7	357.8	361.4	363.0	365.7
15°	336.2	334.2	329.4	329.8	329.4	334.2	336.2	335.4	339.0	341.0	341.8
17.5°	312.0	310.6	310.5	307.6	310.5	310.6	312.0	313.6	316.8	318.9	324.7
20°	297.9	296.9	297.3	294.5	297.3	296.9	297.9	301.1	303.1	305.9	310.6
22.5°	286.8	285.8	284.1	283.3	284.1	285.8	286.8	289.0	291.2	295.2	297.6
25°	270.6	269.0	267.4	268.4	267.4	269.0	270.6	271.8	275.8	277.6	281.2
27.5°	254.4	253.2	251.6	251.4	251.6	253.2	254.4	255.5	257.8	260.8	265.2
30°	244.1	242.9	242.1	241.1	242.1	242.9	244.1	245.1	247.4	250.6	253.7
32.5°	233.7	233.4	232.0	231.8	232.0	233.4	233.7	235.3	237.5	240.6	243.3
35°	220.1	218.9	218.4	218.6	218.4	218.9	220.1	220.8	222.8	225.7	228.3
37.5°	207.1	205.5	204.7	204.1	204.7	205.5	207.1	207.2	209.2	211.1	214.6
40°	197.8	196.2	195.8	195.4	195.8	196.2	197.8	197.6	199.8	201.2	204.4
42.5°	187.4	186.8	186.5	185.7	186.5	186.8	187.4	188.5	189.7	191.7	194.2
45°	173.1	172.9	171.7	172.1	171.7	172.9	173.1	173.7	175.9	177.4	179.5
47.5°	158.1	157.2	156.4	157.0	156.4	157.2	158.1	158.9	160.4	162.1	165.1
50°	147.8	147.4	145.6	146.0	145.6	147.4	147.8	148.6	149.6	151.9	154.5
52.5°	137.6	136.0	135.3	135.1	135.3	136.0	137.6	138.4	139.6	142.1	144.0
55°	120.5	118.7	118.0	117.5	118.0	118.7	120.5	122.0	123.6	126.4	128.4
57.5°	103.8	103.4	102.7	103.1	102.7	103.4	103.8	106.2	107.8	109.9	112.4
60°	94.1	94.1	94.1	93.8	94.1	94.1	94.1	96.1	97.5	99.7	102.3
62.5°	86.5	86.0	85.9	86.2	85.9	86.0	86.5	87.4	88.9	90.2	92.6
65°	75.0	74.8	74.0	73.8	74.0	74.8	75.0	75.6	76.8	77.8	79.5
67.5°	64.1	63.5	63.2	62.9	63.2	63.5	64.1	64.7	65.4	66.7	67.6
70°	56.0	55.5	54.3	54.6	54.3	55.5	56.0	57.0	57.8	59.4	60.2
72.5°	47.2	46.8	46.5	46.2	46.5	46.8	47.2	48.1	48.9	50.7	52.0
75°	37.3	37.1	36.9	37.7	36.9	37.1	37.3	37.5	37.7	38.3	38.9
77.5°	29.9	29.9	30.0	29.7	30.0	29.9	29.9	29.9	29.9	30.2	30.3
80°	25.1	25.1	24.9	24.9	24.9	25.1	25.1	25.1	25.1	25.1	24.9
82.5°	20.1	20.2	20.4	20.1	20.4	20.2	20.1	20.4	20.6	20.2	20.4
85°	13.3	13.0	13.4	13.3	13.4	13.0	13.3	13.3	12.8	13.3	13.0
87.5°	10.8	10.6	10.8	10.8	10.8	10.6	10.8	10.6	10.2	10.1	9.7
90°	24.0	24.9	25.7	24.9	25.7	24.9	24.0	24.9	23.2	22.4	21.5
92.5°	44.7	42.1	43.0	41.4	43.0	42.1	44.7	46.2	50.7	57.4	72.3
95°	116.9	109.2	103.1	99.7	103.1	109.2	116.9	133.2	164.2	209.7	309.4
97.5°	340.7	302.0	278.8	271.4	278.8	302.0	340.7	404.1	506.9	617.8	771.3
100°	634.3	571.5	538.0	538.9	538.0	571.5	634.3	721.1	843.1	943.7	1013.3
102.5°	887.9	838.3	810.3	790.5	810.3	838.3	887.9	955.5	1032.9	1091.5	1093.7
105°	1157.6	1125.0	1097.5	1093.2	1097.5	1125.0	1157.6	1197.2	1219.5	1203.2	1117.2
107.5°	1295.7	1284.7	1275.4	1267.5	1275.4	1284.7	1295.7	1295.0	1264.4	1189.1	1049.6
110°	1335.6	1342.5	1340.7	1339.0	1340.7	1342.5	1335.6	1311.5	1251.3	1143.1	984.9



TEST NUMBER: P332260-935

CATALOG NUMBER: S123RDIP-S340D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1325.3	1346.5	1353.1	1353.4	1353.1	1346.5	1325.3	1281.3	1203.9	1082.5	920.9
115°	1270.2	1308.0	1325.3	1329.6	1325.3	1308.0	1270.2	1205.7	1112.1	985.8	836.2
117.5°	1179.7	1223.0	1247.8	1253.5	1247.8	1223.0	1179.7	1112.4	1017.4	904.0	774.9
120°	1116.4	1164.5	1185.2	1190.3	1185.2	1164.5	1116.4	1048.5	961.7	858.6	742.5
122.5°	1058.7	1102.0	1124.6	1131.2	1124.6	1102.0	1058.7	998.3	917.7	822.2	717.1
125°	983.2	1021.0	1042.5	1048.5	1042.5	1021.0	983.2	928.2	859.5	777.0	683.3
127.5°	923.2	955.5	974.9	980.4	974.9	955.5	923.2	874.2	811.7	737.2	653.7
130°	886.1	917.1	935.0	941.9	935.0	917.1	886.1	840.5	782.0	712.5	635.2
132.5°	852.4	883.3	899.3	904.1	899.3	883.3	852.4	809.6	753.9	689.1	617.9
135°	802.7	828.5	844.0	850.0	844.0	828.5	802.7	760.6	711.6	655.7	594.7
137.5°	749.6	775.8	788.8	792.7	788.8	775.8	749.6	714.2	671.8	623.6	573.6
140°	715.9	739.9	753.7	752.9	753.7	739.9	715.9	683.3	646.3	605.0	561.2
142.5°	682.9	704.2	716.6	715.7	716.6	704.2	682.9	655.0	622.9	587.2	549.5
145°	637.7	655.7	662.6	664.3	662.6	655.7	637.7	616.2	591.2	563.8	535.5
147.5°	602.6	614.8	621.4	622.1	621.4	614.8	602.6	586.3	568.6	546.4	523.9
150°	582.7	592.1	597.3	597.3	597.3	592.1	582.7	569.8	553.5	535.5	515.7
152.5°	564.8	573.6	576.7	576.7	576.7	573.6	564.8	554.7	541.1	525.1	508.1
155°	541.5	548.3	550.0	550.9	550.0	548.3	541.5	533.7	523.4	510.5	496.7
157.5°	521.0	526.2	527.5	527.4	527.5	526.2	521.0	514.3	506.2	496.2	484.7
160°	507.9	513.1	513.1	512.2	513.1	513.1	507.9	501.9	495.8	487.3	477.9
162.5°	494.9	499.3	499.3	498.4	499.3	499.3	494.9	490.9	485.6	477.7	469.6
165°	477.9	481.3	480.4	480.4	480.4	481.3	477.9	474.4	470.1	464.1	458.9
167.5°	461.7	464.1	463.2	463.2	463.2	464.1	461.7	460.1	457.0	453.6	449.6
170°	452.0	453.7	452.9	452.9	452.9	453.7	452.0	451.2	449.4	446.1	443.5
172.5°	443.8	445.6	444.0	443.3	444.0	445.6	443.8	443.7	442.6	439.9	438.0
175°	433.2	434.0	433.2	432.3	433.2	434.0	433.2	433.2	433.2	431.4	430.6
177.5°	426.6	427.3	425.9	425.9	425.9	427.3	426.6	427.3	427.3	426.6	425.9
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P332260-935

CATALOG NUMBER: S123RDIP-S340D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	447.3	449.5	451.8	453.8	457.0	458.5	460.5	461.4	463.7	467.3	470.2
5°	420.1	423.3	427.5	430.8	436.3	440.5	445.1	449.5	454.8	462.2	468.8
7.5°	397.0	400.1	405.2	411.6	417.5	423.5	429.8	435.8	443.2	453.9	464.4
10°	381.8	385.6	391.6	398.4	405.8	411.6	419.0	426.6	435.9	448.2	460.8
12.5°	368.6	371.4	378.4	384.9	393.3	400.7	407.9	416.9	427.4	440.4	455.6
15°	347.7	351.6	358.4	365.7	374.5	382.4	391.8	402.6	412.8	428.9	447.3
17.5°	326.6	332.7	339.8	347.9	354.5	365.3	375.5	386.6	399.2	416.2	436.5
20°	313.1	318.0	324.6	336.4	345.0	353.3	362.7	376.5	388.1	407.4	428.4
22.5°	301.7	305.2	312.7	322.4	332.5	342.0	351.6	364.8	379.2	397.4	420.3
25°	284.8	290.5	296.1	303.1	313.9	325.4	335.8	347.1	362.3	381.8	406.4
27.5°	268.4	273.5	279.0	287.6	295.8	306.5	317.5	330.3	346.6	367.2	392.3
30°	257.8	261.6	266.8	277.8	285.2	294.5	307.3	318.7	334.0	355.9	382.4
32.5°	246.8	251.8	257.5	266.0	275.2	283.9	295.6	308.0	323.6	345.1	372.2
35°	231.3	237.1	242.9	249.2	258.4	267.4	277.2	290.8	306.7	327.6	354.2
37.5°	217.0	221.6	226.4	234.1	242.8	251.4	260.6	274.1	289.0	311.5	336.0
40°	207.8	212.1	215.7	223.7	232.1	241.3	250.4	262.2	278.2	299.3	323.0
42.5°	197.9	201.7	206.6	213.3	222.3	230.1	239.1	250.3	265.4	286.8	307.5
45°	183.0	187.4	191.6	197.8	206.8	214.5	222.5	233.1	248.6	266.2	284.6
47.5°	167.4	171.9	176.7	182.7	190.5	198.3	206.3	215.7	229.8	247.1	259.6
50°	157.5	161.1	165.9	171.9	179.2	187.4	194.6	204.8	218.3	231.9	242.7
52.5°	147.2	150.5	155.9	162.3	169.0	176.2	183.8	192.6	204.7	217.6	226.2
55°	131.2	135.2	139.8	146.0	152.7	158.7	166.1	175.1	184.8	194.4	200.2
57.5°	116.2	119.6	123.5	129.8	135.6	142.8	149.5	156.4	165.4	172.6	176.4
60°	105.3	108.3	113.3	119.0	124.3	130.6	138.2	145.3	152.1	157.9	160.8
62.5°	95.1	98.5	102.9	108.1	113.9	119.9	126.5	132.4	138.4	143.4	145.5
65°	81.6	84.5	87.6	92.5	97.3	103.3	108.5	114.5	119.0	121.7	123.6
67.5°	69.5	71.3	73.7	77.0	81.7	87.0	92.0	96.7	100.4	102.3	103.9
70°	61.6	62.8	64.6	67.8	71.4	76.0	81.3	84.6	87.8	89.5	91.1
72.5°	53.7	55.3	56.9	59.5	62.4	65.8	69.6	73.7	75.5	77.4	78.4
75°	40.7	43.0	45.1	46.8	48.7	51.3	54.8	57.3	58.4	60.0	60.2
77.5°	30.7	31.3	32.8	34.8	36.5	38.4	40.6	42.9	43.4	44.2	44.8
80°	25.3	25.3	25.3	26.5	28.5	29.9	31.9	33.1	33.9	34.1	34.3
82.5°	20.3	20.3	20.1	20.4	21.1	21.9	23.7	25.1	25.7	25.6	25.1
85°	13.3	12.8	12.8	12.7	12.8	12.4	12.2	13.0	14.2	14.2	13.9
87.5°	9.6	9.6	9.2	8.5	7.9	7.2	6.4	6.2	5.7	5.9	5.5
90°	20.7	21.5	18.9	16.4	13.8	11.2	9.5	7.7	5.2	3.4	1.7
92.5°	99.7	132.2	145.4	109.2	72.2	49.7	36.9	29.7	23.1	15.8	10.7
95°	413.4	509.6	453.7	312.8	184.8	111.8	78.2	55.9	41.2	31.8	29.2
97.5°	845.0	789.8	578.2	343.3	198.9	129.1	92.8	70.8	58.1	50.7	49.9
100°	983.2	813.9	550.0	324.0	196.8	136.6	103.1	82.5	70.5	64.5	63.6
102.5°	990.1	769.2	508.8	307.5	199.6	145.6	114.9	96.3	84.9	79.6	78.0
105°	937.6	691.0	458.1	295.7	207.2	160.7	134.1	117.8	107.5	102.3	99.7
107.5°	845.8	621.9	425.8	294.8	221.2	180.5	155.8	140.4	130.3	125.3	122.7
110°	788.1	582.7	413.4	298.3	232.9	194.2	170.1	155.6	146.1	141.8	139.2



TEST NUMBER: P332260-935

CATALOG NUMBER: S123RDIP-S340D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	737.9	556.6	406.5	305.1	244.6	208.7	185.3	170.7	161.3	157.0	154.4
115°	677.3	528.6	403.9	316.2	263.8	231.2	208.0	193.4	184.8	179.6	176.2
117.5°	640.6	512.0	405.4	331.1	284.3	252.0	230.5	214.1	206.3	202.0	198.0
120°	621.4	504.5	408.2	342.1	297.4	266.4	245.0	228.6	220.0	215.7	213.1
122.5°	605.5	499.6	413.0	352.4	311.1	280.9	258.0	242.4	233.1	228.8	226.2
125°	585.3	493.4	420.3	368.7	330.9	300.8	277.6	261.2	251.8	246.7	245.0
127.5°	567.4	490.3	428.5	382.1	348.1	319.0	295.8	277.8	268.1	261.7	259.2
130°	557.8	488.2	434.0	391.1	358.3	330.0	306.8	288.8	278.4	270.7	268.1
132.5°	548.8	487.5	438.2	399.3	367.3	339.7	317.1	299.1	286.7	278.3	275.0
135°	537.2	486.5	444.4	409.9	380.7	354.0	330.9	312.8	300.0	290.5	287.1
137.5°	527.0	484.6	448.4	417.8	390.0	364.4	342.9	325.0	311.3	302.0	298.4
140°	520.8	483.9	451.2	422.0	396.2	371.3	349.8	332.6	318.8	310.2	306.0
142.5°	515.3	482.5	453.2	426.1	401.1	376.8	356.6	339.5	327.1	317.8	314.2
145°	507.9	480.4	454.6	430.6	407.3	385.0	365.2	350.7	337.8	330.0	327.4
147.5°	500.7	477.2	454.6	433.3	412.5	392.1	375.2	361.1	350.0	342.4	340.9
150°	495.8	474.4	454.6	434.0	415.9	396.2	380.7	368.7	357.5	350.7	349.8
152.5°	490.4	471.0	452.5	435.4	418.0	401.1	386.2	375.6	365.8	358.9	358.7
155°	482.2	464.9	450.3	435.8	422.0	407.3	395.4	385.9	377.3	372.1	372.1
157.5°	472.9	459.6	447.5	436.6	424.2	412.5	403.2	395.2	387.6	383.5	382.8
160°	466.7	455.5	446.1	436.6	426.3	415.9	407.3	401.3	394.5	391.1	391.1
162.5°	460.5	451.3	443.3	435.9	427.0	418.0	410.8	405.4	400.0	397.3	397.3
165°	452.0	445.2	439.2	434.0	428.0	421.1	415.1	411.6	407.3	405.6	406.5
167.5°	444.0	439.0	435.1	432.7	427.8	422.8	419.0	416.6	413.4	412.5	413.5
170°	439.2	434.9	432.3	430.6	427.1	422.8	421.1	419.4	416.8	415.9	417.7
172.5°	434.4	431.4	430.2	429.9	427.1	423.5	422.5	421.5	419.6	419.4	420.4
175°	428.9	427.1	427.1	428.0	426.3	424.6	423.7	423.7	422.0	422.8	423.7
177.5°	425.2	424.6	425.2	426.6	425.2	424.6	424.6	424.6	423.9	424.6	425.2
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P332260-935

CATALOG NUMBER: S123RDIP-S340D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	471.1	472.9	475.2	478.5	481.1	483.4	483.8	484.5	486.1	488.8	490.9
5°	474.2	478.8	486.2	493.4	501.3	507.7	513.8	518.0	521.9	530.4	537.2
7.5°	473.2	483.5	495.2	508.1	521.2	533.9	545.7	556.3	566.8	579.1	593.1
10°	472.6	484.7	500.3	516.9	535.2	553.0	570.3	583.8	599.3	613.5	631.3
12.5°	469.6	486.9	505.6	526.8	549.3	569.9	592.6	611.1	629.0	649.4	670.1
15°	465.5	486.6	510.3	538.6	572.7	597.5	620.9	653.2	675.2	697.2	726.9
17.5°	458.3	484.1	513.6	550.4	578.8	612.3	647.2	672.8	702.5	733.6	760.4
20°	452.5	482.4	515.6	551.6	588.0	624.2	658.1	688.6	719.4	755.3	777.3
22.5°	446.8	476.3	510.7	549.1	588.1	626.4	664.7	700.5	735.0	771.3	799.4
25°	434.5	469.6	506.9	546.0	584.5	626.6	672.4	712.3	755.0	792.4	819.1
27.5°	422.1	454.3	491.4	531.1	573.9	623.6	677.4	722.8	765.6	792.4	800.7
30°	410.8	444.9	479.1	519.4	565.7	621.2	678.4	730.4	765.4	777.1	768.4
32.5°	399.4	430.3	464.1	505.4	554.6	615.3	679.7	725.9	747.0	738.1	703.0
35°	379.4	407.2	439.9	481.2	537.8	612.0	674.4	705.7	700.5	650.3	584.1
37.5°	357.8	380.6	410.8	454.0	520.4	599.0	651.6	656.3	611.1	534.1	457.6
40°	340.8	361.3	392.4	437.5	506.9	586.2	628.7	610.0	540.0	454.3	390.5
42.5°	324.3	341.6	371.5	420.2	494.0	568.6	594.5	553.9	473.1	392.1	334.1
45°	296.3	312.5	342.6	392.5	467.8	535.2	531.8	461.2	380.3	315.1	267.0
47.5°	269.8	284.0	312.2	363.2	437.0	485.0	453.1	378.0	309.4	257.1	222.7
50°	251.0	265.0	293.1	343.5	412.2	447.3	401.8	329.4	266.6	223.3	196.0
52.5°	233.0	246.7	272.3	321.4	382.4	403.4	354.5	287.3	235.0	197.6	174.2
55°	207.8	218.3	241.3	288.3	333.8	338.6	289.0	232.9	189.8	163.7	147.7
57.5°	182.2	191.1	214.0	251.3	283.3	280.8	233.8	185.2	156.2	136.8	125.2
60°	165.5	174.4	194.4	226.4	250.6	242.1	199.0	159.9	135.0	120.8	111.5
62.5°	149.9	156.8	175.6	199.1	216.4	206.8	170.1	137.8	118.0	106.0	98.7
65°	127.3	133.0	148.0	160.3	169.9	160.7	130.2	107.7	93.5	85.1	80.1
67.5°	106.0	109.5	119.0	123.5	130.3	120.1	97.9	82.8	74.7	67.7	64.1
70°	92.5	95.1	100.1	103.8	105.5	95.1	78.6	67.6	60.8	55.8	53.6
72.5°	79.0	81.3	82.3	85.2	84.3	74.6	63.2	54.4	49.5	46.1	43.3
75°	60.4	61.4	60.4	59.2	56.6	49.8	41.9	37.5	33.9	32.3	31.3
77.5°	44.0	43.7	42.4	40.5	36.0	31.7	27.5	26.0	24.5	23.6	23.2
80°	33.9	33.1	31.9	28.8	25.1	22.0	21.1	20.1	19.5	18.4	18.3
82.5°	25.2	24.7	22.7	20.2	17.6	16.1	15.3	14.9	14.3	13.8	13.8
85°	13.4	12.8	10.6	9.2	8.9	8.4	8.3	8.3	7.4	7.2	7.2
87.5°	5.0	4.4	4.7	4.6	5.0	5.2	5.9	6.0	6.4	6.4	6.2
90°	3.4	5.2	7.7	9.5	11.2	13.8	16.4	18.9	21.5	20.7	21.5
92.5°	15.8	23.1	29.7	36.9	49.7	72.2	109.2	145.4	132.2	99.7	72.3
95°	31.8	41.2	55.9	78.2	111.8	184.8	312.8	453.7	509.6	413.4	309.4
97.5°	50.7	58.1	70.8	92.8	129.1	198.9	343.3	578.2	789.8	845.0	771.3
100°	64.5	70.5	82.5	103.1	136.6	196.8	324.0	550.0	813.9	983.2	1013.3
102.5°	79.6	84.9	96.3	114.9	145.6	199.6	307.5	508.8	769.2	990.1	1093.7
105°	102.3	107.5	117.8	134.1	160.7	207.2	295.7	458.1	691.0	937.6	1117.2
107.5°	125.3	130.3	140.4	155.8	180.5	221.2	294.8	425.8	621.9	845.8	1049.6
110°	141.8	146.1	155.6	170.1	194.2	232.9	298.3	413.4	582.7	788.1	984.9





TEST NUMBER: P332260-935

CATALOG NUMBER: S123RDIP-S340D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	157.0	161.3	170.7	185.3	208.7	244.6	305.1	406.5	556.6	737.9	920.9
115°	179.6	184.8	193.4	208.0	231.2	263.8	316.2	403.9	528.6	677.3	836.2
117.5°	202.0	206.3	214.1	230.5	252.0	284.3	331.1	405.4	512.0	640.6	774.9
120°	215.7	220.0	228.6	245.0	266.4	297.4	342.1	408.2	504.5	621.4	742.5
122.5°	228.8	233.1	242.4	258.0	280.9	311.1	352.4	413.0	499.6	605.5	717.1
125°	246.7	251.8	261.2	277.6	300.8	330.9	368.7	420.3	493.4	585.3	683.3
127.5°	261.7	268.1	277.8	295.8	319.0	348.1	382.1	428.5	490.3	567.4	653.7
130°	270.7	278.4	288.8	306.8	330.0	358.3	391.1	434.0	488.2	557.8	635.2
132.5°	278.3	286.7	299.1	317.1	339.7	367.3	399.3	438.2	487.5	548.8	617.9
135°	290.5	300.0	312.8	330.9	354.0	380.7	409.9	444.4	486.5	537.2	594.7
137.5°	302.0	311.3	325.0	342.9	364.4	390.0	417.8	448.4	484.6	527.0	573.6
140°	310.2	318.8	332.6	349.8	371.3	396.2	422.0	451.2	483.9	520.8	561.2
142.5°	317.8	327.1	339.5	356.6	376.8	401.1	426.1	453.2	482.5	515.3	549.5
145°	330.0	337.8	350.7	365.2	385.0	407.3	430.6	454.6	480.4	507.9	535.5
147.5°	342.4	350.0	361.1	375.2	392.1	412.5	433.3	454.6	477.2	500.7	523.9
150°	350.7	357.5	368.7	380.7	396.2	415.9	434.0	454.6	474.4	495.8	515.7
152.5°	358.9	365.8	375.6	386.2	401.1	418.0	435.4	452.5	471.0	490.4	508.1
155°	372.1	377.3	385.9	395.4	407.3	422.0	435.8	450.3	464.9	482.2	496.7
157.5°	383.5	387.6	395.2	403.2	412.5	424.2	436.6	447.5	459.6	472.9	484.7
160°	391.1	394.5	401.3	407.3	415.9	426.3	436.6	446.1	455.5	466.7	477.9
162.5°	397.3	400.0	405.4	410.8	418.0	427.0	435.9	443.3	451.3	460.5	469.6
165°	405.6	407.3	411.6	415.1	421.1	428.0	434.0	439.2	445.2	452.0	458.9
167.5°	412.5	413.4	416.6	419.0	422.8	427.8	432.7	435.1	439.0	444.0	449.6
170°	415.9	416.8	419.4	421.1	422.8	427.1	430.6	432.3	434.9	439.2	443.5
172.5°	419.4	419.6	421.5	422.5	423.5	427.1	429.9	430.2	431.4	434.4	438.0
175°	422.8	422.0	423.7	423.7	424.6	426.3	428.0	427.1	427.1	428.9	430.6
177.5°	424.6	423.9	424.6	424.6	424.6	425.2	426.6	425.2	424.6	425.2	425.9
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P332260-935

CATALOG NUMBER: S123RDIP-S340D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	494.3	494.3	494.9	497.3	497.7	499.7	499.1
5°	543.2	547.0	548.5	554.5	558.0	559.6	556.5
7.5°	603.0	613.8	618.9	625.3	630.8	632.5	628.1
10°	646.7	658.0	667.4	673.2	678.6	682.3	686.8
12.5°	688.9	702.7	711.7	719.9	725.5	730.0	730.8
15°	734.8	755.6	771.5	783.2	788.9	791.9	790.7
17.5°	781.0	800.4	811.7	823.5	831.6	832.0	832.2
20°	807.2	826.0	839.1	847.9	857.0	856.5	858.6
22.5°	824.7	839.6	849.5	855.9	859.0	857.5	857.9
25°	832.8	837.3	835.5	825.3	822.6	813.2	814.9
27.5°	790.7	769.8	748.2	720.5	698.5	681.1	681.9
30°	733.4	696.5	654.4	619.1	587.4	578.5	559.6
32.5°	653.3	598.0	548.6	515.7	488.5	481.1	464.7
35°	517.5	463.7	413.0	382.5	370.5	353.6	353.4
37.5°	402.3	354.9	328.1	305.2	293.3	283.0	282.1
40°	338.4	301.5	281.2	264.8	253.0	245.3	243.5
42.5°	293.8	264.0	245.0	234.8	225.7	221.7	218.8
45°	239.9	219.8	206.6	197.4	193.2	190.2	188.6
47.5°	200.7	187.3	178.2	172.0	168.7	165.5	166.3
50°	179.3	168.3	161.7	155.8	153.3	151.0	151.3
52.5°	162.1	152.2	146.9	142.7	139.5	137.8	137.2
55°	137.6	131.4	126.0	123.0	121.1	119.0	118.4
57.5°	117.4	112.5	108.1	104.8	104.3	102.2	102.5
60°	103.9	99.9	96.3	94.5	93.1	91.3	91.9
62.5°	92.8	89.5	86.2	84.7	83.3	82.0	82.2
65°	76.0	72.8	70.8	70.0	69.4	68.8	68.2
67.5°	60.6	58.6	57.3	55.6	54.4	54.2	53.6
70°	51.0	48.3	46.1	43.9	43.3	43.1	43.3
72.5°	40.8	39.2	38.6	37.5	37.4	36.9	37.2
75°	30.7	30.0	29.7	28.8	28.8	28.8	28.8
77.5°	22.6	22.3	22.0	21.9	21.7	21.4	21.4
80°	17.7	17.5	17.0	17.0	16.9	17.0	16.9
82.5°	13.3	13.3	12.9	12.9	12.7	12.6	12.7
85°	6.8	6.6	7.1	6.6	6.8	6.5	6.8
87.5°	6.4	6.5	6.7	6.5	6.6	7.1	6.6
90°	22.4	23.2	24.9	24.0	24.9	25.7	24.9
92.5°	57.4	50.7	46.2	44.7	42.1	43.0	41.4
95°	209.7	164.2	133.2	116.9	109.2	103.1	99.7
97.5°	617.8	506.9	404.1	340.7	302.0	278.8	271.4
100°	943.7	843.1	721.1	634.3	571.5	538.0	538.9
102.5°	1091.5	1032.9	955.5	887.9	838.3	810.3	790.5
105°	1203.2	1219.5	1197.2	1157.6	1125.0	1097.5	1093.2
107.5°	1189.1	1264.4	1295.0	1295.7	1284.7	1275.4	1267.5
110°	1143.1	1251.3	1311.5	1335.6	1342.5	1340.7	1339.0



TEST NUMBER: P332260-935

CATALOG NUMBER: S123RDIP-S340D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1082.5	1203.9	1281.3	1325.3	1346.5	1353.1	1353.4
115°	985.8	1112.1	1205.7	1270.2	1308.0	1325.3	1329.6
117.5°	904.0	1017.4	1112.4	1179.7	1223.0	1247.8	1253.5
120°	858.6	961.7	1048.5	1116.4	1164.5	1185.2	1190.3
122.5°	822.2	917.7	998.3	1058.7	1102.0	1124.6	1131.2
125°	777.0	859.5	928.2	983.2	1021.0	1042.5	1048.5
127.5°	737.2	811.7	874.2	923.2	955.5	974.9	980.4
130°	712.5	782.0	840.5	886.1	917.1	935.0	941.9
132.5°	689.1	753.9	809.6	852.4	883.3	899.3	904.1
135°	655.7	711.6	760.6	802.7	828.5	844.0	850.0
137.5°	623.6	671.8	714.2	749.6	775.8	788.8	792.7
140°	605.0	646.3	683.3	715.9	739.9	753.7	752.9
142.5°	587.2	622.9	655.0	682.9	704.2	716.6	715.7
145°	563.8	591.2	616.2	637.7	655.7	662.6	664.3
147.5°	546.4	568.6	586.3	602.6	614.8	621.4	622.1
150°	535.5	553.5	569.8	582.7	592.1	597.3	597.3
152.5°	525.1	541.1	554.7	564.8	573.6	576.7	576.7
155°	510.5	523.4	533.7	541.5	548.3	550.0	550.9
157.5°	496.2	506.2	514.3	521.0	526.2	527.5	527.4
160°	487.3	495.8	501.9	507.9	513.1	513.1	512.2
162.5°	477.7	485.6	490.9	494.9	499.3	499.3	498.4
165°	464.1	470.1	474.4	477.9	481.3	480.4	480.4
167.5°	453.6	457.0	460.1	461.7	464.1	463.2	463.2
170°	446.1	449.4	451.2	452.0	453.7	452.9	452.9
172.5°	439.9	442.6	443.7	443.8	445.6	444.0	443.3
175°	431.4	433.2	433.2	433.2	434.0	433.2	432.3
177.5°	426.6	427.3	427.3	426.6	427.3	425.9	425.9
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6

(END OF REPORT)