

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832107

Luminaire Tested: S123RDIP-S340D365U935-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832107
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D365U935-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2517.4 lumens
Efficiency: N/A
Efficacy: 112.4 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 22.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832107

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P832107

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	56	56	56	50				
1	99	95	91	88	91	88	85	82	74	72	70	62	61	59	51	50	49	44				
2	91	84	78	73	83	78	73	68	66	63	60	56	53	51	46	44	43	38				
3	83	74	67	62	77	69	63	58	59	55	51	50	47	44	42	39	37	34				
4	77	66	59	53	71	62	55	50	53	48	44	45	42	39	38	35	33	30				
5	71	60	52	46	65	56	49	44	48	43	39	41	37	34	35	32	30	26				
6	66	54	46	41	61	51	44	39	44	39	35	38	34	31	32	29	27	24				
7	61	49	42	36	56	46	39	35	40	35	31	35	31	28	30	26	24	22				
8	57	45	38	33	53	42	36	31	37	32	28	32	28	25	27	24	22	20				
9	53	41	34	29	49	39	33	28	34	29	25	30	26	23	26	23	20	18				
10	50	38	31	27	46	36	30	26	32	27	23	28	24	21	24	21	19	17				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	10296	10296	10296	10296	10296
5°	12225	11835	10361	8375	7775
10°	11076	12021	10309	6710	5757
15°	7626	10307	10200	5485	4553
20°	5306	7936	9995	4624	4002
25°	4043	6048	9697	4111	3689
30°	3519	4835	9324	3817	3417
35°	3231	4079	8796	3569	3169
40°	2948	3642	8106	3326	2942
45°	2662	3331	7360	3095	2716
50°	2416	3073	6482	2870	2436
55°	2186	2822	5637	2650	2091
60°	1959	2566	4898	2407	1976
65°	1808	2277	4215	2162	1867
70°	1470	1970	3679	1958	1517
75°	1289	1564	3115	1622	1339
80°	1165	1327	2554	1364	1265
85°	1062	1161	1939	1235	1161

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 7767 cd/sqm



TEST NUMBER: P832107

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.2	3.5
10°-20°	201.7	8.0
20°-30°	231.5	9.2
30°-40°	228.2	9.1
40°-50°	201.2	8.0
50°-60°	154.8	6.1
60°-70°	101.8	4.0
70°-80°	49.4	2.0
80°-90°	13.3	0.5
90°-100°	14.4	0.6
100°-110°	69.8	2.8
110°-120°	171.1	6.8
120°-130°	217.2	8.6
130°-140°	232.0	9.2
140°-150°	217.0	8.6
150°-160°	175.0	7.0
160°-170°	112.9	4.5
170°-180°	38.9	1.5
0°-30°	520.4	20.7
0°-40°	748.5	29.7
0°-60°	1104.5	43.9
0°-90°	1269.0	50.4
90°-120°	255.3	10.1
90°-150°	921.5	36.6
90°-180°	1248.0	49.6
0°-180°	2517.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	956	956	956	956	956	
5°	1131	1095	959	775	720	103
15°	684	925	915	492	409	193
25°	340	509	816	346	311	161
35°	246	310	669	272	241	153
45°	175	219	484	203	178	136
55°	116	150	300	141	111	104
65°	71	89	166	85	73	70
75°	31	38	75	39	32	33
85°	9	9	16	10	9	9
90°	9	7	0	7	9	4
95°	12	9	19	9	12	10
105°	13	67	91	67	13	28
115°	179	175	170	175	179	168
125°	245	243	240	243	245	219
135°	302	302	298	302	302	233
145°	348	347	344	347	348	217
155°	379	379	379	379	379	175
165°	399	399	400	399	399	113
175°	408	408	410	408	408	39
180°	410	410	410	410	410	



TEST NUMBER: P832107

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5
2.5°	1060.0	1056.7	1053.4	1052.4	1051.4	1048.3	1045.1	1038.1	1031.0	1023.8	1016.5
5°	1131.4	1131.8	1132.2	1131.2	1130.2	1126.1	1122.0	1113.4	1104.7	1095.3	1085.9
7.5°	1109.5	1115.7	1122.0	1123.2	1124.4	1127.5	1130.6	1128.7	1126.7	1123.2	1119.6
10°	1013.4	1013.0	1012.6	1019.6	1026.7	1047.7	1068.7	1079.5	1090.2	1099.8	1109.5
12.5°	856.5	857.1	857.7	880.8	904.0	923.8	943.6	971.0	998.5	1028.1	1057.7
15°	684.3	693.9	703.6	724.1	744.7	774.5	804.3	841.2	878.1	924.9	971.8
17.5°	562.0	566.1	570.2	590.0	609.8	638.1	666.3	708.1	749.8	810.2	870.6
20°	463.2	466.9	470.6	484.9	499.2	526.3	553.4	593.2	633.0	692.8	752.6
22.5°	386.7	393.9	401.2	410.8	420.4	440.0	459.6	500.2	540.8	595.3	649.8
25°	340.4	343.7	347.1	355.3	363.5	382.4	401.2	428.1	454.9	509.2	563.6
27.5°	309.0	310.0	311.0	317.1	323.1	335.3	347.5	372.4	397.3	442.0	486.7
30°	283.1	284.9	286.7	291.4	296.1	304.9	313.7	331.4	349.0	389.0	429.0
32.5°	263.1	264.1	265.1	269.0	273.0	279.4	285.9	299.8	313.7	344.3	374.9
35°	245.9	246.1	246.3	249.2	252.2	258.4	264.7	276.3	287.9	310.4	333.0
37.5°	226.3	227.7	229.0	231.2	233.3	238.8	244.3	253.7	263.1	281.8	300.4
40°	209.8	211.0	212.2	214.7	217.3	221.6	225.9	234.5	243.1	259.2	275.3
42.5°	193.3	194.1	194.9	197.5	200.0	205.3	210.6	217.5	224.3	237.7	251.0
45°	174.9	176.9	178.8	181.6	184.3	188.8	193.3	200.4	207.5	218.8	230.2
47.5°	159.6	160.6	161.6	163.9	166.3	171.8	177.3	183.5	189.8	200.4	211.0
50°	144.3	144.7	145.1	147.3	149.4	154.3	159.2	166.5	173.7	183.5	193.3
52.5°	129.8	130.8	131.8	133.9	136.1	139.4	142.8	150.2	157.7	167.3	176.9
55°	116.5	117.1	117.7	119.2	120.8	124.7	128.6	135.1	141.6	150.4	159.2
57.5°	103.9	104.7	105.5	106.7	107.8	111.4	114.9	120.6	126.3	135.1	143.9
60°	91.0	92.0	92.9	94.3	95.7	98.4	101.2	106.3	111.4	119.2	127.1
62.5°	81.6	81.8	82.0	83.1	84.3	86.3	88.2	92.4	96.5	104.3	112.2
65°	71.0	71.6	72.2	72.7	73.3	74.9	76.5	80.0	83.5	89.4	95.3
67.5°	60.0	60.6	61.2	62.2	63.1	64.5	65.9	68.2	70.6	76.1	81.6
70°	46.7	46.7	46.7	48.2	49.8	52.2	54.5	56.3	58.0	62.6	67.1
72.5°	38.0	38.2	38.4	38.6	38.8	40.2	41.6	44.5	47.5	50.2	52.9
75°	31.0	31.2	31.4	31.6	31.8	32.2	32.6	33.5	34.5	37.6	40.8
77.5°	24.7	24.9	25.1	25.3	25.5	25.9	26.3	26.7	27.1	28.2	29.4
80°	18.8	19.0	19.2	19.4	19.6	19.8	20.0	20.4	20.8	21.4	22.0
82.5°	13.7	13.7	13.7	13.7	13.7	14.1	14.5	14.5	14.5	14.9	15.3
85°	8.6	8.6	8.6	8.8	9.0	9.0	9.0	9.2	9.4	9.4	9.4
87.5°	3.9	3.7	3.5	3.7	3.9	3.9	3.9	4.1	4.3	4.3	4.3
90°	9.1	9.0	8.9	8.7	8.6	8.4	8.1	7.8	7.6	7.3	6.4
92.5°	10.3	10.3	10.2	10.1	10.1	9.8	9.3	8.9	8.4	7.9	7.3
95°	11.6	11.6	11.6	11.6	11.6	11.3	10.9	10.4	9.9	9.4	8.7
97.5°	12.5	12.4	12.3	12.3	12.2	11.9	11.4	10.8	10.3	9.7	13.2
100°	12.8	12.7	12.6	12.6	12.5	12.2	11.7	11.1	10.6	10.0	20.6
102.5°	13.1	12.9	12.8	12.7	12.5	13.6	15.8	18.1	20.3	22.5	34.3
105°	13.4	13.3	13.1	13.0	12.8	18.8	30.7	42.7	54.7	66.6	72.7
107.5°	31.6	40.5	49.4	58.2	67.1	76.7	87.1	97.5	107.9	118.4	117.3
110°	83.7	93.3	103.0	112.7	122.3	128.3	130.5	132.8	135.0	137.2	136.5



TEST NUMBER: P832107

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	158.5	158.6	158.8	158.9	159.1	158.8	158.2	157.6	157.0	156.4	155.6
115°	178.9	178.6	178.4	178.1	177.8	177.3	176.7	176.0	175.3	174.6	174.0
117.5°	195.3	195.3	195.2	195.1	195.1	194.8	194.2	193.7	193.1	192.6	192.3
120°	212.4	212.4	212.4	212.4	212.4	212.1	211.6	211.0	210.5	209.9	209.7
122.5°	229.1	229.0	229.0	228.9	228.8	228.6	228.3	228.0	227.6	227.3	227.0
125°	244.6	244.5	244.3	244.2	244.1	243.9	243.8	243.7	243.5	243.4	243.1
127.5°	259.8	260.0	260.1	260.2	260.4	260.3	260.1	259.9	259.7	259.5	259.2
130°	274.4	274.6	274.7	274.8	275.0	274.9	274.6	274.4	274.1	273.8	273.6
132.5°	287.8	288.0	288.2	288.4	288.6	288.6	288.3	288.1	287.8	287.5	287.3
135°	301.5	301.7	301.9	302.1	302.3	302.3	302.1	301.9	301.7	301.5	301.2
137.5°	314.6	314.7	314.9	315.0	315.1	315.0	314.7	314.4	314.0	313.7	313.5
140°	326.2	326.3	326.4	326.6	326.7	326.6	326.4	326.1	325.8	325.5	325.3
142.5°	336.8	337.0	337.2	337.4	337.6	337.6	337.4	337.2	337.0	336.8	336.6
145°	347.8	347.8	347.8	347.8	347.8	347.7	347.6	347.4	347.3	347.1	347.0
147.5°	355.7	356.0	356.3	356.7	357.0	357.1	357.0	356.9	356.7	356.6	356.4
150°	364.8	365.0	365.2	365.4	365.6	365.6	365.5	365.4	365.2	365.1	365.0
152.5°	372.1	372.4	372.8	373.1	373.5	373.5	373.2	372.9	372.7	372.4	372.3
155°	378.8	379.2	379.6	380.0	380.4	380.4	380.1	379.8	379.4	379.1	379.0
157.5°	384.6	385.1	385.7	386.2	386.7	386.8	386.4	386.0	385.6	385.2	385.2
160°	390.0	390.5	391.0	391.5	391.9	392.0	391.6	391.2	390.8	390.4	390.4
162.5°	395.2	395.6	396.0	396.4	396.8	396.8	396.3	395.9	395.4	394.9	395.0
165°	399.2	399.6	400.1	400.6	401.1	401.0	400.5	400.0	399.4	398.9	398.9
167.5°	402.2	402.8	403.3	403.8	404.4	404.4	403.8	403.3	402.8	402.2	402.2
170°	405.0	405.5	406.0	406.6	407.1	407.1	406.6	406.0	405.5	405.0	405.0
172.5°	406.5	407.1	407.7	408.3	408.9	408.9	408.4	407.9	407.3	406.8	406.7
175°	408.0	408.5	409.1	409.6	410.2	410.2	409.7	409.3	408.8	408.3	408.2
177.5°	408.3	409.0	409.7	410.3	411.0	411.1	410.5	410.0	409.5	408.9	408.8
180°	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5



TEST NUMBER: P832107

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5
2.5°	1015.5	1014.5	1005.1	995.7	986.5	977.3	970.4	963.6	952.0	940.4	933.2
5°	1078.5	1071.0	1056.1	1041.2	1018.9	996.5	977.7	958.9	934.9	911.0	891.0
7.5°	1113.6	1107.5	1089.5	1071.4	1041.8	1012.2	982.8	953.4	918.1	882.8	852.6
10°	1114.6	1119.6	1104.7	1089.8	1056.5	1023.2	983.2	943.2	895.7	848.3	809.2
12.5°	1079.6	1101.6	1098.5	1095.3	1061.4	1027.5	978.9	930.2	872.0	813.8	764.9
15°	1014.4	1056.9	1069.5	1082.0	1054.0	1025.9	970.6	915.3	846.9	778.5	722.4
17.5°	930.2	989.8	1023.0	1056.1	1035.7	1015.3	954.7	894.2	817.1	740.0	679.0
20°	830.6	908.7	960.6	1012.6	1005.1	997.7	935.1	872.6	789.4	706.3	640.2
22.5°	732.2	814.5	886.3	958.1	965.7	973.4	910.2	847.1	756.1	665.1	597.9
25°	647.3	731.0	816.5	902.0	919.3	936.5	876.5	816.5	722.2	627.9	561.0
27.5°	566.3	645.9	740.0	834.1	865.5	896.9	842.0	787.1	688.8	590.6	523.9
30°	500.2	571.4	667.5	763.6	807.3	851.0	800.6	750.2	652.8	555.3	490.0
32.5°	438.6	502.4	598.8	695.3	746.1	796.9	753.4	709.8	616.1	522.4	457.9
35°	390.0	447.1	537.1	627.1	683.9	740.8	705.1	669.4	577.9	486.3	425.3
37.5°	348.2	396.1	480.6	565.1	625.5	685.9	656.1	626.3	540.2	454.1	396.5
40°	313.7	352.2	430.8	509.4	568.6	627.9	602.4	576.9	499.8	422.8	368.8
42.5°	284.1	317.3	387.9	458.4	512.8	567.1	550.2	533.4	463.5	393.7	343.7
45°	258.0	285.9	348.1	410.2	460.2	510.2	496.9	483.5	423.3	363.2	317.3
47.5°	234.9	258.8	314.3	369.8	414.7	459.6	447.3	434.9	385.1	335.3	293.5
50°	213.7	234.1	280.4	326.7	367.1	407.5	397.3	387.1	345.9	304.7	268.6
52.5°	193.7	210.6	252.2	293.7	326.3	358.8	351.0	343.2	311.4	279.6	246.9
55°	174.7	190.2	225.3	260.4	288.2	316.1	308.2	300.4	275.7	251.0	222.2
57.5°	157.5	171.0	199.4	227.9	250.0	272.2	268.4	264.7	244.1	223.5	199.8
60°	139.2	151.4	175.9	200.4	218.2	236.1	231.8	227.5	212.8	198.0	177.7
62.5°	122.9	133.7	153.3	172.9	187.5	202.0	198.8	195.7	184.5	173.3	156.5
65°	105.9	116.5	132.4	148.2	159.6	171.0	168.2	165.5	157.1	148.6	135.1
67.5°	90.4	99.2	112.9	126.7	134.3	142.0	140.4	138.8	132.4	125.9	115.3
70°	74.7	82.4	93.7	105.1	110.4	115.7	116.3	116.9	111.0	105.1	97.3
72.5°	59.0	65.1	75.7	86.3	90.4	94.5	94.3	94.1	90.6	87.1	80.0
75°	45.3	49.8	58.0	66.3	69.8	73.3	74.1	74.9	71.6	68.2	64.3
77.5°	32.6	35.7	42.0	48.2	52.2	56.1	56.5	56.9	55.3	53.7	50.0
80°	22.9	23.9	27.8	31.8	35.9	40.0	40.6	41.2	39.6	38.0	35.7
82.5°	15.9	16.5	17.8	19.2	22.5	25.9	26.7	27.5	26.7	25.9	23.3
85°	9.6	9.8	10.4	11.0	12.5	14.1	14.9	15.7	15.3	14.9	13.5
87.5°	4.3	4.3	4.5	4.7	5.1	5.5	6.5	7.5	6.9	6.3	5.7
90°	5.5	4.7	3.8	3.0	2.3	1.7	1.0	0.3	1.0	1.7	2.3
92.5°	6.7	6.1	5.5	5.4	5.8	6.2	6.6	7.0	6.6	6.2	5.8
95°	7.9	7.2	6.5	7.5	10.2	13.0	15.8	18.6	15.8	13.0	10.2
97.5°	16.6	20.1	23.5	26.2	28.1	30.0	31.9	33.8	31.9	30.0	28.1
100°	31.1	41.7	52.2	56.8	55.5	54.1	52.8	51.4	52.8	54.1	55.5
102.5°	46.0	57.8	69.6	75.0	74.1	73.3	72.4	71.5	72.4	73.3	74.1
105°	78.8	84.9	91.0	93.6	92.9	92.2	91.4	90.7	91.4	92.2	92.9
107.5°	116.3	115.3	114.3	113.5	112.9	112.3	111.7	111.1	111.7	112.3	112.9
110°	135.7	135.0	134.2	133.6	133.1	132.5	132.0	131.4	132.0	132.5	133.1



TEST NUMBER: P832107

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	154.9	154.2	153.4	152.8	152.3	151.9	151.4	150.9	151.4	151.9	152.3
115°	173.4	172.8	172.2	171.7	171.3	170.9	170.5	170.1	170.5	170.9	171.3
117.5°	191.9	191.6	191.2	190.8	190.4	189.9	189.4	188.9	189.4	189.9	190.4
120°	209.5	209.3	209.1	208.7	208.1	207.5	206.9	206.3	206.9	207.5	208.1
122.5°	226.7	226.5	226.2	225.8	225.3	224.9	224.4	223.9	224.4	224.9	225.3
125°	242.9	242.6	242.3	241.9	241.4	240.8	240.3	239.7	240.3	240.8	241.4
127.5°	258.8	258.5	258.2	257.7	257.2	256.7	256.1	255.6	256.1	256.7	257.2
130°	273.3	273.0	272.7	272.3	271.8	271.3	270.7	270.2	270.7	271.3	271.8
132.5°	287.1	286.9	286.7	286.3	285.8	285.3	284.7	284.2	284.7	285.3	285.8
135°	301.0	300.7	300.4	300.1	299.7	299.3	298.9	298.5	298.9	299.3	299.7
137.5°	313.4	313.3	313.1	312.8	312.3	311.7	311.2	310.6	311.2	311.7	312.3
140°	325.1	324.9	324.7	324.4	324.0	323.6	323.2	322.8	323.2	323.6	324.0
142.5°	336.4	336.2	336.0	335.7	335.3	334.9	334.5	334.1	334.5	334.9	335.3
145°	346.9	346.7	346.6	346.3	345.8	345.4	344.9	344.4	344.9	345.4	345.8
147.5°	356.3	356.2	356.0	355.8	355.5	355.1	354.8	354.5	354.8	355.1	355.5
150°	364.8	364.7	364.6	364.4	364.2	364.0	363.8	363.6	363.8	364.0	364.2
152.5°	372.3	372.2	372.1	372.1	372.0	371.9	371.9	371.8	371.9	371.9	372.0
155°	379.0	378.9	378.8	378.9	379.0	379.1	379.3	379.4	379.3	379.1	379.0
157.5°	385.3	385.4	385.5	385.5	385.5	385.5	385.5	385.5	385.5	385.5	385.5
160°	390.5	390.6	390.6	390.7	390.8	390.8	390.9	391.0	390.9	390.8	390.8
162.5°	395.1	395.1	395.2	395.3	395.5	395.7	395.9	396.1	395.9	395.7	395.5
165°	399.0	399.1	399.1	399.3	399.5	399.7	399.9	400.1	399.9	399.7	399.5
167.5°	402.2	402.2	402.2	402.4	402.6	402.9	403.2	403.4	403.2	402.9	402.6
170°	405.0	405.0	405.0	405.1	405.4	405.6	405.9	406.2	405.9	405.6	405.4
172.5°	406.6	406.6	406.5	406.6	407.0	407.3	407.7	408.0	407.7	407.3	407.0
175°	408.2	408.1	408.0	408.2	408.5	408.8	409.2	409.5	409.2	408.8	408.5
177.5°	408.8	408.7	408.6	408.8	409.1	409.5	409.8	410.1	409.8	409.5	409.1
180°	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5



TEST NUMBER: P832107

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5
2.5°	925.9	914.7	903.6	895.5	887.5	877.5	867.5	867.1	866.7	859.2	851.8
5°	871.0	851.6	832.2	813.2	794.1	775.1	756.1	751.8	747.5	741.0	734.5
7.5°	822.4	791.4	760.4	736.1	711.8	692.8	673.8	660.8	647.9	637.9	627.9
10°	770.2	731.8	693.4	663.9	634.5	613.9	593.4	578.5	563.6	556.5	549.4
12.5°	716.1	674.3	632.6	603.7	574.9	550.2	525.5	512.0	498.5	488.6	478.8
15°	666.3	621.4	576.5	545.9	515.3	492.2	469.0	455.5	442.0	432.2	422.4
17.5°	618.1	572.8	527.5	496.5	465.5	444.5	423.5	410.4	397.3	391.2	385.1
20°	574.1	528.5	482.8	453.5	424.3	403.7	383.2	376.1	369.0	363.3	357.7
22.5°	530.6	486.7	442.8	414.7	386.7	371.8	356.9	351.2	345.5	341.2	336.9
25°	494.1	450.4	406.7	382.2	357.7	346.1	334.5	330.8	327.1	322.8	318.4
27.5°	457.3	415.7	374.1	354.5	334.9	325.5	316.1	311.4	306.7	303.1	299.6
30°	424.7	386.3	347.9	331.6	315.3	307.1	298.8	293.7	288.6	285.3	282.0
32.5°	393.3	359.2	325.1	311.2	297.3	289.2	281.2	276.3	271.4	267.5	263.5
35°	364.3	334.7	305.1	292.4	279.6	271.6	263.5	258.6	253.7	249.8	245.9
37.5°	338.8	312.0	285.1	273.1	261.2	254.1	247.1	242.0	236.9	232.8	228.6
40°	314.9	291.2	267.5	255.9	244.3	236.7	229.0	224.5	220.0	216.3	212.6
42.5°	293.7	272.0	250.2	238.8	227.5	220.2	212.9	207.7	202.4	200.2	198.0
45°	271.4	252.2	232.9	222.0	211.0	203.3	195.7	191.2	186.7	184.7	182.8
47.5°	251.8	233.9	216.1	205.3	194.5	187.7	180.8	177.3	173.7	171.0	168.2
50°	232.6	215.3	198.0	187.7	177.3	171.4	165.5	161.2	156.9	154.9	152.9
52.5°	214.1	198.4	182.8	172.2	161.6	155.9	150.2	146.5	142.8	138.6	134.5
55°	193.3	179.6	165.9	156.5	147.1	141.2	135.3	131.0	126.7	122.4	118.0
57.5°	176.1	162.6	149.0	140.6	132.2	126.5	120.8	116.1	111.4	107.8	104.3
60°	157.3	145.5	133.7	125.5	117.3	111.8	106.3	101.8	97.3	95.5	93.7
62.5°	139.6	128.6	117.7	110.4	103.1	97.8	92.6	89.6	86.7	85.5	84.3
65°	121.6	112.2	102.7	96.1	89.4	84.9	80.4	79.0	77.6	76.7	75.7
67.5°	104.7	96.7	88.6	82.7	76.9	73.7	70.6	69.0	67.5	66.3	65.1
70°	89.4	82.4	75.3	70.2	65.1	62.2	59.2	57.8	56.5	54.3	52.2
72.5°	72.9	67.5	62.0	58.0	54.1	51.6	49.0	46.3	43.5	41.6	39.6
75°	60.4	54.9	49.4	45.7	42.0	39.0	36.1	35.1	34.1	33.5	32.9
77.5°	46.3	41.6	36.9	33.9	31.0	29.6	28.2	27.6	27.1	26.9	26.7
80°	33.3	29.4	25.5	23.9	22.4	22.0	21.6	21.2	20.8	20.6	20.4
82.5°	20.8	18.8	16.9	16.5	16.1	15.9	15.7	15.5	15.3	15.1	14.9
85°	12.2	11.4	10.6	10.4	10.2	10.0	9.8	9.8	9.8	9.8	9.8
87.5°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	4.9	4.7
90°	3.0	3.8	4.7	5.5	6.4	7.3	7.6	7.8	8.1	8.4	8.6
92.5°	5.4	5.5	6.1	6.7	7.3	7.9	8.4	8.9	9.3	9.8	10.1
95°	7.5	6.5	7.2	7.9	8.7	9.4	9.9	10.4	10.9	11.3	11.6
97.5°	26.2	23.5	20.1	16.6	13.2	9.7	10.3	10.8	11.4	11.9	12.2
100°	56.8	52.2	41.7	31.1	20.6	10.0	10.6	11.1	11.7	12.2	12.5
102.5°	75.0	69.6	57.8	46.0	34.3	22.5	20.3	18.1	15.8	13.6	12.5
105°	93.6	91.0	84.9	78.8	72.7	66.6	54.7	42.7	30.7	18.8	12.8
107.5°	113.5	114.3	115.3	116.3	117.3	118.4	107.9	97.5	87.1	76.7	67.1
110°	133.6	134.2	135.0	135.7	136.5	137.2	135.0	132.8	130.5	128.3	122.3



TEST NUMBER: P832107

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	152.8	153.4	154.2	154.9	155.6	156.4	157.0	157.6	158.2	158.8	159.1
115°	171.7	172.2	172.8	173.4	174.0	174.6	175.3	176.0	176.7	177.3	177.8
117.5°	190.8	191.2	191.6	191.9	192.3	192.6	193.1	193.7	194.2	194.8	195.1
120°	208.7	209.1	209.3	209.5	209.7	209.9	210.5	211.0	211.6	212.1	212.4
122.5°	225.8	226.2	226.5	226.7	227.0	227.3	227.6	228.0	228.3	228.6	228.8
125°	241.9	242.3	242.6	242.9	243.1	243.4	243.5	243.7	243.8	243.9	244.1
127.5°	257.7	258.2	258.5	258.8	259.2	259.5	259.7	259.9	260.1	260.3	260.4
130°	272.3	272.7	273.0	273.3	273.6	273.8	274.1	274.4	274.6	274.9	275.0
132.5°	286.3	286.7	286.9	287.1	287.3	287.5	287.8	288.1	288.3	288.6	288.6
135°	300.1	300.4	300.7	301.0	301.2	301.5	301.7	301.9	302.1	302.3	302.3
137.5°	312.8	313.1	313.3	313.4	313.5	313.7	314.0	314.4	314.7	315.0	315.1
140°	324.4	324.7	324.9	325.1	325.3	325.5	325.8	326.1	326.4	326.6	326.7
142.5°	335.7	336.0	336.2	336.4	336.6	336.8	337.0	337.2	337.4	337.6	337.6
145°	346.3	346.6	346.7	346.9	347.0	347.1	347.3	347.4	347.6	347.7	347.8
147.5°	355.8	356.0	356.2	356.3	356.4	356.6	356.7	356.9	357.0	357.1	357.0
150°	364.4	364.6	364.7	364.8	365.0	365.1	365.2	365.4	365.5	365.6	365.6
152.5°	372.1	372.1	372.2	372.3	372.3	372.4	372.7	372.9	373.2	373.5	373.5
155°	378.9	378.8	378.9	379.0	379.0	379.1	379.4	379.8	380.1	380.4	380.4
157.5°	385.5	385.5	385.4	385.3	385.2	385.2	385.6	386.0	386.4	386.8	386.7
160°	390.7	390.6	390.6	390.5	390.4	390.4	390.8	391.2	391.6	392.0	391.9
162.5°	395.3	395.2	395.1	395.1	395.0	394.9	395.4	395.9	396.3	396.8	396.8
165°	399.3	399.1	399.1	399.0	398.9	398.9	399.4	400.0	400.5	401.0	401.1
167.5°	402.4	402.2	402.2	402.2	402.2	402.2	402.8	403.3	403.8	404.4	404.4
170°	405.1	405.0	405.0	405.0	405.0	405.0	405.5	406.0	406.6	407.1	407.1
172.5°	406.6	406.5	406.6	406.6	406.7	406.8	407.3	407.9	408.4	408.9	408.9
175°	408.2	408.0	408.1	408.2	408.2	408.3	408.8	409.3	409.7	410.2	410.2
177.5°	408.8	408.6	408.7	408.8	408.8	408.9	409.5	410.0	410.5	411.1	411.0
180°	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5



TEST NUMBER: P832107

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	956.5	956.5	956.5	956.5
2.5°	849.8	847.9	847.1	846.3
5°	728.5	722.4	721.0	719.6
7.5°	625.3	622.8	614.3	605.9
10°	541.6	533.7	530.2	526.7
12.5°	471.6	464.3	463.2	462.0
15°	417.3	412.2	410.4	408.6
17.5°	381.6	378.1	375.9	373.7
20°	355.1	352.6	351.0	349.4
22.5°	334.9	333.0	331.8	330.6
25°	315.5	312.6	311.6	310.6
27.5°	297.1	294.5	293.5	292.6
30°	279.8	277.7	276.3	274.9
32.5°	261.0	258.4	257.7	256.9
35°	244.3	242.8	242.0	241.2
37.5°	226.7	224.7	223.5	222.4
40°	211.6	210.6	210.0	209.4
42.5°	196.3	194.5	194.3	194.1
45°	181.0	179.2	178.8	178.4
47.5°	166.7	165.1	164.9	164.7
50°	150.8	148.6	147.1	145.5
52.5°	132.6	130.6	129.2	127.8
55°	115.9	113.7	112.6	111.4
57.5°	103.3	102.4	101.8	101.2
60°	93.1	92.6	92.2	91.8
62.5°	83.7	83.1	83.1	83.1
65°	75.1	74.5	73.9	73.3
67.5°	63.9	62.7	62.6	62.4
70°	50.4	48.6	48.4	48.2
72.5°	39.4	39.2	38.8	38.4
75°	32.6	32.2	32.2	32.2
77.5°	26.3	25.9	25.9	25.9
80°	20.2	20.0	20.2	20.4
82.5°	14.9	14.9	14.7	14.5
85°	9.6	9.4	9.4	9.4
87.5°	4.7	4.7	4.7	4.7
90°	8.7	8.9	9.0	9.1
92.5°	10.1	10.2	10.3	10.3
95°	11.6	11.6	11.6	11.6
97.5°	12.3	12.3	12.4	12.5
100°	12.6	12.6	12.7	12.8
102.5°	12.7	12.8	12.9	13.1
105°	13.0	13.1	13.3	13.4
107.5°	58.2	49.4	40.5	31.6
110°	112.7	103.0	93.3	83.7



TEST NUMBER: P832107

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	158.9	158.8	158.6	158.5
115°	178.1	178.4	178.6	178.9
117.5°	195.1	195.2	195.3	195.3
120°	212.4	212.4	212.4	212.4
122.5°	228.9	229.0	229.0	229.1
125°	244.2	244.3	244.5	244.6
127.5°	260.2	260.1	260.0	259.8
130°	274.8	274.7	274.6	274.4
132.5°	288.4	288.2	288.0	287.8
135°	302.1	301.9	301.7	301.5
137.5°	315.0	314.9	314.7	314.6
140°	326.6	326.4	326.3	326.2
142.5°	337.4	337.2	337.0	336.8
145°	347.8	347.8	347.8	347.8
147.5°	356.7	356.3	356.0	355.7
150°	365.4	365.2	365.0	364.8
152.5°	373.1	372.8	372.4	372.1
155°	380.0	379.6	379.2	378.8
157.5°	386.2	385.7	385.1	384.6
160°	391.5	391.0	390.5	390.0
162.5°	396.4	396.0	395.6	395.2
165°	400.6	400.1	399.6	399.2
167.5°	403.8	403.3	402.8	402.2
170°	406.6	406.0	405.5	405.0
172.5°	408.3	407.7	407.1	406.5
175°	409.6	409.1	408.5	408.0
177.5°	410.3	409.7	409.0	408.3
180°	409.5	409.5	409.5	409.5



TEST NUMBER: P832107

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.88	9.70	9.85	10.67	11.94	13.55	14.36	14.51	15.33	16.60
	3H	10.10	10.83	11.08	11.81	13.10	15.05	15.77	16.02	16.75	18.05
	4H	10.49	11.17	11.48	12.16	13.46	15.54	16.22	16.53	17.21	18.51
	6H	10.77	11.40	11.77	12.39	13.70	15.85	16.48	16.85	17.47	18.78
	8H	10.85	11.45	11.86	12.46	13.77	15.93	16.52	16.93	17.53	18.84
	12H	10.90	11.47	11.91	12.47	13.80	15.96	16.53	16.97	17.53	18.86
4H	2H	9.61	10.29	10.60	11.27	12.58	13.54	14.23	14.54	15.21	16.51
	3H	10.97	11.54	11.98	12.56	13.87	15.20	15.77	16.20	16.78	18.10
	4H	11.43	11.95	12.44	12.95	14.29	15.80	16.32	16.82	17.33	18.67
	6H	11.80	12.24	12.82	13.27	14.61	16.24	16.69	17.26	17.72	19.05
	8H	11.92	12.34	12.94	13.36	14.71	16.37	16.79	17.40	17.81	19.16
	12H	11.99	12.37	13.04	13.41	14.76	16.43	16.81	17.48	17.85	19.20
8H	4H	11.74	12.16	12.77	13.18	14.53	15.77	16.19	16.79	17.21	18.56
	6H	12.20	12.55	13.25	13.61	14.96	16.27	16.61	17.31	17.67	19.02
	8H	12.40	12.70	13.45	13.75	15.11	16.45	16.75	17.51	17.80	19.17
	12H	12.54	12.80	13.59	13.84	15.25	16.57	16.83	17.63	17.88	19.29
12H	4H	11.75	12.13	12.79	13.16	14.52	15.72	16.09	16.76	17.13	18.49
	6H	12.26	12.56	13.32	13.62	14.98	16.24	16.54	17.30	17.59	18.96
	8H	12.48	12.74	13.54	13.79	15.20	16.43	16.70	17.49	17.74	19.15