

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832109

Luminaire Tested: S123RDIP-S340D365U935-4F0-1E-UDD-G4

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832109
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-17)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D365U935-4F0-1E-UDD-G4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2399.6 lumens
Efficiency: N/A
Efficacy: 107.1 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 22.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832109

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-G4

Luminous Intensity Polar Plot





TEST NUMBER: P832109

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-G4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53				
1	99	95	92	88	92	88	85	83	76	73	71	64	62	61	53	52	51	46				
2	91	84	78	74	84	78	73	69	67	64	61	57	55	52	48	46	45	40				
3	84	75	68	63	77	70	64	59	60	56	52	52	48	45	43	41	39	35				
4	77	67	60	54	71	63	56	51	54	49	45	47	43	40	39	37	35	31				
5	71	60	53	47	66	56	50	45	49	44	40	42	38	35	36	33	31	28				
6	66	55	47	41	61	51	44	39	45	39	35	39	35	32	33	30	28	25				
7	61	50	42	37	57	47	40	35	41	36	32	36	32	28	31	28	25	23				
8	57	46	38	33	53	43	36	32	38	32	29	33	29	26	29	25	23	21				
9	54	42	35	30	50	40	33	29	35	30	26	31	27	24	27	23	21	19				
10	50	39	32	27	47	37	30	26	33	27	24	29	25	22	25	22	20	18				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	10296	10296	10296	10296	10296
5°	12225	11835	10361	8375	7775
10°	11076	12021	10309	6710	5757
15°	7626	10307	10200	5485	4553
20°	5306	7936	9995	4624	4002
25°	4043	6048	9697	4111	3689
30°	3519	4835	9324	3817	3417
35°	3231	4079	8796	3569	3169
40°	2948	3642	8106	3326	2942
45°	2662	3331	7360	3095	2716
50°	2416	3073	6482	2870	2436
55°	2186	2822	5637	2650	2091
60°	1959	2566	4898	2407	1976
65°	1808	2277	4215	2162	1867
70°	1470	1970	3679	1958	1517
75°	1289	1564	3115	1622	1339
80°	1165	1327	2554	1364	1265
85°	1062	1161	1939	1235	1161

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 7767 cd/sqm



TEST NUMBER: P832109

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-G4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.2	3.6
10°-20°	201.7	8.4
20°-30°	231.5	9.6
30°-40°	228.2	9.5
40°-50°	201.2	8.4
50°-60°	154.8	6.5
60°-70°	101.8	4.2
70°-80°	49.4	2.1
80°-90°	13.3	0.6
90°-100°	81.6	3.4
100°-110°	238.8	10.0
110°-120°	233.2	9.7
120°-130°	185.7	7.7
130°-140°	146.5	6.1
140°-150°	109.3	4.6
150°-160°	76.2	3.2
160°-170°	44.8	1.9
170°-180°	14.6	0.6
0°-30°	520.4	21.7
0°-40°	748.5	31.2
0°-60°	1104.5	46.0
0°-90°	1269.0	52.9
90°-120°	553.5	23.1
90°-150°	995.1	41.5
90°-180°	1131.0	47.1
0°-180°	2399.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	956	956	956	956	956	
5°	1131	1095	959	775	720	103
15°	684	925	915	492	409	193
25°	340	509	816	346	311	161
35°	246	310	669	272	241	153
45°	175	219	484	203	178	136
55°	116	150	300	141	111	104
65°	71	89	166	85	73	70
75°	31	38	75	39	32	33
85°	9	9	16	10	9	9
90°	9	8	1	8	9	5
95°	35	180	10	180	35	57
105°	387	245	35	245	387	386
115°	471	187	62	187	471	459
125°	371	175	87	175	371	336
135°	301	172	102	172	301	233
145°	235	170	116	170	235	149
155°	195	165	132	165	195	91
165°	170	158	144	158	170	49
175°	153	151	150	151	153	15
180°	150	150	150	150	150	



TEST NUMBER: P832109

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5
2.5°	1060.0	1056.7	1053.4	1052.4	1051.4	1048.3	1045.1	1038.1	1031.0	1023.8	1016.5
5°	1131.4	1131.8	1132.2	1131.2	1130.2	1126.1	1122.0	1113.4	1104.7	1095.3	1085.9
7.5°	1109.5	1115.7	1122.0	1123.2	1124.4	1127.5	1130.6	1128.7	1126.7	1123.2	1119.6
10°	1013.4	1013.0	1012.6	1019.6	1026.7	1047.7	1068.7	1079.5	1090.2	1099.8	1109.5
12.5°	856.5	857.1	857.7	880.8	904.0	923.8	943.6	971.0	998.5	1028.1	1057.7
15°	684.3	693.9	703.6	724.1	744.7	774.5	804.3	841.2	878.1	924.9	971.8
17.5°	562.0	566.1	570.2	590.0	609.8	638.1	666.3	708.1	749.8	810.2	870.6
20°	463.2	466.9	470.6	484.9	499.2	526.3	553.4	593.2	633.0	692.8	752.6
22.5°	386.7	393.9	401.2	410.8	420.4	440.0	459.6	500.2	540.8	595.3	649.8
25°	340.4	343.7	347.1	355.3	363.5	382.4	401.2	428.1	454.9	509.2	563.6
27.5°	309.0	310.0	311.0	317.1	323.1	335.3	347.5	372.4	397.3	442.0	486.7
30°	283.1	284.9	286.7	291.4	296.1	304.9	313.7	331.4	349.0	389.0	429.0
32.5°	263.1	264.1	265.1	269.0	273.0	279.4	285.9	299.8	313.7	344.3	374.9
35°	245.9	246.1	246.3	249.2	252.2	258.4	264.7	276.3	287.9	310.4	333.0
37.5°	226.3	227.7	229.0	231.2	233.3	238.8	244.3	253.7	263.1	281.8	300.4
40°	209.8	211.0	212.2	214.7	217.3	221.6	225.9	234.5	243.1	259.2	275.3
42.5°	193.3	194.1	194.9	197.5	200.0	205.3	210.6	217.5	224.3	237.7	251.0
45°	174.9	176.9	178.8	181.6	184.3	188.8	193.3	200.4	207.5	218.8	230.2
47.5°	159.6	160.6	161.6	163.9	166.3	171.8	177.3	183.5	189.8	200.4	211.0
50°	144.3	144.7	145.1	147.3	149.4	154.3	159.2	166.5	173.7	183.5	193.3
52.5°	129.8	130.8	131.8	133.9	136.1	139.4	142.8	150.2	157.7	167.3	176.9
55°	116.5	117.1	117.7	119.2	120.8	124.7	128.6	135.1	141.6	150.4	159.2
57.5°	103.9	104.7	105.5	106.7	107.8	111.4	114.9	120.6	126.3	135.1	143.9
60°	91.0	92.0	92.9	94.3	95.7	98.4	101.2	106.3	111.4	119.2	127.1
62.5°	81.6	81.8	82.0	83.1	84.3	86.3	88.2	92.4	96.5	104.3	112.2
65°	71.0	71.6	72.2	72.7	73.3	74.9	76.5	80.0	83.5	89.4	95.3
67.5°	60.0	60.6	61.2	62.2	63.1	64.5	65.9	68.2	70.6	76.1	81.6
70°	46.7	46.7	46.7	48.2	49.8	52.2	54.5	56.3	58.0	62.6	67.1
72.5°	38.0	38.2	38.4	38.6	38.8	40.2	41.6	44.5	47.5	50.2	52.9
75°	31.0	31.2	31.4	31.6	31.8	32.2	32.6	33.5	34.5	37.6	40.8
77.5°	24.7	24.9	25.1	25.3	25.5	25.9	26.3	26.7	27.1	28.2	29.4
80°	18.8	19.0	19.2	19.4	19.6	19.8	20.0	20.4	20.8	21.4	22.0
82.5°	13.7	13.7	13.7	13.7	13.7	14.1	14.5	14.5	14.5	14.9	15.3
85°	8.6	8.6	8.6	8.8	9.0	9.0	9.0	9.2	9.4	9.4	9.4
87.5°	3.9	3.7	3.5	3.7	3.9	3.9	3.9	4.1	4.3	4.3	4.3
90°	8.8	9.1	8.8	8.5	8.8	8.2	7.9	7.6	7.3	7.6	6.7
92.5°	16.1	16.7	16.4	17.6	18.3	20.4	23.4	30.1	42.3	56.6	62.7
95°	35.3	36.5	38.6	41.4	47.2	58.1	74.2	109.5	146.3	180.4	160.6
97.5°	72.4	75.8	83.1	94.6	115.0	149.7	189.9	251.6	286.9	277.5	207.2
100°	190.8	190.5	202.3	224.5	255.3	298.5	334.1	358.7	348.1	288.1	194.7
102.5°	302.1	311.0	320.4	336.8	359.0	382.5	399.5	394.3	351.1	268.4	176.5
105°	387.0	388.5	398.3	409.8	423.8	431.7	426.0	395.5	331.9	244.6	162.2
107.5°	442.4	445.7	449.7	455.2	457.0	448.8	425.1	377.3	304.6	223.6	151.8
110°	474.0	474.6	475.3	472.8	464.3	443.0	404.7	348.7	279.0	206.3	146.3



TEST NUMBER: P832109

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	480.4	480.1	477.1	468.3	450.9	422.0	377.9	320.4	256.8	194.7	143.3
115°	470.7	469.2	463.1	449.7	426.9	393.7	349.0	296.0	239.8	187.1	143.0
117.5°	449.4	447.3	438.1	423.2	399.5	365.1	324.0	277.2	228.5	181.9	143.3
120°	421.4	419.6	412.3	395.2	371.2	340.5	304.0	262.9	220.0	178.6	144.5
122.5°	395.2	392.8	384.6	369.7	349.0	321.0	287.8	251.6	213.0	176.5	146.7
125°	371.2	369.1	361.5	348.1	328.6	304.3	275.1	241.9	207.2	174.6	148.8
127.5°	350.5	348.7	341.7	330.1	312.5	290.0	263.2	233.1	201.7	173.7	151.2
130°	333.5	331.0	324.6	313.7	297.6	276.9	252.2	224.8	197.5	172.8	153.7
132.5°	316.7	315.2	309.7	298.8	283.9	264.4	241.9	217.2	193.5	172.5	155.5
135°	300.9	298.8	293.3	284.2	269.3	251.9	232.2	210.5	190.2	172.2	157.3
137.5°	284.2	282.4	277.8	268.4	255.6	240.1	222.4	204.2	187.1	171.6	158.5
140°	266.5	266.8	262.0	253.4	241.9	228.8	214.2	198.7	184.4	171.3	159.7
142.5°	250.1	250.4	246.1	238.8	229.4	218.5	206.3	193.5	181.9	170.7	160.6
145°	235.2	234.6	232.2	225.8	218.2	209.3	199.6	189.6	179.8	170.1	161.0
147.5°	222.4	222.1	219.7	215.1	209.0	202.6	194.4	186.2	177.7	169.2	161.0
150°	211.5	211.5	209.6	206.3	201.7	195.9	189.6	182.6	175.6	168.0	161.0
152.5°	202.3	202.3	201.4	198.4	195.0	190.5	185.0	179.2	173.1	166.4	160.0
155°	195.0	194.7	194.1	191.7	188.9	185.3	180.7	175.9	170.7	164.6	159.4
157.5°	188.0	188.0	187.4	185.6	183.2	180.1	176.5	172.2	168.0	163.1	158.5
160°	181.3	181.6	181.6	179.8	177.7	175.6	172.5	169.2	165.2	161.3	157.9
162.5°	175.3	175.6	175.6	174.0	172.8	171.0	168.3	165.5	162.5	159.4	156.7
165°	170.1	170.1	170.4	169.2	168.0	166.4	164.3	162.5	160.0	157.6	155.5
167.5°	164.9	164.9	165.2	164.3	163.7	162.5	161.3	159.7	157.6	155.8	154.3
170°	160.3	160.3	160.6	160.0	159.7	159.1	157.9	157.0	155.5	154.0	153.0
172.5°	156.1	156.4	157.0	156.4	156.4	156.1	155.2	154.6	153.3	152.4	152.1
175°	153.0	153.3	153.7	153.3	153.3	153.3	152.7	152.4	151.8	151.2	151.2
177.5°	150.9	150.9	151.5	151.2	151.5	151.5	151.2	150.9	150.6	150.3	150.6
180°	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3



TEST NUMBER: P832109

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5
2.5°	1015.5	1014.5	1005.1	995.7	986.5	977.3	970.4	963.6	952.0	940.4	933.2
5°	1078.5	1071.0	1056.1	1041.2	1018.9	996.5	977.7	958.9	934.9	911.0	891.0
7.5°	1113.6	1107.5	1089.5	1071.4	1041.8	1012.2	982.8	953.4	918.1	882.8	852.6
10°	1114.6	1119.6	1104.7	1089.8	1056.5	1023.2	983.2	943.2	895.7	848.3	809.2
12.5°	1079.6	1101.6	1098.5	1095.3	1061.4	1027.5	978.9	930.2	872.0	813.8	764.9
15°	1014.4	1056.9	1069.5	1082.0	1054.0	1025.9	970.6	915.3	846.9	778.5	722.4
17.5°	930.2	989.8	1023.0	1056.1	1035.7	1015.3	954.7	894.2	817.1	740.0	679.0
20°	830.6	908.7	960.6	1012.6	1005.1	997.7	935.1	872.6	789.4	706.3	640.2
22.5°	732.2	814.5	886.3	958.1	965.7	973.4	910.2	847.1	756.1	665.1	597.9
25°	647.3	731.0	816.5	902.0	919.3	936.5	876.5	816.5	722.2	627.9	561.0
27.5°	566.3	645.9	740.0	834.1	865.5	896.9	842.0	787.1	688.8	590.6	523.9
30°	500.2	571.4	667.5	763.6	807.3	851.0	800.6	750.2	652.8	555.3	490.0
32.5°	438.6	502.4	598.8	695.3	746.1	796.9	753.4	709.8	616.1	522.4	457.9
35°	390.0	447.1	537.1	627.1	683.9	740.8	705.1	669.4	577.9	486.3	425.3
37.5°	348.2	396.1	480.6	565.1	625.5	685.9	656.1	626.3	540.2	454.1	396.5
40°	313.7	352.2	430.8	509.4	568.6	627.9	602.4	576.9	499.8	422.8	368.8
42.5°	284.1	317.3	387.9	458.4	512.8	567.1	550.2	533.4	463.5	393.7	343.7
45°	258.0	285.9	348.1	410.2	460.2	510.2	496.9	483.5	423.3	363.2	317.3
47.5°	234.9	258.8	314.3	369.8	414.7	459.6	447.3	434.9	385.1	335.3	293.5
50°	213.7	234.1	280.4	326.7	367.1	407.5	397.3	387.1	345.9	304.7	268.6
52.5°	193.7	210.6	252.2	293.7	326.3	358.8	351.0	343.2	311.4	279.6	246.9
55°	174.7	190.2	225.3	260.4	288.2	316.1	308.2	300.4	275.7	251.0	222.2
57.5°	157.5	171.0	199.4	227.9	250.0	272.2	268.4	264.7	244.1	223.5	199.8
60°	139.2	151.4	175.9	200.4	218.2	236.1	231.8	227.5	212.8	198.0	177.7
62.5°	122.9	133.7	153.3	172.9	187.5	202.0	198.8	195.7	184.5	173.3	156.5
65°	105.9	116.5	132.4	148.2	159.6	171.0	168.2	165.5	157.1	148.6	135.1
67.5°	90.4	99.2	112.9	126.7	134.3	142.0	140.4	138.8	132.4	125.9	115.3
70°	74.7	82.4	93.7	105.1	110.4	115.7	116.3	116.9	111.0	105.1	97.3
72.5°	59.0	65.1	75.7	86.3	90.4	94.5	94.3	94.1	90.6	87.1	80.0
75°	45.3	49.8	58.0	66.3	69.8	73.3	74.1	74.9	71.6	68.2	64.3
77.5°	32.6	35.7	42.0	48.2	52.2	56.1	56.5	56.9	55.3	53.7	50.0
80°	22.9	23.9	27.8	31.8	35.9	40.0	40.6	41.2	39.6	38.0	35.7
82.5°	15.9	16.5	17.8	19.2	22.5	25.9	26.7	27.5	26.7	25.9	23.3
85°	9.6	9.8	10.4	11.0	12.5	14.1	14.9	15.7	15.3	14.9	13.5
87.5°	4.3	4.3	4.5	4.7	5.1	5.5	6.5	7.5	6.9	6.3	5.7
90°	5.8	4.9	4.0	3.3	2.7	1.8	1.2	0.6	1.2	1.8	2.7
92.5°	46.9	30.7	21.0	15.5	12.5	9.7	6.7	4.6	6.7	9.7	12.5
95°	110.8	65.4	39.6	27.7	19.8	14.6	11.3	10.3	11.3	14.6	19.8
97.5°	123.2	70.6	45.0	31.9	24.0	19.5	16.7	16.4	16.7	19.5	24.0
100°	114.7	69.7	48.4	36.5	29.2	24.9	22.8	22.5	22.8	24.9	29.2
102.5°	107.4	70.9	52.3	41.7	35.3	31.3	29.5	28.9	29.5	31.3	35.3
105°	104.7	73.3	56.9	47.5	41.7	38.0	36.2	35.3	36.2	38.0	41.7
107.5°	104.1	77.3	62.7	53.9	48.4	44.7	42.9	42.0	42.9	44.7	48.4
110°	105.6	82.5	68.8	60.2	55.1	51.7	50.2	49.3	50.2	51.7	55.1



TEST NUMBER: P832109

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	108.6	87.6	75.2	66.9	61.8	58.4	56.9	56.0	56.9	58.4	61.8
115°	112.0	93.4	81.8	73.6	68.5	65.4	63.6	62.4	63.6	65.4	68.5
117.5°	116.2	99.5	87.9	80.3	74.5	71.8	70.3	68.8	70.3	71.8	74.5
120°	121.1	105.3	94.3	86.7	80.9	77.9	76.4	75.5	76.4	77.9	80.9
122.5°	125.7	111.4	100.7	92.5	87.0	83.7	82.2	81.2	82.2	83.7	87.0
125°	130.5	117.1	106.5	98.3	92.5	89.1	87.3	86.7	87.3	89.1	92.5
127.5°	134.5	122.3	112.0	103.8	97.4	94.0	91.9	91.0	91.9	94.0	97.4
130°	138.4	126.9	116.8	108.6	102.2	98.6	95.8	94.9	95.8	98.6	102.2
132.5°	142.1	130.8	121.1	113.2	106.8	102.2	99.2	98.0	99.2	102.2	106.8
135°	145.1	134.8	125.4	117.1	110.8	106.2	102.8	101.6	102.8	106.2	110.8
137.5°	147.6	137.5	128.4	120.8	114.4	109.5	106.2	105.0	106.2	109.5	114.4
140°	149.4	140.3	131.4	123.8	117.7	112.9	109.8	108.3	109.8	112.9	117.7
142.5°	151.2	142.4	133.9	126.9	120.8	116.5	113.2	112.0	113.2	116.5	120.8
145°	152.4	144.2	136.3	129.3	124.1	119.6	116.8	115.9	116.8	119.6	124.1
147.5°	153.3	145.7	138.4	132.4	127.2	123.2	120.5	119.9	120.5	123.2	127.2
150°	153.7	147.3	140.3	134.8	130.5	126.6	124.1	123.8	124.1	126.6	130.5
152.5°	154.3	148.2	142.4	137.2	133.6	130.2	127.8	127.8	127.8	130.2	133.6
155°	154.3	149.4	144.2	140.0	136.6	133.6	131.7	131.7	131.7	133.6	136.6
157.5°	154.6	150.0	145.7	142.4	139.4	136.6	135.1	134.8	135.1	136.6	139.4
160°	154.6	150.9	147.3	144.2	142.1	139.7	138.4	138.4	138.4	139.7	142.1
162.5°	154.3	151.2	148.2	145.7	143.9	142.1	141.2	141.2	141.2	142.1	143.9
165°	153.7	151.5	149.1	147.0	145.7	144.2	143.6	143.9	143.6	144.2	145.7
167.5°	153.3	151.5	149.7	148.2	147.3	146.0	145.7	146.0	145.7	146.0	147.3
170°	152.4	151.2	149.7	149.1	148.5	147.6	147.3	147.9	147.3	147.6	148.5
172.5°	152.1	151.2	150.0	149.7	149.4	148.8	148.8	149.1	148.8	148.8	149.4
175°	151.5	150.9	150.3	150.0	150.0	149.4	149.7	150.0	149.7	149.4	150.0
177.5°	151.2	150.6	150.3	150.3	150.3	150.0	150.3	150.6	150.3	150.0	150.3
180°	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3



TEST NUMBER: P832109

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5
2.5°	925.9	914.7	903.6	895.5	887.5	877.5	867.5	867.1	866.7	859.2	851.8
5°	871.0	851.6	832.2	813.2	794.1	775.1	756.1	751.8	747.5	741.0	734.5
7.5°	822.4	791.4	760.4	736.1	711.8	692.8	673.8	660.8	647.9	637.9	627.9
10°	770.2	731.8	693.4	663.9	634.5	613.9	593.4	578.5	563.6	556.5	549.4
12.5°	716.1	674.3	632.6	603.7	574.9	550.2	525.5	512.0	498.5	488.6	478.8
15°	666.3	621.4	576.5	545.9	515.3	492.2	469.0	455.5	442.0	432.2	422.4
17.5°	618.1	572.8	527.5	496.5	465.5	444.5	423.5	410.4	397.3	391.2	385.1
20°	574.1	528.5	482.8	453.5	424.3	403.7	383.2	376.1	369.0	363.3	357.7
22.5°	530.6	486.7	442.8	414.7	386.7	371.8	356.9	351.2	345.5	341.2	336.9
25°	494.1	450.4	406.7	382.2	357.7	346.1	334.5	330.8	327.1	322.8	318.4
27.5°	457.3	415.7	374.1	354.5	334.9	325.5	316.1	311.4	306.7	303.1	299.6
30°	424.7	386.3	347.9	331.6	315.3	307.1	298.8	293.7	288.6	285.3	282.0
32.5°	393.3	359.2	325.1	311.2	297.3	289.2	281.2	276.3	271.4	267.5	263.5
35°	364.3	334.7	305.1	292.4	279.6	271.6	263.5	258.6	253.7	249.8	245.9
37.5°	338.8	312.0	285.1	273.1	261.2	254.1	247.1	242.0	236.9	232.8	228.6
40°	314.9	291.2	267.5	255.9	244.3	236.7	229.0	224.5	220.0	216.3	212.6
42.5°	293.7	272.0	250.2	238.8	227.5	220.2	212.9	207.7	202.4	200.2	198.0
45°	271.4	252.2	232.9	222.0	211.0	203.3	195.7	191.2	186.7	184.7	182.8
47.5°	251.8	233.9	216.1	205.3	194.5	187.7	180.8	177.3	173.7	171.0	168.2
50°	232.6	215.3	198.0	187.7	177.3	171.4	165.5	161.2	156.9	154.9	152.9
52.5°	214.1	198.4	182.8	172.2	161.6	155.9	150.2	146.5	142.8	138.6	134.5
55°	193.3	179.6	165.9	156.5	147.1	141.2	135.3	131.0	126.7	122.4	118.0
57.5°	176.1	162.6	149.0	140.6	132.2	126.5	120.8	116.1	111.4	107.8	104.3
60°	157.3	145.5	133.7	125.5	117.3	111.8	106.3	101.8	97.3	95.5	93.7
62.5°	139.6	128.6	117.7	110.4	103.1	97.8	92.6	89.6	86.7	85.5	84.3
65°	121.6	112.2	102.7	96.1	89.4	84.9	80.4	79.0	77.6	76.7	75.7
67.5°	104.7	96.7	88.6	82.7	76.9	73.7	70.6	69.0	67.5	66.3	65.1
70°	89.4	82.4	75.3	70.2	65.1	62.2	59.2	57.8	56.5	54.3	52.2
72.5°	72.9	67.5	62.0	58.0	54.1	51.6	49.0	46.3	43.5	41.6	39.6
75°	60.4	54.9	49.4	45.7	42.0	39.0	36.1	35.1	34.1	33.5	32.9
77.5°	46.3	41.6	36.9	33.9	31.0	29.6	28.2	27.6	27.1	26.9	26.7
80°	33.3	29.4	25.5	23.9	22.4	22.0	21.6	21.2	20.8	20.6	20.4
82.5°	20.8	18.8	16.9	16.5	16.1	15.9	15.7	15.5	15.3	15.1	14.9
85°	12.2	11.4	10.6	10.4	10.2	10.0	9.8	9.8	9.8	9.8	9.8
87.5°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	4.9	4.7
90°	3.3	4.0	4.9	5.8	6.7	7.6	7.3	7.6	7.9	8.2	8.8
92.5°	15.5	21.0	30.7	46.9	62.7	56.6	42.3	30.1	23.4	20.4	18.3
95°	27.7	39.6	65.4	110.8	160.6	180.4	146.3	109.5	74.2	58.1	47.2
97.5°	31.9	45.0	70.6	123.2	207.2	277.5	286.9	251.6	189.9	149.7	115.0
100°	36.5	48.4	69.7	114.7	194.7	288.1	348.1	358.7	334.1	298.5	255.3
102.5°	41.7	52.3	70.9	107.4	176.5	268.4	351.1	394.3	399.5	382.5	359.0
105°	47.5	56.9	73.3	104.7	162.2	244.6	331.9	395.5	426.0	431.7	423.8
107.5°	53.9	62.7	77.3	104.1	151.8	223.6	304.6	377.3	425.1	448.8	457.0
110°	60.2	68.8	82.5	105.6	146.3	206.3	279.0	348.7	404.7	443.0	464.3



TEST NUMBER: P832109

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	66.9	75.2	87.6	108.6	143.3	194.7	256.8	320.4	377.9	422.0	450.9
115°	73.6	81.8	93.4	112.0	143.0	187.1	239.8	296.0	349.0	393.7	426.9
117.5°	80.3	87.9	99.5	116.2	143.3	181.9	228.5	277.2	324.0	365.1	399.5
120°	86.7	94.3	105.3	121.1	144.5	178.6	220.0	262.9	304.0	340.5	371.2
122.5°	92.5	100.7	111.4	125.7	146.7	176.5	213.0	251.6	287.8	321.0	349.0
125°	98.3	106.5	117.1	130.5	148.8	174.6	207.2	241.9	275.1	304.3	328.6
127.5°	103.8	112.0	122.3	134.5	151.2	173.7	201.7	233.1	263.2	290.0	312.5
130°	108.6	116.8	126.9	138.4	153.7	172.8	197.5	224.8	252.2	276.9	297.6
132.5°	113.2	121.1	130.8	142.1	155.5	172.5	193.5	217.2	241.9	264.4	283.9
135°	117.1	125.4	134.8	145.1	157.3	172.2	190.2	210.5	232.2	251.9	269.3
137.5°	120.8	128.4	137.5	147.6	158.5	171.6	187.1	204.2	222.4	240.1	255.6
140°	123.8	131.4	140.3	149.4	159.7	171.3	184.4	198.7	214.2	228.8	241.9
142.5°	126.9	133.9	142.4	151.2	160.6	170.7	181.9	193.5	206.3	218.5	229.4
145°	129.3	136.3	144.2	152.4	161.0	170.1	179.8	189.6	199.6	209.3	218.2
147.5°	132.4	138.4	145.7	153.3	161.0	169.2	177.7	186.2	194.4	202.6	209.0
150°	134.8	140.3	147.3	153.7	161.0	168.0	175.6	182.6	189.6	195.9	201.7
152.5°	137.2	142.4	148.2	154.3	160.0	166.4	173.1	179.2	185.0	190.5	195.0
155°	140.0	144.2	149.4	154.3	159.4	164.6	170.7	175.9	180.7	185.3	188.9
157.5°	142.4	145.7	150.0	154.6	158.5	163.1	168.0	172.2	176.5	180.1	183.2
160°	144.2	147.3	150.9	154.6	157.9	161.3	165.2	169.2	172.5	175.6	177.7
162.5°	145.7	148.2	151.2	154.3	156.7	159.4	162.5	165.5	168.3	171.0	172.8
165°	147.0	149.1	151.5	153.7	155.5	157.6	160.0	162.5	164.3	166.4	168.0
167.5°	148.2	149.7	151.5	153.3	154.3	155.8	157.6	159.7	161.3	162.5	163.7
170°	149.1	149.7	151.2	152.4	153.0	154.0	155.5	157.0	157.9	159.1	159.7
172.5°	149.7	150.0	151.2	152.1	152.1	152.4	153.3	154.6	155.2	156.1	156.4
175°	150.0	150.3	150.9	151.5	151.2	151.2	151.8	152.4	152.7	153.3	153.3
177.5°	150.3	150.3	150.6	151.2	150.6	150.3	150.6	150.9	151.2	151.5	151.5
180°	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3

TEST NUMBER: P832109

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	956.5	956.5	956.5	956.5
2.5°	849.8	847.9	847.1	846.3
5°	728.5	722.4	721.0	719.6
7.5°	625.3	622.8	614.3	605.9
10°	541.6	533.7	530.2	526.7
12.5°	471.6	464.3	463.2	462.0
15°	417.3	412.2	410.4	408.6
17.5°	381.6	378.1	375.9	373.7
20°	355.1	352.6	351.0	349.4
22.5°	334.9	333.0	331.8	330.6
25°	315.5	312.6	311.6	310.6
27.5°	297.1	294.5	293.5	292.6
30°	279.8	277.7	276.3	274.9
32.5°	261.0	258.4	257.7	256.9
35°	244.3	242.8	242.0	241.2
37.5°	226.7	224.7	223.5	222.4
40°	211.6	210.6	210.0	209.4
42.5°	196.3	194.5	194.3	194.1
45°	181.0	179.2	178.8	178.4
47.5°	166.7	165.1	164.9	164.7
50°	150.8	148.6	147.1	145.5
52.5°	132.6	130.6	129.2	127.8
55°	115.9	113.7	112.6	111.4
57.5°	103.3	102.4	101.8	101.2
60°	93.1	92.6	92.2	91.8
62.5°	83.7	83.1	83.1	83.1
65°	75.1	74.5	73.9	73.3
67.5°	63.9	62.7	62.6	62.4
70°	50.4	48.6	48.4	48.2
72.5°	39.4	39.2	38.8	38.4
75°	32.6	32.2	32.2	32.2
77.5°	26.3	25.9	25.9	25.9
80°	20.2	20.0	20.2	20.4
82.5°	14.9	14.9	14.7	14.5
85°	9.6	9.4	9.4	9.4
87.5°	4.7	4.7	4.7	4.7
90°	8.5	8.8	9.1	8.8
92.5°	17.6	16.4	16.7	16.1
95°	41.4	38.6	36.5	35.3
97.5°	94.6	83.1	75.8	72.4
100°	224.5	202.3	190.5	190.8
102.5°	336.8	320.4	311.0	302.1
105°	409.8	398.3	388.5	387.0
107.5°	455.2	449.7	445.7	442.4
110°	472.8	475.3	474.6	474.0



TEST NUMBER: P832109

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	468.3	477.1	480.1	480.4
115°	449.7	463.1	469.2	470.7
117.5°	423.2	438.1	447.3	449.4
120°	395.2	412.3	419.6	421.4
122.5°	369.7	384.6	392.8	395.2
125°	348.1	361.5	369.1	371.2
127.5°	330.1	341.7	348.7	350.5
130°	313.7	324.6	331.0	333.5
132.5°	298.8	309.7	315.2	316.7
135°	284.2	293.3	298.8	300.9
137.5°	268.4	277.8	282.4	284.2
140°	253.4	262.0	266.8	266.5
142.5°	238.8	246.1	250.4	250.1
145°	225.8	232.2	234.6	235.2
147.5°	215.1	219.7	222.1	222.4
150°	206.3	209.6	211.5	211.5
152.5°	198.4	201.4	202.3	202.3
155°	191.7	194.1	194.7	195.0
157.5°	185.6	187.4	188.0	188.0
160°	179.8	181.6	181.6	181.3
162.5°	174.0	175.6	175.6	175.3
165°	169.2	170.4	170.1	170.1
167.5°	164.3	165.2	164.9	164.9
170°	160.0	160.6	160.3	160.3
172.5°	156.4	157.0	156.4	156.1
175°	153.3	153.7	153.3	153.0
177.5°	151.2	151.5	150.9	150.9
180°	150.3	150.3	150.3	150.3



TEST NUMBER: P832109

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-G4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.11	9.94	10.06	10.90	12.13	13.78	14.61	14.72	15.56	16.79
	3H	10.33	11.08	11.29	12.04	13.29	15.28	16.02	16.23	16.98	18.24
	4H	10.72	11.42	11.69	12.38	13.65	15.77	16.47	16.74	17.43	18.70
	6H	11.00	11.64	11.98	12.61	13.89	16.08	16.72	17.06	17.70	18.97
	8H	11.08	11.70	12.07	12.68	13.96	16.16	16.77	17.15	17.76	19.03
	12H	11.14	11.72	12.13	12.70	14.00	16.19	16.77	17.18	17.75	19.05
4H	2H	9.84	10.54	10.81	11.50	12.77	13.77	14.47	14.75	15.44	16.71
	3H	11.21	11.79	12.19	12.78	14.06	15.43	16.01	16.42	17.01	18.29
	4H	11.66	12.19	12.65	13.18	14.49	16.04	16.57	17.03	17.56	18.86
	6H	12.03	12.49	13.03	13.50	14.80	16.48	16.93	17.48	17.94	19.25
	8H	12.15	12.58	13.16	13.58	14.90	16.61	17.03	17.61	18.04	19.35
	12H	12.23	12.61	13.25	13.63	14.95	16.67	17.05	17.69	18.07	19.39
8H	4H	11.98	12.40	12.98	13.41	14.72	16.01	16.43	17.01	17.44	18.75
	6H	12.44	12.79	13.47	13.84	15.15	16.50	16.85	17.53	17.90	19.21
	8H	12.63	12.94	13.67	13.97	15.31	16.69	17.00	17.73	18.03	19.36
	12H	12.77	13.04	13.81	14.07	15.45	16.80	17.07	17.84	18.10	19.48
12H	4H	11.99	12.37	13.01	13.39	14.71	15.96	16.34	16.98	17.36	18.68
	6H	12.50	12.81	13.54	13.84	15.17	16.48	16.79	17.51	17.82	19.15
	8H	12.72	12.99	13.76	14.01	15.39	16.67	16.94	17.71	17.97	19.35