

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832135

Luminaire Tested: S123RDIP-S340D585U935-4F0-1E-UDD-G1

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832135
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D585U935-4F0-1E-UDD-G1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3001.7 lumens
Efficiency: N/A
Efficacy: 108.8 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 27.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832135

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-G1

Luminous Intensity Polar Plot





TEST NUMBER: P832135

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-G1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42				
1	97	93	89	86	88	85	82	79	70	68	66	57	55	54	44	43	43	37				
2	89	82	76	71	81	75	70	66	62	59	56	51	48	46	40	38	37	32				
3	81	73	66	60	74	67	61	56	56	51	48	45	43	40	36	34	32	28				
4	75	65	57	52	68	60	53	48	50	45	42	41	38	35	33	31	29	25				
5	69	58	50	45	63	54	47	42	45	40	36	37	34	31	30	28	26	22				
6	64	52	45	39	58	48	42	37	41	36	32	34	30	28	28	25	23	20				
7	59	48	40	35	54	44	38	33	38	32	29	31	28	25	25	23	21	18				
8	55	43	36	31	51	40	34	29	34	29	26	29	25	22	24	21	19	17				
9	51	40	33	28	47	37	31	26	32	27	23	27	23	20	22	19	17	15				
10	48	37	30	25	44	34	28	24	29	25	21	25	21	19	21	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	10296	10296	10296	10296	10296
5°	12225	11835	10361	8375	7775
10°	11076	12021	10309	6710	5757
15°	7626	10307	10200	5485	4553
20°	5306	7936	9995	4624	4002
25°	4043	6048	9697	4111	3689
30°	3519	4835	9324	3817	3417
35°	3231	4079	8796	3569	3169
40°	2948	3642	8106	3326	2942
45°	2662	3331	7360	3095	2716
50°	2416	3073	6482	2870	2436
55°	2186	2822	5637	2650	2091
60°	1959	2566	4898	2407	1976
65°	1808	2277	4215	2162	1867
70°	1470	1970	3679	1958	1517
75°	1289	1564	3115	1622	1339
80°	1165	1327	2554	1364	1265
85°	1062	1161	1939	1235	1161

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 7767 cd/sqm



TEST NUMBER: P832135

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-G1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.2	2.9
10°-20°	201.7	6.7
20°-30°	231.5	7.7
30°-40°	228.2	7.6
40°-50°	201.2	6.7
50°-60°	154.8	5.2
60°-70°	101.8	3.4
70°-80°	49.4	1.6
80°-90°	13.8	0.5
90°-100°	40.2	1.3
100°-110°	121.8	4.1
110°-120°	207.4	6.9
120°-130°	272.8	9.1
130°-140°	306.6	10.2
140°-150°	301.5	10.0
150°-160°	253.8	8.5
160°-170°	169.0	5.6
170°-180°	59.2	2.0
0°-30°	520.4	17.3
0°-40°	748.5	24.9
0°-60°	1104.5	36.8
0°-90°	1269.5	42.3
90°-120°	369.4	12.3
90°-150°	1250.3	41.7
90°-180°	1732.0	57.7
0°-180°	3001.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	956	956	956	956	956	
5°	1131	1095	959	775	720	103
15°	684	925	915	492	409	193
25°	340	509	816	346	311	161
35°	246	310	669	272	241	153
45°	175	219	484	203	178	136
55°	116	150	300	141	111	104
65°	71	89	166	85	73	70
75°	31	38	75	39	32	33
85°	9	9	16	10	9	9
90°	15	12	0	12	15	7
95°	38	36	29	36	38	38
105°	117	116	110	116	117	124
115°	209	209	209	209	209	207
125°	302	306	306	306	302	270
135°	396	399	396	399	396	304
145°	481	483	481	483	481	300
155°	550	551	550	551	550	253
165°	598	598	600	598	598	169
175°	621	622	624	622	621	59
180°	625	625	625	625	625	



TEST NUMBER: P832135

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5
2.5°	1060.0	1056.7	1053.4	1052.4	1051.4	1048.3	1045.1	1038.1	1031.0	1023.8	1016.5
5°	1131.4	1131.8	1132.2	1131.2	1130.2	1126.1	1122.0	1113.4	1104.7	1095.3	1085.9
7.5°	1109.5	1115.7	1122.0	1123.2	1124.4	1127.5	1130.6	1128.7	1126.7	1123.2	1119.6
10°	1013.4	1013.0	1012.6	1019.6	1026.7	1047.7	1068.7	1079.5	1090.2	1099.8	1109.5
12.5°	856.5	857.1	857.7	880.8	904.0	923.8	943.6	971.0	998.5	1028.1	1057.7
15°	684.3	693.9	703.6	724.1	744.7	774.5	804.3	841.2	878.1	924.9	971.8
17.5°	562.0	566.1	570.2	590.0	609.8	638.1	666.3	708.1	749.8	810.2	870.6
20°	463.2	466.9	470.6	484.9	499.2	526.3	553.4	593.2	633.0	692.8	752.6
22.5°	386.7	393.9	401.2	410.8	420.4	440.0	459.6	500.2	540.8	595.3	649.8
25°	340.4	343.7	347.1	355.3	363.5	382.4	401.2	428.1	454.9	509.2	563.6
27.5°	309.0	310.0	311.0	317.1	323.1	335.3	347.5	372.4	397.3	442.0	486.7
30°	283.1	284.9	286.7	291.4	296.1	304.9	313.7	331.4	349.0	389.0	429.0
32.5°	263.1	264.1	265.1	269.0	273.0	279.4	285.9	299.8	313.7	344.3	374.9
35°	245.9	246.1	246.3	249.2	252.2	258.4	264.7	276.3	287.9	310.4	333.0
37.5°	226.3	227.7	229.0	231.2	233.3	238.8	244.3	253.7	263.1	281.8	300.4
40°	209.8	211.0	212.2	214.7	217.3	221.6	225.9	234.5	243.1	259.2	275.3
42.5°	193.3	194.1	194.9	197.5	200.0	205.3	210.6	217.5	224.3	237.7	251.0
45°	174.9	176.9	178.8	181.6	184.3	188.8	193.3	200.4	207.5	218.8	230.2
47.5°	159.6	160.6	161.6	163.9	166.3	171.8	177.3	183.5	189.8	200.4	211.0
50°	144.3	144.7	145.1	147.3	149.4	154.3	159.2	166.5	173.7	183.5	193.3
52.5°	129.8	130.8	131.8	133.9	136.1	139.4	142.8	150.2	157.7	167.3	176.9
55°	116.5	117.1	117.7	119.2	120.8	124.7	128.6	135.1	141.6	150.4	159.2
57.5°	103.9	104.7	105.5	106.7	107.8	111.4	114.9	120.6	126.3	135.1	143.9
60°	91.0	92.0	92.9	94.3	95.7	98.4	101.2	106.3	111.4	119.2	127.1
62.5°	81.6	81.8	82.0	83.1	84.3	86.3	88.2	92.4	96.5	104.3	112.2
65°	71.0	71.6	72.2	72.7	73.3	74.9	76.5	80.0	83.5	89.4	95.3
67.5°	60.0	60.6	61.2	62.2	63.1	64.5	65.9	68.2	70.6	76.1	81.6
70°	46.7	46.7	46.7	48.2	49.8	52.2	54.5	56.3	58.0	62.6	67.1
72.5°	38.0	38.2	38.4	38.6	38.8	40.2	41.6	44.5	47.5	50.2	52.9
75°	31.0	31.2	31.4	31.6	31.8	32.2	32.6	33.5	34.5	37.6	40.8
77.5°	24.7	24.9	25.1	25.3	25.5	25.9	26.3	26.7	27.1	28.2	29.4
80°	18.8	19.0	19.2	19.4	19.6	19.8	20.0	20.4	20.8	21.4	22.0
82.5°	13.7	13.7	13.7	13.7	13.7	14.1	14.5	14.5	14.5	14.9	15.3
85°	8.6	8.6	8.6	8.8	9.0	9.0	9.0	9.2	9.4	9.4	9.4
87.5°	3.9	3.7	3.5	3.7	3.9	3.9	3.9	4.1	4.3	4.3	4.3
90°	14.7	14.5	14.3	14.1	13.9	13.5	13.1	12.7	12.2	11.8	10.4
92.5°	21.1	21.3	21.6	21.8	22.0	21.9	21.6	21.3	21.0	20.6	20.0
95°	38.3	38.3	38.3	38.3	38.3	38.1	37.7	37.2	36.8	36.3	35.5
97.5°	55.0	55.1	55.2	55.3	55.4	55.2	54.7	54.1	53.6	53.0	52.4
100°	74.6	74.4	74.2	74.0	73.8	73.5	73.2	72.8	72.5	72.2	71.6
102.5°	94.8	94.9	95.0	95.1	95.2	95.1	94.8	94.5	94.1	93.8	93.0
105°	116.9	116.7	116.4	116.2	116.0	115.9	115.9	115.9	115.9	115.9	114.9
107.5°	139.5	139.6	139.7	139.8	139.9	139.8	139.5	139.1	138.8	138.5	138.1
110°	162.6	162.8	163.0	163.2	163.4	163.3	162.9	162.4	162.0	161.6	161.4



TEST NUMBER: P832135

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	187.1	187.1	187.1	187.1	187.1	186.8	186.3	185.7	185.2	184.7	184.7
115°	209.2	209.3	209.4	209.5	209.6	209.6	209.5	209.4	209.3	209.2	209.4
117.5°	231.8	232.1	232.5	232.8	233.1	233.3	233.3	233.3	233.3	233.3	233.5
120°	255.9	256.1	256.3	256.5	256.7	256.9	257.0	257.1	257.2	257.3	257.9
122.5°	278.9	279.3	279.6	279.9	280.3	280.6	280.9	281.2	281.6	281.9	282.1
125°	302.0	302.5	302.9	303.3	303.8	304.2	304.6	305.1	305.5	306.0	306.2
127.5°	325.1	325.5	326.0	326.4	326.9	327.4	328.1	328.7	329.4	330.0	330.2
130°	347.7	348.5	349.2	350.0	350.8	351.4	351.8	352.2	352.7	353.1	353.4
132.5°	371.3	371.8	372.4	372.9	373.5	374.0	374.5	375.1	375.6	376.2	376.4
135°	395.8	396.0	396.3	396.5	396.7	397.0	397.5	397.9	398.3	398.8	398.9
137.5°	417.4	417.8	418.1	418.4	418.7	419.2	419.7	420.3	420.8	421.4	421.0
140°	438.6	439.3	440.1	440.8	441.6	442.0	442.2	442.3	442.4	442.5	442.4
142.5°	460.2	460.7	461.3	461.8	462.3	462.7	462.8	462.9	463.0	463.1	462.9
145°	480.8	481.2	481.7	482.1	482.5	482.8	482.9	483.0	483.1	483.2	482.9
147.5°	499.5	500.1	500.8	501.4	502.1	502.4	502.4	502.4	502.4	502.4	502.1
150°	517.1	517.8	518.4	519.1	519.8	520.1	520.1	520.1	520.1	520.1	519.9
152.5°	534.3	534.9	535.4	536.0	536.5	536.7	536.5	536.2	536.0	535.8	535.7
155°	549.5	550.3	551.1	551.8	552.6	552.8	552.3	551.9	551.5	551.0	550.9
157.5°	563.8	564.4	565.1	565.8	566.4	566.5	566.1	565.6	565.2	564.8	564.7
160°	577.5	578.0	578.4	578.8	579.3	579.2	578.7	578.1	577.6	577.0	577.0
162.5°	587.9	588.6	589.4	590.1	590.9	591.0	590.5	589.9	589.4	588.8	588.7
165°	597.7	598.4	599.2	600.0	600.7	600.8	600.1	599.5	598.8	598.2	598.2
167.5°	606.5	607.2	607.8	608.5	609.1	609.1	608.5	607.8	607.2	606.5	606.4
170°	612.9	613.7	614.4	615.2	616.0	616.0	615.2	614.4	613.7	612.9	612.9
172.5°	617.8	618.6	619.3	620.1	620.9	620.9	620.3	619.6	619.0	618.3	618.3
175°	621.2	622.0	622.8	623.5	624.3	624.4	623.7	623.0	622.4	621.7	621.7
177.5°	623.2	624.0	624.7	625.5	626.3	626.3	625.7	625.0	624.4	623.7	623.7
180°	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2



TEST NUMBER: P832135

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5
2.5°	1015.5	1014.5	1005.1	995.7	986.5	977.3	970.4	963.6	952.0	940.4	933.2
5°	1078.5	1071.0	1056.1	1041.2	1018.9	996.5	977.7	958.9	934.9	911.0	891.0
7.5°	1113.6	1107.5	1089.5	1071.4	1041.8	1012.2	982.8	953.4	918.1	882.8	852.6
10°	1114.6	1119.6	1104.7	1089.8	1056.5	1023.2	983.2	943.2	895.7	848.3	809.2
12.5°	1079.6	1101.6	1098.5	1095.3	1061.4	1027.5	978.9	930.2	872.0	813.8	764.9
15°	1014.4	1056.9	1069.5	1082.0	1054.0	1025.9	970.6	915.3	846.9	778.5	722.4
17.5°	930.2	989.8	1023.0	1056.1	1035.7	1015.3	954.7	894.2	817.1	740.0	679.0
20°	830.6	908.7	960.6	1012.6	1005.1	997.7	935.1	872.6	789.4	706.3	640.2
22.5°	732.2	814.5	886.3	958.1	965.7	973.4	910.2	847.1	756.1	665.1	597.9
25°	647.3	731.0	816.5	902.0	919.3	936.5	876.5	816.5	722.2	627.9	561.0
27.5°	566.3	645.9	740.0	834.1	865.5	896.9	842.0	787.1	688.8	590.6	523.9
30°	500.2	571.4	667.5	763.6	807.3	851.0	800.6	750.2	652.8	555.3	490.0
32.5°	438.6	502.4	598.8	695.3	746.1	796.9	753.4	709.8	616.1	522.4	457.9
35°	390.0	447.1	537.1	627.1	683.9	740.8	705.1	669.4	577.9	486.3	425.3
37.5°	348.2	396.1	480.6	565.1	625.5	685.9	656.1	626.3	540.2	454.1	396.5
40°	313.7	352.2	430.8	509.4	568.6	627.9	602.4	576.9	499.8	422.8	368.8
42.5°	284.1	317.3	387.9	458.4	512.8	567.1	550.2	533.4	463.5	393.7	343.7
45°	258.0	285.9	348.1	410.2	460.2	510.2	496.9	483.5	423.3	363.2	317.3
47.5°	234.9	258.8	314.3	369.8	414.7	459.6	447.3	434.9	385.1	335.3	293.5
50°	213.7	234.1	280.4	326.7	367.1	407.5	397.3	387.1	345.9	304.7	268.6
52.5°	193.7	210.6	252.2	293.7	326.3	358.8	351.0	343.2	311.4	279.6	246.9
55°	174.7	190.2	225.3	260.4	288.2	316.1	308.2	300.4	275.7	251.0	222.2
57.5°	157.5	171.0	199.4	227.9	250.0	272.2	268.4	264.7	244.1	223.5	199.8
60°	139.2	151.4	175.9	200.4	218.2	236.1	231.8	227.5	212.8	198.0	177.7
62.5°	122.9	133.7	153.3	172.9	187.5	202.0	198.8	195.7	184.5	173.3	156.5
65°	105.9	116.5	132.4	148.2	159.6	171.0	168.2	165.5	157.1	148.6	135.1
67.5°	90.4	99.2	112.9	126.7	134.3	142.0	140.4	138.8	132.4	125.9	115.3
70°	74.7	82.4	93.7	105.1	110.4	115.7	116.3	116.9	111.0	105.1	97.3
72.5°	59.0	65.1	75.7	86.3	90.4	94.5	94.3	94.1	90.6	87.1	80.0
75°	45.3	49.8	58.0	66.3	69.8	73.3	74.1	74.9	71.6	68.2	64.3
77.5°	32.6	35.7	42.0	48.2	52.2	56.1	56.5	56.9	55.3	53.7	50.0
80°	22.9	23.9	27.8	31.8	35.9	40.0	40.6	41.2	39.6	38.0	35.7
82.5°	15.9	16.5	17.8	19.2	22.5	25.9	26.7	27.5	26.7	25.9	23.3
85°	9.6	9.8	10.4	11.0	12.5	14.1	14.9	15.7	15.3	14.9	13.5
87.5°	4.3	4.3	4.5	4.7	5.1	5.5	6.5	7.5	6.9	6.3	5.7
90°	8.9	7.5	6.1	4.9	3.8	2.7	1.6	0.5	1.6	2.7	3.8
92.5°	19.3	18.7	18.0	17.4	16.7	16.0	15.4	14.7	15.4	16.0	16.7
95°	34.6	33.7	32.8	32.0	31.3	30.5	29.7	29.0	29.7	30.5	31.3
97.5°	51.7	51.1	50.4	49.8	49.3	48.7	48.2	47.6	48.2	48.7	49.3
100°	71.1	70.6	70.0	69.4	68.8	68.1	67.4	66.8	67.4	68.1	68.8
102.5°	92.3	91.5	90.7	90.2	89.9	89.5	89.2	88.9	89.2	89.5	89.9
105°	113.9	113.0	112.0	111.4	111.2	110.9	110.7	110.5	110.7	110.9	111.2
107.5°	137.6	137.2	136.7	136.5	136.4	136.3	136.1	136.0	136.1	136.3	136.4
110°	161.1	160.9	160.7	160.5	160.3	160.0	159.8	159.6	159.8	160.0	160.3



TEST NUMBER: P832135

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	184.7	184.7	184.7	184.6	184.5	184.4	184.3	184.2	184.3	184.4	184.5
115°	209.6	209.9	210.1	210.0	209.7	209.4	209.0	208.7	209.0	209.4	209.7
117.5°	233.7	233.9	234.1	234.2	234.1	234.0	233.9	233.8	233.9	234.0	234.1
120°	258.4	259.0	259.5	259.5	258.8	258.2	257.5	256.8	257.5	258.2	258.8
122.5°	282.3	282.5	282.8	282.7	282.2	281.8	281.3	280.9	281.3	281.8	282.2
125°	306.4	306.6	306.8	306.8	306.4	306.1	305.8	305.5	305.8	306.1	306.4
127.5°	330.5	330.7	330.9	330.7	330.0	329.4	328.7	328.1	328.7	329.4	330.0
130°	353.8	354.1	354.4	354.1	353.3	352.4	351.5	350.6	351.5	352.4	353.3
132.5°	376.6	376.8	377.1	376.7	375.9	375.0	374.1	373.2	374.1	375.0	375.9
135°	399.0	399.1	399.2	398.9	398.3	397.6	397.0	396.3	397.0	397.6	398.3
137.5°	420.7	420.4	420.1	419.6	419.1	418.5	418.0	417.4	418.0	418.5	419.1
140°	442.3	442.2	442.0	441.7	441.2	440.6	440.1	439.5	440.1	440.6	441.2
142.5°	462.7	462.5	462.2	461.9	461.3	460.8	460.2	459.7	460.2	460.8	461.3
145°	482.6	482.3	481.9	481.7	481.4	481.2	481.0	480.8	481.0	481.2	481.4
147.5°	501.7	501.4	501.1	500.7	500.3	499.8	499.4	499.0	499.4	499.8	500.3
150°	519.6	519.4	519.2	519.0	518.8	518.6	518.3	518.1	518.3	518.6	518.8
152.5°	535.6	535.5	535.4	535.1	534.8	534.5	534.2	533.8	534.2	534.5	534.8
155°	550.8	550.7	550.6	550.5	550.5	550.5	550.5	550.5	550.5	550.5	550.5
157.5°	564.6	564.4	564.3	564.3	564.4	564.6	564.7	564.8	564.7	564.6	564.4
160°	577.0	577.0	577.0	577.2	577.4	577.6	577.8	578.0	577.8	577.6	577.4
162.5°	588.6	588.5	588.4	588.5	588.8	589.2	589.5	589.8	589.5	589.2	588.8
165°	598.2	598.2	598.2	598.3	598.7	599.0	599.3	599.6	599.3	599.0	598.7
167.5°	606.3	606.2	606.1	606.2	606.7	607.1	607.6	608.0	607.6	607.1	606.7
170°	612.9	612.9	612.9	613.1	613.6	614.0	614.4	614.9	614.4	614.0	613.6
172.5°	618.3	618.3	618.3	618.5	619.0	619.4	619.8	620.3	619.8	619.4	619.0
175°	621.7	621.7	621.7	622.0	622.4	622.8	623.3	623.7	623.3	622.8	622.4
177.5°	623.7	623.7	623.7	623.9	624.4	624.8	625.2	625.7	625.2	624.8	624.4
180°	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2



TEST NUMBER: P832135

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5
2.5°	925.9	914.7	903.6	895.5	887.5	877.5	867.5	867.1	866.7	859.2	851.8
5°	871.0	851.6	832.2	813.2	794.1	775.1	756.1	751.8	747.5	741.0	734.5
7.5°	822.4	791.4	760.4	736.1	711.8	692.8	673.8	660.8	647.9	637.9	627.9
10°	770.2	731.8	693.4	663.9	634.5	613.9	593.4	578.5	563.6	556.5	549.4
12.5°	716.1	674.3	632.6	603.7	574.9	550.2	525.5	512.0	498.5	488.6	478.8
15°	666.3	621.4	576.5	545.9	515.3	492.2	469.0	455.5	442.0	432.2	422.4
17.5°	618.1	572.8	527.5	496.5	465.5	444.5	423.5	410.4	397.3	391.2	385.1
20°	574.1	528.5	482.8	453.5	424.3	403.7	383.2	376.1	369.0	363.3	357.7
22.5°	530.6	486.7	442.8	414.7	386.7	371.8	356.9	351.2	345.5	341.2	336.9
25°	494.1	450.4	406.7	382.2	357.7	346.1	334.5	330.8	327.1	322.8	318.4
27.5°	457.3	415.7	374.1	354.5	334.9	325.5	316.1	311.4	306.7	303.1	299.6
30°	424.7	386.3	347.9	331.6	315.3	307.1	298.8	293.7	288.6	285.3	282.0
32.5°	393.3	359.2	325.1	311.2	297.3	289.2	281.2	276.3	271.4	267.5	263.5
35°	364.3	334.7	305.1	292.4	279.6	271.6	263.5	258.6	253.7	249.8	245.9
37.5°	338.8	312.0	285.1	273.1	261.2	254.1	247.1	242.0	236.9	232.8	228.6
40°	314.9	291.2	267.5	255.9	244.3	236.7	229.0	224.5	220.0	216.3	212.6
42.5°	293.7	272.0	250.2	238.8	227.5	220.2	212.9	207.7	202.4	200.2	198.0
45°	271.4	252.2	232.9	222.0	211.0	203.3	195.7	191.2	186.7	184.7	182.8
47.5°	251.8	233.9	216.1	205.3	194.5	187.7	180.8	177.3	173.7	171.0	168.2
50°	232.6	215.3	198.0	187.7	177.3	171.4	165.5	161.2	156.9	154.9	152.9
52.5°	214.1	198.4	182.8	172.2	161.6	155.9	150.2	146.5	142.8	138.6	134.5
55°	193.3	179.6	165.9	156.5	147.1	141.2	135.3	131.0	126.7	122.4	118.0
57.5°	176.1	162.6	149.0	140.6	132.2	126.5	120.8	116.1	111.4	107.8	104.3
60°	157.3	145.5	133.7	125.5	117.3	111.8	106.3	101.8	97.3	95.5	93.7
62.5°	139.6	128.6	117.7	110.4	103.1	97.8	92.6	89.6	86.7	85.5	84.3
65°	121.6	112.2	102.7	96.1	89.4	84.9	80.4	79.0	77.6	76.7	75.7
67.5°	104.7	96.7	88.6	82.7	76.9	73.7	70.6	69.0	67.5	66.3	65.1
70°	89.4	82.4	75.3	70.2	65.1	62.2	59.2	57.8	56.5	54.3	52.2
72.5°	72.9	67.5	62.0	58.0	54.1	51.6	49.0	46.3	43.5	41.6	39.6
75°	60.4	54.9	49.4	45.7	42.0	39.0	36.1	35.1	34.1	33.5	32.9
77.5°	46.3	41.6	36.9	33.9	31.0	29.6	28.2	27.6	27.1	26.9	26.7
80°	33.3	29.4	25.5	23.9	22.4	22.0	21.6	21.2	20.8	20.6	20.4
82.5°	20.8	18.8	16.9	16.5	16.1	15.9	15.7	15.5	15.3	15.1	14.9
85°	12.2	11.4	10.6	10.4	10.2	10.0	9.8	9.8	9.8	9.8	9.8
87.5°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	4.9	4.7
90°	4.9	6.1	7.5	8.9	10.4	11.8	12.2	12.7	13.1	13.5	13.9
92.5°	17.4	18.0	18.7	19.3	20.0	20.6	21.0	21.3	21.6	21.9	22.0
95°	32.0	32.8	33.7	34.6	35.5	36.3	36.8	37.2	37.7	38.1	38.3
97.5°	49.8	50.4	51.1	51.7	52.4	53.0	53.6	54.1	54.7	55.2	55.4
100°	69.4	70.0	70.6	71.1	71.6	72.2	72.5	72.8	73.2	73.5	73.8
102.5°	90.2	90.7	91.5	92.3	93.0	93.8	94.1	94.5	94.8	95.1	95.2
105°	111.4	112.0	113.0	113.9	114.9	115.9	115.9	115.9	115.9	115.9	116.0
107.5°	136.5	136.7	137.2	137.6	138.1	138.5	138.8	139.1	139.5	139.8	139.9
110°	160.5	160.7	160.9	161.1	161.4	161.6	162.0	162.4	162.9	163.3	163.4



TEST NUMBER: P832135

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	184.6	184.7	184.7	184.7	184.7	184.7	185.2	185.7	186.3	186.8	187.1
115°	210.0	210.1	209.9	209.6	209.4	209.2	209.3	209.4	209.5	209.6	209.6
117.5°	234.2	234.1	233.9	233.7	233.5	233.3	233.3	233.3	233.3	233.3	233.1
120°	259.5	259.5	259.0	258.4	257.9	257.3	257.2	257.1	257.0	256.9	256.7
122.5°	282.7	282.8	282.5	282.3	282.1	281.9	281.6	281.2	280.9	280.6	280.3
125°	306.8	306.8	306.6	306.4	306.2	306.0	305.5	305.1	304.6	304.2	303.8
127.5°	330.7	330.9	330.7	330.5	330.2	330.0	329.4	328.7	328.1	327.4	326.9
130°	354.1	354.4	354.1	353.8	353.4	353.1	352.7	352.2	351.8	351.4	350.8
132.5°	376.7	377.1	376.8	376.6	376.4	376.2	375.6	375.1	374.5	374.0	373.5
135°	398.9	399.2	399.1	399.0	398.9	398.8	398.3	397.9	397.5	397.0	396.7
137.5°	419.6	420.1	420.4	420.7	421.0	421.4	420.8	420.3	419.7	419.2	418.7
140°	441.7	442.0	442.2	442.3	442.4	442.5	442.4	442.3	442.2	442.0	441.6
142.5°	461.9	462.2	462.5	462.7	462.9	463.1	463.0	462.9	462.8	462.7	462.3
145°	481.7	481.9	482.3	482.6	482.9	483.2	483.1	483.0	482.9	482.8	482.5
147.5°	500.7	501.1	501.4	501.7	502.1	502.4	502.4	502.4	502.4	502.4	502.1
150°	519.0	519.2	519.4	519.6	519.9	520.1	520.1	520.1	520.1	520.1	519.8
152.5°	535.1	535.4	535.5	535.6	535.7	535.8	536.0	536.2	536.5	536.7	536.5
155°	550.5	550.6	550.7	550.8	550.9	551.0	551.5	551.9	552.3	552.8	552.6
157.5°	564.3	564.3	564.4	564.6	564.7	564.8	565.2	565.6	566.1	566.5	566.4
160°	577.2	577.0	577.0	577.0	577.0	577.0	577.6	578.1	578.7	579.2	579.3
162.5°	588.5	588.4	588.5	588.6	588.7	588.8	589.4	589.9	590.5	591.0	590.9
165°	598.3	598.2	598.2	598.2	598.2	598.2	598.8	599.5	600.1	600.8	600.7
167.5°	606.2	606.1	606.2	606.3	606.4	606.5	607.2	607.8	608.5	609.1	609.1
170°	613.1	612.9	612.9	612.9	612.9	612.9	613.7	614.4	615.2	616.0	616.0
172.5°	618.5	618.3	618.3	618.3	618.3	618.3	619.0	619.6	620.3	620.9	620.9
175°	622.0	621.7	621.7	621.7	621.7	621.7	622.4	623.0	623.7	624.4	624.3
177.5°	623.9	623.7	623.7	623.7	623.7	623.7	624.4	625.0	625.7	626.3	626.3
180°	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2

TEST NUMBER: P832135

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	956.5	956.5	956.5	956.5
2.5°	849.8	847.9	847.1	846.3
5°	728.5	722.4	721.0	719.6
7.5°	625.3	622.8	614.3	605.9
10°	541.6	533.7	530.2	526.7
12.5°	471.6	464.3	463.2	462.0
15°	417.3	412.2	410.4	408.6
17.5°	381.6	378.1	375.9	373.7
20°	355.1	352.6	351.0	349.4
22.5°	334.9	333.0	331.8	330.6
25°	315.5	312.6	311.6	310.6
27.5°	297.1	294.5	293.5	292.6
30°	279.8	277.7	276.3	274.9
32.5°	261.0	258.4	257.7	256.9
35°	244.3	242.8	242.0	241.2
37.5°	226.7	224.7	223.5	222.4
40°	211.6	210.6	210.0	209.4
42.5°	196.3	194.5	194.3	194.1
45°	181.0	179.2	178.8	178.4
47.5°	166.7	165.1	164.9	164.7
50°	150.8	148.6	147.1	145.5
52.5°	132.6	130.6	129.2	127.8
55°	115.9	113.7	112.6	111.4
57.5°	103.3	102.4	101.8	101.2
60°	93.1	92.6	92.2	91.8
62.5°	83.7	83.1	83.1	83.1
65°	75.1	74.5	73.9	73.3
67.5°	63.9	62.7	62.6	62.4
70°	50.4	48.6	48.4	48.2
72.5°	39.4	39.2	38.8	38.4
75°	32.6	32.2	32.2	32.2
77.5°	26.3	25.9	25.9	25.9
80°	20.2	20.0	20.2	20.4
82.5°	14.9	14.9	14.7	14.5
85°	9.6	9.4	9.4	9.4
87.5°	4.7	4.7	4.7	4.7
90°	14.1	14.3	14.5	14.7
92.5°	21.8	21.6	21.3	21.1
95°	38.3	38.3	38.3	38.3
97.5°	55.3	55.2	55.1	55.0
100°	74.0	74.2	74.4	74.6
102.5°	95.1	95.0	94.9	94.8
105°	116.2	116.4	116.7	116.9
107.5°	139.8	139.7	139.6	139.5
110°	163.2	163.0	162.8	162.6



TEST NUMBER: P832135

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	187.1	187.1	187.1	187.1
115°	209.5	209.4	209.3	209.2
117.5°	232.8	232.5	232.1	231.8
120°	256.5	256.3	256.1	255.9
122.5°	279.9	279.6	279.3	278.9
125°	303.3	302.9	302.5	302.0
127.5°	326.4	326.0	325.5	325.1
130°	350.0	349.2	348.5	347.7
132.5°	372.9	372.4	371.8	371.3
135°	396.5	396.3	396.0	395.8
137.5°	418.4	418.1	417.8	417.4
140°	440.8	440.1	439.3	438.6
142.5°	461.8	461.3	460.7	460.2
145°	482.1	481.7	481.2	480.8
147.5°	501.4	500.8	500.1	499.5
150°	519.1	518.4	517.8	517.1
152.5°	536.0	535.4	534.9	534.3
155°	551.8	551.1	550.3	549.5
157.5°	565.8	565.1	564.4	563.8
160°	578.8	578.4	578.0	577.5
162.5°	590.1	589.4	588.6	587.9
165°	600.0	599.2	598.4	597.7
167.5°	608.5	607.8	607.2	606.5
170°	615.2	614.4	613.7	612.9
172.5°	620.1	619.3	618.6	617.8
175°	623.5	622.8	622.0	621.2
177.5°	625.5	624.7	624.0	623.2
180°	625.2	625.2	625.2	625.2



TEST NUMBER: P832135

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-G1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.08	8.83	9.11	9.86	11.24	12.74	13.49	13.77	14.52	15.91
	3H	9.29	9.96	10.33	11.00	12.40	14.23	14.91	15.28	15.95	17.35
	4H	9.67	10.31	10.72	11.35	12.76	14.72	15.36	15.77	16.40	17.81
	6H	9.95	10.53	11.01	11.58	13.00	15.03	15.61	16.09	16.66	18.08
	8H	10.03	10.59	11.10	11.65	13.07	15.11	15.66	16.17	16.72	18.14
	12H	10.08	10.61	11.15	11.66	13.10	15.13	15.66	16.21	16.72	18.16
4H	2H	8.79	9.43	9.85	10.47	11.88	12.73	13.36	13.79	14.41	15.81
	3H	10.15	10.68	11.22	11.75	13.17	14.38	14.91	15.44	15.98	17.40
	4H	10.61	11.09	11.68	12.15	13.59	14.98	15.47	16.05	16.53	17.97
	6H	10.97	11.38	12.05	12.47	13.91	15.42	15.83	16.50	16.92	18.35
	8H	11.09	11.48	12.17	12.56	14.01	15.55	15.93	16.63	17.01	18.46
	12H	11.16	11.51	12.26	12.60	14.06	15.60	15.95	16.70	17.04	18.50
8H	4H	10.91	11.30	11.99	12.38	13.83	14.94	15.33	16.02	16.41	17.86
	6H	11.38	11.69	12.48	12.81	14.26	15.44	15.76	16.54	16.88	18.32
	8H	11.57	11.85	12.68	12.95	14.42	15.62	15.90	16.73	17.00	18.47
	12H	11.70	11.95	12.82	13.05	14.56	15.74	15.98	16.85	17.08	18.59
12H	4H	10.92	11.27	12.02	12.36	13.82	14.89	15.24	15.99	16.33	17.79
	6H	11.43	11.71	12.54	12.81	14.28	15.41	15.69	16.52	16.79	18.26
	8H	11.65	11.89	12.76	12.99	14.50	15.60	15.85	16.71	16.94	18.45