

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332276-935

Luminaire Tested: **S123RDIP-S560D585U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332276-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D585U935-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3935.6 lumens
Efficiency: N/A
Efficacy: 120.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332276-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332276-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	49	48	48	42
2	90	83	77	72	83	77	71	67	65	61	58	54	52	49	44	42	41	36
3	82	73	66	61	76	68	62	57	58	53	49	48	45	42	40	37	35	31
4	75	65	58	52	69	60	54	49	52	47	43	43	40	37	36	33	31	27
5	69	58	50	45	64	54	47	42	46	41	37	39	35	32	33	30	27	24
6	64	52	45	39	59	49	42	37	42	37	33	36	32	28	30	27	24	21
7	59	48	40	34	55	44	37	33	38	33	29	33	28	25	27	24	22	19
8	55	43	36	31	51	40	34	29	35	30	26	30	26	23	25	22	20	17
9	51	40	32	27	48	37	30	26	32	27	23	28	23	21	23	20	18	16
10	48	36	29	25	44	34	28	23	30	25	21	26	21	19	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8291	8291	8291	8291
5°	9884	8327	7333	8327
10°	12342	8279	6625	8279
15°	14487	8195	6042	8195
20°	16167	8069	5545	8069
25°	15909	7935	5241	7935
30°	11436	7812	4927	7812
35°	7636	7653	4724	7653
40°	5626	7461	4513	7461
45°	4719	7124	4306	7124
50°	4165	6683	4019	6683
55°	3652	6178	3626	6178
60°	3251	5694	3324	5694
65°	2855	5173	3092	5173
70°	2241	4711	2823	4711
75°	1975	4113	2578	4113
80°	1717	3496	2535	3496
85°	1383	2803	2692	2803



TEST NUMBER: P332276-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.8	1.9
10°-20°	236.7	6.0
20°-30°	371.8	9.4
30°-40°	387.9	9.9
40°-50°	332.0	8.4
50°-60°	253.0	6.4
60°-70°	162.2	4.1
70°-80°	78.0	2.0
80°-90°	22.5	0.6
90°-100°	24.0	0.6
100°-110°	114.5	2.9
110°-120°	275.1	7.0
120°-130°	350.3	8.9
130°-140°	374.3	9.5
140°-150°	350.0	8.9
150°-160°	282.3	7.2
160°-170°	182.2	4.6
170°-180°	62.8	1.6
0°-30°	684.3	17.4
0°-40°	1072.2	27.2
0°-60°	1657.2	42.1
0°-90°	1919.9	48.8
90°-120°	413.7	10.5
90°-150°	1488.3	37.8
90°-180°	2016.0	51.2
0°-180°	3935.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	770	770	770	770	770	
5°	915	771	679	771	915	94
15°	1300	735	542	735	1300	369
25°	1340	668	441	668	1340	576
35°	581	582	360	582	581	381
45°	310	468	283	468	310	244
55°	195	329	193	329	195	176
65°	112	203	121	203	112	110
75°	48	99	62	99	48	51
85°	11	23	22	23	11	13
90°	15	0	15	0	15	7
95°	19	30	19	30	19	16
105°	22	146	22	146	22	49
115°	289	274	289	274	289	267
125°	395	387	395	387	395	353
135°	487	482	487	482	487	375
145°	561	556	561	556	561	350
155°	611	612	611	612	611	282
165°	644	646	644	646	644	182
175°	658	661	658	661	658	63
180°	661	661	661	661	661	



TEST NUMBER: P332276-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	820.4	821.6	818.1	817.6	813.6	812.6	812.6	807.0	803.6	799.1	796.5
5°	914.8	920.1	917.5	911.5	901.6	899.3	893.0	883.1	871.9	858.1	851.5
7.5°	1032.6	1039.8	1037.0	1027.9	1017.5	1009.1	991.4	975.0	952.0	931.9	914.6
10°	1129.2	1121.5	1115.7	1106.7	1097.2	1081.7	1063.2	1037.8	1008.5	985.4	959.7
12.5°	1201.4	1200.2	1192.7	1183.5	1170.0	1155.3	1132.6	1101.6	1067.6	1034.1	1004.8
15°	1300.0	1302.0	1297.0	1287.5	1268.3	1242.3	1208.0	1195.2	1146.3	1110.0	1073.8
17.5°	1368.2	1367.8	1367.1	1353.8	1334.4	1315.8	1284.0	1250.2	1206.0	1154.9	1106.0
20°	1411.4	1408.2	1408.9	1394.0	1379.5	1358.1	1327.1	1277.9	1241.6	1182.6	1132.1
22.5°	1410.4	1409.7	1412.2	1407.1	1396.6	1380.2	1355.8	1314.3	1268.0	1208.4	1151.7
25°	1339.5	1337.0	1352.5	1356.7	1373.6	1376.5	1369.2	1346.5	1302.6	1241.3	1171.0
27.5°	1121.1	1119.6	1148.4	1184.4	1230.1	1265.6	1299.9	1316.4	1302.6	1258.7	1188.4
30°	920.1	951.1	965.6	1017.7	1075.7	1145.0	1205.7	1263.3	1277.6	1258.4	1200.8
32.5°	763.9	790.9	803.1	847.8	901.9	983.0	1074.0	1155.7	1213.5	1228.1	1193.3
35°	581.1	581.4	609.1	628.9	679.0	762.4	850.8	960.3	1069.1	1151.6	1160.2
37.5°	463.6	465.3	482.1	501.8	539.4	583.5	661.3	752.3	878.0	1004.6	1078.8
40°	400.4	403.3	415.9	435.3	462.4	495.7	556.4	642.0	746.9	887.8	1002.9
42.5°	359.7	364.5	371.0	386.0	402.7	433.9	483.0	549.2	644.5	777.7	910.5
45°	310.0	312.6	317.5	324.5	339.7	361.4	394.4	438.9	518.1	625.3	758.2
47.5°	273.5	272.1	277.2	282.9	293.0	307.8	329.9	366.3	422.8	508.7	621.5
50°	248.7	248.3	251.9	256.2	265.8	276.7	294.8	322.2	367.0	438.2	541.5
52.5°	225.4	226.7	229.3	234.6	241.5	250.3	266.6	286.3	324.9	386.3	472.3
55°	194.6	195.5	199.1	202.2	207.1	216.0	226.3	242.7	269.1	311.9	382.9
57.5°	168.4	168.0	171.5	172.2	177.8	185.0	193.0	205.8	224.9	256.8	304.5
60°	151.0	150.1	153.0	155.3	158.3	164.2	170.8	183.4	198.5	222.0	262.9
62.5°	135.2	134.7	136.9	139.2	141.6	147.1	152.7	162.2	174.3	194.0	226.4
65°	112.1	113.1	114.1	115.1	116.4	119.7	125.0	131.6	139.8	153.7	177.1
67.5°	88.1	89.1	89.5	91.4	94.3	96.3	99.6	105.5	111.2	122.9	136.2
70°	71.2	70.9	71.2	72.2	75.9	79.5	83.8	88.1	91.7	100.0	111.2
72.5°	61.2	60.6	61.5	61.6	63.5	64.4	67.2	71.2	75.9	81.5	89.5
75°	47.5	47.5	47.5	47.5	48.8	49.5	50.5	51.5	53.1	55.7	61.6
77.5°	35.1	35.1	35.6	35.9	36.2	36.6	37.2	38.2	38.7	40.2	42.7
80°	27.7	28.1	27.7	28.1	28.1	28.7	29.0	30.0	30.3	32.0	33.0
82.5°	20.8	20.7	20.8	21.2	21.2	21.9	21.9	22.6	22.7	23.5	24.5
85°	11.2	10.6	11.2	10.8	11.5	10.8	11.2	11.9	11.9	12.2	13.5
87.5°	5.6	6.0	5.5	5.7	5.7	5.9	5.8	5.7	6.1	5.8	5.8
90°	14.7	14.6	14.3	14.1	13.9	13.5	13.1	12.7	12.2	11.8	10.3
92.5°	16.3	16.2	16.0	15.9	15.8	15.3	14.6	13.9	13.3	12.6	11.5
95°	18.7	18.7	18.7	18.7	18.7	18.3	17.5	16.8	16.0	15.2	14.0
97.5°	20.2	20.1	20.0	19.9	19.8	19.3	18.4	17.6	16.7	15.8	23.7
100°	20.7	20.5	20.4	20.3	20.1	19.7	18.9	17.9	17.0	16.2	33.2
102.5°	21.0	20.8	20.7	20.4	20.2	21.5	24.2	26.9	29.6	32.3	50.9
105°	21.6	21.4	21.2	20.9	20.8	30.3	49.6	68.9	88.3	107.5	117.4
107.5°	67.8	82.4	96.9	111.5	126.1	140.4	154.6	168.8	183.0	197.1	195.5
110°	135.0	150.7	166.3	181.8	197.4	207.1	210.7	214.3	217.8	221.4	220.2



TEST NUMBER: P332276-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	231.7	235.0	238.2	241.6	244.9	246.5	246.4	246.3	246.3	246.2	245.0
115°	288.8	288.3	287.9	287.4	287.0	286.3	285.2	284.0	283.0	281.9	280.9
117.5°	320.8	320.7	320.6	320.6	320.5	319.9	319.1	318.2	317.4	316.4	316.0
120°	342.8	342.8	342.8	342.8	342.8	342.3	341.5	340.6	339.8	338.8	338.5
122.5°	364.4	364.3	364.2	364.1	364.0	363.7	363.1	362.5	361.9	361.3	360.8
125°	394.9	394.6	394.4	394.2	394.0	393.7	393.5	393.3	393.0	392.9	392.4
127.5°	424.1	424.3	424.6	424.7	425.0	424.9	424.6	424.2	423.9	423.5	423.0
130°	443.0	443.2	443.4	443.6	443.8	443.7	443.2	442.8	442.4	442.0	441.5
132.5°	460.2	460.5	460.8	461.2	461.5	461.4	461.0	460.5	460.1	459.7	459.3
135°	486.6	487.0	487.3	487.7	487.9	487.9	487.7	487.3	487.0	486.6	486.2
137.5°	511.5	511.7	512.0	512.1	512.4	512.2	511.7	511.2	510.7	510.1	509.9
140°	526.4	526.7	526.8	527.1	527.3	527.2	526.8	526.3	525.9	525.5	525.1
142.5°	540.2	540.4	540.8	541.1	541.4	541.4	541.1	540.7	540.4	540.0	539.7
145°	561.3	561.3	561.3	561.3	561.3	561.2	560.9	560.8	560.5	560.3	560.1
147.5°	577.0	577.6	578.0	578.5	579.0	579.2	578.9	578.8	578.5	578.3	578.1
150°	588.8	589.1	589.4	589.8	590.1	590.1	590.0	589.7	589.5	589.3	589.1
152.5°	598.2	598.7	599.3	599.8	600.2	600.3	599.9	599.5	599.1	598.7	598.6
155°	611.4	612.1	612.7	613.4	614.0	614.1	613.5	612.9	612.4	611.9	611.7
157.5°	622.5	623.4	624.2	625.0	625.9	626.0	625.3	624.7	624.1	623.4	623.5
160°	629.6	630.3	631.1	631.9	632.6	632.7	632.0	631.4	630.7	630.1	630.2
162.5°	636.3	636.9	637.6	638.3	638.9	638.9	638.2	637.4	636.7	635.9	636.0
165°	644.3	645.1	645.8	646.6	647.4	647.3	646.4	645.6	644.7	643.8	643.9
167.5°	650.1	651.0	651.9	652.7	653.6	653.6	652.7	651.9	651.0	650.1	650.1
170°	653.6	654.5	655.4	656.3	657.1	657.1	656.3	655.4	654.5	653.6	653.6
172.5°	655.6	656.5	657.5	658.5	659.4	659.4	658.6	657.7	656.9	656.0	655.9
175°	658.5	659.4	660.3	661.2	662.0	662.1	661.3	660.6	659.8	659.0	658.9
177.5°	659.4	660.3	661.2	662.0	662.9	663.0	662.3	661.6	660.9	660.2	660.1
180°	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0



TEST NUMBER: P332276-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	795.4	794.6	790.9	786.7	781.2	777.5	774.6	773.0	768.3	762.4	758.5
5°	844.6	834.7	824.1	811.2	799.4	787.2	779.6	770.7	759.8	747.6	739.0
7.5°	897.2	877.8	856.9	835.3	814.0	794.9	778.0	763.5	746.2	728.8	716.4
10°	937.5	909.2	879.9	849.8	822.4	796.8	777.0	757.5	736.8	716.6	701.5
12.5°	974.2	936.9	903.1	866.2	831.2	800.5	772.0	749.1	724.1	702.7	685.4
15°	1020.6	982.4	941.5	885.5	839.0	800.0	765.4	735.4	705.1	678.7	661.9
17.5°	1064.0	1006.5	951.6	904.7	844.4	795.7	753.5	717.6	684.3	656.3	635.6
20°	1082.0	1026.3	966.6	906.9	847.6	793.2	744.0	704.4	669.8	638.1	619.0
22.5°	1092.8	1029.7	966.8	902.7	839.6	783.1	734.5	691.0	653.4	623.4	599.8
25°	1105.4	1030.2	961.0	897.7	833.4	772.0	714.3	668.1	627.6	595.6	570.5
27.5°	1113.7	1025.3	943.4	873.1	807.8	746.7	693.9	644.9	603.7	569.9	543.0
30°	1115.3	1021.3	930.0	853.8	787.5	731.4	675.4	628.5	585.0	549.1	524.0
32.5°	1117.4	1011.6	911.8	830.9	763.0	707.5	656.7	611.9	567.3	531.9	506.4
35°	1108.7	1006.2	884.2	791.2	723.2	669.4	623.6	582.4	538.6	504.2	478.2
37.5°	1071.3	984.7	855.5	746.4	675.4	625.6	588.2	552.3	512.1	475.1	450.6
40°	1033.5	963.6	833.4	719.3	645.1	593.9	560.3	531.0	492.1	457.4	431.0
42.5°	977.3	934.9	812.3	690.8	610.7	561.5	533.1	505.6	471.5	436.3	411.5
45°	874.3	879.9	769.0	645.4	563.3	513.8	487.1	468.0	437.6	408.6	383.2
47.5°	744.9	797.4	718.3	597.0	513.2	466.7	443.4	426.7	406.3	377.8	354.6
50°	660.6	735.4	677.7	564.6	481.8	435.7	412.6	399.1	381.3	358.8	336.7
52.5°	582.7	663.1	628.6	528.4	447.8	405.5	383.0	371.9	357.7	336.7	316.7
55°	475.2	556.6	548.7	473.9	396.7	358.8	341.6	329.2	319.5	303.8	287.9
57.5°	384.4	461.6	465.7	413.2	351.7	314.3	299.5	290.1	283.8	271.9	257.3
60°	327.2	398.0	411.9	372.3	319.5	286.5	272.1	264.5	259.5	249.9	238.8
62.5°	279.7	340.0	355.7	327.2	288.7	257.8	246.5	239.2	235.8	227.6	217.7
65°	214.0	264.2	279.3	263.5	243.4	218.6	209.4	203.1	200.2	195.5	188.3
67.5°	160.9	197.5	214.1	202.9	195.7	180.0	174.2	170.8	168.2	165.1	158.9
70°	129.2	156.4	173.5	170.5	164.5	156.4	152.1	149.7	147.1	144.5	139.1
72.5°	103.9	122.5	138.6	140.2	135.3	133.6	129.8	128.9	127.3	124.2	121.2
75°	69.0	81.8	93.0	97.3	99.3	100.9	99.3	98.9	98.6	96.0	94.3
77.5°	45.2	52.1	59.2	66.5	69.6	71.8	72.3	73.5	72.7	71.3	70.5
80°	34.6	36.2	41.2	47.5	52.4	54.4	55.7	56.4	56.1	55.7	54.4
82.5°	25.1	26.5	28.8	33.2	37.4	40.7	41.5	41.3	42.1	42.3	41.2
85°	13.5	13.9	14.6	15.2	17.5	21.1	22.1	22.7	23.4	23.4	21.4
87.5°	6.0	5.4	5.7	5.4	6.0	6.1	7.4	8.5	9.0	8.2	8.4
90°	9.0	7.5	6.1	4.8	3.8	2.7	1.5	0.5	1.5	2.7	3.8
92.5°	10.4	9.4	8.3	7.9	8.2	8.5	8.9	9.1	8.9	8.5	8.2
95°	12.8	11.6	10.4	12.1	16.5	21.0	25.5	30.0	25.5	21.0	16.5
97.5°	31.5	39.3	47.3	52.2	54.2	56.2	58.2	60.2	58.2	56.2	54.2
100°	50.3	67.2	84.3	91.7	89.5	87.4	85.2	83.0	85.2	87.4	89.5
102.5°	69.5	88.1	106.7	115.2	113.7	112.1	110.5	108.9	110.5	112.1	113.7
105°	127.2	137.0	146.8	151.1	149.9	148.8	147.6	146.4	147.6	148.8	149.9
107.5°	194.0	192.4	190.9	189.7	188.7	187.8	186.8	185.8	186.8	187.8	188.7
110°	219.0	217.8	216.7	215.6	214.7	213.9	213.0	212.2	213.0	213.9	214.7



TEST NUMBER: P332276-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	243.8	242.6	241.4	240.4	239.6	238.8	238.1	237.3	238.1	238.8	239.6
115°	279.9	279.0	277.9	277.2	276.5	275.8	275.2	274.5	275.2	275.8	276.5
117.5°	315.5	315.0	314.4	313.7	313.0	312.2	311.3	310.6	311.3	312.2	313.0
120°	338.2	337.9	337.5	336.9	335.9	334.9	333.9	332.9	333.9	334.9	335.9
122.5°	360.4	360.0	359.6	359.0	358.2	357.3	356.5	355.8	356.5	357.3	358.2
125°	392.0	391.6	391.2	390.5	389.6	388.7	387.9	386.9	387.9	388.7	389.6
127.5°	422.5	421.9	421.4	420.7	419.8	419.0	418.1	417.2	418.1	419.0	419.8
130°	441.1	440.7	440.2	439.5	438.7	437.8	437.0	436.1	437.0	437.8	438.7
132.5°	458.9	458.6	458.2	457.6	456.8	455.9	455.0	454.2	455.0	455.9	456.8
135°	485.8	485.3	484.9	484.4	483.7	483.0	482.4	481.7	482.4	483.0	483.7
137.5°	509.6	509.4	509.2	508.6	507.8	507.0	506.2	505.3	506.2	507.0	507.8
140°	524.8	524.4	524.2	523.7	523.0	522.4	521.7	521.0	521.7	522.4	523.0
142.5°	539.3	539.0	538.6	538.2	537.5	536.9	536.2	535.5	536.2	536.9	537.5
145°	559.9	559.6	559.5	559.0	558.2	557.4	556.6	555.9	556.6	557.4	558.2
147.5°	577.8	577.6	577.4	577.0	576.5	576.1	575.6	575.1	575.6	576.1	576.5
150°	588.8	588.7	588.4	588.1	587.8	587.5	587.2	586.9	587.2	587.5	587.8
152.5°	598.5	598.3	598.2	598.1	597.9	597.7	597.6	597.4	597.6	597.7	597.9
155°	611.7	611.6	611.5	611.5	611.7	611.9	612.2	612.3	612.2	611.9	611.7
157.5°	623.6	623.7	623.8	623.9	623.9	623.9	624.0	624.0	624.0	623.9	623.9
160°	630.3	630.3	630.5	630.6	630.7	630.9	630.9	631.0	630.9	630.9	630.7
162.5°	636.2	636.3	636.4	636.5	636.9	637.1	637.4	637.7	637.4	637.1	636.9
165°	644.0	644.1	644.2	644.5	644.8	645.1	645.4	645.8	645.4	645.1	644.8
167.5°	650.1	650.1	650.1	650.3	650.7	651.2	651.6	652.0	651.6	651.2	650.7
170°	653.6	653.6	653.6	653.8	654.3	654.7	655.1	655.6	655.1	654.7	654.3
172.5°	655.8	655.7	655.7	655.8	656.3	656.9	657.5	658.0	657.5	656.9	656.3
175°	658.8	658.7	658.6	658.8	659.4	659.9	660.5	661.0	660.5	659.9	659.4
177.5°	660.0	660.0	659.9	660.0	660.5	660.9	661.3	661.8	661.3	660.9	660.5
180°	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0



TEST NUMBER: P332276-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	757.2	753.7	751.4	746.1	742.7	739.0	735.3	737.6	737.4	737.1	737.1
5°	731.8	724.2	717.3	708.3	702.7	695.9	690.5	689.9	691.2	686.6	684.0
7.5°	706.6	696.2	686.4	676.6	666.2	657.8	652.6	650.2	646.9	644.0	641.0
10°	688.9	676.7	667.1	655.0	643.8	633.9	627.6	623.3	621.0	618.6	614.4
12.5°	670.7	658.8	646.5	632.7	622.1	610.6	606.0	601.2	596.7	594.1	588.2
15°	644.0	628.5	615.7	601.2	589.4	578.1	571.5	562.0	560.6	557.3	551.4
17.5°	617.3	600.5	582.8	572.0	558.6	547.0	536.9	533.7	524.3	520.7	515.6
20°	596.2	580.7	567.2	553.0	533.6	522.7	514.8	510.5	502.9	498.3	495.0
22.5°	578.1	562.2	546.6	530.1	514.0	501.9	496.0	489.4	485.3	478.8	475.2
25°	552.1	534.9	516.1	498.3	486.7	477.5	468.3	462.4	456.4	453.4	446.9
27.5°	521.9	503.9	486.4	472.9	458.7	449.5	441.2	435.9	428.8	423.8	420.2
30°	505.2	484.1	469.0	456.8	438.6	430.1	423.8	417.2	411.9	406.7	402.9
32.5°	485.9	466.7	452.3	437.2	423.3	414.0	405.8	400.0	395.5	390.5	386.9
35°	455.7	439.6	424.7	409.6	399.3	389.8	380.2	375.3	371.0	366.4	363.1
37.5°	428.4	413.4	399.2	384.9	372.2	364.4	356.7	352.9	347.2	344.1	340.7
40°	411.6	396.7	381.6	367.7	354.5	348.6	341.6	336.0	330.8	328.5	324.9
42.5°	393.1	378.2	365.5	350.5	339.8	331.7	325.3	319.2	315.2	311.9	309.8
45°	365.8	352.5	340.0	325.2	315.0	308.0	300.7	295.2	291.5	289.2	285.6
47.5°	339.1	326.0	313.2	300.3	290.4	282.5	275.3	271.3	266.6	263.7	261.2
50°	319.9	308.0	294.5	282.6	272.8	264.8	258.9	253.9	249.6	246.0	244.4
52.5°	302.2	289.6	277.8	266.8	256.4	247.4	242.0	236.8	233.6	229.4	227.5
55°	273.0	260.9	251.0	240.0	229.9	222.3	215.7	211.0	207.8	203.1	200.5
57.5°	245.6	234.7	222.9	213.5	202.9	196.6	191.1	184.8	180.8	177.2	174.6
60°	227.2	214.6	204.5	195.5	186.3	178.1	173.1	168.2	163.9	160.2	158.0
62.5°	207.9	197.0	187.4	177.6	169.2	162.0	156.3	152.1	148.4	146.0	143.7
65°	178.4	169.9	160.0	152.1	144.1	138.9	134.2	130.6	127.9	126.3	124.3
67.5°	151.3	142.9	134.3	126.5	121.2	117.2	114.2	111.1	109.8	107.6	106.3
70°	133.5	125.0	117.4	111.5	106.2	103.2	101.3	98.9	97.6	95.0	93.7
72.5°	114.3	108.1	102.6	97.7	93.5	90.8	88.3	85.5	83.3	80.5	79.1
75°	90.1	84.5	80.2	76.8	74.2	70.6	67.0	64.0	63.0	62.0	61.6
77.5°	66.6	63.1	60.0	57.3	54.0	51.3	50.5	49.9	49.7	49.2	49.2
80°	52.4	49.2	46.8	43.6	41.6	41.6	41.6	40.9	41.2	41.2	41.2
82.5°	39.0	35.9	34.7	33.5	33.1	33.4	33.4	33.5	33.3	33.8	33.6
85°	20.1	20.4	21.1	20.8	21.1	21.1	21.8	21.4	21.8	21.1	21.8
87.5°	8.4	9.4	10.0	10.5	11.0	11.0	11.5	11.5	11.9	12.0	12.0
90°	4.8	6.1	7.5	9.0	10.3	11.8	12.2	12.7	13.1	13.5	13.9
92.5°	7.9	8.3	9.4	10.4	11.5	12.6	13.3	13.9	14.6	15.3	15.8
95°	12.1	10.4	11.6	12.8	14.0	15.2	16.0	16.8	17.5	18.3	18.7
97.5°	52.2	47.3	39.3	31.5	23.7	15.8	16.7	17.6	18.4	19.3	19.8
100°	91.7	84.3	67.2	50.3	33.2	16.2	17.0	17.9	18.9	19.7	20.1
102.5°	115.2	106.7	88.1	69.5	50.9	32.3	29.6	26.9	24.2	21.5	20.2
105°	151.1	146.8	137.0	127.2	117.4	107.5	88.3	68.9	49.6	30.3	20.8
107.5°	189.7	190.9	192.4	194.0	195.5	197.1	183.0	168.8	154.6	140.4	126.1
110°	215.6	216.7	217.8	219.0	220.2	221.4	217.8	214.3	210.7	207.1	197.4



TEST NUMBER: P332276-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	240.4	241.4	242.6	243.8	245.0	246.2	246.3	246.3	246.4	246.5	244.9
115°	277.2	277.9	279.0	279.9	280.9	281.9	283.0	284.0	285.2	286.3	287.0
117.5°	313.7	314.4	315.0	315.5	316.0	316.4	317.4	318.2	319.1	319.9	320.5
120°	336.9	337.5	337.9	338.2	338.5	338.8	339.8	340.6	341.5	342.3	342.8
122.5°	359.0	359.6	360.0	360.4	360.8	361.3	361.9	362.5	363.1	363.7	364.0
125°	390.5	391.2	391.6	392.0	392.4	392.9	393.0	393.3	393.5	393.7	394.0
127.5°	420.7	421.4	421.9	422.5	423.0	423.5	423.9	424.2	424.6	424.9	425.0
130°	439.5	440.2	440.7	441.1	441.5	442.0	442.4	442.8	443.2	443.7	443.8
132.5°	457.6	458.2	458.6	458.9	459.3	459.7	460.1	460.5	461.0	461.4	461.5
135°	484.4	484.9	485.3	485.8	486.2	486.6	487.0	487.3	487.7	487.9	487.9
137.5°	508.6	509.2	509.4	509.6	509.9	510.1	510.7	511.2	511.7	512.2	512.4
140°	523.7	524.2	524.4	524.8	525.1	525.5	525.9	526.3	526.8	527.2	527.3
142.5°	538.2	538.6	539.0	539.3	539.7	540.0	540.4	540.7	541.1	541.4	541.4
145°	559.0	559.5	559.6	559.9	560.1	560.3	560.5	560.8	560.9	561.2	561.3
147.5°	577.0	577.4	577.6	577.8	578.1	578.3	578.5	578.8	578.9	579.2	579.0
150°	588.1	588.4	588.7	588.8	589.1	589.3	589.5	589.7	590.0	590.1	590.1
152.5°	598.1	598.2	598.3	598.5	598.6	598.7	599.1	599.5	599.9	600.3	600.2
155°	611.5	611.5	611.6	611.7	611.7	611.9	612.4	612.9	613.5	614.1	614.0
157.5°	623.9	623.8	623.7	623.6	623.5	623.4	624.1	624.7	625.3	626.0	625.9
160°	630.6	630.5	630.3	630.3	630.2	630.1	630.7	631.4	632.0	632.7	632.6
162.5°	636.5	636.4	636.3	636.2	636.0	635.9	636.7	637.4	638.2	638.9	638.9
165°	644.5	644.2	644.1	644.0	643.9	643.8	644.7	645.6	646.4	647.3	647.4
167.5°	650.3	650.1	650.1	650.1	650.1	650.1	651.0	651.9	652.7	653.6	653.6
170°	653.8	653.6	653.6	653.6	653.6	653.6	654.5	655.4	656.3	657.1	657.1
172.5°	655.8	655.7	655.7	655.8	655.9	656.0	656.9	657.7	658.6	659.4	659.4
175°	658.8	658.6	658.7	658.8	658.9	659.0	659.8	660.6	661.3	662.1	662.0
177.5°	660.0	659.9	660.0	660.0	660.1	660.2	660.9	661.6	662.3	663.0	662.9
180°	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0



TEST NUMBER: P332276-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	733.9	733.7	733.9	732.9	733.9	733.7	733.9	737.1	737.1	737.4	737.6
5°	682.9	682.6	681.7	678.7	681.7	682.6	682.9	684.0	686.6	691.2	689.9
7.5°	638.4	638.0	635.1	635.2	635.1	638.0	638.4	641.0	644.0	646.9	650.2
10°	612.1	612.4	608.5	606.1	608.5	612.4	612.1	614.4	618.6	621.0	623.3
12.5°	586.5	585.0	581.8	579.2	581.8	585.0	586.5	588.2	594.1	596.7	601.2
15°	552.7	549.4	541.5	542.2	541.5	549.4	552.7	551.4	557.3	560.6	562.0
17.5°	512.9	510.5	510.4	505.8	510.4	510.5	512.9	515.6	520.7	524.3	533.7
20°	489.7	488.1	488.7	484.1	488.7	488.1	489.7	495.0	498.3	502.9	510.5
22.5°	471.5	469.8	467.1	465.6	467.1	469.8	471.5	475.2	478.8	485.3	489.4
25°	444.9	442.2	439.6	441.3	439.6	442.2	444.9	446.9	453.4	456.4	462.4
27.5°	418.2	416.2	413.6	413.3	413.6	416.2	418.2	420.2	423.8	428.8	435.9
30°	401.3	399.3	398.0	396.4	398.0	399.3	401.3	402.9	406.7	411.9	417.2
32.5°	384.2	383.8	381.4	381.1	381.4	383.8	384.2	386.9	390.5	395.5	400.0
35°	361.8	359.8	359.1	359.5	359.1	359.8	361.8	363.1	366.4	371.0	375.3
37.5°	340.4	337.9	336.7	335.4	336.7	337.9	340.4	340.7	344.1	347.2	352.9
40°	325.2	322.5	321.8	321.2	321.8	322.5	325.2	324.9	328.5	330.8	336.0
42.5°	308.0	306.9	306.6	305.4	306.6	306.9	308.0	309.8	311.9	315.2	319.2
45°	284.6	284.3	282.3	282.9	282.3	284.3	284.6	285.6	289.2	291.5	295.2
47.5°	259.9	258.5	257.1	258.0	257.1	258.5	259.9	261.2	263.7	266.6	271.3
50°	243.1	242.4	239.4	240.0	239.4	242.4	243.1	244.4	246.0	249.6	253.9
52.5°	226.2	223.7	222.6	222.1	222.6	223.7	226.2	227.5	229.4	233.6	236.8
55°	198.2	195.2	193.9	193.2	193.9	195.2	198.2	200.5	203.1	207.8	211.0
57.5°	170.7	170.0	168.9	169.6	168.9	170.0	170.7	174.6	177.2	180.8	184.8
60°	154.6	154.6	154.6	154.4	154.6	154.6	154.6	158.0	160.2	163.9	168.2
62.5°	142.2	141.5	141.2	141.6	141.2	141.5	142.2	143.7	146.0	148.4	152.1
65°	123.3	123.0	121.7	121.4	121.7	123.0	123.3	124.3	126.3	127.9	130.6
67.5°	105.5	104.3	103.9	103.4	103.9	104.3	105.5	106.3	107.6	109.8	111.1
70°	92.0	91.4	89.4	89.7	89.4	91.4	92.0	93.7	95.0	97.6	98.9
72.5°	77.5	76.8	76.5	75.9	76.5	76.8	77.5	79.1	80.5	83.3	85.5
75°	61.3	61.0	60.7	62.0	60.7	61.0	61.3	61.6	62.0	63.0	64.0
77.5°	49.2	49.2	49.3	48.8	49.3	49.2	49.2	49.2	49.2	49.7	49.9
80°	41.2	41.2	40.9	40.9	40.9	41.2	41.2	41.2	41.2	41.2	40.9
82.5°	33.1	33.3	33.5	33.0	33.5	33.3	33.1	33.6	33.8	33.3	33.5
85°	21.8	21.4	22.1	21.8	22.1	21.4	21.8	21.8	21.1	21.8	21.4
87.5°	12.6	12.1	12.1	12.5	12.1	12.1	12.6	12.0	12.0	11.9	11.5
90°	14.1	14.3	14.6	14.7	14.6	14.3	14.1	13.9	13.5	13.1	12.7
92.5°	15.9	16.0	16.2	16.3	16.2	16.0	15.9	15.8	15.3	14.6	13.9
95°	18.7	18.7	18.7	18.7	18.7	18.7	18.7	18.7	18.3	17.5	16.8
97.5°	19.9	20.0	20.1	20.2	20.1	20.0	19.9	19.8	19.3	18.4	17.6
100°	20.3	20.4	20.5	20.7	20.5	20.4	20.3	20.1	19.7	18.9	17.9
102.5°	20.4	20.7	20.8	21.0	20.8	20.7	20.4	20.2	21.5	24.2	26.9
105°	20.9	21.2	21.4	21.6	21.4	21.2	20.9	20.8	30.3	49.6	68.9
107.5°	111.5	96.9	82.4	67.8	82.4	96.9	111.5	126.1	140.4	154.6	168.8
110°	181.8	166.3	150.7	135.0	150.7	166.3	181.8	197.4	207.1	210.7	214.3



TEST NUMBER: P332276-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	241.6	238.2	235.0	231.7	235.0	238.2	241.6	244.9	246.5	246.4	246.3
115°	287.4	287.9	288.3	288.8	288.3	287.9	287.4	287.0	286.3	285.2	284.0
117.5°	320.6	320.6	320.7	320.8	320.7	320.6	320.6	320.5	319.9	319.1	318.2
120°	342.8	342.8	342.8	342.8	342.8	342.8	342.8	342.8	342.3	341.5	340.6
122.5°	364.1	364.2	364.3	364.4	364.3	364.2	364.1	364.0	363.7	363.1	362.5
125°	394.2	394.4	394.6	394.9	394.6	394.4	394.2	394.0	393.7	393.5	393.3
127.5°	424.7	424.6	424.3	424.1	424.3	424.6	424.7	425.0	424.9	424.6	424.2
130°	443.6	443.4	443.2	443.0	443.2	443.4	443.6	443.8	443.7	443.2	442.8
132.5°	461.2	460.8	460.5	460.2	460.5	460.8	461.2	461.5	461.4	461.0	460.5
135°	487.7	487.3	487.0	486.6	487.0	487.3	487.7	487.9	487.9	487.7	487.3
137.5°	512.1	512.0	511.7	511.5	511.7	512.0	512.1	512.4	512.2	511.7	511.2
140°	527.1	526.8	526.7	526.4	526.7	526.8	527.1	527.3	527.2	526.8	526.3
142.5°	541.1	540.8	540.4	540.2	540.4	540.8	541.1	541.4	541.4	541.1	540.7
145°	561.3	561.3	561.3	561.3	561.3	561.3	561.3	561.3	561.2	560.9	560.8
147.5°	578.5	578.0	577.6	577.0	577.6	578.0	578.5	579.0	579.2	578.9	578.8
150°	589.8	589.4	589.1	588.8	589.1	589.4	589.8	590.1	590.1	590.0	589.7
152.5°	599.8	599.3	598.7	598.2	598.7	599.3	599.8	600.2	600.3	599.9	599.5
155°	613.4	612.7	612.1	611.4	612.1	612.7	613.4	614.0	614.1	613.5	612.9
157.5°	625.0	624.2	623.4	622.5	623.4	624.2	625.0	625.9	626.0	625.3	624.7
160°	631.9	631.1	630.3	629.6	630.3	631.1	631.9	632.6	632.7	632.0	631.4
162.5°	638.3	637.6	636.9	636.3	636.9	637.6	638.3	638.9	638.9	638.2	637.4
165°	646.6	645.8	645.1	644.3	645.1	645.8	646.6	647.4	647.3	646.4	645.6
167.5°	652.7	651.9	651.0	650.1	651.0	651.9	652.7	653.6	653.6	652.7	651.9
170°	656.3	655.4	654.5	653.6	654.5	655.4	656.3	657.1	657.1	656.3	655.4
172.5°	658.5	657.5	656.5	655.6	656.5	657.5	658.5	659.4	659.4	658.6	657.7
175°	661.2	660.3	659.4	658.5	659.4	660.3	661.2	662.0	662.1	661.3	660.6
177.5°	662.0	661.2	660.3	659.4	660.3	661.2	662.0	662.9	663.0	662.3	661.6
180°	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0



TEST NUMBER: P332276-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	735.3	739.0	742.7	746.1	751.4	753.7	757.2	758.5	762.4	768.3	773.0
5°	690.5	695.9	702.7	708.3	717.3	724.2	731.8	739.0	747.6	759.8	770.7
7.5°	652.6	657.8	666.2	676.6	686.4	696.2	706.6	716.4	728.8	746.2	763.5
10°	627.6	633.9	643.8	655.0	667.1	676.7	688.9	701.5	716.6	736.8	757.5
12.5°	606.0	610.6	622.1	632.7	646.5	658.8	670.7	685.4	702.7	724.1	749.1
15°	571.5	578.1	589.4	601.2	615.7	628.5	644.0	661.9	678.7	705.1	735.4
17.5°	536.9	547.0	558.6	572.0	582.8	600.5	617.3	635.6	656.3	684.3	717.6
20°	514.8	522.7	533.6	553.0	567.2	580.7	596.2	619.0	638.1	669.8	704.4
22.5°	496.0	501.9	514.0	530.1	546.6	562.2	578.1	599.8	623.4	653.4	691.0
25°	468.3	477.5	486.7	498.3	516.1	534.9	552.1	570.5	595.6	627.6	668.1
27.5°	441.2	449.5	458.7	472.9	486.4	503.9	521.9	543.0	569.9	603.7	644.9
30°	423.8	430.1	438.6	456.8	469.0	484.1	505.2	524.0	549.1	585.0	628.5
32.5°	405.8	414.0	423.3	437.2	452.3	466.7	485.9	506.4	531.9	567.3	611.9
35°	380.2	389.8	399.3	409.6	424.7	439.6	455.7	478.2	504.2	538.6	582.4
37.5°	356.7	364.4	372.2	384.9	399.2	413.4	428.4	450.6	475.1	512.1	552.3
40°	341.6	348.6	354.5	367.7	381.6	396.7	411.6	431.0	457.4	492.1	531.0
42.5°	325.3	331.7	339.8	350.5	365.5	378.2	393.1	411.5	436.3	471.5	505.6
45°	300.7	308.0	315.0	325.2	340.0	352.5	365.8	383.2	408.6	437.6	468.0
47.5°	275.3	282.5	290.4	300.3	313.2	326.0	339.1	354.6	377.8	406.3	426.7
50°	258.9	264.8	272.8	282.6	294.5	308.0	319.9	336.7	358.8	381.3	399.1
52.5°	242.0	247.4	256.4	266.8	277.8	289.6	302.2	316.7	336.7	357.7	371.9
55°	215.7	222.3	229.9	240.0	251.0	260.9	273.0	287.9	303.8	319.5	329.2
57.5°	191.1	196.6	202.9	213.5	222.9	234.7	245.6	257.3	271.9	283.8	290.1
60°	173.1	178.1	186.3	195.5	204.5	214.6	227.2	238.8	249.9	259.5	264.5
62.5°	156.3	162.0	169.2	177.6	187.4	197.0	207.9	217.7	227.6	235.8	239.2
65°	134.2	138.9	144.1	152.1	160.0	169.9	178.4	188.3	195.5	200.2	203.1
67.5°	114.2	117.2	121.2	126.5	134.3	142.9	151.3	158.9	165.1	168.2	170.8
70°	101.3	103.2	106.2	111.5	117.4	125.0	133.5	139.1	144.5	147.1	149.7
72.5°	88.3	90.8	93.5	97.7	102.6	108.1	114.3	121.2	124.2	127.3	128.9
75°	67.0	70.6	74.2	76.8	80.2	84.5	90.1	94.3	96.0	98.6	98.9
77.5°	50.5	51.3	54.0	57.3	60.0	63.1	66.6	70.5	71.3	72.7	73.5
80°	41.6	41.6	41.6	43.6	46.8	49.2	52.4	54.4	55.7	56.1	56.4
82.5°	33.4	33.4	33.1	33.5	34.7	35.9	39.0	41.2	42.3	42.1	41.3
85°	21.8	21.1	21.1	20.8	21.1	20.4	20.1	21.4	23.4	23.4	22.7
87.5°	11.5	11.0	11.0	10.5	10.0	9.4	8.4	8.4	8.2	9.0	8.5
90°	12.2	11.8	10.3	9.0	7.5	6.1	4.8	3.8	2.7	1.5	0.5
92.5°	13.3	12.6	11.5	10.4	9.4	8.3	7.9	8.2	8.5	8.9	9.1
95°	16.0	15.2	14.0	12.8	11.6	10.4	12.1	16.5	21.0	25.5	30.0
97.5°	16.7	15.8	23.7	31.5	39.3	47.3	52.2	54.2	56.2	58.2	60.2
100°	17.0	16.2	33.2	50.3	67.2	84.3	91.7	89.5	87.4	85.2	83.0
102.5°	29.6	32.3	50.9	69.5	88.1	106.7	115.2	113.7	112.1	110.5	108.9
105°	88.3	107.5	117.4	127.2	137.0	146.8	151.1	149.9	148.8	147.6	146.4
107.5°	183.0	197.1	195.5	194.0	192.4	190.9	189.7	188.7	187.8	186.8	185.8
110°	217.8	221.4	220.2	219.0	217.8	216.7	215.6	214.7	213.9	213.0	212.2



TEST NUMBER: P332276-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	246.3	246.2	245.0	243.8	242.6	241.4	240.4	239.6	238.8	238.1	237.3
115°	283.0	281.9	280.9	279.9	279.0	277.9	277.2	276.5	275.8	275.2	274.5
117.5°	317.4	316.4	316.0	315.5	315.0	314.4	313.7	313.0	312.2	311.3	310.6
120°	339.8	338.8	338.5	338.2	337.9	337.5	336.9	335.9	334.9	333.9	332.9
122.5°	361.9	361.3	360.8	360.4	360.0	359.6	359.0	358.2	357.3	356.5	355.8
125°	393.0	392.9	392.4	392.0	391.6	391.2	390.5	389.6	388.7	387.9	386.9
127.5°	423.9	423.5	423.0	422.5	421.9	421.4	420.7	419.8	419.0	418.1	417.2
130°	442.4	442.0	441.5	441.1	440.7	440.2	439.5	438.7	437.8	437.0	436.1
132.5°	460.1	459.7	459.3	458.9	458.6	458.2	457.6	456.8	455.9	455.0	454.2
135°	487.0	486.6	486.2	485.8	485.3	484.9	484.4	483.7	483.0	482.4	481.7
137.5°	510.7	510.1	509.9	509.6	509.4	509.2	508.6	507.8	507.0	506.2	505.3
140°	525.9	525.5	525.1	524.8	524.4	524.2	523.7	523.0	522.4	521.7	521.0
142.5°	540.4	540.0	539.7	539.3	539.0	538.6	538.2	537.5	536.9	536.2	535.5
145°	560.5	560.3	560.1	559.9	559.6	559.5	559.0	558.2	557.4	556.6	555.9
147.5°	578.5	578.3	578.1	577.8	577.6	577.4	577.0	576.5	576.1	575.6	575.1
150°	589.5	589.3	589.1	588.8	588.7	588.4	588.1	587.8	587.5	587.2	586.9
152.5°	599.1	598.7	598.6	598.5	598.3	598.2	598.1	597.9	597.7	597.6	597.4
155°	612.4	611.9	611.7	611.7	611.6	611.5	611.5	611.7	611.9	612.2	612.3
157.5°	624.1	623.4	623.5	623.6	623.7	623.8	623.9	623.9	623.9	624.0	624.0
160°	630.7	630.1	630.2	630.3	630.3	630.5	630.6	630.7	630.9	630.9	631.0
162.5°	636.7	635.9	636.0	636.2	636.3	636.4	636.5	636.9	637.1	637.4	637.7
165°	644.7	643.8	643.9	644.0	644.1	644.2	644.5	644.8	645.1	645.4	645.8
167.5°	651.0	650.1	650.1	650.1	650.1	650.1	650.3	650.7	651.2	651.6	652.0
170°	654.5	653.6	653.6	653.6	653.6	653.6	653.8	654.3	654.7	655.1	655.6
172.5°	656.9	656.0	655.9	655.8	655.7	655.7	655.8	656.3	656.9	657.5	658.0
175°	659.8	659.0	658.9	658.8	658.7	658.6	658.8	659.4	659.9	660.5	661.0
177.5°	660.9	660.2	660.1	660.0	660.0	659.9	660.0	660.5	660.9	661.3	661.8
180°	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0



TEST NUMBER: P332276-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	774.6	777.5	781.2	786.7	790.9	794.6	795.4	796.5	799.1	803.6	807.0
5°	779.6	787.2	799.4	811.2	824.1	834.7	844.6	851.5	858.1	871.9	883.1
7.5°	778.0	794.9	814.0	835.3	856.9	877.8	897.2	914.6	931.9	952.0	975.0
10°	777.0	796.8	822.4	849.8	879.9	909.2	937.5	959.7	985.4	1008.5	1037.8
12.5°	772.0	800.5	831.2	866.2	903.1	936.9	974.2	1004.8	1034.1	1067.6	1101.6
15°	765.4	800.0	839.0	885.5	941.5	982.4	1020.6	1073.8	1110.0	1146.3	1195.2
17.5°	753.5	795.7	844.4	904.7	951.6	1006.5	1064.0	1106.0	1154.9	1206.0	1250.2
20°	744.0	793.2	847.6	906.9	966.6	1026.3	1082.0	1132.1	1182.6	1241.6	1277.9
22.5°	734.5	783.1	839.6	902.7	966.8	1029.7	1092.8	1151.7	1208.4	1268.0	1314.3
25°	714.3	772.0	833.4	897.7	961.0	1030.2	1105.4	1171.0	1241.3	1302.6	1346.5
27.5°	693.9	746.7	807.8	873.1	943.4	1025.3	1113.7	1188.4	1258.7	1302.6	1316.4
30°	675.4	731.4	787.5	853.8	930.0	1021.3	1115.3	1200.8	1258.4	1277.6	1263.3
32.5°	656.7	707.5	763.0	830.9	911.8	1011.6	1117.4	1193.3	1228.1	1213.5	1155.7
35°	623.6	669.4	723.2	791.2	884.2	1006.2	1108.7	1160.2	1151.6	1069.1	960.3
37.5°	588.2	625.6	675.4	746.4	855.5	984.7	1071.3	1078.8	1004.6	878.0	752.3
40°	560.3	593.9	645.1	719.3	833.4	963.6	1033.5	1002.9	887.8	746.9	642.0
42.5°	533.1	561.5	610.7	690.8	812.3	934.9	977.3	910.5	777.7	644.5	549.2
45°	487.1	513.8	563.3	645.4	769.0	879.9	874.3	758.2	625.3	518.1	438.9
47.5°	443.4	466.7	513.2	597.0	718.3	797.4	744.9	621.5	508.7	422.8	366.3
50°	412.6	435.7	481.8	564.6	677.7	735.4	660.6	541.5	438.2	367.0	322.2
52.5°	383.0	405.5	447.8	528.4	628.6	663.1	582.7	472.3	386.3	324.9	286.3
55°	341.6	358.8	396.7	473.9	548.7	556.6	475.2	382.9	311.9	269.1	242.7
57.5°	299.5	314.3	351.7	413.2	465.7	461.6	384.4	304.5	256.8	224.9	205.8
60°	272.1	286.5	319.5	372.3	411.9	398.0	327.2	262.9	222.0	198.5	183.4
62.5°	246.5	257.8	288.7	327.2	355.7	340.0	279.7	226.4	194.0	174.3	162.2
65°	209.4	218.6	243.4	263.5	279.3	264.2	214.0	177.1	153.7	139.8	131.6
67.5°	174.2	180.0	195.7	202.9	214.1	197.5	160.9	136.2	122.9	111.2	105.5
70°	152.1	156.4	164.5	170.5	173.5	156.4	129.2	111.2	100.0	91.7	88.1
72.5°	129.8	133.6	135.3	140.2	138.6	122.5	103.9	89.5	81.5	75.9	71.2
75°	99.3	100.9	99.3	97.3	93.0	81.8	69.0	61.6	55.7	53.1	51.5
77.5°	72.3	71.8	69.6	66.5	59.2	52.1	45.2	42.7	40.2	38.7	38.2
80°	55.7	54.4	52.4	47.5	41.2	36.2	34.6	33.0	32.0	30.3	30.0
82.5°	41.5	40.7	37.4	33.2	28.8	26.5	25.1	24.5	23.5	22.7	22.6
85°	22.1	21.1	17.5	15.2	14.6	13.9	13.5	13.5	12.2	11.9	11.9
87.5°	7.4	6.1	6.0	5.4	5.7	5.4	6.0	5.8	5.8	6.1	5.7
90°	1.5	2.7	3.8	4.8	6.1	7.5	9.0	10.3	11.8	12.2	12.7
92.5°	8.9	8.5	8.2	7.9	8.3	9.4	10.4	11.5	12.6	13.3	13.9
95°	25.5	21.0	16.5	12.1	10.4	11.6	12.8	14.0	15.2	16.0	16.8
97.5°	58.2	56.2	54.2	52.2	47.3	39.3	31.5	23.7	15.8	16.7	17.6
100°	85.2	87.4	89.5	91.7	84.3	67.2	50.3	33.2	16.2	17.0	17.9
102.5°	110.5	112.1	113.7	115.2	106.7	88.1	69.5	50.9	32.3	29.6	26.9
105°	147.6	148.8	149.9	151.1	146.8	137.0	127.2	117.4	107.5	88.3	68.9
107.5°	186.8	187.8	188.7	189.7	190.9	192.4	194.0	195.5	197.1	183.0	168.8
110°	213.0	213.9	214.7	215.6	216.7	217.8	219.0	220.2	221.4	217.8	214.3



TEST NUMBER: P332276-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	238.1	238.8	239.6	240.4	241.4	242.6	243.8	245.0	246.2	246.3	246.3
115°	275.2	275.8	276.5	277.2	277.9	279.0	279.9	280.9	281.9	283.0	284.0
117.5°	311.3	312.2	313.0	313.7	314.4	315.0	315.5	316.0	316.4	317.4	318.2
120°	333.9	334.9	335.9	336.9	337.5	337.9	338.2	338.5	338.8	339.8	340.6
122.5°	356.5	357.3	358.2	359.0	359.6	360.0	360.4	360.8	361.3	361.9	362.5
125°	387.9	388.7	389.6	390.5	391.2	391.6	392.0	392.4	392.9	393.0	393.3
127.5°	418.1	419.0	419.8	420.7	421.4	421.9	422.5	423.0	423.5	423.9	424.2
130°	437.0	437.8	438.7	439.5	440.2	440.7	441.1	441.5	442.0	442.4	442.8
132.5°	455.0	455.9	456.8	457.6	458.2	458.6	458.9	459.3	459.7	460.1	460.5
135°	482.4	483.0	483.7	484.4	484.9	485.3	485.8	486.2	486.6	487.0	487.3
137.5°	506.2	507.0	507.8	508.6	509.2	509.4	509.6	509.9	510.1	510.7	511.2
140°	521.7	522.4	523.0	523.7	524.2	524.4	524.8	525.1	525.5	525.9	526.3
142.5°	536.2	536.9	537.5	538.2	538.6	539.0	539.3	539.7	540.0	540.4	540.7
145°	556.6	557.4	558.2	559.0	559.5	559.6	559.9	560.1	560.3	560.5	560.8
147.5°	575.6	576.1	576.5	577.0	577.4	577.6	577.8	578.1	578.3	578.5	578.8
150°	587.2	587.5	587.8	588.1	588.4	588.7	588.8	589.1	589.3	589.5	589.7
152.5°	597.6	597.7	597.9	598.1	598.2	598.3	598.5	598.6	598.7	599.1	599.5
155°	612.2	611.9	611.7	611.5	611.5	611.6	611.7	611.7	611.9	612.4	612.9
157.5°	624.0	623.9	623.9	623.9	623.8	623.7	623.6	623.5	623.4	624.1	624.7
160°	630.9	630.9	630.7	630.6	630.5	630.3	630.3	630.2	630.1	630.7	631.4
162.5°	637.4	637.1	636.9	636.5	636.4	636.3	636.2	636.0	635.9	636.7	637.4
165°	645.4	645.1	644.8	644.5	644.2	644.1	644.0	643.9	643.8	644.7	645.6
167.5°	651.6	651.2	650.7	650.3	650.1	650.1	650.1	650.1	650.1	651.0	651.9
170°	655.1	654.7	654.3	653.8	653.6	653.6	653.6	653.6	653.6	654.5	655.4
172.5°	657.5	656.9	656.3	655.8	655.7	655.7	655.8	655.9	656.0	656.9	657.7
175°	660.5	659.9	659.4	658.8	658.6	658.7	658.8	658.9	659.0	659.8	660.6
177.5°	661.3	660.9	660.5	660.0	659.9	660.0	660.0	660.1	660.2	660.9	661.6
180°	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0



TEST NUMBER: P332276-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	812.6	812.6	813.6	817.6	818.1	821.6	820.4
5°	893.0	899.3	901.6	911.5	917.5	920.1	914.8
7.5°	991.4	1009.1	1017.5	1027.9	1037.0	1039.8	1032.6
10°	1063.2	1081.7	1097.2	1106.7	1115.7	1121.5	1129.2
12.5°	1132.6	1155.3	1170.0	1183.5	1192.7	1200.2	1201.4
15°	1208.0	1242.3	1268.3	1287.5	1297.0	1302.0	1300.0
17.5°	1284.0	1315.8	1334.4	1353.8	1367.1	1367.8	1368.2
20°	1327.1	1358.1	1379.5	1394.0	1408.9	1408.2	1411.4
22.5°	1355.8	1380.2	1396.6	1407.1	1412.2	1409.7	1410.4
25°	1369.2	1376.5	1373.6	1356.7	1352.5	1337.0	1339.5
27.5°	1299.9	1265.6	1230.1	1184.4	1148.4	1119.6	1121.1
30°	1205.7	1145.0	1075.7	1017.7	965.6	951.1	920.1
32.5°	1074.0	983.0	901.9	847.8	803.1	790.9	763.9
35°	850.8	762.4	679.0	628.9	609.1	581.4	581.1
37.5°	661.3	583.5	539.4	501.8	482.1	465.3	463.6
40°	556.4	495.7	462.4	435.3	415.9	403.3	400.4
42.5°	483.0	433.9	402.7	386.0	371.0	364.5	359.7
45°	394.4	361.4	339.7	324.5	317.5	312.6	310.0
47.5°	329.9	307.8	293.0	282.9	277.2	272.1	273.5
50°	294.8	276.7	265.8	256.2	251.9	248.3	248.7
52.5°	266.6	250.3	241.5	234.6	229.3	226.7	225.4
55°	226.3	216.0	207.1	202.2	199.1	195.5	194.6
57.5°	193.0	185.0	177.8	172.2	171.5	168.0	168.4
60°	170.8	164.2	158.3	155.3	153.0	150.1	151.0
62.5°	152.7	147.1	141.6	139.2	136.9	134.7	135.2
65°	125.0	119.7	116.4	115.1	114.1	113.1	112.1
67.5°	99.6	96.3	94.3	91.4	89.5	89.1	88.1
70°	83.8	79.5	75.9	72.2	71.2	70.9	71.2
72.5°	67.2	64.4	63.5	61.6	61.5	60.6	61.2
75°	50.5	49.5	48.8	47.5	47.5	47.5	47.5
77.5°	37.2	36.6	36.2	35.9	35.6	35.1	35.1
80°	29.0	28.7	28.1	28.1	27.7	28.1	27.7
82.5°	21.9	21.9	21.2	21.2	20.8	20.7	20.8
85°	11.2	10.8	11.5	10.8	11.2	10.6	11.2
87.5°	5.8	5.9	5.7	5.7	5.5	6.0	5.6
90°	13.1	13.5	13.9	14.1	14.3	14.6	14.7
92.5°	14.6	15.3	15.8	15.9	16.0	16.2	16.3
95°	17.5	18.3	18.7	18.7	18.7	18.7	18.7
97.5°	18.4	19.3	19.8	19.9	20.0	20.1	20.2
100°	18.9	19.7	20.1	20.3	20.4	20.5	20.7
102.5°	24.2	21.5	20.2	20.4	20.7	20.8	21.0
105°	49.6	30.3	20.8	20.9	21.2	21.4	21.6
107.5°	154.6	140.4	126.1	111.5	96.9	82.4	67.8
110°	210.7	207.1	197.4	181.8	166.3	150.7	135.0



TEST NUMBER: P332276-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	246.4	246.5	244.9	241.6	238.2	235.0	231.7
115°	285.2	286.3	287.0	287.4	287.9	288.3	288.8
117.5°	319.1	319.9	320.5	320.6	320.6	320.7	320.8
120°	341.5	342.3	342.8	342.8	342.8	342.8	342.8
122.5°	363.1	363.7	364.0	364.1	364.2	364.3	364.4
125°	393.5	393.7	394.0	394.2	394.4	394.6	394.9
127.5°	424.6	424.9	425.0	424.7	424.6	424.3	424.1
130°	443.2	443.7	443.8	443.6	443.4	443.2	443.0
132.5°	461.0	461.4	461.5	461.2	460.8	460.5	460.2
135°	487.7	487.9	487.9	487.7	487.3	487.0	486.6
137.5°	511.7	512.2	512.4	512.1	512.0	511.7	511.5
140°	526.8	527.2	527.3	527.1	526.8	526.7	526.4
142.5°	541.1	541.4	541.4	541.1	540.8	540.4	540.2
145°	560.9	561.2	561.3	561.3	561.3	561.3	561.3
147.5°	578.9	579.2	579.0	578.5	578.0	577.6	577.0
150°	590.0	590.1	590.1	589.8	589.4	589.1	588.8
152.5°	599.9	600.3	600.2	599.8	599.3	598.7	598.2
155°	613.5	614.1	614.0	613.4	612.7	612.1	611.4
157.5°	625.3	626.0	625.9	625.0	624.2	623.4	622.5
160°	632.0	632.7	632.6	631.9	631.1	630.3	629.6
162.5°	638.2	638.9	638.9	638.3	637.6	636.9	636.3
165°	646.4	647.3	647.4	646.6	645.8	645.1	644.3
167.5°	652.7	653.6	653.6	652.7	651.9	651.0	650.1
170°	656.3	657.1	657.1	656.3	655.4	654.5	653.6
172.5°	658.6	659.4	659.4	658.5	657.5	656.5	655.6
175°	661.3	662.1	662.0	661.2	660.3	659.4	658.5
177.5°	662.3	663.0	662.9	662.0	661.2	660.3	659.4
180°	661.0	661.0	661.0	661.0	661.0	661.0	661.0

(END OF REPORT)