

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332278-935

Luminaire Tested: **S123RDIP-S560D585U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332278-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S560D585U935-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3745.1 lumens  
Efficiency: N/A  
Efficacy: 114.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 32.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332278-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332278-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	99	95	91	88	91	88	84	82	75	72	70	63	61	60	52	51	50	44
2	90	83	77	73	83	77	72	68	66	62	59	56	53	51	46	44	43	38
3	83	74	67	61	76	69	62	57	59	54	50	50	46	44	41	39	37	33
4	76	66	58	52	70	61	54	49	53	47	43	45	41	38	37	35	32	29
5	70	59	51	45	65	55	48	43	47	42	38	40	36	33	34	31	29	25
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	31	28	25	23
7	60	48	40	35	55	45	38	33	39	34	30	34	29	26	28	25	23	20
8	56	44	36	31	51	41	34	29	36	30	26	31	27	23	26	23	21	18
9	52	40	33	28	48	37	31	26	33	27	24	28	24	21	24	21	19	17
10	49	37	30	25	45	34	28	24	30	25	21	26	22	19	23	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8291	8291	8291	8291
5°	9884	8327	7333	8327
10°	12342	8279	6625	8279
15°	14487	8195	6042	8195
20°	16167	8069	5545	8069
25°	15909	7935	5241	7935
30°	11436	7812	4927	7812
35°	7636	7653	4724	7653
40°	5626	7461	4513	7461
45°	4719	7124	4306	7124
50°	4165	6683	4019	6683
55°	3652	6178	3626	6178
60°	3251	5694	3324	5694
65°	2855	5173	3092	5173
70°	2241	4711	2823	4711
75°	1975	4113	2578	4113
80°	1717	3496	2535	3496
85°	1383	2803	2692	2803



TEST NUMBER: P332278-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	75.8	2.0
10°-20°	236.7	6.3
20°-30°	371.8	9.9
30°-40°	387.9	10.4
40°-50°	332.0	8.9
50°-60°	253.0	6.8
60°-70°	162.2	4.3
70°-80°	78.0	2.1
80°-90°	22.5	0.6
90°-100°	135.0	3.6
100°-110°	382.3	10.2
110°-120°	376.1	10.0
120°-130°	300.0	8.0
130°-140°	236.5	6.3
140°-150°	176.5	4.7
150°-160°	123.0	3.3
160°-170°	72.3	1.9
170°-180°	23.5	0.6
0°-30°	684.3	18.3
0°-40°	1072.2	28.6
0°-60°	1657.2	44.2
0°-90°	1920.0	51.3
90°-120°	893.4	23.9
90°-150°	1606.4	42.9
90°-180°	1825.0	48.7
0°-180°	3745.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	770	770	770	770	770	
5°	915	771	679	771	915	94
15°	1300	735	542	735	1300	369
25°	1340	668	441	668	1340	576
35°	581	582	360	582	581	381
45°	310	468	283	468	310	244
55°	195	329	193	329	195	176
65°	112	203	121	203	112	110
75°	48	99	62	99	48	51
85°	11	23	22	23	11	13
90°	14	1	14	1	14	8
95°	57	17	57	17	57	103
105°	625	57	625	57	625	616
115°	760	101	760	101	760	738
125°	599	140	599	140	599	543
135°	486	164	486	164	486	377
145°	380	187	380	187	380	241
155°	315	213	315	213	315	147
165°	274	232	274	232	274	78
175°	247	242	247	242	247	24
180°	243	243	243	243	243	



TEST NUMBER: P332278-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	820.4	821.6	818.1	817.6	813.6	812.6	812.6	807.0	803.6	799.1	796.5
5°	914.8	920.1	917.5	911.5	901.6	899.3	893.0	883.1	871.9	858.1	851.5
7.5°	1032.6	1039.8	1037.0	1027.9	1017.5	1009.1	991.4	975.0	952.0	931.9	914.6
10°	1129.2	1121.5	1115.7	1106.7	1097.2	1081.7	1063.2	1037.8	1008.5	985.4	959.7
12.5°	1201.4	1200.2	1192.7	1183.5	1170.0	1155.3	1132.6	1101.6	1067.6	1034.1	1004.8
15°	1300.0	1302.0	1297.0	1287.5	1268.3	1242.3	1208.0	1195.2	1146.3	1110.0	1073.8
17.5°	1368.2	1367.8	1367.1	1353.8	1334.4	1315.8	1284.0	1250.2	1206.0	1154.9	1106.0
20°	1411.4	1408.2	1408.9	1394.0	1379.5	1358.1	1327.1	1277.9	1241.6	1182.6	1132.1
22.5°	1410.4	1409.7	1412.2	1407.1	1396.6	1380.2	1355.8	1314.3	1268.0	1208.4	1151.7
25°	1339.5	1337.0	1352.5	1356.7	1373.6	1376.5	1369.2	1346.5	1302.6	1241.3	1171.0
27.5°	1121.1	1119.6	1148.4	1184.4	1230.1	1265.6	1299.9	1316.4	1302.6	1258.7	1188.4
30°	920.1	951.1	965.6	1017.7	1075.7	1145.0	1205.7	1263.3	1277.6	1258.4	1200.8
32.5°	763.9	790.9	803.1	847.8	901.9	983.0	1074.0	1155.7	1213.5	1228.1	1193.3
35°	581.1	581.4	609.1	628.9	679.0	762.4	850.8	960.3	1069.1	1151.6	1160.2
37.5°	463.6	465.3	482.1	501.8	539.4	583.5	661.3	752.3	878.0	1004.6	1078.8
40°	400.4	403.3	415.9	435.3	462.4	495.7	556.4	642.0	746.9	887.8	1002.9
42.5°	359.7	364.5	371.0	386.0	402.7	433.9	483.0	549.2	644.5	777.7	910.5
45°	310.0	312.6	317.5	324.5	339.7	361.4	394.4	438.9	518.1	625.3	758.2
47.5°	273.5	272.1	277.2	282.9	293.0	307.8	329.9	366.3	422.8	508.7	621.5
50°	248.7	248.3	251.9	256.2	265.8	276.7	294.8	322.2	367.0	438.2	541.5
52.5°	225.4	226.7	229.3	234.6	241.5	250.3	266.6	286.3	324.9	386.3	472.3
55°	194.6	195.5	199.1	202.2	207.1	216.0	226.3	242.7	269.1	311.9	382.9
57.5°	168.4	168.0	171.5	172.2	177.8	185.0	193.0	205.8	224.9	256.8	304.5
60°	151.0	150.1	153.0	155.3	158.3	164.2	170.8	183.4	198.5	222.0	262.9
62.5°	135.2	134.7	136.9	139.2	141.6	147.1	152.7	162.2	174.3	194.0	226.4
65°	112.1	113.1	114.1	115.1	116.4	119.7	125.0	131.6	139.8	153.7	177.1
67.5°	88.1	89.1	89.5	91.4	94.3	96.3	99.6	105.5	111.2	122.9	136.2
70°	71.2	70.9	71.2	72.2	75.9	79.5	83.8	88.1	91.7	100.0	111.2
72.5°	61.2	60.6	61.5	61.6	63.5	64.4	67.2	71.2	75.9	81.5	89.5
75°	47.5	47.5	47.5	47.5	48.8	49.5	50.5	51.5	53.1	55.7	61.6
77.5°	35.1	35.1	35.6	35.9	36.2	36.6	37.2	38.2	38.7	40.2	42.7
80°	27.7	28.1	27.7	28.1	28.1	28.7	29.0	30.0	30.3	32.0	33.0
82.5°	20.8	20.7	20.8	21.2	21.2	21.9	21.9	22.6	22.7	23.5	24.5
85°	11.2	10.6	11.2	10.8	11.5	10.8	11.2	11.9	11.9	12.2	13.5
87.5°	5.5	6.1	5.5	5.7	5.8	5.9	5.7	5.6	6.0	5.9	5.9
90°	14.2	14.7	14.2	13.8	14.2	13.3	12.7	12.3	11.8	12.3	10.8
92.5°	23.7	24.5	24.0	25.6	26.4	29.0	32.8	41.3	57.0	75.5	83.1
95°	57.0	58.9	62.3	66.8	76.1	93.8	119.9	176.8	236.2	291.2	259.3
97.5°	155.1	159.3	172.5	194.7	230.9	289.6	353.0	440.7	482.8	451.3	330.4
100°	307.9	307.5	326.6	362.4	412.0	481.7	539.2	579.0	561.8	465.0	314.3
102.5°	451.7	463.0	479.0	507.4	546.0	590.2	623.7	625.0	565.8	439.5	290.8
105°	624.7	627.2	642.8	661.5	684.1	696.9	687.5	638.4	535.8	394.9	261.7
107.5°	724.3	728.8	734.1	740.4	739.9	722.5	679.5	599.7	483.4	355.3	243.3
110°	765.1	766.1	767.1	763.2	749.4	715.1	653.2	562.7	450.3	332.9	236.2



TEST NUMBER: P332278-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	773.4	773.2	769.5	757.2	732.1	687.9	618.5	526.2	421.6	318.1	232.3
115°	759.7	757.2	747.4	725.8	689.0	635.5	563.3	477.9	387.0	302.0	230.8
117.5°	716.3	713.0	698.8	674.1	635.7	581.3	516.5	442.7	366.1	292.6	231.7
120°	680.2	677.2	665.5	637.9	599.2	549.5	490.6	424.3	355.1	288.3	233.2
122.5°	646.4	642.7	629.6	604.9	570.4	524.3	469.8	409.7	346.0	285.5	236.0
125°	599.2	595.7	583.4	561.8	530.4	491.1	443.9	390.4	334.4	281.9	240.1
127.5°	560.3	557.1	546.0	527.5	499.6	463.8	421.3	373.5	324.3	280.1	244.9
130°	538.2	534.3	524.0	506.4	480.3	446.9	407.1	362.9	318.7	279.0	248.0
132.5°	516.6	513.8	504.7	487.1	462.6	430.8	393.7	353.1	313.6	278.5	250.4
135°	485.7	482.2	473.4	458.7	434.6	406.7	374.7	339.8	306.9	277.9	253.9
137.5°	453.0	450.7	443.2	428.3	408.1	383.8	356.4	327.8	301.2	276.9	256.2
140°	430.2	430.7	422.8	409.1	390.4	369.3	345.7	320.7	297.6	276.5	257.8
142.5°	409.0	409.5	402.4	390.2	374.3	355.9	335.5	314.0	294.5	275.7	259.0
145°	379.6	378.7	374.7	364.4	352.1	337.9	322.2	305.9	290.2	274.5	259.8
147.5°	355.4	355.1	351.3	344.3	335.0	324.9	312.2	299.4	286.1	272.7	259.8
150°	341.3	341.3	338.4	332.9	325.6	316.2	305.9	294.6	283.4	271.0	259.8
152.5°	329.5	329.5	327.8	322.7	316.9	309.2	300.1	290.3	280.3	269.1	258.6
155°	314.8	314.3	313.3	309.4	305.0	299.1	291.7	283.9	275.5	265.7	257.4
157.5°	301.4	301.4	300.7	297.7	293.9	289.3	283.5	277.0	270.2	262.6	255.6
160°	292.7	293.2	293.2	290.2	286.8	283.4	278.4	273.0	266.7	260.3	254.9
162.5°	284.8	285.3	285.3	282.8	280.5	277.5	272.9	268.4	263.1	258.0	253.3
165°	274.5	274.5	275.0	273.0	271.0	268.6	265.2	262.3	258.3	254.4	251.0
167.5°	264.7	264.7	265.2	263.8	262.9	261.1	259.2	256.9	253.7	250.8	248.6
170°	258.8	258.8	259.3	258.3	257.8	256.8	254.9	253.4	251.0	248.5	247.0
172.5°	253.3	253.7	254.6	253.6	253.5	252.9	251.3	250.3	248.2	246.5	245.8
175°	247.0	247.5	248.0	247.5	247.5	247.5	246.5	246.1	245.0	244.1	244.1
177.5°	243.4	243.4	244.2	243.7	244.2	244.2	243.7	243.4	243.0	242.6	243.0
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P332278-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	795.4	794.6	790.9	786.7	781.2	777.5	774.6	773.0	768.3	762.4	758.5
5°	844.6	834.7	824.1	811.2	799.4	787.2	779.6	770.7	759.8	747.6	739.0
7.5°	897.2	877.8	856.9	835.3	814.0	794.9	778.0	763.5	746.2	728.8	716.4
10°	937.5	909.2	879.9	849.8	822.4	796.8	777.0	757.5	736.8	716.6	701.5
12.5°	974.2	936.9	903.1	866.2	831.2	800.5	772.0	749.1	724.1	702.7	685.4
15°	1020.6	982.4	941.5	885.5	839.0	800.0	765.4	735.4	705.1	678.7	661.9
17.5°	1064.0	1006.5	951.6	904.7	844.4	795.7	753.5	717.6	684.3	656.3	635.6
20°	1082.0	1026.3	966.6	906.9	847.6	793.2	744.0	704.4	669.8	638.1	619.0
22.5°	1092.8	1029.7	966.8	902.7	839.6	783.1	734.5	691.0	653.4	623.4	599.8
25°	1105.4	1030.2	961.0	897.7	833.4	772.0	714.3	668.1	627.6	595.6	570.5
27.5°	1113.7	1025.3	943.4	873.1	807.8	746.7	693.9	644.9	603.7	569.9	543.0
30°	1115.3	1021.3	930.0	853.8	787.5	731.4	675.4	628.5	585.0	549.1	524.0
32.5°	1117.4	1011.6	911.8	830.9	763.0	707.5	656.7	611.9	567.3	531.9	506.4
35°	1108.7	1006.2	884.2	791.2	723.2	669.4	623.6	582.4	538.6	504.2	478.2
37.5°	1071.3	984.7	855.5	746.4	675.4	625.6	588.2	552.3	512.1	475.1	450.6
40°	1033.5	963.6	833.4	719.3	645.1	593.9	560.3	531.0	492.1	457.4	431.0
42.5°	977.3	934.9	812.3	690.8	610.7	561.5	533.1	505.6	471.5	436.3	411.5
45°	874.3	879.9	769.0	645.4	563.3	513.8	487.1	468.0	437.6	408.6	383.2
47.5°	744.9	797.4	718.3	597.0	513.2	466.7	443.4	426.7	406.3	377.8	354.6
50°	660.6	735.4	677.7	564.6	481.8	435.7	412.6	399.1	381.3	358.8	336.7
52.5°	582.7	663.1	628.6	528.4	447.8	405.5	383.0	371.9	357.7	336.7	316.7
55°	475.2	556.6	548.7	473.9	396.7	358.8	341.6	329.2	319.5	303.8	287.9
57.5°	384.4	461.6	465.7	413.2	351.7	314.3	299.5	290.1	283.8	271.9	257.3
60°	327.2	398.0	411.9	372.3	319.5	286.5	272.1	264.5	259.5	249.9	238.8
62.5°	279.7	340.0	355.7	327.2	288.7	257.8	246.5	239.2	235.8	227.6	217.7
65°	214.0	264.2	279.3	263.5	243.4	218.6	209.4	203.1	200.2	195.5	188.3
67.5°	160.9	197.5	214.1	202.9	195.7	180.0	174.2	170.8	168.2	165.1	158.9
70°	129.2	156.4	173.5	170.5	164.5	156.4	152.1	149.7	147.1	144.5	139.1
72.5°	103.9	122.5	138.6	140.2	135.3	133.6	129.8	128.9	127.3	124.2	121.2
75°	69.0	81.8	93.0	97.3	99.3	100.9	99.3	98.9	98.6	96.0	94.3
77.5°	45.2	52.1	59.2	66.5	69.6	71.8	72.3	73.5	72.7	71.3	70.5
80°	34.6	36.2	41.2	47.5	52.4	54.4	55.7	56.4	56.1	55.7	54.4
82.5°	25.1	26.5	28.8	33.2	37.4	40.7	41.5	41.3	42.1	42.3	41.2
85°	13.5	13.9	14.6	15.2	17.5	21.1	22.1	22.7	23.4	23.4	21.4
87.5°	6.1	5.5	5.8	5.6	6.2	6.1	7.5	8.6	9.1	8.3	8.5
90°	9.3	7.8	6.4	5.4	4.4	2.9	2.0	0.9	2.0	2.9	4.4
92.5°	62.3	41.2	28.4	21.1	17.0	13.2	9.0	6.1	9.0	13.2	17.0
95°	178.7	105.6	63.8	44.7	31.9	23.6	18.2	16.7	18.2	23.6	31.9
97.5°	196.1	113.7	73.8	53.0	40.5	33.2	29.0	28.5	29.0	33.2	40.5
100°	185.1	112.4	78.1	58.9	47.2	40.3	36.9	36.3	36.9	40.3	47.2
102.5°	175.7	114.0	83.2	65.6	55.0	48.6	45.5	44.6	45.5	48.6	55.0
105°	168.9	118.4	91.9	76.6	67.2	61.4	58.5	57.0	58.5	61.4	67.2
107.5°	168.4	126.4	103.1	89.0	80.2	74.5	71.6	70.1	71.6	74.5	80.2
110°	170.4	133.1	111.0	97.2	88.9	83.5	81.0	79.6	81.0	83.5	88.9





TEST NUMBER: P332278-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	174.4	139.7	119.2	105.9	97.6	92.1	89.7	88.2	89.7	92.1	97.6
115°	180.7	150.8	132.1	118.8	110.5	105.6	102.6	100.7	102.6	105.6	110.5
117.5°	189.2	162.5	144.0	131.7	122.3	117.9	115.4	113.1	115.4	117.9	122.3
120°	195.4	169.9	152.2	140.0	130.6	125.7	123.3	121.8	123.3	125.7	130.6
122.5°	201.4	177.8	160.5	147.4	138.4	133.2	130.7	129.2	130.7	133.2	138.4
125°	210.7	189.1	171.9	158.6	149.3	143.9	140.9	140.0	140.9	143.9	149.3
127.5°	218.3	198.9	182.3	169.0	158.7	153.3	149.6	148.1	149.6	153.3	158.7
130°	223.4	204.7	188.6	175.3	165.0	159.1	154.7	153.3	154.7	159.1	165.0
132.5°	228.2	209.9	194.1	181.2	170.9	163.8	159.0	157.1	159.0	163.8	170.9
135°	234.3	217.6	202.3	189.1	178.7	171.4	166.0	164.0	166.0	171.4	178.7
137.5°	238.8	222.8	208.2	196.0	185.7	177.9	172.5	170.5	172.5	177.9	185.7
140°	241.2	226.4	212.2	199.8	190.0	182.2	177.3	174.9	177.3	182.2	190.0
142.5°	243.5	229.1	215.3	203.8	194.0	186.9	181.6	179.5	181.6	186.9	194.0
145°	246.1	232.8	220.0	208.7	200.4	193.0	188.6	187.1	188.6	193.0	200.4
147.5°	247.6	235.7	224.0	214.4	206.4	200.0	195.6	194.8	195.6	200.0	206.4
150°	248.0	237.7	226.4	217.6	210.7	204.3	200.4	199.8	200.4	204.3	210.7
152.5°	248.8	238.8	229.1	220.7	214.6	209.1	205.1	205.0	205.1	209.1	214.6
155°	249.0	241.2	232.8	225.9	220.5	215.6	212.7	212.7	212.7	215.6	220.5
157.5°	249.5	242.4	235.7	230.4	225.8	221.4	219.1	218.7	219.1	221.4	225.8
160°	249.5	243.6	237.7	232.8	229.4	225.4	223.4	223.4	223.4	225.4	229.4
162.5°	249.1	244.0	238.8	234.7	231.7	228.6	227.0	227.0	227.0	228.6	231.7
165°	248.0	244.5	240.6	237.2	235.2	232.8	231.8	232.3	231.8	232.8	235.2
167.5°	247.2	244.4	241.6	239.4	238.1	236.2	235.7	236.3	235.7	236.2	238.1
170°	246.1	244.1	241.6	240.6	239.6	238.2	237.7	238.7	237.7	238.2	239.6
172.5°	245.6	244.1	242.0	241.4	240.8	239.8	239.6	240.2	239.6	239.8	240.8
175°	244.5	243.6	242.6	242.1	242.1	241.2	241.6	242.1	241.6	241.2	242.1
177.5°	243.7	243.0	242.6	242.6	242.6	242.2	242.6	243.0	242.6	242.2	242.6
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P332278-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	757.2	753.7	751.4	746.1	742.7	739.0	735.3	737.6	737.4	737.1	737.1
5°	731.8	724.2	717.3	708.3	702.7	695.9	690.5	689.9	691.2	686.6	684.0
7.5°	706.6	696.2	686.4	676.6	666.2	657.8	652.6	650.2	646.9	644.0	641.0
10°	688.9	676.7	667.1	655.0	643.8	633.9	627.6	623.3	621.0	618.6	614.4
12.5°	670.7	658.8	646.5	632.7	622.1	610.6	606.0	601.2	596.7	594.1	588.2
15°	644.0	628.5	615.7	601.2	589.4	578.1	571.5	562.0	560.6	557.3	551.4
17.5°	617.3	600.5	582.8	572.0	558.6	547.0	536.9	533.7	524.3	520.7	515.6
20°	596.2	580.7	567.2	553.0	533.6	522.7	514.8	510.5	502.9	498.3	495.0
22.5°	578.1	562.2	546.6	530.1	514.0	501.9	496.0	489.4	485.3	478.8	475.2
25°	552.1	534.9	516.1	498.3	486.7	477.5	468.3	462.4	456.4	453.4	446.9
27.5°	521.9	503.9	486.4	472.9	458.7	449.5	441.2	435.9	428.8	423.8	420.2
30°	505.2	484.1	469.0	456.8	438.6	430.1	423.8	417.2	411.9	406.7	402.9
32.5°	485.9	466.7	452.3	437.2	423.3	414.0	405.8	400.0	395.5	390.5	386.9
35°	455.7	439.6	424.7	409.6	399.3	389.8	380.2	375.3	371.0	366.4	363.1
37.5°	428.4	413.4	399.2	384.9	372.2	364.4	356.7	352.9	347.2	344.1	340.7
40°	411.6	396.7	381.6	367.7	354.5	348.6	341.6	336.0	330.8	328.5	324.9
42.5°	393.1	378.2	365.5	350.5	339.8	331.7	325.3	319.2	315.2	311.9	309.8
45°	365.8	352.5	340.0	325.2	315.0	308.0	300.7	295.2	291.5	289.2	285.6
47.5°	339.1	326.0	313.2	300.3	290.4	282.5	275.3	271.3	266.6	263.7	261.2
50°	319.9	308.0	294.5	282.6	272.8	264.8	258.9	253.9	249.6	246.0	244.4
52.5°	302.2	289.6	277.8	266.8	256.4	247.4	242.0	236.8	233.6	229.4	227.5
55°	273.0	260.9	251.0	240.0	229.9	222.3	215.7	211.0	207.8	203.1	200.5
57.5°	245.6	234.7	222.9	213.5	202.9	196.6	191.1	184.8	180.8	177.2	174.6
60°	227.2	214.6	204.5	195.5	186.3	178.1	173.1	168.2	163.9	160.2	158.0
62.5°	207.9	197.0	187.4	177.6	169.2	162.0	156.3	152.1	148.4	146.0	143.7
65°	178.4	169.9	160.0	152.1	144.1	138.9	134.2	130.6	127.9	126.3	124.3
67.5°	151.3	142.9	134.3	126.5	121.2	117.2	114.2	111.1	109.8	107.6	106.3
70°	133.5	125.0	117.4	111.5	106.2	103.2	101.3	98.9	97.6	95.0	93.7
72.5°	114.3	108.1	102.6	97.7	93.5	90.8	88.3	85.5	83.3	80.5	79.1
75°	90.1	84.5	80.2	76.8	74.2	70.6	67.0	64.0	63.0	62.0	61.6
77.5°	66.6	63.1	60.0	57.3	54.0	51.3	50.5	49.9	49.7	49.2	49.2
80°	52.4	49.2	46.8	43.6	41.6	41.6	41.6	40.9	41.2	41.2	41.2
82.5°	39.0	35.9	34.7	33.5	33.1	33.4	33.4	33.5	33.3	33.8	33.6
85°	20.1	20.4	21.1	20.8	21.1	21.1	21.8	21.4	21.8	21.1	21.8
87.5°	8.4	9.5	10.0	10.6	11.1	11.2	11.4	11.5	11.8	11.9	12.1
90°	5.4	6.4	7.8	9.3	10.8	12.3	11.8	12.3	12.7	13.3	14.2
92.5°	21.1	28.4	41.2	62.3	83.1	75.5	57.0	41.3	32.8	29.0	26.4
95°	44.7	63.8	105.6	178.7	259.3	291.2	236.2	176.8	119.9	93.8	76.1
97.5°	53.0	73.8	113.7	196.1	330.4	451.3	482.8	440.7	353.0	289.6	230.9
100°	58.9	78.1	112.4	185.1	314.3	465.0	561.8	579.0	539.2	481.7	412.0
102.5°	65.6	83.2	114.0	175.7	290.8	439.5	565.8	625.0	623.7	590.2	546.0
105°	76.6	91.9	118.4	168.9	261.7	394.9	535.8	638.4	687.5	696.9	684.1
107.5°	89.0	103.1	126.4	168.4	243.3	355.3	483.4	599.7	679.5	722.5	739.9
110°	97.2	111.0	133.1	170.4	236.2	332.9	450.3	562.7	653.2	715.1	749.4



TEST NUMBER: P332278-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	105.9	119.2	139.7	174.4	232.3	318.1	421.6	526.2	618.5	687.9	732.1
115°	118.8	132.1	150.8	180.7	230.8	302.0	387.0	477.9	563.3	635.5	689.0
117.5°	131.7	144.0	162.5	189.2	231.7	292.6	366.1	442.7	516.5	581.3	635.7
120°	140.0	152.2	169.9	195.4	233.2	288.3	355.1	424.3	490.6	549.5	599.2
122.5°	147.4	160.5	177.8	201.4	236.0	285.5	346.0	409.7	469.8	524.3	570.4
125°	158.6	171.9	189.1	210.7	240.1	281.9	334.4	390.4	443.9	491.1	530.4
127.5°	169.0	182.3	198.9	218.3	244.9	280.1	324.3	373.5	421.3	463.8	499.6
130°	175.3	188.6	204.7	223.4	248.0	279.0	318.7	362.9	407.1	446.9	480.3
132.5°	181.2	194.1	209.9	228.2	250.4	278.5	313.6	353.1	393.7	430.8	462.6
135°	189.1	202.3	217.6	234.3	253.9	277.9	306.9	339.8	374.7	406.7	434.6
137.5°	196.0	208.2	222.8	238.8	256.2	276.9	301.2	327.8	356.4	383.8	408.1
140°	199.8	212.2	226.4	241.2	257.8	276.5	297.6	320.7	345.7	369.3	390.4
142.5°	203.8	215.3	229.1	243.5	259.0	275.7	294.5	314.0	335.5	355.9	374.3
145°	208.7	220.0	232.8	246.1	259.8	274.5	290.2	305.9	322.2	337.9	352.1
147.5°	214.4	224.0	235.7	247.6	259.8	272.7	286.1	299.4	312.2	324.9	335.0
150°	217.6	226.4	237.7	248.0	259.8	271.0	283.4	294.6	305.9	316.2	325.6
152.5°	220.7	229.1	238.8	248.8	258.6	269.1	280.3	290.3	300.1	309.2	316.9
155°	225.9	232.8	241.2	249.0	257.4	265.7	275.5	283.9	291.7	299.1	305.0
157.5°	230.4	235.7	242.4	249.5	255.6	262.6	270.2	277.0	283.5	289.3	293.9
160°	232.8	237.7	243.6	249.5	254.9	260.3	266.7	273.0	278.4	283.4	286.8
162.5°	234.7	238.8	244.0	249.1	253.3	258.0	263.1	268.4	272.9	277.5	280.5
165°	237.2	240.6	244.5	248.0	251.0	254.4	258.3	262.3	265.2	268.6	271.0
167.5°	239.4	241.6	244.4	247.2	248.6	250.8	253.7	256.9	259.2	261.1	262.9
170°	240.6	241.6	244.1	246.1	247.0	248.5	251.0	253.4	254.9	256.8	257.8
172.5°	241.4	242.0	244.1	245.6	245.8	246.5	248.2	250.3	251.3	252.9	253.5
175°	242.1	242.6	243.6	244.5	244.1	244.1	245.0	246.1	246.5	247.5	247.5
177.5°	242.6	242.6	243.0	243.7	243.0	242.6	243.0	243.4	243.7	244.2	244.2
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P332278-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	733.9	733.7	733.9	732.9	733.9	733.7	733.9	737.1	737.1	737.4	737.6
5°	682.9	682.6	681.7	678.7	681.7	682.6	682.9	684.0	686.6	691.2	689.9
7.5°	638.4	638.0	635.1	635.2	635.1	638.0	638.4	641.0	644.0	646.9	650.2
10°	612.1	612.4	608.5	606.1	608.5	612.4	612.1	614.4	618.6	621.0	623.3
12.5°	586.5	585.0	581.8	579.2	581.8	585.0	586.5	588.2	594.1	596.7	601.2
15°	552.7	549.4	541.5	542.2	541.5	549.4	552.7	551.4	557.3	560.6	562.0
17.5°	512.9	510.5	510.4	505.8	510.4	510.5	512.9	515.6	520.7	524.3	533.7
20°	489.7	488.1	488.7	484.1	488.7	488.1	489.7	495.0	498.3	502.9	510.5
22.5°	471.5	469.8	467.1	465.6	467.1	469.8	471.5	475.2	478.8	485.3	489.4
25°	444.9	442.2	439.6	441.3	439.6	442.2	444.9	446.9	453.4	456.4	462.4
27.5°	418.2	416.2	413.6	413.3	413.6	416.2	418.2	420.2	423.8	428.8	435.9
30°	401.3	399.3	398.0	396.4	398.0	399.3	401.3	402.9	406.7	411.9	417.2
32.5°	384.2	383.8	381.4	381.1	381.4	383.8	384.2	386.9	390.5	395.5	400.0
35°	361.8	359.8	359.1	359.5	359.1	359.8	361.8	363.1	366.4	371.0	375.3
37.5°	340.4	337.9	336.7	335.4	336.7	337.9	340.4	340.7	344.1	347.2	352.9
40°	325.2	322.5	321.8	321.2	321.8	322.5	325.2	324.9	328.5	330.8	336.0
42.5°	308.0	306.9	306.6	305.4	306.6	306.9	308.0	309.8	311.9	315.2	319.2
45°	284.6	284.3	282.3	282.9	282.3	284.3	284.6	285.6	289.2	291.5	295.2
47.5°	259.9	258.5	257.1	258.0	257.1	258.5	259.9	261.2	263.7	266.6	271.3
50°	243.1	242.4	239.4	240.0	239.4	242.4	243.1	244.4	246.0	249.6	253.9
52.5°	226.2	223.7	222.6	222.1	222.6	223.7	226.2	227.5	229.4	233.6	236.8
55°	198.2	195.2	193.9	193.2	193.9	195.2	198.2	200.5	203.1	207.8	211.0
57.5°	170.7	170.0	168.9	169.6	168.9	170.0	170.7	174.6	177.2	180.8	184.8
60°	154.6	154.6	154.6	154.4	154.6	154.6	154.6	158.0	160.2	163.9	168.2
62.5°	142.2	141.5	141.2	141.6	141.2	141.5	142.2	143.7	146.0	148.4	152.1
65°	123.3	123.0	121.7	121.4	121.7	123.0	123.3	124.3	126.3	127.9	130.6
67.5°	105.5	104.3	103.9	103.4	103.9	104.3	105.5	106.3	107.6	109.8	111.1
70°	92.0	91.4	89.4	89.7	89.4	91.4	92.0	93.7	95.0	97.6	98.9
72.5°	77.5	76.8	76.5	75.9	76.5	76.8	77.5	79.1	80.5	83.3	85.5
75°	61.3	61.0	60.7	62.0	60.7	61.0	61.3	61.6	62.0	63.0	64.0
77.5°	49.2	49.2	49.3	48.8	49.3	49.2	49.2	49.2	49.2	49.7	49.9
80°	41.2	41.2	40.9	40.9	40.9	41.2	41.2	41.2	41.2	41.2	40.9
82.5°	33.1	33.3	33.5	33.0	33.5	33.3	33.1	33.6	33.8	33.3	33.5
85°	21.8	21.4	22.1	21.8	22.1	21.4	21.8	21.8	21.1	21.8	21.4
87.5°	12.5	12.1	12.1	12.3	12.1	12.1	12.5	12.1	11.9	11.8	11.5
90°	13.8	14.2	14.7	14.2	14.7	14.2	13.8	14.2	13.3	12.7	12.3
92.5°	25.6	24.0	24.5	23.7	24.5	24.0	25.6	26.4	29.0	32.8	41.3
95°	66.8	62.3	58.9	57.0	58.9	62.3	66.8	76.1	93.8	119.9	176.8
97.5°	194.7	172.5	159.3	155.1	159.3	172.5	194.7	230.9	289.6	353.0	440.7
100°	362.4	326.6	307.5	307.9	307.5	326.6	362.4	412.0	481.7	539.2	579.0
102.5°	507.4	479.0	463.0	451.7	463.0	479.0	507.4	546.0	590.2	623.7	625.0
105°	661.5	642.8	627.2	624.7	627.2	642.8	661.5	684.1	696.9	687.5	638.4
107.5°	740.4	734.1	728.8	724.3	728.8	734.1	740.4	739.9	722.5	679.5	599.7
110°	763.2	767.1	766.1	765.1	766.1	767.1	763.2	749.4	715.1	653.2	562.7



TEST NUMBER: P332278-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	757.2	769.5	773.2	773.4	773.2	769.5	757.2	732.1	687.9	618.5	526.2
115°	725.8	747.4	757.2	759.7	757.2	747.4	725.8	689.0	635.5	563.3	477.9
117.5°	674.1	698.8	713.0	716.3	713.0	698.8	674.1	635.7	581.3	516.5	442.7
120°	637.9	665.5	677.2	680.2	677.2	665.5	637.9	599.2	549.5	490.6	424.3
122.5°	604.9	629.6	642.7	646.4	642.7	629.6	604.9	570.4	524.3	469.8	409.7
125°	561.8	583.4	595.7	599.2	595.7	583.4	561.8	530.4	491.1	443.9	390.4
127.5°	527.5	546.0	557.1	560.3	557.1	546.0	527.5	499.6	463.8	421.3	373.5
130°	506.4	524.0	534.3	538.2	534.3	524.0	506.4	480.3	446.9	407.1	362.9
132.5°	487.1	504.7	513.8	516.6	513.8	504.7	487.1	462.6	430.8	393.7	353.1
135°	458.7	473.4	482.2	485.7	482.2	473.4	458.7	434.6	406.7	374.7	339.8
137.5°	428.3	443.2	450.7	453.0	450.7	443.2	428.3	408.1	383.8	356.4	327.8
140°	409.1	422.8	430.7	430.2	430.7	422.8	409.1	390.4	369.3	345.7	320.7
142.5°	390.2	402.4	409.5	409.0	409.5	402.4	390.2	374.3	355.9	335.5	314.0
145°	364.4	374.7	378.7	379.6	378.7	374.7	364.4	352.1	337.9	322.2	305.9
147.5°	344.3	351.3	355.1	355.4	355.1	351.3	344.3	335.0	324.9	312.2	299.4
150°	332.9	338.4	341.3	341.3	341.3	338.4	332.9	325.6	316.2	305.9	294.6
152.5°	322.7	327.8	329.5	329.5	329.5	327.8	322.7	316.9	309.2	300.1	290.3
155°	309.4	313.3	314.3	314.8	314.3	313.3	309.4	305.0	299.1	291.7	283.9
157.5°	297.7	300.7	301.4	301.4	301.4	300.7	297.7	293.9	289.3	283.5	277.0
160°	290.2	293.2	293.2	292.7	293.2	293.2	290.2	286.8	283.4	278.4	273.0
162.5°	282.8	285.3	285.3	284.8	285.3	285.3	282.8	280.5	277.5	272.9	268.4
165°	273.0	275.0	274.5	274.5	274.5	275.0	273.0	271.0	268.6	265.2	262.3
167.5°	263.8	265.2	264.7	264.7	264.7	265.2	263.8	262.9	261.1	259.2	256.9
170°	258.3	259.3	258.8	258.8	258.8	259.3	258.3	257.8	256.8	254.9	253.4
172.5°	253.6	254.6	253.7	253.3	253.7	254.6	253.6	253.5	252.9	251.3	250.3
175°	247.5	248.0	247.5	247.0	247.5	248.0	247.5	247.5	247.5	246.5	246.1
177.5°	243.7	244.2	243.4	243.4	243.4	244.2	243.7	244.2	244.2	243.7	243.4
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P332278-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	735.3	739.0	742.7	746.1	751.4	753.7	757.2	758.5	762.4	768.3	773.0
5°	690.5	695.9	702.7	708.3	717.3	724.2	731.8	739.0	747.6	759.8	770.7
7.5°	652.6	657.8	666.2	676.6	686.4	696.2	706.6	716.4	728.8	746.2	763.5
10°	627.6	633.9	643.8	655.0	667.1	676.7	688.9	701.5	716.6	736.8	757.5
12.5°	606.0	610.6	622.1	632.7	646.5	658.8	670.7	685.4	702.7	724.1	749.1
15°	571.5	578.1	589.4	601.2	615.7	628.5	644.0	661.9	678.7	705.1	735.4
17.5°	536.9	547.0	558.6	572.0	582.8	600.5	617.3	635.6	656.3	684.3	717.6
20°	514.8	522.7	533.6	553.0	567.2	580.7	596.2	619.0	638.1	669.8	704.4
22.5°	496.0	501.9	514.0	530.1	546.6	562.2	578.1	599.8	623.4	653.4	691.0
25°	468.3	477.5	486.7	498.3	516.1	534.9	552.1	570.5	595.6	627.6	668.1
27.5°	441.2	449.5	458.7	472.9	486.4	503.9	521.9	543.0	569.9	603.7	644.9
30°	423.8	430.1	438.6	456.8	469.0	484.1	505.2	524.0	549.1	585.0	628.5
32.5°	405.8	414.0	423.3	437.2	452.3	466.7	485.9	506.4	531.9	567.3	611.9
35°	380.2	389.8	399.3	409.6	424.7	439.6	455.7	478.2	504.2	538.6	582.4
37.5°	356.7	364.4	372.2	384.9	399.2	413.4	428.4	450.6	475.1	512.1	552.3
40°	341.6	348.6	354.5	367.7	381.6	396.7	411.6	431.0	457.4	492.1	531.0
42.5°	325.3	331.7	339.8	350.5	365.5	378.2	393.1	411.5	436.3	471.5	505.6
45°	300.7	308.0	315.0	325.2	340.0	352.5	365.8	383.2	408.6	437.6	468.0
47.5°	275.3	282.5	290.4	300.3	313.2	326.0	339.1	354.6	377.8	406.3	426.7
50°	258.9	264.8	272.8	282.6	294.5	308.0	319.9	336.7	358.8	381.3	399.1
52.5°	242.0	247.4	256.4	266.8	277.8	289.6	302.2	316.7	336.7	357.7	371.9
55°	215.7	222.3	229.9	240.0	251.0	260.9	273.0	287.9	303.8	319.5	329.2
57.5°	191.1	196.6	202.9	213.5	222.9	234.7	245.6	257.3	271.9	283.8	290.1
60°	173.1	178.1	186.3	195.5	204.5	214.6	227.2	238.8	249.9	259.5	264.5
62.5°	156.3	162.0	169.2	177.6	187.4	197.0	207.9	217.7	227.6	235.8	239.2
65°	134.2	138.9	144.1	152.1	160.0	169.9	178.4	188.3	195.5	200.2	203.1
67.5°	114.2	117.2	121.2	126.5	134.3	142.9	151.3	158.9	165.1	168.2	170.8
70°	101.3	103.2	106.2	111.5	117.4	125.0	133.5	139.1	144.5	147.1	149.7
72.5°	88.3	90.8	93.5	97.7	102.6	108.1	114.3	121.2	124.2	127.3	128.9
75°	67.0	70.6	74.2	76.8	80.2	84.5	90.1	94.3	96.0	98.6	98.9
77.5°	50.5	51.3	54.0	57.3	60.0	63.1	66.6	70.5	71.3	72.7	73.5
80°	41.6	41.6	41.6	43.6	46.8	49.2	52.4	54.4	55.7	56.1	56.4
82.5°	33.4	33.4	33.1	33.5	34.7	35.9	39.0	41.2	42.3	42.1	41.3
85°	21.8	21.1	21.1	20.8	21.1	20.4	20.1	21.4	23.4	23.4	22.7
87.5°	11.4	11.2	11.1	10.6	10.0	9.5	8.4	8.5	8.3	9.1	8.6
90°	11.8	12.3	10.8	9.3	7.8	6.4	5.4	4.4	2.9	2.0	0.9
92.5°	57.0	75.5	83.1	62.3	41.2	28.4	21.1	17.0	13.2	9.0	6.1
95°	236.2	291.2	259.3	178.7	105.6	63.8	44.7	31.9	23.6	18.2	16.7
97.5°	482.8	451.3	330.4	196.1	113.7	73.8	53.0	40.5	33.2	29.0	28.5
100°	561.8	465.0	314.3	185.1	112.4	78.1	58.9	47.2	40.3	36.9	36.3
102.5°	565.8	439.5	290.8	175.7	114.0	83.2	65.6	55.0	48.6	45.5	44.6
105°	535.8	394.9	261.7	168.9	118.4	91.9	76.6	67.2	61.4	58.5	57.0
107.5°	483.4	355.3	243.3	168.4	126.4	103.1	89.0	80.2	74.5	71.6	70.1
110°	450.3	332.9	236.2	170.4	133.1	111.0	97.2	88.9	83.5	81.0	79.6



TEST NUMBER: P332278-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	421.6	318.1	232.3	174.4	139.7	119.2	105.9	97.6	92.1	89.7	88.2
115°	387.0	302.0	230.8	180.7	150.8	132.1	118.8	110.5	105.6	102.6	100.7
117.5°	366.1	292.6	231.7	189.2	162.5	144.0	131.7	122.3	117.9	115.4	113.1
120°	355.1	288.3	233.2	195.4	169.9	152.2	140.0	130.6	125.7	123.3	121.8
122.5°	346.0	285.5	236.0	201.4	177.8	160.5	147.4	138.4	133.2	130.7	129.2
125°	334.4	281.9	240.1	210.7	189.1	171.9	158.6	149.3	143.9	140.9	140.0
127.5°	324.3	280.1	244.9	218.3	198.9	182.3	169.0	158.7	153.3	149.6	148.1
130°	318.7	279.0	248.0	223.4	204.7	188.6	175.3	165.0	159.1	154.7	153.3
132.5°	313.6	278.5	250.4	228.2	209.9	194.1	181.2	170.9	163.8	159.0	157.1
135°	306.9	277.9	253.9	234.3	217.6	202.3	189.1	178.7	171.4	166.0	164.0
137.5°	301.2	276.9	256.2	238.8	222.8	208.2	196.0	185.7	177.9	172.5	170.5
140°	297.6	276.5	257.8	241.2	226.4	212.2	199.8	190.0	182.2	177.3	174.9
142.5°	294.5	275.7	259.0	243.5	229.1	215.3	203.8	194.0	186.9	181.6	179.5
145°	290.2	274.5	259.8	246.1	232.8	220.0	208.7	200.4	193.0	188.6	187.1
147.5°	286.1	272.7	259.8	247.6	235.7	224.0	214.4	206.4	200.0	195.6	194.8
150°	283.4	271.0	259.8	248.0	237.7	226.4	217.6	210.7	204.3	200.4	199.8
152.5°	280.3	269.1	258.6	248.8	238.8	229.1	220.7	214.6	209.1	205.1	205.0
155°	275.5	265.7	257.4	249.0	241.2	232.8	225.9	220.5	215.6	212.7	212.7
157.5°	270.2	262.6	255.6	249.5	242.4	235.7	230.4	225.8	221.4	219.1	218.7
160°	266.7	260.3	254.9	249.5	243.6	237.7	232.8	229.4	225.4	223.4	223.4
162.5°	263.1	258.0	253.3	249.1	244.0	238.8	234.7	231.7	228.6	227.0	227.0
165°	258.3	254.4	251.0	248.0	244.5	240.6	237.2	235.2	232.8	231.8	232.3
167.5°	253.7	250.8	248.6	247.2	244.4	241.6	239.4	238.1	236.2	235.7	236.3
170°	251.0	248.5	247.0	246.1	244.1	241.6	240.6	239.6	238.2	237.7	238.7
172.5°	248.2	246.5	245.8	245.6	244.1	242.0	241.4	240.8	239.8	239.6	240.2
175°	245.0	244.1	244.1	244.5	243.6	242.6	242.1	242.1	241.2	241.6	242.1
177.5°	243.0	242.6	243.0	243.7	243.0	242.6	242.6	242.6	242.2	242.6	243.0
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P332278-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	774.6	777.5	781.2	786.7	790.9	794.6	795.4	796.5	799.1	803.6	807.0
5°	779.6	787.2	799.4	811.2	824.1	834.7	844.6	851.5	858.1	871.9	883.1
7.5°	778.0	794.9	814.0	835.3	856.9	877.8	897.2	914.6	931.9	952.0	975.0
10°	777.0	796.8	822.4	849.8	879.9	909.2	937.5	959.7	985.4	1008.5	1037.8
12.5°	772.0	800.5	831.2	866.2	903.1	936.9	974.2	1004.8	1034.1	1067.6	1101.6
15°	765.4	800.0	839.0	885.5	941.5	982.4	1020.6	1073.8	1110.0	1146.3	1195.2
17.5°	753.5	795.7	844.4	904.7	951.6	1006.5	1064.0	1106.0	1154.9	1206.0	1250.2
20°	744.0	793.2	847.6	906.9	966.6	1026.3	1082.0	1132.1	1182.6	1241.6	1277.9
22.5°	734.5	783.1	839.6	902.7	966.8	1029.7	1092.8	1151.7	1208.4	1268.0	1314.3
25°	714.3	772.0	833.4	897.7	961.0	1030.2	1105.4	1171.0	1241.3	1302.6	1346.5
27.5°	693.9	746.7	807.8	873.1	943.4	1025.3	1113.7	1188.4	1258.7	1302.6	1316.4
30°	675.4	731.4	787.5	853.8	930.0	1021.3	1115.3	1200.8	1258.4	1277.6	1263.3
32.5°	656.7	707.5	763.0	830.9	911.8	1011.6	1117.4	1193.3	1228.1	1213.5	1155.7
35°	623.6	669.4	723.2	791.2	884.2	1006.2	1108.7	1160.2	1151.6	1069.1	960.3
37.5°	588.2	625.6	675.4	746.4	855.5	984.7	1071.3	1078.8	1004.6	878.0	752.3
40°	560.3	593.9	645.1	719.3	833.4	963.6	1033.5	1002.9	887.8	746.9	642.0
42.5°	533.1	561.5	610.7	690.8	812.3	934.9	977.3	910.5	777.7	644.5	549.2
45°	487.1	513.8	563.3	645.4	769.0	879.9	874.3	758.2	625.3	518.1	438.9
47.5°	443.4	466.7	513.2	597.0	718.3	797.4	744.9	621.5	508.7	422.8	366.3
50°	412.6	435.7	481.8	564.6	677.7	735.4	660.6	541.5	438.2	367.0	322.2
52.5°	383.0	405.5	447.8	528.4	628.6	663.1	582.7	472.3	386.3	324.9	286.3
55°	341.6	358.8	396.7	473.9	548.7	556.6	475.2	382.9	311.9	269.1	242.7
57.5°	299.5	314.3	351.7	413.2	465.7	461.6	384.4	304.5	256.8	224.9	205.8
60°	272.1	286.5	319.5	372.3	411.9	398.0	327.2	262.9	222.0	198.5	183.4
62.5°	246.5	257.8	288.7	327.2	355.7	340.0	279.7	226.4	194.0	174.3	162.2
65°	209.4	218.6	243.4	263.5	279.3	264.2	214.0	177.1	153.7	139.8	131.6
67.5°	174.2	180.0	195.7	202.9	214.1	197.5	160.9	136.2	122.9	111.2	105.5
70°	152.1	156.4	164.5	170.5	173.5	156.4	129.2	111.2	100.0	91.7	88.1
72.5°	129.8	133.6	135.3	140.2	138.6	122.5	103.9	89.5	81.5	75.9	71.2
75°	99.3	100.9	99.3	97.3	93.0	81.8	69.0	61.6	55.7	53.1	51.5
77.5°	72.3	71.8	69.6	66.5	59.2	52.1	45.2	42.7	40.2	38.7	38.2
80°	55.7	54.4	52.4	47.5	41.2	36.2	34.6	33.0	32.0	30.3	30.0
82.5°	41.5	40.7	37.4	33.2	28.8	26.5	25.1	24.5	23.5	22.7	22.6
85°	22.1	21.1	17.5	15.2	14.6	13.9	13.5	13.5	12.2	11.9	11.9
87.5°	7.5	6.1	6.2	5.6	5.8	5.5	6.1	5.9	5.9	6.0	5.6
90°	2.0	2.9	4.4	5.4	6.4	7.8	9.3	10.8	12.3	11.8	12.3
92.5°	9.0	13.2	17.0	21.1	28.4	41.2	62.3	83.1	75.5	57.0	41.3
95°	18.2	23.6	31.9	44.7	63.8	105.6	178.7	259.3	291.2	236.2	176.8
97.5°	29.0	33.2	40.5	53.0	73.8	113.7	196.1	330.4	451.3	482.8	440.7
100°	36.9	40.3	47.2	58.9	78.1	112.4	185.1	314.3	465.0	561.8	579.0
102.5°	45.5	48.6	55.0	65.6	83.2	114.0	175.7	290.8	439.5	565.8	625.0
105°	58.5	61.4	67.2	76.6	91.9	118.4	168.9	261.7	394.9	535.8	638.4
107.5°	71.6	74.5	80.2	89.0	103.1	126.4	168.4	243.3	355.3	483.4	599.7
110°	81.0	83.5	88.9	97.2	111.0	133.1	170.4	236.2	332.9	450.3	562.7





TEST NUMBER: P332278-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	89.7	92.1	97.6	105.9	119.2	139.7	174.4	232.3	318.1	421.6	526.2
115°	102.6	105.6	110.5	118.8	132.1	150.8	180.7	230.8	302.0	387.0	477.9
117.5°	115.4	117.9	122.3	131.7	144.0	162.5	189.2	231.7	292.6	366.1	442.7
120°	123.3	125.7	130.6	140.0	152.2	169.9	195.4	233.2	288.3	355.1	424.3
122.5°	130.7	133.2	138.4	147.4	160.5	177.8	201.4	236.0	285.5	346.0	409.7
125°	140.9	143.9	149.3	158.6	171.9	189.1	210.7	240.1	281.9	334.4	390.4
127.5°	149.6	153.3	158.7	169.0	182.3	198.9	218.3	244.9	280.1	324.3	373.5
130°	154.7	159.1	165.0	175.3	188.6	204.7	223.4	248.0	279.0	318.7	362.9
132.5°	159.0	163.8	170.9	181.2	194.1	209.9	228.2	250.4	278.5	313.6	353.1
135°	166.0	171.4	178.7	189.1	202.3	217.6	234.3	253.9	277.9	306.9	339.8
137.5°	172.5	177.9	185.7	196.0	208.2	222.8	238.8	256.2	276.9	301.2	327.8
140°	177.3	182.2	190.0	199.8	212.2	226.4	241.2	257.8	276.5	297.6	320.7
142.5°	181.6	186.9	194.0	203.8	215.3	229.1	243.5	259.0	275.7	294.5	314.0
145°	188.6	193.0	200.4	208.7	220.0	232.8	246.1	259.8	274.5	290.2	305.9
147.5°	195.6	200.0	206.4	214.4	224.0	235.7	247.6	259.8	272.7	286.1	299.4
150°	200.4	204.3	210.7	217.6	226.4	237.7	248.0	259.8	271.0	283.4	294.6
152.5°	205.1	209.1	214.6	220.7	229.1	238.8	248.8	258.6	269.1	280.3	290.3
155°	212.7	215.6	220.5	225.9	232.8	241.2	249.0	257.4	265.7	275.5	283.9
157.5°	219.1	221.4	225.8	230.4	235.7	242.4	249.5	255.6	262.6	270.2	277.0
160°	223.4	225.4	229.4	232.8	237.7	243.6	249.5	254.9	260.3	266.7	273.0
162.5°	227.0	228.6	231.7	234.7	238.8	244.0	249.1	253.3	258.0	263.1	268.4
165°	231.8	232.8	235.2	237.2	240.6	244.5	248.0	251.0	254.4	258.3	262.3
167.5°	235.7	236.2	238.1	239.4	241.6	244.4	247.2	248.6	250.8	253.7	256.9
170°	237.7	238.2	239.6	240.6	241.6	244.1	246.1	247.0	248.5	251.0	253.4
172.5°	239.6	239.8	240.8	241.4	242.0	244.1	245.6	245.8	246.5	248.2	250.3
175°	241.6	241.2	242.1	242.1	242.6	243.6	244.5	244.1	244.1	245.0	246.1
177.5°	242.6	242.2	242.6	242.6	242.6	243.0	243.7	243.0	242.6	243.0	243.4
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P332278-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	812.6	812.6	813.6	817.6	818.1	821.6	820.4
5°	893.0	899.3	901.6	911.5	917.5	920.1	914.8
7.5°	991.4	1009.1	1017.5	1027.9	1037.0	1039.8	1032.6
10°	1063.2	1081.7	1097.2	1106.7	1115.7	1121.5	1129.2
12.5°	1132.6	1155.3	1170.0	1183.5	1192.7	1200.2	1201.4
15°	1208.0	1242.3	1268.3	1287.5	1297.0	1302.0	1300.0
17.5°	1284.0	1315.8	1334.4	1353.8	1367.1	1367.8	1368.2
20°	1327.1	1358.1	1379.5	1394.0	1408.9	1408.2	1411.4
22.5°	1355.8	1380.2	1396.6	1407.1	1412.2	1409.7	1410.4
25°	1369.2	1376.5	1373.6	1356.7	1352.5	1337.0	1339.5
27.5°	1299.9	1265.6	1230.1	1184.4	1148.4	1119.6	1121.1
30°	1205.7	1145.0	1075.7	1017.7	965.6	951.1	920.1
32.5°	1074.0	983.0	901.9	847.8	803.1	790.9	763.9
35°	850.8	762.4	679.0	628.9	609.1	581.4	581.1
37.5°	661.3	583.5	539.4	501.8	482.1	465.3	463.6
40°	556.4	495.7	462.4	435.3	415.9	403.3	400.4
42.5°	483.0	433.9	402.7	386.0	371.0	364.5	359.7
45°	394.4	361.4	339.7	324.5	317.5	312.6	310.0
47.5°	329.9	307.8	293.0	282.9	277.2	272.1	273.5
50°	294.8	276.7	265.8	256.2	251.9	248.3	248.7
52.5°	266.6	250.3	241.5	234.6	229.3	226.7	225.4
55°	226.3	216.0	207.1	202.2	199.1	195.5	194.6
57.5°	193.0	185.0	177.8	172.2	171.5	168.0	168.4
60°	170.8	164.2	158.3	155.3	153.0	150.1	151.0
62.5°	152.7	147.1	141.6	139.2	136.9	134.7	135.2
65°	125.0	119.7	116.4	115.1	114.1	113.1	112.1
67.5°	99.6	96.3	94.3	91.4	89.5	89.1	88.1
70°	83.8	79.5	75.9	72.2	71.2	70.9	71.2
72.5°	67.2	64.4	63.5	61.6	61.5	60.6	61.2
75°	50.5	49.5	48.8	47.5	47.5	47.5	47.5
77.5°	37.2	36.6	36.2	35.9	35.6	35.1	35.1
80°	29.0	28.7	28.1	28.1	27.7	28.1	27.7
82.5°	21.9	21.9	21.2	21.2	20.8	20.7	20.8
85°	11.2	10.8	11.5	10.8	11.2	10.6	11.2
87.5°	5.7	5.9	5.8	5.7	5.5	6.1	5.5
90°	12.7	13.3	14.2	13.8	14.2	14.7	14.2
92.5°	32.8	29.0	26.4	25.6	24.0	24.5	23.7
95°	119.9	93.8	76.1	66.8	62.3	58.9	57.0
97.5°	353.0	289.6	230.9	194.7	172.5	159.3	155.1
100°	539.2	481.7	412.0	362.4	326.6	307.5	307.9
102.5°	623.7	590.2	546.0	507.4	479.0	463.0	451.7
105°	687.5	696.9	684.1	661.5	642.8	627.2	624.7
107.5°	679.5	722.5	739.9	740.4	734.1	728.8	724.3
110°	653.2	715.1	749.4	763.2	767.1	766.1	765.1



TEST NUMBER: P332278-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	618.5	687.9	732.1	757.2	769.5	773.2	773.4
115°	563.3	635.5	689.0	725.8	747.4	757.2	759.7
117.5°	516.5	581.3	635.7	674.1	698.8	713.0	716.3
120°	490.6	549.5	599.2	637.9	665.5	677.2	680.2
122.5°	469.8	524.3	570.4	604.9	629.6	642.7	646.4
125°	443.9	491.1	530.4	561.8	583.4	595.7	599.2
127.5°	421.3	463.8	499.6	527.5	546.0	557.1	560.3
130°	407.1	446.9	480.3	506.4	524.0	534.3	538.2
132.5°	393.7	430.8	462.6	487.1	504.7	513.8	516.6
135°	374.7	406.7	434.6	458.7	473.4	482.2	485.7
137.5°	356.4	383.8	408.1	428.3	443.2	450.7	453.0
140°	345.7	369.3	390.4	409.1	422.8	430.7	430.2
142.5°	335.5	355.9	374.3	390.2	402.4	409.5	409.0
145°	322.2	337.9	352.1	364.4	374.7	378.7	379.6
147.5°	312.2	324.9	335.0	344.3	351.3	355.1	355.4
150°	305.9	316.2	325.6	332.9	338.4	341.3	341.3
152.5°	300.1	309.2	316.9	322.7	327.8	329.5	329.5
155°	291.7	299.1	305.0	309.4	313.3	314.3	314.8
157.5°	283.5	289.3	293.9	297.7	300.7	301.4	301.4
160°	278.4	283.4	286.8	290.2	293.2	293.2	292.7
162.5°	272.9	277.5	280.5	282.8	285.3	285.3	284.8
165°	265.2	268.6	271.0	273.0	275.0	274.5	274.5
167.5°	259.2	261.1	262.9	263.8	265.2	264.7	264.7
170°	254.9	256.8	257.8	258.3	259.3	258.8	258.8
172.5°	251.3	252.9	253.5	253.6	254.6	253.7	253.3
175°	246.5	247.5	247.5	247.5	248.0	247.5	247.0
177.5°	243.7	244.2	244.2	243.7	244.2	243.4	243.4
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6

(END OF REPORT)