

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332319-935

Luminaire Tested: **S123RDIP-S775D1025U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332319-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D1025U935-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5656.4 lumens
Efficiency: N/A
Efficacy: 108.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332319-935

CATALOG NUMBER: S123RDIP-S775D1025U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332319-935

CATALOG NUMBER: S123RDIP-S775D1025U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53	46
1	98	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	71	82	76	71	67	64	60	57	53	50	48	42	41	39	35
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	38	36	34	30
4	75	65	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30	26
5	69	58	50	44	63	54	47	42	46	40	36	38	34	31	31	28	26	23
6	64	52	44	39	58	48	41	36	41	36	32	35	31	28	28	26	23	20
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21	18
8	55	43	35	30	50	40	33	29	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	37	30	26	31	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11334	11334	11334	11334
5°	13511	11382	10024	11382
10°	16869	11317	9055	11317
15°	19801	11202	8259	11202
20°	22100	11030	7581	11030
25°	21747	10847	7163	10847
30°	15632	10679	6734	10679
35°	10437	10461	6457	10461
40°	7690	10197	6169	10197
45°	6450	9736	5888	9736
50°	5692	9133	5494	9133
55°	4992	8443	4958	8443
60°	4445	7782	4540	7782
65°	3904	7073	4225	7073
70°	3065	6442	3858	6442
75°	2699	5627	3523	5627
80°	2349	4779	3465	4779
85°	1890	3841	3680	3841



TEST NUMBER: P332319-935

CATALOG NUMBER: S123RDIP-S775D1025U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.6	1.8
10°-20°	323.5	5.7
20°-30°	508.3	9.0
30°-40°	530.3	9.4
40°-50°	453.8	8.0
50°-60°	345.9	6.1
60°-70°	221.7	3.9
70°-80°	106.6	1.9
80°-90°	31.5	0.6
90°-100°	71.3	1.3
100°-110°	213.3	3.8
110°-120°	362.8	6.4
120°-130°	477.3	8.4
130°-140°	536.4	9.5
140°-150°	527.3	9.3
150°-160°	443.9	7.8
160°-170°	295.5	5.2
170°-180°	103.5	1.8
0°-30°	935.3	16.5
0°-40°	1465.6	25.9
0°-60°	2265.3	40.0
0°-90°	2625.1	46.4
90°-120°	647.5	11.4
90°-150°	2188.5	38.7
90°-180°	3031.0	53.6
0°-180°	5656.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1053	1053	1053	1053	1053	
5°	1250	1053	928	1053	1250	129
15°	1777	1005	741	1005	1777	504
25°	1831	913	603	913	1831	787
35°	794	796	491	796	794	521
45°	424	640	387	640	424	333
55°	266	450	264	450	266	240
65°	153	278	166	278	153	151
75°	65	135	85	135	65	70
85°	15	31	30	31	15	18
90°	26	1	26	1	26	13
95°	67	51	67	51	67	69
105°	205	193	205	193	205	217
115°	366	365	366	365	366	362
125°	529	535	529	535	529	473
135°	693	694	693	694	693	533
145°	841	841	841	841	841	525
155°	962	964	962	964	962	443
165°	1046	1049	1046	1049	1046	295
175°	1087	1092	1087	1092	1087	103
180°	1094	1094	1094	1094	1094	



TEST NUMBER: P332319-935

CATALOG NUMBER: S123RDIP-S775D1025U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1121.5	1123.0	1118.3	1117.6	1112.2	1110.7	1110.7	1103.1	1098.5	1092.4	1088.7
5°	1250.4	1257.7	1254.0	1246.0	1232.4	1229.2	1220.7	1207.2	1191.9	1172.9	1163.9
7.5°	1411.4	1421.3	1417.6	1405.0	1390.9	1379.4	1355.2	1332.7	1301.3	1273.7	1250.1
10°	1543.4	1533.1	1525.0	1512.8	1499.8	1478.5	1453.3	1418.6	1378.5	1346.9	1311.7
12.5°	1642.3	1640.5	1630.3	1617.7	1599.3	1579.2	1548.2	1505.9	1459.2	1413.7	1373.5
15°	1776.9	1779.7	1772.9	1759.8	1733.7	1698.1	1651.2	1633.6	1566.9	1517.3	1467.7
17.5°	1870.2	1869.7	1868.7	1850.6	1823.9	1798.6	1755.1	1708.9	1648.5	1578.6	1511.8
20°	1929.3	1924.9	1925.7	1905.4	1885.6	1856.3	1814.0	1746.8	1697.2	1616.5	1547.5
22.5°	1927.9	1927.0	1930.4	1923.5	1909.0	1886.6	1853.2	1796.6	1733.3	1651.8	1574.2
25°	1831.1	1827.5	1848.7	1854.5	1877.5	1881.5	1871.6	1840.6	1780.5	1696.7	1600.7
27.5°	1532.5	1530.5	1569.8	1619.0	1681.4	1729.9	1776.8	1799.4	1780.5	1720.5	1624.4
30°	1257.7	1300.0	1319.9	1391.1	1470.4	1565.1	1648.0	1726.9	1746.3	1720.2	1641.2
32.5°	1044.2	1081.2	1097.7	1158.8	1232.8	1343.7	1468.1	1579.8	1658.7	1678.7	1631.2
35°	794.3	794.7	832.6	859.6	928.2	1042.2	1163.0	1312.7	1461.4	1574.1	1585.8
37.5°	633.8	636.0	658.9	685.9	737.3	797.6	904.0	1028.4	1200.2	1373.2	1474.6
40°	547.3	551.3	568.4	595.0	632.0	677.5	760.4	877.7	1021.0	1213.5	1370.8
42.5°	491.7	498.3	507.1	527.6	550.5	593.1	660.2	750.7	881.1	1063.1	1244.6
45°	423.7	427.3	434.1	443.6	464.3	494.0	539.2	599.9	708.2	854.7	1036.3
47.5°	373.8	371.9	379.0	386.7	400.5	420.8	451.0	500.7	577.8	695.3	849.5
50°	339.9	339.4	344.4	350.3	363.3	378.2	403.0	440.4	501.7	599.1	740.2
52.5°	308.2	309.9	313.4	320.7	330.1	342.2	364.4	391.3	444.0	528.1	645.7
55°	266.0	267.3	272.2	276.3	283.1	295.2	309.3	331.7	367.8	426.5	523.3
57.5°	230.2	229.6	234.4	235.4	243.1	253.0	263.8	281.3	307.5	350.9	416.2
60°	206.5	205.1	209.1	212.3	216.4	224.5	233.5	250.6	271.4	303.3	359.3
62.5°	184.9	184.2	187.2	190.3	193.6	201.0	208.6	221.8	238.2	265.2	309.5
65°	153.3	154.6	155.9	157.3	159.1	163.6	170.8	179.9	191.1	210.1	242.0
67.5°	120.5	121.8	122.3	125.0	128.9	131.7	136.1	144.1	152.0	168.0	186.1
70°	97.4	96.9	97.4	98.8	103.7	108.7	114.5	120.4	125.3	136.6	151.9
72.5°	83.7	82.8	84.0	84.3	86.7	88.1	91.8	97.3	103.7	111.3	122.3
75°	64.9	64.9	64.9	64.9	66.7	67.6	69.0	70.3	72.6	76.2	84.3
77.5°	48.0	48.0	48.6	49.2	49.5	50.0	50.9	52.2	53.0	54.9	58.5
80°	37.9	38.3	37.9	38.3	38.3	39.2	39.7	41.0	41.5	43.7	45.1
82.5°	28.5	28.2	28.5	28.9	28.9	29.9	30.0	30.9	31.0	32.2	33.6
85°	15.3	14.5	15.3	14.9	15.8	14.9	15.3	16.2	16.2	16.7	18.5
87.5°	8.8	9.4	8.6	8.9	8.8	9.0	8.9	8.8	9.3	8.8	8.7
90°	25.7	25.4	25.1	24.6	24.3	23.7	22.9	22.1	21.4	20.7	18.2
92.5°	34.7	35.0	35.2	35.4	35.6	35.5	34.9	34.3	33.6	33.0	31.6
95°	67.1	67.1	67.1	67.1	67.1	66.6	65.9	65.1	64.4	63.6	62.1
97.5°	103.1	103.2	103.3	103.4	103.4	103.1	102.2	101.3	100.4	99.5	98.4
100°	130.6	130.3	129.8	129.5	129.2	128.6	128.0	127.5	126.9	126.3	125.4
102.5°	158.9	158.9	158.9	159.0	159.1	158.9	158.3	157.7	157.1	156.6	155.3
105°	204.6	204.1	203.8	203.4	203.0	202.9	202.9	202.9	202.9	202.9	201.1
107.5°	252.2	252.4	252.6	252.9	253.0	252.9	252.3	251.7	251.1	250.5	249.8
110°	284.5	284.9	285.2	285.6	286.0	285.9	285.1	284.3	283.5	282.8	282.4



TEST NUMBER: P332319-935

CATALOG NUMBER: S123RDIP-S775D1025U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	318.8	318.9	319.0	319.1	319.2	318.7	317.8	316.9	316.0	315.0	315.0
115°	366.1	366.4	366.5	366.7	366.9	366.9	366.7	366.5	366.4	366.1	366.5
117.5°	414.1	414.7	415.2	415.7	416.2	416.6	416.6	416.6	416.6	416.6	417.2
120°	447.8	448.2	448.6	448.9	449.3	449.6	449.8	450.0	450.1	450.4	451.3
122.5°	480.1	480.6	481.1	481.7	482.2	482.8	483.3	483.7	484.2	484.7	485.3
125°	528.6	529.3	530.1	530.9	531.6	532.4	533.1	533.9	534.7	535.5	535.8
127.5°	576.9	577.7	578.6	579.5	580.4	581.3	582.5	583.5	584.5	585.7	586.1
130°	608.5	609.8	611.1	612.5	613.8	614.9	615.6	616.4	617.2	617.9	618.5
132.5°	641.5	642.6	643.6	644.6	645.7	646.6	647.6	648.4	649.4	650.2	650.7
135°	692.8	693.1	693.4	693.9	694.2	694.8	695.6	696.4	697.2	697.8	698.1
137.5°	738.0	738.7	739.3	740.1	740.8	741.6	742.4	743.2	744.0	744.8	744.3
140°	767.5	768.9	770.2	771.5	772.8	773.6	773.8	774.0	774.2	774.4	774.2
142.5°	797.7	798.7	799.8	800.8	801.8	802.5	802.7	802.9	803.1	803.2	802.9
145°	841.4	842.1	842.9	843.7	844.5	844.9	845.2	845.3	845.5	845.7	845.2
147.5°	880.3	881.4	882.5	883.7	884.8	885.5	885.5	885.5	885.5	885.5	884.8
150°	905.0	906.1	907.3	908.4	909.6	910.2	910.2	910.2	910.2	910.2	909.8
152.5°	929.1	930.1	931.1	932.0	933.1	933.4	933.1	932.8	932.5	932.2	931.9
155°	961.7	963.0	964.4	965.8	967.1	967.3	966.6	965.9	965.1	964.3	964.1
157.5°	991.4	992.6	993.6	994.7	995.7	995.9	995.1	994.3	993.5	992.6	992.6
160°	1010.7	1011.5	1012.3	1013.1	1013.7	1013.7	1012.7	1011.8	1010.8	1009.9	1009.9
162.5°	1025.2	1026.4	1027.6	1028.8	1030.0	1030.2	1029.2	1028.3	1027.3	1026.4	1026.2
165°	1045.9	1047.3	1048.6	1050.0	1051.3	1051.4	1050.2	1049.1	1047.9	1046.8	1046.8
167.5°	1063.7	1064.9	1066.0	1067.2	1068.4	1068.4	1067.2	1066.0	1064.9	1063.7	1063.5
170°	1072.6	1073.9	1075.3	1076.6	1078.0	1078.0	1076.6	1075.3	1073.9	1072.6	1072.6
172.5°	1079.4	1080.8	1082.2	1083.5	1084.9	1084.9	1083.7	1082.5	1081.3	1080.1	1080.1
175°	1087.2	1088.6	1089.9	1091.2	1092.5	1092.7	1091.5	1090.4	1089.3	1088.0	1088.0
177.5°	1091.3	1092.4	1093.5	1094.6	1095.6	1095.7	1094.8	1093.9	1093.0	1092.0	1092.0
180°	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1



TEST NUMBER: P332319-935

CATALOG NUMBER: S123RDIP-S775D1025U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1087.3	1086.2	1081.2	1075.4	1067.8	1062.7	1058.8	1056.6	1050.2	1042.2	1036.8
5°	1154.4	1140.9	1126.5	1108.9	1092.7	1076.0	1065.7	1053.4	1038.6	1021.9	1010.2
7.5°	1226.4	1199.9	1171.3	1141.9	1112.7	1086.6	1063.5	1043.7	1020.0	996.1	979.4
10°	1281.6	1242.8	1202.6	1161.7	1124.2	1089.1	1062.0	1035.4	1007.0	979.6	958.8
12.5°	1331.7	1280.7	1234.4	1184.0	1136.2	1094.2	1055.2	1023.9	989.7	960.4	936.8
15°	1395.2	1342.9	1286.9	1210.3	1146.8	1093.6	1046.3	1005.2	963.8	927.7	904.7
17.5°	1454.5	1375.8	1300.7	1236.7	1154.2	1087.7	1029.9	980.9	935.4	897.2	868.8
20°	1479.0	1402.8	1321.2	1239.7	1158.5	1084.1	1016.9	962.9	915.5	872.3	846.1
22.5°	1493.7	1407.5	1321.5	1233.9	1147.7	1070.4	1004.0	944.4	893.2	852.0	819.8
25°	1511.0	1408.3	1313.5	1227.0	1139.1	1055.2	976.4	913.3	857.8	814.1	779.8
27.5°	1522.3	1401.4	1289.6	1193.3	1104.2	1020.7	948.4	881.6	825.3	779.0	742.3
30°	1524.5	1396.0	1271.2	1167.1	1076.4	999.8	923.2	859.2	799.7	750.5	716.3
32.5°	1527.4	1382.7	1246.3	1135.7	1042.9	967.0	897.6	836.5	775.5	727.1	692.2
35°	1515.5	1375.4	1208.5	1081.4	988.5	915.1	852.4	796.1	736.2	689.2	653.6
37.5°	1464.3	1346.0	1169.4	1020.3	923.2	855.1	804.1	754.9	700.0	649.4	615.9
40°	1412.7	1317.2	1139.1	983.2	881.8	811.8	765.9	725.7	672.5	625.3	589.2
42.5°	1335.9	1277.9	1110.3	944.2	834.8	767.5	728.8	691.1	644.5	596.4	562.5
45°	1195.0	1202.6	1051.2	882.2	769.9	702.3	665.8	639.6	598.2	558.5	523.8
47.5°	1018.3	1089.9	981.9	816.1	701.5	638.0	606.1	583.3	555.3	516.4	484.7
50°	902.9	1005.2	926.3	771.7	658.6	595.5	564.0	545.4	521.1	490.4	460.2
52.5°	796.5	906.5	859.3	722.3	612.1	554.4	523.6	508.3	489.0	460.1	432.8
55°	649.5	761.0	750.1	647.7	542.3	490.4	467.0	449.9	436.8	415.2	393.6
57.5°	525.5	631.0	636.6	564.8	480.8	429.6	409.4	396.5	388.0	371.6	351.6
60°	447.2	544.1	563.0	508.9	436.8	391.8	371.9	361.5	354.7	341.7	326.4
62.5°	382.3	464.8	486.2	447.3	394.6	352.4	336.9	326.9	322.3	311.0	297.5
65°	292.6	361.1	381.8	360.2	332.7	298.9	286.3	277.7	273.6	267.3	257.4
67.5°	220.0	269.9	292.7	277.4	267.5	246.2	238.1	233.5	229.9	225.6	217.3
70°	176.7	213.7	237.1	233.1	225.0	213.7	207.8	204.7	201.0	197.4	190.2
72.5°	142.1	167.6	189.5	191.6	184.9	182.6	177.5	176.2	174.0	169.7	165.7
75°	94.2	111.8	127.1	132.9	135.7	137.9	135.7	135.3	134.7	131.2	128.9
77.5°	61.7	71.2	80.8	90.8	95.1	98.2	98.9	100.6	99.4	97.5	96.3
80°	47.4	49.6	56.3	64.9	71.6	74.4	76.2	77.1	76.6	76.2	74.4
82.5°	34.4	36.2	39.4	45.5	51.1	55.6	56.7	56.6	57.5	57.8	56.3
85°	18.5	18.9	19.8	20.8	23.8	28.8	30.2	31.1	32.0	32.0	29.3
87.5°	8.9	8.0	8.3	7.8	8.5	8.5	10.3	11.7	12.5	11.4	11.8
90°	15.7	13.2	10.7	8.5	6.6	4.6	2.8	0.9	2.8	4.6	6.6
92.5°	30.1	28.8	27.4	26.0	24.7	23.4	22.1	20.8	22.1	23.4	24.7
95°	60.5	59.0	57.5	56.1	54.8	53.4	52.0	50.7	52.0	53.4	54.8
97.5°	97.3	96.2	95.1	94.0	93.1	92.0	91.1	90.1	91.1	92.0	93.1
100°	124.4	123.5	122.5	121.5	120.3	119.2	118.0	116.9	118.0	119.2	120.3
102.5°	154.0	152.8	151.5	150.6	149.9	149.2	148.5	147.8	148.5	149.2	149.9
105°	199.4	197.7	196.0	194.9	194.5	194.2	193.7	193.4	193.7	194.2	194.5
107.5°	249.1	248.4	247.7	247.3	247.0	246.8	246.6	246.3	246.6	246.8	247.0
110°	282.0	281.6	281.2	280.9	280.4	280.1	279.7	279.3	279.7	280.1	280.4



TEST NUMBER: P332319-935

CATALOG NUMBER: S123RDIP-S775D1025U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	315.0	314.9	314.8	314.6	314.4	314.2	313.9	313.7	313.9	314.2	314.4
115°	366.9	367.3	367.6	367.6	367.0	366.4	365.8	365.2	365.8	366.4	367.0
117.5°	417.7	418.2	418.6	418.7	418.4	417.9	417.6	417.2	417.6	417.9	418.4
120°	452.3	453.2	454.2	454.1	453.0	451.8	450.6	449.5	450.6	451.8	453.0
122.5°	485.7	486.2	486.7	486.6	485.7	484.8	484.1	483.2	484.1	484.8	485.7
125°	536.2	536.6	537.0	536.8	536.3	535.7	535.2	534.6	535.2	535.7	536.3
127.5°	586.5	586.9	587.3	586.9	585.7	584.4	583.2	582.0	583.2	584.4	585.7
130°	619.1	619.7	620.3	619.7	618.2	616.7	615.2	613.6	615.2	616.7	618.2
132.5°	651.1	651.5	651.9	651.4	649.9	648.3	646.8	645.3	646.8	648.3	649.9
135°	698.3	698.4	698.6	698.2	697.0	695.9	694.7	693.6	694.7	695.9	697.0
137.5°	743.8	743.3	742.8	742.1	741.1	740.2	739.3	738.3	739.3	740.2	741.1
140°	774.0	773.8	773.6	773.0	772.1	771.1	770.2	769.2	770.2	771.1	772.1
142.5°	802.5	802.2	801.8	801.2	800.3	799.4	798.3	797.4	798.3	799.4	800.3
145°	844.6	844.0	843.4	842.9	842.6	842.1	841.8	841.4	841.8	842.1	842.6
147.5°	884.3	883.8	883.3	882.7	882.0	881.3	880.6	879.9	880.6	881.3	882.0
150°	909.4	909.0	908.6	908.3	907.8	907.5	907.1	906.7	907.1	907.5	907.8
152.5°	931.7	931.5	931.3	930.8	930.3	929.8	929.3	928.8	929.3	929.8	930.3
155°	963.9	963.7	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5
157.5°	992.4	992.2	992.0	992.1	992.3	992.6	992.8	993.0	992.8	992.6	992.3
160°	1009.9	1009.9	1009.9	1010.0	1010.5	1010.8	1011.2	1011.6	1011.2	1010.8	1010.5
162.5°	1026.1	1025.9	1025.8	1026.0	1026.5	1027.0	1027.5	1028.1	1027.5	1027.0	1026.5
165°	1046.8	1046.8	1046.8	1047.1	1047.7	1048.3	1048.8	1049.4	1048.8	1048.3	1047.7
167.5°	1063.3	1063.2	1063.1	1063.3	1064.1	1064.9	1065.7	1066.4	1065.7	1064.9	1064.1
170°	1072.6	1072.6	1072.6	1073.0	1073.8	1074.5	1075.3	1076.1	1075.3	1074.5	1073.8
172.5°	1080.1	1080.1	1080.1	1080.6	1081.3	1082.1	1082.9	1083.6	1082.9	1082.1	1081.3
175°	1088.0	1088.0	1088.0	1088.5	1089.3	1089.9	1090.7	1091.5	1090.7	1089.9	1089.3
177.5°	1092.0	1092.0	1092.0	1092.4	1093.0	1093.6	1094.2	1094.8	1094.2	1093.6	1093.0
180°	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1



TEST NUMBER: P332319-935

CATALOG NUMBER: S123RDIP-S775D1025U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1035.0	1030.3	1027.1	1019.9	1015.1	1010.1	1005.0	1008.3	1008.0	1007.5	1007.5
5°	1000.3	989.9	980.4	968.3	960.6	951.1	943.9	943.1	944.9	938.5	934.9
7.5°	965.9	951.7	938.2	924.8	910.6	899.2	892.1	888.7	884.2	880.3	876.2
10°	941.7	925.0	911.9	895.3	879.9	866.4	857.8	852.0	848.8	845.7	839.8
12.5°	916.8	900.4	883.8	865.0	850.3	834.7	828.3	821.7	815.6	812.1	804.1
15°	880.4	859.2	841.6	821.7	805.6	790.2	781.2	768.1	766.3	761.8	753.7
17.5°	843.9	820.9	796.6	782.0	763.6	747.7	733.9	729.5	716.6	711.8	704.7
20°	815.0	793.8	775.3	756.0	729.4	714.5	703.7	697.8	687.4	681.1	676.6
22.5°	790.1	768.6	747.2	724.6	702.7	686.0	678.0	668.9	663.3	654.4	649.5
25°	754.6	731.2	705.5	681.1	665.4	652.7	640.1	632.0	623.9	619.8	610.8
27.5°	713.3	688.8	664.8	646.4	627.0	614.5	603.0	595.8	586.1	579.3	574.3
30°	690.6	661.8	641.0	624.3	599.5	587.8	579.3	570.2	563.0	555.8	550.9
32.5°	664.3	637.9	618.3	597.6	578.6	565.8	554.7	546.8	540.6	533.8	528.8
35°	622.9	600.9	580.6	559.8	545.9	532.8	519.8	513.0	507.1	500.8	496.3
37.5°	585.7	565.0	545.7	526.1	508.8	498.1	487.6	482.4	474.5	470.3	465.6
40°	562.6	542.3	521.5	502.7	484.6	476.5	467.0	459.3	452.1	449.0	444.0
42.5°	537.4	517.0	499.6	479.1	464.4	453.4	444.6	436.3	430.8	426.3	423.4
45°	499.9	481.9	464.8	444.4	430.5	421.0	411.1	403.5	398.5	395.4	390.4
47.5°	463.6	445.6	428.2	410.4	396.9	386.2	376.3	370.9	364.3	360.4	357.1
50°	437.2	421.0	402.5	386.3	372.8	362.0	353.9	347.1	341.2	336.3	334.1
52.5°	413.1	395.8	379.8	364.7	350.4	338.2	330.8	323.6	319.3	313.6	310.9
55°	373.2	356.5	343.0	328.1	314.2	303.8	294.8	288.5	284.0	277.7	274.1
57.5°	335.8	320.9	304.7	291.8	277.4	268.6	261.1	252.6	247.1	242.2	238.7
60°	310.6	293.4	279.5	267.3	254.7	243.4	236.7	229.9	224.0	219.0	215.9
62.5°	284.3	269.3	256.1	242.8	231.3	221.4	213.6	207.9	202.8	199.6	196.5
65°	243.8	232.1	218.6	207.8	197.0	189.8	183.5	178.5	174.9	172.6	170.0
67.5°	206.7	195.4	183.6	172.9	165.7	160.2	156.1	151.8	150.0	147.1	145.3
70°	182.5	170.8	160.5	152.4	145.2	141.1	138.4	135.3	133.5	129.8	128.0
72.5°	156.3	147.7	140.3	133.6	127.9	124.2	120.7	116.8	114.0	109.9	108.2
75°	123.0	115.4	109.5	105.0	101.4	96.4	91.5	87.5	86.1	84.7	84.3
77.5°	91.2	86.3	82.1	78.3	73.8	70.2	69.1	68.2	67.8	67.2	67.2
80°	71.6	67.2	64.0	59.5	56.8	56.8	56.8	55.9	56.3	56.3	56.3
82.5°	53.3	49.2	47.4	45.8	45.3	45.6	45.6	45.8	45.5	46.2	45.9
85°	27.5	28.0	28.8	28.4	28.8	28.8	29.8	29.3	29.8	28.8	29.8
87.5°	11.8	13.3	14.2	15.1	15.9	16.0	16.5	16.7	17.2	17.4	17.5
90°	8.5	10.7	13.2	15.7	18.2	20.7	21.4	22.1	22.9	23.7	24.3
92.5°	26.0	27.4	28.8	30.1	31.6	33.0	33.6	34.3	34.9	35.5	35.6
95°	56.1	57.5	59.0	60.5	62.1	63.6	64.4	65.1	65.9	66.6	67.1
97.5°	94.0	95.1	96.2	97.3	98.4	99.5	100.4	101.3	102.2	103.1	103.4
100°	121.5	122.5	123.5	124.4	125.4	126.3	126.9	127.5	128.0	128.6	129.2
102.5°	150.6	151.5	152.8	154.0	155.3	156.6	157.1	157.7	158.3	158.9	159.1
105°	194.9	196.0	197.7	199.4	201.1	202.9	202.9	202.9	202.9	202.9	203.0
107.5°	247.3	247.7	248.4	249.1	249.8	250.5	251.1	251.7	252.3	252.9	253.0
110°	280.9	281.2	281.6	282.0	282.4	282.8	283.5	284.3	285.1	285.9	286.0



TEST NUMBER: P332319-935

CATALOG NUMBER: S123RDIP-S775D1025U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	314.6	314.8	314.9	315.0	315.0	315.0	316.0	316.9	317.8	318.7	319.2
115°	367.6	367.6	367.3	366.9	366.5	366.1	366.4	366.5	366.7	366.9	366.9
117.5°	418.7	418.6	418.2	417.7	417.2	416.6	416.6	416.6	416.6	416.6	416.2
120°	454.1	454.2	453.2	452.3	451.3	450.4	450.1	450.0	449.8	449.6	449.3
122.5°	486.6	486.7	486.2	485.7	485.3	484.7	484.2	483.7	483.3	482.8	482.2
125°	536.8	537.0	536.6	536.2	535.8	535.5	534.7	533.9	533.1	532.4	531.6
127.5°	586.9	587.3	586.9	586.5	586.1	585.7	584.5	583.5	582.5	581.3	580.4
130°	619.7	620.3	619.7	619.1	618.5	617.9	617.2	616.4	615.6	614.9	613.8
132.5°	651.4	651.9	651.5	651.1	650.7	650.2	649.4	648.4	647.6	646.6	645.7
135°	698.2	698.6	698.4	698.3	698.1	697.8	697.2	696.4	695.6	694.8	694.2
137.5°	742.1	742.8	743.3	743.8	744.3	744.8	744.0	743.2	742.4	741.6	740.8
140°	773.0	773.6	773.8	774.0	774.2	774.4	774.2	774.0	773.8	773.6	772.8
142.5°	801.2	801.8	802.2	802.5	802.9	803.2	803.1	802.9	802.7	802.5	801.8
145°	842.9	843.4	844.0	844.6	845.2	845.7	845.5	845.3	845.2	844.9	844.5
147.5°	882.7	883.3	883.8	884.3	884.8	885.5	885.5	885.5	885.5	885.5	884.8
150°	908.3	908.6	909.0	909.4	909.8	910.2	910.2	910.2	910.2	910.2	909.6
152.5°	930.8	931.3	931.5	931.7	931.9	932.2	932.5	932.8	933.1	933.4	933.1
155°	963.5	963.5	963.7	963.9	964.1	964.3	965.1	965.9	966.6	967.3	967.1
157.5°	992.1	992.0	992.2	992.4	992.6	992.6	993.5	994.3	995.1	995.9	995.7
160°	1010.0	1009.9	1009.9	1009.9	1009.9	1009.9	1010.8	1011.8	1012.7	1013.7	1013.7
162.5°	1026.0	1025.8	1025.9	1026.1	1026.2	1026.4	1027.3	1028.3	1029.2	1030.2	1030.0
165°	1047.1	1046.8	1046.8	1046.8	1046.8	1046.8	1047.9	1049.1	1050.2	1051.4	1051.3
167.5°	1063.3	1063.1	1063.2	1063.3	1063.5	1063.7	1064.9	1066.0	1067.2	1068.4	1068.4
170°	1073.0	1072.6	1072.6	1072.6	1072.6	1072.6	1073.9	1075.3	1076.6	1078.0	1078.0
172.5°	1080.6	1080.1	1080.1	1080.1	1080.1	1080.1	1081.3	1082.5	1083.7	1084.9	1084.9
175°	1088.5	1088.0	1088.0	1088.0	1088.0	1088.0	1089.3	1090.4	1091.5	1092.7	1092.5
177.5°	1092.4	1092.0	1092.0	1092.0	1092.0	1092.0	1093.0	1093.9	1094.8	1095.7	1095.6
180°	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1



TEST NUMBER: P332319-935

CATALOG NUMBER: S123RDIP-S775D1025U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1003.2	1002.9	1003.2	1001.8	1003.2	1002.9	1003.2	1007.5	1007.5	1008.0	1008.3
5°	933.6	933.1	931.8	927.7	931.8	933.1	933.6	934.9	938.5	944.9	943.1
7.5°	872.7	872.1	868.1	868.2	868.1	872.1	872.7	876.2	880.3	884.2	888.7
10°	836.6	837.1	831.7	828.5	831.7	837.1	836.6	839.8	845.7	848.8	852.0
12.5°	801.7	799.6	795.2	791.8	795.2	799.6	801.7	804.1	812.1	815.6	821.7
15°	755.5	751.0	740.2	741.1	740.2	751.0	755.5	753.7	761.8	766.3	768.1
17.5°	701.1	697.8	697.6	691.3	697.6	697.8	701.1	704.7	711.8	716.6	729.5
20°	669.4	667.2	668.0	661.8	668.0	667.2	669.4	676.6	681.1	687.4	697.8
22.5°	644.5	642.3	638.5	636.5	638.5	642.3	644.5	649.5	654.4	663.3	668.9
25°	608.1	604.5	600.9	603.1	600.9	604.5	608.1	610.8	619.8	623.9	632.0
27.5°	571.7	568.9	565.3	564.9	565.3	568.9	571.7	574.3	579.3	586.1	595.8
30°	548.6	545.9	544.1	541.8	544.1	545.9	548.6	550.9	555.8	563.0	570.2
32.5°	525.1	524.6	521.3	520.9	521.3	524.6	525.1	528.8	533.8	540.6	546.8
35°	494.5	491.8	490.9	491.4	490.9	491.8	494.5	496.3	500.8	507.1	513.0
37.5°	465.4	461.8	460.1	458.6	460.1	461.8	465.4	465.6	470.3	474.5	482.4
40°	444.4	440.8	440.0	439.0	440.0	440.8	444.4	444.0	449.0	452.1	459.3
42.5°	421.0	419.6	419.0	417.4	419.0	419.6	421.0	423.4	426.3	430.8	436.3
45°	389.0	388.6	385.9	386.8	385.9	388.6	389.0	390.4	395.4	398.5	403.5
47.5°	355.3	353.4	351.5	352.7	351.5	353.4	355.3	357.1	360.4	364.3	370.9
50°	332.3	331.3	327.3	328.1	327.3	331.3	332.3	334.1	336.3	341.2	347.1
52.5°	309.2	305.7	304.2	303.7	304.2	305.7	309.2	310.9	313.6	319.3	323.6
55°	271.0	266.8	265.0	264.2	265.0	266.8	271.0	274.1	277.7	284.0	288.5
57.5°	233.4	232.3	230.9	231.9	230.9	232.3	233.4	238.7	242.2	247.1	252.6
60°	211.4	211.4	211.4	210.9	211.4	211.4	211.4	215.9	219.0	224.0	229.9
62.5°	194.5	193.4	193.0	193.6	193.0	193.4	194.5	196.5	199.6	202.8	207.9
65°	168.6	168.2	166.3	165.9	166.3	168.2	168.6	170.0	172.6	174.9	178.5
67.5°	144.1	142.5	142.0	141.4	142.0	142.5	144.1	145.3	147.1	150.0	151.8
70°	125.8	124.8	122.2	122.6	122.2	124.8	125.8	128.0	129.8	133.5	135.3
72.5°	105.9	105.0	104.5	103.8	104.5	105.0	105.9	108.2	109.9	114.0	116.8
75°	83.9	83.4	82.9	84.7	82.9	83.4	83.9	84.3	84.7	86.1	87.5
77.5°	67.2	67.2	67.4	66.7	67.4	67.2	67.2	67.2	67.2	67.8	68.2
80°	56.3	56.3	55.9	55.9	55.9	56.3	56.3	56.3	56.3	56.3	55.9
82.5°	45.2	45.5	45.8	45.1	45.8	45.5	45.2	45.9	46.2	45.5	45.8
85°	29.8	29.3	30.2	29.8	30.2	29.3	29.8	29.8	28.8	29.8	29.3
87.5°	18.3	17.7	17.7	18.2	17.7	17.7	18.3	17.5	17.4	17.2	16.7
90°	24.6	25.1	25.4	25.7	25.4	25.1	24.6	24.3	23.7	22.9	22.1
92.5°	35.4	35.2	35.0	34.7	35.0	35.2	35.4	35.6	35.5	34.9	34.3
95°	67.1	67.1	67.1	67.1	67.1	67.1	67.1	67.1	66.6	65.9	65.1
97.5°	103.4	103.3	103.2	103.1	103.2	103.3	103.4	103.4	103.1	102.2	101.3
100°	129.5	129.8	130.3	130.6	130.3	129.8	129.5	129.2	128.6	128.0	127.5
102.5°	159.0	158.9	158.9	158.9	158.9	158.9	159.0	159.1	158.9	158.3	157.7
105°	203.4	203.8	204.1	204.6	204.1	203.8	203.4	203.0	202.9	202.9	202.9
107.5°	252.9	252.6	252.4	252.2	252.4	252.6	252.9	253.0	252.9	252.3	251.7
110°	285.6	285.2	284.9	284.5	284.9	285.2	285.6	286.0	285.9	285.1	284.3



TEST NUMBER: P332319-935

CATALOG NUMBER: S123RDIP-S775D1025U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	319.1	319.0	318.9	318.8	318.9	319.0	319.1	319.2	318.7	317.8	316.9
115°	366.7	366.5	366.4	366.1	366.4	366.5	366.7	366.9	366.9	366.7	366.5
117.5°	415.7	415.2	414.7	414.1	414.7	415.2	415.7	416.2	416.6	416.6	416.6
120°	448.9	448.6	448.2	447.8	448.2	448.6	448.9	449.3	449.6	449.8	450.0
122.5°	481.7	481.1	480.6	480.1	480.6	481.1	481.7	482.2	482.8	483.3	483.7
125°	530.9	530.1	529.3	528.6	529.3	530.1	530.9	531.6	532.4	533.1	533.9
127.5°	579.5	578.6	577.7	576.9	577.7	578.6	579.5	580.4	581.3	582.5	583.5
130°	612.5	611.1	609.8	608.5	609.8	611.1	612.5	613.8	614.9	615.6	616.4
132.5°	644.6	643.6	642.6	641.5	642.6	643.6	644.6	645.7	646.6	647.6	648.4
135°	693.9	693.4	693.1	692.8	693.1	693.4	693.9	694.2	694.8	695.6	696.4
137.5°	740.1	739.3	738.7	738.0	738.7	739.3	740.1	740.8	741.6	742.4	743.2
140°	771.5	770.2	768.9	767.5	768.9	770.2	771.5	772.8	773.6	773.8	774.0
142.5°	800.8	799.8	798.7	797.7	798.7	799.8	800.8	801.8	802.5	802.7	802.9
145°	843.7	842.9	842.1	841.4	842.1	842.9	843.7	844.5	844.9	845.2	845.3
147.5°	883.7	882.5	881.4	880.3	881.4	882.5	883.7	884.8	885.5	885.5	885.5
150°	908.4	907.3	906.1	905.0	906.1	907.3	908.4	909.6	910.2	910.2	910.2
152.5°	932.0	931.1	930.1	929.1	930.1	931.1	932.0	933.1	933.4	933.1	932.8
155°	965.8	964.4	963.0	961.7	963.0	964.4	965.8	967.1	967.3	966.6	965.9
157.5°	994.7	993.6	992.6	991.4	992.6	993.6	994.7	995.7	995.9	995.1	994.3
160°	1013.1	1012.3	1011.5	1010.7	1011.5	1012.3	1013.1	1013.7	1013.7	1012.7	1011.8
162.5°	1028.8	1027.6	1026.4	1025.2	1026.4	1027.6	1028.8	1030.0	1030.2	1029.2	1028.3
165°	1050.0	1048.6	1047.3	1045.9	1047.3	1048.6	1050.0	1051.3	1051.4	1050.2	1049.1
167.5°	1067.2	1066.0	1064.9	1063.7	1064.9	1066.0	1067.2	1068.4	1068.4	1067.2	1066.0
170°	1076.6	1075.3	1073.9	1072.6	1073.9	1075.3	1076.6	1078.0	1078.0	1076.6	1075.3
172.5°	1083.5	1082.2	1080.8	1079.4	1080.8	1082.2	1083.5	1084.9	1084.9	1083.7	1082.5
175°	1091.2	1089.9	1088.6	1087.2	1088.6	1089.9	1091.2	1092.5	1092.7	1091.5	1090.4
177.5°	1094.6	1093.5	1092.4	1091.3	1092.4	1093.5	1094.6	1095.6	1095.7	1094.8	1093.9
180°	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1



TEST NUMBER: P332319-935

CATALOG NUMBER: S123RDIP-S775D1025U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1005.0	1010.1	1015.1	1019.9	1027.1	1030.3	1035.0	1036.8	1042.2	1050.2	1056.6
5°	943.9	951.1	960.6	968.3	980.4	989.9	1000.3	1010.2	1021.9	1038.6	1053.4
7.5°	892.1	899.2	910.6	924.8	938.2	951.7	965.9	979.4	996.1	1020.0	1043.7
10°	857.8	866.4	879.9	895.3	911.9	925.0	941.7	958.8	979.6	1007.0	1035.4
12.5°	828.3	834.7	850.3	865.0	883.8	900.4	916.8	936.8	960.4	989.7	1023.9
15°	781.2	790.2	805.6	821.7	841.6	859.2	880.4	904.7	927.7	963.8	1005.2
17.5°	733.9	747.7	763.6	782.0	796.6	820.9	843.9	868.8	897.2	935.4	980.9
20°	703.7	714.5	729.4	756.0	775.3	793.8	815.0	846.1	872.3	915.5	962.9
22.5°	678.0	686.0	702.7	724.6	747.2	768.6	790.1	819.8	852.0	893.2	944.4
25°	640.1	652.7	665.4	681.1	705.5	731.2	754.6	779.8	814.1	857.8	913.3
27.5°	603.0	614.5	627.0	646.4	664.8	688.8	713.3	742.3	779.0	825.3	881.6
30°	579.3	587.8	599.5	624.3	641.0	661.8	690.6	716.3	750.5	799.7	859.2
32.5°	554.7	565.8	578.6	597.6	618.3	637.9	664.3	692.2	727.1	775.5	836.5
35°	519.8	532.8	545.9	559.8	580.6	600.9	622.9	653.6	689.2	736.2	796.1
37.5°	487.6	498.1	508.8	526.1	545.7	565.0	585.7	615.9	649.4	700.0	754.9
40°	467.0	476.5	484.6	502.7	521.5	542.3	562.6	589.2	625.3	672.5	725.7
42.5°	444.6	453.4	464.4	479.1	499.6	517.0	537.4	562.5	596.4	644.5	691.1
45°	411.1	421.0	430.5	444.4	464.8	481.9	499.9	523.8	558.5	598.2	639.6
47.5°	376.3	386.2	396.9	410.4	428.2	445.6	463.6	484.7	516.4	555.3	583.3
50°	353.9	362.0	372.8	386.3	402.5	421.0	437.2	460.2	490.4	521.1	545.4
52.5°	330.8	338.2	350.4	364.7	379.8	395.8	413.1	432.8	460.1	489.0	508.3
55°	294.8	303.8	314.2	328.1	343.0	356.5	373.2	393.6	415.2	436.8	449.9
57.5°	261.1	268.6	277.4	291.8	304.7	320.9	335.8	351.6	371.6	388.0	396.5
60°	236.7	243.4	254.7	267.3	279.5	293.4	310.6	326.4	341.7	354.7	361.5
62.5°	213.6	221.4	231.3	242.8	256.1	269.3	284.3	297.5	311.0	322.3	326.9
65°	183.5	189.8	197.0	207.8	218.6	232.1	243.8	257.4	267.3	273.6	277.7
67.5°	156.1	160.2	165.7	172.9	183.6	195.4	206.7	217.3	225.6	229.9	233.5
70°	138.4	141.1	145.2	152.4	160.5	170.8	182.5	190.2	197.4	201.0	204.7
72.5°	120.7	124.2	127.9	133.6	140.3	147.7	156.3	165.7	169.7	174.0	176.2
75°	91.5	96.4	101.4	105.0	109.5	115.4	123.0	128.9	131.2	134.7	135.3
77.5°	69.1	70.2	73.8	78.3	82.1	86.3	91.2	96.3	97.5	99.4	100.6
80°	56.8	56.8	56.8	59.5	64.0	67.2	71.6	74.4	76.2	76.6	77.1
82.5°	45.6	45.6	45.3	45.8	47.4	49.2	53.3	56.3	57.8	57.5	56.6
85°	29.8	28.8	28.8	28.4	28.8	28.0	27.5	29.3	32.0	32.0	31.1
87.5°	16.5	16.0	15.9	15.1	14.2	13.3	11.8	11.8	11.4	12.5	11.7
90°	21.4	20.7	18.2	15.7	13.2	10.7	8.5	6.6	4.6	2.8	0.9
92.5°	33.6	33.0	31.6	30.1	28.8	27.4	26.0	24.7	23.4	22.1	20.8
95°	64.4	63.6	62.1	60.5	59.0	57.5	56.1	54.8	53.4	52.0	50.7
97.5°	100.4	99.5	98.4	97.3	96.2	95.1	94.0	93.1	92.0	91.1	90.1
100°	126.9	126.3	125.4	124.4	123.5	122.5	121.5	120.3	119.2	118.0	116.9
102.5°	157.1	156.6	155.3	154.0	152.8	151.5	150.6	149.9	149.2	148.5	147.8
105°	202.9	202.9	201.1	199.4	197.7	196.0	194.9	194.5	194.2	193.7	193.4
107.5°	251.1	250.5	249.8	249.1	248.4	247.7	247.3	247.0	246.8	246.6	246.3
110°	283.5	282.8	282.4	282.0	281.6	281.2	280.9	280.4	280.1	279.7	279.3



TEST NUMBER: P332319-935

CATALOG NUMBER: S123RDIP-S775D1025U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	316.0	315.0	315.0	315.0	314.9	314.8	314.6	314.4	314.2	313.9	313.7
115°	366.4	366.1	366.5	366.9	367.3	367.6	367.6	367.0	366.4	365.8	365.2
117.5°	416.6	416.6	417.2	417.7	418.2	418.6	418.7	418.4	417.9	417.6	417.2
120°	450.1	450.4	451.3	452.3	453.2	454.2	454.1	453.0	451.8	450.6	449.5
122.5°	484.2	484.7	485.3	485.7	486.2	486.7	486.6	485.7	484.8	484.1	483.2
125°	534.7	535.5	535.8	536.2	536.6	537.0	536.8	536.3	535.7	535.2	534.6
127.5°	584.5	585.7	586.1	586.5	586.9	587.3	586.9	585.7	584.4	583.2	582.0
130°	617.2	617.9	618.5	619.1	619.7	620.3	619.7	618.2	616.7	615.2	613.6
132.5°	649.4	650.2	650.7	651.1	651.5	651.9	651.4	649.9	648.3	646.8	645.3
135°	697.2	697.8	698.1	698.3	698.4	698.6	698.2	697.0	695.9	694.7	693.6
137.5°	744.0	744.8	744.3	743.8	743.3	742.8	742.1	741.1	740.2	739.3	738.3
140°	774.2	774.4	774.2	774.0	773.8	773.6	773.0	772.1	771.1	770.2	769.2
142.5°	803.1	803.2	802.9	802.5	802.2	801.8	801.2	800.3	799.4	798.3	797.4
145°	845.5	845.7	845.2	844.6	844.0	843.4	842.9	842.6	842.1	841.8	841.4
147.5°	885.5	885.5	884.8	884.3	883.8	883.3	882.7	882.0	881.3	880.6	879.9
150°	910.2	910.2	909.8	909.4	909.0	908.6	908.3	907.8	907.5	907.1	906.7
152.5°	932.5	932.2	931.9	931.7	931.5	931.3	930.8	930.3	929.8	929.3	928.8
155°	965.1	964.3	964.1	963.9	963.7	963.5	963.5	963.5	963.5	963.5	963.5
157.5°	993.5	992.6	992.6	992.4	992.2	992.0	992.1	992.3	992.6	992.8	993.0
160°	1010.8	1009.9	1009.9	1009.9	1009.9	1009.9	1010.0	1010.5	1010.8	1011.2	1011.6
162.5°	1027.3	1026.4	1026.2	1026.1	1025.9	1025.8	1026.0	1026.5	1027.0	1027.5	1028.1
165°	1047.9	1046.8	1046.8	1046.8	1046.8	1046.8	1047.1	1047.7	1048.3	1048.8	1049.4
167.5°	1064.9	1063.7	1063.5	1063.3	1063.2	1063.1	1063.3	1064.1	1064.9	1065.7	1066.4
170°	1073.9	1072.6	1072.6	1072.6	1072.6	1072.6	1073.0	1073.8	1074.5	1075.3	1076.1
172.5°	1081.3	1080.1	1080.1	1080.1	1080.1	1080.1	1080.6	1081.3	1082.1	1082.9	1083.6
175°	1089.3	1088.0	1088.0	1088.0	1088.0	1088.0	1088.5	1089.3	1089.9	1090.7	1091.5
177.5°	1093.0	1092.0	1092.0	1092.0	1092.0	1092.0	1092.4	1093.0	1093.6	1094.2	1094.8
180°	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1



TEST NUMBER: P332319-935

CATALOG NUMBER: S123RDIP-S775D1025U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1058.8	1062.7	1067.8	1075.4	1081.2	1086.2	1087.3	1088.7	1092.4	1098.5	1103.1
5°	1065.7	1076.0	1092.7	1108.9	1126.5	1140.9	1154.4	1163.9	1172.9	1191.9	1207.2
7.5°	1063.5	1086.6	1112.7	1141.9	1171.3	1199.9	1226.4	1250.1	1273.7	1301.3	1332.7
10°	1062.0	1089.1	1124.2	1161.7	1202.6	1242.8	1281.6	1311.7	1346.9	1378.5	1418.6
12.5°	1055.2	1094.2	1136.2	1184.0	1234.4	1280.7	1331.7	1373.5	1413.7	1459.2	1505.9
15°	1046.3	1093.6	1146.8	1210.3	1286.9	1342.9	1395.2	1467.7	1517.3	1566.9	1633.6
17.5°	1029.9	1087.7	1154.2	1236.7	1300.7	1375.8	1454.5	1511.8	1578.6	1648.5	1708.9
20°	1016.9	1084.1	1158.5	1239.7	1321.2	1402.8	1479.0	1547.5	1616.5	1697.2	1746.8
22.5°	1004.0	1070.4	1147.7	1233.9	1321.5	1407.5	1493.7	1574.2	1651.8	1733.3	1796.6
25°	976.4	1055.2	1139.1	1227.0	1313.5	1408.3	1511.0	1600.7	1696.7	1780.5	1840.6
27.5°	948.4	1020.7	1104.2	1193.3	1289.6	1401.4	1522.3	1624.4	1720.5	1780.5	1799.4
30°	923.2	999.8	1076.4	1167.1	1271.2	1396.0	1524.5	1641.2	1720.2	1746.3	1726.9
32.5°	897.6	967.0	1042.9	1135.7	1246.3	1382.7	1527.4	1631.2	1678.7	1658.7	1579.8
35°	852.4	915.1	988.5	1081.4	1208.5	1375.4	1515.5	1585.8	1574.1	1461.4	1312.7
37.5°	804.1	855.1	923.2	1020.3	1169.4	1346.0	1464.3	1474.6	1373.2	1200.2	1028.4
40°	765.9	811.8	881.8	983.2	1139.1	1317.2	1412.7	1370.8	1213.5	1021.0	877.7
42.5°	728.8	767.5	834.8	944.2	1110.3	1277.9	1335.9	1244.6	1063.1	881.1	750.7
45°	665.8	702.3	769.9	882.2	1051.2	1202.6	1195.0	1036.3	854.7	708.2	599.9
47.5°	606.1	638.0	701.5	816.1	981.9	1089.9	1018.3	849.5	695.3	577.8	500.7
50°	564.0	595.5	658.6	771.7	926.3	1005.2	902.9	740.2	599.1	501.7	440.4
52.5°	523.6	554.4	612.1	722.3	859.3	906.5	796.5	645.7	528.1	444.0	391.3
55°	467.0	490.4	542.3	647.7	750.1	761.0	649.5	523.3	426.5	367.8	331.7
57.5°	409.4	429.6	480.8	564.8	636.6	631.0	525.5	416.2	350.9	307.5	281.3
60°	371.9	391.8	436.8	508.9	563.0	544.1	447.2	359.3	303.3	271.4	250.6
62.5°	336.9	352.4	394.6	447.3	486.2	464.8	382.3	309.5	265.2	238.2	221.8
65°	286.3	298.9	332.7	360.2	381.8	361.1	292.6	242.0	210.1	191.1	179.9
67.5°	238.1	246.2	267.5	277.4	292.7	269.9	220.0	186.1	168.0	152.0	144.1
70°	207.8	213.7	225.0	233.1	237.1	213.7	176.7	151.9	136.6	125.3	120.4
72.5°	177.5	182.6	184.9	191.6	189.5	167.6	142.1	122.3	111.3	103.7	97.3
75°	135.7	137.9	135.7	132.9	127.1	111.8	94.2	84.3	76.2	72.6	70.3
77.5°	98.9	98.2	95.1	90.8	80.8	71.2	61.7	58.5	54.9	53.0	52.2
80°	76.2	74.4	71.6	64.9	56.3	49.6	47.4	45.1	43.7	41.5	41.0
82.5°	56.7	55.6	51.1	45.5	39.4	36.2	34.4	33.6	32.2	31.0	30.9
85°	30.2	28.8	23.8	20.8	19.8	18.9	18.5	18.5	16.7	16.2	16.2
87.5°	10.3	8.5	8.5	7.8	8.3	8.0	8.9	8.7	8.8	9.3	8.8
90°	2.8	4.6	6.6	8.5	10.7	13.2	15.7	18.2	20.7	21.4	22.1
92.5°	22.1	23.4	24.7	26.0	27.4	28.8	30.1	31.6	33.0	33.6	34.3
95°	52.0	53.4	54.8	56.1	57.5	59.0	60.5	62.1	63.6	64.4	65.1
97.5°	91.1	92.0	93.1	94.0	95.1	96.2	97.3	98.4	99.5	100.4	101.3
100°	118.0	119.2	120.3	121.5	122.5	123.5	124.4	125.4	126.3	126.9	127.5
102.5°	148.5	149.2	149.9	150.6	151.5	152.8	154.0	155.3	156.6	157.1	157.7
105°	193.7	194.2	194.5	194.9	196.0	197.7	199.4	201.1	202.9	202.9	202.9
107.5°	246.6	246.8	247.0	247.3	247.7	248.4	249.1	249.8	250.5	251.1	251.7
110°	279.7	280.1	280.4	280.9	281.2	281.6	282.0	282.4	282.8	283.5	284.3



TEST NUMBER: P332319-935

CATALOG NUMBER: S123RDIP-S775D1025U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	313.9	314.2	314.4	314.6	314.8	314.9	315.0	315.0	315.0	316.0	316.9
115°	365.8	366.4	367.0	367.6	367.6	367.3	366.9	366.5	366.1	366.4	366.5
117.5°	417.6	417.9	418.4	418.7	418.6	418.2	417.7	417.2	416.6	416.6	416.6
120°	450.6	451.8	453.0	454.1	454.2	453.2	452.3	451.3	450.4	450.1	450.0
122.5°	484.1	484.8	485.7	486.6	486.7	486.2	485.7	485.3	484.7	484.2	483.7
125°	535.2	535.7	536.3	536.8	537.0	536.6	536.2	535.8	535.5	534.7	533.9
127.5°	583.2	584.4	585.7	586.9	587.3	586.9	586.5	586.1	585.7	584.5	583.5
130°	615.2	616.7	618.2	619.7	620.3	619.7	619.1	618.5	617.9	617.2	616.4
132.5°	646.8	648.3	649.9	651.4	651.9	651.5	651.1	650.7	650.2	649.4	648.4
135°	694.7	695.9	697.0	698.2	698.6	698.4	698.3	698.1	697.8	697.2	696.4
137.5°	739.3	740.2	741.1	742.1	742.8	743.3	743.8	744.3	744.8	744.0	743.2
140°	770.2	771.1	772.1	773.0	773.6	773.8	774.0	774.2	774.4	774.2	774.0
142.5°	798.3	799.4	800.3	801.2	801.8	802.2	802.5	802.9	803.2	803.1	802.9
145°	841.8	842.1	842.6	842.9	843.4	844.0	844.6	845.2	845.7	845.5	845.3
147.5°	880.6	881.3	882.0	882.7	883.3	883.8	884.3	884.8	885.5	885.5	885.5
150°	907.1	907.5	907.8	908.3	908.6	909.0	909.4	909.8	910.2	910.2	910.2
152.5°	929.3	929.8	930.3	930.8	931.3	931.5	931.7	931.9	932.2	932.5	932.8
155°	963.5	963.5	963.5	963.5	963.5	963.7	963.9	964.1	964.3	965.1	965.9
157.5°	992.8	992.6	992.3	992.1	992.0	992.2	992.4	992.6	992.6	993.5	994.3
160°	1011.2	1010.8	1010.5	1010.0	1009.9	1009.9	1009.9	1009.9	1009.9	1010.8	1011.8
162.5°	1027.5	1027.0	1026.5	1026.0	1025.8	1025.9	1026.1	1026.2	1026.4	1027.3	1028.3
165°	1048.8	1048.3	1047.7	1047.1	1046.8	1046.8	1046.8	1046.8	1046.8	1047.9	1049.1
167.5°	1065.7	1064.9	1064.1	1063.3	1063.1	1063.2	1063.3	1063.5	1063.7	1064.9	1066.0
170°	1075.3	1074.5	1073.8	1073.0	1072.6	1072.6	1072.6	1072.6	1072.6	1073.9	1075.3
172.5°	1082.9	1082.1	1081.3	1080.6	1080.1	1080.1	1080.1	1080.1	1080.1	1081.3	1082.5
175°	1090.7	1089.9	1089.3	1088.5	1088.0	1088.0	1088.0	1088.0	1088.0	1089.3	1090.4
177.5°	1094.2	1093.6	1093.0	1092.4	1092.0	1092.0	1092.0	1092.0	1092.0	1093.0	1093.9
180°	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1



TEST NUMBER: P332319-935

CATALOG NUMBER: S123RDIP-S775D1025U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1110.7	1110.7	1112.2	1117.6	1118.3	1123.0	1121.5
5°	1220.7	1229.2	1232.4	1246.0	1254.0	1257.7	1250.4
7.5°	1355.2	1379.4	1390.9	1405.0	1417.6	1421.3	1411.4
10°	1453.3	1478.5	1499.8	1512.8	1525.0	1533.1	1543.4
12.5°	1548.2	1579.2	1599.3	1617.7	1630.3	1640.5	1642.3
15°	1651.2	1698.1	1733.7	1759.8	1772.9	1779.7	1776.9
17.5°	1755.1	1798.6	1823.9	1850.6	1868.7	1869.7	1870.2
20°	1814.0	1856.3	1885.6	1905.4	1925.7	1924.9	1929.3
22.5°	1853.2	1886.6	1909.0	1923.5	1930.4	1927.0	1927.9
25°	1871.6	1881.5	1877.5	1854.5	1848.7	1827.5	1831.1
27.5°	1776.8	1729.9	1681.4	1619.0	1569.8	1530.5	1532.5
30°	1648.0	1565.1	1470.4	1391.1	1319.9	1300.0	1257.7
32.5°	1468.1	1343.7	1232.8	1158.8	1097.7	1081.2	1044.2
35°	1163.0	1042.2	928.2	859.6	832.6	794.7	794.3
37.5°	904.0	797.6	737.3	685.9	658.9	636.0	633.8
40°	760.4	677.5	632.0	595.0	568.4	551.3	547.3
42.5°	660.2	593.1	550.5	527.6	507.1	498.3	491.7
45°	539.2	494.0	464.3	443.6	434.1	427.3	423.7
47.5°	451.0	420.8	400.5	386.7	379.0	371.9	373.8
50°	403.0	378.2	363.3	350.3	344.4	339.4	339.9
52.5°	364.4	342.2	330.1	320.7	313.4	309.9	308.2
55°	309.3	295.2	283.1	276.3	272.2	267.3	266.0
57.5°	263.8	253.0	243.1	235.4	234.4	229.6	230.2
60°	233.5	224.5	216.4	212.3	209.1	205.1	206.5
62.5°	208.6	201.0	193.6	190.3	187.2	184.2	184.9
65°	170.8	163.6	159.1	157.3	155.9	154.6	153.3
67.5°	136.1	131.7	128.9	125.0	122.3	121.8	120.5
70°	114.5	108.7	103.7	98.8	97.4	96.9	97.4
72.5°	91.8	88.1	86.7	84.3	84.0	82.8	83.7
75°	69.0	67.6	66.7	64.9	64.9	64.9	64.9
77.5°	50.9	50.0	49.5	49.2	48.6	48.0	48.0
80°	39.7	39.2	38.3	38.3	37.9	38.3	37.9
82.5°	30.0	29.9	28.9	28.9	28.5	28.2	28.5
85°	15.3	14.9	15.8	14.9	15.3	14.5	15.3
87.5°	8.9	9.0	8.8	8.9	8.6	9.4	8.8
90°	22.9	23.7	24.3	24.6	25.1	25.4	25.7
92.5°	34.9	35.5	35.6	35.4	35.2	35.0	34.7
95°	65.9	66.6	67.1	67.1	67.1	67.1	67.1
97.5°	102.2	103.1	103.4	103.4	103.3	103.2	103.1
100°	128.0	128.6	129.2	129.5	129.8	130.3	130.6
102.5°	158.3	158.9	159.1	159.0	158.9	158.9	158.9
105°	202.9	202.9	203.0	203.4	203.8	204.1	204.6
107.5°	252.3	252.9	253.0	252.9	252.6	252.4	252.2
110°	285.1	285.9	286.0	285.6	285.2	284.9	284.5



TEST NUMBER: P332319-935

CATALOG NUMBER: S123RDIP-S775D1025U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	317.8	318.7	319.2	319.1	319.0	318.9	318.8
115°	366.7	366.9	366.9	366.7	366.5	366.4	366.1
117.5°	416.6	416.6	416.2	415.7	415.2	414.7	414.1
120°	449.8	449.6	449.3	448.9	448.6	448.2	447.8
122.5°	483.3	482.8	482.2	481.7	481.1	480.6	480.1
125°	533.1	532.4	531.6	530.9	530.1	529.3	528.6
127.5°	582.5	581.3	580.4	579.5	578.6	577.7	576.9
130°	615.6	614.9	613.8	612.5	611.1	609.8	608.5
132.5°	647.6	646.6	645.7	644.6	643.6	642.6	641.5
135°	695.6	694.8	694.2	693.9	693.4	693.1	692.8
137.5°	742.4	741.6	740.8	740.1	739.3	738.7	738.0
140°	773.8	773.6	772.8	771.5	770.2	768.9	767.5
142.5°	802.7	802.5	801.8	800.8	799.8	798.7	797.7
145°	845.2	844.9	844.5	843.7	842.9	842.1	841.4
147.5°	885.5	885.5	884.8	883.7	882.5	881.4	880.3
150°	910.2	910.2	909.6	908.4	907.3	906.1	905.0
152.5°	933.1	933.4	933.1	932.0	931.1	930.1	929.1
155°	966.6	967.3	967.1	965.8	964.4	963.0	961.7
157.5°	995.1	995.9	995.7	994.7	993.6	992.6	991.4
160°	1012.7	1013.7	1013.7	1013.1	1012.3	1011.5	1010.7
162.5°	1029.2	1030.2	1030.0	1028.8	1027.6	1026.4	1025.2
165°	1050.2	1051.4	1051.3	1050.0	1048.6	1047.3	1045.9
167.5°	1067.2	1068.4	1068.4	1067.2	1066.0	1064.9	1063.7
170°	1076.6	1078.0	1078.0	1076.6	1075.3	1073.9	1072.6
172.5°	1083.7	1084.9	1084.9	1083.5	1082.2	1080.8	1079.4
175°	1091.5	1092.7	1092.5	1091.2	1089.9	1088.6	1087.2
177.5°	1094.8	1095.7	1095.6	1094.6	1093.5	1092.4	1091.3
180°	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1

(END OF REPORT)