

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332326-935

Luminaire Tested: **S123RDIP-S775D1195U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332326-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D1195U935-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6343.6 lumens
Efficiency: N/A
Efficacy: 111.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332326-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332326-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41
1	96	92	89	85	88	84	81	78	70	67	65	56	54	53	43	42	42	36
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36	31
3	81	72	65	59	73	66	60	55	55	50	47	44	41	39	35	33	31	27
4	74	64	56	50	67	59	52	47	49	44	40	40	36	34	31	29	27	23
5	68	57	49	43	62	52	46	41	44	39	35	36	32	29	28	26	24	20
6	63	51	43	38	57	47	40	35	40	34	31	33	29	26	26	23	21	18
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19	16
8	54	42	35	29	49	39	32	28	33	28	24	27	23	21	22	19	17	15
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	20	18	16	13
10	47	35	28	24	43	33	26	22	28	23	19	23	19	17	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11334	11334	11334	11334
5°	13511	11382	10024	11382
10°	16869	11317	9055	11317
15°	19801	11202	8259	11202
20°	22100	11030	7581	11030
25°	21747	10847	7163	10847
30°	15632	10679	6734	10679
35°	10437	10461	6457	10461
40°	7690	10197	6169	10197
45°	6450	9736	5888	9736
50°	5692	9133	5494	9133
55°	4992	8443	4958	8443
60°	4445	7782	4540	7782
65°	3904	7073	4225	7073
70°	3065	6442	3858	6442
75°	2699	5627	3523	5627
80°	2349	4779	3465	4779
85°	1890	3841	3680	3841



TEST NUMBER: P332326-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.6	1.6
10°-20°	323.5	5.1
20°-30°	508.3	8.0
30°-40°	530.3	8.4
40°-50°	453.8	7.2
50°-60°	345.9	5.5
60°-70°	221.7	3.5
70°-80°	106.6	1.7
80°-90°	32.0	0.5
90°-100°	275.0	4.3
100°-110°	778.7	12.3
110°-120°	766.1	12.1
120°-130°	611.0	9.6
130°-140°	481.8	7.6
140°-150°	359.6	5.7
150°-160°	250.6	4.0
160°-170°	147.2	2.3
170°-180°	47.9	0.8
0°-30°	935.3	14.7
0°-40°	1465.6	23.1
0°-60°	2265.3	35.7
0°-90°	2625.6	41.4
90°-120°	1819.8	28.7
90°-150°	3272.2	51.6
90°-180°	3718.0	58.6
0°-180°	6343.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1053	1053	1053	1053	1053	
5°	1250	1053	928	1053	1250	129
15°	1777	1005	741	1005	1777	504
25°	1831	913	603	913	1831	787
35°	794	796	491	796	794	521
45°	424	640	387	640	424	333
55°	266	450	264	450	266	240
65°	153	278	166	278	153	151
75°	65	135	85	135	65	70
85°	15	31	30	31	15	18
90°	29	2	29	2	29	16
95°	116	34	116	34	116	209
105°	1272	116	1272	116	1272	1255
115°	1548	205	1548	205	1548	1504
125°	1220	285	1220	285	1220	1106
135°	989	334	989	334	989	767
145°	773	381	773	381	773	492
155°	641	433	641	433	641	299
165°	559	473	559	473	559	160
175°	503	493	503	493	503	49
180°	494	494	494	494	494	



TEST NUMBER: P332326-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1121.5	1123.0	1118.3	1117.6	1112.2	1110.7	1110.7	1103.1	1098.5	1092.4	1088.7
5°	1250.4	1257.7	1254.0	1246.0	1232.4	1229.2	1220.7	1207.2	1191.9	1172.9	1163.9
7.5°	1411.4	1421.3	1417.6	1405.0	1390.9	1379.4	1355.2	1332.7	1301.3	1273.7	1250.1
10°	1543.4	1533.1	1525.0	1512.8	1499.8	1478.5	1453.3	1418.6	1378.5	1346.9	1311.7
12.5°	1642.3	1640.5	1630.3	1617.7	1599.3	1579.2	1548.2	1505.9	1459.2	1413.7	1373.5
15°	1776.9	1779.7	1772.9	1759.8	1733.7	1698.1	1651.2	1633.6	1566.9	1517.3	1467.7
17.5°	1870.2	1869.7	1868.7	1850.6	1823.9	1798.6	1755.1	1708.9	1648.5	1578.6	1511.8
20°	1929.3	1924.9	1925.7	1905.4	1885.6	1856.3	1814.0	1746.8	1697.2	1616.5	1547.5
22.5°	1927.9	1927.0	1930.4	1923.5	1909.0	1886.6	1853.2	1796.6	1733.3	1651.8	1574.2
25°	1831.1	1827.5	1848.7	1854.5	1877.5	1881.5	1871.6	1840.6	1780.5	1696.7	1600.7
27.5°	1532.5	1530.5	1569.8	1619.0	1681.4	1729.9	1776.8	1799.4	1780.5	1720.5	1624.4
30°	1257.7	1300.0	1319.9	1391.1	1470.4	1565.1	1648.0	1726.9	1746.3	1720.2	1641.2
32.5°	1044.2	1081.2	1097.7	1158.8	1232.8	1343.7	1468.1	1579.8	1658.7	1678.7	1631.2
35°	794.3	794.7	832.6	859.6	928.2	1042.2	1163.0	1312.7	1461.4	1574.1	1585.8
37.5°	633.8	636.0	658.9	685.9	737.3	797.6	904.0	1028.4	1200.2	1373.2	1474.6
40°	547.3	551.3	568.4	595.0	632.0	677.5	760.4	877.7	1021.0	1213.5	1370.8
42.5°	491.7	498.3	507.1	527.6	550.5	593.1	660.2	750.7	881.1	1063.1	1244.6
45°	423.7	427.3	434.1	443.6	464.3	494.0	539.2	599.9	708.2	854.7	1036.3
47.5°	373.8	371.9	379.0	386.7	400.5	420.8	451.0	500.7	577.8	695.3	849.5
50°	339.9	339.4	344.4	350.3	363.3	378.2	403.0	440.4	501.7	599.1	740.2
52.5°	308.2	309.9	313.4	320.7	330.1	342.2	364.4	391.3	444.0	528.1	645.7
55°	266.0	267.3	272.2	276.3	283.1	295.2	309.3	331.7	367.8	426.5	523.3
57.5°	230.2	229.6	234.4	235.4	243.1	253.0	263.8	281.3	307.5	350.9	416.2
60°	206.5	205.1	209.1	212.3	216.4	224.5	233.5	250.6	271.4	303.3	359.3
62.5°	184.9	184.2	187.2	190.3	193.6	201.0	208.6	221.8	238.2	265.2	309.5
65°	153.3	154.6	155.9	157.3	159.1	163.6	170.8	179.9	191.1	210.1	242.0
67.5°	120.5	121.8	122.3	125.0	128.9	131.7	136.1	144.1	152.0	168.0	186.1
70°	97.4	96.9	97.4	98.8	103.7	108.7	114.5	120.4	125.3	136.6	151.9
72.5°	83.7	82.8	84.0	84.3	86.7	88.1	91.8	97.3	103.7	111.3	122.3
75°	64.9	64.9	64.9	64.9	66.7	67.6	69.0	70.3	72.6	76.2	84.3
77.5°	48.0	48.0	48.6	49.2	49.5	50.0	50.9	52.2	53.0	54.9	58.5
80°	37.9	38.3	37.9	38.3	38.3	39.2	39.7	41.0	41.5	43.7	45.1
82.5°	28.5	28.2	28.5	28.9	28.9	29.9	30.0	30.9	31.0	32.2	33.6
85°	15.3	14.5	15.3	14.9	15.8	14.9	15.3	16.2	16.2	16.7	18.5
87.5°	9.4	10.3	9.4	9.6	9.7	9.7	9.6	9.3	9.8	9.7	9.5
90°	29.0	30.0	29.0	28.0	29.0	27.0	26.0	25.0	24.0	25.0	22.0
92.5°	48.2	50.0	49.0	52.0	53.8	59.0	66.8	84.2	116.1	153.9	169.3
95°	116.1	120.0	127.1	136.0	155.1	191.1	244.1	360.2	481.1	593.2	528.2
97.5°	315.9	324.5	351.5	396.6	470.4	590.0	719.0	897.7	983.5	919.3	673.0
100°	627.2	626.2	665.2	738.2	839.3	981.4	1098.4	1179.4	1144.4	947.4	640.2
102.5°	920.2	943.1	975.8	1033.5	1112.2	1202.2	1270.4	1273.1	1152.4	895.4	592.2
105°	1272.5	1277.5	1309.5	1347.5	1393.5	1419.5	1400.5	1300.5	1091.4	804.3	533.2
107.5°	1475.3	1484.5	1495.3	1508.1	1507.4	1471.7	1384.1	1221.6	984.6	723.8	495.6
110°	1558.6	1560.6	1562.5	1554.5	1526.6	1456.6	1330.5	1146.4	917.3	678.2	481.1



TEST NUMBER: P332326-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1575.4	1574.9	1567.4	1542.6	1491.3	1401.3	1260.1	1071.9	858.9	647.8	473.2
115°	1547.6	1542.6	1522.5	1478.5	1403.5	1294.4	1147.4	973.4	788.2	615.2	470.2
117.5°	1459.1	1452.3	1423.5	1373.1	1294.9	1184.2	1052.1	901.9	745.6	596.0	472.0
120°	1385.5	1379.5	1355.5	1299.4	1220.5	1119.4	999.4	864.3	723.2	587.2	475.2
122.5°	1316.6	1309.1	1282.6	1232.3	1162.0	1068.2	956.9	834.7	704.8	581.6	480.8
125°	1220.5	1213.4	1188.4	1144.4	1080.4	1000.3	904.3	795.3	681.2	574.2	489.1
127.5°	1141.2	1134.8	1112.2	1074.6	1017.5	944.7	858.1	760.9	660.5	570.6	498.8
130°	1096.4	1088.4	1067.4	1031.4	978.4	910.3	829.3	739.3	649.2	568.2	505.1
132.5°	1052.4	1046.8	1028.1	992.1	942.4	877.5	802.1	719.3	638.9	567.4	510.0
135°	989.4	982.3	964.3	934.4	885.3	828.3	763.3	692.2	625.3	566.2	517.2
137.5°	922.7	918.1	902.9	872.5	831.3	781.9	725.8	667.6	613.4	564.0	522.0
140°	876.3	877.3	861.3	833.3	795.3	752.3	704.2	653.2	606.2	563.2	525.2
142.5°	833.1	834.1	819.7	794.9	762.5	725.0	683.5	639.6	599.8	561.6	527.6
145°	773.3	771.3	763.3	742.3	717.2	688.3	656.3	623.2	591.2	559.2	529.2
147.5°	724.0	723.2	715.7	701.5	682.4	661.9	636.0	609.8	582.8	555.4	529.2
150°	695.3	695.3	689.2	678.2	663.2	644.2	623.2	600.2	577.2	552.2	529.2
152.5°	671.2	671.2	667.6	657.5	645.7	629.8	611.2	591.4	570.8	548.2	526.8
155°	641.2	640.2	638.3	630.3	621.2	609.2	594.2	578.2	561.2	541.2	524.2
157.5°	613.8	614.0	612.4	606.4	598.6	589.2	577.6	564.2	550.4	535.0	520.8
160°	596.2	597.2	597.2	591.2	584.2	577.2	567.2	556.2	543.2	530.2	519.2
162.5°	580.2	581.2	581.2	576.0	571.4	565.2	556.0	546.6	536.0	525.4	516.0
165°	559.2	559.2	560.2	556.2	552.2	547.2	540.2	534.2	526.2	518.1	511.2
167.5°	539.2	539.2	540.2	537.4	535.6	532.0	528.0	523.4	516.8	511.0	506.4
170°	527.2	527.2	528.2	526.2	525.2	523.1	519.2	516.2	511.2	506.2	503.2
172.5°	516.0	516.8	518.6	516.6	516.3	515.2	512.0	509.8	505.6	502.1	500.8
175°	503.2	504.2	505.1	504.2	504.2	504.2	502.1	501.2	499.2	497.1	497.1
177.5°	495.8	495.8	497.4	496.5	497.4	497.4	496.5	495.8	495.0	494.2	495.0
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P332326-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1087.3	1086.2	1081.2	1075.4	1067.8	1062.7	1058.8	1056.6	1050.2	1042.2	1036.8
5°	1154.4	1140.9	1126.5	1108.9	1092.7	1076.0	1065.7	1053.4	1038.6	1021.9	1010.2
7.5°	1226.4	1199.9	1171.3	1141.9	1112.7	1086.6	1063.5	1043.7	1020.0	996.1	979.4
10°	1281.6	1242.8	1202.6	1161.7	1124.2	1089.1	1062.0	1035.4	1007.0	979.6	958.8
12.5°	1331.7	1280.7	1234.4	1184.0	1136.2	1094.2	1055.2	1023.9	989.7	960.4	936.8
15°	1395.2	1342.9	1286.9	1210.3	1146.8	1093.6	1046.3	1005.2	963.8	927.7	904.7
17.5°	1454.5	1375.8	1300.7	1236.7	1154.2	1087.7	1029.9	980.9	935.4	897.2	868.8
20°	1479.0	1402.8	1321.2	1239.7	1158.5	1084.1	1016.9	962.9	915.5	872.3	846.1
22.5°	1493.7	1407.5	1321.5	1233.9	1147.7	1070.4	1004.0	944.4	893.2	852.0	819.8
25°	1511.0	1408.3	1313.5	1227.0	1139.1	1055.2	976.4	913.3	857.8	814.1	779.8
27.5°	1522.3	1401.4	1289.6	1193.3	1104.2	1020.7	948.4	881.6	825.3	779.0	742.3
30°	1524.5	1396.0	1271.2	1167.1	1076.4	999.8	923.2	859.2	799.7	750.5	716.3
32.5°	1527.4	1382.7	1246.3	1135.7	1042.9	967.0	897.6	836.5	775.5	727.1	692.2
35°	1515.5	1375.4	1208.5	1081.4	988.5	915.1	852.4	796.1	736.2	689.2	653.6
37.5°	1464.3	1346.0	1169.4	1020.3	923.2	855.1	804.1	754.9	700.0	649.4	615.9
40°	1412.7	1317.2	1139.1	983.2	881.8	811.8	765.9	725.7	672.5	625.3	589.2
42.5°	1335.9	1277.9	1110.3	944.2	834.8	767.5	728.8	691.1	644.5	596.4	562.5
45°	1195.0	1202.6	1051.2	882.2	769.9	702.3	665.8	639.6	598.2	558.5	523.8
47.5°	1018.3	1089.9	981.9	816.1	701.5	638.0	606.1	583.3	555.3	516.4	484.7
50°	902.9	1005.2	926.3	771.7	658.6	595.5	564.0	545.4	521.1	490.4	460.2
52.5°	796.5	906.5	859.3	722.3	612.1	554.4	523.6	508.3	489.0	460.1	432.8
55°	649.5	761.0	750.1	647.7	542.3	490.4	467.0	449.9	436.8	415.2	393.6
57.5°	525.5	631.0	636.6	564.8	480.8	429.6	409.4	396.5	388.0	371.6	351.6
60°	447.2	544.1	563.0	508.9	436.8	391.8	371.9	361.5	354.7	341.7	326.4
62.5°	382.3	464.8	486.2	447.3	394.6	352.4	336.9	326.9	322.3	311.0	297.5
65°	292.6	361.1	381.8	360.2	332.7	298.9	286.3	277.7	273.6	267.3	257.4
67.5°	220.0	269.9	292.7	277.4	267.5	246.2	238.1	233.5	229.9	225.6	217.3
70°	176.7	213.7	237.1	233.1	225.0	213.7	207.8	204.7	201.0	197.4	190.2
72.5°	142.1	167.6	189.5	191.6	184.9	182.6	177.5	176.2	174.0	169.7	165.7
75°	94.2	111.8	127.1	132.9	135.7	137.9	135.7	135.3	134.7	131.2	128.9
77.5°	61.7	71.2	80.8	90.8	95.1	98.2	98.9	100.6	99.4	97.5	96.3
80°	47.4	49.6	56.3	64.9	71.6	74.4	76.2	77.1	76.6	76.2	74.4
82.5°	34.4	36.2	39.4	45.5	51.1	55.6	56.7	56.6	57.5	57.8	56.3
85°	18.5	18.9	19.8	20.8	23.8	28.8	30.2	31.1	32.0	32.0	29.3
87.5°	9.6	8.6	8.7	8.4	9.0	8.8	10.5	12.0	12.7	11.6	12.2
90°	19.0	16.0	13.0	11.0	9.0	6.0	4.0	2.0	4.0	6.0	9.0
92.5°	127.1	84.0	57.9	43.0	34.6	26.8	18.4	12.4	18.4	26.8	34.6
95°	364.1	215.1	130.0	91.0	65.0	48.0	37.0	34.0	37.0	48.0	65.0
97.5°	399.5	231.5	150.2	108.1	82.4	67.6	59.0	58.0	59.0	67.6	82.4
100°	377.1	229.1	159.0	120.0	96.0	82.1	75.0	74.0	75.0	82.1	96.0
102.5°	357.9	232.3	169.4	133.6	112.0	98.8	92.6	90.8	92.6	98.8	112.0
105°	344.1	241.1	187.1	156.0	137.1	125.0	119.1	116.1	119.1	125.0	137.1
107.5°	343.1	257.5	210.1	181.2	163.4	151.6	145.9	142.8	145.9	151.6	163.4
110°	347.2	271.1	226.1	198.0	181.1	170.0	165.1	162.0	165.1	170.0	181.1



TEST NUMBER: P332326-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	355.2	284.7	242.9	215.7	198.6	187.7	182.7	179.7	182.7	187.7	198.6
115°	368.2	307.1	269.1	242.1	225.1	215.1	209.1	205.1	209.1	215.1	225.1
117.5°	385.3	330.9	293.3	268.3	249.3	240.0	235.1	230.5	235.1	240.0	249.3
120°	398.1	346.1	310.1	285.1	266.1	256.1	251.1	248.1	251.1	256.1	266.1
122.5°	410.2	362.1	326.9	300.3	282.1	271.3	266.3	263.3	266.3	271.3	282.1
125°	429.1	385.1	350.1	323.1	304.1	293.1	287.1	285.1	287.1	293.1	304.1
127.5°	444.8	405.1	371.3	344.3	323.3	312.1	304.7	301.7	304.7	312.1	323.3
130°	455.1	417.2	384.1	357.1	336.1	324.1	315.1	312.1	315.1	324.1	336.1
132.5°	464.8	427.6	395.4	369.1	348.1	333.7	323.9	320.1	323.9	333.7	348.1
135°	477.2	443.2	412.2	385.1	364.1	349.1	338.1	334.2	338.1	349.1	364.1
137.5°	486.4	453.9	424.1	399.2	378.3	362.3	351.5	347.3	351.5	362.3	378.3
140°	491.2	461.2	432.1	407.2	387.1	371.1	361.1	356.1	361.1	371.1	387.1
142.5°	495.9	466.7	438.6	415.2	395.1	380.7	370.0	365.8	370.0	380.7	395.1
145°	501.2	474.2	448.2	425.2	408.1	393.1	384.1	381.2	384.1	393.1	408.1
147.5°	504.4	480.2	456.3	436.8	420.3	407.3	398.6	396.7	398.6	407.3	420.3
150°	505.1	484.1	461.2	443.2	429.1	416.1	408.1	407.2	408.1	416.1	429.1
152.5°	506.8	486.6	466.7	449.5	437.1	425.8	417.8	417.6	417.8	425.8	437.1
155°	507.2	491.2	474.2	460.1	449.2	439.2	433.2	433.2	433.2	439.2	449.2
157.5°	508.2	493.8	480.2	469.3	459.9	451.2	446.3	445.6	446.3	451.2	459.9
160°	508.2	496.2	484.1	474.2	467.2	459.2	455.1	455.1	455.1	459.2	467.2
162.5°	507.4	497.0	486.6	478.2	472.0	465.5	462.4	462.4	462.4	465.5	472.0
165°	505.1	498.2	490.2	483.2	479.1	474.2	472.2	473.2	472.2	474.2	479.1
167.5°	503.6	498.0	492.1	487.8	485.0	481.1	480.2	481.4	480.2	481.1	485.0
170°	501.2	497.1	492.1	490.2	488.2	485.2	484.1	486.2	484.1	485.2	488.2
172.5°	500.4	497.1	493.0	491.8	490.6	488.4	488.2	489.4	488.2	488.4	490.6
175°	498.2	496.2	494.2	493.2	493.2	491.2	492.1	493.2	492.1	491.2	493.2
177.5°	496.5	495.0	494.2	494.2	494.2	493.4	494.2	495.0	494.2	493.4	494.2
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P332326-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1035.0	1030.3	1027.1	1019.9	1015.1	1010.1	1005.0	1008.3	1008.0	1007.5	1007.5
5°	1000.3	989.9	980.4	968.3	960.6	951.1	943.9	943.1	944.9	938.5	934.9
7.5°	965.9	951.7	938.2	924.8	910.6	899.2	892.1	888.7	884.2	880.3	876.2
10°	941.7	925.0	911.9	895.3	879.9	866.4	857.8	852.0	848.8	845.7	839.8
12.5°	916.8	900.4	883.8	865.0	850.3	834.7	828.3	821.7	815.6	812.1	804.1
15°	880.4	859.2	841.6	821.7	805.6	790.2	781.2	768.1	766.3	761.8	753.7
17.5°	843.9	820.9	796.6	782.0	763.6	747.7	733.9	729.5	716.6	711.8	704.7
20°	815.0	793.8	775.3	756.0	729.4	714.5	703.7	697.8	687.4	681.1	676.6
22.5°	790.1	768.6	747.2	724.6	702.7	686.0	678.0	668.9	663.3	654.4	649.5
25°	754.6	731.2	705.5	681.1	665.4	652.7	640.1	632.0	623.9	619.8	610.8
27.5°	713.3	688.8	664.8	646.4	627.0	614.5	603.0	595.8	586.1	579.3	574.3
30°	690.6	661.8	641.0	624.3	599.5	587.8	579.3	570.2	563.0	555.8	550.9
32.5°	664.3	637.9	618.3	597.6	578.6	565.8	554.7	546.8	540.6	533.8	528.8
35°	622.9	600.9	580.6	559.8	545.9	532.8	519.8	513.0	507.1	500.8	496.3
37.5°	585.7	565.0	545.7	526.1	508.8	498.1	487.6	482.4	474.5	470.3	465.6
40°	562.6	542.3	521.5	502.7	484.6	476.5	467.0	459.3	452.1	449.0	444.0
42.5°	537.4	517.0	499.6	479.1	464.4	453.4	444.6	436.3	430.8	426.3	423.4
45°	499.9	481.9	464.8	444.4	430.5	421.0	411.1	403.5	398.5	395.4	390.4
47.5°	463.6	445.6	428.2	410.4	396.9	386.2	376.3	370.9	364.3	360.4	357.1
50°	437.2	421.0	402.5	386.3	372.8	362.0	353.9	347.1	341.2	336.3	334.1
52.5°	413.1	395.8	379.8	364.7	350.4	338.2	330.8	323.6	319.3	313.6	310.9
55°	373.2	356.5	343.0	328.1	314.2	303.8	294.8	288.5	284.0	277.7	274.1
57.5°	335.8	320.9	304.7	291.8	277.4	268.6	261.1	252.6	247.1	242.2	238.7
60°	310.6	293.4	279.5	267.3	254.7	243.4	236.7	229.9	224.0	219.0	215.9
62.5°	284.3	269.3	256.1	242.8	231.3	221.4	213.6	207.9	202.8	199.6	196.5
65°	243.8	232.1	218.6	207.8	197.0	189.8	183.5	178.5	174.9	172.6	170.0
67.5°	206.7	195.4	183.6	172.9	165.7	160.2	156.1	151.8	150.0	147.1	145.3
70°	182.5	170.8	160.5	152.4	145.2	141.1	138.4	135.3	133.5	129.8	128.0
72.5°	156.3	147.7	140.3	133.6	127.9	124.2	120.7	116.8	114.0	109.9	108.2
75°	123.0	115.4	109.5	105.0	101.4	96.4	91.5	87.5	86.1	84.7	84.3
77.5°	91.2	86.3	82.1	78.3	73.8	70.2	69.1	68.2	67.8	67.2	67.2
80°	71.6	67.2	64.0	59.5	56.8	56.8	56.8	55.9	56.3	56.3	56.3
82.5°	53.3	49.2	47.4	45.8	45.3	45.6	45.6	45.8	45.5	46.2	45.9
85°	27.5	28.0	28.8	28.4	28.8	28.8	29.8	29.3	29.8	28.8	29.8
87.5°	12.3	13.8	14.7	15.7	16.7	16.9	17.0	17.2	17.8	18.0	18.4
90°	11.0	13.0	16.0	19.0	22.0	25.0	24.0	25.0	26.0	27.0	29.0
92.5°	43.0	57.9	84.0	127.1	169.3	153.9	116.1	84.2	66.8	59.0	53.8
95°	91.0	130.0	215.1	364.1	528.2	593.2	481.1	360.2	244.1	191.1	155.1
97.5°	108.1	150.2	231.5	399.5	673.0	919.3	983.5	897.7	719.0	590.0	470.4
100°	120.0	159.0	229.1	377.1	640.2	947.4	1144.4	1179.4	1098.4	981.4	839.3
102.5°	133.6	169.4	232.3	357.9	592.2	895.4	1152.4	1273.1	1270.4	1202.2	1112.2
105°	156.0	187.1	241.1	344.1	533.2	804.3	1091.4	1300.5	1400.5	1419.5	1393.5
107.5°	181.2	210.1	257.5	343.1	495.6	723.8	984.6	1221.6	1384.1	1471.7	1507.4
110°	198.0	226.1	271.1	347.2	481.1	678.2	917.3	1146.4	1330.5	1456.6	1526.6



TEST NUMBER: P332326-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	215.7	242.9	284.7	355.2	473.2	647.8	858.9	1071.9	1260.1	1401.3	1491.3
115°	242.1	269.1	307.1	368.2	470.2	615.2	788.2	973.4	1147.4	1294.4	1403.5
117.5°	268.3	293.3	330.9	385.3	472.0	596.0	745.6	901.9	1052.1	1184.2	1294.9
120°	285.1	310.1	346.1	398.1	475.2	587.2	723.2	864.3	999.4	1119.4	1220.5
122.5°	300.3	326.9	362.1	410.2	480.8	581.6	704.8	834.7	956.9	1068.2	1162.0
125°	323.1	350.1	385.1	429.1	489.1	574.2	681.2	795.3	904.3	1000.3	1080.4
127.5°	344.3	371.3	405.1	444.8	498.8	570.6	660.5	760.9	858.1	944.7	1017.5
130°	357.1	384.1	417.2	455.1	505.1	568.2	649.2	739.3	829.3	910.3	978.4
132.5°	369.1	395.4	427.6	464.8	510.0	567.4	638.9	719.3	802.1	877.5	942.4
135°	385.1	412.2	443.2	477.2	517.2	566.2	625.3	692.2	763.3	828.3	885.3
137.5°	399.2	424.1	453.9	486.4	522.0	564.0	613.4	667.6	725.8	781.9	831.3
140°	407.2	432.1	461.2	491.2	525.2	563.2	606.2	653.2	704.2	752.3	795.3
142.5°	415.2	438.6	466.7	495.9	527.6	561.6	599.8	639.6	683.5	725.0	762.5
145°	425.2	448.2	474.2	501.2	529.2	559.2	591.2	623.2	656.3	688.3	717.2
147.5°	436.8	456.3	480.2	504.4	529.2	555.4	582.8	609.8	636.0	661.9	682.4
150°	443.2	461.2	484.1	505.1	529.2	552.2	577.2	600.2	623.2	644.2	663.2
152.5°	449.5	466.7	486.6	506.8	526.8	548.2	570.8	591.4	611.2	629.8	645.7
155°	460.1	474.2	491.2	507.2	524.2	541.2	561.2	578.2	594.2	609.2	621.2
157.5°	469.3	480.2	493.8	508.2	520.8	535.0	550.4	564.2	577.6	589.2	598.6
160°	474.2	484.1	496.2	508.2	519.2	530.2	543.2	556.2	567.2	577.2	584.2
162.5°	478.2	486.6	497.0	507.4	516.0	525.4	536.0	546.6	556.0	565.2	571.4
165°	483.2	490.2	498.2	505.1	511.2	518.1	526.2	534.2	540.2	547.2	552.2
167.5°	487.8	492.1	498.0	503.6	506.4	511.0	516.8	523.4	528.0	532.0	535.6
170°	490.2	492.1	497.1	501.2	503.2	506.2	511.2	516.2	519.2	523.1	525.2
172.5°	491.8	493.0	497.1	500.4	500.8	502.1	505.6	509.8	512.0	515.2	516.3
175°	493.2	494.2	496.2	498.2	497.1	497.1	499.2	501.2	502.1	504.2	504.2
177.5°	494.2	494.2	495.0	496.5	495.0	494.2	495.0	495.8	496.5	497.4	497.4
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P332326-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1003.2	1002.9	1003.2	1001.8	1003.2	1002.9	1003.2	1007.5	1007.5	1008.0	1008.3
5°	933.6	933.1	931.8	927.7	931.8	933.1	933.6	934.9	938.5	944.9	943.1
7.5°	872.7	872.1	868.1	868.2	868.1	872.1	872.7	876.2	880.3	884.2	888.7
10°	836.6	837.1	831.7	828.5	831.7	837.1	836.6	839.8	845.7	848.8	852.0
12.5°	801.7	799.6	795.2	791.8	795.2	799.6	801.7	804.1	812.1	815.6	821.7
15°	755.5	751.0	740.2	741.1	740.2	751.0	755.5	753.7	761.8	766.3	768.1
17.5°	701.1	697.8	697.6	691.3	697.6	697.8	701.1	704.7	711.8	716.6	729.5
20°	669.4	667.2	668.0	661.8	668.0	667.2	669.4	676.6	681.1	687.4	697.8
22.5°	644.5	642.3	638.5	636.5	638.5	642.3	644.5	649.5	654.4	663.3	668.9
25°	608.1	604.5	600.9	603.1	600.9	604.5	608.1	610.8	619.8	623.9	632.0
27.5°	571.7	568.9	565.3	564.9	565.3	568.9	571.7	574.3	579.3	586.1	595.8
30°	548.6	545.9	544.1	541.8	544.1	545.9	548.6	550.9	555.8	563.0	570.2
32.5°	525.1	524.6	521.3	520.9	521.3	524.6	525.1	528.8	533.8	540.6	546.8
35°	494.5	491.8	490.9	491.4	490.9	491.8	494.5	496.3	500.8	507.1	513.0
37.5°	465.4	461.8	460.1	458.6	460.1	461.8	465.4	465.6	470.3	474.5	482.4
40°	444.4	440.8	440.0	439.0	440.0	440.8	444.4	444.0	449.0	452.1	459.3
42.5°	421.0	419.6	419.0	417.4	419.0	419.6	421.0	423.4	426.3	430.8	436.3
45°	389.0	388.6	385.9	386.8	385.9	388.6	389.0	390.4	395.4	398.5	403.5
47.5°	355.3	353.4	351.5	352.7	351.5	353.4	355.3	357.1	360.4	364.3	370.9
50°	332.3	331.3	327.3	328.1	327.3	331.3	332.3	334.1	336.3	341.2	347.1
52.5°	309.2	305.7	304.2	303.7	304.2	305.7	309.2	310.9	313.6	319.3	323.6
55°	271.0	266.8	265.0	264.2	265.0	266.8	271.0	274.1	277.7	284.0	288.5
57.5°	233.4	232.3	230.9	231.9	230.9	232.3	233.4	238.7	242.2	247.1	252.6
60°	211.4	211.4	211.4	210.9	211.4	211.4	211.4	215.9	219.0	224.0	229.9
62.5°	194.5	193.4	193.0	193.6	193.0	193.4	194.5	196.5	199.6	202.8	207.9
65°	168.6	168.2	166.3	165.9	166.3	168.2	168.6	170.0	172.6	174.9	178.5
67.5°	144.1	142.5	142.0	141.4	142.0	142.5	144.1	145.3	147.1	150.0	151.8
70°	125.8	124.8	122.2	122.6	122.2	124.8	125.8	128.0	129.8	133.5	135.3
72.5°	105.9	105.0	104.5	103.8	104.5	105.0	105.9	108.2	109.9	114.0	116.8
75°	83.9	83.4	82.9	84.7	82.9	83.4	83.9	84.3	84.7	86.1	87.5
77.5°	67.2	67.2	67.4	66.7	67.4	67.2	67.2	67.2	67.2	67.8	68.2
80°	56.3	56.3	55.9	55.9	55.9	56.3	56.3	56.3	56.3	56.3	55.9
82.5°	45.2	45.5	45.8	45.1	45.8	45.5	45.2	45.9	46.2	45.5	45.8
85°	29.8	29.3	30.2	29.8	30.2	29.3	29.8	29.8	28.8	29.8	29.3
87.5°	18.9	18.4	18.6	18.8	18.6	18.4	18.9	18.4	18.0	17.8	17.2
90°	28.0	29.0	30.0	29.0	30.0	29.0	28.0	29.0	27.0	26.0	25.0
92.5°	52.0	49.0	50.0	48.2	50.0	49.0	52.0	53.8	59.0	66.8	84.2
95°	136.0	127.1	120.0	116.1	120.0	127.1	136.0	155.1	191.1	244.1	360.2
97.5°	396.6	351.5	324.5	315.9	324.5	351.5	396.6	470.4	590.0	719.0	897.7
100°	738.2	665.2	626.2	627.2	626.2	665.2	738.2	839.3	981.4	1098.4	1179.4
102.5°	1033.5	975.8	943.1	920.2	943.1	975.8	1033.5	1112.2	1202.2	1270.4	1273.1
105°	1347.5	1309.5	1277.5	1272.5	1277.5	1309.5	1347.5	1393.5	1419.5	1400.5	1300.5
107.5°	1508.1	1495.3	1484.5	1475.3	1484.5	1495.3	1508.1	1507.4	1471.7	1384.1	1221.6
110°	1554.5	1562.5	1560.6	1558.6	1560.6	1562.5	1554.5	1526.6	1456.6	1330.5	1146.4



TEST NUMBER: P332326-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1542.6	1567.4	1574.9	1575.4	1574.9	1567.4	1542.6	1491.3	1401.3	1260.1	1071.9
115°	1478.5	1522.5	1542.6	1547.6	1542.6	1522.5	1478.5	1403.5	1294.4	1147.4	973.4
117.5°	1373.1	1423.5	1452.3	1459.1	1452.3	1423.5	1373.1	1294.9	1184.2	1052.1	901.9
120°	1299.4	1355.5	1379.5	1385.5	1379.5	1355.5	1299.4	1220.5	1119.4	999.4	864.3
122.5°	1232.3	1282.6	1309.1	1316.6	1309.1	1282.6	1232.3	1162.0	1068.2	956.9	834.7
125°	1144.4	1188.4	1213.4	1220.5	1213.4	1188.4	1144.4	1080.4	1000.3	904.3	795.3
127.5°	1074.6	1112.2	1134.8	1141.2	1134.8	1112.2	1074.6	1017.5	944.7	858.1	760.9
130°	1031.4	1067.4	1088.4	1096.4	1088.4	1067.4	1031.4	978.4	910.3	829.3	739.3
132.5°	992.1	1028.1	1046.8	1052.4	1046.8	1028.1	992.1	942.4	877.5	802.1	719.3
135°	934.4	964.3	982.3	989.4	982.3	964.3	934.4	885.3	828.3	763.3	692.2
137.5°	872.5	902.9	918.1	922.7	918.1	902.9	872.5	831.3	781.9	725.8	667.6
140°	833.3	861.3	877.3	876.3	877.3	861.3	833.3	795.3	752.3	704.2	653.2
142.5°	794.9	819.7	834.1	833.1	834.1	819.7	794.9	762.5	725.0	683.5	639.6
145°	742.3	763.3	771.3	773.3	771.3	763.3	742.3	717.2	688.3	656.3	623.2
147.5°	701.5	715.7	723.2	724.0	723.2	715.7	701.5	682.4	661.9	636.0	609.8
150°	678.2	689.2	695.3	695.3	695.3	689.2	678.2	663.2	644.2	623.2	600.2
152.5°	657.5	667.6	671.2	671.2	671.2	667.6	657.5	645.7	629.8	611.2	591.4
155°	630.3	638.3	640.2	641.2	640.2	638.3	630.3	621.2	609.2	594.2	578.2
157.5°	606.4	612.4	614.0	613.8	614.0	612.4	606.4	598.6	589.2	577.6	564.2
160°	591.2	597.2	597.2	596.2	597.2	597.2	591.2	584.2	577.2	567.2	556.2
162.5°	576.0	581.2	581.2	580.2	581.2	581.2	576.0	571.4	565.2	556.0	546.6
165°	556.2	560.2	559.2	559.2	559.2	560.2	556.2	552.2	547.2	540.2	534.2
167.5°	537.4	540.2	539.2	539.2	539.2	540.2	537.4	535.6	532.0	528.0	523.4
170°	526.2	528.2	527.2	527.2	527.2	528.2	526.2	525.2	523.1	519.2	516.2
172.5°	516.6	518.6	516.8	516.0	516.8	518.6	516.6	516.3	515.2	512.0	509.8
175°	504.2	505.1	504.2	503.2	504.2	505.1	504.2	504.2	504.2	502.1	501.2
177.5°	496.5	497.4	495.8	495.8	495.8	497.4	496.5	497.4	497.4	496.5	495.8
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P332326-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1005.0	1010.1	1015.1	1019.9	1027.1	1030.3	1035.0	1036.8	1042.2	1050.2	1056.6
5°	943.9	951.1	960.6	968.3	980.4	989.9	1000.3	1010.2	1021.9	1038.6	1053.4
7.5°	892.1	899.2	910.6	924.8	938.2	951.7	965.9	979.4	996.1	1020.0	1043.7
10°	857.8	866.4	879.9	895.3	911.9	925.0	941.7	958.8	979.6	1007.0	1035.4
12.5°	828.3	834.7	850.3	865.0	883.8	900.4	916.8	936.8	960.4	989.7	1023.9
15°	781.2	790.2	805.6	821.7	841.6	859.2	880.4	904.7	927.7	963.8	1005.2
17.5°	733.9	747.7	763.6	782.0	796.6	820.9	843.9	868.8	897.2	935.4	980.9
20°	703.7	714.5	729.4	756.0	775.3	793.8	815.0	846.1	872.3	915.5	962.9
22.5°	678.0	686.0	702.7	724.6	747.2	768.6	790.1	819.8	852.0	893.2	944.4
25°	640.1	652.7	665.4	681.1	705.5	731.2	754.6	779.8	814.1	857.8	913.3
27.5°	603.0	614.5	627.0	646.4	664.8	688.8	713.3	742.3	779.0	825.3	881.6
30°	579.3	587.8	599.5	624.3	641.0	661.8	690.6	716.3	750.5	799.7	859.2
32.5°	554.7	565.8	578.6	597.6	618.3	637.9	664.3	692.2	727.1	775.5	836.5
35°	519.8	532.8	545.9	559.8	580.6	600.9	622.9	653.6	689.2	736.2	796.1
37.5°	487.6	498.1	508.8	526.1	545.7	565.0	585.7	615.9	649.4	700.0	754.9
40°	467.0	476.5	484.6	502.7	521.5	542.3	562.6	589.2	625.3	672.5	725.7
42.5°	444.6	453.4	464.4	479.1	499.6	517.0	537.4	562.5	596.4	644.5	691.1
45°	411.1	421.0	430.5	444.4	464.8	481.9	499.9	523.8	558.5	598.2	639.6
47.5°	376.3	386.2	396.9	410.4	428.2	445.6	463.6	484.7	516.4	555.3	583.3
50°	353.9	362.0	372.8	386.3	402.5	421.0	437.2	460.2	490.4	521.1	545.4
52.5°	330.8	338.2	350.4	364.7	379.8	395.8	413.1	432.8	460.1	489.0	508.3
55°	294.8	303.8	314.2	328.1	343.0	356.5	373.2	393.6	415.2	436.8	449.9
57.5°	261.1	268.6	277.4	291.8	304.7	320.9	335.8	351.6	371.6	388.0	396.5
60°	236.7	243.4	254.7	267.3	279.5	293.4	310.6	326.4	341.7	354.7	361.5
62.5°	213.6	221.4	231.3	242.8	256.1	269.3	284.3	297.5	311.0	322.3	326.9
65°	183.5	189.8	197.0	207.8	218.6	232.1	243.8	257.4	267.3	273.6	277.7
67.5°	156.1	160.2	165.7	172.9	183.6	195.4	206.7	217.3	225.6	229.9	233.5
70°	138.4	141.1	145.2	152.4	160.5	170.8	182.5	190.2	197.4	201.0	204.7
72.5°	120.7	124.2	127.9	133.6	140.3	147.7	156.3	165.7	169.7	174.0	176.2
75°	91.5	96.4	101.4	105.0	109.5	115.4	123.0	128.9	131.2	134.7	135.3
77.5°	69.1	70.2	73.8	78.3	82.1	86.3	91.2	96.3	97.5	99.4	100.6
80°	56.8	56.8	56.8	59.5	64.0	67.2	71.6	74.4	76.2	76.6	77.1
82.5°	45.6	45.6	45.3	45.8	47.4	49.2	53.3	56.3	57.8	57.5	56.6
85°	29.8	28.8	28.8	28.4	28.8	28.0	27.5	29.3	32.0	32.0	31.1
87.5°	17.0	16.9	16.7	15.7	14.7	13.8	12.3	12.2	11.6	12.7	12.0
90°	24.0	25.0	22.0	19.0	16.0	13.0	11.0	9.0	6.0	4.0	2.0
92.5°	116.1	153.9	169.3	127.1	84.0	57.9	43.0	34.6	26.8	18.4	12.4
95°	481.1	593.2	528.2	364.1	215.1	130.0	91.0	65.0	48.0	37.0	34.0
97.5°	983.5	919.3	673.0	399.5	231.5	150.2	108.1	82.4	67.6	59.0	58.0
100°	1144.4	947.4	640.2	377.1	229.1	159.0	120.0	96.0	82.1	75.0	74.0
102.5°	1152.4	895.4	592.2	357.9	232.3	169.4	133.6	112.0	98.8	92.6	90.8
105°	1091.4	804.3	533.2	344.1	241.1	187.1	156.0	137.1	125.0	119.1	116.1
107.5°	984.6	723.8	495.6	343.1	257.5	210.1	181.2	163.4	151.6	145.9	142.8
110°	917.3	678.2	481.1	347.2	271.1	226.1	198.0	181.1	170.0	165.1	162.0



TEST NUMBER: P332326-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	858.9	647.8	473.2	355.2	284.7	242.9	215.7	198.6	187.7	182.7	179.7
115°	788.2	615.2	470.2	368.2	307.1	269.1	242.1	225.1	215.1	209.1	205.1
117.5°	745.6	596.0	472.0	385.3	330.9	293.3	268.3	249.3	240.0	235.1	230.5
120°	723.2	587.2	475.2	398.1	346.1	310.1	285.1	266.1	256.1	251.1	248.1
122.5°	704.8	581.6	480.8	410.2	362.1	326.9	300.3	282.1	271.3	266.3	263.3
125°	681.2	574.2	489.1	429.1	385.1	350.1	323.1	304.1	293.1	287.1	285.1
127.5°	660.5	570.6	498.8	444.8	405.1	371.3	344.3	323.3	312.1	304.7	301.7
130°	649.2	568.2	505.1	455.1	417.2	384.1	357.1	336.1	324.1	315.1	312.1
132.5°	638.9	567.4	510.0	464.8	427.6	395.4	369.1	348.1	333.7	323.9	320.1
135°	625.3	566.2	517.2	477.2	443.2	412.2	385.1	364.1	349.1	338.1	334.2
137.5°	613.4	564.0	522.0	486.4	453.9	424.1	399.2	378.3	362.3	351.5	347.3
140°	606.2	563.2	525.2	491.2	461.2	432.1	407.2	387.1	371.1	361.1	356.1
142.5°	599.8	561.6	527.6	495.9	466.7	438.6	415.2	395.1	380.7	370.0	365.8
145°	591.2	559.2	529.2	501.2	474.2	448.2	425.2	408.1	393.1	384.1	381.2
147.5°	582.8	555.4	529.2	504.4	480.2	456.3	436.8	420.3	407.3	398.6	396.7
150°	577.2	552.2	529.2	505.1	484.1	461.2	443.2	429.1	416.1	408.1	407.2
152.5°	570.8	548.2	526.8	506.8	486.6	466.7	449.5	437.1	425.8	417.8	417.6
155°	561.2	541.2	524.2	507.2	491.2	474.2	460.1	449.2	439.2	433.2	433.2
157.5°	550.4	535.0	520.8	508.2	493.8	480.2	469.3	459.9	451.2	446.3	445.6
160°	543.2	530.2	519.2	508.2	496.2	484.1	474.2	467.2	459.2	455.1	455.1
162.5°	536.0	525.4	516.0	507.4	497.0	486.6	478.2	472.0	465.5	462.4	462.4
165°	526.2	518.1	511.2	505.1	498.2	490.2	483.2	479.1	474.2	472.2	473.2
167.5°	516.8	511.0	506.4	503.6	498.0	492.1	487.8	485.0	481.1	480.2	481.4
170°	511.2	506.2	503.2	501.2	497.1	492.1	490.2	488.2	485.2	484.1	486.2
172.5°	505.6	502.1	500.8	500.4	497.1	493.0	491.8	490.6	488.4	488.2	489.4
175°	499.2	497.1	497.1	498.2	496.2	494.2	493.2	493.2	491.2	492.1	493.2
177.5°	495.0	494.2	495.0	496.5	495.0	494.2	494.2	494.2	493.4	494.2	495.0
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P332326-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1058.8	1062.7	1067.8	1075.4	1081.2	1086.2	1087.3	1088.7	1092.4	1098.5	1103.1
5°	1065.7	1076.0	1092.7	1108.9	1126.5	1140.9	1154.4	1163.9	1172.9	1191.9	1207.2
7.5°	1063.5	1086.6	1112.7	1141.9	1171.3	1199.9	1226.4	1250.1	1273.7	1301.3	1332.7
10°	1062.0	1089.1	1124.2	1161.7	1202.6	1242.8	1281.6	1311.7	1346.9	1378.5	1418.6
12.5°	1055.2	1094.2	1136.2	1184.0	1234.4	1280.7	1331.7	1373.5	1413.7	1459.2	1505.9
15°	1046.3	1093.6	1146.8	1210.3	1286.9	1342.9	1395.2	1467.7	1517.3	1566.9	1633.6
17.5°	1029.9	1087.7	1154.2	1236.7	1300.7	1375.8	1454.5	1511.8	1578.6	1648.5	1708.9
20°	1016.9	1084.1	1158.5	1239.7	1321.2	1402.8	1479.0	1547.5	1616.5	1697.2	1746.8
22.5°	1004.0	1070.4	1147.7	1233.9	1321.5	1407.5	1493.7	1574.2	1651.8	1733.3	1796.6
25°	976.4	1055.2	1139.1	1227.0	1313.5	1408.3	1511.0	1600.7	1696.7	1780.5	1840.6
27.5°	948.4	1020.7	1104.2	1193.3	1289.6	1401.4	1522.3	1624.4	1720.5	1780.5	1799.4
30°	923.2	999.8	1076.4	1167.1	1271.2	1396.0	1524.5	1641.2	1720.2	1746.3	1726.9
32.5°	897.6	967.0	1042.9	1135.7	1246.3	1382.7	1527.4	1631.2	1678.7	1658.7	1579.8
35°	852.4	915.1	988.5	1081.4	1208.5	1375.4	1515.5	1585.8	1574.1	1461.4	1312.7
37.5°	804.1	855.1	923.2	1020.3	1169.4	1346.0	1464.3	1474.6	1373.2	1200.2	1028.4
40°	765.9	811.8	881.8	983.2	1139.1	1317.2	1412.7	1370.8	1213.5	1021.0	877.7
42.5°	728.8	767.5	834.8	944.2	1110.3	1277.9	1335.9	1244.6	1063.1	881.1	750.7
45°	665.8	702.3	769.9	882.2	1051.2	1202.6	1195.0	1036.3	854.7	708.2	599.9
47.5°	606.1	638.0	701.5	816.1	981.9	1089.9	1018.3	849.5	695.3	577.8	500.7
50°	564.0	595.5	658.6	771.7	926.3	1005.2	902.9	740.2	599.1	501.7	440.4
52.5°	523.6	554.4	612.1	722.3	859.3	906.5	796.5	645.7	528.1	444.0	391.3
55°	467.0	490.4	542.3	647.7	750.1	761.0	649.5	523.3	426.5	367.8	331.7
57.5°	409.4	429.6	480.8	564.8	636.6	631.0	525.5	416.2	350.9	307.5	281.3
60°	371.9	391.8	436.8	508.9	563.0	544.1	447.2	359.3	303.3	271.4	250.6
62.5°	336.9	352.4	394.6	447.3	486.2	464.8	382.3	309.5	265.2	238.2	221.8
65°	286.3	298.9	332.7	360.2	381.8	361.1	292.6	242.0	210.1	191.1	179.9
67.5°	238.1	246.2	267.5	277.4	292.7	269.9	220.0	186.1	168.0	152.0	144.1
70°	207.8	213.7	225.0	233.1	237.1	213.7	176.7	151.9	136.6	125.3	120.4
72.5°	177.5	182.6	184.9	191.6	189.5	167.6	142.1	122.3	111.3	103.7	97.3
75°	135.7	137.9	135.7	132.9	127.1	111.8	94.2	84.3	76.2	72.6	70.3
77.5°	98.9	98.2	95.1	90.8	80.8	71.2	61.7	58.5	54.9	53.0	52.2
80°	76.2	74.4	71.6	64.9	56.3	49.6	47.4	45.1	43.7	41.5	41.0
82.5°	56.7	55.6	51.1	45.5	39.4	36.2	34.4	33.6	32.2	31.0	30.9
85°	30.2	28.8	23.8	20.8	19.8	18.9	18.5	18.5	16.7	16.2	16.2
87.5°	10.5	8.8	9.0	8.4	8.7	8.6	9.6	9.5	9.7	9.8	9.3
90°	4.0	6.0	9.0	11.0	13.0	16.0	19.0	22.0	25.0	24.0	25.0
92.5°	18.4	26.8	34.6	43.0	57.9	84.0	127.1	169.3	153.9	116.1	84.2
95°	37.0	48.0	65.0	91.0	130.0	215.1	364.1	528.2	593.2	481.1	360.2
97.5°	59.0	67.6	82.4	108.1	150.2	231.5	399.5	673.0	919.3	983.5	897.7
100°	75.0	82.1	96.0	120.0	159.0	229.1	377.1	640.2	947.4	1144.4	1179.4
102.5°	92.6	98.8	112.0	133.6	169.4	232.3	357.9	592.2	895.4	1152.4	1273.1
105°	119.1	125.0	137.1	156.0	187.1	241.1	344.1	533.2	804.3	1091.4	1300.5
107.5°	145.9	151.6	163.4	181.2	210.1	257.5	343.1	495.6	723.8	984.6	1221.6
110°	165.1	170.0	181.1	198.0	226.1	271.1	347.2	481.1	678.2	917.3	1146.4



TEST NUMBER: P332326-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	182.7	187.7	198.6	215.7	242.9	284.7	355.2	473.2	647.8	858.9	1071.9
115°	209.1	215.1	225.1	242.1	269.1	307.1	368.2	470.2	615.2	788.2	973.4
117.5°	235.1	240.0	249.3	268.3	293.3	330.9	385.3	472.0	596.0	745.6	901.9
120°	251.1	256.1	266.1	285.1	310.1	346.1	398.1	475.2	587.2	723.2	864.3
122.5°	266.3	271.3	282.1	300.3	326.9	362.1	410.2	480.8	581.6	704.8	834.7
125°	287.1	293.1	304.1	323.1	350.1	385.1	429.1	489.1	574.2	681.2	795.3
127.5°	304.7	312.1	323.3	344.3	371.3	405.1	444.8	498.8	570.6	660.5	760.9
130°	315.1	324.1	336.1	357.1	384.1	417.2	455.1	505.1	568.2	649.2	739.3
132.5°	323.9	333.7	348.1	369.1	395.4	427.6	464.8	510.0	567.4	638.9	719.3
135°	338.1	349.1	364.1	385.1	412.2	443.2	477.2	517.2	566.2	625.3	692.2
137.5°	351.5	362.3	378.3	399.2	424.1	453.9	486.4	522.0	564.0	613.4	667.6
140°	361.1	371.1	387.1	407.2	432.1	461.2	491.2	525.2	563.2	606.2	653.2
142.5°	370.0	380.7	395.1	415.2	438.6	466.7	495.9	527.6	561.6	599.8	639.6
145°	384.1	393.1	408.1	425.2	448.2	474.2	501.2	529.2	559.2	591.2	623.2
147.5°	398.6	407.3	420.3	436.8	456.3	480.2	504.4	529.2	555.4	582.8	609.8
150°	408.1	416.1	429.1	443.2	461.2	484.1	505.1	529.2	552.2	577.2	600.2
152.5°	417.8	425.8	437.1	449.5	466.7	486.6	506.8	526.8	548.2	570.8	591.4
155°	433.2	439.2	449.2	460.1	474.2	491.2	507.2	524.2	541.2	561.2	578.2
157.5°	446.3	451.2	459.9	469.3	480.2	493.8	508.2	520.8	535.0	550.4	564.2
160°	455.1	459.2	467.2	474.2	484.1	496.2	508.2	519.2	530.2	543.2	556.2
162.5°	462.4	465.5	472.0	478.2	486.6	497.0	507.4	516.0	525.4	536.0	546.6
165°	472.2	474.2	479.1	483.2	490.2	498.2	505.1	511.2	518.1	526.2	534.2
167.5°	480.2	481.1	485.0	487.8	492.1	498.0	503.6	506.4	511.0	516.8	523.4
170°	484.1	485.2	488.2	490.2	492.1	497.1	501.2	503.2	506.2	511.2	516.2
172.5°	488.2	488.4	490.6	491.8	493.0	497.1	500.4	500.8	502.1	505.6	509.8
175°	492.1	491.2	493.2	493.2	494.2	496.2	498.2	497.1	497.1	499.2	501.2
177.5°	494.2	493.4	494.2	494.2	494.2	495.0	496.5	495.0	494.2	495.0	495.8
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P332326-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1110.7	1110.7	1112.2	1117.6	1118.3	1123.0	1121.5
5°	1220.7	1229.2	1232.4	1246.0	1254.0	1257.7	1250.4
7.5°	1355.2	1379.4	1390.9	1405.0	1417.6	1421.3	1411.4
10°	1453.3	1478.5	1499.8	1512.8	1525.0	1533.1	1543.4
12.5°	1548.2	1579.2	1599.3	1617.7	1630.3	1640.5	1642.3
15°	1651.2	1698.1	1733.7	1759.8	1772.9	1779.7	1776.9
17.5°	1755.1	1798.6	1823.9	1850.6	1868.7	1869.7	1870.2
20°	1814.0	1856.3	1885.6	1905.4	1925.7	1924.9	1929.3
22.5°	1853.2	1886.6	1909.0	1923.5	1930.4	1927.0	1927.9
25°	1871.6	1881.5	1877.5	1854.5	1848.7	1827.5	1831.1
27.5°	1776.8	1729.9	1681.4	1619.0	1569.8	1530.5	1532.5
30°	1648.0	1565.1	1470.4	1391.1	1319.9	1300.0	1257.7
32.5°	1468.1	1343.7	1232.8	1158.8	1097.7	1081.2	1044.2
35°	1163.0	1042.2	928.2	859.6	832.6	794.7	794.3
37.5°	904.0	797.6	737.3	685.9	658.9	636.0	633.8
40°	760.4	677.5	632.0	595.0	568.4	551.3	547.3
42.5°	660.2	593.1	550.5	527.6	507.1	498.3	491.7
45°	539.2	494.0	464.3	443.6	434.1	427.3	423.7
47.5°	451.0	420.8	400.5	386.7	379.0	371.9	373.8
50°	403.0	378.2	363.3	350.3	344.4	339.4	339.9
52.5°	364.4	342.2	330.1	320.7	313.4	309.9	308.2
55°	309.3	295.2	283.1	276.3	272.2	267.3	266.0
57.5°	263.8	253.0	243.1	235.4	234.4	229.6	230.2
60°	233.5	224.5	216.4	212.3	209.1	205.1	206.5
62.5°	208.6	201.0	193.6	190.3	187.2	184.2	184.9
65°	170.8	163.6	159.1	157.3	155.9	154.6	153.3
67.5°	136.1	131.7	128.9	125.0	122.3	121.8	120.5
70°	114.5	108.7	103.7	98.8	97.4	96.9	97.4
72.5°	91.8	88.1	86.7	84.3	84.0	82.8	83.7
75°	69.0	67.6	66.7	64.9	64.9	64.9	64.9
77.5°	50.9	50.0	49.5	49.2	48.6	48.0	48.0
80°	39.7	39.2	38.3	38.3	37.9	38.3	37.9
82.5°	30.0	29.9	28.9	28.9	28.5	28.2	28.5
85°	15.3	14.9	15.8	14.9	15.3	14.5	15.3
87.5°	9.6	9.7	9.7	9.6	9.4	10.3	9.4
90°	26.0	27.0	29.0	28.0	29.0	30.0	29.0
92.5°	66.8	59.0	53.8	52.0	49.0	50.0	48.2
95°	244.1	191.1	155.1	136.0	127.1	120.0	116.1
97.5°	719.0	590.0	470.4	396.6	351.5	324.5	315.9
100°	1098.4	981.4	839.3	738.2	665.2	626.2	627.2
102.5°	1270.4	1202.2	1112.2	1033.5	975.8	943.1	920.2
105°	1400.5	1419.5	1393.5	1347.5	1309.5	1277.5	1272.5
107.5°	1384.1	1471.7	1507.4	1508.1	1495.3	1484.5	1475.3
110°	1330.5	1456.6	1526.6	1554.5	1562.5	1560.6	1558.6



TEST NUMBER: P332326-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1260.1	1401.3	1491.3	1542.6	1567.4	1574.9	1575.4
115°	1147.4	1294.4	1403.5	1478.5	1522.5	1542.6	1547.6
117.5°	1052.1	1184.2	1294.9	1373.1	1423.5	1452.3	1459.1
120°	999.4	1119.4	1220.5	1299.4	1355.5	1379.5	1385.5
122.5°	956.9	1068.2	1162.0	1232.3	1282.6	1309.1	1316.6
125°	904.3	1000.3	1080.4	1144.4	1188.4	1213.4	1220.5
127.5°	858.1	944.7	1017.5	1074.6	1112.2	1134.8	1141.2
130°	829.3	910.3	978.4	1031.4	1067.4	1088.4	1096.4
132.5°	802.1	877.5	942.4	992.1	1028.1	1046.8	1052.4
135°	763.3	828.3	885.3	934.4	964.3	982.3	989.4
137.5°	725.8	781.9	831.3	872.5	902.9	918.1	922.7
140°	704.2	752.3	795.3	833.3	861.3	877.3	876.3
142.5°	683.5	725.0	762.5	794.9	819.7	834.1	833.1
145°	656.3	688.3	717.2	742.3	763.3	771.3	773.3
147.5°	636.0	661.9	682.4	701.5	715.7	723.2	724.0
150°	623.2	644.2	663.2	678.2	689.2	695.3	695.3
152.5°	611.2	629.8	645.7	657.5	667.6	671.2	671.2
155°	594.2	609.2	621.2	630.3	638.3	640.2	641.2
157.5°	577.6	589.2	598.6	606.4	612.4	614.0	613.8
160°	567.2	577.2	584.2	591.2	597.2	597.2	596.2
162.5°	556.0	565.2	571.4	576.0	581.2	581.2	580.2
165°	540.2	547.2	552.2	556.2	560.2	559.2	559.2
167.5°	528.0	532.0	535.6	537.4	540.2	539.2	539.2
170°	519.2	523.1	525.2	526.2	528.2	527.2	527.2
172.5°	512.0	515.2	516.3	516.6	518.6	516.8	516.0
175°	502.1	504.2	504.2	504.2	505.1	504.2	503.2
177.5°	496.5	497.4	497.4	496.5	497.4	495.8	495.8
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2

(END OF REPORT)