

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332312-935

Luminaire Tested: **S123RDIP-S775D805U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332312-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D805U935-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5387.3 lumens
Efficiency: N/A
Efficacy: 117.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332312-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332312-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	49	48	47	42
2	90	83	77	72	83	77	71	67	65	61	58	54	52	49	44	42	41	36
3	82	73	66	61	76	68	62	57	58	53	49	48	45	42	40	37	35	31
4	75	65	58	52	69	60	54	49	52	47	43	43	40	37	36	33	31	27
5	69	58	50	45	64	54	47	42	46	41	37	39	35	32	32	30	27	24
6	64	52	45	39	59	49	42	37	42	37	33	36	32	28	30	27	24	21
7	59	47	40	34	55	44	37	33	38	33	29	33	28	25	27	24	22	19
8	55	43	36	31	51	40	34	29	35	30	26	30	26	23	25	22	20	17
9	51	40	32	27	47	37	30	26	32	27	23	28	23	20	23	20	18	16
10	48	36	29	25	44	34	28	23	30	25	21	25	21	19	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11334	11334	11334	11334
5°	13511	11382	10024	11382
10°	16869	11317	9055	11317
15°	19801	11202	8259	11202
20°	22100	11030	7581	11030
25°	21747	10847	7163	10847
30°	15632	10679	6734	10679
35°	10437	10461	6457	10461
40°	7690	10197	6169	10197
45°	6450	9736	5888	9736
50°	5692	9133	5494	9133
55°	4992	8443	4958	8443
60°	4445	7782	4540	7782
65°	3904	7073	4225	7073
70°	3065	6442	3858	6442
75°	2699	5627	3523	5627
80°	2349	4779	3465	4779
85°	1890	3841	3680	3841



TEST NUMBER: P332312-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.6	1.9
10°-20°	323.5	6.0
20°-30°	508.3	9.4
30°-40°	530.3	9.8
40°-50°	453.8	8.4
50°-60°	345.9	6.4
60°-70°	221.7	4.1
70°-80°	106.6	2.0
80°-90°	30.8	0.6
90°-100°	32.9	0.6
100°-110°	157.0	2.9
110°-120°	377.1	7.0
120°-130°	480.2	8.9
130°-140°	513.1	9.5
140°-150°	479.8	8.9
150°-160°	387.0	7.2
160°-170°	249.8	4.6
170°-180°	86.1	1.6
0°-30°	935.3	17.4
0°-40°	1465.6	27.2
0°-60°	2265.3	42.0
0°-90°	2624.4	48.7
90°-120°	567.0	10.5
90°-150°	2040.1	37.9
90°-180°	2763.0	51.3
0°-180°	5387.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1053	1053	1053	1053	1053	
5°	1250	1053	928	1053	1250	129
15°	1777	1005	741	1005	1777	504
25°	1831	913	603	913	1831	787
35°	794	796	491	796	794	521
45°	424	640	387	640	424	333
55°	266	450	264	450	266	240
65°	153	278	166	278	153	151
75°	65	135	85	135	65	70
85°	15	31	30	31	15	18
90°	20	1	20	1	20	10
95°	26	41	26	41	26	21
105°	30	201	30	201	30	68
115°	396	376	396	376	396	366
125°	541	530	541	530	541	483
135°	667	660	667	660	667	514
145°	769	762	769	762	769	480
155°	838	839	838	839	838	386
165°	883	885	883	885	883	249
175°	903	906	903	906	903	86
180°	906	906	906	906	906	



TEST NUMBER: P332312-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1121.5	1123.0	1118.3	1117.6	1112.2	1110.7	1110.7	1103.1	1098.5	1092.4	1088.7
5°	1250.4	1257.7	1254.0	1246.0	1232.4	1229.2	1220.7	1207.2	1191.9	1172.9	1163.9
7.5°	1411.4	1421.3	1417.6	1405.0	1390.9	1379.4	1355.2	1332.7	1301.3	1273.7	1250.1
10°	1543.4	1533.1	1525.0	1512.8	1499.8	1478.5	1453.3	1418.6	1378.5	1346.9	1311.7
12.5°	1642.3	1640.5	1630.3	1617.7	1599.3	1579.2	1548.2	1505.9	1459.2	1413.7	1373.5
15°	1776.9	1779.7	1772.9	1759.8	1733.7	1698.1	1651.2	1633.6	1566.9	1517.3	1467.7
17.5°	1870.2	1869.7	1868.7	1850.6	1823.9	1798.6	1755.1	1708.9	1648.5	1578.6	1511.8
20°	1929.3	1924.9	1925.7	1905.4	1885.6	1856.3	1814.0	1746.8	1697.2	1616.5	1547.5
22.5°	1927.9	1927.0	1930.4	1923.5	1909.0	1886.6	1853.2	1796.6	1733.3	1651.8	1574.2
25°	1831.1	1827.5	1848.7	1854.5	1877.5	1881.5	1871.6	1840.6	1780.5	1696.7	1600.7
27.5°	1532.5	1530.5	1569.8	1619.0	1681.4	1729.9	1776.8	1799.4	1780.5	1720.5	1624.4
30°	1257.7	1300.0	1319.9	1391.1	1470.4	1565.1	1648.0	1726.9	1746.3	1720.2	1641.2
32.5°	1044.2	1081.2	1097.7	1158.8	1232.8	1343.7	1468.1	1579.8	1658.7	1678.7	1631.2
35°	794.3	794.7	832.6	859.6	928.2	1042.2	1163.0	1312.7	1461.4	1574.1	1585.8
37.5°	633.8	636.0	658.9	685.9	737.3	797.6	904.0	1028.4	1200.2	1373.2	1474.6
40°	547.3	551.3	568.4	595.0	632.0	677.5	760.4	877.7	1021.0	1213.5	1370.8
42.5°	491.7	498.3	507.1	527.6	550.5	593.1	660.2	750.7	881.1	1063.1	1244.6
45°	423.7	427.3	434.1	443.6	464.3	494.0	539.2	599.9	708.2	854.7	1036.3
47.5°	373.8	371.9	379.0	386.7	400.5	420.8	451.0	500.7	577.8	695.3	849.5
50°	339.9	339.4	344.4	350.3	363.3	378.2	403.0	440.4	501.7	599.1	740.2
52.5°	308.2	309.9	313.4	320.7	330.1	342.2	364.4	391.3	444.0	528.1	645.7
55°	266.0	267.3	272.2	276.3	283.1	295.2	309.3	331.7	367.8	426.5	523.3
57.5°	230.2	229.6	234.4	235.4	243.1	253.0	263.8	281.3	307.5	350.9	416.2
60°	206.5	205.1	209.1	212.3	216.4	224.5	233.5	250.6	271.4	303.3	359.3
62.5°	184.9	184.2	187.2	190.3	193.6	201.0	208.6	221.8	238.2	265.2	309.5
65°	153.3	154.6	155.9	157.3	159.1	163.6	170.8	179.9	191.1	210.1	242.0
67.5°	120.5	121.8	122.3	125.0	128.9	131.7	136.1	144.1	152.0	168.0	186.1
70°	97.4	96.9	97.4	98.8	103.7	108.7	114.5	120.4	125.3	136.6	151.9
72.5°	83.7	82.8	84.0	84.3	86.7	88.1	91.8	97.3	103.7	111.3	122.3
75°	64.9	64.9	64.9	64.9	66.7	67.6	69.0	70.3	72.6	76.2	84.3
77.5°	48.0	48.0	48.6	49.2	49.5	50.0	50.9	52.2	53.0	54.9	58.5
80°	37.9	38.3	37.9	38.3	38.3	39.2	39.7	41.0	41.5	43.7	45.1
82.5°	28.5	28.2	28.5	28.9	28.9	29.9	30.0	30.9	31.0	32.2	33.6
85°	15.3	14.5	15.3	14.9	15.8	14.9	15.3	16.2	16.2	16.7	18.5
87.5°	7.7	8.3	7.5	7.8	7.7	8.0	7.9	7.8	8.4	7.9	7.9
90°	20.2	19.9	19.6	19.3	19.0	18.5	17.9	17.4	16.8	16.2	14.2
92.5°	22.4	22.1	22.0	21.8	21.6	21.1	20.1	19.1	18.2	17.2	15.8
95°	25.6	25.6	25.6	25.6	25.6	25.1	24.0	23.0	22.0	20.8	19.2
97.5°	27.7	27.6	27.5	27.3	27.1	26.4	25.2	24.1	22.9	21.7	32.5
100°	28.2	28.2	28.0	27.8	27.6	27.0	25.8	24.6	23.4	22.2	45.5
102.5°	28.8	28.5	28.2	28.0	27.7	29.4	33.1	36.9	40.6	44.3	69.7
105°	29.6	29.4	29.0	28.8	28.4	41.5	68.0	94.5	121.0	147.4	160.8
107.5°	93.0	113.0	132.9	152.9	172.8	192.5	212.0	231.4	250.8	270.2	268.0
110°	185.1	206.5	227.9	249.3	270.7	283.9	288.8	293.7	298.7	303.6	302.0



TEST NUMBER: P332312-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	317.6	322.1	326.6	331.1	335.6	337.9	337.8	337.7	337.6	337.5	335.9
115°	395.8	395.2	394.6	394.0	393.4	392.4	390.9	389.3	387.9	386.4	385.0
117.5°	439.7	439.5	439.5	439.4	439.2	438.5	437.4	436.2	435.0	433.8	433.1
120°	469.8	469.8	469.8	469.8	469.8	469.2	468.0	466.8	465.6	464.4	464.0
122.5°	499.5	499.4	499.2	499.1	498.9	498.5	497.7	496.8	496.0	495.2	494.6
125°	541.2	540.9	540.6	540.3	540.0	539.7	539.4	539.1	538.8	538.5	537.9
127.5°	581.3	581.6	581.9	582.2	582.5	582.4	581.9	581.4	581.0	580.5	579.8
130°	607.2	607.4	607.8	608.0	608.4	608.2	607.6	607.0	606.4	605.8	605.2
132.5°	630.9	631.3	631.7	632.1	632.5	632.4	631.8	631.2	630.7	630.1	629.6
135°	667.1	667.5	668.0	668.4	668.8	668.8	668.4	668.0	667.5	667.1	666.5
137.5°	701.1	701.5	701.7	702.1	702.3	702.1	701.4	700.7	700.0	699.2	698.9
140°	721.6	721.9	722.2	722.5	722.8	722.6	722.0	721.4	720.8	720.2	719.8
142.5°	740.5	740.9	741.2	741.7	742.1	742.1	741.6	741.1	740.6	740.2	739.7
145°	769.4	769.4	769.4	769.4	769.4	769.2	769.0	768.6	768.4	768.0	767.8
147.5°	790.9	791.6	792.3	793.0	793.7	793.8	793.6	793.2	793.0	792.6	792.4
150°	807.1	807.5	808.0	808.4	808.9	808.9	808.7	808.3	808.0	807.8	807.4
152.5°	820.0	820.7	821.4	822.1	822.8	822.9	822.3	821.7	821.2	820.7	820.5
155°	838.0	839.0	839.8	840.8	841.6	841.7	840.9	840.2	839.5	838.7	838.5
157.5°	853.3	854.5	855.6	856.8	857.9	858.1	857.1	856.3	855.4	854.5	854.6
160°	863.0	864.0	865.0	866.1	867.1	867.2	866.3	865.4	864.5	863.6	863.8
162.5°	872.1	873.1	873.9	874.9	875.8	875.7	874.8	873.7	872.7	871.7	871.8
165°	883.1	884.2	885.2	886.3	887.3	887.3	886.1	884.8	883.6	882.4	882.6
167.5°	891.0	892.3	893.5	894.7	895.9	895.9	894.7	893.5	892.3	891.0	891.0
170°	896.0	897.2	898.3	899.5	900.7	900.7	899.5	898.3	897.2	896.0	896.0
172.5°	898.6	899.9	901.3	902.6	903.9	904.0	902.8	901.6	900.3	899.1	899.1
175°	902.7	903.9	905.1	906.3	907.4	907.5	906.5	905.4	904.4	903.4	903.2
177.5°	903.9	905.1	906.3	907.5	908.7	908.8	907.8	906.9	905.9	904.9	904.8
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P332312-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1087.3	1086.2	1081.2	1075.4	1067.8	1062.7	1058.8	1056.6	1050.2	1042.2	1036.8
5°	1154.4	1140.9	1126.5	1108.9	1092.7	1076.0	1065.7	1053.4	1038.6	1021.9	1010.2
7.5°	1226.4	1199.9	1171.3	1141.9	1112.7	1086.6	1063.5	1043.7	1020.0	996.1	979.4
10°	1281.6	1242.8	1202.6	1161.7	1124.2	1089.1	1062.0	1035.4	1007.0	979.6	958.8
12.5°	1331.7	1280.7	1234.4	1184.0	1136.2	1094.2	1055.2	1023.9	989.7	960.4	936.8
15°	1395.2	1342.9	1286.9	1210.3	1146.8	1093.6	1046.3	1005.2	963.8	927.7	904.7
17.5°	1454.5	1375.8	1300.7	1236.7	1154.2	1087.7	1029.9	980.9	935.4	897.2	868.8
20°	1479.0	1402.8	1321.2	1239.7	1158.5	1084.1	1016.9	962.9	915.5	872.3	846.1
22.5°	1493.7	1407.5	1321.5	1233.9	1147.7	1070.4	1004.0	944.4	893.2	852.0	819.8
25°	1511.0	1408.3	1313.5	1227.0	1139.1	1055.2	976.4	913.3	857.8	814.1	779.8
27.5°	1522.3	1401.4	1289.6	1193.3	1104.2	1020.7	948.4	881.6	825.3	779.0	742.3
30°	1524.5	1396.0	1271.2	1167.1	1076.4	999.8	923.2	859.2	799.7	750.5	716.3
32.5°	1527.4	1382.7	1246.3	1135.7	1042.9	967.0	897.6	836.5	775.5	727.1	692.2
35°	1515.5	1375.4	1208.5	1081.4	988.5	915.1	852.4	796.1	736.2	689.2	653.6
37.5°	1464.3	1346.0	1169.4	1020.3	923.2	855.1	804.1	754.9	700.0	649.4	615.9
40°	1412.7	1317.2	1139.1	983.2	881.8	811.8	765.9	725.7	672.5	625.3	589.2
42.5°	1335.9	1277.9	1110.3	944.2	834.8	767.5	728.8	691.1	644.5	596.4	562.5
45°	1195.0	1202.6	1051.2	882.2	769.9	702.3	665.8	639.6	598.2	558.5	523.8
47.5°	1018.3	1089.9	981.9	816.1	701.5	638.0	606.1	583.3	555.3	516.4	484.7
50°	902.9	1005.2	926.3	771.7	658.6	595.5	564.0	545.4	521.1	490.4	460.2
52.5°	796.5	906.5	859.3	722.3	612.1	554.4	523.6	508.3	489.0	460.1	432.8
55°	649.5	761.0	750.1	647.7	542.3	490.4	467.0	449.9	436.8	415.2	393.6
57.5°	525.5	631.0	636.6	564.8	480.8	429.6	409.4	396.5	388.0	371.6	351.6
60°	447.2	544.1	563.0	508.9	436.8	391.8	371.9	361.5	354.7	341.7	326.4
62.5°	382.3	464.8	486.2	447.3	394.6	352.4	336.9	326.9	322.3	311.0	297.5
65°	292.6	361.1	381.8	360.2	332.7	298.9	286.3	277.7	273.6	267.3	257.4
67.5°	220.0	269.9	292.7	277.4	267.5	246.2	238.1	233.5	229.9	225.6	217.3
70°	176.7	213.7	237.1	233.1	225.0	213.7	207.8	204.7	201.0	197.4	190.2
72.5°	142.1	167.6	189.5	191.6	184.9	182.6	177.5	176.2	174.0	169.7	165.7
75°	94.2	111.8	127.1	132.9	135.7	137.9	135.7	135.3	134.7	131.2	128.9
77.5°	61.7	71.2	80.8	90.8	95.1	98.2	98.9	100.6	99.4	97.5	96.3
80°	47.4	49.6	56.3	64.9	71.6	74.4	76.2	77.1	76.6	76.2	74.4
82.5°	34.4	36.2	39.4	45.5	51.1	55.6	56.7	56.6	57.5	57.8	56.3
85°	18.5	18.9	19.8	20.8	23.8	28.8	30.2	31.1	32.0	32.0	29.3
87.5°	8.3	7.5	7.8	7.5	8.3	8.3	10.2	11.7	12.3	11.2	11.5
90°	12.2	10.3	8.4	6.6	5.2	3.7	2.2	0.7	2.2	3.7	5.2
92.5°	14.3	12.8	11.4	10.8	11.3	11.7	12.1	12.5	12.1	11.7	11.3
95°	17.6	15.9	14.3	16.5	22.6	28.8	35.0	41.1	35.0	28.8	22.6
97.5°	43.2	54.0	64.7	71.5	74.3	77.1	79.8	82.5	79.8	77.1	74.3
100°	68.9	92.2	115.5	125.7	122.7	119.8	116.8	113.7	116.8	119.8	122.7
102.5°	95.2	120.8	146.3	157.9	155.8	153.6	151.4	149.3	151.4	153.6	155.8
105°	174.4	187.8	201.3	207.2	205.5	203.9	202.2	200.6	202.2	203.9	205.5
107.5°	266.0	263.8	261.7	259.9	258.6	257.4	256.1	254.7	256.1	257.4	258.6
110°	300.3	298.7	297.0	295.6	294.4	293.2	292.0	290.8	292.0	293.2	294.4



TEST NUMBER: P332312-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	334.2	332.6	330.9	329.6	328.5	327.4	326.3	325.3	326.3	327.4	328.5
115°	383.7	382.4	381.0	379.9	379.0	378.1	377.2	376.3	377.2	378.1	379.0
117.5°	432.4	431.7	431.0	430.1	429.0	427.9	426.8	425.7	426.8	427.9	429.0
120°	463.6	463.1	462.7	461.8	460.4	459.1	457.7	456.4	457.7	459.1	460.4
122.5°	494.0	493.4	492.8	492.1	490.9	489.8	488.7	487.6	488.7	489.8	490.9
125°	537.3	536.7	536.1	535.2	534.0	532.8	531.6	530.5	531.6	532.8	534.0
127.5°	579.1	578.3	577.6	576.7	575.5	574.3	573.1	571.9	573.1	574.3	575.5
130°	604.6	604.0	603.4	602.5	601.3	600.1	598.9	597.7	598.9	600.1	601.3
132.5°	629.0	628.6	628.1	627.3	626.1	624.9	623.7	622.5	623.7	624.9	626.1
135°	665.9	665.3	664.7	663.9	663.1	662.1	661.2	660.3	661.2	662.1	663.1
137.5°	698.6	698.3	697.9	697.2	696.0	694.9	693.8	692.7	693.8	694.9	696.0
140°	719.4	718.9	718.4	717.8	716.9	716.0	715.1	714.2	715.1	716.0	716.9
142.5°	739.3	738.8	738.4	737.7	736.8	735.9	735.0	734.1	735.0	735.9	736.8
145°	767.4	767.2	766.8	766.2	765.1	764.1	763.0	762.0	763.0	764.1	765.1
147.5°	792.0	791.8	791.5	791.0	790.3	789.6	788.9	788.2	788.9	789.6	790.3
150°	807.2	806.8	806.6	806.2	805.7	805.3	804.9	804.3	804.9	805.3	805.7
152.5°	820.3	820.1	819.9	819.8	819.6	819.3	819.2	818.9	819.2	819.3	819.6
155°	838.4	838.3	838.1	838.2	838.5	838.8	839.1	839.4	839.1	838.8	838.5
157.5°	854.8	854.9	855.1	855.1	855.1	855.2	855.2	855.2	855.2	855.2	855.1
160°	863.9	864.1	864.2	864.4	864.5	864.7	864.8	865.0	864.8	864.7	864.5
162.5°	872.0	872.1	872.3	872.5	873.0	873.3	873.7	874.1	873.7	873.3	873.0
165°	882.8	883.0	883.0	883.4	883.8	884.2	884.7	885.2	884.7	884.2	883.8
167.5°	891.0	891.0	891.0	891.4	892.0	892.6	893.2	893.8	893.2	892.6	892.0
170°	896.0	896.0	896.0	896.2	896.8	897.4	898.0	898.6	898.0	897.4	896.8
172.5°	898.9	898.8	898.7	899.0	899.7	900.4	901.1	901.8	901.1	900.4	899.7
175°	903.0	902.8	902.8	903.0	903.8	904.6	905.3	906.0	905.3	904.6	903.8
177.5°	904.7	904.6	904.5	904.7	905.3	905.9	906.5	907.1	906.5	905.9	905.3
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P332312-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1035.0	1030.3	1027.1	1019.9	1015.1	1010.1	1005.0	1008.3	1008.0	1007.5	1007.5
5°	1000.3	989.9	980.4	968.3	960.6	951.1	943.9	943.1	944.9	938.5	934.9
7.5°	965.9	951.7	938.2	924.8	910.6	899.2	892.1	888.7	884.2	880.3	876.2
10°	941.7	925.0	911.9	895.3	879.9	866.4	857.8	852.0	848.8	845.7	839.8
12.5°	916.8	900.4	883.8	865.0	850.3	834.7	828.3	821.7	815.6	812.1	804.1
15°	880.4	859.2	841.6	821.7	805.6	790.2	781.2	768.1	766.3	761.8	753.7
17.5°	843.9	820.9	796.6	782.0	763.6	747.7	733.9	729.5	716.6	711.8	704.7
20°	815.0	793.8	775.3	756.0	729.4	714.5	703.7	697.8	687.4	681.1	676.6
22.5°	790.1	768.6	747.2	724.6	702.7	686.0	678.0	668.9	663.3	654.4	649.5
25°	754.6	731.2	705.5	681.1	665.4	652.7	640.1	632.0	623.9	619.8	610.8
27.5°	713.3	688.8	664.8	646.4	627.0	614.5	603.0	595.8	586.1	579.3	574.3
30°	690.6	661.8	641.0	624.3	599.5	587.8	579.3	570.2	563.0	555.8	550.9
32.5°	664.3	637.9	618.3	597.6	578.6	565.8	554.7	546.8	540.6	533.8	528.8
35°	622.9	600.9	580.6	559.8	545.9	532.8	519.8	513.0	507.1	500.8	496.3
37.5°	585.7	565.0	545.7	526.1	508.8	498.1	487.6	482.4	474.5	470.3	465.6
40°	562.6	542.3	521.5	502.7	484.6	476.5	467.0	459.3	452.1	449.0	444.0
42.5°	537.4	517.0	499.6	479.1	464.4	453.4	444.6	436.3	430.8	426.3	423.4
45°	499.9	481.9	464.8	444.4	430.5	421.0	411.1	403.5	398.5	395.4	390.4
47.5°	463.6	445.6	428.2	410.4	396.9	386.2	376.3	370.9	364.3	360.4	357.1
50°	437.2	421.0	402.5	386.3	372.8	362.0	353.9	347.1	341.2	336.3	334.1
52.5°	413.1	395.8	379.8	364.7	350.4	338.2	330.8	323.6	319.3	313.6	310.9
55°	373.2	356.5	343.0	328.1	314.2	303.8	294.8	288.5	284.0	277.7	274.1
57.5°	335.8	320.9	304.7	291.8	277.4	268.6	261.1	252.6	247.1	242.2	238.7
60°	310.6	293.4	279.5	267.3	254.7	243.4	236.7	229.9	224.0	219.0	215.9
62.5°	284.3	269.3	256.1	242.8	231.3	221.4	213.6	207.9	202.8	199.6	196.5
65°	243.8	232.1	218.6	207.8	197.0	189.8	183.5	178.5	174.9	172.6	170.0
67.5°	206.7	195.4	183.6	172.9	165.7	160.2	156.1	151.8	150.0	147.1	145.3
70°	182.5	170.8	160.5	152.4	145.2	141.1	138.4	135.3	133.5	129.8	128.0
72.5°	156.3	147.7	140.3	133.6	127.9	124.2	120.7	116.8	114.0	109.9	108.2
75°	123.0	115.4	109.5	105.0	101.4	96.4	91.5	87.5	86.1	84.7	84.3
77.5°	91.2	86.3	82.1	78.3	73.8	70.2	69.1	68.2	67.8	67.2	67.2
80°	71.6	67.2	64.0	59.5	56.8	56.8	56.8	55.9	56.3	56.3	56.3
82.5°	53.3	49.2	47.4	45.8	45.3	45.6	45.6	45.8	45.5	46.2	45.9
85°	27.5	28.0	28.8	28.4	28.8	28.8	29.8	29.3	29.8	28.8	29.8
87.5°	11.5	12.8	13.6	14.4	15.1	15.2	15.6	15.8	16.2	16.4	16.4
90°	6.6	8.4	10.3	12.2	14.2	16.2	16.8	17.4	17.9	18.5	19.0
92.5°	10.8	11.4	12.8	14.3	15.8	17.2	18.2	19.1	20.1	21.1	21.6
95°	16.5	14.3	15.9	17.6	19.2	20.8	22.0	23.0	24.0	25.1	25.6
97.5°	71.5	64.7	54.0	43.2	32.5	21.7	22.9	24.1	25.2	26.4	27.1
100°	125.7	115.5	92.2	68.9	45.5	22.2	23.4	24.6	25.8	27.0	27.6
102.5°	157.9	146.3	120.8	95.2	69.7	44.3	40.6	36.9	33.1	29.4	27.7
105°	207.2	201.3	187.8	174.4	160.8	147.4	121.0	94.5	68.0	41.5	28.4
107.5°	259.9	261.7	263.8	266.0	268.0	270.2	250.8	231.4	212.0	192.5	172.8
110°	295.6	297.0	298.7	300.3	302.0	303.6	298.7	293.7	288.8	283.9	270.7



TEST NUMBER: P332312-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	329.6	330.9	332.6	334.2	335.9	337.5	337.6	337.7	337.8	337.9	335.6
115°	379.9	381.0	382.4	383.7	385.0	386.4	387.9	389.3	390.9	392.4	393.4
117.5°	430.1	431.0	431.7	432.4	433.1	433.8	435.0	436.2	437.4	438.5	439.2
120°	461.8	462.7	463.1	463.6	464.0	464.4	465.6	466.8	468.0	469.2	469.8
122.5°	492.1	492.8	493.4	494.0	494.6	495.2	496.0	496.8	497.7	498.5	498.9
125°	535.2	536.1	536.7	537.3	537.9	538.5	538.8	539.1	539.4	539.7	540.0
127.5°	576.7	577.6	578.3	579.1	579.8	580.5	581.0	581.4	581.9	582.4	582.5
130°	602.5	603.4	604.0	604.6	605.2	605.8	606.4	607.0	607.6	608.2	608.4
132.5°	627.3	628.1	628.6	629.0	629.6	630.1	630.7	631.2	631.8	632.4	632.5
135°	663.9	664.7	665.3	665.9	666.5	667.1	667.5	668.0	668.4	668.8	668.8
137.5°	697.2	697.9	698.3	698.6	698.9	699.2	700.0	700.7	701.4	702.1	702.3
140°	717.8	718.4	718.9	719.4	719.8	720.2	720.8	721.4	722.0	722.6	722.8
142.5°	737.7	738.4	738.8	739.3	739.7	740.2	740.6	741.1	741.6	742.1	742.1
145°	766.2	766.8	767.2	767.4	767.8	768.0	768.4	768.6	769.0	769.2	769.4
147.5°	791.0	791.5	791.8	792.0	792.4	792.6	793.0	793.2	793.6	793.8	793.7
150°	806.2	806.6	806.8	807.2	807.4	807.8	808.0	808.3	808.7	808.9	808.9
152.5°	819.8	819.9	820.1	820.3	820.5	820.7	821.2	821.7	822.3	822.9	822.8
155°	838.2	838.1	838.3	838.4	838.5	838.7	839.5	840.2	840.9	841.7	841.6
157.5°	855.1	855.1	854.9	854.8	854.6	854.5	855.4	856.3	857.1	858.1	857.9
160°	864.4	864.2	864.1	863.9	863.8	863.6	864.5	865.4	866.3	867.2	867.1
162.5°	872.5	872.3	872.1	872.0	871.8	871.7	872.7	873.7	874.8	875.7	875.8
165°	883.4	883.0	883.0	882.8	882.6	882.4	883.6	884.8	886.1	887.3	887.3
167.5°	891.4	891.0	891.0	891.0	891.0	891.0	892.3	893.5	894.7	895.9	895.9
170°	896.2	896.0	896.0	896.0	896.0	896.0	897.2	898.3	899.5	900.7	900.7
172.5°	899.0	898.7	898.8	898.9	899.1	899.1	900.3	901.6	902.8	904.0	903.9
175°	903.0	902.8	902.8	903.0	903.2	903.4	904.4	905.4	906.5	907.5	907.4
177.5°	904.7	904.5	904.6	904.7	904.8	904.9	905.9	906.9	907.8	908.8	908.7
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P332312-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1003.2	1002.9	1003.2	1001.8	1003.2	1002.9	1003.2	1007.5	1007.5	1008.0	1008.3
5°	933.6	933.1	931.8	927.7	931.8	933.1	933.6	934.9	938.5	944.9	943.1
7.5°	872.7	872.1	868.1	868.2	868.1	872.1	872.7	876.2	880.3	884.2	888.7
10°	836.6	837.1	831.7	828.5	831.7	837.1	836.6	839.8	845.7	848.8	852.0
12.5°	801.7	799.6	795.2	791.8	795.2	799.6	801.7	804.1	812.1	815.6	821.7
15°	755.5	751.0	740.2	741.1	740.2	751.0	755.5	753.7	761.8	766.3	768.1
17.5°	701.1	697.8	697.6	691.3	697.6	697.8	701.1	704.7	711.8	716.6	729.5
20°	669.4	667.2	668.0	661.8	668.0	667.2	669.4	676.6	681.1	687.4	697.8
22.5°	644.5	642.3	638.5	636.5	638.5	642.3	644.5	649.5	654.4	663.3	668.9
25°	608.1	604.5	600.9	603.1	600.9	604.5	608.1	610.8	619.8	623.9	632.0
27.5°	571.7	568.9	565.3	564.9	565.3	568.9	571.7	574.3	579.3	586.1	595.8
30°	548.6	545.9	544.1	541.8	544.1	545.9	548.6	550.9	555.8	563.0	570.2
32.5°	525.1	524.6	521.3	520.9	521.3	524.6	525.1	528.8	533.8	540.6	546.8
35°	494.5	491.8	490.9	491.4	490.9	491.8	494.5	496.3	500.8	507.1	513.0
37.5°	465.4	461.8	460.1	458.6	460.1	461.8	465.4	465.6	470.3	474.5	482.4
40°	444.4	440.8	440.0	439.0	440.0	440.8	444.4	444.0	449.0	452.1	459.3
42.5°	421.0	419.6	419.0	417.4	419.0	419.6	421.0	423.4	426.3	430.8	436.3
45°	389.0	388.6	385.9	386.8	385.9	388.6	389.0	390.4	395.4	398.5	403.5
47.5°	355.3	353.4	351.5	352.7	351.5	353.4	355.3	357.1	360.4	364.3	370.9
50°	332.3	331.3	327.3	328.1	327.3	331.3	332.3	334.1	336.3	341.2	347.1
52.5°	309.2	305.7	304.2	303.7	304.2	305.7	309.2	310.9	313.6	319.3	323.6
55°	271.0	266.8	265.0	264.2	265.0	266.8	271.0	274.1	277.7	284.0	288.5
57.5°	233.4	232.3	230.9	231.9	230.9	232.3	233.4	238.7	242.2	247.1	252.6
60°	211.4	211.4	211.4	210.9	211.4	211.4	211.4	215.9	219.0	224.0	229.9
62.5°	194.5	193.4	193.0	193.6	193.0	193.4	194.5	196.5	199.6	202.8	207.9
65°	168.6	168.2	166.3	165.9	166.3	168.2	168.6	170.0	172.6	174.9	178.5
67.5°	144.1	142.5	142.0	141.4	142.0	142.5	144.1	145.3	147.1	150.0	151.8
70°	125.8	124.8	122.2	122.6	122.2	124.8	125.8	128.0	129.8	133.5	135.3
72.5°	105.9	105.0	104.5	103.8	104.5	105.0	105.9	108.2	109.9	114.0	116.8
75°	83.9	83.4	82.9	84.7	82.9	83.4	83.9	84.3	84.7	86.1	87.5
77.5°	67.2	67.2	67.4	66.7	67.4	67.2	67.2	67.2	67.2	67.8	68.2
80°	56.3	56.3	55.9	55.9	55.9	56.3	56.3	56.3	56.3	56.3	55.9
82.5°	45.2	45.5	45.8	45.1	45.8	45.5	45.2	45.9	46.2	45.5	45.8
85°	29.8	29.3	30.2	29.8	30.2	29.3	29.8	29.8	28.8	29.8	29.3
87.5°	17.2	16.5	16.6	17.0	16.6	16.5	17.2	16.4	16.4	16.2	15.8
90°	19.3	19.6	19.9	20.2	19.9	19.6	19.3	19.0	18.5	17.9	17.4
92.5°	21.8	22.0	22.1	22.4	22.1	22.0	21.8	21.6	21.1	20.1	19.1
95°	25.6	25.6	25.6	25.6	25.6	25.6	25.6	25.6	25.1	24.0	23.0
97.5°	27.3	27.5	27.6	27.7	27.6	27.5	27.3	27.1	26.4	25.2	24.1
100°	27.8	28.0	28.2	28.2	28.2	28.0	27.8	27.6	27.0	25.8	24.6
102.5°	28.0	28.2	28.5	28.8	28.5	28.2	28.0	27.7	29.4	33.1	36.9
105°	28.8	29.0	29.4	29.6	29.4	29.0	28.8	28.4	41.5	68.0	94.5
107.5°	152.9	132.9	113.0	93.0	113.0	132.9	152.9	172.8	192.5	212.0	231.4
110°	249.3	227.9	206.5	185.1	206.5	227.9	249.3	270.7	283.9	288.8	293.7



TEST NUMBER: P332312-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	331.1	326.6	322.1	317.6	322.1	326.6	331.1	335.6	337.9	337.8	337.7
115°	394.0	394.6	395.2	395.8	395.2	394.6	394.0	393.4	392.4	390.9	389.3
117.5°	439.4	439.5	439.5	439.7	439.5	439.5	439.4	439.2	438.5	437.4	436.2
120°	469.8	469.8	469.8	469.8	469.8	469.8	469.8	469.8	469.2	468.0	466.8
122.5°	499.1	499.2	499.4	499.5	499.4	499.2	499.1	498.9	498.5	497.7	496.8
125°	540.3	540.6	540.9	541.2	540.9	540.6	540.3	540.0	539.7	539.4	539.1
127.5°	582.2	581.9	581.6	581.3	581.6	581.9	582.2	582.5	582.4	581.9	581.4
130°	608.0	607.8	607.4	607.2	607.4	607.8	608.0	608.4	608.2	607.6	607.0
132.5°	632.1	631.7	631.3	630.9	631.3	631.7	632.1	632.5	632.4	631.8	631.2
135°	668.4	668.0	667.5	667.1	667.5	668.0	668.4	668.8	668.8	668.4	668.0
137.5°	702.1	701.7	701.5	701.1	701.5	701.7	702.1	702.3	702.1	701.4	700.7
140°	722.5	722.2	721.9	721.6	721.9	722.2	722.5	722.8	722.6	722.0	721.4
142.5°	741.7	741.2	740.9	740.5	740.9	741.2	741.7	742.1	742.1	741.6	741.1
145°	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.2	769.0	768.6
147.5°	793.0	792.3	791.6	790.9	791.6	792.3	793.0	793.7	793.8	793.6	793.2
150°	808.4	808.0	807.5	807.1	807.5	808.0	808.4	808.9	808.9	808.7	808.3
152.5°	822.1	821.4	820.7	820.0	820.7	821.4	822.1	822.8	822.9	822.3	821.7
155°	840.8	839.8	839.0	838.0	839.0	839.8	840.8	841.6	841.7	840.9	840.2
157.5°	856.8	855.6	854.5	853.3	854.5	855.6	856.8	857.9	858.1	857.1	856.3
160°	866.1	865.0	864.0	863.0	864.0	865.0	866.1	867.1	867.2	866.3	865.4
162.5°	874.9	873.9	873.1	872.1	873.1	873.9	874.9	875.8	875.7	874.8	873.7
165°	886.3	885.2	884.2	883.1	884.2	885.2	886.3	887.3	887.3	886.1	884.8
167.5°	894.7	893.5	892.3	891.0	892.3	893.5	894.7	895.9	895.9	894.7	893.5
170°	899.5	898.3	897.2	896.0	897.2	898.3	899.5	900.7	900.7	899.5	898.3
172.5°	902.6	901.3	899.9	898.6	899.9	901.3	902.6	903.9	904.0	902.8	901.6
175°	906.3	905.1	903.9	902.7	903.9	905.1	906.3	907.4	907.5	906.5	905.4
177.5°	907.5	906.3	905.1	903.9	905.1	906.3	907.5	908.7	908.8	907.8	906.9
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P332312-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1005.0	1010.1	1015.1	1019.9	1027.1	1030.3	1035.0	1036.8	1042.2	1050.2	1056.6
5°	943.9	951.1	960.6	968.3	980.4	989.9	1000.3	1010.2	1021.9	1038.6	1053.4
7.5°	892.1	899.2	910.6	924.8	938.2	951.7	965.9	979.4	996.1	1020.0	1043.7
10°	857.8	866.4	879.9	895.3	911.9	925.0	941.7	958.8	979.6	1007.0	1035.4
12.5°	828.3	834.7	850.3	865.0	883.8	900.4	916.8	936.8	960.4	989.7	1023.9
15°	781.2	790.2	805.6	821.7	841.6	859.2	880.4	904.7	927.7	963.8	1005.2
17.5°	733.9	747.7	763.6	782.0	796.6	820.9	843.9	868.8	897.2	935.4	980.9
20°	703.7	714.5	729.4	756.0	775.3	793.8	815.0	846.1	872.3	915.5	962.9
22.5°	678.0	686.0	702.7	724.6	747.2	768.6	790.1	819.8	852.0	893.2	944.4
25°	640.1	652.7	665.4	681.1	705.5	731.2	754.6	779.8	814.1	857.8	913.3
27.5°	603.0	614.5	627.0	646.4	664.8	688.8	713.3	742.3	779.0	825.3	881.6
30°	579.3	587.8	599.5	624.3	641.0	661.8	690.6	716.3	750.5	799.7	859.2
32.5°	554.7	565.8	578.6	597.6	618.3	637.9	664.3	692.2	727.1	775.5	836.5
35°	519.8	532.8	545.9	559.8	580.6	600.9	622.9	653.6	689.2	736.2	796.1
37.5°	487.6	498.1	508.8	526.1	545.7	565.0	585.7	615.9	649.4	700.0	754.9
40°	467.0	476.5	484.6	502.7	521.5	542.3	562.6	589.2	625.3	672.5	725.7
42.5°	444.6	453.4	464.4	479.1	499.6	517.0	537.4	562.5	596.4	644.5	691.1
45°	411.1	421.0	430.5	444.4	464.8	481.9	499.9	523.8	558.5	598.2	639.6
47.5°	376.3	386.2	396.9	410.4	428.2	445.6	463.6	484.7	516.4	555.3	583.3
50°	353.9	362.0	372.8	386.3	402.5	421.0	437.2	460.2	490.4	521.1	545.4
52.5°	330.8	338.2	350.4	364.7	379.8	395.8	413.1	432.8	460.1	489.0	508.3
55°	294.8	303.8	314.2	328.1	343.0	356.5	373.2	393.6	415.2	436.8	449.9
57.5°	261.1	268.6	277.4	291.8	304.7	320.9	335.8	351.6	371.6	388.0	396.5
60°	236.7	243.4	254.7	267.3	279.5	293.4	310.6	326.4	341.7	354.7	361.5
62.5°	213.6	221.4	231.3	242.8	256.1	269.3	284.3	297.5	311.0	322.3	326.9
65°	183.5	189.8	197.0	207.8	218.6	232.1	243.8	257.4	267.3	273.6	277.7
67.5°	156.1	160.2	165.7	172.9	183.6	195.4	206.7	217.3	225.6	229.9	233.5
70°	138.4	141.1	145.2	152.4	160.5	170.8	182.5	190.2	197.4	201.0	204.7
72.5°	120.7	124.2	127.9	133.6	140.3	147.7	156.3	165.7	169.7	174.0	176.2
75°	91.5	96.4	101.4	105.0	109.5	115.4	123.0	128.9	131.2	134.7	135.3
77.5°	69.1	70.2	73.8	78.3	82.1	86.3	91.2	96.3	97.5	99.4	100.6
80°	56.8	56.8	56.8	59.5	64.0	67.2	71.6	74.4	76.2	76.6	77.1
82.5°	45.6	45.6	45.3	45.8	47.4	49.2	53.3	56.3	57.8	57.5	56.6
85°	29.8	28.8	28.8	28.4	28.8	28.0	27.5	29.3	32.0	32.0	31.1
87.5°	15.6	15.2	15.1	14.4	13.6	12.8	11.5	11.5	11.2	12.3	11.7
90°	16.8	16.2	14.2	12.2	10.3	8.4	6.6	5.2	3.7	2.2	0.7
92.5°	18.2	17.2	15.8	14.3	12.8	11.4	10.8	11.3	11.7	12.1	12.5
95°	22.0	20.8	19.2	17.6	15.9	14.3	16.5	22.6	28.8	35.0	41.1
97.5°	22.9	21.7	32.5	43.2	54.0	64.7	71.5	74.3	77.1	79.8	82.5
100°	23.4	22.2	45.5	68.9	92.2	115.5	125.7	122.7	119.8	116.8	113.7
102.5°	40.6	44.3	69.7	95.2	120.8	146.3	157.9	155.8	153.6	151.4	149.3
105°	121.0	147.4	160.8	174.4	187.8	201.3	207.2	205.5	203.9	202.2	200.6
107.5°	250.8	270.2	268.0	266.0	263.8	261.7	259.9	258.6	257.4	256.1	254.7
110°	298.7	303.6	302.0	300.3	298.7	297.0	295.6	294.4	293.2	292.0	290.8



TEST NUMBER: P332312-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	337.6	337.5	335.9	334.2	332.6	330.9	329.6	328.5	327.4	326.3	325.3
115°	387.9	386.4	385.0	383.7	382.4	381.0	379.9	379.0	378.1	377.2	376.3
117.5°	435.0	433.8	433.1	432.4	431.7	431.0	430.1	429.0	427.9	426.8	425.7
120°	465.6	464.4	464.0	463.6	463.1	462.7	461.8	460.4	459.1	457.7	456.4
122.5°	496.0	495.2	494.6	494.0	493.4	492.8	492.1	490.9	489.8	488.7	487.6
125°	538.8	538.5	537.9	537.3	536.7	536.1	535.2	534.0	532.8	531.6	530.5
127.5°	581.0	580.5	579.8	579.1	578.3	577.6	576.7	575.5	574.3	573.1	571.9
130°	606.4	605.8	605.2	604.6	604.0	603.4	602.5	601.3	600.1	598.9	597.7
132.5°	630.7	630.1	629.6	629.0	628.6	628.1	627.3	626.1	624.9	623.7	622.5
135°	667.5	667.1	666.5	665.9	665.3	664.7	663.9	663.1	662.1	661.2	660.3
137.5°	700.0	699.2	698.9	698.6	698.3	697.9	697.2	696.0	694.9	693.8	692.7
140°	720.8	720.2	719.8	719.4	718.9	718.4	717.8	716.9	716.0	715.1	714.2
142.5°	740.6	740.2	739.7	739.3	738.8	738.4	737.7	736.8	735.9	735.0	734.1
145°	768.4	768.0	767.8	767.4	767.2	766.8	766.2	765.1	764.1	763.0	762.0
147.5°	793.0	792.6	792.4	792.0	791.8	791.5	791.0	790.3	789.6	788.9	788.2
150°	808.0	807.8	807.4	807.2	806.8	806.6	806.2	805.7	805.3	804.9	804.3
152.5°	821.2	820.7	820.5	820.3	820.1	819.9	819.8	819.6	819.3	819.2	818.9
155°	839.5	838.7	838.5	838.4	838.3	838.1	838.2	838.5	838.8	839.1	839.4
157.5°	855.4	854.5	854.6	854.8	854.9	855.1	855.1	855.1	855.2	855.2	855.2
160°	864.5	863.6	863.8	863.9	864.1	864.2	864.4	864.5	864.7	864.8	865.0
162.5°	872.7	871.7	871.8	872.0	872.1	872.3	872.5	873.0	873.3	873.7	874.1
165°	883.6	882.4	882.6	882.8	883.0	883.0	883.4	883.8	884.2	884.7	885.2
167.5°	892.3	891.0	891.0	891.0	891.0	891.0	891.4	892.0	892.6	893.2	893.8
170°	897.2	896.0	896.0	896.0	896.0	896.0	896.2	896.8	897.4	898.0	898.6
172.5°	900.3	899.1	899.1	898.9	898.8	898.7	899.0	899.7	900.4	901.1	901.8
175°	904.4	903.4	903.2	903.0	902.8	902.8	903.0	903.8	904.6	905.3	906.0
177.5°	905.9	904.9	904.8	904.7	904.6	904.5	904.7	905.3	905.9	906.5	907.1
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P332312-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1058.8	1062.7	1067.8	1075.4	1081.2	1086.2	1087.3	1088.7	1092.4	1098.5	1103.1
5°	1065.7	1076.0	1092.7	1108.9	1126.5	1140.9	1154.4	1163.9	1172.9	1191.9	1207.2
7.5°	1063.5	1086.6	1112.7	1141.9	1171.3	1199.9	1226.4	1250.1	1273.7	1301.3	1332.7
10°	1062.0	1089.1	1124.2	1161.7	1202.6	1242.8	1281.6	1311.7	1346.9	1378.5	1418.6
12.5°	1055.2	1094.2	1136.2	1184.0	1234.4	1280.7	1331.7	1373.5	1413.7	1459.2	1505.9
15°	1046.3	1093.6	1146.8	1210.3	1286.9	1342.9	1395.2	1467.7	1517.3	1566.9	1633.6
17.5°	1029.9	1087.7	1154.2	1236.7	1300.7	1375.8	1454.5	1511.8	1578.6	1648.5	1708.9
20°	1016.9	1084.1	1158.5	1239.7	1321.2	1402.8	1479.0	1547.5	1616.5	1697.2	1746.8
22.5°	1004.0	1070.4	1147.7	1233.9	1321.5	1407.5	1493.7	1574.2	1651.8	1733.3	1796.6
25°	976.4	1055.2	1139.1	1227.0	1313.5	1408.3	1511.0	1600.7	1696.7	1780.5	1840.6
27.5°	948.4	1020.7	1104.2	1193.3	1289.6	1401.4	1522.3	1624.4	1720.5	1780.5	1799.4
30°	923.2	999.8	1076.4	1167.1	1271.2	1396.0	1524.5	1641.2	1720.2	1746.3	1726.9
32.5°	897.6	967.0	1042.9	1135.7	1246.3	1382.7	1527.4	1631.2	1678.7	1658.7	1579.8
35°	852.4	915.1	988.5	1081.4	1208.5	1375.4	1515.5	1585.8	1574.1	1461.4	1312.7
37.5°	804.1	855.1	923.2	1020.3	1169.4	1346.0	1464.3	1474.6	1373.2	1200.2	1028.4
40°	765.9	811.8	881.8	983.2	1139.1	1317.2	1412.7	1370.8	1213.5	1021.0	877.7
42.5°	728.8	767.5	834.8	944.2	1110.3	1277.9	1335.9	1244.6	1063.1	881.1	750.7
45°	665.8	702.3	769.9	882.2	1051.2	1202.6	1195.0	1036.3	854.7	708.2	599.9
47.5°	606.1	638.0	701.5	816.1	981.9	1089.9	1018.3	849.5	695.3	577.8	500.7
50°	564.0	595.5	658.6	771.7	926.3	1005.2	902.9	740.2	599.1	501.7	440.4
52.5°	523.6	554.4	612.1	722.3	859.3	906.5	796.5	645.7	528.1	444.0	391.3
55°	467.0	490.4	542.3	647.7	750.1	761.0	649.5	523.3	426.5	367.8	331.7
57.5°	409.4	429.6	480.8	564.8	636.6	631.0	525.5	416.2	350.9	307.5	281.3
60°	371.9	391.8	436.8	508.9	563.0	544.1	447.2	359.3	303.3	271.4	250.6
62.5°	336.9	352.4	394.6	447.3	486.2	464.8	382.3	309.5	265.2	238.2	221.8
65°	286.3	298.9	332.7	360.2	381.8	361.1	292.6	242.0	210.1	191.1	179.9
67.5°	238.1	246.2	267.5	277.4	292.7	269.9	220.0	186.1	168.0	152.0	144.1
70°	207.8	213.7	225.0	233.1	237.1	213.7	176.7	151.9	136.6	125.3	120.4
72.5°	177.5	182.6	184.9	191.6	189.5	167.6	142.1	122.3	111.3	103.7	97.3
75°	135.7	137.9	135.7	132.9	127.1	111.8	94.2	84.3	76.2	72.6	70.3
77.5°	98.9	98.2	95.1	90.8	80.8	71.2	61.7	58.5	54.9	53.0	52.2
80°	76.2	74.4	71.6	64.9	56.3	49.6	47.4	45.1	43.7	41.5	41.0
82.5°	56.7	55.6	51.1	45.5	39.4	36.2	34.4	33.6	32.2	31.0	30.9
85°	30.2	28.8	23.8	20.8	19.8	18.9	18.5	18.5	16.7	16.2	16.2
87.5°	10.2	8.3	8.3	7.5	7.8	7.5	8.3	7.9	7.9	8.4	7.8
90°	2.2	3.7	5.2	6.6	8.4	10.3	12.2	14.2	16.2	16.8	17.4
92.5°	12.1	11.7	11.3	10.8	11.4	12.8	14.3	15.8	17.2	18.2	19.1
95°	35.0	28.8	22.6	16.5	14.3	15.9	17.6	19.2	20.8	22.0	23.0
97.5°	79.8	77.1	74.3	71.5	64.7	54.0	43.2	32.5	21.7	22.9	24.1
100°	116.8	119.8	122.7	125.7	115.5	92.2	68.9	45.5	22.2	23.4	24.6
102.5°	151.4	153.6	155.8	157.9	146.3	120.8	95.2	69.7	44.3	40.6	36.9
105°	202.2	203.9	205.5	207.2	201.3	187.8	174.4	160.8	147.4	121.0	94.5
107.5°	256.1	257.4	258.6	259.9	261.7	263.8	266.0	268.0	270.2	250.8	231.4
110°	292.0	293.2	294.4	295.6	297.0	298.7	300.3	302.0	303.6	298.7	293.7



TEST NUMBER: P332312-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	326.3	327.4	328.5	329.6	330.9	332.6	334.2	335.9	337.5	337.6	337.7
115°	377.2	378.1	379.0	379.9	381.0	382.4	383.7	385.0	386.4	387.9	389.3
117.5°	426.8	427.9	429.0	430.1	431.0	431.7	432.4	433.1	433.8	435.0	436.2
120°	457.7	459.1	460.4	461.8	462.7	463.1	463.6	464.0	464.4	465.6	466.8
122.5°	488.7	489.8	490.9	492.1	492.8	493.4	494.0	494.6	495.2	496.0	496.8
125°	531.6	532.8	534.0	535.2	536.1	536.7	537.3	537.9	538.5	538.8	539.1
127.5°	573.1	574.3	575.5	576.7	577.6	578.3	579.1	579.8	580.5	581.0	581.4
130°	598.9	600.1	601.3	602.5	603.4	604.0	604.6	605.2	605.8	606.4	607.0
132.5°	623.7	624.9	626.1	627.3	628.1	628.6	629.0	629.6	630.1	630.7	631.2
135°	661.2	662.1	663.1	663.9	664.7	665.3	665.9	666.5	667.1	667.5	668.0
137.5°	693.8	694.9	696.0	697.2	697.9	698.3	698.6	698.9	699.2	700.0	700.7
140°	715.1	716.0	716.9	717.8	718.4	718.9	719.4	719.8	720.2	720.8	721.4
142.5°	735.0	735.9	736.8	737.7	738.4	738.8	739.3	739.7	740.2	740.6	741.1
145°	763.0	764.1	765.1	766.2	766.8	767.2	767.4	767.8	768.0	768.4	768.6
147.5°	788.9	789.6	790.3	791.0	791.5	791.8	792.0	792.4	792.6	793.0	793.2
150°	804.9	805.3	805.7	806.2	806.6	806.8	807.2	807.4	807.8	808.0	808.3
152.5°	819.2	819.3	819.6	819.8	819.9	820.1	820.3	820.5	820.7	821.2	821.7
155°	839.1	838.8	838.5	838.2	838.1	838.3	838.4	838.5	838.7	839.5	840.2
157.5°	855.2	855.2	855.1	855.1	855.1	854.9	854.8	854.6	854.5	855.4	856.3
160°	864.8	864.7	864.5	864.4	864.2	864.1	863.9	863.8	863.6	864.5	865.4
162.5°	873.7	873.3	873.0	872.5	872.3	872.1	872.0	871.8	871.7	872.7	873.7
165°	884.7	884.2	883.8	883.4	883.0	883.0	882.8	882.6	882.4	883.6	884.8
167.5°	893.2	892.6	892.0	891.4	891.0	891.0	891.0	891.0	891.0	892.3	893.5
170°	898.0	897.4	896.8	896.2	896.0	896.0	896.0	896.0	896.0	897.2	898.3
172.5°	901.1	900.4	899.7	899.0	898.7	898.8	898.9	899.1	899.1	900.3	901.6
175°	905.3	904.6	903.8	903.0	902.8	902.8	903.0	903.2	903.4	904.4	905.4
177.5°	906.5	905.9	905.3	904.7	904.5	904.6	904.7	904.8	904.9	905.9	906.9
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P332312-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1110.7	1110.7	1112.2	1117.6	1118.3	1123.0	1121.5
5°	1220.7	1229.2	1232.4	1246.0	1254.0	1257.7	1250.4
7.5°	1355.2	1379.4	1390.9	1405.0	1417.6	1421.3	1411.4
10°	1453.3	1478.5	1499.8	1512.8	1525.0	1533.1	1543.4
12.5°	1548.2	1579.2	1599.3	1617.7	1630.3	1640.5	1642.3
15°	1651.2	1698.1	1733.7	1759.8	1772.9	1779.7	1776.9
17.5°	1755.1	1798.6	1823.9	1850.6	1868.7	1869.7	1870.2
20°	1814.0	1856.3	1885.6	1905.4	1925.7	1924.9	1929.3
22.5°	1853.2	1886.6	1909.0	1923.5	1930.4	1927.0	1927.9
25°	1871.6	1881.5	1877.5	1854.5	1848.7	1827.5	1831.1
27.5°	1776.8	1729.9	1681.4	1619.0	1569.8	1530.5	1532.5
30°	1648.0	1565.1	1470.4	1391.1	1319.9	1300.0	1257.7
32.5°	1468.1	1343.7	1232.8	1158.8	1097.7	1081.2	1044.2
35°	1163.0	1042.2	928.2	859.6	832.6	794.7	794.3
37.5°	904.0	797.6	737.3	685.9	658.9	636.0	633.8
40°	760.4	677.5	632.0	595.0	568.4	551.3	547.3
42.5°	660.2	593.1	550.5	527.6	507.1	498.3	491.7
45°	539.2	494.0	464.3	443.6	434.1	427.3	423.7
47.5°	451.0	420.8	400.5	386.7	379.0	371.9	373.8
50°	403.0	378.2	363.3	350.3	344.4	339.4	339.9
52.5°	364.4	342.2	330.1	320.7	313.4	309.9	308.2
55°	309.3	295.2	283.1	276.3	272.2	267.3	266.0
57.5°	263.8	253.0	243.1	235.4	234.4	229.6	230.2
60°	233.5	224.5	216.4	212.3	209.1	205.1	206.5
62.5°	208.6	201.0	193.6	190.3	187.2	184.2	184.9
65°	170.8	163.6	159.1	157.3	155.9	154.6	153.3
67.5°	136.1	131.7	128.9	125.0	122.3	121.8	120.5
70°	114.5	108.7	103.7	98.8	97.4	96.9	97.4
72.5°	91.8	88.1	86.7	84.3	84.0	82.8	83.7
75°	69.0	67.6	66.7	64.9	64.9	64.9	64.9
77.5°	50.9	50.0	49.5	49.2	48.6	48.0	48.0
80°	39.7	39.2	38.3	38.3	37.9	38.3	37.9
82.5°	30.0	29.9	28.9	28.9	28.5	28.2	28.5
85°	15.3	14.9	15.8	14.9	15.3	14.5	15.3
87.5°	7.9	8.0	7.7	7.8	7.5	8.3	7.7
90°	17.9	18.5	19.0	19.3	19.6	19.9	20.2
92.5°	20.1	21.1	21.6	21.8	22.0	22.1	22.4
95°	24.0	25.1	25.6	25.6	25.6	25.6	25.6
97.5°	25.2	26.4	27.1	27.3	27.5	27.6	27.7
100°	25.8	27.0	27.6	27.8	28.0	28.2	28.2
102.5°	33.1	29.4	27.7	28.0	28.2	28.5	28.8
105°	68.0	41.5	28.4	28.8	29.0	29.4	29.6
107.5°	212.0	192.5	172.8	152.9	132.9	113.0	93.0
110°	288.8	283.9	270.7	249.3	227.9	206.5	185.1



TEST NUMBER: P332312-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	337.8	337.9	335.6	331.1	326.6	322.1	317.6
115°	390.9	392.4	393.4	394.0	394.6	395.2	395.8
117.5°	437.4	438.5	439.2	439.4	439.5	439.5	439.7
120°	468.0	469.2	469.8	469.8	469.8	469.8	469.8
122.5°	497.7	498.5	498.9	499.1	499.2	499.4	499.5
125°	539.4	539.7	540.0	540.3	540.6	540.9	541.2
127.5°	581.9	582.4	582.5	582.2	581.9	581.6	581.3
130°	607.6	608.2	608.4	608.0	607.8	607.4	607.2
132.5°	631.8	632.4	632.5	632.1	631.7	631.3	630.9
135°	668.4	668.8	668.8	668.4	668.0	667.5	667.1
137.5°	701.4	702.1	702.3	702.1	701.7	701.5	701.1
140°	722.0	722.6	722.8	722.5	722.2	721.9	721.6
142.5°	741.6	742.1	742.1	741.7	741.2	740.9	740.5
145°	769.0	769.2	769.4	769.4	769.4	769.4	769.4
147.5°	793.6	793.8	793.7	793.0	792.3	791.6	790.9
150°	808.7	808.9	808.9	808.4	808.0	807.5	807.1
152.5°	822.3	822.9	822.8	822.1	821.4	820.7	820.0
155°	840.9	841.7	841.6	840.8	839.8	839.0	838.0
157.5°	857.1	858.1	857.9	856.8	855.6	854.5	853.3
160°	866.3	867.2	867.1	866.1	865.0	864.0	863.0
162.5°	874.8	875.7	875.8	874.9	873.9	873.1	872.1
165°	886.1	887.3	887.3	886.3	885.2	884.2	883.1
167.5°	894.7	895.9	895.9	894.7	893.5	892.3	891.0
170°	899.5	900.7	900.7	899.5	898.3	897.2	896.0
172.5°	902.8	904.0	903.9	902.6	901.3	899.9	898.6
175°	906.5	907.5	907.4	906.3	905.1	903.9	902.7
177.5°	907.8	908.8	908.7	907.5	906.3	905.1	903.9
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0

(END OF REPORT)