

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332314-935

Luminaire Tested: **S123RDIP-S775D805U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332314-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D805U935-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5126.2 lumens
Efficiency: N/A
Efficacy: 111.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332314-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332314-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	99	95	91	88	91	88	84	82	75	72	70	63	61	60	51	50	49	44
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	46	44	43	38
3	83	74	67	61	76	69	62	57	59	54	50	50	46	44	41	39	37	33
4	76	66	58	52	70	61	54	49	53	47	43	45	41	38	37	35	32	29
5	70	59	51	45	65	55	48	43	47	42	38	40	36	33	34	31	28	25
6	65	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25	23
7	60	48	40	35	55	45	38	33	39	34	30	34	29	26	28	25	23	20
8	56	44	36	31	51	41	34	29	36	30	26	31	27	23	26	23	20	18
9	52	40	33	28	48	37	31	26	33	27	24	28	24	21	24	21	19	17
10	49	37	30	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11334	11334	11334	11334
5°	13511	11382	10024	11382
10°	16869	11317	9055	11317
15°	19801	11202	8259	11202
20°	22100	11030	7581	11030
25°	21747	10847	7163	10847
30°	15632	10679	6734	10679
35°	10437	10461	6457	10461
40°	7690	10197	6169	10197
45°	6450	9736	5888	9736
50°	5692	9133	5494	9133
55°	4992	8443	4958	8443
60°	4445	7782	4540	7782
65°	3904	7073	4225	7073
70°	3065	6442	3858	6442
75°	2699	5627	3523	5627
80°	2349	4779	3465	4779
85°	1890	3841	3680	3841



TEST NUMBER: P332314-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.6	2.0
10°-20°	323.5	6.3
20°-30°	508.3	9.9
30°-40°	530.3	10.3
40°-50°	453.8	8.9
50°-60°	345.9	6.7
60°-70°	221.7	4.3
70°-80°	106.6	2.1
80°-90°	30.8	0.6
90°-100°	185.1	3.6
100°-110°	524.0	10.2
110°-120°	515.5	10.1
120°-130°	411.2	8.0
130°-140°	324.2	6.3
140°-150°	242.0	4.7
150°-160°	168.6	3.3
160°-170°	99.1	1.9
170°-180°	32.2	0.6
0°-30°	935.3	18.2
0°-40°	1465.6	28.6
0°-60°	2265.3	44.2
0°-90°	2624.4	51.2
90°-120°	1224.6	23.9
90°-150°	2201.9	43.0
90°-180°	2502.0	48.8
0°-180°	5126.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1053	1053	1053	1053	1053	
5°	1250	1053	928	1053	1250	129
15°	1777	1005	741	1005	1777	504
25°	1831	913	603	913	1831	787
35°	794	796	491	796	794	521
45°	424	640	387	640	424	333
55°	266	450	264	450	266	240
65°	153	278	166	278	153	151
75°	65	135	85	135	65	70
85°	15	31	30	31	15	18
90°	20	1	20	1	20	11
95°	78	23	78	23	78	141
105°	856	78	856	78	856	845
115°	1041	138	1041	138	1041	1012
125°	821	192	821	192	821	744
135°	666	225	666	225	666	516
145°	520	256	520	256	520	331
155°	431	291	431	291	431	201
165°	376	318	376	318	376	108
175°	339	332	339	332	339	33
180°	332	332	332	332	332	



TEST NUMBER: P332314-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1121.5	1123.0	1118.3	1117.6	1112.2	1110.7	1110.7	1103.1	1098.5	1092.4	1088.7
5°	1250.4	1257.7	1254.0	1246.0	1232.4	1229.2	1220.7	1207.2	1191.9	1172.9	1163.9
7.5°	1411.4	1421.3	1417.6	1405.0	1390.9	1379.4	1355.2	1332.7	1301.3	1273.7	1250.1
10°	1543.4	1533.1	1525.0	1512.8	1499.8	1478.5	1453.3	1418.6	1378.5	1346.9	1311.7
12.5°	1642.3	1640.5	1630.3	1617.7	1599.3	1579.2	1548.2	1505.9	1459.2	1413.7	1373.5
15°	1776.9	1779.7	1772.9	1759.8	1733.7	1698.1	1651.2	1633.6	1566.9	1517.3	1467.7
17.5°	1870.2	1869.7	1868.7	1850.6	1823.9	1798.6	1755.1	1708.9	1648.5	1578.6	1511.8
20°	1929.3	1924.9	1925.7	1905.4	1885.6	1856.3	1814.0	1746.8	1697.2	1616.5	1547.5
22.5°	1927.9	1927.0	1930.4	1923.5	1909.0	1886.6	1853.2	1796.6	1733.3	1651.8	1574.2
25°	1831.1	1827.5	1848.7	1854.5	1877.5	1881.5	1871.6	1840.6	1780.5	1696.7	1600.7
27.5°	1532.5	1530.5	1569.8	1619.0	1681.4	1729.9	1776.8	1799.4	1780.5	1720.5	1624.4
30°	1257.7	1300.0	1319.9	1391.1	1470.4	1565.1	1648.0	1726.9	1746.3	1720.2	1641.2
32.5°	1044.2	1081.2	1097.7	1158.8	1232.8	1343.7	1468.1	1579.8	1658.7	1678.7	1631.2
35°	794.3	794.7	832.6	859.6	928.2	1042.2	1163.0	1312.7	1461.4	1574.1	1585.8
37.5°	633.8	636.0	658.9	685.9	737.3	797.6	904.0	1028.4	1200.2	1373.2	1474.6
40°	547.3	551.3	568.4	595.0	632.0	677.5	760.4	877.7	1021.0	1213.5	1370.8
42.5°	491.7	498.3	507.1	527.6	550.5	593.1	660.2	750.7	881.1	1063.1	1244.6
45°	423.7	427.3	434.1	443.6	464.3	494.0	539.2	599.9	708.2	854.7	1036.3
47.5°	373.8	371.9	379.0	386.7	400.5	420.8	451.0	500.7	577.8	695.3	849.5
50°	339.9	339.4	344.4	350.3	363.3	378.2	403.0	440.4	501.7	599.1	740.2
52.5°	308.2	309.9	313.4	320.7	330.1	342.2	364.4	391.3	444.0	528.1	645.7
55°	266.0	267.3	272.2	276.3	283.1	295.2	309.3	331.7	367.8	426.5	523.3
57.5°	230.2	229.6	234.4	235.4	243.1	253.0	263.8	281.3	307.5	350.9	416.2
60°	206.5	205.1	209.1	212.3	216.4	224.5	233.5	250.6	271.4	303.3	359.3
62.5°	184.9	184.2	187.2	190.3	193.6	201.0	208.6	221.8	238.2	265.2	309.5
65°	153.3	154.6	155.9	157.3	159.1	163.6	170.8	179.9	191.1	210.1	242.0
67.5°	120.5	121.8	122.3	125.0	128.9	131.7	136.1	144.1	152.0	168.0	186.1
70°	97.4	96.9	97.4	98.8	103.7	108.7	114.5	120.4	125.3	136.6	151.9
72.5°	83.7	82.8	84.0	84.3	86.7	88.1	91.8	97.3	103.7	111.3	122.3
75°	64.9	64.9	64.9	64.9	66.7	67.6	69.0	70.3	72.6	76.2	84.3
77.5°	48.0	48.0	48.6	49.2	49.5	50.0	50.9	52.2	53.0	54.9	58.5
80°	37.9	38.3	37.9	38.3	38.3	39.2	39.7	41.0	41.5	43.7	45.1
82.5°	28.5	28.2	28.5	28.9	28.9	29.9	30.0	30.9	31.0	32.2	33.6
85°	15.3	14.5	15.3	14.9	15.8	14.9	15.3	16.2	16.2	16.7	18.5
87.5°	7.5	8.4	7.5	7.7	7.8	7.9	7.8	7.7	8.3	8.1	8.0
90°	19.5	20.2	19.5	18.9	19.5	18.2	17.5	16.8	16.2	16.8	14.8
92.5°	32.5	33.7	33.0	35.0	36.2	39.7	44.9	56.7	78.1	103.5	113.9
95°	78.1	80.8	85.5	91.5	104.4	128.5	164.3	242.4	323.8	399.2	355.4
97.5°	212.6	218.3	236.5	266.8	316.5	397.0	483.9	604.1	661.9	618.6	452.9
100°	422.1	421.4	447.6	496.8	564.7	660.4	739.1	793.7	770.1	637.5	430.8
102.5°	619.1	634.6	656.6	695.5	748.4	809.0	854.9	856.6	775.5	602.4	398.5
105°	856.3	859.6	881.1	906.7	937.7	955.2	942.4	875.1	734.4	541.2	358.8
107.5°	992.7	998.9	1006.3	1014.9	1014.3	990.3	931.3	822.1	662.5	487.1	333.5
110°	1048.8	1050.1	1051.5	1046.0	1027.3	980.1	895.3	771.5	617.3	456.4	323.8



TEST NUMBER: P332314-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1060.1	1059.8	1054.7	1038.0	1003.5	943.0	847.9	721.3	578.0	435.9	318.4
115°	1041.4	1038.0	1024.5	994.9	944.4	871.1	772.1	655.0	530.5	414.0	316.4
117.5°	981.9	977.2	957.9	923.9	871.3	796.9	708.0	606.9	501.8	401.1	317.6
120°	932.3	928.2	912.1	874.4	821.2	753.3	672.4	581.6	486.7	395.1	319.8
122.5°	886.0	880.9	863.1	829.1	782.0	718.8	643.9	561.7	474.3	391.4	323.5
125°	821.2	816.5	799.7	770.1	727.0	673.1	608.6	535.1	458.4	386.4	329.2
127.5°	767.9	763.6	748.4	723.1	684.8	635.8	577.4	512.0	444.4	384.0	335.6
130°	737.8	732.4	718.2	694.1	658.3	612.6	558.0	497.5	436.9	382.4	339.9
132.5°	708.2	704.4	691.9	667.6	634.1	590.5	539.8	484.0	429.9	381.8	343.2
135°	665.7	661.0	648.9	628.7	595.7	557.3	513.6	465.8	420.7	381.0	348.0
137.5°	621.0	617.9	607.6	587.1	559.4	526.2	488.4	449.3	412.8	379.5	351.3
140°	589.7	590.4	579.5	560.8	535.1	506.2	473.9	439.5	407.9	379.0	353.4
142.5°	560.6	561.3	551.6	534.9	513.1	487.9	459.9	430.4	403.6	377.9	355.0
145°	520.3	519.0	513.6	499.5	482.7	463.1	441.6	419.4	397.9	376.3	356.1
147.5°	487.2	486.7	481.6	472.0	459.3	445.4	428.0	410.4	392.2	373.8	356.1
150°	467.9	467.9	463.8	456.4	446.3	433.5	419.4	403.9	388.4	371.6	356.1
152.5°	451.7	451.7	449.3	442.4	434.5	423.8	411.3	398.0	384.1	368.9	354.5
155°	431.4	430.8	429.5	424.0	418.0	409.9	399.8	389.1	377.6	364.2	352.8
157.5°	413.0	413.2	412.1	408.0	402.8	396.5	388.7	379.6	370.4	360.0	350.4
160°	401.2	401.8	401.8	397.9	393.1	388.4	381.7	374.3	365.5	356.8	349.4
162.5°	390.5	391.1	391.1	387.6	384.5	380.3	374.1	367.8	360.7	353.5	347.2
165°	376.3	376.3	376.9	374.3	371.6	368.2	363.5	359.5	354.0	348.7	344.0
167.5°	362.8	362.8	363.5	361.6	360.4	358.0	355.2	352.1	347.8	343.9	340.8
170°	354.7	354.7	355.4	354.0	353.4	352.1	349.4	347.3	344.0	340.6	338.6
172.5°	347.2	347.8	349.0	347.6	347.5	346.6	344.5	343.0	340.2	337.9	337.0
175°	338.6	339.2	339.9	339.2	339.2	339.2	337.9	337.3	335.9	334.6	334.6
177.5°	333.6	333.6	334.7	334.2	334.7	334.7	334.2	333.6	333.0	332.5	333.0
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P332314-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1087.3	1086.2	1081.2	1075.4	1067.8	1062.7	1058.8	1056.6	1050.2	1042.2	1036.8
5°	1154.4	1140.9	1126.5	1108.9	1092.7	1076.0	1065.7	1053.4	1038.6	1021.9	1010.2
7.5°	1226.4	1199.9	1171.3	1141.9	1112.7	1086.6	1063.5	1043.7	1020.0	996.1	979.4
10°	1281.6	1242.8	1202.6	1161.7	1124.2	1089.1	1062.0	1035.4	1007.0	979.6	958.8
12.5°	1331.7	1280.7	1234.4	1184.0	1136.2	1094.2	1055.2	1023.9	989.7	960.4	936.8
15°	1395.2	1342.9	1286.9	1210.3	1146.8	1093.6	1046.3	1005.2	963.8	927.7	904.7
17.5°	1454.5	1375.8	1300.7	1236.7	1154.2	1087.7	1029.9	980.9	935.4	897.2	868.8
20°	1479.0	1402.8	1321.2	1239.7	1158.5	1084.1	1016.9	962.9	915.5	872.3	846.1
22.5°	1493.7	1407.5	1321.5	1233.9	1147.7	1070.4	1004.0	944.4	893.2	852.0	819.8
25°	1511.0	1408.3	1313.5	1227.0	1139.1	1055.2	976.4	913.3	857.8	814.1	779.8
27.5°	1522.3	1401.4	1289.6	1193.3	1104.2	1020.7	948.4	881.6	825.3	779.0	742.3
30°	1524.5	1396.0	1271.2	1167.1	1076.4	999.8	923.2	859.2	799.7	750.5	716.3
32.5°	1527.4	1382.7	1246.3	1135.7	1042.9	967.0	897.6	836.5	775.5	727.1	692.2
35°	1515.5	1375.4	1208.5	1081.4	988.5	915.1	852.4	796.1	736.2	689.2	653.6
37.5°	1464.3	1346.0	1169.4	1020.3	923.2	855.1	804.1	754.9	700.0	649.4	615.9
40°	1412.7	1317.2	1139.1	983.2	881.8	811.8	765.9	725.7	672.5	625.3	589.2
42.5°	1335.9	1277.9	1110.3	944.2	834.8	767.5	728.8	691.1	644.5	596.4	562.5
45°	1195.0	1202.6	1051.2	882.2	769.9	702.3	665.8	639.6	598.2	558.5	523.8
47.5°	1018.3	1089.9	981.9	816.1	701.5	638.0	606.1	583.3	555.3	516.4	484.7
50°	902.9	1005.2	926.3	771.7	658.6	595.5	564.0	545.4	521.1	490.4	460.2
52.5°	796.5	906.5	859.3	722.3	612.1	554.4	523.6	508.3	489.0	460.1	432.8
55°	649.5	761.0	750.1	647.7	542.3	490.4	467.0	449.9	436.8	415.2	393.6
57.5°	525.5	631.0	636.6	564.8	480.8	429.6	409.4	396.5	388.0	371.6	351.6
60°	447.2	544.1	563.0	508.9	436.8	391.8	371.9	361.5	354.7	341.7	326.4
62.5°	382.3	464.8	486.2	447.3	394.6	352.4	336.9	326.9	322.3	311.0	297.5
65°	292.6	361.1	381.8	360.2	332.7	298.9	286.3	277.7	273.6	267.3	257.4
67.5°	220.0	269.9	292.7	277.4	267.5	246.2	238.1	233.5	229.9	225.6	217.3
70°	176.7	213.7	237.1	233.1	225.0	213.7	207.8	204.7	201.0	197.4	190.2
72.5°	142.1	167.6	189.5	191.6	184.9	182.6	177.5	176.2	174.0	169.7	165.7
75°	94.2	111.8	127.1	132.9	135.7	137.9	135.7	135.3	134.7	131.2	128.9
77.5°	61.7	71.2	80.8	90.8	95.1	98.2	98.9	100.6	99.4	97.5	96.3
80°	47.4	49.6	56.3	64.9	71.6	74.4	76.2	77.1	76.6	76.2	74.4
82.5°	34.4	36.2	39.4	45.5	51.1	55.6	56.7	56.6	57.5	57.8	56.3
85°	18.5	18.9	19.8	20.8	23.8	28.8	30.2	31.1	32.0	32.0	29.3
87.5°	8.4	7.6	7.9	7.6	8.4	8.4	10.2	11.8	12.4	11.3	11.7
90°	12.8	10.8	8.8	7.4	6.0	4.0	2.7	1.4	2.7	4.0	6.0
92.5°	85.5	56.6	38.9	28.9	23.3	18.1	12.4	8.4	12.4	18.1	23.3
95°	245.0	144.7	87.5	61.2	43.7	32.3	24.9	22.9	24.9	32.3	43.7
97.5°	268.9	155.8	101.1	72.7	55.4	45.5	39.7	39.0	39.7	45.5	55.4
100°	253.7	154.1	107.0	80.8	64.7	55.2	50.5	49.9	50.5	55.2	64.7
102.5°	240.8	156.3	114.0	90.0	75.4	66.5	62.3	61.1	62.3	66.5	75.4
105°	231.5	162.2	125.9	105.0	92.2	84.1	80.1	78.1	80.1	84.1	92.2
107.5°	230.9	173.2	141.4	122.0	109.9	102.0	98.2	96.1	98.2	102.0	109.9
110°	233.6	182.4	152.1	133.3	121.8	114.4	111.1	109.1	111.1	114.4	121.8



TEST NUMBER: P332314-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	238.9	191.6	163.4	145.2	133.7	126.3	123.0	120.9	123.0	126.3	133.7
115°	247.7	206.6	181.1	162.9	151.4	144.7	140.7	138.0	140.7	144.7	151.4
117.5°	259.3	222.7	197.3	180.6	167.7	161.5	158.2	155.1	158.2	161.5	167.7
120°	267.9	232.9	208.7	191.8	179.1	172.3	168.9	166.9	168.9	172.3	179.1
122.5°	276.0	243.7	220.0	202.1	189.9	182.5	179.2	177.2	179.2	182.5	189.9
125°	288.8	259.2	235.6	217.4	204.7	197.3	193.2	191.8	193.2	197.3	204.7
127.5°	299.3	272.6	249.9	231.7	217.6	210.0	205.0	203.0	205.0	210.0	217.6
130°	306.3	280.7	258.5	240.3	226.2	218.1	212.1	210.0	212.1	218.1	226.2
132.5°	312.7	287.7	266.0	248.4	234.3	224.5	218.0	215.4	218.0	224.5	234.3
135°	321.1	298.2	277.3	259.2	245.0	235.0	227.6	224.8	227.6	235.0	245.0
137.5°	327.3	305.5	285.4	268.5	254.6	243.8	236.5	233.7	236.5	243.8	254.6
140°	330.5	310.3	290.8	274.0	260.5	249.8	243.0	239.6	243.0	249.8	260.5
142.5°	333.7	314.1	295.1	279.4	265.9	256.2	248.9	246.1	248.9	256.2	265.9
145°	337.3	319.1	301.6	286.1	274.7	264.6	258.5	256.5	258.5	264.6	274.7
147.5°	339.4	323.1	307.1	293.9	282.8	274.1	268.2	267.0	268.2	274.1	282.8
150°	339.9	325.8	310.3	298.2	288.8	280.0	274.7	274.0	274.7	280.0	288.8
152.5°	341.0	327.4	314.1	302.5	294.2	286.5	281.1	280.9	281.1	286.5	294.2
155°	341.3	330.5	319.1	309.6	302.2	295.5	291.4	291.4	291.4	295.5	302.2
157.5°	342.0	332.3	323.1	315.8	309.5	303.6	300.3	299.8	300.3	303.6	309.5
160°	342.0	333.9	325.8	319.1	314.4	309.0	306.3	306.3	306.3	309.0	314.4
162.5°	341.4	334.4	327.4	321.8	317.6	313.3	311.2	311.2	311.2	313.3	317.6
165°	339.9	335.2	329.8	325.1	322.4	319.1	317.7	318.4	317.7	319.1	322.4
167.5°	338.9	335.1	331.2	328.2	326.3	323.8	323.1	323.9	323.1	323.8	326.3
170°	337.3	334.6	331.2	329.8	328.5	326.5	325.8	327.2	325.8	326.5	328.5
172.5°	336.7	334.6	331.7	330.9	330.1	328.6	328.5	329.3	328.5	328.6	330.1
175°	335.2	333.9	332.5	331.8	331.8	330.5	331.2	331.8	331.2	330.5	331.8
177.5°	334.2	333.0	332.5	332.5	332.5	332.0	332.5	333.0	332.5	332.0	332.5
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P332314-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1035.0	1030.3	1027.1	1019.9	1015.1	1010.1	1005.0	1008.3	1008.0	1007.5	1007.5
5°	1000.3	989.9	980.4	968.3	960.6	951.1	943.9	943.1	944.9	938.5	934.9
7.5°	965.9	951.7	938.2	924.8	910.6	899.2	892.1	888.7	884.2	880.3	876.2
10°	941.7	925.0	911.9	895.3	879.9	866.4	857.8	852.0	848.8	845.7	839.8
12.5°	916.8	900.4	883.8	865.0	850.3	834.7	828.3	821.7	815.6	812.1	804.1
15°	880.4	859.2	841.6	821.7	805.6	790.2	781.2	768.1	766.3	761.8	753.7
17.5°	843.9	820.9	796.6	782.0	763.6	747.7	733.9	729.5	716.6	711.8	704.7
20°	815.0	793.8	775.3	756.0	729.4	714.5	703.7	697.8	687.4	681.1	676.6
22.5°	790.1	768.6	747.2	724.6	702.7	686.0	678.0	668.9	663.3	654.4	649.5
25°	754.6	731.2	705.5	681.1	665.4	652.7	640.1	632.0	623.9	619.8	610.8
27.5°	713.3	688.8	664.8	646.4	627.0	614.5	603.0	595.8	586.1	579.3	574.3
30°	690.6	661.8	641.0	624.3	599.5	587.8	579.3	570.2	563.0	555.8	550.9
32.5°	664.3	637.9	618.3	597.6	578.6	565.8	554.7	546.8	540.6	533.8	528.8
35°	622.9	600.9	580.6	559.8	545.9	532.8	519.8	513.0	507.1	500.8	496.3
37.5°	585.7	565.0	545.7	526.1	508.8	498.1	487.6	482.4	474.5	470.3	465.6
40°	562.6	542.3	521.5	502.7	484.6	476.5	467.0	459.3	452.1	449.0	444.0
42.5°	537.4	517.0	499.6	479.1	464.4	453.4	444.6	436.3	430.8	426.3	423.4
45°	499.9	481.9	464.8	444.4	430.5	421.0	411.1	403.5	398.5	395.4	390.4
47.5°	463.6	445.6	428.2	410.4	396.9	386.2	376.3	370.9	364.3	360.4	357.1
50°	437.2	421.0	402.5	386.3	372.8	362.0	353.9	347.1	341.2	336.3	334.1
52.5°	413.1	395.8	379.8	364.7	350.4	338.2	330.8	323.6	319.3	313.6	310.9
55°	373.2	356.5	343.0	328.1	314.2	303.8	294.8	288.5	284.0	277.7	274.1
57.5°	335.8	320.9	304.7	291.8	277.4	268.6	261.1	252.6	247.1	242.2	238.7
60°	310.6	293.4	279.5	267.3	254.7	243.4	236.7	229.9	224.0	219.0	215.9
62.5°	284.3	269.3	256.1	242.8	231.3	221.4	213.6	207.9	202.8	199.6	196.5
65°	243.8	232.1	218.6	207.8	197.0	189.8	183.5	178.5	174.9	172.6	170.0
67.5°	206.7	195.4	183.6	172.9	165.7	160.2	156.1	151.8	150.0	147.1	145.3
70°	182.5	170.8	160.5	152.4	145.2	141.1	138.4	135.3	133.5	129.8	128.0
72.5°	156.3	147.7	140.3	133.6	127.9	124.2	120.7	116.8	114.0	109.9	108.2
75°	123.0	115.4	109.5	105.0	101.4	96.4	91.5	87.5	86.1	84.7	84.3
77.5°	91.2	86.3	82.1	78.3	73.8	70.2	69.1	68.2	67.8	67.2	67.2
80°	71.6	67.2	64.0	59.5	56.8	56.8	56.8	55.9	56.3	56.3	56.3
82.5°	53.3	49.2	47.4	45.8	45.3	45.6	45.6	45.8	45.5	46.2	45.9
85°	27.5	28.0	28.8	28.4	28.8	28.8	29.8	29.3	29.8	28.8	29.8
87.5°	11.5	12.9	13.7	14.5	15.2	15.2	15.5	15.6	16.1	16.3	16.5
90°	7.4	8.8	10.8	12.8	14.8	16.8	16.2	16.8	17.5	18.2	19.5
92.5°	28.9	38.9	56.6	85.5	113.9	103.5	78.1	56.7	44.9	39.7	36.2
95°	61.2	87.5	144.7	245.0	355.4	399.2	323.8	242.4	164.3	128.5	104.4
97.5°	72.7	101.1	155.8	268.9	452.9	618.6	661.9	604.1	483.9	397.0	316.5
100°	80.8	107.0	154.1	253.7	430.8	637.5	770.1	793.7	739.1	660.4	564.7
102.5°	90.0	114.0	156.3	240.8	398.5	602.4	775.5	856.6	854.9	809.0	748.4
105°	105.0	125.9	162.2	231.5	358.8	541.2	734.4	875.1	942.4	955.2	937.7
107.5°	122.0	141.4	173.2	230.9	333.5	487.1	662.5	822.1	931.3	990.3	1014.3
110°	133.3	152.1	182.4	233.6	323.8	456.4	617.3	771.5	895.3	980.1	1027.3



TEST NUMBER: P332314-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	145.2	163.4	191.6	238.9	318.4	435.9	578.0	721.3	847.9	943.0	1003.5
115°	162.9	181.1	206.6	247.7	316.4	414.0	530.5	655.0	772.1	871.1	944.4
117.5°	180.6	197.3	222.7	259.3	317.6	401.1	501.8	606.9	708.0	796.9	871.3
120°	191.8	208.7	232.9	267.9	319.8	395.1	486.7	581.6	672.4	753.3	821.2
122.5°	202.1	220.0	243.7	276.0	323.5	391.4	474.3	561.7	643.9	718.8	782.0
125°	217.4	235.6	259.2	288.8	329.2	386.4	458.4	535.1	608.6	673.1	727.0
127.5°	231.7	249.9	272.6	299.3	335.6	384.0	444.4	512.0	577.4	635.8	684.8
130°	240.3	258.5	280.7	306.3	339.9	382.4	436.9	497.5	558.0	612.6	658.3
132.5°	248.4	266.0	287.7	312.7	343.2	381.8	429.9	484.0	539.8	590.5	634.1
135°	259.2	277.3	298.2	321.1	348.0	381.0	420.7	465.8	513.6	557.3	595.7
137.5°	268.5	285.4	305.5	327.3	351.3	379.5	412.8	449.3	488.4	526.2	559.4
140°	274.0	290.8	310.3	330.5	353.4	379.0	407.9	439.5	473.9	506.2	535.1
142.5°	279.4	295.1	314.1	333.7	355.0	377.9	403.6	430.4	459.9	487.9	513.1
145°	286.1	301.6	319.1	337.3	356.1	376.3	397.9	419.4	441.6	463.1	482.7
147.5°	293.9	307.1	323.1	339.4	356.1	373.8	392.2	410.4	428.0	445.4	459.3
150°	298.2	310.3	325.8	339.9	356.1	371.6	388.4	403.9	419.4	433.5	446.3
152.5°	302.5	314.1	327.4	341.0	354.5	368.9	384.1	398.0	411.3	423.8	434.5
155°	309.6	319.1	330.5	341.3	352.8	364.2	377.6	389.1	399.8	409.9	418.0
157.5°	315.8	323.1	332.3	342.0	350.4	360.0	370.4	379.6	388.7	396.5	402.8
160°	319.1	325.8	333.9	342.0	349.4	356.8	365.5	374.3	381.7	388.4	393.1
162.5°	321.8	327.4	334.4	341.4	347.2	353.5	360.7	367.8	374.1	380.3	384.5
165°	325.1	329.8	335.2	339.9	344.0	348.7	354.0	359.5	363.5	368.2	371.6
167.5°	328.2	331.2	335.1	338.9	340.8	343.9	347.8	352.1	355.2	358.0	360.4
170°	329.8	331.2	334.6	337.3	338.6	340.6	344.0	347.3	349.4	352.1	353.4
172.5°	330.9	331.7	334.6	336.7	337.0	337.9	340.2	343.0	344.5	346.6	347.5
175°	331.8	332.5	333.9	335.2	334.6	334.6	335.9	337.3	337.9	339.2	339.2
177.5°	332.5	332.5	333.0	334.2	333.0	332.5	333.0	333.6	334.2	334.7	334.7
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P332314-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1003.2	1002.9	1003.2	1001.8	1003.2	1002.9	1003.2	1007.5	1007.5	1008.0	1008.3
5°	933.6	933.1	931.8	927.7	931.8	933.1	933.6	934.9	938.5	944.9	943.1
7.5°	872.7	872.1	868.1	868.2	868.1	872.1	872.7	876.2	880.3	884.2	888.7
10°	836.6	837.1	831.7	828.5	831.7	837.1	836.6	839.8	845.7	848.8	852.0
12.5°	801.7	799.6	795.2	791.8	795.2	799.6	801.7	804.1	812.1	815.6	821.7
15°	755.5	751.0	740.2	741.1	740.2	751.0	755.5	753.7	761.8	766.3	768.1
17.5°	701.1	697.8	697.6	691.3	697.6	697.8	701.1	704.7	711.8	716.6	729.5
20°	669.4	667.2	668.0	661.8	668.0	667.2	669.4	676.6	681.1	687.4	697.8
22.5°	644.5	642.3	638.5	636.5	638.5	642.3	644.5	649.5	654.4	663.3	668.9
25°	608.1	604.5	600.9	603.1	600.9	604.5	608.1	610.8	619.8	623.9	632.0
27.5°	571.7	568.9	565.3	564.9	565.3	568.9	571.7	574.3	579.3	586.1	595.8
30°	548.6	545.9	544.1	541.8	544.1	545.9	548.6	550.9	555.8	563.0	570.2
32.5°	525.1	524.6	521.3	520.9	521.3	524.6	525.1	528.8	533.8	540.6	546.8
35°	494.5	491.8	490.9	491.4	490.9	491.8	494.5	496.3	500.8	507.1	513.0
37.5°	465.4	461.8	460.1	458.6	460.1	461.8	465.4	465.6	470.3	474.5	482.4
40°	444.4	440.8	440.0	439.0	440.0	440.8	444.4	444.0	449.0	452.1	459.3
42.5°	421.0	419.6	419.0	417.4	419.0	419.6	421.0	423.4	426.3	430.8	436.3
45°	389.0	388.6	385.9	386.8	385.9	388.6	389.0	390.4	395.4	398.5	403.5
47.5°	355.3	353.4	351.5	352.7	351.5	353.4	355.3	357.1	360.4	364.3	370.9
50°	332.3	331.3	327.3	328.1	327.3	331.3	332.3	334.1	336.3	341.2	347.1
52.5°	309.2	305.7	304.2	303.7	304.2	305.7	309.2	310.9	313.6	319.3	323.6
55°	271.0	266.8	265.0	264.2	265.0	266.8	271.0	274.1	277.7	284.0	288.5
57.5°	233.4	232.3	230.9	231.9	230.9	232.3	233.4	238.7	242.2	247.1	252.6
60°	211.4	211.4	211.4	210.9	211.4	211.4	211.4	215.9	219.0	224.0	229.9
62.5°	194.5	193.4	193.0	193.6	193.0	193.4	194.5	196.5	199.6	202.8	207.9
65°	168.6	168.2	166.3	165.9	166.3	168.2	168.6	170.0	172.6	174.9	178.5
67.5°	144.1	142.5	142.0	141.4	142.0	142.5	144.1	145.3	147.1	150.0	151.8
70°	125.8	124.8	122.2	122.6	122.2	124.8	125.8	128.0	129.8	133.5	135.3
72.5°	105.9	105.0	104.5	103.8	104.5	105.0	105.9	108.2	109.9	114.0	116.8
75°	83.9	83.4	82.9	84.7	82.9	83.4	83.9	84.3	84.7	86.1	87.5
77.5°	67.2	67.2	67.4	66.7	67.4	67.2	67.2	67.2	67.2	67.8	68.2
80°	56.3	56.3	55.9	55.9	55.9	56.3	56.3	56.3	56.3	56.3	55.9
82.5°	45.2	45.5	45.8	45.1	45.8	45.5	45.2	45.9	46.2	45.5	45.8
85°	29.8	29.3	30.2	29.8	30.2	29.3	29.8	29.8	28.8	29.8	29.3
87.5°	17.1	16.5	16.7	16.9	16.7	16.5	17.1	16.5	16.3	16.1	15.6
90°	18.9	19.5	20.2	19.5	20.2	19.5	18.9	19.5	18.2	17.5	16.8
92.5°	35.0	33.0	33.7	32.5	33.7	33.0	35.0	36.2	39.7	44.9	56.7
95°	91.5	85.5	80.8	78.1	80.8	85.5	91.5	104.4	128.5	164.3	242.4
97.5°	266.8	236.5	218.3	212.6	218.3	236.5	266.8	316.5	397.0	483.9	604.1
100°	496.8	447.6	421.4	422.1	421.4	447.6	496.8	564.7	660.4	739.1	793.7
102.5°	695.5	656.6	634.6	619.1	634.6	656.6	695.5	748.4	809.0	854.9	856.6
105°	906.7	881.1	859.6	856.3	859.6	881.1	906.7	937.7	955.2	942.4	875.1
107.5°	1014.9	1006.3	998.9	992.7	998.9	1006.3	1014.9	1014.3	990.3	931.3	822.1
110°	1046.0	1051.5	1050.1	1048.8	1050.1	1051.5	1046.0	1027.3	980.1	895.3	771.5



TEST NUMBER: P332314-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1038.0	1054.7	1059.8	1060.1	1059.8	1054.7	1038.0	1003.5	943.0	847.9	721.3
115°	994.9	1024.5	1038.0	1041.4	1038.0	1024.5	994.9	944.4	871.1	772.1	655.0
117.5°	923.9	957.9	977.2	981.9	977.2	957.9	923.9	871.3	796.9	708.0	606.9
120°	874.4	912.1	928.2	932.3	928.2	912.1	874.4	821.2	753.3	672.4	581.6
122.5°	829.1	863.1	880.9	886.0	880.9	863.1	829.1	782.0	718.8	643.9	561.7
125°	770.1	799.7	816.5	821.2	816.5	799.7	770.1	727.0	673.1	608.6	535.1
127.5°	723.1	748.4	763.6	767.9	763.6	748.4	723.1	684.8	635.8	577.4	512.0
130°	694.1	718.2	732.4	737.8	732.4	718.2	694.1	658.3	612.6	558.0	497.5
132.5°	667.6	691.9	704.4	708.2	704.4	691.9	667.6	634.1	590.5	539.8	484.0
135°	628.7	648.9	661.0	665.7	661.0	648.9	628.7	595.7	557.3	513.6	465.8
137.5°	587.1	607.6	617.9	621.0	617.9	607.6	587.1	559.4	526.2	488.4	449.3
140°	560.8	579.5	590.4	589.7	590.4	579.5	560.8	535.1	506.2	473.9	439.5
142.5°	534.9	551.6	561.3	560.6	561.3	551.6	534.9	513.1	487.9	459.9	430.4
145°	499.5	513.6	519.0	520.3	519.0	513.6	499.5	482.7	463.1	441.6	419.4
147.5°	472.0	481.6	486.7	487.2	486.7	481.6	472.0	459.3	445.4	428.0	410.4
150°	456.4	463.8	467.9	467.9	467.9	463.8	456.4	446.3	433.5	419.4	403.9
152.5°	442.4	449.3	451.7	451.7	451.7	449.3	442.4	434.5	423.8	411.3	398.0
155°	424.0	429.5	430.8	431.4	430.8	429.5	424.0	418.0	409.9	399.8	389.1
157.5°	408.0	412.1	413.2	413.0	413.2	412.1	408.0	402.8	396.5	388.7	379.6
160°	397.9	401.8	401.8	401.2	401.8	401.8	397.9	393.1	388.4	381.7	374.3
162.5°	387.6	391.1	391.1	390.5	391.1	391.1	387.6	384.5	380.3	374.1	367.8
165°	374.3	376.9	376.3	376.3	376.3	376.9	374.3	371.6	368.2	363.5	359.5
167.5°	361.6	363.5	362.8	362.8	362.8	363.5	361.6	360.4	358.0	355.2	352.1
170°	354.0	355.4	354.7	354.7	354.7	355.4	354.0	353.4	352.1	349.4	347.3
172.5°	347.6	349.0	347.8	347.2	347.8	349.0	347.6	347.5	346.6	344.5	343.0
175°	339.2	339.9	339.2	338.6	339.2	339.9	339.2	339.2	339.2	337.9	337.3
177.5°	334.2	334.7	333.6	333.6	333.6	334.7	334.2	334.7	334.7	334.2	333.6
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P332314-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1005.0	1010.1	1015.1	1019.9	1027.1	1030.3	1035.0	1036.8	1042.2	1050.2	1056.6
5°	943.9	951.1	960.6	968.3	980.4	989.9	1000.3	1010.2	1021.9	1038.6	1053.4
7.5°	892.1	899.2	910.6	924.8	938.2	951.7	965.9	979.4	996.1	1020.0	1043.7
10°	857.8	866.4	879.9	895.3	911.9	925.0	941.7	958.8	979.6	1007.0	1035.4
12.5°	828.3	834.7	850.3	865.0	883.8	900.4	916.8	936.8	960.4	989.7	1023.9
15°	781.2	790.2	805.6	821.7	841.6	859.2	880.4	904.7	927.7	963.8	1005.2
17.5°	733.9	747.7	763.6	782.0	796.6	820.9	843.9	868.8	897.2	935.4	980.9
20°	703.7	714.5	729.4	756.0	775.3	793.8	815.0	846.1	872.3	915.5	962.9
22.5°	678.0	686.0	702.7	724.6	747.2	768.6	790.1	819.8	852.0	893.2	944.4
25°	640.1	652.7	665.4	681.1	705.5	731.2	754.6	779.8	814.1	857.8	913.3
27.5°	603.0	614.5	627.0	646.4	664.8	688.8	713.3	742.3	779.0	825.3	881.6
30°	579.3	587.8	599.5	624.3	641.0	661.8	690.6	716.3	750.5	799.7	859.2
32.5°	554.7	565.8	578.6	597.6	618.3	637.9	664.3	692.2	727.1	775.5	836.5
35°	519.8	532.8	545.9	559.8	580.6	600.9	622.9	653.6	689.2	736.2	796.1
37.5°	487.6	498.1	508.8	526.1	545.7	565.0	585.7	615.9	649.4	700.0	754.9
40°	467.0	476.5	484.6	502.7	521.5	542.3	562.6	589.2	625.3	672.5	725.7
42.5°	444.6	453.4	464.4	479.1	499.6	517.0	537.4	562.5	596.4	644.5	691.1
45°	411.1	421.0	430.5	444.4	464.8	481.9	499.9	523.8	558.5	598.2	639.6
47.5°	376.3	386.2	396.9	410.4	428.2	445.6	463.6	484.7	516.4	555.3	583.3
50°	353.9	362.0	372.8	386.3	402.5	421.0	437.2	460.2	490.4	521.1	545.4
52.5°	330.8	338.2	350.4	364.7	379.8	395.8	413.1	432.8	460.1	489.0	508.3
55°	294.8	303.8	314.2	328.1	343.0	356.5	373.2	393.6	415.2	436.8	449.9
57.5°	261.1	268.6	277.4	291.8	304.7	320.9	335.8	351.6	371.6	388.0	396.5
60°	236.7	243.4	254.7	267.3	279.5	293.4	310.6	326.4	341.7	354.7	361.5
62.5°	213.6	221.4	231.3	242.8	256.1	269.3	284.3	297.5	311.0	322.3	326.9
65°	183.5	189.8	197.0	207.8	218.6	232.1	243.8	257.4	267.3	273.6	277.7
67.5°	156.1	160.2	165.7	172.9	183.6	195.4	206.7	217.3	225.6	229.9	233.5
70°	138.4	141.1	145.2	152.4	160.5	170.8	182.5	190.2	197.4	201.0	204.7
72.5°	120.7	124.2	127.9	133.6	140.3	147.7	156.3	165.7	169.7	174.0	176.2
75°	91.5	96.4	101.4	105.0	109.5	115.4	123.0	128.9	131.2	134.7	135.3
77.5°	69.1	70.2	73.8	78.3	82.1	86.3	91.2	96.3	97.5	99.4	100.6
80°	56.8	56.8	56.8	59.5	64.0	67.2	71.6	74.4	76.2	76.6	77.1
82.5°	45.6	45.6	45.3	45.8	47.4	49.2	53.3	56.3	57.8	57.5	56.6
85°	29.8	28.8	28.8	28.4	28.8	28.0	27.5	29.3	32.0	32.0	31.1
87.5°	15.5	15.2	15.2	14.5	13.7	12.9	11.5	11.7	11.3	12.4	11.8
90°	16.2	16.8	14.8	12.8	10.8	8.8	7.4	6.0	4.0	2.7	1.4
92.5°	78.1	103.5	113.9	85.5	56.6	38.9	28.9	23.3	18.1	12.4	8.4
95°	323.8	399.2	355.4	245.0	144.7	87.5	61.2	43.7	32.3	24.9	22.9
97.5°	661.9	618.6	452.9	268.9	155.8	101.1	72.7	55.4	45.5	39.7	39.0
100°	770.1	637.5	430.8	253.7	154.1	107.0	80.8	64.7	55.2	50.5	49.9
102.5°	775.5	602.4	398.5	240.8	156.3	114.0	90.0	75.4	66.5	62.3	61.1
105°	734.4	541.2	358.8	231.5	162.2	125.9	105.0	92.2	84.1	80.1	78.1
107.5°	662.5	487.1	333.5	230.9	173.2	141.4	122.0	109.9	102.0	98.2	96.1
110°	617.3	456.4	323.8	233.6	182.4	152.1	133.3	121.8	114.4	111.1	109.1



TEST NUMBER: P332314-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	578.0	435.9	318.4	238.9	191.6	163.4	145.2	133.7	126.3	123.0	120.9
115°	530.5	414.0	316.4	247.7	206.6	181.1	162.9	151.4	144.7	140.7	138.0
117.5°	501.8	401.1	317.6	259.3	222.7	197.3	180.6	167.7	161.5	158.2	155.1
120°	486.7	395.1	319.8	267.9	232.9	208.7	191.8	179.1	172.3	168.9	166.9
122.5°	474.3	391.4	323.5	276.0	243.7	220.0	202.1	189.9	182.5	179.2	177.2
125°	458.4	386.4	329.2	288.8	259.2	235.6	217.4	204.7	197.3	193.2	191.8
127.5°	444.4	384.0	335.6	299.3	272.6	249.9	231.7	217.6	210.0	205.0	203.0
130°	436.9	382.4	339.9	306.3	280.7	258.5	240.3	226.2	218.1	212.1	210.0
132.5°	429.9	381.8	343.2	312.7	287.7	266.0	248.4	234.3	224.5	218.0	215.4
135°	420.7	381.0	348.0	321.1	298.2	277.3	259.2	245.0	235.0	227.6	224.8
137.5°	412.8	379.5	351.3	327.3	305.5	285.4	268.5	254.6	243.8	236.5	233.7
140°	407.9	379.0	353.4	330.5	310.3	290.8	274.0	260.5	249.8	243.0	239.6
142.5°	403.6	377.9	355.0	333.7	314.1	295.1	279.4	265.9	256.2	248.9	246.1
145°	397.9	376.3	356.1	337.3	319.1	301.6	286.1	274.7	264.6	258.5	256.5
147.5°	392.2	373.8	356.1	339.4	323.1	307.1	293.9	282.8	274.1	268.2	267.0
150°	388.4	371.6	356.1	339.9	325.8	310.3	298.2	288.8	280.0	274.7	274.0
152.5°	384.1	368.9	354.5	341.0	327.4	314.1	302.5	294.2	286.5	281.1	280.9
155°	377.6	364.2	352.8	341.3	330.5	319.1	309.6	302.2	295.5	291.4	291.4
157.5°	370.4	360.0	350.4	342.0	332.3	323.1	315.8	309.5	303.6	300.3	299.8
160°	365.5	356.8	349.4	342.0	333.9	325.8	319.1	314.4	309.0	306.3	306.3
162.5°	360.7	353.5	347.2	341.4	334.4	327.4	321.8	317.6	313.3	311.2	311.2
165°	354.0	348.7	344.0	339.9	335.2	329.8	325.1	322.4	319.1	317.7	318.4
167.5°	347.8	343.9	340.8	338.9	335.1	331.2	328.2	326.3	323.8	323.1	323.9
170°	344.0	340.6	338.6	337.3	334.6	331.2	329.8	328.5	326.5	325.8	327.2
172.5°	340.2	337.9	337.0	336.7	334.6	331.7	330.9	330.1	328.6	328.5	329.3
175°	335.9	334.6	334.6	335.2	333.9	332.5	331.8	331.8	330.5	331.2	331.8
177.5°	333.0	332.5	333.0	334.2	333.0	332.5	332.5	332.5	332.0	332.5	333.0
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P332314-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1058.8	1062.7	1067.8	1075.4	1081.2	1086.2	1087.3	1088.7	1092.4	1098.5	1103.1
5°	1065.7	1076.0	1092.7	1108.9	1126.5	1140.9	1154.4	1163.9	1172.9	1191.9	1207.2
7.5°	1063.5	1086.6	1112.7	1141.9	1171.3	1199.9	1226.4	1250.1	1273.7	1301.3	1332.7
10°	1062.0	1089.1	1124.2	1161.7	1202.6	1242.8	1281.6	1311.7	1346.9	1378.5	1418.6
12.5°	1055.2	1094.2	1136.2	1184.0	1234.4	1280.7	1331.7	1373.5	1413.7	1459.2	1505.9
15°	1046.3	1093.6	1146.8	1210.3	1286.9	1342.9	1395.2	1467.7	1517.3	1566.9	1633.6
17.5°	1029.9	1087.7	1154.2	1236.7	1300.7	1375.8	1454.5	1511.8	1578.6	1648.5	1708.9
20°	1016.9	1084.1	1158.5	1239.7	1321.2	1402.8	1479.0	1547.5	1616.5	1697.2	1746.8
22.5°	1004.0	1070.4	1147.7	1233.9	1321.5	1407.5	1493.7	1574.2	1651.8	1733.3	1796.6
25°	976.4	1055.2	1139.1	1227.0	1313.5	1408.3	1511.0	1600.7	1696.7	1780.5	1840.6
27.5°	948.4	1020.7	1104.2	1193.3	1289.6	1401.4	1522.3	1624.4	1720.5	1780.5	1799.4
30°	923.2	999.8	1076.4	1167.1	1271.2	1396.0	1524.5	1641.2	1720.2	1746.3	1726.9
32.5°	897.6	967.0	1042.9	1135.7	1246.3	1382.7	1527.4	1631.2	1678.7	1658.7	1579.8
35°	852.4	915.1	988.5	1081.4	1208.5	1375.4	1515.5	1585.8	1574.1	1461.4	1312.7
37.5°	804.1	855.1	923.2	1020.3	1169.4	1346.0	1464.3	1474.6	1373.2	1200.2	1028.4
40°	765.9	811.8	881.8	983.2	1139.1	1317.2	1412.7	1370.8	1213.5	1021.0	877.7
42.5°	728.8	767.5	834.8	944.2	1110.3	1277.9	1335.9	1244.6	1063.1	881.1	750.7
45°	665.8	702.3	769.9	882.2	1051.2	1202.6	1195.0	1036.3	854.7	708.2	599.9
47.5°	606.1	638.0	701.5	816.1	981.9	1089.9	1018.3	849.5	695.3	577.8	500.7
50°	564.0	595.5	658.6	771.7	926.3	1005.2	902.9	740.2	599.1	501.7	440.4
52.5°	523.6	554.4	612.1	722.3	859.3	906.5	796.5	645.7	528.1	444.0	391.3
55°	467.0	490.4	542.3	647.7	750.1	761.0	649.5	523.3	426.5	367.8	331.7
57.5°	409.4	429.6	480.8	564.8	636.6	631.0	525.5	416.2	350.9	307.5	281.3
60°	371.9	391.8	436.8	508.9	563.0	544.1	447.2	359.3	303.3	271.4	250.6
62.5°	336.9	352.4	394.6	447.3	486.2	464.8	382.3	309.5	265.2	238.2	221.8
65°	286.3	298.9	332.7	360.2	381.8	361.1	292.6	242.0	210.1	191.1	179.9
67.5°	238.1	246.2	267.5	277.4	292.7	269.9	220.0	186.1	168.0	152.0	144.1
70°	207.8	213.7	225.0	233.1	237.1	213.7	176.7	151.9	136.6	125.3	120.4
72.5°	177.5	182.6	184.9	191.6	189.5	167.6	142.1	122.3	111.3	103.7	97.3
75°	135.7	137.9	135.7	132.9	127.1	111.8	94.2	84.3	76.2	72.6	70.3
77.5°	98.9	98.2	95.1	90.8	80.8	71.2	61.7	58.5	54.9	53.0	52.2
80°	76.2	74.4	71.6	64.9	56.3	49.6	47.4	45.1	43.7	41.5	41.0
82.5°	56.7	55.6	51.1	45.5	39.4	36.2	34.4	33.6	32.2	31.0	30.9
85°	30.2	28.8	23.8	20.8	19.8	18.9	18.5	18.5	16.7	16.2	16.2
87.5°	10.2	8.4	8.4	7.6	7.9	7.6	8.4	8.0	8.1	8.3	7.7
90°	2.7	4.0	6.0	7.4	8.8	10.8	12.8	14.8	16.8	16.2	16.8
92.5°	12.4	18.1	23.3	28.9	38.9	56.6	85.5	113.9	103.5	78.1	56.7
95°	24.9	32.3	43.7	61.2	87.5	144.7	245.0	355.4	399.2	323.8	242.4
97.5°	39.7	45.5	55.4	72.7	101.1	155.8	268.9	452.9	618.6	661.9	604.1
100°	50.5	55.2	64.7	80.8	107.0	154.1	253.7	430.8	637.5	770.1	793.7
102.5°	62.3	66.5	75.4	90.0	114.0	156.3	240.8	398.5	602.4	775.5	856.6
105°	80.1	84.1	92.2	105.0	125.9	162.2	231.5	358.8	541.2	734.4	875.1
107.5°	98.2	102.0	109.9	122.0	141.4	173.2	230.9	333.5	487.1	662.5	822.1
110°	111.1	114.4	121.8	133.3	152.1	182.4	233.6	323.8	456.4	617.3	771.5



TEST NUMBER: P332314-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	123.0	126.3	133.7	145.2	163.4	191.6	238.9	318.4	435.9	578.0	721.3
115°	140.7	144.7	151.4	162.9	181.1	206.6	247.7	316.4	414.0	530.5	655.0
117.5°	158.2	161.5	167.7	180.6	197.3	222.7	259.3	317.6	401.1	501.8	606.9
120°	168.9	172.3	179.1	191.8	208.7	232.9	267.9	319.8	395.1	486.7	581.6
122.5°	179.2	182.5	189.9	202.1	220.0	243.7	276.0	323.5	391.4	474.3	561.7
125°	193.2	197.3	204.7	217.4	235.6	259.2	288.8	329.2	386.4	458.4	535.1
127.5°	205.0	210.0	217.6	231.7	249.9	272.6	299.3	335.6	384.0	444.4	512.0
130°	212.1	218.1	226.2	240.3	258.5	280.7	306.3	339.9	382.4	436.9	497.5
132.5°	218.0	224.5	234.3	248.4	266.0	287.7	312.7	343.2	381.8	429.9	484.0
135°	227.6	235.0	245.0	259.2	277.3	298.2	321.1	348.0	381.0	420.7	465.8
137.5°	236.5	243.8	254.6	268.5	285.4	305.5	327.3	351.3	379.5	412.8	449.3
140°	243.0	249.8	260.5	274.0	290.8	310.3	330.5	353.4	379.0	407.9	439.5
142.5°	248.9	256.2	265.9	279.4	295.1	314.1	333.7	355.0	377.9	403.6	430.4
145°	258.5	264.6	274.7	286.1	301.6	319.1	337.3	356.1	376.3	397.9	419.4
147.5°	268.2	274.1	282.8	293.9	307.1	323.1	339.4	356.1	373.8	392.2	410.4
150°	274.7	280.0	288.8	298.2	310.3	325.8	339.9	356.1	371.6	388.4	403.9
152.5°	281.1	286.5	294.2	302.5	314.1	327.4	341.0	354.5	368.9	384.1	398.0
155°	291.4	295.5	302.2	309.6	319.1	330.5	341.3	352.8	364.2	377.6	389.1
157.5°	300.3	303.6	309.5	315.8	323.1	332.3	342.0	350.4	360.0	370.4	379.6
160°	306.3	309.0	314.4	319.1	325.8	333.9	342.0	349.4	356.8	365.5	374.3
162.5°	311.2	313.3	317.6	321.8	327.4	334.4	341.4	347.2	353.5	360.7	367.8
165°	317.7	319.1	322.4	325.1	329.8	335.2	339.9	344.0	348.7	354.0	359.5
167.5°	323.1	323.8	326.3	328.2	331.2	335.1	338.9	340.8	343.9	347.8	352.1
170°	325.8	326.5	328.5	329.8	331.2	334.6	337.3	338.6	340.6	344.0	347.3
172.5°	328.5	328.6	330.1	330.9	331.7	334.6	336.7	337.0	337.9	340.2	343.0
175°	331.2	330.5	331.8	331.8	332.5	333.9	335.2	334.6	334.6	335.9	337.3
177.5°	332.5	332.0	332.5	332.5	332.5	333.0	334.2	333.0	332.5	333.0	333.6
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P332314-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1110.7	1110.7	1112.2	1117.6	1118.3	1123.0	1121.5
5°	1220.7	1229.2	1232.4	1246.0	1254.0	1257.7	1250.4
7.5°	1355.2	1379.4	1390.9	1405.0	1417.6	1421.3	1411.4
10°	1453.3	1478.5	1499.8	1512.8	1525.0	1533.1	1543.4
12.5°	1548.2	1579.2	1599.3	1617.7	1630.3	1640.5	1642.3
15°	1651.2	1698.1	1733.7	1759.8	1772.9	1779.7	1776.9
17.5°	1755.1	1798.6	1823.9	1850.6	1868.7	1869.7	1870.2
20°	1814.0	1856.3	1885.6	1905.4	1925.7	1924.9	1929.3
22.5°	1853.2	1886.6	1909.0	1923.5	1930.4	1927.0	1927.9
25°	1871.6	1881.5	1877.5	1854.5	1848.7	1827.5	1831.1
27.5°	1776.8	1729.9	1681.4	1619.0	1569.8	1530.5	1532.5
30°	1648.0	1565.1	1470.4	1391.1	1319.9	1300.0	1257.7
32.5°	1468.1	1343.7	1232.8	1158.8	1097.7	1081.2	1044.2
35°	1163.0	1042.2	928.2	859.6	832.6	794.7	794.3
37.5°	904.0	797.6	737.3	685.9	658.9	636.0	633.8
40°	760.4	677.5	632.0	595.0	568.4	551.3	547.3
42.5°	660.2	593.1	550.5	527.6	507.1	498.3	491.7
45°	539.2	494.0	464.3	443.6	434.1	427.3	423.7
47.5°	451.0	420.8	400.5	386.7	379.0	371.9	373.8
50°	403.0	378.2	363.3	350.3	344.4	339.4	339.9
52.5°	364.4	342.2	330.1	320.7	313.4	309.9	308.2
55°	309.3	295.2	283.1	276.3	272.2	267.3	266.0
57.5°	263.8	253.0	243.1	235.4	234.4	229.6	230.2
60°	233.5	224.5	216.4	212.3	209.1	205.1	206.5
62.5°	208.6	201.0	193.6	190.3	187.2	184.2	184.9
65°	170.8	163.6	159.1	157.3	155.9	154.6	153.3
67.5°	136.1	131.7	128.9	125.0	122.3	121.8	120.5
70°	114.5	108.7	103.7	98.8	97.4	96.9	97.4
72.5°	91.8	88.1	86.7	84.3	84.0	82.8	83.7
75°	69.0	67.6	66.7	64.9	64.9	64.9	64.9
77.5°	50.9	50.0	49.5	49.2	48.6	48.0	48.0
80°	39.7	39.2	38.3	38.3	37.9	38.3	37.9
82.5°	30.0	29.9	28.9	28.9	28.5	28.2	28.5
85°	15.3	14.9	15.8	14.9	15.3	14.5	15.3
87.5°	7.8	7.9	7.8	7.7	7.5	8.4	7.5
90°	17.5	18.2	19.5	18.9	19.5	20.2	19.5
92.5°	44.9	39.7	36.2	35.0	33.0	33.7	32.5
95°	164.3	128.5	104.4	91.5	85.5	80.8	78.1
97.5°	483.9	397.0	316.5	266.8	236.5	218.3	212.6
100°	739.1	660.4	564.7	496.8	447.6	421.4	422.1
102.5°	854.9	809.0	748.4	695.5	656.6	634.6	619.1
105°	942.4	955.2	937.7	906.7	881.1	859.6	856.3
107.5°	931.3	990.3	1014.3	1014.9	1006.3	998.9	992.7
110°	895.3	980.1	1027.3	1046.0	1051.5	1050.1	1048.8



TEST NUMBER: P332314-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	847.9	943.0	1003.5	1038.0	1054.7	1059.8	1060.1
115°	772.1	871.1	944.4	994.9	1024.5	1038.0	1041.4
117.5°	708.0	796.9	871.3	923.9	957.9	977.2	981.9
120°	672.4	753.3	821.2	874.4	912.1	928.2	932.3
122.5°	643.9	718.8	782.0	829.1	863.1	880.9	886.0
125°	608.6	673.1	727.0	770.1	799.7	816.5	821.2
127.5°	577.4	635.8	684.8	723.1	748.4	763.6	767.9
130°	558.0	612.6	658.3	694.1	718.2	732.4	737.8
132.5°	539.8	590.5	634.1	667.6	691.9	704.4	708.2
135°	513.6	557.3	595.7	628.7	648.9	661.0	665.7
137.5°	488.4	526.2	559.4	587.1	607.6	617.9	621.0
140°	473.9	506.2	535.1	560.8	579.5	590.4	589.7
142.5°	459.9	487.9	513.1	534.9	551.6	561.3	560.6
145°	441.6	463.1	482.7	499.5	513.6	519.0	520.3
147.5°	428.0	445.4	459.3	472.0	481.6	486.7	487.2
150°	419.4	433.5	446.3	456.4	463.8	467.9	467.9
152.5°	411.3	423.8	434.5	442.4	449.3	451.7	451.7
155°	399.8	409.9	418.0	424.0	429.5	430.8	431.4
157.5°	388.7	396.5	402.8	408.0	412.1	413.2	413.0
160°	381.7	388.4	393.1	397.9	401.8	401.8	401.2
162.5°	374.1	380.3	384.5	387.6	391.1	391.1	390.5
165°	363.5	368.2	371.6	374.3	376.9	376.3	376.3
167.5°	355.2	358.0	360.4	361.6	363.5	362.8	362.8
170°	349.4	352.1	353.4	354.0	355.4	354.7	354.7
172.5°	344.5	346.6	347.5	347.6	349.0	347.8	347.2
175°	337.9	339.2	339.2	339.2	339.9	339.2	338.6
177.5°	334.2	334.7	334.7	334.2	334.7	333.6	333.6
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5

(END OF REPORT)