

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331876-840

Luminaire Tested: **S123DIP-S340D585U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331876-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D585U840-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3608.6 lumens
Efficiency: N/A
Efficacy: 141.0 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331876-840
CATALOG NUMBER: S123DIP-S340D585U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331876-840

CATALOG NUMBER: S123DIP-S340D585U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41																				
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	41	35																				
2	87	80	74	69	79	73	68	64	60	57	54	49	46	44	38	36	34	29																				
3	80	71	64	58	73	65	59	54	53	49	45	43	40	37	33	31	30	25																				
4	73	63	55	49	66	57	51	46	48	43	39	38	35	32	30	28	26	22																				
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	27	24	22	19																				
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	17																				
7	57	45	37	32	52	42	35	30	35	29	26	28	24	22	22	20	18	15																				
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13																				
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12																				
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5226	5226	5226	5226
5°	6232	5249	4652	5249
10°	7802	5223	4203	5223
15°	9569	5180	3911	5180
20°	11399	5116	3725	5116
25°	12105	5035	3682	5035
30°	10376	4977	3701	4977
35°	7215	4893	3741	4893
40°	5435	4796	3729	4796
45°	4512	4652	3682	4652
50°	4042	4357	3647	4357
55°	3780	4040	3603	4040
60°	3546	3707	3565	3707
65°	3331	3380	3451	3380
70°	3125	3006	3286	3006
75°	2799	2633	3015	2633
80°	2448	2157	2597	2157
85°	1927	1568	1741	1568



TEST NUMBER: P331876-840

CATALOG NUMBER: S123DIP-S340D585U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.8	1.3
10°-20°	153.4	4.3
20°-30°	257.4	7.1
30°-40°	291.5	8.1
40°-50°	261.4	7.2
50°-60°	210.9	5.8
60°-70°	147.0	4.1
70°-80°	77.3	2.1
80°-90°	21.1	0.6
90°-100°	158.3	4.4
100°-110°	448.4	12.4
110°-120°	441.1	12.2
120°-130°	351.8	9.7
130°-140°	277.4	7.7
140°-150°	207.0	5.7
150°-160°	144.3	4.0
160°-170°	84.8	2.3
170°-180°	27.6	0.8
0°-30°	458.6	12.7
0°-40°	750.1	20.8
0°-60°	1222.4	33.9
0°-90°	1467.8	40.7
90°-120°	1047.8	29.0
90°-150°	1884.1	52.2
90°-180°	2141.0	59.3
0°-180°	3608.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	486	486	486	486	486	
5°	577	486	430	486	577	60
15°	859	465	351	465	859	248
25°	1019	424	310	424	1019	447
35°	549	372	285	372	549	357
45°	296	306	242	306	296	235
55°	201	215	192	215	201	181
65°	131	133	136	133	131	130
75°	67	63	72	63	67	72
85°	16	13	14	13	16	19
90°	17	1	17	1	17	10
95°	67	20	67	20	67	120
105°	733	67	733	67	733	723
115°	891	118	891	118	891	866
125°	703	164	703	164	703	637
135°	570	192	570	192	570	442
145°	445	219	445	219	445	283
155°	369	249	369	249	369	172
165°	322	272	322	272	322	92
175°	290	284	290	284	290	28
180°	285	285	285	285	285	



TEST NUMBER: P331876-840

CATALOG NUMBER: S123DIP-S340D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	515.3	514.9	514.0	514.7	513.2	511.2	511.0	509.1	503.6	503.3	501.8
5°	576.8	575.0	574.7	574.5	571.2	566.7	558.3	557.5	546.2	540.7	533.8
7.5°	656.6	657.5	654.1	651.2	641.1	634.4	625.3	613.7	599.9	585.7	576.4
10°	713.8	721.5	712.0	705.3	699.2	687.7	674.3	657.5	640.9	621.4	606.5
12.5°	775.2	778.9	777.0	770.8	761.3	743.8	720.0	701.6	686.2	653.7	640.6
15°	858.7	873.0	863.8	842.7	843.1	826.5	795.5	761.3	743.2	714.7	675.9
17.5°	947.8	949.5	945.6	928.0	916.3	893.2	864.5	831.9	795.2	760.7	719.5
20°	995.1	993.7	985.5	976.3	956.1	938.3	907.0	870.5	823.4	789.5	744.6
22.5°	1021.5	1019.2	1015.2	1007.5	990.8	971.6	943.4	903.6	858.8	812.1	760.2
25°	1019.2	1022.2	1022.7	1020.6	1014.7	1003.2	981.1	949.3	904.6	844.6	790.5
27.5°	927.0	931.3	943.8	955.0	967.5	980.2	978.5	962.7	929.6	877.8	811.6
30°	834.8	825.3	848.6	878.0	898.0	933.3	953.0	954.2	935.6	891.2	826.7
32.5°	706.7	717.1	727.4	763.6	807.3	846.9	886.3	917.9	921.5	891.9	835.6
35°	549.1	562.1	580.9	599.7	646.7	687.2	756.4	816.6	864.5	870.9	836.4
37.5°	442.5	448.9	460.8	479.7	510.4	558.5	611.9	688.0	757.6	809.3	811.5
40°	386.8	388.7	402.0	416.4	441.3	480.9	529.1	596.4	679.6	751.9	782.0
42.5°	345.0	349.1	354.9	368.6	388.5	418.2	463.0	518.7	595.0	678.1	737.0
45°	296.4	301.1	304.7	313.9	328.0	348.0	379.2	430.1	488.2	574.0	653.3
47.5°	264.4	264.7	267.3	274.3	283.9	298.9	321.0	353.7	407.0	476.7	558.1
50°	241.4	245.1	246.1	251.5	259.0	270.0	288.4	316.2	359.9	421.1	495.9
52.5°	225.2	226.3	228.9	232.9	239.4	248.0	264.0	285.7	320.0	372.2	441.0
55°	201.4	201.4	204.0	207.0	210.8	218.5	229.1	245.1	271.2	311.7	368.7
57.5°	179.4	180.6	182.4	183.3	186.5	191.7	200.5	212.7	232.1	263.3	308.5
60°	164.7	166.8	166.5	168.4	171.3	175.3	182.8	192.7	210.1	235.0	273.2
62.5°	151.9	151.8	151.7	154.0	156.7	160.6	165.5	174.0	188.8	211.0	243.4
65°	130.8	130.4	132.0	133.4	134.3	137.1	140.9	148.5	158.3	174.8	200.0
67.5°	112.1	110.7	111.6	112.1	113.7	115.9	119.5	124.1	131.9	145.1	164.1
70°	99.3	98.1	97.9	98.4	99.8	101.4	104.0	108.5	115.7	126.3	140.2
72.5°	86.1	85.3	85.2	86.3	86.9	88.1	89.9	93.9	99.8	107.8	120.7
75°	67.3	67.3	67.3	67.6	68.3	69.2	70.6	72.7	77.2	82.8	91.5
77.5°	50.4	50.4	50.1	50.1	51.1	51.5	51.8	53.8	56.4	60.1	66.4
80°	39.5	38.4	38.8	39.5	40.0	40.2	40.9	41.4	43.5	45.6	50.1
82.5°	29.4	28.4	28.5	29.6	29.7	29.9	30.6	31.2	32.0	33.9	36.4
85°	15.6	15.6	15.8	15.8	16.0	15.8	16.5	16.7	16.7	17.9	19.3
87.5°	9.0	8.7	8.8	8.9	8.8	8.8	8.8	8.9	9.0	9.3	9.1
90°	16.7	17.3	16.7	16.2	16.7	15.6	14.9	14.4	13.8	14.4	12.6
92.5°	27.8	28.8	28.2	30.0	31.0	34.0	38.5	48.5	66.9	88.6	97.5
95°	66.9	69.1	73.1	78.4	89.3	110.0	140.6	207.3	277.0	341.5	304.2
97.5°	181.9	186.8	202.4	228.3	270.8	339.7	414.0	516.9	566.3	529.4	387.5
100°	361.1	360.6	383.0	425.1	483.2	565.0	632.5	679.1	658.9	545.4	368.6
102.5°	529.8	543.0	561.8	595.1	640.4	692.3	731.5	733.1	663.6	515.5	341.0
105°	732.7	735.6	754.0	775.9	802.3	817.4	806.4	748.8	628.4	463.1	307.0
107.5°	849.5	854.7	861.0	868.4	867.9	847.4	797.0	703.4	566.9	416.8	285.4
110°	897.4	898.6	899.7	895.1	879.0	838.7	766.1	660.0	528.2	390.5	277.0



TEST NUMBER: P331876-840

CATALOG NUMBER: S123DIP-S340D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	907.1	906.9	902.5	888.2	858.7	806.9	725.5	617.2	494.5	373.0	272.5
115°	891.1	888.2	876.7	851.3	808.1	745.4	660.7	560.5	453.9	354.3	270.7
117.5°	840.1	836.3	819.6	790.6	745.6	681.9	605.8	519.3	429.4	343.2	271.8
120°	797.8	794.3	780.5	748.2	702.8	644.5	575.4	497.7	416.5	338.1	273.6
122.5°	758.1	753.8	738.5	709.5	669.0	615.0	551.0	480.6	405.9	334.9	276.8
125°	702.8	698.7	684.3	658.9	622.1	576.0	520.7	457.9	392.2	330.6	281.7
127.5°	657.1	653.4	640.4	618.7	585.9	544.0	494.1	438.1	380.3	328.5	287.2
130°	631.3	626.7	614.6	593.9	563.3	524.1	477.5	425.7	373.9	327.2	290.8
132.5°	605.9	602.7	592.0	571.3	542.6	505.2	461.8	414.1	367.8	326.7	293.7
135°	569.7	565.6	555.2	538.0	509.8	477.0	439.5	398.6	360.0	326.0	297.8
137.5°	531.3	528.7	519.9	502.4	478.7	450.2	418.0	384.5	353.3	324.8	300.5
140°	504.5	505.1	495.9	479.8	457.9	433.1	405.5	376.2	349.0	324.3	302.4
142.5°	479.7	480.3	472.0	457.7	439.0	417.5	393.5	368.3	345.4	323.4	303.8
145°	445.2	444.1	439.5	427.4	413.0	396.3	377.9	358.8	340.4	321.9	304.7
147.5°	416.9	416.5	412.0	403.8	392.9	381.1	366.2	351.1	335.6	319.8	304.7
150°	400.3	400.3	396.9	390.5	381.9	370.9	358.8	345.6	332.3	317.9	304.7
152.5°	386.5	386.5	384.5	378.5	371.7	362.6	351.9	340.5	328.7	315.7	303.4
155°	369.2	368.6	367.5	362.8	357.7	350.8	342.1	333.0	323.2	311.6	301.8
157.5°	353.5	353.6	352.6	349.2	344.7	339.3	332.5	324.9	316.9	308.0	299.8
160°	343.3	343.9	343.9	340.4	336.4	332.3	326.6	320.2	312.8	305.3	298.9
162.5°	334.1	334.7	334.7	331.6	329.0	325.5	320.1	314.8	308.6	302.6	297.1
165°	321.9	321.9	322.6	320.2	317.9	315.1	311.0	307.6	303.0	298.4	294.4
167.5°	310.4	310.4	311.0	309.4	308.4	306.3	304.0	301.3	297.6	294.2	291.5
170°	303.6	303.6	304.2	303.0	302.4	301.2	298.9	297.2	294.4	291.4	289.7
172.5°	297.1	297.6	298.6	297.4	297.3	296.6	294.8	293.6	291.1	289.1	288.3
175°	289.7	290.3	290.8	290.3	290.3	290.3	289.1	288.6	287.4	286.3	286.3
177.5°	285.5	285.5	286.4	285.9	286.4	286.4	285.9	285.5	285.0	284.6	285.0
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P331876-840

CATALOG NUMBER: S123DIP-S340D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	500.6	499.2	497.7	495.0	492.7	489.6	488.6	487.5	484.0	481.1	478.8
5°	531.2	525.5	517.4	509.8	503.7	495.4	490.8	485.8	478.8	472.4	467.3
7.5°	563.2	552.1	539.3	525.5	512.6	500.2	490.2	481.2	471.3	462.0	454.6
10°	588.7	572.6	554.7	535.4	519.0	503.0	489.6	477.9	465.1	454.0	444.8
12.5°	617.6	593.9	569.3	545.8	526.3	504.1	487.9	472.9	458.5	445.2	434.9
15°	651.9	621.8	592.6	560.4	530.8	503.0	483.7	464.8	448.2	434.5	421.3
17.5°	683.2	649.0	610.6	571.4	535.6	502.7	475.7	454.4	433.5	416.9	403.7
20°	700.8	662.1	618.5	577.8	538.3	501.6	471.9	446.6	423.9	406.3	391.5
22.5°	716.1	670.7	625.6	582.1	538.1	498.6	464.9	438.8	414.3	397.1	381.3
25°	732.0	677.5	632.4	581.4	532.2	491.2	453.6	423.9	399.5	379.2	363.0
27.5°	745.5	677.1	623.5	568.6	522.8	481.8	441.6	409.8	383.8	361.8	345.4
30°	754.5	678.0	614.3	560.0	513.8	471.5	432.4	400.4	373.1	350.8	335.3
32.5°	760.1	677.4	605.8	547.9	499.5	462.0	422.4	389.3	361.2	339.3	324.4
35°	763.5	673.3	591.2	523.0	476.5	439.9	406.8	372.4	343.1	322.6	305.6
37.5°	756.8	664.6	574.3	499.0	448.0	412.1	384.2	355.0	326.8	304.3	289.6
40°	746.5	658.9	561.1	482.0	428.4	393.8	370.1	341.3	313.6	292.2	278.5
42.5°	726.7	647.5	546.6	463.2	408.1	373.5	351.6	327.6	301.3	281.2	267.6
45°	678.5	622.5	524.8	435.0	378.1	342.3	323.1	305.6	281.9	262.4	250.5
47.5°	611.6	584.9	493.4	405.3	346.7	312.4	292.3	278.3	260.9	245.1	233.9
50°	565.1	554.0	472.2	384.9	325.9	292.2	272.9	260.2	247.7	232.0	221.7
52.5°	511.5	518.3	447.4	363.9	304.6	271.5	253.4	243.3	232.0	218.9	210.0
55°	436.0	460.6	404.5	328.4	272.9	241.4	224.2	215.3	208.6	199.0	191.3
57.5°	365.3	396.7	358.0	292.0	241.8	214.6	198.1	188.4	184.2	179.2	173.0
60°	323.3	354.3	324.9	267.5	221.0	195.0	180.5	172.2	167.9	164.4	159.3
62.5°	285.8	317.2	292.6	242.7	200.4	176.4	163.7	155.6	152.4	150.6	146.1
65°	234.3	261.4	244.9	204.0	171.1	149.9	138.4	132.7	129.7	129.0	126.1
67.5°	190.7	211.3	199.3	169.2	143.3	125.0	115.2	110.4	108.1	107.8	105.6
70°	162.1	181.4	172.2	144.9	122.6	108.3	99.8	95.5	94.1	93.9	92.7
72.5°	139.9	153.3	146.0	123.3	106.0	93.0	86.7	82.3	80.8	81.1	80.3
75°	103.5	113.6	109.4	93.6	79.8	71.3	66.1	63.3	61.9	62.6	61.6
77.5°	74.5	80.9	77.1	66.1	57.6	51.5	47.7	45.9	44.6	44.6	44.2
80°	56.2	60.0	57.9	51.3	44.2	39.1	36.0	34.8	34.1	33.8	33.6
82.5°	40.1	43.2	40.7	36.3	31.4	28.3	26.6	25.0	24.5	24.6	24.4
85°	20.2	21.4	20.5	17.7	15.8	14.3	13.4	12.7	12.2	12.4	12.0
87.5°	9.2	9.0	8.1	7.1	6.5	5.6	5.4	4.7	4.6	4.8	4.9
90°	10.9	9.2	7.5	6.4	5.2	3.4	2.3	1.1	2.3	3.4	5.2
92.5°	73.1	48.4	33.3	24.7	19.9	15.5	10.6	7.2	10.6	15.5	19.9
95°	209.6	123.8	74.8	52.4	37.5	27.7	21.3	19.6	21.3	27.7	37.5
97.5°	230.0	133.3	86.5	62.2	47.5	39.0	34.0	33.4	34.0	39.0	47.5
100°	217.1	131.9	91.6	69.1	55.3	47.3	43.2	42.6	43.2	47.3	55.3
102.5°	206.1	133.7	97.6	77.0	64.5	57.0	53.3	52.3	53.3	57.0	64.5
105°	198.1	138.9	107.8	89.9	78.9	72.0	68.6	66.9	68.6	72.0	78.9
107.5°	197.5	148.2	121.0	104.4	94.1	87.4	84.0	82.2	84.0	87.4	94.1
110°	199.9	156.1	130.2	114.0	104.2	98.0	95.0	93.3	95.0	98.0	104.2



TEST NUMBER: P331876-840

CATALOG NUMBER: S123DIP-S340D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	204.5	163.9	139.9	124.2	114.4	108.1	105.2	103.4	105.2	108.1	114.4
115°	212.0	176.8	154.9	139.4	129.6	123.8	120.4	118.1	120.4	123.8	129.6
117.5°	221.9	190.6	168.8	154.5	143.5	138.3	135.3	132.7	135.3	138.3	143.5
120°	229.2	199.2	178.5	164.2	153.2	147.4	144.6	142.9	144.6	147.4	153.2
122.5°	236.2	208.5	188.2	172.9	162.4	156.2	153.3	151.6	153.3	156.2	162.4
125°	247.1	221.8	201.6	186.0	175.1	168.7	165.3	164.2	165.3	168.7	175.1
127.5°	256.1	233.3	213.8	198.2	186.1	179.8	175.4	173.7	175.4	179.8	186.1
130°	262.1	240.1	221.2	205.6	193.5	186.6	181.5	179.8	181.5	186.6	193.5
132.5°	267.6	246.2	227.6	212.6	200.5	192.2	186.5	184.3	186.5	192.2	200.5
135°	274.8	255.2	237.3	221.8	209.6	201.1	194.7	192.4	194.7	201.1	209.6
137.5°	280.0	261.4	244.2	229.8	217.8	208.6	202.4	200.0	202.4	208.6	217.8
140°	282.9	265.5	248.8	234.4	222.9	213.7	207.9	205.1	207.9	213.7	222.9
142.5°	285.6	268.7	252.6	239.0	227.5	219.2	213.0	210.6	213.0	219.2	227.5
145°	288.6	273.1	258.0	244.8	235.0	226.4	221.2	219.4	221.2	226.4	235.0
147.5°	290.4	276.5	262.8	251.5	242.1	234.6	229.4	228.4	229.4	234.6	242.1
150°	290.8	278.8	265.5	255.2	247.1	239.6	235.0	234.4	235.0	239.6	247.1
152.5°	291.9	280.1	268.7	258.8	251.8	245.2	240.5	240.4	240.5	245.2	251.8
155°	292.1	282.9	273.1	265.0	258.6	252.9	249.4	249.4	249.4	252.9	258.6
157.5°	292.7	284.3	276.5	270.2	264.9	259.7	257.0	256.5	257.0	259.7	264.9
160°	292.7	285.7	278.8	273.1	269.0	264.4	262.1	262.1	262.1	264.4	269.0
162.5°	292.2	286.2	280.1	275.3	271.8	268.1	266.2	266.2	266.2	268.1	271.8
165°	290.8	286.8	282.3	278.2	275.9	273.1	271.9	272.5	271.9	273.1	275.9
167.5°	289.9	286.7	283.4	280.8	279.2	277.0	276.5	277.2	276.5	277.0	279.2
170°	288.6	286.3	283.4	282.3	281.0	279.3	278.8	279.9	278.8	279.3	281.0
172.5°	288.1	286.3	283.9	283.2	282.5	281.2	281.0	281.8	281.0	281.2	282.5
175°	286.8	285.7	284.6	284.0	284.0	282.9	283.4	284.0	283.4	282.9	284.0
177.5°	285.9	285.0	284.6	284.6	284.6	284.1	284.6	285.0	284.6	284.1	284.6
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P331876-840

CATALOG NUMBER: S123DIP-S340D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	477.5	476.2	474.3	471.5	469.2	465.6	465.6	466.2	466.2	466.1	465.6
5°	463.0	459.5	455.2	450.3	445.1	439.9	439.0	437.1	435.8	434.7	433.6
7.5°	447.7	441.4	435.3	428.4	422.0	416.9	413.2	410.2	408.3	406.2	404.7
10°	437.4	429.6	422.3	415.1	407.0	400.6	396.7	393.8	391.7	389.8	388.9
12.5°	425.2	416.3	408.2	401.2	392.5	386.0	382.1	380.8	378.4	374.4	372.3
15°	407.3	399.0	389.4	378.8	374.6	366.6	362.0	359.9	358.5	355.5	354.6
17.5°	391.9	381.2	370.3	362.4	354.6	348.1	345.6	343.0	341.1	338.6	337.8
20°	379.7	370.1	360.2	351.7	343.5	336.4	334.3	332.4	330.5	329.4	328.4
22.5°	367.3	357.7	349.4	341.5	332.8	328.1	325.9	323.8	322.4	321.6	320.7
25°	349.8	341.3	332.1	325.2	318.1	315.0	313.6	312.5	311.4	310.3	310.0
27.5°	334.3	325.0	317.6	310.9	305.9	303.4	301.9	301.4	301.6	302.1	302.4
30°	322.6	314.1	308.0	302.4	297.6	295.3	295.0	295.0	296.0	296.2	296.7
32.5°	311.8	304.9	298.7	293.3	289.7	288.1	289.0	289.0	289.7	290.3	291.2
35°	296.2	290.0	285.4	280.6	277.6	278.3	278.8	279.2	280.4	281.9	282.8
37.5°	281.2	276.0	271.0	267.4	266.0	267.2	268.4	269.3	270.7	271.9	272.8
40°	270.5	266.5	261.9	258.5	259.0	259.7	260.6	261.9	263.1	263.8	264.7
42.5°	260.5	256.4	252.8	250.0	250.7	251.7	252.2	252.8	254.2	255.5	256.0
45°	245.4	242.1	238.8	237.1	237.6	238.1	238.5	239.2	240.4	241.4	241.7
47.5°	228.3	226.0	223.8	222.2	223.0	222.8	223.4	224.9	225.2	225.8	227.1
50°	217.4	215.3	212.7	212.2	212.2	212.2	212.5	214.3	214.3	215.3	216.2
52.5°	205.3	204.0	202.4	201.5	201.1	201.1	202.1	203.0	203.4	204.7	205.7
55°	187.5	186.1	184.7	184.0	183.5	184.0	185.8	186.3	187.5	188.2	188.9
57.5°	169.0	167.8	166.7	166.3	166.2	166.8	167.8	169.3	169.6	171.8	172.8
60°	156.7	155.0	154.1	154.1	153.6	155.7	155.3	157.6	158.1	159.6	161.2
62.5°	144.1	141.9	141.5	141.5	142.2	142.8	143.4	144.4	145.7	147.4	148.8
65°	123.7	122.6	124.2	124.0	123.5	124.9	124.9	126.1	127.5	129.2	131.8
67.5°	104.5	103.9	104.0	104.0	104.7	105.5	106.2	107.2	109.0	110.7	112.4
70°	91.5	92.2	91.1	92.0	92.7	92.9	93.4	94.8	96.6	97.9	99.8
72.5°	78.9	78.9	79.0	79.4	80.1	80.5	81.0	82.6	84.6	85.6	87.2
75°	60.7	60.5	61.2	61.2	62.3	62.8	63.3	64.0	65.8	67.3	68.5
77.5°	44.3	44.6	44.4	45.2	44.9	45.0	46.5	47.2	47.4	50.2	50.8
80°	33.4	33.8	34.1	34.3	34.5	34.1	35.7	36.5	36.5	38.1	39.3
82.5°	24.0	24.2	24.8	25.1	25.1	25.7	25.8	26.3	26.9	27.6	29.1
85°	12.0	12.7	12.9	12.7	12.9	12.4	13.1	13.4	13.6	13.6	13.6
87.5°	5.0	5.5	5.7	6.2	6.3	6.9	6.8	6.5	6.6	7.3	6.8
90°	6.4	7.5	9.2	10.9	12.6	14.4	13.8	14.4	14.9	15.6	16.7
92.5°	24.7	33.3	48.4	73.1	97.5	88.6	66.9	48.5	38.5	34.0	31.0
95°	52.4	74.8	123.8	209.6	304.2	341.5	277.0	207.3	140.6	110.0	89.3
97.5°	62.2	86.5	133.3	230.0	387.5	529.4	566.3	516.9	414.0	339.7	270.8
100°	69.1	91.6	131.9	217.1	368.6	545.4	658.9	679.1	632.5	565.0	483.2
102.5°	77.0	97.6	133.7	206.1	341.0	515.5	663.6	733.1	731.5	692.3	640.4
105°	89.9	107.8	138.9	198.1	307.0	463.1	628.4	748.8	806.4	817.4	802.3
107.5°	104.4	121.0	148.2	197.5	285.4	416.8	566.9	703.4	797.0	847.4	867.9
110°	114.0	130.2	156.1	199.9	277.0	390.5	528.2	660.0	766.1	838.7	879.0



TEST NUMBER: P331876-840

CATALOG NUMBER: S123DIP-S340D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	124.2	139.9	163.9	204.5	272.5	373.0	494.5	617.2	725.5	806.9	858.7
115°	139.4	154.9	176.8	212.0	270.7	354.3	453.9	560.5	660.7	745.4	808.1
117.5°	154.5	168.8	190.6	221.9	271.8	343.2	429.4	519.3	605.8	681.9	745.6
120°	164.2	178.5	199.2	229.2	273.6	338.1	416.5	497.7	575.4	644.5	702.8
122.5°	172.9	188.2	208.5	236.2	276.8	334.9	405.9	480.6	551.0	615.0	669.0
125°	186.0	201.6	221.8	247.1	281.7	330.6	392.2	457.9	520.7	576.0	622.1
127.5°	198.2	213.8	233.3	256.1	287.2	328.5	380.3	438.1	494.1	544.0	585.9
130°	205.6	221.2	240.1	262.1	290.8	327.2	373.9	425.7	477.5	524.1	563.3
132.5°	212.6	227.6	246.2	267.6	293.7	326.7	367.8	414.1	461.8	505.2	542.6
135°	221.8	237.3	255.2	274.8	297.8	326.0	360.0	398.6	439.5	477.0	509.8
137.5°	229.8	244.2	261.4	280.0	300.5	324.8	353.3	384.5	418.0	450.2	478.7
140°	234.4	248.8	265.5	282.9	302.4	324.3	349.0	376.2	405.5	433.1	457.9
142.5°	239.0	252.6	268.7	285.6	303.8	323.4	345.4	368.3	393.5	417.5	439.0
145°	244.8	258.0	273.1	288.6	304.7	321.9	340.4	358.8	377.9	396.3	413.0
147.5°	251.5	262.8	276.5	290.4	304.7	319.8	335.6	351.1	366.2	381.1	392.9
150°	255.2	265.5	278.8	290.8	304.7	317.9	332.3	345.6	358.8	370.9	381.9
152.5°	258.8	268.7	280.1	291.9	303.4	315.7	328.7	340.5	351.9	362.6	371.7
155°	265.0	273.1	282.9	292.1	301.8	311.6	323.2	333.0	342.1	350.8	357.7
157.5°	270.2	276.5	284.3	292.7	299.8	308.0	316.9	324.9	332.5	339.3	344.7
160°	273.1	278.8	285.7	292.7	298.9	305.3	312.8	320.2	326.6	332.3	336.4
162.5°	275.3	280.1	286.2	292.2	297.1	302.6	308.6	314.8	320.1	325.5	329.0
165°	278.2	282.3	286.8	290.8	294.4	298.4	303.0	307.6	311.0	315.1	317.9
167.5°	280.8	283.4	286.7	289.9	291.5	294.2	297.6	301.3	304.0	306.3	308.4
170°	282.3	283.4	286.3	288.6	289.7	291.4	294.4	297.2	298.9	301.2	302.4
172.5°	283.2	283.9	286.3	288.1	288.3	289.1	291.1	293.6	294.8	296.6	297.3
175°	284.0	284.6	285.7	286.8	286.3	286.3	287.4	288.6	289.1	290.3	290.3
177.5°	284.6	284.6	285.0	285.9	285.0	284.6	285.0	285.5	285.9	286.4	286.4
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P331876-840

CATALOG NUMBER: S123DIP-S340D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	464.3	464.1	465.4	464.5	465.4	464.1	464.3	465.6	466.1	466.2	466.2
5°	432.2	432.9	430.5	430.5	430.5	432.9	432.2	433.6	434.7	435.8	437.1
7.5°	403.5	402.5	402.6	401.3	402.6	402.5	403.5	404.7	406.2	408.3	410.2
10°	386.1	384.7	384.2	384.5	384.2	384.7	386.1	388.9	389.8	391.7	393.8
12.5°	371.5	371.3	368.2	368.2	368.2	371.3	371.5	372.3	374.4	378.4	380.8
15°	354.6	350.1	349.6	351.0	349.6	350.1	354.6	354.6	355.5	358.5	359.9
17.5°	337.5	335.1	335.3	334.6	335.3	335.1	337.5	337.8	338.6	341.1	343.0
20°	328.4	327.0	326.8	325.2	326.8	327.0	328.4	328.4	329.4	330.5	332.4
22.5°	320.1	319.7	319.8	318.0	319.8	319.7	320.1	320.7	321.6	322.4	323.8
25°	309.8	311.0	310.0	310.0	310.0	311.0	309.8	310.0	310.3	311.4	312.5
27.5°	302.9	302.9	302.4	302.4	302.4	302.9	302.9	302.4	302.1	301.6	301.4
30°	297.6	297.4	297.8	297.8	297.8	297.4	297.6	296.7	296.2	296.0	295.0
32.5°	292.4	292.7	292.8	293.0	292.8	292.7	292.4	291.2	290.3	289.7	289.0
35°	284.2	284.5	285.2	284.7	285.2	284.5	284.2	282.8	281.9	280.4	279.2
37.5°	273.2	274.3	274.1	274.4	274.1	274.3	273.2	272.8	271.9	270.7	269.3
40°	264.9	265.6	265.4	265.4	265.4	265.6	264.9	264.7	263.8	263.1	261.9
42.5°	256.4	256.9	256.3	256.0	256.3	256.9	256.4	256.0	255.5	254.2	252.8
45°	242.6	242.1	242.8	241.9	242.8	242.1	242.6	241.7	241.4	240.4	239.2
47.5°	227.0	227.5	227.7	228.4	227.7	227.5	227.0	227.1	225.8	225.2	224.9
50°	216.7	218.1	218.1	217.8	218.1	218.1	216.7	216.2	215.3	214.3	214.3
52.5°	206.5	207.1	208.1	208.0	208.1	207.1	206.5	205.7	204.7	203.4	203.0
55°	190.8	191.3	191.8	192.0	191.8	191.3	190.8	188.9	188.2	187.5	186.3
57.5°	174.5	174.3	175.4	175.8	175.4	174.3	174.5	172.8	171.8	169.6	169.3
60°	163.0	163.0	164.9	165.6	164.9	163.0	163.0	161.2	159.6	158.1	157.6
62.5°	150.8	151.6	153.4	152.5	153.4	151.6	150.8	148.8	147.4	145.7	144.4
65°	132.9	134.8	134.6	135.5	134.6	134.8	132.9	131.8	129.2	127.5	126.1
67.5°	114.2	115.4	117.1	117.2	117.1	115.4	114.2	112.4	110.7	109.0	107.2
70°	101.6	102.8	103.7	104.4	103.7	102.8	101.6	99.8	97.9	96.6	94.8
72.5°	89.4	90.0	92.3	91.3	92.3	90.0	89.4	87.2	85.6	84.6	82.6
75°	70.1	71.8	73.2	72.5	73.2	71.8	70.1	68.5	67.3	65.8	64.0
77.5°	51.8	53.5	54.1	53.5	54.1	53.5	51.8	50.8	50.2	47.4	47.2
80°	40.9	40.7	42.1	41.9	42.1	40.7	40.9	39.3	38.1	36.5	36.5
82.5°	30.0	29.8	30.4	30.6	30.4	29.8	30.0	29.1	27.6	26.9	26.3
85°	14.5	15.2	14.3	14.1	14.3	15.2	14.5	13.6	13.6	13.6	13.4
87.5°	6.6	6.8	6.7	6.4	6.7	6.8	6.6	6.8	7.3	6.6	6.5
90°	16.2	16.7	17.3	16.7	17.3	16.7	16.2	16.7	15.6	14.9	14.4
92.5°	30.0	28.2	28.8	27.8	28.8	28.2	30.0	31.0	34.0	38.5	48.5
95°	78.4	73.1	69.1	66.9	69.1	73.1	78.4	89.3	110.0	140.6	207.3
97.5°	228.3	202.4	186.8	181.9	186.8	202.4	228.3	270.8	339.7	414.0	516.9
100°	425.1	383.0	360.6	361.1	360.6	383.0	425.1	483.2	565.0	632.5	679.1
102.5°	595.1	561.8	543.0	529.8	543.0	561.8	595.1	640.4	692.3	731.5	733.1
105°	775.9	754.0	735.6	732.7	735.6	754.0	775.9	802.3	817.4	806.4	748.8
107.5°	868.4	861.0	854.7	849.5	854.7	861.0	868.4	867.9	847.4	797.0	703.4
110°	895.1	899.7	898.6	897.4	898.6	899.7	895.1	879.0	838.7	766.1	660.0



TEST NUMBER: P331876-840

CATALOG NUMBER: S123DIP-S340D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	888.2	902.5	906.9	907.1	906.9	902.5	888.2	858.7	806.9	725.5	617.2
115°	851.3	876.7	888.2	891.1	888.2	876.7	851.3	808.1	745.4	660.7	560.5
117.5°	790.6	819.6	836.3	840.1	836.3	819.6	790.6	745.6	681.9	605.8	519.3
120°	748.2	780.5	794.3	797.8	794.3	780.5	748.2	702.8	644.5	575.4	497.7
122.5°	709.5	738.5	753.8	758.1	753.8	738.5	709.5	669.0	615.0	551.0	480.6
125°	658.9	684.3	698.7	702.8	698.7	684.3	658.9	622.1	576.0	520.7	457.9
127.5°	618.7	640.4	653.4	657.1	653.4	640.4	618.7	585.9	544.0	494.1	438.1
130°	593.9	614.6	626.7	631.3	626.7	614.6	593.9	563.3	524.1	477.5	425.7
132.5°	571.3	592.0	602.7	605.9	602.7	592.0	571.3	542.6	505.2	461.8	414.1
135°	538.0	555.2	565.6	569.7	565.6	555.2	538.0	509.8	477.0	439.5	398.6
137.5°	502.4	519.9	528.7	531.3	528.7	519.9	502.4	478.7	450.2	418.0	384.5
140°	479.8	495.9	505.1	504.5	505.1	495.9	479.8	457.9	433.1	405.5	376.2
142.5°	457.7	472.0	480.3	479.7	480.3	472.0	457.7	439.0	417.5	393.5	368.3
145°	427.4	439.5	444.1	445.2	444.1	439.5	427.4	413.0	396.3	377.9	358.8
147.5°	403.8	412.0	416.5	416.9	416.5	412.0	403.8	392.9	381.1	366.2	351.1
150°	390.5	396.9	400.3	400.3	400.3	396.9	390.5	381.9	370.9	358.8	345.6
152.5°	378.5	384.5	386.5	386.5	386.5	384.5	378.5	371.7	362.6	351.9	340.5
155°	362.8	367.5	368.6	369.2	368.6	367.5	362.8	357.7	350.8	342.1	333.0
157.5°	349.2	352.6	353.6	353.5	353.6	352.6	349.2	344.7	339.3	332.5	324.9
160°	340.4	343.9	343.9	343.3	343.9	343.9	340.4	336.4	332.3	326.6	320.2
162.5°	331.6	334.7	334.7	334.1	334.7	334.7	331.6	329.0	325.5	320.1	314.8
165°	320.2	322.6	321.9	321.9	321.9	322.6	320.2	317.9	315.1	311.0	307.6
167.5°	309.4	311.0	310.4	310.4	310.4	311.0	309.4	308.4	306.3	304.0	301.3
170°	303.0	304.2	303.6	303.6	303.6	304.2	303.0	302.4	301.2	298.9	297.2
172.5°	297.4	298.6	297.6	297.1	297.6	298.6	297.4	297.3	296.6	294.8	293.6
175°	290.3	290.8	290.3	289.7	290.3	290.8	290.3	290.3	290.3	289.1	288.6
177.5°	285.9	286.4	285.5	285.5	285.5	286.4	285.9	286.4	286.4	285.9	285.5
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P331876-840

CATALOG NUMBER: S123DIP-S340D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	465.6	465.6	469.2	471.5	474.3	476.2	477.5	478.8	481.1	484.0	487.5
5°	439.0	439.9	445.1	450.3	455.2	459.5	463.0	467.3	472.4	478.8	485.8
7.5°	413.2	416.9	422.0	428.4	435.3	441.4	447.7	454.6	462.0	471.3	481.2
10°	396.7	400.6	407.0	415.1	422.3	429.6	437.4	444.8	454.0	465.1	477.9
12.5°	382.1	386.0	392.5	401.2	408.2	416.3	425.2	434.9	445.2	458.5	472.9
15°	362.0	366.6	374.6	378.8	389.4	399.0	407.3	421.3	434.5	448.2	464.8
17.5°	345.6	348.1	354.6	362.4	370.3	381.2	391.9	403.7	416.9	433.5	454.4
20°	334.3	336.4	343.5	351.7	360.2	370.1	379.7	391.5	406.3	423.9	446.6
22.5°	325.9	328.1	332.8	341.5	349.4	357.7	367.3	381.3	397.1	414.3	438.8
25°	313.6	315.0	318.1	325.2	332.1	341.3	349.8	363.0	379.2	399.5	423.9
27.5°	301.9	303.4	305.9	310.9	317.6	325.0	334.3	345.4	361.8	383.8	409.8
30°	295.0	295.3	297.6	302.4	308.0	314.1	322.6	335.3	350.8	373.1	400.4
32.5°	289.0	288.1	289.7	293.3	298.7	304.9	311.8	324.4	339.3	361.2	389.3
35°	278.8	278.3	277.6	280.6	285.4	290.0	296.2	305.6	322.6	343.1	372.4
37.5°	268.4	267.2	266.0	267.4	271.0	276.0	281.2	289.6	304.3	326.8	355.0
40°	260.6	259.7	259.0	258.5	261.9	266.5	270.5	278.5	292.2	313.6	341.3
42.5°	252.2	251.7	250.7	250.0	252.8	256.4	260.5	267.6	281.2	301.3	327.6
45°	238.5	238.1	237.6	237.1	238.8	242.1	245.4	250.5	262.4	281.9	305.6
47.5°	223.4	222.8	223.0	222.2	223.8	226.0	228.3	233.9	245.1	260.9	278.3
50°	212.5	212.2	212.2	212.2	212.7	215.3	217.4	221.7	232.0	247.7	260.2
52.5°	202.1	201.1	201.1	201.5	202.4	204.0	205.3	210.0	218.9	232.0	243.3
55°	185.8	184.0	183.5	184.0	184.7	186.1	187.5	191.3	199.0	208.6	215.3
57.5°	167.8	166.8	166.2	166.3	166.7	167.8	169.0	173.0	179.2	184.2	188.4
60°	155.3	155.7	153.6	154.1	154.1	155.0	156.7	159.3	164.4	167.9	172.2
62.5°	143.4	142.8	142.2	141.5	141.5	141.9	144.1	146.1	150.6	152.4	155.6
65°	124.9	124.9	123.5	124.0	124.2	122.6	123.7	126.1	129.0	129.7	132.7
67.5°	106.2	105.5	104.7	104.0	104.0	103.9	104.5	105.6	107.8	108.1	110.4
70°	93.4	92.9	92.7	92.0	91.1	92.2	91.5	92.7	93.9	94.1	95.5
72.5°	81.0	80.5	80.1	79.4	79.0	78.9	78.9	80.3	81.1	80.8	82.3
75°	63.3	62.8	62.3	61.2	61.2	60.5	60.7	61.6	62.6	61.9	63.3
77.5°	46.5	45.0	44.9	45.2	44.4	44.6	44.3	44.2	44.6	44.6	45.9
80°	35.7	34.1	34.5	34.3	34.1	33.8	33.4	33.6	33.8	34.1	34.8
82.5°	25.8	25.7	25.1	25.1	24.8	24.2	24.0	24.4	24.6	24.5	25.0
85°	13.1	12.4	12.9	12.7	12.9	12.7	12.0	12.0	12.4	12.2	12.7
87.5°	6.8	6.9	6.3	6.2	5.7	5.5	5.0	4.9	4.8	4.6	4.7
90°	13.8	14.4	12.6	10.9	9.2	7.5	6.4	5.2	3.4	2.3	1.1
92.5°	66.9	88.6	97.5	73.1	48.4	33.3	24.7	19.9	15.5	10.6	7.2
95°	277.0	341.5	304.2	209.6	123.8	74.8	52.4	37.5	27.7	21.3	19.6
97.5°	566.3	529.4	387.5	230.0	133.3	86.5	62.2	47.5	39.0	34.0	33.4
100°	658.9	545.4	368.6	217.1	131.9	91.6	69.1	55.3	47.3	43.2	42.6
102.5°	663.6	515.5	341.0	206.1	133.7	97.6	77.0	64.5	57.0	53.3	52.3
105°	628.4	463.1	307.0	198.1	138.9	107.8	89.9	78.9	72.0	68.6	66.9
107.5°	566.9	416.8	285.4	197.5	148.2	121.0	104.4	94.1	87.4	84.0	82.2
110°	528.2	390.5	277.0	199.9	156.1	130.2	114.0	104.2	98.0	95.0	93.3



TEST NUMBER: P331876-840

CATALOG NUMBER: S123DIP-S340D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	494.5	373.0	272.5	204.5	163.9	139.9	124.2	114.4	108.1	105.2	103.4
115°	453.9	354.3	270.7	212.0	176.8	154.9	139.4	129.6	123.8	120.4	118.1
117.5°	429.4	343.2	271.8	221.9	190.6	168.8	154.5	143.5	138.3	135.3	132.7
120°	416.5	338.1	273.6	229.2	199.2	178.5	164.2	153.2	147.4	144.6	142.9
122.5°	405.9	334.9	276.8	236.2	208.5	188.2	172.9	162.4	156.2	153.3	151.6
125°	392.2	330.6	281.7	247.1	221.8	201.6	186.0	175.1	168.7	165.3	164.2
127.5°	380.3	328.5	287.2	256.1	233.3	213.8	198.2	186.1	179.8	175.4	173.7
130°	373.9	327.2	290.8	262.1	240.1	221.2	205.6	193.5	186.6	181.5	179.8
132.5°	367.8	326.7	293.7	267.6	246.2	227.6	212.6	200.5	192.2	186.5	184.3
135°	360.0	326.0	297.8	274.8	255.2	237.3	221.8	209.6	201.1	194.7	192.4
137.5°	353.3	324.8	300.5	280.0	261.4	244.2	229.8	217.8	208.6	202.4	200.0
140°	349.0	324.3	302.4	282.9	265.5	248.8	234.4	222.9	213.7	207.9	205.1
142.5°	345.4	323.4	303.8	285.6	268.7	252.6	239.0	227.5	219.2	213.0	210.6
145°	340.4	321.9	304.7	288.6	273.1	258.0	244.8	235.0	226.4	221.2	219.4
147.5°	335.6	319.8	304.7	290.4	276.5	262.8	251.5	242.1	234.6	229.4	228.4
150°	332.3	317.9	304.7	290.8	278.8	265.5	255.2	247.1	239.6	235.0	234.4
152.5°	328.7	315.7	303.4	291.9	280.1	268.7	258.8	251.8	245.2	240.5	240.4
155°	323.2	311.6	301.8	292.1	282.9	273.1	265.0	258.6	252.9	249.4	249.4
157.5°	316.9	308.0	299.8	292.7	284.3	276.5	270.2	264.9	259.7	257.0	256.5
160°	312.8	305.3	298.9	292.7	285.7	278.8	273.1	269.0	264.4	262.1	262.1
162.5°	308.6	302.6	297.1	292.2	286.2	280.1	275.3	271.8	268.1	266.2	266.2
165°	303.0	298.4	294.4	290.8	286.8	282.3	278.2	275.9	273.1	271.9	272.5
167.5°	297.6	294.2	291.5	289.9	286.7	283.4	280.8	279.2	277.0	276.5	277.2
170°	294.4	291.4	289.7	288.6	286.3	283.4	282.3	281.0	279.3	278.8	279.9
172.5°	291.1	289.1	288.3	288.1	286.3	283.9	283.2	282.5	281.2	281.0	281.8
175°	287.4	286.3	286.3	286.8	285.7	284.6	284.0	284.0	282.9	283.4	284.0
177.5°	285.0	284.6	285.0	285.9	285.0	284.6	284.6	284.6	284.1	284.6	285.0
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P331876-840

CATALOG NUMBER: S123DIP-S340D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	488.6	489.6	492.7	495.0	497.7	499.2	500.6	501.8	503.3	503.6	509.1
5°	490.8	495.4	503.7	509.8	517.4	525.5	531.2	533.8	540.7	546.2	557.5
7.5°	490.2	500.2	512.6	525.5	539.3	552.1	563.2	576.4	585.7	599.9	613.7
10°	489.6	503.0	519.0	535.4	554.7	572.6	588.7	606.5	621.4	640.9	657.5
12.5°	487.9	504.1	526.3	545.8	569.3	593.9	617.6	640.6	653.7	686.2	701.6
15°	483.7	503.0	530.8	560.4	592.6	621.8	651.9	675.9	714.7	743.2	761.3
17.5°	475.7	502.7	535.6	571.4	610.6	649.0	683.2	719.5	760.7	795.2	831.9
20°	471.9	501.6	538.3	577.8	618.5	662.1	700.8	744.6	789.5	823.4	870.5
22.5°	464.9	498.6	538.1	582.1	625.6	670.7	716.1	760.2	812.1	858.8	903.6
25°	453.6	491.2	532.2	581.4	632.4	677.5	732.0	790.5	844.6	904.6	949.3
27.5°	441.6	481.8	522.8	568.6	623.5	677.1	745.5	811.6	877.8	929.6	962.7
30°	432.4	471.5	513.8	560.0	614.3	678.0	754.5	826.7	891.2	935.6	954.2
32.5°	422.4	462.0	499.5	547.9	605.8	677.4	760.1	835.6	891.9	921.5	917.9
35°	406.8	439.9	476.5	523.0	591.2	673.3	763.5	836.4	870.9	864.5	816.6
37.5°	384.2	412.1	448.0	499.0	574.3	664.6	756.8	811.5	809.3	757.6	688.0
40°	370.1	393.8	428.4	482.0	561.1	658.9	746.5	782.0	751.9	679.6	596.4
42.5°	351.6	373.5	408.1	463.2	546.6	647.5	726.7	737.0	678.1	595.0	518.7
45°	323.1	342.3	378.1	435.0	524.8	622.5	678.5	653.3	574.0	488.2	430.1
47.5°	292.3	312.4	346.7	405.3	493.4	584.9	611.6	558.1	476.7	407.0	353.7
50°	272.9	292.2	325.9	384.9	472.2	554.0	565.1	495.9	421.1	359.9	316.2
52.5°	253.4	271.5	304.6	363.9	447.4	518.3	511.5	441.0	372.2	320.0	285.7
55°	224.2	241.4	272.9	328.4	404.5	460.6	436.0	368.7	311.7	271.2	245.1
57.5°	198.1	214.6	241.8	292.0	358.0	396.7	365.3	308.5	263.3	232.1	212.7
60°	180.5	195.0	221.0	267.5	324.9	354.3	323.3	273.2	235.0	210.1	192.7
62.5°	163.7	176.4	200.4	242.7	292.6	317.2	285.8	243.4	211.0	188.8	174.0
65°	138.4	149.9	171.1	204.0	244.9	261.4	234.3	200.0	174.8	158.3	148.5
67.5°	115.2	125.0	143.3	169.2	199.3	211.3	190.7	164.1	145.1	131.9	124.1
70°	99.8	108.3	122.6	144.9	172.2	181.4	162.1	140.2	126.3	115.7	108.5
72.5°	86.7	93.0	106.0	123.3	146.0	153.3	139.9	120.7	107.8	99.8	93.9
75°	66.1	71.3	79.8	93.6	109.4	113.6	103.5	91.5	82.8	77.2	72.7
77.5°	47.7	51.5	57.6	66.1	77.1	80.9	74.5	66.4	60.1	56.4	53.8
80°	36.0	39.1	44.2	51.3	57.9	60.0	56.2	50.1	45.6	43.5	41.4
82.5°	26.6	28.3	31.4	36.3	40.7	43.2	40.1	36.4	33.9	32.0	31.2
85°	13.4	14.3	15.8	17.7	20.5	21.4	20.2	19.3	17.9	16.7	16.7
87.5°	5.4	5.6	6.5	7.1	8.1	9.0	9.2	9.1	9.3	9.0	8.9
90°	2.3	3.4	5.2	6.4	7.5	9.2	10.9	12.6	14.4	13.8	14.4
92.5°	10.6	15.5	19.9	24.7	33.3	48.4	73.1	97.5	88.6	66.9	48.5
95°	21.3	27.7	37.5	52.4	74.8	123.8	209.6	304.2	341.5	277.0	207.3
97.5°	34.0	39.0	47.5	62.2	86.5	133.3	230.0	387.5	529.4	566.3	516.9
100°	43.2	47.3	55.3	69.1	91.6	131.9	217.1	368.6	545.4	658.9	679.1
102.5°	53.3	57.0	64.5	77.0	97.6	133.7	206.1	341.0	515.5	663.6	733.1
105°	68.6	72.0	78.9	89.9	107.8	138.9	198.1	307.0	463.1	628.4	748.8
107.5°	84.0	87.4	94.1	104.4	121.0	148.2	197.5	285.4	416.8	566.9	703.4
110°	95.0	98.0	104.2	114.0	130.2	156.1	199.9	277.0	390.5	528.2	660.0



TEST NUMBER: P331876-840

CATALOG NUMBER: S123DIP-S340D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	105.2	108.1	114.4	124.2	139.9	163.9	204.5	272.5	373.0	494.5	617.2
115°	120.4	123.8	129.6	139.4	154.9	176.8	212.0	270.7	354.3	453.9	560.5
117.5°	135.3	138.3	143.5	154.5	168.8	190.6	221.9	271.8	343.2	429.4	519.3
120°	144.6	147.4	153.2	164.2	178.5	199.2	229.2	273.6	338.1	416.5	497.7
122.5°	153.3	156.2	162.4	172.9	188.2	208.5	236.2	276.8	334.9	405.9	480.6
125°	165.3	168.7	175.1	186.0	201.6	221.8	247.1	281.7	330.6	392.2	457.9
127.5°	175.4	179.8	186.1	198.2	213.8	233.3	256.1	287.2	328.5	380.3	438.1
130°	181.5	186.6	193.5	205.6	221.2	240.1	262.1	290.8	327.2	373.9	425.7
132.5°	186.5	192.2	200.5	212.6	227.6	246.2	267.6	293.7	326.7	367.8	414.1
135°	194.7	201.1	209.6	221.8	237.3	255.2	274.8	297.8	326.0	360.0	398.6
137.5°	202.4	208.6	217.8	229.8	244.2	261.4	280.0	300.5	324.8	353.3	384.5
140°	207.9	213.7	222.9	234.4	248.8	265.5	282.9	302.4	324.3	349.0	376.2
142.5°	213.0	219.2	227.5	239.0	252.6	268.7	285.6	303.8	323.4	345.4	368.3
145°	221.2	226.4	235.0	244.8	258.0	273.1	288.6	304.7	321.9	340.4	358.8
147.5°	229.4	234.6	242.1	251.5	262.8	276.5	290.4	304.7	319.8	335.6	351.1
150°	235.0	239.6	247.1	255.2	265.5	278.8	290.8	304.7	317.9	332.3	345.6
152.5°	240.5	245.2	251.8	258.8	268.7	280.1	291.9	303.4	315.7	328.7	340.5
155°	249.4	252.9	258.6	265.0	273.1	282.9	292.1	301.8	311.6	323.2	333.0
157.5°	257.0	259.7	264.9	270.2	276.5	284.3	292.7	299.8	308.0	316.9	324.9
160°	262.1	264.4	269.0	273.1	278.8	285.7	292.7	298.9	305.3	312.8	320.2
162.5°	266.2	268.1	271.8	275.3	280.1	286.2	292.2	297.1	302.6	308.6	314.8
165°	271.9	273.1	275.9	278.2	282.3	286.8	290.8	294.4	298.4	303.0	307.6
167.5°	276.5	277.0	279.2	280.8	283.4	286.7	289.9	291.5	294.2	297.6	301.3
170°	278.8	279.3	281.0	282.3	283.4	286.3	288.6	289.7	291.4	294.4	297.2
172.5°	281.0	281.2	282.5	283.2	283.9	286.3	288.1	288.3	289.1	291.1	293.6
175°	283.4	282.9	284.0	284.0	284.6	285.7	286.8	286.3	286.3	287.4	288.6
177.5°	284.6	284.1	284.6	284.6	284.6	285.0	285.9	285.0	284.6	285.0	285.5
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P331876-840

CATALOG NUMBER: S123DIP-S340D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	511.0	511.2	513.2	514.7	514.0	514.9	515.3
5°	558.3	566.7	571.2	574.5	574.7	575.0	576.8
7.5°	625.3	634.4	641.1	651.2	654.1	657.5	656.6
10°	674.3	687.7	699.2	705.3	712.0	721.5	713.8
12.5°	720.0	743.8	761.3	770.8	777.0	778.9	775.2
15°	795.5	826.5	843.1	842.7	863.8	873.0	858.7
17.5°	864.5	893.2	916.3	928.0	945.6	949.5	947.8
20°	907.0	938.3	956.1	976.3	985.5	993.7	995.1
22.5°	943.4	971.6	990.8	1007.5	1015.2	1019.2	1021.5
25°	981.1	1003.2	1014.7	1020.6	1022.7	1022.2	1019.2
27.5°	978.5	980.2	967.5	955.0	943.8	931.3	927.0
30°	953.0	933.3	898.0	878.0	848.6	825.3	834.8
32.5°	886.3	846.9	807.3	763.6	727.4	717.1	706.7
35°	756.4	687.2	646.7	599.7	580.9	562.1	549.1
37.5°	611.9	558.5	510.4	479.7	460.8	448.9	442.5
40°	529.1	480.9	441.3	416.4	402.0	388.7	386.8
42.5°	463.0	418.2	388.5	368.6	354.9	349.1	345.0
45°	379.2	348.0	328.0	313.9	304.7	301.1	296.4
47.5°	321.0	298.9	283.9	274.3	267.3	264.7	264.4
50°	288.4	270.0	259.0	251.5	246.1	245.1	241.4
52.5°	264.0	248.0	239.4	232.9	228.9	226.3	225.2
55°	229.1	218.5	210.8	207.0	204.0	201.4	201.4
57.5°	200.5	191.7	186.5	183.3	182.4	180.6	179.4
60°	182.8	175.3	171.3	168.4	166.5	166.8	164.7
62.5°	165.5	160.6	156.7	154.0	151.7	151.8	151.9
65°	140.9	137.1	134.3	133.4	132.0	130.4	130.8
67.5°	119.5	115.9	113.7	112.1	111.6	110.7	112.1
70°	104.0	101.4	99.8	98.4	97.9	98.1	99.3
72.5°	89.9	88.1	86.9	86.3	85.2	85.3	86.1
75°	70.6	69.2	68.3	67.6	67.3	67.3	67.3
77.5°	51.8	51.5	51.1	50.1	50.1	50.4	50.4
80°	40.9	40.2	40.0	39.5	38.8	38.4	39.5
82.5°	30.6	29.9	29.7	29.6	28.5	28.4	29.4
85°	16.5	15.8	16.0	15.8	15.8	15.6	15.6
87.5°	8.8	8.8	8.8	8.9	8.8	8.7	9.0
90°	14.9	15.6	16.7	16.2	16.7	17.3	16.7
92.5°	38.5	34.0	31.0	30.0	28.2	28.8	27.8
95°	140.6	110.0	89.3	78.4	73.1	69.1	66.9
97.5°	414.0	339.7	270.8	228.3	202.4	186.8	181.9
100°	632.5	565.0	483.2	425.1	383.0	360.6	361.1
102.5°	731.5	692.3	640.4	595.1	561.8	543.0	529.8
105°	806.4	817.4	802.3	775.9	754.0	735.6	732.7
107.5°	797.0	847.4	867.9	868.4	861.0	854.7	849.5
110°	766.1	838.7	879.0	895.1	899.7	898.6	897.4



TEST NUMBER: P331876-840

CATALOG NUMBER: S123DIP-S340D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	725.5	806.9	858.7	888.2	902.5	906.9	907.1
115°	660.7	745.4	808.1	851.3	876.7	888.2	891.1
117.5°	605.8	681.9	745.6	790.6	819.6	836.3	840.1
120°	575.4	644.5	702.8	748.2	780.5	794.3	797.8
122.5°	551.0	615.0	669.0	709.5	738.5	753.8	758.1
125°	520.7	576.0	622.1	658.9	684.3	698.7	702.8
127.5°	494.1	544.0	585.9	618.7	640.4	653.4	657.1
130°	477.5	524.1	563.3	593.9	614.6	626.7	631.3
132.5°	461.8	505.2	542.6	571.3	592.0	602.7	605.9
135°	439.5	477.0	509.8	538.0	555.2	565.6	569.7
137.5°	418.0	450.2	478.7	502.4	519.9	528.7	531.3
140°	405.5	433.1	457.9	479.8	495.9	505.1	504.5
142.5°	393.5	417.5	439.0	457.7	472.0	480.3	479.7
145°	377.9	396.3	413.0	427.4	439.5	444.1	445.2
147.5°	366.2	381.1	392.9	403.8	412.0	416.5	416.9
150°	358.8	370.9	381.9	390.5	396.9	400.3	400.3
152.5°	351.9	362.6	371.7	378.5	384.5	386.5	386.5
155°	342.1	350.8	357.7	362.8	367.5	368.6	369.2
157.5°	332.5	339.3	344.7	349.2	352.6	353.6	353.5
160°	326.6	332.3	336.4	340.4	343.9	343.9	343.3
162.5°	320.1	325.5	329.0	331.6	334.7	334.7	334.1
165°	311.0	315.1	317.9	320.2	322.6	321.9	321.9
167.5°	304.0	306.3	308.4	309.4	311.0	310.4	310.4
170°	298.9	301.2	302.4	303.0	304.2	303.6	303.6
172.5°	294.8	296.6	297.3	297.4	298.6	297.6	297.1
175°	289.1	290.3	290.3	290.3	290.8	290.3	289.7
177.5°	285.9	286.4	286.4	285.9	286.4	285.5	285.5
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6

(END OF REPORT)