

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331885-840

Luminaire Tested: **S123DIP-S340D805U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331885-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D805U840-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4403.0 lumens
Efficiency: N/A
Efficacy: 141.1 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331885-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331885-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	36	35	28
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	30	24
3	78	69	62	57	70	63	57	52	51	46	43	39	36	34	29	27	25	21
4	72	61	54	48	64	56	49	44	45	40	36	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19	16
6	61	49	41	36	54	44	38	33	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	29	33	28	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	22	41	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5226	5226	5226	5226
5°	6232	5249	4652	5249
10°	7802	5223	4203	5223
15°	9569	5180	3911	5180
20°	11399	5116	3725	5116
25°	12105	5035	3682	5035
30°	10376	4977	3701	4977
35°	7215	4893	3741	4893
40°	5435	4796	3729	4796
45°	4512	4652	3682	4652
50°	4042	4357	3647	4357
55°	3780	4040	3603	4040
60°	3546	3707	3565	3707
65°	3331	3380	3451	3380
70°	3125	3006	3286	3006
75°	2799	2633	3015	2633
80°	2448	2157	2597	2157
85°	1927	1568	1741	1568



TEST NUMBER: P331885-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.8	1.1
10°-20°	153.4	3.5
20°-30°	257.4	5.8
30°-40°	291.5	6.6
40°-50°	261.4	5.9
50°-60°	210.9	4.8
60°-70°	147.0	3.3
70°-80°	77.3	1.8
80°-90°	21.9	0.5
90°-100°	217.1	4.9
100°-110°	614.6	14.0
110°-120°	604.6	13.7
120°-130°	482.3	11.0
130°-140°	380.2	8.6
140°-150°	283.8	6.4
150°-160°	197.8	4.5
160°-170°	116.2	2.6
170°-180°	37.8	0.9
0°-30°	458.6	10.4
0°-40°	750.1	17.0
0°-60°	1222.4	27.8
0°-90°	1468.6	33.4
90°-120°	1436.3	32.6
90°-150°	2582.6	58.7
90°-180°	2934.0	66.6
0°-180°	4403.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	486	486	486	486	486	
5°	577	486	430	486	577	60
15°	859	465	351	465	859	248
25°	1019	424	310	424	1019	447
35°	549	372	285	372	549	357
45°	296	306	242	306	296	235
55°	201	215	192	215	201	181
65°	131	133	136	133	131	130
75°	67	63	72	63	67	72
85°	16	13	14	13	16	19
90°	23	2	23	2	23	13
95°	92	27	92	27	92	165
105°	1004	92	1004	92	1004	991
115°	1221	162	1221	162	1221	1187
125°	963	225	963	225	963	873
135°	781	264	781	264	781	606
145°	610	301	610	301	610	388
155°	506	342	506	342	506	236
165°	441	373	441	373	441	126
175°	397	389	397	389	397	39
180°	390	390	390	390	390	



TEST NUMBER: P331885-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	515.3	514.9	514.0	514.7	513.2	511.2	511.0	509.1	503.6	503.3	501.8
5°	576.8	575.0	574.7	574.5	571.2	566.7	558.3	557.5	546.2	540.7	533.8
7.5°	656.6	657.5	654.1	651.2	641.1	634.4	625.3	613.7	599.9	585.7	576.4
10°	713.8	721.5	712.0	705.3	699.2	687.7	674.3	657.5	640.9	621.4	606.5
12.5°	775.2	778.9	777.0	770.8	761.3	743.8	720.0	701.6	686.2	653.7	640.6
15°	858.7	873.0	863.8	842.7	843.1	826.5	795.5	761.3	743.2	714.7	675.9
17.5°	947.8	949.5	945.6	928.0	916.3	893.2	864.5	831.9	795.2	760.7	719.5
20°	995.1	993.7	985.5	976.3	956.1	938.3	907.0	870.5	823.4	789.5	744.6
22.5°	1021.5	1019.2	1015.2	1007.5	990.8	971.6	943.4	903.6	858.8	812.1	760.2
25°	1019.2	1022.2	1022.7	1020.6	1014.7	1003.2	981.1	949.3	904.6	844.6	790.5
27.5°	927.0	931.3	943.8	955.0	967.5	980.2	978.5	962.7	929.6	877.8	811.6
30°	834.8	825.3	848.6	878.0	898.0	933.3	953.0	954.2	935.6	891.2	826.7
32.5°	706.7	717.1	727.4	763.6	807.3	846.9	886.3	917.9	921.5	891.9	835.6
35°	549.1	562.1	580.9	599.7	646.7	687.2	756.4	816.6	864.5	870.9	836.4
37.5°	442.5	448.9	460.8	479.7	510.4	558.5	611.9	688.0	757.6	809.3	811.5
40°	386.8	388.7	402.0	416.4	441.3	480.9	529.1	596.4	679.6	751.9	782.0
42.5°	345.0	349.1	354.9	368.6	388.5	418.2	463.0	518.7	595.0	678.1	737.0
45°	296.4	301.1	304.7	313.9	328.0	348.0	379.2	430.1	488.2	574.0	653.3
47.5°	264.4	264.7	267.3	274.3	283.9	298.9	321.0	353.7	407.0	476.7	558.1
50°	241.4	245.1	246.1	251.5	259.0	270.0	288.4	316.2	359.9	421.1	495.9
52.5°	225.2	226.3	228.9	232.9	239.4	248.0	264.0	285.7	320.0	372.2	441.0
55°	201.4	201.4	204.0	207.0	210.8	218.5	229.1	245.1	271.2	311.7	368.7
57.5°	179.4	180.6	182.4	183.3	186.5	191.7	200.5	212.7	232.1	263.3	308.5
60°	164.7	166.8	166.5	168.4	171.3	175.3	182.8	192.7	210.1	235.0	273.2
62.5°	151.9	151.8	151.7	154.0	156.7	160.6	165.5	174.0	188.8	211.0	243.4
65°	130.8	130.4	132.0	133.4	134.3	137.1	140.9	148.5	158.3	174.8	200.0
67.5°	112.1	110.7	111.6	112.1	113.7	115.9	119.5	124.1	131.9	145.1	164.1
70°	99.3	98.1	97.9	98.4	99.8	101.4	104.0	108.5	115.7	126.3	140.2
72.5°	86.1	85.3	85.2	86.3	86.9	88.1	89.9	93.9	99.8	107.8	120.7
75°	67.3	67.3	67.3	67.6	68.3	69.2	70.6	72.7	77.2	82.8	91.5
77.5°	50.4	50.4	50.1	50.1	51.1	51.5	51.8	53.8	56.4	60.1	66.4
80°	39.5	38.4	38.8	39.5	40.0	40.2	40.9	41.4	43.5	45.6	50.1
82.5°	29.4	28.4	28.5	29.6	29.7	29.9	30.6	31.2	32.0	33.9	36.4
85°	15.6	15.6	15.8	15.8	16.0	15.8	16.5	16.7	16.7	17.9	19.3
87.5°	10.2	10.0	10.0	10.1	10.0	9.9	9.9	10.0	10.0	10.3	10.1
90°	22.9	23.7	22.9	22.1	22.9	21.3	20.5	19.7	19.0	19.7	17.4
92.5°	38.1	39.5	38.7	41.1	42.5	46.6	52.7	66.4	91.6	121.4	133.6
95°	91.6	94.7	100.3	107.3	122.4	150.8	192.7	284.3	379.8	468.2	416.9
97.5°	249.3	256.1	277.4	313.0	371.2	465.6	567.5	708.5	776.3	725.6	531.2
100°	495.0	494.2	525.0	582.7	662.4	774.6	866.9	930.9	903.2	747.7	505.3
102.5°	726.2	744.4	770.1	815.8	877.8	948.9	1002.7	1004.7	909.6	706.6	467.4
105°	1004.3	1008.2	1033.5	1063.5	1099.8	1120.3	1105.3	1026.4	861.4	634.8	420.8
107.5°	1164.4	1171.6	1180.2	1190.3	1189.6	1161.5	1092.4	964.2	777.1	571.3	391.1
110°	1230.1	1231.6	1233.2	1226.9	1204.9	1149.5	1050.1	904.8	724.0	535.3	379.8



TEST NUMBER: P331885-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1243.3	1243.0	1237.1	1217.5	1177.0	1106.0	994.5	846.1	677.9	511.3	373.4
115°	1221.4	1217.5	1201.6	1166.9	1107.7	1021.7	905.5	768.2	622.2	485.5	371.1
117.5°	1151.7	1146.2	1123.5	1083.7	1022.0	934.6	830.4	711.9	588.5	470.4	372.5
120°	1093.5	1088.7	1069.9	1025.6	963.2	883.5	788.7	682.2	570.9	463.4	375.1
122.5°	1039.2	1033.2	1012.3	972.5	917.2	843.0	755.3	658.8	556.3	459.1	379.4
125°	963.2	957.7	938.0	903.2	852.7	789.5	713.8	627.6	537.7	453.2	386.1
127.5°	900.7	895.6	877.8	848.1	803.1	745.7	677.2	600.6	521.3	450.4	393.6
130°	865.4	859.0	842.4	814.1	772.1	718.5	654.5	583.5	512.4	448.5	398.7
132.5°	830.6	826.2	811.5	783.0	743.8	692.6	633.1	567.6	504.2	447.8	402.5
135°	780.8	775.3	761.1	737.4	698.7	653.7	602.4	546.3	493.4	446.9	408.2
137.5°	728.3	724.7	712.7	688.6	656.1	617.1	572.9	526.9	484.1	445.1	412.0
140°	691.7	692.5	679.7	657.7	627.6	593.7	555.8	515.5	478.5	444.5	414.5
142.5°	657.5	658.3	646.9	627.3	601.8	572.3	539.4	504.8	473.4	443.2	416.4
145°	610.3	608.7	602.4	585.8	566.1	543.2	518.0	491.9	466.7	441.3	417.7
147.5°	571.5	570.9	564.8	553.6	538.7	522.4	502.0	481.3	460.0	438.4	417.7
150°	548.8	548.8	544.0	535.3	523.4	508.5	491.9	473.7	455.6	435.9	417.7
152.5°	529.8	529.8	526.9	518.9	509.6	497.1	482.4	466.8	450.5	432.6	415.8
155°	506.0	505.3	503.7	497.4	490.3	480.8	469.0	456.4	442.9	427.2	413.7
157.5°	484.4	484.6	483.3	478.6	472.4	465.0	455.9	445.2	434.4	422.2	411.0
160°	470.6	471.3	471.3	466.7	461.1	455.6	447.7	439.0	428.7	418.5	409.8
162.5°	458.0	458.7	458.7	454.6	451.0	446.1	438.8	431.4	423.0	414.7	407.3
165°	441.3	441.3	442.1	439.0	435.9	431.9	426.4	421.6	415.3	409.0	403.4
167.5°	425.6	425.6	426.4	424.1	422.7	419.9	416.7	413.0	407.9	403.3	399.7
170°	416.1	416.1	416.9	415.3	414.5	412.9	409.8	407.4	403.4	399.5	397.2
172.5°	407.3	407.9	409.3	407.7	407.6	406.6	404.0	402.3	399.0	396.4	395.3
175°	397.2	397.9	398.7	397.9	397.9	397.9	396.4	395.6	393.9	392.4	392.4
177.5°	391.3	391.3	392.5	391.9	392.5	392.5	391.9	391.3	390.6	390.0	390.6
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P331885-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	500.6	499.2	497.7	495.0	492.7	489.6	488.6	487.5	484.0	481.1	478.8
5°	531.2	525.5	517.4	509.8	503.7	495.4	490.8	485.8	478.8	472.4	467.3
7.5°	563.2	552.1	539.3	525.5	512.6	500.2	490.2	481.2	471.3	462.0	454.6
10°	588.7	572.6	554.7	535.4	519.0	503.0	489.6	477.9	465.1	454.0	444.8
12.5°	617.6	593.9	569.3	545.8	526.3	504.1	487.9	472.9	458.5	445.2	434.9
15°	651.9	621.8	592.6	560.4	530.8	503.0	483.7	464.8	448.2	434.5	421.3
17.5°	683.2	649.0	610.6	571.4	535.6	502.7	475.7	454.4	433.5	416.9	403.7
20°	700.8	662.1	618.5	577.8	538.3	501.6	471.9	446.6	423.9	406.3	391.5
22.5°	716.1	670.7	625.6	582.1	538.1	498.6	464.9	438.8	414.3	397.1	381.3
25°	732.0	677.5	632.4	581.4	532.2	491.2	453.6	423.9	399.5	379.2	363.0
27.5°	745.5	677.1	623.5	568.6	522.8	481.8	441.6	409.8	383.8	361.8	345.4
30°	754.5	678.0	614.3	560.0	513.8	471.5	432.4	400.4	373.1	350.8	335.3
32.5°	760.1	677.4	605.8	547.9	499.5	462.0	422.4	389.3	361.2	339.3	324.4
35°	763.5	673.3	591.2	523.0	476.5	439.9	406.8	372.4	343.1	322.6	305.6
37.5°	756.8	664.6	574.3	499.0	448.0	412.1	384.2	355.0	326.8	304.3	289.6
40°	746.5	658.9	561.1	482.0	428.4	393.8	370.1	341.3	313.6	292.2	278.5
42.5°	726.7	647.5	546.6	463.2	408.1	373.5	351.6	327.6	301.3	281.2	267.6
45°	678.5	622.5	524.8	435.0	378.1	342.3	323.1	305.6	281.9	262.4	250.5
47.5°	611.6	584.9	493.4	405.3	346.7	312.4	292.3	278.3	260.9	245.1	233.9
50°	565.1	554.0	472.2	384.9	325.9	292.2	272.9	260.2	247.7	232.0	221.7
52.5°	511.5	518.3	447.4	363.9	304.6	271.5	253.4	243.3	232.0	218.9	210.0
55°	436.0	460.6	404.5	328.4	272.9	241.4	224.2	215.3	208.6	199.0	191.3
57.5°	365.3	396.7	358.0	292.0	241.8	214.6	198.1	188.4	184.2	179.2	173.0
60°	323.3	354.3	324.9	267.5	221.0	195.0	180.5	172.2	167.9	164.4	159.3
62.5°	285.8	317.2	292.6	242.7	200.4	176.4	163.7	155.6	152.4	150.6	146.1
65°	234.3	261.4	244.9	204.0	171.1	149.9	138.4	132.7	129.7	129.0	126.1
67.5°	190.7	211.3	199.3	169.2	143.3	125.0	115.2	110.4	108.1	107.8	105.6
70°	162.1	181.4	172.2	144.9	122.6	108.3	99.8	95.5	94.1	93.9	92.7
72.5°	139.9	153.3	146.0	123.3	106.0	93.0	86.7	82.3	80.8	81.1	80.3
75°	103.5	113.6	109.4	93.6	79.8	71.3	66.1	63.3	61.9	62.6	61.6
77.5°	74.5	80.9	77.1	66.1	57.6	51.5	47.7	45.9	44.6	44.6	44.2
80°	56.2	60.0	57.9	51.3	44.2	39.1	36.0	34.8	34.1	33.8	33.6
82.5°	40.1	43.2	40.7	36.3	31.4	28.3	26.6	25.0	24.5	24.6	24.4
85°	20.2	21.4	20.5	17.7	15.8	14.3	13.4	12.7	12.2	12.4	12.0
87.5°	10.0	9.7	8.7	7.6	6.9	5.9	5.6	4.8	4.7	5.0	5.4
90°	15.0	12.6	10.3	8.7	7.1	4.7	3.1	1.6	3.1	4.7	7.1
92.5°	100.3	66.3	45.6	33.9	27.4	21.2	14.5	9.8	14.5	21.2	27.4
95°	287.4	169.8	102.6	71.8	51.3	37.9	29.2	26.9	29.2	37.9	51.3
97.5°	315.4	182.7	118.6	85.2	65.0	53.4	46.6	45.7	46.6	53.4	65.0
100°	297.6	180.8	125.5	94.7	75.8	64.7	59.2	58.5	59.2	64.7	75.8
102.5°	282.5	183.3	133.7	105.5	88.5	78.0	73.1	71.7	73.1	78.0	88.5
105°	271.6	190.3	147.6	123.2	108.2	98.7	93.9	91.6	93.9	98.7	108.2
107.5°	270.8	203.2	165.8	143.1	129.0	119.7	115.1	112.7	115.1	119.7	129.0
110°	274.0	214.0	178.4	156.3	142.9	134.2	130.3	127.9	130.3	134.2	142.9



TEST NUMBER: P331885-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	280.2	224.7	191.7	170.3	156.8	148.1	144.2	141.8	144.2	148.1	156.8
115°	290.5	242.4	212.4	191.1	177.6	169.8	165.0	161.9	165.0	169.8	177.6
117.5°	304.2	261.2	231.5	211.8	196.7	189.5	185.5	181.9	185.5	189.5	196.7
120°	314.3	273.2	244.8	225.0	210.1	202.1	198.1	195.8	198.1	202.1	210.1
122.5°	323.7	285.8	258.0	237.0	222.7	214.1	210.2	207.8	210.2	214.1	222.7
125°	338.7	304.0	276.3	255.0	240.0	231.4	226.6	225.0	226.6	231.4	240.0
127.5°	351.0	319.7	293.1	271.8	255.2	246.3	240.4	238.1	240.4	246.3	255.2
130°	359.2	329.2	303.2	281.9	265.3	255.8	248.7	246.3	248.7	255.8	265.3
132.5°	366.8	337.4	312.0	291.3	274.8	263.4	255.7	252.7	255.7	263.4	274.8
135°	376.6	349.7	325.3	304.0	287.4	275.6	266.9	263.7	266.9	275.6	287.4
137.5°	383.8	358.3	334.8	315.0	298.6	286.0	277.4	274.1	277.4	286.0	298.6
140°	387.7	364.0	341.0	321.3	305.6	293.0	285.0	281.0	285.0	293.0	305.6
142.5°	391.4	368.4	346.1	327.7	311.8	300.5	292.0	288.6	292.0	300.5	311.8
145°	395.6	374.3	353.8	335.6	322.1	310.3	303.2	300.8	303.2	310.3	322.1
147.5°	398.1	379.0	360.2	344.7	331.7	321.5	314.6	313.2	314.6	321.5	331.7
150°	398.7	382.1	364.0	349.7	338.7	328.4	322.1	321.3	322.1	328.4	338.7
152.5°	400.0	384.1	368.4	354.8	345.1	336.0	329.7	329.5	329.7	336.0	345.1
155°	400.3	387.7	374.3	363.1	354.5	346.6	341.8	341.8	341.8	346.6	354.5
157.5°	401.1	389.7	379.0	370.4	363.0	356.1	352.2	351.6	352.2	356.1	363.0
160°	401.1	391.6	382.1	374.3	368.7	362.4	359.2	359.2	359.2	362.4	368.7
162.5°	400.4	392.2	384.1	377.4	372.5	367.5	365.0	365.0	365.0	367.5	372.5
165°	398.7	393.1	386.9	381.3	378.2	374.3	372.6	373.4	372.6	374.3	378.2
167.5°	397.5	393.0	388.5	385.0	382.7	379.8	379.0	379.9	379.0	379.8	382.7
170°	395.6	392.4	388.5	386.9	385.3	382.9	382.1	383.7	382.1	382.9	385.3
172.5°	395.0	392.4	389.1	388.1	387.2	385.5	385.3	386.3	385.3	385.5	387.2
175°	393.1	391.6	390.0	389.2	389.2	387.7	388.5	389.2	388.5	387.7	389.2
177.5°	391.9	390.6	390.0	390.0	390.0	389.4	390.0	390.6	390.0	389.4	390.0
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P331885-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	477.5	476.2	474.3	471.5	469.2	465.6	465.6	466.2	466.2	466.1	465.6
5°	463.0	459.5	455.2	450.3	445.1	439.9	439.0	437.1	435.8	434.7	433.6
7.5°	447.7	441.4	435.3	428.4	422.0	416.9	413.2	410.2	408.3	406.2	404.7
10°	437.4	429.6	422.3	415.1	407.0	400.6	396.7	393.8	391.7	389.8	388.9
12.5°	425.2	416.3	408.2	401.2	392.5	386.0	382.1	380.8	378.4	374.4	372.3
15°	407.3	399.0	389.4	378.8	374.6	366.6	362.0	359.9	358.5	355.5	354.6
17.5°	391.9	381.2	370.3	362.4	354.6	348.1	345.6	343.0	341.1	338.6	337.8
20°	379.7	370.1	360.2	351.7	343.5	336.4	334.3	332.4	330.5	329.4	328.4
22.5°	367.3	357.7	349.4	341.5	332.8	328.1	325.9	323.8	322.4	321.6	320.7
25°	349.8	341.3	332.1	325.2	318.1	315.0	313.6	312.5	311.4	310.3	310.0
27.5°	334.3	325.0	317.6	310.9	305.9	303.4	301.9	301.4	301.6	302.1	302.4
30°	322.6	314.1	308.0	302.4	297.6	295.3	295.0	295.0	296.0	296.2	296.7
32.5°	311.8	304.9	298.7	293.3	289.7	288.1	289.0	289.0	289.7	290.3	291.2
35°	296.2	290.0	285.4	280.6	277.6	278.3	278.8	279.2	280.4	281.9	282.8
37.5°	281.2	276.0	271.0	267.4	266.0	267.2	268.4	269.3	270.7	271.9	272.8
40°	270.5	266.5	261.9	258.5	259.0	259.7	260.6	261.9	263.1	263.8	264.7
42.5°	260.5	256.4	252.8	250.0	250.7	251.7	252.2	252.8	254.2	255.5	256.0
45°	245.4	242.1	238.8	237.1	237.6	238.1	238.5	239.2	240.4	241.4	241.7
47.5°	228.3	226.0	223.8	222.2	223.0	222.8	223.4	224.9	225.2	225.8	227.1
50°	217.4	215.3	212.7	212.2	212.2	212.2	212.5	214.3	214.3	215.3	216.2
52.5°	205.3	204.0	202.4	201.5	201.1	201.1	202.1	203.0	203.4	204.7	205.7
55°	187.5	186.1	184.7	184.0	183.5	184.0	185.8	186.3	187.5	188.2	188.9
57.5°	169.0	167.8	166.7	166.3	166.2	166.8	167.8	169.3	169.6	171.8	172.8
60°	156.7	155.0	154.1	154.1	153.6	155.7	155.3	157.6	158.1	159.6	161.2
62.5°	144.1	141.9	141.5	141.5	142.2	142.8	143.4	144.4	145.7	147.4	148.8
65°	123.7	122.6	124.2	124.0	123.5	124.9	124.9	126.1	127.5	129.2	131.8
67.5°	104.5	103.9	104.0	104.0	104.7	105.5	106.2	107.2	109.0	110.7	112.4
70°	91.5	92.2	91.1	92.0	92.7	92.9	93.4	94.8	96.6	97.9	99.8
72.5°	78.9	78.9	79.0	79.4	80.1	80.5	81.0	82.6	84.6	85.6	87.2
75°	60.7	60.5	61.2	61.2	62.3	62.8	63.3	64.0	65.8	67.3	68.5
77.5°	44.3	44.6	44.4	45.2	44.9	45.0	46.5	47.2	47.4	50.2	50.8
80°	33.4	33.8	34.1	34.3	34.5	34.1	35.7	36.5	36.5	38.1	39.3
82.5°	24.0	24.2	24.8	25.1	25.1	25.7	25.8	26.3	26.9	27.6	29.1
85°	12.0	12.7	12.9	12.7	12.9	12.4	13.1	13.4	13.6	13.6	13.6
87.5°	5.5	6.0	6.3	7.0	7.3	7.9	7.8	7.6	7.7	8.4	8.0
90°	8.7	10.3	12.6	15.0	17.4	19.7	19.0	19.7	20.5	21.3	22.9
92.5°	33.9	45.6	66.3	100.3	133.6	121.4	91.6	66.4	52.7	46.6	42.5
95°	71.8	102.6	169.8	287.4	416.9	468.2	379.8	284.3	192.7	150.8	122.4
97.5°	85.2	118.6	182.7	315.4	531.2	725.6	776.3	708.5	567.5	465.6	371.2
100°	94.7	125.5	180.8	297.6	505.3	747.7	903.2	930.9	866.9	774.6	662.4
102.5°	105.5	133.7	183.3	282.5	467.4	706.6	909.6	1004.7	1002.7	948.9	877.8
105°	123.2	147.6	190.3	271.6	420.8	634.8	861.4	1026.4	1105.3	1120.3	1099.8
107.5°	143.1	165.8	203.2	270.8	391.1	571.3	777.1	964.2	1092.4	1161.5	1189.6
110°	156.3	178.4	214.0	274.0	379.8	535.3	724.0	904.8	1050.1	1149.5	1204.9



TEST NUMBER: P331885-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	170.3	191.7	224.7	280.2	373.4	511.3	677.9	846.1	994.5	1106.0	1177.0
115°	191.1	212.4	242.4	290.5	371.1	485.5	622.2	768.2	905.5	1021.7	1107.7
117.5°	211.8	231.5	261.2	304.2	372.5	470.4	588.5	711.9	830.4	934.6	1022.0
120°	225.0	244.8	273.2	314.3	375.1	463.4	570.9	682.2	788.7	883.5	963.2
122.5°	237.0	258.0	285.8	323.7	379.4	459.1	556.3	658.8	755.3	843.0	917.2
125°	255.0	276.3	304.0	338.7	386.1	453.2	537.7	627.6	713.8	789.5	852.7
127.5°	271.8	293.1	319.7	351.0	393.6	450.4	521.3	600.6	677.2	745.7	803.1
130°	281.9	303.2	329.2	359.2	398.7	448.5	512.4	583.5	654.5	718.5	772.1
132.5°	291.3	312.0	337.4	366.8	402.5	447.8	504.2	567.6	633.1	692.6	743.8
135°	304.0	325.3	349.7	376.6	408.2	446.9	493.4	546.3	602.4	653.7	698.7
137.5°	315.0	334.8	358.3	383.8	412.0	445.1	484.1	526.9	572.9	617.1	656.1
140°	321.3	341.0	364.0	387.7	414.5	444.5	478.5	515.5	555.8	593.7	627.6
142.5°	327.7	346.1	368.4	391.4	416.4	443.2	473.4	504.8	539.4	572.3	601.8
145°	335.6	353.8	374.3	395.6	417.7	441.3	466.7	491.9	518.0	543.2	566.1
147.5°	344.7	360.2	379.0	398.1	417.7	438.4	460.0	481.3	502.0	522.4	538.7
150°	349.7	364.0	382.1	398.7	417.7	435.9	455.6	473.7	491.9	508.5	523.4
152.5°	354.8	368.4	384.1	400.0	415.8	432.6	450.5	466.8	482.4	497.1	509.6
155°	363.1	374.3	387.7	400.3	413.7	427.2	442.9	456.4	469.0	480.8	490.3
157.5°	370.4	379.0	389.7	401.1	411.0	422.2	434.4	445.2	455.9	465.0	472.4
160°	374.3	382.1	391.6	401.1	409.8	418.5	428.7	439.0	447.7	455.6	461.1
162.5°	377.4	384.1	392.2	400.4	407.3	414.7	423.0	431.4	438.8	446.1	451.0
165°	381.3	386.9	393.1	398.7	403.4	409.0	415.3	421.6	426.4	431.9	435.9
167.5°	385.0	388.5	393.0	397.5	399.7	403.3	407.9	413.0	416.7	419.9	422.7
170°	386.9	388.5	392.4	395.6	397.2	399.5	403.4	407.4	409.8	412.9	414.5
172.5°	388.1	389.1	392.4	395.0	395.3	396.4	399.0	402.3	404.0	406.6	407.6
175°	389.2	390.0	391.6	393.1	392.4	392.4	393.9	395.6	396.4	397.9	397.9
177.5°	390.0	390.0	390.6	391.9	390.6	390.0	390.6	391.3	391.9	392.5	392.5
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P331885-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	464.3	464.1	465.4	464.5	465.4	464.1	464.3	465.6	466.1	466.2	466.2
5°	432.2	432.9	430.5	430.5	430.5	432.9	432.2	433.6	434.7	435.8	437.1
7.5°	403.5	402.5	402.6	401.3	402.6	402.5	403.5	404.7	406.2	408.3	410.2
10°	386.1	384.7	384.2	384.5	384.2	384.7	386.1	388.9	389.8	391.7	393.8
12.5°	371.5	371.3	368.2	368.2	368.2	371.3	371.5	372.3	374.4	378.4	380.8
15°	354.6	350.1	349.6	351.0	349.6	350.1	354.6	354.6	355.5	358.5	359.9
17.5°	337.5	335.1	335.3	334.6	335.3	335.1	337.5	337.8	338.6	341.1	343.0
20°	328.4	327.0	326.8	325.2	326.8	327.0	328.4	328.4	329.4	330.5	332.4
22.5°	320.1	319.7	319.8	318.0	319.8	319.7	320.1	320.7	321.6	322.4	323.8
25°	309.8	311.0	310.0	310.0	310.0	311.0	309.8	310.0	310.3	311.4	312.5
27.5°	302.9	302.9	302.4	302.4	302.4	302.9	302.9	302.4	302.1	301.6	301.4
30°	297.6	297.4	297.8	297.8	297.8	297.4	297.6	296.7	296.2	296.0	295.0
32.5°	292.4	292.7	292.8	293.0	292.8	292.7	292.4	291.2	290.3	289.7	289.0
35°	284.2	284.5	285.2	284.7	285.2	284.5	284.2	282.8	281.9	280.4	279.2
37.5°	273.2	274.3	274.1	274.4	274.1	274.3	273.2	272.8	271.9	270.7	269.3
40°	264.9	265.6	265.4	265.4	265.4	265.6	264.9	264.7	263.8	263.1	261.9
42.5°	256.4	256.9	256.3	256.0	256.3	256.9	256.4	256.0	255.5	254.2	252.8
45°	242.6	242.1	242.8	241.9	242.8	242.1	242.6	241.7	241.4	240.4	239.2
47.5°	227.0	227.5	227.7	228.4	227.7	227.5	227.0	227.1	225.8	225.2	224.9
50°	216.7	218.1	218.1	217.8	218.1	218.1	216.7	216.2	215.3	214.3	214.3
52.5°	206.5	207.1	208.1	208.0	208.1	207.1	206.5	205.7	204.7	203.4	203.0
55°	190.8	191.3	191.8	192.0	191.8	191.3	190.8	188.9	188.2	187.5	186.3
57.5°	174.5	174.3	175.4	175.8	175.4	174.3	174.5	172.8	171.8	169.6	169.3
60°	163.0	163.0	164.9	165.6	164.9	163.0	163.0	161.2	159.6	158.1	157.6
62.5°	150.8	151.6	153.4	152.5	153.4	151.6	150.8	148.8	147.4	145.7	144.4
65°	132.9	134.8	134.6	135.5	134.6	134.8	132.9	131.8	129.2	127.5	126.1
67.5°	114.2	115.4	117.1	117.2	117.1	115.4	114.2	112.4	110.7	109.0	107.2
70°	101.6	102.8	103.7	104.4	103.7	102.8	101.6	99.8	97.9	96.6	94.8
72.5°	89.4	90.0	92.3	91.3	92.3	90.0	89.4	87.2	85.6	84.6	82.6
75°	70.1	71.8	73.2	72.5	73.2	71.8	70.1	68.5	67.3	65.8	64.0
77.5°	51.8	53.5	54.1	53.5	54.1	53.5	51.8	50.8	50.2	47.4	47.2
80°	40.9	40.7	42.1	41.9	42.1	40.7	40.9	39.3	38.1	36.5	36.5
82.5°	30.0	29.8	30.4	30.6	30.4	29.8	30.0	29.1	27.6	26.9	26.3
85°	14.5	15.2	14.3	14.1	14.3	15.2	14.5	13.6	13.6	13.6	13.4
87.5°	7.8	8.0	8.0	7.6	8.0	8.0	7.8	8.0	8.4	7.7	7.6
90°	22.1	22.9	23.7	22.9	23.7	22.9	22.1	22.9	21.3	20.5	19.7
92.5°	41.1	38.7	39.5	38.1	39.5	38.7	41.1	42.5	46.6	52.7	66.4
95°	107.3	100.3	94.7	91.6	94.7	100.3	107.3	122.4	150.8	192.7	284.3
97.5°	313.0	277.4	256.1	249.3	256.1	277.4	313.0	371.2	465.6	567.5	708.5
100°	582.7	525.0	494.2	495.0	494.2	525.0	582.7	662.4	774.6	866.9	930.9
102.5°	815.8	770.1	744.4	726.2	744.4	770.1	815.8	877.8	948.9	1002.7	1004.7
105°	1063.5	1033.5	1008.2	1004.3	1008.2	1033.5	1063.5	1099.8	1120.3	1105.3	1026.4
107.5°	1190.3	1180.2	1171.6	1164.4	1171.6	1180.2	1190.3	1189.6	1161.5	1092.4	964.2
110°	1226.9	1233.2	1231.6	1230.1	1231.6	1233.2	1226.9	1204.9	1149.5	1050.1	904.8



TEST NUMBER: P331885-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1217.5	1237.1	1243.0	1243.3	1243.0	1237.1	1217.5	1177.0	1106.0	994.5	846.1
115°	1166.9	1201.6	1217.5	1221.4	1217.5	1201.6	1166.9	1107.7	1021.7	905.5	768.2
117.5°	1083.7	1123.5	1146.2	1151.7	1146.2	1123.5	1083.7	1022.0	934.6	830.4	711.9
120°	1025.6	1069.9	1088.7	1093.5	1088.7	1069.9	1025.6	963.2	883.5	788.7	682.2
122.5°	972.5	1012.3	1033.2	1039.2	1033.2	1012.3	972.5	917.2	843.0	755.3	658.8
125°	903.2	938.0	957.7	963.2	957.7	938.0	903.2	852.7	789.5	713.8	627.6
127.5°	848.1	877.8	895.6	900.7	895.6	877.8	848.1	803.1	745.7	677.2	600.6
130°	814.1	842.4	859.0	865.4	859.0	842.4	814.1	772.1	718.5	654.5	583.5
132.5°	783.0	811.5	826.2	830.6	826.2	811.5	783.0	743.8	692.6	633.1	567.6
135°	737.4	761.1	775.3	780.8	775.3	761.1	737.4	698.7	653.7	602.4	546.3
137.5°	688.6	712.7	724.7	728.3	724.7	712.7	688.6	656.1	617.1	572.9	526.9
140°	657.7	679.7	692.5	691.7	692.5	679.7	657.7	627.6	593.7	555.8	515.5
142.5°	627.3	646.9	658.3	657.5	658.3	646.9	627.3	601.8	572.3	539.4	504.8
145°	585.8	602.4	608.7	610.3	608.7	602.4	585.8	566.1	543.2	518.0	491.9
147.5°	553.6	564.8	570.9	571.5	570.9	564.8	553.6	538.7	522.4	502.0	481.3
150°	535.3	544.0	548.8	548.8	548.8	544.0	535.3	523.4	508.5	491.9	473.7
152.5°	518.9	526.9	529.8	529.8	529.8	526.9	518.9	509.6	497.1	482.4	466.8
155°	497.4	503.7	505.3	506.0	505.3	503.7	497.4	490.3	480.8	469.0	456.4
157.5°	478.6	483.3	484.6	484.4	484.6	483.3	478.6	472.4	465.0	455.9	445.2
160°	466.7	471.3	471.3	470.6	471.3	471.3	466.7	461.1	455.6	447.7	439.0
162.5°	454.6	458.7	458.7	458.0	458.7	458.7	454.6	451.0	446.1	438.8	431.4
165°	439.0	442.1	441.3	441.3	441.3	442.1	439.0	435.9	431.9	426.4	421.6
167.5°	424.1	426.4	425.6	425.6	425.6	426.4	424.1	422.7	419.9	416.7	413.0
170°	415.3	416.9	416.1	416.1	416.1	416.9	415.3	414.5	412.9	409.8	407.4
172.5°	407.7	409.3	407.9	407.3	407.9	409.3	407.7	407.6	406.6	404.0	402.3
175°	397.9	398.7	397.9	397.2	397.9	398.7	397.9	397.9	397.9	396.4	395.6
177.5°	391.9	392.5	391.3	391.3	391.3	392.5	391.9	392.5	392.5	391.9	391.3
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P331885-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	465.6	465.6	469.2	471.5	474.3	476.2	477.5	478.8	481.1	484.0	487.5
5°	439.0	439.9	445.1	450.3	455.2	459.5	463.0	467.3	472.4	478.8	485.8
7.5°	413.2	416.9	422.0	428.4	435.3	441.4	447.7	454.6	462.0	471.3	481.2
10°	396.7	400.6	407.0	415.1	422.3	429.6	437.4	444.8	454.0	465.1	477.9
12.5°	382.1	386.0	392.5	401.2	408.2	416.3	425.2	434.9	445.2	458.5	472.9
15°	362.0	366.6	374.6	378.8	389.4	399.0	407.3	421.3	434.5	448.2	464.8
17.5°	345.6	348.1	354.6	362.4	370.3	381.2	391.9	403.7	416.9	433.5	454.4
20°	334.3	336.4	343.5	351.7	360.2	370.1	379.7	391.5	406.3	423.9	446.6
22.5°	325.9	328.1	332.8	341.5	349.4	357.7	367.3	381.3	397.1	414.3	438.8
25°	313.6	315.0	318.1	325.2	332.1	341.3	349.8	363.0	379.2	399.5	423.9
27.5°	301.9	303.4	305.9	310.9	317.6	325.0	334.3	345.4	361.8	383.8	409.8
30°	295.0	295.3	297.6	302.4	308.0	314.1	322.6	335.3	350.8	373.1	400.4
32.5°	289.0	288.1	289.7	293.3	298.7	304.9	311.8	324.4	339.3	361.2	389.3
35°	278.8	278.3	277.6	280.6	285.4	290.0	296.2	305.6	322.6	343.1	372.4
37.5°	268.4	267.2	266.0	267.4	271.0	276.0	281.2	289.6	304.3	326.8	355.0
40°	260.6	259.7	259.0	258.5	261.9	266.5	270.5	278.5	292.2	313.6	341.3
42.5°	252.2	251.7	250.7	250.0	252.8	256.4	260.5	267.6	281.2	301.3	327.6
45°	238.5	238.1	237.6	237.1	238.8	242.1	245.4	250.5	262.4	281.9	305.6
47.5°	223.4	222.8	223.0	222.2	223.8	226.0	228.3	233.9	245.1	260.9	278.3
50°	212.5	212.2	212.2	212.2	212.7	215.3	217.4	221.7	232.0	247.7	260.2
52.5°	202.1	201.1	201.1	201.5	202.4	204.0	205.3	210.0	218.9	232.0	243.3
55°	185.8	184.0	183.5	184.0	184.7	186.1	187.5	191.3	199.0	208.6	215.3
57.5°	167.8	166.8	166.2	166.3	166.7	167.8	169.0	173.0	179.2	184.2	188.4
60°	155.3	155.7	153.6	154.1	154.1	155.0	156.7	159.3	164.4	167.9	172.2
62.5°	143.4	142.8	142.2	141.5	141.5	141.9	144.1	146.1	150.6	152.4	155.6
65°	124.9	124.9	123.5	124.0	124.2	122.6	123.7	126.1	129.0	129.7	132.7
67.5°	106.2	105.5	104.7	104.0	104.0	103.9	104.5	105.6	107.8	108.1	110.4
70°	93.4	92.9	92.7	92.0	91.1	92.2	91.5	92.7	93.9	94.1	95.5
72.5°	81.0	80.5	80.1	79.4	79.0	78.9	78.9	80.3	81.1	80.8	82.3
75°	63.3	62.8	62.3	61.2	61.2	60.5	60.7	61.6	62.6	61.9	63.3
77.5°	46.5	45.0	44.9	45.2	44.4	44.6	44.3	44.2	44.6	44.6	45.9
80°	35.7	34.1	34.5	34.3	34.1	33.8	33.4	33.6	33.8	34.1	34.8
82.5°	25.8	25.7	25.1	25.1	24.8	24.2	24.0	24.4	24.6	24.5	25.0
85°	13.1	12.4	12.9	12.7	12.9	12.7	12.0	12.0	12.4	12.2	12.7
87.5°	7.8	7.9	7.3	7.0	6.3	6.0	5.5	5.4	5.0	4.7	4.8
90°	19.0	19.7	17.4	15.0	12.6	10.3	8.7	7.1	4.7	3.1	1.6
92.5°	91.6	121.4	133.6	100.3	66.3	45.6	33.9	27.4	21.2	14.5	9.8
95°	379.8	468.2	416.9	287.4	169.8	102.6	71.8	51.3	37.9	29.2	26.9
97.5°	776.3	725.6	531.2	315.4	182.7	118.6	85.2	65.0	53.4	46.6	45.7
100°	903.2	747.7	505.3	297.6	180.8	125.5	94.7	75.8	64.7	59.2	58.5
102.5°	909.6	706.6	467.4	282.5	183.3	133.7	105.5	88.5	78.0	73.1	71.7
105°	861.4	634.8	420.8	271.6	190.3	147.6	123.2	108.2	98.7	93.9	91.6
107.5°	777.1	571.3	391.1	270.8	203.2	165.8	143.1	129.0	119.7	115.1	112.7
110°	724.0	535.3	379.8	274.0	214.0	178.4	156.3	142.9	134.2	130.3	127.9



TEST NUMBER: P331885-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	677.9	511.3	373.4	280.2	224.7	191.7	170.3	156.8	148.1	144.2	141.8
115°	622.2	485.5	371.1	290.5	242.4	212.4	191.1	177.6	169.8	165.0	161.9
117.5°	588.5	470.4	372.5	304.2	261.2	231.5	211.8	196.7	189.5	185.5	181.9
120°	570.9	463.4	375.1	314.3	273.2	244.8	225.0	210.1	202.1	198.1	195.8
122.5°	556.3	459.1	379.4	323.7	285.8	258.0	237.0	222.7	214.1	210.2	207.8
125°	537.7	453.2	386.1	338.7	304.0	276.3	255.0	240.0	231.4	226.6	225.0
127.5°	521.3	450.4	393.6	351.0	319.7	293.1	271.8	255.2	246.3	240.4	238.1
130°	512.4	448.5	398.7	359.2	329.2	303.2	281.9	265.3	255.8	248.7	246.3
132.5°	504.2	447.8	402.5	366.8	337.4	312.0	291.3	274.8	263.4	255.7	252.7
135°	493.4	446.9	408.2	376.6	349.7	325.3	304.0	287.4	275.6	266.9	263.7
137.5°	484.1	445.1	412.0	383.8	358.3	334.8	315.0	298.6	286.0	277.4	274.1
140°	478.5	444.5	414.5	387.7	364.0	341.0	321.3	305.6	293.0	285.0	281.0
142.5°	473.4	443.2	416.4	391.4	368.4	346.1	327.7	311.8	300.5	292.0	288.6
145°	466.7	441.3	417.7	395.6	374.3	353.8	335.6	322.1	310.3	303.2	300.8
147.5°	460.0	438.4	417.7	398.1	379.0	360.2	344.7	331.7	321.5	314.6	313.2
150°	455.6	435.9	417.7	398.7	382.1	364.0	349.7	338.7	328.4	322.1	321.3
152.5°	450.5	432.6	415.8	400.0	384.1	368.4	354.8	345.1	336.0	329.7	329.5
155°	442.9	427.2	413.7	400.3	387.7	374.3	363.1	354.5	346.6	341.8	341.8
157.5°	434.4	422.2	411.0	401.1	389.7	379.0	370.4	363.0	356.1	352.2	351.6
160°	428.7	418.5	409.8	401.1	391.6	382.1	374.3	368.7	362.4	359.2	359.2
162.5°	423.0	414.7	407.3	400.4	392.2	384.1	377.4	372.5	367.5	365.0	365.0
165°	415.3	409.0	403.4	398.7	393.1	386.9	381.3	378.2	374.3	372.6	373.4
167.5°	407.9	403.3	399.7	397.5	393.0	388.5	385.0	382.7	379.8	379.0	379.9
170°	403.4	399.5	397.2	395.6	392.4	388.5	386.9	385.3	382.9	382.1	383.7
172.5°	399.0	396.4	395.3	395.0	392.4	389.1	388.1	387.2	385.5	385.3	386.3
175°	393.9	392.4	392.4	393.1	391.6	390.0	389.2	389.2	387.7	388.5	389.2
177.5°	390.6	390.0	390.6	391.9	390.6	390.0	390.0	390.0	389.4	390.0	390.6
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P331885-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	488.6	489.6	492.7	495.0	497.7	499.2	500.6	501.8	503.3	503.6	509.1
5°	490.8	495.4	503.7	509.8	517.4	525.5	531.2	533.8	540.7	546.2	557.5
7.5°	490.2	500.2	512.6	525.5	539.3	552.1	563.2	576.4	585.7	599.9	613.7
10°	489.6	503.0	519.0	535.4	554.7	572.6	588.7	606.5	621.4	640.9	657.5
12.5°	487.9	504.1	526.3	545.8	569.3	593.9	617.6	640.6	653.7	686.2	701.6
15°	483.7	503.0	530.8	560.4	592.6	621.8	651.9	675.9	714.7	743.2	761.3
17.5°	475.7	502.7	535.6	571.4	610.6	649.0	683.2	719.5	760.7	795.2	831.9
20°	471.9	501.6	538.3	577.8	618.5	662.1	700.8	744.6	789.5	823.4	870.5
22.5°	464.9	498.6	538.1	582.1	625.6	670.7	716.1	760.2	812.1	858.8	903.6
25°	453.6	491.2	532.2	581.4	632.4	677.5	732.0	790.5	844.6	904.6	949.3
27.5°	441.6	481.8	522.8	568.6	623.5	677.1	745.5	811.6	877.8	929.6	962.7
30°	432.4	471.5	513.8	560.0	614.3	678.0	754.5	826.7	891.2	935.6	954.2
32.5°	422.4	462.0	499.5	547.9	605.8	677.4	760.1	835.6	891.9	921.5	917.9
35°	406.8	439.9	476.5	523.0	591.2	673.3	763.5	836.4	870.9	864.5	816.6
37.5°	384.2	412.1	448.0	499.0	574.3	664.6	756.8	811.5	809.3	757.6	688.0
40°	370.1	393.8	428.4	482.0	561.1	658.9	746.5	782.0	751.9	679.6	596.4
42.5°	351.6	373.5	408.1	463.2	546.6	647.5	726.7	737.0	678.1	595.0	518.7
45°	323.1	342.3	378.1	435.0	524.8	622.5	678.5	653.3	574.0	488.2	430.1
47.5°	292.3	312.4	346.7	405.3	493.4	584.9	611.6	558.1	476.7	407.0	353.7
50°	272.9	292.2	325.9	384.9	472.2	554.0	565.1	495.9	421.1	359.9	316.2
52.5°	253.4	271.5	304.6	363.9	447.4	518.3	511.5	441.0	372.2	320.0	285.7
55°	224.2	241.4	272.9	328.4	404.5	460.6	436.0	368.7	311.7	271.2	245.1
57.5°	198.1	214.6	241.8	292.0	358.0	396.7	365.3	308.5	263.3	232.1	212.7
60°	180.5	195.0	221.0	267.5	324.9	354.3	323.3	273.2	235.0	210.1	192.7
62.5°	163.7	176.4	200.4	242.7	292.6	317.2	285.8	243.4	211.0	188.8	174.0
65°	138.4	149.9	171.1	204.0	244.9	261.4	234.3	200.0	174.8	158.3	148.5
67.5°	115.2	125.0	143.3	169.2	199.3	211.3	190.7	164.1	145.1	131.9	124.1
70°	99.8	108.3	122.6	144.9	172.2	181.4	162.1	140.2	126.3	115.7	108.5
72.5°	86.7	93.0	106.0	123.3	146.0	153.3	139.9	120.7	107.8	99.8	93.9
75°	66.1	71.3	79.8	93.6	109.4	113.6	103.5	91.5	82.8	77.2	72.7
77.5°	47.7	51.5	57.6	66.1	77.1	80.9	74.5	66.4	60.1	56.4	53.8
80°	36.0	39.1	44.2	51.3	57.9	60.0	56.2	50.1	45.6	43.5	41.4
82.5°	26.6	28.3	31.4	36.3	40.7	43.2	40.1	36.4	33.9	32.0	31.2
85°	13.4	14.3	15.8	17.7	20.5	21.4	20.2	19.3	17.9	16.7	16.7
87.5°	5.6	5.9	6.9	7.6	8.7	9.7	10.0	10.1	10.3	10.0	10.0
90°	3.1	4.7	7.1	8.7	10.3	12.6	15.0	17.4	19.7	19.0	19.7
92.5°	14.5	21.2	27.4	33.9	45.6	66.3	100.3	133.6	121.4	91.6	66.4
95°	29.2	37.9	51.3	71.8	102.6	169.8	287.4	416.9	468.2	379.8	284.3
97.5°	46.6	53.4	65.0	85.2	118.6	182.7	315.4	531.2	725.6	776.3	708.5
100°	59.2	64.7	75.8	94.7	125.5	180.8	297.6	505.3	747.7	903.2	930.9
102.5°	73.1	78.0	88.5	105.5	133.7	183.3	282.5	467.4	706.6	909.6	1004.7
105°	93.9	98.7	108.2	123.2	147.6	190.3	271.6	420.8	634.8	861.4	1026.4
107.5°	115.1	119.7	129.0	143.1	165.8	203.2	270.8	391.1	571.3	777.1	964.2
110°	130.3	134.2	142.9	156.3	178.4	214.0	274.0	379.8	535.3	724.0	904.8



TEST NUMBER: P331885-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	144.2	148.1	156.8	170.3	191.7	224.7	280.2	373.4	511.3	677.9	846.1
115°	165.0	169.8	177.6	191.1	212.4	242.4	290.5	371.1	485.5	622.2	768.2
117.5°	185.5	189.5	196.7	211.8	231.5	261.2	304.2	372.5	470.4	588.5	711.9
120°	198.1	202.1	210.1	225.0	244.8	273.2	314.3	375.1	463.4	570.9	682.2
122.5°	210.2	214.1	222.7	237.0	258.0	285.8	323.7	379.4	459.1	556.3	658.8
125°	226.6	231.4	240.0	255.0	276.3	304.0	338.7	386.1	453.2	537.7	627.6
127.5°	240.4	246.3	255.2	271.8	293.1	319.7	351.0	393.6	450.4	521.3	600.6
130°	248.7	255.8	265.3	281.9	303.2	329.2	359.2	398.7	448.5	512.4	583.5
132.5°	255.7	263.4	274.8	291.3	312.0	337.4	366.8	402.5	447.8	504.2	567.6
135°	266.9	275.6	287.4	304.0	325.3	349.7	376.6	408.2	446.9	493.4	546.3
137.5°	277.4	286.0	298.6	315.0	334.8	358.3	383.8	412.0	445.1	484.1	526.9
140°	285.0	293.0	305.6	321.3	341.0	364.0	387.7	414.5	444.5	478.5	515.5
142.5°	292.0	300.5	311.8	327.7	346.1	368.4	391.4	416.4	443.2	473.4	504.8
145°	303.2	310.3	322.1	335.6	353.8	374.3	395.6	417.7	441.3	466.7	491.9
147.5°	314.6	321.5	331.7	344.7	360.2	379.0	398.1	417.7	438.4	460.0	481.3
150°	322.1	328.4	338.7	349.7	364.0	382.1	398.7	417.7	435.9	455.6	473.7
152.5°	329.7	336.0	345.1	354.8	368.4	384.1	400.0	415.8	432.6	450.5	466.8
155°	341.8	346.6	354.5	363.1	374.3	387.7	400.3	413.7	427.2	442.9	456.4
157.5°	352.2	356.1	363.0	370.4	379.0	389.7	401.1	411.0	422.2	434.4	445.2
160°	359.2	362.4	368.7	374.3	382.1	391.6	401.1	409.8	418.5	428.7	439.0
162.5°	365.0	367.5	372.5	377.4	384.1	392.2	400.4	407.3	414.7	423.0	431.4
165°	372.6	374.3	378.2	381.3	386.9	393.1	398.7	403.4	409.0	415.3	421.6
167.5°	379.0	379.8	382.7	385.0	388.5	393.0	397.5	399.7	403.3	407.9	413.0
170°	382.1	382.9	385.3	386.9	388.5	392.4	395.6	397.2	399.5	403.4	407.4
172.5°	385.3	385.5	387.2	388.1	389.1	392.4	395.0	395.3	396.4	399.0	402.3
175°	388.5	387.7	389.2	389.2	390.0	391.6	393.1	392.4	392.4	393.9	395.6
177.5°	390.0	389.4	390.0	390.0	390.0	390.6	391.9	390.6	390.0	390.6	391.3
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P331885-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	511.0	511.2	513.2	514.7	514.0	514.9	515.3
5°	558.3	566.7	571.2	574.5	574.7	575.0	576.8
7.5°	625.3	634.4	641.1	651.2	654.1	657.5	656.6
10°	674.3	687.7	699.2	705.3	712.0	721.5	713.8
12.5°	720.0	743.8	761.3	770.8	777.0	778.9	775.2
15°	795.5	826.5	843.1	842.7	863.8	873.0	858.7
17.5°	864.5	893.2	916.3	928.0	945.6	949.5	947.8
20°	907.0	938.3	956.1	976.3	985.5	993.7	995.1
22.5°	943.4	971.6	990.8	1007.5	1015.2	1019.2	1021.5
25°	981.1	1003.2	1014.7	1020.6	1022.7	1022.2	1019.2
27.5°	978.5	980.2	967.5	955.0	943.8	931.3	927.0
30°	953.0	933.3	898.0	878.0	848.6	825.3	834.8
32.5°	886.3	846.9	807.3	763.6	727.4	717.1	706.7
35°	756.4	687.2	646.7	599.7	580.9	562.1	549.1
37.5°	611.9	558.5	510.4	479.7	460.8	448.9	442.5
40°	529.1	480.9	441.3	416.4	402.0	388.7	386.8
42.5°	463.0	418.2	388.5	368.6	354.9	349.1	345.0
45°	379.2	348.0	328.0	313.9	304.7	301.1	296.4
47.5°	321.0	298.9	283.9	274.3	267.3	264.7	264.4
50°	288.4	270.0	259.0	251.5	246.1	245.1	241.4
52.5°	264.0	248.0	239.4	232.9	228.9	226.3	225.2
55°	229.1	218.5	210.8	207.0	204.0	201.4	201.4
57.5°	200.5	191.7	186.5	183.3	182.4	180.6	179.4
60°	182.8	175.3	171.3	168.4	166.5	166.8	164.7
62.5°	165.5	160.6	156.7	154.0	151.7	151.8	151.9
65°	140.9	137.1	134.3	133.4	132.0	130.4	130.8
67.5°	119.5	115.9	113.7	112.1	111.6	110.7	112.1
70°	104.0	101.4	99.8	98.4	97.9	98.1	99.3
72.5°	89.9	88.1	86.9	86.3	85.2	85.3	86.1
75°	70.6	69.2	68.3	67.6	67.3	67.3	67.3
77.5°	51.8	51.5	51.1	50.1	50.1	50.4	50.4
80°	40.9	40.2	40.0	39.5	38.8	38.4	39.5
82.5°	30.6	29.9	29.7	29.6	28.5	28.4	29.4
85°	16.5	15.8	16.0	15.8	15.8	15.6	15.6
87.5°	9.9	9.9	10.0	10.1	10.0	10.0	10.2
90°	20.5	21.3	22.9	22.1	22.9	23.7	22.9
92.5°	52.7	46.6	42.5	41.1	38.7	39.5	38.1
95°	192.7	150.8	122.4	107.3	100.3	94.7	91.6
97.5°	567.5	465.6	371.2	313.0	277.4	256.1	249.3
100°	866.9	774.6	662.4	582.7	525.0	494.2	495.0
102.5°	1002.7	948.9	877.8	815.8	770.1	744.4	726.2
105°	1105.3	1120.3	1099.8	1063.5	1033.5	1008.2	1004.3
107.5°	1092.4	1161.5	1189.6	1190.3	1180.2	1171.6	1164.4
110°	1050.1	1149.5	1204.9	1226.9	1233.2	1231.6	1230.1



TEST NUMBER: P331885-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	994.5	1106.0	1177.0	1217.5	1237.1	1243.0	1243.3
115°	905.5	1021.7	1107.7	1166.9	1201.6	1217.5	1221.4
117.5°	830.4	934.6	1022.0	1083.7	1123.5	1146.2	1151.7
120°	788.7	883.5	963.2	1025.6	1069.9	1088.7	1093.5
122.5°	755.3	843.0	917.2	972.5	1012.3	1033.2	1039.2
125°	713.8	789.5	852.7	903.2	938.0	957.7	963.2
127.5°	677.2	745.7	803.1	848.1	877.8	895.6	900.7
130°	654.5	718.5	772.1	814.1	842.4	859.0	865.4
132.5°	633.1	692.6	743.8	783.0	811.5	826.2	830.6
135°	602.4	653.7	698.7	737.4	761.1	775.3	780.8
137.5°	572.9	617.1	656.1	688.6	712.7	724.7	728.3
140°	555.8	593.7	627.6	657.7	679.7	692.5	691.7
142.5°	539.4	572.3	601.8	627.3	646.9	658.3	657.5
145°	518.0	543.2	566.1	585.8	602.4	608.7	610.3
147.5°	502.0	522.4	538.7	553.6	564.8	570.9	571.5
150°	491.9	508.5	523.4	535.3	544.0	548.8	548.8
152.5°	482.4	497.1	509.6	518.9	526.9	529.8	529.8
155°	469.0	480.8	490.3	497.4	503.7	505.3	506.0
157.5°	455.9	465.0	472.4	478.6	483.3	484.6	484.4
160°	447.7	455.6	461.1	466.7	471.3	471.3	470.6
162.5°	438.8	446.1	451.0	454.6	458.7	458.7	458.0
165°	426.4	431.9	435.9	439.0	442.1	441.3	441.3
167.5°	416.7	419.9	422.7	424.1	426.4	425.6	425.6
170°	409.8	412.9	414.5	415.3	416.9	416.1	416.1
172.5°	404.0	406.6	407.6	407.7	409.3	407.9	407.3
175°	396.4	397.9	397.9	397.9	398.7	397.9	397.2
177.5°	391.9	392.5	392.5	391.9	392.5	391.3	391.3
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0

(END OF REPORT)