

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331921-840

Luminaire Tested: **S123DIP-S560D585U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331921-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D585U840-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4552.4 lumens
Efficiency: N/A
Efficacy: 138.8 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331921-840

CATALOG NUMBER: S123DIP-S560D585U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331921-840

CATALOG NUMBER: S123DIP-S560D585U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	87	91	88	84	81	75	73	70	63	62	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	38
3	82	73	66	60	76	68	62	57	58	54	50	50	46	43	41	39	37	33
4	75	65	57	51	70	60	53	48	52	47	43	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	30	28	25
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	30	27	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	37	30	25	32	26	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	29	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8593	8593	8593	8593
5°	10247	8630	7648	8630
10°	12826	8587	6908	8587
15°	15731	8517	6430	8517
20°	18741	8409	6123	8409
25°	19899	8278	6055	8278
30°	17056	8182	6087	8182
35°	11862	8046	6150	8046
40°	8934	7886	6131	7886
45°	7419	7648	6052	7648
50°	6646	7164	5998	7164
55°	6212	6641	5923	6641
60°	5828	6097	5862	6097
65°	5476	5555	5675	5555
70°	5136	4941	5404	4941
75°	4600	4325	4957	4325
80°	4023	3552	4271	3552
85°	3149	2581	2865	2581



TEST NUMBER: P331921-840

CATALOG NUMBER: S123DIP-S560D585U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.6	1.7
10°-20°	252.2	5.5
20°-30°	423.2	9.3
30°-40°	479.2	10.5
40°-50°	429.7	9.4
50°-60°	346.8	7.6
60°-70°	241.7	5.3
70°-80°	127.0	2.8
80°-90°	33.3	0.7
90°-100°	158.3	3.5
100°-110°	448.4	9.8
110°-120°	441.1	9.7
120°-130°	351.8	7.7
130°-140°	277.4	6.1
140°-150°	207.0	4.5
150°-160°	144.3	3.2
160°-170°	84.8	1.9
170°-180°	27.6	0.6
0°-30°	754.0	16.6
0°-40°	1233.2	27.1
0°-60°	2009.7	44.1
0°-90°	2411.6	53.0
90°-120°	1047.8	23.0
90°-150°	1884.1	41.4
90°-180°	2141.0	47.0
0°-180°	4552.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	798	798	798	798	798	
5°	948	799	708	799	948	98
15°	1412	764	577	764	1412	408
25°	1676	697	510	697	1676	735
35°	903	612	468	612	903	586
45°	487	502	398	502	487	386
55°	331	354	316	354	331	297
65°	215	218	223	218	215	214
75°	111	104	119	104	111	118
85°	26	21	23	21	26	31
90°	17	1	17	1	17	10
95°	67	20	67	20	67	120
105°	733	67	733	67	733	723
115°	891	118	891	118	891	866
125°	703	164	703	164	703	637
135°	570	192	570	192	570	442
145°	445	219	445	219	445	283
155°	369	249	369	249	369	172
165°	322	272	322	272	322	92
175°	290	284	290	284	290	28
180°	285	285	285	285	285	



TEST NUMBER: P331921-840

CATALOG NUMBER: S123DIP-S560D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	847.2	846.6	845.1	846.3	843.7	840.4	840.1	837.0	828.0	827.4	825.0
5°	948.4	945.2	944.9	944.5	939.1	931.7	917.8	916.7	898.1	888.8	877.6
7.5°	1079.4	1081.1	1075.4	1070.5	1053.9	1043.0	1028.0	1009.0	986.1	963.0	947.6
10°	1173.5	1186.2	1170.3	1159.5	1149.5	1130.5	1108.5	1081.1	1053.6	1021.5	997.1
12.5°	1274.3	1280.6	1277.5	1267.2	1251.6	1222.7	1183.7	1153.5	1128.1	1074.7	1053.1
15°	1411.7	1435.3	1420.3	1385.4	1386.2	1358.8	1307.7	1251.6	1221.8	1175.0	1111.2
17.5°	1558.1	1561.0	1554.6	1525.6	1506.2	1468.5	1421.4	1367.7	1307.3	1250.7	1183.0
20°	1636.1	1633.8	1620.2	1605.1	1571.9	1542.5	1491.0	1431.1	1353.7	1298.0	1224.2
22.5°	1679.4	1675.5	1669.1	1656.5	1628.8	1597.2	1551.1	1485.5	1411.9	1335.1	1249.8
25°	1675.5	1680.5	1681.3	1677.8	1668.2	1649.2	1612.9	1560.6	1487.1	1388.6	1299.6
27.5°	1523.9	1531.0	1551.7	1570.0	1590.5	1611.3	1608.6	1582.7	1528.3	1443.1	1334.3
30°	1372.3	1356.8	1395.1	1443.4	1476.3	1534.3	1566.8	1568.7	1538.2	1465.1	1359.1
32.5°	1161.8	1178.9	1195.8	1255.3	1327.2	1392.3	1456.9	1509.0	1515.0	1466.3	1373.6
35°	902.7	924.0	954.9	985.9	1063.3	1129.7	1243.4	1342.5	1421.4	1431.8	1374.9
37.5°	727.4	738.0	757.5	788.5	839.1	918.1	1006.0	1131.1	1245.5	1330.5	1334.2
40°	635.8	638.9	661.0	684.6	725.6	790.5	869.9	980.5	1117.4	1236.2	1285.7
42.5°	567.1	574.0	583.3	606.0	638.6	687.5	761.2	852.7	978.2	1114.8	1211.6
45°	487.4	495.0	500.9	515.9	539.2	572.0	623.5	707.0	802.5	943.7	1074.1
47.5°	434.5	435.2	439.5	450.9	466.7	491.4	527.8	581.4	669.1	783.6	917.5
50°	396.9	403.0	404.6	413.4	425.9	444.0	474.2	519.8	591.8	692.4	815.4
52.5°	370.2	372.0	376.4	382.8	393.6	407.8	433.9	469.7	526.1	611.9	725.0
55°	331.0	331.0	335.4	340.3	346.6	359.3	376.7	403.0	446.0	512.5	606.1
57.5°	294.9	296.8	299.8	301.3	306.6	315.1	329.6	349.6	381.6	432.8	507.3
60°	270.7	274.2	273.9	276.9	281.6	288.1	300.5	316.8	345.4	386.4	449.1
62.5°	249.7	249.4	249.4	253.1	257.7	264.0	272.1	286.1	310.4	346.8	400.1
65°	215.0	214.3	217.0	219.3	220.9	225.5	231.7	244.1	260.3	287.4	328.7
67.5°	184.3	182.0	183.5	184.3	186.9	190.6	196.3	204.0	216.9	238.6	269.8
70°	163.2	161.3	160.9	161.7	164.0	166.7	171.0	178.3	190.3	207.7	230.6
72.5°	141.6	140.3	140.2	141.9	143.0	144.7	147.7	154.5	164.0	177.0	198.3
75°	110.6	110.6	110.6	111.0	112.2	113.7	116.0	119.5	126.8	136.1	150.5
77.5°	82.9	82.8	82.4	82.3	84.0	84.7	85.2	88.5	92.6	98.9	109.3
80°	64.9	63.0	63.8	64.9	65.7	66.1	67.3	68.1	71.6	75.0	82.4
82.5°	48.3	46.7	46.8	48.6	48.8	49.1	50.3	51.4	52.7	55.8	59.8
85°	25.5	25.5	26.0	26.0	26.3	26.0	27.1	27.5	27.5	29.4	31.7
87.5°	12.6	12.1	12.3	12.5	12.3	12.4	12.6	12.8	12.9	13.4	13.3
90°	16.7	17.3	16.7	16.2	16.7	15.6	14.9	14.4	13.8	14.4	12.6
92.5°	27.8	28.8	28.2	30.0	31.0	34.0	38.5	48.5	66.9	88.6	97.5
95°	66.9	69.1	73.1	78.4	89.3	110.0	140.6	207.3	277.0	341.5	304.2
97.5°	181.9	186.8	202.4	228.3	270.8	339.7	414.0	516.9	566.3	529.4	387.5
100°	361.1	360.6	383.0	425.1	483.2	565.0	632.5	679.1	658.9	545.4	368.6
102.5°	529.8	543.0	561.8	595.1	640.4	692.3	731.5	733.1	663.6	515.5	341.0
105°	732.7	735.6	754.0	775.9	802.3	817.4	806.4	748.8	628.4	463.1	307.0
107.5°	849.5	854.7	861.0	868.4	867.9	847.4	797.0	703.4	566.9	416.8	285.4
110°	897.4	898.6	899.7	895.1	879.0	838.7	766.1	660.0	528.2	390.5	277.0



TEST NUMBER: P331921-840

CATALOG NUMBER: S123DIP-S560D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	907.1	906.9	902.5	888.2	858.7	806.9	725.5	617.2	494.5	373.0	272.5
115°	891.1	888.2	876.7	851.3	808.1	745.4	660.7	560.5	453.9	354.3	270.7
117.5°	840.1	836.3	819.6	790.6	745.6	681.9	605.8	519.3	429.4	343.2	271.8
120°	797.8	794.3	780.5	748.2	702.8	644.5	575.4	497.7	416.5	338.1	273.6
122.5°	758.1	753.8	738.5	709.5	669.0	615.0	551.0	480.6	405.9	334.9	276.8
125°	702.8	698.7	684.3	658.9	622.1	576.0	520.7	457.9	392.2	330.6	281.7
127.5°	657.1	653.4	640.4	618.7	585.9	544.0	494.1	438.1	380.3	328.5	287.2
130°	631.3	626.7	614.6	593.9	563.3	524.1	477.5	425.7	373.9	327.2	290.8
132.5°	605.9	602.7	592.0	571.3	542.6	505.2	461.8	414.1	367.8	326.7	293.7
135°	569.7	565.6	555.2	538.0	509.8	477.0	439.5	398.6	360.0	326.0	297.8
137.5°	531.3	528.7	519.9	502.4	478.7	450.2	418.0	384.5	353.3	324.8	300.5
140°	504.5	505.1	495.9	479.8	457.9	433.1	405.5	376.2	349.0	324.3	302.4
142.5°	479.7	480.3	472.0	457.7	439.0	417.5	393.5	368.3	345.4	323.4	303.8
145°	445.2	444.1	439.5	427.4	413.0	396.3	377.9	358.8	340.4	321.9	304.7
147.5°	416.9	416.5	412.0	403.8	392.9	381.1	366.2	351.1	335.6	319.8	304.7
150°	400.3	400.3	396.9	390.5	381.9	370.9	358.8	345.6	332.3	317.9	304.7
152.5°	386.5	386.5	384.5	378.5	371.7	362.6	351.9	340.5	328.7	315.7	303.4
155°	369.2	368.6	367.5	362.8	357.7	350.8	342.1	333.0	323.2	311.6	301.8
157.5°	353.5	353.6	352.6	349.2	344.7	339.3	332.5	324.9	316.9	308.0	299.8
160°	343.3	343.9	343.9	340.4	336.4	332.3	326.6	320.2	312.8	305.3	298.9
162.5°	334.1	334.7	334.7	331.6	329.0	325.5	320.1	314.8	308.6	302.6	297.1
165°	321.9	321.9	322.6	320.2	317.9	315.1	311.0	307.6	303.0	298.4	294.4
167.5°	310.4	310.4	311.0	309.4	308.4	306.3	304.0	301.3	297.6	294.2	291.5
170°	303.6	303.6	304.2	303.0	302.4	301.2	298.9	297.2	294.4	291.4	289.7
172.5°	297.1	297.6	298.6	297.4	297.3	296.6	294.8	293.6	291.1	289.1	288.3
175°	289.7	290.3	290.8	290.3	290.3	290.3	289.1	288.6	287.4	286.3	286.3
177.5°	285.5	285.5	286.4	285.9	286.4	286.4	285.9	285.5	285.0	284.6	285.0
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P331921-840

CATALOG NUMBER: S123DIP-S560D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	823.0	820.6	818.1	813.7	810.0	804.8	803.2	801.4	795.9	790.8	787.2
5°	873.3	864.0	850.5	838.1	828.1	814.6	806.8	798.7	787.1	776.7	768.1
7.5°	925.9	907.7	886.7	863.9	842.7	822.2	805.8	791.1	774.9	759.4	747.5
10°	967.8	941.4	912.0	880.3	853.2	826.9	804.9	785.6	764.7	746.5	731.3
12.5°	1015.3	976.3	935.8	897.3	865.3	828.8	802.1	777.5	753.9	732.0	715.0
15°	1071.8	1022.3	974.3	921.3	872.5	826.9	795.2	764.3	736.8	714.4	692.7
17.5°	1123.1	1067.0	1003.8	939.4	880.6	826.5	782.0	747.1	712.8	685.3	663.7
20°	1152.2	1088.3	1016.8	949.9	884.9	824.6	775.9	734.1	697.0	667.9	643.6
22.5°	1177.3	1102.6	1028.5	957.0	884.6	819.6	764.5	721.4	681.2	652.8	626.9
25°	1203.3	1113.9	1039.7	955.7	874.8	807.6	745.7	697.0	656.7	623.5	596.8
27.5°	1225.6	1113.2	1025.0	934.7	859.6	792.1	726.1	673.8	631.1	594.9	567.8
30°	1240.4	1114.7	1009.9	920.5	844.8	775.1	710.8	658.3	613.4	576.6	551.2
32.5°	1249.7	1113.8	995.9	900.7	821.2	759.6	694.5	640.1	593.9	557.8	533.2
35°	1255.1	1106.9	972.0	859.8	783.3	723.3	668.7	612.3	563.9	530.3	502.4
37.5°	1244.3	1092.7	944.1	820.3	736.5	677.5	631.6	583.5	537.2	500.2	476.2
40°	1227.2	1083.4	922.4	792.5	704.3	647.4	608.4	561.2	515.5	480.4	458.0
42.5°	1194.8	1064.5	898.7	761.5	670.9	614.0	578.0	538.7	495.4	462.4	440.0
45°	1115.5	1023.4	862.9	715.2	621.6	562.8	531.1	502.4	463.3	431.2	411.9
47.5°	1005.4	961.6	811.2	666.2	570.1	513.5	480.5	457.5	428.9	403.0	384.5
50°	929.1	910.9	776.3	632.8	535.6	480.4	448.7	427.8	407.3	381.3	364.4
52.5°	840.8	852.0	735.4	598.1	500.7	446.4	416.5	399.9	381.3	360.0	345.2
55°	716.7	757.3	664.9	540.0	448.7	396.9	368.6	353.9	343.1	327.2	314.5
57.5°	600.5	652.1	588.5	480.0	397.5	352.8	325.8	309.7	302.8	294.5	284.5
60°	531.4	582.5	534.1	439.8	363.1	320.6	296.7	283.2	276.2	270.3	261.9
62.5°	469.9	521.5	480.9	398.9	329.4	290.0	269.1	255.9	250.4	247.4	240.1
65°	385.3	429.7	402.6	335.4	281.1	246.4	227.4	218.1	213.1	212.0	207.3
67.5°	313.6	347.4	327.7	278.1	235.5	205.4	189.3	181.5	177.6	177.2	173.7
70°	266.5	298.2	283.2	238.2	201.5	177.9	164.0	157.0	154.7	154.3	152.4
72.5°	229.9	252.1	240.1	202.7	174.3	152.9	142.6	135.3	132.7	133.3	132.0
75°	170.2	186.8	179.9	153.9	131.1	117.1	108.7	104.0	101.7	102.9	101.3
77.5°	122.5	133.0	126.7	108.8	94.7	84.6	78.4	75.5	73.4	73.3	72.6
80°	92.4	98.7	95.1	84.3	72.7	64.2	59.2	57.3	56.0	55.7	55.3
82.5°	65.8	71.1	67.0	59.6	51.7	46.6	43.7	41.2	40.3	40.5	40.2
85°	33.2	35.2	33.6	29.0	26.0	23.6	22.0	20.9	20.1	20.5	19.7
87.5°	13.6	13.6	12.3	10.9	10.0	8.8	8.5	7.7	7.3	7.5	7.6
90°	10.9	9.2	7.5	6.4	5.2	3.4	2.3	1.1	2.3	3.4	5.2
92.5°	73.1	48.4	33.3	24.7	19.9	15.5	10.6	7.2	10.6	15.5	19.9
95°	209.6	123.8	74.8	52.4	37.5	27.7	21.3	19.6	21.3	27.7	37.5
97.5°	230.0	133.3	86.5	62.2	47.5	39.0	34.0	33.4	34.0	39.0	47.5
100°	217.1	131.9	91.6	69.1	55.3	47.3	43.2	42.6	43.2	47.3	55.3
102.5°	206.1	133.7	97.6	77.0	64.5	57.0	53.3	52.3	53.3	57.0	64.5
105°	198.1	138.9	107.8	89.9	78.9	72.0	68.6	66.9	68.6	72.0	78.9
107.5°	197.5	148.2	121.0	104.4	94.1	87.4	84.0	82.2	84.0	87.4	94.1
110°	199.9	156.1	130.2	114.0	104.2	98.0	95.0	93.3	95.0	98.0	104.2



TEST NUMBER: P331921-840

CATALOG NUMBER: S123DIP-S560D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	204.5	163.9	139.9	124.2	114.4	108.1	105.2	103.4	105.2	108.1	114.4
115°	212.0	176.8	154.9	139.4	129.6	123.8	120.4	118.1	120.4	123.8	129.6
117.5°	221.9	190.6	168.8	154.5	143.5	138.3	135.3	132.7	135.3	138.3	143.5
120°	229.2	199.2	178.5	164.2	153.2	147.4	144.6	142.9	144.6	147.4	153.2
122.5°	236.2	208.5	188.2	172.9	162.4	156.2	153.3	151.6	153.3	156.2	162.4
125°	247.1	221.8	201.6	186.0	175.1	168.7	165.3	164.2	165.3	168.7	175.1
127.5°	256.1	233.3	213.8	198.2	186.1	179.8	175.4	173.7	175.4	179.8	186.1
130°	262.1	240.1	221.2	205.6	193.5	186.6	181.5	179.8	181.5	186.6	193.5
132.5°	267.6	246.2	227.6	212.6	200.5	192.2	186.5	184.3	186.5	192.2	200.5
135°	274.8	255.2	237.3	221.8	209.6	201.1	194.7	192.4	194.7	201.1	209.6
137.5°	280.0	261.4	244.2	229.8	217.8	208.6	202.4	200.0	202.4	208.6	217.8
140°	282.9	265.5	248.8	234.4	222.9	213.7	207.9	205.1	207.9	213.7	222.9
142.5°	285.6	268.7	252.6	239.0	227.5	219.2	213.0	210.6	213.0	219.2	227.5
145°	288.6	273.1	258.0	244.8	235.0	226.4	221.2	219.4	221.2	226.4	235.0
147.5°	290.4	276.5	262.8	251.5	242.1	234.6	229.4	228.4	229.4	234.6	242.1
150°	290.8	278.8	265.5	255.2	247.1	239.6	235.0	234.4	235.0	239.6	247.1
152.5°	291.9	280.1	268.7	258.8	251.8	245.2	240.5	240.4	240.5	245.2	251.8
155°	292.1	282.9	273.1	265.0	258.6	252.9	249.4	249.4	249.4	252.9	258.6
157.5°	292.7	284.3	276.5	270.2	264.9	259.7	257.0	256.5	257.0	259.7	264.9
160°	292.7	285.7	278.8	273.1	269.0	264.4	262.1	262.1	262.1	264.4	269.0
162.5°	292.2	286.2	280.1	275.3	271.8	268.1	266.2	266.2	266.2	268.1	271.8
165°	290.8	286.8	282.3	278.2	275.9	273.1	271.9	272.5	271.9	273.1	275.9
167.5°	289.9	286.7	283.4	280.8	279.2	277.0	276.5	277.2	276.5	277.0	279.2
170°	288.6	286.3	283.4	282.3	281.0	279.3	278.8	279.9	278.8	279.3	281.0
172.5°	288.1	286.3	283.9	283.2	282.5	281.2	281.0	281.8	281.0	281.2	282.5
175°	286.8	285.7	284.6	284.0	284.0	282.9	283.4	284.0	283.4	282.9	284.0
177.5°	285.9	285.0	284.6	284.6	284.6	284.1	284.6	285.0	284.6	284.1	284.6
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P331921-840

CATALOG NUMBER: S123DIP-S560D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	785.0	782.8	779.7	775.1	771.3	765.5	765.5	766.4	766.4	766.1	765.5
5°	761.1	755.4	748.4	740.3	731.7	723.3	721.8	718.6	716.3	714.8	712.9
7.5°	736.0	725.8	715.6	704.3	693.9	685.3	679.3	674.4	671.2	667.8	665.3
10°	719.0	706.2	694.3	682.3	669.1	658.6	652.1	647.4	644.0	640.9	639.3
12.5°	698.9	684.3	671.1	659.6	645.3	634.5	628.2	626.1	622.0	615.5	612.1
15°	669.5	656.0	640.2	622.7	615.7	602.6	595.2	591.8	589.5	584.4	582.9
17.5°	644.4	626.6	608.8	595.8	582.9	572.3	568.2	563.8	560.8	556.6	555.4
20°	624.3	608.4	592.2	578.2	564.7	553.1	549.6	546.5	543.4	541.5	540.0
22.5°	603.8	587.9	574.5	561.5	547.0	539.5	535.6	532.3	530.1	528.8	527.3
25°	575.1	561.2	546.1	534.5	522.9	517.9	515.5	513.6	512.1	510.2	509.8
27.5°	549.5	534.3	522.1	511.2	502.9	498.7	496.4	495.5	495.8	496.6	497.0
30°	530.3	516.3	506.2	497.0	489.3	485.4	485.0	485.0	486.6	487.0	487.8
32.5°	512.6	501.2	491.1	482.1	476.3	473.6	475.1	475.1	476.4	477.4	478.8
35°	487.0	476.9	469.2	461.4	456.4	457.6	458.3	459.1	461.0	463.3	464.9
37.5°	462.4	453.7	445.7	439.6	437.3	439.4	441.2	442.8	445.1	446.9	448.4
40°	444.7	438.2	430.5	425.1	425.9	427.0	428.6	430.5	432.4	433.5	435.2
42.5°	428.4	421.5	415.7	411.1	412.2	413.7	414.7	415.7	417.9	420.0	420.9
45°	403.4	398.0	392.5	389.9	390.6	391.4	392.2	393.3	395.3	396.9	397.2
47.5°	375.4	371.5	367.9	365.3	366.5	366.2	367.2	369.7	370.3	371.2	373.3
50°	357.4	353.9	349.6	348.9	348.9	348.9	349.2	352.3	352.3	353.9	355.5
52.5°	337.6	335.4	332.6	331.2	330.6	330.6	332.2	333.8	334.4	336.6	338.1
55°	308.2	305.9	303.7	302.5	301.6	302.5	305.6	306.3	308.2	309.4	310.5
57.5°	277.7	275.9	274.1	273.5	273.3	274.3	276.0	278.3	278.8	282.4	284.1
60°	257.6	254.9	253.4	253.4	252.6	256.0	255.3	259.1	259.9	262.3	265.0
62.5°	236.8	233.2	232.6	232.6	233.7	234.7	235.8	237.5	239.5	242.5	244.5
65°	203.5	201.5	204.2	203.8	203.1	205.4	205.4	207.3	209.6	212.4	216.6
67.5°	171.8	170.8	171.1	171.1	172.2	173.5	174.6	176.3	179.0	182.0	184.7
70°	150.5	151.6	149.7	151.3	152.4	152.8	153.5	155.8	159.0	160.9	164.0
72.5°	129.8	129.7	129.9	130.5	131.7	132.4	133.1	135.7	139.2	140.8	143.3
75°	99.8	99.4	100.6	100.6	102.5	103.3	104.0	105.2	108.3	110.6	112.6
77.5°	72.9	73.3	73.1	74.4	73.9	74.0	76.4	77.6	77.9	82.5	83.5
80°	54.9	55.7	56.0	56.5	56.9	56.0	58.8	60.0	60.0	62.6	64.6
82.5°	39.5	39.9	40.9	41.3	41.4	42.1	42.4	43.2	44.1	45.3	47.9
85°	19.7	20.9	21.3	20.9	21.3	20.5	21.6	22.0	22.4	22.4	22.4
87.5°	7.5	8.0	8.1	8.7	8.7	9.4	9.3	8.8	8.9	9.9	8.9
90°	6.4	7.5	9.2	10.9	12.6	14.4	13.8	14.4	14.9	15.6	16.7
92.5°	24.7	33.3	48.4	73.1	97.5	88.6	66.9	48.5	38.5	34.0	31.0
95°	52.4	74.8	123.8	209.6	304.2	341.5	277.0	207.3	140.6	110.0	89.3
97.5°	62.2	86.5	133.3	230.0	387.5	529.4	566.3	516.9	414.0	339.7	270.8
100°	69.1	91.6	131.9	217.1	368.6	545.4	658.9	679.1	632.5	565.0	483.2
102.5°	77.0	97.6	133.7	206.1	341.0	515.5	663.6	733.1	731.5	692.3	640.4
105°	89.9	107.8	138.9	198.1	307.0	463.1	628.4	748.8	806.4	817.4	802.3
107.5°	104.4	121.0	148.2	197.5	285.4	416.8	566.9	703.4	797.0	847.4	867.9
110°	114.0	130.2	156.1	199.9	277.0	390.5	528.2	660.0	766.1	838.7	879.0



TEST NUMBER: P331921-840

CATALOG NUMBER: S123DIP-S560D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	124.2	139.9	163.9	204.5	272.5	373.0	494.5	617.2	725.5	806.9	858.7
115°	139.4	154.9	176.8	212.0	270.7	354.3	453.9	560.5	660.7	745.4	808.1
117.5°	154.5	168.8	190.6	221.9	271.8	343.2	429.4	519.3	605.8	681.9	745.6
120°	164.2	178.5	199.2	229.2	273.6	338.1	416.5	497.7	575.4	644.5	702.8
122.5°	172.9	188.2	208.5	236.2	276.8	334.9	405.9	480.6	551.0	615.0	669.0
125°	186.0	201.6	221.8	247.1	281.7	330.6	392.2	457.9	520.7	576.0	622.1
127.5°	198.2	213.8	233.3	256.1	287.2	328.5	380.3	438.1	494.1	544.0	585.9
130°	205.6	221.2	240.1	262.1	290.8	327.2	373.9	425.7	477.5	524.1	563.3
132.5°	212.6	227.6	246.2	267.6	293.7	326.7	367.8	414.1	461.8	505.2	542.6
135°	221.8	237.3	255.2	274.8	297.8	326.0	360.0	398.6	439.5	477.0	509.8
137.5°	229.8	244.2	261.4	280.0	300.5	324.8	353.3	384.5	418.0	450.2	478.7
140°	234.4	248.8	265.5	282.9	302.4	324.3	349.0	376.2	405.5	433.1	457.9
142.5°	239.0	252.6	268.7	285.6	303.8	323.4	345.4	368.3	393.5	417.5	439.0
145°	244.8	258.0	273.1	288.6	304.7	321.9	340.4	358.8	377.9	396.3	413.0
147.5°	251.5	262.8	276.5	290.4	304.7	319.8	335.6	351.1	366.2	381.1	392.9
150°	255.2	265.5	278.8	290.8	304.7	317.9	332.3	345.6	358.8	370.9	381.9
152.5°	258.8	268.7	280.1	291.9	303.4	315.7	328.7	340.5	351.9	362.6	371.7
155°	265.0	273.1	282.9	292.1	301.8	311.6	323.2	333.0	342.1	350.8	357.7
157.5°	270.2	276.5	284.3	292.7	299.8	308.0	316.9	324.9	332.5	339.3	344.7
160°	273.1	278.8	285.7	292.7	298.9	305.3	312.8	320.2	326.6	332.3	336.4
162.5°	275.3	280.1	286.2	292.2	297.1	302.6	308.6	314.8	320.1	325.5	329.0
165°	278.2	282.3	286.8	290.8	294.4	298.4	303.0	307.6	311.0	315.1	317.9
167.5°	280.8	283.4	286.7	289.9	291.5	294.2	297.6	301.3	304.0	306.3	308.4
170°	282.3	283.4	286.3	288.6	289.7	291.4	294.4	297.2	298.9	301.2	302.4
172.5°	283.2	283.9	286.3	288.1	288.3	289.1	291.1	293.6	294.8	296.6	297.3
175°	284.0	284.6	285.7	286.8	286.3	286.3	287.4	288.6	289.1	290.3	290.3
177.5°	284.6	284.6	285.0	285.9	285.0	284.6	285.0	285.5	285.9	286.4	286.4
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P331921-840

CATALOG NUMBER: S123DIP-S560D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	763.4	763.1	765.2	763.7	765.2	763.1	763.4	765.5	766.1	766.4	766.4
5°	710.5	711.7	707.8	707.8	707.8	711.7	710.5	712.9	714.8	716.3	718.6
7.5°	663.5	661.8	662.0	659.8	662.0	661.8	663.5	665.3	667.8	671.2	674.4
10°	634.7	632.4	631.6	632.0	631.6	632.4	634.7	639.3	640.9	644.0	647.4
12.5°	610.9	610.4	605.3	605.4	605.3	610.4	610.9	612.1	615.5	622.0	626.1
15°	582.9	575.5	574.7	577.0	574.7	575.5	582.9	582.9	584.4	589.5	591.8
17.5°	554.8	550.9	551.2	550.0	551.2	550.9	554.8	555.4	556.6	560.8	563.8
20°	540.0	537.7	537.2	534.5	537.2	537.7	540.0	540.0	541.5	543.4	546.5
22.5°	526.3	525.5	525.7	522.8	525.7	525.5	526.3	527.3	528.8	530.1	532.3
25°	509.4	511.3	509.8	509.8	509.8	511.3	509.4	509.8	510.2	512.1	513.6
27.5°	498.0	497.9	497.1	497.1	497.1	497.9	498.0	497.0	496.6	495.8	495.5
30°	489.3	488.9	489.7	489.7	489.7	488.9	489.3	487.8	487.0	486.6	485.0
32.5°	480.6	481.1	481.3	481.6	481.3	481.1	480.6	478.8	477.4	476.4	475.1
35°	467.3	467.6	468.8	468.0	468.8	467.6	467.3	464.9	463.3	461.0	459.1
37.5°	449.1	450.9	450.5	451.1	450.5	450.9	449.1	448.4	446.9	445.1	442.8
40°	435.6	436.7	436.3	436.3	436.3	436.7	435.6	435.2	433.5	432.4	430.5
42.5°	421.6	422.4	421.4	420.8	421.4	422.4	421.6	420.9	420.0	417.9	415.7
45°	398.8	398.0	399.2	397.6	399.2	398.0	398.8	397.2	396.9	395.3	393.3
47.5°	373.2	374.1	374.4	375.5	374.4	374.1	373.2	373.3	371.2	370.3	369.7
50°	356.2	358.5	358.5	358.2	358.5	358.5	356.2	355.5	353.9	352.3	352.3
52.5°	339.5	340.6	342.1	342.0	342.1	340.6	339.5	338.1	336.6	334.4	333.8
55°	313.7	314.5	315.2	315.6	315.2	314.5	313.7	310.5	309.4	308.2	306.3
57.5°	286.9	286.6	288.4	289.0	288.4	286.6	286.9	284.1	282.4	278.8	278.3
60°	268.0	268.0	271.1	272.3	271.1	268.0	268.0	265.0	262.3	259.9	259.1
62.5°	247.9	249.1	252.3	250.6	252.3	249.1	247.9	244.5	242.5	239.5	237.5
65°	218.5	221.7	221.3	222.8	221.3	221.7	218.5	216.6	212.4	209.6	207.3
67.5°	187.8	189.8	192.6	192.8	192.6	189.8	187.8	184.7	182.0	179.0	176.3
70°	167.1	169.1	170.6	171.7	170.6	169.1	167.1	164.0	160.9	159.0	155.8
72.5°	146.9	147.9	151.7	150.1	151.7	147.9	146.9	143.3	140.8	139.2	135.7
75°	115.2	118.0	120.3	119.2	120.3	118.0	115.2	112.6	110.6	108.3	105.2
77.5°	85.2	88.0	89.1	88.1	89.1	88.0	85.2	83.5	82.5	77.9	77.6
80°	67.3	67.0	69.3	68.9	69.3	67.0	67.3	64.6	62.6	60.0	60.0
82.5°	49.4	49.0	50.1	50.3	50.1	49.0	49.4	47.9	45.3	44.1	43.2
85°	23.9	25.1	23.6	23.2	23.6	25.1	23.9	22.4	22.4	22.4	22.0
87.5°	8.8	8.9	8.7	8.3	8.7	8.9	8.8	8.9	9.9	8.9	8.8
90°	16.2	16.7	17.3	16.7	17.3	16.7	16.2	16.7	15.6	14.9	14.4
92.5°	30.0	28.2	28.8	27.8	28.8	28.2	30.0	31.0	34.0	38.5	48.5
95°	78.4	73.1	69.1	66.9	69.1	73.1	78.4	89.3	110.0	140.6	207.3
97.5°	228.3	202.4	186.8	181.9	186.8	202.4	228.3	270.8	339.7	414.0	516.9
100°	425.1	383.0	360.6	361.1	360.6	383.0	425.1	483.2	565.0	632.5	679.1
102.5°	595.1	561.8	543.0	529.8	543.0	561.8	595.1	640.4	692.3	731.5	733.1
105°	775.9	754.0	735.6	732.7	735.6	754.0	775.9	802.3	817.4	806.4	748.8
107.5°	868.4	861.0	854.7	849.5	854.7	861.0	868.4	867.9	847.4	797.0	703.4
110°	895.1	899.7	898.6	897.4	898.6	899.7	895.1	879.0	838.7	766.1	660.0



TEST NUMBER: P331921-840

CATALOG NUMBER: S123DIP-S560D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	888.2	902.5	906.9	907.1	906.9	902.5	888.2	858.7	806.9	725.5	617.2
115°	851.3	876.7	888.2	891.1	888.2	876.7	851.3	808.1	745.4	660.7	560.5
117.5°	790.6	819.6	836.3	840.1	836.3	819.6	790.6	745.6	681.9	605.8	519.3
120°	748.2	780.5	794.3	797.8	794.3	780.5	748.2	702.8	644.5	575.4	497.7
122.5°	709.5	738.5	753.8	758.1	753.8	738.5	709.5	669.0	615.0	551.0	480.6
125°	658.9	684.3	698.7	702.8	698.7	684.3	658.9	622.1	576.0	520.7	457.9
127.5°	618.7	640.4	653.4	657.1	653.4	640.4	618.7	585.9	544.0	494.1	438.1
130°	593.9	614.6	626.7	631.3	626.7	614.6	593.9	563.3	524.1	477.5	425.7
132.5°	571.3	592.0	602.7	605.9	602.7	592.0	571.3	542.6	505.2	461.8	414.1
135°	538.0	555.2	565.6	569.7	565.6	555.2	538.0	509.8	477.0	439.5	398.6
137.5°	502.4	519.9	528.7	531.3	528.7	519.9	502.4	478.7	450.2	418.0	384.5
140°	479.8	495.9	505.1	504.5	505.1	495.9	479.8	457.9	433.1	405.5	376.2
142.5°	457.7	472.0	480.3	479.7	480.3	472.0	457.7	439.0	417.5	393.5	368.3
145°	427.4	439.5	444.1	445.2	444.1	439.5	427.4	413.0	396.3	377.9	358.8
147.5°	403.8	412.0	416.5	416.9	416.5	412.0	403.8	392.9	381.1	366.2	351.1
150°	390.5	396.9	400.3	400.3	400.3	396.9	390.5	381.9	370.9	358.8	345.6
152.5°	378.5	384.5	386.5	386.5	386.5	384.5	378.5	371.7	362.6	351.9	340.5
155°	362.8	367.5	368.6	369.2	368.6	367.5	362.8	357.7	350.8	342.1	333.0
157.5°	349.2	352.6	353.6	353.5	353.6	352.6	349.2	344.7	339.3	332.5	324.9
160°	340.4	343.9	343.9	343.3	343.9	343.9	340.4	336.4	332.3	326.6	320.2
162.5°	331.6	334.7	334.7	334.1	334.7	334.7	331.6	329.0	325.5	320.1	314.8
165°	320.2	322.6	321.9	321.9	321.9	322.6	320.2	317.9	315.1	311.0	307.6
167.5°	309.4	311.0	310.4	310.4	310.4	311.0	309.4	308.4	306.3	304.0	301.3
170°	303.0	304.2	303.6	303.6	303.6	304.2	303.0	302.4	301.2	298.9	297.2
172.5°	297.4	298.6	297.6	297.1	297.6	298.6	297.4	297.3	296.6	294.8	293.6
175°	290.3	290.8	290.3	289.7	290.3	290.8	290.3	290.3	290.3	289.1	288.6
177.5°	285.9	286.4	285.5	285.5	285.5	286.4	285.9	286.4	286.4	285.9	285.5
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P331921-840

CATALOG NUMBER: S123DIP-S560D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	765.5	765.5	771.3	775.1	779.7	782.8	785.0	787.2	790.8	795.9	801.4
5°	721.8	723.3	731.7	740.3	748.4	755.4	761.1	768.1	776.7	787.1	798.7
7.5°	679.3	685.3	693.9	704.3	715.6	725.8	736.0	747.5	759.4	774.9	791.1
10°	652.1	658.6	669.1	682.3	694.3	706.2	719.0	731.3	746.5	764.7	785.6
12.5°	628.2	634.5	645.3	659.6	671.1	684.3	698.9	715.0	732.0	753.9	777.5
15°	595.2	602.6	615.7	622.7	640.2	656.0	669.5	692.7	714.4	736.8	764.3
17.5°	568.2	572.3	582.9	595.8	608.8	626.6	644.4	663.7	685.3	712.8	747.1
20°	549.6	553.1	564.7	578.2	592.2	608.4	624.3	643.6	667.9	697.0	734.1
22.5°	535.6	539.5	547.0	561.5	574.5	587.9	603.8	626.9	652.8	681.2	721.4
25°	515.5	517.9	522.9	534.5	546.1	561.2	575.1	596.8	623.5	656.7	697.0
27.5°	496.4	498.7	502.9	511.2	522.1	534.3	549.5	567.8	594.9	631.1	673.8
30°	485.0	485.4	489.3	497.0	506.2	516.3	530.3	551.2	576.6	613.4	658.3
32.5°	475.1	473.6	476.3	482.1	491.1	501.2	512.6	533.2	557.8	593.9	640.1
35°	458.3	457.6	456.4	461.4	469.2	476.9	487.0	502.4	530.3	563.9	612.3
37.5°	441.2	439.4	437.3	439.6	445.7	453.7	462.4	476.2	500.2	537.2	583.5
40°	428.6	427.0	425.9	425.1	430.5	438.2	444.7	458.0	480.4	515.5	561.2
42.5°	414.7	413.7	412.2	411.1	415.7	421.5	428.4	440.0	462.4	495.4	538.7
45°	392.2	391.4	390.6	389.9	392.5	398.0	403.4	411.9	431.2	463.3	502.4
47.5°	367.2	366.2	366.5	365.3	367.9	371.5	375.4	384.5	403.0	428.9	457.5
50°	349.2	348.9	348.9	348.9	349.6	353.9	357.4	364.4	381.3	407.3	427.8
52.5°	332.2	330.6	330.6	331.2	332.6	335.4	337.6	345.2	360.0	381.3	399.9
55°	305.6	302.5	301.6	302.5	303.7	305.9	308.2	314.5	327.2	343.1	353.9
57.5°	276.0	274.3	273.3	273.5	274.1	275.9	277.7	284.5	294.5	302.8	309.7
60°	255.3	256.0	252.6	253.4	253.4	254.9	257.6	261.9	270.3	276.2	283.2
62.5°	235.8	234.7	233.7	232.6	232.6	233.2	236.8	240.1	247.4	250.4	255.9
65°	205.4	205.4	203.1	203.8	204.2	201.5	203.5	207.3	212.0	213.1	218.1
67.5°	174.6	173.5	172.2	171.1	171.1	170.8	171.8	173.7	177.2	177.6	181.5
70°	153.5	152.8	152.4	151.3	149.7	151.6	150.5	152.4	154.3	154.7	157.0
72.5°	133.1	132.4	131.7	130.5	129.9	129.7	129.8	132.0	133.3	132.7	135.3
75°	104.0	103.3	102.5	100.6	100.6	99.4	99.8	101.3	102.9	101.7	104.0
77.5°	76.4	74.0	73.9	74.4	73.1	73.3	72.9	72.6	73.3	73.4	75.5
80°	58.8	56.0	56.9	56.5	56.0	55.7	54.9	55.3	55.7	56.0	57.3
82.5°	42.4	42.1	41.4	41.3	40.9	39.9	39.5	40.2	40.5	40.3	41.2
85°	21.6	20.5	21.3	20.9	21.3	20.9	19.7	19.7	20.5	20.1	20.9
87.5°	9.3	9.4	8.7	8.7	8.1	8.0	7.5	7.6	7.5	7.3	7.7
90°	13.8	14.4	12.6	10.9	9.2	7.5	6.4	5.2	3.4	2.3	1.1
92.5°	66.9	88.6	97.5	73.1	48.4	33.3	24.7	19.9	15.5	10.6	7.2
95°	277.0	341.5	304.2	209.6	123.8	74.8	52.4	37.5	27.7	21.3	19.6
97.5°	566.3	529.4	387.5	230.0	133.3	86.5	62.2	47.5	39.0	34.0	33.4
100°	658.9	545.4	368.6	217.1	131.9	91.6	69.1	55.3	47.3	43.2	42.6
102.5°	663.6	515.5	341.0	206.1	133.7	97.6	77.0	64.5	57.0	53.3	52.3
105°	628.4	463.1	307.0	198.1	138.9	107.8	89.9	78.9	72.0	68.6	66.9
107.5°	566.9	416.8	285.4	197.5	148.2	121.0	104.4	94.1	87.4	84.0	82.2
110°	528.2	390.5	277.0	199.9	156.1	130.2	114.0	104.2	98.0	95.0	93.3



TEST NUMBER: P331921-840

CATALOG NUMBER: S123DIP-S560D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	494.5	373.0	272.5	204.5	163.9	139.9	124.2	114.4	108.1	105.2	103.4
115°	453.9	354.3	270.7	212.0	176.8	154.9	139.4	129.6	123.8	120.4	118.1
117.5°	429.4	343.2	271.8	221.9	190.6	168.8	154.5	143.5	138.3	135.3	132.7
120°	416.5	338.1	273.6	229.2	199.2	178.5	164.2	153.2	147.4	144.6	142.9
122.5°	405.9	334.9	276.8	236.2	208.5	188.2	172.9	162.4	156.2	153.3	151.6
125°	392.2	330.6	281.7	247.1	221.8	201.6	186.0	175.1	168.7	165.3	164.2
127.5°	380.3	328.5	287.2	256.1	233.3	213.8	198.2	186.1	179.8	175.4	173.7
130°	373.9	327.2	290.8	262.1	240.1	221.2	205.6	193.5	186.6	181.5	179.8
132.5°	367.8	326.7	293.7	267.6	246.2	227.6	212.6	200.5	192.2	186.5	184.3
135°	360.0	326.0	297.8	274.8	255.2	237.3	221.8	209.6	201.1	194.7	192.4
137.5°	353.3	324.8	300.5	280.0	261.4	244.2	229.8	217.8	208.6	202.4	200.0
140°	349.0	324.3	302.4	282.9	265.5	248.8	234.4	222.9	213.7	207.9	205.1
142.5°	345.4	323.4	303.8	285.6	268.7	252.6	239.0	227.5	219.2	213.0	210.6
145°	340.4	321.9	304.7	288.6	273.1	258.0	244.8	235.0	226.4	221.2	219.4
147.5°	335.6	319.8	304.7	290.4	276.5	262.8	251.5	242.1	234.6	229.4	228.4
150°	332.3	317.9	304.7	290.8	278.8	265.5	255.2	247.1	239.6	235.0	234.4
152.5°	328.7	315.7	303.4	291.9	280.1	268.7	258.8	251.8	245.2	240.5	240.4
155°	323.2	311.6	301.8	292.1	282.9	273.1	265.0	258.6	252.9	249.4	249.4
157.5°	316.9	308.0	299.8	292.7	284.3	276.5	270.2	264.9	259.7	257.0	256.5
160°	312.8	305.3	298.9	292.7	285.7	278.8	273.1	269.0	264.4	262.1	262.1
162.5°	308.6	302.6	297.1	292.2	286.2	280.1	275.3	271.8	268.1	266.2	266.2
165°	303.0	298.4	294.4	290.8	286.8	282.3	278.2	275.9	273.1	271.9	272.5
167.5°	297.6	294.2	291.5	289.9	286.7	283.4	280.8	279.2	277.0	276.5	277.2
170°	294.4	291.4	289.7	288.6	286.3	283.4	282.3	281.0	279.3	278.8	279.9
172.5°	291.1	289.1	288.3	288.1	286.3	283.9	283.2	282.5	281.2	281.0	281.8
175°	287.4	286.3	286.3	286.8	285.7	284.6	284.0	284.0	282.9	283.4	284.0
177.5°	285.0	284.6	285.0	285.9	285.0	284.6	284.6	284.6	284.1	284.6	285.0
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P331921-840

CATALOG NUMBER: S123DIP-S560D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	803.2	804.8	810.0	813.7	818.1	820.6	823.0	825.0	827.4	828.0	837.0
5°	806.8	814.6	828.1	838.1	850.5	864.0	873.3	877.6	888.8	898.1	916.7
7.5°	805.8	822.2	842.7	863.9	886.7	907.7	925.9	947.6	963.0	986.1	1009.0
10°	804.9	826.9	853.2	880.3	912.0	941.4	967.8	997.1	1021.5	1053.6	1081.1
12.5°	802.1	828.8	865.3	897.3	935.8	976.3	1015.3	1053.1	1074.7	1128.1	1153.5
15°	795.2	826.9	872.5	921.3	974.3	1022.3	1071.8	1111.2	1175.0	1221.8	1251.6
17.5°	782.0	826.5	880.6	939.4	1003.8	1067.0	1123.1	1183.0	1250.7	1307.3	1367.7
20°	775.9	824.6	884.9	949.9	1016.8	1088.3	1152.2	1224.2	1298.0	1353.7	1431.1
22.5°	764.5	819.6	884.6	957.0	1028.5	1102.6	1177.3	1249.8	1335.1	1411.9	1485.5
25°	745.7	807.6	874.8	955.7	1039.7	1113.9	1203.3	1299.6	1388.6	1487.1	1560.6
27.5°	726.1	792.1	859.6	934.7	1025.0	1113.2	1225.6	1334.3	1443.1	1528.3	1582.7
30°	710.8	775.1	844.8	920.5	1009.9	1114.7	1240.4	1359.1	1465.1	1538.2	1568.7
32.5°	694.5	759.6	821.2	900.7	995.9	1113.8	1249.7	1373.6	1466.3	1515.0	1509.0
35°	668.7	723.3	783.3	859.8	972.0	1106.9	1255.1	1374.9	1431.8	1421.4	1342.5
37.5°	631.6	677.5	736.5	820.3	944.1	1092.7	1244.3	1334.2	1330.5	1245.5	1131.1
40°	608.4	647.4	704.3	792.5	922.4	1083.4	1227.2	1285.7	1236.2	1117.4	980.5
42.5°	578.0	614.0	670.9	761.5	898.7	1064.5	1194.8	1211.6	1114.8	978.2	852.7
45°	531.1	562.8	621.6	715.2	862.9	1023.4	1115.5	1074.1	943.7	802.5	707.0
47.5°	480.5	513.5	570.1	666.2	811.2	961.6	1005.4	917.5	783.6	669.1	581.4
50°	448.7	480.4	535.6	632.8	776.3	910.9	929.1	815.4	692.4	591.8	519.8
52.5°	416.5	446.4	500.7	598.1	735.4	852.0	840.8	725.0	611.9	526.1	469.7
55°	368.6	396.9	448.7	540.0	664.9	757.3	716.7	606.1	512.5	446.0	403.0
57.5°	325.8	352.8	397.5	480.0	588.5	652.1	600.5	507.3	432.8	381.6	349.6
60°	296.7	320.6	363.1	439.8	534.1	582.5	531.4	449.1	386.4	345.4	316.8
62.5°	269.1	290.0	329.4	398.9	480.9	521.5	469.9	400.1	346.8	310.4	286.1
65°	227.4	246.4	281.1	335.4	402.6	429.7	385.3	328.7	287.4	260.3	244.1
67.5°	189.3	205.4	235.5	278.1	327.7	347.4	313.6	269.8	238.6	216.9	204.0
70°	164.0	177.9	201.5	238.2	283.2	298.2	266.5	230.6	207.7	190.3	178.3
72.5°	142.6	152.9	174.3	202.7	240.1	252.1	229.9	198.3	177.0	164.0	154.5
75°	108.7	117.1	131.1	153.9	179.9	186.8	170.2	150.5	136.1	126.8	119.5
77.5°	78.4	84.6	94.7	108.8	126.7	133.0	122.5	109.3	98.9	92.6	88.5
80°	59.2	64.2	72.7	84.3	95.1	98.7	92.4	82.4	75.0	71.6	68.1
82.5°	43.7	46.6	51.7	59.6	67.0	71.1	65.8	59.8	55.8	52.7	51.4
85°	22.0	23.6	26.0	29.0	33.6	35.2	33.2	31.7	29.4	27.5	27.5
87.5°	8.5	8.8	10.0	10.9	12.3	13.6	13.6	13.3	13.4	12.9	12.8
90°	2.3	3.4	5.2	6.4	7.5	9.2	10.9	12.6	14.4	13.8	14.4
92.5°	10.6	15.5	19.9	24.7	33.3	48.4	73.1	97.5	88.6	66.9	48.5
95°	21.3	27.7	37.5	52.4	74.8	123.8	209.6	304.2	341.5	277.0	207.3
97.5°	34.0	39.0	47.5	62.2	86.5	133.3	230.0	387.5	529.4	566.3	516.9
100°	43.2	47.3	55.3	69.1	91.6	131.9	217.1	368.6	545.4	658.9	679.1
102.5°	53.3	57.0	64.5	77.0	97.6	133.7	206.1	341.0	515.5	663.6	733.1
105°	68.6	72.0	78.9	89.9	107.8	138.9	198.1	307.0	463.1	628.4	748.8
107.5°	84.0	87.4	94.1	104.4	121.0	148.2	197.5	285.4	416.8	566.9	703.4
110°	95.0	98.0	104.2	114.0	130.2	156.1	199.9	277.0	390.5	528.2	660.0



TEST NUMBER: P331921-840

CATALOG NUMBER: S123DIP-S560D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	105.2	108.1	114.4	124.2	139.9	163.9	204.5	272.5	373.0	494.5	617.2
115°	120.4	123.8	129.6	139.4	154.9	176.8	212.0	270.7	354.3	453.9	560.5
117.5°	135.3	138.3	143.5	154.5	168.8	190.6	221.9	271.8	343.2	429.4	519.3
120°	144.6	147.4	153.2	164.2	178.5	199.2	229.2	273.6	338.1	416.5	497.7
122.5°	153.3	156.2	162.4	172.9	188.2	208.5	236.2	276.8	334.9	405.9	480.6
125°	165.3	168.7	175.1	186.0	201.6	221.8	247.1	281.7	330.6	392.2	457.9
127.5°	175.4	179.8	186.1	198.2	213.8	233.3	256.1	287.2	328.5	380.3	438.1
130°	181.5	186.6	193.5	205.6	221.2	240.1	262.1	290.8	327.2	373.9	425.7
132.5°	186.5	192.2	200.5	212.6	227.6	246.2	267.6	293.7	326.7	367.8	414.1
135°	194.7	201.1	209.6	221.8	237.3	255.2	274.8	297.8	326.0	360.0	398.6
137.5°	202.4	208.6	217.8	229.8	244.2	261.4	280.0	300.5	324.8	353.3	384.5
140°	207.9	213.7	222.9	234.4	248.8	265.5	282.9	302.4	324.3	349.0	376.2
142.5°	213.0	219.2	227.5	239.0	252.6	268.7	285.6	303.8	323.4	345.4	368.3
145°	221.2	226.4	235.0	244.8	258.0	273.1	288.6	304.7	321.9	340.4	358.8
147.5°	229.4	234.6	242.1	251.5	262.8	276.5	290.4	304.7	319.8	335.6	351.1
150°	235.0	239.6	247.1	255.2	265.5	278.8	290.8	304.7	317.9	332.3	345.6
152.5°	240.5	245.2	251.8	258.8	268.7	280.1	291.9	303.4	315.7	328.7	340.5
155°	249.4	252.9	258.6	265.0	273.1	282.9	292.1	301.8	311.6	323.2	333.0
157.5°	257.0	259.7	264.9	270.2	276.5	284.3	292.7	299.8	308.0	316.9	324.9
160°	262.1	264.4	269.0	273.1	278.8	285.7	292.7	298.9	305.3	312.8	320.2
162.5°	266.2	268.1	271.8	275.3	280.1	286.2	292.2	297.1	302.6	308.6	314.8
165°	271.9	273.1	275.9	278.2	282.3	286.8	290.8	294.4	298.4	303.0	307.6
167.5°	276.5	277.0	279.2	280.8	283.4	286.7	289.9	291.5	294.2	297.6	301.3
170°	278.8	279.3	281.0	282.3	283.4	286.3	288.6	289.7	291.4	294.4	297.2
172.5°	281.0	281.2	282.5	283.2	283.9	286.3	288.1	288.3	289.1	291.1	293.6
175°	283.4	282.9	284.0	284.0	284.6	285.7	286.8	286.3	286.3	287.4	288.6
177.5°	284.6	284.1	284.6	284.6	284.6	285.0	285.9	285.0	284.6	285.0	285.5
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P331921-840

CATALOG NUMBER: S123DIP-S560D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	840.1	840.4	843.7	846.3	845.1	846.6	847.2
5°	917.8	931.7	939.1	944.5	944.9	945.2	948.4
7.5°	1028.0	1043.0	1053.9	1070.5	1075.4	1081.1	1079.4
10°	1108.5	1130.5	1149.5	1159.5	1170.3	1186.2	1173.5
12.5°	1183.7	1222.7	1251.6	1267.2	1277.5	1280.6	1274.3
15°	1307.7	1358.8	1386.2	1385.4	1420.3	1435.3	1411.7
17.5°	1421.4	1468.5	1506.2	1525.6	1554.6	1561.0	1558.1
20°	1491.0	1542.5	1571.9	1605.1	1620.2	1633.8	1636.1
22.5°	1551.1	1597.2	1628.8	1656.5	1669.1	1675.5	1679.4
25°	1612.9	1649.2	1668.2	1677.8	1681.3	1680.5	1675.5
27.5°	1608.6	1611.3	1590.5	1570.0	1551.7	1531.0	1523.9
30°	1566.8	1534.3	1476.3	1443.4	1395.1	1356.8	1372.3
32.5°	1456.9	1392.3	1327.2	1255.3	1195.8	1178.9	1161.8
35°	1243.4	1129.7	1063.3	985.9	954.9	924.0	902.7
37.5°	1006.0	918.1	839.1	788.5	757.5	738.0	727.4
40°	869.9	790.5	725.6	684.6	661.0	638.9	635.8
42.5°	761.2	687.5	638.6	606.0	583.3	574.0	567.1
45°	623.5	572.0	539.2	515.9	500.9	495.0	487.4
47.5°	527.8	491.4	466.7	450.9	439.5	435.2	434.5
50°	474.2	444.0	425.9	413.4	404.6	403.0	396.9
52.5°	433.9	407.8	393.6	382.8	376.4	372.0	370.2
55°	376.7	359.3	346.6	340.3	335.4	331.0	331.0
57.5°	329.6	315.1	306.6	301.3	299.8	296.8	294.9
60°	300.5	288.1	281.6	276.9	273.9	274.2	270.7
62.5°	272.1	264.0	257.7	253.1	249.4	249.4	249.7
65°	231.7	225.5	220.9	219.3	217.0	214.3	215.0
67.5°	196.3	190.6	186.9	184.3	183.5	182.0	184.3
70°	171.0	166.7	164.0	161.7	160.9	161.3	163.2
72.5°	147.7	144.7	143.0	141.9	140.2	140.3	141.6
75°	116.0	113.7	112.2	111.0	110.6	110.6	110.6
77.5°	85.2	84.7	84.0	82.3	82.4	82.8	82.9
80°	67.3	66.1	65.7	64.9	63.8	63.0	64.9
82.5°	50.3	49.1	48.8	48.6	46.8	46.7	48.3
85°	27.1	26.0	26.3	26.0	26.0	25.5	25.5
87.5°	12.6	12.4	12.3	12.5	12.3	12.1	12.6
90°	14.9	15.6	16.7	16.2	16.7	17.3	16.7
92.5°	38.5	34.0	31.0	30.0	28.2	28.8	27.8
95°	140.6	110.0	89.3	78.4	73.1	69.1	66.9
97.5°	414.0	339.7	270.8	228.3	202.4	186.8	181.9
100°	632.5	565.0	483.2	425.1	383.0	360.6	361.1
102.5°	731.5	692.3	640.4	595.1	561.8	543.0	529.8
105°	806.4	817.4	802.3	775.9	754.0	735.6	732.7
107.5°	797.0	847.4	867.9	868.4	861.0	854.7	849.5
110°	766.1	838.7	879.0	895.1	899.7	898.6	897.4



TEST NUMBER: P331921-840

CATALOG NUMBER: S123DIP-S560D585U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	725.5	806.9	858.7	888.2	902.5	906.9	907.1
115°	660.7	745.4	808.1	851.3	876.7	888.2	891.1
117.5°	605.8	681.9	745.6	790.6	819.6	836.3	840.1
120°	575.4	644.5	702.8	748.2	780.5	794.3	797.8
122.5°	551.0	615.0	669.0	709.5	738.5	753.8	758.1
125°	520.7	576.0	622.1	658.9	684.3	698.7	702.8
127.5°	494.1	544.0	585.9	618.7	640.4	653.4	657.1
130°	477.5	524.1	563.3	593.9	614.6	626.7	631.3
132.5°	461.8	505.2	542.6	571.3	592.0	602.7	605.9
135°	439.5	477.0	509.8	538.0	555.2	565.6	569.7
137.5°	418.0	450.2	478.7	502.4	519.9	528.7	531.3
140°	405.5	433.1	457.9	479.8	495.9	505.1	504.5
142.5°	393.5	417.5	439.0	457.7	472.0	480.3	479.7
145°	377.9	396.3	413.0	427.4	439.5	444.1	445.2
147.5°	366.2	381.1	392.9	403.8	412.0	416.5	416.9
150°	358.8	370.9	381.9	390.5	396.9	400.3	400.3
152.5°	351.9	362.6	371.7	378.5	384.5	386.5	386.5
155°	342.1	350.8	357.7	362.8	367.5	368.6	369.2
157.5°	332.5	339.3	344.7	349.2	352.6	353.6	353.5
160°	326.6	332.3	336.4	340.4	343.9	343.9	343.3
162.5°	320.1	325.5	329.0	331.6	334.7	334.7	334.1
165°	311.0	315.1	317.9	320.2	322.6	321.9	321.9
167.5°	304.0	306.3	308.4	309.4	311.0	310.4	310.4
170°	298.9	301.2	302.4	303.0	304.2	303.6	303.6
172.5°	294.8	296.6	297.3	297.4	298.6	297.6	297.1
175°	289.1	290.3	290.3	290.3	290.8	290.3	289.7
177.5°	285.9	286.4	286.4	285.9	286.4	285.5	285.5
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6

(END OF REPORT)