

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331993-840

Luminaire Tested: **S123DIP-S775D1195U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331993-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1195U840-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7658.7 lumens
Efficiency: N/A
Efficacy: 134.6 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331993-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331993-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43				
1	96	92	89	85	88	85	81	78	70	68	66	57	55	54	44	43	42	37				
2	88	81	75	70	80	74	69	65	62	58	55	50	47	45	39	38	36	31				
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	27				
4	74	63	55	49	67	58	51	46	48	43	39	40	36	33	31	29	27	23				
5	68	56	48	42	62	52	45	40	43	38	34	36	32	29	28	26	23	20				
6	62	50	42	37	57	47	40	34	39	34	30	32	28	25	26	23	21	18				
7	58	45	38	32	52	42	35	30	35	30	26	29	25	22	23	21	18	16				
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	22	19	16	14				
9	50	38	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15	13				
10	46	34	27	23	42	32	26	21	27	22	19	23	19	16	18	16	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11746	11746	11746	11746
5°	14008	11797	10454	11797
10°	17533	11737	9441	11737
15°	21504	11642	8790	11642
20°	25616	11494	8369	11494
25°	27201	11315	8276	11315
30°	23313	11184	8319	11184
35°	16215	10997	8406	10997
40°	12213	10779	8379	10779
45°	10140	10455	8273	10455
50°	9083	9791	8199	9791
55°	8492	9077	8096	9077
60°	7967	8331	8013	8331
65°	7488	7595	7755	7595
70°	7021	6754	7386	6754
75°	6288	5914	6771	5914
80°	5511	4854	5833	4854
85°	4310	3532	3915	3532



TEST NUMBER: P331993-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.5	1.4
10°-20°	344.7	4.5
20°-30°	578.5	7.6
30°-40°	655.0	8.6
40°-50°	587.4	7.7
50°-60°	474.0	6.2
60°-70°	330.3	4.3
70°-80°	173.6	2.3
80°-90°	46.9	0.6
90°-100°	322.6	4.2
100°-110°	913.4	11.9
110°-120°	898.5	11.7
120°-130°	716.7	9.4
130°-140°	565.1	7.4
140°-150°	421.7	5.5
150°-160°	294.0	3.8
160°-170°	172.7	2.3
170°-180°	56.2	0.7
0°-30°	1030.6	13.5
0°-40°	1685.7	22.0
0°-60°	2747.1	35.9
0°-90°	3297.9	43.1
90°-120°	2134.4	27.9
90°-150°	3837.9	50.1
90°-180°	4361.0	56.9
0°-180°	7658.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1091	1091	1091	1091	1091	
5°	1296	1092	968	1092	1296	134
15°	1930	1045	789	1045	1930	557
25°	2290	953	697	953	2290	1004
35°	1234	837	640	837	1234	802
45°	666	687	544	687	666	527
55°	452	484	431	484	452	406
65°	294	298	304	298	294	293
75°	151	142	163	142	151	162
85°	35	29	32	29	35	42
90°	34	2	34	2	34	20
95°	136	40	136	40	136	245
105°	1492	136	1492	136	1492	1472
115°	1815	240	1815	240	1815	1764
125°	1432	334	1432	334	1432	1297
135°	1160	392	1160	392	1160	900
145°	907	447	907	447	907	577
155°	752	508	752	508	752	351
165°	656	555	656	555	656	187
175°	590	578	590	578	590	57
180°	580	580	580	580	580	



TEST NUMBER: P331993-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1158.0	1157.2	1155.1	1156.8	1153.4	1148.7	1148.3	1144.1	1131.8	1130.9	1127.6
5°	1296.4	1292.1	1291.6	1291.0	1283.6	1273.6	1254.6	1252.9	1227.6	1214.9	1199.6
7.5°	1475.4	1477.6	1470.0	1463.2	1440.6	1425.6	1405.2	1379.1	1348.0	1316.4	1295.3
10°	1604.1	1621.4	1599.8	1585.0	1571.2	1545.3	1515.2	1477.6	1440.2	1396.2	1362.9
12.5°	1741.9	1750.5	1746.2	1732.2	1710.8	1671.4	1618.0	1576.6	1542.1	1468.9	1439.5
15°	1929.7	1962.0	1941.4	1893.7	1894.8	1857.2	1787.5	1710.8	1670.1	1606.1	1518.9
17.5°	2129.7	2133.7	2125.0	2085.4	2058.9	2007.3	1942.9	1869.5	1787.0	1709.5	1617.0
20°	2236.3	2233.1	2214.6	2194.0	2148.6	2108.4	2038.1	1956.1	1850.4	1774.2	1673.2
22.5°	2295.5	2290.3	2281.5	2264.2	2226.3	2183.2	2120.1	2030.5	1930.0	1825.0	1708.4
25°	2290.3	2297.1	2298.1	2293.4	2280.2	2254.3	2204.6	2133.2	2032.8	1897.9	1776.4
27.5°	2083.0	2092.7	2121.0	2146.1	2174.0	2202.6	2198.8	2163.3	2089.0	1972.7	1823.9
30°	1875.7	1854.6	1906.9	1973.1	2018.0	2097.3	2141.7	2144.3	2102.5	2002.7	1857.7
32.5°	1588.1	1611.4	1634.6	1715.9	1814.1	1903.2	1991.6	2062.8	2070.8	2004.4	1877.6
35°	1234.0	1263.0	1305.4	1347.6	1453.4	1544.3	1699.7	1835.0	1942.9	1957.2	1879.5
37.5°	994.3	1008.8	1035.5	1077.8	1147.0	1254.9	1375.1	1546.2	1702.4	1818.7	1823.7
40°	869.2	873.4	903.5	935.7	991.8	1080.7	1189.0	1340.2	1527.3	1689.7	1757.4
42.5°	775.3	784.6	797.4	828.3	872.9	939.8	1040.6	1165.5	1337.1	1523.9	1656.3
45°	666.1	676.7	684.7	705.3	737.0	781.9	852.2	966.4	1097.0	1290.0	1468.1
47.5°	594.0	594.9	600.8	616.3	637.9	671.7	721.3	794.8	914.6	1071.1	1254.1
50°	542.4	550.9	553.0	565.1	582.1	606.9	648.1	710.5	808.9	946.3	1114.5
52.5°	506.0	508.6	514.5	523.3	538.1	557.4	593.2	642.1	719.2	836.4	991.0
55°	452.5	452.5	458.4	465.2	473.7	491.1	514.9	550.9	609.6	700.5	828.5
57.5°	403.0	405.7	409.8	411.9	419.1	430.7	450.5	477.9	521.6	591.6	693.3
60°	370.1	374.9	374.4	378.5	384.9	393.8	410.8	433.0	472.1	528.2	613.8
62.5°	341.3	341.0	340.9	346.0	352.3	360.9	371.8	391.1	424.3	474.0	546.9
65°	294.0	292.9	296.6	299.7	301.8	308.2	316.7	333.6	355.8	392.8	449.4
67.5°	251.9	248.8	250.9	251.9	255.5	260.4	268.3	278.8	296.5	326.2	368.8
70°	223.1	220.5	219.9	221.0	224.2	227.8	233.7	243.7	260.1	283.9	315.1
72.5°	193.5	191.7	191.6	193.9	195.4	197.8	202.0	211.2	224.2	242.1	271.1
75°	151.2	151.2	151.2	151.7	153.3	155.4	158.6	163.4	173.4	186.1	205.6
77.5°	113.3	113.2	112.6	112.5	114.8	115.8	116.5	121.0	126.5	135.1	149.4
80°	88.9	86.1	87.3	88.9	89.9	90.4	92.0	93.0	97.9	102.6	112.6
82.5°	65.9	63.7	63.9	66.4	66.7	67.2	68.8	70.2	72.0	76.3	81.7
85°	34.9	34.9	35.4	35.4	36.0	35.4	37.0	37.6	37.6	40.2	43.3
87.5°	19.5	18.9	19.1	19.3	19.1	19.0	19.2	19.4	19.6	20.2	20.0
90°	34.0	35.2	34.0	32.8	34.0	31.7	30.5	29.3	28.2	29.3	25.9
92.5°	56.6	58.7	57.5	61.0	63.1	69.2	78.4	98.8	136.1	180.5	198.5
95°	136.1	140.8	149.1	159.6	181.9	224.1	286.3	422.4	564.3	695.8	619.6
97.5°	370.5	380.6	412.3	465.1	551.7	692.1	843.3	1052.9	1153.6	1078.2	789.4
100°	735.7	734.5	780.2	865.9	984.4	1151.0	1288.3	1383.3	1342.3	1111.2	750.9
102.5°	1079.2	1106.2	1144.5	1212.2	1304.4	1410.1	1490.1	1493.2	1351.6	1050.2	694.6
105°	1492.5	1498.3	1535.9	1580.4	1634.5	1665.0	1642.6	1525.3	1280.1	943.3	625.4
107.5°	1730.4	1741.2	1753.8	1768.9	1768.0	1726.2	1623.4	1432.8	1154.8	849.0	581.3
110°	1828.1	1830.4	1832.7	1823.3	1790.5	1708.4	1560.5	1344.6	1075.9	795.5	564.3



TEST NUMBER: P331993-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1847.8	1847.2	1838.4	1809.3	1749.2	1643.6	1477.9	1257.3	1007.4	759.8	555.0
115°	1815.1	1809.3	1785.7	1734.1	1646.2	1518.2	1345.7	1141.7	924.5	721.5	551.5
117.5°	1711.4	1703.4	1669.6	1610.5	1518.7	1389.0	1234.1	1057.8	874.5	699.0	553.6
120°	1625.1	1618.0	1589.8	1524.1	1431.5	1312.9	1172.2	1013.7	848.3	688.7	557.3
122.5°	1544.3	1535.4	1504.4	1445.3	1362.9	1252.8	1122.4	979.0	826.7	682.2	563.9
125°	1431.5	1423.2	1393.9	1342.3	1267.2	1173.3	1060.7	932.8	799.0	673.5	573.7
127.5°	1338.5	1331.0	1304.4	1260.4	1193.5	1108.0	1006.4	892.4	774.7	669.2	585.0
130°	1286.0	1276.6	1251.9	1209.7	1147.5	1067.7	972.7	867.1	761.4	666.4	592.5
132.5°	1234.4	1227.8	1205.9	1163.7	1105.3	1029.3	940.8	843.6	749.3	665.5	598.1
135°	1160.4	1152.2	1131.0	1095.9	1038.3	971.5	895.2	811.9	733.4	664.1	606.6
137.5°	1082.3	1076.8	1059.0	1023.4	975.0	917.1	851.3	783.0	719.4	661.5	612.3
140°	1027.8	1029.0	1010.3	977.3	932.8	882.3	826.0	766.2	711.0	660.6	616.0
142.5°	977.1	978.3	961.4	932.3	894.3	850.4	801.6	750.2	703.5	658.7	618.8
145°	907.0	904.6	895.2	870.6	841.2	807.3	769.7	730.9	693.5	655.9	620.7
147.5°	849.2	848.3	839.4	822.7	800.4	776.3	746.0	715.3	683.6	651.5	620.7
150°	815.5	815.5	808.4	795.5	777.9	755.6	730.9	704.0	677.0	647.6	620.7
152.5°	787.3	787.3	783.0	771.1	757.3	738.7	716.9	693.7	669.5	643.0	617.8
155°	752.0	750.9	748.6	739.2	728.6	714.6	696.9	678.1	658.2	634.8	614.8
157.5°	719.9	720.1	718.3	711.2	702.1	691.1	677.5	661.8	645.5	627.5	610.9
160°	699.3	700.4	700.4	693.5	685.2	677.0	665.3	652.4	637.1	621.9	608.9
162.5°	680.5	681.7	681.7	675.6	670.1	662.9	652.2	641.1	628.6	616.2	605.2
165°	655.9	655.9	657.0	652.4	647.6	641.8	633.6	626.5	617.1	607.7	599.6
167.5°	632.4	632.4	633.6	630.3	628.2	624.0	619.2	613.9	606.1	599.4	593.9
170°	618.3	618.3	619.6	617.1	616.0	613.6	608.9	605.4	599.6	593.7	590.2
172.5°	605.2	606.1	608.2	605.9	605.6	604.3	600.5	597.9	593.0	589.0	587.3
175°	590.2	591.4	592.5	591.4	591.4	591.4	589.0	587.8	585.5	583.1	583.1
177.5°	581.5	581.5	583.4	582.4	583.4	583.4	582.4	581.5	580.6	579.7	580.6
180°	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7



TEST NUMBER: P331993-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1125.0	1121.7	1118.2	1112.4	1107.3	1100.0	1097.9	1095.4	1087.8	1081.1	1076.0
5°	1193.8	1181.0	1162.6	1145.7	1132.0	1113.4	1102.9	1091.8	1075.9	1061.6	1050.0
7.5°	1265.7	1240.7	1211.9	1180.8	1151.9	1124.0	1101.5	1081.4	1059.1	1038.1	1021.8
10°	1322.7	1286.8	1246.7	1203.3	1166.3	1130.3	1100.1	1073.8	1045.2	1020.4	999.8
12.5°	1387.9	1334.6	1279.2	1226.6	1182.8	1132.9	1096.4	1062.8	1030.4	1000.5	977.3
15°	1465.0	1397.4	1331.7	1259.3	1192.8	1130.3	1087.0	1044.7	1007.1	976.4	946.8
17.5°	1535.2	1458.5	1372.1	1284.0	1203.7	1129.7	1069.0	1021.2	974.2	936.8	907.3
20°	1575.0	1487.7	1389.9	1298.5	1209.6	1127.1	1060.6	1003.4	952.7	913.0	879.7
22.5°	1609.2	1507.1	1405.9	1308.2	1209.2	1120.3	1044.9	986.1	931.1	892.3	856.9
25°	1644.8	1522.6	1421.1	1306.4	1195.9	1103.9	1019.3	952.7	897.7	852.2	815.8
27.5°	1675.2	1521.6	1401.1	1277.7	1175.0	1082.8	992.4	921.0	862.6	813.2	776.2
30°	1695.5	1523.7	1380.4	1258.3	1154.7	1059.4	971.7	899.8	838.5	788.3	753.4
32.5°	1708.2	1522.4	1361.4	1231.2	1122.5	1038.3	949.3	874.8	811.8	762.4	728.8
35°	1715.6	1513.1	1328.6	1175.3	1070.6	988.7	914.1	836.9	770.8	724.8	686.8
37.5°	1700.8	1493.5	1290.5	1121.4	1006.7	926.0	863.3	797.6	734.4	683.7	651.0
40°	1677.5	1480.9	1260.9	1083.3	962.7	885.0	831.6	767.1	704.7	656.6	625.9
42.5°	1633.1	1455.0	1228.3	1041.0	917.1	839.3	790.2	736.3	677.2	632.1	601.5
45°	1524.7	1398.9	1179.5	977.5	849.6	769.2	725.9	686.8	633.4	589.5	563.0
47.5°	1374.3	1314.4	1108.8	910.6	779.2	701.9	656.8	625.3	586.3	550.9	525.5
50°	1269.9	1245.1	1061.1	864.9	732.3	656.6	613.3	584.7	556.7	521.3	498.1
52.5°	1149.3	1164.7	1005.2	817.6	684.4	610.1	569.3	546.6	521.2	492.1	471.8
55°	979.7	1035.1	908.8	738.0	613.3	542.4	503.8	483.7	469.0	447.3	429.8
57.5°	820.7	891.4	804.6	656.1	543.4	482.3	445.2	423.3	413.8	402.5	388.8
60°	726.4	796.2	730.1	601.1	496.4	438.3	405.5	387.0	377.5	369.5	357.9
62.5°	642.3	712.9	657.3	545.3	450.3	396.4	367.9	349.8	342.3	338.2	328.3
65°	526.5	587.3	550.4	458.4	384.4	336.8	310.8	298.2	291.3	289.7	283.4
67.5°	428.6	474.8	447.9	380.2	321.9	280.8	258.8	248.0	242.8	242.3	237.5
70°	364.3	407.6	387.0	325.7	275.5	243.2	224.2	214.6	211.5	211.0	208.3
72.5°	314.4	344.6	328.2	277.0	238.2	208.9	195.0	185.0	181.5	182.2	180.4
75°	232.6	255.4	245.8	210.5	179.3	160.2	148.6	142.2	139.1	140.7	138.6
77.5°	167.3	181.8	173.2	148.7	129.5	115.6	107.1	103.2	100.4	100.3	99.3
80°	126.3	134.8	130.1	115.2	99.4	87.8	80.9	78.3	76.6	76.1	75.6
82.5°	90.0	97.1	91.6	81.4	70.6	63.6	59.8	56.2	55.1	55.4	54.8
85°	45.4	48.1	45.9	39.7	35.4	32.2	30.1	28.6	27.5	28.0	27.0
87.5°	20.1	19.8	17.9	15.7	14.3	12.4	11.9	10.6	10.2	10.7	11.0
90°	22.3	18.8	15.2	12.9	10.6	7.1	4.6	2.3	4.6	7.1	10.6
92.5°	149.1	98.6	67.9	50.5	40.6	31.4	21.6	14.5	21.6	31.4	40.6
95°	427.1	252.3	152.5	106.7	76.2	56.4	43.4	39.9	43.4	56.4	76.2
97.5°	468.6	271.6	176.2	126.7	96.6	79.3	69.2	68.1	69.2	79.3	96.6
100°	442.3	268.7	186.5	140.8	112.6	96.2	88.0	86.8	88.0	96.2	112.6
102.5°	419.8	272.5	198.7	156.7	131.4	115.9	108.7	106.5	108.7	115.9	131.4
105°	403.6	282.8	219.4	183.0	160.8	146.6	139.7	136.1	139.7	146.6	160.8
107.5°	402.4	302.1	246.4	212.6	191.7	177.8	171.1	167.5	171.1	177.8	191.7
110°	407.2	318.0	265.2	232.3	212.4	199.4	193.6	190.1	193.6	199.4	212.4



TEST NUMBER: P331993-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	416.6	334.0	284.9	253.0	233.0	220.2	214.3	210.8	214.3	220.2	233.0
115°	431.8	360.2	315.6	284.0	264.0	252.3	245.2	240.5	245.2	252.3	264.0
117.5°	451.9	388.1	344.1	314.7	292.4	281.6	275.7	270.3	275.7	281.6	292.4
120°	467.0	406.0	363.8	334.4	312.1	300.3	294.5	290.9	294.5	300.3	312.1
122.5°	481.1	424.7	383.4	352.2	330.8	318.2	312.4	308.8	312.4	318.2	330.8
125°	503.3	451.7	410.6	379.0	356.7	343.8	336.8	334.4	336.8	343.8	356.7
127.5°	521.7	475.1	435.6	403.8	379.2	366.1	357.4	353.9	357.4	366.1	379.2
130°	533.8	489.3	450.5	418.9	394.3	380.1	369.6	366.1	369.6	380.1	394.3
132.5°	545.1	501.5	463.7	432.9	408.3	391.4	379.9	375.5	379.9	391.4	408.3
135°	559.7	519.8	483.4	451.7	427.1	409.5	396.6	391.9	396.6	409.5	427.1
137.5°	570.5	532.4	497.5	468.2	443.7	425.0	412.3	407.4	412.3	425.0	443.7
140°	576.1	540.9	506.9	477.6	454.0	435.3	423.5	417.7	423.5	435.3	454.0
142.5°	581.7	547.4	514.4	487.0	463.4	446.6	433.9	429.0	433.9	446.6	463.4
145°	587.8	556.1	525.6	498.7	478.7	461.1	450.5	447.1	450.5	461.1	478.7
147.5°	591.6	563.2	535.2	512.3	493.0	477.8	467.5	465.3	467.5	477.8	493.0
150°	592.5	567.8	540.9	519.8	503.3	488.1	478.7	477.6	478.7	488.1	503.3
152.5°	594.4	570.7	547.4	527.3	512.7	499.4	490.0	489.8	490.0	499.4	512.7
155°	594.9	576.1	556.1	539.7	526.8	515.1	508.1	508.1	508.1	515.1	526.8
157.5°	596.0	579.2	563.2	550.5	539.5	529.2	523.5	522.6	523.5	529.2	539.5
160°	596.0	582.0	567.8	556.1	548.0	538.6	533.8	533.8	533.8	538.6	548.0
162.5°	595.1	582.9	570.7	560.9	553.6	546.0	542.3	542.3	542.3	546.0	553.6
165°	592.5	584.3	574.9	566.7	562.0	556.1	553.8	555.0	553.8	556.1	562.0
167.5°	590.7	584.1	577.2	572.1	568.9	564.3	563.2	564.6	563.2	564.3	568.9
170°	587.8	583.1	577.2	574.9	572.6	569.1	567.8	570.3	567.8	569.1	572.6
172.5°	586.9	583.1	578.2	576.8	575.4	572.8	572.6	574.0	572.6	572.8	575.4
175°	584.3	582.0	579.7	578.5	578.5	576.1	577.2	578.5	577.2	576.1	578.5
177.5°	582.4	580.6	579.7	579.7	579.7	578.7	579.7	580.6	579.7	578.7	579.7
180°	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7



TEST NUMBER: P331993-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1073.0	1070.1	1065.8	1059.4	1054.4	1046.3	1046.3	1047.6	1047.6	1047.2	1046.3
5°	1040.5	1032.5	1023.0	1011.9	1000.3	988.7	986.5	982.3	979.2	977.0	974.3
7.5°	1006.1	992.0	978.2	962.6	948.5	936.8	928.6	921.8	917.5	912.8	909.5
10°	982.8	965.3	949.0	932.6	914.6	900.4	891.4	885.0	880.3	876.1	873.9
12.5°	955.3	935.3	917.3	901.7	882.0	867.4	858.8	855.9	850.2	841.3	836.7
15°	915.1	896.7	874.9	851.2	841.6	823.6	813.6	808.9	805.7	798.8	796.7
17.5°	880.8	856.6	832.2	814.5	796.8	782.2	776.6	770.7	766.5	760.8	759.2
20°	853.3	831.6	809.4	790.4	771.8	756.0	751.2	747.0	742.8	740.1	738.0
22.5°	825.4	803.8	785.3	767.5	747.8	737.4	732.3	727.6	724.6	722.9	720.7
25°	786.2	767.1	746.5	730.6	714.8	707.9	704.7	702.1	699.9	697.3	696.8
27.5°	751.0	730.3	713.6	698.8	687.4	681.7	678.6	677.3	677.8	678.7	679.3
30°	724.8	705.8	692.1	679.3	668.8	663.5	663.0	663.0	665.1	665.6	666.7
32.5°	700.7	685.1	671.4	659.0	651.1	647.4	649.4	649.4	651.2	652.5	654.4
35°	665.6	651.9	641.3	630.8	623.9	625.4	626.5	627.5	630.2	633.4	635.5
37.5°	632.1	620.2	609.2	600.9	597.7	600.6	603.1	605.3	608.4	610.9	613.0
40°	607.9	599.0	588.4	581.0	582.1	583.7	585.8	588.4	591.1	592.7	594.8
42.5°	585.5	576.1	568.2	562.0	563.5	565.5	566.7	568.2	571.2	574.0	575.3
45°	551.4	544.0	536.6	532.9	534.0	535.0	536.0	537.7	540.3	542.4	543.0
47.5°	513.0	507.9	502.9	499.3	501.0	500.6	501.9	505.3	506.1	507.5	510.4
50°	488.5	483.7	478.0	476.9	476.9	476.9	477.4	481.6	481.6	483.7	485.8
52.5°	461.4	458.4	454.6	452.7	451.9	451.9	454.1	456.3	457.1	460.1	462.2
55°	421.3	418.2	415.1	413.4	412.3	413.4	417.7	418.7	421.3	422.9	424.5
57.5°	379.6	377.2	374.7	373.8	373.5	375.0	377.3	380.4	381.1	386.0	388.4
60°	352.1	348.4	346.3	346.3	345.3	350.0	348.9	354.3	355.3	358.4	362.1
62.5°	323.8	318.8	317.9	317.9	319.4	320.8	322.2	324.6	327.4	331.3	334.3
65°	278.1	275.5	279.1	278.6	277.5	280.7	280.7	283.4	286.5	290.2	296.1
67.5°	234.8	233.5	233.8	233.8	235.4	237.2	238.6	241.0	244.8	248.7	252.5
70°	205.6	207.2	204.6	206.7	208.3	208.8	209.8	213.1	217.3	219.9	224.2
72.5°	177.3	177.2	177.5	178.3	180.0	180.9	182.0	185.6	190.3	192.5	195.8
75°	136.4	135.8	137.4	137.4	140.1	141.2	142.2	143.8	148.0	151.2	153.8
77.5°	99.6	100.3	99.9	101.7	101.0	101.2	104.4	106.0	106.4	112.7	114.1
80°	75.0	76.1	76.6	77.2	77.8	76.6	80.4	81.9	81.9	85.6	88.3
82.5°	53.9	54.5	55.9	56.5	56.6	57.7	58.0	59.1	60.4	62.0	65.4
85°	27.0	28.6	29.1	28.6	29.1	28.0	29.6	30.1	30.7	30.7	30.7
87.5°	11.0	11.9	12.2	13.3	13.6	14.7	14.5	13.9	14.1	15.7	14.4
90°	12.9	15.2	18.8	22.3	25.9	29.3	28.2	29.3	30.5	31.7	34.0
92.5°	50.5	67.9	98.6	149.1	198.5	180.5	136.1	98.8	78.4	69.2	63.1
95°	106.7	152.5	252.3	427.1	619.6	695.8	564.3	422.4	286.3	224.1	181.9
97.5°	126.7	176.2	271.6	468.6	789.4	1078.2	1153.6	1052.9	843.3	692.1	551.7
100°	140.8	186.5	268.7	442.3	750.9	1111.2	1342.3	1383.3	1288.3	1151.0	984.4
102.5°	156.7	198.7	272.5	419.8	694.6	1050.2	1351.6	1493.2	1490.1	1410.1	1304.4
105°	183.0	219.4	282.8	403.6	625.4	943.3	1280.1	1525.3	1642.6	1665.0	1634.5
107.5°	212.6	246.4	302.1	402.4	581.3	849.0	1154.8	1432.8	1623.4	1726.2	1768.0
110°	232.3	265.2	318.0	407.2	564.3	795.5	1075.9	1344.6	1560.5	1708.4	1790.5



TEST NUMBER: P331993-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	253.0	284.9	334.0	416.6	555.0	759.8	1007.4	1257.3	1477.9	1643.6	1749.2
115°	284.0	315.6	360.2	431.8	551.5	721.5	924.5	1141.7	1345.7	1518.2	1646.2
117.5°	314.7	344.1	388.1	451.9	553.6	699.0	874.5	1057.8	1234.1	1389.0	1518.7
120°	334.4	363.8	406.0	467.0	557.3	688.7	848.3	1013.7	1172.2	1312.9	1431.5
122.5°	352.2	383.4	424.7	481.1	563.9	682.2	826.7	979.0	1122.4	1252.8	1362.9
125°	379.0	410.6	451.7	503.3	573.7	673.5	799.0	932.8	1060.7	1173.3	1267.2
127.5°	403.8	435.6	475.1	521.7	585.0	669.2	774.7	892.4	1006.4	1108.0	1193.5
130°	418.9	450.5	489.3	533.8	592.5	666.4	761.4	867.1	972.7	1067.7	1147.5
132.5°	432.9	463.7	501.5	545.1	598.1	665.5	749.3	843.6	940.8	1029.3	1105.3
135°	451.7	483.4	519.8	559.7	606.6	664.1	733.4	811.9	895.2	971.5	1038.3
137.5°	468.2	497.5	532.4	570.5	612.3	661.5	719.4	783.0	851.3	917.1	975.0
140°	477.6	506.9	540.9	576.1	616.0	660.6	711.0	766.2	826.0	882.3	932.8
142.5°	487.0	514.4	547.4	581.7	618.8	658.7	703.5	750.2	801.6	850.4	894.3
145°	498.7	525.6	556.1	587.8	620.7	655.9	693.5	730.9	769.7	807.3	841.2
147.5°	512.3	535.2	563.2	591.6	620.7	651.5	683.6	715.3	746.0	776.3	800.4
150°	519.8	540.9	567.8	592.5	620.7	647.6	677.0	704.0	730.9	755.6	777.9
152.5°	527.3	547.4	570.7	594.4	617.8	643.0	669.5	693.7	716.9	738.7	757.3
155°	539.7	556.1	576.1	594.9	614.8	634.8	658.2	678.1	696.9	714.6	728.6
157.5°	550.5	563.2	579.2	596.0	610.9	627.5	645.5	661.8	677.5	691.1	702.1
160°	556.1	567.8	582.0	596.0	608.9	621.9	637.1	652.4	665.3	677.0	685.2
162.5°	560.9	570.7	582.9	595.1	605.2	616.2	628.6	641.1	652.2	662.9	670.1
165°	566.7	574.9	584.3	592.5	599.6	607.7	617.1	626.5	633.6	641.8	647.6
167.5°	572.1	577.2	584.1	590.7	593.9	599.4	606.1	613.9	619.2	624.0	628.2
170°	574.9	577.2	583.1	587.8	590.2	593.7	599.6	605.4	608.9	613.6	616.0
172.5°	576.8	578.2	583.1	586.9	587.3	589.0	593.0	597.9	600.5	604.3	605.6
175°	578.5	579.7	582.0	584.3	583.1	583.1	585.5	587.8	589.0	591.4	591.4
177.5°	579.7	579.7	580.6	582.4	580.6	579.7	580.6	581.5	582.4	583.4	583.4
180°	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7



TEST NUMBER: P331993-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1043.4	1043.0	1045.9	1043.8	1045.9	1043.0	1043.4	1046.3	1047.2	1047.6	1047.6
5°	971.2	972.8	967.5	967.5	967.5	972.8	971.2	974.3	977.0	979.2	982.3
7.5°	906.9	904.5	904.7	901.9	904.7	904.5	906.9	909.5	912.8	917.5	921.8
10°	867.6	864.4	863.3	863.8	863.3	864.4	867.6	873.9	876.1	880.3	885.0
12.5°	835.0	834.4	827.4	827.5	827.4	834.4	835.0	836.7	841.3	850.2	855.9
15°	796.7	786.7	785.6	788.8	785.6	786.7	796.7	796.7	798.8	805.7	808.9
17.5°	758.3	753.1	753.4	751.7	753.4	753.1	758.3	759.2	760.8	766.5	770.7
20°	738.0	734.9	734.4	730.6	734.4	734.9	738.0	738.0	740.1	742.8	747.0
22.5°	719.4	718.4	718.7	714.6	718.7	718.4	719.4	720.7	722.9	724.6	727.6
25°	696.3	698.9	696.8	696.8	696.8	698.9	696.3	696.8	697.3	699.9	702.1
27.5°	680.6	680.5	679.4	679.4	679.4	680.5	680.6	679.3	678.7	677.8	677.3
30°	668.8	668.2	669.3	669.3	669.3	668.2	668.8	666.7	665.6	665.1	663.0
32.5°	656.9	657.7	657.9	658.3	657.9	657.7	656.9	654.4	652.5	651.2	649.4
35°	638.6	639.1	640.8	639.7	640.8	639.1	638.6	635.5	633.4	630.2	627.5
37.5°	613.9	616.3	615.8	616.6	615.8	616.3	613.9	613.0	610.9	608.4	605.3
40°	595.3	596.9	596.3	596.3	596.3	596.9	595.3	594.8	592.7	591.1	588.4
42.5°	576.2	577.4	576.0	575.2	576.0	577.4	576.2	575.3	574.0	571.2	568.2
45°	545.0	544.0	545.6	543.5	545.6	544.0	545.0	543.0	542.4	540.3	537.7
47.5°	510.2	511.2	511.7	513.2	511.7	511.2	510.2	510.4	507.5	506.1	505.3
50°	487.0	490.1	490.1	489.6	490.1	490.1	487.0	485.8	483.7	481.6	481.6
52.5°	464.0	465.5	467.7	467.6	467.7	465.5	464.0	462.2	460.1	457.1	456.3
55°	428.8	429.8	430.9	431.4	430.9	429.8	428.8	424.5	422.9	421.3	418.7
57.5°	392.1	391.7	394.3	395.1	394.3	391.7	392.1	388.4	386.0	381.1	380.4
60°	366.4	366.4	370.6	372.2	370.6	366.4	366.4	362.1	358.4	355.3	354.3
62.5°	338.9	340.6	344.8	342.5	344.8	340.6	338.9	334.3	331.3	327.4	324.6
65°	298.7	303.0	302.5	304.5	302.5	303.0	298.7	296.1	290.2	286.5	283.4
67.5°	256.7	259.3	263.2	263.5	263.2	259.3	256.7	252.5	248.7	244.8	241.0
70°	228.4	231.1	233.2	234.7	233.2	231.1	228.4	224.2	219.9	217.3	213.1
72.5°	200.9	202.3	207.3	205.1	207.3	202.3	200.9	195.8	192.5	190.3	185.6
75°	157.5	161.3	164.4	162.8	164.4	161.3	157.5	153.8	151.2	148.0	143.8
77.5°	116.5	120.2	121.7	120.4	121.7	120.2	116.5	114.1	112.7	106.4	106.0
80°	92.0	91.5	94.6	94.1	94.6	91.5	92.0	88.3	85.6	81.9	81.9
82.5°	67.5	67.0	68.4	68.8	68.4	67.0	67.5	65.4	62.0	60.4	59.1
85°	32.8	34.3	32.2	31.7	32.2	34.3	32.8	30.7	30.7	30.7	30.1
87.5°	14.1	14.4	14.2	13.5	14.2	14.4	14.1	14.4	15.7	14.1	13.9
90°	32.8	34.0	35.2	34.0	35.2	34.0	32.8	34.0	31.7	30.5	29.3
92.5°	61.0	57.5	58.7	56.6	58.7	57.5	61.0	63.1	69.2	78.4	98.8
95°	159.6	149.1	140.8	136.1	140.8	149.1	159.6	181.9	224.1	286.3	422.4
97.5°	465.1	412.3	380.6	370.5	380.6	412.3	465.1	551.7	692.1	843.3	1052.9
100°	865.9	780.2	734.5	735.7	734.5	780.2	865.9	984.4	1151.0	1288.3	1383.3
102.5°	1212.2	1144.5	1106.2	1079.2	1106.2	1144.5	1212.2	1304.4	1410.1	1490.1	1493.2
105°	1580.4	1535.9	1498.3	1492.5	1498.3	1535.9	1580.4	1634.5	1665.0	1642.6	1525.3
107.5°	1768.9	1753.8	1741.2	1730.4	1741.2	1753.8	1768.9	1768.0	1726.2	1623.4	1432.8
110°	1823.3	1832.7	1830.4	1828.1	1830.4	1832.7	1823.3	1790.5	1708.4	1560.5	1344.6



TEST NUMBER: P331993-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1809.3	1838.4	1847.2	1847.8	1847.2	1838.4	1809.3	1749.2	1643.6	1477.9	1257.3
115°	1734.1	1785.7	1809.3	1815.1	1809.3	1785.7	1734.1	1646.2	1518.2	1345.7	1141.7
117.5°	1610.5	1669.6	1703.4	1711.4	1703.4	1669.6	1610.5	1518.7	1389.0	1234.1	1057.8
120°	1524.1	1589.8	1618.0	1625.1	1618.0	1589.8	1524.1	1431.5	1312.9	1172.2	1013.7
122.5°	1445.3	1504.4	1535.4	1544.3	1535.4	1504.4	1445.3	1362.9	1252.8	1122.4	979.0
125°	1342.3	1393.9	1423.2	1431.5	1423.2	1393.9	1342.3	1267.2	1173.3	1060.7	932.8
127.5°	1260.4	1304.4	1331.0	1338.5	1331.0	1304.4	1260.4	1193.5	1108.0	1006.4	892.4
130°	1209.7	1251.9	1276.6	1286.0	1276.6	1251.9	1209.7	1147.5	1067.7	972.7	867.1
132.5°	1163.7	1205.9	1227.8	1234.4	1227.8	1205.9	1163.7	1105.3	1029.3	940.8	843.6
135°	1095.9	1131.0	1152.2	1160.4	1152.2	1131.0	1095.9	1038.3	971.5	895.2	811.9
137.5°	1023.4	1059.0	1076.8	1082.3	1076.8	1059.0	1023.4	975.0	917.1	851.3	783.0
140°	977.3	1010.3	1029.0	1027.8	1029.0	1010.3	977.3	932.8	882.3	826.0	766.2
142.5°	932.3	961.4	978.3	977.1	978.3	961.4	932.3	894.3	850.4	801.6	750.2
145°	870.6	895.2	904.6	907.0	904.6	895.2	870.6	841.2	807.3	769.7	730.9
147.5°	822.7	839.4	848.3	849.2	848.3	839.4	822.7	800.4	776.3	746.0	715.3
150°	795.5	808.4	815.5	815.5	815.5	808.4	795.5	777.9	755.6	730.9	704.0
152.5°	771.1	783.0	787.3	787.3	787.3	783.0	771.1	757.3	738.7	716.9	693.7
155°	739.2	748.6	750.9	752.0	750.9	748.6	739.2	728.6	714.6	696.9	678.1
157.5°	711.2	718.3	720.1	719.9	720.1	718.3	711.2	702.1	691.1	677.5	661.8
160°	693.5	700.4	700.4	699.3	700.4	700.4	693.5	685.2	677.0	665.3	652.4
162.5°	675.6	681.7	681.7	680.5	681.7	681.7	675.6	670.1	662.9	652.2	641.1
165°	652.4	657.0	655.9	655.9	655.9	657.0	652.4	647.6	641.8	633.6	626.5
167.5°	630.3	633.6	632.4	632.4	632.4	633.6	630.3	628.2	624.0	619.2	613.9
170°	617.1	619.6	618.3	618.3	618.3	619.6	617.1	616.0	613.6	608.9	605.4
172.5°	605.9	608.2	606.1	605.2	606.1	608.2	605.9	605.6	604.3	600.5	597.9
175°	591.4	592.5	591.4	590.2	591.4	592.5	591.4	591.4	591.4	589.0	587.8
177.5°	582.4	583.4	581.5	581.5	581.5	583.4	582.4	583.4	583.4	582.4	581.5
180°	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7



TEST NUMBER: P331993-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1046.3	1046.3	1054.4	1059.4	1065.8	1070.1	1073.0	1076.0	1081.1	1087.8	1095.4
5°	986.5	988.7	1000.3	1011.9	1023.0	1032.5	1040.5	1050.0	1061.6	1075.9	1091.8
7.5°	928.6	936.8	948.5	962.6	978.2	992.0	1006.1	1021.8	1038.1	1059.1	1081.4
10°	891.4	900.4	914.6	932.6	949.0	965.3	982.8	999.8	1020.4	1045.2	1073.8
12.5°	858.8	867.4	882.0	901.7	917.3	935.3	955.3	977.3	1000.5	1030.4	1062.8
15°	813.6	823.6	841.6	851.2	874.9	896.7	915.1	946.8	976.4	1007.1	1044.7
17.5°	776.6	782.2	796.8	814.5	832.2	856.6	880.8	907.3	936.8	974.2	1021.2
20°	751.2	756.0	771.8	790.4	809.4	831.6	853.3	879.7	913.0	952.7	1003.4
22.5°	732.3	737.4	747.8	767.5	785.3	803.8	825.4	856.9	892.3	931.1	986.1
25°	704.7	707.9	714.8	730.6	746.5	767.1	786.2	815.8	852.2	897.7	952.7
27.5°	678.6	681.7	687.4	698.8	713.6	730.3	751.0	776.2	813.2	862.6	921.0
30°	663.0	663.5	668.8	679.3	692.1	705.8	724.8	753.4	788.3	838.5	899.8
32.5°	649.4	647.4	651.1	659.0	671.4	685.1	700.7	728.8	762.4	811.8	874.8
35°	626.5	625.4	623.9	630.8	641.3	651.9	665.6	686.8	724.8	770.8	836.9
37.5°	603.1	600.6	597.7	600.9	609.2	620.2	632.1	651.0	683.7	734.4	797.6
40°	585.8	583.7	582.1	581.0	588.4	599.0	607.9	625.9	656.6	704.7	767.1
42.5°	566.7	565.5	563.5	562.0	568.2	576.1	585.5	601.5	632.1	677.2	736.3
45°	536.0	535.0	534.0	532.9	536.6	544.0	551.4	563.0	589.5	633.4	686.8
47.5°	501.9	500.6	501.0	499.3	502.9	507.9	513.0	525.5	550.9	586.3	625.3
50°	477.4	476.9	476.9	476.9	478.0	483.7	488.5	498.1	521.3	556.7	584.7
52.5°	454.1	451.9	451.9	452.7	454.6	458.4	461.4	471.8	492.1	521.2	546.6
55°	417.7	413.4	412.3	413.4	415.1	418.2	421.3	429.8	447.3	469.0	483.7
57.5°	377.3	375.0	373.5	373.8	374.7	377.2	379.6	388.8	402.5	413.8	423.3
60°	348.9	350.0	345.3	346.3	346.3	348.4	352.1	357.9	369.5	377.5	387.0
62.5°	322.2	320.8	319.4	317.9	317.9	318.8	323.8	328.3	338.2	342.3	349.8
65°	280.7	280.7	277.5	278.6	279.1	275.5	278.1	283.4	289.7	291.3	298.2
67.5°	238.6	237.2	235.4	233.8	233.8	233.5	234.8	237.5	242.3	242.8	248.0
70°	209.8	208.8	208.3	206.7	204.6	207.2	205.6	208.3	211.0	211.5	214.6
72.5°	182.0	180.9	180.0	178.3	177.5	177.2	177.3	180.4	182.2	181.5	185.0
75°	142.2	141.2	140.1	137.4	137.4	135.8	136.4	138.6	140.7	139.1	142.2
77.5°	104.4	101.2	101.0	101.7	99.9	100.3	99.6	99.3	100.3	100.4	103.2
80°	80.4	76.6	77.8	77.2	76.6	76.1	75.0	75.6	76.1	76.6	78.3
82.5°	58.0	57.7	56.6	56.5	55.9	54.5	53.9	54.8	55.4	55.1	56.2
85°	29.6	28.0	29.1	28.6	29.1	28.6	27.0	27.0	28.0	27.5	28.6
87.5°	14.5	14.7	13.6	13.3	12.2	11.9	11.0	11.0	10.7	10.2	10.6
90°	28.2	29.3	25.9	22.3	18.8	15.2	12.9	10.6	7.1	4.6	2.3
92.5°	136.1	180.5	198.5	149.1	98.6	67.9	50.5	40.6	31.4	21.6	14.5
95°	564.3	695.8	619.6	427.1	252.3	152.5	106.7	76.2	56.4	43.4	39.9
97.5°	1153.6	1078.2	789.4	468.6	271.6	176.2	126.7	96.6	79.3	69.2	68.1
100°	1342.3	1111.2	750.9	442.3	268.7	186.5	140.8	112.6	96.2	88.0	86.8
102.5°	1351.6	1050.2	694.6	419.8	272.5	198.7	156.7	131.4	115.9	108.7	106.5
105°	1280.1	943.3	625.4	403.6	282.8	219.4	183.0	160.8	146.6	139.7	136.1
107.5°	1154.8	849.0	581.3	402.4	302.1	246.4	212.6	191.7	177.8	171.1	167.5
110°	1075.9	795.5	564.3	407.2	318.0	265.2	232.3	212.4	199.4	193.6	190.1



TEST NUMBER: P331993-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	1007.4	759.8	555.0	416.6	334.0	284.9	253.0	233.0	220.2	214.3	210.8
115°	924.5	721.5	551.5	431.8	360.2	315.6	284.0	264.0	252.3	245.2	240.5
117.5°	874.5	699.0	553.6	451.9	388.1	344.1	314.7	292.4	281.6	275.7	270.3
120°	848.3	688.7	557.3	467.0	406.0	363.8	334.4	312.1	300.3	294.5	290.9
122.5°	826.7	682.2	563.9	481.1	424.7	383.4	352.2	330.8	318.2	312.4	308.8
125°	799.0	673.5	573.7	503.3	451.7	410.6	379.0	356.7	343.8	336.8	334.4
127.5°	774.7	669.2	585.0	521.7	475.1	435.6	403.8	379.2	366.1	357.4	353.9
130°	761.4	666.4	592.5	533.8	489.3	450.5	418.9	394.3	380.1	369.6	366.1
132.5°	749.3	665.5	598.1	545.1	501.5	463.7	432.9	408.3	391.4	379.9	375.5
135°	733.4	664.1	606.6	559.7	519.8	483.4	451.7	427.1	409.5	396.6	391.9
137.5°	719.4	661.5	612.3	570.5	532.4	497.5	468.2	443.7	425.0	412.3	407.4
140°	711.0	660.6	616.0	576.1	540.9	506.9	477.6	454.0	435.3	423.5	417.7
142.5°	703.5	658.7	618.8	581.7	547.4	514.4	487.0	463.4	446.6	433.9	429.0
145°	693.5	655.9	620.7	587.8	556.1	525.6	498.7	478.7	461.1	450.5	447.1
147.5°	683.6	651.5	620.7	591.6	563.2	535.2	512.3	493.0	477.8	467.5	465.3
150°	677.0	647.6	620.7	592.5	567.8	540.9	519.8	503.3	488.1	478.7	477.6
152.5°	669.5	643.0	617.8	594.4	570.7	547.4	527.3	512.7	499.4	490.0	489.8
155°	658.2	634.8	614.8	594.9	576.1	556.1	539.7	526.8	515.1	508.1	508.1
157.5°	645.5	627.5	610.9	596.0	579.2	563.2	550.5	539.5	529.2	523.5	522.6
160°	637.1	621.9	608.9	596.0	582.0	567.8	556.1	548.0	538.6	533.8	533.8
162.5°	628.6	616.2	605.2	595.1	582.9	570.7	560.9	553.6	546.0	542.3	542.3
165°	617.1	607.7	599.6	592.5	584.3	574.9	566.7	562.0	556.1	553.8	555.0
167.5°	606.1	599.4	593.9	590.7	584.1	577.2	572.1	568.9	564.3	563.2	564.6
170°	599.6	593.7	590.2	587.8	583.1	577.2	574.9	572.6	569.1	567.8	570.3
172.5°	593.0	589.0	587.3	586.9	583.1	578.2	576.8	575.4	572.8	572.6	574.0
175°	585.5	583.1	583.1	584.3	582.0	579.7	578.5	578.5	576.1	577.2	578.5
177.5°	580.6	579.7	580.6	582.4	580.6	579.7	579.7	579.7	578.7	579.7	580.6
180°	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7



TEST NUMBER: P331993-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1097.9	1100.0	1107.3	1112.4	1118.2	1121.7	1125.0	1127.6	1130.9	1131.8	1144.1
5°	1102.9	1113.4	1132.0	1145.7	1162.6	1181.0	1193.8	1199.6	1214.9	1227.6	1252.9
7.5°	1101.5	1124.0	1151.9	1180.8	1211.9	1240.7	1265.7	1295.3	1316.4	1348.0	1379.1
10°	1100.1	1130.3	1166.3	1203.3	1246.7	1286.8	1322.7	1362.9	1396.2	1440.2	1477.6
12.5°	1096.4	1132.9	1182.8	1226.6	1279.2	1334.6	1387.9	1439.5	1468.9	1542.1	1576.6
15°	1087.0	1130.3	1192.8	1259.3	1331.7	1397.4	1465.0	1518.9	1606.1	1670.1	1710.8
17.5°	1069.0	1129.7	1203.7	1284.0	1372.1	1458.5	1535.2	1617.0	1709.5	1787.0	1869.5
20°	1060.6	1127.1	1209.6	1298.5	1389.9	1487.7	1575.0	1673.2	1774.2	1850.4	1956.1
22.5°	1044.9	1120.3	1209.2	1308.2	1405.9	1507.1	1609.2	1708.4	1825.0	1930.0	2030.5
25°	1019.3	1103.9	1195.9	1306.4	1421.1	1522.6	1644.8	1776.4	1897.9	2032.8	2133.2
27.5°	992.4	1082.8	1175.0	1277.7	1401.1	1521.6	1675.2	1823.9	1972.7	2089.0	2163.3
30°	971.7	1059.4	1154.7	1258.3	1380.4	1523.7	1695.5	1857.7	2002.7	2102.5	2144.3
32.5°	949.3	1038.3	1122.5	1231.2	1361.4	1522.4	1708.2	1877.6	2004.4	2070.8	2062.8
35°	914.1	988.7	1070.6	1175.3	1328.6	1513.1	1715.6	1879.5	1957.2	1942.9	1835.0
37.5°	863.3	926.0	1006.7	1121.4	1290.5	1493.5	1700.8	1823.7	1818.7	1702.4	1546.2
40°	831.6	885.0	962.7	1083.3	1260.9	1480.9	1677.5	1757.4	1689.7	1527.3	1340.2
42.5°	790.2	839.3	917.1	1041.0	1228.3	1455.0	1633.1	1656.3	1523.9	1337.1	1165.5
45°	725.9	769.2	849.6	977.5	1179.5	1398.9	1524.7	1468.1	1290.0	1097.0	966.4
47.5°	656.8	701.9	779.2	910.6	1108.8	1314.4	1374.3	1254.1	1071.1	914.6	794.8
50°	613.3	656.6	732.3	864.9	1061.1	1245.1	1269.9	1114.5	946.3	808.9	710.5
52.5°	569.3	610.1	684.4	817.6	1005.2	1164.7	1149.3	991.0	836.4	719.2	642.1
55°	503.8	542.4	613.3	738.0	908.8	1035.1	979.7	828.5	700.5	609.6	550.9
57.5°	445.2	482.3	543.4	656.1	804.6	891.4	820.7	693.3	591.6	521.6	477.9
60°	405.5	438.3	496.4	601.1	730.1	796.2	726.4	613.8	528.2	472.1	433.0
62.5°	367.9	396.4	450.3	545.3	657.3	712.9	642.3	546.9	474.0	424.3	391.1
65°	310.8	336.8	384.4	458.4	550.4	587.3	526.5	449.4	392.8	355.8	333.6
67.5°	258.8	280.8	321.9	380.2	447.9	474.8	428.6	368.8	326.2	296.5	278.8
70°	224.2	243.2	275.5	325.7	387.0	407.6	364.3	315.1	283.9	260.1	243.7
72.5°	195.0	208.9	238.2	277.0	328.2	344.6	314.4	271.1	242.1	224.2	211.2
75°	148.6	160.2	179.3	210.5	245.8	255.4	232.6	205.6	186.1	173.4	163.4
77.5°	107.1	115.6	129.5	148.7	173.2	181.8	167.3	149.4	135.1	126.5	121.0
80°	80.9	87.8	99.4	115.2	130.1	134.8	126.3	112.6	102.6	97.9	93.0
82.5°	59.8	63.6	70.6	81.4	91.6	97.1	90.0	81.7	76.3	72.0	70.2
85°	30.1	32.2	35.4	39.7	45.9	48.1	45.4	43.3	40.2	37.6	37.6
87.5°	11.9	12.4	14.3	15.7	17.9	19.8	20.1	20.0	20.2	19.6	19.4
90°	4.6	7.1	10.6	12.9	15.2	18.8	22.3	25.9	29.3	28.2	29.3
92.5°	21.6	31.4	40.6	50.5	67.9	98.6	149.1	198.5	180.5	136.1	98.8
95°	43.4	56.4	76.2	106.7	152.5	252.3	427.1	619.6	695.8	564.3	422.4
97.5°	69.2	79.3	96.6	126.7	176.2	271.6	468.6	789.4	1078.2	1153.6	1052.9
100°	88.0	96.2	112.6	140.8	186.5	268.7	442.3	750.9	1111.2	1342.3	1383.3
102.5°	108.7	115.9	131.4	156.7	198.7	272.5	419.8	694.6	1050.2	1351.6	1493.2
105°	139.7	146.6	160.8	183.0	219.4	282.8	403.6	625.4	943.3	1280.1	1525.3
107.5°	171.1	177.8	191.7	212.6	246.4	302.1	402.4	581.3	849.0	1154.8	1432.8
110°	193.6	199.4	212.4	232.3	265.2	318.0	407.2	564.3	795.5	1075.9	1344.6



TEST NUMBER: P331993-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	214.3	220.2	233.0	253.0	284.9	334.0	416.6	555.0	759.8	1007.4	1257.3
115°	245.2	252.3	264.0	284.0	315.6	360.2	431.8	551.5	721.5	924.5	1141.7
117.5°	275.7	281.6	292.4	314.7	344.1	388.1	451.9	553.6	699.0	874.5	1057.8
120°	294.5	300.3	312.1	334.4	363.8	406.0	467.0	557.3	688.7	848.3	1013.7
122.5°	312.4	318.2	330.8	352.2	383.4	424.7	481.1	563.9	682.2	826.7	979.0
125°	336.8	343.8	356.7	379.0	410.6	451.7	503.3	573.7	673.5	799.0	932.8
127.5°	357.4	366.1	379.2	403.8	435.6	475.1	521.7	585.0	669.2	774.7	892.4
130°	369.6	380.1	394.3	418.9	450.5	489.3	533.8	592.5	666.4	761.4	867.1
132.5°	379.9	391.4	408.3	432.9	463.7	501.5	545.1	598.1	665.5	749.3	843.6
135°	396.6	409.5	427.1	451.7	483.4	519.8	559.7	606.6	664.1	733.4	811.9
137.5°	412.3	425.0	443.7	468.2	497.5	532.4	570.5	612.3	661.5	719.4	783.0
140°	423.5	435.3	454.0	477.6	506.9	540.9	576.1	616.0	660.6	711.0	766.2
142.5°	433.9	446.6	463.4	487.0	514.4	547.4	581.7	618.8	658.7	703.5	750.2
145°	450.5	461.1	478.7	498.7	525.6	556.1	587.8	620.7	655.9	693.5	730.9
147.5°	467.5	477.8	493.0	512.3	535.2	563.2	591.6	620.7	651.5	683.6	715.3
150°	478.7	488.1	503.3	519.8	540.9	567.8	592.5	620.7	647.6	677.0	704.0
152.5°	490.0	499.4	512.7	527.3	547.4	570.7	594.4	617.8	643.0	669.5	693.7
155°	508.1	515.1	526.8	539.7	556.1	576.1	594.9	614.8	634.8	658.2	678.1
157.5°	523.5	529.2	539.5	550.5	563.2	579.2	596.0	610.9	627.5	645.5	661.8
160°	533.8	538.6	548.0	556.1	567.8	582.0	596.0	608.9	621.9	637.1	652.4
162.5°	542.3	546.0	553.6	560.9	570.7	582.9	595.1	605.2	616.2	628.6	641.1
165°	553.8	556.1	562.0	566.7	574.9	584.3	592.5	599.6	607.7	617.1	626.5
167.5°	563.2	564.3	568.9	572.1	577.2	584.1	590.7	593.9	599.4	606.1	613.9
170°	567.8	569.1	572.6	574.9	577.2	583.1	587.8	590.2	593.7	599.6	605.4
172.5°	572.6	572.8	575.4	576.8	578.2	583.1	586.9	587.3	589.0	593.0	597.9
175°	577.2	576.1	578.5	578.5	579.7	582.0	584.3	583.1	583.1	585.5	587.8
177.5°	579.7	578.7	579.7	579.7	579.7	580.6	582.4	580.6	579.7	580.6	581.5
180°	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7



TEST NUMBER: P331993-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1148.3	1148.7	1153.4	1156.8	1155.1	1157.2	1158.0
5°	1254.6	1273.6	1283.6	1291.0	1291.6	1292.1	1296.4
7.5°	1405.2	1425.6	1440.6	1463.2	1470.0	1477.6	1475.4
10°	1515.2	1545.3	1571.2	1585.0	1599.8	1621.4	1604.1
12.5°	1618.0	1671.4	1710.8	1732.2	1746.2	1750.5	1741.9
15°	1787.5	1857.2	1894.8	1893.7	1941.4	1962.0	1929.7
17.5°	1942.9	2007.3	2058.9	2085.4	2125.0	2133.7	2129.7
20°	2038.1	2108.4	2148.6	2194.0	2214.6	2233.1	2236.3
22.5°	2120.1	2183.2	2226.3	2264.2	2281.5	2290.3	2295.5
25°	2204.6	2254.3	2280.2	2293.4	2298.1	2297.1	2290.3
27.5°	2198.8	2202.6	2174.0	2146.1	2121.0	2092.7	2083.0
30°	2141.7	2097.3	2018.0	1973.1	1906.9	1854.6	1875.7
32.5°	1991.6	1903.2	1814.1	1715.9	1634.6	1611.4	1588.1
35°	1699.7	1544.3	1453.4	1347.6	1305.4	1263.0	1234.0
37.5°	1375.1	1254.9	1147.0	1077.8	1035.5	1008.8	994.3
40°	1189.0	1080.7	991.8	935.7	903.5	873.4	869.2
42.5°	1040.6	939.8	872.9	828.3	797.4	784.6	775.3
45°	852.2	781.9	737.0	705.3	684.7	676.7	666.1
47.5°	721.3	671.7	637.9	616.3	600.8	594.9	594.0
50°	648.1	606.9	582.1	565.1	553.0	550.9	542.4
52.5°	593.2	557.4	538.1	523.3	514.5	508.6	506.0
55°	514.9	491.1	473.7	465.2	458.4	452.5	452.5
57.5°	450.5	430.7	419.1	411.9	409.8	405.7	403.0
60°	410.8	393.8	384.9	378.5	374.4	374.9	370.1
62.5°	371.8	360.9	352.3	346.0	340.9	341.0	341.3
65°	316.7	308.2	301.8	299.7	296.6	292.9	294.0
67.5°	268.3	260.4	255.5	251.9	250.9	248.8	251.9
70°	233.7	227.8	224.2	221.0	219.9	220.5	223.1
72.5°	202.0	197.8	195.4	193.9	191.6	191.7	193.5
75°	158.6	155.4	153.3	151.7	151.2	151.2	151.2
77.5°	116.5	115.8	114.8	112.5	112.6	113.2	113.3
80°	92.0	90.4	89.9	88.9	87.3	86.1	88.9
82.5°	68.8	67.2	66.7	66.4	63.9	63.7	65.9
85°	37.0	35.4	36.0	35.4	35.4	34.9	34.9
87.5°	19.2	19.0	19.1	19.3	19.1	18.9	19.5
90°	30.5	31.7	34.0	32.8	34.0	35.2	34.0
92.5°	78.4	69.2	63.1	61.0	57.5	58.7	56.6
95°	286.3	224.1	181.9	159.6	149.1	140.8	136.1
97.5°	843.3	692.1	551.7	465.1	412.3	380.6	370.5
100°	1288.3	1151.0	984.4	865.9	780.2	734.5	735.7
102.5°	1490.1	1410.1	1304.4	1212.2	1144.5	1106.2	1079.2
105°	1642.6	1665.0	1634.5	1580.4	1535.9	1498.3	1492.5
107.5°	1623.4	1726.2	1768.0	1768.9	1753.8	1741.2	1730.4
110°	1560.5	1708.4	1790.5	1823.3	1832.7	1830.4	1828.1



TEST NUMBER: P331993-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1477.9	1643.6	1749.2	1809.3	1838.4	1847.2	1847.8
115°	1345.7	1518.2	1646.2	1734.1	1785.7	1809.3	1815.1
117.5°	1234.1	1389.0	1518.7	1610.5	1669.6	1703.4	1711.4
120°	1172.2	1312.9	1431.5	1524.1	1589.8	1618.0	1625.1
122.5°	1122.4	1252.8	1362.9	1445.3	1504.4	1535.4	1544.3
125°	1060.7	1173.3	1267.2	1342.3	1393.9	1423.2	1431.5
127.5°	1006.4	1108.0	1193.5	1260.4	1304.4	1331.0	1338.5
130°	972.7	1067.7	1147.5	1209.7	1251.9	1276.6	1286.0
132.5°	940.8	1029.3	1105.3	1163.7	1205.9	1227.8	1234.4
135°	895.2	971.5	1038.3	1095.9	1131.0	1152.2	1160.4
137.5°	851.3	917.1	975.0	1023.4	1059.0	1076.8	1082.3
140°	826.0	882.3	932.8	977.3	1010.3	1029.0	1027.8
142.5°	801.6	850.4	894.3	932.3	961.4	978.3	977.1
145°	769.7	807.3	841.2	870.6	895.2	904.6	907.0
147.5°	746.0	776.3	800.4	822.7	839.4	848.3	849.2
150°	730.9	755.6	777.9	795.5	808.4	815.5	815.5
152.5°	716.9	738.7	757.3	771.1	783.0	787.3	787.3
155°	696.9	714.6	728.6	739.2	748.6	750.9	752.0
157.5°	677.5	691.1	702.1	711.2	718.3	720.1	719.9
160°	665.3	677.0	685.2	693.5	700.4	700.4	699.3
162.5°	652.2	662.9	670.1	675.6	681.7	681.7	680.5
165°	633.6	641.8	647.6	652.4	657.0	655.9	655.9
167.5°	619.2	624.0	628.2	630.3	633.6	632.4	632.4
170°	608.9	613.6	616.0	617.1	619.6	618.3	618.3
172.5°	600.5	604.3	605.6	605.9	608.2	606.1	605.2
175°	589.0	591.4	591.4	591.4	592.5	591.4	590.2
177.5°	582.4	583.4	583.4	582.4	583.4	581.5	581.5
180°	579.7	579.7	579.7	579.7	579.7	579.7	579.7

(END OF REPORT)