

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331957-840

Luminaire Tested: **S123DIP-S775D365U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331957-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S775D365U840-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4621.2 lumens  
Efficiency: N/A  
Efficacy: 132.0 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331957-840  
CATALOG NUMBER: S123DIP-S775D365U840-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331957-840

CATALOG NUMBER: S123DIP-S775D365U840-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	71
1	103	99	95	91	97	94	90	87	84	82	79	76	74	72	68	66	65	61
2	94	87	80	75	89	82	77	72	74	70	66	67	63	61	60	57	55	52
3	86	76	69	63	81	73	66	61	66	60	56	59	55	52	53	50	47	44
4	79	68	60	54	75	65	58	52	59	53	48	53	48	45	48	44	41	38
5	73	61	53	46	69	58	51	45	53	47	42	48	43	39	43	39	36	33
6	67	55	46	41	63	52	45	39	48	41	37	43	38	34	39	35	32	29
7	62	50	41	36	59	47	40	35	43	37	33	40	34	30	36	32	28	26
8	58	45	37	32	55	43	36	31	40	33	29	36	31	27	33	29	25	23
9	54	41	34	29	51	40	33	28	36	30	26	33	28	25	31	26	23	21
10	50	38	31	26	48	37	30	25	34	28	24	31	26	22	28	24	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	11746	11746	11746	11746
5°	14008	11797	10454	11797
10°	17533	11737	9441	11737
15°	21504	11642	8790	11642
20°	25616	11494	8369	11494
25°	27201	11315	8276	11315
30°	23313	11184	8319	11184
35°	16215	10997	8406	10997
40°	12213	10779	8379	10779
45°	10140	10455	8273	10455
50°	9083	9791	8199	9791
55°	8492	9077	8096	9077
60°	7967	8331	8013	8331
65°	7488	7595	7755	7595
70°	7021	6754	7386	6754
75°	6288	5914	6771	5914
80°	5511	4854	5833	4854
85°	4310	3532	3915	3532



TEST NUMBER: P331957-840

CATALOG NUMBER: S123DIP-S775D365U840-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	107.5	2.3
10°-20°	344.7	7.5
20°-30°	578.5	12.5
30°-40°	655.0	14.2
40°-50°	587.4	12.7
50°-60°	474.0	10.3
60°-70°	330.3	7.1
70°-80°	173.6	3.8
80°-90°	43.8	0.9
90°-100°	98.1	2.1
100°-110°	277.8	6.0
110°-120°	273.3	5.9
120°-130°	218.0	4.7
130°-140°	171.9	3.7
140°-150°	128.3	2.8
150°-160°	89.4	1.9
160°-170°	52.5	1.1
170°-180°	17.1	0.4
0°-30°	1030.6	22.3
0°-40°	1685.7	36.5
0°-60°	2747.1	59.4
0°-90°	3294.8	71.3
90°-120°	649.2	14.0
90°-150°	1167.3	25.3
90°-180°	1326.0	28.7
0°-180°	4621.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1091	1091	1091	1091	1091	
5°	1296	1092	968	1092	1296	134
15°	1930	1045	789	1045	1930	557
25°	2290	953	697	953	2290	1004
35°	1234	837	640	837	1234	802
45°	666	687	544	687	666	527
55°	452	484	431	484	452	406
65°	294	298	304	298	294	293
75°	151	142	163	142	151	162
85°	35	29	32	29	35	41
90°	10	1	10	1	10	7
95°	41	12	41	12	41	75
105°	454	41	454	41	454	448
115°	552	73	552	73	552	536
125°	435	102	435	102	435	395
135°	353	119	353	119	353	274
145°	276	136	276	136	276	175
155°	229	154	229	154	229	107
165°	199	169	199	169	199	57
175°	180	176	180	176	180	17
180°	176	176	176	176	176	



TEST NUMBER: P331957-840

CATALOG NUMBER: S123DIP-S775D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1158.0	1157.2	1155.1	1156.8	1153.4	1148.7	1148.3	1144.1	1131.8	1130.9	1127.6
5°	1296.4	1292.1	1291.6	1291.0	1283.6	1273.6	1254.6	1252.9	1227.6	1214.9	1199.6
7.5°	1475.4	1477.6	1470.0	1463.2	1440.6	1425.6	1405.2	1379.1	1348.0	1316.4	1295.3
10°	1604.1	1621.4	1599.8	1585.0	1571.2	1545.3	1515.2	1477.6	1440.2	1396.2	1362.9
12.5°	1741.9	1750.5	1746.2	1732.2	1710.8	1671.4	1618.0	1576.6	1542.1	1468.9	1439.5
15°	1929.7	1962.0	1941.4	1893.7	1894.8	1857.2	1787.5	1710.8	1670.1	1606.1	1518.9
17.5°	2129.7	2133.7	2125.0	2085.4	2058.9	2007.3	1942.9	1869.5	1787.0	1709.5	1617.0
20°	2236.3	2233.1	2214.6	2194.0	2148.6	2108.4	2038.1	1956.1	1850.4	1774.2	1673.2
22.5°	2295.5	2290.3	2281.5	2264.2	2226.3	2183.2	2120.1	2030.5	1930.0	1825.0	1708.4
25°	2290.3	2297.1	2298.1	2293.4	2280.2	2254.3	2204.6	2133.2	2032.8	1897.9	1776.4
27.5°	2083.0	2092.7	2121.0	2146.1	2174.0	2202.6	2198.8	2163.3	2089.0	1972.7	1823.9
30°	1875.7	1854.6	1906.9	1973.1	2018.0	2097.3	2141.7	2144.3	2102.5	2002.7	1857.7
32.5°	1588.1	1611.4	1634.6	1715.9	1814.1	1903.2	1991.6	2062.8	2070.8	2004.4	1877.6
35°	1234.0	1263.0	1305.4	1347.6	1453.4	1544.3	1699.7	1835.0	1942.9	1957.2	1879.5
37.5°	994.3	1008.8	1035.5	1077.8	1147.0	1254.9	1375.1	1546.2	1702.4	1818.7	1823.7
40°	869.2	873.4	903.5	935.7	991.8	1080.7	1189.0	1340.2	1527.3	1689.7	1757.4
42.5°	775.3	784.6	797.4	828.3	872.9	939.8	1040.6	1165.5	1337.1	1523.9	1656.3
45°	666.1	676.7	684.7	705.3	737.0	781.9	852.2	966.4	1097.0	1290.0	1468.1
47.5°	594.0	594.9	600.8	616.3	637.9	671.7	721.3	794.8	914.6	1071.1	1254.1
50°	542.4	550.9	553.0	565.1	582.1	606.9	648.1	710.5	808.9	946.3	1114.5
52.5°	506.0	508.6	514.5	523.3	538.1	557.4	593.2	642.1	719.2	836.4	991.0
55°	452.5	452.5	458.4	465.2	473.7	491.1	514.9	550.9	609.6	700.5	828.5
57.5°	403.0	405.7	409.8	411.9	419.1	430.7	450.5	477.9	521.6	591.6	693.3
60°	370.1	374.9	374.4	378.5	384.9	393.8	410.8	433.0	472.1	528.2	613.8
62.5°	341.3	341.0	340.9	346.0	352.3	360.9	371.8	391.1	424.3	474.0	546.9
65°	294.0	292.9	296.6	299.7	301.8	308.2	316.7	333.6	355.8	392.8	449.4
67.5°	251.9	248.8	250.9	251.9	255.5	260.4	268.3	278.8	296.5	326.2	368.8
70°	223.1	220.5	219.9	221.0	224.2	227.8	233.7	243.7	260.1	283.9	315.1
72.5°	193.5	191.7	191.6	193.9	195.4	197.8	202.0	211.2	224.2	242.1	271.1
75°	151.2	151.2	151.2	151.7	153.3	155.4	158.6	163.4	173.4	186.1	205.6
77.5°	113.3	113.2	112.6	112.5	114.8	115.8	116.5	121.0	126.5	135.1	149.4
80°	88.9	86.1	87.3	88.9	89.9	90.4	92.0	93.0	97.9	102.6	112.6
82.5°	65.9	63.7	63.9	66.4	66.7	67.2	68.8	70.2	72.0	76.3	81.7
85°	34.9	34.9	35.4	35.4	36.0	35.4	37.0	37.6	37.6	40.2	43.3
87.5°	14.7	13.9	14.3	14.6	14.3	14.6	14.9	15.3	15.7	16.2	16.4
90°	10.3	10.7	10.3	10.0	10.3	9.6	9.3	8.9	8.6	8.9	7.9
92.5°	17.2	17.9	17.5	18.6	19.2	21.0	23.8	30.1	41.4	54.8	60.4
95°	41.4	42.8	45.3	48.6	55.3	68.2	87.1	128.5	171.7	211.7	188.4
97.5°	112.7	115.7	125.4	141.5	167.8	210.5	256.5	320.2	350.8	328.0	240.1
100°	223.8	223.4	237.3	263.4	299.4	350.1	391.8	420.7	408.3	338.0	228.4
102.5°	328.2	336.5	348.1	368.7	396.8	428.9	453.2	454.1	411.1	319.4	211.3
105°	453.9	455.8	467.2	480.7	497.2	506.3	499.6	463.9	389.3	286.9	190.3
107.5°	526.3	529.6	533.4	538.1	537.8	525.0	493.7	435.8	351.2	258.2	176.8
110°	556.0	556.7	557.4	554.6	544.6	519.6	474.6	409.0	327.3	242.0	171.7



TEST NUMBER: P331957-840

CATALOG NUMBER: S123DIP-S775D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	562.0	561.9	559.2	550.3	532.0	499.9	449.5	382.4	306.4	231.1	168.7
115°	552.1	550.3	543.1	527.5	500.7	461.8	409.3	347.2	281.2	219.4	167.7
117.5°	520.5	518.1	507.9	489.9	461.9	422.4	375.4	321.7	266.0	212.6	168.3
120°	494.2	492.1	483.5	463.5	435.4	399.3	356.5	308.3	258.0	209.4	169.6
122.5°	469.7	467.0	457.6	439.6	414.5	381.0	341.3	297.8	251.5	207.5	171.5
125°	435.4	432.9	423.9	408.3	385.5	356.9	322.7	283.7	243.1	204.8	174.5
127.5°	407.1	404.9	396.8	383.3	363.0	337.0	306.1	271.5	235.6	203.6	177.9
130°	391.1	388.3	380.8	367.9	349.0	324.8	295.9	263.7	231.6	202.7	180.3
132.5°	375.5	373.4	366.8	354.0	336.2	313.1	286.1	256.6	227.9	202.4	182.0
135°	352.9	350.4	344.1	333.4	315.8	295.5	272.3	246.9	223.1	202.0	184.5
137.5°	329.2	327.5	322.1	311.2	296.6	278.9	258.9	238.1	218.8	201.2	186.2
140°	312.7	313.0	307.3	297.3	283.7	268.3	251.3	233.1	216.2	201.0	187.3
142.5°	297.2	297.5	292.5	283.6	272.0	258.6	243.8	228.2	214.0	200.4	188.2
145°	275.9	275.2	272.3	264.8	255.9	245.5	234.1	222.4	210.9	199.4	188.7
147.5°	258.3	258.0	255.3	250.2	243.5	236.1	226.9	217.5	207.9	198.1	188.7
150°	248.0	248.0	245.9	242.0	236.6	229.8	222.4	214.1	205.9	197.0	188.7
152.5°	239.4	239.4	238.1	234.5	230.4	224.7	218.0	211.0	203.6	195.6	187.9
155°	228.7	228.4	227.7	224.8	221.6	217.3	212.0	206.3	200.2	193.1	187.0
157.5°	218.9	219.0	218.4	216.3	213.6	210.2	206.0	201.3	196.3	190.9	185.8
160°	212.7	213.1	213.1	210.9	208.4	205.9	202.4	198.4	193.8	189.1	185.2
162.5°	207.0	207.3	207.3	205.5	203.9	201.7	198.3	195.0	191.2	187.4	184.1
165°	199.4	199.4	199.9	198.4	197.0	195.2	192.7	190.6	187.7	184.9	182.4
167.5°	192.4	192.4	192.7	191.7	191.1	189.8	188.3	186.7	184.4	182.3	180.7
170°	188.0	188.0	188.4	187.7	187.3	186.6	185.2	184.1	182.4	180.6	179.6
172.5°	184.1	184.4	185.0	184.3	184.2	183.8	182.7	181.9	180.4	179.2	178.6
175°	179.6	179.9	180.3	179.9	179.9	179.9	179.2	178.7	178.0	177.3	177.3
177.5°	176.8	176.8	177.4	177.1	177.4	177.4	177.1	176.8	176.6	176.3	176.6
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3



TEST NUMBER: P331957-840

CATALOG NUMBER: S123DIP-S775D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1125.0	1121.7	1118.2	1112.4	1107.3	1100.0	1097.9	1095.4	1087.8	1081.1	1076.0
5°	1193.8	1181.0	1162.6	1145.7	1132.0	1113.4	1102.9	1091.8	1075.9	1061.6	1050.0
7.5°	1265.7	1240.7	1211.9	1180.8	1151.9	1124.0	1101.5	1081.4	1059.1	1038.1	1021.8
10°	1322.7	1286.8	1246.7	1203.3	1166.3	1130.3	1100.1	1073.8	1045.2	1020.4	999.8
12.5°	1387.9	1334.6	1279.2	1226.6	1182.8	1132.9	1096.4	1062.8	1030.4	1000.5	977.3
15°	1465.0	1397.4	1331.7	1259.3	1192.8	1130.3	1087.0	1044.7	1007.1	976.4	946.8
17.5°	1535.2	1458.5	1372.1	1284.0	1203.7	1129.7	1069.0	1021.2	974.2	936.8	907.3
20°	1575.0	1487.7	1389.9	1298.5	1209.6	1127.1	1060.6	1003.4	952.7	913.0	879.7
22.5°	1609.2	1507.1	1405.9	1308.2	1209.2	1120.3	1044.9	986.1	931.1	892.3	856.9
25°	1644.8	1522.6	1421.1	1306.4	1195.9	1103.9	1019.3	952.7	897.7	852.2	815.8
27.5°	1675.2	1521.6	1401.1	1277.7	1175.0	1082.8	992.4	921.0	862.6	813.2	776.2
30°	1695.5	1523.7	1380.4	1258.3	1154.7	1059.4	971.7	899.8	838.5	788.3	753.4
32.5°	1708.2	1522.4	1361.4	1231.2	1122.5	1038.3	949.3	874.8	811.8	762.4	728.8
35°	1715.6	1513.1	1328.6	1175.3	1070.6	988.7	914.1	836.9	770.8	724.8	686.8
37.5°	1700.8	1493.5	1290.5	1121.4	1006.7	926.0	863.3	797.6	734.4	683.7	651.0
40°	1677.5	1480.9	1260.9	1083.3	962.7	885.0	831.6	767.1	704.7	656.6	625.9
42.5°	1633.1	1455.0	1228.3	1041.0	917.1	839.3	790.2	736.3	677.2	632.1	601.5
45°	1524.7	1398.9	1179.5	977.5	849.6	769.2	725.9	686.8	633.4	589.5	563.0
47.5°	1374.3	1314.4	1108.8	910.6	779.2	701.9	656.8	625.3	586.3	550.9	525.5
50°	1269.9	1245.1	1061.1	864.9	732.3	656.6	613.3	584.7	556.7	521.3	498.1
52.5°	1149.3	1164.7	1005.2	817.6	684.4	610.1	569.3	546.6	521.2	492.1	471.8
55°	979.7	1035.1	908.8	738.0	613.3	542.4	503.8	483.7	469.0	447.3	429.8
57.5°	820.7	891.4	804.6	656.1	543.4	482.3	445.2	423.3	413.8	402.5	388.8
60°	726.4	796.2	730.1	601.1	496.4	438.3	405.5	387.0	377.5	369.5	357.9
62.5°	642.3	712.9	657.3	545.3	450.3	396.4	367.9	349.8	342.3	338.2	328.3
65°	526.5	587.3	550.4	458.4	384.4	336.8	310.8	298.2	291.3	289.7	283.4
67.5°	428.6	474.8	447.9	380.2	321.9	280.8	258.8	248.0	242.8	242.3	237.5
70°	364.3	407.6	387.0	325.7	275.5	243.2	224.2	214.6	211.5	211.0	208.3
72.5°	314.4	344.6	328.2	277.0	238.2	208.9	195.0	185.0	181.5	182.2	180.4
75°	232.6	255.4	245.8	210.5	179.3	160.2	148.6	142.2	139.1	140.7	138.6
77.5°	167.3	181.8	173.2	148.7	129.5	115.6	107.1	103.2	100.4	100.3	99.3
80°	126.3	134.8	130.1	115.2	99.4	87.8	80.9	78.3	76.6	76.1	75.6
82.5°	90.0	97.1	91.6	81.4	70.6	63.6	59.8	56.2	55.1	55.4	54.8
85°	45.4	48.1	45.9	39.7	35.4	32.2	30.1	28.6	27.5	28.0	27.0
87.5°	17.0	17.2	15.8	13.9	12.9	11.4	11.3	10.3	9.6	9.7	9.5
90°	6.8	5.8	4.6	3.9	3.2	2.1	1.4	0.7	1.4	2.1	3.2
92.5°	45.3	30.0	20.6	15.3	12.3	9.6	6.6	4.4	6.6	9.6	12.3
95°	129.9	76.7	46.4	32.5	23.2	17.2	13.2	12.1	13.2	17.2	23.2
97.5°	142.5	82.6	53.6	38.6	29.4	24.1	21.0	20.7	21.0	24.1	29.4
100°	134.5	81.7	56.8	42.8	34.2	29.3	26.8	26.5	26.8	29.3	34.2
102.5°	127.6	82.9	60.5	47.7	40.0	35.2	33.0	32.4	33.0	35.2	40.0
105°	122.8	86.0	66.8	55.6	48.9	44.6	42.5	41.4	42.5	44.6	48.9
107.5°	122.4	91.9	74.9	64.6	58.3	54.1	52.0	51.0	52.0	54.1	58.3
110°	123.8	96.7	80.7	70.7	64.6	60.7	58.9	57.8	58.9	60.7	64.6





TEST NUMBER: P331957-840

CATALOG NUMBER: S123DIP-S775D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	126.7	101.6	86.6	77.0	70.9	67.0	65.1	64.1	65.1	67.0	70.9
115°	131.3	109.6	96.0	86.3	80.3	76.7	74.6	73.1	74.6	76.7	80.3
117.5°	137.4	118.1	104.6	95.7	89.0	85.6	83.8	82.2	83.8	85.6	89.0
120°	142.0	123.5	110.6	101.7	94.9	91.4	89.6	88.5	89.6	91.4	94.9
122.5°	146.3	129.2	116.6	107.1	100.7	96.7	95.0	93.9	95.0	96.7	100.7
125°	153.1	137.4	124.9	115.2	108.5	104.5	102.4	101.7	102.4	104.5	108.5
127.5°	158.6	144.5	132.5	122.8	115.3	111.4	108.7	107.7	108.7	111.4	115.3
130°	162.4	148.9	137.0	127.4	119.9	115.6	112.4	111.4	112.4	115.6	119.9
132.5°	165.8	152.5	141.1	131.7	124.2	119.1	115.5	114.2	115.5	119.1	124.2
135°	170.3	158.0	147.0	137.4	129.9	124.5	120.6	119.2	120.6	124.5	129.9
137.5°	173.5	162.0	151.3	142.4	134.9	129.3	125.4	123.9	125.4	129.3	134.9
140°	175.2	164.5	154.2	145.2	138.1	132.4	128.9	127.0	128.9	132.4	138.1
142.5°	176.9	166.5	156.4	148.1	141.0	135.8	132.0	130.5	132.0	135.8	141.0
145°	178.7	169.2	159.9	151.7	145.6	140.3	137.0	135.9	137.0	140.3	145.6
147.5°	180.0	171.3	162.8	155.8	150.0	145.3	142.2	141.6	142.2	145.3	150.0
150°	180.3	172.7	164.5	158.0	153.1	148.5	145.6	145.2	145.6	148.5	153.1
152.5°	180.8	173.6	166.5	160.4	155.9	151.9	149.1	149.0	149.1	151.9	155.9
155°	181.0	175.2	169.2	164.2	160.3	156.6	154.5	154.5	154.5	156.6	160.3
157.5°	181.3	176.1	171.3	167.4	164.1	161.0	159.3	159.0	159.3	161.0	164.1
160°	181.3	177.0	172.7	169.2	166.6	163.8	162.4	162.4	162.4	163.8	166.6
162.5°	181.0	177.3	173.6	170.6	168.3	166.1	164.9	164.9	164.9	166.1	168.3
165°	180.3	177.7	174.9	172.4	171.0	169.2	168.4	168.7	168.4	169.2	171.0
167.5°	179.7	177.6	175.6	174.0	173.0	171.7	171.3	171.7	171.3	171.7	173.0
170°	178.7	177.3	175.6	174.9	174.1	173.1	172.7	173.4	172.7	173.1	174.1
172.5°	178.5	177.3	175.8	175.4	175.0	174.2	174.1	174.6	174.1	174.2	175.0
175°	177.7	177.0	176.3	175.9	175.9	175.2	175.6	175.9	175.6	175.2	175.9
177.5°	177.1	176.6	176.3	176.3	176.3	176.0	176.3	176.6	176.3	176.0	176.3
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3



TEST NUMBER: P331957-840

CATALOG NUMBER: S123DIP-S775D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1073.0	1070.1	1065.8	1059.4	1054.4	1046.3	1046.3	1047.6	1047.6	1047.2	1046.3
5°	1040.5	1032.5	1023.0	1011.9	1000.3	988.7	986.5	982.3	979.2	977.0	974.3
7.5°	1006.1	992.0	978.2	962.6	948.5	936.8	928.6	921.8	917.5	912.8	909.5
10°	982.8	965.3	949.0	932.6	914.6	900.4	891.4	885.0	880.3	876.1	873.9
12.5°	955.3	935.3	917.3	901.7	882.0	867.4	858.8	855.9	850.2	841.3	836.7
15°	915.1	896.7	874.9	851.2	841.6	823.6	813.6	808.9	805.7	798.8	796.7
17.5°	880.8	856.6	832.2	814.5	796.8	782.2	776.6	770.7	766.5	760.8	759.2
20°	853.3	831.6	809.4	790.4	771.8	756.0	751.2	747.0	742.8	740.1	738.0
22.5°	825.4	803.8	785.3	767.5	747.8	737.4	732.3	727.6	724.6	722.9	720.7
25°	786.2	767.1	746.5	730.6	714.8	707.9	704.7	702.1	699.9	697.3	696.8
27.5°	751.0	730.3	713.6	698.8	687.4	681.7	678.6	677.3	677.8	678.7	679.3
30°	724.8	705.8	692.1	679.3	668.8	663.5	663.0	663.0	665.1	665.6	666.7
32.5°	700.7	685.1	671.4	659.0	651.1	647.4	649.4	649.4	651.2	652.5	654.4
35°	665.6	651.9	641.3	630.8	623.9	625.4	626.5	627.5	630.2	633.4	635.5
37.5°	632.1	620.2	609.2	600.9	597.7	600.6	603.1	605.3	608.4	610.9	613.0
40°	607.9	599.0	588.4	581.0	582.1	583.7	585.8	588.4	591.1	592.7	594.8
42.5°	585.5	576.1	568.2	562.0	563.5	565.5	566.7	568.2	571.2	574.0	575.3
45°	551.4	544.0	536.6	532.9	534.0	535.0	536.0	537.7	540.3	542.4	543.0
47.5°	513.0	507.9	502.9	499.3	501.0	500.6	501.9	505.3	506.1	507.5	510.4
50°	488.5	483.7	478.0	476.9	476.9	476.9	477.4	481.6	481.6	483.7	485.8
52.5°	461.4	458.4	454.6	452.7	451.9	451.9	454.1	456.3	457.1	460.1	462.2
55°	421.3	418.2	415.1	413.4	412.3	413.4	417.7	418.7	421.3	422.9	424.5
57.5°	379.6	377.2	374.7	373.8	373.5	375.0	377.3	380.4	381.1	386.0	388.4
60°	352.1	348.4	346.3	346.3	345.3	350.0	348.9	354.3	355.3	358.4	362.1
62.5°	323.8	318.8	317.9	317.9	319.4	320.8	322.2	324.6	327.4	331.3	334.3
65°	278.1	275.5	279.1	278.6	277.5	280.7	280.7	283.4	286.5	290.2	296.1
67.5°	234.8	233.5	233.8	233.8	235.4	237.2	238.6	241.0	244.8	248.7	252.5
70°	205.6	207.2	204.6	206.7	208.3	208.8	209.8	213.1	217.3	219.9	224.2
72.5°	177.3	177.2	177.5	178.3	180.0	180.9	182.0	185.6	190.3	192.5	195.8
75°	136.4	135.8	137.4	137.4	140.1	141.2	142.2	143.8	148.0	151.2	153.8
77.5°	99.6	100.3	99.9	101.7	101.0	101.2	104.4	106.0	106.4	112.7	114.1
80°	75.0	76.1	76.6	77.2	77.8	76.6	80.4	81.9	81.9	85.6	88.3
82.5°	53.9	54.5	55.9	56.5	56.6	57.7	58.0	59.1	60.4	62.0	65.4
85°	27.0	28.6	29.1	28.6	29.1	28.0	29.6	30.1	30.7	30.7	30.7
87.5°	9.3	9.8	9.6	10.2	10.0	10.7	10.6	9.8	9.9	11.2	9.7
90°	3.9	4.6	5.8	6.8	7.9	8.9	8.6	8.9	9.3	9.6	10.3
92.5°	15.3	20.6	30.0	45.3	60.4	54.8	41.4	30.1	23.8	21.0	19.2
95°	32.5	46.4	76.7	129.9	188.4	211.7	171.7	128.5	87.1	68.2	55.3
97.5°	38.6	53.6	82.6	142.5	240.1	328.0	350.8	320.2	256.5	210.5	167.8
100°	42.8	56.8	81.7	134.5	228.4	338.0	408.3	420.7	391.8	350.1	299.4
102.5°	47.7	60.5	82.9	127.6	211.3	319.4	411.1	454.1	453.2	428.9	396.8
105°	55.6	66.8	86.0	122.8	190.3	286.9	389.3	463.9	499.6	506.3	497.2
107.5°	64.6	74.9	91.9	122.4	176.8	258.2	351.2	435.8	493.7	525.0	537.8
110°	70.7	80.7	96.7	123.8	171.7	242.0	327.3	409.0	474.6	519.6	544.6



TEST NUMBER: P331957-840

CATALOG NUMBER: S123DIP-S775D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	77.0	86.6	101.6	126.7	168.7	231.1	306.4	382.4	449.5	499.9	532.0
115°	86.3	96.0	109.6	131.3	167.7	219.4	281.2	347.2	409.3	461.8	500.7
117.5°	95.7	104.6	118.1	137.4	168.3	212.6	266.0	321.7	375.4	422.4	461.9
120°	101.7	110.6	123.5	142.0	169.6	209.4	258.0	308.3	356.5	399.3	435.4
122.5°	107.1	116.6	129.2	146.3	171.5	207.5	251.5	297.8	341.3	381.0	414.5
125°	115.2	124.9	137.4	153.1	174.5	204.8	243.1	283.7	322.7	356.9	385.5
127.5°	122.8	132.5	144.5	158.6	177.9	203.6	235.6	271.5	306.1	337.0	363.0
130°	127.4	137.0	148.9	162.4	180.3	202.7	231.6	263.7	295.9	324.8	349.0
132.5°	131.7	141.1	152.5	165.8	182.0	202.4	227.9	256.6	286.1	313.1	336.2
135°	137.4	147.0	158.0	170.3	184.5	202.0	223.1	246.9	272.3	295.5	315.8
137.5°	142.4	151.3	162.0	173.5	186.2	201.2	218.8	238.1	258.9	278.9	296.6
140°	145.2	154.2	164.5	175.2	187.3	201.0	216.2	233.1	251.3	268.3	283.7
142.5°	148.1	156.4	166.5	176.9	188.2	200.4	214.0	228.2	243.8	258.6	272.0
145°	151.7	159.9	169.2	178.7	188.7	199.4	210.9	222.4	234.1	245.5	255.9
147.5°	155.8	162.8	171.3	180.0	188.7	198.1	207.9	217.5	226.9	236.1	243.5
150°	158.0	164.5	172.7	180.3	188.7	197.0	205.9	214.1	222.4	229.8	236.6
152.5°	160.4	166.5	173.6	180.8	187.9	195.6	203.6	211.0	218.0	224.7	230.4
155°	164.2	169.2	175.2	181.0	187.0	193.1	200.2	206.3	212.0	217.3	221.6
157.5°	167.4	171.3	176.1	181.3	185.8	190.9	196.3	201.3	206.0	210.2	213.6
160°	169.2	172.7	177.0	181.3	185.2	189.1	193.8	198.4	202.4	205.9	208.4
162.5°	170.6	173.6	177.3	181.0	184.1	187.4	191.2	195.0	198.3	201.7	203.9
165°	172.4	174.9	177.7	180.3	182.4	184.9	187.7	190.6	192.7	195.2	197.0
167.5°	174.0	175.6	177.6	179.7	180.7	182.3	184.4	186.7	188.3	189.8	191.1
170°	174.9	175.6	177.3	178.7	179.6	180.6	182.4	184.1	185.2	186.6	187.3
172.5°	175.4	175.8	177.3	178.5	178.6	179.2	180.4	181.9	182.7	183.8	184.2
175°	175.9	176.3	177.0	177.7	177.3	177.3	178.0	178.7	179.2	179.9	179.9
177.5°	176.3	176.3	176.6	177.1	176.6	176.3	176.6	176.8	177.1	177.4	177.4
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3



TEST NUMBER: P331957-840

CATALOG NUMBER: S123DIP-S775D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1043.4	1043.0	1045.9	1043.8	1045.9	1043.0	1043.4	1046.3	1047.2	1047.6	1047.6
5°	971.2	972.8	967.5	967.5	967.5	972.8	971.2	974.3	977.0	979.2	982.3
7.5°	906.9	904.5	904.7	901.9	904.7	904.5	906.9	909.5	912.8	917.5	921.8
10°	867.6	864.4	863.3	863.8	863.3	864.4	867.6	873.9	876.1	880.3	885.0
12.5°	835.0	834.4	827.4	827.5	827.4	834.4	835.0	836.7	841.3	850.2	855.9
15°	796.7	786.7	785.6	788.8	785.6	786.7	796.7	796.7	798.8	805.7	808.9
17.5°	758.3	753.1	753.4	751.7	753.4	753.1	758.3	759.2	760.8	766.5	770.7
20°	738.0	734.9	734.4	730.6	734.4	734.9	738.0	738.0	740.1	742.8	747.0
22.5°	719.4	718.4	718.7	714.6	718.7	718.4	719.4	720.7	722.9	724.6	727.6
25°	696.3	698.9	696.8	696.8	696.8	698.9	696.3	696.8	697.3	699.9	702.1
27.5°	680.6	680.5	679.4	679.4	679.4	680.5	680.6	679.3	678.7	677.8	677.3
30°	668.8	668.2	669.3	669.3	669.3	668.2	668.8	666.7	665.6	665.1	663.0
32.5°	656.9	657.7	657.9	658.3	657.9	657.7	656.9	654.4	652.5	651.2	649.4
35°	638.6	639.1	640.8	639.7	640.8	639.1	638.6	635.5	633.4	630.2	627.5
37.5°	613.9	616.3	615.8	616.6	615.8	616.3	613.9	613.0	610.9	608.4	605.3
40°	595.3	596.9	596.3	596.3	596.3	596.9	595.3	594.8	592.7	591.1	588.4
42.5°	576.2	577.4	576.0	575.2	576.0	577.4	576.2	575.3	574.0	571.2	568.2
45°	545.0	544.0	545.6	543.5	545.6	544.0	545.0	543.0	542.4	540.3	537.7
47.5°	510.2	511.2	511.7	513.2	511.7	511.2	510.2	510.4	507.5	506.1	505.3
50°	487.0	490.1	490.1	489.6	490.1	490.1	487.0	485.8	483.7	481.6	481.6
52.5°	464.0	465.5	467.7	467.6	467.7	465.5	464.0	462.2	460.1	457.1	456.3
55°	428.8	429.8	430.9	431.4	430.9	429.8	428.8	424.5	422.9	421.3	418.7
57.5°	392.1	391.7	394.3	395.1	394.3	391.7	392.1	388.4	386.0	381.1	380.4
60°	366.4	366.4	370.6	372.2	370.6	366.4	366.4	362.1	358.4	355.3	354.3
62.5°	338.9	340.6	344.8	342.5	344.8	340.6	338.9	334.3	331.3	327.4	324.6
65°	298.7	303.0	302.5	304.5	302.5	303.0	298.7	296.1	290.2	286.5	283.4
67.5°	256.7	259.3	263.2	263.5	263.2	259.3	256.7	252.5	248.7	244.8	241.0
70°	228.4	231.1	233.2	234.7	233.2	231.1	228.4	224.2	219.9	217.3	213.1
72.5°	200.9	202.3	207.3	205.1	207.3	202.3	200.9	195.8	192.5	190.3	185.6
75°	157.5	161.3	164.4	162.8	164.4	161.3	157.5	153.8	151.2	148.0	143.8
77.5°	116.5	120.2	121.7	120.4	121.7	120.2	116.5	114.1	112.7	106.4	106.0
80°	92.0	91.5	94.6	94.1	94.6	91.5	92.0	88.3	85.6	81.9	81.9
82.5°	67.5	67.0	68.4	68.8	68.4	67.0	67.5	65.4	62.0	60.4	59.1
85°	32.8	34.3	32.2	31.7	32.2	34.3	32.8	30.7	30.7	30.7	30.1
87.5°	9.6	9.7	9.3	8.9	9.3	9.7	9.6	9.7	11.2	9.9	9.8
90°	10.0	10.3	10.7	10.3	10.7	10.3	10.0	10.3	9.6	9.3	8.9
92.5°	18.6	17.5	17.9	17.2	17.9	17.5	18.6	19.2	21.0	23.8	30.1
95°	48.6	45.3	42.8	41.4	42.8	45.3	48.6	55.3	68.2	87.1	128.5
97.5°	141.5	125.4	115.7	112.7	115.7	125.4	141.5	167.8	210.5	256.5	320.2
100°	263.4	237.3	223.4	223.8	223.4	237.3	263.4	299.4	350.1	391.8	420.7
102.5°	368.7	348.1	336.5	328.2	336.5	348.1	368.7	396.8	428.9	453.2	454.1
105°	480.7	467.2	455.8	453.9	455.8	467.2	480.7	497.2	506.3	499.6	463.9
107.5°	538.1	533.4	529.6	526.3	529.6	533.4	538.1	537.8	525.0	493.7	435.8
110°	554.6	557.4	556.7	556.0	556.7	557.4	554.6	544.6	519.6	474.6	409.0



TEST NUMBER: P331957-840

CATALOG NUMBER: S123DIP-S775D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	550.3	559.2	561.9	562.0	561.9	559.2	550.3	532.0	499.9	449.5	382.4
115°	527.5	543.1	550.3	552.1	550.3	543.1	527.5	500.7	461.8	409.3	347.2
117.5°	489.9	507.9	518.1	520.5	518.1	507.9	489.9	461.9	422.4	375.4	321.7
120°	463.5	483.5	492.1	494.2	492.1	483.5	463.5	435.4	399.3	356.5	308.3
122.5°	439.6	457.6	467.0	469.7	467.0	457.6	439.6	414.5	381.0	341.3	297.8
125°	408.3	423.9	432.9	435.4	432.9	423.9	408.3	385.5	356.9	322.7	283.7
127.5°	383.3	396.8	404.9	407.1	404.9	396.8	383.3	363.0	337.0	306.1	271.5
130°	367.9	380.8	388.3	391.1	388.3	380.8	367.9	349.0	324.8	295.9	263.7
132.5°	354.0	366.8	373.4	375.5	373.4	366.8	354.0	336.2	313.1	286.1	256.6
135°	333.4	344.1	350.4	352.9	350.4	344.1	333.4	315.8	295.5	272.3	246.9
137.5°	311.2	322.1	327.5	329.2	327.5	322.1	311.2	296.6	278.9	258.9	238.1
140°	297.3	307.3	313.0	312.7	313.0	307.3	297.3	283.7	268.3	251.3	233.1
142.5°	283.6	292.5	297.5	297.2	297.5	292.5	283.6	272.0	258.6	243.8	228.2
145°	264.8	272.3	275.2	275.9	275.2	272.3	264.8	255.9	245.5	234.1	222.4
147.5°	250.2	255.3	258.0	258.3	258.0	255.3	250.2	243.5	236.1	226.9	217.5
150°	242.0	245.9	248.0	248.0	248.0	245.9	242.0	236.6	229.8	222.4	214.1
152.5°	234.5	238.1	239.4	239.4	239.4	238.1	234.5	230.4	224.7	218.0	211.0
155°	224.8	227.7	228.4	228.7	228.4	227.7	224.8	221.6	217.3	212.0	206.3
157.5°	216.3	218.4	219.0	218.9	219.0	218.4	216.3	213.6	210.2	206.0	201.3
160°	210.9	213.1	213.1	212.7	213.1	213.1	210.9	208.4	205.9	202.4	198.4
162.5°	205.5	207.3	207.3	207.0	207.3	207.3	205.5	203.9	201.7	198.3	195.0
165°	198.4	199.9	199.4	199.4	199.4	199.9	198.4	197.0	195.2	192.7	190.6
167.5°	191.7	192.7	192.4	192.4	192.4	192.7	191.7	191.1	189.8	188.3	186.7
170°	187.7	188.4	188.0	188.0	188.0	188.4	187.7	187.3	186.6	185.2	184.1
172.5°	184.3	185.0	184.4	184.1	184.4	185.0	184.3	184.2	183.8	182.7	181.9
175°	179.9	180.3	179.9	179.6	179.9	180.3	179.9	179.9	179.9	179.2	178.7
177.5°	177.1	177.4	176.8	176.8	176.8	177.4	177.1	177.4	177.4	177.1	176.8
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3



TEST NUMBER: P331957-840

CATALOG NUMBER: S123DIP-S775D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1046.3	1046.3	1054.4	1059.4	1065.8	1070.1	1073.0	1076.0	1081.1	1087.8	1095.4
5°	986.5	988.7	1000.3	1011.9	1023.0	1032.5	1040.5	1050.0	1061.6	1075.9	1091.8
7.5°	928.6	936.8	948.5	962.6	978.2	992.0	1006.1	1021.8	1038.1	1059.1	1081.4
10°	891.4	900.4	914.6	932.6	949.0	965.3	982.8	999.8	1020.4	1045.2	1073.8
12.5°	858.8	867.4	882.0	901.7	917.3	935.3	955.3	977.3	1000.5	1030.4	1062.8
15°	813.6	823.6	841.6	851.2	874.9	896.7	915.1	946.8	976.4	1007.1	1044.7
17.5°	776.6	782.2	796.8	814.5	832.2	856.6	880.8	907.3	936.8	974.2	1021.2
20°	751.2	756.0	771.8	790.4	809.4	831.6	853.3	879.7	913.0	952.7	1003.4
22.5°	732.3	737.4	747.8	767.5	785.3	803.8	825.4	856.9	892.3	931.1	986.1
25°	704.7	707.9	714.8	730.6	746.5	767.1	786.2	815.8	852.2	897.7	952.7
27.5°	678.6	681.7	687.4	698.8	713.6	730.3	751.0	776.2	813.2	862.6	921.0
30°	663.0	663.5	668.8	679.3	692.1	705.8	724.8	753.4	788.3	838.5	899.8
32.5°	649.4	647.4	651.1	659.0	671.4	685.1	700.7	728.8	762.4	811.8	874.8
35°	626.5	625.4	623.9	630.8	641.3	651.9	665.6	686.8	724.8	770.8	836.9
37.5°	603.1	600.6	597.7	600.9	609.2	620.2	632.1	651.0	683.7	734.4	797.6
40°	585.8	583.7	582.1	581.0	588.4	599.0	607.9	625.9	656.6	704.7	767.1
42.5°	566.7	565.5	563.5	562.0	568.2	576.1	585.5	601.5	632.1	677.2	736.3
45°	536.0	535.0	534.0	532.9	536.6	544.0	551.4	563.0	589.5	633.4	686.8
47.5°	501.9	500.6	501.0	499.3	502.9	507.9	513.0	525.5	550.9	586.3	625.3
50°	477.4	476.9	476.9	476.9	478.0	483.7	488.5	498.1	521.3	556.7	584.7
52.5°	454.1	451.9	451.9	452.7	454.6	458.4	461.4	471.8	492.1	521.2	546.6
55°	417.7	413.4	412.3	413.4	415.1	418.2	421.3	429.8	447.3	469.0	483.7
57.5°	377.3	375.0	373.5	373.8	374.7	377.2	379.6	388.8	402.5	413.8	423.3
60°	348.9	350.0	345.3	346.3	346.3	348.4	352.1	357.9	369.5	377.5	387.0
62.5°	322.2	320.8	319.4	317.9	317.9	318.8	323.8	328.3	338.2	342.3	349.8
65°	280.7	280.7	277.5	278.6	279.1	275.5	278.1	283.4	289.7	291.3	298.2
67.5°	238.6	237.2	235.4	233.8	233.8	233.5	234.8	237.5	242.3	242.8	248.0
70°	209.8	208.8	208.3	206.7	204.6	207.2	205.6	208.3	211.0	211.5	214.6
72.5°	182.0	180.9	180.0	178.3	177.5	177.2	177.3	180.4	182.2	181.5	185.0
75°	142.2	141.2	140.1	137.4	137.4	135.8	136.4	138.6	140.7	139.1	142.2
77.5°	104.4	101.2	101.0	101.7	99.9	100.3	99.6	99.3	100.3	100.4	103.2
80°	80.4	76.6	77.8	77.2	76.6	76.1	75.0	75.6	76.1	76.6	78.3
82.5°	58.0	57.7	56.6	56.5	55.9	54.5	53.9	54.8	55.4	55.1	56.2
85°	29.6	28.0	29.1	28.6	29.1	28.6	27.0	27.0	28.0	27.5	28.6
87.5°	10.6	10.7	10.0	10.2	9.6	9.8	9.3	9.5	9.7	9.6	10.3
90°	8.6	8.9	7.9	6.8	5.8	4.6	3.9	3.2	2.1	1.4	0.7
92.5°	41.4	54.8	60.4	45.3	30.0	20.6	15.3	12.3	9.6	6.6	4.4
95°	171.7	211.7	188.4	129.9	76.7	46.4	32.5	23.2	17.2	13.2	12.1
97.5°	350.8	328.0	240.1	142.5	82.6	53.6	38.6	29.4	24.1	21.0	20.7
100°	408.3	338.0	228.4	134.5	81.7	56.8	42.8	34.2	29.3	26.8	26.5
102.5°	411.1	319.4	211.3	127.6	82.9	60.5	47.7	40.0	35.2	33.0	32.4
105°	389.3	286.9	190.3	122.8	86.0	66.8	55.6	48.9	44.6	42.5	41.4
107.5°	351.2	258.2	176.8	122.4	91.9	74.9	64.6	58.3	54.1	52.0	51.0
110°	327.3	242.0	171.7	123.8	96.7	80.7	70.7	64.6	60.7	58.9	57.8



TEST NUMBER: P331957-840

CATALOG NUMBER: S123DIP-S775D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	306.4	231.1	168.7	126.7	101.6	86.6	77.0	70.9	67.0	65.1	64.1
115°	281.2	219.4	167.7	131.3	109.6	96.0	86.3	80.3	76.7	74.6	73.1
117.5°	266.0	212.6	168.3	137.4	118.1	104.6	95.7	89.0	85.6	83.8	82.2
120°	258.0	209.4	169.6	142.0	123.5	110.6	101.7	94.9	91.4	89.6	88.5
122.5°	251.5	207.5	171.5	146.3	129.2	116.6	107.1	100.7	96.7	95.0	93.9
125°	243.1	204.8	174.5	153.1	137.4	124.9	115.2	108.5	104.5	102.4	101.7
127.5°	235.6	203.6	177.9	158.6	144.5	132.5	122.8	115.3	111.4	108.7	107.7
130°	231.6	202.7	180.3	162.4	148.9	137.0	127.4	119.9	115.6	112.4	111.4
132.5°	227.9	202.4	182.0	165.8	152.5	141.1	131.7	124.2	119.1	115.5	114.2
135°	223.1	202.0	184.5	170.3	158.0	147.0	137.4	129.9	124.5	120.6	119.2
137.5°	218.8	201.2	186.2	173.5	162.0	151.3	142.4	134.9	129.3	125.4	123.9
140°	216.2	201.0	187.3	175.2	164.5	154.2	145.2	138.1	132.4	128.9	127.0
142.5°	214.0	200.4	188.2	176.9	166.5	156.4	148.1	141.0	135.8	132.0	130.5
145°	210.9	199.4	188.7	178.7	169.2	159.9	151.7	145.6	140.3	137.0	135.9
147.5°	207.9	198.1	188.7	180.0	171.3	162.8	155.8	150.0	145.3	142.2	141.6
150°	205.9	197.0	188.7	180.3	172.7	164.5	158.0	153.1	148.5	145.6	145.2
152.5°	203.6	195.6	187.9	180.8	173.6	166.5	160.4	155.9	151.9	149.1	149.0
155°	200.2	193.1	187.0	181.0	175.2	169.2	164.2	160.3	156.6	154.5	154.5
157.5°	196.3	190.9	185.8	181.3	176.1	171.3	167.4	164.1	161.0	159.3	159.0
160°	193.8	189.1	185.2	181.3	177.0	172.7	169.2	166.6	163.8	162.4	162.4
162.5°	191.2	187.4	184.1	181.0	177.3	173.6	170.6	168.3	166.1	164.9	164.9
165°	187.7	184.9	182.4	180.3	177.7	174.9	172.4	171.0	169.2	168.4	168.7
167.5°	184.4	182.3	180.7	179.7	177.6	175.6	174.0	173.0	171.7	171.3	171.7
170°	182.4	180.6	179.6	178.7	177.3	175.6	174.9	174.1	173.1	172.7	173.4
172.5°	180.4	179.2	178.6	178.5	177.3	175.8	175.4	175.0	174.2	174.1	174.6
175°	178.0	177.3	177.3	177.7	177.0	176.3	175.9	175.9	175.2	175.6	175.9
177.5°	176.6	176.3	176.6	177.1	176.6	176.3	176.3	176.3	176.0	176.3	176.6
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3



TEST NUMBER: P331957-840

CATALOG NUMBER: S123DIP-S775D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1097.9	1100.0	1107.3	1112.4	1118.2	1121.7	1125.0	1127.6	1130.9	1131.8	1144.1
5°	1102.9	1113.4	1132.0	1145.7	1162.6	1181.0	1193.8	1199.6	1214.9	1227.6	1252.9
7.5°	1101.5	1124.0	1151.9	1180.8	1211.9	1240.7	1265.7	1295.3	1316.4	1348.0	1379.1
10°	1100.1	1130.3	1166.3	1203.3	1246.7	1286.8	1322.7	1362.9	1396.2	1440.2	1477.6
12.5°	1096.4	1132.9	1182.8	1226.6	1279.2	1334.6	1387.9	1439.5	1468.9	1542.1	1576.6
15°	1087.0	1130.3	1192.8	1259.3	1331.7	1397.4	1465.0	1518.9	1606.1	1670.1	1710.8
17.5°	1069.0	1129.7	1203.7	1284.0	1372.1	1458.5	1535.2	1617.0	1709.5	1787.0	1869.5
20°	1060.6	1127.1	1209.6	1298.5	1389.9	1487.7	1575.0	1673.2	1774.2	1850.4	1956.1
22.5°	1044.9	1120.3	1209.2	1308.2	1405.9	1507.1	1609.2	1708.4	1825.0	1930.0	2030.5
25°	1019.3	1103.9	1195.9	1306.4	1421.1	1522.6	1644.8	1776.4	1897.9	2032.8	2133.2
27.5°	992.4	1082.8	1175.0	1277.7	1401.1	1521.6	1675.2	1823.9	1972.7	2089.0	2163.3
30°	971.7	1059.4	1154.7	1258.3	1380.4	1523.7	1695.5	1857.7	2002.7	2102.5	2144.3
32.5°	949.3	1038.3	1122.5	1231.2	1361.4	1522.4	1708.2	1877.6	2004.4	2070.8	2062.8
35°	914.1	988.7	1070.6	1175.3	1328.6	1513.1	1715.6	1879.5	1957.2	1942.9	1835.0
37.5°	863.3	926.0	1006.7	1121.4	1290.5	1493.5	1700.8	1823.7	1818.7	1702.4	1546.2
40°	831.6	885.0	962.7	1083.3	1260.9	1480.9	1677.5	1757.4	1689.7	1527.3	1340.2
42.5°	790.2	839.3	917.1	1041.0	1228.3	1455.0	1633.1	1656.3	1523.9	1337.1	1165.5
45°	725.9	769.2	849.6	977.5	1179.5	1398.9	1524.7	1468.1	1290.0	1097.0	966.4
47.5°	656.8	701.9	779.2	910.6	1108.8	1314.4	1374.3	1254.1	1071.1	914.6	794.8
50°	613.3	656.6	732.3	864.9	1061.1	1245.1	1269.9	1114.5	946.3	808.9	710.5
52.5°	569.3	610.1	684.4	817.6	1005.2	1164.7	1149.3	991.0	836.4	719.2	642.1
55°	503.8	542.4	613.3	738.0	908.8	1035.1	979.7	828.5	700.5	609.6	550.9
57.5°	445.2	482.3	543.4	656.1	804.6	891.4	820.7	693.3	591.6	521.6	477.9
60°	405.5	438.3	496.4	601.1	730.1	796.2	726.4	613.8	528.2	472.1	433.0
62.5°	367.9	396.4	450.3	545.3	657.3	712.9	642.3	546.9	474.0	424.3	391.1
65°	310.8	336.8	384.4	458.4	550.4	587.3	526.5	449.4	392.8	355.8	333.6
67.5°	258.8	280.8	321.9	380.2	447.9	474.8	428.6	368.8	326.2	296.5	278.8
70°	224.2	243.2	275.5	325.7	387.0	407.6	364.3	315.1	283.9	260.1	243.7
72.5°	195.0	208.9	238.2	277.0	328.2	344.6	314.4	271.1	242.1	224.2	211.2
75°	148.6	160.2	179.3	210.5	245.8	255.4	232.6	205.6	186.1	173.4	163.4
77.5°	107.1	115.6	129.5	148.7	173.2	181.8	167.3	149.4	135.1	126.5	121.0
80°	80.9	87.8	99.4	115.2	130.1	134.8	126.3	112.6	102.6	97.9	93.0
82.5°	59.8	63.6	70.6	81.4	91.6	97.1	90.0	81.7	76.3	72.0	70.2
85°	30.1	32.2	35.4	39.7	45.9	48.1	45.4	43.3	40.2	37.6	37.6
87.5°	11.3	11.4	12.9	13.9	15.8	17.2	17.0	16.4	16.2	15.7	15.3
90°	1.4	2.1	3.2	3.9	4.6	5.8	6.8	7.9	8.9	8.6	8.9
92.5°	6.6	9.6	12.3	15.3	20.6	30.0	45.3	60.4	54.8	41.4	30.1
95°	13.2	17.2	23.2	32.5	46.4	76.7	129.9	188.4	211.7	171.7	128.5
97.5°	21.0	24.1	29.4	38.6	53.6	82.6	142.5	240.1	328.0	350.8	320.2
100°	26.8	29.3	34.2	42.8	56.8	81.7	134.5	228.4	338.0	408.3	420.7
102.5°	33.0	35.2	40.0	47.7	60.5	82.9	127.6	211.3	319.4	411.1	454.1
105°	42.5	44.6	48.9	55.6	66.8	86.0	122.8	190.3	286.9	389.3	463.9
107.5°	52.0	54.1	58.3	64.6	74.9	91.9	122.4	176.8	258.2	351.2	435.8
110°	58.9	60.7	64.6	70.7	80.7	96.7	123.8	171.7	242.0	327.3	409.0





TEST NUMBER: P331957-840

CATALOG NUMBER: S123DIP-S775D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	65.1	67.0	70.9	77.0	86.6	101.6	126.7	168.7	231.1	306.4	382.4
115°	74.6	76.7	80.3	86.3	96.0	109.6	131.3	167.7	219.4	281.2	347.2
117.5°	83.8	85.6	89.0	95.7	104.6	118.1	137.4	168.3	212.6	266.0	321.7
120°	89.6	91.4	94.9	101.7	110.6	123.5	142.0	169.6	209.4	258.0	308.3
122.5°	95.0	96.7	100.7	107.1	116.6	129.2	146.3	171.5	207.5	251.5	297.8
125°	102.4	104.5	108.5	115.2	124.9	137.4	153.1	174.5	204.8	243.1	283.7
127.5°	108.7	111.4	115.3	122.8	132.5	144.5	158.6	177.9	203.6	235.6	271.5
130°	112.4	115.6	119.9	127.4	137.0	148.9	162.4	180.3	202.7	231.6	263.7
132.5°	115.5	119.1	124.2	131.7	141.1	152.5	165.8	182.0	202.4	227.9	256.6
135°	120.6	124.5	129.9	137.4	147.0	158.0	170.3	184.5	202.0	223.1	246.9
137.5°	125.4	129.3	134.9	142.4	151.3	162.0	173.5	186.2	201.2	218.8	238.1
140°	128.9	132.4	138.1	145.2	154.2	164.5	175.2	187.3	201.0	216.2	233.1
142.5°	132.0	135.8	141.0	148.1	156.4	166.5	176.9	188.2	200.4	214.0	228.2
145°	137.0	140.3	145.6	151.7	159.9	169.2	178.7	188.7	199.4	210.9	222.4
147.5°	142.2	145.3	150.0	155.8	162.8	171.3	180.0	188.7	198.1	207.9	217.5
150°	145.6	148.5	153.1	158.0	164.5	172.7	180.3	188.7	197.0	205.9	214.1
152.5°	149.1	151.9	155.9	160.4	166.5	173.6	180.8	187.9	195.6	203.6	211.0
155°	154.5	156.6	160.3	164.2	169.2	175.2	181.0	187.0	193.1	200.2	206.3
157.5°	159.3	161.0	164.1	167.4	171.3	176.1	181.3	185.8	190.9	196.3	201.3
160°	162.4	163.8	166.6	169.2	172.7	177.0	181.3	185.2	189.1	193.8	198.4
162.5°	164.9	166.1	168.3	170.6	173.6	177.3	181.0	184.1	187.4	191.2	195.0
165°	168.4	169.2	171.0	172.4	174.9	177.7	180.3	182.4	184.9	187.7	190.6
167.5°	171.3	171.7	173.0	174.0	175.6	177.6	179.7	180.7	182.3	184.4	186.7
170°	172.7	173.1	174.1	174.9	175.6	177.3	178.7	179.6	180.6	182.4	184.1
172.5°	174.1	174.2	175.0	175.4	175.8	177.3	178.5	178.6	179.2	180.4	181.9
175°	175.6	175.2	175.9	175.9	176.3	177.0	177.7	177.3	177.3	178.0	178.7
177.5°	176.3	176.0	176.3	176.3	176.3	176.6	177.1	176.6	176.3	176.6	176.8
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3



TEST NUMBER: P331957-840

CATALOG NUMBER: S123DIP-S775D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1148.3	1148.7	1153.4	1156.8	1155.1	1157.2	1158.0
5°	1254.6	1273.6	1283.6	1291.0	1291.6	1292.1	1296.4
7.5°	1405.2	1425.6	1440.6	1463.2	1470.0	1477.6	1475.4
10°	1515.2	1545.3	1571.2	1585.0	1599.8	1621.4	1604.1
12.5°	1618.0	1671.4	1710.8	1732.2	1746.2	1750.5	1741.9
15°	1787.5	1857.2	1894.8	1893.7	1941.4	1962.0	1929.7
17.5°	1942.9	2007.3	2058.9	2085.4	2125.0	2133.7	2129.7
20°	2038.1	2108.4	2148.6	2194.0	2214.6	2233.1	2236.3
22.5°	2120.1	2183.2	2226.3	2264.2	2281.5	2290.3	2295.5
25°	2204.6	2254.3	2280.2	2293.4	2298.1	2297.1	2290.3
27.5°	2198.8	2202.6	2174.0	2146.1	2121.0	2092.7	2083.0
30°	2141.7	2097.3	2018.0	1973.1	1906.9	1854.6	1875.7
32.5°	1991.6	1903.2	1814.1	1715.9	1634.6	1611.4	1588.1
35°	1699.7	1544.3	1453.4	1347.6	1305.4	1263.0	1234.0
37.5°	1375.1	1254.9	1147.0	1077.8	1035.5	1008.8	994.3
40°	1189.0	1080.7	991.8	935.7	903.5	873.4	869.2
42.5°	1040.6	939.8	872.9	828.3	797.4	784.6	775.3
45°	852.2	781.9	737.0	705.3	684.7	676.7	666.1
47.5°	721.3	671.7	637.9	616.3	600.8	594.9	594.0
50°	648.1	606.9	582.1	565.1	553.0	550.9	542.4
52.5°	593.2	557.4	538.1	523.3	514.5	508.6	506.0
55°	514.9	491.1	473.7	465.2	458.4	452.5	452.5
57.5°	450.5	430.7	419.1	411.9	409.8	405.7	403.0
60°	410.8	393.8	384.9	378.5	374.4	374.9	370.1
62.5°	371.8	360.9	352.3	346.0	340.9	341.0	341.3
65°	316.7	308.2	301.8	299.7	296.6	292.9	294.0
67.5°	268.3	260.4	255.5	251.9	250.9	248.8	251.9
70°	233.7	227.8	224.2	221.0	219.9	220.5	223.1
72.5°	202.0	197.8	195.4	193.9	191.6	191.7	193.5
75°	158.6	155.4	153.3	151.7	151.2	151.2	151.2
77.5°	116.5	115.8	114.8	112.5	112.6	113.2	113.3
80°	92.0	90.4	89.9	88.9	87.3	86.1	88.9
82.5°	68.8	67.2	66.7	66.4	63.9	63.7	65.9
85°	37.0	35.4	36.0	35.4	35.4	34.9	34.9
87.5°	14.9	14.6	14.3	14.6	14.3	13.9	14.7
90°	9.3	9.6	10.3	10.0	10.3	10.7	10.3
92.5°	23.8	21.0	19.2	18.6	17.5	17.9	17.2
95°	87.1	68.2	55.3	48.6	45.3	42.8	41.4
97.5°	256.5	210.5	167.8	141.5	125.4	115.7	112.7
100°	391.8	350.1	299.4	263.4	237.3	223.4	223.8
102.5°	453.2	428.9	396.8	368.7	348.1	336.5	328.2
105°	499.6	506.3	497.2	480.7	467.2	455.8	453.9
107.5°	493.7	525.0	537.8	538.1	533.4	529.6	526.3
110°	474.6	519.6	544.6	554.6	557.4	556.7	556.0



TEST NUMBER: P331957-840

CATALOG NUMBER: S123DIP-S775D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	449.5	499.9	532.0	550.3	559.2	561.9	562.0
115°	409.3	461.8	500.7	527.5	543.1	550.3	552.1
117.5°	375.4	422.4	461.9	489.9	507.9	518.1	520.5
120°	356.5	399.3	435.4	463.5	483.5	492.1	494.2
122.5°	341.3	381.0	414.5	439.6	457.6	467.0	469.7
125°	322.7	356.9	385.5	408.3	423.9	432.9	435.4
127.5°	306.1	337.0	363.0	383.3	396.8	404.9	407.1
130°	295.9	324.8	349.0	367.9	380.8	388.3	391.1
132.5°	286.1	313.1	336.2	354.0	366.8	373.4	375.5
135°	272.3	295.5	315.8	333.4	344.1	350.4	352.9
137.5°	258.9	278.9	296.6	311.2	322.1	327.5	329.2
140°	251.3	268.3	283.7	297.3	307.3	313.0	312.7
142.5°	243.8	258.6	272.0	283.6	292.5	297.5	297.2
145°	234.1	245.5	255.9	264.8	272.3	275.2	275.9
147.5°	226.9	236.1	243.5	250.2	255.3	258.0	258.3
150°	222.4	229.8	236.6	242.0	245.9	248.0	248.0
152.5°	218.0	224.7	230.4	234.5	238.1	239.4	239.4
155°	212.0	217.3	221.6	224.8	227.7	228.4	228.7
157.5°	206.0	210.2	213.6	216.3	218.4	219.0	218.9
160°	202.4	205.9	208.4	210.9	213.1	213.1	212.7
162.5°	198.3	201.7	203.9	205.5	207.3	207.3	207.0
165°	192.7	195.2	197.0	198.4	199.9	199.4	199.4
167.5°	188.3	189.8	191.1	191.7	192.7	192.4	192.4
170°	185.2	186.6	187.3	187.7	188.4	188.0	188.0
172.5°	182.7	183.8	184.2	184.3	185.0	184.4	184.1
175°	179.2	179.9	179.9	179.9	180.3	179.9	179.6
177.5°	177.1	177.4	177.4	177.1	177.4	176.8	176.8
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3

(END OF REPORT)