

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332333-840

Luminaire Tested: **S123RDIP-S1000D365U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332333-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D365U840-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5294.6 lumens
Efficiency: N/A
Efficacy: 121.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332333-840

CATALOG NUMBER: S123RDIP-S1000D365U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332333-840

CATALOG NUMBER: S123RDIP-S1000D365U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	77	77	77	72
1	103	99	95	92	98	94	91	88	85	82	80	76	74	73	69	67	66	62
2	94	87	81	76	89	83	77	73	75	71	67	68	64	61	61	58	56	53
3	86	77	70	64	82	73	67	61	67	61	57	60	56	52	54	51	48	45
4	79	68	60	54	75	65	58	53	59	54	49	54	49	45	49	45	42	39
5	73	61	53	47	69	59	51	46	54	47	43	49	44	40	44	40	37	34
6	68	55	47	41	64	53	45	40	48	42	37	44	39	35	40	36	33	30
7	63	50	42	36	59	48	41	35	44	38	33	40	35	31	37	33	29	27
8	58	46	38	33	55	44	37	32	40	34	30	37	32	28	34	30	26	24
9	55	42	34	29	52	40	33	28	37	31	27	34	29	25	32	27	24	22
10	51	39	31	27	49	37	30	26	34	29	24	32	27	23	29	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18243	18243	18243
5°	18312	18058	18163
10°	18208	17832	17772
15°	18013	17415	17231
20°	17743	16893	16501
25°	17467	16308	15785
30°	17100	15632	14777
35°	16724	14954	13853
40°	16378	14155	12708
45°	15923	13370	11676
50°	15421	12476	10518
55°	14910	11453	9439
60°	14441	10357	8254
65°	13827	9172	7070
70°	13064	7701	5712
75°	11948	6059	5373
80°	10649	5362	4940
85°	8991	4755	4409



TEST NUMBER: P332333-840

CATALOG NUMBER: S123RDIP-S1000D365U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.1	3.0
10°-20°	442.8	8.4
20°-30°	637.6	12.0
30°-40°	718.2	13.6
40°-50°	687.1	13.0
50°-60°	562.6	10.6
60°-70°	379.6	7.2
70°-80°	191.0	3.6
80°-90°	51.9	1.0
90°-100°	17.5	0.3
100°-110°	83.2	1.6
110°-120°	199.9	3.8
120°-130°	254.6	4.8
130°-140°	272.0	5.1
140°-150°	254.4	4.8
150°-160°	205.2	3.9
160°-170°	132.4	2.5
170°-180°	45.6	0.9
0°-30°	1239.5	23.4
0°-40°	1957.7	37.0
0°-60°	3207.4	60.6
0°-90°	3829.9	72.3
90°-120°	300.6	5.7
90°-150°	1081.5	20.4
90°-180°	1465.0	27.7
0°-180°	5294.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1695	1695	1695	1695	1695	
5°	1695	1687	1671	1683	1681	161
15°	1616	1600	1563	1556	1546	455
25°	1471	1435	1373	1345	1329	676
35°	1273	1221	1138	1081	1054	796
45°	1046	982	878	802	767	807
55°	794	724	610	533	503	712
65°	543	466	360	296	278	537
75°	287	221	146	133	129	306
85°	73	44	38	36	36	82
90°	0	4	9	10	11	5
95°	22	8	11	13	14	27
105°	106	108	78	18	16	113
115°	199	202	205	208	210	197
125°	281	284	286	286	287	251
135°	350	352	354	355	354	269
145°	404	406	407	408	408	253
155°	445	444	445	446	444	205
165°	469	468	468	470	468	133
175°	480	479	479	481	479	46
180°	480	480	480	480	480	



TEST NUMBER: P332333-840

CATALOG NUMBER: S123RDIP-S1000D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8
2.5°	1700.2	1699.2	1698.3	1697.3	1696.3	1694.4	1691.4	1688.5	1685.6	1682.6	1685.3
5°	1694.8	1693.1	1691.6	1690.1	1688.6	1686.0	1682.3	1678.7	1675.1	1671.3	1674.1
7.5°	1679.0	1677.4	1675.8	1674.1	1672.4	1669.2	1664.5	1659.7	1655.0	1650.2	1651.7
10°	1665.9	1663.8	1661.5	1659.4	1657.3	1653.5	1648.0	1642.4	1637.0	1631.5	1631.8
12.5°	1647.2	1644.8	1642.4	1640.0	1637.6	1633.1	1626.4	1619.6	1613.0	1606.2	1606.0
15°	1616.4	1613.1	1609.6	1606.3	1603.0	1597.0	1588.4	1579.8	1571.3	1562.8	1561.3
17.5°	1577.6	1573.7	1569.8	1565.9	1562.0	1554.6	1543.7	1532.9	1522.0	1511.1	1507.8
20°	1549.0	1544.2	1539.2	1534.4	1529.4	1521.3	1509.6	1498.0	1486.4	1474.8	1470.9
22.5°	1517.1	1511.6	1505.9	1500.3	1494.7	1485.7	1473.3	1461.0	1448.7	1436.3	1431.4
25°	1470.7	1463.1	1455.4	1447.7	1440.2	1429.3	1415.2	1401.2	1387.2	1373.1	1366.7
27.5°	1414.3	1405.9	1397.5	1389.1	1380.6	1368.6	1352.9	1337.3	1321.6	1306.1	1297.1
30°	1375.8	1366.7	1357.6	1348.4	1339.2	1326.1	1309.0	1291.8	1274.8	1257.7	1247.3
32.5°	1337.4	1327.0	1316.6	1306.2	1295.9	1281.6	1263.5	1245.5	1227.3	1209.2	1197.9
35°	1272.7	1261.7	1250.7	1239.8	1228.8	1213.8	1194.9	1175.9	1157.0	1138.0	1124.9
37.5°	1207.3	1195.1	1182.9	1170.6	1158.4	1142.3	1122.1	1101.8	1081.6	1061.4	1046.4
40°	1165.6	1152.2	1138.6	1125.2	1111.8	1094.2	1072.6	1050.9	1029.2	1007.4	991.6
42.5°	1118.2	1104.8	1091.4	1077.9	1064.5	1046.6	1024.2	1001.8	979.4	956.9	939.6
45°	1046.0	1032.2	1018.4	1004.7	991.0	972.4	948.9	925.3	901.8	878.3	860.9
47.5°	973.7	958.6	943.5	928.4	913.3	894.0	870.5	847.0	823.4	799.9	781.0
50°	920.9	906.6	892.2	877.9	863.4	843.9	819.2	794.5	769.7	745.0	726.0
52.5°	873.6	858.1	842.4	826.9	811.3	791.2	766.8	742.3	717.8	693.3	673.6
55°	794.5	779.5	764.5	749.5	734.6	714.1	688.1	662.2	636.2	610.3	592.6
57.5°	721.3	705.0	688.7	672.4	656.1	634.9	608.7	582.7	556.6	530.6	513.8
60°	670.8	654.0	637.1	620.4	603.5	582.5	557.1	531.8	506.4	481.1	464.5
62.5°	620.2	603.4	586.5	569.8	553.0	531.9	506.5	481.2	455.9	430.5	415.0
65°	542.9	526.1	509.3	492.5	475.7	455.4	431.6	407.8	384.0	360.1	345.2
67.5°	465.6	448.7	431.7	414.8	397.8	377.8	355.0	332.1	309.3	286.4	275.3
70°	415.1	398.6	382.1	365.6	349.1	330.2	308.8	287.4	266.0	244.7	234.0
72.5°	364.5	348.3	332.0	315.8	299.5	281.7	262.3	242.9	223.4	204.0	195.2
75°	287.3	272.6	257.9	243.3	228.6	212.9	196.1	179.3	162.5	145.7	142.6
77.5°	216.9	203.6	190.4	177.1	163.9	151.8	141.0	130.2	119.4	108.6	106.9
80°	171.8	159.3	146.7	134.2	121.7	112.3	105.8	99.4	93.0	86.5	85.6
82.5°	129.0	118.2	107.3	96.4	85.6	78.8	75.7	72.8	69.8	66.8	65.8
85°	72.8	66.1	59.4	52.7	45.9	42.1	41.2	40.3	39.4	38.5	37.9
87.5°	26.5	23.9	21.4	18.9	16.4	15.1	15.3	15.6	15.8	16.1	15.9
90°	0.4	1.1	1.9	2.7	3.5	4.4	5.5	6.5	7.6	8.6	8.9
92.5°	6.7	6.5	6.2	6.0	5.8	6.1	6.8	7.6	8.4	9.1	9.6
95°	21.8	18.5	15.2	12.0	8.8	7.6	8.5	9.3	10.2	11.1	11.6
97.5°	43.7	42.3	40.8	39.4	37.9	34.3	28.6	22.9	17.2	11.5	12.1
100°	60.3	61.9	63.5	65.0	66.7	61.3	48.9	36.6	24.1	11.8	12.4
102.5°	79.2	80.3	81.4	82.6	83.7	77.6	64.0	50.5	37.0	23.5	21.5
105°	106.3	107.2	108.1	109.0	109.9	106.7	99.6	92.4	85.3	78.2	64.1
107.5°	135.0	135.7	136.4	137.1	137.8	138.8	139.9	141.0	142.1	143.2	132.9
110°	154.2	154.8	155.4	156.0	156.7	157.4	158.3	159.2	160.1	161.0	158.3



TEST NUMBER: P332333-840

CATALOG NUMBER: S123RDIP-S1000D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	172.4	173.0	173.6	174.1	174.7	175.4	176.3	177.2	178.0	178.9	178.9
115°	199.4	200.0	200.5	200.9	201.4	202.0	202.7	203.4	204.1	204.8	205.6
117.5°	225.7	226.3	226.8	227.4	228.0	228.5	228.8	229.2	229.6	229.9	230.6
120°	242.0	242.7	243.4	244.1	244.8	245.3	245.5	245.8	246.0	246.2	246.9
122.5°	258.5	259.1	259.6	260.2	260.8	261.3	261.6	261.9	262.2	262.5	263.0
125°	281.2	281.9	282.5	283.1	283.8	284.2	284.6	284.9	285.2	285.5	285.7
127.5°	303.2	303.9	304.5	305.1	305.7	306.2	306.6	307.0	307.4	307.7	308.0
130°	316.9	317.5	318.1	318.8	319.4	319.9	320.2	320.5	320.8	321.1	321.4
132.5°	330.0	330.6	331.3	331.9	332.5	333.0	333.3	333.6	333.8	334.1	334.4
135°	350.1	350.5	351.0	351.5	351.9	352.3	352.6	353.0	353.4	353.7	353.9
137.5°	367.2	367.8	368.4	369.0	369.6	370.0	370.2	370.3	370.5	370.7	371.1
140°	378.6	379.1	379.6	380.0	380.5	380.9	381.1	381.3	381.6	381.8	382.1
142.5°	389.2	389.7	390.1	390.6	391.1	391.4	391.7	391.9	392.1	392.4	392.6
145°	403.9	404.6	405.1	405.7	406.2	406.6	406.7	406.9	407.0	407.2	407.4
147.5°	417.9	418.3	418.6	419.0	419.3	419.6	419.8	419.9	420.1	420.2	420.4
150°	426.5	426.7	426.9	427.2	427.4	427.6	427.8	427.9	428.1	428.2	428.4
152.5°	434.1	434.2	434.3	434.4	434.5	434.7	434.7	434.8	434.9	435.0	435.4
155°	445.0	444.8	444.6	444.5	444.3	444.3	444.4	444.4	444.5	444.6	445.0
157.5°	453.4	453.4	453.4	453.3	453.3	453.3	453.2	453.1	453.0	453.0	453.4
160°	458.6	458.5	458.4	458.3	458.3	458.2	458.1	458.0	458.0	457.9	458.3
162.5°	463.4	463.2	463.0	462.8	462.6	462.4	462.3	462.3	462.2	462.1	462.6
165°	469.3	469.0	468.8	468.6	468.3	468.2	468.1	468.0	467.9	467.9	468.5
167.5°	473.8	473.5	473.2	472.9	472.5	472.4	472.4	472.4	472.4	472.4	473.0
170°	476.4	476.1	475.7	475.4	475.1	474.9	474.9	474.9	474.9	474.9	475.6
172.5°	478.1	477.8	477.4	477.0	476.6	476.5	476.5	476.6	476.7	476.7	477.4
175°	480.3	479.9	479.5	479.2	478.8	478.6	478.7	478.8	478.8	478.9	479.5
177.5°	480.9	480.6	480.3	480.0	479.6	479.5	479.6	479.6	479.7	479.8	480.3
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3



TEST NUMBER: P332333-840

CATALOG NUMBER: S123RDIP-S1000D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8
2.5°	1688.0	1690.7	1693.3	1694.5	1693.9	1693.5	1693.0	1692.5
5°	1676.9	1679.6	1682.3	1683.4	1682.8	1682.2	1681.6	1681.0
7.5°	1653.3	1654.8	1656.3	1656.6	1655.5	1654.5	1653.5	1652.3
10°	1632.1	1632.4	1632.7	1632.1	1630.5	1629.0	1627.5	1626.0
12.5°	1605.8	1605.7	1605.5	1604.5	1602.8	1600.9	1599.2	1597.4
15°	1559.7	1558.2	1556.7	1554.8	1552.7	1550.5	1548.4	1546.3
17.5°	1504.6	1501.4	1498.1	1494.9	1491.8	1488.5	1485.4	1482.2
20°	1466.8	1462.9	1459.0	1455.1	1451.5	1447.7	1444.1	1440.5
22.5°	1426.4	1421.5	1416.5	1412.3	1409.0	1405.5	1402.1	1398.7
25°	1360.3	1353.8	1347.5	1342.5	1339.2	1335.8	1332.5	1329.1
27.5°	1288.2	1279.3	1270.3	1263.3	1258.2	1253.0	1247.9	1242.8
30°	1236.9	1226.5	1216.1	1208.5	1203.6	1198.7	1193.8	1188.9
32.5°	1186.5	1175.2	1163.8	1155.6	1150.4	1145.3	1140.1	1135.0
35°	1111.8	1098.6	1085.5	1076.2	1070.8	1065.2	1059.8	1054.2
37.5°	1031.6	1016.6	1001.8	990.9	984.1	977.3	970.6	963.8
40°	975.7	959.9	943.9	932.5	925.4	918.5	911.4	904.4
42.5°	922.2	904.8	887.5	875.7	869.4	863.1	856.8	850.5
45°	843.4	826.1	808.6	796.3	788.9	781.6	774.3	767.0
47.5°	762.0	743.2	724.2	711.4	704.9	698.4	691.9	685.3
50°	707.1	688.1	669.2	656.2	649.2	642.2	635.2	628.1
52.5°	654.0	634.3	614.6	601.6	595.3	589.1	582.8	576.4
55°	574.8	557.1	539.4	527.5	521.4	515.2	509.2	503.0
57.5°	497.1	480.3	463.6	452.6	447.5	442.2	437.1	431.8
60°	448.1	431.6	415.1	404.2	399.1	393.8	388.7	383.4
62.5°	399.4	384.0	368.4	357.9	352.5	347.1	341.6	336.2
65°	330.2	315.2	300.2	291.0	287.7	284.4	281.0	277.6
67.5°	264.1	252.9	241.8	234.3	230.8	227.1	223.5	219.9
70°	223.3	212.6	201.9	194.9	191.5	188.1	184.8	181.5
72.5°	186.5	177.7	169.1	164.0	162.6	161.2	159.8	158.3
75°	139.6	136.5	133.5	131.7	131.1	130.4	129.8	129.2
77.5°	105.3	103.6	102.0	100.9	100.3	99.7	99.1	98.5
80°	84.7	83.8	82.9	82.2	81.6	81.0	80.3	79.7
82.5°	64.9	64.0	63.1	62.6	62.5	62.4	62.2	62.1
85°	37.3	36.7	36.1	35.7	35.7	35.7	35.7	35.7
87.5°	15.7	15.5	15.2	15.0	14.8	14.6	14.4	14.2
90°	9.2	9.5	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	10.2	10.7	11.2	11.5	11.5	11.6	11.7	11.8
95°	12.2	12.7	13.3	13.5	13.5	13.5	13.5	13.5
97.5°	12.7	13.4	14.0	14.3	14.4	14.5	14.6	14.7
100°	13.0	13.6	14.3	14.6	14.7	14.8	14.9	14.9
102.5°	19.6	17.6	15.7	14.7	14.8	14.9	15.1	15.2
105°	50.1	36.1	22.0	15.0	15.2	15.3	15.6	15.7
107.5°	122.7	112.4	102.1	91.6	81.1	70.5	59.9	49.3
110°	155.7	153.1	150.5	143.5	132.2	120.8	109.5	98.2



TEST NUMBER: P332333-840

CATALOG NUMBER: S123RDIP-S1000D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	179.0	179.0	179.2	177.9	175.5	173.2	170.8	168.3
115°	206.4	207.2	208.0	208.5	208.8	209.2	209.5	209.8
117.5°	231.3	231.9	232.5	232.9	232.9	233.0	233.1	233.1
120°	247.5	248.1	248.7	249.1	249.1	249.1	249.1	249.1
122.5°	263.4	263.9	264.3	264.5	264.6	264.7	264.7	264.8
125°	285.8	286.0	286.1	286.3	286.4	286.6	286.8	286.9
127.5°	308.2	308.5	308.8	308.8	308.6	308.5	308.3	308.2
130°	321.8	322.1	322.4	322.6	322.3	322.2	322.0	321.8
132.5°	334.7	335.0	335.3	335.4	335.1	334.9	334.7	334.5
135°	354.2	354.4	354.6	354.6	354.4	354.2	353.9	353.7
137.5°	371.4	371.8	372.2	372.3	372.1	372.0	371.8	371.7
140°	382.4	382.7	383.1	383.1	383.0	382.8	382.7	382.5
142.5°	392.9	393.1	393.4	393.4	393.2	392.9	392.7	392.5
145°	407.5	407.7	407.8	407.9	407.9	407.9	407.9	407.9
147.5°	420.5	420.7	420.9	420.8	420.4	420.0	419.7	419.3
150°	428.6	428.7	428.9	428.8	428.6	428.4	428.1	427.9
152.5°	435.7	436.0	436.3	436.2	435.9	435.5	435.0	434.7
155°	445.5	445.9	446.3	446.2	445.8	445.2	444.7	444.2
157.5°	453.9	454.4	454.9	454.8	454.2	453.6	452.9	452.3
160°	458.8	459.3	459.8	459.7	459.2	458.6	458.1	457.5
162.5°	463.2	463.7	464.2	464.3	463.8	463.3	462.8	462.3
165°	469.1	469.8	470.4	470.4	469.9	469.3	468.8	468.2
167.5°	473.6	474.3	474.9	474.9	474.3	473.6	473.0	472.4
170°	476.3	476.9	477.5	477.5	476.9	476.3	475.6	474.9
172.5°	478.0	478.6	479.2	479.2	478.5	477.8	477.1	476.4
175°	480.0	480.6	481.1	481.1	480.5	479.8	479.2	478.6
177.5°	480.8	481.3	481.8	481.7	481.1	480.5	479.8	479.2
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3

(END OF REPORT)