

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332334-840

Luminaire Tested: **S123RDIP-S1000D365U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332334-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1000D365U840-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5088.6 lumens  
Efficiency: N/A  
Efficacy: 117.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332334-840

CATALOG NUMBER: S123RDIP-S1000D365U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332334-840

CATALOG NUMBER: S123RDIP-S1000D365U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75
1	104	100	96	92	99	95	92	89	86	84	81	78	76	74	71	69	68	64
2	95	88	81	76	90	84	78	73	76	72	68	69	66	63	63	60	58	55
3	87	77	70	64	83	74	67	62	68	62	58	62	57	54	56	53	50	47
4	80	69	61	55	76	66	59	53	61	55	50	55	51	47	51	47	43	41
5	74	62	54	47	70	59	52	46	54	48	43	50	45	41	46	42	38	36
6	68	56	48	42	65	54	46	40	49	43	38	45	40	36	42	37	34	31
7	63	51	43	37	60	49	41	36	45	39	34	42	36	32	38	34	30	28
8	59	46	38	33	56	45	37	32	41	35	30	38	33	29	35	31	27	25
9	55	42	35	30	52	41	34	29	38	32	28	35	30	26	33	28	25	23
10	52	39	32	27	49	38	31	26	35	29	25	33	27	24	30	26	23	21

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18243	18243	18243
5°	18312	18058	18163
10°	18208	17832	17772
15°	18013	17415	17231
20°	17743	16893	16501
25°	17467	16308	15785
30°	17100	15632	14777
35°	16724	14954	13853
40°	16378	14155	12708
45°	15923	13370	11676
50°	15421	12476	10518
55°	14910	11453	9439
60°	14441	10357	8254
65°	13827	9172	7070
70°	13064	7701	5712
75°	11948	6059	5373
80°	10649	5362	4940
85°	8991	4755	4409



TEST NUMBER: P332334-840

CATALOG NUMBER: S123RDIP-S1000D365U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	159.1	3.1
10°-20°	442.8	8.7
20°-30°	637.6	12.5
30°-40°	718.2	14.1
40°-50°	687.1	13.5
50°-60°	562.6	11.1
60°-70°	379.6	7.5
70°-80°	191.0	3.8
80°-90°	51.9	1.0
90°-100°	29.6	0.6
100°-110°	88.6	1.7
110°-120°	150.7	3.0
120°-130°	198.2	3.9
130°-140°	222.7	4.4
140°-150°	219.0	4.3
150°-160°	184.3	3.6
160°-170°	122.7	2.4
170°-180°	43.0	0.8
0°-30°	1239.5	24.4
0°-40°	1957.7	38.5
0°-60°	3207.4	63.0
0°-90°	3829.9	75.3
90°-120°	268.8	5.3
90°-150°	908.7	17.9
90°-180°	1259.0	24.7
0°-180°	5088.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1695	1695	1695	1695	1695	
5°	1695	1687	1671	1683	1681	161
15°	1616	1600	1563	1556	1546	455
25°	1471	1435	1373	1345	1329	676
35°	1273	1221	1138	1081	1054	796
45°	1046	982	878	802	767	807
55°	794	724	610	533	503	712
65°	543	466	360	296	278	537
75°	287	221	146	133	129	306
85°	73	44	38	36	36	82
90°	0	4	9	10	11	5
95°	21	24	26	28	28	24
105°	80	81	84	84	85	86
115°	152	153	152	152	152	150
125°	222	223	222	221	219	198
135°	288	290	290	288	288	222
145°	349	350	351	351	349	218
155°	400	400	400	402	399	184
165°	436	435	435	437	434	123
175°	453	452	452	454	451	43
180°	454	454	454	454	454	



TEST NUMBER: P332334-840

CATALOG NUMBER: S123RDIP-S1000D365U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8
2.5°	1700.2	1699.2	1698.3	1697.3	1696.3	1694.4	1691.4	1688.5	1685.6	1682.6	1685.3
5°	1694.8	1693.1	1691.6	1690.1	1688.6	1686.0	1682.3	1678.7	1675.1	1671.3	1674.1
7.5°	1679.0	1677.4	1675.8	1674.1	1672.4	1669.2	1664.5	1659.7	1655.0	1650.2	1651.7
10°	1665.9	1663.8	1661.5	1659.4	1657.3	1653.5	1648.0	1642.4	1637.0	1631.5	1631.8
12.5°	1647.2	1644.8	1642.4	1640.0	1637.6	1633.1	1626.4	1619.6	1613.0	1606.2	1606.0
15°	1616.4	1613.1	1609.6	1606.3	1603.0	1597.0	1588.4	1579.8	1571.3	1562.8	1561.3
17.5°	1577.6	1573.7	1569.8	1565.9	1562.0	1554.6	1543.7	1532.9	1522.0	1511.1	1507.8
20°	1549.0	1544.2	1539.2	1534.4	1529.4	1521.3	1509.6	1498.0	1486.4	1474.8	1470.9
22.5°	1517.1	1511.6	1505.9	1500.3	1494.7	1485.7	1473.3	1461.0	1448.7	1436.3	1431.4
25°	1470.7	1463.1	1455.4	1447.7	1440.2	1429.3	1415.2	1401.2	1387.2	1373.1	1366.7
27.5°	1414.3	1405.9	1397.5	1389.1	1380.6	1368.6	1352.9	1337.3	1321.6	1306.1	1297.1
30°	1375.8	1366.7	1357.6	1348.4	1339.2	1326.1	1309.0	1291.8	1274.8	1257.7	1247.3
32.5°	1337.4	1327.0	1316.6	1306.2	1295.9	1281.6	1263.5	1245.5	1227.3	1209.2	1197.9
35°	1272.7	1261.7	1250.7	1239.8	1228.8	1213.8	1194.9	1175.9	1157.0	1138.0	1124.9
37.5°	1207.3	1195.1	1182.9	1170.6	1158.4	1142.3	1122.1	1101.8	1081.6	1061.4	1046.4
40°	1165.6	1152.2	1138.6	1125.2	1111.8	1094.2	1072.6	1050.9	1029.2	1007.4	991.6
42.5°	1118.2	1104.8	1091.4	1077.9	1064.5	1046.6	1024.2	1001.8	979.4	956.9	939.6
45°	1046.0	1032.2	1018.4	1004.7	991.0	972.4	948.9	925.3	901.8	878.3	860.9
47.5°	973.7	958.6	943.5	928.4	913.3	894.0	870.5	847.0	823.4	799.9	781.0
50°	920.9	906.6	892.2	877.9	863.4	843.9	819.2	794.5	769.7	745.0	726.0
52.5°	873.6	858.1	842.4	826.9	811.3	791.2	766.8	742.3	717.8	693.3	673.6
55°	794.5	779.5	764.5	749.5	734.6	714.1	688.1	662.2	636.2	610.3	592.6
57.5°	721.3	705.0	688.7	672.4	656.1	634.9	608.7	582.7	556.6	530.6	513.8
60°	670.8	654.0	637.1	620.4	603.5	582.5	557.1	531.8	506.4	481.1	464.5
62.5°	620.2	603.4	586.5	569.8	553.0	531.9	506.5	481.2	455.9	430.5	415.0
65°	542.9	526.1	509.3	492.5	475.7	455.4	431.6	407.8	384.0	360.1	345.2
67.5°	465.6	448.7	431.7	414.8	397.8	377.8	355.0	332.1	309.3	286.4	275.3
70°	415.1	398.6	382.1	365.6	349.1	330.2	308.8	287.4	266.0	244.7	234.0
72.5°	364.5	348.3	332.0	315.8	299.5	281.7	262.3	242.9	223.4	204.0	195.2
75°	287.3	272.6	257.9	243.3	228.6	212.9	196.1	179.3	162.5	145.7	142.6
77.5°	216.9	203.6	190.4	177.1	163.9	151.8	141.0	130.2	119.4	108.6	106.9
80°	171.8	159.3	146.7	134.2	121.7	112.3	105.8	99.4	93.0	86.5	85.6
82.5°	129.0	118.2	107.3	96.4	85.6	78.8	75.7	72.8	69.8	66.8	65.8
85°	72.8	66.1	59.4	52.7	45.9	42.1	41.2	40.3	39.4	38.5	37.9
87.5°	26.5	23.9	21.4	18.9	16.4	15.1	15.3	15.6	15.8	16.1	15.9
90°	0.4	1.1	1.9	2.7	3.5	4.4	5.5	6.5	7.6	8.6	8.9
92.5°	8.7	9.2	9.7	10.3	10.8	11.3	11.9	12.5	13.1	13.7	13.9
95°	21.1	21.6	22.1	22.7	23.2	23.8	24.5	25.1	25.8	26.5	26.8
97.5°	37.4	37.8	38.3	38.7	39.1	39.5	40.0	40.4	40.9	41.3	41.7
100°	48.6	49.0	49.5	50.0	50.4	50.9	51.3	51.7	52.1	52.4	52.7
102.5°	61.4	61.7	61.9	62.2	62.5	62.9	63.4	64.0	64.5	65.0	65.2
105°	80.3	80.5	80.6	80.8	80.9	81.4	82.1	82.8	83.5	84.2	84.2
107.5°	102.3	102.4	102.5	102.6	102.7	102.8	103.1	103.4	103.7	104.0	104.2
110°	116.0	116.1	116.3	116.4	116.6	116.7	116.9	117.1	117.2	117.4	117.8



TEST NUMBER: P332334-840

CATALOG NUMBER: S123RDIP-S1000D365U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	130.3	130.4	130.5	130.6	130.7	130.7	130.8	130.8	130.8	130.9	131.2
115°	151.7	151.9	152.2	152.4	152.6	152.7	152.5	152.4	152.2	152.0	152.1
117.5°	173.2	173.4	173.6	173.7	173.9	173.8	173.6	173.4	173.2	173.0	173.0
120°	186.6	187.1	187.6	188.0	188.5	188.5	188.2	187.8	187.4	187.0	186.9
122.5°	200.7	201.0	201.4	201.7	202.1	202.1	201.9	201.7	201.5	201.3	201.1
125°	222.0	222.2	222.5	222.7	223.0	223.0	222.8	222.7	222.5	222.4	222.0
127.5°	241.7	242.2	242.7	243.2	243.7	243.9	243.7	243.5	243.4	243.2	242.8
130°	254.8	255.4	256.1	256.7	257.3	257.5	257.3	257.1	256.8	256.6	256.3
132.5°	267.9	268.6	269.2	269.8	270.4	270.7	270.5	270.3	270.1	270.0	269.6
135°	288.0	288.5	288.9	289.4	289.9	290.1	290.0	289.9	289.8	289.8	289.4
137.5°	306.6	307.0	307.3	307.7	308.1	308.4	308.6	308.8	309.0	309.2	308.9
140°	319.4	319.8	320.2	320.6	321.0	321.2	321.3	321.3	321.4	321.5	321.4
142.5°	331.1	331.5	331.9	332.3	332.6	333.0	333.2	333.3	333.4	333.6	333.5
145°	349.4	349.5	349.7	349.8	350.0	350.2	350.4	350.7	350.9	351.1	351.1
147.5°	365.4	365.7	366.0	366.3	366.5	366.8	367.0	367.2	367.4	367.7	367.7
150°	376.5	376.7	376.8	377.0	377.2	377.3	377.5	377.6	377.8	377.9	377.9
152.5°	385.7	385.9	386.1	386.3	386.6	386.7	386.8	386.9	387.0	387.1	387.2
155°	400.1	400.1	400.1	400.1	400.1	400.1	400.2	400.2	400.3	400.4	400.7
157.5°	412.3	412.2	412.1	412.0	411.9	411.9	412.0	412.0	412.1	412.2	412.5
160°	420.0	419.9	419.7	419.6	419.4	419.3	419.3	419.3	419.3	419.3	419.7
162.5°	426.9	426.7	426.5	426.3	426.0	426.0	426.0	426.1	426.2	426.2	426.6
165°	435.8	435.6	435.3	435.0	434.7	434.6	434.6	434.6	434.6	434.6	435.2
167.5°	442.8	442.5	442.2	441.8	441.5	441.4	441.5	441.5	441.6	441.7	442.1
170°	446.8	446.5	446.2	445.9	445.6	445.4	445.4	445.4	445.4	445.4	446.0
172.5°	450.0	449.6	449.3	449.0	448.7	448.5	448.5	448.5	448.5	448.5	449.0
175°	453.2	452.9	452.6	452.3	452.0	451.8	451.8	451.8	451.8	451.8	452.3
177.5°	454.5	454.3	454.0	453.8	453.5	453.4	453.4	453.4	453.4	453.4	453.8
180°	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3



TEST NUMBER: P332334-840

CATALOG NUMBER: S123RDIP-S1000D365U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8
2.5°	1688.0	1690.7	1693.3	1694.5	1693.9	1693.5	1693.0	1692.5
5°	1676.9	1679.6	1682.3	1683.4	1682.8	1682.2	1681.6	1681.0
7.5°	1653.3	1654.8	1656.3	1656.6	1655.5	1654.5	1653.5	1652.3
10°	1632.1	1632.4	1632.7	1632.1	1630.5	1629.0	1627.5	1626.0
12.5°	1605.8	1605.7	1605.5	1604.5	1602.8	1600.9	1599.2	1597.4
15°	1559.7	1558.2	1556.7	1554.8	1552.7	1550.5	1548.4	1546.3
17.5°	1504.6	1501.4	1498.1	1494.9	1491.8	1488.5	1485.4	1482.2
20°	1466.8	1462.9	1459.0	1455.1	1451.5	1447.7	1444.1	1440.5
22.5°	1426.4	1421.5	1416.5	1412.3	1409.0	1405.5	1402.1	1398.7
25°	1360.3	1353.8	1347.5	1342.5	1339.2	1335.8	1332.5	1329.1
27.5°	1288.2	1279.3	1270.3	1263.3	1258.2	1253.0	1247.9	1242.8
30°	1236.9	1226.5	1216.1	1208.5	1203.6	1198.7	1193.8	1188.9
32.5°	1186.5	1175.2	1163.8	1155.6	1150.4	1145.3	1140.1	1135.0
35°	1111.8	1098.6	1085.5	1076.2	1070.8	1065.2	1059.8	1054.2
37.5°	1031.6	1016.6	1001.8	990.9	984.1	977.3	970.6	963.8
40°	975.7	959.9	943.9	932.5	925.4	918.5	911.4	904.4
42.5°	922.2	904.8	887.5	875.7	869.4	863.1	856.8	850.5
45°	843.4	826.1	808.6	796.3	788.9	781.6	774.3	767.0
47.5°	762.0	743.2	724.2	711.4	704.9	698.4	691.9	685.3
50°	707.1	688.1	669.2	656.2	649.2	642.2	635.2	628.1
52.5°	654.0	634.3	614.6	601.6	595.3	589.1	582.8	576.4
55°	574.8	557.1	539.4	527.5	521.4	515.2	509.2	503.0
57.5°	497.1	480.3	463.6	452.6	447.5	442.2	437.1	431.8
60°	448.1	431.6	415.1	404.2	399.1	393.8	388.7	383.4
62.5°	399.4	384.0	368.4	357.9	352.5	347.1	341.6	336.2
65°	330.2	315.2	300.2	291.0	287.7	284.4	281.0	277.6
67.5°	264.1	252.9	241.8	234.3	230.8	227.1	223.5	219.9
70°	223.3	212.6	201.9	194.9	191.5	188.1	184.8	181.5
72.5°	186.5	177.7	169.1	164.0	162.6	161.2	159.8	158.3
75°	139.6	136.5	133.5	131.7	131.1	130.4	129.8	129.2
77.5°	105.3	103.6	102.0	100.9	100.3	99.7	99.1	98.5
80°	84.7	83.8	82.9	82.2	81.6	81.0	80.3	79.7
82.5°	64.9	64.0	63.1	62.6	62.5	62.4	62.2	62.1
85°	37.3	36.7	36.1	35.7	35.7	35.7	35.7	35.7
87.5°	15.7	15.5	15.2	15.0	14.8	14.6	14.4	14.2
90°	9.2	9.5	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	14.2	14.4	14.7	14.8	14.7	14.6	14.5	14.4
95°	27.1	27.4	27.7	27.9	27.9	27.9	27.9	27.9
97.5°	42.0	42.4	42.8	42.9	42.9	42.9	42.8	42.8
100°	52.9	53.2	53.4	53.6	53.7	53.9	54.1	54.2
102.5°	65.5	65.7	65.9	66.0	66.0	66.0	65.9	65.9
105°	84.2	84.2	84.2	84.3	84.4	84.6	84.8	84.9
107.5°	104.5	104.7	105.0	105.1	105.0	104.9	104.8	104.7
110°	118.1	118.4	118.7	118.8	118.6	118.5	118.3	118.2





TEST NUMBER: P332334-840

CATALOG NUMBER: S123RDIP-S1000D365U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	131.6	132.0	132.4	132.5	132.5	132.5	132.4	132.4
115°	152.2	152.3	152.4	152.4	152.3	152.2	152.1	152.0
117.5°	173.0	173.0	173.0	172.8	172.6	172.4	172.2	172.0
120°	186.8	186.7	186.7	186.5	186.4	186.2	186.1	185.9
122.5°	200.9	200.7	200.5	200.3	200.1	199.8	199.5	199.3
125°	221.7	221.4	221.1	220.8	220.5	220.2	219.7	219.4
127.5°	242.3	241.9	241.4	241.0	240.7	240.2	239.9	239.5
130°	256.0	255.6	255.3	254.9	254.4	253.8	253.3	252.7
132.5°	269.2	268.8	268.5	268.1	267.6	267.2	266.8	266.4
135°	289.1	288.8	288.5	288.3	288.1	287.9	287.8	287.6
137.5°	308.6	308.3	307.9	307.6	307.3	307.0	306.7	306.4
140°	321.3	321.3	321.2	320.9	320.3	319.8	319.2	318.7
142.5°	333.4	333.3	333.3	333.0	332.5	332.1	331.6	331.2
145°	351.0	350.9	350.8	350.6	350.3	350.0	349.7	349.4
147.5°	367.7	367.7	367.7	367.4	367.0	366.5	366.0	365.5
150°	377.9	377.9	377.9	377.7	377.2	376.8	376.3	375.8
152.5°	387.3	387.5	387.6	387.4	387.0	386.6	386.2	385.8
155°	401.0	401.3	401.7	401.5	401.0	400.4	399.9	399.3
157.5°	412.8	413.2	413.5	413.4	413.0	412.6	412.1	411.7
160°	420.1	420.5	420.9	420.9	420.6	420.3	420.0	419.7
162.5°	427.0	427.4	427.8	427.7	427.2	426.7	426.2	425.7
165°	435.7	436.1	436.6	436.6	436.0	435.5	434.8	434.3
167.5°	442.6	443.1	443.6	443.6	443.1	442.6	442.1	441.7
170°	446.5	447.1	447.6	447.6	447.1	446.5	446.0	445.4
172.5°	449.5	450.0	450.5	450.5	449.9	449.4	448.8	448.3
175°	452.7	453.2	453.7	453.6	453.1	452.5	452.0	451.4
177.5°	454.2	454.5	454.9	454.9	454.5	454.0	453.6	453.1
180°	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3

(END OF REPORT)