

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332241-840

Luminaire Tested: **S123RDIP-S340D365U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332241-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D365U840-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2628.5 lumens
Efficiency: N/A
Efficacy: 129.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332241-840

CATALOG NUMBER: S123RDIP-S340D365U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332241-840

CATALOG NUMBER: S123RDIP-S340D365U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52
1	99	95	91	88	91	88	85	82	75	73	71	63	62	60	52	51	50	45
2	91	83	78	73	84	78	72	68	66	63	59	56	54	51	47	45	43	39
3	83	74	67	61	77	69	63	58	59	55	51	50	47	44	42	40	37	34
4	76	66	58	52	70	61	55	49	53	48	44	45	41	38	38	35	33	29
5	70	59	51	45	65	55	48	43	48	42	38	41	37	33	34	31	29	26
6	65	53	45	40	60	50	43	38	43	38	34	37	33	30	31	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21
8	56	44	36	31	52	41	34	30	36	30	27	31	27	24	27	23	21	19
9	52	40	33	28	48	38	31	26	33	28	24	29	24	21	25	21	19	17
10	49	37	30	25	45	35	28	24	30	25	22	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5916	5916	5916	5916
5°	7052	5942	5232	5942
10°	8805	5908	4726	5908
15°	10336	5846	4310	5846
20°	11535	5756	3956	5756
25°	11351	5662	3739	5662
30°	8158	5574	3515	5574
35°	5447	5460	3369	5460
40°	4013	5323	3219	5323
45°	3367	5083	3073	5083
50°	2971	4767	2869	4767
55°	2607	4406	2586	4406
60°	2321	4060	2370	4060
65°	2038	3691	2203	3691
70°	1599	3361	2014	3361
75°	1406	2936	1838	2936
80°	1227	2492	1810	2492
85°	988	2013	1927	2013



TEST NUMBER: P332241-840

CATALOG NUMBER: S123RDIP-S340D365U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.0	2.1
10°-20°	168.9	6.4
20°-30°	265.3	10.1
30°-40°	276.8	10.5
40°-50°	236.9	9.0
50°-60°	180.5	6.9
60°-70°	115.7	4.4
70°-80°	55.7	2.1
80°-90°	16.1	0.6
90°-100°	29.6	1.1
100°-110°	88.6	3.4
110°-120°	150.7	5.7
120°-130°	198.2	7.5
130°-140°	222.7	8.5
140°-150°	219.0	8.3
150°-160°	184.3	7.0
160°-170°	122.7	4.7
170°-180°	43.0	1.6
0°-30°	488.2	18.6
0°-40°	764.9	29.1
0°-60°	1182.3	45.0
0°-90°	1369.8	52.1
90°-120°	268.8	10.2
90°-150°	908.7	34.6
90°-180°	1259.0	47.9
0°-180°	2628.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	550	550	550	550	550	
5°	653	550	484	550	653	67
15°	928	525	387	525	928	263
25°	956	477	315	477	956	411
35°	414	416	256	416	414	272
45°	221	334	202	334	221	174
55°	139	235	138	235	139	126
65°	80	145	86	145	80	79
75°	34	71	44	71	34	36
85°	8	16	16	16	8	9
90°	11	0	11	0	11	5
95°	28	21	28	21	28	29
105°	85	80	85	80	85	90
115°	152	152	152	152	152	151
125°	219	222	219	222	219	196
135°	288	288	288	288	288	221
145°	349	349	349	349	349	218
155°	399	400	399	400	399	184
165°	434	436	434	436	434	122
175°	451	453	451	453	451	43
180°	454	454	454	454	454	



TEST NUMBER: P332241-840

CATALOG NUMBER: S123RDIP-S340D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	585.4	586.1	583.7	583.3	580.5	579.8	579.8	575.7	573.3	570.2	568.3
5°	652.7	656.4	654.5	650.4	643.3	641.6	637.1	630.1	622.1	612.2	607.5
7.5°	736.7	741.8	739.8	733.4	725.9	719.9	707.3	695.6	679.2	664.8	652.5
10°	805.6	800.2	796.0	789.6	782.7	771.7	758.5	740.4	719.5	703.0	684.7
12.5°	857.2	856.3	850.9	844.3	834.8	824.3	808.0	786.0	761.6	737.8	716.8
15°	927.5	928.9	925.3	918.6	904.8	886.3	861.8	852.6	817.8	791.9	766.1
17.5°	976.1	975.8	975.3	965.9	952.0	938.8	916.0	891.9	860.4	823.9	789.1
20°	1007.0	1004.6	1005.1	994.5	984.2	968.9	946.7	911.7	885.9	843.7	807.7
22.5°	1006.2	1005.7	1007.5	1003.9	996.4	984.7	967.2	937.7	904.6	862.1	821.6
25°	955.7	953.8	964.8	968.0	980.0	982.1	976.8	960.7	929.4	885.6	835.5
27.5°	799.8	798.8	819.3	845.1	877.6	902.9	927.4	939.2	929.4	898.0	847.8
30°	656.4	678.5	688.9	726.1	767.5	816.9	860.2	901.3	911.5	897.8	856.7
32.5°	545.0	564.3	573.0	604.8	643.5	701.4	766.3	824.6	865.8	876.2	851.4
35°	414.5	414.8	434.5	448.7	484.4	543.9	607.0	685.1	762.8	821.6	827.7
37.5°	330.8	331.9	344.0	358.0	384.9	416.3	471.8	536.7	626.4	716.7	769.7
40°	285.6	287.7	296.7	310.5	329.8	353.7	396.9	458.1	532.9	633.4	715.5
42.5°	256.6	260.0	264.7	275.4	287.3	309.6	344.6	391.8	459.9	554.9	649.6
45°	221.2	223.1	226.6	231.6	242.4	257.8	281.3	313.2	369.6	446.1	540.9
47.5°	195.1	194.1	197.8	201.8	209.0	219.6	235.4	261.3	301.5	362.9	443.3
50°	177.4	177.1	179.8	182.8	189.7	197.4	210.4	229.8	261.9	312.7	386.4
52.5°	160.9	161.7	163.6	167.3	172.3	178.5	190.2	204.3	231.8	275.6	337.0
55°	138.9	139.6	142.1	144.2	147.7	154.1	161.4	173.2	192.0	222.6	273.2
57.5°	120.2	119.9	122.3	122.9	126.8	132.0	137.6	146.8	160.5	183.2	217.2
60°	107.8	107.0	109.2	110.8	112.9	117.1	121.9	130.8	141.7	158.3	187.5
62.5°	96.4	96.1	97.7	99.4	101.1	104.9	108.9	115.7	124.3	138.4	161.6
65°	80.0	80.7	81.4	82.1	83.0	85.4	89.2	93.9	99.8	109.7	126.3
67.5°	62.9	63.6	63.8	65.2	67.3	68.8	71.1	75.2	79.4	87.7	97.1
70°	50.8	50.6	50.8	51.5	54.1	56.7	59.8	62.8	65.4	71.3	79.3
72.5°	43.6	43.2	43.8	44.0	45.2	45.9	47.9	50.8	54.1	58.1	63.8
75°	33.8	33.8	33.8	33.8	34.8	35.2	36.0	36.7	37.9	39.8	44.0
77.5°	25.0	25.0	25.4	25.7	25.9	26.2	26.6	27.3	27.7	28.7	30.5
80°	19.8	20.0	19.8	20.0	20.0	20.5	20.7	21.4	21.6	22.8	23.5
82.5°	14.8	14.7	14.8	15.1	15.1	15.6	15.7	16.2	16.2	16.8	17.5
85°	8.0	7.6	8.0	7.8	8.3	7.8	8.0	8.5	8.5	8.7	9.7
87.5°	4.0	4.3	3.9	4.1	4.0	4.2	4.1	4.1	4.4	4.1	4.1
90°	10.7	10.5	10.4	10.2	10.1	9.8	9.5	9.2	8.9	8.6	7.6
92.5°	14.4	14.5	14.6	14.7	14.8	14.7	14.4	14.2	13.9	13.7	13.1
95°	27.9	27.9	27.9	27.9	27.9	27.7	27.4	27.1	26.8	26.5	25.8
97.5°	42.8	42.8	42.9	42.9	42.9	42.8	42.4	42.0	41.7	41.3	40.9
100°	54.2	54.1	53.9	53.7	53.6	53.4	53.2	52.9	52.7	52.4	52.1
102.5°	65.9	65.9	66.0	66.0	66.0	65.9	65.7	65.5	65.2	65.0	64.5
105°	84.9	84.8	84.6	84.4	84.3	84.2	84.2	84.2	84.2	84.2	83.5
107.5°	104.7	104.8	104.9	105.0	105.1	105.0	104.7	104.5	104.2	104.0	103.7
110°	118.2	118.3	118.5	118.6	118.8	118.7	118.4	118.1	117.8	117.4	117.2



TEST NUMBER: P332241-840

CATALOG NUMBER: S123RDIP-S340D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	132.4	132.4	132.5	132.5	132.5	132.4	132.0	131.6	131.2	130.9	130.8
115°	152.0	152.1	152.2	152.3	152.4	152.4	152.3	152.2	152.1	152.0	152.2
117.5°	172.0	172.2	172.4	172.6	172.8	173.0	173.0	173.0	173.0	173.0	173.2
120°	185.9	186.1	186.2	186.4	186.5	186.7	186.7	186.8	186.9	187.0	187.4
122.5°	199.3	199.5	199.8	200.1	200.3	200.5	200.7	200.9	201.1	201.3	201.5
125°	219.4	219.7	220.2	220.5	220.8	221.1	221.4	221.7	222.0	222.4	222.5
127.5°	239.5	239.9	240.2	240.7	241.0	241.4	241.9	242.3	242.8	243.2	243.4
130°	252.7	253.3	253.8	254.4	254.9	255.3	255.6	256.0	256.3	256.6	256.8
132.5°	266.4	266.8	267.2	267.6	268.1	268.5	268.8	269.2	269.6	270.0	270.1
135°	287.6	287.8	287.9	288.1	288.3	288.5	288.8	289.1	289.4	289.8	289.8
137.5°	306.4	306.7	307.0	307.3	307.6	307.9	308.3	308.6	308.9	309.2	309.0
140°	318.7	319.2	319.8	320.3	320.9	321.2	321.3	321.3	321.4	321.5	321.4
142.5°	331.2	331.6	332.1	332.5	333.0	333.3	333.3	333.4	333.5	333.6	333.4
145°	349.4	349.7	350.0	350.3	350.6	350.8	350.9	351.0	351.1	351.1	350.9
147.5°	365.5	366.0	366.5	367.0	367.4	367.7	367.7	367.7	367.7	367.7	367.4
150°	375.8	376.3	376.8	377.2	377.7	377.9	377.9	377.9	377.9	377.9	377.8
152.5°	385.8	386.2	386.6	387.0	387.4	387.6	387.5	387.3	387.2	387.1	387.0
155°	399.3	399.9	400.4	401.0	401.5	401.7	401.3	401.0	400.7	400.4	400.3
157.5°	411.7	412.1	412.6	413.0	413.4	413.5	413.2	412.8	412.5	412.2	412.1
160°	419.7	420.0	420.3	420.6	420.9	420.9	420.5	420.1	419.7	419.3	419.3
162.5°	425.7	426.2	426.7	427.2	427.7	427.8	427.4	427.0	426.6	426.2	426.2
165°	434.3	434.8	435.5	436.0	436.6	436.6	436.1	435.7	435.2	434.6	434.6
167.5°	441.7	442.1	442.6	443.1	443.6	443.6	443.1	442.6	442.1	441.7	441.6
170°	445.4	446.0	446.5	447.1	447.6	447.6	447.1	446.5	446.0	445.4	445.4
172.5°	448.3	448.8	449.4	449.9	450.5	450.5	450.0	449.5	449.0	448.5	448.5
175°	451.4	452.0	452.5	453.1	453.6	453.7	453.2	452.7	452.3	451.8	451.8
177.5°	453.1	453.6	454.0	454.5	454.9	454.9	454.5	454.2	453.8	453.4	453.4
180°	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3



TEST NUMBER: P332241-840

CATALOG NUMBER: S123RDIP-S340D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	567.4	566.9	564.3	561.3	557.3	554.7	552.6	551.5	548.1	543.9	541.2
5°	602.6	595.5	587.9	578.8	570.3	561.6	556.2	549.9	542.1	533.4	527.3
7.5°	640.1	626.2	611.4	595.9	580.8	567.1	555.0	544.7	532.4	519.9	511.2
10°	668.9	648.6	627.7	606.3	586.8	568.5	554.3	540.5	525.6	511.3	500.4
12.5°	695.1	668.4	644.3	617.9	593.0	571.1	550.8	534.4	516.5	501.3	489.0
15°	728.2	700.8	671.8	631.7	598.5	570.8	546.0	524.6	503.0	484.2	472.2
17.5°	759.1	718.1	678.8	645.5	602.4	567.7	537.6	512.0	488.2	468.3	453.4
20°	771.9	732.2	689.6	647.0	604.7	565.8	530.8	502.5	477.9	455.2	441.6
22.5°	779.6	734.7	689.7	644.0	599.1	558.7	524.0	492.9	466.2	444.7	427.9
25°	788.6	735.0	685.6	640.5	594.5	550.8	509.6	476.7	447.8	425.0	407.1
27.5°	794.6	731.4	673.1	622.9	576.3	532.8	495.0	460.1	430.7	406.6	387.4
30°	795.7	728.6	663.5	609.2	561.9	521.8	481.8	448.5	417.4	391.7	373.9
32.5°	797.2	721.6	650.5	592.8	544.3	504.7	468.5	436.6	404.8	379.5	361.2
35°	791.0	717.8	630.8	564.4	515.9	477.6	444.9	415.5	384.3	359.7	341.1
37.5°	764.3	702.6	610.4	532.5	481.8	446.4	419.7	394.0	365.4	338.9	321.4
40°	737.4	687.5	594.5	513.1	460.2	423.7	399.7	378.8	351.0	326.3	307.5
42.5°	697.3	666.9	579.5	492.8	435.8	400.6	380.3	360.7	336.4	311.2	293.6
45°	623.7	627.7	548.7	460.4	401.8	366.6	347.5	333.9	312.3	291.5	273.4
47.5°	531.5	568.9	512.5	426.0	366.2	333.1	316.4	304.5	289.8	269.5	253.0
50°	471.3	524.6	483.5	402.8	343.8	310.8	294.4	284.7	272.0	256.0	240.2
52.5°	415.8	473.1	448.5	377.0	319.4	289.3	273.3	265.3	255.2	240.1	225.9
55°	339.0	397.2	391.5	338.1	283.1	256.0	243.8	234.8	228.0	216.7	205.4
57.5°	274.3	329.3	332.2	294.8	251.0	224.2	213.7	206.9	202.5	194.0	183.5
60°	233.4	284.0	293.9	265.6	228.0	204.5	194.1	188.6	185.2	178.3	170.4
62.5°	199.5	242.6	253.8	233.5	206.0	183.9	175.8	170.7	168.2	162.4	155.3
65°	152.7	188.4	199.2	188.0	173.6	156.0	149.4	144.9	142.8	139.6	134.3
67.5°	114.8	140.9	152.8	144.8	139.6	128.5	124.3	121.9	120.0	117.8	113.4
70°	92.2	111.5	123.7	121.7	117.4	111.5	108.5	106.8	104.9	103.0	99.3
72.5°	74.1	87.5	98.9	100.0	96.5	95.3	92.6	91.9	90.8	88.6	86.4
75°	49.2	58.4	66.3	69.4	70.8	72.0	70.8	70.6	70.4	68.5	67.3
77.5°	32.2	37.2	42.2	47.5	49.7	51.2	51.6	52.5	51.8	50.9	50.3
80°	24.7	25.9	29.4	33.8	37.4	38.8	39.8	40.2	40.0	39.8	38.8
82.5°	18.0	18.9	20.6	23.7	26.7	29.0	29.6	29.5	30.0	30.2	29.4
85°	9.7	9.9	10.4	10.8	12.4	15.0	15.8	16.3	16.7	16.7	15.2
87.5°	4.3	3.9	4.0	3.9	4.3	4.3	5.4	6.1	6.5	5.9	6.0
90°	6.5	5.5	4.4	3.5	2.7	1.9	1.1	0.4	1.1	1.9	2.7
92.5°	12.5	11.9	11.3	10.8	10.3	9.7	9.2	8.7	9.2	9.7	10.3
95°	25.1	24.5	23.8	23.2	22.7	22.1	21.6	21.1	21.6	22.1	22.7
97.5°	40.4	40.0	39.5	39.1	38.7	38.3	37.8	37.4	37.8	38.3	38.7
100°	51.7	51.3	50.9	50.4	50.0	49.5	49.0	48.6	49.0	49.5	50.0
102.5°	64.0	63.4	62.9	62.5	62.2	61.9	61.7	61.4	61.7	61.9	62.2
105°	82.8	82.1	81.4	80.9	80.8	80.6	80.5	80.3	80.5	80.6	80.8
107.5°	103.4	103.1	102.8	102.7	102.6	102.5	102.4	102.3	102.4	102.5	102.6
110°	117.1	116.9	116.7	116.6	116.4	116.3	116.1	116.0	116.1	116.3	116.4



TEST NUMBER: P332241-840

CATALOG NUMBER: S123RDIP-S340D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	130.8	130.8	130.7	130.7	130.6	130.5	130.4	130.3	130.4	130.5	130.6
115°	152.4	152.5	152.7	152.6	152.4	152.2	151.9	151.7	151.9	152.2	152.4
117.5°	173.4	173.6	173.8	173.9	173.7	173.6	173.4	173.2	173.4	173.6	173.7
120°	187.8	188.2	188.5	188.5	188.0	187.6	187.1	186.6	187.1	187.6	188.0
122.5°	201.7	201.9	202.1	202.1	201.7	201.4	201.0	200.7	201.0	201.4	201.7
125°	222.7	222.8	223.0	223.0	222.7	222.5	222.2	222.0	222.2	222.5	222.7
127.5°	243.5	243.7	243.9	243.7	243.2	242.7	242.2	241.7	242.2	242.7	243.2
130°	257.1	257.3	257.5	257.3	256.7	256.1	255.4	254.8	255.4	256.1	256.7
132.5°	270.3	270.5	270.7	270.4	269.8	269.2	268.6	267.9	268.6	269.2	269.8
135°	289.9	290.0	290.1	289.9	289.4	288.9	288.5	288.0	288.5	288.9	289.4
137.5°	308.8	308.6	308.4	308.1	307.7	307.3	307.0	306.6	307.0	307.3	307.7
140°	321.3	321.3	321.2	321.0	320.6	320.2	319.8	319.4	319.8	320.2	320.6
142.5°	333.3	333.2	333.0	332.6	332.3	331.9	331.5	331.1	331.5	331.9	332.3
145°	350.7	350.4	350.2	350.0	349.8	349.7	349.5	349.4	349.5	349.7	349.8
147.5°	367.2	367.0	366.8	366.5	366.3	366.0	365.7	365.4	365.7	366.0	366.3
150°	377.6	377.5	377.3	377.2	377.0	376.8	376.7	376.5	376.7	376.8	377.0
152.5°	386.9	386.8	386.7	386.6	386.3	386.1	385.9	385.7	385.9	386.1	386.3
155°	400.2	400.2	400.1	400.1	400.1	400.1	400.1	400.1	400.1	400.1	400.1
157.5°	412.0	412.0	411.9	411.9	412.0	412.1	412.2	412.3	412.2	412.1	412.0
160°	419.3	419.3	419.3	419.4	419.6	419.7	419.9	420.0	419.9	419.7	419.6
162.5°	426.1	426.0	426.0	426.0	426.3	426.5	426.7	426.9	426.7	426.5	426.3
165°	434.6	434.6	434.6	434.7	435.0	435.3	435.6	435.8	435.6	435.3	435.0
167.5°	441.5	441.5	441.4	441.5	441.8	442.2	442.5	442.8	442.5	442.2	441.8
170°	445.4	445.4	445.4	445.6	445.9	446.2	446.5	446.8	446.5	446.2	445.9
172.5°	448.5	448.5	448.5	448.7	449.0	449.3	449.6	450.0	449.6	449.3	449.0
175°	451.8	451.8	451.8	452.0	452.3	452.6	452.9	453.2	452.9	452.6	452.3
177.5°	453.4	453.4	453.4	453.5	453.8	454.0	454.3	454.5	454.3	454.0	453.8
180°	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3



TEST NUMBER: P332241-840

CATALOG NUMBER: S123RDIP-S340D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	540.2	537.8	536.0	532.3	529.9	527.3	524.6	526.2	526.0	525.9	525.9
5°	522.1	516.6	511.7	505.3	501.4	496.4	492.7	492.2	493.1	489.9	488.0
7.5°	504.1	496.8	489.7	482.7	475.2	469.3	465.6	463.8	461.5	459.5	457.4
10°	491.5	482.8	475.9	467.3	459.3	452.2	447.8	444.6	443.0	441.4	438.3
12.5°	478.5	470.0	461.3	451.4	443.8	435.7	432.3	428.9	425.8	423.8	419.7
15°	459.5	448.5	439.3	428.9	420.4	412.4	407.8	400.9	400.0	397.6	393.3
17.5°	440.4	428.5	415.8	408.1	398.6	390.2	383.0	380.8	374.1	371.5	367.8
20°	425.4	414.3	404.7	394.6	380.7	372.9	367.3	364.3	358.8	355.5	353.1
22.5°	412.4	401.1	390.0	378.2	366.8	358.0	353.9	349.1	346.2	341.5	339.0
25°	393.8	381.6	368.2	355.5	347.3	340.7	334.1	329.8	325.6	323.5	318.8
27.5°	372.3	359.5	347.0	337.3	327.2	320.7	314.8	311.0	305.9	302.4	299.7
30°	360.4	345.4	334.6	325.9	313.0	306.8	302.4	297.6	293.9	290.1	287.5
32.5°	346.7	333.0	322.8	311.9	302.1	295.3	289.5	285.4	282.2	278.6	276.0
35°	325.2	313.7	303.1	292.3	284.9	278.1	271.2	267.7	264.7	261.4	259.0
37.5°	305.7	294.9	284.8	274.6	265.5	259.9	254.5	251.8	247.6	245.4	243.1
40°	293.7	283.1	272.3	262.4	253.0	248.7	243.8	239.7	236.0	234.3	231.8
42.5°	280.4	269.8	260.7	250.1	242.4	236.6	232.1	227.7	224.9	222.5	221.1
45°	260.9	251.6	242.6	232.0	224.7	219.7	214.6	210.6	208.0	206.3	203.8
47.5°	242.0	232.6	223.5	214.3	207.2	201.6	196.3	193.6	190.2	188.1	186.4
50°	228.2	219.7	210.2	201.7	194.6	188.9	184.7	181.2	178.1	175.5	174.3
52.5°	215.6	206.6	198.2	190.4	182.9	176.5	172.7	169.0	166.6	163.7	162.3
55°	194.8	186.1	179.0	171.3	164.0	158.5	153.9	150.6	148.2	144.9	143.1
57.5°	175.3	167.4	159.1	152.3	144.8	140.3	136.3	131.9	129.0	126.4	124.5
60°	162.1	153.2	145.8	139.6	132.9	127.0	123.5	120.0	116.9	114.3	112.7
62.5°	148.3	140.6	133.6	126.7	120.7	115.5	111.5	108.6	105.8	104.2	102.5
65°	127.2	121.2	114.1	108.5	102.8	99.1	95.7	93.2	91.3	90.1	88.7
67.5°	107.9	102.0	95.8	90.3	86.4	83.6	81.5	79.3	78.3	76.7	75.8
70°	95.3	89.2	83.7	79.5	75.7	73.6	72.2	70.6	69.7	67.8	66.9
72.5°	81.6	77.2	73.2	69.8	66.8	64.8	63.0	61.0	59.5	57.4	56.5
75°	64.2	60.2	57.2	54.8	52.9	50.4	47.8	45.6	44.9	44.2	44.0
77.5°	47.6	45.0	42.8	40.8	38.5	36.7	36.1	35.5	35.4	35.0	35.0
80°	37.4	35.0	33.4	31.1	29.7	29.7	29.7	29.2	29.4	29.4	29.4
82.5°	27.8	25.7	24.7	23.9	23.6	23.8	23.8	23.9	23.7	24.1	23.9
85°	14.3	14.5	15.0	14.8	15.0	15.0	15.6	15.2	15.6	15.0	15.6
87.5°	6.0	6.8	7.1	7.5	7.9	7.9	8.2	8.3	8.5	8.6	8.6
90°	3.5	4.4	5.5	6.5	7.6	8.6	8.9	9.2	9.5	9.8	10.1
92.5°	10.8	11.3	11.9	12.5	13.1	13.7	13.9	14.2	14.4	14.7	14.8
95°	23.2	23.8	24.5	25.1	25.8	26.5	26.8	27.1	27.4	27.7	27.9
97.5°	39.1	39.5	40.0	40.4	40.9	41.3	41.7	42.0	42.4	42.8	42.9
100°	50.4	50.9	51.3	51.7	52.1	52.4	52.7	52.9	53.2	53.4	53.6
102.5°	62.5	62.9	63.4	64.0	64.5	65.0	65.2	65.5	65.7	65.9	66.0
105°	80.9	81.4	82.1	82.8	83.5	84.2	84.2	84.2	84.2	84.2	84.3
107.5°	102.7	102.8	103.1	103.4	103.7	104.0	104.2	104.5	104.7	105.0	105.1
110°	116.6	116.7	116.9	117.1	117.2	117.4	117.8	118.1	118.4	118.7	118.8



TEST NUMBER: P332241-840

CATALOG NUMBER: S123RDIP-S340D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	130.7	130.7	130.8	130.8	130.8	130.9	131.2	131.6	132.0	132.4	132.5
115°	152.6	152.7	152.5	152.4	152.2	152.0	152.1	152.2	152.3	152.4	152.4
117.5°	173.9	173.8	173.6	173.4	173.2	173.0	173.0	173.0	173.0	173.0	172.8
120°	188.5	188.5	188.2	187.8	187.4	187.0	186.9	186.8	186.7	186.7	186.5
122.5°	202.1	202.1	201.9	201.7	201.5	201.3	201.1	200.9	200.7	200.5	200.3
125°	223.0	223.0	222.8	222.7	222.5	222.4	222.0	221.7	221.4	221.1	220.8
127.5°	243.7	243.9	243.7	243.5	243.4	243.2	242.8	242.3	241.9	241.4	241.0
130°	257.3	257.5	257.3	257.1	256.8	256.6	256.3	256.0	255.6	255.3	254.9
132.5°	270.4	270.7	270.5	270.3	270.1	270.0	269.6	269.2	268.8	268.5	268.1
135°	289.9	290.1	290.0	289.9	289.8	289.8	289.4	289.1	288.8	288.5	288.3
137.5°	308.1	308.4	308.6	308.8	309.0	309.2	308.9	308.6	308.3	307.9	307.6
140°	321.0	321.2	321.3	321.3	321.4	321.5	321.4	321.3	321.3	321.2	320.9
142.5°	332.6	333.0	333.2	333.3	333.4	333.6	333.5	333.4	333.3	333.3	333.0
145°	350.0	350.2	350.4	350.7	350.9	351.1	351.1	351.0	350.9	350.8	350.6
147.5°	366.5	366.8	367.0	367.2	367.4	367.7	367.7	367.7	367.7	367.7	367.4
150°	377.2	377.3	377.5	377.6	377.8	377.9	377.9	377.9	377.9	377.9	377.7
152.5°	386.6	386.7	386.8	386.9	387.0	387.1	387.2	387.3	387.5	387.6	387.4
155°	400.1	400.1	400.2	400.2	400.3	400.4	400.7	401.0	401.3	401.7	401.5
157.5°	411.9	411.9	412.0	412.0	412.1	412.2	412.5	412.8	413.2	413.5	413.4
160°	419.4	419.3	419.3	419.3	419.3	419.3	419.7	420.1	420.5	420.9	420.9
162.5°	426.0	426.0	426.0	426.1	426.2	426.2	426.6	427.0	427.4	427.8	427.7
165°	434.7	434.6	434.6	434.6	434.6	434.6	435.2	435.7	436.1	436.6	436.6
167.5°	441.5	441.4	441.5	441.5	441.6	441.7	442.1	442.6	443.1	443.6	443.6
170°	445.6	445.4	445.4	445.4	445.4	445.4	446.0	446.5	447.1	447.6	447.6
172.5°	448.7	448.5	448.5	448.5	448.5	448.5	449.0	449.5	450.0	450.5	450.5
175°	452.0	451.8	451.8	451.8	451.8	451.8	452.3	452.7	453.2	453.7	453.6
177.5°	453.5	453.4	453.4	453.4	453.4	453.4	453.8	454.2	454.5	454.9	454.9
180°	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3



TEST NUMBER: P332241-840

CATALOG NUMBER: S123RDIP-S340D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	523.6	523.4	523.6	522.9	523.6	523.4	523.6	525.9	525.9	526.0	526.2
5°	487.3	487.1	486.4	484.2	486.4	487.1	487.3	488.0	489.9	493.1	492.2
7.5°	455.4	455.1	453.1	453.1	453.1	455.1	455.4	457.4	459.5	461.5	463.8
10°	436.7	436.9	434.0	432.4	434.0	436.9	436.7	438.3	441.4	443.0	444.6
12.5°	418.4	417.4	415.1	413.2	415.1	417.4	418.4	419.7	423.8	425.8	428.9
15°	394.4	391.9	386.4	386.8	386.4	391.9	394.4	393.3	397.6	400.0	400.9
17.5°	366.0	364.3	364.2	360.8	364.2	364.3	366.0	367.8	371.5	374.1	380.8
20°	349.4	348.2	348.7	345.4	348.7	348.2	349.4	353.1	355.5	358.8	364.3
22.5°	336.4	335.2	333.3	332.2	333.3	335.2	336.4	339.0	341.5	346.2	349.1
25°	317.4	315.5	313.7	314.8	313.7	315.5	317.4	318.8	323.5	325.6	329.8
27.5°	298.4	297.0	295.1	294.9	295.1	297.0	298.4	299.7	302.4	305.9	311.0
30°	286.3	284.9	284.0	282.8	284.0	284.9	286.3	287.5	290.1	293.9	297.6
32.5°	274.1	273.8	272.2	271.9	272.2	273.8	274.1	276.0	278.6	282.2	285.4
35°	258.1	256.7	256.2	256.4	256.2	256.7	258.1	259.0	261.4	264.7	267.7
37.5°	242.9	241.1	240.1	239.3	240.1	241.1	242.9	243.1	245.4	247.6	251.8
40°	232.0	230.1	229.6	229.1	229.6	230.1	232.0	231.8	234.3	236.0	239.7
42.5°	219.7	219.0	218.7	217.8	218.7	219.0	219.7	221.1	222.5	224.9	227.7
45°	203.1	202.8	201.4	201.9	201.4	202.8	203.1	203.8	206.3	208.0	210.6
47.5°	185.4	184.4	183.4	184.1	183.4	184.4	185.4	186.4	188.1	190.2	193.6
50°	173.4	172.9	170.8	171.3	170.8	172.9	173.4	174.3	175.5	178.1	181.2
52.5°	161.4	159.6	158.8	158.4	158.8	159.6	161.4	162.3	163.7	166.6	169.0
55°	141.4	139.3	138.4	137.8	138.4	139.3	141.4	143.1	144.9	148.2	150.6
57.5°	121.8	121.3	120.5	121.0	120.5	121.3	121.8	124.5	126.4	129.0	131.9
60°	110.4	110.4	110.4	110.1	110.4	110.4	110.4	112.7	114.3	116.9	120.0
62.5°	101.5	100.9	100.8	101.1	100.8	100.9	101.5	102.5	104.2	105.8	108.6
65°	88.0	87.8	86.8	86.5	86.8	87.8	88.0	88.7	90.1	91.3	93.2
67.5°	75.2	74.4	74.1	73.8	74.1	74.4	75.2	75.8	76.7	78.3	79.3
70°	65.6	65.1	63.7	64.0	63.7	65.1	65.6	66.9	67.8	69.7	70.6
72.5°	55.3	54.8	54.5	54.2	54.5	54.8	55.3	56.5	57.4	59.5	61.0
75°	43.7	43.5	43.3	44.2	43.3	43.5	43.7	44.0	44.2	44.9	45.6
77.5°	35.0	35.0	35.2	34.8	35.2	35.0	35.0	35.0	35.0	35.4	35.5
80°	29.4	29.4	29.2	29.2	29.2	29.4	29.4	29.4	29.4	29.4	29.2
82.5°	23.5	23.7	23.9	23.5	23.9	23.7	23.5	23.9	24.1	23.7	23.9
85°	15.6	15.2	15.8	15.6	15.8	15.2	15.6	15.6	15.0	15.6	15.2
87.5°	9.0	8.7	8.7	8.9	8.7	8.7	9.0	8.6	8.6	8.5	8.3
90°	10.2	10.4	10.5	10.7	10.5	10.4	10.2	10.1	9.8	9.5	9.2
92.5°	14.7	14.6	14.5	14.4	14.5	14.6	14.7	14.8	14.7	14.4	14.2
95°	27.9	27.9	27.9	27.9	27.9	27.9	27.9	27.9	27.7	27.4	27.1
97.5°	42.9	42.9	42.8	42.8	42.8	42.9	42.9	42.9	42.8	42.4	42.0
100°	53.7	53.9	54.1	54.2	54.1	53.9	53.7	53.6	53.4	53.2	52.9
102.5°	66.0	66.0	65.9	65.9	65.9	66.0	66.0	66.0	65.9	65.7	65.5
105°	84.4	84.6	84.8	84.9	84.8	84.6	84.4	84.3	84.2	84.2	84.2
107.5°	105.0	104.9	104.8	104.7	104.8	104.9	105.0	105.1	105.0	104.7	104.5
110°	118.6	118.5	118.3	118.2	118.3	118.5	118.6	118.8	118.7	118.4	118.1



TEST NUMBER: P332241-840

CATALOG NUMBER: S123RDIP-S340D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	132.5	132.5	132.4	132.4	132.4	132.5	132.5	132.5	132.4	132.0	131.6
115°	152.3	152.2	152.1	152.0	152.1	152.2	152.3	152.4	152.4	152.3	152.2
117.5°	172.6	172.4	172.2	172.0	172.2	172.4	172.6	172.8	173.0	173.0	173.0
120°	186.4	186.2	186.1	185.9	186.1	186.2	186.4	186.5	186.7	186.7	186.8
122.5°	200.1	199.8	199.5	199.3	199.5	199.8	200.1	200.3	200.5	200.7	200.9
125°	220.5	220.2	219.7	219.4	219.7	220.2	220.5	220.8	221.1	221.4	221.7
127.5°	240.7	240.2	239.9	239.5	239.9	240.2	240.7	241.0	241.4	241.9	242.3
130°	254.4	253.8	253.3	252.7	253.3	253.8	254.4	254.9	255.3	255.6	256.0
132.5°	267.6	267.2	266.8	266.4	266.8	267.2	267.6	268.1	268.5	268.8	269.2
135°	288.1	287.9	287.8	287.6	287.8	287.9	288.1	288.3	288.5	288.8	289.1
137.5°	307.3	307.0	306.7	306.4	306.7	307.0	307.3	307.6	307.9	308.3	308.6
140°	320.3	319.8	319.2	318.7	319.2	319.8	320.3	320.9	321.2	321.3	321.3
142.5°	332.5	332.1	331.6	331.2	331.6	332.1	332.5	333.0	333.3	333.3	333.4
145°	350.3	350.0	349.7	349.4	349.7	350.0	350.3	350.6	350.8	350.9	351.0
147.5°	367.0	366.5	366.0	365.5	366.0	366.5	367.0	367.4	367.7	367.7	367.7
150°	377.2	376.8	376.3	375.8	376.3	376.8	377.2	377.7	377.9	377.9	377.9
152.5°	387.0	386.6	386.2	385.8	386.2	386.6	387.0	387.4	387.6	387.5	387.3
155°	401.0	400.4	399.9	399.3	399.9	400.4	401.0	401.5	401.7	401.3	401.0
157.5°	413.0	412.6	412.1	411.7	412.1	412.6	413.0	413.4	413.5	413.2	412.8
160°	420.6	420.3	420.0	419.7	420.0	420.3	420.6	420.9	420.9	420.5	420.1
162.5°	427.2	426.7	426.2	425.7	426.2	426.7	427.2	427.7	427.8	427.4	427.0
165°	436.0	435.5	434.8	434.3	434.8	435.5	436.0	436.6	436.6	436.1	435.7
167.5°	443.1	442.6	442.1	441.7	442.1	442.6	443.1	443.6	443.6	443.1	442.6
170°	447.1	446.5	446.0	445.4	446.0	446.5	447.1	447.6	447.6	447.1	446.5
172.5°	449.9	449.4	448.8	448.3	448.8	449.4	449.9	450.5	450.5	450.0	449.5
175°	453.1	452.5	452.0	451.4	452.0	452.5	453.1	453.6	453.7	453.2	452.7
177.5°	454.5	454.0	453.6	453.1	453.6	454.0	454.5	454.9	454.9	454.5	454.2
180°	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3



TEST NUMBER: P332241-840

CATALOG NUMBER: S123RDIP-S340D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	524.6	527.3	529.9	532.3	536.0	537.8	540.2	541.2	543.9	548.1	551.5
5°	492.7	496.4	501.4	505.3	511.7	516.6	522.1	527.3	533.4	542.1	549.9
7.5°	465.6	469.3	475.2	482.7	489.7	496.8	504.1	511.2	519.9	532.4	544.7
10°	447.8	452.2	459.3	467.3	475.9	482.8	491.5	500.4	511.3	525.6	540.5
12.5°	432.3	435.7	443.8	451.4	461.3	470.0	478.5	489.0	501.3	516.5	534.4
15°	407.8	412.4	420.4	428.9	439.3	448.5	459.5	472.2	484.2	503.0	524.6
17.5°	383.0	390.2	398.6	408.1	415.8	428.5	440.4	453.4	468.3	488.2	512.0
20°	367.3	372.9	380.7	394.6	404.7	414.3	425.4	441.6	455.2	477.9	502.5
22.5°	353.9	358.0	366.8	378.2	390.0	401.1	412.4	427.9	444.7	466.2	492.9
25°	334.1	340.7	347.3	355.5	368.2	381.6	393.8	407.1	425.0	447.8	476.7
27.5°	314.8	320.7	327.2	337.3	347.0	359.5	372.3	387.4	406.6	430.7	460.1
30°	302.4	306.8	313.0	325.9	334.6	345.4	360.4	373.9	391.7	417.4	448.5
32.5°	289.5	295.3	302.1	311.9	322.8	333.0	346.7	361.2	379.5	404.8	436.6
35°	271.2	278.1	284.9	292.3	303.1	313.7	325.2	341.1	359.7	384.3	415.5
37.5°	254.5	259.9	265.5	274.6	284.8	294.9	305.7	321.4	338.9	365.4	394.0
40°	243.8	248.7	253.0	262.4	272.3	283.1	293.7	307.5	326.3	351.0	378.8
42.5°	232.1	236.6	242.4	250.1	260.7	269.8	280.4	293.6	311.2	336.4	360.7
45°	214.6	219.7	224.7	232.0	242.6	251.6	260.9	273.4	291.5	312.3	333.9
47.5°	196.3	201.6	207.2	214.3	223.5	232.6	242.0	253.0	269.5	289.8	304.5
50°	184.7	188.9	194.6	201.7	210.2	219.7	228.2	240.2	256.0	272.0	284.7
52.5°	172.7	176.5	182.9	190.4	198.2	206.6	215.6	225.9	240.1	255.2	265.3
55°	153.9	158.5	164.0	171.3	179.0	186.1	194.8	205.4	216.7	228.0	234.8
57.5°	136.3	140.3	144.8	152.3	159.1	167.4	175.3	183.5	194.0	202.5	206.9
60°	123.5	127.0	132.9	139.6	145.8	153.2	162.1	170.4	178.3	185.2	188.6
62.5°	111.5	115.5	120.7	126.7	133.6	140.6	148.3	155.3	162.4	168.2	170.7
65°	95.7	99.1	102.8	108.5	114.1	121.2	127.2	134.3	139.6	142.8	144.9
67.5°	81.5	83.6	86.4	90.3	95.8	102.0	107.9	113.4	117.8	120.0	121.9
70°	72.2	73.6	75.7	79.5	83.7	89.2	95.3	99.3	103.0	104.9	106.8
72.5°	63.0	64.8	66.8	69.8	73.2	77.2	81.6	86.4	88.6	90.8	91.9
75°	47.8	50.4	52.9	54.8	57.2	60.2	64.2	67.3	68.5	70.4	70.6
77.5°	36.1	36.7	38.5	40.8	42.8	45.0	47.6	50.3	50.9	51.8	52.5
80°	29.7	29.7	29.7	31.1	33.4	35.0	37.4	38.8	39.8	40.0	40.2
82.5°	23.8	23.8	23.6	23.9	24.7	25.7	27.8	29.4	30.2	30.0	29.5
85°	15.6	15.0	15.0	14.8	15.0	14.5	14.3	15.2	16.7	16.7	16.3
87.5°	8.2	7.9	7.9	7.5	7.1	6.8	6.0	6.0	5.9	6.5	6.1
90°	8.9	8.6	7.6	6.5	5.5	4.4	3.5	2.7	1.9	1.1	0.4
92.5°	13.9	13.7	13.1	12.5	11.9	11.3	10.8	10.3	9.7	9.2	8.7
95°	26.8	26.5	25.8	25.1	24.5	23.8	23.2	22.7	22.1	21.6	21.1
97.5°	41.7	41.3	40.9	40.4	40.0	39.5	39.1	38.7	38.3	37.8	37.4
100°	52.7	52.4	52.1	51.7	51.3	50.9	50.4	50.0	49.5	49.0	48.6
102.5°	65.2	65.0	64.5	64.0	63.4	62.9	62.5	62.2	61.9	61.7	61.4
105°	84.2	84.2	83.5	82.8	82.1	81.4	80.9	80.8	80.6	80.5	80.3
107.5°	104.2	104.0	103.7	103.4	103.1	102.8	102.7	102.6	102.5	102.4	102.3
110°	117.8	117.4	117.2	117.1	116.9	116.7	116.6	116.4	116.3	116.1	116.0



TEST NUMBER: P332241-840

CATALOG NUMBER: S123RDIP-S340D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	131.2	130.9	130.8	130.8	130.8	130.7	130.7	130.6	130.5	130.4	130.3
115°	152.1	152.0	152.2	152.4	152.5	152.7	152.6	152.4	152.2	151.9	151.7
117.5°	173.0	173.0	173.2	173.4	173.6	173.8	173.9	173.7	173.6	173.4	173.2
120°	186.9	187.0	187.4	187.8	188.2	188.5	188.5	188.0	187.6	187.1	186.6
122.5°	201.1	201.3	201.5	201.7	201.9	202.1	202.1	201.7	201.4	201.0	200.7
125°	222.0	222.4	222.5	222.7	222.8	223.0	223.0	222.7	222.5	222.2	222.0
127.5°	242.8	243.2	243.4	243.5	243.7	243.9	243.7	243.2	242.7	242.2	241.7
130°	256.3	256.6	256.8	257.1	257.3	257.5	257.3	256.7	256.1	255.4	254.8
132.5°	269.6	270.0	270.1	270.3	270.5	270.7	270.4	269.8	269.2	268.6	267.9
135°	289.4	289.8	289.8	289.9	290.0	290.1	289.9	289.4	288.9	288.5	288.0
137.5°	308.9	309.2	309.0	308.8	308.6	308.4	308.1	307.7	307.3	307.0	306.6
140°	321.4	321.5	321.4	321.3	321.3	321.2	321.0	320.6	320.2	319.8	319.4
142.5°	333.5	333.6	333.4	333.3	333.2	333.0	332.6	332.3	331.9	331.5	331.1
145°	351.1	351.1	350.9	350.7	350.4	350.2	350.0	349.8	349.7	349.5	349.4
147.5°	367.7	367.7	367.4	367.2	367.0	366.8	366.5	366.3	366.0	365.7	365.4
150°	377.9	377.9	377.8	377.6	377.5	377.3	377.2	377.0	376.8	376.7	376.5
152.5°	387.2	387.1	387.0	386.9	386.8	386.7	386.6	386.3	386.1	385.9	385.7
155°	400.7	400.4	400.3	400.2	400.2	400.1	400.1	400.1	400.1	400.1	400.1
157.5°	412.5	412.2	412.1	412.0	412.0	411.9	411.9	412.0	412.1	412.2	412.3
160°	419.7	419.3	419.3	419.3	419.3	419.3	419.4	419.6	419.7	419.9	420.0
162.5°	426.6	426.2	426.2	426.1	426.0	426.0	426.0	426.3	426.5	426.7	426.9
165°	435.2	434.6	434.6	434.6	434.6	434.6	434.7	435.0	435.3	435.6	435.8
167.5°	442.1	441.7	441.6	441.5	441.5	441.4	441.5	441.8	442.2	442.5	442.8
170°	446.0	445.4	445.4	445.4	445.4	445.4	445.6	445.9	446.2	446.5	446.8
172.5°	449.0	448.5	448.5	448.5	448.5	448.5	448.7	449.0	449.3	449.6	450.0
175°	452.3	451.8	451.8	451.8	451.8	451.8	452.0	452.3	452.6	452.9	453.2
177.5°	453.8	453.4	453.4	453.4	453.4	453.4	453.5	453.8	454.0	454.3	454.5
180°	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3



TEST NUMBER: P332241-840

CATALOG NUMBER: S123RDIP-S340D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	552.6	554.7	557.3	561.3	564.3	566.9	567.4	568.3	570.2	573.3	575.7
5°	556.2	561.6	570.3	578.8	587.9	595.5	602.6	607.5	612.2	622.1	630.1
7.5°	555.0	567.1	580.8	595.9	611.4	626.2	640.1	652.5	664.8	679.2	695.6
10°	554.3	568.5	586.8	606.3	627.7	648.6	668.9	684.7	703.0	719.5	740.4
12.5°	550.8	571.1	593.0	617.9	644.3	668.4	695.1	716.8	737.8	761.6	786.0
15°	546.0	570.8	598.5	631.7	671.8	700.8	728.2	766.1	791.9	817.8	852.6
17.5°	537.6	567.7	602.4	645.5	678.8	718.1	759.1	789.1	823.9	860.4	891.9
20°	530.8	565.8	604.7	647.0	689.6	732.2	771.9	807.7	843.7	885.9	911.7
22.5°	524.0	558.7	599.1	644.0	689.7	734.7	779.6	821.6	862.1	904.6	937.7
25°	509.6	550.8	594.5	640.5	685.6	735.0	788.6	835.5	885.6	929.4	960.7
27.5°	495.0	532.8	576.3	622.9	673.1	731.4	794.6	847.8	898.0	929.4	939.2
30°	481.8	521.8	561.9	609.2	663.5	728.6	795.7	856.7	897.8	911.5	901.3
32.5°	468.5	504.7	544.3	592.8	650.5	721.6	797.2	851.4	876.2	865.8	824.6
35°	444.9	477.6	515.9	564.4	630.8	717.8	791.0	827.7	821.6	762.8	685.1
37.5°	419.7	446.4	481.8	532.5	610.4	702.6	764.3	769.7	716.7	626.4	536.7
40°	399.7	423.7	460.2	513.1	594.5	687.5	737.4	715.5	633.4	532.9	458.1
42.5°	380.3	400.6	435.8	492.8	579.5	666.9	697.3	649.6	554.9	459.9	391.8
45°	347.5	366.6	401.8	460.4	548.7	627.7	623.7	540.9	446.1	369.6	313.2
47.5°	316.4	333.1	366.2	426.0	512.5	568.9	531.5	443.3	362.9	301.5	261.3
50°	294.4	310.8	343.8	402.8	483.5	524.6	471.3	386.4	312.7	261.9	229.8
52.5°	273.3	289.3	319.4	377.0	448.5	473.1	415.8	337.0	275.6	231.8	204.3
55°	243.8	256.0	283.1	338.1	391.5	397.2	339.0	273.2	222.6	192.0	173.2
57.5°	213.7	224.2	251.0	294.8	332.2	329.3	274.3	217.2	183.2	160.5	146.8
60°	194.1	204.5	228.0	265.6	293.9	284.0	233.4	187.5	158.3	141.7	130.8
62.5°	175.8	183.9	206.0	233.5	253.8	242.6	199.5	161.6	138.4	124.3	115.7
65°	149.4	156.0	173.6	188.0	199.2	188.4	152.7	126.3	109.7	99.8	93.9
67.5°	124.3	128.5	139.6	144.8	152.8	140.9	114.8	97.1	87.7	79.4	75.2
70°	108.5	111.5	117.4	121.7	123.7	111.5	92.2	79.3	71.3	65.4	62.8
72.5°	92.6	95.3	96.5	100.0	98.9	87.5	74.1	63.8	58.1	54.1	50.8
75°	70.8	72.0	70.8	69.4	66.3	58.4	49.2	44.0	39.8	37.9	36.7
77.5°	51.6	51.2	49.7	47.5	42.2	37.2	32.2	30.5	28.7	27.7	27.3
80°	39.8	38.8	37.4	33.8	29.4	25.9	24.7	23.5	22.8	21.6	21.4
82.5°	29.6	29.0	26.7	23.7	20.6	18.9	18.0	17.5	16.8	16.2	16.2
85°	15.8	15.0	12.4	10.8	10.4	9.9	9.7	9.7	8.7	8.5	8.5
87.5°	5.4	4.3	4.3	3.9	4.0	3.9	4.3	4.1	4.1	4.4	4.1
90°	1.1	1.9	2.7	3.5	4.4	5.5	6.5	7.6	8.6	8.9	9.2
92.5°	9.2	9.7	10.3	10.8	11.3	11.9	12.5	13.1	13.7	13.9	14.2
95°	21.6	22.1	22.7	23.2	23.8	24.5	25.1	25.8	26.5	26.8	27.1
97.5°	37.8	38.3	38.7	39.1	39.5	40.0	40.4	40.9	41.3	41.7	42.0
100°	49.0	49.5	50.0	50.4	50.9	51.3	51.7	52.1	52.4	52.7	52.9
102.5°	61.7	61.9	62.2	62.5	62.9	63.4	64.0	64.5	65.0	65.2	65.5
105°	80.5	80.6	80.8	80.9	81.4	82.1	82.8	83.5	84.2	84.2	84.2
107.5°	102.4	102.5	102.6	102.7	102.8	103.1	103.4	103.7	104.0	104.2	104.5
110°	116.1	116.3	116.4	116.6	116.7	116.9	117.1	117.2	117.4	117.8	118.1



TEST NUMBER: P332241-840

CATALOG NUMBER: S123RDIP-S340D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	130.4	130.5	130.6	130.7	130.7	130.8	130.8	130.8	130.9	131.2	131.6
115°	151.9	152.2	152.4	152.6	152.7	152.5	152.4	152.2	152.0	152.1	152.2
117.5°	173.4	173.6	173.7	173.9	173.8	173.6	173.4	173.2	173.0	173.0	173.0
120°	187.1	187.6	188.0	188.5	188.5	188.2	187.8	187.4	187.0	186.9	186.8
122.5°	201.0	201.4	201.7	202.1	202.1	201.9	201.7	201.5	201.3	201.1	200.9
125°	222.2	222.5	222.7	223.0	223.0	222.8	222.7	222.5	222.4	222.0	221.7
127.5°	242.2	242.7	243.2	243.7	243.9	243.7	243.5	243.4	243.2	242.8	242.3
130°	255.4	256.1	256.7	257.3	257.5	257.3	257.1	256.8	256.6	256.3	256.0
132.5°	268.6	269.2	269.8	270.4	270.7	270.5	270.3	270.1	270.0	269.6	269.2
135°	288.5	288.9	289.4	289.9	290.1	290.0	289.9	289.8	289.8	289.4	289.1
137.5°	307.0	307.3	307.7	308.1	308.4	308.6	308.8	309.0	309.2	308.9	308.6
140°	319.8	320.2	320.6	321.0	321.2	321.3	321.3	321.4	321.5	321.4	321.3
142.5°	331.5	331.9	332.3	332.6	333.0	333.2	333.3	333.4	333.6	333.5	333.4
145°	349.5	349.7	349.8	350.0	350.2	350.4	350.7	350.9	351.1	351.1	351.0
147.5°	365.7	366.0	366.3	366.5	366.8	367.0	367.2	367.4	367.7	367.7	367.7
150°	376.7	376.8	377.0	377.2	377.3	377.5	377.6	377.8	377.9	377.9	377.9
152.5°	385.9	386.1	386.3	386.6	386.7	386.8	386.9	387.0	387.1	387.2	387.3
155°	400.1	400.1	400.1	400.1	400.1	400.2	400.2	400.3	400.4	400.7	401.0
157.5°	412.2	412.1	412.0	411.9	411.9	412.0	412.0	412.1	412.2	412.5	412.8
160°	419.9	419.7	419.6	419.4	419.3	419.3	419.3	419.3	419.3	419.7	420.1
162.5°	426.7	426.5	426.3	426.0	426.0	426.0	426.1	426.2	426.2	426.6	427.0
165°	435.6	435.3	435.0	434.7	434.6	434.6	434.6	434.6	434.6	435.2	435.7
167.5°	442.5	442.2	441.8	441.5	441.4	441.5	441.5	441.6	441.7	442.1	442.6
170°	446.5	446.2	445.9	445.6	445.4	445.4	445.4	445.4	445.4	446.0	446.5
172.5°	449.6	449.3	449.0	448.7	448.5	448.5	448.5	448.5	448.5	449.0	449.5
175°	452.9	452.6	452.3	452.0	451.8	451.8	451.8	451.8	451.8	452.3	452.7
177.5°	454.3	454.0	453.8	453.5	453.4	453.4	453.4	453.4	453.4	453.8	454.2
180°	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3



TEST NUMBER: P332241-840

CATALOG NUMBER: S123RDIP-S340D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	579.8	579.8	580.5	583.3	583.7	586.1	585.4
5°	637.1	641.6	643.3	650.4	654.5	656.4	652.7
7.5°	707.3	719.9	725.9	733.4	739.8	741.8	736.7
10°	758.5	771.7	782.7	789.6	796.0	800.2	805.6
12.5°	808.0	824.3	834.8	844.3	850.9	856.3	857.2
15°	861.8	886.3	904.8	918.6	925.3	928.9	927.5
17.5°	916.0	938.8	952.0	965.9	975.3	975.8	976.1
20°	946.7	968.9	984.2	994.5	1005.1	1004.6	1007.0
22.5°	967.2	984.7	996.4	1003.9	1007.5	1005.7	1006.2
25°	976.8	982.1	980.0	968.0	964.8	953.8	955.7
27.5°	927.4	902.9	877.6	845.1	819.3	798.8	799.8
30°	860.2	816.9	767.5	726.1	688.9	678.5	656.4
32.5°	766.3	701.4	643.5	604.8	573.0	564.3	545.0
35°	607.0	543.9	484.4	448.7	434.5	414.8	414.5
37.5°	471.8	416.3	384.9	358.0	344.0	331.9	330.8
40°	396.9	353.7	329.8	310.5	296.7	287.7	285.6
42.5°	344.6	309.6	287.3	275.4	264.7	260.0	256.6
45°	281.3	257.8	242.4	231.6	226.6	223.1	221.2
47.5°	235.4	219.6	209.0	201.8	197.8	194.1	195.1
50°	210.4	197.4	189.7	182.8	179.8	177.1	177.4
52.5°	190.2	178.5	172.3	167.3	163.6	161.7	160.9
55°	161.4	154.1	147.7	144.2	142.1	139.6	138.9
57.5°	137.6	132.0	126.8	122.9	122.3	119.9	120.2
60°	121.9	117.1	112.9	110.8	109.2	107.0	107.8
62.5°	108.9	104.9	101.1	99.4	97.7	96.1	96.4
65°	89.2	85.4	83.0	82.1	81.4	80.7	80.0
67.5°	71.1	68.8	67.3	65.2	63.8	63.6	62.9
70°	59.8	56.7	54.1	51.5	50.8	50.6	50.8
72.5°	47.9	45.9	45.2	44.0	43.8	43.2	43.6
75°	36.0	35.2	34.8	33.8	33.8	33.8	33.8
77.5°	26.6	26.2	25.9	25.7	25.4	25.0	25.0
80°	20.7	20.5	20.0	20.0	19.8	20.0	19.8
82.5°	15.7	15.6	15.1	15.1	14.8	14.7	14.8
85°	8.0	7.8	8.3	7.8	8.0	7.6	8.0
87.5°	4.1	4.2	4.0	4.1	3.9	4.3	4.0
90°	9.5	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	14.4	14.7	14.8	14.7	14.6	14.5	14.4
95°	27.4	27.7	27.9	27.9	27.9	27.9	27.9
97.5°	42.4	42.8	42.9	42.9	42.9	42.8	42.8
100°	53.2	53.4	53.6	53.7	53.9	54.1	54.2
102.5°	65.7	65.9	66.0	66.0	66.0	65.9	65.9
105°	84.2	84.2	84.3	84.4	84.6	84.8	84.9
107.5°	104.7	105.0	105.1	105.0	104.9	104.8	104.7
110°	118.4	118.7	118.8	118.6	118.5	118.3	118.2



TEST NUMBER: P332241-840

CATALOG NUMBER: S123RDIP-S340D365U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	132.0	132.4	132.5	132.5	132.5	132.4	132.4
115°	152.3	152.4	152.4	152.3	152.2	152.1	152.0
117.5°	173.0	173.0	172.8	172.6	172.4	172.2	172.0
120°	186.7	186.7	186.5	186.4	186.2	186.1	185.9
122.5°	200.7	200.5	200.3	200.1	199.8	199.5	199.3
125°	221.4	221.1	220.8	220.5	220.2	219.7	219.4
127.5°	241.9	241.4	241.0	240.7	240.2	239.9	239.5
130°	255.6	255.3	254.9	254.4	253.8	253.3	252.7
132.5°	268.8	268.5	268.1	267.6	267.2	266.8	266.4
135°	288.8	288.5	288.3	288.1	287.9	287.8	287.6
137.5°	308.3	307.9	307.6	307.3	307.0	306.7	306.4
140°	321.3	321.2	320.9	320.3	319.8	319.2	318.7
142.5°	333.3	333.3	333.0	332.5	332.1	331.6	331.2
145°	350.9	350.8	350.6	350.3	350.0	349.7	349.4
147.5°	367.7	367.7	367.4	367.0	366.5	366.0	365.5
150°	377.9	377.9	377.7	377.2	376.8	376.3	375.8
152.5°	387.5	387.6	387.4	387.0	386.6	386.2	385.8
155°	401.3	401.7	401.5	401.0	400.4	399.9	399.3
157.5°	413.2	413.5	413.4	413.0	412.6	412.1	411.7
160°	420.5	420.9	420.9	420.6	420.3	420.0	419.7
162.5°	427.4	427.8	427.7	427.2	426.7	426.2	425.7
165°	436.1	436.6	436.6	436.0	435.5	434.8	434.3
167.5°	443.1	443.6	443.6	443.1	442.6	442.1	441.7
170°	447.1	447.6	447.6	447.1	446.5	446.0	445.4
172.5°	450.0	450.5	450.5	449.9	449.4	448.8	448.3
175°	453.2	453.7	453.6	453.1	452.5	452.0	451.4
177.5°	454.5	454.9	454.9	454.5	454.0	453.6	453.1
180°	454.3	454.3	454.3	454.3	454.3	454.3	454.3

(END OF REPORT)