

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332248-840

Luminaire Tested: **S123RDIP-S340D585U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332248-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D585U840-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3511.4 lumens  
Efficiency: N/A  
Efficacy: 137.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332248-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332248-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	92	88	85	87	84	80	78	68	66	64	54	53	52	41	41	40	34
2	88	81	75	70	79	74	69	64	60	57	54	48	46	44	37	35	34	29
3	80	71	64	59	73	65	59	54	54	49	46	43	40	38	33	31	30	25
4	73	63	56	50	67	58	51	46	48	43	39	39	35	32	30	28	26	22
5	68	56	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20	17
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18	15
8	53	42	34	29	49	38	32	27	32	27	24	26	23	20	21	18	16	14
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	19	17	15	13
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	5916	5916	5916	5916
5°	7052	5942	5232	5942
10°	8805	5908	4726	5908
15°	10336	5846	4310	5846
20°	11535	5756	3956	5756
25°	11351	5662	3739	5662
30°	8158	5574	3515	5574
35°	5447	5460	3369	5460
40°	4013	5323	3219	5323
45°	3367	5083	3073	5083
50°	2971	4767	2869	4767
55°	2607	4406	2586	4406
60°	2321	4060	2370	4060
65°	2038	3691	2203	3691
70°	1599	3361	2014	3361
75°	1406	2936	1838	2936
80°	1227	2492	1810	2492
85°	988	2013	1927	2013



TEST NUMBER: P332248-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.0	1.5
10°-20°	168.9	4.8
20°-30°	265.3	7.6
30°-40°	276.8	7.9
40°-50°	236.9	6.7
50°-60°	180.5	5.1
60°-70°	115.7	3.3
70°-80°	55.7	1.6
80°-90°	16.9	0.5
90°-100°	158.3	4.5
100°-110°	448.4	12.8
110°-120°	441.1	12.6
120°-130°	351.8	10.0
130°-140°	277.4	7.9
140°-150°	207.0	5.9
150°-160°	144.3	4.1
160°-170°	84.8	2.4
170°-180°	27.6	0.8
0°-30°	488.2	13.9
0°-40°	764.9	21.8
0°-60°	1182.3	33.7
0°-90°	1370.6	39.0
90°-120°	1047.8	29.8
90°-150°	1884.1	53.7
90°-180°	2141.0	61.0
0°-180°	3511.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	550	550	550	550	550	
5°	653	550	484	550	653	67
15°	928	525	387	525	928	263
25°	956	477	315	477	956	411
35°	414	416	256	416	414	272
45°	221	334	202	334	221	174
55°	139	235	138	235	139	126
65°	80	145	86	145	80	79
75°	34	71	44	71	34	36
85°	8	16	16	16	8	10
90°	17	1	17	1	17	9
95°	67	20	67	20	67	120
105°	733	67	733	67	733	723
115°	891	118	891	118	891	866
125°	703	164	703	164	703	637
135°	570	192	570	192	570	442
145°	445	219	445	219	445	283
155°	369	249	369	249	369	172
165°	322	272	322	272	322	92
175°	290	284	290	284	290	28
180°	285	285	285	285	285	



TEST NUMBER: P332248-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	585.4	586.1	583.7	583.3	580.5	579.8	579.8	575.7	573.3	570.2	568.3
5°	652.7	656.4	654.5	650.4	643.3	641.6	637.1	630.1	622.1	612.2	607.5
7.5°	736.7	741.8	739.8	733.4	725.9	719.9	707.3	695.6	679.2	664.8	652.5
10°	805.6	800.2	796.0	789.6	782.7	771.7	758.5	740.4	719.5	703.0	684.7
12.5°	857.2	856.3	850.9	844.3	834.8	824.3	808.0	786.0	761.6	737.8	716.8
15°	927.5	928.9	925.3	918.6	904.8	886.3	861.8	852.6	817.8	791.9	766.1
17.5°	976.1	975.8	975.3	965.9	952.0	938.8	916.0	891.9	860.4	823.9	789.1
20°	1007.0	1004.6	1005.1	994.5	984.2	968.9	946.7	911.7	885.9	843.7	807.7
22.5°	1006.2	1005.7	1007.5	1003.9	996.4	984.7	967.2	937.7	904.6	862.1	821.6
25°	955.7	953.8	964.8	968.0	980.0	982.1	976.8	960.7	929.4	885.6	835.5
27.5°	799.8	798.8	819.3	845.1	877.6	902.9	927.4	939.2	929.4	898.0	847.8
30°	656.4	678.5	688.9	726.1	767.5	816.9	860.2	901.3	911.5	897.8	856.7
32.5°	545.0	564.3	573.0	604.8	643.5	701.4	766.3	824.6	865.8	876.2	851.4
35°	414.5	414.8	434.5	448.7	484.4	543.9	607.0	685.1	762.8	821.6	827.7
37.5°	330.8	331.9	344.0	358.0	384.9	416.3	471.8	536.7	626.4	716.7	769.7
40°	285.6	287.7	296.7	310.5	329.8	353.7	396.9	458.1	532.9	633.4	715.5
42.5°	256.6	260.0	264.7	275.4	287.3	309.6	344.6	391.8	459.9	554.9	649.6
45°	221.2	223.1	226.6	231.6	242.4	257.8	281.3	313.2	369.6	446.1	540.9
47.5°	195.1	194.1	197.8	201.8	209.0	219.6	235.4	261.3	301.5	362.9	443.3
50°	177.4	177.1	179.8	182.8	189.7	197.4	210.4	229.8	261.9	312.7	386.4
52.5°	160.9	161.7	163.6	167.3	172.3	178.5	190.2	204.3	231.8	275.6	337.0
55°	138.9	139.6	142.1	144.2	147.7	154.1	161.4	173.2	192.0	222.6	273.2
57.5°	120.2	119.9	122.3	122.9	126.8	132.0	137.6	146.8	160.5	183.2	217.2
60°	107.8	107.0	109.2	110.8	112.9	117.1	121.9	130.8	141.7	158.3	187.5
62.5°	96.4	96.1	97.7	99.4	101.1	104.9	108.9	115.7	124.3	138.4	161.6
65°	80.0	80.7	81.4	82.1	83.0	85.4	89.2	93.9	99.8	109.7	126.3
67.5°	62.9	63.6	63.8	65.2	67.3	68.8	71.1	75.2	79.4	87.7	97.1
70°	50.8	50.6	50.8	51.5	54.1	56.7	59.8	62.8	65.4	71.3	79.3
72.5°	43.6	43.2	43.8	44.0	45.2	45.9	47.9	50.8	54.1	58.1	63.8
75°	33.8	33.8	33.8	33.8	34.8	35.2	36.0	36.7	37.9	39.8	44.0
77.5°	25.0	25.0	25.4	25.7	25.9	26.2	26.6	27.3	27.7	28.7	30.5
80°	19.8	20.0	19.8	20.0	20.0	20.5	20.7	21.4	21.6	22.8	23.5
82.5°	14.8	14.7	14.8	15.1	15.1	15.6	15.7	16.2	16.2	16.8	17.5
85°	8.0	7.6	8.0	7.8	8.3	7.8	8.0	8.5	8.5	8.7	9.7
87.5°	5.3	5.8	5.3	5.3	5.5	5.4	5.3	5.2	5.4	5.4	5.2
90°	16.7	17.3	16.7	16.2	16.7	15.6	14.9	14.4	13.8	14.4	12.6
92.5°	27.8	28.8	28.2	30.0	31.0	34.0	38.5	48.5	66.9	88.6	97.5
95°	66.9	69.1	73.1	78.4	89.3	110.0	140.6	207.3	277.0	341.5	304.2
97.5°	181.9	186.8	202.4	228.3	270.8	339.7	414.0	516.9	566.3	529.4	387.5
100°	361.1	360.6	383.0	425.1	483.2	565.0	632.5	679.1	658.9	545.4	368.6
102.5°	529.8	543.0	561.8	595.1	640.4	692.3	731.5	733.1	663.6	515.5	341.0
105°	732.7	735.6	754.0	775.9	802.3	817.4	806.4	748.8	628.4	463.1	307.0
107.5°	849.5	854.7	861.0	868.4	867.9	847.4	797.0	703.4	566.9	416.8	285.4
110°	897.4	898.6	899.7	895.1	879.0	838.7	766.1	660.0	528.2	390.5	277.0



TEST NUMBER: P332248-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	907.1	906.9	902.5	888.2	858.7	806.9	725.5	617.2	494.5	373.0	272.5
115°	891.1	888.2	876.7	851.3	808.1	745.4	660.7	560.5	453.9	354.3	270.7
117.5°	840.1	836.3	819.6	790.6	745.6	681.9	605.8	519.3	429.4	343.2	271.8
120°	797.8	794.3	780.5	748.2	702.8	644.5	575.4	497.7	416.5	338.1	273.6
122.5°	758.1	753.8	738.5	709.5	669.0	615.0	551.0	480.6	405.9	334.9	276.8
125°	702.8	698.7	684.3	658.9	622.1	576.0	520.7	457.9	392.2	330.6	281.7
127.5°	657.1	653.4	640.4	618.7	585.9	544.0	494.1	438.1	380.3	328.5	287.2
130°	631.3	626.7	614.6	593.9	563.3	524.1	477.5	425.7	373.9	327.2	290.8
132.5°	605.9	602.7	592.0	571.3	542.6	505.2	461.8	414.1	367.8	326.7	293.7
135°	569.7	565.6	555.2	538.0	509.8	477.0	439.5	398.6	360.0	326.0	297.8
137.5°	531.3	528.7	519.9	502.4	478.7	450.2	418.0	384.5	353.3	324.8	300.5
140°	504.5	505.1	495.9	479.8	457.9	433.1	405.5	376.2	349.0	324.3	302.4
142.5°	479.7	480.3	472.0	457.7	439.0	417.5	393.5	368.3	345.4	323.4	303.8
145°	445.2	444.1	439.5	427.4	413.0	396.3	377.9	358.8	340.4	321.9	304.7
147.5°	416.9	416.5	412.0	403.8	392.9	381.1	366.2	351.1	335.6	319.8	304.7
150°	400.3	400.3	396.9	390.5	381.9	370.9	358.8	345.6	332.3	317.9	304.7
152.5°	386.5	386.5	384.5	378.5	371.7	362.6	351.9	340.5	328.7	315.7	303.4
155°	369.2	368.6	367.5	362.8	357.7	350.8	342.1	333.0	323.2	311.6	301.8
157.5°	353.5	353.6	352.6	349.2	344.7	339.3	332.5	324.9	316.9	308.0	299.8
160°	343.3	343.9	343.9	340.4	336.4	332.3	326.6	320.2	312.8	305.3	298.9
162.5°	334.1	334.7	334.7	331.6	329.0	325.5	320.1	314.8	308.6	302.6	297.1
165°	321.9	321.9	322.6	320.2	317.9	315.1	311.0	307.6	303.0	298.4	294.4
167.5°	310.4	310.4	311.0	309.4	308.4	306.3	304.0	301.3	297.6	294.2	291.5
170°	303.6	303.6	304.2	303.0	302.4	301.2	298.9	297.2	294.4	291.4	289.7
172.5°	297.1	297.6	298.6	297.4	297.3	296.6	294.8	293.6	291.1	289.1	288.3
175°	289.7	290.3	290.8	290.3	290.3	290.3	289.1	288.6	287.4	286.3	286.3
177.5°	285.5	285.5	286.4	285.9	286.4	286.4	285.9	285.5	285.0	284.6	285.0
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P332248-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	567.4	566.9	564.3	561.3	557.3	554.7	552.6	551.5	548.1	543.9	541.2
5°	602.6	595.5	587.9	578.8	570.3	561.6	556.2	549.9	542.1	533.4	527.3
7.5°	640.1	626.2	611.4	595.9	580.8	567.1	555.0	544.7	532.4	519.9	511.2
10°	668.9	648.6	627.7	606.3	586.8	568.5	554.3	540.5	525.6	511.3	500.4
12.5°	695.1	668.4	644.3	617.9	593.0	571.1	550.8	534.4	516.5	501.3	489.0
15°	728.2	700.8	671.8	631.7	598.5	570.8	546.0	524.6	503.0	484.2	472.2
17.5°	759.1	718.1	678.8	645.5	602.4	567.7	537.6	512.0	488.2	468.3	453.4
20°	771.9	732.2	689.6	647.0	604.7	565.8	530.8	502.5	477.9	455.2	441.6
22.5°	779.6	734.7	689.7	644.0	599.1	558.7	524.0	492.9	466.2	444.7	427.9
25°	788.6	735.0	685.6	640.5	594.5	550.8	509.6	476.7	447.8	425.0	407.1
27.5°	794.6	731.4	673.1	622.9	576.3	532.8	495.0	460.1	430.7	406.6	387.4
30°	795.7	728.6	663.5	609.2	561.9	521.8	481.8	448.5	417.4	391.7	373.9
32.5°	797.2	721.6	650.5	592.8	544.3	504.7	468.5	436.6	404.8	379.5	361.2
35°	791.0	717.8	630.8	564.4	515.9	477.6	444.9	415.5	384.3	359.7	341.1
37.5°	764.3	702.6	610.4	532.5	481.8	446.4	419.7	394.0	365.4	338.9	321.4
40°	737.4	687.5	594.5	513.1	460.2	423.7	399.7	378.8	351.0	326.3	307.5
42.5°	697.3	666.9	579.5	492.8	435.8	400.6	380.3	360.7	336.4	311.2	293.6
45°	623.7	627.7	548.7	460.4	401.8	366.6	347.5	333.9	312.3	291.5	273.4
47.5°	531.5	568.9	512.5	426.0	366.2	333.1	316.4	304.5	289.8	269.5	253.0
50°	471.3	524.6	483.5	402.8	343.8	310.8	294.4	284.7	272.0	256.0	240.2
52.5°	415.8	473.1	448.5	377.0	319.4	289.3	273.3	265.3	255.2	240.1	225.9
55°	339.0	397.2	391.5	338.1	283.1	256.0	243.8	234.8	228.0	216.7	205.4
57.5°	274.3	329.3	332.2	294.8	251.0	224.2	213.7	206.9	202.5	194.0	183.5
60°	233.4	284.0	293.9	265.6	228.0	204.5	194.1	188.6	185.2	178.3	170.4
62.5°	199.5	242.6	253.8	233.5	206.0	183.9	175.8	170.7	168.2	162.4	155.3
65°	152.7	188.4	199.2	188.0	173.6	156.0	149.4	144.9	142.8	139.6	134.3
67.5°	114.8	140.9	152.8	144.8	139.6	128.5	124.3	121.9	120.0	117.8	113.4
70°	92.2	111.5	123.7	121.7	117.4	111.5	108.5	106.8	104.9	103.0	99.3
72.5°	74.1	87.5	98.9	100.0	96.5	95.3	92.6	91.9	90.8	88.6	86.4
75°	49.2	58.4	66.3	69.4	70.8	72.0	70.8	70.6	70.4	68.5	67.3
77.5°	32.2	37.2	42.2	47.5	49.7	51.2	51.6	52.5	51.8	50.9	50.3
80°	24.7	25.9	29.4	33.8	37.4	38.8	39.8	40.2	40.0	39.8	38.8
82.5°	18.0	18.9	20.6	23.7	26.7	29.0	29.6	29.5	30.0	30.2	29.4
85°	9.7	9.9	10.4	10.8	12.4	15.0	15.8	16.3	16.7	16.7	15.2
87.5°	5.2	4.6	4.7	4.4	4.8	4.6	5.6	6.3	6.7	6.2	6.5
90°	10.9	9.2	7.5	6.4	5.2	3.4	2.3	1.1	2.3	3.4	5.2
92.5°	73.1	48.4	33.3	24.7	19.9	15.5	10.6	7.2	10.6	15.5	19.9
95°	209.6	123.8	74.8	52.4	37.5	27.7	21.3	19.6	21.3	27.7	37.5
97.5°	230.0	133.3	86.5	62.2	47.5	39.0	34.0	33.4	34.0	39.0	47.5
100°	217.1	131.9	91.6	69.1	55.3	47.3	43.2	42.6	43.2	47.3	55.3
102.5°	206.1	133.7	97.6	77.0	64.5	57.0	53.3	52.3	53.3	57.0	64.5
105°	198.1	138.9	107.8	89.9	78.9	72.0	68.6	66.9	68.6	72.0	78.9
107.5°	197.5	148.2	121.0	104.4	94.1	87.4	84.0	82.2	84.0	87.4	94.1
110°	199.9	156.1	130.2	114.0	104.2	98.0	95.0	93.3	95.0	98.0	104.2





TEST NUMBER: P332248-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	204.5	163.9	139.9	124.2	114.4	108.1	105.2	103.4	105.2	108.1	114.4
115°	212.0	176.8	154.9	139.4	129.6	123.8	120.4	118.1	120.4	123.8	129.6
117.5°	221.9	190.6	168.8	154.5	143.5	138.3	135.3	132.7	135.3	138.3	143.5
120°	229.2	199.2	178.5	164.2	153.2	147.4	144.6	142.9	144.6	147.4	153.2
122.5°	236.2	208.5	188.2	172.9	162.4	156.2	153.3	151.6	153.3	156.2	162.4
125°	247.1	221.8	201.6	186.0	175.1	168.7	165.3	164.2	165.3	168.7	175.1
127.5°	256.1	233.3	213.8	198.2	186.1	179.8	175.4	173.7	175.4	179.8	186.1
130°	262.1	240.1	221.2	205.6	193.5	186.6	181.5	179.8	181.5	186.6	193.5
132.5°	267.6	246.2	227.6	212.6	200.5	192.2	186.5	184.3	186.5	192.2	200.5
135°	274.8	255.2	237.3	221.8	209.6	201.1	194.7	192.4	194.7	201.1	209.6
137.5°	280.0	261.4	244.2	229.8	217.8	208.6	202.4	200.0	202.4	208.6	217.8
140°	282.9	265.5	248.8	234.4	222.9	213.7	207.9	205.1	207.9	213.7	222.9
142.5°	285.6	268.7	252.6	239.0	227.5	219.2	213.0	210.6	213.0	219.2	227.5
145°	288.6	273.1	258.0	244.8	235.0	226.4	221.2	219.4	221.2	226.4	235.0
147.5°	290.4	276.5	262.8	251.5	242.1	234.6	229.4	228.4	229.4	234.6	242.1
150°	290.8	278.8	265.5	255.2	247.1	239.6	235.0	234.4	235.0	239.6	247.1
152.5°	291.9	280.1	268.7	258.8	251.8	245.2	240.5	240.4	240.5	245.2	251.8
155°	292.1	282.9	273.1	265.0	258.6	252.9	249.4	249.4	249.4	252.9	258.6
157.5°	292.7	284.3	276.5	270.2	264.9	259.7	257.0	256.5	257.0	259.7	264.9
160°	292.7	285.7	278.8	273.1	269.0	264.4	262.1	262.1	262.1	264.4	269.0
162.5°	292.2	286.2	280.1	275.3	271.8	268.1	266.2	266.2	266.2	268.1	271.8
165°	290.8	286.8	282.3	278.2	275.9	273.1	271.9	272.5	271.9	273.1	275.9
167.5°	289.9	286.7	283.4	280.8	279.2	277.0	276.5	277.2	276.5	277.0	279.2
170°	288.6	286.3	283.4	282.3	281.0	279.3	278.8	279.9	278.8	279.3	281.0
172.5°	288.1	286.3	283.9	283.2	282.5	281.2	281.0	281.8	281.0	281.2	282.5
175°	286.8	285.7	284.6	284.0	284.0	282.9	283.4	284.0	283.4	282.9	284.0
177.5°	285.9	285.0	284.6	284.6	284.6	284.1	284.6	285.0	284.6	284.1	284.6
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P332248-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	540.2	537.8	536.0	532.3	529.9	527.3	524.6	526.2	526.0	525.9	525.9
5°	522.1	516.6	511.7	505.3	501.4	496.4	492.7	492.2	493.1	489.9	488.0
7.5°	504.1	496.8	489.7	482.7	475.2	469.3	465.6	463.8	461.5	459.5	457.4
10°	491.5	482.8	475.9	467.3	459.3	452.2	447.8	444.6	443.0	441.4	438.3
12.5°	478.5	470.0	461.3	451.4	443.8	435.7	432.3	428.9	425.8	423.8	419.7
15°	459.5	448.5	439.3	428.9	420.4	412.4	407.8	400.9	400.0	397.6	393.3
17.5°	440.4	428.5	415.8	408.1	398.6	390.2	383.0	380.8	374.1	371.5	367.8
20°	425.4	414.3	404.7	394.6	380.7	372.9	367.3	364.3	358.8	355.5	353.1
22.5°	412.4	401.1	390.0	378.2	366.8	358.0	353.9	349.1	346.2	341.5	339.0
25°	393.8	381.6	368.2	355.5	347.3	340.7	334.1	329.8	325.6	323.5	318.8
27.5°	372.3	359.5	347.0	337.3	327.2	320.7	314.8	311.0	305.9	302.4	299.7
30°	360.4	345.4	334.6	325.9	313.0	306.8	302.4	297.6	293.9	290.1	287.5
32.5°	346.7	333.0	322.8	311.9	302.1	295.3	289.5	285.4	282.2	278.6	276.0
35°	325.2	313.7	303.1	292.3	284.9	278.1	271.2	267.7	264.7	261.4	259.0
37.5°	305.7	294.9	284.8	274.6	265.5	259.9	254.5	251.8	247.6	245.4	243.1
40°	293.7	283.1	272.3	262.4	253.0	248.7	243.8	239.7	236.0	234.3	231.8
42.5°	280.4	269.8	260.7	250.1	242.4	236.6	232.1	227.7	224.9	222.5	221.1
45°	260.9	251.6	242.6	232.0	224.7	219.7	214.6	210.6	208.0	206.3	203.8
47.5°	242.0	232.6	223.5	214.3	207.2	201.6	196.3	193.6	190.2	188.1	186.4
50°	228.2	219.7	210.2	201.7	194.6	188.9	184.7	181.2	178.1	175.5	174.3
52.5°	215.6	206.6	198.2	190.4	182.9	176.5	172.7	169.0	166.6	163.7	162.3
55°	194.8	186.1	179.0	171.3	164.0	158.5	153.9	150.6	148.2	144.9	143.1
57.5°	175.3	167.4	159.1	152.3	144.8	140.3	136.3	131.9	129.0	126.4	124.5
60°	162.1	153.2	145.8	139.6	132.9	127.0	123.5	120.0	116.9	114.3	112.7
62.5°	148.3	140.6	133.6	126.7	120.7	115.5	111.5	108.6	105.8	104.2	102.5
65°	127.2	121.2	114.1	108.5	102.8	99.1	95.7	93.2	91.3	90.1	88.7
67.5°	107.9	102.0	95.8	90.3	86.4	83.6	81.5	79.3	78.3	76.7	75.8
70°	95.3	89.2	83.7	79.5	75.7	73.6	72.2	70.6	69.7	67.8	66.9
72.5°	81.6	77.2	73.2	69.8	66.8	64.8	63.0	61.0	59.5	57.4	56.5
75°	64.2	60.2	57.2	54.8	52.9	50.4	47.8	45.6	44.9	44.2	44.0
77.5°	47.6	45.0	42.8	40.8	38.5	36.7	36.1	35.5	35.4	35.0	35.0
80°	37.4	35.0	33.4	31.1	29.7	29.7	29.7	29.2	29.4	29.4	29.4
82.5°	27.8	25.7	24.7	23.9	23.6	23.8	23.8	23.9	23.7	24.1	23.9
85°	14.3	14.5	15.0	14.8	15.0	15.0	15.6	15.2	15.6	15.0	15.6
87.5°	6.6	7.4	7.9	8.4	8.9	9.1	9.2	9.3	9.6	9.7	9.9
90°	6.4	7.5	9.2	10.9	12.6	14.4	13.8	14.4	14.9	15.6	16.7
92.5°	24.7	33.3	48.4	73.1	97.5	88.6	66.9	48.5	38.5	34.0	31.0
95°	52.4	74.8	123.8	209.6	304.2	341.5	277.0	207.3	140.6	110.0	89.3
97.5°	62.2	86.5	133.3	230.0	387.5	529.4	566.3	516.9	414.0	339.7	270.8
100°	69.1	91.6	131.9	217.1	368.6	545.4	658.9	679.1	632.5	565.0	483.2
102.5°	77.0	97.6	133.7	206.1	341.0	515.5	663.6	733.1	731.5	692.3	640.4
105°	89.9	107.8	138.9	198.1	307.0	463.1	628.4	748.8	806.4	817.4	802.3
107.5°	104.4	121.0	148.2	197.5	285.4	416.8	566.9	703.4	797.0	847.4	867.9
110°	114.0	130.2	156.1	199.9	277.0	390.5	528.2	660.0	766.1	838.7	879.0



TEST NUMBER: P332248-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	124.2	139.9	163.9	204.5	272.5	373.0	494.5	617.2	725.5	806.9	858.7
115°	139.4	154.9	176.8	212.0	270.7	354.3	453.9	560.5	660.7	745.4	808.1
117.5°	154.5	168.8	190.6	221.9	271.8	343.2	429.4	519.3	605.8	681.9	745.6
120°	164.2	178.5	199.2	229.2	273.6	338.1	416.5	497.7	575.4	644.5	702.8
122.5°	172.9	188.2	208.5	236.2	276.8	334.9	405.9	480.6	551.0	615.0	669.0
125°	186.0	201.6	221.8	247.1	281.7	330.6	392.2	457.9	520.7	576.0	622.1
127.5°	198.2	213.8	233.3	256.1	287.2	328.5	380.3	438.1	494.1	544.0	585.9
130°	205.6	221.2	240.1	262.1	290.8	327.2	373.9	425.7	477.5	524.1	563.3
132.5°	212.6	227.6	246.2	267.6	293.7	326.7	367.8	414.1	461.8	505.2	542.6
135°	221.8	237.3	255.2	274.8	297.8	326.0	360.0	398.6	439.5	477.0	509.8
137.5°	229.8	244.2	261.4	280.0	300.5	324.8	353.3	384.5	418.0	450.2	478.7
140°	234.4	248.8	265.5	282.9	302.4	324.3	349.0	376.2	405.5	433.1	457.9
142.5°	239.0	252.6	268.7	285.6	303.8	323.4	345.4	368.3	393.5	417.5	439.0
145°	244.8	258.0	273.1	288.6	304.7	321.9	340.4	358.8	377.9	396.3	413.0
147.5°	251.5	262.8	276.5	290.4	304.7	319.8	335.6	351.1	366.2	381.1	392.9
150°	255.2	265.5	278.8	290.8	304.7	317.9	332.3	345.6	358.8	370.9	381.9
152.5°	258.8	268.7	280.1	291.9	303.4	315.7	328.7	340.5	351.9	362.6	371.7
155°	265.0	273.1	282.9	292.1	301.8	311.6	323.2	333.0	342.1	350.8	357.7
157.5°	270.2	276.5	284.3	292.7	299.8	308.0	316.9	324.9	332.5	339.3	344.7
160°	273.1	278.8	285.7	292.7	298.9	305.3	312.8	320.2	326.6	332.3	336.4
162.5°	275.3	280.1	286.2	292.2	297.1	302.6	308.6	314.8	320.1	325.5	329.0
165°	278.2	282.3	286.8	290.8	294.4	298.4	303.0	307.6	311.0	315.1	317.9
167.5°	280.8	283.4	286.7	289.9	291.5	294.2	297.6	301.3	304.0	306.3	308.4
170°	282.3	283.4	286.3	288.6	289.7	291.4	294.4	297.2	298.9	301.2	302.4
172.5°	283.2	283.9	286.3	288.1	288.3	289.1	291.1	293.6	294.8	296.6	297.3
175°	284.0	284.6	285.7	286.8	286.3	286.3	287.4	288.6	289.1	290.3	290.3
177.5°	284.6	284.6	285.0	285.9	285.0	284.6	285.0	285.5	285.9	286.4	286.4
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P332248-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	523.6	523.4	523.6	522.9	523.6	523.4	523.6	525.9	525.9	526.0	526.2
5°	487.3	487.1	486.4	484.2	486.4	487.1	487.3	488.0	489.9	493.1	492.2
7.5°	455.4	455.1	453.1	453.1	453.1	455.1	455.4	457.4	459.5	461.5	463.8
10°	436.7	436.9	434.0	432.4	434.0	436.9	436.7	438.3	441.4	443.0	444.6
12.5°	418.4	417.4	415.1	413.2	415.1	417.4	418.4	419.7	423.8	425.8	428.9
15°	394.4	391.9	386.4	386.8	386.4	391.9	394.4	393.3	397.6	400.0	400.9
17.5°	366.0	364.3	364.2	360.8	364.2	364.3	366.0	367.8	371.5	374.1	380.8
20°	349.4	348.2	348.7	345.4	348.7	348.2	349.4	353.1	355.5	358.8	364.3
22.5°	336.4	335.2	333.3	332.2	333.3	335.2	336.4	339.0	341.5	346.2	349.1
25°	317.4	315.5	313.7	314.8	313.7	315.5	317.4	318.8	323.5	325.6	329.8
27.5°	298.4	297.0	295.1	294.9	295.1	297.0	298.4	299.7	302.4	305.9	311.0
30°	286.3	284.9	284.0	282.8	284.0	284.9	286.3	287.5	290.1	293.9	297.6
32.5°	274.1	273.8	272.2	271.9	272.2	273.8	274.1	276.0	278.6	282.2	285.4
35°	258.1	256.7	256.2	256.4	256.2	256.7	258.1	259.0	261.4	264.7	267.7
37.5°	242.9	241.1	240.1	239.3	240.1	241.1	242.9	243.1	245.4	247.6	251.8
40°	232.0	230.1	229.6	229.1	229.6	230.1	232.0	231.8	234.3	236.0	239.7
42.5°	219.7	219.0	218.7	217.8	218.7	219.0	219.7	221.1	222.5	224.9	227.7
45°	203.1	202.8	201.4	201.9	201.4	202.8	203.1	203.8	206.3	208.0	210.6
47.5°	185.4	184.4	183.4	184.1	183.4	184.4	185.4	186.4	188.1	190.2	193.6
50°	173.4	172.9	170.8	171.3	170.8	172.9	173.4	174.3	175.5	178.1	181.2
52.5°	161.4	159.6	158.8	158.4	158.8	159.6	161.4	162.3	163.7	166.6	169.0
55°	141.4	139.3	138.4	137.8	138.4	139.3	141.4	143.1	144.9	148.2	150.6
57.5°	121.8	121.3	120.5	121.0	120.5	121.3	121.8	124.5	126.4	129.0	131.9
60°	110.4	110.4	110.4	110.1	110.4	110.4	110.4	112.7	114.3	116.9	120.0
62.5°	101.5	100.9	100.8	101.1	100.8	100.9	101.5	102.5	104.2	105.8	108.6
65°	88.0	87.8	86.8	86.5	86.8	87.8	88.0	88.7	90.1	91.3	93.2
67.5°	75.2	74.4	74.1	73.8	74.1	74.4	75.2	75.8	76.7	78.3	79.3
70°	65.6	65.1	63.7	64.0	63.7	65.1	65.6	66.9	67.8	69.7	70.6
72.5°	55.3	54.8	54.5	54.2	54.5	54.8	55.3	56.5	57.4	59.5	61.0
75°	43.7	43.5	43.3	44.2	43.3	43.5	43.7	44.0	44.2	44.9	45.6
77.5°	35.0	35.0	35.2	34.8	35.2	35.0	35.0	35.0	35.0	35.4	35.5
80°	29.4	29.4	29.2	29.2	29.2	29.4	29.4	29.4	29.4	29.4	29.2
82.5°	23.5	23.7	23.9	23.5	23.9	23.7	23.5	23.9	24.1	23.7	23.9
85°	15.6	15.2	15.8	15.6	15.8	15.2	15.6	15.6	15.0	15.6	15.2
87.5°	10.2	9.9	10.0	10.1	10.0	9.9	10.2	9.9	9.7	9.6	9.3
90°	16.2	16.7	17.3	16.7	17.3	16.7	16.2	16.7	15.6	14.9	14.4
92.5°	30.0	28.2	28.8	27.8	28.8	28.2	30.0	31.0	34.0	38.5	48.5
95°	78.4	73.1	69.1	66.9	69.1	73.1	78.4	89.3	110.0	140.6	207.3
97.5°	228.3	202.4	186.8	181.9	186.8	202.4	228.3	270.8	339.7	414.0	516.9
100°	425.1	383.0	360.6	361.1	360.6	383.0	425.1	483.2	565.0	632.5	679.1
102.5°	595.1	561.8	543.0	529.8	543.0	561.8	595.1	640.4	692.3	731.5	733.1
105°	775.9	754.0	735.6	732.7	735.6	754.0	775.9	802.3	817.4	806.4	748.8
107.5°	868.4	861.0	854.7	849.5	854.7	861.0	868.4	867.9	847.4	797.0	703.4
110°	895.1	899.7	898.6	897.4	898.6	899.7	895.1	879.0	838.7	766.1	660.0



TEST NUMBER: P332248-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	888.2	902.5	906.9	907.1	906.9	902.5	888.2	858.7	806.9	725.5	617.2
115°	851.3	876.7	888.2	891.1	888.2	876.7	851.3	808.1	745.4	660.7	560.5
117.5°	790.6	819.6	836.3	840.1	836.3	819.6	790.6	745.6	681.9	605.8	519.3
120°	748.2	780.5	794.3	797.8	794.3	780.5	748.2	702.8	644.5	575.4	497.7
122.5°	709.5	738.5	753.8	758.1	753.8	738.5	709.5	669.0	615.0	551.0	480.6
125°	658.9	684.3	698.7	702.8	698.7	684.3	658.9	622.1	576.0	520.7	457.9
127.5°	618.7	640.4	653.4	657.1	653.4	640.4	618.7	585.9	544.0	494.1	438.1
130°	593.9	614.6	626.7	631.3	626.7	614.6	593.9	563.3	524.1	477.5	425.7
132.5°	571.3	592.0	602.7	605.9	602.7	592.0	571.3	542.6	505.2	461.8	414.1
135°	538.0	555.2	565.6	569.7	565.6	555.2	538.0	509.8	477.0	439.5	398.6
137.5°	502.4	519.9	528.7	531.3	528.7	519.9	502.4	478.7	450.2	418.0	384.5
140°	479.8	495.9	505.1	504.5	505.1	495.9	479.8	457.9	433.1	405.5	376.2
142.5°	457.7	472.0	480.3	479.7	480.3	472.0	457.7	439.0	417.5	393.5	368.3
145°	427.4	439.5	444.1	445.2	444.1	439.5	427.4	413.0	396.3	377.9	358.8
147.5°	403.8	412.0	416.5	416.9	416.5	412.0	403.8	392.9	381.1	366.2	351.1
150°	390.5	396.9	400.3	400.3	400.3	396.9	390.5	381.9	370.9	358.8	345.6
152.5°	378.5	384.5	386.5	386.5	386.5	384.5	378.5	371.7	362.6	351.9	340.5
155°	362.8	367.5	368.6	369.2	368.6	367.5	362.8	357.7	350.8	342.1	333.0
157.5°	349.2	352.6	353.6	353.5	353.6	352.6	349.2	344.7	339.3	332.5	324.9
160°	340.4	343.9	343.9	343.3	343.9	343.9	340.4	336.4	332.3	326.6	320.2
162.5°	331.6	334.7	334.7	334.1	334.7	334.7	331.6	329.0	325.5	320.1	314.8
165°	320.2	322.6	321.9	321.9	321.9	322.6	320.2	317.9	315.1	311.0	307.6
167.5°	309.4	311.0	310.4	310.4	310.4	311.0	309.4	308.4	306.3	304.0	301.3
170°	303.0	304.2	303.6	303.6	303.6	304.2	303.0	302.4	301.2	298.9	297.2
172.5°	297.4	298.6	297.6	297.1	297.6	298.6	297.4	297.3	296.6	294.8	293.6
175°	290.3	290.8	290.3	289.7	290.3	290.8	290.3	290.3	290.3	289.1	288.6
177.5°	285.9	286.4	285.5	285.5	285.5	286.4	285.9	286.4	286.4	285.9	285.5
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P332248-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	524.6	527.3	529.9	532.3	536.0	537.8	540.2	541.2	543.9	548.1	551.5
5°	492.7	496.4	501.4	505.3	511.7	516.6	522.1	527.3	533.4	542.1	549.9
7.5°	465.6	469.3	475.2	482.7	489.7	496.8	504.1	511.2	519.9	532.4	544.7
10°	447.8	452.2	459.3	467.3	475.9	482.8	491.5	500.4	511.3	525.6	540.5
12.5°	432.3	435.7	443.8	451.4	461.3	470.0	478.5	489.0	501.3	516.5	534.4
15°	407.8	412.4	420.4	428.9	439.3	448.5	459.5	472.2	484.2	503.0	524.6
17.5°	383.0	390.2	398.6	408.1	415.8	428.5	440.4	453.4	468.3	488.2	512.0
20°	367.3	372.9	380.7	394.6	404.7	414.3	425.4	441.6	455.2	477.9	502.5
22.5°	353.9	358.0	366.8	378.2	390.0	401.1	412.4	427.9	444.7	466.2	492.9
25°	334.1	340.7	347.3	355.5	368.2	381.6	393.8	407.1	425.0	447.8	476.7
27.5°	314.8	320.7	327.2	337.3	347.0	359.5	372.3	387.4	406.6	430.7	460.1
30°	302.4	306.8	313.0	325.9	334.6	345.4	360.4	373.9	391.7	417.4	448.5
32.5°	289.5	295.3	302.1	311.9	322.8	333.0	346.7	361.2	379.5	404.8	436.6
35°	271.2	278.1	284.9	292.3	303.1	313.7	325.2	341.1	359.7	384.3	415.5
37.5°	254.5	259.9	265.5	274.6	284.8	294.9	305.7	321.4	338.9	365.4	394.0
40°	243.8	248.7	253.0	262.4	272.3	283.1	293.7	307.5	326.3	351.0	378.8
42.5°	232.1	236.6	242.4	250.1	260.7	269.8	280.4	293.6	311.2	336.4	360.7
45°	214.6	219.7	224.7	232.0	242.6	251.6	260.9	273.4	291.5	312.3	333.9
47.5°	196.3	201.6	207.2	214.3	223.5	232.6	242.0	253.0	269.5	289.8	304.5
50°	184.7	188.9	194.6	201.7	210.2	219.7	228.2	240.2	256.0	272.0	284.7
52.5°	172.7	176.5	182.9	190.4	198.2	206.6	215.6	225.9	240.1	255.2	265.3
55°	153.9	158.5	164.0	171.3	179.0	186.1	194.8	205.4	216.7	228.0	234.8
57.5°	136.3	140.3	144.8	152.3	159.1	167.4	175.3	183.5	194.0	202.5	206.9
60°	123.5	127.0	132.9	139.6	145.8	153.2	162.1	170.4	178.3	185.2	188.6
62.5°	111.5	115.5	120.7	126.7	133.6	140.6	148.3	155.3	162.4	168.2	170.7
65°	95.7	99.1	102.8	108.5	114.1	121.2	127.2	134.3	139.6	142.8	144.9
67.5°	81.5	83.6	86.4	90.3	95.8	102.0	107.9	113.4	117.8	120.0	121.9
70°	72.2	73.6	75.7	79.5	83.7	89.2	95.3	99.3	103.0	104.9	106.8
72.5°	63.0	64.8	66.8	69.8	73.2	77.2	81.6	86.4	88.6	90.8	91.9
75°	47.8	50.4	52.9	54.8	57.2	60.2	64.2	67.3	68.5	70.4	70.6
77.5°	36.1	36.7	38.5	40.8	42.8	45.0	47.6	50.3	50.9	51.8	52.5
80°	29.7	29.7	29.7	31.1	33.4	35.0	37.4	38.8	39.8	40.0	40.2
82.5°	23.8	23.8	23.6	23.9	24.7	25.7	27.8	29.4	30.2	30.0	29.5
85°	15.6	15.0	15.0	14.8	15.0	14.5	14.3	15.2	16.7	16.7	16.3
87.5°	9.2	9.1	8.9	8.4	7.9	7.4	6.6	6.5	6.2	6.7	6.3
90°	13.8	14.4	12.6	10.9	9.2	7.5	6.4	5.2	3.4	2.3	1.1
92.5°	66.9	88.6	97.5	73.1	48.4	33.3	24.7	19.9	15.5	10.6	7.2
95°	277.0	341.5	304.2	209.6	123.8	74.8	52.4	37.5	27.7	21.3	19.6
97.5°	566.3	529.4	387.5	230.0	133.3	86.5	62.2	47.5	39.0	34.0	33.4
100°	658.9	545.4	368.6	217.1	131.9	91.6	69.1	55.3	47.3	43.2	42.6
102.5°	663.6	515.5	341.0	206.1	133.7	97.6	77.0	64.5	57.0	53.3	52.3
105°	628.4	463.1	307.0	198.1	138.9	107.8	89.9	78.9	72.0	68.6	66.9
107.5°	566.9	416.8	285.4	197.5	148.2	121.0	104.4	94.1	87.4	84.0	82.2
110°	528.2	390.5	277.0	199.9	156.1	130.2	114.0	104.2	98.0	95.0	93.3



TEST NUMBER: P332248-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	494.5	373.0	272.5	204.5	163.9	139.9	124.2	114.4	108.1	105.2	103.4
115°	453.9	354.3	270.7	212.0	176.8	154.9	139.4	129.6	123.8	120.4	118.1
117.5°	429.4	343.2	271.8	221.9	190.6	168.8	154.5	143.5	138.3	135.3	132.7
120°	416.5	338.1	273.6	229.2	199.2	178.5	164.2	153.2	147.4	144.6	142.9
122.5°	405.9	334.9	276.8	236.2	208.5	188.2	172.9	162.4	156.2	153.3	151.6
125°	392.2	330.6	281.7	247.1	221.8	201.6	186.0	175.1	168.7	165.3	164.2
127.5°	380.3	328.5	287.2	256.1	233.3	213.8	198.2	186.1	179.8	175.4	173.7
130°	373.9	327.2	290.8	262.1	240.1	221.2	205.6	193.5	186.6	181.5	179.8
132.5°	367.8	326.7	293.7	267.6	246.2	227.6	212.6	200.5	192.2	186.5	184.3
135°	360.0	326.0	297.8	274.8	255.2	237.3	221.8	209.6	201.1	194.7	192.4
137.5°	353.3	324.8	300.5	280.0	261.4	244.2	229.8	217.8	208.6	202.4	200.0
140°	349.0	324.3	302.4	282.9	265.5	248.8	234.4	222.9	213.7	207.9	205.1
142.5°	345.4	323.4	303.8	285.6	268.7	252.6	239.0	227.5	219.2	213.0	210.6
145°	340.4	321.9	304.7	288.6	273.1	258.0	244.8	235.0	226.4	221.2	219.4
147.5°	335.6	319.8	304.7	290.4	276.5	262.8	251.5	242.1	234.6	229.4	228.4
150°	332.3	317.9	304.7	290.8	278.8	265.5	255.2	247.1	239.6	235.0	234.4
152.5°	328.7	315.7	303.4	291.9	280.1	268.7	258.8	251.8	245.2	240.5	240.4
155°	323.2	311.6	301.8	292.1	282.9	273.1	265.0	258.6	252.9	249.4	249.4
157.5°	316.9	308.0	299.8	292.7	284.3	276.5	270.2	264.9	259.7	257.0	256.5
160°	312.8	305.3	298.9	292.7	285.7	278.8	273.1	269.0	264.4	262.1	262.1
162.5°	308.6	302.6	297.1	292.2	286.2	280.1	275.3	271.8	268.1	266.2	266.2
165°	303.0	298.4	294.4	290.8	286.8	282.3	278.2	275.9	273.1	271.9	272.5
167.5°	297.6	294.2	291.5	289.9	286.7	283.4	280.8	279.2	277.0	276.5	277.2
170°	294.4	291.4	289.7	288.6	286.3	283.4	282.3	281.0	279.3	278.8	279.9
172.5°	291.1	289.1	288.3	288.1	286.3	283.9	283.2	282.5	281.2	281.0	281.8
175°	287.4	286.3	286.3	286.8	285.7	284.6	284.0	284.0	282.9	283.4	284.0
177.5°	285.0	284.6	285.0	285.9	285.0	284.6	284.6	284.6	284.1	284.6	285.0
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P332248-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	552.6	554.7	557.3	561.3	564.3	566.9	567.4	568.3	570.2	573.3	575.7
5°	556.2	561.6	570.3	578.8	587.9	595.5	602.6	607.5	612.2	622.1	630.1
7.5°	555.0	567.1	580.8	595.9	611.4	626.2	640.1	652.5	664.8	679.2	695.6
10°	554.3	568.5	586.8	606.3	627.7	648.6	668.9	684.7	703.0	719.5	740.4
12.5°	550.8	571.1	593.0	617.9	644.3	668.4	695.1	716.8	737.8	761.6	786.0
15°	546.0	570.8	598.5	631.7	671.8	700.8	728.2	766.1	791.9	817.8	852.6
17.5°	537.6	567.7	602.4	645.5	678.8	718.1	759.1	789.1	823.9	860.4	891.9
20°	530.8	565.8	604.7	647.0	689.6	732.2	771.9	807.7	843.7	885.9	911.7
22.5°	524.0	558.7	599.1	644.0	689.7	734.7	779.6	821.6	862.1	904.6	937.7
25°	509.6	550.8	594.5	640.5	685.6	735.0	788.6	835.5	885.6	929.4	960.7
27.5°	495.0	532.8	576.3	622.9	673.1	731.4	794.6	847.8	898.0	929.4	939.2
30°	481.8	521.8	561.9	609.2	663.5	728.6	795.7	856.7	897.8	911.5	901.3
32.5°	468.5	504.7	544.3	592.8	650.5	721.6	797.2	851.4	876.2	865.8	824.6
35°	444.9	477.6	515.9	564.4	630.8	717.8	791.0	827.7	821.6	762.8	685.1
37.5°	419.7	446.4	481.8	532.5	610.4	702.6	764.3	769.7	716.7	626.4	536.7
40°	399.7	423.7	460.2	513.1	594.5	687.5	737.4	715.5	633.4	532.9	458.1
42.5°	380.3	400.6	435.8	492.8	579.5	666.9	697.3	649.6	554.9	459.9	391.8
45°	347.5	366.6	401.8	460.4	548.7	627.7	623.7	540.9	446.1	369.6	313.2
47.5°	316.4	333.1	366.2	426.0	512.5	568.9	531.5	443.3	362.9	301.5	261.3
50°	294.4	310.8	343.8	402.8	483.5	524.6	471.3	386.4	312.7	261.9	229.8
52.5°	273.3	289.3	319.4	377.0	448.5	473.1	415.8	337.0	275.6	231.8	204.3
55°	243.8	256.0	283.1	338.1	391.5	397.2	339.0	273.2	222.6	192.0	173.2
57.5°	213.7	224.2	251.0	294.8	332.2	329.3	274.3	217.2	183.2	160.5	146.8
60°	194.1	204.5	228.0	265.6	293.9	284.0	233.4	187.5	158.3	141.7	130.8
62.5°	175.8	183.9	206.0	233.5	253.8	242.6	199.5	161.6	138.4	124.3	115.7
65°	149.4	156.0	173.6	188.0	199.2	188.4	152.7	126.3	109.7	99.8	93.9
67.5°	124.3	128.5	139.6	144.8	152.8	140.9	114.8	97.1	87.7	79.4	75.2
70°	108.5	111.5	117.4	121.7	123.7	111.5	92.2	79.3	71.3	65.4	62.8
72.5°	92.6	95.3	96.5	100.0	98.9	87.5	74.1	63.8	58.1	54.1	50.8
75°	70.8	72.0	70.8	69.4	66.3	58.4	49.2	44.0	39.8	37.9	36.7
77.5°	51.6	51.2	49.7	47.5	42.2	37.2	32.2	30.5	28.7	27.7	27.3
80°	39.8	38.8	37.4	33.8	29.4	25.9	24.7	23.5	22.8	21.6	21.4
82.5°	29.6	29.0	26.7	23.7	20.6	18.9	18.0	17.5	16.8	16.2	16.2
85°	15.8	15.0	12.4	10.8	10.4	9.9	9.7	9.7	8.7	8.5	8.5
87.5°	5.6	4.6	4.8	4.4	4.7	4.6	5.2	5.2	5.4	5.4	5.2
90°	2.3	3.4	5.2	6.4	7.5	9.2	10.9	12.6	14.4	13.8	14.4
92.5°	10.6	15.5	19.9	24.7	33.3	48.4	73.1	97.5	88.6	66.9	48.5
95°	21.3	27.7	37.5	52.4	74.8	123.8	209.6	304.2	341.5	277.0	207.3
97.5°	34.0	39.0	47.5	62.2	86.5	133.3	230.0	387.5	529.4	566.3	516.9
100°	43.2	47.3	55.3	69.1	91.6	131.9	217.1	368.6	545.4	658.9	679.1
102.5°	53.3	57.0	64.5	77.0	97.6	133.7	206.1	341.0	515.5	663.6	733.1
105°	68.6	72.0	78.9	89.9	107.8	138.9	198.1	307.0	463.1	628.4	748.8
107.5°	84.0	87.4	94.1	104.4	121.0	148.2	197.5	285.4	416.8	566.9	703.4
110°	95.0	98.0	104.2	114.0	130.2	156.1	199.9	277.0	390.5	528.2	660.0





TEST NUMBER: P332248-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	105.2	108.1	114.4	124.2	139.9	163.9	204.5	272.5	373.0	494.5	617.2
115°	120.4	123.8	129.6	139.4	154.9	176.8	212.0	270.7	354.3	453.9	560.5
117.5°	135.3	138.3	143.5	154.5	168.8	190.6	221.9	271.8	343.2	429.4	519.3
120°	144.6	147.4	153.2	164.2	178.5	199.2	229.2	273.6	338.1	416.5	497.7
122.5°	153.3	156.2	162.4	172.9	188.2	208.5	236.2	276.8	334.9	405.9	480.6
125°	165.3	168.7	175.1	186.0	201.6	221.8	247.1	281.7	330.6	392.2	457.9
127.5°	175.4	179.8	186.1	198.2	213.8	233.3	256.1	287.2	328.5	380.3	438.1
130°	181.5	186.6	193.5	205.6	221.2	240.1	262.1	290.8	327.2	373.9	425.7
132.5°	186.5	192.2	200.5	212.6	227.6	246.2	267.6	293.7	326.7	367.8	414.1
135°	194.7	201.1	209.6	221.8	237.3	255.2	274.8	297.8	326.0	360.0	398.6
137.5°	202.4	208.6	217.8	229.8	244.2	261.4	280.0	300.5	324.8	353.3	384.5
140°	207.9	213.7	222.9	234.4	248.8	265.5	282.9	302.4	324.3	349.0	376.2
142.5°	213.0	219.2	227.5	239.0	252.6	268.7	285.6	303.8	323.4	345.4	368.3
145°	221.2	226.4	235.0	244.8	258.0	273.1	288.6	304.7	321.9	340.4	358.8
147.5°	229.4	234.6	242.1	251.5	262.8	276.5	290.4	304.7	319.8	335.6	351.1
150°	235.0	239.6	247.1	255.2	265.5	278.8	290.8	304.7	317.9	332.3	345.6
152.5°	240.5	245.2	251.8	258.8	268.7	280.1	291.9	303.4	315.7	328.7	340.5
155°	249.4	252.9	258.6	265.0	273.1	282.9	292.1	301.8	311.6	323.2	333.0
157.5°	257.0	259.7	264.9	270.2	276.5	284.3	292.7	299.8	308.0	316.9	324.9
160°	262.1	264.4	269.0	273.1	278.8	285.7	292.7	298.9	305.3	312.8	320.2
162.5°	266.2	268.1	271.8	275.3	280.1	286.2	292.2	297.1	302.6	308.6	314.8
165°	271.9	273.1	275.9	278.2	282.3	286.8	290.8	294.4	298.4	303.0	307.6
167.5°	276.5	277.0	279.2	280.8	283.4	286.7	289.9	291.5	294.2	297.6	301.3
170°	278.8	279.3	281.0	282.3	283.4	286.3	288.6	289.7	291.4	294.4	297.2
172.5°	281.0	281.2	282.5	283.2	283.9	286.3	288.1	288.3	289.1	291.1	293.6
175°	283.4	282.9	284.0	284.0	284.6	285.7	286.8	286.3	286.3	287.4	288.6
177.5°	284.6	284.1	284.6	284.6	284.6	285.0	285.9	285.0	284.6	285.0	285.5
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P332248-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	579.8	579.8	580.5	583.3	583.7	586.1	585.4
5°	637.1	641.6	643.3	650.4	654.5	656.4	652.7
7.5°	707.3	719.9	725.9	733.4	739.8	741.8	736.7
10°	758.5	771.7	782.7	789.6	796.0	800.2	805.6
12.5°	808.0	824.3	834.8	844.3	850.9	856.3	857.2
15°	861.8	886.3	904.8	918.6	925.3	928.9	927.5
17.5°	916.0	938.8	952.0	965.9	975.3	975.8	976.1
20°	946.7	968.9	984.2	994.5	1005.1	1004.6	1007.0
22.5°	967.2	984.7	996.4	1003.9	1007.5	1005.7	1006.2
25°	976.8	982.1	980.0	968.0	964.8	953.8	955.7
27.5°	927.4	902.9	877.6	845.1	819.3	798.8	799.8
30°	860.2	816.9	767.5	726.1	688.9	678.5	656.4
32.5°	766.3	701.4	643.5	604.8	573.0	564.3	545.0
35°	607.0	543.9	484.4	448.7	434.5	414.8	414.5
37.5°	471.8	416.3	384.9	358.0	344.0	331.9	330.8
40°	396.9	353.7	329.8	310.5	296.7	287.7	285.6
42.5°	344.6	309.6	287.3	275.4	264.7	260.0	256.6
45°	281.3	257.8	242.4	231.6	226.6	223.1	221.2
47.5°	235.4	219.6	209.0	201.8	197.8	194.1	195.1
50°	210.4	197.4	189.7	182.8	179.8	177.1	177.4
52.5°	190.2	178.5	172.3	167.3	163.6	161.7	160.9
55°	161.4	154.1	147.7	144.2	142.1	139.6	138.9
57.5°	137.6	132.0	126.8	122.9	122.3	119.9	120.2
60°	121.9	117.1	112.9	110.8	109.2	107.0	107.8
62.5°	108.9	104.9	101.1	99.4	97.7	96.1	96.4
65°	89.2	85.4	83.0	82.1	81.4	80.7	80.0
67.5°	71.1	68.8	67.3	65.2	63.8	63.6	62.9
70°	59.8	56.7	54.1	51.5	50.8	50.6	50.8
72.5°	47.9	45.9	45.2	44.0	43.8	43.2	43.6
75°	36.0	35.2	34.8	33.8	33.8	33.8	33.8
77.5°	26.6	26.2	25.9	25.7	25.4	25.0	25.0
80°	20.7	20.5	20.0	20.0	19.8	20.0	19.8
82.5°	15.7	15.6	15.1	15.1	14.8	14.7	14.8
85°	8.0	7.8	8.3	7.8	8.0	7.6	8.0
87.5°	5.3	5.4	5.5	5.3	5.3	5.8	5.3
90°	14.9	15.6	16.7	16.2	16.7	17.3	16.7
92.5°	38.5	34.0	31.0	30.0	28.2	28.8	27.8
95°	140.6	110.0	89.3	78.4	73.1	69.1	66.9
97.5°	414.0	339.7	270.8	228.3	202.4	186.8	181.9
100°	632.5	565.0	483.2	425.1	383.0	360.6	361.1
102.5°	731.5	692.3	640.4	595.1	561.8	543.0	529.8
105°	806.4	817.4	802.3	775.9	754.0	735.6	732.7
107.5°	797.0	847.4	867.9	868.4	861.0	854.7	849.5
110°	766.1	838.7	879.0	895.1	899.7	898.6	897.4



TEST NUMBER: P332248-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	725.5	806.9	858.7	888.2	902.5	906.9	907.1
115°	660.7	745.4	808.1	851.3	876.7	888.2	891.1
117.5°	605.8	681.9	745.6	790.6	819.6	836.3	840.1
120°	575.4	644.5	702.8	748.2	780.5	794.3	797.8
122.5°	551.0	615.0	669.0	709.5	738.5	753.8	758.1
125°	520.7	576.0	622.1	658.9	684.3	698.7	702.8
127.5°	494.1	544.0	585.9	618.7	640.4	653.4	657.1
130°	477.5	524.1	563.3	593.9	614.6	626.7	631.3
132.5°	461.8	505.2	542.6	571.3	592.0	602.7	605.9
135°	439.5	477.0	509.8	538.0	555.2	565.6	569.7
137.5°	418.0	450.2	478.7	502.4	519.9	528.7	531.3
140°	405.5	433.1	457.9	479.8	495.9	505.1	504.5
142.5°	393.5	417.5	439.0	457.7	472.0	480.3	479.7
145°	377.9	396.3	413.0	427.4	439.5	444.1	445.2
147.5°	366.2	381.1	392.9	403.8	412.0	416.5	416.9
150°	358.8	370.9	381.9	390.5	396.9	400.3	400.3
152.5°	351.9	362.6	371.7	378.5	384.5	386.5	386.5
155°	342.1	350.8	357.7	362.8	367.5	368.6	369.2
157.5°	332.5	339.3	344.7	349.2	352.6	353.6	353.5
160°	326.6	332.3	336.4	340.4	343.9	343.9	343.3
162.5°	320.1	325.5	329.0	331.6	334.7	334.7	334.1
165°	311.0	315.1	317.9	320.2	322.6	321.9	321.9
167.5°	304.0	306.3	308.4	309.4	311.0	310.4	310.4
170°	298.9	301.2	302.4	303.0	304.2	303.6	303.6
172.5°	294.8	296.6	297.3	297.4	298.6	297.6	297.1
175°	289.1	290.3	290.3	290.3	290.8	290.3	289.7
177.5°	285.9	286.4	286.4	285.9	286.4	285.5	285.5
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6

(END OF REPORT)